

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332118-927

Luminaire Tested: **S123DIW-S340D1535U927-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332118-927
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-5,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123DIW-S340D1535U927-4F0-1E-UDD-F
Description: DEFINE 3 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 340 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 1535 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5982.7 lumens
Efficiency: N/A
Efficacy: 112.0 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 53.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332118-927

CATALOG NUMBER: S123DIW-S340D1535U927-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P332118-927

CATALOG NUMBER: S123DIW-S340D1535U927-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	100	100	100	100	88	88	88	88	66	66	66	46	46	46	27	27	27	19				
1	91	87	83	80	80	76	73	71	58	56	54	40	39	38	24	24	23	16				
2	83	76	70	65	73	67	62	58	50	47	44	35	33	32	21	20	19	13				
3	75	66	59	54	66	59	53	48	44	40	37	31	29	27	19	17	16	11				
4	69	58	51	45	60	52	46	41	39	35	32	28	25	23	17	15	14	10				
5	63	52	44	39	55	46	40	35	35	30	27	25	22	20	15	13	12	8				
6	58	46	39	33	51	41	35	30	31	27	23	22	19	17	14	12	11	7				
7	53	42	34	29	47	37	31	26	28	24	20	20	17	15	12	11	9	6				
8	49	38	30	25	43	33	27	23	26	21	18	18	15	13	11	10	8	6				
9	46	34	27	22	40	30	24	20	23	19	16	17	14	12	10	9	8	5				
10	43	31	24	20	37	28	22	18	21	17	14	15	12	10	10	8	7	5				

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	4621	4621	4621
5°	4643	4578	4611
10°	4611	4539	4568
15°	4558	4488	4496
20°	4495	4415	4418
25°	4410	4327	4318
30°	4318	4230	4197
35°	4221	4127	4075
40°	4118	4014	3953
45°	4007	3911	3815
50°	3893	3783	3677
55°	3748	3652	3539
60°	3599	3496	3384
65°	3469	3326	3224
70°	3276	3138	2996
75°	2994	2886	2766
80°	2703	2585	2566
85°	2371	2285	2186



TEST NUMBER: P332118-927

CATALOG NUMBER: S123DIW-S340D1535U927-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	40.4	0.7
10°-20°	114.2	1.9
20°-30°	168.7	2.8
30°-40°	197.0	3.3
40°-50°	198.1	3.3
50°-60°	174.0	2.9
60°-70°	129.6	2.2
70°-80°	73.8	1.2
80°-90°	25.7	0.4
90°-100°	58.0	1.0
100°-110°	276.2	4.6
110°-120°	663.5	11.1
120°-130°	844.9	14.1
130°-140°	902.7	15.1
140°-150°	844.1	14.1
150°-160°	680.9	11.4
160°-170°	439.5	7.3
170°-180°	151.5	2.5
0°-30°	323.3	5.4
0°-40°	520.3	8.7
0°-60°	892.4	14.9
0°-90°	1121.5	18.7
90°-120°	997.6	16.7
90°-150°	3589.3	60.0
90°-180°	4861.0	81.3
0°-180°	5982.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	429	429	429	429	429	
5°	430	428	424	427	427	41
15°	409	407	403	405	404	115
25°	371	369	364	365	364	171
35°	321	319	314	312	310	201
45°	263	262	257	253	251	203
55°	200	199	195	191	189	179
65°	136	134	131	128	127	134
75°	72	70	69	68	66	77
85°	19	18	18	18	18	21
90°	1	13	28	33	36	4
95°	72	27	37	44	45	89
105°	353	359	259	62	52	374
115°	662	669	680	691	696	653
125°	933	942	948	950	952	833
135°	1162	1169	1174	1177	1174	894
145°	1341	1349	1351	1354	1354	839
155°	1477	1475	1476	1481	1474	680
165°	1557	1554	1553	1561	1554	440
175°	1594	1588	1589	1597	1588	152
180°	1594	1594	1594	1594	1594	



TEST NUMBER: P332118-927

CATALOG NUMBER: S123DIW-S340D1535U927-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	429.3	429.3	429.3	429.3	429.3	429.3	429.3	429.3	429.3	429.3	429.3
2.5°	430.8	430.5	430.2	430.0	429.7	429.2	428.5	427.8	427.1	426.4	427.0
5°	429.7	429.2	428.8	428.4	428.0	427.4	426.4	425.6	424.6	423.7	424.5
7.5°	425.5	425.0	424.6	424.2	423.8	423.1	422.2	421.3	420.3	419.4	420.1
10°	421.9	421.5	421.0	420.6	420.3	419.5	418.4	417.4	416.3	415.3	416.0
12.5°	417.2	416.8	416.5	416.1	415.8	415.1	414.2	413.1	412.1	411.1	411.7
15°	409.0	408.7	408.3	408.0	407.7	406.9	405.9	404.8	403.8	402.7	403.4
17.5°	399.4	399.0	398.6	398.2	397.8	397.0	395.9	394.9	393.8	392.8	393.2
20°	392.4	391.9	391.4	390.9	390.4	389.6	388.6	387.5	386.4	385.4	385.7
22.5°	384.4	383.9	383.4	382.9	382.5	381.7	380.6	379.5	378.4	377.4	377.6
25°	371.3	370.8	370.3	369.9	369.4	368.6	367.5	366.5	365.4	364.3	364.4
27.5°	357.4	356.9	356.4	355.9	355.5	354.7	353.6	352.4	351.3	350.1	350.1
30°	347.4	346.9	346.5	346.1	345.7	344.9	343.8	342.6	341.5	340.3	340.3
32.5°	337.3	336.8	336.2	335.6	335.2	334.4	333.5	332.6	331.8	330.9	330.4
35°	321.2	320.7	320.1	319.6	319.2	318.4	317.3	316.2	315.2	314.1	313.6
37.5°	304.6	304.0	303.3	302.7	302.1	301.3	300.2	299.0	298.0	296.9	296.4
40°	293.1	292.6	292.1	291.6	291.1	290.3	289.1	288.0	286.8	285.7	285.0
42.5°	281.5	281.0	280.4	279.9	279.3	278.5	277.3	276.2	275.0	273.9	273.2
45°	263.2	262.8	262.5	262.2	261.9	261.2	260.1	259.0	257.9	256.9	256.0
47.5°	244.9	244.5	244.0	243.5	243.0	242.3	241.3	240.3	239.3	238.3	237.3
50°	232.5	232.1	231.7	231.3	230.9	230.1	229.1	228.1	227.0	225.9	225.0
52.5°	219.5	219.3	219.0	218.7	218.4	217.7	216.6	215.5	214.4	213.2	212.5
55°	199.7	199.6	199.6	199.5	199.4	198.8	197.7	196.6	195.6	194.6	193.6
57.5°	180.8	180.5	180.2	180.0	179.7	179.1	178.2	177.4	176.6	175.7	174.9
60°	167.2	167.2	167.1	167.0	166.9	166.4	165.3	164.4	163.4	162.4	161.7
62.5°	155.1	154.9	154.7	154.5	154.2	153.7	152.7	151.7	150.7	149.7	149.0
65°	136.2	135.8	135.4	135.0	134.6	134.0	133.2	132.3	131.5	130.6	130.0
67.5°	116.2	115.8	115.5	115.1	114.8	114.2	113.7	113.0	112.4	111.8	111.2
70°	104.1	103.6	103.1	102.6	102.1	101.6	101.2	100.6	100.1	99.7	99.1
72.5°	91.4	91.0	90.7	90.3	89.9	89.5	89.0	88.4	87.9	87.3	86.7
75°	72.0	71.6	71.3	71.0	70.7	70.3	70.1	69.9	69.6	69.4	69.0
77.5°	54.7	54.6	54.4	54.3	54.0	53.8	53.6	53.2	52.9	52.6	52.4
80°	43.6	43.3	43.1	42.9	42.5	42.4	42.2	42.1	41.9	41.7	41.6
82.5°	32.6	32.6	32.6	32.5	32.4	32.4	32.3	32.3	32.3	32.2	32.1
85°	19.2	19.0	18.9	18.7	18.5	18.5	18.5	18.5	18.5	18.5	18.3
87.5°	7.9	8.2	8.6	8.9	9.3	9.7	10.3	10.9	11.6	12.2	12.4
90°	1.2	3.8	6.4	9.1	11.7	14.7	18.1	21.5	25.0	28.4	29.5
92.5°	22.0	21.3	20.5	19.8	19.1	20.0	22.6	25.2	27.7	30.3	32.0
95°	72.2	61.5	50.7	39.8	29.1	25.1	28.0	30.9	33.8	36.7	38.6
97.5°	145.2	140.4	135.5	130.6	125.8	113.9	95.0	76.0	57.1	38.1	40.2
100°	200.2	205.4	210.6	215.9	221.2	203.3	162.2	121.2	80.2	39.1	41.2
102.5°	262.7	266.5	270.3	274.0	277.8	257.3	212.5	167.6	122.8	78.0	71.4
105°	352.9	355.8	358.7	361.6	364.5	354.1	330.4	306.7	283.0	259.4	212.8
107.5°	448.1	450.4	452.7	455.1	457.4	460.4	464.1	467.9	471.7	475.4	441.2
110°	511.6	513.7	515.8	517.9	520.1	522.5	525.5	528.3	531.2	534.1	525.5



TEST NUMBER: P332118-927

CATALOG NUMBER: S123DIW-S340D1535U927-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	572.3	574.2	576.1	578.0	579.8	582.3	585.1	588.0	590.9	593.8	594.0
115°	662.0	663.6	665.2	666.8	668.4	670.3	672.7	675.0	677.4	679.8	682.4
117.5°	748.9	750.9	752.8	754.8	756.8	758.4	759.5	760.7	761.9	763.2	765.2
120°	803.0	805.3	807.7	810.1	812.5	814.0	814.8	815.6	816.3	817.1	819.3
122.5°	857.9	859.8	861.8	863.7	865.7	867.2	868.2	869.2	870.1	871.2	872.7
125°	933.2	935.3	937.5	939.5	941.7	943.3	944.3	945.3	946.4	947.5	948.0
127.5°	1006.2	1008.3	1010.4	1012.5	1014.6	1016.3	1017.6	1018.8	1020.1	1021.4	1022.2
130°	1051.6	1053.8	1055.9	1058.0	1060.1	1061.7	1062.7	1063.7	1064.9	1065.9	1066.9
132.5°	1095.3	1097.3	1099.5	1101.5	1103.7	1105.2	1106.0	1106.8	1107.6	1108.5	1109.5
135°	1161.8	1163.4	1165.0	1166.6	1168.2	1169.4	1170.4	1171.6	1172.6	1173.6	1174.4
137.5°	1218.6	1220.7	1222.7	1224.6	1226.6	1228.0	1228.5	1229.1	1229.7	1230.3	1231.5
140°	1256.6	1258.1	1259.7	1261.3	1262.9	1264.0	1264.8	1265.6	1266.4	1267.2	1268.3
142.5°	1291.6	1293.2	1294.7	1296.3	1297.9	1299.1	1299.9	1300.7	1301.5	1302.3	1303.1
145°	1340.6	1342.4	1344.3	1346.2	1348.0	1349.2	1349.7	1350.2	1350.8	1351.3	1351.8
147.5°	1386.8	1388.1	1389.3	1390.4	1391.6	1392.5	1393.1	1393.6	1394.1	1394.6	1395.2
150°	1415.2	1416.0	1416.8	1417.6	1418.4	1419.0	1419.6	1420.1	1420.6	1421.2	1421.7
152.5°	1440.8	1441.2	1441.5	1441.9	1442.3	1442.6	1443.0	1443.3	1443.6	1443.9	1444.9
155°	1476.8	1476.3	1475.8	1475.3	1474.7	1474.6	1474.9	1475.1	1475.4	1475.6	1476.9
157.5°	1504.8	1504.8	1504.7	1504.6	1504.6	1504.4	1504.1	1503.9	1503.6	1503.3	1504.9
160°	1521.9	1521.5	1521.3	1521.1	1520.8	1520.5	1520.3	1520.0	1519.7	1519.5	1521.1
162.5°	1537.9	1537.2	1536.6	1535.9	1535.2	1534.7	1534.5	1534.2	1533.9	1533.7	1535.5
165°	1557.4	1556.6	1555.8	1555.0	1554.2	1553.7	1553.4	1553.2	1552.9	1552.6	1554.7
167.5°	1572.5	1571.5	1570.4	1569.4	1568.3	1567.8	1567.8	1567.8	1567.8	1567.8	1569.9
170°	1581.0	1580.0	1578.9	1577.9	1576.8	1576.3	1576.3	1576.3	1576.3	1576.3	1578.4
172.5°	1586.7	1585.5	1584.2	1582.9	1581.7	1581.1	1581.4	1581.6	1581.8	1582.0	1584.1
175°	1594.0	1592.8	1591.4	1590.1	1588.8	1588.2	1588.6	1588.8	1589.0	1589.4	1591.2
177.5°	1595.9	1594.9	1593.9	1592.8	1591.7	1591.3	1591.6	1591.7	1592.0	1592.2	1593.9
180°	1594.0	1594.0	1594.0	1594.0	1594.0	1594.0	1594.0	1594.0	1594.0	1594.0	1594.0



TEST NUMBER: P332118-927

CATALOG NUMBER: S123DIW-S340D1535U927-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	429.3	429.3	429.3	429.3	429.3	429.3	429.3	429.3
2.5°	427.6	428.3	429.0	429.3	429.2	429.1	429.0	429.0
5°	425.4	426.2	427.1	427.4	427.2	427.1	426.8	426.7
7.5°	420.9	421.6	422.3	422.6	422.6	422.5	422.4	422.2
10°	416.8	417.5	418.2	418.5	418.4	418.2	418.0	417.9
12.5°	412.2	412.7	413.3	413.5	413.4	413.3	413.2	413.1
15°	404.0	404.6	405.4	405.4	404.9	404.4	403.9	403.5
17.5°	393.6	394.1	394.6	394.7	394.5	394.3	394.2	394.0
20°	386.0	386.3	386.7	386.7	386.4	386.2	386.0	385.7
22.5°	377.9	378.2	378.4	378.4	378.1	377.8	377.5	377.2
25°	364.5	364.6	364.6	364.6	364.3	364.1	363.8	363.6
27.5°	350.2	350.3	350.3	350.2	349.9	349.6	349.3	349.0
30°	340.3	340.3	340.3	340.0	339.5	338.9	338.3	337.7
32.5°	329.9	329.5	329.1	328.7	328.4	328.0	327.7	327.4
35°	313.1	312.7	312.1	311.7	311.3	310.9	310.5	310.1
37.5°	295.7	295.2	294.5	294.1	293.9	293.6	293.3	293.1
40°	284.4	283.8	283.0	282.6	282.3	281.9	281.6	281.3
42.5°	272.6	271.9	271.2	270.8	270.5	270.1	269.8	269.4
45°	254.9	254.0	252.9	252.3	251.8	251.4	251.0	250.6
47.5°	236.4	235.4	234.4	233.8	233.4	233.1	232.7	232.3
50°	224.1	223.2	222.3	221.6	221.1	220.6	220.1	219.6
52.5°	211.7	210.9	210.1	209.5	209.0	208.5	208.0	207.6
55°	192.7	191.8	190.9	190.3	189.9	189.4	189.0	188.6
57.5°	174.1	173.3	172.5	171.8	171.3	170.9	170.4	169.9
60°	161.0	160.2	159.5	158.9	158.4	158.0	157.6	157.2
62.5°	148.2	147.5	146.8	146.2	146.0	145.7	145.4	145.1
65°	129.4	128.7	128.0	127.6	127.4	127.1	126.8	126.6
67.5°	110.6	110.0	109.5	109.0	108.7	108.3	108.0	107.7
70°	98.5	97.9	97.4	96.9	96.5	96.1	95.6	95.2
72.5°	86.3	85.7	85.2	84.8	84.7	84.4	84.2	84.0
75°	68.6	68.1	67.7	67.4	67.2	66.9	66.7	66.5
77.5°	52.0	51.8	51.5	51.4	51.4	51.4	51.4	51.4
80°	41.5	41.4	41.4	41.4	41.4	41.4	41.4	41.4
82.5°	32.0	31.8	31.7	31.5	31.5	31.4	31.4	31.3
85°	18.1	18.0	17.8	17.7	17.7	17.7	17.7	17.7
87.5°	12.4	12.6	12.8	12.9	13.0	13.1	13.2	13.3
90°	30.5	31.6	32.6	33.4	34.0	34.5	35.0	35.5
92.5°	33.7	35.4	37.1	38.0	38.3	38.7	39.0	39.3
95°	40.4	42.2	44.0	45.0	45.0	45.0	45.0	45.0
97.5°	42.4	44.4	46.6	47.8	48.0	48.2	48.6	48.8
100°	43.3	45.4	47.5	48.7	49.0	49.2	49.5	49.7
102.5°	64.9	58.4	51.8	48.8	49.3	49.7	50.2	50.7
105°	166.2	119.6	73.0	50.0	50.5	51.1	51.6	52.1
107.5°	407.0	372.9	338.7	304.1	269.0	233.9	198.8	163.7
110°	516.7	508.0	499.4	476.2	438.6	400.9	363.3	325.7



TEST NUMBER: P332118-927

CATALOG NUMBER: S123DIW-S340D1535U927-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	594.1	594.3	594.5	590.6	582.6	574.6	566.7	558.7
115°	685.1	687.7	690.3	692.1	693.2	694.3	695.3	696.4
117.5°	767.4	769.4	771.6	772.8	772.9	773.2	773.4	773.6
120°	821.4	823.5	825.6	826.6	826.6	826.6	826.6	826.6
122.5°	874.1	875.6	877.1	877.9	878.1	878.3	878.5	878.8
125°	948.5	949.0	949.5	950.1	950.6	951.1	951.6	952.2
127.5°	1023.0	1023.9	1024.7	1024.8	1024.4	1023.8	1023.3	1022.8
130°	1067.9	1069.1	1070.1	1070.3	1069.8	1069.3	1068.7	1068.3
132.5°	1110.6	1111.7	1112.7	1112.9	1112.1	1111.4	1110.6	1109.9
135°	1175.2	1176.0	1176.8	1176.8	1176.0	1175.2	1174.4	1173.6
137.5°	1232.8	1234.1	1235.3	1235.6	1235.2	1234.6	1234.1	1233.6
140°	1269.3	1270.3	1271.4	1271.7	1271.1	1270.7	1270.1	1269.6
142.5°	1303.9	1304.8	1305.6	1305.7	1305.0	1304.2	1303.5	1302.7
145°	1352.3	1352.9	1353.4	1353.7	1353.7	1353.7	1353.7	1353.7
147.5°	1395.7	1396.2	1396.8	1396.4	1395.2	1394.0	1392.7	1391.5
150°	1422.2	1422.8	1423.2	1423.2	1422.4	1421.6	1420.8	1420.0
152.5°	1445.8	1446.8	1447.7	1447.6	1446.4	1445.1	1443.9	1442.7
155°	1478.3	1479.6	1480.9	1480.7	1479.2	1477.6	1476.0	1474.5
157.5°	1506.5	1508.1	1509.7	1509.4	1507.4	1505.3	1503.2	1501.2
160°	1522.7	1524.2	1525.7	1525.7	1523.8	1521.9	1520.1	1518.3
162.5°	1537.2	1539.1	1540.8	1540.9	1539.3	1537.6	1536.0	1534.4
165°	1556.8	1558.9	1561.1	1561.2	1559.3	1557.5	1555.6	1553.8
167.5°	1572.0	1574.1	1576.2	1576.2	1574.1	1572.0	1569.9	1567.8
170°	1580.5	1582.6	1584.8	1584.8	1582.6	1580.5	1578.4	1576.3
172.5°	1586.2	1588.3	1590.4	1590.3	1588.0	1585.7	1583.3	1581.0
175°	1593.0	1594.8	1596.7	1596.6	1594.4	1592.4	1590.2	1588.2
177.5°	1595.5	1597.2	1598.9	1598.7	1596.6	1594.5	1592.4	1590.3
180°	1594.0	1594.0	1594.0	1594.0	1594.0	1594.0	1594.0	1594.0

(END OF REPORT)