

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332101-927

Luminaire Tested: **S123DIW-S340D755U927-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332101-927
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-9,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123DIW-S340D755U927-4F0-1E-UDD-F1
Description: DEFINE 3 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 340 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 755 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3193.1 lumens
Efficiency: N/A
Efficacy: 105.0 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 30.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332101-927

CATALOG NUMBER: S123DIW-S340D755U927-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P332101-927

CATALOG NUMBER: S123DIW-S340D755U927-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	104	104	104	104	94	94	94	94	75	75	75	58	58	58	42	42	42	35
1	94	90	86	83	85	82	78	75	66	63	61	51	49	48	37	36	36	29
2	86	79	73	68	77	71	66	62	57	54	51	45	42	40	33	31	30	25
3	78	69	62	56	70	63	57	52	51	46	43	39	36	34	29	27	25	21
4	72	61	53	47	64	55	49	44	45	40	36	35	32	29	26	24	22	18
5	66	54	46	40	59	49	42	37	40	35	31	31	28	25	23	21	19	15
6	60	49	41	35	54	44	37	32	36	31	27	28	25	22	21	19	17	14
7	56	44	36	31	50	40	33	28	33	27	24	26	22	19	19	17	15	12
8	52	40	32	27	47	36	30	25	30	25	21	23	20	17	18	15	13	11
9	48	36	29	24	43	33	27	22	27	22	19	22	18	15	16	14	12	10
10	45	33	26	21	40	30	24	20	25	20	17	20	16	14	15	13	11	9

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	4621	4621	4621
5°	4643	4578	4611
10°	4611	4539	4568
15°	4558	4488	4496
20°	4495	4415	4418
25°	4410	4327	4318
30°	4318	4230	4197
35°	4221	4127	4075
40°	4118	4014	3953
45°	4007	3911	3815
50°	3893	3783	3677
55°	3748	3652	3539
60°	3599	3496	3384
65°	3469	3326	3224
70°	3276	3138	2996
75°	2994	2886	2766
80°	2703	2585	2566
85°	2371	2285	2186



TEST NUMBER: P332101-927

CATALOG NUMBER: S123DIW-S340D755U927-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	40.4	1.3
10°-20°	114.2	3.6
20°-30°	168.7	5.3
30°-40°	197.0	6.2
40°-50°	198.1	6.2
50°-60°	174.0	5.4
60°-70°	129.6	4.1
70°-80°	73.8	2.3
80°-90°	23.4	0.7
90°-100°	48.8	1.5
100°-110°	145.9	4.6
110°-120°	248.2	7.8
120°-130°	326.5	10.2
130°-140°	367.0	11.5
140°-150°	360.7	11.3
150°-160°	303.7	9.5
160°-170°	202.2	6.3
170°-180°	70.8	2.2
0°-30°	323.3	10.1
0°-40°	520.3	16.3
0°-60°	892.4	27.9
0°-90°	1119.2	35.1
90°-120°	442.9	13.9
90°-150°	1497.2	46.9
90°-180°	2074.0	65.0
0°-180°	3193.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	429	429	429	429	429	
5°	430	428	424	427	427	41
15°	409	407	403	405	404	115
25°	371	369	364	365	364	171
35°	321	319	314	312	310	201
45°	263	262	257	253	251	203
55°	200	199	195	191	189	179
65°	136	134	131	128	127	134
75°	72	70	69	68	66	77
85°	19	18	18	18	18	21
90°	1	7	14	16	18	3
95°	35	39	44	46	46	39
105°	132	134	139	139	140	142
115°	250	251	250	251	250	247
125°	366	367	366	364	362	326
135°	474	478	477	475	474	366
145°	576	577	579	578	576	359
155°	659	659	660	662	658	303
165°	718	716	716	719	716	202
175°	747	745	744	748	744	71
180°	748	748	748	748	748	



TEST NUMBER: P332101-927

CATALOG NUMBER: S123DIW-S340D755U927-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	429.3	429.3	429.3	429.3	429.3	429.3	429.3	429.3	429.3	429.3	429.3
2.5°	430.8	430.5	430.2	430.0	429.7	429.2	428.5	427.8	427.1	426.4	427.0
5°	429.7	429.2	428.8	428.4	428.0	427.4	426.4	425.6	424.6	423.7	424.5
7.5°	425.5	425.0	424.6	424.2	423.8	423.1	422.2	421.3	420.3	419.4	420.1
10°	421.9	421.5	421.0	420.6	420.3	419.5	418.4	417.4	416.3	415.3	416.0
12.5°	417.2	416.8	416.5	416.1	415.8	415.1	414.2	413.1	412.1	411.1	411.7
15°	409.0	408.7	408.3	408.0	407.7	406.9	405.9	404.8	403.8	402.7	403.4
17.5°	399.4	399.0	398.6	398.2	397.8	397.0	395.9	394.9	393.8	392.8	393.2
20°	392.4	391.9	391.4	390.9	390.4	389.6	388.6	387.5	386.4	385.4	385.7
22.5°	384.4	383.9	383.4	382.9	382.5	381.7	380.6	379.5	378.4	377.4	377.6
25°	371.3	370.8	370.3	369.9	369.4	368.6	367.5	366.5	365.4	364.3	364.4
27.5°	357.4	356.9	356.4	355.9	355.5	354.7	353.6	352.4	351.3	350.1	350.1
30°	347.4	346.9	346.5	346.1	345.7	344.9	343.8	342.6	341.5	340.3	340.3
32.5°	337.3	336.8	336.2	335.6	335.2	334.4	333.5	332.6	331.8	330.9	330.4
35°	321.2	320.7	320.1	319.6	319.2	318.4	317.3	316.2	315.2	314.1	313.6
37.5°	304.6	304.0	303.3	302.7	302.1	301.3	300.2	299.0	298.0	296.9	296.4
40°	293.1	292.6	292.1	291.6	291.1	290.3	289.1	288.0	286.8	285.7	285.0
42.5°	281.5	281.0	280.4	279.9	279.3	278.5	277.3	276.2	275.0	273.9	273.2
45°	263.2	262.8	262.5	262.2	261.9	261.2	260.1	259.0	257.9	256.9	256.0
47.5°	244.9	244.5	244.0	243.5	243.0	242.3	241.3	240.3	239.3	238.3	237.3
50°	232.5	232.1	231.7	231.3	230.9	230.1	229.1	228.1	227.0	225.9	225.0
52.5°	219.5	219.3	219.0	218.7	218.4	217.7	216.6	215.5	214.4	213.2	212.5
55°	199.7	199.6	199.6	199.5	199.4	198.8	197.7	196.6	195.6	194.6	193.6
57.5°	180.8	180.5	180.2	180.0	179.7	179.1	178.2	177.4	176.6	175.7	174.9
60°	167.2	167.2	167.1	167.0	166.9	166.4	165.3	164.4	163.4	162.4	161.7
62.5°	155.1	154.9	154.7	154.5	154.2	153.7	152.7	151.7	150.7	149.7	149.0
65°	136.2	135.8	135.4	135.0	134.6	134.0	133.2	132.3	131.5	130.6	130.0
67.5°	116.2	115.8	115.5	115.1	114.8	114.2	113.7	113.0	112.4	111.8	111.2
70°	104.1	103.6	103.1	102.6	102.1	101.6	101.2	100.6	100.1	99.7	99.1
72.5°	91.4	91.0	90.7	90.3	89.9	89.5	89.0	88.4	87.9	87.3	86.7
75°	72.0	71.6	71.3	71.0	70.7	70.3	70.1	69.9	69.6	69.4	69.0
77.5°	54.7	54.6	54.4	54.3	54.0	53.8	53.6	53.2	52.9	52.6	52.4
80°	43.6	43.3	43.1	42.9	42.5	42.4	42.2	42.1	41.9	41.7	41.6
82.5°	32.6	32.6	32.6	32.5	32.4	32.4	32.3	32.3	32.3	32.2	32.1
85°	19.2	19.0	18.9	18.7	18.5	18.5	18.5	18.5	18.5	18.5	18.3
87.5°	7.8	7.8	7.9	8.0	8.1	8.2	8.5	8.8	9.0	9.3	9.3
90°	0.6	1.9	3.2	4.5	5.8	7.3	9.0	10.7	12.4	14.1	14.7
92.5°	14.3	15.1	16.0	16.9	17.7	18.7	19.6	20.7	21.6	22.6	23.0
95°	34.7	35.6	36.5	37.5	38.3	39.3	40.4	41.4	42.5	43.5	44.0
97.5°	61.6	62.3	63.0	63.7	64.3	65.0	65.8	66.5	67.3	68.1	68.7
100°	79.9	80.7	81.5	82.3	83.1	83.8	84.4	85.2	85.8	86.4	86.8
102.5°	101.2	101.6	102.1	102.5	103.0	103.7	104.6	105.4	106.2	107.1	107.5
105°	132.3	132.5	132.8	133.1	133.3	134.0	135.2	136.4	137.6	138.8	138.8
107.5°	168.5	168.7	168.8	169.0	169.1	169.4	169.9	170.4	170.9	171.3	171.7
110°	191.1	191.4	191.6	191.9	192.1	192.4	192.7	192.9	193.2	193.5	194.0



TEST NUMBER: P332101-927

CATALOG NUMBER: S123DIW-S340D755U927-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	214.6	214.8	214.9	215.1	215.2	215.3	215.4	215.5	215.5	215.6	216.2
115°	249.9	250.3	250.6	251.0	251.4	251.5	251.3	251.0	250.7	250.5	250.6
117.5°	285.4	285.7	285.9	286.2	286.5	286.5	286.1	285.7	285.4	285.0	285.0
120°	307.5	308.3	309.1	309.9	310.7	310.7	310.1	309.4	308.8	308.1	308.0
122.5°	330.6	331.1	331.7	332.3	332.9	333.0	332.6	332.3	332.0	331.6	331.3
125°	365.8	366.1	366.5	366.9	367.3	367.3	367.1	366.9	366.5	366.3	365.8
127.5°	398.2	399.0	399.9	400.7	401.6	401.8	401.6	401.2	400.9	400.7	399.9
130°	419.9	420.9	421.9	422.9	424.0	424.4	424.0	423.6	423.2	422.8	422.2
132.5°	441.5	442.5	443.5	444.6	445.7	446.0	445.8	445.4	445.1	444.9	444.3
135°	474.5	475.3	476.1	476.9	477.6	478.0	477.8	477.7	477.6	477.4	476.9
137.5°	505.1	505.7	506.4	507.1	507.7	508.2	508.5	508.9	509.2	509.5	509.0
140°	526.2	526.9	527.6	528.2	528.9	529.3	529.4	529.5	529.7	529.8	529.7
142.5°	545.6	546.2	546.8	547.5	548.1	548.6	548.8	549.1	549.3	549.5	549.4
145°	575.7	575.9	576.2	576.4	576.7	577.0	577.4	577.8	578.2	578.6	578.5
147.5°	602.0	602.5	602.9	603.4	603.9	604.3	604.7	605.0	605.4	605.8	605.8
150°	620.4	620.6	620.8	621.2	621.4	621.6	621.9	622.2	622.4	622.7	622.7
152.5°	635.4	635.7	636.1	636.5	636.8	637.1	637.2	637.4	637.5	637.7	637.9
155°	659.2	659.2	659.2	659.2	659.2	659.2	659.3	659.5	659.6	659.7	660.3
157.5°	679.4	679.2	679.1	678.9	678.7	678.7	678.8	678.9	679.1	679.1	679.7
160°	692.1	691.8	691.6	691.3	691.0	690.9	690.9	690.9	690.9	690.9	691.6
162.5°	703.4	703.0	702.6	702.3	701.9	701.8	701.9	702.0	702.1	702.2	702.8
165°	718.0	717.6	717.2	716.8	716.4	716.1	716.1	716.1	716.1	716.1	716.9
167.5°	729.6	729.0	728.6	728.0	727.5	727.3	727.4	727.5	727.6	727.7	728.5
170°	736.2	735.6	735.1	734.6	734.0	733.8	733.8	733.8	733.8	733.8	734.7
172.5°	741.3	740.8	740.3	739.7	739.3	738.9	738.9	738.9	738.9	738.9	739.8
175°	746.7	746.2	745.7	745.2	744.7	744.4	744.4	744.4	744.4	744.4	745.2
177.5°	749.0	748.5	748.1	747.7	747.3	747.1	747.1	747.1	747.1	747.1	747.7
180°	748.5	748.5	748.5	748.5	748.5	748.5	748.5	748.5	748.5	748.5	748.5



TEST NUMBER: P332101-927

CATALOG NUMBER: S123DIW-S340D755U927-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	429.3	429.3	429.3	429.3	429.3	429.3	429.3	429.3
2.5°	427.6	428.3	429.0	429.3	429.2	429.1	429.0	429.0
5°	425.4	426.2	427.1	427.4	427.2	427.1	426.8	426.7
7.5°	420.9	421.6	422.3	422.6	422.6	422.5	422.4	422.2
10°	416.8	417.5	418.2	418.5	418.4	418.2	418.0	417.9
12.5°	412.2	412.7	413.3	413.5	413.4	413.3	413.2	413.1
15°	404.0	404.6	405.4	405.4	404.9	404.4	403.9	403.5
17.5°	393.6	394.1	394.6	394.7	394.5	394.3	394.2	394.0
20°	386.0	386.3	386.7	386.7	386.4	386.2	386.0	385.7
22.5°	377.9	378.2	378.4	378.4	378.1	377.8	377.5	377.2
25°	364.5	364.6	364.6	364.6	364.3	364.1	363.8	363.6
27.5°	350.2	350.3	350.3	350.2	349.9	349.6	349.3	349.0
30°	340.3	340.3	340.3	340.0	339.5	338.9	338.3	337.7
32.5°	329.9	329.5	329.1	328.7	328.4	328.0	327.7	327.4
35°	313.1	312.7	312.1	311.7	311.3	310.9	310.5	310.1
37.5°	295.7	295.2	294.5	294.1	293.9	293.6	293.3	293.1
40°	284.4	283.8	283.0	282.6	282.3	281.9	281.6	281.3
42.5°	272.6	271.9	271.2	270.8	270.5	270.1	269.8	269.4
45°	254.9	254.0	252.9	252.3	251.8	251.4	251.0	250.6
47.5°	236.4	235.4	234.4	233.8	233.4	233.1	232.7	232.3
50°	224.1	223.2	222.3	221.6	221.1	220.6	220.1	219.6
52.5°	211.7	210.9	210.1	209.5	209.0	208.5	208.0	207.6
55°	192.7	191.8	190.9	190.3	189.9	189.4	189.0	188.6
57.5°	174.1	173.3	172.5	171.8	171.3	170.9	170.4	169.9
60°	161.0	160.2	159.5	158.9	158.4	158.0	157.6	157.2
62.5°	148.2	147.5	146.8	146.2	146.0	145.7	145.4	145.1
65°	129.4	128.7	128.0	127.6	127.4	127.1	126.8	126.6
67.5°	110.6	110.0	109.5	109.0	108.7	108.3	108.0	107.7
70°	98.5	97.9	97.4	96.9	96.5	96.1	95.6	95.2
72.5°	86.3	85.7	85.2	84.8	84.7	84.4	84.2	84.0
75°	68.6	68.1	67.7	67.4	67.2	66.9	66.7	66.5
77.5°	52.0	51.8	51.5	51.4	51.4	51.4	51.4	51.4
80°	41.5	41.4	41.4	41.4	41.4	41.4	41.4	41.4
82.5°	32.0	31.8	31.7	31.5	31.5	31.4	31.4	31.3
85°	18.1	18.0	17.8	17.7	17.7	17.7	17.7	17.7
87.5°	9.4	9.4	9.5	9.5	9.6	9.6	9.7	9.7
90°	15.1	15.7	16.2	16.6	16.9	17.1	17.3	17.7
92.5°	23.4	23.8	24.2	24.4	24.2	24.1	23.9	23.8
95°	44.5	45.1	45.6	45.9	45.9	45.9	45.9	45.9
97.5°	69.3	69.9	70.5	70.7	70.7	70.7	70.6	70.6
100°	87.2	87.6	88.0	88.3	88.6	88.9	89.1	89.4
102.5°	107.9	108.3	108.7	108.8	108.8	108.8	108.7	108.7
105°	138.8	138.8	138.8	138.9	139.2	139.4	139.7	140.0
107.5°	172.1	172.6	173.0	173.2	173.0	172.9	172.7	172.5
110°	194.5	195.0	195.5	195.7	195.4	195.1	194.9	194.6



TEST NUMBER: P332101-927

CATALOG NUMBER: S123DIW-S340D755U927-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	216.8	217.5	218.1	218.3	218.3	218.2	218.2	218.2
115°	250.7	250.9	251.0	251.0	250.9	250.7	250.6	250.5
117.5°	285.0	284.9	284.9	284.8	284.4	284.0	283.7	283.3
120°	307.8	307.7	307.6	307.4	307.1	306.9	306.6	306.3
122.5°	331.0	330.6	330.3	329.9	329.5	329.2	328.8	328.4
125°	365.3	364.7	364.2	363.7	363.2	362.7	362.1	361.6
127.5°	399.2	398.5	397.8	397.0	396.5	395.9	395.3	394.7
130°	421.8	421.2	420.6	419.9	419.1	418.1	417.2	416.3
132.5°	443.6	443.0	442.4	441.7	441.0	440.3	439.6	438.9
135°	476.4	475.9	475.4	475.0	474.7	474.4	474.2	473.9
137.5°	508.4	507.9	507.4	506.8	506.4	505.8	505.3	504.9
140°	529.5	529.4	529.3	528.7	527.8	526.9	526.0	525.1
142.5°	549.3	549.1	549.0	548.6	547.9	547.2	546.4	545.7
145°	578.3	578.2	578.1	577.7	577.2	576.7	576.2	575.7
147.5°	605.8	605.8	605.8	605.4	604.6	603.8	603.0	602.2
150°	622.7	622.7	622.7	622.3	621.5	620.8	620.0	619.2
152.5°	638.2	638.3	638.6	638.3	637.6	637.0	636.3	635.6
155°	660.8	661.3	661.8	661.6	660.7	659.8	658.9	658.0
157.5°	680.2	680.8	681.4	681.2	680.5	679.8	679.1	678.3
160°	692.2	692.8	693.5	693.6	693.1	692.5	692.0	691.5
162.5°	703.5	704.2	704.8	704.7	703.9	703.1	702.2	701.3
165°	717.7	718.5	719.3	719.2	718.4	717.4	716.5	715.6
167.5°	729.3	730.2	730.9	730.9	730.2	729.3	728.5	727.7
170°	735.6	736.6	737.4	737.4	736.6	735.6	734.7	733.8
172.5°	740.6	741.4	742.2	742.2	741.2	740.4	739.4	738.6
175°	746.0	746.7	747.5	747.5	746.6	745.6	744.7	743.8
177.5°	748.4	749.0	749.6	749.6	748.8	748.1	747.3	746.6
180°	748.5	748.5	748.5	748.5	748.5	748.5	748.5	748.5

(END OF REPORT)