

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331487-840

Luminaire Tested: **S122DIW-S290D1240U840-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331487-840
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122DIW-S290D1240U840-4F0-1E-UDD-F
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 290 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 1240 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6221.1 lumens
Efficiency: N/A
Efficacy: 133.5 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.3
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 46.6
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331487-840

CATALOG NUMBER: S122DIW-S290D1240U840-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P331487-840

CATALOG NUMBER: S122DIW-S290D1240U840-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	100	100	100	100	88	88	88	88	66	66	66	46	46	46	28	28	28	20				
1	91	87	83	80	80	77	74	71	58	56	54	41	40	38	25	24	24	16				
2	83	76	70	65	73	67	62	58	51	48	45	36	34	32	22	21	20	14				
3	75	66	60	54	66	59	53	48	45	41	38	32	29	27	19	18	17	12				
4	69	59	51	46	61	52	46	41	40	35	32	28	25	23	17	16	15	10				
5	63	52	44	39	55	46	40	35	35	31	27	25	22	20	15	14	13	9				
6	58	47	39	33	51	41	35	30	32	27	24	23	20	17	14	12	11	8				
7	53	42	34	29	47	37	31	26	29	24	21	20	17	15	13	11	10	7				
8	49	38	30	25	44	34	27	23	26	21	18	19	16	13	12	10	9	6				
9	46	34	27	22	40	31	24	20	24	19	16	17	14	12	11	9	8	5				
10	43	31	24	20	38	28	22	18	22	17	14	16	13	11	10	8	7	5				

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	7703	7703	7703
5°	7733	7621	7666
10°	7688	7543	7581
15°	7590	7447	7438
20°	7455	7301	7290
25°	7322	7119	7119
30°	7150	6952	6893
35°	6991	6753	6654
40°	6787	6555	6431
45°	6588	6357	6202
50°	6373	6154	5935
55°	6145	5917	5695
60°	5896	5628	5422
65°	5624	5349	5100
70°	5282	4999	4763
75°	4810	4604	4492
80°	4258	4138	3924
85°	3483	3316	2983



TEST NUMBER: P331487-840

CATALOG NUMBER: S122DIW-S290D1240U840-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	44.9	0.7
10°-20°	126.2	2.0
20°-30°	185.5	3.0
30°-40°	215.5	3.5
40°-50°	215.3	3.5
50°-60°	187.7	3.0
60°-70°	138.8	2.2
70°-80°	78.6	1.3
80°-90°	25.3	0.4
90°-100°	56.9	0.9
100°-110°	208.8	3.4
110°-120°	558.2	9.0
120°-130°	921.5	14.8
130°-140°	980.0	15.8
140°-150°	910.9	14.6
150°-160°	732.3	11.8
160°-170°	471.9	7.6
170°-180°	162.4	2.6
0°-30°	356.6	5.7
0°-40°	572.2	9.2
0°-60°	975.2	15.7
0°-90°	1218.0	19.6
90°-120°	824.0	13.2
90°-150°	3636.4	58.5
90°-180°	5003.0	80.4
0°-180°	6221.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	477	477	477	477	477	
5°	477	475	470	474	473	45
15°	454	451	446	447	445	128
25°	411	407	400	400	400	189
35°	355	350	343	340	338	221
45°	288	285	278	274	272	223
55°	218	215	210	205	202	195
65°	147	144	140	136	134	146
75°	77	76	74	71	72	82
85°	19	18	18	17	16	22
90°	1	15	25	31	33	5
95°	80	42	48	54	53	98
105°	376	392	75	88	94	401
115°	710	732	762	217	101	699
125°	1004	1021	1044	1052	1056	895
135°	1243	1262	1274	1285	1284	959
145°	1442	1442	1461	1469	1464	901
155°	1587	1578	1591	1598	1589	731
165°	1673	1666	1669	1677	1669	472
175°	1711	1703	1705	1712	1701	163
180°	1707	1707	1707	1707	1707	



TEST NUMBER: P331487-840

CATALOG NUMBER: S122DIW-S290D1240U840-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	477.1	477.1	477.1	477.1	477.1	477.1	477.1	477.1	477.1	477.1	477.1
2.5°	479.3	478.9	478.5	478.1	477.7	477.1	476.2	475.2	474.3	473.4	474.2
5°	477.1	476.7	476.3	475.8	475.4	474.7	473.6	472.5	471.3	470.2	471.0
7.5°	472.9	472.2	471.6	471.0	470.4	469.5	468.4	467.2	466.1	464.9	465.7
10°	468.9	468.2	467.5	466.8	466.0	465.0	463.8	462.6	461.4	460.1	460.9
12.5°	463.3	462.7	462.1	461.4	460.8	459.9	458.7	457.5	456.3	455.0	455.6
15°	454.1	453.5	452.9	452.3	451.7	450.8	449.4	448.1	446.8	445.5	445.9
17.5°	442.4	441.8	441.2	440.6	440.0	439.0	437.7	436.3	434.9	433.6	434.0
20°	433.9	433.3	432.7	432.1	431.5	430.5	429.1	427.7	426.3	424.9	425.2
22.5°	425.6	424.6	423.8	422.9	422.1	421.0	419.7	418.3	417.0	415.7	415.7
25°	411.0	410.2	409.4	408.6	407.8	406.5	404.8	403.0	401.3	399.6	399.8
27.5°	394.6	393.8	393.0	392.3	391.6	390.5	389.2	387.8	386.5	385.1	384.8
30°	383.5	382.7	381.9	381.1	380.2	379.1	377.6	376.1	374.5	372.9	372.6
32.5°	371.7	371.1	370.5	369.8	369.2	368.0	366.4	364.9	363.2	361.6	361.0
35°	354.7	353.6	352.5	351.5	350.5	349.2	347.6	346.0	344.4	342.6	342.0
37.5°	335.3	334.4	333.5	332.5	331.6	330.4	328.8	327.2	325.5	323.9	323.2
40°	322.0	321.2	320.4	319.6	318.8	317.6	315.9	314.3	312.7	311.0	310.1
42.5°	309.2	308.4	307.6	306.8	306.0	304.7	303.1	301.4	299.8	298.2	297.2
45°	288.5	287.8	287.1	286.4	285.7	284.6	283.1	281.6	280.0	278.4	277.3
47.5°	268.0	267.3	266.7	266.0	265.3	264.2	262.6	261.1	259.4	257.8	256.6
50°	253.7	253.2	252.7	252.2	251.7	250.6	249.2	247.8	246.4	245.0	243.6
52.5°	239.7	239.0	238.4	237.7	237.0	236.0	234.7	233.4	232.0	230.7	229.4
55°	218.3	217.7	217.1	216.5	215.9	215.0	213.8	212.6	211.4	210.2	208.8
57.5°	196.9	196.4	195.9	195.4	194.9	194.0	192.7	191.4	190.0	188.6	187.4
60°	182.6	182.2	181.8	181.4	181.0	180.1	178.6	177.2	175.7	174.3	173.2
62.5°	168.6	167.9	167.3	166.7	166.0	165.1	164.0	163.0	161.9	160.8	159.7
65°	147.2	146.6	146.0	145.4	144.8	144.0	143.0	142.0	141.0	140.0	139.0
67.5°	125.5	125.0	124.5	124.0	123.6	122.9	121.9	121.0	120.1	119.2	118.5
70°	111.9	111.5	111.1	110.7	110.3	109.7	108.8	107.9	106.8	105.9	105.2
72.5°	98.0	97.6	97.1	96.7	96.3	95.8	95.2	94.7	94.1	93.5	92.8
75°	77.1	76.9	76.6	76.4	76.2	75.9	75.4	74.8	74.3	73.8	73.2
77.5°	58.4	58.0	57.7	57.4	57.0	56.7	56.5	56.2	56.0	55.8	55.5
80°	45.8	45.7	45.6	45.5	45.4	45.3	45.1	44.9	44.7	44.5	44.2
82.5°	34.1	34.1	34.1	34.0	34.0	33.9	33.8	33.7	33.6	33.5	33.1
85°	18.8	18.7	18.6	18.5	18.4	18.3	18.2	18.1	18.0	17.9	17.6
87.5°	6.9	7.3	7.8	8.2	8.6	9.0	9.3	9.5	9.8	10.1	10.1
90°	1.2	4.2	7.3	10.3	13.3	16.0	18.1	20.3	22.5	24.7	26.1
92.5°	24.9	24.6	24.4	24.1	23.8	24.2	25.3	26.5	27.6	28.7	29.4
95°	80.3	71.2	62.2	53.1	44.0	40.5	42.4	44.3	46.3	48.2	49.6
97.5°	159.4	133.8	108.3	82.8	57.3	46.7	51.1	55.5	60.1	64.5	65.5
100°	218.6	181.1	143.4	105.8	68.3	51.7	56.5	61.1	65.7	70.4	72.6
102.5°	283.9	275.9	267.9	260.0	252.1	228.5	189.5	150.5	111.4	72.4	75.2
105°	375.6	383.7	392.0	400.2	408.5	375.2	300.2	225.2	150.3	75.3	78.4
107.5°	480.1	486.7	493.3	500.0	506.6	465.0	375.2	285.3	195.4	105.5	102.4
110°	547.2	553.0	558.8	564.5	570.3	533.5	454.2	374.9	295.5	216.2	188.7



TEST NUMBER: P331487-840

CATALOG NUMBER: S122DIW-S290D1240U840-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	610.5	615.6	620.7	625.8	631.0	623.7	604.1	584.5	564.9	545.2	445.1
115°	710.3	715.0	719.6	724.3	729.0	734.8	741.6	748.5	755.4	762.2	635.1
117.5°	799.5	804.8	809.9	815.2	820.4	825.4	830.0	834.8	839.5	844.2	813.4
120°	864.7	868.9	872.9	877.1	881.2	885.8	890.7	895.6	900.6	905.4	908.8
122.5°	920.1	924.4	928.8	933.1	937.5	942.3	947.7	953.0	958.5	963.8	965.7
125°	1004.3	1007.8	1011.5	1015.0	1018.5	1023.0	1028.2	1033.4	1038.6	1043.9	1045.8
127.5°	1080.7	1084.6	1088.5	1092.6	1096.5	1100.4	1104.3	1108.2	1112.1	1116.0	1118.8
130°	1129.1	1133.5	1137.9	1142.3	1146.7	1150.3	1153.4	1156.4	1159.4	1162.5	1165.5
132.5°	1178.5	1182.2	1186.0	1189.7	1193.5	1196.8	1199.8	1202.9	1205.9	1208.9	1211.4
135°	1242.7	1247.1	1251.5	1255.9	1260.3	1263.7	1266.2	1268.7	1271.1	1273.6	1276.4
137.5°	1307.7	1310.8	1313.8	1317.0	1320.0	1322.9	1325.8	1328.6	1331.3	1334.1	1336.9
140°	1350.2	1352.4	1354.6	1356.8	1359.0	1361.6	1364.6	1367.7	1370.7	1373.7	1376.1
142.5°	1385.8	1387.8	1389.8	1391.7	1393.7	1396.4	1399.9	1403.3	1406.7	1410.3	1412.5
145°	1441.6	1441.4	1441.1	1440.8	1440.6	1442.7	1447.4	1452.1	1456.7	1461.4	1463.3
147.5°	1490.3	1489.2	1488.2	1487.1	1486.1	1487.9	1492.5	1497.1	1501.8	1506.3	1507.8
150°	1522.0	1520.0	1518.1	1516.1	1514.2	1515.5	1519.8	1524.3	1528.6	1533.1	1534.7
152.5°	1548.6	1546.5	1544.3	1542.2	1540.0	1541.1	1545.2	1549.4	1553.6	1557.7	1559.4
155°	1587.4	1584.9	1582.5	1579.9	1577.5	1577.9	1581.2	1584.5	1587.8	1591.1	1592.8
157.5°	1617.8	1615.7	1613.6	1611.5	1609.4	1609.5	1611.8	1614.2	1616.5	1618.8	1620.6
160°	1635.6	1634.0	1632.2	1630.6	1629.0	1629.0	1630.6	1632.2	1634.0	1635.6	1637.2
162.5°	1651.4	1649.7	1648.1	1646.5	1644.8	1644.7	1646.1	1647.5	1649.0	1650.4	1652.2
165°	1672.6	1671.0	1669.3	1667.7	1666.1	1665.7	1666.5	1667.3	1668.1	1668.9	1670.8
167.5°	1688.5	1686.8	1685.2	1683.5	1681.8	1681.4	1682.2	1682.9	1683.7	1684.5	1686.4
170°	1697.4	1695.7	1694.0	1692.4	1690.7	1690.2	1690.7	1691.3	1691.8	1692.4	1694.4
172.5°	1703.2	1701.6	1700.0	1698.3	1696.7	1696.2	1696.7	1697.2	1697.8	1698.3	1700.2
175°	1710.9	1709.0	1707.1	1705.2	1703.2	1702.5	1703.1	1703.6	1704.2	1704.8	1706.7
177.5°	1712.1	1710.6	1709.1	1707.6	1706.0	1705.4	1705.6	1705.8	1706.0	1706.3	1707.8
180°	1707.2	1707.2	1707.2	1707.2	1707.2	1707.2	1707.2	1707.2	1707.2	1707.2	1707.2



TEST NUMBER: P331487-840

CATALOG NUMBER: S122DIW-S290D1240U840-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	477.1	477.1	477.1	477.1	477.1	477.1	477.1	477.1
2.5°	475.0	475.8	476.7	477.1	476.9	476.7	476.6	476.4
5°	471.9	472.7	473.5	473.8	473.6	473.4	473.2	473.0
7.5°	466.6	467.4	468.2	468.5	468.3	468.0	467.8	467.6
10°	461.8	462.6	463.4	463.6	463.3	463.0	462.7	462.4
12.5°	456.2	456.7	457.3	457.5	457.3	457.0	456.8	456.6
15°	446.3	446.7	447.1	447.1	446.6	446.1	445.6	445.0
17.5°	434.5	435.0	435.5	435.5	434.9	434.5	434.0	433.5
20°	425.5	425.8	426.1	426.0	425.6	425.2	424.7	424.3
22.5°	415.8	415.9	415.9	415.8	415.6	415.3	415.1	414.9
25°	400.0	400.2	400.4	400.4	400.2	400.0	399.8	399.6
27.5°	384.5	384.2	383.8	383.4	382.9	382.4	382.0	381.5
30°	372.3	372.0	371.7	371.4	371.0	370.6	370.2	369.7
32.5°	360.5	359.9	359.4	358.9	358.5	358.1	357.7	357.3
35°	341.4	340.8	340.2	339.7	339.2	338.7	338.2	337.6
37.5°	322.3	321.6	320.8	320.2	319.7	319.2	318.8	318.3
40°	309.2	308.3	307.4	306.7	306.3	305.9	305.5	305.1
42.5°	296.2	295.2	294.2	293.4	292.9	292.3	291.8	291.1
45°	276.2	275.1	274.0	273.2	272.8	272.4	272.0	271.6
47.5°	255.5	254.3	253.1	252.2	251.7	251.1	250.4	249.8
50°	242.2	240.7	239.2	238.3	237.8	237.3	236.8	236.3
52.5°	228.3	227.1	225.9	225.0	224.3	223.7	223.0	222.3
55°	207.6	206.4	205.2	204.4	203.9	203.3	202.8	202.3
57.5°	186.2	185.0	183.8	183.0	182.7	182.3	181.9	181.5
60°	172.1	171.0	169.9	169.2	168.8	168.5	168.2	167.9
62.5°	158.6	157.6	156.6	155.9	155.5	155.1	154.7	154.3
65°	138.0	137.1	136.2	135.5	135.0	134.5	134.0	133.5
67.5°	117.8	117.0	116.3	115.7	115.3	114.9	114.5	114.1
70°	104.5	103.8	103.1	102.6	102.2	101.7	101.3	100.9
72.5°	92.1	91.4	90.7	90.1	89.8	89.5	89.2	88.8
75°	72.6	72.0	71.4	71.2	71.4	71.6	71.8	72.0
77.5°	55.2	54.9	54.6	54.3	54.0	53.8	53.5	53.2
80°	43.9	43.6	43.3	43.0	42.8	42.6	42.4	42.2
82.5°	32.7	32.3	31.9	31.7	31.7	31.6	31.6	31.6
85°	17.3	17.0	16.7	16.5	16.4	16.3	16.2	16.1
87.5°	10.1	10.2	10.2	10.2	10.3	10.3	10.3	10.3
90°	27.5	28.8	30.2	31.2	31.7	32.2	32.8	33.3
92.5°	30.1	30.8	31.5	32.0	32.3	32.7	33.0	33.3
95°	50.9	52.3	53.6	54.2	53.9	53.6	53.4	53.1
97.5°	66.7	67.8	68.9	69.6	69.9	70.3	70.6	70.9
100°	74.8	77.0	79.2	80.6	81.1	81.7	82.2	82.8
102.5°	78.1	81.0	83.8	85.6	86.3	87.2	88.0	88.7
105°	81.4	84.4	87.5	89.5	90.6	91.7	92.8	93.9
107.5°	99.4	96.2	93.2	92.2	93.3	94.4	95.5	96.6
110°	161.3	133.8	106.3	93.2	94.3	95.4	96.5	97.6



TEST NUMBER: P331487-840

CATALOG NUMBER: S122DIW-S290D1240U840-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	345.0	244.9	144.7	95.0	95.9	96.8	97.7	98.6
115°	508.0	380.9	253.8	180.4	160.6	140.9	121.1	101.3
117.5°	782.7	751.9	721.2	673.4	608.4	543.5	478.6	413.5
120°	912.1	915.3	918.7	901.8	864.7	827.7	790.6	753.6
122.5°	967.8	969.8	971.7	969.1	961.9	954.7	947.6	940.3
125°	1047.7	1049.7	1051.6	1052.9	1053.7	1054.6	1055.4	1056.2
127.5°	1121.6	1124.4	1127.2	1128.7	1128.8	1129.0	1129.1	1129.3
130°	1168.5	1171.5	1174.5	1175.9	1175.6	1175.4	1175.1	1174.8
132.5°	1214.1	1216.6	1219.2	1220.3	1220.1	1219.8	1219.5	1219.3
135°	1279.1	1281.8	1284.6	1285.7	1285.2	1284.6	1284.0	1283.5
137.5°	1339.5	1342.2	1344.9	1345.7	1344.8	1343.9	1343.0	1342.0
140°	1378.7	1381.1	1383.6	1384.1	1382.7	1381.4	1380.0	1378.7
142.5°	1414.7	1417.0	1419.3	1419.7	1418.4	1416.9	1415.5	1414.2
145°	1465.2	1467.1	1469.1	1469.4	1467.9	1466.6	1465.2	1463.9
147.5°	1509.2	1510.7	1512.1	1512.2	1511.1	1509.8	1508.7	1507.6
150°	1536.3	1538.0	1539.6	1539.7	1538.4	1537.0	1535.6	1534.3
152.5°	1561.0	1562.7	1564.4	1564.3	1562.5	1560.6	1558.8	1557.0
155°	1594.4	1596.1	1597.7	1597.4	1595.2	1593.1	1590.8	1588.6
157.5°	1622.6	1624.4	1626.3	1626.1	1624.0	1621.8	1619.7	1617.5
160°	1638.9	1640.5	1642.1	1642.0	1640.1	1638.2	1636.3	1634.4
162.5°	1654.2	1656.0	1657.9	1657.6	1655.3	1652.8	1650.5	1648.2
165°	1672.7	1674.7	1676.6	1676.6	1674.7	1672.7	1670.8	1668.9
167.5°	1688.3	1690.2	1692.1	1691.9	1689.4	1687.0	1684.5	1682.0
170°	1696.3	1698.2	1700.1	1699.8	1697.4	1694.9	1692.4	1689.9
172.5°	1702.1	1704.0	1706.0	1705.8	1703.2	1700.8	1698.3	1695.9
175°	1708.6	1710.5	1712.4	1712.0	1709.3	1706.6	1703.7	1701.0
177.5°	1709.3	1710.8	1712.4	1712.1	1710.2	1708.2	1706.3	1704.2
180°	1707.2	1707.2	1707.2	1707.2	1707.2	1707.2	1707.2	1707.2

(END OF REPORT)