

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331493-840

Luminaire Tested: **S122DIW-S290D1440U840-4F0-1E-UDD-F**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P331493-840  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S122DIW-S290D1440U840-4F0-1E-UDD-F  
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 290 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
UPLIGHT 1440 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 7035.6 lumens  
Efficiency: N/A  
Efficacy: 131.8 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.3  
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')  
CIE Type: Semi-Indirect


Input Watts (W): 53.4  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P331493-840

CATALOG NUMBER: S122DIW-S290D1440U840-4F0-1E-UDD-F

### Luminous Intensity Polar Plot





TEST NUMBER: P331493-840

CATALOG NUMBER: S122DIW-S290D1440U840-4F0-1E-UDD-F

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									20									
RC	80									70									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																			
RCR																																														
0	99	99	99	99	87	87	87	87	65	65	65	45	45	45	26	26	26	17																												
1	90	86	83	79	79	76	73	70	57	55	53	39	38	37	23	22	22	15																												
2	82	75	70	65	72	66	62	58	50	47	44	34	33	31	20	19	18	12																												
3	75	66	59	54	66	58	53	48	44	40	37	30	28	26	18	17	16	10																												
4	68	58	51	45	60	52	45	40	39	35	31	27	24	22	16	15	13	9																												
5	63	52	44	38	55	46	39	34	35	30	27	24	21	19	14	13	12	8																												
6	58	46	39	33	50	41	34	30	31	26	23	22	19	17	13	11	10	7																												
7	53	41	34	29	47	37	30	26	28	23	20	20	17	15	12	10	9	6																												
8	49	37	30	25	43	33	27	23	25	21	18	18	15	13	11	9	8	5																												
9	46	34	27	22	40	30	24	20	23	19	16	16	13	11	10	8	7	5																												
10	42	31	24	20	37	28	22	18	21	17	14	15	12	10	9	8	7	4																												

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	7703	7703	7703
5°	7733	7621	7666
10°	7688	7543	7581
15°	7590	7447	7438
20°	7455	7301	7290
25°	7322	7119	7119
30°	7150	6952	6893
35°	6991	6753	6654
40°	6787	6555	6431
45°	6588	6357	6202
50°	6373	6154	5935
55°	6145	5917	5695
60°	5896	5628	5422
65°	5624	5349	5100
70°	5282	4999	4763
75°	4810	4604	4492
80°	4258	4138	3924
85°	3483	3316	2983



TEST NUMBER: P331493-840

CATALOG NUMBER: S122DIW-S290D1440U840-4F0-1E-UDD-F

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	44.9	0.6
10°-20°	126.2	1.8
20°-30°	185.5	2.6
30°-40°	215.5	3.1
40°-50°	215.3	3.1
50°-60°	187.7	2.7
60°-70°	138.8	2.0
70°-80°	78.6	1.1
80°-90°	26.0	0.4
90°-100°	66.2	0.9
100°-110°	242.8	3.5
110°-120°	649.0	9.2
120°-130°	1071.4	15.2
130°-140°	1139.4	16.2
140°-150°	1059.0	15.1
150°-160°	851.5	12.1
160°-170°	548.7	7.8
170°-180°	188.9	2.7
0°-30°	356.6	5.1
0°-40°	572.2	8.1
0°-60°	975.2	13.9
0°-90°	1218.7	17.3
90°-120°	958.1	13.6
90°-150°	4227.9	60.1
90°-180°	5817.0	82.7
0°-180°	7035.6	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	477	477	477	477	477	
5°	477	475	470	474	473	45
15°	454	451	446	447	445	128
25°	411	407	400	400	400	189
35°	355	350	343	340	338	221
45°	288	285	278	274	272	223
55°	218	215	210	205	202	195
65°	147	144	140	136	134	146
75°	77	76	74	71	72	82
85°	19	18	18	17	16	22
90°	1	17	29	36	39	5
95°	93	49	56	63	62	114
105°	437	456	88	103	109	467
115°	826	851	886	252	118	813
125°	1168	1187	1214	1223	1228	1041
135°	1445	1467	1481	1494	1492	1116
145°	1676	1676	1699	1708	1702	1048
155°	1846	1834	1850	1857	1847	850
165°	1945	1937	1940	1949	1940	549
175°	1989	1980	1982	1991	1978	189
180°	1985	1985	1985	1985	1985	



TEST NUMBER: P331493-840

CATALOG NUMBER: S122DIW-S290D1440U840-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	477.1	477.1	477.1	477.1	477.1	477.1	477.1	477.1	477.1	477.1	477.1
2.5°	479.3	478.9	478.5	478.1	477.7	477.1	476.2	475.2	474.3	473.4	474.2
5°	477.1	476.7	476.3	475.8	475.4	474.7	473.6	472.5	471.3	470.2	471.0
7.5°	472.9	472.2	471.6	471.0	470.4	469.5	468.4	467.2	466.1	464.9	465.7
10°	468.9	468.2	467.5	466.8	466.0	465.0	463.8	462.6	461.4	460.1	460.9
12.5°	463.3	462.7	462.1	461.4	460.8	459.9	458.7	457.5	456.3	455.0	455.6
15°	454.1	453.5	452.9	452.3	451.7	450.8	449.4	448.1	446.8	445.5	445.9
17.5°	442.4	441.8	441.2	440.6	440.0	439.0	437.7	436.3	434.9	433.6	434.0
20°	433.9	433.3	432.7	432.1	431.5	430.5	429.1	427.7	426.3	424.9	425.2
22.5°	425.6	424.6	423.8	422.9	422.1	421.0	419.7	418.3	417.0	415.7	415.7
25°	411.0	410.2	409.4	408.6	407.8	406.5	404.8	403.0	401.3	399.6	399.8
27.5°	394.6	393.8	393.0	392.3	391.6	390.5	389.2	387.8	386.5	385.1	384.8
30°	383.5	382.7	381.9	381.1	380.2	379.1	377.6	376.1	374.5	372.9	372.6
32.5°	371.7	371.1	370.5	369.8	369.2	368.0	366.4	364.9	363.2	361.6	361.0
35°	354.7	353.6	352.5	351.5	350.5	349.2	347.6	346.0	344.4	342.6	342.0
37.5°	335.3	334.4	333.5	332.5	331.6	330.4	328.8	327.2	325.5	323.9	323.2
40°	322.0	321.2	320.4	319.6	318.8	317.6	315.9	314.3	312.7	311.0	310.1
42.5°	309.2	308.4	307.6	306.8	306.0	304.7	303.1	301.4	299.8	298.2	297.2
45°	288.5	287.8	287.1	286.4	285.7	284.6	283.1	281.6	280.0	278.4	277.3
47.5°	268.0	267.3	266.7	266.0	265.3	264.2	262.6	261.1	259.4	257.8	256.6
50°	253.7	253.2	252.7	252.2	251.7	250.6	249.2	247.8	246.4	245.0	243.6
52.5°	239.7	239.0	238.4	237.7	237.0	236.0	234.7	233.4	232.0	230.7	229.4
55°	218.3	217.7	217.1	216.5	215.9	215.0	213.8	212.6	211.4	210.2	208.8
57.5°	196.9	196.4	195.9	195.4	194.9	194.0	192.7	191.4	190.0	188.6	187.4
60°	182.6	182.2	181.8	181.4	181.0	180.1	178.6	177.2	175.7	174.3	173.2
62.5°	168.6	167.9	167.3	166.7	166.0	165.1	164.0	163.0	161.9	160.8	159.7
65°	147.2	146.6	146.0	145.4	144.8	144.0	143.0	142.0	141.0	140.0	139.0
67.5°	125.5	125.0	124.5	124.0	123.6	122.9	121.9	121.0	120.1	119.2	118.5
70°	111.9	111.5	111.1	110.7	110.3	109.7	108.8	107.9	106.8	105.9	105.2
72.5°	98.0	97.6	97.1	96.7	96.3	95.8	95.2	94.7	94.1	93.5	92.8
75°	77.1	76.9	76.6	76.4	76.2	75.9	75.4	74.8	74.3	73.8	73.2
77.5°	58.4	58.0	57.7	57.4	57.0	56.7	56.5	56.2	56.0	55.8	55.5
80°	45.8	45.7	45.6	45.5	45.4	45.3	45.1	44.9	44.7	44.5	44.2
82.5°	34.1	34.1	34.1	34.0	34.0	33.9	33.8	33.7	33.6	33.5	33.1
85°	18.8	18.7	18.6	18.5	18.4	18.3	18.2	18.1	18.0	17.9	17.6
87.5°	6.9	7.5	8.0	8.5	9.1	9.5	9.8	10.2	10.5	10.9	11.0
90°	1.4	4.9	8.5	12.0	15.5	18.5	21.1	23.6	26.2	28.7	30.3
92.5°	29.0	28.7	28.4	28.1	27.8	28.2	29.5	30.8	32.0	33.3	34.1
95°	93.3	82.8	72.3	61.8	51.2	47.1	49.3	51.5	53.8	56.0	57.6
97.5°	185.3	155.6	125.9	96.2	66.6	54.3	59.5	64.6	69.8	74.9	76.2
100°	254.2	210.5	166.7	123.0	79.3	60.2	65.5	71.0	76.4	81.9	84.4
102.5°	330.0	320.8	311.5	302.3	293.1	265.7	220.4	174.9	129.6	84.1	87.5
105°	436.7	446.2	455.8	465.3	474.9	436.2	349.0	261.9	174.7	87.7	91.1
107.5°	558.2	565.8	573.6	581.3	589.1	540.7	436.2	331.6	227.1	122.7	119.1
110°	636.3	643.0	649.6	656.4	663.1	620.3	528.1	435.9	343.6	251.4	219.4



TEST NUMBER: P331493-840

CATALOG NUMBER: S122DIW-S290D1440U840-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	709.8	715.7	721.6	727.6	733.6	725.1	702.4	679.5	656.7	634.0	517.6
115°	825.9	831.3	836.7	842.1	847.6	854.2	862.2	870.2	878.2	886.2	738.4
117.5°	929.6	935.6	941.7	947.8	953.8	959.6	965.0	970.6	976.0	981.6	945.8
120°	1005.4	1010.2	1014.9	1019.8	1024.5	1029.8	1035.5	1041.3	1047.0	1052.8	1056.6
122.5°	1069.8	1074.8	1079.8	1084.9	1089.9	1095.6	1101.8	1108.0	1114.3	1120.5	1122.9
125°	1167.7	1171.8	1176.0	1180.1	1184.3	1189.4	1195.5	1201.5	1207.6	1213.7	1215.9
127.5°	1256.5	1261.0	1265.7	1270.2	1274.9	1279.4	1283.9	1288.5	1293.0	1297.6	1300.8
130°	1312.7	1317.9	1322.9	1328.1	1333.2	1337.5	1341.0	1344.5	1348.0	1351.5	1355.0
132.5°	1370.2	1374.5	1378.9	1383.2	1387.6	1391.5	1395.0	1398.5	1402.0	1405.5	1408.6
135°	1444.9	1450.0	1455.1	1460.2	1465.3	1469.3	1472.2	1475.0	1477.9	1480.8	1484.0
137.5°	1520.5	1524.0	1527.6	1531.2	1534.7	1538.1	1541.4	1544.7	1547.9	1551.2	1554.3
140°	1569.8	1572.4	1575.0	1577.5	1580.0	1583.1	1586.6	1590.1	1593.7	1597.1	1600.0
142.5°	1611.2	1613.5	1615.8	1618.1	1620.4	1623.6	1627.6	1631.6	1635.6	1639.6	1642.2
145°	1676.2	1675.8	1675.5	1675.2	1674.9	1677.4	1682.8	1688.3	1693.6	1699.1	1701.3
147.5°	1732.7	1731.5	1730.3	1729.1	1727.9	1729.9	1735.3	1740.7	1746.1	1751.4	1753.0
150°	1769.5	1767.3	1765.0	1762.8	1760.5	1762.0	1767.1	1772.2	1777.3	1782.4	1784.3
152.5°	1800.5	1798.1	1795.5	1793.0	1790.6	1791.7	1796.5	1801.4	1806.2	1811.1	1813.0
155°	1845.6	1842.7	1839.9	1836.9	1834.1	1834.6	1838.5	1842.3	1846.1	1849.9	1851.8
157.5°	1881.0	1878.6	1876.1	1873.7	1871.3	1871.4	1874.0	1876.7	1879.4	1882.1	1884.3
160°	1901.6	1899.7	1897.8	1895.9	1894.0	1894.0	1895.9	1897.8	1899.7	1901.6	1903.5
162.5°	1920.0	1918.1	1916.2	1914.3	1912.4	1912.2	1913.9	1915.5	1917.2	1918.8	1921.1
165°	1944.7	1942.8	1940.9	1938.9	1937.0	1936.6	1937.5	1938.4	1939.4	1940.4	1942.7
167.5°	1963.1	1961.2	1959.2	1957.3	1955.4	1954.9	1955.8	1956.7	1957.6	1958.5	1960.8
170°	1973.5	1971.6	1969.6	1967.7	1965.8	1965.1	1965.8	1966.4	1967.0	1967.7	1969.9
172.5°	1980.3	1978.4	1976.5	1974.6	1972.7	1972.1	1972.7	1973.3	1974.0	1974.6	1976.8
175°	1989.2	1987.0	1984.8	1982.6	1980.3	1979.5	1980.1	1980.7	1981.5	1982.1	1984.3
177.5°	1990.6	1988.9	1987.1	1985.3	1983.5	1982.8	1983.0	1983.3	1983.5	1983.8	1985.6
180°	1984.9	1984.9	1984.9	1984.9	1984.9	1984.9	1984.9	1984.9	1984.9	1984.9	1984.9



TEST NUMBER: P331493-840

CATALOG NUMBER: S122DIW-S290D1440U840-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	477.1	477.1	477.1	477.1	477.1	477.1	477.1	477.1
2.5°	475.0	475.8	476.7	477.1	476.9	476.7	476.6	476.4
5°	471.9	472.7	473.5	473.8	473.6	473.4	473.2	473.0
7.5°	466.6	467.4	468.2	468.5	468.3	468.0	467.8	467.6
10°	461.8	462.6	463.4	463.6	463.3	463.0	462.7	462.4
12.5°	456.2	456.7	457.3	457.5	457.3	457.0	456.8	456.6
15°	446.3	446.7	447.1	447.1	446.6	446.1	445.6	445.0
17.5°	434.5	435.0	435.5	435.5	434.9	434.5	434.0	433.5
20°	425.5	425.8	426.1	426.0	425.6	425.2	424.7	424.3
22.5°	415.8	415.9	415.9	415.8	415.6	415.3	415.1	414.9
25°	400.0	400.2	400.4	400.4	400.2	400.0	399.8	399.6
27.5°	384.5	384.2	383.8	383.4	382.9	382.4	382.0	381.5
30°	372.3	372.0	371.7	371.4	371.0	370.6	370.2	369.7
32.5°	360.5	359.9	359.4	358.9	358.5	358.1	357.7	357.3
35°	341.4	340.8	340.2	339.7	339.2	338.7	338.2	337.6
37.5°	322.3	321.6	320.8	320.2	319.7	319.2	318.8	318.3
40°	309.2	308.3	307.4	306.7	306.3	305.9	305.5	305.1
42.5°	296.2	295.2	294.2	293.4	292.9	292.3	291.8	291.1
45°	276.2	275.1	274.0	273.2	272.8	272.4	272.0	271.6
47.5°	255.5	254.3	253.1	252.2	251.7	251.1	250.4	249.8
50°	242.2	240.7	239.2	238.3	237.8	237.3	236.8	236.3
52.5°	228.3	227.1	225.9	225.0	224.3	223.7	223.0	222.3
55°	207.6	206.4	205.2	204.4	203.9	203.3	202.8	202.3
57.5°	186.2	185.0	183.8	183.0	182.7	182.3	181.9	181.5
60°	172.1	171.0	169.9	169.2	168.8	168.5	168.2	167.9
62.5°	158.6	157.6	156.6	155.9	155.5	155.1	154.7	154.3
65°	138.0	137.1	136.2	135.5	135.0	134.5	134.0	133.5
67.5°	117.8	117.0	116.3	115.7	115.3	114.9	114.5	114.1
70°	104.5	103.8	103.1	102.6	102.2	101.7	101.3	100.9
72.5°	92.1	91.4	90.7	90.1	89.8	89.5	89.2	88.8
75°	72.6	72.0	71.4	71.2	71.4	71.6	71.8	72.0
77.5°	55.2	54.9	54.6	54.3	54.0	53.8	53.5	53.2
80°	43.9	43.6	43.3	43.0	42.8	42.6	42.4	42.2
82.5°	32.7	32.3	31.9	31.7	31.7	31.6	31.6	31.6
85°	17.3	17.0	16.7	16.5	16.4	16.3	16.2	16.1
87.5°	11.0	11.1	11.2	11.2	11.3	11.3	11.4	11.4
90°	31.9	33.5	35.1	36.3	36.9	37.5	38.2	38.8
92.5°	34.9	35.9	36.7	37.3	37.7	38.0	38.4	38.8
95°	59.2	60.8	62.4	63.0	62.7	62.4	62.1	61.8
97.5°	77.6	78.8	80.1	80.9	81.3	81.7	82.1	82.4
100°	86.9	89.6	92.1	93.7	94.3	94.9	95.6	96.2
102.5°	90.8	94.1	97.5	99.6	100.5	101.3	102.2	103.1
105°	94.6	98.2	101.7	104.0	105.3	106.6	107.9	109.2
107.5°	115.5	111.9	108.4	107.2	108.5	109.8	111.1	112.3
110°	187.5	155.6	123.7	108.4	109.7	110.9	112.2	113.5





TEST NUMBER: P331493-840

CATALOG NUMBER: S122DIW-S290D1440U840-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	401.1	284.7	168.2	110.5	111.6	112.6	113.6	114.6
115°	590.7	442.8	295.1	209.6	186.7	163.7	140.8	117.8
117.5°	910.1	874.3	838.6	782.9	707.4	631.9	556.3	480.9
120°	1060.5	1064.3	1068.1	1048.4	1005.4	962.3	919.2	876.2
122.5°	1125.2	1127.5	1129.7	1126.7	1118.3	1110.0	1101.7	1093.3
125°	1218.1	1220.3	1222.5	1224.2	1225.2	1226.1	1227.1	1228.0
127.5°	1304.0	1307.3	1310.5	1312.3	1312.4	1312.6	1312.8	1313.0
130°	1358.6	1362.1	1365.5	1367.2	1366.9	1366.5	1366.2	1365.8
132.5°	1411.5	1414.5	1417.5	1418.9	1418.6	1418.3	1418.0	1417.5
135°	1487.1	1490.4	1493.6	1494.8	1494.2	1493.6	1492.9	1492.3
137.5°	1557.4	1560.5	1563.7	1564.7	1563.6	1562.6	1561.5	1560.3
140°	1602.9	1605.8	1608.6	1609.2	1607.7	1606.1	1604.5	1602.9
142.5°	1644.9	1647.5	1650.1	1650.6	1649.0	1647.4	1645.9	1644.3
145°	1703.5	1705.8	1708.1	1708.4	1706.8	1705.2	1703.5	1702.0
147.5°	1754.7	1756.4	1758.1	1758.2	1756.9	1755.5	1754.1	1752.8
150°	1786.2	1788.2	1790.1	1790.2	1788.7	1787.1	1785.4	1783.8
152.5°	1814.9	1816.8	1818.8	1818.7	1816.5	1814.5	1812.4	1810.3
155°	1853.7	1855.6	1857.5	1857.2	1854.7	1852.2	1849.6	1847.0
157.5°	1886.4	1888.5	1890.8	1890.6	1888.1	1885.6	1883.1	1880.7
160°	1905.4	1907.3	1909.3	1909.1	1906.9	1904.6	1902.4	1900.2
162.5°	1923.2	1925.4	1927.5	1927.2	1924.5	1921.8	1919.0	1916.3
165°	1944.9	1947.1	1949.3	1949.3	1947.1	1944.9	1942.7	1940.4
167.5°	1963.0	1965.2	1967.4	1967.1	1964.3	1961.4	1958.5	1955.6
170°	1972.2	1974.4	1976.6	1976.3	1973.5	1970.5	1967.7	1964.8
172.5°	1979.0	1981.3	1983.5	1983.2	1980.3	1977.4	1974.6	1971.7
175°	1986.5	1988.7	1990.9	1990.5	1987.3	1984.1	1981.0	1977.7
177.5°	1987.3	1989.1	1990.9	1990.6	1988.3	1986.1	1983.8	1981.5
180°	1984.9	1984.9	1984.9	1984.9	1984.9	1984.9	1984.9	1984.9

(END OF REPORT)