

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332148-927

Luminaire Tested: **S123DIW-S560D1535U927-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332148-927
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-5,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123DIW-S560D1535U927-4F0-1E-UDD-F
Description: DEFINE 3 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 560 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 1535 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6702.0 lumens
Efficiency: N/A
Efficacy: 110.6 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 60.6
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332148-927

CATALOG NUMBER: S123DIW-S560D1535U927-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P332148-927

CATALOG NUMBER: S123DIW-S560D1535U927-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	102	102	102	102	91	91	91	91	71	71	71	52	52	52	35	35	35	27
1	93	88	85	81	83	79	76	73	62	60	58	46	45	43	31	30	30	23
2	84	77	71	66	75	69	64	60	54	51	48	40	38	36	27	26	25	19
3	77	68	61	55	68	61	55	50	48	44	40	36	33	30	24	23	21	16
4	70	60	52	46	62	54	47	42	42	38	34	32	29	26	22	20	18	14
5	64	53	45	40	57	48	41	36	38	33	29	28	25	22	19	17	16	12
6	59	48	40	34	53	43	36	31	34	29	25	25	22	20	18	16	14	11
7	55	43	35	30	49	39	32	27	31	26	22	23	20	17	16	14	12	9
8	51	39	31	26	45	35	28	24	28	23	20	21	18	15	15	13	11	8
9	47	35	28	23	42	32	25	21	25	21	17	19	16	14	14	11	10	8
10	44	32	25	21	39	29	23	19	23	19	16	18	15	12	13	10	9	7

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	7597	7597	7597
5°	7632	7527	7580
10°	7581	7462	7508
15°	7492	7377	7392
20°	7389	7257	7263
25°	7251	7114	7099
30°	7097	6954	6901
35°	6937	6786	6699
40°	6770	6600	6497
45°	6587	6428	6272
50°	6402	6219	6047
55°	6161	6001	5819
60°	5918	5748	5565
65°	5703	5471	5300
70°	5385	5155	4925
75°	4924	4745	4541
80°	4438	4252	4215
85°	3890	3742	3606



TEST NUMBER: P332148-927

CATALOG NUMBER: S123DIW-S560D1535U927-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	66.5	1.0
10°-20°	187.7	2.8
20°-30°	277.3	4.1
30°-40°	323.9	4.8
40°-50°	325.6	4.9
50°-60°	286.0	4.3
60°-70°	213.1	3.2
70°-80°	121.4	1.8
80°-90°	39.3	0.6
90°-100°	58.0	0.9
100°-110°	276.2	4.1
110°-120°	663.5	9.9
120°-130°	844.9	12.6
130°-140°	902.7	13.5
140°-150°	844.1	12.6
150°-160°	680.9	10.2
160°-170°	439.5	6.6
170°-180°	151.5	2.3
0°-30°	531.5	7.9
0°-40°	855.4	12.8
0°-60°	1467.0	21.9
0°-90°	1840.9	27.5
90°-120°	997.6	14.9
90°-150°	3589.3	53.6
90°-180°	4861.0	72.5
0°-180°	6702.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	706	706	706	706	706	
5°	706	703	697	702	702	67
15°	672	670	662	666	663	189
25°	610	607	599	599	598	281
35°	528	524	516	513	510	330
45°	433	430	422	415	412	334
55°	328	327	320	313	310	294
65°	224	221	215	210	208	221
75°	118	116	114	111	109	127
85°	32	30	30	29	29	35
90°	1	13	28	33	36	5
95°	72	27	37	44	45	89
105°	353	359	259	62	52	374
115°	662	669	680	691	696	653
125°	933	942	948	950	952	833
135°	1162	1169	1174	1177	1174	894
145°	1341	1349	1351	1354	1354	839
155°	1477	1475	1476	1481	1474	680
165°	1557	1554	1553	1561	1554	440
175°	1594	1588	1589	1597	1588	152
180°	1594	1594	1594	1594	1594	



TEST NUMBER: P332148-927

CATALOG NUMBER: S123DIW-S560D1535U927-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	705.8	705.8	705.8	705.8	705.8	705.8	705.8	705.8	705.8	705.8	705.8
2.5°	708.1	707.7	707.3	706.9	706.5	705.6	704.4	703.2	702.1	700.9	702.0
5°	706.3	705.7	705.0	704.3	703.6	702.6	701.1	699.6	698.2	696.6	698.0
7.5°	699.4	698.8	698.1	697.4	696.7	695.6	694.1	692.5	691.0	689.5	690.7
10°	693.6	692.9	692.3	691.6	690.9	689.7	687.9	686.2	684.4	682.7	683.9
12.5°	685.9	685.2	684.7	684.1	683.6	682.5	680.8	679.1	677.6	675.9	676.8
15°	672.3	671.8	671.3	670.7	670.2	669.1	667.3	665.6	663.8	662.0	663.1
17.5°	656.7	656.0	655.3	654.6	653.9	652.7	650.9	649.2	647.5	645.6	646.4
20°	645.1	644.3	643.4	642.6	641.8	640.6	638.8	637.1	635.3	633.5	634.1
22.5°	631.9	631.1	630.3	629.5	628.7	627.4	625.7	623.9	622.2	620.4	620.8
25°	610.5	609.7	608.9	608.1	607.2	605.9	604.2	602.5	600.7	599.0	599.0
27.5°	587.6	586.8	586.0	585.2	584.4	583.0	581.1	579.3	577.4	575.5	575.6
30°	571.0	570.4	569.7	569.0	568.3	567.0	565.1	563.2	561.4	559.5	559.5
32.5°	554.5	553.7	552.7	551.8	551.0	549.8	548.3	546.8	545.4	544.0	543.2
35°	527.9	527.1	526.3	525.5	524.7	523.4	521.7	519.9	518.2	516.4	515.6
37.5°	500.7	499.7	498.7	497.6	496.6	495.3	493.5	491.7	489.9	488.1	487.2
40°	481.8	481.0	480.2	479.4	478.6	477.2	475.3	473.5	471.6	469.7	468.6
42.5°	462.9	462.0	461.1	460.1	459.2	457.8	455.9	454.1	452.2	450.3	449.2
45°	432.7	432.1	431.6	431.0	430.5	429.4	427.6	425.9	424.1	422.3	420.7
47.5°	402.7	401.9	401.2	400.4	399.6	398.3	396.7	395.1	393.4	391.7	390.1
50°	382.3	381.6	381.0	380.2	379.6	378.4	376.6	374.9	373.1	371.4	369.9
52.5°	360.9	360.4	360.0	359.6	359.1	357.9	356.1	354.3	352.4	350.5	349.3
55°	328.3	328.1	328.0	327.9	327.7	326.8	325.0	323.3	321.5	319.8	318.3
57.5°	297.2	296.8	296.3	295.9	295.4	294.5	293.0	291.7	290.3	288.8	287.6
60°	274.9	274.7	274.6	274.5	274.3	273.5	271.9	270.2	268.6	267.0	265.8
62.5°	255.0	254.6	254.3	254.0	253.6	252.6	251.0	249.4	247.7	246.1	244.9
65°	223.9	223.2	222.6	221.9	221.3	220.2	218.9	217.5	216.2	214.8	213.7
67.5°	191.0	190.4	189.8	189.3	188.6	187.8	186.8	185.8	184.7	183.8	182.8
70°	171.1	170.3	169.5	168.7	167.9	167.1	166.3	165.5	164.6	163.8	162.9
72.5°	150.3	149.6	149.1	148.5	147.9	147.1	146.2	145.3	144.3	143.5	142.6
75°	118.4	117.8	117.2	116.7	116.2	115.7	115.3	114.9	114.5	114.1	113.4
77.5°	90.1	89.8	89.4	89.2	88.9	88.5	88.0	87.5	87.0	86.5	86.1
80°	71.6	71.2	70.8	70.4	69.9	69.6	69.4	69.1	68.8	68.6	68.4
82.5°	53.6	53.6	53.5	53.4	53.3	53.2	53.2	53.2	53.1	53.1	52.8
85°	31.5	31.3	31.1	30.7	30.5	30.3	30.3	30.3	30.3	30.3	30.1
87.5°	12.8	13.1	13.2	13.5	13.7	14.0	14.7	15.2	15.8	16.4	16.5
90°	1.2	3.8	6.4	9.1	11.7	14.7	18.1	21.5	25.0	28.4	29.5
92.5°	22.0	21.3	20.5	19.8	19.1	20.0	22.6	25.2	27.7	30.3	32.0
95°	72.2	61.5	50.7	39.8	29.1	25.1	28.0	30.9	33.8	36.7	38.6
97.5°	145.2	140.4	135.5	130.6	125.8	113.9	95.0	76.0	57.1	38.1	40.2
100°	200.2	205.4	210.6	215.9	221.2	203.3	162.2	121.2	80.2	39.1	41.2
102.5°	262.7	266.5	270.3	274.0	277.8	257.3	212.5	167.6	122.8	78.0	71.4
105°	352.9	355.8	358.7	361.6	364.5	354.1	330.4	306.7	283.0	259.4	212.8
107.5°	448.1	450.4	452.7	455.1	457.4	460.4	464.1	467.9	471.7	475.4	441.2
110°	511.6	513.7	515.8	517.9	520.1	522.5	525.5	528.3	531.2	534.1	525.5



TEST NUMBER: P332148-927

CATALOG NUMBER: S123DIW-S560D1535U927-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	572.3	574.2	576.1	578.0	579.8	582.3	585.1	588.0	590.9	593.8	594.0
115°	662.0	663.6	665.2	666.8	668.4	670.3	672.7	675.0	677.4	679.8	682.4
117.5°	748.9	750.9	752.8	754.8	756.8	758.4	759.5	760.7	761.9	763.2	765.2
120°	803.0	805.3	807.7	810.1	812.5	814.0	814.8	815.6	816.3	817.1	819.3
122.5°	857.9	859.8	861.8	863.7	865.7	867.2	868.2	869.2	870.1	871.2	872.7
125°	933.2	935.3	937.5	939.5	941.7	943.3	944.3	945.3	946.4	947.5	948.0
127.5°	1006.2	1008.3	1010.4	1012.5	1014.6	1016.3	1017.6	1018.8	1020.1	1021.4	1022.2
130°	1051.6	1053.8	1055.9	1058.0	1060.1	1061.7	1062.7	1063.7	1064.9	1065.9	1066.9
132.5°	1095.3	1097.3	1099.5	1101.5	1103.7	1105.2	1106.0	1106.8	1107.6	1108.5	1109.5
135°	1161.8	1163.4	1165.0	1166.6	1168.2	1169.4	1170.4	1171.6	1172.6	1173.6	1174.4
137.5°	1218.6	1220.7	1222.7	1224.6	1226.6	1228.0	1228.5	1229.1	1229.7	1230.3	1231.5
140°	1256.6	1258.1	1259.7	1261.3	1262.9	1264.0	1264.8	1265.6	1266.4	1267.2	1268.3
142.5°	1291.6	1293.2	1294.7	1296.3	1297.9	1299.1	1299.9	1300.7	1301.5	1302.3	1303.1
145°	1340.6	1342.4	1344.3	1346.2	1348.0	1349.2	1349.7	1350.2	1350.8	1351.3	1351.8
147.5°	1386.8	1388.1	1389.3	1390.4	1391.6	1392.5	1393.1	1393.6	1394.1	1394.6	1395.2
150°	1415.2	1416.0	1416.8	1417.6	1418.4	1419.0	1419.6	1420.1	1420.6	1421.2	1421.7
152.5°	1440.8	1441.2	1441.5	1441.9	1442.3	1442.6	1443.0	1443.3	1443.6	1443.9	1444.9
155°	1476.8	1476.3	1475.8	1475.3	1474.7	1474.6	1474.9	1475.1	1475.4	1475.6	1476.9
157.5°	1504.8	1504.8	1504.7	1504.6	1504.6	1504.4	1504.1	1503.9	1503.6	1503.3	1504.9
160°	1521.9	1521.5	1521.3	1521.1	1520.8	1520.5	1520.3	1520.0	1519.7	1519.5	1521.1
162.5°	1537.9	1537.2	1536.6	1535.9	1535.2	1534.7	1534.5	1534.2	1533.9	1533.7	1535.5
165°	1557.4	1556.6	1555.8	1555.0	1554.2	1553.7	1553.4	1553.2	1552.9	1552.6	1554.7
167.5°	1572.5	1571.5	1570.4	1569.4	1568.3	1567.8	1567.8	1567.8	1567.8	1567.8	1569.9
170°	1581.0	1580.0	1578.9	1577.9	1576.8	1576.3	1576.3	1576.3	1576.3	1576.3	1578.4
172.5°	1586.7	1585.5	1584.2	1582.9	1581.7	1581.1	1581.4	1581.6	1581.8	1582.0	1584.1
175°	1594.0	1592.8	1591.4	1590.1	1588.8	1588.2	1588.6	1588.8	1589.0	1589.4	1591.2
177.5°	1595.9	1594.9	1593.9	1592.8	1591.7	1591.3	1591.6	1591.7	1592.0	1592.2	1593.9
180°	1594.0	1594.0	1594.0	1594.0	1594.0	1594.0	1594.0	1594.0	1594.0	1594.0	1594.0



TEST NUMBER: P332148-927

CATALOG NUMBER: S123DIW-S560D1535U927-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	705.8	705.8	705.8	705.8	705.8	705.8	705.8	705.8
2.5°	703.1	704.1	705.2	705.7	705.6	705.4	705.4	705.3
5°	699.3	700.7	702.0	702.6	702.3	702.0	701.8	701.5
7.5°	691.9	693.1	694.3	694.8	694.7	694.5	694.3	694.2
10°	685.1	686.3	687.5	688.0	687.8	687.5	687.2	686.9
12.5°	677.6	678.6	679.5	679.8	679.6	679.5	679.3	679.1
15°	664.2	665.3	666.4	666.5	665.7	664.9	664.1	663.3
17.5°	647.2	647.9	648.7	648.9	648.6	648.3	648.0	647.7
20°	634.6	635.2	635.6	635.7	635.3	634.9	634.5	634.1
22.5°	621.3	621.7	622.2	622.1	621.6	621.1	620.6	620.0
25°	599.2	599.4	599.4	599.4	599.0	598.6	598.1	597.7
27.5°	575.8	575.8	575.9	575.8	575.2	574.7	574.2	573.7
30°	559.5	559.5	559.5	559.0	558.1	557.1	556.2	555.2
32.5°	542.5	541.7	540.9	540.3	539.8	539.3	538.8	538.3
35°	514.8	514.0	513.2	512.5	511.7	511.1	510.4	509.8
37.5°	486.2	485.2	484.3	483.5	483.2	482.7	482.3	481.8
40°	467.5	466.4	465.4	464.5	464.0	463.5	463.0	462.4
42.5°	448.1	447.0	445.9	445.1	444.6	444.1	443.5	443.0
45°	419.1	417.5	415.9	414.7	414.1	413.4	412.7	412.0
47.5°	388.6	387.0	385.4	384.3	383.7	383.1	382.5	381.9
50°	368.4	366.9	365.4	364.3	363.5	362.7	361.9	361.1
52.5°	348.0	346.7	345.5	344.4	343.6	342.8	342.0	341.2
55°	316.8	315.4	313.9	312.8	312.1	311.4	310.8	310.1
57.5°	286.2	284.9	283.6	282.5	281.7	281.0	280.2	279.4
60°	264.6	263.4	262.1	261.2	260.5	259.8	259.2	258.5
62.5°	243.7	242.5	241.3	240.4	240.0	239.6	239.1	238.6
65°	212.6	211.6	210.5	209.8	209.4	209.0	208.6	208.1
67.5°	181.9	180.9	180.0	179.2	178.6	178.1	177.5	177.0
70°	161.9	161.1	160.1	159.2	158.6	157.9	157.2	156.5
72.5°	141.8	140.9	140.1	139.5	139.2	138.8	138.5	138.1
75°	112.7	112.1	111.4	110.8	110.4	110.0	109.6	109.2
77.5°	85.6	85.2	84.7	84.4	84.4	84.4	84.4	84.4
80°	68.3	68.1	68.0	68.0	68.0	68.0	68.0	68.0
82.5°	52.5	52.3	52.0	51.9	51.8	51.7	51.6	51.5
85°	29.8	29.5	29.2	29.2	29.2	29.2	29.2	29.2
87.5°	16.6	16.6	16.8	16.9	17.0	17.1	17.2	17.3
90°	30.5	31.6	32.6	33.4	34.0	34.5	35.0	35.5
92.5°	33.7	35.4	37.1	38.0	38.3	38.7	39.0	39.3
95°	40.4	42.2	44.0	45.0	45.0	45.0	45.0	45.0
97.5°	42.4	44.4	46.6	47.8	48.0	48.2	48.6	48.8
100°	43.3	45.4	47.5	48.7	49.0	49.2	49.5	49.7
102.5°	64.9	58.4	51.8	48.8	49.3	49.7	50.2	50.7
105°	166.2	119.6	73.0	50.0	50.5	51.1	51.6	52.1
107.5°	407.0	372.9	338.7	304.1	269.0	233.9	198.8	163.7
110°	516.7	508.0	499.4	476.2	438.6	400.9	363.3	325.7



TEST NUMBER: P332148-927

CATALOG NUMBER: S123DIW-S560D1535U927-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	594.1	594.3	594.5	590.6	582.6	574.6	566.7	558.7
115°	685.1	687.7	690.3	692.1	693.2	694.3	695.3	696.4
117.5°	767.4	769.4	771.6	772.8	772.9	773.2	773.4	773.6
120°	821.4	823.5	825.6	826.6	826.6	826.6	826.6	826.6
122.5°	874.1	875.6	877.1	877.9	878.1	878.3	878.5	878.8
125°	948.5	949.0	949.5	950.1	950.6	951.1	951.6	952.2
127.5°	1023.0	1023.9	1024.7	1024.8	1024.4	1023.8	1023.3	1022.8
130°	1067.9	1069.1	1070.1	1070.3	1069.8	1069.3	1068.7	1068.3
132.5°	1110.6	1111.7	1112.7	1112.9	1112.1	1111.4	1110.6	1109.9
135°	1175.2	1176.0	1176.8	1176.8	1176.0	1175.2	1174.4	1173.6
137.5°	1232.8	1234.1	1235.3	1235.6	1235.2	1234.6	1234.1	1233.6
140°	1269.3	1270.3	1271.4	1271.7	1271.1	1270.7	1270.1	1269.6
142.5°	1303.9	1304.8	1305.6	1305.7	1305.0	1304.2	1303.5	1302.7
145°	1352.3	1352.9	1353.4	1353.7	1353.7	1353.7	1353.7	1353.7
147.5°	1395.7	1396.2	1396.8	1396.4	1395.2	1394.0	1392.7	1391.5
150°	1422.2	1422.8	1423.2	1423.2	1422.4	1421.6	1420.8	1420.0
152.5°	1445.8	1446.8	1447.7	1447.6	1446.4	1445.1	1443.9	1442.7
155°	1478.3	1479.6	1480.9	1480.7	1479.2	1477.6	1476.0	1474.5
157.5°	1506.5	1508.1	1509.7	1509.4	1507.4	1505.3	1503.2	1501.2
160°	1522.7	1524.2	1525.7	1525.7	1523.8	1521.9	1520.1	1518.3
162.5°	1537.2	1539.1	1540.8	1540.9	1539.3	1537.6	1536.0	1534.4
165°	1556.8	1558.9	1561.1	1561.2	1559.3	1557.5	1555.6	1553.8
167.5°	1572.0	1574.1	1576.2	1576.2	1574.1	1572.0	1569.9	1567.8
170°	1580.5	1582.6	1584.8	1584.8	1582.6	1580.5	1578.4	1576.3
172.5°	1586.2	1588.3	1590.4	1590.3	1588.0	1585.7	1583.3	1581.0
175°	1593.0	1594.8	1596.7	1596.6	1594.4	1592.4	1590.2	1588.2
177.5°	1595.5	1597.2	1598.9	1598.7	1596.6	1594.5	1592.4	1590.3
180°	1594.0	1594.0	1594.0	1594.0	1594.0	1594.0	1594.0	1594.0

(END OF REPORT)