

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332126-927

Luminaire Tested: **S123DIW-S560D755U927-4F0-1E-UDD-A**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P332126-927  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-5,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S123DIW-S560D755U927-4F0-1E-UDD-A  
Description: DEFINE 3 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 560 LUMENS PER FOOT, ASYMMETRIC DIFFUSER  
UPLIGHT 755 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 4285.0 lumens  
Efficiency: N/A  
Efficacy: 114.0 lumens/watt  
Spacing Criteria (0/90/45): 1.37 / 1.23 / 1.49  
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')  
CIE Type: General Diffuse


Input Watts (W): 37.6  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332126-927

CATALOG NUMBER: S123DIW-S560D755U927-4F0-1E-UDD-A

### Luminous Intensity Polar Plot



— 0°-180°    - - - 45°-225°    - · - · - 90°-270°    - · - · - 135°-315°



TEST NUMBER: P332126-927

CATALOG NUMBER: S123DIW-S560D755U927-4F0-1E-UDD-A

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	106	106	106	106	97	97	97	97	80	80	80	65	65	65	51	51	51	44				
1	97	93	89	85	88	85	82	79	71	68	66	57	56	54	45	44	43	38				
2	88	81	75	70	81	74	69	65	62	58	55	51	48	46	40	38	37	32				
3	81	71	64	59	74	66	59	55	55	50	47	45	42	39	36	33	32	27				
4	74	63	56	50	67	58	52	46	49	44	40	40	36	33	32	29	27	24				
5	68	56	48	43	62	52	45	40	44	38	34	36	32	29	29	26	24	21				
6	62	51	43	37	57	47	40	35	39	34	30	33	29	26	26	23	21	18				
7	58	46	38	32	53	42	35	30	36	30	26	30	26	23	24	21	19	16				
8	54	41	34	29	49	38	32	27	33	27	23	27	23	20	22	19	17	14				
9	50	38	30	25	46	35	28	24	30	25	21	25	21	18	20	17	15	13				
10	46	35	27	23	43	32	26	21	27	22	19	23	19	16	19	16	14	12				

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	6740	6740	6740	6740
5°	8038	6769	5999	6769
10°	10061	6735	5418	6735
15°	12340	6681	5045	6681
20°	14701	6596	4803	6596
25°	15610	6494	4749	6494
30°	13380	6418	4774	6418
35°	9305	6311	4824	6311
40°	7009	6185	4808	6185
45°	5820	5999	4748	5999
50°	5213	5620	4706	5620
55°	4874	5210	4647	5210
60°	4573	4781	4598	4781
65°	4297	4358	4452	4358
70°	4028	3877	4239	3877
75°	3606	3394	3889	3394
80°	3155	2783	3347	2783
85°	2470	2025	2248	2025



TEST NUMBER: P332126-927

CATALOG NUMBER: S123DIW-S560D755U927-4F0-1E-UDD-A

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	61.7	1.4
10°-20°	197.8	4.6
20°-30°	332.0	7.7
30°-40°	375.9	8.8
40°-50°	337.1	7.9
50°-60°	272.0	6.3
60°-70°	189.6	4.4
70°-80°	99.6	2.3
80°-90°	26.6	0.6
90°-100°	28.5	0.7
100°-110°	136.0	3.2
110°-120°	326.6	7.6
120°-130°	415.9	9.7
130°-140°	444.3	10.4
140°-150°	415.5	9.7
150°-160°	335.2	7.8
160°-170°	216.3	5.0
170°-180°	74.5	1.7
0°-30°	591.5	13.8
0°-40°	967.4	22.6
0°-60°	1576.5	36.8
0°-90°	1892.3	44.2
90°-120°	491.1	11.5
90°-150°	1766.8	41.2
90°-180°	2393.0	55.8
0°-180°	4285.0	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	626	626	626	626	626	
5°	744	626	555	626	744	77
15°	1107	600	453	600	1107	320
25°	1314	547	400	547	1314	576
35°	708	480	367	480	708	460
45°	382	394	312	394	382	303
55°	260	278	248	278	260	233
65°	169	171	175	171	169	168
75°	87	82	94	82	87	93
85°	20	16	18	16	20	24
90°	18	1	18	1	18	9
95°	22	36	22	36	22	19
105°	26	174	26	174	26	59
115°	343	326	343	326	343	317
125°	469	459	469	459	469	419
135°	578	572	578	572	578	445
145°	666	660	666	660	666	416
155°	726	727	726	727	726	335
165°	765	767	765	767	765	216
175°	782	785	782	785	782	74
180°	785	785	785	785	785	



TEST NUMBER: P332126-927

CATALOG NUMBER: S123DIW-S560D755U927-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	626.2	626.2	626.2	626.2	626.2	626.2	626.2	626.2	626.2	626.2	626.2
2.5°	664.6	664.1	662.9	663.8	661.9	659.3	659.0	656.6	649.5	649.0	647.1
5°	743.9	741.5	741.2	740.9	736.7	730.9	719.9	719.1	704.5	697.2	688.4
7.5°	846.8	848.0	843.6	839.7	826.7	818.2	806.4	791.5	773.6	755.4	743.3
10°	920.5	930.5	918.1	909.6	901.7	886.8	869.6	848.0	826.5	801.3	782.2
12.5°	999.7	1004.6	1002.1	994.0	981.8	959.2	928.5	904.8	884.9	843.0	826.1
15°	1107.4	1125.9	1114.1	1086.8	1087.4	1065.9	1025.8	981.8	958.5	921.7	871.6
17.5°	1222.3	1224.6	1219.5	1196.7	1181.5	1152.0	1115.0	1072.9	1025.5	981.1	928.0
20°	1283.4	1281.6	1271.0	1259.1	1233.0	1210.0	1169.6	1122.6	1061.9	1018.2	960.3
22.5°	1317.4	1314.3	1309.3	1299.4	1277.7	1252.9	1216.7	1165.3	1107.6	1047.3	980.4
25°	1314.3	1318.3	1318.9	1316.1	1308.6	1293.7	1265.2	1224.2	1166.6	1089.3	1019.5
27.5°	1195.4	1200.9	1217.2	1231.6	1247.7	1264.0	1261.9	1241.5	1198.9	1132.0	1046.7
30°	1076.5	1064.3	1094.4	1132.3	1158.1	1203.6	1229.1	1230.6	1206.7	1149.3	1066.1
32.5°	911.4	924.8	938.0	984.7	1041.1	1092.2	1142.9	1183.8	1188.4	1150.2	1077.5
35°	708.1	724.8	749.1	773.4	834.1	886.2	975.4	1053.1	1115.0	1123.2	1078.6
37.5°	570.6	578.9	594.2	618.5	658.2	720.2	789.2	887.3	977.0	1043.7	1046.6
40°	498.8	501.2	518.5	537.0	569.2	620.1	682.4	769.1	876.5	969.7	1008.5
42.5°	444.9	450.3	457.6	475.4	501.0	539.3	597.1	668.9	767.3	874.5	950.5
45°	382.3	388.3	392.9	404.7	422.9	448.7	489.1	554.6	629.5	740.3	842.6
47.5°	340.9	341.4	344.8	353.7	366.1	385.5	414.0	456.1	524.9	614.7	719.7
50°	311.3	316.2	317.3	324.3	334.1	348.3	372.0	407.7	464.2	543.1	639.6
52.5°	290.4	291.8	295.2	300.3	308.8	319.9	340.4	368.4	412.7	480.0	568.7
55°	259.7	259.7	263.1	267.0	271.9	281.9	295.5	316.2	349.8	402.0	475.5
57.5°	231.3	232.8	235.2	236.4	240.5	247.2	258.6	274.3	299.4	339.5	397.9
60°	212.4	215.1	214.8	217.2	220.9	226.0	235.8	248.5	270.9	303.1	352.3
62.5°	195.9	195.7	195.7	198.5	202.2	207.1	213.4	224.4	243.5	272.0	313.9
65°	168.7	168.1	170.2	172.1	173.3	176.9	181.7	191.5	204.2	225.5	257.9
67.5°	144.6	142.8	143.9	144.6	146.6	149.5	154.0	160.0	170.2	187.2	211.7
70°	128.0	126.5	126.2	126.8	128.7	130.8	134.1	139.9	149.2	163.0	180.9
72.5°	111.1	110.0	110.0	111.3	112.2	113.5	115.9	121.2	128.7	138.9	155.6
75°	86.7	86.7	86.7	87.1	88.0	89.2	91.0	93.7	99.5	106.8	118.0
77.5°	65.0	65.0	64.6	64.6	65.9	66.5	66.9	69.4	72.6	77.6	85.7
80°	50.9	49.4	50.1	50.9	51.6	51.9	52.8	53.4	56.2	58.9	64.6
82.5°	37.9	36.6	36.7	38.1	38.3	38.5	39.5	40.3	41.4	43.8	46.9
85°	20.0	20.0	20.4	20.4	20.6	20.4	21.2	21.5	21.5	23.1	24.9
87.5°	10.8	10.2	10.5	10.6	10.3	10.5	10.6	10.8	10.9	11.0	10.9
90°	17.5	17.2	17.0	16.7	16.5	16.1	15.5	15.1	14.5	14.0	12.3
92.5°	19.3	19.2	19.0	18.9	18.7	18.2	17.4	16.6	15.8	14.9	13.6
95°	22.2	22.2	22.2	22.2	22.2	21.7	20.8	19.9	19.0	18.1	16.6
97.5°	24.0	23.9	23.8	23.6	23.5	22.9	21.9	20.8	19.8	18.8	28.1
100°	24.5	24.3	24.2	24.1	24.0	23.4	22.3	21.3	20.3	19.3	39.5
102.5°	25.0	24.7	24.5	24.2	24.0	25.5	28.8	31.9	35.2	38.3	60.4
105°	25.7	25.4	25.1	24.9	24.6	36.0	58.9	81.8	104.7	127.7	139.3
107.5°	80.6	97.8	115.1	132.4	149.7	166.8	183.5	200.3	217.1	234.0	232.2
110°	160.3	178.8	197.3	215.9	234.4	245.8	250.1	254.4	258.6	262.9	261.5



TEST NUMBER: P332126-927

CATALOG NUMBER: S123DIW-S560D755U927-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	275.0	278.9	282.9	286.8	290.7	292.6	292.6	292.5	292.4	292.3	290.9
115°	342.8	342.2	341.7	341.2	340.7	339.8	338.5	337.2	335.9	334.6	333.4
117.5°	380.8	380.6	380.6	380.5	380.3	379.8	378.7	377.7	376.7	375.7	375.0
120°	406.9	406.9	406.9	406.9	406.9	406.4	405.4	404.3	403.3	402.2	401.9
122.5°	432.5	432.5	432.3	432.2	432.1	431.7	430.9	430.2	429.5	428.8	428.3
125°	468.7	468.4	468.2	467.9	467.6	467.4	467.1	466.8	466.6	466.4	465.8
127.5°	503.4	503.7	503.9	504.2	504.5	504.4	504.0	503.6	503.1	502.7	502.1
130°	525.8	526.1	526.3	526.6	526.9	526.7	526.2	525.7	525.1	524.7	524.1
132.5°	546.3	546.7	547.1	547.4	547.8	547.7	547.2	546.7	546.1	545.7	545.2
135°	577.7	578.1	578.5	578.8	579.2	579.2	578.8	578.5	578.1	577.7	577.2
137.5°	607.2	607.4	607.7	608.0	608.2	608.1	607.4	606.8	606.2	605.5	605.3
140°	624.9	625.2	625.4	625.7	626.0	625.8	625.3	624.8	624.2	623.8	623.4
142.5°	641.2	641.6	642.0	642.3	642.7	642.6	642.2	641.8	641.4	641.0	640.6
145°	666.3	666.3	666.3	666.3	666.3	666.1	665.9	665.7	665.4	665.1	664.9
147.5°	684.9	685.6	686.1	686.7	687.3	687.5	687.2	687.0	686.7	686.4	686.2
150°	698.9	699.3	699.7	700.1	700.5	700.5	700.3	700.1	699.8	699.5	699.3
152.5°	710.1	710.7	711.3	711.9	712.5	712.6	712.1	711.6	711.1	710.7	710.6
155°	725.7	726.5	727.3	728.1	728.9	729.0	728.3	727.6	727.0	726.4	726.2
157.5°	738.9	740.0	740.9	742.0	743.0	743.1	742.3	741.6	740.8	740.0	740.1
160°	747.3	748.2	749.2	750.0	751.0	751.0	750.3	749.5	748.7	747.9	748.1
162.5°	755.3	756.1	756.9	757.6	758.4	758.4	757.6	756.7	755.8	754.9	755.0
165°	764.8	765.7	766.6	767.5	768.4	768.3	767.3	766.3	765.2	764.2	764.4
167.5°	771.7	772.7	773.7	774.8	775.9	775.9	774.8	773.7	772.7	771.7	771.7
170°	775.9	776.9	777.9	779.0	780.1	780.1	779.0	777.9	776.9	775.9	775.9
172.5°	778.2	779.3	780.5	781.6	782.8	782.8	781.8	780.8	779.7	778.7	778.6
175°	781.7	782.8	783.8	784.8	785.8	785.9	785.1	784.1	783.2	782.3	782.2
177.5°	782.8	783.8	784.8	785.8	786.9	787.0	786.2	785.4	784.5	783.7	783.6
180°	784.7	784.7	784.7	784.7	784.7	784.7	784.7	784.7	784.7	784.7	784.7



TEST NUMBER: P332126-927

CATALOG NUMBER: S123DIW-S560D755U927-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	626.2	626.2	626.2	626.2	626.2	626.2	626.2	626.2	626.2	626.2	626.2
2.5°	645.6	643.7	641.7	638.3	635.4	631.3	630.1	628.7	624.3	620.4	617.5
5°	685.1	677.8	667.2	657.4	649.6	639.0	632.9	626.5	617.4	609.3	602.5
7.5°	726.4	712.0	695.5	677.7	661.1	645.0	632.1	620.6	607.8	595.7	586.4
10°	759.1	738.5	715.4	690.5	669.3	648.6	631.4	616.2	599.8	585.6	573.7
12.5°	796.5	765.9	734.1	703.9	678.7	650.1	629.2	609.9	591.4	574.2	560.9
15°	840.7	801.9	764.3	722.7	684.4	648.6	623.8	599.5	578.0	560.4	543.4
17.5°	881.0	837.0	787.4	736.9	690.8	648.3	613.5	586.1	559.1	537.6	520.6
20°	903.8	853.7	797.6	745.1	694.2	646.8	608.6	575.8	546.8	523.9	504.9
22.5°	923.5	864.9	806.8	750.8	694.0	642.9	599.7	565.9	534.3	512.1	491.8
25°	943.9	873.8	815.6	749.7	686.3	633.5	584.9	546.8	515.2	489.1	468.2
27.5°	961.4	873.2	804.1	733.2	674.3	621.4	569.6	528.5	495.0	466.7	445.4
30°	973.0	874.4	792.2	722.1	662.7	608.0	557.6	516.4	481.2	452.3	432.4
32.5°	980.3	873.7	781.3	706.5	644.2	595.9	544.8	502.1	465.9	437.6	418.3
35°	984.5	868.3	762.5	674.5	614.4	567.4	524.6	480.3	442.4	416.0	394.1
37.5°	976.0	857.1	740.6	643.5	577.7	531.5	495.4	457.7	421.4	392.4	373.5
40°	962.7	849.9	723.6	621.7	552.5	507.9	477.3	440.2	404.4	376.8	359.3
42.5°	937.2	835.0	705.0	597.4	526.2	481.6	453.4	422.6	388.6	362.7	345.2
45°	875.0	802.8	676.9	561.0	487.6	441.5	416.6	394.1	363.5	338.3	323.1
47.5°	788.7	754.3	636.4	522.6	447.2	402.8	376.9	358.9	336.4	316.2	301.6
50°	728.8	714.5	609.0	496.4	420.2	376.8	352.0	335.6	319.5	299.1	285.8
52.5°	659.6	668.4	576.9	469.2	392.8	350.1	326.7	313.7	299.1	282.4	270.8
55°	562.2	594.1	521.6	423.6	352.0	311.3	289.1	277.6	269.1	256.7	246.7
57.5°	471.0	511.5	461.7	376.5	311.8	276.8	255.6	243.0	237.5	231.0	223.2
60°	416.8	456.9	419.0	345.0	284.9	251.5	232.7	222.1	216.7	212.1	205.4
62.5°	368.6	409.1	377.2	312.9	258.4	227.5	211.1	200.7	196.5	194.1	188.4
65°	302.2	337.1	315.8	263.1	220.5	193.3	178.4	171.1	167.2	166.3	162.6
67.5°	246.0	272.5	257.1	218.2	184.7	161.1	148.5	142.4	139.3	139.0	136.3
70°	209.1	233.9	222.1	186.9	158.0	139.6	128.7	123.2	121.4	121.0	119.5
72.5°	180.4	197.7	188.4	159.0	136.7	119.9	111.9	106.2	104.1	104.6	103.5
75°	133.5	146.6	141.1	120.7	102.8	91.9	85.2	81.6	79.8	80.7	79.5
77.5°	96.1	104.3	99.4	85.3	74.3	66.4	61.5	59.3	57.6	57.5	57.0
80°	72.5	77.4	74.6	66.1	57.0	50.4	46.4	44.9	44.0	43.7	43.4
82.5°	51.7	55.8	52.5	46.7	40.6	36.5	34.3	32.3	31.6	31.8	31.5
85°	26.1	27.6	26.4	22.7	20.4	18.5	17.3	16.4	15.8	16.1	15.4
87.5°	11.1	11.0	10.0	8.7	7.9	7.0	6.7	5.9	5.7	5.9	6.0
90°	10.6	9.0	7.3	5.8	4.4	3.2	1.9	0.6	1.9	3.2	4.4
92.5°	12.4	11.1	9.8	9.4	9.7	10.1	10.5	10.9	10.5	10.1	9.7
95°	15.2	13.8	12.4	14.3	19.6	25.0	30.3	35.6	30.3	25.0	19.6
97.5°	37.4	46.7	56.1	61.9	64.3	66.7	69.1	71.5	69.1	66.7	64.3
100°	59.7	79.9	100.1	108.8	106.3	103.7	101.1	98.5	101.1	103.7	106.3
102.5°	82.5	104.6	126.7	136.7	134.9	133.0	131.2	129.3	131.2	133.0	134.9
105°	151.0	162.6	174.3	179.4	178.0	176.6	175.2	173.7	175.2	176.6	178.0
107.5°	230.3	228.5	226.6	225.1	224.0	222.8	221.7	220.5	221.7	222.8	224.0
110°	260.1	258.6	257.2	256.0	254.9	253.9	252.9	251.8	252.9	253.9	254.9





TEST NUMBER: P332126-927

CATALOG NUMBER: S123DIW-S560D755U927-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	289.5	288.0	286.6	285.4	284.5	283.5	282.6	281.7	282.6	283.5	284.5
115°	332.2	331.1	329.9	329.0	328.2	327.4	326.6	325.8	326.6	327.4	328.2
117.5°	374.5	373.8	373.3	372.5	371.5	370.6	369.6	368.7	369.6	370.6	371.5
120°	401.5	401.1	400.7	399.9	398.7	397.6	396.4	395.2	396.4	397.6	398.7
122.5°	427.9	427.3	426.8	426.1	425.2	424.2	423.3	422.3	423.3	424.2	425.2
125°	465.3	464.8	464.3	463.5	462.5	461.4	460.4	459.4	460.4	461.4	462.5
127.5°	501.5	500.9	500.3	499.4	498.4	497.3	496.3	495.3	496.3	497.3	498.4
130°	523.6	523.1	522.6	521.8	520.8	519.8	518.7	517.6	518.7	519.8	520.8
132.5°	544.8	544.4	544.0	543.3	542.2	541.1	540.1	539.1	540.1	541.1	542.2
135°	576.6	576.2	575.6	575.0	574.2	573.4	572.7	571.9	572.7	573.4	574.2
137.5°	605.0	604.7	604.4	603.8	602.8	601.8	600.8	599.8	600.8	601.8	602.8
140°	623.0	622.6	622.2	621.6	620.8	620.0	619.2	618.5	619.2	620.0	620.8
142.5°	640.2	639.8	639.4	638.9	638.1	637.3	636.5	635.7	636.5	637.3	638.1
145°	664.6	664.3	664.1	663.5	662.6	661.7	660.8	659.9	660.8	661.7	662.6
147.5°	686.0	685.7	685.4	685.0	684.4	683.8	683.2	682.6	683.2	683.8	684.4
150°	699.0	698.8	698.5	698.2	697.8	697.4	697.0	696.6	697.0	697.4	697.8
152.5°	710.4	710.3	710.1	710.0	709.7	709.6	709.4	709.2	709.4	709.6	709.7
155°	726.1	726.0	725.8	725.9	726.1	726.4	726.7	726.9	726.7	726.4	726.1
157.5°	740.2	740.4	740.5	740.6	740.6	740.6	740.7	740.7	740.7	740.6	740.6
160°	748.1	748.3	748.5	748.5	748.7	748.8	748.9	749.1	748.9	748.8	748.7
162.5°	755.2	755.3	755.4	755.7	756.0	756.3	756.7	757.0	756.7	756.3	756.0
165°	764.5	764.6	764.8	765.0	765.4	765.8	766.2	766.6	766.2	765.8	765.4
167.5°	771.7	771.7	771.7	772.0	772.5	773.0	773.5	774.0	773.5	773.0	772.5
170°	775.9	775.9	775.9	776.2	776.7	777.2	777.7	778.2	777.7	777.2	776.7
172.5°	778.5	778.4	778.2	778.6	779.2	779.7	780.4	781.0	780.4	779.7	779.2
175°	782.0	781.9	781.8	782.0	782.7	783.3	783.9	784.7	783.9	783.3	782.7
177.5°	783.5	783.4	783.3	783.5	784.0	784.5	785.1	785.5	785.1	784.5	784.0
180°	784.7	784.7	784.7	784.7	784.7	784.7	784.7	784.7	784.7	784.7	784.7



TEST NUMBER: P332126-927

CATALOG NUMBER: S123DIW-S560D755U927-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	626.2	626.2	626.2	626.2	626.2	626.2	626.2	626.2	626.2	626.2	626.2
2.5°	615.8	614.1	611.6	608.0	605.1	600.5	600.5	601.2	601.2	600.9	600.5
5°	597.1	592.6	587.1	580.7	574.0	567.4	566.2	563.7	561.9	560.7	559.2
7.5°	577.3	569.3	561.3	552.5	544.3	537.6	532.9	529.0	526.5	523.9	521.9
10°	564.0	554.0	544.6	535.2	524.9	516.7	511.5	507.9	505.2	502.7	501.5
12.5°	548.3	536.8	526.4	517.5	506.2	497.7	492.8	491.2	487.9	482.8	480.1
15°	525.2	514.6	502.2	488.5	483.0	472.7	466.9	464.2	462.4	458.4	457.2
17.5°	505.5	491.5	477.6	467.4	457.2	448.9	445.7	442.3	439.9	436.7	435.7
20°	489.7	477.3	464.5	453.6	443.0	433.9	431.1	428.7	426.3	424.8	423.6
22.5°	473.6	461.2	450.7	440.5	429.1	423.2	420.2	417.6	415.8	414.8	413.6
25°	451.1	440.2	428.4	419.3	410.2	406.2	404.4	402.9	401.7	400.2	399.9
27.5°	431.0	419.1	409.6	401.0	394.5	391.2	389.4	388.7	389.0	389.5	389.8
30°	416.0	405.0	397.1	389.8	383.8	380.8	380.5	380.5	381.7	382.0	382.6
32.5°	402.1	393.2	385.2	378.2	373.6	371.5	372.7	372.7	373.7	374.5	375.6
35°	382.0	374.1	368.0	361.9	358.0	358.9	359.5	360.1	361.6	363.5	364.7
37.5°	362.7	355.9	349.6	344.8	343.0	344.7	346.1	347.4	349.2	350.5	351.7
40°	348.9	343.7	337.7	333.4	334.1	334.9	336.2	337.7	339.2	340.1	341.4
42.5°	336.0	330.7	326.1	322.5	323.4	324.6	325.3	326.1	327.8	329.5	330.2
45°	316.5	312.2	307.9	305.9	306.4	307.0	307.7	308.6	310.1	311.3	311.6
47.5°	294.5	291.4	288.6	286.5	287.5	287.2	288.0	290.0	290.5	291.2	292.9
50°	280.4	277.6	274.3	273.7	273.7	273.7	273.9	276.4	276.4	277.6	278.8
52.5°	264.8	263.1	260.9	259.8	259.4	259.4	260.6	261.8	262.3	264.0	265.2
55°	241.8	240.0	238.2	237.3	236.6	237.3	239.7	240.3	241.8	242.7	243.6
57.5°	217.9	216.4	215.0	214.5	214.4	215.2	216.5	218.3	218.7	221.5	222.8
60°	202.1	199.9	198.8	198.8	198.1	200.8	200.3	203.3	203.9	205.7	207.9
62.5°	185.8	182.9	182.4	182.4	183.3	184.1	185.0	186.3	187.9	190.2	191.8
65°	159.6	158.0	160.2	159.9	159.3	161.1	161.1	162.6	164.5	166.6	169.9
67.5°	134.8	134.0	134.2	134.2	135.1	136.1	137.0	138.3	140.5	142.8	144.9
70°	118.0	118.9	117.4	118.7	119.5	119.9	120.4	122.2	124.7	126.2	128.7
72.5°	101.8	101.7	101.9	102.3	103.3	103.9	104.4	106.5	109.2	110.4	112.4
75°	78.3	78.0	78.9	78.9	80.4	81.0	81.6	82.5	84.9	86.7	88.3
77.5°	57.2	57.5	57.4	58.4	58.0	58.1	60.0	60.8	61.1	64.7	65.5
80°	43.1	43.7	44.0	44.3	44.6	44.0	46.1	47.1	47.1	49.1	50.7
82.5°	31.0	31.3	32.1	32.4	32.5	33.0	33.3	33.9	34.6	35.6	37.5
85°	15.4	16.4	16.7	16.4	16.7	16.1	17.0	17.3	17.6	17.6	17.6
87.5°	6.0	6.6	6.7	7.2	7.3	7.9	8.0	7.6	7.7	8.6	7.7
90°	5.8	7.3	9.0	10.6	12.3	14.0	14.5	15.1	15.5	16.1	16.5
92.5°	9.4	9.8	11.1	12.4	13.6	14.9	15.8	16.6	17.4	18.2	18.7
95°	14.3	12.4	13.8	15.2	16.6	18.1	19.0	19.9	20.8	21.7	22.2
97.5°	61.9	56.1	46.7	37.4	28.1	18.8	19.8	20.8	21.9	22.9	23.5
100°	108.8	100.1	79.9	59.7	39.5	19.3	20.3	21.3	22.3	23.4	24.0
102.5°	136.7	126.7	104.6	82.5	60.4	38.3	35.2	31.9	28.8	25.5	24.0
105°	179.4	174.3	162.6	151.0	139.3	127.7	104.7	81.8	58.9	36.0	24.6
107.5°	225.1	226.6	228.5	230.3	232.2	234.0	217.1	200.3	183.5	166.8	149.7
110°	256.0	257.2	258.6	260.1	261.5	262.9	258.6	254.4	250.1	245.8	234.4



TEST NUMBER: P332126-927

CATALOG NUMBER: S123DIW-S560D755U927-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	285.4	286.6	288.0	289.5	290.9	292.3	292.4	292.5	292.6	292.6	290.7
115°	329.0	329.9	331.1	332.2	333.4	334.6	335.9	337.2	338.5	339.8	340.7
117.5°	372.5	373.3	373.8	374.5	375.0	375.7	376.7	377.7	378.7	379.8	380.3
120°	399.9	400.7	401.1	401.5	401.9	402.2	403.3	404.3	405.4	406.4	406.9
122.5°	426.1	426.8	427.3	427.9	428.3	428.8	429.5	430.2	430.9	431.7	432.1
125°	463.5	464.3	464.8	465.3	465.8	466.4	466.6	466.8	467.1	467.4	467.6
127.5°	499.4	500.3	500.9	501.5	502.1	502.7	503.1	503.6	504.0	504.4	504.5
130°	521.8	522.6	523.1	523.6	524.1	524.7	525.1	525.7	526.2	526.7	526.9
132.5°	543.3	544.0	544.4	544.8	545.2	545.7	546.1	546.7	547.2	547.7	547.8
135°	575.0	575.6	576.2	576.6	577.2	577.7	578.1	578.5	578.8	579.2	579.2
137.5°	603.8	604.4	604.7	605.0	605.3	605.5	606.2	606.8	607.4	608.1	608.2
140°	621.6	622.2	622.6	623.0	623.4	623.8	624.2	624.8	625.3	625.8	626.0
142.5°	638.9	639.4	639.8	640.2	640.6	641.0	641.4	641.8	642.2	642.6	642.7
145°	663.5	664.1	664.3	664.6	664.9	665.1	665.4	665.7	665.9	666.1	666.3
147.5°	685.0	685.4	685.7	686.0	686.2	686.4	686.7	687.0	687.2	687.5	687.3
150°	698.2	698.5	698.8	699.0	699.3	699.5	699.8	700.1	700.3	700.5	700.5
152.5°	710.0	710.1	710.3	710.4	710.6	710.7	711.1	711.6	712.1	712.6	712.5
155°	725.9	725.8	726.0	726.1	726.2	726.4	727.0	727.6	728.3	729.0	728.9
157.5°	740.6	740.5	740.4	740.2	740.1	740.0	740.8	741.6	742.3	743.1	743.0
160°	748.5	748.5	748.3	748.1	748.1	747.9	748.7	749.5	750.3	751.0	751.0
162.5°	755.7	755.4	755.3	755.2	755.0	754.9	755.8	756.7	757.6	758.4	758.4
165°	765.0	764.8	764.6	764.5	764.4	764.2	765.2	766.3	767.3	768.3	768.4
167.5°	772.0	771.7	771.7	771.7	771.7	771.7	772.7	773.7	774.8	775.9	775.9
170°	776.2	775.9	775.9	775.9	775.9	775.9	776.9	777.9	779.0	780.1	780.1
172.5°	778.6	778.2	778.4	778.5	778.6	778.7	779.7	780.8	781.8	782.8	782.8
175°	782.0	781.8	781.9	782.0	782.2	782.3	783.2	784.1	785.1	785.9	785.8
177.5°	783.5	783.3	783.4	783.5	783.6	783.7	784.5	785.4	786.2	787.0	786.9
180°	784.7	784.7	784.7	784.7	784.7	784.7	784.7	784.7	784.7	784.7	784.7



TEST NUMBER: P332126-927

CATALOG NUMBER: S123DIW-S560D755U927-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	626.2	626.2	626.2	626.2	626.2	626.2	626.2	626.2	626.2	626.2	626.2
2.5°	598.8	598.6	600.2	599.0	600.2	598.6	598.8	600.5	600.9	601.2	601.2
5°	557.4	558.3	555.2	555.2	555.2	558.3	557.4	559.2	560.7	561.9	563.7
7.5°	520.5	519.1	519.3	517.6	519.3	519.1	520.5	521.9	523.9	526.5	529.0
10°	497.9	496.1	495.4	495.7	495.4	496.1	497.9	501.5	502.7	505.2	507.9
12.5°	479.2	478.8	474.8	474.9	474.8	478.8	479.2	480.1	482.8	487.9	491.2
15°	457.2	451.5	450.8	452.7	450.8	451.5	457.2	457.2	458.4	462.4	464.2
17.5°	435.2	432.1	432.4	431.4	432.4	432.1	435.2	435.7	436.7	439.9	442.3
20°	423.6	421.8	421.4	419.3	421.4	421.8	423.6	423.6	424.8	426.3	428.7
22.5°	412.9	412.3	412.4	410.1	412.4	412.3	412.9	413.6	414.8	415.8	417.6
25°	399.6	401.1	399.9	399.9	399.9	401.1	399.6	399.9	400.2	401.7	402.9
27.5°	390.6	390.5	389.9	389.9	389.9	390.5	390.6	389.8	389.5	389.0	388.7
30°	383.8	383.5	384.1	384.1	384.1	383.5	383.8	382.6	382.0	381.7	380.5
32.5°	377.0	377.4	377.6	377.8	377.6	377.4	377.0	375.6	374.5	373.7	372.7
35°	366.5	366.8	367.7	367.1	367.7	366.8	366.5	364.7	363.5	361.6	360.1
37.5°	352.3	353.7	353.4	353.9	353.4	353.7	352.3	351.7	350.5	349.2	347.4
40°	341.7	342.5	342.2	342.2	342.2	342.5	341.7	341.4	340.1	339.2	337.7
42.5°	330.7	331.4	330.6	330.1	330.6	331.4	330.7	330.2	329.5	327.8	326.1
45°	312.8	312.2	313.1	311.9	313.1	312.2	312.8	311.6	311.3	310.1	308.6
47.5°	292.8	293.4	293.7	294.5	293.7	293.4	292.8	292.9	291.2	290.5	290.0
50°	279.4	281.2	281.2	281.0	281.2	281.2	279.4	278.8	277.6	276.4	276.4
52.5°	266.3	267.2	268.4	268.3	268.4	267.2	266.3	265.2	264.0	262.3	261.8
55°	246.1	246.7	247.2	247.6	247.2	246.7	246.1	243.6	242.7	241.8	240.3
57.5°	225.1	224.8	226.2	226.7	226.2	224.8	225.1	222.8	221.5	218.7	218.3
60°	210.2	210.2	212.7	213.6	212.7	210.2	210.2	207.9	205.7	203.9	203.3
62.5°	194.5	195.4	197.9	196.6	197.9	195.4	194.5	191.8	190.2	187.9	186.3
65°	171.4	173.9	173.6	174.8	173.6	173.9	171.4	169.9	166.6	164.5	162.6
67.5°	147.3	148.9	151.1	151.2	151.1	148.9	147.3	144.9	142.8	140.5	138.3
70°	131.1	132.6	133.8	134.7	133.8	132.6	131.1	128.7	126.2	124.7	122.2
72.5°	115.3	116.1	119.0	117.7	119.0	116.1	115.3	112.4	110.4	109.2	106.5
75°	90.4	92.5	94.3	93.5	94.3	92.5	90.4	88.3	86.7	84.9	82.5
77.5°	66.9	69.0	69.9	69.1	69.9	69.0	66.9	65.5	64.7	61.1	60.8
80°	52.8	52.5	54.3	54.0	54.3	52.5	52.8	50.7	49.1	47.1	47.1
82.5°	38.7	38.4	39.3	39.5	39.3	38.4	38.7	37.5	35.6	34.6	33.9
85°	18.8	19.7	18.5	18.2	18.5	19.7	18.8	17.6	17.6	17.6	17.3
87.5°	7.7	7.8	7.6	7.4	7.6	7.8	7.7	7.7	8.6	7.7	7.6
90°	16.7	17.0	17.2	17.5	17.2	17.0	16.7	16.5	16.1	15.5	15.1
92.5°	18.9	19.0	19.2	19.3	19.2	19.0	18.9	18.7	18.2	17.4	16.6
95°	22.2	22.2	22.2	22.2	22.2	22.2	22.2	22.2	21.7	20.8	19.9
97.5°	23.6	23.8	23.9	24.0	23.9	23.8	23.6	23.5	22.9	21.9	20.8
100°	24.1	24.2	24.3	24.5	24.3	24.2	24.1	24.0	23.4	22.3	21.3
102.5°	24.2	24.5	24.7	25.0	24.7	24.5	24.2	24.0	25.5	28.8	31.9
105°	24.9	25.1	25.4	25.7	25.4	25.1	24.9	24.6	36.0	58.9	81.8
107.5°	132.4	115.1	97.8	80.6	97.8	115.1	132.4	149.7	166.8	183.5	200.3
110°	215.9	197.3	178.8	160.3	178.8	197.3	215.9	234.4	245.8	250.1	254.4



TEST NUMBER: P332126-927

CATALOG NUMBER: S123DIW-S560D755U927-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	286.8	282.9	278.9	275.0	278.9	282.9	286.8	290.7	292.6	292.6	292.5
115°	341.2	341.7	342.2	342.8	342.2	341.7	341.2	340.7	339.8	338.5	337.2
117.5°	380.5	380.6	380.6	380.8	380.6	380.6	380.5	380.3	379.8	378.7	377.7
120°	406.9	406.9	406.9	406.9	406.9	406.9	406.9	406.9	406.4	405.4	404.3
122.5°	432.2	432.3	432.5	432.5	432.5	432.3	432.2	432.1	431.7	430.9	430.2
125°	467.9	468.2	468.4	468.7	468.4	468.2	467.9	467.6	467.4	467.1	466.8
127.5°	504.2	503.9	503.7	503.4	503.7	503.9	504.2	504.5	504.4	504.0	503.6
130°	526.6	526.3	526.1	525.8	526.1	526.3	526.6	526.9	526.7	526.2	525.7
132.5°	547.4	547.1	546.7	546.3	546.7	547.1	547.4	547.8	547.7	547.2	546.7
135°	578.8	578.5	578.1	577.7	578.1	578.5	578.8	579.2	579.2	578.8	578.5
137.5°	608.0	607.7	607.4	607.2	607.4	607.7	608.0	608.2	608.1	607.4	606.8
140°	625.7	625.4	625.2	624.9	625.2	625.4	625.7	626.0	625.8	625.3	624.8
142.5°	642.3	642.0	641.6	641.2	641.6	642.0	642.3	642.7	642.6	642.2	641.8
145°	666.3	666.3	666.3	666.3	666.3	666.3	666.3	666.3	666.1	665.9	665.7
147.5°	686.7	686.1	685.6	684.9	685.6	686.1	686.7	687.3	687.5	687.2	687.0
150°	700.1	699.7	699.3	698.9	699.3	699.7	700.1	700.5	700.5	700.3	700.1
152.5°	711.9	711.3	710.7	710.1	710.7	711.3	711.9	712.5	712.6	712.1	711.6
155°	728.1	727.3	726.5	725.7	726.5	727.3	728.1	728.9	729.0	728.3	727.6
157.5°	742.0	740.9	740.0	738.9	740.0	740.9	742.0	743.0	743.1	742.3	741.6
160°	750.0	749.2	748.2	747.3	748.2	749.2	750.0	751.0	751.0	750.3	749.5
162.5°	757.6	756.9	756.1	755.3	756.1	756.9	757.6	758.4	758.4	757.6	756.7
165°	767.5	766.6	765.7	764.8	765.7	766.6	767.5	768.4	768.3	767.3	766.3
167.5°	774.8	773.7	772.7	771.7	772.7	773.7	774.8	775.9	775.9	774.8	773.7
170°	779.0	777.9	776.9	775.9	776.9	777.9	779.0	780.1	780.1	779.0	777.9
172.5°	781.6	780.5	779.3	778.2	779.3	780.5	781.6	782.8	782.8	781.8	780.8
175°	784.8	783.8	782.8	781.7	782.8	783.8	784.8	785.8	785.9	785.1	784.1
177.5°	785.8	784.8	783.8	782.8	783.8	784.8	785.8	786.9	787.0	786.2	785.4
180°	784.7	784.7	784.7	784.7	784.7	784.7	784.7	784.7	784.7	784.7	784.7



TEST NUMBER: P332126-927

CATALOG NUMBER: S123DIW-S560D755U927-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	626.2	626.2	626.2	626.2	626.2	626.2	626.2	626.2	626.2	626.2	626.2
2.5°	600.5	600.5	605.1	608.0	611.6	614.1	615.8	617.5	620.4	624.3	628.7
5°	566.2	567.4	574.0	580.7	587.1	592.6	597.1	602.5	609.3	617.4	626.5
7.5°	532.9	537.6	544.3	552.5	561.3	569.3	577.3	586.4	595.7	607.8	620.6
10°	511.5	516.7	524.9	535.2	544.6	554.0	564.0	573.7	585.6	599.8	616.2
12.5°	492.8	497.7	506.2	517.5	526.4	536.8	548.3	560.9	574.2	591.4	609.9
15°	466.9	472.7	483.0	488.5	502.2	514.6	525.2	543.4	560.4	578.0	599.5
17.5°	445.7	448.9	457.2	467.4	477.6	491.5	505.5	520.6	537.6	559.1	586.1
20°	431.1	433.9	443.0	453.6	464.5	477.3	489.7	504.9	523.9	546.8	575.8
22.5°	420.2	423.2	429.1	440.5	450.7	461.2	473.6	491.8	512.1	534.3	565.9
25°	404.4	406.2	410.2	419.3	428.4	440.2	451.1	468.2	489.1	515.2	546.8
27.5°	389.4	391.2	394.5	401.0	409.6	419.1	431.0	445.4	466.7	495.0	528.5
30°	380.5	380.8	383.8	389.8	397.1	405.0	416.0	432.4	452.3	481.2	516.4
32.5°	372.7	371.5	373.6	378.2	385.2	393.2	402.1	418.3	437.6	465.9	502.1
35°	359.5	358.9	358.0	361.9	368.0	374.1	382.0	394.1	416.0	442.4	480.3
37.5°	346.1	344.7	343.0	344.8	349.6	355.9	362.7	373.5	392.4	421.4	457.7
40°	336.2	334.9	334.1	333.4	337.7	343.7	348.9	359.3	376.8	404.4	440.2
42.5°	325.3	324.6	323.4	322.5	326.1	330.7	336.0	345.2	362.7	388.6	422.6
45°	307.7	307.0	306.4	305.9	307.9	312.2	316.5	323.1	338.3	363.5	394.1
47.5°	288.0	287.2	287.5	286.5	288.6	291.4	294.5	301.6	316.2	336.4	358.9
50°	273.9	273.7	273.7	273.7	274.3	277.6	280.4	285.8	299.1	319.5	335.6
52.5°	260.6	259.4	259.4	259.8	260.9	263.1	264.8	270.8	282.4	299.1	313.7
55°	239.7	237.3	236.6	237.3	238.2	240.0	241.8	246.7	256.7	269.1	277.6
57.5°	216.5	215.2	214.4	214.5	215.0	216.4	217.9	223.2	231.0	237.5	243.0
60°	200.3	200.8	198.1	198.8	198.8	199.9	202.1	205.4	212.1	216.7	222.1
62.5°	185.0	184.1	183.3	182.4	182.4	182.9	185.8	188.4	194.1	196.5	200.7
65°	161.1	161.1	159.3	159.9	160.2	158.0	159.6	162.6	166.3	167.2	171.1
67.5°	137.0	136.1	135.1	134.2	134.2	134.0	134.8	136.3	139.0	139.3	142.4
70°	120.4	119.9	119.5	118.7	117.4	118.9	118.0	119.5	121.0	121.4	123.2
72.5°	104.4	103.9	103.3	102.3	101.9	101.7	101.8	103.5	104.6	104.1	106.2
75°	81.6	81.0	80.4	78.9	78.9	78.0	78.3	79.5	80.7	79.8	81.6
77.5°	60.0	58.1	58.0	58.4	57.4	57.5	57.2	57.0	57.5	57.6	59.3
80°	46.1	44.0	44.6	44.3	44.0	43.7	43.1	43.4	43.7	44.0	44.9
82.5°	33.3	33.0	32.5	32.4	32.1	31.3	31.0	31.5	31.8	31.6	32.3
85°	17.0	16.1	16.7	16.4	16.7	16.4	15.4	15.4	16.1	15.8	16.4
87.5°	8.0	7.9	7.3	7.2	6.7	6.6	6.0	6.0	5.9	5.7	5.9
90°	14.5	14.0	12.3	10.6	9.0	7.3	5.8	4.4	3.2	1.9	0.6
92.5°	15.8	14.9	13.6	12.4	11.1	9.8	9.4	9.7	10.1	10.5	10.9
95°	19.0	18.1	16.6	15.2	13.8	12.4	14.3	19.6	25.0	30.3	35.6
97.5°	19.8	18.8	28.1	37.4	46.7	56.1	61.9	64.3	66.7	69.1	71.5
100°	20.3	19.3	39.5	59.7	79.9	100.1	108.8	106.3	103.7	101.1	98.5
102.5°	35.2	38.3	60.4	82.5	104.6	126.7	136.7	134.9	133.0	131.2	129.3
105°	104.7	127.7	139.3	151.0	162.6	174.3	179.4	178.0	176.6	175.2	173.7
107.5°	217.1	234.0	232.2	230.3	228.5	226.6	225.1	224.0	222.8	221.7	220.5
110°	258.6	262.9	261.5	260.1	258.6	257.2	256.0	254.9	253.9	252.9	251.8



TEST NUMBER: P332126-927

CATALOG NUMBER: S123DIW-S560D755U927-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	292.4	292.3	290.9	289.5	288.0	286.6	285.4	284.5	283.5	282.6	281.7
115°	335.9	334.6	333.4	332.2	331.1	329.9	329.0	328.2	327.4	326.6	325.8
117.5°	376.7	375.7	375.0	374.5	373.8	373.3	372.5	371.5	370.6	369.6	368.7
120°	403.3	402.2	401.9	401.5	401.1	400.7	399.9	398.7	397.6	396.4	395.2
122.5°	429.5	428.8	428.3	427.9	427.3	426.8	426.1	425.2	424.2	423.3	422.3
125°	466.6	466.4	465.8	465.3	464.8	464.3	463.5	462.5	461.4	460.4	459.4
127.5°	503.1	502.7	502.1	501.5	500.9	500.3	499.4	498.4	497.3	496.3	495.3
130°	525.1	524.7	524.1	523.6	523.1	522.6	521.8	520.8	519.8	518.7	517.6
132.5°	546.1	545.7	545.2	544.8	544.4	544.0	543.3	542.2	541.1	540.1	539.1
135°	578.1	577.7	577.2	576.6	576.2	575.6	575.0	574.2	573.4	572.7	571.9
137.5°	606.2	605.5	605.3	605.0	604.7	604.4	603.8	602.8	601.8	600.8	599.8
140°	624.2	623.8	623.4	623.0	622.6	622.2	621.6	620.8	620.0	619.2	618.5
142.5°	641.4	641.0	640.6	640.2	639.8	639.4	638.9	638.1	637.3	636.5	635.7
145°	665.4	665.1	664.9	664.6	664.3	664.1	663.5	662.6	661.7	660.8	659.9
147.5°	686.7	686.4	686.2	686.0	685.7	685.4	685.0	684.4	683.8	683.2	682.6
150°	699.8	699.5	699.3	699.0	698.8	698.5	698.2	697.8	697.4	697.0	696.6
152.5°	711.1	710.7	710.6	710.4	710.3	710.1	710.0	709.7	709.6	709.4	709.2
155°	727.0	726.4	726.2	726.1	726.0	725.8	725.9	726.1	726.4	726.7	726.9
157.5°	740.8	740.0	740.1	740.2	740.4	740.5	740.6	740.6	740.6	740.7	740.7
160°	748.7	747.9	748.1	748.1	748.3	748.5	748.5	748.7	748.8	748.9	749.1
162.5°	755.8	754.9	755.0	755.2	755.3	755.4	755.7	756.0	756.3	756.7	757.0
165°	765.2	764.2	764.4	764.5	764.6	764.8	765.0	765.4	765.8	766.2	766.6
167.5°	772.7	771.7	771.7	771.7	771.7	771.7	772.0	772.5	773.0	773.5	774.0
170°	776.9	775.9	775.9	775.9	775.9	775.9	776.2	776.7	777.2	777.7	778.2
172.5°	779.7	778.7	778.6	778.5	778.4	778.2	778.6	779.2	779.7	780.4	781.0
175°	783.2	782.3	782.2	782.0	781.9	781.8	782.0	782.7	783.3	783.9	784.7
177.5°	784.5	783.7	783.6	783.5	783.4	783.3	783.5	784.0	784.5	785.1	785.5
180°	784.7	784.7	784.7	784.7	784.7	784.7	784.7	784.7	784.7	784.7	784.7



TEST NUMBER: P332126-927

CATALOG NUMBER: S123DIW-S560D755U927-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	626.2	626.2	626.2	626.2	626.2	626.2	626.2	626.2	626.2	626.2	626.2
2.5°	630.1	631.3	635.4	638.3	641.7	643.7	645.6	647.1	649.0	649.5	656.6
5°	632.9	639.0	649.6	657.4	667.2	677.8	685.1	688.4	697.2	704.5	719.1
7.5°	632.1	645.0	661.1	677.7	695.5	712.0	726.4	743.3	755.4	773.6	791.5
10°	631.4	648.6	669.3	690.5	715.4	738.5	759.1	782.2	801.3	826.5	848.0
12.5°	629.2	650.1	678.7	703.9	734.1	765.9	796.5	826.1	843.0	884.9	904.8
15°	623.8	648.6	684.4	722.7	764.3	801.9	840.7	871.6	921.7	958.5	981.8
17.5°	613.5	648.3	690.8	736.9	787.4	837.0	881.0	928.0	981.1	1025.5	1072.9
20°	608.6	646.8	694.2	745.1	797.6	853.7	903.8	960.3	1018.2	1061.9	1122.6
22.5°	599.7	642.9	694.0	750.8	806.8	864.9	923.5	980.4	1047.3	1107.6	1165.3
25°	584.9	633.5	686.3	749.7	815.6	873.8	943.9	1019.5	1089.3	1166.6	1224.2
27.5°	569.6	621.4	674.3	733.2	804.1	873.2	961.4	1046.7	1132.0	1198.9	1241.5
30°	557.6	608.0	662.7	722.1	792.2	874.4	973.0	1066.1	1149.3	1206.7	1230.6
32.5°	544.8	595.9	644.2	706.5	781.3	873.7	980.3	1077.5	1150.2	1188.4	1183.8
35°	524.6	567.4	614.4	674.5	762.5	868.3	984.5	1078.6	1123.2	1115.0	1053.1
37.5°	495.4	531.5	577.7	643.5	740.6	857.1	976.0	1046.6	1043.7	977.0	887.3
40°	477.3	507.9	552.5	621.7	723.6	849.9	962.7	1008.5	969.7	876.5	769.1
42.5°	453.4	481.6	526.2	597.4	705.0	835.0	937.2	950.5	874.5	767.3	668.9
45°	416.6	441.5	487.6	561.0	676.9	802.8	875.0	842.6	740.3	629.5	554.6
47.5°	376.9	402.8	447.2	522.6	636.4	754.3	788.7	719.7	614.7	524.9	456.1
50°	352.0	376.8	420.2	496.4	609.0	714.5	728.8	639.6	543.1	464.2	407.7
52.5°	326.7	350.1	392.8	469.2	576.9	668.4	659.6	568.7	480.0	412.7	368.4
55°	289.1	311.3	352.0	423.6	521.6	594.1	562.2	475.5	402.0	349.8	316.2
57.5°	255.6	276.8	311.8	376.5	461.7	511.5	471.0	397.9	339.5	299.4	274.3
60°	232.7	251.5	284.9	345.0	419.0	456.9	416.8	352.3	303.1	270.9	248.5
62.5°	211.1	227.5	258.4	312.9	377.2	409.1	368.6	313.9	272.0	243.5	224.4
65°	178.4	193.3	220.5	263.1	315.8	337.1	302.2	257.9	225.5	204.2	191.5
67.5°	148.5	161.1	184.7	218.2	257.1	272.5	246.0	211.7	187.2	170.2	160.0
70°	128.7	139.6	158.0	186.9	222.1	233.9	209.1	180.9	163.0	149.2	139.9
72.5°	111.9	119.9	136.7	159.0	188.4	197.7	180.4	155.6	138.9	128.7	121.2
75°	85.2	91.9	102.8	120.7	141.1	146.6	133.5	118.0	106.8	99.5	93.7
77.5°	61.5	66.4	74.3	85.3	99.4	104.3	96.1	85.7	77.6	72.6	69.4
80°	46.4	50.4	57.0	66.1	74.6	77.4	72.5	64.6	58.9	56.2	53.4
82.5°	34.3	36.5	40.6	46.7	52.5	55.8	51.7	46.9	43.8	41.4	40.3
85°	17.3	18.5	20.4	22.7	26.4	27.6	26.1	24.9	23.1	21.5	21.5
87.5°	6.7	7.0	7.9	8.7	10.0	11.0	11.1	10.9	11.0	10.9	10.8
90°	1.9	3.2	4.4	5.8	7.3	9.0	10.6	12.3	14.0	14.5	15.1
92.5°	10.5	10.1	9.7	9.4	9.8	11.1	12.4	13.6	14.9	15.8	16.6
95°	30.3	25.0	19.6	14.3	12.4	13.8	15.2	16.6	18.1	19.0	19.9
97.5°	69.1	66.7	64.3	61.9	56.1	46.7	37.4	28.1	18.8	19.8	20.8
100°	101.1	103.7	106.3	108.8	100.1	79.9	59.7	39.5	19.3	20.3	21.3
102.5°	131.2	133.0	134.9	136.7	126.7	104.6	82.5	60.4	38.3	35.2	31.9
105°	175.2	176.6	178.0	179.4	174.3	162.6	151.0	139.3	127.7	104.7	81.8
107.5°	221.7	222.8	224.0	225.1	226.6	228.5	230.3	232.2	234.0	217.1	200.3
110°	252.9	253.9	254.9	256.0	257.2	258.6	260.1	261.5	262.9	258.6	254.4





TEST NUMBER: P332126-927

CATALOG NUMBER: S123DIW-S560D755U927-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	282.6	283.5	284.5	285.4	286.6	288.0	289.5	290.9	292.3	292.4	292.5
115°	326.6	327.4	328.2	329.0	329.9	331.1	332.2	333.4	334.6	335.9	337.2
117.5°	369.6	370.6	371.5	372.5	373.3	373.8	374.5	375.0	375.7	376.7	377.7
120°	396.4	397.6	398.7	399.9	400.7	401.1	401.5	401.9	402.2	403.3	404.3
122.5°	423.3	424.2	425.2	426.1	426.8	427.3	427.9	428.3	428.8	429.5	430.2
125°	460.4	461.4	462.5	463.5	464.3	464.8	465.3	465.8	466.4	466.6	466.8
127.5°	496.3	497.3	498.4	499.4	500.3	500.9	501.5	502.1	502.7	503.1	503.6
130°	518.7	519.8	520.8	521.8	522.6	523.1	523.6	524.1	524.7	525.1	525.7
132.5°	540.1	541.1	542.2	543.3	544.0	544.4	544.8	545.2	545.7	546.1	546.7
135°	572.7	573.4	574.2	575.0	575.6	576.2	576.6	577.2	577.7	578.1	578.5
137.5°	600.8	601.8	602.8	603.8	604.4	604.7	605.0	605.3	605.5	606.2	606.8
140°	619.2	620.0	620.8	621.6	622.2	622.6	623.0	623.4	623.8	624.2	624.8
142.5°	636.5	637.3	638.1	638.9	639.4	639.8	640.2	640.6	641.0	641.4	641.8
145°	660.8	661.7	662.6	663.5	664.1	664.3	664.6	664.9	665.1	665.4	665.7
147.5°	683.2	683.8	684.4	685.0	685.4	685.7	686.0	686.2	686.4	686.7	687.0
150°	697.0	697.4	697.8	698.2	698.5	698.8	699.0	699.3	699.5	699.8	700.1
152.5°	709.4	709.6	709.7	710.0	710.1	710.3	710.4	710.6	710.7	711.1	711.6
155°	726.7	726.4	726.1	725.9	725.8	726.0	726.1	726.2	726.4	727.0	727.6
157.5°	740.7	740.6	740.6	740.6	740.5	740.4	740.2	740.1	740.0	740.8	741.6
160°	748.9	748.8	748.7	748.5	748.5	748.3	748.1	748.1	747.9	748.7	749.5
162.5°	756.7	756.3	756.0	755.7	755.4	755.3	755.2	755.0	754.9	755.8	756.7
165°	766.2	765.8	765.4	765.0	764.8	764.6	764.5	764.4	764.2	765.2	766.3
167.5°	773.5	773.0	772.5	772.0	771.7	771.7	771.7	771.7	771.7	772.7	773.7
170°	777.7	777.2	776.7	776.2	775.9	775.9	775.9	775.9	775.9	776.9	777.9
172.5°	780.4	779.7	779.2	778.6	778.2	778.4	778.5	778.6	778.7	779.7	780.8
175°	783.9	783.3	782.7	782.0	781.8	781.9	782.0	782.2	782.3	783.2	784.1
177.5°	785.1	784.5	784.0	783.5	783.3	783.4	783.5	783.6	783.7	784.5	785.4
180°	784.7	784.7	784.7	784.7	784.7	784.7	784.7	784.7	784.7	784.7	784.7



TEST NUMBER: P332126-927

CATALOG NUMBER: S123DIW-S560D755U927-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	626.2	626.2	626.2	626.2	626.2	626.2	626.2
2.5°	659.0	659.3	661.9	663.8	662.9	664.1	664.6
5°	719.9	730.9	736.7	740.9	741.2	741.5	743.9
7.5°	806.4	818.2	826.7	839.7	843.6	848.0	846.8
10°	869.6	886.8	901.7	909.6	918.1	930.5	920.5
12.5°	928.5	959.2	981.8	994.0	1002.1	1004.6	999.7
15°	1025.8	1065.9	1087.4	1086.8	1114.1	1125.9	1107.4
17.5°	1115.0	1152.0	1181.5	1196.7	1219.5	1224.6	1222.3
20°	1169.6	1210.0	1233.0	1259.1	1271.0	1281.6	1283.4
22.5°	1216.7	1252.9	1277.7	1299.4	1309.3	1314.3	1317.4
25°	1265.2	1293.7	1308.6	1316.1	1318.9	1318.3	1314.3
27.5°	1261.9	1264.0	1247.7	1231.6	1217.2	1200.9	1195.4
30°	1229.1	1203.6	1158.1	1132.3	1094.4	1064.3	1076.5
32.5°	1142.9	1092.2	1041.1	984.7	938.0	924.8	911.4
35°	975.4	886.2	834.1	773.4	749.1	724.8	708.1
37.5°	789.2	720.2	658.2	618.5	594.2	578.9	570.6
40°	682.4	620.1	569.2	537.0	518.5	501.2	498.8
42.5°	597.1	539.3	501.0	475.4	457.6	450.3	444.9
45°	489.1	448.7	422.9	404.7	392.9	388.3	382.3
47.5°	414.0	385.5	366.1	353.7	344.8	341.4	340.9
50°	372.0	348.3	334.1	324.3	317.3	316.2	311.3
52.5°	340.4	319.9	308.8	300.3	295.2	291.8	290.4
55°	295.5	281.9	271.9	267.0	263.1	259.7	259.7
57.5°	258.6	247.2	240.5	236.4	235.2	232.8	231.3
60°	235.8	226.0	220.9	217.2	214.8	215.1	212.4
62.5°	213.4	207.1	202.2	198.5	195.7	195.7	195.9
65°	181.7	176.9	173.3	172.1	170.2	168.1	168.7
67.5°	154.0	149.5	146.6	144.6	143.9	142.8	144.6
70°	134.1	130.8	128.7	126.8	126.2	126.5	128.0
72.5°	115.9	113.5	112.2	111.3	110.0	110.0	111.1
75°	91.0	89.2	88.0	87.1	86.7	86.7	86.7
77.5°	66.9	66.5	65.9	64.6	64.6	65.0	65.0
80°	52.8	51.9	51.6	50.9	50.1	49.4	50.9
82.5°	39.5	38.5	38.3	38.1	36.7	36.6	37.9
85°	21.2	20.4	20.6	20.4	20.4	20.0	20.0
87.5°	10.6	10.5	10.3	10.6	10.5	10.2	10.8
90°	15.5	16.1	16.5	16.7	17.0	17.2	17.5
92.5°	17.4	18.2	18.7	18.9	19.0	19.2	19.3
95°	20.8	21.7	22.2	22.2	22.2	22.2	22.2
97.5°	21.9	22.9	23.5	23.6	23.8	23.9	24.0
100°	22.3	23.4	24.0	24.1	24.2	24.3	24.5
102.5°	28.8	25.5	24.0	24.2	24.5	24.7	25.0
105°	58.9	36.0	24.6	24.9	25.1	25.4	25.7
107.5°	183.5	166.8	149.7	132.4	115.1	97.8	80.6
110°	250.1	245.8	234.4	215.9	197.3	178.8	160.3



TEST NUMBER: P332126-927

CATALOG NUMBER: S123DIW-S560D755U927-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	292.6	292.6	290.7	286.8	282.9	278.9	275.0
115°	338.5	339.8	340.7	341.2	341.7	342.2	342.8
117.5°	378.7	379.8	380.3	380.5	380.6	380.6	380.8
120°	405.4	406.4	406.9	406.9	406.9	406.9	406.9
122.5°	430.9	431.7	432.1	432.2	432.3	432.5	432.5
125°	467.1	467.4	467.6	467.9	468.2	468.4	468.7
127.5°	504.0	504.4	504.5	504.2	503.9	503.7	503.4
130°	526.2	526.7	526.9	526.6	526.3	526.1	525.8
132.5°	547.2	547.7	547.8	547.4	547.1	546.7	546.3
135°	578.8	579.2	579.2	578.8	578.5	578.1	577.7
137.5°	607.4	608.1	608.2	608.0	607.7	607.4	607.2
140°	625.3	625.8	626.0	625.7	625.4	625.2	624.9
142.5°	642.2	642.6	642.7	642.3	642.0	641.6	641.2
145°	665.9	666.1	666.3	666.3	666.3	666.3	666.3
147.5°	687.2	687.5	687.3	686.7	686.1	685.6	684.9
150°	700.3	700.5	700.5	700.1	699.7	699.3	698.9
152.5°	712.1	712.6	712.5	711.9	711.3	710.7	710.1
155°	728.3	729.0	728.9	728.1	727.3	726.5	725.7
157.5°	742.3	743.1	743.0	742.0	740.9	740.0	738.9
160°	750.3	751.0	751.0	750.0	749.2	748.2	747.3
162.5°	757.6	758.4	758.4	757.6	756.9	756.1	755.3
165°	767.3	768.3	768.4	767.5	766.6	765.7	764.8
167.5°	774.8	775.9	775.9	774.8	773.7	772.7	771.7
170°	779.0	780.1	780.1	779.0	777.9	776.9	775.9
172.5°	781.8	782.8	782.8	781.6	780.5	779.3	778.2
175°	785.1	785.9	785.8	784.8	783.8	782.8	781.7
177.5°	786.2	787.0	786.9	785.8	784.8	783.8	782.8
180°	784.7	784.7	784.7	784.7	784.7	784.7	784.7

(END OF REPORT)