

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332168-927

Luminaire Tested: **S123DIW-S775D1320U927-4F0-1E-UDD-A**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332168-927
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-5,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123DIW-S775D1320U927-4F0-1E-UDD-A
Description: DEFINE 3 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 775 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 1320 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6768.4 lumens
Efficiency: N/A
Efficacy: 110.2 lumens/watt
Spacing Criteria (0/90/45): 1.37 / 1.23 / 1.49
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 61.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332168-927

CATALOG NUMBER: S123DIW-S775D1320U927-4F0-1E-UDD-A

Luminous Intensity Polar Plot





TEST NUMBER: P332168-927

CATALOG NUMBER: S123DIW-S775D1320U927-4F0-1E-UDD-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	104	104	104	104	95	95	95	95	77	77	77	60	60	60	45	45	45	38
1	95	91	87	84	86	83	80	77	68	65	63	53	52	51	40	39	39	33
2	87	80	74	69	79	73	68	63	59	56	53	47	45	43	36	34	33	28
3	79	70	63	58	72	64	58	53	53	48	44	42	39	36	32	30	28	24
4	73	62	55	49	66	57	50	45	47	42	38	37	34	31	29	26	24	20
5	67	55	48	42	60	51	44	39	42	37	33	33	30	27	26	23	21	18
6	61	50	42	36	56	46	39	34	38	32	29	30	26	24	23	21	19	16
7	57	45	37	32	51	41	34	29	34	29	25	27	24	21	21	19	17	14
8	53	41	33	28	48	37	31	26	31	26	22	25	21	19	20	17	15	12
9	49	37	30	25	44	34	28	23	28	23	20	23	19	17	18	15	13	11
10	46	34	27	22	41	31	25	21	26	21	18	21	18	15	17	14	12	10

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	9214	9214	9214	9214
5°	10988	9253	8200	9253
10°	13753	9206	7406	9206
15°	16868	9132	6896	9132
20°	20095	9016	6565	9016
25°	21338	8875	6492	8875
30°	18288	8772	6527	8772
35°	12720	8627	6594	8627
40°	9580	8455	6573	8455
45°	7954	8202	6491	8202
50°	7125	7681	6430	7681
55°	6662	7122	6351	7122
60°	6250	6536	6286	6536
65°	5873	5957	6082	5957
70°	5508	5297	5794	5297
75°	4932	4637	5311	4637
80°	4320	3806	4575	3806
85°	3384	2766	3075	2766



TEST NUMBER: P332168-927

CATALOG NUMBER: S123DIW-S775D1320U927-4F0-1E-UDD-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	84.3	1.2
10°-20°	270.4	4.0
20°-30°	453.8	6.7
30°-40°	513.8	7.6
40°-50°	460.8	6.8
50°-60°	371.8	5.5
60°-70°	259.1	3.8
70°-80°	136.2	2.0
80°-90°	37.1	0.5
90°-100°	49.8	0.7
100°-110°	237.6	3.5
110°-120°	570.6	8.4
120°-130°	726.7	10.7
130°-140°	776.4	11.5
140°-150°	726.0	10.7
150°-160°	585.6	8.7
160°-170°	378.0	5.6
170°-180°	130.3	1.9
0°-30°	808.5	11.9
0°-40°	1322.3	19.5
0°-60°	2154.9	31.8
0°-90°	2587.4	38.2
90°-120°	858.1	12.7
90°-150°	3087.2	45.6
90°-180°	4181.0	61.8
0°-180°	6768.4	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	856	856	856	856	856	
5°	1017	856	759	856	1017	105
15°	1514	820	619	820	1514	437
25°	1797	747	547	747	1797	788
35°	968	656	502	656	968	629
45°	522	539	426	539	522	413
55°	355	380	338	380	355	319
65°	231	234	239	234	231	230
75°	119	112	128	112	119	127
85°	27	22	25	22	27	33
90°	31	1	31	1	31	15
95°	39	62	39	62	39	32
105°	45	304	45	304	45	102
115°	599	569	599	569	599	553
125°	819	803	819	803	819	731
135°	1010	999	1010	999	1010	778
145°	1164	1153	1164	1153	1164	727
155°	1268	1270	1268	1270	1268	585
165°	1336	1340	1336	1340	1336	377
175°	1366	1371	1366	1371	1366	130
180°	1371	1371	1371	1371	1371	



TEST NUMBER: P332168-927

CATALOG NUMBER: S123DIW-S775D1320U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	856.0	856.0	856.0	856.0	856.0	856.0	856.0	856.0	856.0	856.0	856.0
2.5°	908.4	907.8	906.1	907.4	904.8	901.1	900.8	897.5	887.8	887.2	884.6
5°	1016.9	1013.6	1013.2	1012.7	1006.9	999.1	984.1	982.9	963.0	953.0	941.0
7.5°	1157.4	1159.1	1153.1	1147.8	1130.0	1118.3	1102.3	1081.8	1057.4	1032.6	1016.1
10°	1258.3	1271.9	1255.0	1243.3	1232.6	1212.2	1188.6	1159.1	1129.7	1095.3	1069.1
12.5°	1366.4	1373.2	1369.8	1358.8	1342.0	1311.1	1269.2	1236.8	1209.7	1152.3	1129.2
15°	1513.7	1539.1	1522.9	1485.5	1486.4	1456.9	1402.2	1342.0	1310.1	1259.9	1191.5
17.5°	1670.6	1673.8	1666.9	1635.9	1615.1	1574.6	1524.1	1466.5	1401.8	1341.0	1268.4
20°	1754.3	1751.8	1737.3	1721.1	1685.4	1653.9	1598.8	1534.5	1451.5	1391.8	1312.6
22.5°	1800.7	1796.6	1789.7	1776.2	1746.4	1712.6	1663.1	1592.8	1513.9	1431.6	1340.1
25°	1796.6	1802.0	1802.8	1799.0	1788.7	1768.4	1729.4	1673.4	1594.6	1488.8	1393.4
27.5°	1634.0	1641.6	1663.8	1683.5	1705.4	1727.8	1724.8	1697.0	1638.7	1547.4	1430.8
30°	1471.4	1454.8	1495.9	1547.8	1583.0	1645.2	1680.1	1682.1	1649.3	1571.0	1457.3
32.5°	1245.8	1264.1	1282.2	1346.0	1423.1	1492.9	1562.3	1618.1	1624.4	1572.3	1472.9
35°	968.0	990.8	1024.0	1057.1	1140.1	1211.4	1333.3	1439.5	1524.1	1535.3	1474.3
37.5°	780.0	791.3	812.3	845.5	899.8	984.4	1078.7	1212.9	1335.5	1426.6	1430.6
40°	681.8	685.2	708.8	734.0	778.0	847.7	932.7	1051.3	1198.1	1325.5	1378.6
42.5°	608.2	615.4	625.5	649.7	684.8	737.2	816.3	914.3	1048.8	1195.4	1299.3
45°	522.5	530.8	537.1	553.3	578.1	613.4	668.5	758.1	860.5	1011.9	1151.7
47.5°	466.0	466.7	471.3	483.5	500.4	526.9	565.9	623.4	717.5	840.2	983.7
50°	425.5	432.1	433.8	443.3	456.6	476.1	508.4	557.4	634.5	742.4	874.3
52.5°	397.0	398.9	403.6	410.5	422.1	437.3	465.3	503.7	564.2	656.1	777.4
55°	355.0	355.0	359.6	365.0	371.6	385.2	403.9	432.1	478.2	549.5	649.9
57.5°	316.2	318.2	321.5	323.1	328.8	337.9	353.4	374.9	409.2	464.1	543.8
60°	290.3	294.1	293.7	296.9	301.9	309.0	322.3	339.7	370.3	414.3	481.5
62.5°	267.8	267.5	267.4	271.4	276.4	283.1	291.7	306.8	332.9	371.9	429.0
65°	230.6	229.7	232.7	235.1	236.8	241.8	248.4	261.7	279.1	308.2	352.5
67.5°	197.6	195.2	196.8	197.6	200.4	204.3	210.5	218.7	232.6	255.9	289.3
70°	175.0	172.9	172.5	173.3	175.9	178.7	183.3	191.2	204.1	222.7	247.2
72.5°	151.8	150.4	150.3	152.1	153.3	155.2	158.4	165.6	175.9	189.9	212.7
75°	118.6	118.6	118.6	119.0	120.3	121.9	124.5	128.2	136.0	146.0	161.3
77.5°	88.9	88.8	88.3	88.2	90.1	90.9	91.4	94.9	99.3	106.0	117.2
80°	69.7	67.6	68.4	69.7	70.5	70.9	72.2	73.0	76.8	80.5	88.3
82.5°	51.7	50.0	50.1	52.1	52.3	52.7	53.9	55.1	56.5	59.9	64.1
85°	27.4	27.4	27.8	27.8	28.2	27.8	29.0	29.5	29.5	31.5	34.0
87.5°	16.1	15.3	15.5	15.8	15.4	15.6	15.7	15.8	16.0	16.2	15.9
90°	30.6	30.1	29.6	29.2	28.8	28.0	27.2	26.2	25.3	24.5	21.5
92.5°	33.8	33.5	33.3	33.0	32.7	31.8	30.4	29.0	27.5	26.1	23.8
95°	38.7	38.7	38.7	38.7	38.7	37.9	36.4	34.8	33.2	31.6	29.1
97.5°	42.0	41.7	41.5	41.3	41.0	40.0	38.3	36.4	34.6	32.8	49.1
100°	42.8	42.5	42.3	42.1	41.9	40.9	39.1	37.2	35.4	33.6	68.9
102.5°	43.6	43.2	42.8	42.4	42.0	44.6	50.1	55.8	61.4	67.0	105.6
105°	44.8	44.4	43.9	43.5	43.0	62.8	102.9	142.9	183.0	223.1	243.4
107.5°	140.8	171.0	201.1	231.4	261.6	291.4	320.8	350.1	379.5	408.8	405.7
110°	280.1	312.5	344.8	377.2	409.6	429.5	437.0	444.4	451.9	459.4	456.9



TEST NUMBER: P332168-927

CATALOG NUMBER: S123DIW-S775D1320U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	480.6	487.4	494.2	501.1	507.9	511.3	511.1	511.0	510.9	510.7	508.3
115°	599.0	598.0	597.1	596.2	595.3	593.7	591.4	589.2	586.9	584.7	582.7
117.5°	665.4	665.2	665.0	664.8	664.6	663.6	661.8	660.0	658.2	656.4	655.4
120°	711.0	711.0	711.0	711.0	711.0	710.1	708.3	706.5	704.6	702.8	702.2
122.5°	755.8	755.7	755.4	755.3	755.1	754.4	753.1	751.9	750.6	749.3	748.5
125°	819.0	818.5	818.1	817.6	817.1	816.7	816.3	815.8	815.3	814.9	814.0
127.5°	879.6	880.1	880.6	881.1	881.5	881.4	880.6	879.9	879.2	878.5	877.3
130°	918.8	919.2	919.7	920.1	920.6	920.4	919.5	918.5	917.7	916.7	915.8
132.5°	954.7	955.3	955.9	956.6	957.2	957.0	956.2	955.2	954.3	953.4	952.7
135°	1009.5	1010.1	1010.8	1011.5	1012.2	1012.2	1011.5	1010.8	1010.1	1009.5	1008.5
137.5°	1061.0	1061.4	1061.9	1062.3	1062.8	1062.5	1061.4	1060.3	1059.2	1058.1	1057.6
140°	1091.9	1092.4	1092.8	1093.3	1093.8	1093.5	1092.7	1091.7	1090.8	1089.9	1089.3
142.5°	1120.5	1121.1	1121.7	1122.4	1123.0	1123.0	1122.2	1121.5	1120.8	1120.1	1119.4
145°	1164.3	1164.3	1164.3	1164.3	1164.3	1164.0	1163.6	1163.2	1162.7	1162.2	1161.8
147.5°	1196.8	1197.9	1199.0	1200.0	1201.0	1201.3	1200.9	1200.4	1200.0	1199.5	1199.0
150°	1221.3	1222.0	1222.7	1223.4	1224.0	1224.2	1223.7	1223.2	1222.8	1222.3	1221.9
152.5°	1240.9	1241.9	1242.9	1244.0	1245.1	1245.2	1244.4	1243.5	1242.7	1241.9	1241.6
155°	1268.2	1269.6	1270.9	1272.2	1273.6	1273.7	1272.6	1271.5	1270.3	1269.2	1269.0
157.5°	1291.2	1292.9	1294.7	1296.5	1298.2	1298.5	1297.1	1295.8	1294.3	1293.0	1293.2
160°	1305.8	1307.4	1309.0	1310.6	1312.2	1312.3	1311.0	1309.6	1308.2	1306.9	1307.1
162.5°	1319.7	1321.1	1322.5	1323.9	1325.3	1325.2	1323.7	1322.2	1320.6	1319.1	1319.3
165°	1336.4	1338.0	1339.6	1341.2	1342.7	1342.7	1340.8	1339.0	1337.2	1335.4	1335.6
167.5°	1348.5	1350.3	1352.1	1353.8	1355.7	1355.7	1353.8	1352.1	1350.3	1348.5	1348.5
170°	1355.7	1357.6	1359.4	1361.2	1363.0	1363.0	1361.2	1359.4	1357.6	1355.7	1355.7
172.5°	1359.9	1361.8	1363.8	1365.8	1367.8	1367.9	1366.1	1364.3	1362.5	1360.7	1360.5
175°	1366.0	1367.8	1369.6	1371.4	1373.2	1373.3	1371.7	1370.2	1368.6	1367.0	1366.8
177.5°	1367.8	1369.6	1371.4	1373.2	1375.1	1375.2	1373.8	1372.3	1370.9	1369.4	1369.2
180°	1371.0	1371.0	1371.0	1371.0	1371.0	1371.0	1371.0	1371.0	1371.0	1371.0	1371.0



TEST NUMBER: P332168-927

CATALOG NUMBER: S123DIW-S775D1320U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	856.0	856.0	856.0	856.0	856.0	856.0	856.0	856.0	856.0	856.0	856.0
2.5°	882.5	879.9	877.2	872.6	868.6	862.9	861.3	859.3	853.3	848.0	844.1
5°	936.4	926.5	912.0	898.7	888.0	873.4	865.1	856.4	844.0	832.7	823.6
7.5°	992.8	973.3	950.7	926.3	903.6	881.7	864.0	848.3	830.8	814.4	801.5
10°	1037.6	1009.4	977.9	943.9	914.9	886.7	863.0	842.3	819.9	800.4	784.3
12.5°	1088.7	1046.9	1003.5	962.2	927.8	888.7	860.1	833.7	808.3	784.8	766.7
15°	1149.2	1096.1	1044.7	987.9	935.6	886.7	852.7	819.5	790.0	766.0	742.8
17.5°	1204.3	1144.1	1076.3	1007.3	944.2	886.2	838.6	801.1	764.2	734.8	711.7
20°	1235.5	1167.0	1090.3	1018.6	948.9	884.2	831.9	787.1	747.3	716.2	690.1
22.5°	1262.3	1182.3	1102.9	1026.2	948.6	878.8	819.7	773.6	730.4	700.0	672.2
25°	1290.2	1194.4	1114.8	1024.8	938.1	865.9	799.5	747.3	704.2	668.5	639.9
27.5°	1314.1	1193.6	1099.1	1002.3	921.7	849.4	778.5	722.5	676.7	637.9	608.9
30°	1330.0	1195.2	1082.8	987.1	905.8	831.1	762.2	705.8	657.7	618.4	591.0
32.5°	1340.0	1194.2	1067.9	965.8	880.5	814.5	744.7	686.3	636.8	598.1	571.7
35°	1345.8	1186.9	1042.2	921.9	839.8	775.5	717.1	656.5	604.7	568.5	538.8
37.5°	1334.2	1171.6	1012.3	879.6	789.7	726.4	677.2	625.7	576.1	536.3	510.6
40°	1315.9	1161.7	989.1	849.8	755.2	694.3	652.4	601.7	552.8	515.1	491.0
42.5°	1281.0	1141.4	963.5	816.6	719.4	658.4	619.9	577.6	531.2	495.8	471.8
45°	1196.0	1097.3	925.3	766.8	666.5	603.4	569.4	538.8	496.9	462.4	441.6
47.5°	1078.1	1031.1	869.8	714.3	611.2	550.6	515.2	490.5	459.9	432.1	412.3
50°	996.2	976.7	832.3	678.5	574.4	515.1	481.1	458.7	436.7	408.9	390.7
52.5°	901.6	913.6	788.5	641.4	536.9	478.6	446.6	428.8	408.8	386.0	370.1
55°	768.5	812.0	712.9	578.9	481.1	425.5	395.2	379.5	367.9	350.9	337.2
57.5°	643.8	699.3	631.1	514.7	426.3	378.3	349.3	332.1	324.6	315.8	305.0
60°	569.8	624.6	572.7	471.5	389.4	343.8	318.1	303.6	296.1	289.9	280.7
62.5°	503.8	559.2	515.6	427.8	353.2	310.9	288.6	274.4	268.5	265.3	257.5
65°	413.0	460.7	431.7	359.6	301.5	264.2	243.8	233.9	228.5	227.3	222.3
67.5°	336.2	372.5	351.3	298.3	252.5	220.3	203.0	194.6	190.4	190.0	186.3
70°	285.7	319.7	303.6	255.5	216.1	190.8	175.9	168.3	165.9	165.5	163.4
72.5°	246.6	270.3	257.5	217.3	186.9	163.9	153.0	145.1	142.4	142.9	141.5
75°	182.4	200.3	192.8	165.1	140.6	125.6	116.5	111.5	109.1	110.4	108.7
77.5°	131.3	142.6	135.9	116.6	101.6	90.7	84.1	81.0	78.7	78.7	77.9
80°	99.1	105.8	102.0	90.4	78.0	68.8	63.5	61.4	60.1	59.7	59.3
82.5°	70.6	76.2	71.9	63.8	55.4	49.9	46.9	44.1	43.3	43.5	43.0
85°	35.6	37.7	36.0	31.1	27.8	25.3	23.6	22.4	21.5	21.9	21.2
87.5°	16.0	15.8	14.2	12.3	11.2	9.7	9.3	8.2	7.9	8.4	8.6
90°	18.5	15.6	12.7	10.1	7.8	5.5	3.2	1.0	3.2	5.5	7.8
92.5°	21.6	19.4	17.2	16.4	17.0	17.7	18.3	18.9	18.3	17.7	17.0
95°	26.6	24.1	21.6	25.0	34.3	43.6	52.8	62.1	52.8	43.6	34.3
97.5°	65.4	81.7	98.0	108.2	112.4	116.5	120.7	124.8	120.7	116.5	112.4
100°	104.3	139.6	174.8	190.3	185.7	181.2	176.7	172.1	176.7	181.2	185.7
102.5°	144.2	182.8	221.3	239.0	235.7	232.4	229.2	225.9	229.2	232.4	235.7
105°	263.8	284.2	304.6	313.5	311.0	308.6	306.0	303.6	306.0	308.6	311.0
107.5°	402.4	399.3	396.0	393.4	391.4	389.4	387.5	385.5	387.5	389.4	391.4
110°	454.4	451.9	449.4	447.3	445.4	443.6	441.9	440.1	441.9	443.6	445.4



TEST NUMBER: P332168-927

CATALOG NUMBER: S123DIW-S775D1320U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	505.7	503.3	500.7	498.7	497.1	495.4	493.8	492.2	493.8	495.4	497.1
115°	580.6	578.5	576.6	574.8	573.5	572.1	570.8	569.4	570.8	572.1	573.5
117.5°	654.3	653.2	652.2	650.9	649.2	647.5	645.9	644.2	645.9	647.5	649.2
120°	701.5	700.8	700.1	698.8	696.7	694.7	692.7	690.6	692.7	694.7	696.7
122.5°	747.6	746.7	745.8	744.6	742.9	741.2	739.6	737.9	739.6	741.2	742.9
125°	813.1	812.1	811.3	809.9	808.1	806.3	804.5	802.6	804.5	806.3	808.1
127.5°	876.3	875.2	874.1	872.7	870.8	869.0	867.2	865.4	867.2	869.0	870.8
130°	915.0	914.0	913.1	911.8	910.0	908.2	906.3	904.5	906.3	908.2	910.0
132.5°	952.0	951.3	950.5	949.3	947.5	945.6	943.8	942.0	943.8	945.6	947.5
135°	1007.7	1006.7	1005.8	1004.7	1003.3	1002.0	1000.6	999.3	1000.6	1002.0	1003.3
137.5°	1057.2	1056.6	1056.1	1055.0	1053.3	1051.6	1049.9	1048.1	1049.9	1051.6	1053.3
140°	1088.5	1087.9	1087.2	1086.2	1084.8	1083.5	1082.1	1080.8	1082.1	1083.5	1084.8
142.5°	1118.7	1118.0	1117.4	1116.3	1115.0	1113.6	1112.2	1110.9	1112.2	1113.6	1115.0
145°	1161.3	1160.9	1160.4	1159.4	1157.9	1156.3	1154.7	1153.1	1154.7	1156.3	1157.9
147.5°	1198.6	1198.2	1197.7	1197.0	1195.9	1194.8	1193.8	1192.8	1193.8	1194.8	1195.9
150°	1221.4	1221.0	1220.5	1220.0	1219.2	1218.6	1217.9	1217.3	1217.9	1218.6	1219.2
152.5°	1241.3	1241.1	1240.8	1240.5	1240.2	1239.8	1239.5	1239.2	1239.5	1239.8	1240.2
155°	1268.8	1268.5	1268.3	1268.4	1268.8	1269.3	1269.8	1270.2	1269.8	1269.3	1268.8
157.5°	1293.5	1293.7	1294.0	1294.0	1294.1	1294.2	1294.2	1294.3	1294.2	1294.2	1294.1
160°	1307.3	1307.6	1307.8	1308.0	1308.2	1308.4	1308.7	1308.9	1308.7	1308.4	1308.2
162.5°	1319.5	1319.8	1320.0	1320.4	1321.0	1321.6	1322.2	1322.8	1322.2	1321.6	1321.0
165°	1335.9	1336.1	1336.3	1336.7	1337.4	1338.1	1338.8	1339.5	1338.8	1338.1	1337.4
167.5°	1348.5	1348.5	1348.5	1348.8	1349.8	1350.7	1351.6	1352.5	1351.6	1350.7	1349.8
170°	1355.7	1355.7	1355.7	1356.2	1357.2	1358.0	1358.9	1359.9	1358.9	1358.0	1357.2
172.5°	1360.3	1360.1	1359.9	1360.4	1361.4	1362.6	1363.7	1364.8	1363.7	1362.6	1361.4
175°	1366.5	1366.3	1366.0	1366.5	1367.6	1368.8	1369.9	1371.0	1369.9	1368.8	1367.6
177.5°	1369.0	1368.9	1368.7	1369.0	1370.0	1370.9	1371.7	1372.7	1371.7	1370.9	1370.0
180°	1371.0	1371.0	1371.0	1371.0	1371.0	1371.0	1371.0	1371.0	1371.0	1371.0	1371.0



TEST NUMBER: P332168-927

CATALOG NUMBER: S123DIW-S775D1320U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	856.0	856.0	856.0	856.0	856.0	856.0	856.0	856.0	856.0	856.0	856.0
2.5°	841.7	839.4	836.1	831.1	827.1	820.8	820.8	821.8	821.8	821.5	820.8
5°	816.2	809.9	802.5	793.8	784.7	775.5	773.9	770.6	768.1	766.4	764.3
7.5°	789.3	778.2	767.3	755.1	744.0	734.8	728.4	723.1	719.7	716.1	713.4
10°	771.0	757.2	744.4	731.6	717.5	706.3	699.3	694.3	690.5	687.2	685.6
12.5°	749.4	733.7	719.5	707.3	691.9	680.4	673.7	671.4	666.9	660.0	656.3
15°	717.9	703.4	686.3	667.7	660.2	646.1	638.3	634.5	632.0	626.6	625.0
17.5°	690.9	671.9	652.8	638.9	625.0	613.6	609.2	604.6	601.3	596.8	595.6
20°	669.4	652.4	634.9	620.0	605.5	593.0	589.3	586.0	582.7	580.6	578.9
22.5°	647.5	630.5	616.0	602.1	586.6	578.5	574.4	570.8	568.4	567.0	565.4
25°	616.7	601.7	585.6	573.1	560.7	555.3	552.8	550.7	549.1	547.0	546.6
27.5°	589.1	572.9	559.8	548.2	539.2	534.7	532.3	531.3	531.7	532.4	532.9
30°	568.5	553.7	542.9	532.9	524.7	520.5	520.1	520.1	521.7	522.1	523.0
32.5°	549.7	537.4	526.6	517.0	510.7	507.9	509.5	509.5	510.8	511.8	513.3
35°	522.1	511.4	503.0	494.8	489.4	490.6	491.5	492.3	494.3	496.9	498.5
37.5°	495.8	486.5	477.8	471.3	468.9	471.1	473.1	474.8	477.3	479.2	480.9
40°	476.9	469.8	461.6	455.7	456.6	457.9	459.5	461.6	463.7	464.9	466.6
42.5°	459.3	451.9	445.7	440.8	442.0	443.6	444.6	445.7	448.1	450.3	451.3
45°	432.5	426.7	421.0	418.0	418.9	419.7	420.5	421.8	423.8	425.5	426.0
47.5°	402.4	398.4	394.5	391.7	393.0	392.7	393.7	396.4	397.0	398.1	400.4
50°	383.2	379.5	374.9	374.1	374.1	374.1	374.5	377.8	377.8	379.5	381.1
52.5°	361.9	359.6	356.6	355.1	354.5	354.5	356.2	357.9	358.5	360.9	362.6
55°	330.5	328.0	325.6	324.3	323.4	324.3	327.6	328.4	330.5	331.8	333.0
57.5°	297.8	295.9	293.9	293.2	293.0	294.1	296.0	298.4	299.0	302.8	304.7
60°	276.2	273.3	271.6	271.6	270.8	274.6	273.7	277.9	278.7	281.1	284.1
62.5°	254.0	250.1	249.4	249.4	250.6	251.7	252.8	254.6	256.8	259.9	262.2
65°	218.2	216.1	219.0	218.6	217.7	220.2	220.2	222.3	224.7	227.7	232.3
67.5°	184.2	183.2	183.4	183.4	184.7	186.1	187.2	189.0	192.0	195.1	198.0
70°	161.3	162.6	160.5	162.2	163.4	163.8	164.6	167.2	170.5	172.5	175.9
72.5°	139.1	139.0	139.3	139.9	141.2	141.9	142.8	145.6	149.2	151.0	153.6
75°	107.0	106.5	107.8	107.8	109.9	110.7	111.5	112.8	116.1	118.6	120.6
77.5°	78.1	78.7	78.3	79.8	79.2	79.4	81.9	83.2	83.5	88.4	89.5
80°	58.9	59.7	60.1	60.5	61.0	60.1	63.1	64.2	64.2	67.2	69.2
82.5°	42.3	42.8	43.9	44.3	44.4	45.2	45.5	46.3	47.4	48.6	51.3
85°	21.2	22.4	22.8	22.4	22.8	21.9	23.2	23.6	24.1	24.1	24.1
87.5°	8.6	9.5	9.7	10.7	10.9	11.9	12.0	11.6	11.7	12.9	11.7
90°	10.1	12.7	15.6	18.5	21.5	24.5	25.3	26.2	27.2	28.0	28.8
92.5°	16.4	17.2	19.4	21.6	23.8	26.1	27.5	29.0	30.4	31.8	32.7
95°	25.0	21.6	24.1	26.6	29.1	31.6	33.2	34.8	36.4	37.9	38.7
97.5°	108.2	98.0	81.7	65.4	49.1	32.8	34.6	36.4	38.3	40.0	41.0
100°	190.3	174.8	139.6	104.3	68.9	33.6	35.4	37.2	39.1	40.9	41.9
102.5°	239.0	221.3	182.8	144.2	105.6	67.0	61.4	55.8	50.1	44.6	42.0
105°	313.5	304.6	284.2	263.8	243.4	223.1	183.0	142.9	102.9	62.8	43.0
107.5°	393.4	396.0	399.3	402.4	405.7	408.8	379.5	350.1	320.8	291.4	261.6
110°	447.3	449.4	451.9	454.4	456.9	459.4	451.9	444.4	437.0	429.5	409.6



TEST NUMBER: P332168-927

CATALOG NUMBER: S123DIW-S775D1320U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	498.7	500.7	503.3	505.7	508.3	510.7	510.9	511.0	511.1	511.3	507.9
115°	574.8	576.6	578.5	580.6	582.7	584.7	586.9	589.2	591.4	593.7	595.3
117.5°	650.9	652.2	653.2	654.3	655.4	656.4	658.2	660.0	661.8	663.6	664.6
120°	698.8	700.1	700.8	701.5	702.2	702.8	704.6	706.5	708.3	710.1	711.0
122.5°	744.6	745.8	746.7	747.6	748.5	749.3	750.6	751.9	753.1	754.4	755.1
125°	809.9	811.3	812.1	813.1	814.0	814.9	815.3	815.8	816.3	816.7	817.1
127.5°	872.7	874.1	875.2	876.3	877.3	878.5	879.2	879.9	880.6	881.4	881.5
130°	911.8	913.1	914.0	915.0	915.8	916.7	917.7	918.5	919.5	920.4	920.6
132.5°	949.3	950.5	951.3	952.0	952.7	953.4	954.3	955.2	956.2	957.0	957.2
135°	1004.7	1005.8	1006.7	1007.7	1008.5	1009.5	1010.1	1010.8	1011.5	1012.2	1012.2
137.5°	1055.0	1056.1	1056.6	1057.2	1057.6	1058.1	1059.2	1060.3	1061.4	1062.5	1062.8
140°	1086.2	1087.2	1087.9	1088.5	1089.3	1089.9	1090.8	1091.7	1092.7	1093.5	1093.8
142.5°	1116.3	1117.4	1118.0	1118.7	1119.4	1120.1	1120.8	1121.5	1122.2	1123.0	1123.0
145°	1159.4	1160.4	1160.9	1161.3	1161.8	1162.2	1162.7	1163.2	1163.6	1164.0	1164.3
147.5°	1197.0	1197.7	1198.2	1198.6	1199.0	1199.5	1200.0	1200.4	1200.9	1201.3	1201.0
150°	1220.0	1220.5	1221.0	1221.4	1221.9	1222.3	1222.8	1223.2	1223.7	1224.2	1224.0
152.5°	1240.5	1240.8	1241.1	1241.3	1241.6	1241.9	1242.7	1243.5	1244.4	1245.2	1245.1
155°	1268.4	1268.3	1268.5	1268.8	1269.0	1269.2	1270.3	1271.5	1272.6	1273.7	1273.6
157.5°	1294.0	1294.0	1293.7	1293.5	1293.2	1293.0	1294.3	1295.8	1297.1	1298.5	1298.2
160°	1308.0	1307.8	1307.6	1307.3	1307.1	1306.9	1308.2	1309.6	1311.0	1312.3	1312.2
162.5°	1320.4	1320.0	1319.8	1319.5	1319.3	1319.1	1320.6	1322.2	1323.7	1325.2	1325.3
165°	1336.7	1336.3	1336.1	1335.9	1335.6	1335.4	1337.2	1339.0	1340.8	1342.7	1342.7
167.5°	1348.8	1348.5	1348.5	1348.5	1348.5	1348.5	1350.3	1352.1	1353.8	1355.7	1355.7
170°	1356.2	1355.7	1355.7	1355.7	1355.7	1355.7	1357.6	1359.4	1361.2	1363.0	1363.0
172.5°	1360.4	1359.9	1360.1	1360.3	1360.5	1360.7	1362.5	1364.3	1366.1	1367.9	1367.8
175°	1366.5	1366.0	1366.3	1366.5	1366.8	1367.0	1368.6	1370.2	1371.7	1373.3	1373.2
177.5°	1369.0	1368.7	1368.9	1369.0	1369.2	1369.4	1370.9	1372.3	1373.8	1375.2	1375.1
180°	1371.0	1371.0	1371.0	1371.0	1371.0	1371.0	1371.0	1371.0	1371.0	1371.0	1371.0



TEST NUMBER: P332168-927

CATALOG NUMBER: S123DIW-S775D1320U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	856.0	856.0	856.0	856.0	856.0	856.0	856.0	856.0	856.0	856.0	856.0
2.5°	818.5	818.2	820.5	818.8	820.5	818.2	818.5	820.8	821.5	821.8	821.8
5°	761.8	763.1	758.9	758.9	758.9	763.1	761.8	764.3	766.4	768.1	770.6
7.5°	711.4	709.6	709.7	707.5	709.7	709.6	711.4	713.4	716.1	719.7	723.1
10°	680.6	678.1	677.2	677.6	677.2	678.1	680.6	685.6	687.2	690.5	694.3
12.5°	655.0	654.5	649.0	649.1	649.0	654.5	655.0	656.3	660.0	666.9	671.4
15°	625.0	617.1	616.2	618.8	616.2	617.1	625.0	625.0	626.6	632.0	634.5
17.5°	594.8	590.7	591.0	589.7	591.0	590.7	594.8	595.6	596.8	601.3	604.6
20°	578.9	576.5	576.1	573.1	576.1	576.5	578.9	578.9	580.6	582.7	586.0
22.5°	564.4	563.6	563.8	560.5	563.8	563.6	564.4	565.4	567.0	568.4	570.8
25°	546.2	548.3	546.6	546.6	546.6	548.3	546.2	546.6	547.0	549.1	550.7
27.5°	533.9	533.9	533.0	533.0	533.0	533.9	533.9	532.9	532.4	531.7	531.3
30°	524.7	524.2	525.1	525.1	525.1	524.2	524.7	523.0	522.1	521.7	520.1
32.5°	515.3	515.9	516.1	516.4	516.1	515.9	515.3	513.3	511.8	510.8	509.5
35°	501.0	501.4	502.6	501.8	502.6	501.4	501.0	498.5	496.9	494.3	492.3
37.5°	481.6	483.5	483.1	483.7	483.1	483.5	481.6	480.9	479.2	477.3	474.8
40°	467.0	468.3	467.8	467.8	467.8	468.3	467.0	466.6	464.9	463.7	461.6
42.5°	452.0	453.0	451.9	451.2	451.9	453.0	452.0	451.3	450.3	448.1	445.7
45°	427.5	426.7	428.0	426.4	428.0	426.7	427.5	426.0	425.5	423.8	421.8
47.5°	400.2	401.0	401.4	402.6	401.4	401.0	400.2	400.4	398.1	397.0	396.4
50°	382.0	384.4	384.4	384.0	384.4	384.4	382.0	381.1	379.5	377.8	377.8
52.5°	364.0	365.2	366.9	366.8	366.9	365.2	364.0	362.6	360.9	358.5	357.9
55°	336.4	337.2	338.0	338.4	338.0	337.2	336.4	333.0	331.8	330.5	328.4
57.5°	307.6	307.3	309.3	309.9	309.3	307.3	307.6	304.7	302.8	299.0	298.4
60°	287.4	287.4	290.7	292.0	290.7	287.4	287.4	284.1	281.1	278.7	277.9
62.5°	265.9	267.2	270.5	268.7	270.5	267.2	265.9	262.2	259.9	256.8	254.6
65°	234.3	237.7	237.3	238.8	237.3	237.7	234.3	232.3	227.7	224.7	222.3
67.5°	201.4	203.4	206.4	206.7	206.4	203.4	201.4	198.0	195.1	192.0	189.0
70°	179.2	181.3	182.9	184.1	182.9	181.3	179.2	175.9	172.5	170.5	167.2
72.5°	157.6	158.7	162.6	160.9	162.6	158.7	157.6	153.6	151.0	149.2	145.6
75°	123.6	126.5	129.0	127.7	129.0	126.5	123.6	120.6	118.6	116.1	112.8
77.5°	91.4	94.3	95.5	94.4	95.5	94.3	91.4	89.5	88.4	83.5	83.2
80°	72.2	71.8	74.2	73.8	74.2	71.8	72.2	69.2	67.2	64.2	64.2
82.5°	52.9	52.5	53.6	53.9	53.6	52.5	52.9	51.3	48.6	47.4	46.3
85°	25.7	26.9	25.3	24.9	25.3	26.9	25.7	24.1	24.1	24.1	23.6
87.5°	11.8	11.9	11.6	11.4	11.6	11.9	11.8	11.7	12.9	11.7	11.6
90°	29.2	29.6	30.1	30.6	30.1	29.6	29.2	28.8	28.0	27.2	26.2
92.5°	33.0	33.3	33.5	33.8	33.5	33.3	33.0	32.7	31.8	30.4	29.0
95°	38.7	38.7	38.7	38.7	38.7	38.7	38.7	38.7	37.9	36.4	34.8
97.5°	41.3	41.5	41.7	42.0	41.7	41.5	41.3	41.0	40.0	38.3	36.4
100°	42.1	42.3	42.5	42.8	42.5	42.3	42.1	41.9	40.9	39.1	37.2
102.5°	42.4	42.8	43.2	43.6	43.2	42.8	42.4	42.0	44.6	50.1	55.8
105°	43.5	43.9	44.4	44.8	44.4	43.9	43.5	43.0	62.8	102.9	142.9
107.5°	231.4	201.1	171.0	140.8	171.0	201.1	231.4	261.6	291.4	320.8	350.1
110°	377.2	344.8	312.5	280.1	312.5	344.8	377.2	409.6	429.5	437.0	444.4



TEST NUMBER: P332168-927

CATALOG NUMBER: S123DIW-S775D1320U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	501.1	494.2	487.4	480.6	487.4	494.2	501.1	507.9	511.3	511.1	511.0
115°	596.2	597.1	598.0	599.0	598.0	597.1	596.2	595.3	593.7	591.4	589.2
117.5°	664.8	665.0	665.2	665.4	665.2	665.0	664.8	664.6	663.6	661.8	660.0
120°	711.0	711.0	711.0	711.0	711.0	711.0	711.0	711.0	710.1	708.3	706.5
122.5°	755.3	755.4	755.7	755.8	755.7	755.4	755.3	755.1	754.4	753.1	751.9
125°	817.6	818.1	818.5	819.0	818.5	818.1	817.6	817.1	816.7	816.3	815.8
127.5°	881.1	880.6	880.1	879.6	880.1	880.6	881.1	881.5	881.4	880.6	879.9
130°	920.1	919.7	919.2	918.8	919.2	919.7	920.1	920.6	920.4	919.5	918.5
132.5°	956.6	955.9	955.3	954.7	955.3	955.9	956.6	957.2	957.0	956.2	955.2
135°	1011.5	1010.8	1010.1	1009.5	1010.1	1010.8	1011.5	1012.2	1012.2	1011.5	1010.8
137.5°	1062.3	1061.9	1061.4	1061.0	1061.4	1061.9	1062.3	1062.8	1062.5	1061.4	1060.3
140°	1093.3	1092.8	1092.4	1091.9	1092.4	1092.8	1093.3	1093.8	1093.5	1092.7	1091.7
142.5°	1122.4	1121.7	1121.1	1120.5	1121.1	1121.7	1122.4	1123.0	1123.0	1122.2	1121.5
145°	1164.3	1164.3	1164.3	1164.3	1164.3	1164.3	1164.3	1164.3	1164.0	1163.6	1163.2
147.5°	1200.0	1199.0	1197.9	1196.8	1197.9	1199.0	1200.0	1201.0	1201.3	1200.9	1200.4
150°	1223.4	1222.7	1222.0	1221.3	1222.0	1222.7	1223.4	1224.0	1224.2	1223.7	1223.2
152.5°	1244.0	1242.9	1241.9	1240.9	1241.9	1242.9	1244.0	1245.1	1245.2	1244.4	1243.5
155°	1272.2	1270.9	1269.6	1268.2	1269.6	1270.9	1272.2	1273.6	1273.7	1272.6	1271.5
157.5°	1296.5	1294.7	1292.9	1291.2	1292.9	1294.7	1296.5	1298.2	1298.5	1297.1	1295.8
160°	1310.6	1309.0	1307.4	1305.8	1307.4	1309.0	1310.6	1312.2	1312.3	1311.0	1309.6
162.5°	1323.9	1322.5	1321.1	1319.7	1321.1	1322.5	1323.9	1325.3	1325.2	1323.7	1322.2
165°	1341.2	1339.6	1338.0	1336.4	1338.0	1339.6	1341.2	1342.7	1342.7	1340.8	1339.0
167.5°	1353.8	1352.1	1350.3	1348.5	1350.3	1352.1	1353.8	1355.7	1355.7	1353.8	1352.1
170°	1361.2	1359.4	1357.6	1355.7	1357.6	1359.4	1361.2	1363.0	1363.0	1361.2	1359.4
172.5°	1365.8	1363.8	1361.8	1359.9	1361.8	1363.8	1365.8	1367.8	1367.9	1366.1	1364.3
175°	1371.4	1369.6	1367.8	1366.0	1367.8	1369.6	1371.4	1373.2	1373.3	1371.7	1370.2
177.5°	1373.2	1371.4	1369.6	1367.8	1369.6	1371.4	1373.2	1375.1	1375.2	1373.8	1372.3
180°	1371.0	1371.0	1371.0	1371.0	1371.0	1371.0	1371.0	1371.0	1371.0	1371.0	1371.0



TEST NUMBER: P332168-927

CATALOG NUMBER: S123DIW-S775D1320U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	856.0	856.0	856.0	856.0	856.0	856.0	856.0	856.0	856.0	856.0	856.0
2.5°	820.8	820.8	827.1	831.1	836.1	839.4	841.7	844.1	848.0	853.3	859.3
5°	773.9	775.5	784.7	793.8	802.5	809.9	816.2	823.6	832.7	844.0	856.4
7.5°	728.4	734.8	744.0	755.1	767.3	778.2	789.3	801.5	814.4	830.8	848.3
10°	699.3	706.3	717.5	731.6	744.4	757.2	771.0	784.3	800.4	819.9	842.3
12.5°	673.7	680.4	691.9	707.3	719.5	733.7	749.4	766.7	784.8	808.3	833.7
15°	638.3	646.1	660.2	667.7	686.3	703.4	717.9	742.8	766.0	790.0	819.5
17.5°	609.2	613.6	625.0	638.9	652.8	671.9	690.9	711.7	734.8	764.2	801.1
20°	589.3	593.0	605.5	620.0	634.9	652.4	669.4	690.1	716.2	747.3	787.1
22.5°	574.4	578.5	586.6	602.1	616.0	630.5	647.5	672.2	700.0	730.4	773.6
25°	552.8	555.3	560.7	573.1	585.6	601.7	616.7	639.9	668.5	704.2	747.3
27.5°	532.3	534.7	539.2	548.2	559.8	572.9	589.1	608.9	637.9	676.7	722.5
30°	520.1	520.5	524.7	532.9	542.9	553.7	568.5	591.0	618.4	657.7	705.8
32.5°	509.5	507.9	510.7	517.0	526.6	537.4	549.7	571.7	598.1	636.8	686.3
35°	491.5	490.6	489.4	494.8	503.0	511.4	522.1	538.8	568.5	604.7	656.5
37.5°	473.1	471.1	468.9	471.3	477.8	486.5	495.8	510.6	536.3	576.1	625.7
40°	459.5	457.9	456.6	455.7	461.6	469.8	476.9	491.0	515.1	552.8	601.7
42.5°	444.6	443.6	442.0	440.8	445.7	451.9	459.3	471.8	495.8	531.2	577.6
45°	420.5	419.7	418.9	418.0	421.0	426.7	432.5	441.6	462.4	496.9	538.8
47.5°	393.7	392.7	393.0	391.7	394.5	398.4	402.4	412.3	432.1	459.9	490.5
50°	374.5	374.1	374.1	374.1	374.9	379.5	383.2	390.7	408.9	436.7	458.7
52.5°	356.2	354.5	354.5	355.1	356.6	359.6	361.9	370.1	386.0	408.8	428.8
55°	327.6	324.3	323.4	324.3	325.6	328.0	330.5	337.2	350.9	367.9	379.5
57.5°	296.0	294.1	293.0	293.2	293.9	295.9	297.8	305.0	315.8	324.6	332.1
60°	273.7	274.6	270.8	271.6	271.6	273.3	276.2	280.7	289.9	296.1	303.6
62.5°	252.8	251.7	250.6	249.4	249.4	250.1	254.0	257.5	265.3	268.5	274.4
65°	220.2	220.2	217.7	218.6	219.0	216.1	218.2	222.3	227.3	228.5	233.9
67.5°	187.2	186.1	184.7	183.4	183.4	183.2	184.2	186.3	190.0	190.4	194.6
70°	164.6	163.8	163.4	162.2	160.5	162.6	161.3	163.4	165.5	165.9	168.3
72.5°	142.8	141.9	141.2	139.9	139.3	139.0	139.1	141.5	142.9	142.4	145.1
75°	111.5	110.7	109.9	107.8	107.8	106.5	107.0	108.7	110.4	109.1	111.5
77.5°	81.9	79.4	79.2	79.8	78.3	78.7	78.1	77.9	78.7	78.7	81.0
80°	63.1	60.1	61.0	60.5	60.1	59.7	58.9	59.3	59.7	60.1	61.4
82.5°	45.5	45.2	44.4	44.3	43.9	42.8	42.3	43.0	43.5	43.3	44.1
85°	23.2	21.9	22.8	22.4	22.8	22.4	21.2	21.2	21.9	21.5	22.4
87.5°	12.0	11.9	10.9	10.7	9.7	9.5	8.6	8.6	8.4	7.9	8.2
90°	25.3	24.5	21.5	18.5	15.6	12.7	10.1	7.8	5.5	3.2	1.0
92.5°	27.5	26.1	23.8	21.6	19.4	17.2	16.4	17.0	17.7	18.3	18.9
95°	33.2	31.6	29.1	26.6	24.1	21.6	25.0	34.3	43.6	52.8	62.1
97.5°	34.6	32.8	49.1	65.4	81.7	98.0	108.2	112.4	116.5	120.7	124.8
100°	35.4	33.6	68.9	104.3	139.6	174.8	190.3	185.7	181.2	176.7	172.1
102.5°	61.4	67.0	105.6	144.2	182.8	221.3	239.0	235.7	232.4	229.2	225.9
105°	183.0	223.1	243.4	263.8	284.2	304.6	313.5	311.0	308.6	306.0	303.6
107.5°	379.5	408.8	405.7	402.4	399.3	396.0	393.4	391.4	389.4	387.5	385.5
110°	451.9	459.4	456.9	454.4	451.9	449.4	447.3	445.4	443.6	441.9	440.1



TEST NUMBER: P332168-927

CATALOG NUMBER: S123DIW-S775D1320U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	510.9	510.7	508.3	505.7	503.3	500.7	498.7	497.1	495.4	493.8	492.2
115°	586.9	584.7	582.7	580.6	578.5	576.6	574.8	573.5	572.1	570.8	569.4
117.5°	658.2	656.4	655.4	654.3	653.2	652.2	650.9	649.2	647.5	645.9	644.2
120°	704.6	702.8	702.2	701.5	700.8	700.1	698.8	696.7	694.7	692.7	690.6
122.5°	750.6	749.3	748.5	747.6	746.7	745.8	744.6	742.9	741.2	739.6	737.9
125°	815.3	814.9	814.0	813.1	812.1	811.3	809.9	808.1	806.3	804.5	802.6
127.5°	879.2	878.5	877.3	876.3	875.2	874.1	872.7	870.8	869.0	867.2	865.4
130°	917.7	916.7	915.8	915.0	914.0	913.1	911.8	910.0	908.2	906.3	904.5
132.5°	954.3	953.4	952.7	952.0	951.3	950.5	949.3	947.5	945.6	943.8	942.0
135°	1010.1	1009.5	1008.5	1007.7	1006.7	1005.8	1004.7	1003.3	1002.0	1000.6	999.3
137.5°	1059.2	1058.1	1057.6	1057.2	1056.6	1056.1	1055.0	1053.3	1051.6	1049.9	1048.1
140°	1090.8	1089.9	1089.3	1088.5	1087.9	1087.2	1086.2	1084.8	1083.5	1082.1	1080.8
142.5°	1120.8	1120.1	1119.4	1118.7	1118.0	1117.4	1116.3	1115.0	1113.6	1112.2	1110.9
145°	1162.7	1162.2	1161.8	1161.3	1160.9	1160.4	1159.4	1157.9	1156.3	1154.7	1153.1
147.5°	1200.0	1199.5	1199.0	1198.6	1198.2	1197.7	1197.0	1195.9	1194.8	1193.8	1192.8
150°	1222.8	1222.3	1221.9	1221.4	1221.0	1220.5	1220.0	1219.2	1218.6	1217.9	1217.3
152.5°	1242.7	1241.9	1241.6	1241.3	1241.1	1240.8	1240.5	1240.2	1239.8	1239.5	1239.2
155°	1270.3	1269.2	1269.0	1268.8	1268.5	1268.3	1268.4	1268.8	1269.3	1269.8	1270.2
157.5°	1294.3	1293.0	1293.2	1293.5	1293.7	1294.0	1294.0	1294.1	1294.2	1294.2	1294.3
160°	1308.2	1306.9	1307.1	1307.3	1307.6	1307.8	1308.0	1308.2	1308.4	1308.7	1308.9
162.5°	1320.6	1319.1	1319.3	1319.5	1319.8	1320.0	1320.4	1321.0	1321.6	1322.2	1322.8
165°	1337.2	1335.4	1335.6	1335.9	1336.1	1336.3	1336.7	1337.4	1338.1	1338.8	1339.5
167.5°	1350.3	1348.5	1348.5	1348.5	1348.5	1348.5	1348.8	1349.8	1350.7	1351.6	1352.5
170°	1357.6	1355.7	1355.7	1355.7	1355.7	1355.7	1356.2	1357.2	1358.0	1358.9	1359.9
172.5°	1362.5	1360.7	1360.5	1360.3	1360.1	1359.9	1360.4	1361.4	1362.6	1363.7	1364.8
175°	1368.6	1367.0	1366.8	1366.5	1366.3	1366.0	1366.5	1367.6	1368.8	1369.9	1371.0
177.5°	1370.9	1369.4	1369.2	1369.0	1368.9	1368.7	1369.0	1370.0	1370.9	1371.7	1372.7
180°	1371.0	1371.0	1371.0	1371.0	1371.0	1371.0	1371.0	1371.0	1371.0	1371.0	1371.0



TEST NUMBER: P332168-927

CATALOG NUMBER: S123DIW-S775D1320U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	856.0	856.0	856.0	856.0	856.0	856.0	856.0	856.0	856.0	856.0	856.0
2.5°	861.3	862.9	868.6	872.6	877.2	879.9	882.5	884.6	887.2	887.8	897.5
5°	865.1	873.4	888.0	898.7	912.0	926.5	936.4	941.0	953.0	963.0	982.9
7.5°	864.0	881.7	903.6	926.3	950.7	973.3	992.8	1016.1	1032.6	1057.4	1081.8
10°	863.0	886.7	914.9	943.9	977.9	1009.4	1037.6	1069.1	1095.3	1129.7	1159.1
12.5°	860.1	888.7	927.8	962.2	1003.5	1046.9	1088.7	1129.2	1152.3	1209.7	1236.8
15°	852.7	886.7	935.6	987.9	1044.7	1096.1	1149.2	1191.5	1259.9	1310.1	1342.0
17.5°	838.6	886.2	944.2	1007.3	1076.3	1144.1	1204.3	1268.4	1341.0	1401.8	1466.5
20°	831.9	884.2	948.9	1018.6	1090.3	1167.0	1235.5	1312.6	1391.8	1451.5	1534.5
22.5°	819.7	878.8	948.6	1026.2	1102.9	1182.3	1262.3	1340.1	1431.6	1513.9	1592.8
25°	799.5	865.9	938.1	1024.8	1114.8	1194.4	1290.2	1393.4	1488.8	1594.6	1673.4
27.5°	778.5	849.4	921.7	1002.3	1099.1	1193.6	1314.1	1430.8	1547.4	1638.7	1697.0
30°	762.2	831.1	905.8	987.1	1082.8	1195.2	1330.0	1457.3	1571.0	1649.3	1682.1
32.5°	744.7	814.5	880.5	965.8	1067.9	1194.2	1340.0	1472.9	1572.3	1624.4	1618.1
35°	717.1	775.5	839.8	921.9	1042.2	1186.9	1345.8	1474.3	1535.3	1524.1	1439.5
37.5°	677.2	726.4	789.7	879.6	1012.3	1171.6	1334.2	1430.6	1426.6	1335.5	1212.9
40°	652.4	694.3	755.2	849.8	989.1	1161.7	1315.9	1378.6	1325.5	1198.1	1051.3
42.5°	619.9	658.4	719.4	816.6	963.5	1141.4	1281.0	1299.3	1195.4	1048.8	914.3
45°	569.4	603.4	666.5	766.8	925.3	1097.3	1196.0	1151.7	1011.9	860.5	758.1
47.5°	515.2	550.6	611.2	714.3	869.8	1031.1	1078.1	983.7	840.2	717.5	623.4
50°	481.1	515.1	574.4	678.5	832.3	976.7	996.2	874.3	742.4	634.5	557.4
52.5°	446.6	478.6	536.9	641.4	788.5	913.6	901.6	777.4	656.1	564.2	503.7
55°	395.2	425.5	481.1	578.9	712.9	812.0	768.5	649.9	549.5	478.2	432.1
57.5°	349.3	378.3	426.3	514.7	631.1	699.3	643.8	543.8	464.1	409.2	374.9
60°	318.1	343.8	389.4	471.5	572.7	624.6	569.8	481.5	414.3	370.3	339.7
62.5°	288.6	310.9	353.2	427.8	515.6	559.2	503.8	429.0	371.9	332.9	306.8
65°	243.8	264.2	301.5	359.6	431.7	460.7	413.0	352.5	308.2	279.1	261.7
67.5°	203.0	220.3	252.5	298.3	351.3	372.5	336.2	289.3	255.9	232.6	218.7
70°	175.9	190.8	216.1	255.5	303.6	319.7	285.7	247.2	222.7	204.1	191.2
72.5°	153.0	163.9	186.9	217.3	257.5	270.3	246.6	212.7	189.9	175.9	165.6
75°	116.5	125.6	140.6	165.1	192.8	200.3	182.4	161.3	146.0	136.0	128.2
77.5°	84.1	90.7	101.6	116.6	135.9	142.6	131.3	117.2	106.0	99.3	94.9
80°	63.5	68.8	78.0	90.4	102.0	105.8	99.1	88.3	80.5	76.8	73.0
82.5°	46.9	49.9	55.4	63.8	71.9	76.2	70.6	64.1	59.9	56.5	55.1
85°	23.6	25.3	27.8	31.1	36.0	37.7	35.6	34.0	31.5	29.5	29.5
87.5°	9.3	9.7	11.2	12.3	14.2	15.8	16.0	15.9	16.2	16.0	15.8
90°	3.2	5.5	7.8	10.1	12.7	15.6	18.5	21.5	24.5	25.3	26.2
92.5°	18.3	17.7	17.0	16.4	17.2	19.4	21.6	23.8	26.1	27.5	29.0
95°	52.8	43.6	34.3	25.0	21.6	24.1	26.6	29.1	31.6	33.2	34.8
97.5°	120.7	116.5	112.4	108.2	98.0	81.7	65.4	49.1	32.8	34.6	36.4
100°	176.7	181.2	185.7	190.3	174.8	139.6	104.3	68.9	33.6	35.4	37.2
102.5°	229.2	232.4	235.7	239.0	221.3	182.8	144.2	105.6	67.0	61.4	55.8
105°	306.0	308.6	311.0	313.5	304.6	284.2	263.8	243.4	223.1	183.0	142.9
107.5°	387.5	389.4	391.4	393.4	396.0	399.3	402.4	405.7	408.8	379.5	350.1
110°	441.9	443.6	445.4	447.3	449.4	451.9	454.4	456.9	459.4	451.9	444.4



TEST NUMBER: P332168-927

CATALOG NUMBER: S123DIW-S775D1320U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	493.8	495.4	497.1	498.7	500.7	503.3	505.7	508.3	510.7	510.9	511.0
115°	570.8	572.1	573.5	574.8	576.6	578.5	580.6	582.7	584.7	586.9	589.2
117.5°	645.9	647.5	649.2	650.9	652.2	653.2	654.3	655.4	656.4	658.2	660.0
120°	692.7	694.7	696.7	698.8	700.1	700.8	701.5	702.2	702.8	704.6	706.5
122.5°	739.6	741.2	742.9	744.6	745.8	746.7	747.6	748.5	749.3	750.6	751.9
125°	804.5	806.3	808.1	809.9	811.3	812.1	813.1	814.0	814.9	815.3	815.8
127.5°	867.2	869.0	870.8	872.7	874.1	875.2	876.3	877.3	878.5	879.2	879.9
130°	906.3	908.2	910.0	911.8	913.1	914.0	915.0	915.8	916.7	917.7	918.5
132.5°	943.8	945.6	947.5	949.3	950.5	951.3	952.0	952.7	953.4	954.3	955.2
135°	1000.6	1002.0	1003.3	1004.7	1005.8	1006.7	1007.7	1008.5	1009.5	1010.1	1010.8
137.5°	1049.9	1051.6	1053.3	1055.0	1056.1	1056.6	1057.2	1057.6	1058.1	1059.2	1060.3
140°	1082.1	1083.5	1084.8	1086.2	1087.2	1087.9	1088.5	1089.3	1089.9	1090.8	1091.7
142.5°	1112.2	1113.6	1115.0	1116.3	1117.4	1118.0	1118.7	1119.4	1120.1	1120.8	1121.5
145°	1154.7	1156.3	1157.9	1159.4	1160.4	1160.9	1161.3	1161.8	1162.2	1162.7	1163.2
147.5°	1193.8	1194.8	1195.9	1197.0	1197.7	1198.2	1198.6	1199.0	1199.5	1200.0	1200.4
150°	1217.9	1218.6	1219.2	1220.0	1220.5	1221.0	1221.4	1221.9	1222.3	1222.8	1223.2
152.5°	1239.5	1239.8	1240.2	1240.5	1240.8	1241.1	1241.3	1241.6	1241.9	1242.7	1243.5
155°	1269.8	1269.3	1268.8	1268.4	1268.3	1268.5	1268.8	1269.0	1269.2	1270.3	1271.5
157.5°	1294.2	1294.2	1294.1	1294.0	1294.0	1293.7	1293.5	1293.2	1293.0	1294.3	1295.8
160°	1308.7	1308.4	1308.2	1308.0	1307.8	1307.6	1307.3	1307.1	1306.9	1308.2	1309.6
162.5°	1322.2	1321.6	1321.0	1320.4	1320.0	1319.8	1319.5	1319.3	1319.1	1320.6	1322.2
165°	1338.8	1338.1	1337.4	1336.7	1336.3	1336.1	1335.9	1335.6	1335.4	1337.2	1339.0
167.5°	1351.6	1350.7	1349.8	1348.8	1348.5	1348.5	1348.5	1348.5	1348.5	1350.3	1352.1
170°	1358.9	1358.0	1357.2	1356.2	1355.7	1355.7	1355.7	1355.7	1355.7	1357.6	1359.4
172.5°	1363.7	1362.6	1361.4	1360.4	1359.9	1360.1	1360.3	1360.5	1360.7	1362.5	1364.3
175°	1369.9	1368.8	1367.6	1366.5	1366.0	1366.3	1366.5	1366.8	1367.0	1368.6	1370.2
177.5°	1371.7	1370.9	1370.0	1369.0	1368.7	1368.9	1369.0	1369.2	1369.4	1370.9	1372.3
180°	1371.0	1371.0	1371.0	1371.0	1371.0	1371.0	1371.0	1371.0	1371.0	1371.0	1371.0



TEST NUMBER: P332168-927

CATALOG NUMBER: S123DIW-S775D1320U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	856.0	856.0	856.0	856.0	856.0	856.0	856.0
2.5°	900.8	901.1	904.8	907.4	906.1	907.8	908.4
5°	984.1	999.1	1006.9	1012.7	1013.2	1013.6	1016.9
7.5°	1102.3	1118.3	1130.0	1147.8	1153.1	1159.1	1157.4
10°	1188.6	1212.2	1232.6	1243.3	1255.0	1271.9	1258.3
12.5°	1269.2	1311.1	1342.0	1358.8	1369.8	1373.2	1366.4
15°	1402.2	1456.9	1486.4	1485.5	1522.9	1539.1	1513.7
17.5°	1524.1	1574.6	1615.1	1635.9	1666.9	1673.8	1670.6
20°	1598.8	1653.9	1685.4	1721.1	1737.3	1751.8	1754.3
22.5°	1663.1	1712.6	1746.4	1776.2	1789.7	1796.6	1800.7
25°	1729.4	1768.4	1788.7	1799.0	1802.8	1802.0	1796.6
27.5°	1724.8	1727.8	1705.4	1683.5	1663.8	1641.6	1634.0
30°	1680.1	1645.2	1583.0	1547.8	1495.9	1454.8	1471.4
32.5°	1562.3	1492.9	1423.1	1346.0	1282.2	1264.1	1245.8
35°	1333.3	1211.4	1140.1	1057.1	1024.0	990.8	968.0
37.5°	1078.7	984.4	899.8	845.5	812.3	791.3	780.0
40°	932.7	847.7	778.0	734.0	708.8	685.2	681.8
42.5°	816.3	737.2	684.8	649.7	625.5	615.4	608.2
45°	668.5	613.4	578.1	553.3	537.1	530.8	522.5
47.5°	565.9	526.9	500.4	483.5	471.3	466.7	466.0
50°	508.4	476.1	456.6	443.3	433.8	432.1	425.5
52.5°	465.3	437.3	422.1	410.5	403.6	398.9	397.0
55°	403.9	385.2	371.6	365.0	359.6	355.0	355.0
57.5°	353.4	337.9	328.8	323.1	321.5	318.2	316.2
60°	322.3	309.0	301.9	296.9	293.7	294.1	290.3
62.5°	291.7	283.1	276.4	271.4	267.4	267.5	267.8
65°	248.4	241.8	236.8	235.1	232.7	229.7	230.6
67.5°	210.5	204.3	200.4	197.6	196.8	195.2	197.6
70°	183.3	178.7	175.9	173.3	172.5	172.9	175.0
72.5°	158.4	155.2	153.3	152.1	150.3	150.4	151.8
75°	124.5	121.9	120.3	119.0	118.6	118.6	118.6
77.5°	91.4	90.9	90.1	88.2	88.3	88.8	88.9
80°	72.2	70.9	70.5	69.7	68.4	67.6	69.7
82.5°	53.9	52.7	52.3	52.1	50.1	50.0	51.7
85°	29.0	27.8	28.2	27.8	27.8	27.4	27.4
87.5°	15.7	15.6	15.4	15.8	15.5	15.3	16.1
90°	27.2	28.0	28.8	29.2	29.6	30.1	30.6
92.5°	30.4	31.8	32.7	33.0	33.3	33.5	33.8
95°	36.4	37.9	38.7	38.7	38.7	38.7	38.7
97.5°	38.3	40.0	41.0	41.3	41.5	41.7	42.0
100°	39.1	40.9	41.9	42.1	42.3	42.5	42.8
102.5°	50.1	44.6	42.0	42.4	42.8	43.2	43.6
105°	102.9	62.8	43.0	43.5	43.9	44.4	44.8
107.5°	320.8	291.4	261.6	231.4	201.1	171.0	140.8
110°	437.0	429.5	409.6	377.2	344.8	312.5	280.1



TEST NUMBER: P332168-927

CATALOG NUMBER: S123DIW-S775D1320U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	511.1	511.3	507.9	501.1	494.2	487.4	480.6
115°	591.4	593.7	595.3	596.2	597.1	598.0	599.0
117.5°	661.8	663.6	664.6	664.8	665.0	665.2	665.4
120°	708.3	710.1	711.0	711.0	711.0	711.0	711.0
122.5°	753.1	754.4	755.1	755.3	755.4	755.7	755.8
125°	816.3	816.7	817.1	817.6	818.1	818.5	819.0
127.5°	880.6	881.4	881.5	881.1	880.6	880.1	879.6
130°	919.5	920.4	920.6	920.1	919.7	919.2	918.8
132.5°	956.2	957.0	957.2	956.6	955.9	955.3	954.7
135°	1011.5	1012.2	1012.2	1011.5	1010.8	1010.1	1009.5
137.5°	1061.4	1062.5	1062.8	1062.3	1061.9	1061.4	1061.0
140°	1092.7	1093.5	1093.8	1093.3	1092.8	1092.4	1091.9
142.5°	1122.2	1123.0	1123.0	1122.4	1121.7	1121.1	1120.5
145°	1163.6	1164.0	1164.3	1164.3	1164.3	1164.3	1164.3
147.5°	1200.9	1201.3	1201.0	1200.0	1199.0	1197.9	1196.8
150°	1223.7	1224.2	1224.0	1223.4	1222.7	1222.0	1221.3
152.5°	1244.4	1245.2	1245.1	1244.0	1242.9	1241.9	1240.9
155°	1272.6	1273.7	1273.6	1272.2	1270.9	1269.6	1268.2
157.5°	1297.1	1298.5	1298.2	1296.5	1294.7	1292.9	1291.2
160°	1311.0	1312.3	1312.2	1310.6	1309.0	1307.4	1305.8
162.5°	1323.7	1325.2	1325.3	1323.9	1322.5	1321.1	1319.7
165°	1340.8	1342.7	1342.7	1341.2	1339.6	1338.0	1336.4
167.5°	1353.8	1355.7	1355.7	1353.8	1352.1	1350.3	1348.5
170°	1361.2	1363.0	1363.0	1361.2	1359.4	1357.6	1355.7
172.5°	1366.1	1367.9	1367.8	1365.8	1363.8	1361.8	1359.9
175°	1371.7	1373.3	1373.2	1371.4	1369.6	1367.8	1366.0
177.5°	1373.8	1375.2	1375.1	1373.2	1371.4	1369.6	1367.8
180°	1371.0	1371.0	1371.0	1371.0	1371.0	1371.0	1371.0

(END OF REPORT)