

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331500-840

Luminaire Tested: **S122DIW-S485D435U840-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331500-840
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-8,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122DIW-S485D435U840-4F0-1E-UDD-F1
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 485 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 435 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3513.7 lumens
Efficiency: N/A
Efficacy: 116.3 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.3
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 30.2
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331500-840
CATALOG NUMBER: S122DIW-S485D435U840-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P331500-840

CATALOG NUMBER: S122DIW-S485D435U840-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	109	109	109	109	101	101	101	101	87	87	87	74	74	74	62	62	62	57
1	99	95	91	87	92	88	85	82	76	74	72	65	64	62	55	54	53	48
2	90	83	77	71	84	77	72	67	67	63	59	57	54	52	49	46	44	40
3	83	73	65	60	76	68	62	56	59	54	50	51	47	44	43	40	38	34
4	76	65	57	50	70	60	53	48	53	47	43	45	41	37	38	35	33	29
5	69	58	49	43	64	54	47	41	47	41	37	41	36	33	35	31	28	25
6	64	52	43	38	59	48	41	36	42	37	32	37	32	29	31	28	25	22
7	59	47	39	33	55	44	37	31	39	33	28	33	29	25	29	25	22	20
8	55	42	35	29	51	40	33	28	35	29	25	31	26	23	26	23	20	18
9	51	39	31	26	48	37	30	25	32	27	23	28	24	20	24	21	18	16
10	48	36	28	23	45	34	27	22	30	24	20	26	22	18	23	19	16	14

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	12665	12665	12665
5°	12713	12530	12603
10°	12637	12403	12463
15°	12481	12242	12227
20°	12259	12000	11986
25°	12039	11703	11703
30°	11757	11432	11332
35°	11491	11105	10941
40°	11160	10779	10570
45°	10832	10453	10195
50°	10477	10115	9756
55°	10106	9723	9362
60°	9691	9255	8913
65°	9249	8787	8382
70°	8686	8224	7832
75°	7904	7573	7392
80°	7011	6797	6453
85°	5724	5446	4891



TEST NUMBER: P331500-840

CATALOG NUMBER: S122DIW-S485D435U840-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	73.8	2.1
10°-20°	207.5	5.9
20°-30°	305.0	8.7
30°-40°	354.3	10.1
40°-50°	354.0	10.1
50°-60°	308.7	8.8
60°-70°	228.2	6.5
70°-80°	129.3	3.7
80°-90°	36.9	1.1
90°-100°	34.4	1.0
100°-110°	106.7	3.0
110°-120°	182.4	5.2
120°-130°	239.9	6.8
130°-140°	269.2	7.7
140°-150°	263.9	7.5
150°-160°	221.4	6.3
160°-170°	146.8	4.2
170°-180°	51.3	1.5
0°-30°	586.3	16.7
0°-40°	940.7	26.8
0°-60°	1603.3	45.6
0°-90°	1997.7	56.9
90°-120°	323.4	9.2
90°-150°	1096.4	31.2
90°-180°	1516.0	43.1
0°-180°	3513.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	784	784	784	784	784	
5°	784	781	773	779	778	74
15°	747	742	732	735	732	210
25°	676	669	657	658	657	311
35°	583	575	563	559	555	364
45°	474	469	458	450	446	366
55°	359	354	345	337	333	321
65°	242	237	230	223	219	239
75°	127	125	121	117	118	135
85°	31	30	29	27	26	35
90°	0	6	16	15	16	3
95°	24	28	29	29	28	27
105°	98	100	101	102	102	104
115°	183	186	185	184	183	181
125°	266	270	269	268	267	238
135°	345	349	350	350	349	266
145°	418	421	424	424	423	261
155°	478	480	481	483	482	220
165°	520	520	520	523	521	147
175°	541	540	539	542	540	51
180°	542	542	542	542	542	



TEST NUMBER: P331500-840

CATALOG NUMBER: S122DIW-S485D435U840-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	784.4	784.4	784.4	784.4	784.4	784.4	784.4	784.4	784.4	784.4	784.4
2.5°	788.0	787.3	786.7	786.0	785.3	784.3	782.7	781.3	779.8	778.3	779.7
5°	784.4	783.7	783.0	782.3	781.7	780.4	778.6	776.8	774.9	773.1	774.4
7.5°	777.4	776.4	775.4	774.3	773.3	771.8	769.9	768.1	766.2	764.3	765.7
10°	770.8	769.6	768.4	767.3	766.1	764.5	762.4	760.5	758.5	756.5	757.8
12.5°	761.7	760.7	759.6	758.6	757.6	756.1	754.1	752.0	750.0	748.0	748.9
15°	746.7	745.7	744.7	743.7	742.7	741.0	738.8	736.7	734.5	732.4	733.0
17.5°	727.3	726.4	725.4	724.4	723.4	721.8	719.5	717.3	715.1	712.9	713.7
20°	713.5	712.5	711.4	710.4	709.4	707.8	705.4	703.1	700.7	698.4	698.9
22.5°	699.6	698.2	696.8	695.4	694.0	692.2	689.9	687.7	685.5	683.3	683.4
25°	675.8	674.4	673.1	671.8	670.4	668.3	665.5	662.6	659.7	656.9	657.2
27.5°	648.6	647.4	646.2	645.0	643.8	642.1	639.9	637.5	635.3	633.1	632.6
30°	630.6	629.1	627.8	626.5	625.1	623.2	620.7	618.2	615.7	613.2	612.7
32.5°	611.2	610.2	609.0	607.9	606.9	605.0	602.4	599.8	597.1	594.5	593.6
35°	583.0	581.3	579.7	577.9	576.3	574.1	571.5	568.8	566.0	563.4	562.4
37.5°	551.2	549.7	548.3	546.7	545.2	543.2	540.5	537.9	535.1	532.5	531.2
40°	529.5	528.1	526.7	525.4	524.1	522.1	519.4	516.7	514.0	511.4	509.9
42.5°	508.4	507.0	505.6	504.3	503.0	501.0	498.3	495.6	492.9	490.2	488.6
45°	474.4	473.2	472.0	470.9	469.7	467.9	465.3	462.8	460.3	457.8	456.0
47.5°	440.6	439.5	438.4	437.3	436.2	434.3	431.7	429.1	426.5	423.8	421.9
50°	417.1	416.3	415.4	414.5	413.7	412.1	409.8	407.5	405.1	402.7	400.4
52.5°	394.2	393.0	391.9	390.8	389.7	388.1	385.9	383.6	381.4	379.2	377.3
55°	359.0	358.0	357.0	356.0	355.0	353.5	351.4	349.4	347.4	345.4	343.5
57.5°	323.7	322.9	322.0	321.3	320.5	319.0	316.8	314.6	312.4	310.1	308.1
60°	300.1	299.5	298.8	298.1	297.5	296.0	293.7	291.2	288.9	286.6	284.8
62.5°	277.2	276.2	275.1	274.0	273.0	271.6	269.7	267.9	266.1	264.3	262.6
65°	242.1	241.1	240.0	239.0	238.1	236.7	235.1	233.4	231.7	230.0	228.5
67.5°	206.3	205.5	204.7	203.9	203.1	202.0	200.5	198.9	197.4	195.9	194.8
70°	184.0	183.4	182.7	182.0	181.4	180.3	178.7	177.2	175.7	174.2	173.1
72.5°	161.1	160.5	159.8	159.1	158.4	157.6	156.6	155.6	154.7	153.7	152.5
75°	126.7	126.3	126.0	125.7	125.3	124.8	123.9	123.1	122.3	121.4	120.4
77.5°	95.9	95.3	94.8	94.2	93.6	93.2	92.9	92.5	92.2	91.9	91.4
80°	75.4	75.2	75.1	74.9	74.7	74.5	74.1	73.8	73.5	73.1	72.6
82.5°	56.1	56.0	56.0	56.0	55.9	55.8	55.6	55.4	55.2	55.0	54.4
85°	30.9	30.8	30.6	30.4	30.3	30.1	29.9	29.8	29.6	29.4	28.9
87.5°	10.9	10.9	10.9	10.9	10.8	10.9	11.1	11.3	11.5	11.6	11.2
90°	0.5	1.7	2.9	4.1	5.4	7.1	9.3	11.5	13.7	16.1	15.9
92.5°	8.2	9.1	9.9	10.8	11.7	12.4	12.9	13.5	14.0	14.5	14.5
95°	23.8	24.8	25.9	26.9	27.9	28.5	28.7	28.9	29.1	29.3	29.3
97.5°	43.4	44.3	45.2	46.2	47.1	47.7	48.1	48.5	48.9	49.2	49.2
100°	58.1	58.9	59.7	60.6	61.4	61.9	62.2	62.5	62.8	63.1	63.1
102.5°	73.5	74.1	74.7	75.4	76.0	76.6	77.0	77.4	77.8	78.2	78.3
105°	98.4	98.7	99.0	99.3	99.6	99.9	100.1	100.3	100.5	100.7	100.9
107.5°	123.4	123.9	124.3	124.8	125.2	125.4	125.4	125.4	125.4	125.4	125.5
110°	139.6	140.2	140.8	141.4	142.0	142.3	142.3	142.3	142.3	142.3	142.3



TEST NUMBER: P331500-840

CATALOG NUMBER: S122DIW-S485D435U840-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	157.1	157.7	158.3	159.0	159.6	159.9	159.8	159.7	159.6	159.5	159.3
115°	183.0	183.6	184.2	184.8	185.4	185.6	185.4	185.2	185.0	184.8	184.7
117.5°	208.8	209.6	210.5	211.3	212.1	212.2	211.7	211.1	210.5	210.0	209.6
120°	226.0	226.8	227.6	228.4	229.2	229.2	228.4	227.6	226.8	226.0	226.0
122.5°	241.8	242.8	243.7	244.7	245.7	245.9	245.3	244.7	244.2	243.6	243.4
125°	266.3	267.2	268.1	269.0	269.9	270.2	269.9	269.6	269.3	269.0	268.7
127.5°	290.1	291.3	292.5	293.7	294.8	295.2	294.9	294.5	294.1	293.8	293.4
130°	305.2	306.5	307.8	309.1	310.4	311.0	310.8	310.6	310.4	310.2	310.0
132.5°	322.0	323.1	324.2	325.3	326.3	326.9	326.9	327.0	327.0	327.0	326.6
135°	344.6	345.7	346.8	347.9	349.0	349.6	349.8	350.0	350.2	350.4	350.3
137.5°	368.2	369.1	370.0	370.9	371.8	372.4	372.7	373.0	373.2	373.5	373.4
140°	382.5	383.4	384.4	385.3	386.2	386.9	387.4	387.9	388.4	388.9	388.9
142.5°	397.2	398.1	399.0	399.9	400.8	401.4	401.7	402.1	402.4	402.8	402.9
145°	418.2	418.9	419.6	420.3	421.0	421.7	422.3	422.9	423.5	424.1	424.2
147.5°	437.0	437.8	438.7	439.5	440.4	441.0	441.4	441.8	442.2	442.6	442.8
150°	449.8	450.4	451.0	451.6	452.2	452.7	453.1	453.5	453.9	454.3	454.6
152.5°	461.1	461.7	462.3	462.9	463.5	464.1	464.5	465.0	465.5	466.1	466.5
155°	478.1	478.4	478.7	479.1	479.4	479.7	480.0	480.3	480.6	480.9	481.4
157.5°	492.7	492.9	493.1	493.3	493.5	493.6	493.8	494.0	494.2	494.4	495.1
160°	501.5	501.7	501.9	502.1	502.3	502.4	502.5	502.6	502.7	502.8	503.4
162.5°	509.5	509.6	509.6	509.6	509.7	509.8	509.9	510.0	510.1	510.2	510.8
165°	520.2	520.1	520.0	519.9	519.8	519.8	519.8	519.8	519.8	519.8	520.5
167.5°	529.2	528.9	528.6	528.3	528.0	527.8	527.8	527.8	527.8	527.8	528.5
170°	533.9	533.6	533.3	533.0	532.7	532.5	532.4	532.3	532.2	532.1	532.8
172.5°	537.2	536.9	536.6	536.3	536.0	535.8	535.7	535.6	535.5	535.4	536.1
175°	541.3	541.0	540.7	540.4	540.1	539.8	539.6	539.4	539.2	539.0	539.7
177.5°	542.9	542.7	542.4	542.2	541.9	541.7	541.6	541.4	541.2	541.1	541.6
180°	542.2	542.2	542.2	542.2	542.2	542.2	542.2	542.2	542.2	542.2	542.2



TEST NUMBER: P331500-840

CATALOG NUMBER: S122DIW-S485D435U840-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	784.4	784.4	784.4	784.4	784.4	784.4	784.4	784.4
2.5°	781.0	782.3	783.7	784.3	784.0	783.7	783.5	783.2
5°	775.8	777.1	778.4	778.9	778.6	778.2	777.9	777.6
7.5°	767.0	768.3	769.7	770.1	769.8	769.4	769.0	768.7
10°	759.1	760.5	761.8	762.2	761.7	761.2	760.7	760.2
12.5°	749.9	750.8	751.7	752.0	751.6	751.3	750.9	750.5
15°	733.7	734.4	735.0	734.9	734.1	733.3	732.5	731.5
17.5°	714.4	715.2	716.0	715.9	715.1	714.4	713.6	712.8
20°	699.4	699.9	700.4	700.3	699.6	698.9	698.3	697.6
22.5°	683.5	683.6	683.7	683.6	683.2	682.8	682.4	682.0
25°	657.6	657.9	658.2	658.2	657.9	657.6	657.2	656.9
27.5°	632.1	631.6	631.1	630.5	629.7	628.8	628.0	627.2
30°	612.2	611.7	611.2	610.6	609.9	609.3	608.5	607.8
32.5°	592.7	591.8	590.9	590.1	589.4	588.8	588.0	587.3
35°	561.4	560.4	559.4	558.5	557.6	556.7	555.9	555.1
37.5°	530.0	528.8	527.6	526.4	525.6	524.8	524.0	523.3
40°	508.4	506.9	505.3	504.2	503.5	502.9	502.2	501.5
42.5°	487.0	485.3	483.6	482.4	481.4	480.5	479.6	478.6
45°	454.1	452.3	450.4	449.2	448.5	447.9	447.2	446.5
47.5°	420.0	418.0	416.1	414.7	413.6	412.7	411.7	410.7
50°	398.1	395.7	393.3	391.7	390.9	390.1	389.2	388.4
52.5°	375.4	373.3	371.4	369.9	368.8	367.7	366.6	365.5
55°	341.4	339.4	337.4	336.0	335.1	334.3	333.5	332.6
57.5°	306.2	304.2	302.3	300.9	300.2	299.6	299.0	298.3
60°	282.9	281.0	279.2	278.0	277.5	277.0	276.5	276.0
62.5°	260.8	259.1	257.4	256.3	255.6	255.0	254.4	253.7
65°	227.0	225.5	224.0	222.8	222.0	221.2	220.4	219.4
67.5°	193.6	192.4	191.3	190.4	189.7	188.9	188.3	187.6
70°	171.9	170.7	169.6	168.6	167.9	167.2	166.6	165.9
72.5°	151.4	150.2	149.1	148.1	147.6	147.0	146.5	146.0
75°	119.4	118.5	117.4	117.0	117.4	117.8	118.1	118.5
77.5°	90.9	90.4	89.9	89.4	88.9	88.5	88.0	87.5
80°	72.1	71.6	71.2	70.7	70.4	70.1	69.7	69.4
82.5°	53.8	53.1	52.5	52.1	52.1	52.0	51.9	51.9
85°	28.4	27.9	27.4	27.1	26.9	26.8	26.6	26.4
87.5°	10.8	10.3	9.9	9.6	9.5	9.4	9.3	9.2
90°	15.7	15.5	15.2	15.1	15.2	15.3	15.5	15.6
92.5°	14.6	14.6	14.7	14.7	14.7	14.7	14.8	14.8
95°	29.3	29.3	29.3	29.2	29.0	28.8	28.6	28.4
97.5°	49.2	49.2	49.2	49.2	49.2	49.2	49.2	49.2
100°	63.1	63.1	63.1	63.1	63.0	62.9	62.8	62.7
102.5°	78.3	78.4	78.5	78.5	78.4	78.3	78.2	78.1
105°	101.1	101.3	101.5	101.6	101.6	101.6	101.6	101.6
107.5°	125.6	125.7	125.8	125.6	125.1	124.6	124.2	123.7
110°	142.3	142.3	142.3	142.1	141.8	141.5	141.2	140.9



TEST NUMBER: P331500-840

CATALOG NUMBER: S122DIW-S485D435U840-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	159.1	158.8	158.5	158.2	158.0	157.8	157.6	157.4
115°	184.6	184.5	184.4	184.2	183.9	183.6	183.3	183.0
117.5°	209.4	209.1	208.9	208.6	208.3	208.0	207.7	207.4
120°	226.0	226.0	226.0	225.9	225.6	225.3	225.0	224.7
122.5°	243.1	242.9	242.6	242.4	242.2	242.0	241.7	241.5
125°	268.4	268.1	267.8	267.6	267.5	267.4	267.3	267.2
127.5°	293.0	292.7	292.3	292.0	291.5	291.2	290.9	290.6
130°	309.8	309.6	309.4	309.1	308.7	308.3	307.9	307.5
132.5°	326.2	325.7	325.3	324.9	324.6	324.2	323.9	323.6
135°	350.2	350.1	350.0	349.8	349.5	349.2	348.9	348.6
137.5°	373.3	373.2	373.2	372.9	372.5	372.1	371.7	371.3
140°	388.9	388.9	388.9	388.7	388.3	387.9	387.5	387.1
142.5°	402.9	403.0	403.1	402.9	402.5	402.1	401.7	401.3
145°	424.3	424.4	424.5	424.3	423.9	423.5	423.1	422.7
147.5°	443.0	443.3	443.5	443.4	443.0	442.6	442.2	441.9
150°	454.9	455.2	455.6	455.6	455.2	454.9	454.6	454.3
152.5°	466.8	467.2	467.6	467.6	467.2	466.8	466.5	466.1
155°	481.9	482.4	482.9	483.0	482.7	482.4	482.1	481.8
157.5°	495.7	496.4	497.2	497.3	496.8	496.2	495.8	495.3
160°	504.0	504.6	505.2	505.3	504.9	504.5	504.1	503.7
162.5°	511.5	512.2	512.9	513.0	512.5	512.0	511.5	511.1
165°	521.2	521.9	522.6	522.7	522.2	521.7	521.2	520.7
167.5°	529.2	529.9	530.6	530.7	530.1	529.6	529.1	528.6
170°	533.5	534.2	534.9	535.0	534.4	533.8	533.2	532.6
172.5°	536.8	537.6	538.3	538.3	537.7	537.0	536.4	535.8
175°	540.4	541.1	541.8	541.9	541.3	540.7	540.1	539.5
177.5°	542.1	542.5	543.0	543.0	542.5	542.1	541.6	541.1
180°	542.2	542.2	542.2	542.2	542.2	542.2	542.2	542.2

(END OF REPORT)