

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331501-840

Luminaire Tested: **S122DIW-S485D710U840-4F0-1E-UDD-A**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P331501-840  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S122DIW-S485D710U840-4F0-1E-UDD-A  
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 485 LUMENS PER FOOT, ASYMMETRIC DIFFUSER  
UPLIGHT 710 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 5030.6 lumens  
Efficiency: N/A  
Efficacy: 133.8 lumens/watt  
Spacing Criteria (0/90/45): 1.08 / 1.16 / 1.23  
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')  
CIE Type: General Diffuse


Input Watts (W): 37.6  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P331501-840

CATALOG NUMBER: S122DIW-S485D710U840-4F0-1E-UDD-A

### Luminous Intensity Polar Plot





TEST NUMBER: P331501-840

CATALOG NUMBER: S122DIW-S485D710U840-4F0-1E-UDD-A

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	105	105	105	105	96	96	96	96	79	79	79	64	64	64	50	50	50	43
1	97	93	89	85	88	85	82	79	70	68	66	57	55	54	45	44	43	37
2	88	81	75	70	81	75	70	65	62	58	55	50	48	46	40	38	37	32
3	81	72	65	59	74	66	60	55	55	51	47	45	42	39	36	33	32	27
4	74	64	56	50	68	59	52	47	49	44	40	40	37	34	32	30	28	24
5	68	57	49	43	62	53	46	41	44	39	35	36	33	30	29	26	24	21
6	63	51	43	38	57	47	40	35	40	35	31	33	29	26	27	24	22	19
7	58	46	39	33	53	43	36	31	36	31	27	30	26	23	24	22	19	17
8	54	42	35	29	49	39	32	28	33	28	24	28	24	21	22	20	17	15
9	50	39	31	26	46	36	29	25	30	25	22	25	22	19	21	18	16	14
10	47	35	28	24	43	33	27	22	28	23	20	24	20	17	19	17	15	13

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	15844	15844	15844	15844
5°	17763	15948	14131	15948
10°	20354	15816	12231	15816
15°	22519	15527	10805	15527
20°	22175	15216	9850	15216
25°	19996	14801	9246	14801
30°	16524	14139	8804	14139
35°	12043	13448	8489	13448
40°	9619	12631	8315	12631
45°	8405	11686	8079	11686
50°	7902	10771	7920	10771
55°	7282	9841	7707	9841
60°	6675	8854	7379	8854
65°	6082	7966	7060	7966
70°	5519	7105	6590	7105
75°	4897	6145	5833	6145
80°	4203	5086	4695	5086
85°	3779	3779	2779	3779



TEST NUMBER: P331501-840

CATALOG NUMBER: S122DIW-S485D710U840-4F0-1E-UDD-A

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	93.5	1.9
10°-20°	271.7	5.4
20°-30°	394.3	7.8
30°-40°	416.1	8.3
40°-50°	368.4	7.3
50°-60°	294.0	5.8
60°-70°	199.8	4.0
70°-80°	102.5	2.0
80°-90°	27.1	0.5
90°-100°	32.6	0.6
100°-110°	119.5	2.4
110°-120°	319.5	6.4
120°-130°	527.3	10.5
130°-140°	560.8	11.1
140°-150°	521.3	10.4
150°-160°	419.1	8.3
160°-170°	270.1	5.4
170°-180°	93.0	1.8
0°-30°	759.5	15.1
0°-40°	1175.6	23.4
0°-60°	1838.0	36.5
0°-90°	2167.4	43.1
90°-120°	471.6	9.4
90°-150°	2081.0	41.4
90°-180°	2863.0	56.9
0°-180°	5030.6	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	981	981	981	981	981	
5°	1096	984	872	984	1096	109
15°	1347	929	646	929	1347	372
25°	1122	831	519	831	1122	507
35°	611	682	431	682	611	397
45°	368	512	354	512	368	289
55°	259	350	274	350	259	232
65°	159	208	185	208	159	158
75°	78	98	94	98	78	84
85°	20	20	15	20	20	23
90°	19	1	19	1	19	9
95°	30	46	30	46	30	28
105°	54	215	54	215	54	56
115°	58	406	58	406	58	145
125°	604	575	604	575	604	523
135°	735	711	735	711	735	566
145°	838	825	838	825	838	524
155°	909	908	909	908	909	419
165°	955	957	955	957	955	270
175°	974	979	974	979	974	93
180°	977	977	977	977	977	



TEST NUMBER: P331501-840

CATALOG NUMBER: S122DIW-S485D710U840-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	981.3	981.3	981.3	981.3	981.3	981.3	981.3	981.3	981.3	981.3	981.3
2.5°	1026.6	1026.9	1027.4	1022.7	1022.1	1022.1	1017.8	1014.2	1010.0	1004.2	1004.8
5°	1096.0	1100.1	1101.7	1097.1	1090.4	1089.5	1083.2	1072.6	1062.8	1054.9	1049.2
7.5°	1178.8	1180.4	1176.8	1170.8	1165.8	1156.7	1144.8	1133.1	1116.7	1101.7	1090.6
10°	1241.5	1243.9	1237.4	1228.7	1221.5	1211.0	1193.7	1175.9	1154.5	1133.7	1117.1
12.5°	1289.2	1294.8	1286.6	1285.5	1273.1	1258.7	1238.0	1229.0	1198.8	1169.9	1152.1
15°	1347.2	1346.8	1347.6	1340.4	1331.3	1329.1	1307.2	1283.4	1240.8	1223.9	1194.4
17.5°	1330.4	1336.2	1338.8	1338.7	1338.5	1337.1	1330.0	1315.0	1293.6	1266.2	1232.2
20°	1290.6	1298.1	1299.3	1308.0	1312.8	1319.3	1321.9	1317.8	1304.5	1281.5	1252.1
22.5°	1229.0	1231.1	1234.7	1248.2	1258.8	1274.9	1283.2	1297.2	1292.1	1280.9	1256.4
25°	1122.4	1118.6	1131.8	1138.6	1163.1	1188.7	1207.2	1227.6	1245.7	1256.7	1249.5
27.5°	994.3	988.7	1008.5	1026.4	1046.3	1074.1	1102.9	1136.9	1165.2	1200.6	1212.7
30°	886.3	889.7	908.6	927.8	958.0	997.1	1029.6	1066.9	1107.3	1146.9	1174.4
32.5°	769.8	782.8	794.8	824.3	850.8	894.5	942.1	988.8	1039.2	1084.1	1126.7
35°	611.0	626.0	642.7	664.2	701.5	744.9	791.2	854.2	922.9	984.3	1034.9
37.5°	514.2	511.9	521.4	536.9	567.1	602.2	655.5	717.8	798.6	870.8	942.1
40°	456.4	454.8	461.6	475.9	499.0	524.6	571.4	626.0	701.1	789.3	874.2
42.5°	416.5	417.4	421.2	431.3	447.1	468.2	503.2	549.8	618.4	701.6	792.7
45°	368.1	370.7	374.9	379.8	388.8	406.2	425.8	459.0	513.3	582.7	672.5
47.5°	333.3	333.4	337.5	341.8	347.2	357.0	373.0	393.8	432.1	488.7	565.8
50°	314.6	311.8	314.9	318.3	324.0	330.7	341.3	360.9	386.6	432.2	496.7
52.5°	291.6	291.6	294.4	295.7	300.7	307.5	317.2	330.7	354.0	389.7	442.7
55°	258.7	260.6	262.2	264.4	268.9	273.8	281.3	290.4	308.5	335.3	374.5
57.5°	227.8	228.4	229.9	234.2	237.1	241.6	248.7	257.0	268.7	288.6	318.1
60°	206.7	206.7	209.6	211.6	215.3	219.8	225.5	233.5	244.0	260.2	284.0
62.5°	187.3	187.0	188.2	191.4	194.2	198.4	204.1	210.9	220.8	235.2	254.7
65°	159.2	158.4	160.7	161.4	164.4	168.5	173.1	180.3	188.2	198.7	216.1
67.5°	132.0	132.9	134.1	135.5	137.2	141.6	144.6	149.7	156.3	165.1	176.9
70°	116.9	116.9	116.9	118.1	120.3	122.6	125.6	129.8	136.1	143.7	154.2
72.5°	100.0	101.2	102.4	101.8	104.6	105.9	109.6	111.9	118.1	122.9	132.2
75°	78.5	78.5	78.5	80.3	81.5	82.6	84.8	87.2	90.2	96.1	101.1
77.5°	58.6	58.4	58.8	59.2	60.4	61.8	62.4	64.5	67.3	70.1	74.2
80°	45.2	46.0	46.4	47.2	47.2	47.9	48.3	50.9	52.8	54.7	57.4
82.5°	35.0	35.1	35.2	35.3	35.6	36.2	37.1	38.0	38.6	40.2	42.2
85°	20.4	20.0	20.0	20.7	20.4	20.4	21.1	21.9	21.9	22.2	23.4
87.5°	11.6	11.6	11.8	11.5	11.4	11.6	11.4	11.0	11.1	11.3	11.3
90°	19.1	18.8	18.5	18.2	17.9	17.3	16.5	15.8	14.9	14.1	12.9
92.5°	19.1	18.9	18.7	18.5	18.4	18.1	17.7	17.3	16.8	16.4	15.8
95°	30.4	30.6	30.7	30.9	31.0	30.7	29.9	29.2	28.4	27.6	26.5
97.5°	40.6	40.4	40.2	40.0	39.8	39.4	38.8	38.2	37.6	36.9	34.3
100°	47.4	47.1	46.8	46.5	46.2	45.3	44.0	42.8	41.5	40.3	37.7
102.5°	50.8	50.3	49.9	49.5	49.0	48.0	46.4	44.7	43.0	41.4	63.7
105°	53.7	53.1	52.5	51.8	51.2	50.0	48.3	46.6	44.8	43.1	86.0
107.5°	55.2	54.6	54.0	53.4	52.8	53.3	55.1	56.9	58.6	60.4	111.8
110°	55.8	55.2	54.6	53.9	53.3	60.9	76.5	92.3	108.1	123.7	169.2



TEST NUMBER: P331501-840

CATALOG NUMBER: S122DIW-S485D710U840-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	56.5	55.9	55.4	54.9	54.4	82.8	140.2	197.4	254.8	312.0	323.3
115°	58.0	69.3	80.6	91.9	103.2	145.2	217.9	290.7	363.5	436.2	432.2
117.5°	236.7	273.9	311.0	348.2	385.4	412.7	430.3	448.0	465.5	483.1	480.4
120°	431.2	452.4	473.6	494.8	516.0	525.7	523.8	522.0	520.1	518.2	515.3
122.5°	538.2	542.3	546.3	550.5	554.6	556.1	554.9	553.8	552.7	551.6	548.5
125°	604.4	604.0	603.5	603.0	602.6	601.8	600.7	599.6	598.4	597.3	594.4
127.5°	646.3	646.2	646.1	646.0	645.9	645.1	643.5	641.9	640.3	638.6	636.4
130°	672.4	672.5	672.7	672.8	673.0	672.2	670.4	668.7	667.0	665.3	663.5
132.5°	697.8	697.9	698.1	698.2	698.4	697.7	696.3	694.8	693.3	691.9	690.1
135°	734.6	734.9	735.2	735.5	735.8	735.2	733.6	732.1	730.4	728.9	727.5
137.5°	768.0	768.6	769.1	769.6	770.2	769.7	768.1	766.6	765.1	763.6	761.9
140°	789.0	789.7	790.5	791.3	792.1	791.8	790.4	789.0	787.6	786.2	784.4
142.5°	809.3	810.1	810.9	811.7	812.4	812.2	810.9	809.6	808.4	807.1	805.1
145°	837.8	838.5	839.3	840.1	840.9	840.7	839.6	838.5	837.5	836.4	833.6
147.5°	862.7	863.4	864.1	864.7	865.5	865.4	864.5	863.7	862.9	862.0	859.4
150°	878.1	878.8	879.6	880.4	881.2	881.1	880.2	879.2	878.3	877.4	874.8
152.5°	891.0	892.1	893.1	894.1	895.2	895.2	894.3	893.3	892.4	891.5	889.1
155°	909.2	910.4	911.7	912.9	914.1	914.3	913.4	912.4	911.5	910.6	908.7
157.5°	925.6	927.0	928.2	929.4	930.6	930.7	929.6	928.6	927.5	926.3	925.0
160°	935.3	936.4	937.5	938.6	939.7	939.8	938.9	937.9	937.0	936.0	935.0
162.5°	943.2	944.5	945.9	947.3	948.7	948.8	947.7	946.6	945.5	944.5	943.7
165°	955.1	956.2	957.4	958.4	959.5	959.5	958.4	957.4	956.2	955.1	954.6
167.5°	962.6	964.0	965.4	966.8	968.3	968.4	967.3	966.2	965.1	964.0	963.6
170°	967.1	968.6	970.0	971.4	972.8	972.9	971.8	970.8	969.7	968.6	968.3
172.5°	970.5	971.9	973.3	974.7	976.1	976.3	975.2	974.1	973.0	971.9	971.6
175°	973.5	975.0	976.6	978.2	979.8	980.0	978.9	977.9	976.7	975.6	975.3
177.5°	975.3	976.4	977.5	978.8	979.9	980.0	979.1	978.3	977.3	976.4	976.3
180°	977.0	977.0	977.0	977.0	977.0	977.0	977.0	977.0	977.0	977.0	977.0



TEST NUMBER: P331501-840

CATALOG NUMBER: S122DIW-S485D710U840-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	981.3	981.3	981.3	981.3	981.3	981.3	981.3	981.3	981.3	981.3	981.3
2.5°	1006.9	1004.5	1003.0	997.6	992.8	988.0	986.4	987.0	980.4	974.1	971.4
5°	1046.2	1038.6	1031.5	1021.3	1009.3	996.0	989.3	984.0	970.8	956.4	948.2
7.5°	1081.4	1070.6	1056.7	1037.6	1020.1	999.3	986.0	974.4	955.0	934.8	922.5
10°	1102.8	1088.0	1070.4	1046.9	1025.4	1000.2	982.5	964.7	942.1	918.0	902.9
12.5°	1121.2	1101.4	1083.9	1053.9	1028.4	996.8	975.8	950.9	927.1	898.4	883.5
15°	1165.0	1128.4	1095.2	1061.3	1030.0	985.8	962.5	928.9	897.6	862.1	845.2
17.5°	1198.8	1157.7	1105.5	1062.4	1025.8	976.9	942.6	902.4	865.4	824.9	801.8
20°	1218.2	1171.0	1114.8	1063.6	1019.8	964.0	926.7	885.6	842.1	796.5	771.6
22.5°	1229.6	1180.1	1124.5	1059.0	1007.7	953.4	906.5	861.4	817.4	768.2	742.0
25°	1233.2	1188.0	1129.1	1055.2	992.6	931.2	874.5	830.8	777.7	731.6	693.6
27.5°	1215.3	1182.9	1126.3	1048.1	975.2	903.3	840.3	790.7	734.6	684.7	646.3
30°	1193.3	1174.4	1119.3	1040.9	961.3	884.0	814.7	758.4	702.7	652.1	612.9
32.5°	1159.2	1155.1	1106.7	1030.7	946.5	859.6	787.8	730.9	669.1	619.5	582.1
35°	1092.2	1110.3	1079.7	1007.7	918.7	824.9	747.1	682.3	618.1	570.6	535.5
37.5°	1002.5	1047.4	1039.5	974.1	881.1	787.0	701.1	633.4	572.3	524.3	489.9
40°	940.6	997.9	1006.2	948.5	854.6	757.7	666.8	599.3	539.7	495.9	461.2
42.5°	874.2	941.2	964.0	917.8	825.7	726.9	636.0	566.1	507.2	464.5	433.8
45°	763.0	851.6	892.7	866.3	777.3	676.2	582.7	511.8	458.3	418.3	394.5
47.5°	658.9	755.8	811.1	801.7	723.5	623.4	531.0	462.9	410.8	378.9	357.6
50°	585.3	684.9	751.6	754.7	684.9	585.7	492.9	428.8	380.9	351.1	333.8
52.5°	521.4	616.4	689.2	705.2	641.8	546.4	458.8	395.1	352.8	325.5	309.9
55°	437.9	518.2	599.0	628.3	577.4	486.9	405.8	349.6	310.0	291.1	277.6
57.5°	364.1	431.0	505.5	538.1	506.6	429.2	353.1	304.4	272.3	255.7	245.3
60°	325.1	377.9	444.2	483.1	456.0	387.0	320.5	274.2	247.8	233.1	223.3
62.5°	288.9	335.7	391.7	427.3	412.5	347.4	288.0	247.0	224.3	210.5	203.4
65°	238.3	275.3	318.7	351.5	341.7	292.3	243.7	208.5	190.5	179.6	173.9
67.5°	196.2	223.0	253.1	281.8	273.9	238.8	199.9	172.5	159.0	149.6	146.2
70°	169.8	190.1	216.8	239.8	233.5	204.8	173.9	150.5	138.8	130.9	127.4
72.5°	144.4	161.1	181.6	200.4	196.0	172.2	146.4	128.8	119.8	112.5	109.7
75°	109.0	121.8	134.3	146.7	145.6	127.1	112.0	98.5	91.3	85.6	84.5
77.5°	80.5	87.7	96.1	103.5	101.5	90.9	79.1	71.3	66.0	62.2	61.6
80°	61.5	65.6	71.7	77.0	74.3	69.8	60.4	54.7	50.9	47.2	45.6
82.5°	44.5	48.8	52.3	55.2	53.2	49.0	43.1	39.3	37.1	34.4	33.8
85°	23.4	25.7	27.2	27.9	27.2	24.5	21.9	20.4	18.5	17.4	17.0
87.5°	11.4	11.1	10.9	11.2	9.9	9.6	8.1	6.8	6.9	6.9	6.6
90°	11.6	10.4	9.1	7.6	5.9	4.1	2.4	0.7	2.4	4.1	5.9
92.5°	15.1	14.5	13.9	13.6	13.8	13.9	14.1	14.2	14.1	13.9	13.8
95°	25.3	24.2	23.1	25.2	30.4	35.5	40.8	45.9	40.8	35.5	30.4
97.5°	31.8	29.3	26.8	32.7	47.4	62.0	76.5	91.2	76.5	62.0	47.4
100°	34.9	32.3	29.6	39.1	60.6	82.1	103.6	125.1	103.6	82.1	60.6
102.5°	86.1	108.5	130.8	144.2	148.8	153.3	157.9	162.5	157.9	153.3	148.8
105°	128.9	171.8	214.7	233.8	229.0	224.4	219.6	214.9	219.6	224.4	229.0
107.5°	163.3	214.7	266.1	289.9	286.1	282.4	278.5	274.7	278.5	282.4	286.1
110°	214.5	259.9	305.3	326.4	323.1	319.8	316.5	313.2	316.5	319.8	323.1





TEST NUMBER: P331501-840

CATALOG NUMBER: S122DIW-S485D710U840-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	334.5	345.7	356.9	361.0	358.1	355.3	352.3	349.4	352.3	355.3	358.1
115°	428.4	424.4	420.5	417.2	414.5	411.8	409.2	406.5	409.2	411.8	414.5
117.5°	477.8	475.0	472.3	469.5	466.5	463.5	460.5	457.6	460.5	463.5	466.5
120°	512.5	509.7	506.9	504.3	501.9	499.6	497.3	494.8	497.3	499.6	501.9
122.5°	545.4	542.3	539.3	536.4	534.0	531.5	529.1	526.5	529.1	531.5	534.0
125°	591.4	588.4	585.4	582.9	580.9	578.9	576.8	574.7	576.8	578.9	580.9
127.5°	634.2	632.0	629.8	627.5	625.2	623.0	620.7	618.4	620.7	623.0	625.2
130°	661.8	660.0	658.3	656.2	653.7	651.2	648.6	646.1	648.6	651.2	653.7
132.5°	688.3	686.6	684.9	683.0	680.9	678.7	676.6	674.5	676.6	678.7	680.9
135°	726.1	724.7	723.3	721.2	718.7	716.2	713.7	711.2	713.7	716.2	718.7
137.5°	760.3	758.7	757.1	755.4	753.7	751.9	750.1	748.4	750.1	751.9	753.7
140°	782.6	780.9	779.2	777.7	776.5	775.2	774.0	772.7	774.0	775.2	776.5
142.5°	803.1	801.1	799.1	797.6	796.5	795.4	794.2	793.0	794.2	795.4	796.5
145°	831.0	828.3	825.7	824.4	824.6	824.8	824.9	825.1	824.9	824.8	824.6
147.5°	856.8	854.1	851.5	850.5	851.1	851.7	852.3	852.8	852.3	851.7	851.1
150°	872.3	869.8	867.3	866.6	867.7	868.8	869.9	871.0	869.9	868.8	867.7
152.5°	886.7	884.3	881.9	881.3	882.5	883.8	885.0	886.3	885.0	883.8	882.5
155°	906.8	904.9	903.0	902.8	904.2	905.6	907.1	908.5	907.1	905.6	904.2
157.5°	923.7	922.4	921.1	921.1	922.2	923.4	924.6	925.8	924.6	923.4	922.2
160°	934.1	933.2	932.2	932.2	933.2	934.1	935.0	936.0	935.0	934.1	933.2
162.5°	942.9	942.0	941.2	941.3	942.2	943.2	944.1	945.0	944.1	943.2	942.2
165°	954.1	953.7	953.2	953.4	954.4	955.3	956.2	957.3	956.2	955.3	954.4
167.5°	963.1	962.7	962.3	962.5	963.4	964.4	965.3	966.2	965.3	964.4	963.4
170°	968.0	967.6	967.2	967.6	968.6	969.5	970.4	971.4	970.4	969.5	968.6
172.5°	971.3	971.0	970.7	971.0	971.9	972.9	973.8	974.7	973.8	972.9	971.9
175°	975.0	974.6	974.3	974.7	975.8	976.9	978.1	979.2	978.1	976.9	975.8
177.5°	976.2	976.0	975.9	976.3	977.2	978.1	979.0	979.9	979.0	978.1	977.2
180°	977.0	977.0	977.0	977.0	977.0	977.0	977.0	977.0	977.0	977.0	977.0



TEST NUMBER: P331501-840

CATALOG NUMBER: S122DIW-S485D710U840-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	981.3	981.3	981.3	981.3	981.3	981.3	981.3	981.3	981.3	981.3	981.3
2.5°	968.4	966.5	960.2	956.8	951.5	946.3	943.0	944.5	945.7	945.1	944.2
5°	940.6	933.4	922.5	913.0	906.3	893.8	888.6	886.0	883.6	881.0	878.4
7.5°	907.6	896.3	880.6	867.2	854.4	839.0	830.2	824.9	819.4	813.4	808.2
10°	884.0	868.2	851.6	832.7	817.7	803.7	791.2	782.9	775.4	768.2	763.0
12.5°	859.3	841.0	820.5	794.8	778.1	758.1	756.3	741.6	729.8	725.4	719.2
15°	819.9	794.3	768.2	737.7	724.5	706.4	695.1	683.8	673.6	666.4	664.5
17.5°	775.2	741.9	716.1	694.2	672.6	654.0	643.6	634.5	626.1	616.5	615.3
20°	741.0	712.5	684.2	664.9	642.7	623.8	611.0	601.9	594.7	589.1	584.2
22.5°	708.8	677.4	651.6	630.5	608.5	593.3	583.2	574.5	568.6	562.3	557.6
25°	657.0	632.5	604.2	580.5	562.3	552.5	544.2	536.6	532.9	528.8	523.5
27.5°	611.7	584.4	558.0	539.6	523.6	514.9	509.1	503.9	500.4	498.0	494.9
30°	579.7	552.1	531.4	513.3	500.1	491.4	487.7	484.6	480.5	479.0	477.5
32.5°	548.9	524.1	506.3	490.7	478.1	472.4	469.0	466.3	463.0	461.5	458.5
35°	505.3	484.6	467.3	458.6	448.4	443.5	440.9	437.1	434.1	432.6	432.2
37.5°	464.4	446.4	434.9	423.8	419.5	416.5	412.9	410.3	409.4	409.2	408.8
40°	437.9	423.1	412.9	403.9	402.0	397.5	394.5	392.2	392.2	392.6	392.2
42.5°	413.7	400.5	391.5	383.7	381.5	378.8	375.8	375.7	376.3	377.5	376.3
45°	377.2	367.7	361.3	357.5	353.4	350.7	350.3	351.5	351.8	352.2	353.4
47.5°	343.5	337.2	331.4	327.3	325.5	325.0	324.6	326.5	328.3	329.0	330.7
50°	323.6	316.4	311.5	308.9	307.4	306.6	307.4	309.6	311.1	313.1	314.2
52.5°	301.2	296.2	292.9	290.7	290.1	290.6	290.7	293.4	295.8	296.4	297.0
55°	270.4	266.6	265.9	262.5	264.0	263.6	265.5	267.0	269.2	271.6	272.0
57.5°	239.6	236.6	234.6	234.9	235.3	237.0	238.5	241.3	243.7	246.0	246.3
60°	219.1	217.6	216.5	216.5	217.2	219.5	221.4	224.0	225.5	227.0	228.1
62.5°	200.5	198.9	197.7	198.3	200.4	201.7	203.9	205.3	206.8	208.3	208.8
65°	170.9	170.1	171.3	172.0	172.4	174.2	176.9	178.0	179.6	180.3	182.9
67.5°	143.6	143.8	143.6	144.7	146.8	147.3	149.8	152.5	152.8	154.2	155.9
70°	125.2	125.9	126.7	127.4	129.4	130.1	132.0	133.1	134.6	135.7	136.9
72.5°	108.4	108.5	109.3	109.1	110.7	112.3	113.9	115.0	116.5	118.0	119.1
75°	83.3	83.3	84.1	84.5	86.3	88.3	87.9	88.7	90.2	91.7	92.4
77.5°	60.9	60.1	60.9	61.2	61.8	63.4	63.7	64.8	66.6	66.0	66.9
80°	46.4	45.2	46.4	46.8	46.8	48.7	48.7	49.4	50.5	49.4	50.5
82.5°	33.1	32.6	33.4	33.5	34.1	34.1	34.7	34.9	36.1	35.5	36.1
85°	16.6	16.3	16.6	16.3	16.6	17.0	17.0	16.6	16.6	17.4	16.3
87.5°	6.7	6.7	6.6	6.9	6.8	6.8	6.6	6.8	7.0	6.5	6.6
90°	7.6	9.1	10.4	11.6	12.9	14.1	14.9	15.8	16.5	17.3	17.9
92.5°	13.6	13.9	14.5	15.1	15.8	16.4	16.8	17.3	17.7	18.1	18.4
95°	25.2	23.1	24.2	25.3	26.5	27.6	28.4	29.2	29.9	30.7	31.0
97.5°	32.7	26.8	29.3	31.8	34.3	36.9	37.6	38.2	38.8	39.4	39.8
100°	39.1	29.6	32.3	34.9	37.7	40.3	41.5	42.8	44.0	45.3	46.2
102.5°	144.2	130.8	108.5	86.1	63.7	41.4	43.0	44.7	46.4	48.0	49.0
105°	233.8	214.7	171.8	128.9	86.0	43.1	44.8	46.6	48.3	50.0	51.2
107.5°	289.9	266.1	214.7	163.3	111.8	60.4	58.6	56.9	55.1	53.3	52.8
110°	326.4	305.3	259.9	214.5	169.2	123.7	108.1	92.3	76.5	60.9	53.3



TEST NUMBER: P331501-840

CATALOG NUMBER: S122DIW-S485D710U840-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	361.0	356.9	345.7	334.5	323.3	312.0	254.8	197.4	140.2	82.8	54.4
115°	417.2	420.5	424.4	428.4	432.2	436.2	363.5	290.7	217.9	145.2	103.2
117.5°	469.5	472.3	475.0	477.8	480.4	483.1	465.5	448.0	430.3	412.7	385.4
120°	504.3	506.9	509.7	512.5	515.3	518.2	520.1	522.0	523.8	525.7	516.0
122.5°	536.4	539.3	542.3	545.4	548.5	551.6	552.7	553.8	554.9	556.1	554.6
125°	582.9	585.4	588.4	591.4	594.4	597.3	598.4	599.6	600.7	601.8	602.6
127.5°	627.5	629.8	632.0	634.2	636.4	638.6	640.3	641.9	643.5	645.1	645.9
130°	656.2	658.3	660.0	661.8	663.5	665.3	667.0	668.7	670.4	672.2	673.0
132.5°	683.0	684.9	686.6	688.3	690.1	691.9	693.3	694.8	696.3	697.7	698.4
135°	721.2	723.3	724.7	726.1	727.5	728.9	730.4	732.1	733.6	735.2	735.8
137.5°	755.4	757.1	758.7	760.3	761.9	763.6	765.1	766.6	768.1	769.7	770.2
140°	777.7	779.2	780.9	782.6	784.4	786.2	787.6	789.0	790.4	791.8	792.1
142.5°	797.6	799.1	801.1	803.1	805.1	807.1	808.4	809.6	810.9	812.2	812.4
145°	824.4	825.7	828.3	831.0	833.6	836.4	837.5	838.5	839.6	840.7	840.9
147.5°	850.5	851.5	854.1	856.8	859.4	862.0	862.9	863.7	864.5	865.4	865.5
150°	866.6	867.3	869.8	872.3	874.8	877.4	878.3	879.2	880.2	881.1	881.2
152.5°	881.3	881.9	884.3	886.7	889.1	891.5	892.4	893.3	894.3	895.2	895.2
155°	902.8	903.0	904.9	906.8	908.7	910.6	911.5	912.4	913.4	914.3	914.1
157.5°	921.1	921.1	922.4	923.7	925.0	926.3	927.5	928.6	929.6	930.7	930.6
160°	932.2	932.2	933.2	934.1	935.0	936.0	937.0	937.9	938.9	939.8	939.7
162.5°	941.3	941.2	942.0	942.9	943.7	944.5	945.5	946.6	947.7	948.8	948.7
165°	953.4	953.2	953.7	954.1	954.6	955.1	956.2	957.4	958.4	959.5	959.5
167.5°	962.5	962.3	962.7	963.1	963.6	964.0	965.1	966.2	967.3	968.4	968.3
170°	967.6	967.2	967.6	968.0	968.3	968.6	969.7	970.8	971.8	972.9	972.8
172.5°	971.0	970.7	971.0	971.3	971.6	971.9	973.0	974.1	975.2	976.3	976.1
175°	974.7	974.3	974.6	975.0	975.3	975.6	976.7	977.9	978.9	980.0	979.8
177.5°	976.3	975.9	976.0	976.2	976.3	976.4	977.3	978.3	979.1	980.0	979.9
180°	977.0	977.0	977.0	977.0	977.0	977.0	977.0	977.0	977.0	977.0	977.0



TEST NUMBER: P331501-840

CATALOG NUMBER: S122DIW-S485D710U840-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	981.3	981.3	981.3	981.3	981.3	981.3	981.3	981.3	981.3	981.3	981.3
2.5°	941.2	940.6	940.6	937.9	940.6	940.6	941.2	944.2	945.1	945.7	944.5
5°	873.1	871.9	870.1	871.9	870.1	871.9	873.1	878.4	881.0	883.6	886.0
7.5°	805.8	801.2	800.5	796.1	800.5	801.2	805.8	808.2	813.4	819.4	824.9
10°	756.6	753.6	753.2	746.0	753.2	753.6	756.6	763.0	768.2	775.4	782.9
12.5°	719.1	711.9	713.4	709.2	713.4	711.9	719.1	719.2	725.4	729.8	741.6
15°	654.3	654.3	652.9	646.4	652.9	654.3	654.3	664.5	666.4	673.6	683.8
17.5°	607.8	607.0	603.4	605.2	603.4	607.0	607.8	615.3	616.5	626.1	634.5
20°	580.1	577.7	573.3	573.3	573.3	577.7	580.1	584.2	589.1	594.7	601.9
22.5°	553.8	553.6	548.9	550.4	548.9	553.6	553.8	557.6	562.3	568.6	574.5
25°	523.1	520.1	517.9	519.0	517.9	520.1	523.1	523.5	528.8	532.9	536.6
27.5°	494.0	492.3	492.2	489.1	492.2	492.3	494.0	494.9	498.0	500.4	503.9
30°	477.1	473.3	474.0	472.2	474.0	473.3	477.1	477.5	479.0	480.5	484.6
32.5°	457.8	456.5	455.7	454.0	455.7	456.5	457.8	458.5	461.5	463.0	466.3
35°	431.4	431.8	429.9	430.7	429.9	431.8	431.4	432.2	432.6	434.1	437.1
37.5°	408.5	409.7	408.8	409.0	408.8	409.7	408.5	408.8	409.2	409.4	410.3
40°	393.3	393.3	393.3	394.5	393.3	393.3	393.3	392.2	392.6	392.2	392.2
42.5°	378.9	378.3	377.7	377.6	377.7	378.3	378.9	376.3	377.5	376.3	375.7
45°	354.2	355.3	355.7	353.8	355.7	355.3	354.2	353.4	352.2	351.8	351.5
47.5°	331.7	331.8	331.7	333.4	331.7	331.8	331.7	330.7	329.0	328.3	326.5
50°	316.1	315.3	316.1	315.3	316.1	315.3	316.1	314.2	313.1	311.1	309.6
52.5°	299.4	299.6	299.1	299.0	299.1	299.6	299.4	297.0	296.4	295.8	293.4
55°	273.5	274.2	273.8	273.8	273.8	274.2	273.5	272.0	271.6	269.2	267.0
57.5°	246.5	247.2	247.7	246.0	247.7	247.2	246.5	246.3	246.0	243.7	241.3
60°	227.8	229.6	229.3	228.5	229.3	229.6	227.8	228.1	227.0	225.5	224.0
62.5°	210.6	211.3	211.2	211.1	211.2	211.3	210.6	208.8	208.3	206.8	205.3
65°	184.0	184.8	183.7	184.8	183.7	184.8	184.0	182.9	180.3	179.6	178.0
67.5°	155.4	155.7	156.5	157.0	156.5	155.7	155.4	155.9	154.2	152.8	152.5
70°	137.6	137.2	138.5	139.6	138.5	137.2	137.6	136.9	135.7	134.6	133.1
72.5°	119.0	119.8	119.4	120.3	119.4	119.8	119.0	119.1	118.0	116.5	115.0
75°	91.7	92.8	92.4	93.5	92.4	92.8	91.7	92.4	91.7	90.2	88.7
77.5°	66.2	66.3	66.2	66.9	66.2	66.3	66.2	66.9	66.0	66.6	64.8
80°	50.5	49.8	49.0	50.5	49.0	49.8	50.5	50.5	49.4	50.5	49.4
82.5°	35.1	35.6	34.8	34.8	34.8	35.6	35.1	36.1	35.5	36.1	34.9
85°	16.3	15.9	15.0	15.0	15.0	15.9	16.3	16.3	17.4	16.6	16.6
87.5°	6.7	6.4	6.5	6.3	6.5	6.4	6.7	6.6	6.5	7.0	6.8
90°	18.2	18.5	18.8	19.1	18.8	18.5	18.2	17.9	17.3	16.5	15.8
92.5°	18.5	18.7	18.9	19.1	18.9	18.7	18.5	18.4	18.1	17.7	17.3
95°	30.9	30.7	30.6	30.4	30.6	30.7	30.9	31.0	30.7	29.9	29.2
97.5°	40.0	40.2	40.4	40.6	40.4	40.2	40.0	39.8	39.4	38.8	38.2
100°	46.5	46.8	47.1	47.4	47.1	46.8	46.5	46.2	45.3	44.0	42.8
102.5°	49.5	49.9	50.3	50.8	50.3	49.9	49.5	49.0	48.0	46.4	44.7
105°	51.8	52.5	53.1	53.7	53.1	52.5	51.8	51.2	50.0	48.3	46.6
107.5°	53.4	54.0	54.6	55.2	54.6	54.0	53.4	52.8	53.3	55.1	56.9
110°	53.9	54.6	55.2	55.8	55.2	54.6	53.9	53.3	60.9	76.5	92.3



TEST NUMBER: P331501-840

CATALOG NUMBER: S122DIW-S485D710U840-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	54.9	55.4	55.9	56.5	55.9	55.4	54.9	54.4	82.8	140.2	197.4
115°	91.9	80.6	69.3	58.0	69.3	80.6	91.9	103.2	145.2	217.9	290.7
117.5°	348.2	311.0	273.9	236.7	273.9	311.0	348.2	385.4	412.7	430.3	448.0
120°	494.8	473.6	452.4	431.2	452.4	473.6	494.8	516.0	525.7	523.8	522.0
122.5°	550.5	546.3	542.3	538.2	542.3	546.3	550.5	554.6	556.1	554.9	553.8
125°	603.0	603.5	604.0	604.4	604.0	603.5	603.0	602.6	601.8	600.7	599.6
127.5°	646.0	646.1	646.2	646.3	646.2	646.1	646.0	645.9	645.1	643.5	641.9
130°	672.8	672.7	672.5	672.4	672.5	672.7	672.8	673.0	672.2	670.4	668.7
132.5°	698.2	698.1	697.9	697.8	697.9	698.1	698.2	698.4	697.7	696.3	694.8
135°	735.5	735.2	734.9	734.6	734.9	735.2	735.5	735.8	735.2	733.6	732.1
137.5°	769.6	769.1	768.6	768.0	768.6	769.1	769.6	770.2	769.7	768.1	766.6
140°	791.3	790.5	789.7	789.0	789.7	790.5	791.3	792.1	791.8	790.4	789.0
142.5°	811.7	810.9	810.1	809.3	810.1	810.9	811.7	812.4	812.2	810.9	809.6
145°	840.1	839.3	838.5	837.8	838.5	839.3	840.1	840.9	840.7	839.6	838.5
147.5°	864.7	864.1	863.4	862.7	863.4	864.1	864.7	865.5	865.4	864.5	863.7
150°	880.4	879.6	878.8	878.1	878.8	879.6	880.4	881.2	881.1	880.2	879.2
152.5°	894.1	893.1	892.1	891.0	892.1	893.1	894.1	895.2	895.2	894.3	893.3
155°	912.9	911.7	910.4	909.2	910.4	911.7	912.9	914.1	914.3	913.4	912.4
157.5°	929.4	928.2	927.0	925.6	927.0	928.2	929.4	930.6	930.7	929.6	928.6
160°	938.6	937.5	936.4	935.3	936.4	937.5	938.6	939.7	939.8	938.9	937.9
162.5°	947.3	945.9	944.5	943.2	944.5	945.9	947.3	948.7	948.8	947.7	946.6
165°	958.4	957.4	956.2	955.1	956.2	957.4	958.4	959.5	959.5	958.4	957.4
167.5°	966.8	965.4	964.0	962.6	964.0	965.4	966.8	968.3	968.4	967.3	966.2
170°	971.4	970.0	968.6	967.1	968.6	970.0	971.4	972.8	972.9	971.8	970.8
172.5°	974.7	973.3	971.9	970.5	971.9	973.3	974.7	976.1	976.3	975.2	974.1
175°	978.2	976.6	975.0	973.5	975.0	976.6	978.2	979.8	980.0	978.9	977.9
177.5°	978.8	977.5	976.4	975.3	976.4	977.5	978.8	979.9	980.0	979.1	978.3
180°	977.0	977.0	977.0	977.0	977.0	977.0	977.0	977.0	977.0	977.0	977.0



TEST NUMBER: P331501-840

CATALOG NUMBER: S122DIW-S485D710U840-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	981.3	981.3	981.3	981.3	981.3	981.3	981.3	981.3	981.3	981.3	981.3
2.5°	943.0	946.3	951.5	956.8	960.2	966.5	968.4	971.4	974.1	980.4	987.0
5°	888.6	893.8	906.3	913.0	922.5	933.4	940.6	948.2	956.4	970.8	984.0
7.5°	830.2	839.0	854.4	867.2	880.6	896.3	907.6	922.5	934.8	955.0	974.4
10°	791.2	803.7	817.7	832.7	851.6	868.2	884.0	902.9	918.0	942.1	964.7
12.5°	756.3	758.1	778.1	794.8	820.5	841.0	859.3	883.5	898.4	927.1	950.9
15°	695.1	706.4	724.5	737.7	768.2	794.3	819.9	845.2	862.1	897.6	928.9
17.5°	643.6	654.0	672.6	694.2	716.1	741.9	775.2	801.8	824.9	865.4	902.4
20°	611.0	623.8	642.7	664.9	684.2	712.5	741.0	771.6	796.5	842.1	885.6
22.5°	583.2	593.3	608.5	630.5	651.6	677.4	708.8	742.0	768.2	817.4	861.4
25°	544.2	552.5	562.3	580.5	604.2	632.5	657.0	693.6	731.6	777.7	830.8
27.5°	509.1	514.9	523.6	539.6	558.0	584.4	611.7	646.3	684.7	734.6	790.7
30°	487.7	491.4	500.1	513.3	531.4	552.1	579.7	612.9	652.1	702.7	758.4
32.5°	469.0	472.4	478.1	490.7	506.3	524.1	548.9	582.1	619.5	669.1	730.9
35°	440.9	443.5	448.4	458.6	467.3	484.6	505.3	535.5	570.6	618.1	682.3
37.5°	412.9	416.5	419.5	423.8	434.9	446.4	464.4	489.9	524.3	572.3	633.4
40°	394.5	397.5	402.0	403.9	412.9	423.1	437.9	461.2	495.9	539.7	599.3
42.5°	375.8	378.8	381.5	383.7	391.5	400.5	413.7	433.8	464.5	507.2	566.1
45°	350.3	350.7	353.4	357.5	361.3	367.7	377.2	394.5	418.3	458.3	511.8
47.5°	324.6	325.0	325.5	327.3	331.4	337.2	343.5	357.6	378.9	410.8	462.9
50°	307.4	306.6	307.4	308.9	311.5	316.4	323.6	333.8	351.1	380.9	428.8
52.5°	290.7	290.6	290.1	290.7	292.9	296.2	301.2	309.9	325.5	352.8	395.1
55°	265.5	263.6	264.0	262.5	265.9	266.6	270.4	277.6	291.1	310.0	349.6
57.5°	238.5	237.0	235.3	234.9	234.6	236.6	239.6	245.3	255.7	272.3	304.4
60°	221.4	219.5	217.2	216.5	216.5	217.6	219.1	223.3	233.1	247.8	274.2
62.5°	203.9	201.7	200.4	198.3	197.7	198.9	200.5	203.4	210.5	224.3	247.0
65°	176.9	174.2	172.4	172.0	171.3	170.1	170.9	173.9	179.6	190.5	208.5
67.5°	149.8	147.3	146.8	144.7	143.6	143.8	143.6	146.2	149.6	159.0	172.5
70°	132.0	130.1	129.4	127.4	126.7	125.9	125.2	127.4	130.9	138.8	150.5
72.5°	113.9	112.3	110.7	109.1	109.3	108.5	108.4	109.7	112.5	119.8	128.8
75°	87.9	88.3	86.3	84.5	84.1	83.3	83.3	84.5	85.6	91.3	98.5
77.5°	63.7	63.4	61.8	61.2	60.9	60.1	60.9	61.6	62.2	66.0	71.3
80°	48.7	48.7	46.8	46.8	46.4	45.2	46.4	45.6	47.2	50.9	54.7
82.5°	34.7	34.1	34.1	33.5	33.4	32.6	33.1	33.8	34.4	37.1	39.3
85°	17.0	17.0	16.6	16.3	16.6	16.3	16.6	17.0	17.4	18.5	20.4
87.5°	6.6	6.8	6.8	6.9	6.6	6.7	6.7	6.6	6.9	6.9	6.8
90°	14.9	14.1	12.9	11.6	10.4	9.1	7.6	5.9	4.1	2.4	0.7
92.5°	16.8	16.4	15.8	15.1	14.5	13.9	13.6	13.8	13.9	14.1	14.2
95°	28.4	27.6	26.5	25.3	24.2	23.1	25.2	30.4	35.5	40.8	45.9
97.5°	37.6	36.9	34.3	31.8	29.3	26.8	32.7	47.4	62.0	76.5	91.2
100°	41.5	40.3	37.7	34.9	32.3	29.6	39.1	60.6	82.1	103.6	125.1
102.5°	43.0	41.4	63.7	86.1	108.5	130.8	144.2	148.8	153.3	157.9	162.5
105°	44.8	43.1	86.0	128.9	171.8	214.7	233.8	229.0	224.4	219.6	214.9
107.5°	58.6	60.4	111.8	163.3	214.7	266.1	289.9	286.1	282.4	278.5	274.7
110°	108.1	123.7	169.2	214.5	259.9	305.3	326.4	323.1	319.8	316.5	313.2



TEST NUMBER: P331501-840

CATALOG NUMBER: S122DIW-S485D710U840-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	254.8	312.0	323.3	334.5	345.7	356.9	361.0	358.1	355.3	352.3	349.4
115°	363.5	436.2	432.2	428.4	424.4	420.5	417.2	414.5	411.8	409.2	406.5
117.5°	465.5	483.1	480.4	477.8	475.0	472.3	469.5	466.5	463.5	460.5	457.6
120°	520.1	518.2	515.3	512.5	509.7	506.9	504.3	501.9	499.6	497.3	494.8
122.5°	552.7	551.6	548.5	545.4	542.3	539.3	536.4	534.0	531.5	529.1	526.5
125°	598.4	597.3	594.4	591.4	588.4	585.4	582.9	580.9	578.9	576.8	574.7
127.5°	640.3	638.6	636.4	634.2	632.0	629.8	627.5	625.2	623.0	620.7	618.4
130°	667.0	665.3	663.5	661.8	660.0	658.3	656.2	653.7	651.2	648.6	646.1
132.5°	693.3	691.9	690.1	688.3	686.6	684.9	683.0	680.9	678.7	676.6	674.5
135°	730.4	728.9	727.5	726.1	724.7	723.3	721.2	718.7	716.2	713.7	711.2
137.5°	765.1	763.6	761.9	760.3	758.7	757.1	755.4	753.7	751.9	750.1	748.4
140°	787.6	786.2	784.4	782.6	780.9	779.2	777.7	776.5	775.2	774.0	772.7
142.5°	808.4	807.1	805.1	803.1	801.1	799.1	797.6	796.5	795.4	794.2	793.0
145°	837.5	836.4	833.6	831.0	828.3	825.7	824.4	824.6	824.8	824.9	825.1
147.5°	862.9	862.0	859.4	856.8	854.1	851.5	850.5	851.1	851.7	852.3	852.8
150°	878.3	877.4	874.8	872.3	869.8	867.3	866.6	867.7	868.8	869.9	871.0
152.5°	892.4	891.5	889.1	886.7	884.3	881.9	881.3	882.5	883.8	885.0	886.3
155°	911.5	910.6	908.7	906.8	904.9	903.0	902.8	904.2	905.6	907.1	908.5
157.5°	927.5	926.3	925.0	923.7	922.4	921.1	921.1	922.2	923.4	924.6	925.8
160°	937.0	936.0	935.0	934.1	933.2	932.2	932.2	933.2	934.1	935.0	936.0
162.5°	945.5	944.5	943.7	942.9	942.0	941.2	941.3	942.2	943.2	944.1	945.0
165°	956.2	955.1	954.6	954.1	953.7	953.2	953.4	954.4	955.3	956.2	957.3
167.5°	965.1	964.0	963.6	963.1	962.7	962.3	962.5	963.4	964.4	965.3	966.2
170°	969.7	968.6	968.3	968.0	967.6	967.2	967.6	968.6	969.5	970.4	971.4
172.5°	973.0	971.9	971.6	971.3	971.0	970.7	971.0	971.9	972.9	973.8	974.7
175°	976.7	975.6	975.3	975.0	974.6	974.3	974.7	975.8	976.9	978.1	979.2
177.5°	977.3	976.4	976.3	976.2	976.0	975.9	976.3	977.2	978.1	979.0	979.9
180°	977.0	977.0	977.0	977.0	977.0	977.0	977.0	977.0	977.0	977.0	977.0



TEST NUMBER: P331501-840

CATALOG NUMBER: S122DIW-S485D710U840-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	981.3	981.3	981.3	981.3	981.3	981.3	981.3	981.3	981.3	981.3	981.3
2.5°	986.4	988.0	992.8	997.6	1003.0	1004.5	1006.9	1004.8	1004.2	1010.0	1014.2
5°	989.3	996.0	1009.3	1021.3	1031.5	1038.6	1046.2	1049.2	1054.9	1062.8	1072.6
7.5°	986.0	999.3	1020.1	1037.6	1056.7	1070.6	1081.4	1090.6	1101.7	1116.7	1133.1
10°	982.5	1000.2	1025.4	1046.9	1070.4	1088.0	1102.8	1117.1	1133.7	1154.5	1175.9
12.5°	975.8	996.8	1028.4	1053.9	1083.9	1101.4	1121.2	1152.1	1169.9	1198.8	1229.0
15°	962.5	985.8	1030.0	1061.3	1095.2	1128.4	1165.0	1194.4	1223.9	1240.8	1283.4
17.5°	942.6	976.9	1025.8	1062.4	1105.5	1157.7	1198.8	1232.2	1266.2	1293.6	1315.0
20°	926.7	964.0	1019.8	1063.6	1114.8	1171.0	1218.2	1252.1	1281.5	1304.5	1317.8
22.5°	906.5	953.4	1007.7	1059.0	1124.5	1180.1	1229.6	1256.4	1280.9	1292.1	1297.2
25°	874.5	931.2	992.6	1055.2	1129.1	1188.0	1233.2	1249.5	1256.7	1245.7	1227.6
27.5°	840.3	903.3	975.2	1048.1	1126.3	1182.9	1215.3	1212.7	1200.6	1165.2	1136.9
30°	814.7	884.0	961.3	1040.9	1119.3	1174.4	1193.3	1174.4	1146.9	1107.3	1066.9
32.5°	787.8	859.6	946.5	1030.7	1106.7	1155.1	1159.2	1126.7	1084.1	1039.2	988.8
35°	747.1	824.9	918.7	1007.7	1079.7	1110.3	1092.2	1034.9	984.3	922.9	854.2
37.5°	701.1	787.0	881.1	974.1	1039.5	1047.4	1002.5	942.1	870.8	798.6	717.8
40°	666.8	757.7	854.6	948.5	1006.2	997.9	940.6	874.2	789.3	701.1	626.0
42.5°	636.0	726.9	825.7	917.8	964.0	941.2	874.2	792.7	701.6	618.4	549.8
45°	582.7	676.2	777.3	866.3	892.7	851.6	763.0	672.5	582.7	513.3	459.0
47.5°	531.0	623.4	723.5	801.7	811.1	755.8	658.9	565.8	488.7	432.1	393.8
50°	492.9	585.7	684.9	754.7	751.6	684.9	585.3	496.7	432.2	386.6	360.9
52.5°	458.8	546.4	641.8	705.2	689.2	616.4	521.4	442.7	389.7	354.0	330.7
55°	405.8	486.9	577.4	628.3	599.0	518.2	437.9	374.5	335.3	308.5	290.4
57.5°	353.1	429.2	506.6	538.1	505.5	431.0	364.1	318.1	288.6	268.7	257.0
60°	320.5	387.0	456.0	483.1	444.2	377.9	325.1	284.0	260.2	244.0	233.5
62.5°	288.0	347.4	412.5	427.3	391.7	335.7	288.9	254.7	235.2	220.8	210.9
65°	243.7	292.3	341.7	351.5	318.7	275.3	238.3	216.1	198.7	188.2	180.3
67.5°	199.9	238.8	273.9	281.8	253.1	223.0	196.2	176.9	165.1	156.3	149.7
70°	173.9	204.8	233.5	239.8	216.8	190.1	169.8	154.2	143.7	136.1	129.8
72.5°	146.4	172.2	196.0	200.4	181.6	161.1	144.4	132.2	122.9	118.1	111.9
75°	112.0	127.1	145.6	146.7	134.3	121.8	109.0	101.1	96.1	90.2	87.2
77.5°	79.1	90.9	101.5	103.5	96.1	87.7	80.5	74.2	70.1	67.3	64.5
80°	60.4	69.8	74.3	77.0	71.7	65.6	61.5	57.4	54.7	52.8	50.9
82.5°	43.1	49.0	53.2	55.2	52.3	48.8	44.5	42.2	40.2	38.6	38.0
85°	21.9	24.5	27.2	27.9	27.2	25.7	23.4	23.4	22.2	21.9	21.9
87.5°	8.1	9.6	9.9	11.2	10.9	11.1	11.4	11.3	11.3	11.1	11.0
90°	2.4	4.1	5.9	7.6	9.1	10.4	11.6	12.9	14.1	14.9	15.8
92.5°	14.1	13.9	13.8	13.6	13.9	14.5	15.1	15.8	16.4	16.8	17.3
95°	40.8	35.5	30.4	25.2	23.1	24.2	25.3	26.5	27.6	28.4	29.2
97.5°	76.5	62.0	47.4	32.7	26.8	29.3	31.8	34.3	36.9	37.6	38.2
100°	103.6	82.1	60.6	39.1	29.6	32.3	34.9	37.7	40.3	41.5	42.8
102.5°	157.9	153.3	148.8	144.2	130.8	108.5	86.1	63.7	41.4	43.0	44.7
105°	219.6	224.4	229.0	233.8	214.7	171.8	128.9	86.0	43.1	44.8	46.6
107.5°	278.5	282.4	286.1	289.9	266.1	214.7	163.3	111.8	60.4	58.6	56.9
110°	316.5	319.8	323.1	326.4	305.3	259.9	214.5	169.2	123.7	108.1	92.3





TEST NUMBER: P331501-840

CATALOG NUMBER: S122DIW-S485D710U840-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	352.3	355.3	358.1	361.0	356.9	345.7	334.5	323.3	312.0	254.8	197.4
115°	409.2	411.8	414.5	417.2	420.5	424.4	428.4	432.2	436.2	363.5	290.7
117.5°	460.5	463.5	466.5	469.5	472.3	475.0	477.8	480.4	483.1	465.5	448.0
120°	497.3	499.6	501.9	504.3	506.9	509.7	512.5	515.3	518.2	520.1	522.0
122.5°	529.1	531.5	534.0	536.4	539.3	542.3	545.4	548.5	551.6	552.7	553.8
125°	576.8	578.9	580.9	582.9	585.4	588.4	591.4	594.4	597.3	598.4	599.6
127.5°	620.7	623.0	625.2	627.5	629.8	632.0	634.2	636.4	638.6	640.3	641.9
130°	648.6	651.2	653.7	656.2	658.3	660.0	661.8	663.5	665.3	667.0	668.7
132.5°	676.6	678.7	680.9	683.0	684.9	686.6	688.3	690.1	691.9	693.3	694.8
135°	713.7	716.2	718.7	721.2	723.3	724.7	726.1	727.5	728.9	730.4	732.1
137.5°	750.1	751.9	753.7	755.4	757.1	758.7	760.3	761.9	763.6	765.1	766.6
140°	774.0	775.2	776.5	777.7	779.2	780.9	782.6	784.4	786.2	787.6	789.0
142.5°	794.2	795.4	796.5	797.6	799.1	801.1	803.1	805.1	807.1	808.4	809.6
145°	824.9	824.8	824.6	824.4	825.7	828.3	831.0	833.6	836.4	837.5	838.5
147.5°	852.3	851.7	851.1	850.5	851.5	854.1	856.8	859.4	862.0	862.9	863.7
150°	869.9	868.8	867.7	866.6	867.3	869.8	872.3	874.8	877.4	878.3	879.2
152.5°	885.0	883.8	882.5	881.3	881.9	884.3	886.7	889.1	891.5	892.4	893.3
155°	907.1	905.6	904.2	902.8	903.0	904.9	906.8	908.7	910.6	911.5	912.4
157.5°	924.6	923.4	922.2	921.1	921.1	922.4	923.7	925.0	926.3	927.5	928.6
160°	935.0	934.1	933.2	932.2	932.2	933.2	934.1	935.0	936.0	937.0	937.9
162.5°	944.1	943.2	942.2	941.3	941.2	942.0	942.9	943.7	944.5	945.5	946.6
165°	956.2	955.3	954.4	953.4	953.2	953.7	954.1	954.6	955.1	956.2	957.4
167.5°	965.3	964.4	963.4	962.5	962.3	962.7	963.1	963.6	964.0	965.1	966.2
170°	970.4	969.5	968.6	967.6	967.2	967.6	968.0	968.3	968.6	969.7	970.8
172.5°	973.8	972.9	971.9	971.0	970.7	971.0	971.3	971.6	971.9	973.0	974.1
175°	978.1	976.9	975.8	974.7	974.3	974.6	975.0	975.3	975.6	976.7	977.9
177.5°	979.0	978.1	977.2	976.3	975.9	976.0	976.2	976.3	976.4	977.3	978.3
180°	977.0	977.0	977.0	977.0	977.0	977.0	977.0	977.0	977.0	977.0	977.0



TEST NUMBER: P331501-840

CATALOG NUMBER: S122DIW-S485D710U840-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	981.3	981.3	981.3	981.3	981.3	981.3	981.3
2.5°	1017.8	1022.1	1022.1	1022.7	1027.4	1026.9	1026.6
5°	1083.2	1089.5	1090.4	1097.1	1101.7	1100.1	1096.0
7.5°	1144.8	1156.7	1165.8	1170.8	1176.8	1180.4	1178.8
10°	1193.7	1211.0	1221.5	1228.7	1237.4	1243.9	1241.5
12.5°	1238.0	1258.7	1273.1	1285.5	1286.6	1294.8	1289.2
15°	1307.2	1329.1	1331.3	1340.4	1347.6	1346.8	1347.2
17.5°	1330.0	1337.1	1338.5	1338.7	1338.8	1336.2	1330.4
20°	1321.9	1319.3	1312.8	1308.0	1299.3	1298.1	1290.6
22.5°	1283.2	1274.9	1258.8	1248.2	1234.7	1231.1	1229.0
25°	1207.2	1188.7	1163.1	1138.6	1131.8	1118.6	1122.4
27.5°	1102.9	1074.1	1046.3	1026.4	1008.5	988.7	994.3
30°	1029.6	997.1	958.0	927.8	908.6	889.7	886.3
32.5°	942.1	894.5	850.8	824.3	794.8	782.8	769.8
35°	791.2	744.9	701.5	664.2	642.7	626.0	611.0
37.5°	655.5	602.2	567.1	536.9	521.4	511.9	514.2
40°	571.4	524.6	499.0	475.9	461.6	454.8	456.4
42.5°	503.2	468.2	447.1	431.3	421.2	417.4	416.5
45°	425.8	406.2	388.8	379.8	374.9	370.7	368.1
47.5°	373.0	357.0	347.2	341.8	337.5	333.4	333.3
50°	341.3	330.7	324.0	318.3	314.9	311.8	314.6
52.5°	317.2	307.5	300.7	295.7	294.4	291.6	291.6
55°	281.3	273.8	268.9	264.4	262.2	260.6	258.7
57.5°	248.7	241.6	237.1	234.2	229.9	228.4	227.8
60°	225.5	219.8	215.3	211.6	209.6	206.7	206.7
62.5°	204.1	198.4	194.2	191.4	188.2	187.0	187.3
65°	173.1	168.5	164.4	161.4	160.7	158.4	159.2
67.5°	144.6	141.6	137.2	135.5	134.1	132.9	132.0
70°	125.6	122.6	120.3	118.1	116.9	116.9	116.9
72.5°	109.6	105.9	104.6	101.8	102.4	101.2	100.0
75°	84.8	82.6	81.5	80.3	78.5	78.5	78.5
77.5°	62.4	61.8	60.4	59.2	58.8	58.4	58.6
80°	48.3	47.9	47.2	47.2	46.4	46.0	45.2
82.5°	37.1	36.2	35.6	35.3	35.2	35.1	35.0
85°	21.1	20.4	20.4	20.7	20.0	20.0	20.4
87.5°	11.4	11.6	11.4	11.5	11.8	11.6	11.6
90°	16.5	17.3	17.9	18.2	18.5	18.8	19.1
92.5°	17.7	18.1	18.4	18.5	18.7	18.9	19.1
95°	29.9	30.7	31.0	30.9	30.7	30.6	30.4
97.5°	38.8	39.4	39.8	40.0	40.2	40.4	40.6
100°	44.0	45.3	46.2	46.5	46.8	47.1	47.4
102.5°	46.4	48.0	49.0	49.5	49.9	50.3	50.8
105°	48.3	50.0	51.2	51.8	52.5	53.1	53.7
107.5°	55.1	53.3	52.8	53.4	54.0	54.6	55.2
110°	76.5	60.9	53.3	53.9	54.6	55.2	55.8



TEST NUMBER: P331501-840

CATALOG NUMBER: S122DIW-S485D710U840-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	140.2	82.8	54.4	54.9	55.4	55.9	56.5
115°	217.9	145.2	103.2	91.9	80.6	69.3	58.0
117.5°	430.3	412.7	385.4	348.2	311.0	273.9	236.7
120°	523.8	525.7	516.0	494.8	473.6	452.4	431.2
122.5°	554.9	556.1	554.6	550.5	546.3	542.3	538.2
125°	600.7	601.8	602.6	603.0	603.5	604.0	604.4
127.5°	643.5	645.1	645.9	646.0	646.1	646.2	646.3
130°	670.4	672.2	673.0	672.8	672.7	672.5	672.4
132.5°	696.3	697.7	698.4	698.2	698.1	697.9	697.8
135°	733.6	735.2	735.8	735.5	735.2	734.9	734.6
137.5°	768.1	769.7	770.2	769.6	769.1	768.6	768.0
140°	790.4	791.8	792.1	791.3	790.5	789.7	789.0
142.5°	810.9	812.2	812.4	811.7	810.9	810.1	809.3
145°	839.6	840.7	840.9	840.1	839.3	838.5	837.8
147.5°	864.5	865.4	865.5	864.7	864.1	863.4	862.7
150°	880.2	881.1	881.2	880.4	879.6	878.8	878.1
152.5°	894.3	895.2	895.2	894.1	893.1	892.1	891.0
155°	913.4	914.3	914.1	912.9	911.7	910.4	909.2
157.5°	929.6	930.7	930.6	929.4	928.2	927.0	925.6
160°	938.9	939.8	939.7	938.6	937.5	936.4	935.3
162.5°	947.7	948.8	948.7	947.3	945.9	944.5	943.2
165°	958.4	959.5	959.5	958.4	957.4	956.2	955.1
167.5°	967.3	968.4	968.3	966.8	965.4	964.0	962.6
170°	971.8	972.9	972.8	971.4	970.0	968.6	967.1
172.5°	975.2	976.3	976.1	974.7	973.3	971.9	970.5
175°	978.9	980.0	979.8	978.2	976.6	975.0	973.5
177.5°	979.1	980.0	979.9	978.8	977.5	976.4	975.3
180°	977.0	977.0	977.0	977.0	977.0	977.0	977.0

(END OF REPORT)