

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332155-927

Luminaire Tested: **S123DIW-S775D460U927-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332155-927
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-9,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123DIW-S775D460U927-4F0-1E-UDD-F1
Description: DEFINE 3 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 775 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 460 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3777.8 lumens
Efficiency: N/A
Efficacy: 100.2 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 37.7
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332155-927

CATALOG NUMBER: S123DIW-S775D460U927-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P332155-927

CATALOG NUMBER: S123DIW-S775D460U927-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	111	111	111	111	105	105	105	105	92	92	92	81	81	81	71	71	71	66
1	101	97	93	89	95	91	88	85	81	78	76	72	70	68	63	61	60	56
2	92	85	78	73	87	80	74	69	71	67	63	63	59	57	55	53	51	47
3	84	74	67	61	79	70	64	58	63	57	53	56	51	48	49	46	43	40
4	77	66	58	51	72	62	55	49	56	50	45	50	45	41	44	40	37	34
5	71	59	50	44	66	56	48	42	50	44	39	44	39	36	39	35	32	29
6	65	53	44	38	61	50	43	37	45	39	34	40	35	31	36	32	28	26
7	60	48	40	34	57	45	38	33	41	35	30	37	32	28	33	28	25	23
8	56	43	36	30	53	41	34	29	37	31	27	34	28	25	30	26	23	20
9	52	40	32	27	49	38	31	26	34	28	24	31	26	22	28	24	20	18
10	49	37	29	24	46	35	28	23	32	26	22	29	24	20	26	22	19	17

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	10384	10384	10384
5°	10432	10289	10361
10°	10363	10200	10263
15°	10242	10085	10104
20°	10100	9919	9929
25°	9911	9723	9704
30°	9701	9506	9434
35°	9483	9276	9155
40°	9254	9021	8882
45°	9003	8788	8573
50°	8751	8500	8264
55°	8422	8203	7955
60°	8088	7858	7608
65°	7796	7480	7246
70°	7361	7046	6735
75°	6729	6488	6209
80°	6069	5808	5759
85°	5323	5125	4915



TEST NUMBER: P332155-927

CATALOG NUMBER: S123DIW-S775D460U927-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	90.9	2.4
10°-20°	256.6	6.8
20°-30°	379.0	10.0
30°-40°	442.7	11.7
40°-50°	445.1	11.8
50°-60°	391.0	10.3
60°-70°	291.3	7.7
70°-80°	166.0	4.4
80°-90°	49.0	1.3
90°-100°	29.8	0.8
100°-110°	89.1	2.4
110°-120°	151.6	4.0
120°-130°	199.4	5.3
130°-140°	224.1	5.9
140°-150°	220.3	5.8
150°-160°	185.4	4.9
160°-170°	123.4	3.3
170°-180°	43.2	1.1
0°-30°	726.5	19.2
0°-40°	1169.2	30.9
0°-60°	2005.3	53.1
0°-90°	2511.6	66.5
90°-120°	270.4	7.2
90°-150°	914.1	24.2
90°-180°	1266.0	33.5
0°-180°	3777.8	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	965	965	965	965	965	
5°	966	961	952	960	959	91
15°	919	915	905	911	907	259
25°	834	829	819	819	817	384
35°	722	716	706	701	697	451
45°	591	588	577	568	563	456
55°	449	447	437	428	424	402
65°	306	302	294	287	284	302
75°	162	158	156	152	149	173
85°	43	42	42	40	40	47
90°	0	4	9	10	11	4
95°	21	24	26	28	28	24
105°	81	82	85	85	86	87
115°	153	154	153	153	153	151
125°	223	224	224	222	221	199
135°	290	292	292	290	289	223
145°	352	352	353	353	352	219
155°	402	402	403	404	402	185
165°	438	437	437	439	437	124
175°	456	455	454	456	454	43
180°	457	457	457	457	457	



TEST NUMBER: P332155-927

CATALOG NUMBER: S123DIW-S775D460U927-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	964.7	964.7	964.7	964.7	964.7	964.7	964.7	964.7	964.7	964.7	964.7
2.5°	968.0	967.4	966.9	966.2	965.7	964.6	962.9	961.3	959.6	958.1	959.5
5°	965.5	964.6	963.7	962.7	961.8	960.4	958.3	956.3	954.3	952.2	954.1
7.5°	956.1	955.1	954.2	953.3	952.4	950.9	948.7	946.7	944.5	942.5	944.1
10°	948.1	947.1	946.3	945.3	944.4	942.8	940.3	937.9	935.6	933.2	934.9
12.5°	937.5	936.7	936.0	935.2	934.4	932.9	930.7	928.4	926.1	923.8	925.1
15°	919.1	918.3	917.6	916.9	916.1	914.6	912.1	909.7	907.4	905.0	906.4
17.5°	897.6	896.7	895.7	894.8	893.8	892.2	889.8	887.3	884.9	882.6	883.6
20°	881.7	880.6	879.6	878.5	877.3	875.5	873.1	870.8	868.4	865.9	866.7
22.5°	863.8	862.7	861.6	860.5	859.4	857.6	855.2	852.9	850.5	848.0	848.7
25°	834.5	833.4	832.3	831.2	830.0	828.3	825.9	823.5	821.1	818.7	818.9
27.5°	803.1	802.0	801.0	799.9	798.8	797.0	794.4	791.9	789.3	786.6	786.8
30°	780.5	779.6	778.7	777.8	776.8	775.1	772.5	769.9	767.4	764.8	764.8
32.5°	758.0	756.8	755.5	754.3	753.1	751.5	749.5	747.5	745.5	743.5	742.5
35°	721.7	720.6	719.5	718.4	717.2	715.5	713.0	710.7	708.3	705.9	704.8
37.5°	684.4	683.1	681.7	680.2	678.9	677.0	674.5	672.1	669.6	667.3	665.9
40°	658.6	657.5	656.4	655.3	654.2	652.4	649.7	647.2	644.6	642.0	640.6
42.5°	632.7	631.4	630.2	629.0	627.7	625.8	623.2	620.6	618.1	615.4	614.0
45°	591.4	590.7	589.9	589.2	588.4	586.9	584.5	582.1	579.7	577.3	575.1
47.5°	550.4	549.4	548.3	547.2	546.1	544.5	542.2	540.0	537.7	535.5	533.3
50°	522.6	521.7	520.7	519.8	518.9	517.2	514.8	512.5	510.0	507.6	505.6
52.5°	493.4	492.7	492.1	491.5	490.8	489.3	486.7	484.2	481.6	479.1	477.4
55°	448.8	448.5	448.4	448.2	448.0	446.7	444.3	442.0	439.5	437.1	435.1
57.5°	406.3	405.7	405.0	404.4	403.8	402.5	400.6	398.6	396.7	394.8	393.0
60°	375.7	375.6	375.4	375.2	375.0	373.8	371.6	369.4	367.2	365.0	363.3
62.5°	348.6	348.1	347.6	347.1	346.7	345.3	343.1	340.9	338.7	336.4	334.8
65°	306.1	305.1	304.2	303.3	302.4	301.0	299.1	297.3	295.5	293.7	292.2
67.5°	261.1	260.3	259.5	258.6	257.9	256.7	255.4	254.0	252.5	251.2	249.9
70°	233.9	232.8	231.7	230.6	229.5	228.4	227.3	226.2	225.1	223.9	222.7
72.5°	205.4	204.5	203.7	203.0	202.2	201.1	199.9	198.6	197.3	196.1	195.0
75°	161.8	161.0	160.3	159.5	158.8	158.1	157.6	157.0	156.5	156.0	155.0
77.5°	123.1	122.7	122.3	121.9	121.4	121.0	120.3	119.6	119.0	118.3	117.6
80°	97.9	97.4	96.8	96.3	95.7	95.2	94.8	94.5	94.1	93.7	93.6
82.5°	73.4	73.2	73.1	73.0	72.9	72.8	72.7	72.6	72.6	72.5	72.2
85°	43.1	42.8	42.4	42.1	41.7	41.5	41.5	41.5	41.5	41.5	41.1
87.5°	17.3	17.0	16.8	16.5	16.2	16.1	16.2	16.2	16.2	16.3	16.2
90°	0.4	1.2	2.0	2.8	3.6	4.4	5.5	6.6	7.6	8.6	9.0
92.5°	8.7	9.3	9.7	10.3	10.9	11.4	12.0	12.6	13.2	13.8	14.0
95°	21.2	21.7	22.3	22.9	23.4	24.0	24.6	25.3	25.9	26.5	26.9
97.5°	37.6	38.0	38.4	38.9	39.3	39.7	40.2	40.6	41.1	41.6	41.9
100°	48.8	49.3	49.7	50.2	50.7	51.2	51.6	52.0	52.4	52.8	53.0
102.5°	61.7	62.0	62.3	62.6	62.9	63.3	63.8	64.3	64.9	65.4	65.7
105°	80.8	81.0	81.1	81.3	81.4	81.8	82.5	83.3	84.0	84.7	84.7
107.5°	102.9	103.0	103.1	103.1	103.3	103.5	103.8	104.0	104.3	104.6	104.9
110°	116.7	116.8	117.0	117.2	117.3	117.5	117.6	117.8	118.0	118.1	118.4



TEST NUMBER: P332155-927

CATALOG NUMBER: S123DIW-S775D460U927-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	131.0	131.1	131.3	131.3	131.4	131.5	131.5	131.6	131.6	131.6	132.0
115°	152.6	152.8	153.0	153.3	153.5	153.6	153.4	153.3	153.1	153.0	153.0
117.5°	174.3	174.4	174.6	174.8	174.9	174.8	174.7	174.4	174.3	174.0	174.0
120°	187.7	188.2	188.7	189.2	189.6	189.7	189.3	188.9	188.5	188.1	188.1
122.5°	201.8	202.2	202.6	202.9	203.2	203.3	203.1	202.9	202.7	202.5	202.2
125°	223.3	223.6	223.8	224.0	224.3	224.3	224.1	223.9	223.8	223.6	223.3
127.5°	243.1	243.6	244.2	244.6	245.2	245.3	245.2	244.9	244.8	244.6	244.2
130°	256.4	257.0	257.6	258.3	258.9	259.0	258.8	258.6	258.3	258.1	257.8
132.5°	269.5	270.1	270.8	271.5	272.1	272.4	272.1	272.0	271.8	271.6	271.2
135°	289.7	290.2	290.7	291.1	291.6	291.8	291.8	291.7	291.6	291.5	291.2
137.5°	308.4	308.8	309.2	309.6	310.0	310.3	310.5	310.7	310.9	311.1	310.8
140°	321.3	321.7	322.1	322.5	322.9	323.1	323.2	323.3	323.4	323.4	323.4
142.5°	333.1	333.5	333.9	334.3	334.7	334.9	335.1	335.3	335.4	335.5	335.4
145°	351.5	351.6	351.8	352.0	352.1	352.3	352.5	352.8	353.0	353.2	353.2
147.5°	367.6	367.8	368.1	368.4	368.7	368.9	369.2	369.4	369.6	369.9	369.9
150°	378.7	378.9	379.1	379.2	379.4	379.5	379.7	379.9	380.0	380.2	380.2
152.5°	387.9	388.2	388.4	388.6	388.8	389.0	389.0	389.2	389.3	389.4	389.5
155°	402.4	402.4	402.4	402.4	402.4	402.5	402.6	402.7	402.7	402.8	403.1
157.5°	414.8	414.7	414.6	414.5	414.4	414.4	414.5	414.5	414.5	414.6	414.9
160°	422.6	422.4	422.2	422.1	421.9	421.8	421.8	421.8	421.8	421.8	422.2
162.5°	429.4	429.2	429.0	428.7	428.6	428.5	428.5	428.6	428.6	428.7	429.1
165°	438.3	438.1	437.8	437.6	437.4	437.3	437.3	437.3	437.3	437.3	437.8
167.5°	445.4	445.1	444.8	444.5	444.2	444.0	444.1	444.2	444.3	444.3	444.8
170°	449.5	449.2	448.9	448.5	448.2	448.1	448.1	448.1	448.1	448.1	448.6
172.5°	452.7	452.3	452.0	451.7	451.3	451.1	451.1	451.1	451.1	451.1	451.7
175°	455.9	455.6	455.3	455.0	454.6	454.5	454.5	454.5	454.5	454.5	455.0
177.5°	457.3	457.0	456.8	456.5	456.3	456.1	456.1	456.1	456.1	456.1	456.5
180°	457.0	457.0	457.0	457.0	457.0	457.0	457.0	457.0	457.0	457.0	457.0



TEST NUMBER: P332155-927

CATALOG NUMBER: S123DIW-S775D460U927-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	964.7	964.7	964.7	964.7	964.7	964.7	964.7	964.7
2.5°	961.0	962.5	963.9	964.6	964.5	964.3	964.2	964.0
5°	955.9	957.7	959.6	960.4	960.0	959.6	959.3	958.9
7.5°	945.8	947.5	949.1	949.8	949.6	949.4	949.1	949.0
10°	936.5	938.1	939.8	940.5	940.1	939.7	939.4	939.0
12.5°	926.3	927.5	928.8	929.2	929.0	928.8	928.6	928.4
15°	907.9	909.3	910.9	911.0	909.9	908.8	907.8	906.7
17.5°	884.6	885.7	886.7	887.0	886.6	886.2	885.8	885.4
20°	867.4	868.2	868.9	869.0	868.5	867.9	867.4	866.8
22.5°	849.2	849.9	850.4	850.3	849.7	849.0	848.3	847.6
25°	819.0	819.3	819.4	819.3	818.7	818.2	817.6	817.1
27.5°	787.0	787.1	787.3	787.0	786.3	785.6	784.9	784.2
30°	764.8	764.8	764.8	764.1	762.9	761.5	760.3	759.0
32.5°	741.5	740.5	739.4	738.6	737.8	737.1	736.4	735.8
35°	703.7	702.6	701.5	700.4	699.5	698.6	697.7	696.7
37.5°	664.6	663.2	661.9	661.0	660.4	659.8	659.2	658.6
40°	639.1	637.6	636.1	635.0	634.3	633.5	632.8	632.1
42.5°	612.5	611.0	609.6	608.5	607.8	607.0	606.3	605.5
45°	572.9	570.7	568.5	566.9	566.0	565.1	564.1	563.2
47.5°	531.2	529.0	526.8	525.3	524.5	523.7	522.9	522.0
50°	503.6	501.5	499.6	498.0	496.9	495.7	494.6	493.5
52.5°	475.6	473.9	472.1	470.8	469.7	468.6	467.5	466.4
55°	433.1	431.0	429.0	427.5	426.6	425.7	424.8	423.9
57.5°	391.2	389.4	387.6	386.2	385.1	384.0	382.9	381.9
60°	361.6	360.0	358.3	357.0	356.1	355.2	354.3	353.4
62.5°	333.1	331.4	329.8	328.7	328.0	327.4	326.8	326.1
65°	290.7	289.2	287.7	286.7	286.1	285.6	285.0	284.5
67.5°	248.6	247.3	246.0	244.9	244.2	243.4	242.6	241.9
70°	221.4	220.1	218.8	217.7	216.7	215.9	214.9	214.0
72.5°	193.8	192.7	191.5	190.7	190.2	189.7	189.3	188.8
75°	154.1	153.2	152.3	151.5	151.0	150.4	149.9	149.3
77.5°	117.0	116.4	115.7	115.5	115.5	115.5	115.5	115.5
80°	93.4	93.2	93.0	92.9	92.9	92.9	92.9	92.9
82.5°	71.9	71.5	71.1	70.9	70.8	70.7	70.5	70.3
85°	40.7	40.4	40.0	39.8	39.8	39.8	39.8	39.8
87.5°	16.2	16.1	16.0	15.9	16.0	16.0	16.1	16.1
90°	9.3	9.6	9.9	10.1	10.3	10.5	10.6	10.8
92.5°	14.3	14.6	14.8	14.9	14.8	14.7	14.6	14.5
95°	27.2	27.5	27.8	28.0	28.0	28.0	28.0	28.0
97.5°	42.3	42.7	43.0	43.2	43.2	43.2	43.1	43.1
100°	53.2	53.5	53.7	53.9	54.1	54.3	54.4	54.6
102.5°	65.9	66.1	66.4	66.5	66.5	66.4	66.4	66.3
105°	84.7	84.7	84.7	84.8	85.0	85.2	85.3	85.5
107.5°	105.1	105.4	105.6	105.7	105.6	105.5	105.4	105.4
110°	118.7	119.1	119.4	119.5	119.3	119.1	119.0	118.8



TEST NUMBER: P332155-927

CATALOG NUMBER: S123DIW-S775D460U927-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	132.4	132.8	133.2	133.3	133.2	133.2	133.2	133.2
115°	153.1	153.2	153.3	153.3	153.2	153.1	153.0	153.0
117.5°	174.0	174.0	174.0	173.9	173.6	173.4	173.2	172.9
120°	188.0	187.9	187.8	187.7	187.5	187.4	187.2	187.0
122.5°	202.1	201.8	201.6	201.5	201.2	201.0	200.7	200.5
125°	223.0	222.7	222.4	222.0	221.7	221.4	221.1	220.8
127.5°	243.8	243.3	242.8	242.4	242.1	241.7	241.3	241.0
130°	257.5	257.1	256.8	256.4	255.9	255.3	254.8	254.1
132.5°	270.8	270.5	270.1	269.7	269.3	268.8	268.4	267.9
135°	290.9	290.6	290.3	290.0	289.9	289.7	289.5	289.4
137.5°	310.5	310.1	309.7	309.4	309.1	308.9	308.6	308.2
140°	323.3	323.2	323.1	322.8	322.3	321.7	321.2	320.6
142.5°	335.3	335.3	335.2	334.9	334.5	334.1	333.7	333.2
145°	353.1	353.0	352.9	352.8	352.4	352.1	351.8	351.5
147.5°	369.9	369.9	369.9	369.6	369.2	368.6	368.1	367.7
150°	380.2	380.2	380.2	379.9	379.5	379.0	378.5	378.0
152.5°	389.6	389.8	389.9	389.8	389.4	388.9	388.5	388.1
155°	403.5	403.8	404.1	403.9	403.4	402.8	402.3	401.7
157.5°	415.3	415.7	416.0	415.9	415.5	415.0	414.5	414.2
160°	422.6	423.0	423.4	423.4	423.1	422.8	422.5	422.2
162.5°	429.5	429.9	430.3	430.2	429.8	429.2	428.7	428.2
165°	438.2	438.7	439.2	439.1	438.6	438.0	437.4	436.9
167.5°	445.3	445.8	446.2	446.2	445.8	445.3	444.8	444.3
170°	449.2	449.7	450.3	450.3	449.7	449.2	448.6	448.1
172.5°	452.2	452.7	453.1	453.1	452.6	452.0	451.5	450.9
175°	455.4	455.9	456.4	456.4	455.8	455.3	454.7	454.2
177.5°	456.9	457.3	457.6	457.6	457.2	456.8	456.3	455.8
180°	457.0	457.0	457.0	457.0	457.0	457.0	457.0	457.0

(END OF REPORT)