

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331512-840

Luminaire Tested: **S122DIW-S485D970U840-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331512-840
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-8,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122DIW-S485D970U840-4F0-1E-UDD-F1
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 485 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 970 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5389.5 lumens
Efficiency: N/A
Efficacy: 119.2 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.3
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 45.2
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331512-840

CATALOG NUMBER: S122DIW-S485D970U840-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P331512-840

CATALOG NUMBER: S122DIW-S485D970U840-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	104	104	104	104	94	94	94	94	76	76	76	60	60	60	44	44	44	37
1	95	91	87	83	86	82	79	76	67	64	62	52	51	49	39	38	37	31
2	86	79	73	68	78	72	67	62	58	55	52	46	43	41	34	33	31	26
3	79	69	62	57	71	63	57	52	51	47	43	41	37	35	30	28	27	22
4	72	61	54	48	65	56	49	44	46	41	37	36	33	30	27	25	23	19
5	66	55	47	41	60	50	43	38	41	36	32	32	29	26	25	22	20	17
6	61	49	41	35	55	45	38	33	37	31	28	29	25	23	22	20	18	15
7	56	44	36	31	51	40	33	29	33	28	24	27	23	20	20	18	16	13
8	52	40	32	27	47	37	30	25	30	25	21	24	20	18	19	16	14	12
9	48	36	29	24	44	33	27	22	28	23	19	22	19	16	17	15	13	10
10	45	33	26	22	41	31	24	20	25	21	17	21	17	14	16	13	11	9

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	12665	12665	12665
5°	12713	12530	12603
10°	12637	12403	12463
15°	12481	12242	12227
20°	12259	12000	11986
25°	12039	11703	11703
30°	11757	11432	11332
35°	11491	11105	10941
40°	11160	10779	10570
45°	10832	10453	10195
50°	10477	10115	9756
55°	10106	9723	9362
60°	9691	9255	8913
65°	9249	8787	8382
70°	8686	8224	7832
75°	7904	7573	7392
80°	7011	6797	6453
85°	5724	5446	4891



TEST NUMBER: P331512-840

CATALOG NUMBER: S122DIW-S485D970U840-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	73.8	1.4
10°-20°	207.5	3.9
20°-30°	305.0	5.7
30°-40°	354.3	6.6
40°-50°	354.0	6.6
50°-60°	308.7	5.7
60°-70°	228.2	4.2
70°-80°	129.3	2.4
80°-90°	39.6	0.7
90°-100°	76.8	1.4
100°-110°	238.5	4.4
110°-120°	407.7	7.6
120°-130°	536.2	9.9
130°-140°	601.8	11.2
140°-150°	590.1	10.9
150°-160°	494.9	9.2
160°-170°	328.3	6.1
170°-180°	114.7	2.1
0°-30°	586.3	10.9
0°-40°	940.7	17.5
0°-60°	1603.3	29.7
0°-90°	2000.4	37.1
90°-120°	723.1	13.4
90°-150°	2451.2	45.5
90°-180°	3389.0	62.9
0°-180°	5389.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	784	784	784	784	784	
5°	784	781	773	779	778	74
15°	747	742	732	735	732	210
25°	676	669	657	658	657	311
35°	583	575	563	559	555	364
45°	474	469	458	450	446	366
55°	359	354	345	337	333	321
65°	242	237	230	223	219	239
75°	127	125	121	117	118	135
85°	31	30	29	27	26	35
90°	1	14	36	34	35	4
95°	53	63	65	65	63	61
105°	220	223	225	227	227	232
115°	409	415	413	412	409	405
125°	595	604	602	598	597	532
135°	770	781	784	782	779	595
145°	935	942	948	949	945	584
155°	1069	1072	1075	1080	1077	492
165°	1163	1162	1162	1168	1164	328
175°	1210	1207	1205	1211	1206	115
180°	1212	1212	1212	1212	1212	



TEST NUMBER: P331512-840

CATALOG NUMBER: S122DIW-S485D970U840-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	784.4	784.4	784.4	784.4	784.4	784.4	784.4	784.4	784.4	784.4	784.4
2.5°	788.0	787.3	786.7	786.0	785.3	784.3	782.7	781.3	779.8	778.3	779.7
5°	784.4	783.7	783.0	782.3	781.7	780.4	778.6	776.8	774.9	773.1	774.4
7.5°	777.4	776.4	775.4	774.3	773.3	771.8	769.9	768.1	766.2	764.3	765.7
10°	770.8	769.6	768.4	767.3	766.1	764.5	762.4	760.5	758.5	756.5	757.8
12.5°	761.7	760.7	759.6	758.6	757.6	756.1	754.1	752.0	750.0	748.0	748.9
15°	746.7	745.7	744.7	743.7	742.7	741.0	738.8	736.7	734.5	732.4	733.0
17.5°	727.3	726.4	725.4	724.4	723.4	721.8	719.5	717.3	715.1	712.9	713.7
20°	713.5	712.5	711.4	710.4	709.4	707.8	705.4	703.1	700.7	698.4	698.9
22.5°	699.6	698.2	696.8	695.4	694.0	692.2	689.9	687.7	685.5	683.3	683.4
25°	675.8	674.4	673.1	671.8	670.4	668.3	665.5	662.6	659.7	656.9	657.2
27.5°	648.6	647.4	646.2	645.0	643.8	642.1	639.9	637.5	635.3	633.1	632.6
30°	630.6	629.1	627.8	626.5	625.1	623.2	620.7	618.2	615.7	613.2	612.7
32.5°	611.2	610.2	609.0	607.9	606.9	605.0	602.4	599.8	597.1	594.5	593.6
35°	583.0	581.3	579.7	577.9	576.3	574.1	571.5	568.8	566.0	563.4	562.4
37.5°	551.2	549.7	548.3	546.7	545.2	543.2	540.5	537.9	535.1	532.5	531.2
40°	529.5	528.1	526.7	525.4	524.1	522.1	519.4	516.7	514.0	511.4	509.9
42.5°	508.4	507.0	505.6	504.3	503.0	501.0	498.3	495.6	492.9	490.2	488.6
45°	474.4	473.2	472.0	470.9	469.7	467.9	465.3	462.8	460.3	457.8	456.0
47.5°	440.6	439.5	438.4	437.3	436.2	434.3	431.7	429.1	426.5	423.8	421.9
50°	417.1	416.3	415.4	414.5	413.7	412.1	409.8	407.5	405.1	402.7	400.4
52.5°	394.2	393.0	391.9	390.8	389.7	388.1	385.9	383.6	381.4	379.2	377.3
55°	359.0	358.0	357.0	356.0	355.0	353.5	351.4	349.4	347.4	345.4	343.5
57.5°	323.7	322.9	322.0	321.3	320.5	319.0	316.8	314.6	312.4	310.1	308.1
60°	300.1	299.5	298.8	298.1	297.5	296.0	293.7	291.2	288.9	286.6	284.8
62.5°	277.2	276.2	275.1	274.0	273.0	271.6	269.7	267.9	266.1	264.3	262.6
65°	242.1	241.1	240.0	239.0	238.1	236.7	235.1	233.4	231.7	230.0	228.5
67.5°	206.3	205.5	204.7	203.9	203.1	202.0	200.5	198.9	197.4	195.9	194.8
70°	184.0	183.4	182.7	182.0	181.4	180.3	178.7	177.2	175.7	174.2	173.1
72.5°	161.1	160.5	159.8	159.1	158.4	157.6	156.6	155.6	154.7	153.7	152.5
75°	126.7	126.3	126.0	125.7	125.3	124.8	123.9	123.1	122.3	121.4	120.4
77.5°	95.9	95.3	94.8	94.2	93.6	93.2	92.9	92.5	92.2	91.9	91.4
80°	75.4	75.2	75.1	74.9	74.7	74.5	74.1	73.8	73.5	73.1	72.6
82.5°	56.1	56.0	56.0	56.0	55.9	55.8	55.6	55.4	55.2	55.0	54.4
85°	30.9	30.8	30.6	30.4	30.3	30.1	29.9	29.8	29.6	29.4	28.9
87.5°	11.1	11.3	11.6	11.9	12.2	12.7	13.4	14.1	14.8	15.7	15.1
90°	1.0	3.7	6.5	9.2	11.9	15.8	20.8	25.8	30.8	35.7	35.3
92.5°	18.2	20.2	22.2	24.2	26.3	27.8	29.0	30.2	31.3	32.5	32.6
95°	53.2	55.4	57.8	60.0	62.3	63.6	64.1	64.5	65.0	65.4	65.4
97.5°	97.1	99.2	101.2	103.2	105.1	106.6	107.4	108.4	109.2	110.1	110.1
100°	129.9	131.7	133.5	135.3	137.1	138.5	139.1	139.8	140.5	141.2	141.2
102.5°	164.3	165.7	167.1	168.6	170.1	171.3	172.1	173.0	173.8	174.7	174.9
105°	219.9	220.6	221.3	222.0	222.7	223.2	223.7	224.1	224.6	225.0	225.5
107.5°	276.0	277.0	277.9	278.9	279.9	280.4	280.4	280.4	280.4	280.4	280.6
110°	311.9	313.4	314.7	316.1	317.4	318.1	318.1	318.1	318.1	318.1	318.1



TEST NUMBER: P331512-840

CATALOG NUMBER: S122DIW-S485D970U840-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	351.2	352.6	354.0	355.4	356.7	357.3	357.1	356.9	356.8	356.6	356.0
115°	409.1	410.5	411.8	413.2	414.5	415.1	414.5	414.1	413.6	413.2	413.0
117.5°	466.9	468.7	470.5	472.3	474.1	474.3	473.1	471.8	470.6	469.3	468.8
120°	505.3	507.2	509.0	510.8	512.6	512.6	510.8	509.0	507.2	505.3	505.3
122.5°	540.5	542.7	544.8	547.0	549.2	549.7	548.4	547.1	545.8	544.5	544.0
125°	595.3	597.3	599.4	601.5	603.5	604.2	603.5	602.8	602.1	601.5	600.8
127.5°	648.7	651.3	653.9	656.5	659.0	659.9	659.1	658.3	657.5	656.7	655.8
130°	682.3	685.2	688.1	691.2	694.1	695.3	694.9	694.4	694.0	693.5	693.1
132.5°	719.8	722.3	724.7	727.1	729.5	730.7	730.8	730.9	731.0	731.1	730.1
135°	770.2	772.7	775.2	777.7	780.2	781.6	782.1	782.5	783.0	783.5	783.3
137.5°	823.1	825.3	827.3	829.3	831.3	832.7	833.2	833.8	834.5	835.1	834.9
140°	855.1	857.2	859.2	861.2	863.2	864.8	866.1	867.2	868.3	869.4	869.4
142.5°	887.9	889.9	891.9	893.9	896.1	897.5	898.2	899.0	899.8	900.5	900.7
145°	934.8	936.4	938.1	939.7	941.3	942.7	944.1	945.4	946.8	948.2	948.4
147.5°	976.8	978.8	980.7	982.5	984.4	985.8	986.7	987.6	988.6	989.5	990.0
150°	1005.4	1006.8	1008.1	1009.6	1010.9	1012.1	1013.0	1013.9	1014.8	1015.7	1016.3
152.5°	1030.9	1032.2	1033.6	1034.9	1036.3	1037.5	1038.6	1039.7	1040.8	1041.9	1042.7
155°	1068.8	1069.5	1070.3	1071.0	1071.6	1072.3	1073.0	1073.7	1074.3	1075.0	1076.1
157.5°	1101.4	1101.9	1102.3	1102.8	1103.2	1103.7	1104.1	1104.5	1104.9	1105.3	1106.8
160°	1121.1	1121.5	1122.0	1122.4	1122.9	1123.2	1123.5	1123.7	1123.9	1124.1	1125.5
162.5°	1139.0	1139.1	1139.2	1139.3	1139.4	1139.5	1139.8	1140.0	1140.2	1140.4	1142.1
165°	1163.0	1162.8	1162.6	1162.3	1162.1	1162.0	1162.0	1162.0	1162.0	1162.0	1163.6
167.5°	1183.1	1182.3	1181.6	1180.9	1180.3	1179.9	1179.9	1179.8	1179.8	1179.7	1181.3
170°	1193.7	1193.0	1192.3	1191.6	1190.9	1190.5	1190.2	1190.0	1189.8	1189.6	1191.1
172.5°	1201.0	1200.3	1199.6	1199.0	1198.3	1197.8	1197.6	1197.4	1197.2	1196.9	1198.5
175°	1210.0	1209.3	1208.7	1208.0	1207.3	1206.7	1206.3	1205.8	1205.4	1204.9	1206.5
177.5°	1213.8	1213.2	1212.6	1212.0	1211.5	1211.0	1210.7	1210.3	1210.0	1209.6	1210.7
180°	1212.0	1212.0	1212.0	1212.0	1212.0	1212.0	1212.0	1212.0	1212.0	1212.0	1212.0



TEST NUMBER: P331512-840

CATALOG NUMBER: S122DIW-S485D970U840-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	784.4	784.4	784.4	784.4	784.4	784.4	784.4	784.4
2.5°	781.0	782.3	783.7	784.3	784.0	783.7	783.5	783.2
5°	775.8	777.1	778.4	778.9	778.6	778.2	777.9	777.6
7.5°	767.0	768.3	769.7	770.1	769.8	769.4	769.0	768.7
10°	759.1	760.5	761.8	762.2	761.7	761.2	760.7	760.2
12.5°	749.9	750.8	751.7	752.0	751.6	751.3	750.9	750.5
15°	733.7	734.4	735.0	734.9	734.1	733.3	732.5	731.5
17.5°	714.4	715.2	716.0	715.9	715.1	714.4	713.6	712.8
20°	699.4	699.9	700.4	700.3	699.6	698.9	698.3	697.6
22.5°	683.5	683.6	683.7	683.6	683.2	682.8	682.4	682.0
25°	657.6	657.9	658.2	658.2	657.9	657.6	657.2	656.9
27.5°	632.1	631.6	631.1	630.5	629.7	628.8	628.0	627.2
30°	612.2	611.7	611.2	610.6	609.9	609.3	608.5	607.8
32.5°	592.7	591.8	590.9	590.1	589.4	588.8	588.0	587.3
35°	561.4	560.4	559.4	558.5	557.6	556.7	555.9	555.1
37.5°	530.0	528.8	527.6	526.4	525.6	524.8	524.0	523.3
40°	508.4	506.9	505.3	504.2	503.5	502.9	502.2	501.5
42.5°	487.0	485.3	483.6	482.4	481.4	480.5	479.6	478.6
45°	454.1	452.3	450.4	449.2	448.5	447.9	447.2	446.5
47.5°	420.0	418.0	416.1	414.7	413.6	412.7	411.7	410.7
50°	398.1	395.7	393.3	391.7	390.9	390.1	389.2	388.4
52.5°	375.4	373.3	371.4	369.9	368.8	367.7	366.6	365.5
55°	341.4	339.4	337.4	336.0	335.1	334.3	333.5	332.6
57.5°	306.2	304.2	302.3	300.9	300.2	299.6	299.0	298.3
60°	282.9	281.0	279.2	278.0	277.5	277.0	276.5	276.0
62.5°	260.8	259.1	257.4	256.3	255.6	255.0	254.4	253.7
65°	227.0	225.5	224.0	222.8	222.0	221.2	220.4	219.4
67.5°	193.6	192.4	191.3	190.4	189.7	188.9	188.3	187.6
70°	171.9	170.7	169.6	168.6	167.9	167.2	166.6	165.9
72.5°	151.4	150.2	149.1	148.1	147.6	147.0	146.5	146.0
75°	119.4	118.5	117.4	117.0	117.4	117.8	118.1	118.5
77.5°	90.9	90.4	89.9	89.4	88.9	88.5	88.0	87.5
80°	72.1	71.6	71.2	70.7	70.4	70.1	69.7	69.4
82.5°	53.8	53.1	52.5	52.1	52.1	52.0	51.9	51.9
85°	28.4	27.9	27.4	27.1	26.9	26.8	26.6	26.4
87.5°	14.6	14.1	13.6	13.3	13.2	13.1	13.0	13.0
90°	34.8	34.4	33.9	33.8	34.1	34.3	34.5	34.7
92.5°	32.7	32.8	32.9	32.9	33.0	33.0	33.1	33.1
95°	65.4	65.4	65.4	65.2	64.7	64.3	63.8	63.4
97.5°	110.1	110.1	110.1	110.1	110.0	110.0	109.9	109.9
100°	141.2	141.2	141.2	141.1	140.8	140.6	140.4	140.2
102.5°	175.1	175.2	175.4	175.4	175.2	174.9	174.7	174.5
105°	225.9	226.4	226.8	227.1	227.1	227.1	227.1	227.1
107.5°	280.8	281.0	281.1	280.7	279.7	278.6	277.6	276.6
110°	318.1	318.1	318.1	317.8	317.1	316.4	315.7	315.1



TEST NUMBER: P331512-840

CATALOG NUMBER: S122DIW-S485D970U840-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	355.5	355.0	354.4	353.9	353.4	352.8	352.3	351.8
115°	412.7	412.5	412.3	411.8	411.2	410.5	409.8	409.1
117.5°	468.2	467.7	467.1	466.5	465.9	465.1	464.4	463.7
120°	505.3	505.3	505.3	504.9	504.2	503.6	502.9	502.2
122.5°	543.5	542.9	542.4	541.9	541.4	540.9	540.4	539.9
125°	600.1	599.4	598.7	598.2	598.0	597.8	597.5	597.3
127.5°	655.0	654.2	653.4	652.6	651.9	651.2	650.5	649.7
130°	692.6	692.2	691.7	690.9	690.0	689.1	688.2	687.3
132.5°	729.1	728.1	727.1	726.3	725.6	724.8	724.1	723.4
135°	783.0	782.8	782.5	782.1	781.4	780.7	780.1	779.4
137.5°	834.7	834.6	834.4	833.7	832.8	831.9	831.0	830.1
140°	869.4	869.4	869.4	869.0	868.1	867.2	866.3	865.4
142.5°	900.9	901.1	901.2	900.9	900.0	899.1	898.2	897.3
145°	948.7	948.9	949.1	948.8	947.9	947.0	946.0	945.1
147.5°	990.5	991.0	991.5	991.3	990.5	989.6	988.8	987.8
150°	1017.0	1017.7	1018.4	1018.4	1017.7	1017.0	1016.3	1015.7
152.5°	1043.6	1044.5	1045.3	1045.3	1044.5	1043.6	1042.7	1041.9
155°	1077.3	1078.4	1079.5	1079.7	1079.1	1078.4	1077.7	1077.0
157.5°	1108.4	1109.9	1111.5	1111.7	1110.6	1109.5	1108.4	1107.3
160°	1126.8	1128.2	1129.5	1129.8	1128.9	1128.0	1127.1	1126.2
162.5°	1143.6	1145.1	1146.7	1146.9	1145.8	1144.7	1143.6	1142.6
165°	1165.2	1166.7	1168.3	1168.5	1167.4	1166.3	1165.2	1164.0
167.5°	1183.0	1184.6	1186.1	1186.3	1185.2	1184.0	1182.8	1181.6
170°	1192.8	1194.4	1196.0	1196.1	1194.7	1193.4	1191.9	1190.6
172.5°	1200.1	1201.7	1203.3	1203.5	1202.0	1200.7	1199.3	1198.0
175°	1208.1	1209.7	1211.2	1211.4	1210.0	1208.7	1207.3	1206.0
177.5°	1211.8	1212.8	1214.0	1214.0	1212.8	1211.8	1210.7	1209.6
180°	1212.0	1212.0	1212.0	1212.0	1212.0	1212.0	1212.0	1212.0

(END OF REPORT)