

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332464-927

Luminaire Tested: **S123RDIW-S1000D1320U927-4F0-1E-UDD-F**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P332464-927  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-5,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S123RDIW-S1000D1320U927-4F0-1E-UDD-F  
Description: DEFINE 3 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 1000 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED  
HOUSING  
UPLIGHT 1320 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 7188.2 lumens  
Efficiency: N/A  
Efficacy: 103.0 lumens/watt  
Spacing Criteria (0/90/45): 1.21 / 1.06 / 1.22  
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')  
CIE Type: General Diffuse


Input Watts (W): 69.8  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332464-927

CATALOG NUMBER: S123RDIW-S1000D1320U927-4F0-1E-UDD-F

### Luminous Intensity Polar Plot





TEST NUMBER: P332464-927

CATALOG NUMBER: S123RDIW-S1000D1320U927-4F0-1E-UDD-F

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	105	105	105	105	96	96	96	96	79	79	79	63	63	63	49	49	49	42
1	96	92	88	85	88	84	81	78	69	67	65	56	54	53	43	42	42	36
2	88	81	75	70	80	74	69	65	61	57	54	49	47	45	38	37	35	30
3	80	71	64	58	73	65	59	54	54	50	46	44	41	38	34	32	30	26
4	73	63	55	50	67	58	51	46	48	43	39	39	36	33	31	28	26	23
5	68	56	48	43	61	52	45	40	43	38	34	35	31	29	28	25	23	20
6	62	50	43	37	57	46	40	35	39	34	30	32	28	25	25	23	20	17
7	58	46	38	32	52	42	35	30	35	30	26	29	25	22	23	20	18	16
8	53	41	34	29	49	38	32	27	32	27	23	27	23	20	21	19	16	14
9	50	38	30	26	45	35	28	24	30	24	21	25	21	18	20	17	15	13
10	46	35	28	23	42	32	26	22	27	22	19	23	19	16	18	16	14	12

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	14310	14310	14310
5°	14364	14166	14249
10°	14283	13988	13941
15°	14130	13661	13517
20°	13919	13252	12944
25°	13702	12792	12383
30°	13415	12263	11591
35°	13119	11730	10867
40°	12847	11105	9969
45°	12490	10488	9159
50°	12097	9786	8251
55°	11695	8983	7405
60°	11328	8125	6476
65°	10847	7195	5547
70°	10247	6039	4482
75°	9374	4754	4213
80°	8356	4209	3874
85°	7052	3730	3458



TEST NUMBER: P332464-927

CATALOG NUMBER: S123RDIW-S1000D1320U927-4F0-1E-UDD-F

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	124.8	1.7
10°-20°	347.3	4.8
20°-30°	500.2	7.0
30°-40°	563.4	7.8
40°-50°	539.0	7.5
50°-60°	441.4	6.1
60°-70°	297.8	4.1
70°-80°	149.8	2.1
80°-90°	43.5	0.6
90°-100°	49.8	0.7
100°-110°	237.6	3.3
110°-120°	570.6	7.9
120°-130°	726.7	10.1
130°-140°	776.4	10.8
140°-150°	726.0	10.1
150°-160°	585.6	8.1
160°-170°	378.0	5.3
170°-180°	130.3	1.8
0°-30°	972.3	13.5
0°-40°	1535.7	21.4
0°-60°	2516.0	35.0
0°-90°	3007.1	41.8
90°-120°	858.1	11.9
90°-150°	3087.2	42.9
90°-180°	4181.0	58.2
0°-180°	7188.2	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1329	1329	1329	1329	1329	
5°	1329	1324	1311	1320	1319	126
15°	1268	1255	1226	1220	1213	357
25°	1154	1125	1077	1055	1043	530
35°	998	958	893	848	827	625
45°	820	770	689	629	602	633
55°	623	568	479	418	395	559
65°	426	365	282	232	218	421
75°	225	173	114	104	101	240
85°	57	34	30	28	28	64
90°	1	11	24	28	31	6
95°	62	23	32	38	39	77
105°	304	309	223	53	45	322
115°	569	576	585	594	599	562
125°	803	811	815	817	819	717
135°	999	1005	1010	1012	1010	769
145°	1153	1160	1162	1164	1164	722
155°	1270	1268	1269	1274	1268	585
165°	1340	1336	1335	1343	1336	378
175°	1371	1366	1367	1373	1366	130
180°	1371	1371	1371	1371	1371	



TEST NUMBER: P332464-927

CATALOG NUMBER: S123RDIW-S1000D1320U927-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1329.4	1329.4	1329.4	1329.4	1329.4	1329.4	1329.4	1329.4	1329.4	1329.4	1329.4
2.5°	1333.7	1332.9	1332.2	1331.4	1330.6	1329.1	1326.8	1324.5	1322.2	1319.9	1322.0
5°	1329.4	1328.2	1327.0	1325.8	1324.6	1322.5	1319.7	1316.8	1314.0	1311.1	1313.2
7.5°	1317.1	1315.8	1314.5	1313.2	1311.9	1309.4	1305.7	1302.0	1298.2	1294.5	1295.7
10°	1306.8	1305.1	1303.4	1301.7	1300.1	1297.0	1292.8	1288.4	1284.1	1279.8	1280.1
12.5°	1292.1	1290.2	1288.4	1286.5	1284.6	1281.0	1275.8	1270.5	1265.3	1260.0	1259.8
15°	1268.0	1265.4	1262.7	1260.0	1257.4	1252.8	1246.0	1239.3	1232.6	1225.9	1224.7
17.5°	1237.5	1234.5	1231.4	1228.4	1225.3	1219.5	1210.9	1202.5	1193.9	1185.3	1182.8
20°	1215.1	1211.3	1207.4	1203.6	1199.8	1193.3	1184.2	1175.1	1166.0	1156.9	1153.8
22.5°	1190.1	1185.7	1181.3	1176.9	1172.5	1165.5	1155.7	1146.1	1136.4	1126.7	1122.8
25°	1153.7	1147.7	1141.7	1135.7	1129.7	1121.2	1110.2	1099.2	1088.1	1077.1	1072.1
27.5°	1109.5	1102.9	1096.2	1089.6	1083.0	1073.6	1061.3	1049.0	1036.7	1024.5	1017.5
30°	1079.3	1072.1	1064.9	1057.7	1050.5	1040.2	1026.8	1013.4	1000.0	986.6	978.4
32.5°	1049.1	1040.9	1032.8	1024.6	1016.5	1005.4	991.2	977.0	962.7	948.6	939.7
35°	998.4	989.8	981.1	972.6	963.9	952.1	937.3	922.4	907.6	892.7	882.4
37.5°	947.1	937.5	927.9	918.3	908.7	896.0	880.2	864.3	848.4	832.6	820.9
40°	914.3	903.8	893.2	882.6	872.1	858.3	841.4	824.3	807.3	790.3	777.8
42.5°	877.2	866.6	856.1	845.6	835.0	821.0	803.4	785.8	768.3	750.7	737.0
45°	820.5	809.7	798.9	788.1	777.4	762.8	744.3	725.9	707.4	689.0	675.3
47.5°	763.8	751.9	740.1	728.3	716.4	701.3	682.9	664.4	645.9	627.5	612.7
50°	722.4	711.1	699.9	688.6	677.3	662.0	642.6	623.2	603.8	584.4	569.5
52.5°	685.3	673.1	660.8	648.6	636.4	620.7	601.5	582.3	563.1	543.8	528.4
55°	623.2	611.5	599.7	588.0	576.2	560.2	539.8	519.4	499.1	478.7	464.9
57.5°	565.9	553.0	540.3	527.4	514.7	498.0	477.5	457.1	436.7	416.2	403.1
60°	526.2	513.0	499.8	486.6	473.4	456.9	437.0	417.2	397.3	377.4	364.4
62.5°	486.5	473.3	460.1	446.9	433.8	417.2	397.4	377.5	357.6	337.7	325.5
65°	425.9	412.7	399.5	386.3	373.2	357.3	338.6	319.9	301.2	282.5	270.8
67.5°	365.3	352.0	338.7	325.3	312.0	296.4	278.5	260.5	242.6	224.7	215.9
70°	325.6	312.7	299.8	286.8	273.9	259.0	242.2	225.5	208.7	191.9	183.5
72.5°	285.9	273.2	260.5	247.7	235.0	220.9	205.7	190.5	175.2	160.0	153.1
75°	225.4	213.8	202.3	190.8	179.4	167.0	153.8	140.6	127.5	114.3	111.9
77.5°	170.2	159.7	149.3	138.9	128.6	119.1	110.6	102.1	93.6	85.2	83.9
80°	134.8	124.9	115.1	105.3	95.5	88.1	83.0	78.0	73.0	67.9	67.2
82.5°	101.2	92.7	84.2	75.7	67.2	61.8	59.4	57.1	54.7	52.4	51.7
85°	57.1	51.9	46.6	41.4	36.0	33.0	32.3	31.6	30.9	30.2	29.7
87.5°	20.9	19.3	17.6	15.9	14.3	13.8	14.3	14.9	15.5	16.1	16.1
90°	1.0	3.2	5.5	7.8	10.1	12.7	15.6	18.5	21.5	24.5	25.3
92.5°	18.9	18.3	17.7	17.0	16.4	17.2	19.4	21.6	23.8	26.1	27.5
95°	62.1	52.8	43.6	34.3	25.0	21.6	24.1	26.6	29.1	31.6	33.2
97.5°	124.8	120.7	116.5	112.4	108.2	98.0	81.7	65.4	49.1	32.8	34.6
100°	172.1	176.7	181.2	185.7	190.3	174.8	139.6	104.3	68.9	33.6	35.4
102.5°	225.9	229.2	232.4	235.7	239.0	221.3	182.8	144.2	105.6	67.0	61.4
105°	303.6	306.0	308.6	311.0	313.5	304.6	284.2	263.8	243.4	223.1	183.0
107.5°	385.5	387.5	389.4	391.4	393.4	396.0	399.3	402.4	405.7	408.8	379.5
110°	440.1	441.9	443.6	445.4	447.3	449.4	451.9	454.4	456.9	459.4	451.9



TEST NUMBER: P332464-927

CATALOG NUMBER: S123RDIW-S1000D1320U927-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	492.2	493.8	495.4	497.1	498.7	500.7	503.3	505.7	508.3	510.7	510.9
115°	569.4	570.8	572.1	573.5	574.8	576.6	578.5	580.6	582.7	584.7	586.9
117.5°	644.2	645.9	647.5	649.2	650.9	652.2	653.2	654.3	655.4	656.4	658.2
120°	690.6	692.7	694.7	696.7	698.8	700.1	700.8	701.5	702.2	702.8	704.6
122.5°	737.9	739.6	741.2	742.9	744.6	745.8	746.7	747.6	748.5	749.3	750.6
125°	802.6	804.5	806.3	808.1	809.9	811.3	812.1	813.1	814.0	814.9	815.3
127.5°	865.4	867.2	869.0	870.8	872.7	874.1	875.2	876.3	877.3	878.5	879.2
130°	904.5	906.3	908.2	910.0	911.8	913.1	914.0	915.0	915.8	916.7	917.7
132.5°	942.0	943.8	945.6	947.5	949.3	950.5	951.3	952.0	952.7	953.4	954.3
135°	999.3	1000.6	1002.0	1003.3	1004.7	1005.8	1006.7	1007.7	1008.5	1009.5	1010.1
137.5°	1048.1	1049.9	1051.6	1053.3	1055.0	1056.1	1056.6	1057.2	1057.6	1058.1	1059.2
140°	1080.8	1082.1	1083.5	1084.8	1086.2	1087.2	1087.9	1088.5	1089.3	1089.9	1090.8
142.5°	1110.9	1112.2	1113.6	1115.0	1116.3	1117.4	1118.0	1118.7	1119.4	1120.1	1120.8
145°	1153.1	1154.7	1156.3	1157.9	1159.4	1160.4	1160.9	1161.3	1161.8	1162.2	1162.7
147.5°	1192.8	1193.8	1194.8	1195.9	1197.0	1197.7	1198.2	1198.6	1199.0	1199.5	1200.0
150°	1217.3	1217.9	1218.6	1219.2	1220.0	1220.5	1221.0	1221.4	1221.9	1222.3	1222.8
152.5°	1239.2	1239.5	1239.8	1240.2	1240.5	1240.8	1241.1	1241.3	1241.6	1241.9	1242.7
155°	1270.2	1269.8	1269.3	1268.8	1268.4	1268.3	1268.5	1268.8	1269.0	1269.2	1270.3
157.5°	1294.3	1294.2	1294.2	1294.1	1294.0	1294.0	1293.7	1293.5	1293.2	1293.0	1294.3
160°	1308.9	1308.7	1308.4	1308.2	1308.0	1307.8	1307.6	1307.3	1307.1	1306.9	1308.2
162.5°	1322.8	1322.2	1321.6	1321.0	1320.4	1320.0	1319.8	1319.5	1319.3	1319.1	1320.6
165°	1339.5	1338.8	1338.1	1337.4	1336.7	1336.3	1336.1	1335.9	1335.6	1335.4	1337.2
167.5°	1352.5	1351.6	1350.7	1349.8	1348.8	1348.5	1348.5	1348.5	1348.5	1348.5	1350.3
170°	1359.9	1358.9	1358.0	1357.2	1356.2	1355.7	1355.7	1355.7	1355.7	1355.7	1357.6
172.5°	1364.8	1363.7	1362.6	1361.4	1360.4	1359.9	1360.1	1360.3	1360.5	1360.7	1362.5
175°	1371.0	1369.9	1368.8	1367.6	1366.5	1366.0	1366.3	1366.5	1366.8	1367.0	1368.6
177.5°	1372.7	1371.7	1370.9	1370.0	1369.0	1368.7	1368.9	1369.0	1369.2	1369.4	1370.9
180°	1371.0	1371.0	1371.0	1371.0	1371.0	1371.0	1371.0	1371.0	1371.0	1371.0	1371.0



TEST NUMBER: P332464-927

CATALOG NUMBER: S123RDIW-S1000D1320U927-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1329.4	1329.4	1329.4	1329.4	1329.4	1329.4	1329.4	1329.4
2.5°	1324.1	1326.3	1328.3	1329.2	1328.8	1328.5	1328.1	1327.7
5°	1315.4	1317.6	1319.7	1320.6	1320.1	1319.6	1319.1	1318.7
7.5°	1296.9	1298.1	1299.3	1299.5	1298.6	1297.8	1297.0	1296.2
10°	1280.3	1280.6	1280.8	1280.3	1279.1	1277.9	1276.7	1275.5
12.5°	1259.6	1259.6	1259.4	1258.6	1257.3	1255.8	1254.5	1253.1
15°	1223.5	1222.3	1221.1	1219.6	1218.0	1216.3	1214.7	1213.0
17.5°	1180.3	1177.7	1175.2	1172.7	1170.2	1167.7	1165.2	1162.7
20°	1150.6	1147.6	1144.5	1141.5	1138.6	1135.7	1132.8	1130.0
22.5°	1119.0	1115.1	1111.2	1107.9	1105.3	1102.6	1099.9	1097.2
25°	1067.1	1062.0	1057.0	1053.1	1050.5	1047.9	1045.3	1042.6
27.5°	1010.5	1003.5	996.5	991.0	987.0	982.9	978.9	974.9
30°	970.3	962.1	953.9	948.0	944.1	940.3	936.4	932.6
32.5°	930.7	921.9	912.9	906.5	902.5	898.4	894.4	890.3
35°	872.1	861.8	851.5	844.2	840.0	835.6	831.3	827.0
37.5°	809.2	797.5	785.8	777.3	772.0	766.7	761.4	756.1
40°	765.4	753.0	740.5	731.5	726.0	720.5	714.9	709.5
42.5°	723.4	709.8	696.2	686.9	682.0	677.1	672.1	667.2
45°	661.6	648.0	634.3	624.6	618.9	613.1	607.4	601.7
47.5°	597.8	583.0	568.1	558.1	552.9	547.9	542.7	537.6
50°	554.7	539.8	525.0	514.8	509.3	503.7	498.3	492.7
52.5°	513.0	497.6	482.1	471.9	467.0	462.1	457.2	452.2
55°	450.9	437.0	423.1	413.8	409.0	404.2	399.4	394.6
57.5°	389.9	376.8	363.7	355.1	351.0	346.9	342.9	338.7
60°	351.5	338.6	325.6	317.1	313.1	309.0	304.9	300.8
62.5°	313.3	301.2	289.0	280.7	276.6	272.3	268.0	263.7
65°	259.0	247.2	235.5	228.3	225.7	223.1	220.5	217.8
67.5°	207.2	198.4	189.6	183.8	181.0	178.2	175.3	172.5
70°	175.2	166.8	158.4	152.9	150.2	147.6	145.0	142.4
72.5°	146.3	139.4	132.6	128.7	127.5	126.4	125.3	124.2
75°	109.5	107.1	104.7	103.3	102.8	102.3	101.8	101.3
77.5°	82.6	81.3	80.0	79.1	78.7	78.2	77.7	77.2
80°	66.5	65.8	65.0	64.5	64.0	63.5	63.0	62.5
82.5°	50.9	50.2	49.5	49.1	49.0	49.0	48.8	48.7
85°	29.2	28.8	28.3	28.0	28.0	28.0	28.0	28.0
87.5°	16.1	16.1	16.1	16.0	15.9	15.8	15.7	15.6
90°	26.2	27.2	28.0	28.8	29.2	29.6	30.1	30.6
92.5°	29.0	30.4	31.8	32.7	33.0	33.3	33.5	33.8
95°	34.8	36.4	37.9	38.7	38.7	38.7	38.7	38.7
97.5°	36.4	38.3	40.0	41.0	41.3	41.5	41.7	42.0
100°	37.2	39.1	40.9	41.9	42.1	42.3	42.5	42.8
102.5°	55.8	50.1	44.6	42.0	42.4	42.8	43.2	43.6
105°	142.9	102.9	62.8	43.0	43.5	43.9	44.4	44.8
107.5°	350.1	320.8	291.4	261.6	231.4	201.1	171.0	140.8
110°	444.4	437.0	429.5	409.6	377.2	344.8	312.5	280.1





TEST NUMBER: P332464-927

CATALOG NUMBER: S123RDIW-S1000D1320U927-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	511.0	511.1	511.3	507.9	501.1	494.2	487.4	480.6
115°	589.2	591.4	593.7	595.3	596.2	597.1	598.0	599.0
117.5°	660.0	661.8	663.6	664.6	664.8	665.0	665.2	665.4
120°	706.5	708.3	710.1	711.0	711.0	711.0	711.0	711.0
122.5°	751.9	753.1	754.4	755.1	755.3	755.4	755.7	755.8
125°	815.8	816.3	816.7	817.1	817.6	818.1	818.5	819.0
127.5°	879.9	880.6	881.4	881.5	881.1	880.6	880.1	879.6
130°	918.5	919.5	920.4	920.6	920.1	919.7	919.2	918.8
132.5°	955.2	956.2	957.0	957.2	956.6	955.9	955.3	954.7
135°	1010.8	1011.5	1012.2	1012.2	1011.5	1010.8	1010.1	1009.5
137.5°	1060.3	1061.4	1062.5	1062.8	1062.3	1061.9	1061.4	1061.0
140°	1091.7	1092.7	1093.5	1093.8	1093.3	1092.8	1092.4	1091.9
142.5°	1121.5	1122.2	1123.0	1123.0	1122.4	1121.7	1121.1	1120.5
145°	1163.2	1163.6	1164.0	1164.3	1164.3	1164.3	1164.3	1164.3
147.5°	1200.4	1200.9	1201.3	1201.0	1200.0	1199.0	1197.9	1196.8
150°	1223.2	1223.7	1224.2	1224.0	1223.4	1222.7	1222.0	1221.3
152.5°	1243.5	1244.4	1245.2	1245.1	1244.0	1242.9	1241.9	1240.9
155°	1271.5	1272.6	1273.7	1273.6	1272.2	1270.9	1269.6	1268.2
157.5°	1295.8	1297.1	1298.5	1298.2	1296.5	1294.7	1292.9	1291.2
160°	1309.6	1311.0	1312.3	1312.2	1310.6	1309.0	1307.4	1305.8
162.5°	1322.2	1323.7	1325.2	1325.3	1323.9	1322.5	1321.1	1319.7
165°	1339.0	1340.8	1342.7	1342.7	1341.2	1339.6	1338.0	1336.4
167.5°	1352.1	1353.8	1355.7	1355.7	1353.8	1352.1	1350.3	1348.5
170°	1359.4	1361.2	1363.0	1363.0	1361.2	1359.4	1357.6	1355.7
172.5°	1364.3	1366.1	1367.9	1367.8	1365.8	1363.8	1361.8	1359.9
175°	1370.2	1371.7	1373.3	1373.2	1371.4	1369.6	1367.8	1366.0
177.5°	1372.3	1373.8	1375.2	1375.1	1373.2	1371.4	1369.6	1367.8
180°	1371.0	1371.0	1371.0	1371.0	1371.0	1371.0	1371.0	1371.0

(END OF REPORT)