

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331549-840

Luminaire Tested: **S122DIW-S675D1440U840-4F0-1E-UDD-A**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P331549-840  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S122DIW-S675D1440U840-4F0-1E-UDD-A  
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 675 LUMENS PER FOOT, ASYMMETRIC DIFFUSER  
UPLIGHT 1440 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 8781.1 lumens  
Efficiency: N/A  
Efficacy: 128.9 lumens/watt  
Spacing Criteria (0/90/45): 1.08 / 1.16 / 1.23  
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')  
CIE Type: Semi-Indirect


Input Watts (W): 68.1  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P331549-840

CATALOG NUMBER: S122DIW-S675D1440U840-4F0-1E-UDD-A

### Luminous Intensity Polar Plot





TEST NUMBER: P331549-840

CATALOG NUMBER: S122DIW-S675D1440U840-4F0-1E-UDD-A

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	103	103	103	103	93	93	93	93	74	74	74	57	57	57	41	41	41	34
1	94	90	87	83	85	82	79	76	65	63	61	51	49	48	37	36	35	29
2	86	79	73	69	78	72	67	63	58	54	51	45	43	41	33	31	30	25
3	79	70	63	57	71	63	57	53	51	47	44	40	37	35	29	28	26	21
4	72	62	54	49	65	56	50	45	46	41	37	36	33	30	26	24	23	19
5	66	55	48	42	60	50	44	39	41	36	32	32	29	26	24	22	20	16
6	61	50	42	36	55	45	38	34	37	32	28	29	26	23	22	20	18	15
7	57	45	37	32	51	41	34	30	33	29	25	27	23	20	20	18	16	13
8	52	41	33	28	47	37	31	26	31	26	22	24	21	18	18	16	14	12
9	49	37	30	25	44	34	28	23	28	23	20	22	19	16	17	15	13	11
10	46	34	27	22	41	31	25	21	26	21	18	21	17	15	16	14	12	10

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	21658	21658	21658	21658
5°	24280	21797	19316	21797
10°	27824	21620	16718	21620
15°	30780	21224	14770	21224
20°	30311	20797	13464	20797
25°	27332	20232	12636	20232
30°	22585	19328	12033	19328
35°	16462	18382	11606	18382
40°	13148	17266	11367	17266
45°	11488	15972	11040	15972
50°	10798	14722	10826	14722
55°	9956	13453	10536	13453
60°	9122	12103	10091	12103
65°	8309	10892	9650	10892
70°	7544	9711	9007	9711
75°	6687	8390	7973	8390
80°	5755	6946	6425	6946
85°	5169	5169	3816	5169



TEST NUMBER: P331549-840

CATALOG NUMBER: S122DIW-S675D1440U840-4F0-1E-UDD-A

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	127.7	1.5
10°-20°	371.4	4.2
20°-30°	539.0	6.1
30°-40°	568.8	6.5
40°-50°	503.6	5.7
50°-60°	401.9	4.6
60°-70°	273.2	3.1
70°-80°	140.0	1.6
80°-90°	38.7	0.4
90°-100°	66.2	0.8
100°-110°	242.8	2.8
110°-120°	649.0	7.4
120°-130°	1071.4	12.2
130°-140°	1139.4	13.0
140°-150°	1059.0	12.1
150°-160°	851.5	9.7
160°-170°	548.7	6.2
170°-180°	188.9	2.2
0°-30°	1038.1	11.8
0°-40°	1606.9	18.3
0°-60°	2512.4	28.6
0°-90°	2964.2	33.8
90°-120°	958.1	10.9
90°-150°	4227.9	48.1
90°-180°	5817.0	66.2
0°-180°	8781.1	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	1341	1341	1341	1341	1341	
5°	1498	1345	1192	1345	1498	150
15°	1841	1270	884	1270	1841	508
25°	1534	1136	709	1136	1534	693
35°	835	933	589	933	835	543
45°	503	700	484	700	503	396
55°	354	478	374	478	354	317
65°	218	285	253	285	218	216
75°	107	134	128	134	107	115
85°	28	28	21	28	28	32
90°	39	1	39	1	39	18
95°	62	93	62	93	62	58
105°	109	437	109	437	109	114
115°	118	826	118	826	118	295
125°	1228	1168	1228	1168	1228	1063
135°	1492	1445	1492	1445	1492	1150
145°	1702	1676	1702	1676	1702	1064
155°	1847	1846	1847	1846	1847	852
165°	1940	1945	1940	1945	1940	548
175°	1978	1989	1978	1989	1978	188
180°	1985	1985	1985	1985	1985	



TEST NUMBER: P331549-840

CATALOG NUMBER: S122DIW-S675D1440U840-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4
2.5°	1403.2	1403.6	1404.5	1397.9	1397.0	1397.0	1391.3	1386.3	1380.6	1372.7	1373.5
5°	1498.1	1503.8	1505.8	1499.6	1490.4	1489.3	1480.6	1466.1	1452.7	1441.9	1434.2
7.5°	1611.3	1613.6	1608.5	1600.3	1593.5	1581.1	1564.8	1548.8	1526.4	1505.9	1490.7
10°	1697.1	1700.2	1691.4	1679.6	1669.8	1655.4	1631.6	1607.4	1578.0	1549.6	1526.9
12.5°	1762.2	1769.9	1758.7	1757.1	1740.3	1720.5	1692.2	1680.0	1638.6	1599.1	1574.8
15°	1841.4	1840.9	1842.0	1832.2	1819.8	1816.6	1786.8	1754.3	1696.1	1672.8	1632.6
17.5°	1818.6	1826.3	1830.0	1829.9	1829.6	1827.7	1818.1	1797.6	1768.4	1730.7	1684.3
20°	1764.1	1774.4	1775.9	1787.9	1794.5	1803.3	1806.9	1801.2	1783.2	1751.7	1711.5
22.5°	1680.0	1682.8	1687.7	1706.2	1720.7	1742.6	1754.1	1773.2	1766.3	1750.9	1717.3
25°	1534.2	1529.0	1547.1	1556.3	1589.8	1624.9	1650.2	1678.0	1702.7	1717.7	1707.9
27.5°	1359.1	1351.4	1378.4	1403.0	1430.3	1468.2	1507.6	1554.1	1592.8	1641.1	1657.7
30°	1211.4	1216.1	1241.9	1268.2	1309.4	1363.0	1407.3	1458.4	1513.6	1567.7	1605.3
32.5°	1052.3	1070.2	1086.4	1126.7	1163.0	1222.8	1287.8	1351.6	1420.4	1481.9	1540.1
35°	835.2	855.8	878.5	907.9	958.9	1018.1	1081.6	1167.6	1261.5	1345.5	1414.6
37.5°	703.0	699.6	712.7	733.9	775.3	823.0	896.1	981.2	1091.6	1190.3	1287.8
40°	623.8	621.7	631.0	650.6	682.1	717.1	781.0	855.8	958.4	1078.9	1195.0
42.5°	569.4	570.6	575.7	589.6	611.1	640.0	687.8	751.4	845.4	959.0	1083.6
45°	503.1	506.8	512.4	519.2	531.5	555.2	582.0	627.4	701.7	796.5	919.2
47.5°	455.6	455.7	461.4	467.3	474.6	488.0	509.9	538.3	590.7	667.9	773.4
50°	429.9	426.4	430.5	435.0	442.8	452.1	466.6	493.3	528.4	590.8	678.9
52.5°	398.6	398.7	402.4	404.1	411.1	420.3	433.5	452.1	483.8	532.6	605.1
55°	353.7	356.2	358.3	361.3	367.6	374.3	384.6	397.0	421.7	458.3	511.9
57.5°	311.3	312.1	314.3	320.1	324.1	330.2	340.0	351.2	367.4	394.5	434.7
60°	282.5	282.5	286.6	289.2	294.4	300.5	308.3	319.1	333.6	355.7	388.2
62.5°	256.1	255.7	257.3	261.6	265.5	271.2	279.0	288.2	301.7	321.4	348.2
65°	217.5	216.5	219.6	220.7	224.8	230.5	236.6	246.4	257.2	271.7	295.4
67.5°	180.5	181.7	183.3	185.3	187.5	193.5	197.6	204.6	213.7	225.7	241.8
70°	159.8	159.8	159.8	161.4	164.4	167.5	171.7	177.3	186.1	196.4	210.9
72.5°	136.7	138.4	140.0	139.1	143.0	144.8	149.8	153.0	161.4	167.9	180.8
75°	107.2	107.2	107.2	109.8	111.4	112.9	116.0	119.1	123.2	131.5	138.1
77.5°	80.0	79.8	80.3	80.9	82.6	84.4	85.3	88.2	92.0	95.7	101.5
80°	61.9	62.9	63.4	64.4	64.4	65.4	65.9	69.6	72.2	74.7	78.4
82.5°	47.9	48.1	48.2	48.4	48.8	49.4	50.7	51.9	52.8	54.9	57.8
85°	27.9	27.4	27.4	28.4	27.9	27.9	28.9	29.9	29.9	30.4	31.9
87.5°	18.5	18.4	18.7	18.1	18.0	18.2	17.9	17.1	17.2	17.3	17.2
90°	38.8	38.2	37.5	36.9	36.3	35.1	33.5	31.9	30.3	28.7	26.2
92.5°	38.8	38.4	38.0	37.7	37.3	36.7	35.9	34.9	34.1	33.3	32.0
95°	61.8	62.1	62.4	62.7	63.0	62.4	60.8	59.2	57.6	56.0	53.8
97.5°	82.4	82.1	81.7	81.3	80.9	80.1	78.8	77.6	76.2	74.9	69.8
100°	96.2	95.6	94.9	94.3	93.7	92.1	89.6	86.9	84.4	81.9	76.4
102.5°	103.1	102.2	101.3	100.5	99.6	97.5	94.1	90.8	87.5	84.1	129.6
105°	109.2	107.9	106.6	105.3	104.0	101.7	98.2	94.6	91.1	87.7	174.7
107.5°	112.3	111.1	109.8	108.5	107.2	108.4	111.9	115.5	119.1	122.7	227.1
110°	113.5	112.2	110.9	109.7	108.4	123.7	155.6	187.5	219.4	251.4	343.6



TEST NUMBER: P331549-840

CATALOG NUMBER: S122DIW-S675D1440U840-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	114.6	113.6	112.6	111.6	110.5	168.2	284.7	401.1	517.6	634.0	656.7
115°	117.8	140.8	163.7	186.7	209.6	295.1	442.8	590.7	738.4	886.2	878.2
117.5°	480.9	556.3	631.9	707.4	782.9	838.6	874.3	910.1	945.8	981.6	976.0
120°	876.2	919.2	962.3	1005.4	1048.4	1068.1	1064.3	1060.5	1056.6	1052.8	1047.0
122.5°	1093.3	1101.7	1110.0	1118.3	1126.7	1129.7	1127.5	1125.2	1122.9	1120.5	1114.3
125°	1228.0	1227.1	1226.1	1225.2	1224.2	1222.5	1220.3	1218.1	1215.9	1213.7	1207.6
127.5°	1313.0	1312.8	1312.6	1312.4	1312.3	1310.5	1307.3	1304.0	1300.8	1297.6	1293.0
130°	1365.8	1366.2	1366.5	1366.9	1367.2	1365.5	1362.1	1358.6	1355.0	1351.5	1348.0
132.5°	1417.5	1418.0	1418.3	1418.6	1418.9	1417.5	1414.5	1411.5	1408.6	1405.5	1402.0
135°	1492.3	1492.9	1493.6	1494.2	1494.8	1493.6	1490.4	1487.1	1484.0	1480.8	1477.9
137.5°	1560.3	1561.5	1562.6	1563.6	1564.7	1563.7	1560.5	1557.4	1554.3	1551.2	1547.9
140°	1602.9	1604.5	1606.1	1607.7	1609.2	1608.6	1605.8	1602.9	1600.0	1597.1	1593.7
142.5°	1644.3	1645.9	1647.4	1649.0	1650.6	1650.1	1647.5	1644.9	1642.2	1639.6	1635.6
145°	1702.0	1703.5	1705.2	1706.8	1708.4	1708.1	1705.8	1703.5	1701.3	1699.1	1693.6
147.5°	1752.8	1754.1	1755.5	1756.9	1758.2	1758.1	1756.4	1754.7	1753.0	1751.4	1746.1
150°	1783.8	1785.4	1787.1	1788.7	1790.2	1790.1	1788.2	1786.2	1784.3	1782.4	1777.3
152.5°	1810.3	1812.4	1814.5	1816.5	1818.7	1818.8	1816.8	1814.9	1813.0	1811.1	1806.2
155°	1847.0	1849.6	1852.2	1854.7	1857.2	1857.5	1855.6	1853.7	1851.8	1849.9	1846.1
157.5°	1880.7	1883.1	1885.6	1888.1	1890.6	1890.8	1888.5	1886.4	1884.3	1882.1	1879.4
160°	1900.2	1902.4	1904.6	1906.9	1909.1	1909.3	1907.3	1905.4	1903.5	1901.6	1899.7
162.5°	1916.3	1919.0	1921.8	1924.5	1927.2	1927.5	1925.4	1923.2	1921.1	1918.8	1917.2
165°	1940.4	1942.7	1944.9	1947.1	1949.3	1949.3	1947.1	1944.9	1942.7	1940.4	1939.4
167.5°	1955.6	1958.5	1961.4	1964.3	1967.1	1967.4	1965.2	1963.0	1960.8	1958.5	1957.6
170°	1964.8	1967.7	1970.5	1973.5	1976.3	1976.6	1974.4	1972.2	1969.9	1967.7	1967.0
172.5°	1971.7	1974.6	1977.4	1980.3	1983.2	1983.5	1981.3	1979.0	1976.8	1974.6	1974.0
175°	1977.7	1981.0	1984.1	1987.3	1990.5	1990.9	1988.7	1986.5	1984.3	1982.1	1981.5
177.5°	1981.5	1983.8	1986.1	1988.3	1990.6	1990.9	1989.1	1987.3	1985.6	1983.8	1983.5
180°	1984.9	1984.9	1984.9	1984.9	1984.9	1984.9	1984.9	1984.9	1984.9	1984.9	1984.9



TEST NUMBER: P331549-840

CATALOG NUMBER: S122DIW-S675D1440U840-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4
2.5°	1376.4	1373.1	1371.1	1363.6	1357.1	1350.5	1348.4	1349.2	1340.2	1331.5	1327.8
5°	1430.1	1419.8	1410.0	1396.0	1379.6	1361.5	1352.2	1344.9	1327.0	1307.4	1296.1
7.5°	1478.1	1463.4	1444.5	1418.3	1394.3	1365.9	1347.9	1331.9	1305.5	1277.9	1260.9
10°	1507.4	1487.2	1463.0	1431.1	1401.7	1367.2	1342.9	1318.7	1287.8	1254.8	1234.2
12.5°	1532.6	1505.4	1481.6	1440.6	1405.8	1362.6	1333.8	1299.7	1267.2	1228.0	1207.8
15°	1592.5	1542.5	1497.0	1450.7	1407.9	1347.6	1315.7	1269.7	1226.9	1178.5	1155.3
17.5°	1638.7	1582.6	1511.1	1452.1	1402.2	1335.4	1288.5	1233.6	1183.0	1127.5	1096.0
20°	1665.2	1600.6	1523.9	1453.8	1393.9	1317.7	1266.7	1210.4	1151.1	1088.7	1054.7
22.5°	1680.8	1613.1	1537.1	1447.5	1377.5	1303.2	1239.0	1177.4	1117.3	1050.1	1014.3
25°	1685.8	1623.9	1543.5	1442.4	1356.9	1272.8	1195.5	1135.7	1063.0	1000.1	948.1
27.5°	1661.2	1616.9	1539.5	1432.7	1333.0	1234.8	1148.6	1080.9	1004.1	935.8	883.5
30°	1631.1	1605.3	1530.0	1422.8	1314.0	1208.4	1113.5	1036.7	960.4	891.3	837.7
32.5°	1584.5	1578.9	1512.8	1408.8	1293.8	1175.0	1076.8	999.2	914.6	846.8	795.7
35°	1493.0	1517.7	1475.9	1377.5	1255.8	1127.4	1021.3	932.6	845.0	780.0	732.1
37.5°	1370.3	1431.7	1420.8	1331.6	1204.5	1075.7	958.5	865.8	782.2	716.7	669.6
40°	1285.7	1364.0	1375.4	1296.6	1168.2	1035.7	911.4	819.2	737.7	677.9	630.5
42.5°	1195.0	1286.6	1317.7	1254.5	1128.5	993.6	869.4	773.8	693.2	635.0	593.0
45°	1042.9	1164.1	1220.2	1184.2	1062.5	924.3	796.5	699.5	626.3	571.7	539.3
47.5°	900.7	1033.1	1108.6	1095.9	989.0	852.1	725.8	632.8	561.5	517.9	488.8
50°	800.1	936.1	1027.4	1031.6	936.1	800.6	673.8	586.1	520.7	480.0	456.3
52.5°	712.7	842.5	942.1	963.9	877.2	747.0	627.2	540.0	482.3	444.8	423.6
55°	598.5	708.3	818.6	858.9	789.2	665.5	554.7	477.9	423.7	398.0	379.4
57.5°	497.6	589.2	691.1	735.5	692.6	586.6	482.7	416.1	372.1	349.5	335.3
60°	444.3	516.5	607.2	660.4	623.3	529.0	438.2	374.8	338.7	318.6	305.2
62.5°	394.9	458.8	535.5	584.1	563.9	474.9	393.6	337.7	306.5	287.6	278.0
65°	325.8	376.4	435.7	480.5	467.1	399.5	333.1	285.1	260.3	245.4	237.6
67.5°	268.3	304.8	345.9	385.2	374.4	326.5	273.2	235.8	217.3	204.5	199.9
70°	232.0	259.8	296.4	327.9	319.1	279.9	237.6	205.7	189.8	178.8	174.2
72.5°	197.3	220.3	248.1	273.9	267.9	235.4	200.2	176.0	163.7	153.7	149.9
75°	149.0	166.5	183.5	200.6	198.9	173.7	153.1	134.5	124.7	117.0	115.4
77.5°	110.0	119.8	131.4	141.5	138.7	124.2	108.1	97.5	90.2	85.0	84.2
80°	84.0	89.7	98.0	105.1	101.6	95.3	82.5	74.7	69.6	64.4	62.4
82.5°	60.9	66.7	71.6	75.4	72.7	67.0	59.0	53.7	50.6	47.2	46.3
85°	31.9	35.0	37.2	38.2	37.2	33.5	29.9	27.9	25.2	23.7	23.2
87.5°	17.1	16.6	16.1	16.3	14.3	13.6	11.3	9.4	9.7	9.9	9.8
90°	23.6	21.1	18.5	15.5	12.0	8.5	4.9	1.4	4.9	8.5	12.0
92.5°	30.8	29.5	28.2	27.8	28.1	28.4	28.7	29.0	28.7	28.4	28.1
95°	51.5	49.3	47.1	51.2	61.8	72.3	82.8	93.3	82.8	72.3	61.8
97.5°	64.6	59.5	54.3	66.6	96.2	125.9	155.6	185.3	155.6	125.9	96.2
100°	71.0	65.5	60.2	79.3	123.0	166.7	210.5	254.2	210.5	166.7	123.0
102.5°	174.9	220.4	265.7	293.1	302.3	311.5	320.8	330.0	320.8	311.5	302.3
105°	261.9	349.0	436.2	474.9	465.3	455.8	446.2	436.7	446.2	455.8	465.3
107.5°	331.6	436.2	540.7	589.1	581.3	573.6	565.8	558.2	565.8	573.6	581.3
110°	435.9	528.1	620.3	663.1	656.4	649.6	643.0	636.3	643.0	649.6	656.4





TEST NUMBER: P331549-840

CATALOG NUMBER: S122DIW-S675D1440U840-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	679.5	702.4	725.1	733.6	727.6	721.6	715.7	709.8	715.7	721.6	727.6
115°	870.2	862.2	854.2	847.6	842.1	836.7	831.3	825.9	831.3	836.7	842.1
117.5°	970.6	965.0	959.6	953.8	947.8	941.7	935.6	929.6	935.6	941.7	947.8
120°	1041.3	1035.5	1029.8	1024.5	1019.8	1014.9	1010.2	1005.4	1010.2	1014.9	1019.8
122.5°	1108.0	1101.8	1095.6	1089.9	1084.9	1079.8	1074.8	1069.8	1074.8	1079.8	1084.9
125°	1201.5	1195.5	1189.4	1184.3	1180.1	1176.0	1171.8	1167.7	1171.8	1176.0	1180.1
127.5°	1288.5	1283.9	1279.4	1274.9	1270.2	1265.7	1261.0	1256.5	1261.0	1265.7	1270.2
130°	1344.5	1341.0	1337.5	1333.2	1328.1	1322.9	1317.9	1312.7	1317.9	1322.9	1328.1
132.5°	1398.5	1395.0	1391.5	1387.6	1383.2	1378.9	1374.5	1370.2	1374.5	1378.9	1383.2
135°	1475.0	1472.2	1469.3	1465.3	1460.2	1455.1	1450.0	1444.9	1450.0	1455.1	1460.2
137.5°	1544.7	1541.4	1538.1	1534.7	1531.2	1527.6	1524.0	1520.5	1524.0	1527.6	1531.2
140°	1590.1	1586.6	1583.1	1580.0	1577.5	1575.0	1572.4	1569.8	1572.4	1575.0	1577.5
142.5°	1631.6	1627.6	1623.6	1620.4	1618.1	1615.8	1613.5	1611.2	1613.5	1615.8	1618.1
145°	1688.3	1682.8	1677.4	1674.9	1675.2	1675.5	1675.8	1676.2	1675.8	1675.5	1675.2
147.5°	1740.7	1735.3	1729.9	1727.9	1729.1	1730.3	1731.5	1732.7	1731.5	1730.3	1729.1
150°	1772.2	1767.1	1762.0	1760.5	1762.8	1765.0	1767.3	1769.5	1767.3	1765.0	1762.8
152.5°	1801.4	1796.5	1791.7	1790.6	1793.0	1795.5	1798.1	1800.5	1798.1	1795.5	1793.0
155°	1842.3	1838.5	1834.6	1834.1	1836.9	1839.9	1842.7	1845.6	1842.7	1839.9	1836.9
157.5°	1876.7	1874.0	1871.4	1871.3	1873.7	1876.1	1878.6	1881.0	1878.6	1876.1	1873.7
160°	1897.8	1895.9	1894.0	1894.0	1895.9	1897.8	1899.7	1901.6	1899.7	1897.8	1895.9
162.5°	1915.5	1913.9	1912.2	1912.4	1914.3	1916.2	1918.1	1920.0	1918.1	1916.2	1914.3
165°	1938.4	1937.5	1936.6	1937.0	1938.9	1940.9	1942.8	1944.7	1942.8	1940.9	1938.9
167.5°	1956.7	1955.8	1954.9	1955.4	1957.3	1959.2	1961.2	1963.1	1961.2	1959.2	1957.3
170°	1966.4	1965.8	1965.1	1965.8	1967.7	1969.6	1971.6	1973.5	1971.6	1969.6	1967.7
172.5°	1973.3	1972.7	1972.1	1972.7	1974.6	1976.5	1978.4	1980.3	1978.4	1976.5	1974.6
175°	1980.7	1980.1	1979.5	1980.3	1982.6	1984.8	1987.0	1989.2	1987.0	1984.8	1982.6
177.5°	1983.3	1983.0	1982.8	1983.5	1985.3	1987.1	1988.9	1990.6	1988.9	1987.1	1985.3
180°	1984.9	1984.9	1984.9	1984.9	1984.9	1984.9	1984.9	1984.9	1984.9	1984.9	1984.9



TEST NUMBER: P331549-840

CATALOG NUMBER: S122DIW-S675D1440U840-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4
2.5°	1323.6	1321.2	1312.5	1308.0	1300.5	1293.5	1289.0	1291.1	1292.7	1291.9	1290.6
5°	1285.7	1275.9	1260.9	1248.1	1238.8	1221.7	1214.6	1210.9	1207.9	1204.3	1200.6
7.5°	1240.5	1225.1	1203.7	1185.3	1167.9	1146.8	1134.8	1127.5	1120.1	1112.0	1104.8
10°	1208.4	1186.7	1164.1	1138.2	1117.6	1098.5	1081.6	1070.3	1060.0	1050.2	1042.9
12.5°	1174.6	1149.6	1121.6	1086.3	1063.6	1036.3	1033.7	1013.7	997.6	991.6	983.1
15°	1120.7	1085.7	1050.2	1008.4	990.3	965.5	950.1	934.6	920.7	910.9	908.4
17.5°	1059.6	1014.2	978.9	948.9	919.3	893.9	879.7	867.3	855.9	842.7	841.0
20°	1013.0	973.8	935.1	908.9	878.5	852.6	835.2	822.7	812.9	805.3	798.5
22.5°	968.9	925.9	890.6	861.8	831.8	811.0	797.2	785.3	777.1	768.5	762.2
25°	898.1	864.5	825.9	793.3	768.6	755.3	743.9	733.6	728.4	722.8	715.6
27.5°	836.1	798.8	762.7	737.5	715.8	703.9	695.8	688.8	684.0	680.6	676.6
30°	792.3	754.7	726.4	701.7	683.6	671.8	666.6	662.5	656.8	654.7	652.7
32.5°	750.3	716.4	692.2	670.7	653.5	645.7	641.0	637.3	632.9	630.8	626.6
35°	690.7	662.5	638.7	626.8	613.0	606.2	602.7	597.4	593.4	591.3	590.8
37.5°	634.8	610.2	594.6	579.4	573.5	569.4	564.4	560.9	559.7	559.4	558.9
40°	598.5	578.5	564.5	552.1	549.6	543.3	539.3	536.1	536.1	536.6	536.1
42.5°	565.5	547.4	535.2	524.5	521.5	517.8	513.6	513.4	514.3	516.0	514.3
45°	515.5	502.6	493.8	488.7	483.0	479.4	478.9	480.5	481.0	481.5	483.0
47.5°	469.5	461.0	453.0	447.4	444.8	444.2	443.6	446.4	448.8	449.7	452.1
50°	442.3	432.5	425.9	422.2	420.1	419.1	420.1	423.2	425.3	427.9	429.4
52.5°	411.8	404.9	400.2	397.5	396.7	397.3	397.5	401.0	404.2	405.2	406.0
55°	369.6	364.5	363.5	358.8	360.8	360.3	362.9	365.0	368.1	371.1	371.7
57.5°	327.6	323.5	320.6	321.0	321.6	324.0	326.1	329.7	333.1	336.3	336.6
60°	299.5	297.4	295.9	295.9	296.9	300.0	302.7	306.2	308.3	310.3	311.8
62.5°	274.0	271.9	270.3	271.1	273.9	275.7	278.7	280.6	282.7	284.8	285.5
65°	233.5	232.5	234.1	235.1	235.6	238.1	241.8	243.3	245.4	246.4	250.0
67.5°	196.3	196.5	196.3	197.7	200.8	201.4	204.8	208.3	208.7	210.8	213.1
70°	171.2	172.2	173.2	174.2	176.8	177.8	180.5	182.0	184.0	185.6	187.1
72.5°	148.0	148.2	149.3	149.1	151.3	153.5	155.7	157.2	159.3	161.3	162.8
75°	113.9	113.9	114.9	115.4	118.1	120.7	120.1	121.2	123.2	125.2	126.3
77.5°	83.2	82.1	83.2	83.7	84.5	86.7	87.2	88.6	90.9	90.2	91.4
80°	63.4	61.9	63.4	63.9	63.9	66.6	66.6	67.6	69.1	67.6	69.1
82.5°	45.2	44.5	45.6	45.7	46.6	46.7	47.6	47.8	49.3	48.6	49.3
85°	22.7	22.2	22.7	22.2	22.7	23.2	23.2	22.7	22.7	23.7	22.2
87.5°	10.1	10.3	10.4	10.9	11.0	11.1	11.0	11.3	11.6	11.1	11.4
90°	15.5	18.5	21.1	23.6	26.2	28.7	30.3	31.9	33.5	35.1	36.3
92.5°	27.8	28.2	29.5	30.8	32.0	33.3	34.1	34.9	35.9	36.7	37.3
95°	51.2	47.1	49.3	51.5	53.8	56.0	57.6	59.2	60.8	62.4	63.0
97.5°	66.6	54.3	59.5	64.6	69.8	74.9	76.2	77.6	78.8	80.1	80.9
100°	79.3	60.2	65.5	71.0	76.4	81.9	84.4	86.9	89.6	92.1	93.7
102.5°	293.1	265.7	220.4	174.9	129.6	84.1	87.5	90.8	94.1	97.5	99.6
105°	474.9	436.2	349.0	261.9	174.7	87.7	91.1	94.6	98.2	101.7	104.0
107.5°	589.1	540.7	436.2	331.6	227.1	122.7	119.1	115.5	111.9	108.4	107.2
110°	663.1	620.3	528.1	435.9	343.6	251.4	219.4	187.5	155.6	123.7	108.4



TEST NUMBER: P331549-840

CATALOG NUMBER: S122DIW-S675D1440U840-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	733.6	725.1	702.4	679.5	656.7	634.0	517.6	401.1	284.7	168.2	110.5
115°	847.6	854.2	862.2	870.2	878.2	886.2	738.4	590.7	442.8	295.1	209.6
117.5°	953.8	959.6	965.0	970.6	976.0	981.6	945.8	910.1	874.3	838.6	782.9
120°	1024.5	1029.8	1035.5	1041.3	1047.0	1052.8	1056.6	1060.5	1064.3	1068.1	1048.4
122.5°	1089.9	1095.6	1101.8	1108.0	1114.3	1120.5	1122.9	1125.2	1127.5	1129.7	1126.7
125°	1184.3	1189.4	1195.5	1201.5	1207.6	1213.7	1215.9	1218.1	1220.3	1222.5	1224.2
127.5°	1274.9	1279.4	1283.9	1288.5	1293.0	1297.6	1300.8	1304.0	1307.3	1310.5	1312.3
130°	1333.2	1337.5	1341.0	1344.5	1348.0	1351.5	1355.0	1358.6	1362.1	1365.5	1367.2
132.5°	1387.6	1391.5	1395.0	1398.5	1402.0	1405.5	1408.6	1411.5	1414.5	1417.5	1418.9
135°	1465.3	1469.3	1472.2	1475.0	1477.9	1480.8	1484.0	1487.1	1490.4	1493.6	1494.8
137.5°	1534.7	1538.1	1541.4	1544.7	1547.9	1551.2	1554.3	1557.4	1560.5	1563.7	1564.7
140°	1580.0	1583.1	1586.6	1590.1	1593.7	1597.1	1600.0	1602.9	1605.8	1608.6	1609.2
142.5°	1620.4	1623.6	1627.6	1631.6	1635.6	1639.6	1642.2	1644.9	1647.5	1650.1	1650.6
145°	1674.9	1677.4	1682.8	1688.3	1693.6	1699.1	1701.3	1703.5	1705.8	1708.1	1708.4
147.5°	1727.9	1729.9	1735.3	1740.7	1746.1	1751.4	1753.0	1754.7	1756.4	1758.1	1758.2
150°	1760.5	1762.0	1767.1	1772.2	1777.3	1782.4	1784.3	1786.2	1788.2	1790.1	1790.2
152.5°	1790.6	1791.7	1796.5	1801.4	1806.2	1811.1	1813.0	1814.9	1816.8	1818.8	1818.7
155°	1834.1	1834.6	1838.5	1842.3	1846.1	1849.9	1851.8	1853.7	1855.6	1857.5	1857.2
157.5°	1871.3	1871.4	1874.0	1876.7	1879.4	1882.1	1884.3	1886.4	1888.5	1890.8	1890.6
160°	1894.0	1894.0	1895.9	1897.8	1899.7	1901.6	1903.5	1905.4	1907.3	1909.3	1909.1
162.5°	1912.4	1912.2	1913.9	1915.5	1917.2	1918.8	1921.1	1923.2	1925.4	1927.5	1927.2
165°	1937.0	1936.6	1937.5	1938.4	1939.4	1940.4	1942.7	1944.9	1947.1	1949.3	1949.3
167.5°	1955.4	1954.9	1955.8	1956.7	1957.6	1958.5	1960.8	1963.0	1965.2	1967.4	1967.1
170°	1965.8	1965.1	1965.8	1966.4	1967.0	1967.7	1969.9	1972.2	1974.4	1976.6	1976.3
172.5°	1972.7	1972.1	1972.7	1973.3	1974.0	1974.6	1976.8	1979.0	1981.3	1983.5	1983.2
175°	1980.3	1979.5	1980.1	1980.7	1981.5	1982.1	1984.3	1986.5	1988.7	1990.9	1990.5
177.5°	1983.5	1982.8	1983.0	1983.3	1983.5	1983.8	1985.6	1987.3	1989.1	1990.9	1990.6
180°	1984.9	1984.9	1984.9	1984.9	1984.9	1984.9	1984.9	1984.9	1984.9	1984.9	1984.9



TEST NUMBER: P331549-840

CATALOG NUMBER: S122DIW-S675D1440U840-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4
2.5°	1286.6	1285.7	1285.7	1282.0	1285.7	1285.7	1286.6	1290.6	1291.9	1292.7	1291.1
5°	1193.5	1191.8	1189.3	1191.8	1189.3	1191.8	1193.5	1200.6	1204.3	1207.9	1210.9
7.5°	1101.4	1095.2	1094.3	1088.1	1094.3	1095.2	1101.4	1104.8	1112.0	1120.1	1127.5
10°	1034.1	1030.0	1029.5	1019.7	1029.5	1030.0	1034.1	1042.9	1050.2	1060.0	1070.3
12.5°	983.0	973.1	975.0	969.4	975.0	973.1	983.0	983.1	991.6	997.6	1013.7
15°	894.4	894.4	892.3	883.6	892.3	894.4	894.4	908.4	910.9	920.7	934.6
17.5°	830.8	829.8	824.9	827.3	824.9	829.8	830.8	841.0	842.7	855.9	867.3
20°	792.8	789.8	783.6	783.6	783.6	789.8	792.8	798.5	805.3	812.9	822.7
22.5°	757.0	756.8	750.2	752.2	750.2	756.8	757.0	762.2	768.5	777.1	785.3
25°	715.0	710.9	707.8	709.3	707.8	710.9	715.0	715.6	722.8	728.4	733.6
27.5°	675.2	673.0	672.8	668.5	672.8	673.0	675.2	676.6	680.6	684.0	688.8
30°	652.2	647.0	648.0	645.4	648.0	647.0	652.2	652.7	654.7	656.8	662.5
32.5°	625.7	623.9	622.9	620.7	622.9	623.9	625.7	626.6	630.8	632.9	637.3
35°	589.8	590.3	587.7	588.8	587.7	590.3	589.8	590.8	591.3	593.4	597.4
37.5°	558.4	560.0	558.8	559.1	558.8	560.0	558.4	558.9	559.4	559.7	560.9
40°	537.7	537.7	537.7	539.3	537.7	537.7	537.7	536.1	536.6	536.1	536.1
42.5°	517.9	517.1	516.2	516.1	516.2	517.1	517.9	514.3	516.0	514.3	513.4
45°	484.0	485.6	486.1	483.5	486.1	485.6	484.0	483.0	481.5	481.0	480.5
47.5°	453.4	453.6	453.4	455.8	453.4	453.6	453.4	452.1	449.7	448.8	446.4
50°	432.0	431.0	432.0	431.0	432.0	431.0	432.0	429.4	427.9	425.3	423.2
52.5°	409.3	409.5	408.9	408.7	408.9	409.5	409.3	406.0	405.2	404.2	401.0
55°	373.8	374.8	374.3	374.3	374.3	374.8	373.8	371.7	371.1	368.1	365.0
57.5°	337.0	337.9	338.6	336.3	338.6	337.9	337.0	336.6	336.3	333.1	329.7
60°	311.3	314.0	313.5	312.5	313.5	314.0	311.3	311.8	310.3	308.3	306.2
62.5°	287.9	288.8	288.7	288.5	288.7	288.8	287.9	285.5	284.8	282.7	280.6
65°	251.6	252.6	251.1	252.6	251.1	252.6	251.6	250.0	246.4	245.4	243.3
67.5°	212.5	212.8	214.0	214.7	214.0	212.8	212.5	213.1	210.8	208.7	208.3
70°	188.1	187.6	189.1	190.8	189.1	187.6	188.1	187.1	185.6	184.0	182.0
72.5°	162.6	163.7	163.2	164.3	163.2	163.7	162.6	162.8	161.3	159.3	157.2
75°	125.2	126.8	126.3	127.8	126.3	126.8	125.2	126.3	125.2	123.2	121.2
77.5°	90.5	90.7	90.5	91.4	90.5	90.7	90.5	91.4	90.2	90.9	88.6
80°	69.1	68.1	67.1	69.1	67.1	68.1	69.1	69.1	67.6	69.1	67.6
82.5°	48.1	48.7	47.7	47.7	47.7	48.7	48.1	49.3	48.6	49.3	47.8
85°	22.2	21.6	20.6	20.6	20.6	21.6	22.2	22.2	23.7	22.7	22.7
87.5°	11.5	11.2	11.3	11.0	11.3	11.2	11.5	11.4	11.1	11.6	11.3
90°	36.9	37.5	38.2	38.8	38.2	37.5	36.9	36.3	35.1	33.5	31.9
92.5°	37.7	38.0	38.4	38.8	38.4	38.0	37.7	37.3	36.7	35.9	34.9
95°	62.7	62.4	62.1	61.8	62.1	62.4	62.7	63.0	62.4	60.8	59.2
97.5°	81.3	81.7	82.1	82.4	82.1	81.7	81.3	80.9	80.1	78.8	77.6
100°	94.3	94.9	95.6	96.2	95.6	94.9	94.3	93.7	92.1	89.6	86.9
102.5°	100.5	101.3	102.2	103.1	102.2	101.3	100.5	99.6	97.5	94.1	90.8
105°	105.3	106.6	107.9	109.2	107.9	106.6	105.3	104.0	101.7	98.2	94.6
107.5°	108.5	109.8	111.1	112.3	111.1	109.8	108.5	107.2	108.4	111.9	115.5
110°	109.7	110.9	112.2	113.5	112.2	110.9	109.7	108.4	123.7	155.6	187.5



TEST NUMBER: P331549-840

CATALOG NUMBER: S122DIW-S675D1440U840-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	111.6	112.6	113.6	114.6	113.6	112.6	111.6	110.5	168.2	284.7	401.1
115°	186.7	163.7	140.8	117.8	140.8	163.7	186.7	209.6	295.1	442.8	590.7
117.5°	707.4	631.9	556.3	480.9	556.3	631.9	707.4	782.9	838.6	874.3	910.1
120°	1005.4	962.3	919.2	876.2	919.2	962.3	1005.4	1048.4	1068.1	1064.3	1060.5
122.5°	1118.3	1110.0	1101.7	1093.3	1101.7	1110.0	1118.3	1126.7	1129.7	1127.5	1125.2
125°	1225.2	1226.1	1227.1	1228.0	1227.1	1226.1	1225.2	1224.2	1222.5	1220.3	1218.1
127.5°	1312.4	1312.6	1312.8	1313.0	1312.8	1312.6	1312.4	1312.3	1310.5	1307.3	1304.0
130°	1366.9	1366.5	1366.2	1365.8	1366.2	1366.5	1366.9	1367.2	1365.5	1362.1	1358.6
132.5°	1418.6	1418.3	1418.0	1417.5	1418.0	1418.3	1418.6	1418.9	1417.5	1414.5	1411.5
135°	1494.2	1493.6	1492.9	1492.3	1492.9	1493.6	1494.2	1494.8	1493.6	1490.4	1487.1
137.5°	1563.6	1562.6	1561.5	1560.3	1561.5	1562.6	1563.6	1564.7	1563.7	1560.5	1557.4
140°	1607.7	1606.1	1604.5	1602.9	1604.5	1606.1	1607.7	1609.2	1608.6	1605.8	1602.9
142.5°	1649.0	1647.4	1645.9	1644.3	1645.9	1647.4	1649.0	1650.6	1650.1	1647.5	1644.9
145°	1706.8	1705.2	1703.5	1702.0	1703.5	1705.2	1706.8	1708.4	1708.1	1705.8	1703.5
147.5°	1756.9	1755.5	1754.1	1752.8	1754.1	1755.5	1756.9	1758.2	1758.1	1756.4	1754.7
150°	1788.7	1787.1	1785.4	1783.8	1785.4	1787.1	1788.7	1790.2	1790.1	1788.2	1786.2
152.5°	1816.5	1814.5	1812.4	1810.3	1812.4	1814.5	1816.5	1818.7	1818.8	1816.8	1814.9
155°	1854.7	1852.2	1849.6	1847.0	1849.6	1852.2	1854.7	1857.2	1857.5	1855.6	1853.7
157.5°	1888.1	1885.6	1883.1	1880.7	1883.1	1885.6	1888.1	1890.6	1890.8	1888.5	1886.4
160°	1906.9	1904.6	1902.4	1900.2	1902.4	1904.6	1906.9	1909.1	1909.3	1907.3	1905.4
162.5°	1924.5	1921.8	1919.0	1916.3	1919.0	1921.8	1924.5	1927.2	1927.5	1925.4	1923.2
165°	1947.1	1944.9	1942.7	1940.4	1942.7	1944.9	1947.1	1949.3	1949.3	1947.1	1944.9
167.5°	1964.3	1961.4	1958.5	1955.6	1958.5	1961.4	1964.3	1967.1	1967.4	1965.2	1963.0
170°	1973.5	1970.5	1967.7	1964.8	1967.7	1970.5	1973.5	1976.3	1976.6	1974.4	1972.2
172.5°	1980.3	1977.4	1974.6	1971.7	1974.6	1977.4	1980.3	1983.2	1983.5	1981.3	1979.0
175°	1987.3	1984.1	1981.0	1977.7	1981.0	1984.1	1987.3	1990.5	1990.9	1988.7	1986.5
177.5°	1988.3	1986.1	1983.8	1981.5	1983.8	1986.1	1988.3	1990.6	1990.9	1989.1	1987.3
180°	1984.9	1984.9	1984.9	1984.9	1984.9	1984.9	1984.9	1984.9	1984.9	1984.9	1984.9



TEST NUMBER: P331549-840

CATALOG NUMBER: S122DIW-S675D1440U840-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4
2.5°	1289.0	1293.5	1300.5	1308.0	1312.5	1321.2	1323.6	1327.8	1331.5	1340.2	1349.2
5°	1214.6	1221.7	1238.8	1248.1	1260.9	1275.9	1285.7	1296.1	1307.4	1327.0	1344.9
7.5°	1134.8	1146.8	1167.9	1185.3	1203.7	1225.1	1240.5	1260.9	1277.9	1305.5	1331.9
10°	1081.6	1098.5	1117.6	1138.2	1164.1	1186.7	1208.4	1234.2	1254.8	1287.8	1318.7
12.5°	1033.7	1036.3	1063.6	1086.3	1121.6	1149.6	1174.6	1207.8	1228.0	1267.2	1299.7
15°	950.1	965.5	990.3	1008.4	1050.2	1085.7	1120.7	1155.3	1178.5	1226.9	1269.7
17.5°	879.7	893.9	919.3	948.9	978.9	1014.2	1059.6	1096.0	1127.5	1183.0	1233.6
20°	835.2	852.6	878.5	908.9	935.1	973.8	1013.0	1054.7	1088.7	1151.1	1210.4
22.5°	797.2	811.0	831.8	861.8	890.6	925.9	968.9	1014.3	1050.1	1117.3	1177.4
25°	743.9	755.3	768.6	793.3	825.9	864.5	898.1	948.1	1000.1	1063.0	1135.7
27.5°	695.8	703.9	715.8	737.5	762.7	798.8	836.1	883.5	935.8	1004.1	1080.9
30°	666.6	671.8	683.6	701.7	726.4	754.7	792.3	837.7	891.3	960.4	1036.7
32.5°	641.0	645.7	653.5	670.7	692.2	716.4	750.3	795.7	846.8	914.6	999.2
35°	602.7	606.2	613.0	626.8	638.7	662.5	690.7	732.1	780.0	845.0	932.6
37.5°	564.4	569.4	573.5	579.4	594.6	610.2	634.8	669.6	716.7	782.2	865.8
40°	539.3	543.3	549.6	552.1	564.5	578.5	598.5	630.5	677.9	737.7	819.2
42.5°	513.6	517.8	521.5	524.5	535.2	547.4	565.5	593.0	635.0	693.2	773.8
45°	478.9	479.4	483.0	488.7	493.8	502.6	515.5	539.3	571.7	626.3	699.5
47.5°	443.6	444.2	444.8	447.4	453.0	461.0	469.5	488.8	517.9	561.5	632.8
50°	420.1	419.1	420.1	422.2	425.9	432.5	442.3	456.3	480.0	520.7	586.1
52.5°	397.5	397.3	396.7	397.5	400.2	404.9	411.8	423.6	444.8	482.3	540.0
55°	362.9	360.3	360.8	358.8	363.5	364.5	369.6	379.4	398.0	423.7	477.9
57.5°	326.1	324.0	321.6	321.0	320.6	323.5	327.6	335.3	349.5	372.1	416.1
60°	302.7	300.0	296.9	295.9	295.9	297.4	299.5	305.2	318.6	338.7	374.8
62.5°	278.7	275.7	273.9	271.1	270.3	271.9	274.0	278.0	287.6	306.5	337.7
65°	241.8	238.1	235.6	235.1	234.1	232.5	233.5	237.6	245.4	260.3	285.1
67.5°	204.8	201.4	200.8	197.7	196.3	196.5	196.3	199.9	204.5	217.3	235.8
70°	180.5	177.8	176.8	174.2	173.2	172.2	171.2	174.2	178.8	189.8	205.7
72.5°	155.7	153.5	151.3	149.1	149.3	148.2	148.0	149.9	153.7	163.7	176.0
75°	120.1	120.7	118.1	115.4	114.9	113.9	113.9	115.4	117.0	124.7	134.5
77.5°	87.2	86.7	84.5	83.7	83.2	82.1	83.2	84.2	85.0	90.2	97.5
80°	66.6	66.6	63.9	63.9	63.4	61.9	63.4	62.4	64.4	69.6	74.7
82.5°	47.6	46.7	46.6	45.7	45.6	44.5	45.2	46.3	47.2	50.6	53.7
85°	23.2	23.2	22.7	22.2	22.7	22.2	22.7	23.2	23.7	25.2	27.9
87.5°	11.0	11.1	11.0	10.9	10.4	10.3	10.1	9.8	9.9	9.7	9.4
90°	30.3	28.7	26.2	23.6	21.1	18.5	15.5	12.0	8.5	4.9	1.4
92.5°	34.1	33.3	32.0	30.8	29.5	28.2	27.8	28.1	28.4	28.7	29.0
95°	57.6	56.0	53.8	51.5	49.3	47.1	51.2	61.8	72.3	82.8	93.3
97.5°	76.2	74.9	69.8	64.6	59.5	54.3	66.6	96.2	125.9	155.6	185.3
100°	84.4	81.9	76.4	71.0	65.5	60.2	79.3	123.0	166.7	210.5	254.2
102.5°	87.5	84.1	129.6	174.9	220.4	265.7	293.1	302.3	311.5	320.8	330.0
105°	91.1	87.7	174.7	261.9	349.0	436.2	474.9	465.3	455.8	446.2	436.7
107.5°	119.1	122.7	227.1	331.6	436.2	540.7	589.1	581.3	573.6	565.8	558.2
110°	219.4	251.4	343.6	435.9	528.1	620.3	663.1	656.4	649.6	643.0	636.3



TEST NUMBER: P331549-840

CATALOG NUMBER: S122DIW-S675D1440U840-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	517.6	634.0	656.7	679.5	702.4	725.1	733.6	727.6	721.6	715.7	709.8
115°	738.4	886.2	878.2	870.2	862.2	854.2	847.6	842.1	836.7	831.3	825.9
117.5°	945.8	981.6	976.0	970.6	965.0	959.6	953.8	947.8	941.7	935.6	929.6
120°	1056.6	1052.8	1047.0	1041.3	1035.5	1029.8	1024.5	1019.8	1014.9	1010.2	1005.4
122.5°	1122.9	1120.5	1114.3	1108.0	1101.8	1095.6	1089.9	1084.9	1079.8	1074.8	1069.8
125°	1215.9	1213.7	1207.6	1201.5	1195.5	1189.4	1184.3	1180.1	1176.0	1171.8	1167.7
127.5°	1300.8	1297.6	1293.0	1288.5	1283.9	1279.4	1274.9	1270.2	1265.7	1261.0	1256.5
130°	1355.0	1351.5	1348.0	1344.5	1341.0	1337.5	1333.2	1328.1	1322.9	1317.9	1312.7
132.5°	1408.6	1405.5	1402.0	1398.5	1395.0	1391.5	1387.6	1383.2	1378.9	1374.5	1370.2
135°	1484.0	1480.8	1477.9	1475.0	1472.2	1469.3	1465.3	1460.2	1455.1	1450.0	1444.9
137.5°	1554.3	1551.2	1547.9	1544.7	1541.4	1538.1	1534.7	1531.2	1527.6	1524.0	1520.5
140°	1600.0	1597.1	1593.7	1590.1	1586.6	1583.1	1580.0	1577.5	1575.0	1572.4	1569.8
142.5°	1642.2	1639.6	1635.6	1631.6	1627.6	1623.6	1620.4	1618.1	1615.8	1613.5	1611.2
145°	1701.3	1699.1	1693.6	1688.3	1682.8	1677.4	1674.9	1675.2	1675.5	1675.8	1676.2
147.5°	1753.0	1751.4	1746.1	1740.7	1735.3	1729.9	1727.9	1729.1	1730.3	1731.5	1732.7
150°	1784.3	1782.4	1777.3	1772.2	1767.1	1762.0	1760.5	1762.8	1765.0	1767.3	1769.5
152.5°	1813.0	1811.1	1806.2	1801.4	1796.5	1791.7	1790.6	1793.0	1795.5	1798.1	1800.5
155°	1851.8	1849.9	1846.1	1842.3	1838.5	1834.6	1834.1	1836.9	1839.9	1842.7	1845.6
157.5°	1884.3	1882.1	1879.4	1876.7	1874.0	1871.4	1871.3	1873.7	1876.1	1878.6	1881.0
160°	1903.5	1901.6	1899.7	1897.8	1895.9	1894.0	1894.0	1895.9	1897.8	1899.7	1901.6
162.5°	1921.1	1918.8	1917.2	1915.5	1913.9	1912.2	1912.4	1914.3	1916.2	1918.1	1920.0
165°	1942.7	1940.4	1939.4	1938.4	1937.5	1936.6	1937.0	1938.9	1940.9	1942.8	1944.7
167.5°	1960.8	1958.5	1957.6	1956.7	1955.8	1954.9	1955.4	1957.3	1959.2	1961.2	1963.1
170°	1969.9	1967.7	1967.0	1966.4	1965.8	1965.1	1965.8	1967.7	1969.6	1971.6	1973.5
172.5°	1976.8	1974.6	1974.0	1973.3	1972.7	1972.1	1972.7	1974.6	1976.5	1978.4	1980.3
175°	1984.3	1982.1	1981.5	1980.7	1980.1	1979.5	1980.3	1982.6	1984.8	1987.0	1989.2
177.5°	1985.6	1983.8	1983.5	1983.3	1983.0	1982.8	1983.5	1985.3	1987.1	1988.9	1990.6
180°	1984.9	1984.9	1984.9	1984.9	1984.9	1984.9	1984.9	1984.9	1984.9	1984.9	1984.9



TEST NUMBER: P331549-840

CATALOG NUMBER: S122DIW-S675D1440U840-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4
2.5°	1348.4	1350.5	1357.1	1363.6	1371.1	1373.1	1376.4	1373.5	1372.7	1380.6	1386.3
5°	1352.2	1361.5	1379.6	1396.0	1410.0	1419.8	1430.1	1434.2	1441.9	1452.7	1466.1
7.5°	1347.9	1365.9	1394.3	1418.3	1444.5	1463.4	1478.1	1490.7	1505.9	1526.4	1548.8
10°	1342.9	1367.2	1401.7	1431.1	1463.0	1487.2	1507.4	1526.9	1549.6	1578.0	1607.4
12.5°	1333.8	1362.6	1405.8	1440.6	1481.6	1505.4	1532.6	1574.8	1599.1	1638.6	1680.0
15°	1315.7	1347.6	1407.9	1450.7	1497.0	1542.5	1592.5	1632.6	1672.8	1696.1	1754.3
17.5°	1288.5	1335.4	1402.2	1452.1	1511.1	1582.6	1638.7	1684.3	1730.7	1768.4	1797.6
20°	1266.7	1317.7	1393.9	1453.8	1523.9	1600.6	1665.2	1711.5	1751.7	1783.2	1801.2
22.5°	1239.0	1303.2	1377.5	1447.5	1537.1	1613.1	1680.8	1717.3	1750.9	1766.3	1773.2
25°	1195.5	1272.8	1356.9	1442.4	1543.5	1623.9	1685.8	1707.9	1717.7	1702.7	1678.0
27.5°	1148.6	1234.8	1333.0	1432.7	1539.5	1616.9	1661.2	1657.7	1641.1	1592.8	1554.1
30°	1113.5	1208.4	1314.0	1422.8	1530.0	1605.3	1631.1	1605.3	1567.7	1513.6	1458.4
32.5°	1076.8	1175.0	1293.8	1408.8	1512.8	1578.9	1584.5	1540.1	1481.9	1420.4	1351.6
35°	1021.3	1127.4	1255.8	1377.5	1475.9	1517.7	1493.0	1414.6	1345.5	1261.5	1167.6
37.5°	958.5	1075.7	1204.5	1331.6	1420.8	1431.7	1370.3	1287.8	1190.3	1091.6	981.2
40°	911.4	1035.7	1168.2	1296.6	1375.4	1364.0	1285.7	1195.0	1078.9	958.4	855.8
42.5°	869.4	993.6	1128.5	1254.5	1317.7	1286.6	1195.0	1083.6	959.0	845.4	751.4
45°	796.5	924.3	1062.5	1184.2	1220.2	1164.1	1042.9	919.2	796.5	701.7	627.4
47.5°	725.8	852.1	989.0	1095.9	1108.6	1033.1	900.7	773.4	667.9	590.7	538.3
50°	673.8	800.6	936.1	1031.6	1027.4	936.1	800.1	678.9	590.8	528.4	493.3
52.5°	627.2	747.0	877.2	963.9	942.1	842.5	712.7	605.1	532.6	483.8	452.1
55°	554.7	665.5	789.2	858.9	818.6	708.3	598.5	511.9	458.3	421.7	397.0
57.5°	482.7	586.6	692.6	735.5	691.1	589.2	497.6	434.7	394.5	367.4	351.2
60°	438.2	529.0	623.3	660.4	607.2	516.5	444.3	388.2	355.7	333.6	319.1
62.5°	393.6	474.9	563.9	584.1	535.5	458.8	394.9	348.2	321.4	301.7	288.2
65°	333.1	399.5	467.1	480.5	435.7	376.4	325.8	295.4	271.7	257.2	246.4
67.5°	273.2	326.5	374.4	385.2	345.9	304.8	268.3	241.8	225.7	213.7	204.6
70°	237.6	279.9	319.1	327.9	296.4	259.8	232.0	210.9	196.4	186.1	177.3
72.5°	200.2	235.4	267.9	273.9	248.1	220.3	197.3	180.8	167.9	161.4	153.0
75°	153.1	173.7	198.9	200.6	183.5	166.5	149.0	138.1	131.5	123.2	119.1
77.5°	108.1	124.2	138.7	141.5	131.4	119.8	110.0	101.5	95.7	92.0	88.2
80°	82.5	95.3	101.6	105.1	98.0	89.7	84.0	78.4	74.7	72.2	69.6
82.5°	59.0	67.0	72.7	75.4	71.6	66.7	60.9	57.8	54.9	52.8	51.9
85°	29.9	33.5	37.2	38.2	37.2	35.0	31.9	31.9	30.4	29.9	29.9
87.5°	11.3	13.6	14.3	16.3	16.1	16.6	17.1	17.2	17.3	17.2	17.1
90°	4.9	8.5	12.0	15.5	18.5	21.1	23.6	26.2	28.7	30.3	31.9
92.5°	28.7	28.4	28.1	27.8	28.2	29.5	30.8	32.0	33.3	34.1	34.9
95°	82.8	72.3	61.8	51.2	47.1	49.3	51.5	53.8	56.0	57.6	59.2
97.5°	155.6	125.9	96.2	66.6	54.3	59.5	64.6	69.8	74.9	76.2	77.6
100°	210.5	166.7	123.0	79.3	60.2	65.5	71.0	76.4	81.9	84.4	86.9
102.5°	320.8	311.5	302.3	293.1	265.7	220.4	174.9	129.6	84.1	87.5	90.8
105°	446.2	455.8	465.3	474.9	436.2	349.0	261.9	174.7	87.7	91.1	94.6
107.5°	565.8	573.6	581.3	589.1	540.7	436.2	331.6	227.1	122.7	119.1	115.5
110°	643.0	649.6	656.4	663.1	620.3	528.1	435.9	343.6	251.4	219.4	187.5





TEST NUMBER: P331549-840

CATALOG NUMBER: S122DIW-S675D1440U840-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	715.7	721.6	727.6	733.6	725.1	702.4	679.5	656.7	634.0	517.6	401.1
115°	831.3	836.7	842.1	847.6	854.2	862.2	870.2	878.2	886.2	738.4	590.7
117.5°	935.6	941.7	947.8	953.8	959.6	965.0	970.6	976.0	981.6	945.8	910.1
120°	1010.2	1014.9	1019.8	1024.5	1029.8	1035.5	1041.3	1047.0	1052.8	1056.6	1060.5
122.5°	1074.8	1079.8	1084.9	1089.9	1095.6	1101.8	1108.0	1114.3	1120.5	1122.9	1125.2
125°	1171.8	1176.0	1180.1	1184.3	1189.4	1195.5	1201.5	1207.6	1213.7	1215.9	1218.1
127.5°	1261.0	1265.7	1270.2	1274.9	1279.4	1283.9	1288.5	1293.0	1297.6	1300.8	1304.0
130°	1317.9	1322.9	1328.1	1333.2	1337.5	1341.0	1344.5	1348.0	1351.5	1355.0	1358.6
132.5°	1374.5	1378.9	1383.2	1387.6	1391.5	1395.0	1398.5	1402.0	1405.5	1408.6	1411.5
135°	1450.0	1455.1	1460.2	1465.3	1469.3	1472.2	1475.0	1477.9	1480.8	1484.0	1487.1
137.5°	1524.0	1527.6	1531.2	1534.7	1538.1	1541.4	1544.7	1547.9	1551.2	1554.3	1557.4
140°	1572.4	1575.0	1577.5	1580.0	1583.1	1586.6	1590.1	1593.7	1597.1	1600.0	1602.9
142.5°	1613.5	1615.8	1618.1	1620.4	1623.6	1627.6	1631.6	1635.6	1639.6	1642.2	1644.9
145°	1675.8	1675.5	1675.2	1674.9	1677.4	1682.8	1688.3	1693.6	1699.1	1701.3	1703.5
147.5°	1731.5	1730.3	1729.1	1727.9	1729.9	1735.3	1740.7	1746.1	1751.4	1753.0	1754.7
150°	1767.3	1765.0	1762.8	1760.5	1762.0	1767.1	1772.2	1777.3	1782.4	1784.3	1786.2
152.5°	1798.1	1795.5	1793.0	1790.6	1791.7	1796.5	1801.4	1806.2	1811.1	1813.0	1814.9
155°	1842.7	1839.9	1836.9	1834.1	1834.6	1838.5	1842.3	1846.1	1849.9	1851.8	1853.7
157.5°	1878.6	1876.1	1873.7	1871.3	1871.4	1874.0	1876.7	1879.4	1882.1	1884.3	1886.4
160°	1899.7	1897.8	1895.9	1894.0	1894.0	1895.9	1897.8	1899.7	1901.6	1903.5	1905.4
162.5°	1918.1	1916.2	1914.3	1912.4	1912.2	1913.9	1915.5	1917.2	1918.8	1921.1	1923.2
165°	1942.8	1940.9	1938.9	1937.0	1936.6	1937.5	1938.4	1939.4	1940.4	1942.7	1944.9
167.5°	1961.2	1959.2	1957.3	1955.4	1954.9	1955.8	1956.7	1957.6	1958.5	1960.8	1963.0
170°	1971.6	1969.6	1967.7	1965.8	1965.1	1965.8	1966.4	1967.0	1967.7	1969.9	1972.2
172.5°	1978.4	1976.5	1974.6	1972.7	1972.1	1972.7	1973.3	1974.0	1974.6	1976.8	1979.0
175°	1987.0	1984.8	1982.6	1980.3	1979.5	1980.1	1980.7	1981.5	1982.1	1984.3	1986.5
177.5°	1988.9	1987.1	1985.3	1983.5	1982.8	1983.0	1983.3	1983.5	1983.8	1985.6	1987.3
180°	1984.9	1984.9	1984.9	1984.9	1984.9	1984.9	1984.9	1984.9	1984.9	1984.9	1984.9



TEST NUMBER: P331549-840

CATALOG NUMBER: S122DIW-S675D1440U840-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4
2.5°	1391.3	1397.0	1397.0	1397.9	1404.5	1403.6	1403.2
5°	1480.6	1489.3	1490.4	1499.6	1505.8	1503.8	1498.1
7.5°	1564.8	1581.1	1593.5	1600.3	1608.5	1613.6	1611.3
10°	1631.6	1655.4	1669.8	1679.6	1691.4	1700.2	1697.1
12.5°	1692.2	1720.5	1740.3	1757.1	1758.7	1769.9	1762.2
15°	1786.8	1816.6	1819.8	1832.2	1842.0	1840.9	1841.4
17.5°	1818.1	1827.7	1829.6	1829.9	1830.0	1826.3	1818.6
20°	1806.9	1803.3	1794.5	1787.9	1775.9	1774.4	1764.1
22.5°	1754.1	1742.6	1720.7	1706.2	1687.7	1682.8	1680.0
25°	1650.2	1624.9	1589.8	1556.3	1547.1	1529.0	1534.2
27.5°	1507.6	1468.2	1430.3	1403.0	1378.4	1351.4	1359.1
30°	1407.3	1363.0	1309.4	1268.2	1241.9	1216.1	1211.4
32.5°	1287.8	1222.8	1163.0	1126.7	1086.4	1070.2	1052.3
35°	1081.6	1018.1	958.9	907.9	878.5	855.8	835.2
37.5°	896.1	823.0	775.3	733.9	712.7	699.6	703.0
40°	781.0	717.1	682.1	650.6	631.0	621.7	623.8
42.5°	687.8	640.0	611.1	589.6	575.7	570.6	569.4
45°	582.0	555.2	531.5	519.2	512.4	506.8	503.1
47.5°	509.9	488.0	474.6	467.3	461.4	455.7	455.6
50°	466.6	452.1	442.8	435.0	430.5	426.4	429.9
52.5°	433.5	420.3	411.1	404.1	402.4	398.7	398.6
55°	384.6	374.3	367.6	361.3	358.3	356.2	353.7
57.5°	340.0	330.2	324.1	320.1	314.3	312.1	311.3
60°	308.3	300.5	294.4	289.2	286.6	282.5	282.5
62.5°	279.0	271.2	265.5	261.6	257.3	255.7	256.1
65°	236.6	230.5	224.8	220.7	219.6	216.5	217.5
67.5°	197.6	193.5	187.5	185.3	183.3	181.7	180.5
70°	171.7	167.5	164.4	161.4	159.8	159.8	159.8
72.5°	149.8	144.8	143.0	139.1	140.0	138.4	136.7
75°	116.0	112.9	111.4	109.8	107.2	107.2	107.2
77.5°	85.3	84.4	82.6	80.9	80.3	79.8	80.0
80°	65.9	65.4	64.4	64.4	63.4	62.9	61.9
82.5°	50.7	49.4	48.8	48.4	48.2	48.1	47.9
85°	28.9	27.9	27.9	28.4	27.4	27.4	27.9
87.5°	17.9	18.2	18.0	18.1	18.7	18.4	18.5
90°	33.5	35.1	36.3	36.9	37.5	38.2	38.8
92.5°	35.9	36.7	37.3	37.7	38.0	38.4	38.8
95°	60.8	62.4	63.0	62.7	62.4	62.1	61.8
97.5°	78.8	80.1	80.9	81.3	81.7	82.1	82.4
100°	89.6	92.1	93.7	94.3	94.9	95.6	96.2
102.5°	94.1	97.5	99.6	100.5	101.3	102.2	103.1
105°	98.2	101.7	104.0	105.3	106.6	107.9	109.2
107.5°	111.9	108.4	107.2	108.5	109.8	111.1	112.3
110°	155.6	123.7	108.4	109.7	110.9	112.2	113.5



TEST NUMBER: P331549-840

CATALOG NUMBER: S122DIW-S675D1440U840-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	284.7	168.2	110.5	111.6	112.6	113.6	114.6
115°	442.8	295.1	209.6	186.7	163.7	140.8	117.8
117.5°	874.3	838.6	782.9	707.4	631.9	556.3	480.9
120°	1064.3	1068.1	1048.4	1005.4	962.3	919.2	876.2
122.5°	1127.5	1129.7	1126.7	1118.3	1110.0	1101.7	1093.3
125°	1220.3	1222.5	1224.2	1225.2	1226.1	1227.1	1228.0
127.5°	1307.3	1310.5	1312.3	1312.4	1312.6	1312.8	1313.0
130°	1362.1	1365.5	1367.2	1366.9	1366.5	1366.2	1365.8
132.5°	1414.5	1417.5	1418.9	1418.6	1418.3	1418.0	1417.5
135°	1490.4	1493.6	1494.8	1494.2	1493.6	1492.9	1492.3
137.5°	1560.5	1563.7	1564.7	1563.6	1562.6	1561.5	1560.3
140°	1605.8	1608.6	1609.2	1607.7	1606.1	1604.5	1602.9
142.5°	1647.5	1650.1	1650.6	1649.0	1647.4	1645.9	1644.3
145°	1705.8	1708.1	1708.4	1706.8	1705.2	1703.5	1702.0
147.5°	1756.4	1758.1	1758.2	1756.9	1755.5	1754.1	1752.8
150°	1788.2	1790.1	1790.2	1788.7	1787.1	1785.4	1783.8
152.5°	1816.8	1818.8	1818.7	1816.5	1814.5	1812.4	1810.3
155°	1855.6	1857.5	1857.2	1854.7	1852.2	1849.6	1847.0
157.5°	1888.5	1890.8	1890.6	1888.1	1885.6	1883.1	1880.7
160°	1907.3	1909.3	1909.1	1906.9	1904.6	1902.4	1900.2
162.5°	1925.4	1927.5	1927.2	1924.5	1921.8	1919.0	1916.3
165°	1947.1	1949.3	1949.3	1947.1	1944.9	1942.7	1940.4
167.5°	1965.2	1967.4	1967.1	1964.3	1961.4	1958.5	1955.6
170°	1974.4	1976.6	1976.3	1973.5	1970.5	1967.7	1964.8
172.5°	1981.3	1983.5	1983.2	1980.3	1977.4	1974.6	1971.7
175°	1988.7	1990.9	1990.5	1987.3	1984.1	1981.0	1977.7
177.5°	1989.1	1990.9	1990.6	1988.3	1986.1	1983.8	1981.5
180°	1984.9	1984.9	1984.9	1984.9	1984.9	1984.9	1984.9

(END OF REPORT)