

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332466-927

Luminaire Tested: **S123RDIW-S1000D1535U927-4F0-1E-UDD-A**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332466-927
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-5,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123RDIW-S1000D1535U927-4F0-1E-UDD-A
Description: DEFINE 3 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 1000 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 1535 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 8001.2 lumens
Efficiency: N/A
Efficacy: 104.5 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.22 / 1.36
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 76.6
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332466-927

CATALOG NUMBER: S123RDIW-S1000D1535U927-4F0-1E-UDD-A

Luminous Intensity Polar Plot





TEST NUMBER: P332466-927

CATALOG NUMBER: S123RDIW-S1000D1535U927-4F0-1E-UDD-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	105	105	105	105	95	95	95	95	77	77	77	61	61	61	46	46	46	39
1	96	92	88	85	87	84	81	78	68	66	64	54	53	52	42	41	40	34
2	88	81	75	70	80	74	69	65	60	57	54	48	46	44	37	36	34	29
3	80	71	64	59	73	65	59	54	54	49	46	43	40	38	33	31	30	25
4	74	63	56	50	67	58	51	46	48	43	39	39	35	33	30	28	26	22
5	68	57	49	43	61	52	45	40	43	38	34	35	31	28	27	25	23	19
6	62	51	43	37	57	47	40	35	39	34	30	32	28	25	25	22	20	17
7	58	46	38	33	52	42	36	31	35	30	26	29	25	22	23	20	18	15
8	54	42	34	29	49	38	32	27	32	27	24	26	23	20	21	18	16	14
9	50	38	31	26	45	35	29	24	30	25	21	24	21	18	19	17	15	13
10	47	35	28	23	42	32	26	22	27	22	19	22	19	16	18	15	14	12

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	13555	13555	13555	13555
5°	16159	13613	11988	13613
10°	20176	13535	10831	13535
15°	23682	13397	9877	13397
20°	26431	13190	9065	13190
25°	26008	12973	8568	12973
30°	18695	12771	8054	12771
35°	12482	12510	7721	12510
40°	9197	12197	7378	12197
45°	7715	11645	7042	11645
50°	6807	10923	6571	10923
55°	5970	10098	5928	10098
60°	5315	9309	5431	9309
65°	4669	8458	5053	8458
70°	3666	7704	4614	7704
75°	3227	6729	4213	6729
80°	2808	5715	4147	5715
85°	2260	4594	4397	4594



TEST NUMBER: P332466-927

CATALOG NUMBER: S123RDIW-S1000D1535U927-4F0-1E-UDD-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	123.8	1.5
10°-20°	386.9	4.8
20°-30°	607.8	7.6
30°-40°	634.2	7.9
40°-50°	542.7	6.8
50°-60°	413.6	5.2
60°-70°	265.1	3.3
70°-80°	127.5	1.6
80°-90°	38.2	0.5
90°-100°	58.0	0.7
100°-110°	276.2	3.5
110°-120°	663.5	8.3
120°-130°	844.9	10.6
130°-140°	902.7	11.3
140°-150°	844.1	10.6
150°-160°	680.9	8.5
160°-170°	439.5	5.5
170°-180°	151.5	1.9
0°-30°	1118.6	14.0
0°-40°	1752.8	21.9
0°-60°	2709.1	33.9
0°-90°	3140.0	39.2
90°-120°	997.6	12.5
90°-150°	3589.3	44.9
90°-180°	4861.0	60.8
0°-180°	8001.2	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1259	1259	1259	1259	1259	
5°	1496	1260	1110	1260	1496	154
15°	2125	1202	886	1202	2125	603
25°	2190	1092	721	1092	2190	941
35°	950	952	588	952	950	623
45°	507	765	463	765	507	398
55°	318	538	316	538	318	288
65°	183	332	198	332	183	180
75°	78	162	101	162	78	83
85°	18	37	36	37	18	22
90°	36	1	36	1	36	17
95°	45	72	45	72	45	38
105°	52	353	52	353	52	119
115°	696	662	696	662	696	643
125°	952	933	952	933	952	850
135°	1174	1162	1174	1162	1174	905
145°	1354	1341	1354	1341	1354	845
155°	1474	1477	1474	1477	1474	680
165°	1554	1557	1554	1557	1554	439
175°	1588	1594	1588	1594	1588	151
180°	1594	1594	1594	1594	1594	



TEST NUMBER: P332466-927

CATALOG NUMBER: S123RDIW-S1000D1535U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1259.3	1259.3	1259.3	1259.3	1259.3	1259.3	1259.3	1259.3	1259.3	1259.3	1259.3
2.5°	1341.3	1343.0	1337.4	1336.6	1330.1	1328.3	1328.3	1319.3	1313.7	1306.4	1302.0
5°	1495.5	1504.1	1499.8	1490.1	1473.9	1470.1	1459.9	1443.8	1425.4	1402.7	1391.9
7.5°	1688.1	1699.8	1695.3	1680.3	1663.3	1649.6	1620.8	1593.9	1556.3	1523.3	1495.1
10°	1845.9	1833.5	1823.8	1809.3	1793.6	1768.2	1738.0	1696.5	1648.6	1610.8	1568.8
12.5°	1964.1	1962.0	1949.7	1934.7	1912.6	1888.6	1851.5	1800.9	1745.2	1690.7	1642.5
15°	2125.2	2128.4	2120.3	2104.7	2073.4	2030.8	1974.8	1953.8	1873.9	1814.7	1755.3
17.5°	2236.6	2236.0	2234.9	2213.3	2181.4	2151.0	2099.0	2043.8	1971.5	1887.9	1808.1
20°	2307.4	2302.0	2303.0	2278.8	2255.1	2220.0	2169.4	2089.1	2029.7	1933.2	1850.8
22.5°	2305.6	2304.5	2308.7	2300.3	2283.1	2256.3	2216.4	2148.6	2072.8	1975.5	1882.7
25°	2189.8	2185.6	2210.9	2217.9	2245.4	2250.2	2238.4	2201.2	2129.5	2029.2	1914.4
27.5°	1832.7	1830.3	1877.4	1936.3	2010.9	2068.9	2124.9	2152.0	2129.5	2057.7	1942.6
30°	1504.1	1554.8	1578.5	1663.7	1758.6	1871.8	1970.9	2065.3	2088.5	2057.2	1962.9
32.5°	1248.8	1293.0	1312.8	1385.9	1474.3	1606.9	1755.8	1889.4	1983.7	2007.6	1950.8
35°	949.9	950.5	995.7	1028.1	1110.0	1246.4	1390.9	1569.9	1747.8	1882.5	1896.6
37.5°	758.0	760.7	788.1	820.3	881.8	953.9	1081.1	1229.9	1435.4	1642.4	1763.6
40°	654.5	659.3	679.9	711.6	755.8	810.2	909.5	1049.6	1221.1	1451.3	1639.4
42.5°	588.0	596.0	606.5	631.0	658.4	709.3	789.6	897.9	1053.8	1271.5	1488.5
45°	506.8	511.0	519.2	530.4	555.2	590.9	644.8	717.6	846.9	1022.2	1239.4
47.5°	447.0	444.7	453.3	462.5	479.0	503.2	539.3	598.7	691.0	831.6	1015.9
50°	406.5	405.9	411.9	418.9	434.5	452.3	482.0	526.7	600.0	716.4	885.2
52.5°	368.5	370.6	374.8	383.5	394.8	409.2	435.8	468.0	531.0	631.5	772.2
55°	318.1	319.7	325.6	330.5	338.6	353.1	369.8	396.8	439.9	510.0	625.9
57.5°	275.4	274.6	280.4	281.5	290.7	302.5	315.4	336.4	367.7	419.8	497.8
60°	246.9	245.3	250.2	253.9	258.8	268.5	279.2	299.8	324.6	362.8	429.7
62.5°	221.0	220.3	223.9	227.6	231.6	240.4	249.5	265.2	284.9	317.1	370.2
65°	183.3	184.9	186.6	188.1	190.3	195.7	204.3	215.1	228.5	251.2	289.5
67.5°	144.0	145.7	146.2	149.6	154.2	157.6	162.8	172.4	181.8	200.9	222.7
70°	116.5	115.9	116.5	118.0	124.0	129.9	137.0	143.9	149.9	163.3	181.6
72.5°	100.1	99.1	100.5	100.8	103.7	105.4	109.8	116.4	124.0	133.2	146.3
75°	77.6	77.6	77.6	77.6	79.8	80.9	82.5	84.1	86.8	91.1	100.8
77.5°	57.4	57.4	58.2	58.8	59.2	59.8	60.8	62.4	63.4	65.7	69.9
80°	45.3	45.8	45.3	45.8	45.8	46.9	47.5	49.0	49.6	52.3	53.9
82.5°	34.1	33.7	34.1	34.6	34.6	35.7	35.8	37.0	37.1	38.5	40.1
85°	18.3	17.3	18.3	17.8	18.9	17.8	18.3	19.4	19.4	20.0	22.1
87.5°	11.4	12.2	11.2	11.6	11.4	11.7	11.5	11.2	12.0	11.3	11.0
90°	35.5	35.0	34.5	34.0	33.4	32.6	31.6	30.5	29.5	28.4	25.0
92.5°	39.3	39.0	38.7	38.3	38.0	37.1	35.4	33.7	32.0	30.3	27.7
95°	45.0	45.0	45.0	45.0	45.0	44.0	42.2	40.4	38.6	36.7	33.8
97.5°	48.8	48.6	48.2	48.0	47.8	46.6	44.4	42.4	40.2	38.1	35.1
100°	49.7	49.5	49.2	49.0	48.7	47.5	45.4	43.3	41.2	39.1	37.2
102.5°	50.7	50.2	49.7	49.3	48.8	51.8	58.4	64.9	71.4	78.0	122.8
105°	52.1	51.6	51.1	50.5	50.0	73.0	119.6	166.2	212.8	259.4	283.0
107.5°	163.7	198.8	233.9	269.0	304.1	338.7	372.9	407.0	441.2	475.4	471.7
110°	325.7	363.3	400.9	438.6	476.2	499.4	508.0	516.7	525.5	534.1	531.2



TEST NUMBER: P332466-927

CATALOG NUMBER: S123RDIW-S1000D1535U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	558.7	566.7	574.6	582.6	590.6	594.5	594.3	594.1	594.0	593.8	590.9
115°	696.4	695.3	694.3	693.2	692.1	690.3	687.7	685.1	682.4	679.8	677.4
117.5°	773.6	773.4	773.2	772.9	772.8	771.6	769.4	767.4	765.2	763.2	761.9
120°	826.6	826.6	826.6	826.6	826.6	825.6	823.5	821.4	819.3	817.1	816.3
122.5°	878.8	878.5	878.3	878.1	877.9	877.1	875.6	874.1	872.7	871.2	870.1
125°	952.2	951.6	951.1	950.6	950.1	949.5	949.0	948.5	948.0	947.5	946.4
127.5°	1022.8	1023.3	1023.8	1024.4	1024.8	1024.7	1023.9	1023.0	1022.2	1021.4	1020.1
130°	1068.3	1068.7	1069.3	1069.8	1070.3	1070.1	1069.1	1067.9	1066.9	1065.9	1064.9
132.5°	1109.9	1110.6	1111.4	1112.1	1112.9	1112.7	1111.7	1110.6	1109.5	1108.5	1107.6
135°	1173.6	1174.4	1175.2	1176.0	1176.8	1176.8	1176.0	1175.2	1174.4	1173.6	1172.6
137.5°	1233.6	1234.1	1234.6	1235.2	1235.6	1235.3	1234.1	1232.8	1231.5	1230.3	1229.7
140°	1269.6	1270.1	1270.7	1271.1	1271.7	1271.4	1270.3	1269.3	1268.3	1267.2	1266.4
142.5°	1302.7	1303.5	1304.2	1305.0	1305.7	1305.6	1304.8	1303.9	1303.1	1302.3	1301.5
145°	1353.7	1353.7	1353.7	1353.7	1353.7	1353.4	1352.9	1352.3	1351.8	1351.3	1350.8
147.5°	1391.5	1392.7	1394.0	1395.2	1396.4	1396.8	1396.2	1395.7	1395.2	1394.6	1394.1
150°	1420.0	1420.8	1421.6	1422.4	1423.2	1423.2	1422.8	1422.2	1421.7	1421.2	1420.6
152.5°	1442.7	1443.9	1445.1	1446.4	1447.6	1447.7	1446.8	1445.8	1444.9	1443.9	1443.6
155°	1474.5	1476.0	1477.6	1479.2	1480.7	1480.9	1479.6	1478.3	1476.9	1475.6	1475.4
157.5°	1501.2	1503.2	1505.3	1507.4	1509.4	1509.7	1508.1	1506.5	1504.9	1503.3	1503.6
160°	1518.3	1520.1	1521.9	1523.8	1525.7	1525.7	1524.2	1522.7	1521.1	1519.5	1519.7
162.5°	1534.4	1536.0	1537.6	1539.3	1540.9	1540.8	1539.1	1537.2	1535.5	1533.7	1533.9
165°	1553.8	1555.6	1557.5	1559.3	1561.2	1561.1	1558.9	1556.8	1554.7	1552.6	1552.9
167.5°	1567.8	1569.9	1572.0	1574.1	1576.2	1576.2	1574.1	1572.0	1569.9	1567.8	1567.8
170°	1576.3	1578.4	1580.5	1582.6	1584.8	1584.8	1582.6	1580.5	1578.4	1576.3	1576.3
172.5°	1581.0	1583.3	1585.7	1588.0	1590.3	1590.4	1588.3	1586.2	1584.1	1582.0	1581.8
175°	1588.2	1590.2	1592.4	1594.4	1596.6	1596.7	1594.8	1593.0	1591.2	1589.4	1589.0
177.5°	1590.3	1592.4	1594.5	1596.6	1598.7	1598.9	1597.2	1595.5	1593.9	1592.2	1592.0
180°	1594.0	1594.0	1594.0	1594.0	1594.0	1594.0	1594.0	1594.0	1594.0	1594.0	1594.0



TEST NUMBER: P332466-927

CATALOG NUMBER: S123RDIW-S1000D1535U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1259.3	1259.3	1259.3	1259.3	1259.3	1259.3	1259.3	1259.3	1259.3	1259.3	1259.3
2.5°	1300.3	1299.0	1293.0	1286.1	1277.0	1271.0	1266.2	1263.7	1255.9	1246.4	1239.9
5°	1380.6	1364.5	1347.3	1326.2	1306.8	1286.8	1274.5	1259.9	1242.1	1222.2	1208.2
7.5°	1466.7	1435.0	1400.8	1365.6	1330.7	1299.5	1271.8	1248.2	1219.9	1191.3	1171.2
10°	1532.7	1486.3	1438.4	1389.3	1344.5	1302.5	1270.1	1238.3	1204.4	1171.5	1146.7
12.5°	1592.6	1531.6	1476.3	1416.0	1358.8	1308.5	1261.9	1224.6	1183.7	1148.6	1120.4
15°	1668.5	1606.0	1539.1	1447.5	1371.5	1307.9	1251.3	1202.2	1152.6	1109.5	1082.0
17.5°	1739.5	1645.4	1555.5	1479.1	1380.3	1300.8	1231.8	1173.1	1118.6	1072.9	1039.1
20°	1768.8	1677.7	1580.1	1482.6	1385.5	1296.6	1216.2	1151.5	1095.0	1043.1	1011.9
22.5°	1786.5	1683.3	1580.6	1475.7	1372.5	1280.2	1200.7	1129.6	1068.2	1019.0	980.4
25°	1807.0	1684.2	1571.0	1467.4	1362.3	1262.0	1167.7	1092.3	1026.0	973.6	932.6
27.5°	1820.7	1676.1	1542.3	1427.2	1320.6	1220.8	1134.2	1054.2	987.0	931.7	887.7
30°	1823.3	1669.6	1520.3	1395.7	1287.4	1195.7	1104.1	1027.5	956.4	897.6	856.7
32.5°	1826.7	1653.7	1490.5	1358.2	1247.3	1156.5	1073.5	1000.4	927.5	869.6	827.8
35°	1812.5	1644.8	1445.3	1293.3	1182.3	1094.4	1019.5	952.0	880.4	824.3	781.7
37.5°	1751.2	1609.8	1398.5	1220.2	1104.1	1022.7	961.6	902.9	837.1	776.7	736.5
40°	1689.6	1575.3	1362.3	1175.8	1054.5	970.9	915.9	868.0	804.4	747.7	704.6
42.5°	1597.7	1528.3	1327.9	1129.2	998.4	917.9	871.5	826.6	770.7	713.2	672.7
45°	1429.2	1438.4	1257.2	1055.0	920.8	840.0	796.2	765.0	715.4	668.0	626.5
47.5°	1217.8	1303.5	1174.3	976.0	838.9	763.0	724.8	697.6	664.2	617.6	579.7
50°	1079.8	1202.2	1107.9	923.0	787.7	712.2	674.4	652.3	623.2	586.5	550.4
52.5°	952.6	1084.0	1027.6	863.9	732.0	663.0	626.1	607.9	584.8	550.3	517.6
55°	776.8	910.0	897.1	774.7	648.6	586.5	558.5	538.1	522.4	496.5	470.6
57.5°	628.4	754.6	761.3	675.5	575.0	513.7	489.6	474.2	464.0	444.4	420.5
60°	534.8	650.7	673.4	608.6	522.4	468.5	444.7	432.4	424.3	408.6	390.3
62.5°	457.2	555.8	581.5	534.9	471.9	421.4	402.9	390.9	385.5	372.0	355.8
65°	349.9	431.8	456.6	430.7	397.8	357.4	342.3	332.1	327.3	319.7	307.8
67.5°	263.1	322.8	350.0	331.8	319.9	294.4	284.8	279.2	275.0	269.7	259.8
70°	211.4	255.6	283.6	278.7	269.0	255.6	248.5	244.8	240.4	236.1	227.5
72.5°	169.9	200.3	226.6	229.1	221.2	218.5	212.3	210.7	208.1	203.0	198.2
75°	112.6	133.7	152.0	159.1	162.2	164.9	162.2	161.8	161.2	156.9	154.2
77.5°	73.8	85.2	96.7	108.7	113.8	117.4	118.3	120.3	118.8	116.5	115.3
80°	56.6	59.3	67.4	77.6	85.7	89.0	91.1	92.2	91.7	91.1	89.0
82.5°	41.1	43.3	47.1	54.3	61.2	66.5	67.8	67.6	68.8	69.1	67.4
85°	22.1	22.7	23.7	24.8	28.6	34.5	36.1	37.2	38.3	38.3	35.0
87.5°	11.2	10.1	10.3	9.7	10.5	10.4	12.4	14.0	15.0	13.8	14.3
90°	21.5	18.1	14.7	11.7	9.1	6.4	3.8	1.2	3.8	6.4	9.1
92.5°	25.2	22.6	20.0	19.1	19.8	20.5	21.3	22.0	21.3	20.5	19.8
95°	30.9	28.0	25.1	29.1	39.8	50.7	61.5	72.2	61.5	50.7	39.8
97.5°	76.0	95.0	113.9	125.8	130.6	135.5	140.4	145.2	140.4	135.5	130.6
100°	121.2	162.2	203.3	221.2	215.9	210.6	205.4	200.2	205.4	210.6	215.9
102.5°	167.6	212.5	257.3	277.8	274.0	270.3	266.5	262.7	266.5	270.3	274.0
105°	306.7	330.4	354.1	364.5	361.6	358.7	355.8	352.9	355.8	358.7	361.6
107.5°	467.9	464.1	460.4	457.4	455.1	452.7	450.4	448.1	450.4	452.7	455.1
110°	528.3	525.5	522.5	520.1	517.9	515.8	513.7	511.6	513.7	515.8	517.9



TEST NUMBER: P332466-927

CATALOG NUMBER: S123RDIW-S1000D1535U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	588.0	585.1	582.3	579.8	578.0	576.1	574.2	572.3	574.2	576.1	578.0
115°	675.0	672.7	670.3	668.4	666.8	665.2	663.6	662.0	663.6	665.2	666.8
117.5°	760.7	759.5	758.4	756.8	754.8	752.8	750.9	748.9	750.9	752.8	754.8
120°	815.6	814.8	814.0	812.5	810.1	807.7	805.3	803.0	805.3	807.7	810.1
122.5°	869.2	868.2	867.2	865.7	863.7	861.8	859.8	857.9	859.8	861.8	863.7
125°	945.3	944.3	943.3	941.7	939.5	937.5	935.3	933.2	935.3	937.5	939.5
127.5°	1018.8	1017.6	1016.3	1014.6	1012.5	1010.4	1008.3	1006.2	1008.3	1010.4	1012.5
130°	1063.7	1062.7	1061.7	1060.1	1058.0	1055.9	1053.8	1051.6	1053.8	1055.9	1058.0
132.5°	1106.8	1106.0	1105.2	1103.7	1101.5	1099.5	1097.3	1095.3	1097.3	1099.5	1101.5
135°	1171.6	1170.4	1169.4	1168.2	1166.6	1165.0	1163.4	1161.8	1163.4	1165.0	1166.6
137.5°	1229.1	1228.5	1228.0	1226.6	1224.6	1222.7	1220.7	1218.6	1220.7	1222.7	1224.6
140°	1265.6	1264.8	1264.0	1262.9	1261.3	1259.7	1258.1	1256.6	1258.1	1259.7	1261.3
142.5°	1300.7	1299.9	1299.1	1297.9	1296.3	1294.7	1293.2	1291.6	1293.2	1294.7	1296.3
145°	1350.2	1349.7	1349.2	1348.0	1346.2	1344.3	1342.4	1340.6	1342.4	1344.3	1346.2
147.5°	1393.6	1393.1	1392.5	1391.6	1390.4	1389.3	1388.1	1386.8	1388.1	1389.3	1390.4
150°	1420.1	1419.6	1419.0	1418.4	1417.6	1416.8	1416.0	1415.2	1416.0	1416.8	1417.6
152.5°	1443.3	1443.0	1442.6	1442.3	1441.9	1441.5	1441.2	1440.8	1441.2	1441.5	1441.9
155°	1475.1	1474.9	1474.6	1474.7	1475.3	1475.8	1476.3	1476.8	1476.3	1475.8	1475.3
157.5°	1503.9	1504.1	1504.4	1504.6	1504.6	1504.7	1504.8	1504.8	1504.8	1504.7	1504.6
160°	1520.0	1520.3	1520.5	1520.8	1521.1	1521.3	1521.5	1521.9	1521.5	1521.3	1521.1
162.5°	1534.2	1534.5	1534.7	1535.2	1535.9	1536.6	1537.2	1537.9	1537.2	1536.6	1535.9
165°	1553.2	1553.4	1553.7	1554.2	1555.0	1555.8	1556.6	1557.4	1556.6	1555.8	1555.0
167.5°	1567.8	1567.8	1567.8	1568.3	1569.4	1570.4	1571.5	1572.5	1571.5	1570.4	1569.4
170°	1576.3	1576.3	1576.3	1576.8	1577.9	1578.9	1580.0	1581.0	1580.0	1578.9	1577.9
172.5°	1581.6	1581.4	1581.1	1581.7	1582.9	1584.2	1585.5	1586.7	1585.5	1584.2	1582.9
175°	1588.8	1588.6	1588.2	1588.8	1590.1	1591.4	1592.8	1594.0	1592.8	1591.4	1590.1
177.5°	1591.7	1591.6	1591.3	1591.7	1592.8	1593.9	1594.9	1595.9	1594.9	1593.9	1592.8
180°	1594.0	1594.0	1594.0	1594.0	1594.0	1594.0	1594.0	1594.0	1594.0	1594.0	1594.0



TEST NUMBER: P332466-927

CATALOG NUMBER: S123RDIW-S1000D1535U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1259.3	1259.3	1259.3	1259.3	1259.3	1259.3	1259.3	1259.3	1259.3	1259.3	1259.3
2.5°	1237.8	1232.2	1228.3	1219.6	1214.1	1208.0	1202.0	1205.9	1205.5	1205.0	1205.0
5°	1196.3	1183.8	1172.6	1158.0	1148.8	1137.5	1128.9	1127.8	1130.0	1122.4	1118.1
7.5°	1155.1	1138.1	1122.1	1106.0	1089.0	1075.4	1066.9	1062.9	1057.4	1052.7	1047.9
10°	1126.2	1106.3	1090.6	1070.6	1052.3	1036.2	1026.0	1018.9	1015.1	1011.4	1004.3
12.5°	1096.5	1076.9	1057.0	1034.4	1017.0	998.2	990.5	982.7	975.5	971.2	961.6
15°	1052.9	1027.5	1006.5	982.8	963.4	945.1	934.3	918.6	916.5	911.1	901.4
17.5°	1009.2	981.7	952.7	935.2	913.2	894.1	877.7	872.5	857.1	851.3	842.8
20°	974.7	949.4	927.2	904.1	872.3	854.4	841.5	834.6	822.1	814.6	809.2
22.5°	944.9	919.2	893.7	866.6	840.3	820.4	811.0	800.0	793.2	782.7	776.8
25°	902.5	874.4	843.7	814.6	795.7	780.6	765.6	755.8	746.2	741.2	730.5
27.5°	853.1	823.8	795.0	772.9	749.8	734.9	721.2	712.6	700.9	692.8	686.8
30°	825.9	791.4	766.6	746.6	717.0	703.0	692.8	682.0	673.4	664.7	658.8
32.5°	794.4	763.0	739.4	714.8	692.0	676.7	663.5	653.9	646.6	638.4	632.5
35°	745.0	718.7	694.3	669.6	652.8	637.2	621.6	613.5	606.5	599.0	593.6
37.5°	700.4	675.7	652.7	629.2	608.4	595.7	583.1	576.9	567.4	562.4	556.9
40°	672.8	648.6	623.8	601.1	579.6	569.8	558.5	549.4	540.7	536.9	531.0
42.5°	642.6	618.4	597.5	573.1	555.4	542.2	531.8	521.7	515.3	509.8	506.4
45°	597.9	576.3	555.8	531.6	514.8	503.5	491.6	482.5	476.6	472.8	466.8
47.5°	554.4	532.8	512.1	490.9	474.8	461.8	450.0	443.5	435.7	431.1	427.1
50°	522.9	503.5	481.4	462.0	445.8	432.9	423.2	415.1	408.1	402.2	399.5
52.5°	494.0	473.3	454.2	436.2	419.1	404.4	395.6	387.1	381.8	375.0	371.9
55°	446.4	426.4	410.3	392.4	375.7	363.4	352.6	345.0	339.6	332.1	327.8
57.5°	401.6	383.7	364.4	349.0	331.8	321.3	312.4	302.1	295.6	289.6	285.4
60°	371.5	350.9	334.2	319.7	304.6	291.1	283.0	275.0	267.9	262.0	258.3
62.5°	339.9	322.1	306.2	290.3	276.6	264.8	255.4	248.7	242.5	238.7	235.0
65°	291.7	277.7	261.5	248.5	235.6	227.0	219.4	213.5	209.1	206.4	203.3
67.5°	247.2	233.6	219.5	206.8	198.2	191.6	186.6	181.6	179.4	175.9	173.8
70°	218.3	204.3	191.9	182.2	173.6	168.7	165.5	161.8	159.5	155.3	153.1
72.5°	186.9	176.7	167.8	159.8	152.9	148.5	144.3	139.7	136.3	131.5	129.4
75°	147.2	138.0	131.0	125.6	121.3	115.3	109.4	104.6	103.0	101.3	100.8
77.5°	109.0	103.2	98.2	93.6	88.2	83.9	82.6	81.5	81.2	80.3	80.3
80°	85.7	80.3	76.5	71.1	67.9	67.9	67.9	66.9	67.4	67.4	67.4
82.5°	63.7	58.8	56.7	54.7	54.1	54.6	54.6	54.7	54.4	55.3	54.9
85°	32.9	33.4	34.5	34.0	34.5	34.5	35.6	35.0	35.6	34.5	35.6
87.5°	14.4	16.3	17.4	18.5	19.6	19.9	20.6	20.8	21.4	21.6	21.8
90°	11.7	14.7	18.1	21.5	25.0	28.4	29.5	30.5	31.6	32.6	33.4
92.5°	19.1	20.0	22.6	25.2	27.7	30.3	32.0	33.7	35.4	37.1	38.0
95°	29.1	25.1	28.0	30.9	33.8	36.7	38.6	40.4	42.2	44.0	45.0
97.5°	125.8	113.9	95.0	76.0	57.1	38.1	40.2	42.4	44.4	46.6	47.8
100°	221.2	203.3	162.2	121.2	80.2	39.1	41.2	43.3	45.4	47.5	48.7
102.5°	277.8	257.3	212.5	167.6	122.8	78.0	71.4	64.9	58.4	51.8	48.8
105°	364.5	354.1	330.4	306.7	283.0	259.4	212.8	166.2	119.6	73.0	50.0
107.5°	457.4	460.4	464.1	467.9	471.7	475.4	441.2	407.0	372.9	338.7	304.1
110°	520.1	522.5	525.5	528.3	531.2	534.1	525.5	516.7	508.0	499.4	476.2



TEST NUMBER: P332466-927

CATALOG NUMBER: S123RDIW-S1000D1535U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	579.8	582.3	585.1	588.0	590.9	593.8	594.0	594.1	594.3	594.5	590.6
115°	668.4	670.3	672.7	675.0	677.4	679.8	682.4	685.1	687.7	690.3	692.1
117.5°	756.8	758.4	759.5	760.7	761.9	763.2	765.2	767.4	769.4	771.6	772.8
120°	812.5	814.0	814.8	815.6	816.3	817.1	819.3	821.4	823.5	825.6	826.6
122.5°	865.7	867.2	868.2	869.2	870.1	871.2	872.7	874.1	875.6	877.1	877.9
125°	941.7	943.3	944.3	945.3	946.4	947.5	948.0	948.5	949.0	949.5	950.1
127.5°	1014.6	1016.3	1017.6	1018.8	1020.1	1021.4	1022.2	1023.0	1023.9	1024.7	1024.8
130°	1060.1	1061.7	1062.7	1063.7	1064.9	1065.9	1066.9	1067.9	1069.1	1070.1	1070.3
132.5°	1103.7	1105.2	1106.0	1106.8	1107.6	1108.5	1109.5	1110.6	1111.7	1112.7	1112.9
135°	1168.2	1169.4	1170.4	1171.6	1172.6	1173.6	1174.4	1175.2	1176.0	1176.8	1176.8
137.5°	1226.6	1228.0	1228.5	1229.1	1229.7	1230.3	1231.5	1232.8	1234.1	1235.3	1235.6
140°	1262.9	1264.0	1264.8	1265.6	1266.4	1267.2	1268.3	1269.3	1270.3	1271.4	1271.7
142.5°	1297.9	1299.1	1299.9	1300.7	1301.5	1302.3	1303.1	1303.9	1304.8	1305.6	1305.7
145°	1348.0	1349.2	1349.7	1350.2	1350.8	1351.3	1351.8	1352.3	1352.9	1353.4	1353.7
147.5°	1391.6	1392.5	1393.1	1393.6	1394.1	1394.6	1395.2	1395.7	1396.2	1396.8	1396.4
150°	1418.4	1419.0	1419.6	1420.1	1420.6	1421.2	1421.7	1422.2	1422.8	1423.2	1423.2
152.5°	1442.3	1442.6	1443.0	1443.3	1443.6	1443.9	1444.9	1445.8	1446.8	1447.7	1447.6
155°	1474.7	1474.6	1474.9	1475.1	1475.4	1475.6	1476.9	1478.3	1479.6	1480.9	1480.7
157.5°	1504.6	1504.4	1504.1	1503.9	1503.6	1503.3	1504.9	1506.5	1508.1	1509.7	1509.4
160°	1520.8	1520.5	1520.3	1520.0	1519.7	1519.5	1521.1	1522.7	1524.2	1525.7	1525.7
162.5°	1535.2	1534.7	1534.5	1534.2	1533.9	1533.7	1535.5	1537.2	1539.1	1540.8	1540.9
165°	1554.2	1553.7	1553.4	1553.2	1552.9	1552.6	1554.7	1556.8	1558.9	1561.1	1561.2
167.5°	1568.3	1567.8	1567.8	1567.8	1567.8	1567.8	1569.9	1572.0	1574.1	1576.2	1576.2
170°	1576.8	1576.3	1576.3	1576.3	1576.3	1576.3	1578.4	1580.5	1582.6	1584.8	1584.8
172.5°	1581.7	1581.1	1581.4	1581.6	1581.8	1582.0	1584.1	1586.2	1588.3	1590.4	1590.3
175°	1588.8	1588.2	1588.6	1588.8	1589.0	1589.4	1591.2	1593.0	1594.8	1596.7	1596.6
177.5°	1591.7	1591.3	1591.6	1591.7	1592.0	1592.2	1593.9	1595.5	1597.2	1598.9	1598.7
180°	1594.0	1594.0	1594.0	1594.0	1594.0	1594.0	1594.0	1594.0	1594.0	1594.0	1594.0



TEST NUMBER: P332466-927

CATALOG NUMBER: S123RDIW-S1000D1535U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1259.3	1259.3	1259.3	1259.3	1259.3	1259.3	1259.3	1259.3	1259.3	1259.3	1259.3
2.5°	1199.8	1199.4	1199.8	1198.1	1199.8	1199.4	1199.8	1205.0	1205.0	1205.5	1205.9
5°	1116.5	1115.9	1114.4	1109.5	1114.4	1115.9	1116.5	1118.1	1122.4	1130.0	1127.8
7.5°	1043.7	1043.0	1038.2	1038.3	1038.2	1043.0	1043.7	1047.9	1052.7	1057.4	1062.9
10°	1000.6	1001.1	994.7	990.9	994.7	1001.1	1000.6	1004.3	1011.4	1015.1	1018.9
12.5°	958.8	956.2	951.1	946.9	951.1	956.2	958.8	961.6	971.2	975.5	982.7
15°	903.6	898.2	885.2	886.3	885.2	898.2	903.6	901.4	911.1	916.5	918.6
17.5°	838.5	834.6	834.3	826.8	834.3	834.6	838.5	842.8	851.3	857.1	872.5
20°	800.6	797.9	798.9	791.4	798.9	797.9	800.6	809.2	814.6	822.1	834.6
22.5°	770.8	768.1	763.6	761.2	763.6	768.1	770.8	776.8	782.7	793.2	800.0
25°	727.2	722.9	718.7	721.4	718.7	722.9	727.2	730.5	741.2	746.2	755.8
27.5°	683.7	680.5	676.1	675.6	676.1	680.5	683.7	686.8	692.8	700.9	712.6
30°	656.1	652.8	650.7	648.0	650.7	652.8	656.1	658.8	664.7	673.4	682.0
32.5°	628.0	627.4	623.5	623.0	623.5	627.4	628.0	632.5	638.4	646.6	653.9
35°	591.4	588.2	587.1	587.6	587.1	588.2	591.4	593.6	599.0	606.5	613.5
37.5°	556.6	552.2	550.3	548.3	550.3	552.2	556.6	556.9	562.4	567.4	576.9
40°	531.6	527.3	526.2	525.1	526.2	527.3	531.6	531.0	536.9	540.7	549.4
42.5°	503.5	501.8	501.1	499.2	501.1	501.8	503.5	506.4	509.8	515.3	521.7
45°	465.2	464.7	461.4	462.6	461.4	464.7	465.2	466.8	472.8	476.6	482.5
47.5°	424.9	422.6	420.3	421.8	420.3	422.6	424.9	427.1	431.1	435.7	443.5
50°	397.4	396.2	391.4	392.4	391.4	396.2	397.4	399.5	402.2	408.1	415.1
52.5°	369.7	365.6	363.8	363.1	363.8	365.6	369.7	371.9	375.0	381.8	387.1
55°	324.0	319.2	317.0	315.9	317.0	319.2	324.0	327.8	332.1	339.6	345.0
57.5°	279.2	277.8	276.2	277.3	276.2	277.8	279.2	285.4	289.6	295.6	302.1
60°	252.9	252.9	252.9	252.3	252.9	252.9	252.9	258.3	262.0	267.9	275.0
62.5°	232.6	231.2	230.8	231.6	230.8	231.2	232.6	235.0	238.7	242.5	248.7
65°	201.6	201.1	198.9	198.4	198.9	201.1	201.6	203.3	206.4	209.1	213.5
67.5°	172.4	170.5	169.8	169.1	169.8	170.5	172.4	173.8	175.9	179.4	181.6
70°	150.4	149.3	146.1	146.6	146.1	149.3	150.4	153.1	155.3	159.5	161.8
72.5°	126.7	125.6	124.9	124.2	124.9	125.6	126.7	129.4	131.5	136.3	139.7
75°	100.3	99.7	99.2	101.3	99.2	99.7	100.3	100.8	101.3	103.0	104.6
77.5°	80.3	80.3	80.6	79.8	80.6	80.3	80.3	80.3	80.3	81.2	81.5
80°	67.4	67.4	66.9	66.9	66.9	67.4	67.4	67.4	67.4	67.4	66.9
82.5°	54.0	54.4	54.7	53.9	54.7	54.4	54.0	54.9	55.3	54.4	54.7
85°	35.6	35.0	36.1	35.6	36.1	35.0	35.6	35.6	34.5	35.6	35.0
87.5°	22.7	22.0	22.1	22.7	22.1	22.0	22.7	21.8	21.6	21.4	20.8
90°	34.0	34.5	35.0	35.5	35.0	34.5	34.0	33.4	32.6	31.6	30.5
92.5°	38.3	38.7	39.0	39.3	39.0	38.7	38.3	38.0	37.1	35.4	33.7
95°	45.0	45.0	45.0	45.0	45.0	45.0	45.0	45.0	44.0	42.2	40.4
97.5°	48.0	48.2	48.6	48.8	48.6	48.2	48.0	47.8	46.6	44.4	42.4
100°	49.0	49.2	49.5	49.7	49.5	49.2	49.0	48.7	47.5	45.4	43.3
102.5°	49.3	49.7	50.2	50.7	50.2	49.7	49.3	48.8	51.8	58.4	64.9
105°	50.5	51.1	51.6	52.1	51.6	51.1	50.5	50.0	73.0	119.6	166.2
107.5°	269.0	233.9	198.8	163.7	198.8	233.9	269.0	304.1	338.7	372.9	407.0
110°	438.6	400.9	363.3	325.7	363.3	400.9	438.6	476.2	499.4	508.0	516.7



TEST NUMBER: P332466-927

CATALOG NUMBER: S123RDIW-S1000D1535U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	582.6	574.6	566.7	558.7	566.7	574.6	582.6	590.6	594.5	594.3	594.1
115°	693.2	694.3	695.3	696.4	695.3	694.3	693.2	692.1	690.3	687.7	685.1
117.5°	772.9	773.2	773.4	773.6	773.4	773.2	772.9	772.8	771.6	769.4	767.4
120°	826.6	826.6	826.6	826.6	826.6	826.6	826.6	826.6	825.6	823.5	821.4
122.5°	878.1	878.3	878.5	878.8	878.5	878.3	878.1	877.9	877.1	875.6	874.1
125°	950.6	951.1	951.6	952.2	951.6	951.1	950.6	950.1	949.5	949.0	948.5
127.5°	1024.4	1023.8	1023.3	1022.8	1023.3	1023.8	1024.4	1024.8	1024.7	1023.9	1023.0
130°	1069.8	1069.3	1068.7	1068.3	1068.7	1069.3	1069.8	1070.3	1070.1	1069.1	1067.9
132.5°	1112.1	1111.4	1110.6	1109.9	1110.6	1111.4	1112.1	1112.9	1112.7	1111.7	1110.6
135°	1176.0	1175.2	1174.4	1173.6	1174.4	1175.2	1176.0	1176.8	1176.8	1176.0	1175.2
137.5°	1235.2	1234.6	1234.1	1233.6	1234.1	1234.6	1235.2	1235.6	1235.3	1234.1	1232.8
140°	1271.1	1270.7	1270.1	1269.6	1270.1	1270.7	1271.1	1271.7	1271.4	1270.3	1269.3
142.5°	1305.0	1304.2	1303.5	1302.7	1303.5	1304.2	1305.0	1305.7	1305.6	1304.8	1303.9
145°	1353.7	1353.7	1353.7	1353.7	1353.7	1353.7	1353.7	1353.7	1353.4	1352.9	1352.3
147.5°	1395.2	1394.0	1392.7	1391.5	1392.7	1394.0	1395.2	1396.4	1396.8	1396.2	1395.7
150°	1422.4	1421.6	1420.8	1420.0	1420.8	1421.6	1422.4	1423.2	1423.2	1422.8	1422.2
152.5°	1446.4	1445.1	1443.9	1442.7	1443.9	1445.1	1446.4	1447.6	1447.7	1446.8	1445.8
155°	1479.2	1477.6	1476.0	1474.5	1476.0	1477.6	1479.2	1480.7	1480.9	1479.6	1478.3
157.5°	1507.4	1505.3	1503.2	1501.2	1503.2	1505.3	1507.4	1509.4	1509.7	1508.1	1506.5
160°	1523.8	1521.9	1520.1	1518.3	1520.1	1521.9	1523.8	1525.7	1525.7	1524.2	1522.7
162.5°	1539.3	1537.6	1536.0	1534.4	1536.0	1537.6	1539.3	1540.9	1540.8	1539.1	1537.2
165°	1559.3	1557.5	1555.6	1553.8	1555.6	1557.5	1559.3	1561.2	1561.1	1558.9	1556.8
167.5°	1574.1	1572.0	1569.9	1567.8	1569.9	1572.0	1574.1	1576.2	1576.2	1574.1	1572.0
170°	1582.6	1580.5	1578.4	1576.3	1578.4	1580.5	1582.6	1584.8	1584.8	1582.6	1580.5
172.5°	1588.0	1585.7	1583.3	1581.0	1583.3	1585.7	1588.0	1590.3	1590.4	1588.3	1586.2
175°	1594.4	1592.4	1590.2	1588.2	1590.2	1592.4	1594.4	1596.6	1596.7	1594.8	1593.0
177.5°	1596.6	1594.5	1592.4	1590.3	1592.4	1594.5	1596.6	1598.7	1598.9	1597.2	1595.5
180°	1594.0	1594.0	1594.0	1594.0	1594.0	1594.0	1594.0	1594.0	1594.0	1594.0	1594.0



TEST NUMBER: P332466-927

CATALOG NUMBER: S123RDIW-S1000D1535U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1259.3	1259.3	1259.3	1259.3	1259.3	1259.3	1259.3	1259.3	1259.3	1259.3	1259.3
2.5°	1202.0	1208.0	1214.1	1219.6	1228.3	1232.2	1237.8	1239.9	1246.4	1255.9	1263.7
5°	1128.9	1137.5	1148.8	1158.0	1172.6	1183.8	1196.3	1208.2	1222.2	1242.1	1259.9
7.5°	1066.9	1075.4	1089.0	1106.0	1122.1	1138.1	1155.1	1171.2	1191.3	1219.9	1248.2
10°	1026.0	1036.2	1052.3	1070.6	1090.6	1106.3	1126.2	1146.7	1171.5	1204.4	1238.3
12.5°	990.5	998.2	1017.0	1034.4	1057.0	1076.9	1096.5	1120.4	1148.6	1183.7	1224.6
15°	934.3	945.1	963.4	982.8	1006.5	1027.5	1052.9	1082.0	1109.5	1152.6	1202.2
17.5°	877.7	894.1	913.2	935.2	952.7	981.7	1009.2	1039.1	1072.9	1118.6	1173.1
20°	841.5	854.4	872.3	904.1	927.2	949.4	974.7	1011.9	1043.1	1095.0	1151.5
22.5°	811.0	820.4	840.3	866.6	893.7	919.2	944.9	980.4	1019.0	1068.2	1129.6
25°	765.6	780.6	795.7	814.6	843.7	874.4	902.5	932.6	973.6	1026.0	1092.3
27.5°	721.2	734.9	749.8	772.9	795.0	823.8	853.1	887.7	931.7	987.0	1054.2
30°	692.8	703.0	717.0	746.6	766.6	791.4	825.9	856.7	897.6	956.4	1027.5
32.5°	663.5	676.7	692.0	714.8	739.4	763.0	794.4	827.8	869.6	927.5	1000.4
35°	621.6	637.2	652.8	669.6	694.3	718.7	745.0	781.7	824.3	880.4	952.0
37.5°	583.1	595.7	608.4	629.2	652.7	675.7	700.4	736.5	776.7	837.1	902.9
40°	558.5	569.8	579.6	601.1	623.8	648.6	672.8	704.6	747.7	804.4	868.0
42.5°	531.8	542.2	555.4	573.1	597.5	618.4	642.6	672.7	713.2	770.7	826.6
45°	491.6	503.5	514.8	531.6	555.8	576.3	597.9	626.5	668.0	715.4	765.0
47.5°	450.0	461.8	474.8	490.9	512.1	532.8	554.4	579.7	617.6	664.2	697.6
50°	423.2	432.9	445.8	462.0	481.4	503.5	522.9	550.4	586.5	623.2	652.3
52.5°	395.6	404.4	419.1	436.2	454.2	473.3	494.0	517.6	550.3	584.8	607.9
55°	352.6	363.4	375.7	392.4	410.3	426.4	446.4	470.6	496.5	522.4	538.1
57.5°	312.4	321.3	331.8	349.0	364.4	383.7	401.6	420.5	444.4	464.0	474.2
60°	283.0	291.1	304.6	319.7	334.2	350.9	371.5	390.3	408.6	424.3	432.4
62.5°	255.4	264.8	276.6	290.3	306.2	322.1	339.9	355.8	372.0	385.5	390.9
65°	219.4	227.0	235.6	248.5	261.5	277.7	291.7	307.8	319.7	327.3	332.1
67.5°	186.6	191.6	198.2	206.8	219.5	233.6	247.2	259.8	269.7	275.0	279.2
70°	165.5	168.7	173.6	182.2	191.9	204.3	218.3	227.5	236.1	240.4	244.8
72.5°	144.3	148.5	152.9	159.8	167.8	176.7	186.9	198.2	203.0	208.1	210.7
75°	109.4	115.3	121.3	125.6	131.0	138.0	147.2	154.2	156.9	161.2	161.8
77.5°	82.6	83.9	88.2	93.6	98.2	103.2	109.0	115.3	116.5	118.8	120.3
80°	67.9	67.9	67.9	71.1	76.5	80.3	85.7	89.0	91.1	91.7	92.2
82.5°	54.6	54.6	54.1	54.7	56.7	58.8	63.7	67.4	69.1	68.8	67.6
85°	35.6	34.5	34.5	34.0	34.5	33.4	32.9	35.0	38.3	38.3	37.2
87.5°	20.6	19.9	19.6	18.5	17.4	16.3	14.4	14.3	13.8	15.0	14.0
90°	29.5	28.4	25.0	21.5	18.1	14.7	11.7	9.1	6.4	3.8	1.2
92.5°	32.0	30.3	27.7	25.2	22.6	20.0	19.1	19.8	20.5	21.3	22.0
95°	38.6	36.7	33.8	30.9	28.0	25.1	29.1	39.8	50.7	61.5	72.2
97.5°	40.2	38.1	57.1	76.0	95.0	113.9	125.8	130.6	135.5	140.4	145.2
100°	41.2	39.1	80.2	121.2	162.2	203.3	221.2	215.9	210.6	205.4	200.2
102.5°	71.4	78.0	122.8	167.6	212.5	257.3	277.8	274.0	270.3	266.5	262.7
105°	212.8	259.4	283.0	306.7	330.4	354.1	364.5	361.6	358.7	355.8	352.9
107.5°	441.2	475.4	471.7	467.9	464.1	460.4	457.4	455.1	452.7	450.4	448.1
110°	525.5	534.1	531.2	528.3	525.5	522.5	520.1	517.9	515.8	513.7	511.6



TEST NUMBER: P332466-927

CATALOG NUMBER: S123RDIW-S1000D1535U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	594.0	593.8	590.9	588.0	585.1	582.3	579.8	578.0	576.1	574.2	572.3
115°	682.4	679.8	677.4	675.0	672.7	670.3	668.4	666.8	665.2	663.6	662.0
117.5°	765.2	763.2	761.9	760.7	759.5	758.4	756.8	754.8	752.8	750.9	748.9
120°	819.3	817.1	816.3	815.6	814.8	814.0	812.5	810.1	807.7	805.3	803.0
122.5°	872.7	871.2	870.1	869.2	868.2	867.2	865.7	863.7	861.8	859.8	857.9
125°	948.0	947.5	946.4	945.3	944.3	943.3	941.7	939.5	937.5	935.3	933.2
127.5°	1022.2	1021.4	1020.1	1018.8	1017.6	1016.3	1014.6	1012.5	1010.4	1008.3	1006.2
130°	1066.9	1065.9	1064.9	1063.7	1062.7	1061.7	1060.1	1058.0	1055.9	1053.8	1051.6
132.5°	1109.5	1108.5	1107.6	1106.8	1106.0	1105.2	1103.7	1101.5	1099.5	1097.3	1095.3
135°	1174.4	1173.6	1172.6	1171.6	1170.4	1169.4	1168.2	1166.6	1165.0	1163.4	1161.8
137.5°	1231.5	1230.3	1229.7	1229.1	1228.5	1228.0	1226.6	1224.6	1222.7	1220.7	1218.6
140°	1268.3	1267.2	1266.4	1265.6	1264.8	1264.0	1262.9	1261.3	1259.7	1258.1	1256.6
142.5°	1303.1	1302.3	1301.5	1300.7	1299.9	1299.1	1297.9	1296.3	1294.7	1293.2	1291.6
145°	1351.8	1351.3	1350.8	1350.2	1349.7	1349.2	1348.0	1346.2	1344.3	1342.4	1340.6
147.5°	1395.2	1394.6	1394.1	1393.6	1393.1	1392.5	1391.6	1390.4	1389.3	1388.1	1386.8
150°	1421.7	1421.2	1420.6	1420.1	1419.6	1419.0	1418.4	1417.6	1416.8	1416.0	1415.2
152.5°	1444.9	1443.9	1443.6	1443.3	1443.0	1442.6	1442.3	1441.9	1441.5	1441.2	1440.8
155°	1476.9	1475.6	1475.4	1475.1	1474.9	1474.6	1474.7	1475.3	1475.8	1476.3	1476.8
157.5°	1504.9	1503.3	1503.6	1503.9	1504.1	1504.4	1504.6	1504.6	1504.7	1504.8	1504.8
160°	1521.1	1519.5	1519.7	1520.0	1520.3	1520.5	1520.8	1521.1	1521.3	1521.5	1521.9
162.5°	1535.5	1533.7	1533.9	1534.2	1534.5	1534.7	1535.2	1535.9	1536.6	1537.2	1537.9
165°	1554.7	1552.6	1552.9	1553.2	1553.4	1553.7	1554.2	1555.0	1555.8	1556.6	1557.4
167.5°	1569.9	1567.8	1567.8	1567.8	1567.8	1567.8	1568.3	1569.4	1570.4	1571.5	1572.5
170°	1578.4	1576.3	1576.3	1576.3	1576.3	1576.3	1576.8	1577.9	1578.9	1580.0	1581.0
172.5°	1584.1	1582.0	1581.8	1581.6	1581.4	1581.1	1581.7	1582.9	1584.2	1585.5	1586.7
175°	1591.2	1589.4	1589.0	1588.8	1588.6	1588.2	1588.8	1590.1	1591.4	1592.8	1594.0
177.5°	1593.9	1592.2	1592.0	1591.7	1591.6	1591.3	1591.7	1592.8	1593.9	1594.9	1595.9
180°	1594.0	1594.0	1594.0	1594.0	1594.0	1594.0	1594.0	1594.0	1594.0	1594.0	1594.0



TEST NUMBER: P332466-927

CATALOG NUMBER: S123RDIW-S1000D1535U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1259.3	1259.3	1259.3	1259.3	1259.3	1259.3	1259.3	1259.3	1259.3	1259.3	1259.3
2.5°	1266.2	1271.0	1277.0	1286.1	1293.0	1299.0	1300.3	1302.0	1306.4	1313.7	1319.3
5°	1274.5	1286.8	1306.8	1326.2	1347.3	1364.5	1380.6	1391.9	1402.7	1425.4	1443.8
7.5°	1271.8	1299.5	1330.7	1365.6	1400.8	1435.0	1466.7	1495.1	1523.3	1556.3	1593.9
10°	1270.1	1302.5	1344.5	1389.3	1438.4	1486.3	1532.7	1568.8	1610.8	1648.6	1696.5
12.5°	1261.9	1308.5	1358.8	1416.0	1476.3	1531.6	1592.6	1642.5	1690.7	1745.2	1800.9
15°	1251.3	1307.9	1371.5	1447.5	1539.1	1606.0	1668.5	1755.3	1814.7	1873.9	1953.8
17.5°	1231.8	1300.8	1380.3	1479.1	1555.5	1645.4	1739.5	1808.1	1887.9	1971.5	2043.8
20°	1216.2	1296.6	1385.5	1482.6	1580.1	1677.7	1768.8	1850.8	1933.2	2029.7	2089.1
22.5°	1200.7	1280.2	1372.5	1475.7	1580.6	1683.3	1786.5	1882.7	1975.5	2072.8	2148.6
25°	1167.7	1262.0	1362.3	1467.4	1571.0	1684.2	1807.0	1914.4	2029.2	2129.5	2201.2
27.5°	1134.2	1220.8	1320.6	1427.2	1542.3	1676.1	1820.7	1942.6	2057.7	2129.5	2152.0
30°	1104.1	1195.7	1287.4	1395.7	1520.3	1669.6	1823.3	1962.9	2057.2	2088.5	2065.3
32.5°	1073.5	1156.5	1247.3	1358.2	1490.5	1653.7	1826.7	1950.8	2007.6	1983.7	1889.4
35°	1019.5	1094.4	1182.3	1293.3	1445.3	1644.8	1812.5	1896.6	1882.5	1747.8	1569.9
37.5°	961.6	1022.7	1104.1	1220.2	1398.5	1609.8	1751.2	1763.6	1642.4	1435.4	1229.9
40°	915.9	970.9	1054.5	1175.8	1362.3	1575.3	1689.6	1639.4	1451.3	1221.1	1049.6
42.5°	871.5	917.9	998.4	1129.2	1327.9	1528.3	1597.7	1488.5	1271.5	1053.8	897.9
45°	796.2	840.0	920.8	1055.0	1257.2	1438.4	1429.2	1239.4	1022.2	846.9	717.6
47.5°	724.8	763.0	838.9	976.0	1174.3	1303.5	1217.8	1015.9	831.6	691.0	598.7
50°	674.4	712.2	787.7	923.0	1107.9	1202.2	1079.8	885.2	716.4	600.0	526.7
52.5°	626.1	663.0	732.0	863.9	1027.6	1084.0	952.6	772.2	631.5	531.0	468.0
55°	558.5	586.5	648.6	774.7	897.1	910.0	776.8	625.9	510.0	439.9	396.8
57.5°	489.6	513.7	575.0	675.5	761.3	754.6	628.4	497.8	419.8	367.7	336.4
60°	444.7	468.5	522.4	608.6	673.4	650.7	534.8	429.7	362.8	324.6	299.8
62.5°	402.9	421.4	471.9	534.9	581.5	555.8	457.2	370.2	317.1	284.9	265.2
65°	342.3	357.4	397.8	430.7	456.6	431.8	349.9	289.5	251.2	228.5	215.1
67.5°	284.8	294.4	319.9	331.8	350.0	322.8	263.1	222.7	200.9	181.8	172.4
70°	248.5	255.6	269.0	278.7	283.6	255.6	211.4	181.6	163.3	149.9	143.9
72.5°	212.3	218.5	221.2	229.1	226.6	200.3	169.9	146.3	133.2	124.0	116.4
75°	162.2	164.9	162.2	159.1	152.0	133.7	112.6	100.8	91.1	86.8	84.1
77.5°	118.3	117.4	113.8	108.7	96.7	85.2	73.8	69.9	65.7	63.4	62.4
80°	91.1	89.0	85.7	77.6	67.4	59.3	56.6	53.9	52.3	49.6	49.0
82.5°	67.8	66.5	61.2	54.3	47.1	43.3	41.1	40.1	38.5	37.1	37.0
85°	36.1	34.5	28.6	24.8	23.7	22.7	22.1	22.1	20.0	19.4	19.4
87.5°	12.4	10.4	10.5	9.7	10.3	10.1	11.2	11.0	11.3	12.0	11.2
90°	3.8	6.4	9.1	11.7	14.7	18.1	21.5	25.0	28.4	29.5	30.5
92.5°	21.3	20.5	19.8	19.1	20.0	22.6	25.2	27.7	30.3	32.0	33.7
95°	61.5	50.7	39.8	29.1	25.1	28.0	30.9	33.8	36.7	38.6	40.4
97.5°	140.4	135.5	130.6	125.8	113.9	95.0	76.0	57.1	38.1	40.2	42.4
100°	205.4	210.6	215.9	221.2	203.3	162.2	121.2	80.2	39.1	41.2	43.3
102.5°	266.5	270.3	274.0	277.8	257.3	212.5	167.6	122.8	78.0	71.4	64.9
105°	355.8	358.7	361.6	364.5	354.1	330.4	306.7	283.0	259.4	212.8	166.2
107.5°	450.4	452.7	455.1	457.4	460.4	464.1	467.9	471.7	475.4	441.2	407.0
110°	513.7	515.8	517.9	520.1	522.5	525.5	528.3	531.2	534.1	525.5	516.7



TEST NUMBER: P332466-927

CATALOG NUMBER: S123RDIW-S1000D1535U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	574.2	576.1	578.0	579.8	582.3	585.1	588.0	590.9	593.8	594.0	594.1
115°	663.6	665.2	666.8	668.4	670.3	672.7	675.0	677.4	679.8	682.4	685.1
117.5°	750.9	752.8	754.8	756.8	758.4	759.5	760.7	761.9	763.2	765.2	767.4
120°	805.3	807.7	810.1	812.5	814.0	814.8	815.6	816.3	817.1	819.3	821.4
122.5°	859.8	861.8	863.7	865.7	867.2	868.2	869.2	870.1	871.2	872.7	874.1
125°	935.3	937.5	939.5	941.7	943.3	944.3	945.3	946.4	947.5	948.0	948.5
127.5°	1008.3	1010.4	1012.5	1014.6	1016.3	1017.6	1018.8	1020.1	1021.4	1022.2	1023.0
130°	1053.8	1055.9	1058.0	1060.1	1061.7	1062.7	1063.7	1064.9	1065.9	1066.9	1067.9
132.5°	1097.3	1099.5	1101.5	1103.7	1105.2	1106.0	1106.8	1107.6	1108.5	1109.5	1110.6
135°	1163.4	1165.0	1166.6	1168.2	1169.4	1170.4	1171.6	1172.6	1173.6	1174.4	1175.2
137.5°	1220.7	1222.7	1224.6	1226.6	1228.0	1228.5	1229.1	1229.7	1230.3	1231.5	1232.8
140°	1258.1	1259.7	1261.3	1262.9	1264.0	1264.8	1265.6	1266.4	1267.2	1268.3	1269.3
142.5°	1293.2	1294.7	1296.3	1297.9	1299.1	1299.9	1300.7	1301.5	1302.3	1303.1	1303.9
145°	1342.4	1344.3	1346.2	1348.0	1349.2	1349.7	1350.2	1350.8	1351.3	1351.8	1352.3
147.5°	1388.1	1389.3	1390.4	1391.6	1392.5	1393.1	1393.6	1394.1	1394.6	1395.2	1395.7
150°	1416.0	1416.8	1417.6	1418.4	1419.0	1419.6	1420.1	1420.6	1421.2	1421.7	1422.2
152.5°	1441.2	1441.5	1441.9	1442.3	1442.6	1443.0	1443.3	1443.6	1443.9	1444.9	1445.8
155°	1476.3	1475.8	1475.3	1474.7	1474.6	1474.9	1475.1	1475.4	1475.6	1476.9	1478.3
157.5°	1504.8	1504.7	1504.6	1504.6	1504.4	1504.1	1503.9	1503.6	1503.3	1504.9	1506.5
160°	1521.5	1521.3	1521.1	1520.8	1520.5	1520.3	1520.0	1519.7	1519.5	1521.1	1522.7
162.5°	1537.2	1536.6	1535.9	1535.2	1534.7	1534.5	1534.2	1533.9	1533.7	1535.5	1537.2
165°	1556.6	1555.8	1555.0	1554.2	1553.7	1553.4	1553.2	1552.9	1552.6	1554.7	1556.8
167.5°	1571.5	1570.4	1569.4	1568.3	1567.8	1567.8	1567.8	1567.8	1567.8	1569.9	1572.0
170°	1580.0	1578.9	1577.9	1576.8	1576.3	1576.3	1576.3	1576.3	1576.3	1578.4	1580.5
172.5°	1585.5	1584.2	1582.9	1581.7	1581.1	1581.4	1581.6	1581.8	1582.0	1584.1	1586.2
175°	1592.8	1591.4	1590.1	1588.8	1588.2	1588.6	1588.8	1589.0	1589.4	1591.2	1593.0
177.5°	1594.9	1593.9	1592.8	1591.7	1591.3	1591.6	1591.7	1592.0	1592.2	1593.9	1595.5
180°	1594.0	1594.0	1594.0	1594.0	1594.0	1594.0	1594.0	1594.0	1594.0	1594.0	1594.0



TEST NUMBER: P332466-927

CATALOG NUMBER: S123RDIW-S1000D1535U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1259.3	1259.3	1259.3	1259.3	1259.3	1259.3	1259.3
2.5°	1328.3	1328.3	1330.1	1336.6	1337.4	1343.0	1341.3
5°	1459.9	1470.1	1473.9	1490.1	1499.8	1504.1	1495.5
7.5°	1620.8	1649.6	1663.3	1680.3	1695.3	1699.8	1688.1
10°	1738.0	1768.2	1793.6	1809.3	1823.8	1833.5	1845.9
12.5°	1851.5	1888.6	1912.6	1934.7	1949.7	1962.0	1964.1
15°	1974.8	2030.8	2073.4	2104.7	2120.3	2128.4	2125.2
17.5°	2099.0	2151.0	2181.4	2213.3	2234.9	2236.0	2236.6
20°	2169.4	2220.0	2255.1	2278.8	2303.0	2302.0	2307.4
22.5°	2216.4	2256.3	2283.1	2300.3	2308.7	2304.5	2305.6
25°	2238.4	2250.2	2245.4	2217.9	2210.9	2185.6	2189.8
27.5°	2124.9	2068.9	2010.9	1936.3	1877.4	1830.3	1832.7
30°	1970.9	1871.8	1758.6	1663.7	1578.5	1554.8	1504.1
32.5°	1755.8	1606.9	1474.3	1385.9	1312.8	1293.0	1248.8
35°	1390.9	1246.4	1110.0	1028.1	995.7	950.5	949.9
37.5°	1081.1	953.9	881.8	820.3	788.1	760.7	758.0
40°	909.5	810.2	755.8	711.6	679.9	659.3	654.5
42.5°	789.6	709.3	658.4	631.0	606.5	596.0	588.0
45°	644.8	590.9	555.2	530.4	519.2	511.0	506.8
47.5°	539.3	503.2	479.0	462.5	453.3	444.7	447.0
50°	482.0	452.3	434.5	418.9	411.9	405.9	406.5
52.5°	435.8	409.2	394.8	383.5	374.8	370.6	368.5
55°	369.8	353.1	338.6	330.5	325.6	319.7	318.1
57.5°	315.4	302.5	290.7	281.5	280.4	274.6	275.4
60°	279.2	268.5	258.8	253.9	250.2	245.3	246.9
62.5°	249.5	240.4	231.6	227.6	223.9	220.3	221.0
65°	204.3	195.7	190.3	188.1	186.6	184.9	183.3
67.5°	162.8	157.6	154.2	149.6	146.2	145.7	144.0
70°	137.0	129.9	124.0	118.0	116.5	115.9	116.5
72.5°	109.8	105.4	103.7	100.8	100.5	99.1	100.1
75°	82.5	80.9	79.8	77.6	77.6	77.6	77.6
77.5°	60.8	59.8	59.2	58.8	58.2	57.4	57.4
80°	47.5	46.9	45.8	45.8	45.3	45.8	45.3
82.5°	35.8	35.7	34.6	34.6	34.1	33.7	34.1
85°	18.3	17.8	18.9	17.8	18.3	17.3	18.3
87.5°	11.5	11.7	11.4	11.6	11.2	12.2	11.4
90°	31.6	32.6	33.4	34.0	34.5	35.0	35.5
92.5°	35.4	37.1	38.0	38.3	38.7	39.0	39.3
95°	42.2	44.0	45.0	45.0	45.0	45.0	45.0
97.5°	44.4	46.6	47.8	48.0	48.2	48.6	48.8
100°	45.4	47.5	48.7	49.0	49.2	49.5	49.7
102.5°	58.4	51.8	48.8	49.3	49.7	50.2	50.7
105°	119.6	73.0	50.0	50.5	51.1	51.6	52.1
107.5°	372.9	338.7	304.1	269.0	233.9	198.8	163.7
110°	508.0	499.4	476.2	438.6	400.9	363.3	325.7



TEST NUMBER: P332466-927

CATALOG NUMBER: S123RDIW-S1000D1535U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	594.3	594.5	590.6	582.6	574.6	566.7	558.7
115°	687.7	690.3	692.1	693.2	694.3	695.3	696.4
117.5°	769.4	771.6	772.8	772.9	773.2	773.4	773.6
120°	823.5	825.6	826.6	826.6	826.6	826.6	826.6
122.5°	875.6	877.1	877.9	878.1	878.3	878.5	878.8
125°	949.0	949.5	950.1	950.6	951.1	951.6	952.2
127.5°	1023.9	1024.7	1024.8	1024.4	1023.8	1023.3	1022.8
130°	1069.1	1070.1	1070.3	1069.8	1069.3	1068.7	1068.3
132.5°	1111.7	1112.7	1112.9	1112.1	1111.4	1110.6	1109.9
135°	1176.0	1176.8	1176.8	1176.0	1175.2	1174.4	1173.6
137.5°	1234.1	1235.3	1235.6	1235.2	1234.6	1234.1	1233.6
140°	1270.3	1271.4	1271.7	1271.1	1270.7	1270.1	1269.6
142.5°	1304.8	1305.6	1305.7	1305.0	1304.2	1303.5	1302.7
145°	1352.9	1353.4	1353.7	1353.7	1353.7	1353.7	1353.7
147.5°	1396.2	1396.8	1396.4	1395.2	1394.0	1392.7	1391.5
150°	1422.8	1423.2	1423.2	1422.4	1421.6	1420.8	1420.0
152.5°	1446.8	1447.7	1447.6	1446.4	1445.1	1443.9	1442.7
155°	1479.6	1480.9	1480.7	1479.2	1477.6	1476.0	1474.5
157.5°	1508.1	1509.7	1509.4	1507.4	1505.3	1503.2	1501.2
160°	1524.2	1525.7	1525.7	1523.8	1521.9	1520.1	1518.3
162.5°	1539.1	1540.8	1540.9	1539.3	1537.6	1536.0	1534.4
165°	1558.9	1561.1	1561.2	1559.3	1557.5	1555.6	1553.8
167.5°	1574.1	1576.2	1576.2	1574.1	1572.0	1569.9	1567.8
170°	1582.6	1584.8	1584.8	1582.6	1580.5	1578.4	1576.3
172.5°	1588.3	1590.4	1590.3	1588.0	1585.7	1583.3	1581.0
175°	1594.8	1596.7	1596.6	1594.4	1592.4	1590.2	1588.2
177.5°	1597.2	1598.9	1598.7	1596.6	1594.5	1592.4	1590.3
180°	1594.0	1594.0	1594.0	1594.0	1594.0	1594.0	1594.0

(END OF REPORT)