

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332452-927

Luminaire Tested: **S123RDIW-S1000D460U927-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332452-927
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-5,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123RDIW-S1000D460U927-4F0-1E-UDD-F
Description: DEFINE 3 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 1000 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 460 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4465.5 lumens
Efficiency: N/A
Efficacy: 96.7 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.06 / 1.22
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 46.2
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332452-927

CATALOG NUMBER: S123RDIW-S1000D460U927-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P332452-927

CATALOG NUMBER: S123RDIW-S1000D460U927-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	111	111	111	111	105	105	105	105	93	93	93	82	82	82	72	72	72	67
1	102	98	94	91	96	92	89	86	82	80	77	73	71	69	64	63	62	58
2	93	86	80	75	88	81	76	71	73	68	65	65	61	59	57	55	53	49
3	85	76	69	63	80	72	65	60	64	59	55	57	53	50	51	48	45	42
4	78	68	60	54	74	64	57	51	58	52	47	52	47	43	46	42	39	36
5	72	61	52	46	68	58	50	45	52	46	41	46	42	38	42	38	35	32
6	67	55	46	40	63	52	44	39	47	41	36	42	37	33	38	34	31	28
7	62	49	41	36	58	47	40	35	43	37	32	39	34	30	35	31	27	25
8	58	45	37	32	54	43	36	31	39	33	29	35	30	27	32	28	25	23
9	54	41	34	29	51	40	33	28	36	30	26	33	28	24	30	25	22	20
10	50	38	31	26	48	36	30	25	33	28	24	30	25	22	27	23	20	19

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	14310	14310	14310
5°	14364	14166	14249
10°	14283	13988	13941
15°	14130	13661	13517
20°	13919	13252	12944
25°	13702	12792	12383
30°	13415	12263	11591
35°	13119	11730	10867
40°	12847	11105	9969
45°	12490	10488	9159
50°	12097	9786	8251
55°	11695	8983	7405
60°	11328	8125	6476
65°	10847	7195	5547
70°	10247	6039	4482
75°	9374	4754	4213
80°	8356	4209	3874
85°	7052	3730	3458



TEST NUMBER: P332452-927

CATALOG NUMBER: S123RDIW-S1000D460U927-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	124.8	2.8
10°-20°	347.3	7.8
20°-30°	500.2	11.2
30°-40°	563.4	12.6
40°-50°	539.0	12.1
50°-60°	441.4	9.9
60°-70°	297.8	6.7
70°-80°	149.8	3.4
80°-90°	41.0	0.9
90°-100°	17.4	0.4
100°-110°	83.0	1.9
110°-120°	199.4	4.5
120°-130°	253.9	5.7
130°-140°	271.3	6.1
140°-150°	253.7	5.7
150°-160°	204.6	4.6
160°-170°	132.1	3.0
170°-180°	45.5	1.0
0°-30°	972.3	21.8
0°-40°	1535.7	34.4
0°-60°	2516.0	56.3
0°-90°	3004.6	67.3
90°-120°	299.8	6.7
90°-150°	1078.7	24.2
90°-180°	1461.0	32.7
0°-180°	4465.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1329	1329	1329	1329	1329	
5°	1329	1324	1311	1320	1319	126
15°	1268	1255	1226	1220	1213	357
25°	1154	1125	1077	1055	1043	530
35°	998	958	893	848	827	625
45°	820	770	689	629	602	633
55°	623	568	479	418	395	559
65°	426	365	282	232	218	421
75°	225	173	114	104	101	240
85°	57	34	30	28	28	64
90°	0	4	9	10	11	4
95°	22	8	11	13	14	27
105°	106	108	78	18	16	112
115°	199	201	204	208	209	196
125°	280	283	285	285	286	250
135°	349	351	353	354	353	269
145°	403	405	406	407	407	252
155°	444	443	444	445	443	204
165°	468	467	467	469	467	132
175°	479	477	478	480	477	46
180°	479	479	479	479	479	



TEST NUMBER: P332452-927

CATALOG NUMBER: S123RDIW-S1000D460U927-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1329.4	1329.4	1329.4	1329.4	1329.4	1329.4	1329.4	1329.4	1329.4	1329.4	1329.4
2.5°	1333.7	1332.9	1332.2	1331.4	1330.6	1329.1	1326.8	1324.5	1322.2	1319.9	1322.0
5°	1329.4	1328.2	1327.0	1325.8	1324.6	1322.5	1319.7	1316.8	1314.0	1311.1	1313.2
7.5°	1317.1	1315.8	1314.5	1313.2	1311.9	1309.4	1305.7	1302.0	1298.2	1294.5	1295.7
10°	1306.8	1305.1	1303.4	1301.7	1300.1	1297.0	1292.8	1288.4	1284.1	1279.8	1280.1
12.5°	1292.1	1290.2	1288.4	1286.5	1284.6	1281.0	1275.8	1270.5	1265.3	1260.0	1259.8
15°	1268.0	1265.4	1262.7	1260.0	1257.4	1252.8	1246.0	1239.3	1232.6	1225.9	1224.7
17.5°	1237.5	1234.5	1231.4	1228.4	1225.3	1219.5	1210.9	1202.5	1193.9	1185.3	1182.8
20°	1215.1	1211.3	1207.4	1203.6	1199.8	1193.3	1184.2	1175.1	1166.0	1156.9	1153.8
22.5°	1190.1	1185.7	1181.3	1176.9	1172.5	1165.5	1155.7	1146.1	1136.4	1126.7	1122.8
25°	1153.7	1147.7	1141.7	1135.7	1129.7	1121.2	1110.2	1099.2	1088.1	1077.1	1072.1
27.5°	1109.5	1102.9	1096.2	1089.6	1083.0	1073.6	1061.3	1049.0	1036.7	1024.5	1017.5
30°	1079.3	1072.1	1064.9	1057.7	1050.5	1040.2	1026.8	1013.4	1000.0	986.6	978.4
32.5°	1049.1	1040.9	1032.8	1024.6	1016.5	1005.4	991.2	977.0	962.7	948.6	939.7
35°	998.4	989.8	981.1	972.6	963.9	952.1	937.3	922.4	907.6	892.7	882.4
37.5°	947.1	937.5	927.9	918.3	908.7	896.0	880.2	864.3	848.4	832.6	820.9
40°	914.3	903.8	893.2	882.6	872.1	858.3	841.4	824.3	807.3	790.3	777.8
42.5°	877.2	866.6	856.1	845.6	835.0	821.0	803.4	785.8	768.3	750.7	737.0
45°	820.5	809.7	798.9	788.1	777.4	762.8	744.3	725.9	707.4	689.0	675.3
47.5°	763.8	751.9	740.1	728.3	716.4	701.3	682.9	664.4	645.9	627.5	612.7
50°	722.4	711.1	699.9	688.6	677.3	662.0	642.6	623.2	603.8	584.4	569.5
52.5°	685.3	673.1	660.8	648.6	636.4	620.7	601.5	582.3	563.1	543.8	528.4
55°	623.2	611.5	599.7	588.0	576.2	560.2	539.8	519.4	499.1	478.7	464.9
57.5°	565.9	553.0	540.3	527.4	514.7	498.0	477.5	457.1	436.7	416.2	403.1
60°	526.2	513.0	499.8	486.6	473.4	456.9	437.0	417.2	397.3	377.4	364.4
62.5°	486.5	473.3	460.1	446.9	433.8	417.2	397.4	377.5	357.6	337.7	325.5
65°	425.9	412.7	399.5	386.3	373.2	357.3	338.6	319.9	301.2	282.5	270.8
67.5°	365.3	352.0	338.7	325.3	312.0	296.4	278.5	260.5	242.6	224.7	215.9
70°	325.6	312.7	299.8	286.8	273.9	259.0	242.2	225.5	208.7	191.9	183.5
72.5°	285.9	273.2	260.5	247.7	235.0	220.9	205.7	190.5	175.2	160.0	153.1
75°	225.4	213.8	202.3	190.8	179.4	167.0	153.8	140.6	127.5	114.3	111.9
77.5°	170.2	159.7	149.3	138.9	128.6	119.1	110.6	102.1	93.6	85.2	83.9
80°	134.8	124.9	115.1	105.3	95.5	88.1	83.0	78.0	73.0	67.9	67.2
82.5°	101.2	92.7	84.2	75.7	67.2	61.8	59.4	57.1	54.7	52.4	51.7
85°	57.1	51.9	46.6	41.4	36.0	33.0	32.3	31.6	30.9	30.2	29.7
87.5°	20.8	18.9	16.9	14.9	13.0	12.1	12.3	12.5	12.8	12.9	12.8
90°	0.3	1.1	1.9	2.7	3.5	4.4	5.5	6.5	7.5	8.6	8.9
92.5°	6.7	6.4	6.2	5.9	5.7	6.0	6.8	7.5	8.3	9.1	9.6
95°	21.7	18.5	15.2	12.0	8.7	7.5	8.4	9.3	10.1	11.0	11.6
97.5°	43.6	42.1	40.7	39.3	37.8	34.2	28.5	22.8	17.2	11.5	12.1
100°	60.1	61.7	63.3	64.9	66.5	61.1	48.8	36.4	24.1	11.7	12.4
102.5°	78.9	80.1	81.2	82.4	83.5	77.3	63.8	50.4	36.9	23.4	21.5
105°	106.1	106.9	107.8	108.7	109.6	106.4	99.3	92.2	85.1	78.0	63.9
107.5°	134.7	135.4	136.1	136.7	137.4	138.4	139.5	140.6	141.7	142.8	132.6
110°	153.8	154.4	155.0	155.7	156.3	157.0	157.9	158.8	159.6	160.5	157.9



TEST NUMBER: P332452-927

CATALOG NUMBER: S123RDIW-S1000D460U927-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	172.0	172.5	173.1	173.6	174.3	175.0	175.9	176.7	177.6	178.5	178.5
115°	198.9	199.4	199.9	200.3	200.8	201.5	202.2	202.9	203.6	204.3	205.1
117.5°	225.1	225.7	226.2	226.8	227.4	227.9	228.2	228.6	229.0	229.3	230.0
120°	241.3	242.0	242.7	243.4	244.2	244.6	244.9	245.1	245.3	245.6	246.2
122.5°	257.9	258.4	259.0	259.6	260.2	260.6	260.9	261.2	261.5	261.8	262.2
125°	280.4	281.1	281.7	282.3	283.0	283.4	283.8	284.1	284.4	284.7	284.9
127.5°	302.4	303.0	303.6	304.3	304.9	305.4	305.8	306.2	306.6	307.0	307.2
130°	316.1	316.7	317.3	318.0	318.6	319.1	319.4	319.7	320.0	320.3	320.6
132.5°	329.2	329.8	330.4	331.1	331.7	332.1	332.4	332.6	332.9	333.1	333.4
135°	349.1	349.6	350.1	350.5	351.0	351.4	351.7	352.0	352.4	352.7	352.9
137.5°	366.2	366.9	367.4	368.0	368.6	369.0	369.2	369.4	369.6	369.7	370.1
140°	377.6	378.1	378.6	379.1	379.5	379.9	380.1	380.3	380.6	380.8	381.1
142.5°	388.2	388.6	389.1	389.6	390.1	390.4	390.6	390.9	391.1	391.3	391.6
145°	402.9	403.5	404.0	404.6	405.1	405.4	405.6	405.8	405.9	406.1	406.2
147.5°	416.8	417.2	417.5	417.9	418.2	418.5	418.7	418.8	419.0	419.1	419.3
150°	425.3	425.6	425.8	426.0	426.3	426.4	426.6	426.7	426.9	427.1	427.2
152.5°	433.0	433.1	433.2	433.3	433.5	433.6	433.6	433.7	433.8	434.0	434.2
155°	443.8	443.6	443.5	443.4	443.2	443.1	443.2	443.3	443.4	443.5	443.9
157.5°	452.3	452.2	452.2	452.2	452.2	452.1	452.0	451.9	451.9	451.8	452.3
160°	457.3	457.2	457.2	457.1	457.0	456.9	456.9	456.8	456.7	456.6	457.1
162.5°	462.2	462.0	461.8	461.6	461.4	461.2	461.1	461.1	461.0	460.9	461.4
165°	468.0	467.8	467.5	467.3	467.1	466.9	466.8	466.8	466.7	466.6	467.2
167.5°	472.6	472.3	472.0	471.7	471.3	471.2	471.2	471.2	471.2	471.2	471.8
170°	475.2	474.8	474.5	474.2	473.9	473.7	473.7	473.7	473.7	473.7	474.4
172.5°	476.8	476.5	476.1	475.7	475.3	475.2	475.2	475.3	475.4	475.4	476.0
175°	479.0	478.6	478.2	477.8	477.4	477.3	477.4	477.4	477.5	477.6	478.2
177.5°	479.6	479.3	479.0	478.6	478.3	478.2	478.3	478.3	478.4	478.5	479.0
180°	479.0	479.0	479.0	479.0	479.0	479.0	479.0	479.0	479.0	479.0	479.0



TEST NUMBER: P332452-927

CATALOG NUMBER: S123RDIW-S1000D460U927-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1329.4	1329.4	1329.4	1329.4	1329.4	1329.4	1329.4	1329.4
2.5°	1324.1	1326.3	1328.3	1329.2	1328.8	1328.5	1328.1	1327.7
5°	1315.4	1317.6	1319.7	1320.6	1320.1	1319.6	1319.1	1318.7
7.5°	1296.9	1298.1	1299.3	1299.5	1298.6	1297.8	1297.0	1296.2
10°	1280.3	1280.6	1280.8	1280.3	1279.1	1277.9	1276.7	1275.5
12.5°	1259.6	1259.6	1259.4	1258.6	1257.3	1255.8	1254.5	1253.1
15°	1223.5	1222.3	1221.1	1219.6	1218.0	1216.3	1214.7	1213.0
17.5°	1180.3	1177.7	1175.2	1172.7	1170.2	1167.7	1165.2	1162.7
20°	1150.6	1147.6	1144.5	1141.5	1138.6	1135.7	1132.8	1130.0
22.5°	1119.0	1115.1	1111.2	1107.9	1105.3	1102.6	1099.9	1097.2
25°	1067.1	1062.0	1057.0	1053.1	1050.5	1047.9	1045.3	1042.6
27.5°	1010.5	1003.5	996.5	991.0	987.0	982.9	978.9	974.9
30°	970.3	962.1	953.9	948.0	944.1	940.3	936.4	932.6
32.5°	930.7	921.9	912.9	906.5	902.5	898.4	894.4	890.3
35°	872.1	861.8	851.5	844.2	840.0	835.6	831.3	827.0
37.5°	809.2	797.5	785.8	777.3	772.0	766.7	761.4	756.1
40°	765.4	753.0	740.5	731.5	726.0	720.5	714.9	709.5
42.5°	723.4	709.8	696.2	686.9	682.0	677.1	672.1	667.2
45°	661.6	648.0	634.3	624.6	618.9	613.1	607.4	601.7
47.5°	597.8	583.0	568.1	558.1	552.9	547.9	542.7	537.6
50°	554.7	539.8	525.0	514.8	509.3	503.7	498.3	492.7
52.5°	513.0	497.6	482.1	471.9	467.0	462.1	457.2	452.2
55°	450.9	437.0	423.1	413.8	409.0	404.2	399.4	394.6
57.5°	389.9	376.8	363.7	355.1	351.0	346.9	342.9	338.7
60°	351.5	338.6	325.6	317.1	313.1	309.0	304.9	300.8
62.5°	313.3	301.2	289.0	280.7	276.6	272.3	268.0	263.7
65°	259.0	247.2	235.5	228.3	225.7	223.1	220.5	217.8
67.5°	207.2	198.4	189.6	183.8	181.0	178.2	175.3	172.5
70°	175.2	166.8	158.4	152.9	150.2	147.6	145.0	142.4
72.5°	146.3	139.4	132.6	128.7	127.5	126.4	125.3	124.2
75°	109.5	107.1	104.7	103.3	102.8	102.3	101.8	101.3
77.5°	82.6	81.3	80.0	79.1	78.7	78.2	77.7	77.2
80°	66.5	65.8	65.0	64.5	64.0	63.5	63.0	62.5
82.5°	50.9	50.2	49.5	49.1	49.0	49.0	48.8	48.7
85°	29.2	28.8	28.3	28.0	28.0	28.0	28.0	28.0
87.5°	12.7	12.5	12.4	12.3	12.1	12.0	11.8	11.6
90°	9.2	9.5	9.8	10.1	10.2	10.4	10.5	10.7
92.5°	10.1	10.6	11.2	11.4	11.6	11.6	11.7	11.8
95°	12.1	12.7	13.2	13.5	13.5	13.5	13.5	13.5
97.5°	12.8	13.4	14.0	14.3	14.4	14.5	14.6	14.7
100°	13.0	13.6	14.3	14.7	14.7	14.8	14.9	15.0
102.5°	19.5	17.5	15.6	14.7	14.8	15.0	15.1	15.2
105°	49.9	36.0	21.9	15.1	15.2	15.4	15.5	15.7
107.5°	122.3	112.1	101.8	91.4	80.8	70.3	59.7	49.2
110°	155.3	152.7	150.0	143.1	131.8	120.5	109.2	97.9



TEST NUMBER: P332452-927

CATALOG NUMBER: S123RDIW-S1000D460U927-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	178.6	178.6	178.6	177.4	175.1	172.7	170.3	167.9
115°	205.9	206.7	207.5	208.0	208.3	208.7	209.0	209.3
117.5°	230.6	231.2	231.9	232.2	232.3	232.3	232.4	232.5
120°	246.8	247.5	248.1	248.4	248.4	248.4	248.4	248.4
122.5°	262.7	263.2	263.6	263.8	263.9	264.0	264.0	264.1
125°	285.0	285.2	285.3	285.5	285.7	285.8	286.0	286.1
127.5°	307.4	307.7	307.9	308.0	307.8	307.7	307.5	307.4
130°	320.9	321.2	321.5	321.6	321.5	321.3	321.2	321.0
132.5°	333.7	334.1	334.4	334.5	334.2	334.0	333.7	333.6
135°	353.2	353.4	353.6	353.6	353.4	353.2	352.9	352.7
137.5°	370.5	370.8	371.2	371.4	371.2	371.1	370.9	370.7
140°	381.4	381.8	382.1	382.1	382.0	381.8	381.7	381.5
142.5°	391.9	392.1	392.4	392.4	392.1	392.0	391.7	391.5
145°	406.4	406.5	406.7	406.8	406.8	406.8	406.8	406.8
147.5°	419.5	419.6	419.8	419.6	419.3	418.9	418.6	418.2
150°	427.4	427.5	427.7	427.7	427.5	427.2	427.0	426.7
152.5°	434.5	434.7	435.1	435.0	434.7	434.3	434.0	433.6
155°	444.3	444.7	445.0	445.0	444.5	444.0	443.5	443.1
157.5°	452.7	453.2	453.7	453.6	453.0	452.4	451.8	451.1
160°	457.6	458.0	458.5	458.5	458.0	457.4	456.9	456.3
162.5°	462.0	462.6	463.0	463.1	462.6	462.1	461.6	461.1
165°	467.9	468.5	469.1	469.1	468.6	468.1	467.5	467.0
167.5°	472.5	473.0	473.6	473.6	473.0	472.5	471.8	471.2
170°	475.0	475.6	476.3	476.3	475.6	475.0	474.4	473.7
172.5°	476.7	477.3	477.9	477.9	477.2	476.5	475.9	475.2
175°	478.7	479.3	479.8	479.8	479.2	478.6	477.9	477.3
177.5°	479.5	480.0	480.5	480.5	479.8	479.2	478.6	477.9
180°	479.0	479.0	479.0	479.0	479.0	479.0	479.0	479.0

(END OF REPORT)