

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331525-840

Luminaire Tested: **S122DIW-S675D435U840-4F0-1E-UDD-A**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331525-840
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122DIW-S675D435U840-4F0-1E-UDD-A
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 675 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 435 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4708.9 lumens
Efficiency: N/A
Efficacy: 124.9 lumens/watt
Spacing Criteria (0/90/45): 1.08 / 1.16 / 1.23
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 37.7
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331525-840

CATALOG NUMBER: S122DIW-S675D435U840-4F0-1E-UDD-A

Luminous Intensity Polar Plot





TEST NUMBER: P331525-840

CATALOG NUMBER: S122DIW-S675D435U840-4F0-1E-UDD-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	110	110	110	110	103	103	103	103	90	90	90	79	79	79	68	68	68	63
1	101	97	93	90	95	91	88	85	80	78	76	70	69	67	61	60	59	54
2	93	86	80	75	87	81	75	71	71	67	64	62	59	57	54	52	50	46
3	85	76	69	63	80	71	65	60	63	58	54	56	52	49	49	46	43	40
4	78	68	60	54	73	64	57	51	57	51	47	50	46	42	44	41	38	35
5	72	61	53	47	67	57	50	45	51	45	41	45	41	37	40	36	34	31
6	67	55	47	41	62	52	45	39	46	40	36	41	37	33	37	33	30	27
7	62	50	42	36	58	47	40	35	42	36	32	38	33	29	34	30	27	24
8	58	45	38	32	54	43	36	31	39	33	29	35	30	27	31	27	24	22
9	54	42	34	29	50	40	33	28	36	30	26	32	27	24	29	25	22	20
10	50	38	31	26	47	36	30	25	33	27	24	30	25	22	27	23	20	18

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	21658	21658	21658	21658
5°	24280	21797	19316	21797
10°	27824	21620	16718	21620
15°	30780	21224	14770	21224
20°	30311	20797	13464	20797
25°	27332	20232	12636	20232
30°	22585	19328	12033	19328
35°	16462	18382	11606	18382
40°	13148	17266	11367	17266
45°	11488	15972	11040	15972
50°	10798	14722	10826	14722
55°	9956	13453	10536	13453
60°	9122	12103	10091	12103
65°	8309	10892	9650	10892
70°	7544	9711	9007	9711
75°	6687	8390	7973	8390
80°	5755	6946	6425	6946
85°	5169	5169	3816	5169



TEST NUMBER: P331525-840

CATALOG NUMBER: S122DIW-S675D435U840-4F0-1E-UDD-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	127.7	2.7
10°-20°	371.4	7.9
20°-30°	539.0	11.4
30°-40°	568.8	12.1
40°-50°	503.6	10.7
50°-60°	401.9	8.5
60°-70°	273.2	5.8
70°-80°	140.0	3.0
80°-90°	35.2	0.7
90°-100°	19.9	0.4
100°-110°	73.0	1.5
110°-120°	195.0	4.1
120°-130°	322.0	6.8
130°-140°	342.4	7.3
140°-150°	318.3	6.8
150°-160°	255.9	5.4
160°-170°	164.9	3.5
170°-180°	56.8	1.2
0°-30°	1038.1	22.0
0°-40°	1606.9	34.1
0°-60°	2512.4	53.4
0°-90°	2960.8	62.9
90°-120°	287.9	6.1
90°-150°	1270.6	27.0
90°-180°	1748.0	37.1
0°-180°	4708.9	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1341	1341	1341	1341	1341	
5°	1498	1345	1192	1345	1498	150
15°	1841	1270	884	1270	1841	508
25°	1534	1136	709	1136	1534	693
35°	835	933	589	933	835	543
45°	503	700	484	700	503	396
55°	354	478	374	478	354	317
65°	218	285	253	285	218	216
75°	107	134	128	134	107	115
85°	28	28	21	28	28	31
90°	12	0	12	0	12	7
95°	19	28	19	28	19	17
105°	33	131	33	131	33	34
115°	35	248	35	248	35	89
125°	369	351	369	351	369	319
135°	448	434	448	434	448	346
145°	512	504	512	504	512	320
155°	555	555	555	555	555	256
165°	583	584	583	584	583	165
175°	594	598	594	598	594	57
180°	596	596	596	596	596	



TEST NUMBER: P331525-840

CATALOG NUMBER: S122DIW-S675D435U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4
2.5°	1403.2	1403.6	1404.5	1397.9	1397.0	1397.0	1391.3	1386.3	1380.6	1372.7	1373.5
5°	1498.1	1503.8	1505.8	1499.6	1490.4	1489.3	1480.6	1466.1	1452.7	1441.9	1434.2
7.5°	1611.3	1613.6	1608.5	1600.3	1593.5	1581.1	1564.8	1548.8	1526.4	1505.9	1490.7
10°	1697.1	1700.2	1691.4	1679.6	1669.8	1655.4	1631.6	1607.4	1578.0	1549.6	1526.9
12.5°	1762.2	1769.9	1758.7	1757.1	1740.3	1720.5	1692.2	1680.0	1638.6	1599.1	1574.8
15°	1841.4	1840.9	1842.0	1832.2	1819.8	1816.6	1786.8	1754.3	1696.1	1672.8	1632.6
17.5°	1818.6	1826.3	1830.0	1829.9	1829.6	1827.7	1818.1	1797.6	1768.4	1730.7	1684.3
20°	1764.1	1774.4	1775.9	1787.9	1794.5	1803.3	1806.9	1801.2	1783.2	1751.7	1711.5
22.5°	1680.0	1682.8	1687.7	1706.2	1720.7	1742.6	1754.1	1773.2	1766.3	1750.9	1717.3
25°	1534.2	1529.0	1547.1	1556.3	1589.8	1624.9	1650.2	1678.0	1702.7	1717.7	1707.9
27.5°	1359.1	1351.4	1378.4	1403.0	1430.3	1468.2	1507.6	1554.1	1592.8	1641.1	1657.7
30°	1211.4	1216.1	1241.9	1268.2	1309.4	1363.0	1407.3	1458.4	1513.6	1567.7	1605.3
32.5°	1052.3	1070.2	1086.4	1126.7	1163.0	1222.8	1287.8	1351.6	1420.4	1481.9	1540.1
35°	835.2	855.8	878.5	907.9	958.9	1018.1	1081.6	1167.6	1261.5	1345.5	1414.6
37.5°	703.0	699.6	712.7	733.9	775.3	823.0	896.1	981.2	1091.6	1190.3	1287.8
40°	623.8	621.7	631.0	650.6	682.1	717.1	781.0	855.8	958.4	1078.9	1195.0
42.5°	569.4	570.6	575.7	589.6	611.1	640.0	687.8	751.4	845.4	959.0	1083.6
45°	503.1	506.8	512.4	519.2	531.5	555.2	582.0	627.4	701.7	796.5	919.2
47.5°	455.6	455.7	461.4	467.3	474.6	488.0	509.9	538.3	590.7	667.9	773.4
50°	429.9	426.4	430.5	435.0	442.8	452.1	466.6	493.3	528.4	590.8	678.9
52.5°	398.6	398.7	402.4	404.1	411.1	420.3	433.5	452.1	483.8	532.6	605.1
55°	353.7	356.2	358.3	361.3	367.6	374.3	384.6	397.0	421.7	458.3	511.9
57.5°	311.3	312.1	314.3	320.1	324.1	330.2	340.0	351.2	367.4	394.5	434.7
60°	282.5	282.5	286.6	289.2	294.4	300.5	308.3	319.1	333.6	355.7	388.2
62.5°	256.1	255.7	257.3	261.6	265.5	271.2	279.0	288.2	301.7	321.4	348.2
65°	217.5	216.5	219.6	220.7	224.8	230.5	236.6	246.4	257.2	271.7	295.4
67.5°	180.5	181.7	183.3	185.3	187.5	193.5	197.6	204.6	213.7	225.7	241.8
70°	159.8	159.8	159.8	161.4	164.4	167.5	171.7	177.3	186.1	196.4	210.9
72.5°	136.7	138.4	140.0	139.1	143.0	144.8	149.8	153.0	161.4	167.9	180.8
75°	107.2	107.2	107.2	109.8	111.4	112.9	116.0	119.1	123.2	131.5	138.1
77.5°	80.0	79.8	80.3	80.9	82.6	84.4	85.3	88.2	92.0	95.7	101.5
80°	61.9	62.9	63.4	64.4	64.4	65.4	65.9	69.6	72.2	74.7	78.4
82.5°	47.9	48.1	48.2	48.4	48.8	49.4	50.7	51.9	52.8	54.9	57.8
85°	27.9	27.4	27.4	28.4	27.9	27.9	28.9	29.9	29.9	30.4	31.9
87.5°	13.0	13.0	13.4	12.9	12.9	13.2	13.1	12.6	12.9	13.2	13.5
90°	11.6	11.5	11.3	11.1	10.9	10.5	10.1	9.6	9.1	8.6	7.9
92.5°	11.6	11.5	11.4	11.3	11.2	11.0	10.8	10.5	10.3	10.0	9.6
95°	18.6	18.7	18.8	18.9	19.0	18.8	18.3	17.8	17.3	16.9	16.2
97.5°	24.7	24.6	24.5	24.4	24.3	24.0	23.7	23.3	22.9	22.5	21.0
100°	28.9	28.7	28.6	28.4	28.2	27.7	26.9	26.2	25.3	24.6	22.9
102.5°	31.0	30.7	30.5	30.2	29.9	29.3	28.3	27.3	26.3	25.2	39.0
105°	32.8	32.4	32.0	31.6	31.3	30.6	29.5	28.5	27.4	26.4	52.5
107.5°	33.7	33.3	33.0	32.6	32.2	32.5	33.6	34.7	35.7	36.9	68.3
110°	34.1	33.7	33.3	32.9	32.5	37.2	46.8	56.4	65.9	75.5	103.2



TEST NUMBER: P331525-840

CATALOG NUMBER: S122DIW-S675D435U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	34.4	34.1	33.8	33.5	33.2	50.6	85.5	120.6	155.5	190.6	197.3
115°	35.3	42.3	49.2	56.1	63.0	88.7	133.1	177.5	221.9	266.3	263.9
117.5°	144.5	167.2	189.9	212.6	235.3	252.0	262.8	273.5	284.3	295.0	293.4
120°	263.3	276.2	289.2	302.2	315.1	321.0	319.8	318.7	317.5	316.4	314.7
122.5°	328.5	331.0	333.6	336.1	338.6	339.5	338.8	338.1	337.5	336.8	334.9
125°	369.0	368.8	368.5	368.2	367.9	367.4	366.8	366.1	365.4	364.8	362.9
127.5°	394.6	394.6	394.5	394.5	394.4	393.8	392.8	391.9	390.9	389.9	388.6
130°	410.5	410.6	410.7	410.8	410.9	410.4	409.3	408.3	407.2	406.2	405.2
132.5°	426.1	426.2	426.2	426.3	426.4	426.0	425.1	424.2	423.3	422.4	421.3
135°	448.5	448.7	448.9	449.1	449.2	448.9	447.9	447.0	446.0	445.0	444.1
137.5°	468.9	469.3	469.6	469.9	470.2	469.9	469.0	468.1	467.1	466.2	465.1
140°	481.7	482.2	482.6	483.1	483.6	483.4	482.6	481.7	480.8	480.0	478.9
142.5°	494.1	494.6	495.1	495.5	496.0	495.9	495.1	494.3	493.5	492.7	491.5
145°	511.5	512.0	512.4	512.9	513.4	513.3	512.6	512.0	511.3	510.6	509.0
147.5°	526.7	527.1	527.6	528.0	528.4	528.4	527.9	527.4	526.8	526.3	524.7
150°	536.1	536.5	537.0	537.6	538.1	538.0	537.3	536.8	536.2	535.6	534.1
152.5°	544.0	544.6	545.3	545.9	546.5	546.6	546.0	545.4	544.8	544.3	542.8
155°	555.1	555.8	556.6	557.3	558.2	558.3	557.6	557.1	556.5	555.9	554.8
157.5°	565.2	565.9	566.6	567.4	568.2	568.3	567.5	566.9	566.2	565.6	564.8
160°	571.1	571.7	572.4	573.1	573.7	573.8	573.2	572.6	572.1	571.5	570.9
162.5°	575.9	576.7	577.5	578.3	579.2	579.3	578.7	577.9	577.3	576.6	576.1
165°	583.1	583.8	584.5	585.1	585.8	585.8	585.1	584.5	583.8	583.1	582.9
167.5°	587.7	588.5	589.5	590.3	591.2	591.3	590.6	590.0	589.3	588.5	588.3
170°	590.5	591.4	592.2	593.1	593.9	594.0	593.4	592.7	592.0	591.4	591.2
172.5°	592.6	593.4	594.3	595.1	596.0	596.1	595.4	594.7	594.1	593.4	593.2
175°	594.4	595.3	596.3	597.2	598.2	598.3	597.6	597.0	596.3	595.6	595.4
177.5°	595.5	596.1	596.8	597.5	598.2	598.3	597.7	597.2	596.7	596.1	596.1
180°	596.5	596.5	596.5	596.5	596.5	596.5	596.5	596.5	596.5	596.5	596.5



TEST NUMBER: P331525-840

CATALOG NUMBER: S122DIW-S675D435U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4
2.5°	1376.4	1373.1	1371.1	1363.6	1357.1	1350.5	1348.4	1349.2	1340.2	1331.5	1327.8
5°	1430.1	1419.8	1410.0	1396.0	1379.6	1361.5	1352.2	1344.9	1327.0	1307.4	1296.1
7.5°	1478.1	1463.4	1444.5	1418.3	1394.3	1365.9	1347.9	1331.9	1305.5	1277.9	1260.9
10°	1507.4	1487.2	1463.0	1431.1	1401.7	1367.2	1342.9	1318.7	1287.8	1254.8	1234.2
12.5°	1532.6	1505.4	1481.6	1440.6	1405.8	1362.6	1333.8	1299.7	1267.2	1228.0	1207.8
15°	1592.5	1542.5	1497.0	1450.7	1407.9	1347.6	1315.7	1269.7	1226.9	1178.5	1155.3
17.5°	1638.7	1582.6	1511.1	1452.1	1402.2	1335.4	1288.5	1233.6	1183.0	1127.5	1096.0
20°	1665.2	1600.6	1523.9	1453.8	1393.9	1317.7	1266.7	1210.4	1151.1	1088.7	1054.7
22.5°	1680.8	1613.1	1537.1	1447.5	1377.5	1303.2	1239.0	1177.4	1117.3	1050.1	1014.3
25°	1685.8	1623.9	1543.5	1442.4	1356.9	1272.8	1195.5	1135.7	1063.0	1000.1	948.1
27.5°	1661.2	1616.9	1539.5	1432.7	1333.0	1234.8	1148.6	1080.9	1004.1	935.8	883.5
30°	1631.1	1605.3	1530.0	1422.8	1314.0	1208.4	1113.5	1036.7	960.4	891.3	837.7
32.5°	1584.5	1578.9	1512.8	1408.8	1293.8	1175.0	1076.8	999.2	914.6	846.8	795.7
35°	1493.0	1517.7	1475.9	1377.5	1255.8	1127.4	1021.3	932.6	845.0	780.0	732.1
37.5°	1370.3	1431.7	1420.8	1331.6	1204.5	1075.7	958.5	865.8	782.2	716.7	669.6
40°	1285.7	1364.0	1375.4	1296.6	1168.2	1035.7	911.4	819.2	737.7	677.9	630.5
42.5°	1195.0	1286.6	1317.7	1254.5	1128.5	993.6	869.4	773.8	693.2	635.0	593.0
45°	1042.9	1164.1	1220.2	1184.2	1062.5	924.3	796.5	699.5	626.3	571.7	539.3
47.5°	900.7	1033.1	1108.6	1095.9	989.0	852.1	725.8	632.8	561.5	517.9	488.8
50°	800.1	936.1	1027.4	1031.6	936.1	800.6	673.8	586.1	520.7	480.0	456.3
52.5°	712.7	842.5	942.1	963.9	877.2	747.0	627.2	540.0	482.3	444.8	423.6
55°	598.5	708.3	818.6	858.9	789.2	665.5	554.7	477.9	423.7	398.0	379.4
57.5°	497.6	589.2	691.1	735.5	692.6	586.6	482.7	416.1	372.1	349.5	335.3
60°	444.3	516.5	607.2	660.4	623.3	529.0	438.2	374.8	338.7	318.6	305.2
62.5°	394.9	458.8	535.5	584.1	563.9	474.9	393.6	337.7	306.5	287.6	278.0
65°	325.8	376.4	435.7	480.5	467.1	399.5	333.1	285.1	260.3	245.4	237.6
67.5°	268.3	304.8	345.9	385.2	374.4	326.5	273.2	235.8	217.3	204.5	199.9
70°	232.0	259.8	296.4	327.9	319.1	279.9	237.6	205.7	189.8	178.8	174.2
72.5°	197.3	220.3	248.1	273.9	267.9	235.4	200.2	176.0	163.7	153.7	149.9
75°	149.0	166.5	183.5	200.6	198.9	173.7	153.1	134.5	124.7	117.0	115.4
77.5°	110.0	119.8	131.4	141.5	138.7	124.2	108.1	97.5	90.2	85.0	84.2
80°	84.0	89.7	98.0	105.1	101.6	95.3	82.5	74.7	69.6	64.4	62.4
82.5°	60.9	66.7	71.6	75.4	72.7	67.0	59.0	53.7	50.6	47.2	46.3
85°	31.9	35.0	37.2	38.2	37.2	33.5	29.9	27.9	25.2	23.7	23.2
87.5°	13.8	13.6	13.5	14.1	12.7	12.4	10.6	9.2	9.0	8.8	8.2
90°	7.1	6.4	5.6	4.6	3.6	2.5	1.5	0.4	1.5	2.5	3.6
92.5°	9.3	8.9	8.5	8.4	8.4	8.5	8.6	8.7	8.6	8.5	8.4
95°	15.5	14.8	14.1	15.3	18.6	21.7	24.8	28.1	24.8	21.7	18.6
97.5°	19.4	17.9	16.4	20.0	28.9	37.9	46.8	55.6	46.8	37.9	28.9
100°	21.3	19.7	18.1	23.8	37.0	50.1	63.2	76.4	63.2	50.1	37.0
102.5°	52.6	66.2	79.9	88.1	90.9	93.6	96.4	99.2	96.4	93.6	90.9
105°	78.7	104.9	131.1	142.7	139.9	136.9	134.1	131.2	134.1	136.9	139.9
107.5°	99.7	131.1	162.5	177.0	174.7	172.4	170.1	167.7	170.1	172.4	174.7
110°	131.0	158.6	186.4	199.2	197.2	195.2	193.2	191.2	193.2	195.2	197.2



TEST NUMBER: P331525-840

CATALOG NUMBER: S122DIW-S675D435U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	204.2	211.1	217.9	220.5	218.6	216.9	215.1	213.3	215.1	216.9	218.6
115°	261.6	259.1	256.7	254.7	253.1	251.5	249.8	248.2	249.8	251.5	253.1
117.5°	291.6	290.0	288.4	286.6	284.8	283.0	281.1	279.3	281.1	283.0	284.8
120°	313.0	311.2	309.5	307.9	306.5	305.0	303.6	302.2	303.6	305.0	306.5
122.5°	333.0	331.1	329.2	327.5	326.0	324.5	323.0	321.4	323.0	324.5	326.0
125°	361.1	359.3	357.4	355.9	354.7	353.5	352.1	350.9	352.1	353.5	354.7
127.5°	387.2	385.9	384.5	383.1	381.7	380.3	379.0	377.6	379.0	380.3	381.7
130°	404.0	403.0	401.9	400.6	399.1	397.6	396.1	394.6	396.1	397.6	399.1
132.5°	420.3	419.2	418.2	417.0	415.7	414.3	413.0	411.8	413.0	414.3	415.7
135°	443.3	442.4	441.5	440.4	438.8	437.3	435.8	434.2	435.8	437.3	438.8
137.5°	464.2	463.2	462.2	461.2	460.2	459.1	458.0	457.0	458.0	459.1	460.2
140°	477.9	476.9	475.7	474.8	474.0	473.3	472.5	471.8	472.5	473.3	474.0
142.5°	490.3	489.1	488.0	487.0	486.3	485.5	484.9	484.2	484.9	485.5	486.3
145°	507.4	505.7	504.1	503.3	503.4	503.5	503.6	503.7	503.6	503.5	503.4
147.5°	523.1	521.5	519.9	519.3	519.7	520.0	520.4	520.7	520.4	520.0	519.7
150°	532.6	531.1	529.5	529.1	529.8	530.4	531.1	531.8	531.1	530.4	529.8
152.5°	541.4	539.9	538.5	538.1	538.9	539.6	540.4	541.1	540.4	539.6	538.9
155°	553.6	552.5	551.4	551.2	552.1	552.9	553.8	554.6	553.8	552.9	552.1
157.5°	564.0	563.2	562.4	562.4	563.1	563.8	564.5	565.2	564.5	563.8	563.1
160°	570.4	569.8	569.2	569.2	569.8	570.4	570.9	571.5	570.9	570.4	569.8
162.5°	575.6	575.1	574.7	574.7	575.3	575.8	576.4	577.0	576.4	575.8	575.3
165°	582.6	582.3	582.0	582.1	582.7	583.3	583.9	584.4	583.9	583.3	582.7
167.5°	588.0	587.7	587.5	587.6	588.2	588.9	589.4	590.0	589.4	588.9	588.2
170°	591.0	590.8	590.6	590.8	591.4	591.9	592.5	593.1	592.5	591.9	591.4
172.5°	593.0	592.8	592.7	592.8	593.4	594.0	594.6	595.1	594.6	594.0	593.4
175°	595.3	595.1	594.9	595.1	595.8	596.4	597.1	597.8	597.1	596.4	595.8
177.5°	596.0	595.9	595.8	596.1	596.6	597.1	597.7	598.2	597.7	597.1	596.6
180°	596.5	596.5	596.5	596.5	596.5	596.5	596.5	596.5	596.5	596.5	596.5



TEST NUMBER: P331525-840

CATALOG NUMBER: S122DIW-S675D435U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4
2.5°	1323.6	1321.2	1312.5	1308.0	1300.5	1293.5	1289.0	1291.1	1292.7	1291.9	1290.6
5°	1285.7	1275.9	1260.9	1248.1	1238.8	1221.7	1214.6	1210.9	1207.9	1204.3	1200.6
7.5°	1240.5	1225.1	1203.7	1185.3	1167.9	1146.8	1134.8	1127.5	1120.1	1112.0	1104.8
10°	1208.4	1186.7	1164.1	1138.2	1117.6	1098.5	1081.6	1070.3	1060.0	1050.2	1042.9
12.5°	1174.6	1149.6	1121.6	1086.3	1063.6	1036.3	1033.7	1013.7	997.6	991.6	983.1
15°	1120.7	1085.7	1050.2	1008.4	990.3	965.5	950.1	934.6	920.7	910.9	908.4
17.5°	1059.6	1014.2	978.9	948.9	919.3	893.9	879.7	867.3	855.9	842.7	841.0
20°	1013.0	973.8	935.1	908.9	878.5	852.6	835.2	822.7	812.9	805.3	798.5
22.5°	968.9	925.9	890.6	861.8	831.8	811.0	797.2	785.3	777.1	768.5	762.2
25°	898.1	864.5	825.9	793.3	768.6	755.3	743.9	733.6	728.4	722.8	715.6
27.5°	836.1	798.8	762.7	737.5	715.8	703.9	695.8	688.8	684.0	680.6	676.6
30°	792.3	754.7	726.4	701.7	683.6	671.8	666.6	662.5	656.8	654.7	652.7
32.5°	750.3	716.4	692.2	670.7	653.5	645.7	641.0	637.3	632.9	630.8	626.6
35°	690.7	662.5	638.7	626.8	613.0	606.2	602.7	597.4	593.4	591.3	590.8
37.5°	634.8	610.2	594.6	579.4	573.5	569.4	564.4	560.9	559.7	559.4	558.9
40°	598.5	578.5	564.5	552.1	549.6	543.3	539.3	536.1	536.1	536.6	536.1
42.5°	565.5	547.4	535.2	524.5	521.5	517.8	513.6	513.4	514.3	516.0	514.3
45°	515.5	502.6	493.8	488.7	483.0	479.4	478.9	480.5	481.0	481.5	483.0
47.5°	469.5	461.0	453.0	447.4	444.8	444.2	443.6	446.4	448.8	449.7	452.1
50°	442.3	432.5	425.9	422.2	420.1	419.1	420.1	423.2	425.3	427.9	429.4
52.5°	411.8	404.9	400.2	397.5	396.7	397.3	397.5	401.0	404.2	405.2	406.0
55°	369.6	364.5	363.5	358.8	360.8	360.3	362.9	365.0	368.1	371.1	371.7
57.5°	327.6	323.5	320.6	321.0	321.6	324.0	326.1	329.7	333.1	336.3	336.6
60°	299.5	297.4	295.9	295.9	296.9	300.0	302.7	306.2	308.3	310.3	311.8
62.5°	274.0	271.9	270.3	271.1	273.9	275.7	278.7	280.6	282.7	284.8	285.5
65°	233.5	232.5	234.1	235.1	235.6	238.1	241.8	243.3	245.4	246.4	250.0
67.5°	196.3	196.5	196.3	197.7	200.8	201.4	204.8	208.3	208.7	210.8	213.1
70°	171.2	172.2	173.2	174.2	176.8	177.8	180.5	182.0	184.0	185.6	187.1
72.5°	148.0	148.2	149.3	149.1	151.3	153.5	155.7	157.2	159.3	161.3	162.8
75°	113.9	113.9	114.9	115.4	118.1	120.7	120.1	121.2	123.2	125.2	126.3
77.5°	83.2	82.1	83.2	83.7	84.5	86.7	87.2	88.6	90.9	90.2	91.4
80°	63.4	61.9	63.4	63.9	63.9	66.6	66.6	67.6	69.1	67.6	69.1
82.5°	45.2	44.5	45.6	45.7	46.6	46.7	47.6	47.8	49.3	48.6	49.3
85°	22.7	22.2	22.7	22.2	22.7	23.2	23.2	22.7	22.7	23.7	22.2
87.5°	8.0	7.7	7.5	7.6	7.4	7.1	6.8	6.9	7.0	6.3	6.3
90°	4.6	5.6	6.4	7.1	7.9	8.6	9.1	9.6	10.1	10.5	10.9
92.5°	8.4	8.5	8.9	9.3	9.6	10.0	10.3	10.5	10.8	11.0	11.2
95°	15.3	14.1	14.8	15.5	16.2	16.9	17.3	17.8	18.3	18.8	19.0
97.5°	20.0	16.4	17.9	19.4	21.0	22.5	22.9	23.3	23.7	24.0	24.3
100°	23.8	18.1	19.7	21.3	22.9	24.6	25.3	26.2	26.9	27.7	28.2
102.5°	88.1	79.9	66.2	52.6	39.0	25.2	26.3	27.3	28.3	29.3	29.9
105°	142.7	131.1	104.9	78.7	52.5	26.4	27.4	28.5	29.5	30.6	31.3
107.5°	177.0	162.5	131.1	99.7	68.3	36.9	35.7	34.7	33.6	32.5	32.2
110°	199.2	186.4	158.6	131.0	103.2	75.5	65.9	56.4	46.8	37.2	32.5



TEST NUMBER: P331525-840

CATALOG NUMBER: S122DIW-S675D435U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	220.5	217.9	211.1	204.2	197.3	190.6	155.5	120.6	85.5	50.6	33.2
115°	254.7	256.7	259.1	261.6	263.9	266.3	221.9	177.5	133.1	88.7	63.0
117.5°	286.6	288.4	290.0	291.6	293.4	295.0	284.3	273.5	262.8	252.0	235.3
120°	307.9	309.5	311.2	313.0	314.7	316.4	317.5	318.7	319.8	321.0	315.1
122.5°	327.5	329.2	331.1	333.0	334.9	336.8	337.5	338.1	338.8	339.5	338.6
125°	355.9	357.4	359.3	361.1	362.9	364.8	365.4	366.1	366.8	367.4	367.9
127.5°	383.1	384.5	385.9	387.2	388.6	389.9	390.9	391.9	392.8	393.8	394.4
130°	400.6	401.9	403.0	404.0	405.2	406.2	407.2	408.3	409.3	410.4	410.9
132.5°	417.0	418.2	419.2	420.3	421.3	422.4	423.3	424.2	425.1	426.0	426.4
135°	440.4	441.5	442.4	443.3	444.1	445.0	446.0	447.0	447.9	448.9	449.2
137.5°	461.2	462.2	463.2	464.2	465.1	466.2	467.1	468.1	469.0	469.9	470.2
140°	474.8	475.7	476.9	477.9	478.9	480.0	480.8	481.7	482.6	483.4	483.6
142.5°	487.0	488.0	489.1	490.3	491.5	492.7	493.5	494.3	495.1	495.9	496.0
145°	503.3	504.1	505.7	507.4	509.0	510.6	511.3	512.0	512.6	513.3	513.4
147.5°	519.3	519.9	521.5	523.1	524.7	526.3	526.8	527.4	527.9	528.4	528.4
150°	529.1	529.5	531.1	532.6	534.1	535.6	536.2	536.8	537.3	538.0	538.1
152.5°	538.1	538.5	539.9	541.4	542.8	544.3	544.8	545.4	546.0	546.6	546.5
155°	551.2	551.4	552.5	553.6	554.8	555.9	556.5	557.1	557.6	558.3	558.2
157.5°	562.4	562.4	563.2	564.0	564.8	565.6	566.2	566.9	567.5	568.3	568.2
160°	569.2	569.2	569.8	570.4	570.9	571.5	572.1	572.6	573.2	573.8	573.7
162.5°	574.7	574.7	575.1	575.6	576.1	576.6	577.3	577.9	578.7	579.3	579.2
165°	582.1	582.0	582.3	582.6	582.9	583.1	583.8	584.5	585.1	585.8	585.8
167.5°	587.6	587.5	587.7	588.0	588.3	588.5	589.3	590.0	590.6	591.3	591.2
170°	590.8	590.6	590.8	591.0	591.2	591.4	592.0	592.7	593.4	594.0	593.9
172.5°	592.8	592.7	592.8	593.0	593.2	593.4	594.1	594.7	595.4	596.1	596.0
175°	595.1	594.9	595.1	595.3	595.4	595.6	596.3	597.0	597.6	598.3	598.2
177.5°	596.1	595.8	595.9	596.0	596.1	596.1	596.7	597.2	597.7	598.3	598.2
180°	596.5	596.5	596.5	596.5	596.5	596.5	596.5	596.5	596.5	596.5	596.5



TEST NUMBER: P331525-840

CATALOG NUMBER: S122DIW-S675D435U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4
2.5°	1286.6	1285.7	1285.7	1282.0	1285.7	1285.7	1286.6	1290.6	1291.9	1292.7	1291.1
5°	1193.5	1191.8	1189.3	1191.8	1189.3	1191.8	1193.5	1200.6	1204.3	1207.9	1210.9
7.5°	1101.4	1095.2	1094.3	1088.1	1094.3	1095.2	1101.4	1104.8	1112.0	1120.1	1127.5
10°	1034.1	1030.0	1029.5	1019.7	1029.5	1030.0	1034.1	1042.9	1050.2	1060.0	1070.3
12.5°	983.0	973.1	975.0	969.4	975.0	973.1	983.0	983.1	991.6	997.6	1013.7
15°	894.4	894.4	892.3	883.6	892.3	894.4	894.4	908.4	910.9	920.7	934.6
17.5°	830.8	829.8	824.9	827.3	824.9	829.8	830.8	841.0	842.7	855.9	867.3
20°	792.8	789.8	783.6	783.6	783.6	789.8	792.8	798.5	805.3	812.9	822.7
22.5°	757.0	756.8	750.2	752.2	750.2	756.8	757.0	762.2	768.5	777.1	785.3
25°	715.0	710.9	707.8	709.3	707.8	710.9	715.0	715.6	722.8	728.4	733.6
27.5°	675.2	673.0	672.8	668.5	672.8	673.0	675.2	676.6	680.6	684.0	688.8
30°	652.2	647.0	648.0	645.4	648.0	647.0	652.2	652.7	654.7	656.8	662.5
32.5°	625.7	623.9	622.9	620.7	622.9	623.9	625.7	626.6	630.8	632.9	637.3
35°	589.8	590.3	587.7	588.8	587.7	590.3	589.8	590.8	591.3	593.4	597.4
37.5°	558.4	560.0	558.8	559.1	558.8	560.0	558.4	558.9	559.4	559.7	560.9
40°	537.7	537.7	537.7	539.3	537.7	537.7	537.7	536.1	536.6	536.1	536.1
42.5°	517.9	517.1	516.2	516.1	516.2	517.1	517.9	514.3	516.0	514.3	513.4
45°	484.0	485.6	486.1	483.5	486.1	485.6	484.0	483.0	481.5	481.0	480.5
47.5°	453.4	453.6	453.4	455.8	453.4	453.6	453.4	452.1	449.7	448.8	446.4
50°	432.0	431.0	432.0	431.0	432.0	431.0	432.0	429.4	427.9	425.3	423.2
52.5°	409.3	409.5	408.9	408.7	408.9	409.5	409.3	406.0	405.2	404.2	401.0
55°	373.8	374.8	374.3	374.3	374.3	374.8	373.8	371.7	371.1	368.1	365.0
57.5°	337.0	337.9	338.6	336.3	338.6	337.9	337.0	336.6	336.3	333.1	329.7
60°	311.3	314.0	313.5	312.5	313.5	314.0	311.3	311.8	310.3	308.3	306.2
62.5°	287.9	288.8	288.7	288.5	288.7	288.8	287.9	285.5	284.8	282.7	280.6
65°	251.6	252.6	251.1	252.6	251.1	252.6	251.6	250.0	246.4	245.4	243.3
67.5°	212.5	212.8	214.0	214.7	214.0	212.8	212.5	213.1	210.8	208.7	208.3
70°	188.1	187.6	189.1	190.8	189.1	187.6	188.1	187.1	185.6	184.0	182.0
72.5°	162.6	163.7	163.2	164.3	163.2	163.7	162.6	162.8	161.3	159.3	157.2
75°	125.2	126.8	126.3	127.8	126.3	126.8	125.2	126.3	125.2	123.2	121.2
77.5°	90.5	90.7	90.5	91.4	90.5	90.7	90.5	91.4	90.2	90.9	88.6
80°	69.1	68.1	67.1	69.1	67.1	68.1	69.1	69.1	67.6	69.1	67.6
82.5°	48.1	48.7	47.7	47.7	47.7	48.7	48.1	49.3	48.6	49.3	47.8
85°	22.2	21.6	20.6	20.6	20.6	21.6	22.2	22.2	23.7	22.7	22.7
87.5°	6.4	6.0	6.0	5.7	6.0	6.0	6.4	6.3	6.3	7.0	6.9
90°	11.1	11.3	11.5	11.6	11.5	11.3	11.1	10.9	10.5	10.1	9.6
92.5°	11.3	11.4	11.5	11.6	11.5	11.4	11.3	11.2	11.0	10.8	10.5
95°	18.9	18.8	18.7	18.6	18.7	18.8	18.9	19.0	18.8	18.3	17.8
97.5°	24.4	24.5	24.6	24.7	24.6	24.5	24.4	24.3	24.0	23.7	23.3
100°	28.4	28.6	28.7	28.9	28.7	28.6	28.4	28.2	27.7	26.9	26.2
102.5°	30.2	30.5	30.7	31.0	30.7	30.5	30.2	29.9	29.3	28.3	27.3
105°	31.6	32.0	32.4	32.8	32.4	32.0	31.6	31.3	30.6	29.5	28.5
107.5°	32.6	33.0	33.3	33.7	33.3	33.0	32.6	32.2	32.5	33.6	34.7
110°	32.9	33.3	33.7	34.1	33.7	33.3	32.9	32.5	37.2	46.8	56.4



TEST NUMBER: P331525-840

CATALOG NUMBER: S122DIW-S675D435U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	33.5	33.8	34.1	34.4	34.1	33.8	33.5	33.2	50.6	85.5	120.6
115°	56.1	49.2	42.3	35.3	42.3	49.2	56.1	63.0	88.7	133.1	177.5
117.5°	212.6	189.9	167.2	144.5	167.2	189.9	212.6	235.3	252.0	262.8	273.5
120°	302.2	289.2	276.2	263.3	276.2	289.2	302.2	315.1	321.0	319.8	318.7
122.5°	336.1	333.6	331.0	328.5	331.0	333.6	336.1	338.6	339.5	338.8	338.1
125°	368.2	368.5	368.8	369.0	368.8	368.5	368.2	367.9	367.4	366.8	366.1
127.5°	394.5	394.5	394.6	394.6	394.6	394.5	394.5	394.4	393.8	392.8	391.9
130°	410.8	410.7	410.6	410.5	410.6	410.7	410.8	410.9	410.4	409.3	408.3
132.5°	426.3	426.2	426.2	426.1	426.2	426.2	426.3	426.4	426.0	425.1	424.2
135°	449.1	448.9	448.7	448.5	448.7	448.9	449.1	449.2	448.9	447.9	447.0
137.5°	469.9	469.6	469.3	468.9	469.3	469.6	469.9	470.2	469.9	469.0	468.1
140°	483.1	482.6	482.2	481.7	482.2	482.6	483.1	483.6	483.4	482.6	481.7
142.5°	495.5	495.1	494.6	494.1	494.6	495.1	495.5	496.0	495.9	495.1	494.3
145°	512.9	512.4	512.0	511.5	512.0	512.4	512.9	513.4	513.3	512.6	512.0
147.5°	528.0	527.6	527.1	526.7	527.1	527.6	528.0	528.4	528.4	527.9	527.4
150°	537.6	537.0	536.5	536.1	536.5	537.0	537.6	538.1	538.0	537.3	536.8
152.5°	545.9	545.3	544.6	544.0	544.6	545.3	545.9	546.5	546.6	546.0	545.4
155°	557.3	556.6	555.8	555.1	555.8	556.6	557.3	558.2	558.3	557.6	557.1
157.5°	567.4	566.6	565.9	565.2	565.9	566.6	567.4	568.2	568.3	567.5	566.9
160°	573.1	572.4	571.7	571.1	571.7	572.4	573.1	573.7	573.8	573.2	572.6
162.5°	578.3	577.5	576.7	575.9	576.7	577.5	578.3	579.2	579.3	578.7	577.9
165°	585.1	584.5	583.8	583.1	583.8	584.5	585.1	585.8	585.8	585.1	584.5
167.5°	590.3	589.5	588.5	587.7	588.5	589.5	590.3	591.2	591.3	590.6	590.0
170°	593.1	592.2	591.4	590.5	591.4	592.2	593.1	593.9	594.0	593.4	592.7
172.5°	595.1	594.3	593.4	592.6	593.4	594.3	595.1	596.0	596.1	595.4	594.7
175°	597.2	596.3	595.3	594.4	595.3	596.3	597.2	598.2	598.3	597.6	597.0
177.5°	597.5	596.8	596.1	595.5	596.1	596.8	597.5	598.2	598.3	597.7	597.2
180°	596.5	596.5	596.5	596.5	596.5	596.5	596.5	596.5	596.5	596.5	596.5



TEST NUMBER: P331525-840

CATALOG NUMBER: S122DIW-S675D435U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4
2.5°	1289.0	1293.5	1300.5	1308.0	1312.5	1321.2	1323.6	1327.8	1331.5	1340.2	1349.2
5°	1214.6	1221.7	1238.8	1248.1	1260.9	1275.9	1285.7	1296.1	1307.4	1327.0	1344.9
7.5°	1134.8	1146.8	1167.9	1185.3	1203.7	1225.1	1240.5	1260.9	1277.9	1305.5	1331.9
10°	1081.6	1098.5	1117.6	1138.2	1164.1	1186.7	1208.4	1234.2	1254.8	1287.8	1318.7
12.5°	1033.7	1036.3	1063.6	1086.3	1121.6	1149.6	1174.6	1207.8	1228.0	1267.2	1299.7
15°	950.1	965.5	990.3	1008.4	1050.2	1085.7	1120.7	1155.3	1178.5	1226.9	1269.7
17.5°	879.7	893.9	919.3	948.9	978.9	1014.2	1059.6	1096.0	1127.5	1183.0	1233.6
20°	835.2	852.6	878.5	908.9	935.1	973.8	1013.0	1054.7	1088.7	1151.1	1210.4
22.5°	797.2	811.0	831.8	861.8	890.6	925.9	968.9	1014.3	1050.1	1117.3	1177.4
25°	743.9	755.3	768.6	793.3	825.9	864.5	898.1	948.1	1000.1	1063.0	1135.7
27.5°	695.8	703.9	715.8	737.5	762.7	798.8	836.1	883.5	935.8	1004.1	1080.9
30°	666.6	671.8	683.6	701.7	726.4	754.7	792.3	837.7	891.3	960.4	1036.7
32.5°	641.0	645.7	653.5	670.7	692.2	716.4	750.3	795.7	846.8	914.6	999.2
35°	602.7	606.2	613.0	626.8	638.7	662.5	690.7	732.1	780.0	845.0	932.6
37.5°	564.4	569.4	573.5	579.4	594.6	610.2	634.8	669.6	716.7	782.2	865.8
40°	539.3	543.3	549.6	552.1	564.5	578.5	598.5	630.5	677.9	737.7	819.2
42.5°	513.6	517.8	521.5	524.5	535.2	547.4	565.5	593.0	635.0	693.2	773.8
45°	478.9	479.4	483.0	488.7	493.8	502.6	515.5	539.3	571.7	626.3	699.5
47.5°	443.6	444.2	444.8	447.4	453.0	461.0	469.5	488.8	517.9	561.5	632.8
50°	420.1	419.1	420.1	422.2	425.9	432.5	442.3	456.3	480.0	520.7	586.1
52.5°	397.5	397.3	396.7	397.5	400.2	404.9	411.8	423.6	444.8	482.3	540.0
55°	362.9	360.3	360.8	358.8	363.5	364.5	369.6	379.4	398.0	423.7	477.9
57.5°	326.1	324.0	321.6	321.0	320.6	323.5	327.6	335.3	349.5	372.1	416.1
60°	302.7	300.0	296.9	295.9	295.9	297.4	299.5	305.2	318.6	338.7	374.8
62.5°	278.7	275.7	273.9	271.1	270.3	271.9	274.0	278.0	287.6	306.5	337.7
65°	241.8	238.1	235.6	235.1	234.1	232.5	233.5	237.6	245.4	260.3	285.1
67.5°	204.8	201.4	200.8	197.7	196.3	196.5	196.3	199.9	204.5	217.3	235.8
70°	180.5	177.8	176.8	174.2	173.2	172.2	171.2	174.2	178.8	189.8	205.7
72.5°	155.7	153.5	151.3	149.1	149.3	148.2	148.0	149.9	153.7	163.7	176.0
75°	120.1	120.7	118.1	115.4	114.9	113.9	113.9	115.4	117.0	124.7	134.5
77.5°	87.2	86.7	84.5	83.7	83.2	82.1	83.2	84.2	85.0	90.2	97.5
80°	66.6	66.6	63.9	63.9	63.4	61.9	63.4	62.4	64.4	69.6	74.7
82.5°	47.6	46.7	46.6	45.7	45.6	44.5	45.2	46.3	47.2	50.6	53.7
85°	23.2	23.2	22.7	22.2	22.7	22.2	22.7	23.2	23.7	25.2	27.9
87.5°	6.8	7.1	7.4	7.6	7.5	7.7	8.0	8.2	8.8	9.0	9.2
90°	9.1	8.6	7.9	7.1	6.4	5.6	4.6	3.6	2.5	1.5	0.4
92.5°	10.3	10.0	9.6	9.3	8.9	8.5	8.4	8.4	8.5	8.6	8.7
95°	17.3	16.9	16.2	15.5	14.8	14.1	15.3	18.6	21.7	24.8	28.1
97.5°	22.9	22.5	21.0	19.4	17.9	16.4	20.0	28.9	37.9	46.8	55.6
100°	25.3	24.6	22.9	21.3	19.7	18.1	23.8	37.0	50.1	63.2	76.4
102.5°	26.3	25.2	39.0	52.6	66.2	79.9	88.1	90.9	93.6	96.4	99.2
105°	27.4	26.4	52.5	78.7	104.9	131.1	142.7	139.9	136.9	134.1	131.2
107.5°	35.7	36.9	68.3	99.7	131.1	162.5	177.0	174.7	172.4	170.1	167.7
110°	65.9	75.5	103.2	131.0	158.6	186.4	199.2	197.2	195.2	193.2	191.2



TEST NUMBER: P331525-840

CATALOG NUMBER: S122DIW-S675D435U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	155.5	190.6	197.3	204.2	211.1	217.9	220.5	218.6	216.9	215.1	213.3
115°	221.9	266.3	263.9	261.6	259.1	256.7	254.7	253.1	251.5	249.8	248.2
117.5°	284.3	295.0	293.4	291.6	290.0	288.4	286.6	284.8	283.0	281.1	279.3
120°	317.5	316.4	314.7	313.0	311.2	309.5	307.9	306.5	305.0	303.6	302.2
122.5°	337.5	336.8	334.9	333.0	331.1	329.2	327.5	326.0	324.5	323.0	321.4
125°	365.4	364.8	362.9	361.1	359.3	357.4	355.9	354.7	353.5	352.1	350.9
127.5°	390.9	389.9	388.6	387.2	385.9	384.5	383.1	381.7	380.3	379.0	377.6
130°	407.2	406.2	405.2	404.0	403.0	401.9	400.6	399.1	397.6	396.1	394.6
132.5°	423.3	422.4	421.3	420.3	419.2	418.2	417.0	415.7	414.3	413.0	411.8
135°	446.0	445.0	444.1	443.3	442.4	441.5	440.4	438.8	437.3	435.8	434.2
137.5°	467.1	466.2	465.1	464.2	463.2	462.2	461.2	460.2	459.1	458.0	457.0
140°	480.8	480.0	478.9	477.9	476.9	475.7	474.8	474.0	473.3	472.5	471.8
142.5°	493.5	492.7	491.5	490.3	489.1	488.0	487.0	486.3	485.5	484.9	484.2
145°	511.3	510.6	509.0	507.4	505.7	504.1	503.3	503.4	503.5	503.6	503.7
147.5°	526.8	526.3	524.7	523.1	521.5	519.9	519.3	519.7	520.0	520.4	520.7
150°	536.2	535.6	534.1	532.6	531.1	529.5	529.1	529.8	530.4	531.1	531.8
152.5°	544.8	544.3	542.8	541.4	539.9	538.5	538.1	538.9	539.6	540.4	541.1
155°	556.5	555.9	554.8	553.6	552.5	551.4	551.2	552.1	552.9	553.8	554.6
157.5°	566.2	565.6	564.8	564.0	563.2	562.4	562.4	563.1	563.8	564.5	565.2
160°	572.1	571.5	570.9	570.4	569.8	569.2	569.2	569.8	570.4	570.9	571.5
162.5°	577.3	576.6	576.1	575.6	575.1	574.7	574.7	575.3	575.8	576.4	577.0
165°	583.8	583.1	582.9	582.6	582.3	582.0	582.1	582.7	583.3	583.9	584.4
167.5°	589.3	588.5	588.3	588.0	587.7	587.5	587.6	588.2	588.9	589.4	590.0
170°	592.0	591.4	591.2	591.0	590.8	590.6	590.8	591.4	591.9	592.5	593.1
172.5°	594.1	593.4	593.2	593.0	592.8	592.7	592.8	593.4	594.0	594.6	595.1
175°	596.3	595.6	595.4	595.3	595.1	594.9	595.1	595.8	596.4	597.1	597.8
177.5°	596.7	596.1	596.1	596.0	595.9	595.8	596.1	596.6	597.1	597.7	598.2
180°	596.5	596.5	596.5	596.5	596.5	596.5	596.5	596.5	596.5	596.5	596.5



TEST NUMBER: P331525-840

CATALOG NUMBER: S122DIW-S675D435U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4
2.5°	1348.4	1350.5	1357.1	1363.6	1371.1	1373.1	1376.4	1373.5	1372.7	1380.6	1386.3
5°	1352.2	1361.5	1379.6	1396.0	1410.0	1419.8	1430.1	1434.2	1441.9	1452.7	1466.1
7.5°	1347.9	1365.9	1394.3	1418.3	1444.5	1463.4	1478.1	1490.7	1505.9	1526.4	1548.8
10°	1342.9	1367.2	1401.7	1431.1	1463.0	1487.2	1507.4	1526.9	1549.6	1578.0	1607.4
12.5°	1333.8	1362.6	1405.8	1440.6	1481.6	1505.4	1532.6	1574.8	1599.1	1638.6	1680.0
15°	1315.7	1347.6	1407.9	1450.7	1497.0	1542.5	1592.5	1632.6	1672.8	1696.1	1754.3
17.5°	1288.5	1335.4	1402.2	1452.1	1511.1	1582.6	1638.7	1684.3	1730.7	1768.4	1797.6
20°	1266.7	1317.7	1393.9	1453.8	1523.9	1600.6	1665.2	1711.5	1751.7	1783.2	1801.2
22.5°	1239.0	1303.2	1377.5	1447.5	1537.1	1613.1	1680.8	1717.3	1750.9	1766.3	1773.2
25°	1195.5	1272.8	1356.9	1442.4	1543.5	1623.9	1685.8	1707.9	1717.7	1702.7	1678.0
27.5°	1148.6	1234.8	1333.0	1432.7	1539.5	1616.9	1661.2	1657.7	1641.1	1592.8	1554.1
30°	1113.5	1208.4	1314.0	1422.8	1530.0	1605.3	1631.1	1605.3	1567.7	1513.6	1458.4
32.5°	1076.8	1175.0	1293.8	1408.8	1512.8	1578.9	1584.5	1540.1	1481.9	1420.4	1351.6
35°	1021.3	1127.4	1255.8	1377.5	1475.9	1517.7	1493.0	1414.6	1345.5	1261.5	1167.6
37.5°	958.5	1075.7	1204.5	1331.6	1420.8	1431.7	1370.3	1287.8	1190.3	1091.6	981.2
40°	911.4	1035.7	1168.2	1296.6	1375.4	1364.0	1285.7	1195.0	1078.9	958.4	855.8
42.5°	869.4	993.6	1128.5	1254.5	1317.7	1286.6	1195.0	1083.6	959.0	845.4	751.4
45°	796.5	924.3	1062.5	1184.2	1220.2	1164.1	1042.9	919.2	796.5	701.7	627.4
47.5°	725.8	852.1	989.0	1095.9	1108.6	1033.1	900.7	773.4	667.9	590.7	538.3
50°	673.8	800.6	936.1	1031.6	1027.4	936.1	800.1	678.9	590.8	528.4	493.3
52.5°	627.2	747.0	877.2	963.9	942.1	842.5	712.7	605.1	532.6	483.8	452.1
55°	554.7	665.5	789.2	858.9	818.6	708.3	598.5	511.9	458.3	421.7	397.0
57.5°	482.7	586.6	692.6	735.5	691.1	589.2	497.6	434.7	394.5	367.4	351.2
60°	438.2	529.0	623.3	660.4	607.2	516.5	444.3	388.2	355.7	333.6	319.1
62.5°	393.6	474.9	563.9	584.1	535.5	458.8	394.9	348.2	321.4	301.7	288.2
65°	333.1	399.5	467.1	480.5	435.7	376.4	325.8	295.4	271.7	257.2	246.4
67.5°	273.2	326.5	374.4	385.2	345.9	304.8	268.3	241.8	225.7	213.7	204.6
70°	237.6	279.9	319.1	327.9	296.4	259.8	232.0	210.9	196.4	186.1	177.3
72.5°	200.2	235.4	267.9	273.9	248.1	220.3	197.3	180.8	167.9	161.4	153.0
75°	153.1	173.7	198.9	200.6	183.5	166.5	149.0	138.1	131.5	123.2	119.1
77.5°	108.1	124.2	138.7	141.5	131.4	119.8	110.0	101.5	95.7	92.0	88.2
80°	82.5	95.3	101.6	105.1	98.0	89.7	84.0	78.4	74.7	72.2	69.6
82.5°	59.0	67.0	72.7	75.4	71.6	66.7	60.9	57.8	54.9	52.8	51.9
85°	29.9	33.5	37.2	38.2	37.2	35.0	31.9	31.9	30.4	29.9	29.9
87.5°	10.6	12.4	12.7	14.1	13.5	13.6	13.8	13.5	13.2	12.9	12.6
90°	1.5	2.5	3.6	4.6	5.6	6.4	7.1	7.9	8.6	9.1	9.6
92.5°	8.6	8.5	8.4	8.4	8.5	8.9	9.3	9.6	10.0	10.3	10.5
95°	24.8	21.7	18.6	15.3	14.1	14.8	15.5	16.2	16.9	17.3	17.8
97.5°	46.8	37.9	28.9	20.0	16.4	17.9	19.4	21.0	22.5	22.9	23.3
100°	63.2	50.1	37.0	23.8	18.1	19.7	21.3	22.9	24.6	25.3	26.2
102.5°	96.4	93.6	90.9	88.1	79.9	66.2	52.6	39.0	25.2	26.3	27.3
105°	134.1	136.9	139.9	142.7	131.1	104.9	78.7	52.5	26.4	27.4	28.5
107.5°	170.1	172.4	174.7	177.0	162.5	131.1	99.7	68.3	36.9	35.7	34.7
110°	193.2	195.2	197.2	199.2	186.4	158.6	131.0	103.2	75.5	65.9	56.4



TEST NUMBER: P331525-840

CATALOG NUMBER: S122DIW-S675D435U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	215.1	216.9	218.6	220.5	217.9	211.1	204.2	197.3	190.6	155.5	120.6
115°	249.8	251.5	253.1	254.7	256.7	259.1	261.6	263.9	266.3	221.9	177.5
117.5°	281.1	283.0	284.8	286.6	288.4	290.0	291.6	293.4	295.0	284.3	273.5
120°	303.6	305.0	306.5	307.9	309.5	311.2	313.0	314.7	316.4	317.5	318.7
122.5°	323.0	324.5	326.0	327.5	329.2	331.1	333.0	334.9	336.8	337.5	338.1
125°	352.1	353.5	354.7	355.9	357.4	359.3	361.1	362.9	364.8	365.4	366.1
127.5°	379.0	380.3	381.7	383.1	384.5	385.9	387.2	388.6	389.9	390.9	391.9
130°	396.1	397.6	399.1	400.6	401.9	403.0	404.0	405.2	406.2	407.2	408.3
132.5°	413.0	414.3	415.7	417.0	418.2	419.2	420.3	421.3	422.4	423.3	424.2
135°	435.8	437.3	438.8	440.4	441.5	442.4	443.3	444.1	445.0	446.0	447.0
137.5°	458.0	459.1	460.2	461.2	462.2	463.2	464.2	465.1	466.2	467.1	468.1
140°	472.5	473.3	474.0	474.8	475.7	476.9	477.9	478.9	480.0	480.8	481.7
142.5°	484.9	485.5	486.3	487.0	488.0	489.1	490.3	491.5	492.7	493.5	494.3
145°	503.6	503.5	503.4	503.3	504.1	505.7	507.4	509.0	510.6	511.3	512.0
147.5°	520.4	520.0	519.7	519.3	519.9	521.5	523.1	524.7	526.3	526.8	527.4
150°	531.1	530.4	529.8	529.1	529.5	531.1	532.6	534.1	535.6	536.2	536.8
152.5°	540.4	539.6	538.9	538.1	538.5	539.9	541.4	542.8	544.3	544.8	545.4
155°	553.8	552.9	552.1	551.2	551.4	552.5	553.6	554.8	555.9	556.5	557.1
157.5°	564.5	563.8	563.1	562.4	562.4	563.2	564.0	564.8	565.6	566.2	566.9
160°	570.9	570.4	569.8	569.2	569.2	569.8	570.4	570.9	571.5	572.1	572.6
162.5°	576.4	575.8	575.3	574.7	574.7	575.1	575.6	576.1	576.6	577.3	577.9
165°	583.9	583.3	582.7	582.1	582.0	582.3	582.6	582.9	583.1	583.8	584.5
167.5°	589.4	588.9	588.2	587.6	587.5	587.7	588.0	588.3	588.5	589.3	590.0
170°	592.5	591.9	591.4	590.8	590.6	590.8	591.0	591.2	591.4	592.0	592.7
172.5°	594.6	594.0	593.4	592.8	592.7	592.8	593.0	593.2	593.4	594.1	594.7
175°	597.1	596.4	595.8	595.1	594.9	595.1	595.3	595.4	595.6	596.3	597.0
177.5°	597.7	597.1	596.6	596.1	595.8	595.9	596.0	596.1	596.1	596.7	597.2
180°	596.5	596.5	596.5	596.5	596.5	596.5	596.5	596.5	596.5	596.5	596.5



TEST NUMBER: P331525-840

CATALOG NUMBER: S122DIW-S675D435U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4
2.5°	1391.3	1397.0	1397.0	1397.9	1404.5	1403.6	1403.2
5°	1480.6	1489.3	1490.4	1499.6	1505.8	1503.8	1498.1
7.5°	1564.8	1581.1	1593.5	1600.3	1608.5	1613.6	1611.3
10°	1631.6	1655.4	1669.8	1679.6	1691.4	1700.2	1697.1
12.5°	1692.2	1720.5	1740.3	1757.1	1758.7	1769.9	1762.2
15°	1786.8	1816.6	1819.8	1832.2	1842.0	1840.9	1841.4
17.5°	1818.1	1827.7	1829.6	1829.9	1830.0	1826.3	1818.6
20°	1806.9	1803.3	1794.5	1787.9	1775.9	1774.4	1764.1
22.5°	1754.1	1742.6	1720.7	1706.2	1687.7	1682.8	1680.0
25°	1650.2	1624.9	1589.8	1556.3	1547.1	1529.0	1534.2
27.5°	1507.6	1468.2	1430.3	1403.0	1378.4	1351.4	1359.1
30°	1407.3	1363.0	1309.4	1268.2	1241.9	1216.1	1211.4
32.5°	1287.8	1222.8	1163.0	1126.7	1086.4	1070.2	1052.3
35°	1081.6	1018.1	958.9	907.9	878.5	855.8	835.2
37.5°	896.1	823.0	775.3	733.9	712.7	699.6	703.0
40°	781.0	717.1	682.1	650.6	631.0	621.7	623.8
42.5°	687.8	640.0	611.1	589.6	575.7	570.6	569.4
45°	582.0	555.2	531.5	519.2	512.4	506.8	503.1
47.5°	509.9	488.0	474.6	467.3	461.4	455.7	455.6
50°	466.6	452.1	442.8	435.0	430.5	426.4	429.9
52.5°	433.5	420.3	411.1	404.1	402.4	398.7	398.6
55°	384.6	374.3	367.6	361.3	358.3	356.2	353.7
57.5°	340.0	330.2	324.1	320.1	314.3	312.1	311.3
60°	308.3	300.5	294.4	289.2	286.6	282.5	282.5
62.5°	279.0	271.2	265.5	261.6	257.3	255.7	256.1
65°	236.6	230.5	224.8	220.7	219.6	216.5	217.5
67.5°	197.6	193.5	187.5	185.3	183.3	181.7	180.5
70°	171.7	167.5	164.4	161.4	159.8	159.8	159.8
72.5°	149.8	144.8	143.0	139.1	140.0	138.4	136.7
75°	116.0	112.9	111.4	109.8	107.2	107.2	107.2
77.5°	85.3	84.4	82.6	80.9	80.3	79.8	80.0
80°	65.9	65.4	64.4	64.4	63.4	62.9	61.9
82.5°	50.7	49.4	48.8	48.4	48.2	48.1	47.9
85°	28.9	27.9	27.9	28.4	27.4	27.4	27.9
87.5°	13.1	13.2	12.9	12.9	13.4	13.0	13.0
90°	10.1	10.5	10.9	11.1	11.3	11.5	11.6
92.5°	10.8	11.0	11.2	11.3	11.4	11.5	11.6
95°	18.3	18.8	19.0	18.9	18.8	18.7	18.6
97.5°	23.7	24.0	24.3	24.4	24.5	24.6	24.7
100°	26.9	27.7	28.2	28.4	28.6	28.7	28.9
102.5°	28.3	29.3	29.9	30.2	30.5	30.7	31.0
105°	29.5	30.6	31.3	31.6	32.0	32.4	32.8
107.5°	33.6	32.5	32.2	32.6	33.0	33.3	33.7
110°	46.8	37.2	32.5	32.9	33.3	33.7	34.1



TEST NUMBER: P331525-840

CATALOG NUMBER: S122DIW-S675D435U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	85.5	50.6	33.2	33.5	33.8	34.1	34.4
115°	133.1	88.7	63.0	56.1	49.2	42.3	35.3
117.5°	262.8	252.0	235.3	212.6	189.9	167.2	144.5
120°	319.8	321.0	315.1	302.2	289.2	276.2	263.3
122.5°	338.8	339.5	338.6	336.1	333.6	331.0	328.5
125°	366.8	367.4	367.9	368.2	368.5	368.8	369.0
127.5°	392.8	393.8	394.4	394.5	394.5	394.6	394.6
130°	409.3	410.4	410.9	410.8	410.7	410.6	410.5
132.5°	425.1	426.0	426.4	426.3	426.2	426.2	426.1
135°	447.9	448.9	449.2	449.1	448.9	448.7	448.5
137.5°	469.0	469.9	470.2	469.9	469.6	469.3	468.9
140°	482.6	483.4	483.6	483.1	482.6	482.2	481.7
142.5°	495.1	495.9	496.0	495.5	495.1	494.6	494.1
145°	512.6	513.3	513.4	512.9	512.4	512.0	511.5
147.5°	527.9	528.4	528.4	528.0	527.6	527.1	526.7
150°	537.3	538.0	538.1	537.6	537.0	536.5	536.1
152.5°	546.0	546.6	546.5	545.9	545.3	544.6	544.0
155°	557.6	558.3	558.2	557.3	556.6	555.8	555.1
157.5°	567.5	568.3	568.2	567.4	566.6	565.9	565.2
160°	573.2	573.8	573.7	573.1	572.4	571.7	571.1
162.5°	578.7	579.3	579.2	578.3	577.5	576.7	575.9
165°	585.1	585.8	585.8	585.1	584.5	583.8	583.1
167.5°	590.6	591.3	591.2	590.3	589.5	588.5	587.7
170°	593.4	594.0	593.9	593.1	592.2	591.4	590.5
172.5°	595.4	596.1	596.0	595.1	594.3	593.4	592.6
175°	597.6	598.3	598.2	597.2	596.3	595.3	594.4
177.5°	597.7	598.3	598.2	597.5	596.8	596.1	595.5
180°	596.5	596.5	596.5	596.5	596.5	596.5	596.5

(END OF REPORT)