

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332456-927

Luminaire Tested: **S123RDIW-S1000D755U927-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332456-927
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-5,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123RDIW-S1000D755U927-4F0-1E-UDD-F
Description: DEFINE 3 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 1000 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 755 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5398.2 lumens
Efficiency: N/A
Efficacy: 100.7 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.06 / 1.22
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 53.6
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332456-927

CATALOG NUMBER: S123RDIW-S1000D755U927-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P332456-927

CATALOG NUMBER: S123RDIW-S1000D755U927-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	108	108	108	108	101	101	101	101	86	86	86	73	73	73	61	61	61	56
1	99	95	91	88	92	89	85	82	76	74	72	65	63	62	55	54	53	48
2	91	84	78	72	84	78	73	68	67	63	60	58	55	52	49	47	45	40
3	83	74	67	61	77	69	63	57	60	55	51	51	48	45	43	41	38	35
4	76	66	58	52	71	61	54	49	53	48	44	46	42	38	39	36	33	30
5	70	59	51	45	65	55	48	42	48	42	38	41	37	34	35	32	29	26
6	65	53	45	39	60	49	42	37	43	38	33	38	33	30	32	29	26	23
7	60	48	40	34	56	45	38	33	39	34	29	34	30	26	29	26	23	21
8	56	43	36	30	52	41	34	29	36	30	26	31	27	24	27	24	21	19
9	52	40	32	27	48	37	31	26	33	28	24	29	24	21	25	22	19	17
10	49	37	29	25	45	34	28	23	31	25	21	27	22	19	23	20	17	15

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	14310	14310	14310
5°	14364	14166	14249
10°	14283	13988	13941
15°	14130	13661	13517
20°	13919	13252	12944
25°	13702	12792	12383
30°	13415	12263	11591
35°	13119	11730	10867
40°	12847	11105	9969
45°	12490	10488	9159
50°	12097	9786	8251
55°	11695	8983	7405
60°	11328	8125	6476
65°	10847	7195	5547
70°	10247	6039	4482
75°	9374	4754	4213
80°	8356	4209	3874
85°	7052	3730	3458



TEST NUMBER: P332456-927

CATALOG NUMBER: S123RDIW-S1000D755U927-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	124.8	2.3
10°-20°	347.3	6.4
20°-30°	500.2	9.3
30°-40°	563.4	10.4
40°-50°	539.0	10.0
50°-60°	441.4	8.2
60°-70°	297.8	5.5
70°-80°	149.8	2.8
80°-90°	41.8	0.8
90°-100°	28.5	0.5
100°-110°	136.0	2.5
110°-120°	326.6	6.0
120°-130°	415.9	7.7
130°-140°	444.3	8.2
140°-150°	415.5	7.7
150°-160°	335.2	6.2
160°-170°	216.3	4.0
170°-180°	74.5	1.4
0°-30°	972.3	18.0
0°-40°	1535.7	28.4
0°-60°	2516.0	46.6
0°-90°	3005.5	55.7
90°-120°	491.1	9.1
90°-150°	1766.8	32.7
90°-180°	2393.0	44.3
0°-180°	5398.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1329	1329	1329	1329	1329	
5°	1329	1324	1311	1320	1319	126
15°	1268	1255	1226	1220	1213	357
25°	1154	1125	1077	1055	1043	530
35°	998	958	893	848	827	625
45°	820	770	689	629	602	633
55°	623	568	479	418	395	559
65°	426	365	282	232	218	421
75°	225	173	114	104	101	240
85°	57	34	30	28	28	64
90°	1	7	14	16	18	5
95°	36	13	18	22	22	44
105°	174	177	128	30	26	184
115°	326	329	335	340	343	322
125°	459	464	466	468	469	410
135°	572	575	578	579	578	440
145°	660	664	665	666	666	413
155°	727	726	726	729	726	335
165°	767	765	764	768	765	216
175°	785	782	782	786	782	75
180°	785	785	785	785	785	



TEST NUMBER: P332456-927

CATALOG NUMBER: S123RDIW-S1000D755U927-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1329.4	1329.4	1329.4	1329.4	1329.4	1329.4	1329.4	1329.4	1329.4	1329.4	1329.4
2.5°	1333.7	1332.9	1332.2	1331.4	1330.6	1329.1	1326.8	1324.5	1322.2	1319.9	1322.0
5°	1329.4	1328.2	1327.0	1325.8	1324.6	1322.5	1319.7	1316.8	1314.0	1311.1	1313.2
7.5°	1317.1	1315.8	1314.5	1313.2	1311.9	1309.4	1305.7	1302.0	1298.2	1294.5	1295.7
10°	1306.8	1305.1	1303.4	1301.7	1300.1	1297.0	1292.8	1288.4	1284.1	1279.8	1280.1
12.5°	1292.1	1290.2	1288.4	1286.5	1284.6	1281.0	1275.8	1270.5	1265.3	1260.0	1259.8
15°	1268.0	1265.4	1262.7	1260.0	1257.4	1252.8	1246.0	1239.3	1232.6	1225.9	1224.7
17.5°	1237.5	1234.5	1231.4	1228.4	1225.3	1219.5	1210.9	1202.5	1193.9	1185.3	1182.8
20°	1215.1	1211.3	1207.4	1203.6	1199.8	1193.3	1184.2	1175.1	1166.0	1156.9	1153.8
22.5°	1190.1	1185.7	1181.3	1176.9	1172.5	1165.5	1155.7	1146.1	1136.4	1126.7	1122.8
25°	1153.7	1147.7	1141.7	1135.7	1129.7	1121.2	1110.2	1099.2	1088.1	1077.1	1072.1
27.5°	1109.5	1102.9	1096.2	1089.6	1083.0	1073.6	1061.3	1049.0	1036.7	1024.5	1017.5
30°	1079.3	1072.1	1064.9	1057.7	1050.5	1040.2	1026.8	1013.4	1000.0	986.6	978.4
32.5°	1049.1	1040.9	1032.8	1024.6	1016.5	1005.4	991.2	977.0	962.7	948.6	939.7
35°	998.4	989.8	981.1	972.6	963.9	952.1	937.3	922.4	907.6	892.7	882.4
37.5°	947.1	937.5	927.9	918.3	908.7	896.0	880.2	864.3	848.4	832.6	820.9
40°	914.3	903.8	893.2	882.6	872.1	858.3	841.4	824.3	807.3	790.3	777.8
42.5°	877.2	866.6	856.1	845.6	835.0	821.0	803.4	785.8	768.3	750.7	737.0
45°	820.5	809.7	798.9	788.1	777.4	762.8	744.3	725.9	707.4	689.0	675.3
47.5°	763.8	751.9	740.1	728.3	716.4	701.3	682.9	664.4	645.9	627.5	612.7
50°	722.4	711.1	699.9	688.6	677.3	662.0	642.6	623.2	603.8	584.4	569.5
52.5°	685.3	673.1	660.8	648.6	636.4	620.7	601.5	582.3	563.1	543.8	528.4
55°	623.2	611.5	599.7	588.0	576.2	560.2	539.8	519.4	499.1	478.7	464.9
57.5°	565.9	553.0	540.3	527.4	514.7	498.0	477.5	457.1	436.7	416.2	403.1
60°	526.2	513.0	499.8	486.6	473.4	456.9	437.0	417.2	397.3	377.4	364.4
62.5°	486.5	473.3	460.1	446.9	433.8	417.2	397.4	377.5	357.6	337.7	325.5
65°	425.9	412.7	399.5	386.3	373.2	357.3	338.6	319.9	301.2	282.5	270.8
67.5°	365.3	352.0	338.7	325.3	312.0	296.4	278.5	260.5	242.6	224.7	215.9
70°	325.6	312.7	299.8	286.8	273.9	259.0	242.2	225.5	208.7	191.9	183.5
72.5°	285.9	273.2	260.5	247.7	235.0	220.9	205.7	190.5	175.2	160.0	153.1
75°	225.4	213.8	202.3	190.8	179.4	167.0	153.8	140.6	127.5	114.3	111.9
77.5°	170.2	159.7	149.3	138.9	128.6	119.1	110.6	102.1	93.6	85.2	83.9
80°	134.8	124.9	115.1	105.3	95.5	88.1	83.0	78.0	73.0	67.9	67.2
82.5°	101.2	92.7	84.2	75.7	67.2	61.8	59.4	57.1	54.7	52.4	51.7
85°	57.1	51.9	46.6	41.4	36.0	33.0	32.3	31.6	30.9	30.2	29.7
87.5°	20.8	18.9	17.1	15.3	13.4	12.7	13.0	13.3	13.7	14.0	13.9
90°	0.6	1.9	3.2	4.4	5.8	7.3	9.0	10.6	12.3	14.0	14.5
92.5°	10.9	10.5	10.1	9.7	9.4	9.8	11.1	12.4	13.6	14.9	15.8
95°	35.6	30.3	25.0	19.6	14.3	12.4	13.8	15.2	16.6	18.1	19.0
97.5°	71.5	69.1	66.7	64.3	61.9	56.1	46.7	37.4	28.1	18.8	19.8
100°	98.5	101.1	103.7	106.3	108.8	100.1	79.9	59.7	39.5	19.3	20.3
102.5°	129.3	131.2	133.0	134.9	136.7	126.7	104.6	82.5	60.4	38.3	35.2
105°	173.7	175.2	176.6	178.0	179.4	174.3	162.6	151.0	139.3	127.7	104.7
107.5°	220.5	221.7	222.8	224.0	225.1	226.6	228.5	230.3	232.2	234.0	217.1
110°	251.8	252.9	253.9	254.9	256.0	257.2	258.6	260.1	261.5	262.9	258.6



TEST NUMBER: P332456-927

CATALOG NUMBER: S123RDIW-S1000D755U927-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	281.7	282.6	283.5	284.5	285.4	286.6	288.0	289.5	290.9	292.3	292.4
115°	325.8	326.6	327.4	328.2	329.0	329.9	331.1	332.2	333.4	334.6	335.9
117.5°	368.7	369.6	370.6	371.5	372.5	373.3	373.8	374.5	375.0	375.7	376.7
120°	395.2	396.4	397.6	398.7	399.9	400.7	401.1	401.5	401.9	402.2	403.3
122.5°	422.3	423.3	424.2	425.2	426.1	426.8	427.3	427.9	428.3	428.8	429.5
125°	459.4	460.4	461.4	462.5	463.5	464.3	464.8	465.3	465.8	466.4	466.6
127.5°	495.3	496.3	497.3	498.4	499.4	500.3	500.9	501.5	502.1	502.7	503.1
130°	517.6	518.7	519.8	520.8	521.8	522.6	523.1	523.6	524.1	524.7	525.1
132.5°	539.1	540.1	541.1	542.2	543.3	544.0	544.4	544.8	545.2	545.7	546.1
135°	571.9	572.7	573.4	574.2	575.0	575.6	576.2	576.6	577.2	577.7	578.1
137.5°	599.8	600.8	601.8	602.8	603.8	604.4	604.7	605.0	605.3	605.5	606.2
140°	618.5	619.2	620.0	620.8	621.6	622.2	622.6	623.0	623.4	623.8	624.2
142.5°	635.7	636.5	637.3	638.1	638.9	639.4	639.8	640.2	640.6	641.0	641.4
145°	659.9	660.8	661.7	662.6	663.5	664.1	664.3	664.6	664.9	665.1	665.4
147.5°	682.6	683.2	683.8	684.4	685.0	685.4	685.7	686.0	686.2	686.4	686.7
150°	696.6	697.0	697.4	697.8	698.2	698.5	698.8	699.0	699.3	699.5	699.8
152.5°	709.2	709.4	709.6	709.7	710.0	710.1	710.3	710.4	710.6	710.7	711.1
155°	726.9	726.7	726.4	726.1	725.9	725.8	726.0	726.1	726.2	726.4	727.0
157.5°	740.7	740.7	740.6	740.6	740.6	740.5	740.4	740.2	740.1	740.0	740.8
160°	749.1	748.9	748.8	748.7	748.5	748.5	748.3	748.1	748.1	747.9	748.7
162.5°	757.0	756.7	756.3	756.0	755.7	755.4	755.3	755.2	755.0	754.9	755.8
165°	766.6	766.2	765.8	765.4	765.0	764.8	764.6	764.5	764.4	764.2	765.2
167.5°	774.0	773.5	773.0	772.5	772.0	771.7	771.7	771.7	771.7	771.7	772.7
170°	778.2	777.7	777.2	776.7	776.2	775.9	775.9	775.9	775.9	775.9	776.9
172.5°	781.0	780.4	779.7	779.2	778.6	778.2	778.4	778.5	778.6	778.7	779.7
175°	784.7	783.9	783.3	782.7	782.0	781.8	781.9	782.0	782.2	782.3	783.2
177.5°	785.5	785.1	784.5	784.0	783.5	783.3	783.4	783.5	783.6	783.7	784.5
180°	784.7	784.7	784.7	784.7	784.7	784.7	784.7	784.7	784.7	784.7	784.7



TEST NUMBER: P332456-927

CATALOG NUMBER: S123RDIW-S1000D755U927-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1329.4	1329.4	1329.4	1329.4	1329.4	1329.4	1329.4	1329.4
2.5°	1324.1	1326.3	1328.3	1329.2	1328.8	1328.5	1328.1	1327.7
5°	1315.4	1317.6	1319.7	1320.6	1320.1	1319.6	1319.1	1318.7
7.5°	1296.9	1298.1	1299.3	1299.5	1298.6	1297.8	1297.0	1296.2
10°	1280.3	1280.6	1280.8	1280.3	1279.1	1277.9	1276.7	1275.5
12.5°	1259.6	1259.6	1259.4	1258.6	1257.3	1255.8	1254.5	1253.1
15°	1223.5	1222.3	1221.1	1219.6	1218.0	1216.3	1214.7	1213.0
17.5°	1180.3	1177.7	1175.2	1172.7	1170.2	1167.7	1165.2	1162.7
20°	1150.6	1147.6	1144.5	1141.5	1138.6	1135.7	1132.8	1130.0
22.5°	1119.0	1115.1	1111.2	1107.9	1105.3	1102.6	1099.9	1097.2
25°	1067.1	1062.0	1057.0	1053.1	1050.5	1047.9	1045.3	1042.6
27.5°	1010.5	1003.5	996.5	991.0	987.0	982.9	978.9	974.9
30°	970.3	962.1	953.9	948.0	944.1	940.3	936.4	932.6
32.5°	930.7	921.9	912.9	906.5	902.5	898.4	894.4	890.3
35°	872.1	861.8	851.5	844.2	840.0	835.6	831.3	827.0
37.5°	809.2	797.5	785.8	777.3	772.0	766.7	761.4	756.1
40°	765.4	753.0	740.5	731.5	726.0	720.5	714.9	709.5
42.5°	723.4	709.8	696.2	686.9	682.0	677.1	672.1	667.2
45°	661.6	648.0	634.3	624.6	618.9	613.1	607.4	601.7
47.5°	597.8	583.0	568.1	558.1	552.9	547.9	542.7	537.6
50°	554.7	539.8	525.0	514.8	509.3	503.7	498.3	492.7
52.5°	513.0	497.6	482.1	471.9	467.0	462.1	457.2	452.2
55°	450.9	437.0	423.1	413.8	409.0	404.2	399.4	394.6
57.5°	389.9	376.8	363.7	355.1	351.0	346.9	342.9	338.7
60°	351.5	338.6	325.6	317.1	313.1	309.0	304.9	300.8
62.5°	313.3	301.2	289.0	280.7	276.6	272.3	268.0	263.7
65°	259.0	247.2	235.5	228.3	225.7	223.1	220.5	217.8
67.5°	207.2	198.4	189.6	183.8	181.0	178.2	175.3	172.5
70°	175.2	166.8	158.4	152.9	150.2	147.6	145.0	142.4
72.5°	146.3	139.4	132.6	128.7	127.5	126.4	125.3	124.2
75°	109.5	107.1	104.7	103.3	102.8	102.3	101.8	101.3
77.5°	82.6	81.3	80.0	79.1	78.7	78.2	77.7	77.2
80°	66.5	65.8	65.0	64.5	64.0	63.5	63.0	62.5
82.5°	50.9	50.2	49.5	49.1	49.0	49.0	48.8	48.7
85°	29.2	28.8	28.3	28.0	28.0	28.0	28.0	28.0
87.5°	13.9	13.8	13.6	13.5	13.4	13.2	13.2	13.0
90°	15.1	15.5	16.1	16.5	16.7	17.0	17.2	17.5
92.5°	16.6	17.4	18.2	18.7	18.9	19.0	19.2	19.3
95°	19.9	20.8	21.7	22.2	22.2	22.2	22.2	22.2
97.5°	20.8	21.9	22.9	23.5	23.6	23.8	23.9	24.0
100°	21.3	22.3	23.4	24.0	24.1	24.2	24.3	24.5
102.5°	31.9	28.8	25.5	24.0	24.2	24.5	24.7	25.0
105°	81.8	58.9	36.0	24.6	24.9	25.1	25.4	25.7
107.5°	200.3	183.5	166.8	149.7	132.4	115.1	97.8	80.6
110°	254.4	250.1	245.8	234.4	215.9	197.3	178.8	160.3



TEST NUMBER: P332456-927

CATALOG NUMBER: S123RDIW-S1000D755U927-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	292.5	292.6	292.6	290.7	286.8	282.9	278.9	275.0
115°	337.2	338.5	339.8	340.7	341.2	341.7	342.2	342.8
117.5°	377.7	378.7	379.8	380.3	380.5	380.6	380.6	380.8
120°	404.3	405.4	406.4	406.9	406.9	406.9	406.9	406.9
122.5°	430.2	430.9	431.7	432.1	432.2	432.3	432.5	432.5
125°	466.8	467.1	467.4	467.6	467.9	468.2	468.4	468.7
127.5°	503.6	504.0	504.4	504.5	504.2	503.9	503.7	503.4
130°	525.7	526.2	526.7	526.9	526.6	526.3	526.1	525.8
132.5°	546.7	547.2	547.7	547.8	547.4	547.1	546.7	546.3
135°	578.5	578.8	579.2	579.2	578.8	578.5	578.1	577.7
137.5°	606.8	607.4	608.1	608.2	608.0	607.7	607.4	607.2
140°	624.8	625.3	625.8	626.0	625.7	625.4	625.2	624.9
142.5°	641.8	642.2	642.6	642.7	642.3	642.0	641.6	641.2
145°	665.7	665.9	666.1	666.3	666.3	666.3	666.3	666.3
147.5°	687.0	687.2	687.5	687.3	686.7	686.1	685.6	684.9
150°	700.1	700.3	700.5	700.5	700.1	699.7	699.3	698.9
152.5°	711.6	712.1	712.6	712.5	711.9	711.3	710.7	710.1
155°	727.6	728.3	729.0	728.9	728.1	727.3	726.5	725.7
157.5°	741.6	742.3	743.1	743.0	742.0	740.9	740.0	738.9
160°	749.5	750.3	751.0	751.0	750.0	749.2	748.2	747.3
162.5°	756.7	757.6	758.4	758.4	757.6	756.9	756.1	755.3
165°	766.3	767.3	768.3	768.4	767.5	766.6	765.7	764.8
167.5°	773.7	774.8	775.9	775.9	774.8	773.7	772.7	771.7
170°	777.9	779.0	780.1	780.1	779.0	777.9	776.9	775.9
172.5°	780.8	781.8	782.8	782.8	781.6	780.5	779.3	778.2
175°	784.1	785.1	785.9	785.8	784.8	783.8	782.8	781.7
177.5°	785.4	786.2	787.0	786.9	785.8	784.8	783.8	782.8
180°	784.7	784.7	784.7	784.7	784.7	784.7	784.7	784.7

(END OF REPORT)