

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332481-927

Luminaire Tested: **S123RDIW-S1165D1030U927-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332481-927
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-9,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123RDIW-S1165D1030U927-4F0-1E-UDD-F1
Description: DEFINE 3 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 1165 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 1030 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6302.3 lumens
Efficiency: N/A
Efficacy: 93.5 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.06 / 1.22
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 67.4
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332481-927

CATALOG NUMBER: S123RDIW-S1165D1030U927-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P332481-927

CATALOG NUMBER: S123RDIW-S1165D1030U927-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	108	108	108	108	101	101	101	101	86	86	86	73	73	73	61	61	61	55
1	99	95	91	88	92	88	85	82	76	74	72	65	63	61	54	53	52	47
2	91	83	77	72	84	78	73	68	67	63	60	57	54	52	48	46	44	40
3	83	74	66	61	77	69	62	57	59	55	51	51	47	44	43	40	38	34
4	76	65	58	52	70	61	54	49	53	48	43	46	42	38	39	36	33	30
5	70	58	50	44	65	55	48	42	48	42	38	41	37	33	35	32	29	26
6	65	53	45	39	60	49	42	37	43	37	33	37	33	29	32	28	26	23
7	60	48	40	34	55	45	38	33	39	33	29	34	30	26	29	26	23	20
8	56	43	36	30	52	41	34	29	36	30	26	31	27	23	27	23	21	18
9	52	40	32	27	48	37	31	26	33	27	24	29	24	21	25	21	19	17
10	48	36	29	24	45	34	28	23	30	25	21	27	22	19	23	20	17	15

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	16527	16527	16527
5°	16590	16361	16455
10°	16497	16156	16101
15°	16319	15778	15611
20°	16076	15306	14948
25°	15824	14775	14301
30°	15493	14162	13387
35°	15152	13548	12550
40°	14838	12826	11514
45°	14425	12113	10577
50°	13971	11302	9530
55°	13508	10376	8552
60°	13082	9384	7481
65°	12528	8308	6406
70°	11833	6977	5174
75°	10821	5490	4870
80°	9651	4860	4475
85°	8151	4310	4001



TEST NUMBER: P332481-927

CATALOG NUMBER: S123RDIW-S1165D1030U927-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	144.2	2.3
10°-20°	401.2	6.4
20°-30°	577.6	9.2
30°-40°	650.7	10.3
40°-50°	622.5	9.9
50°-60°	509.7	8.1
60°-70°	343.9	5.5
70°-80°	173.0	2.7
80°-90°	48.8	0.8
90°-100°	66.6	1.1
100°-110°	199.2	3.2
110°-120°	338.8	5.4
120°-130°	445.7	7.1
130°-140°	500.9	7.9
140°-150°	492.4	7.8
150°-160°	414.5	6.6
160°-170°	275.9	4.4
170°-180°	96.6	1.5
0°-30°	1123.0	17.8
0°-40°	1773.6	28.1
0°-60°	2905.8	46.1
0°-90°	3471.6	55.1
90°-120°	604.6	9.6
90°-150°	2043.6	32.4
90°-180°	2831.0	44.9
0°-180°	6302.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1535	1535	1535	1535	1535	
5°	1535	1529	1514	1525	1523	146
15°	1464	1450	1416	1410	1401	412
25°	1332	1300	1244	1219	1204	613
35°	1153	1106	1031	979	955	721
45°	948	889	796	727	695	731
55°	720	656	553	483	456	645
65°	492	422	326	268	252	487
75°	260	200	132	120	117	278
85°	66	40	35	32	32	74
90°	1	9	19	22	24	6
95°	47	53	59	62	63	53
105°	181	182	189	190	191	193
115°	341	343	342	343	342	337
125°	499	501	500	497	494	445
135°	648	652	652	649	647	499
145°	786	787	790	789	786	491
155°	900	900	900	903	898	414
165°	980	978	978	982	977	276
175°	1019	1016	1016	1020	1015	97
180°	1022	1022	1022	1022	1022	



TEST NUMBER: P332481-927

CATALOG NUMBER: S123RDIW-S1165D1030U927-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1535.4	1535.4	1535.4	1535.4	1535.4	1535.4	1535.4	1535.4	1535.4	1535.4	1535.4
2.5°	1540.4	1539.4	1538.6	1537.7	1536.8	1535.0	1532.4	1529.7	1527.1	1524.4	1526.9
5°	1535.4	1534.0	1532.6	1531.2	1529.9	1527.5	1524.2	1520.8	1517.5	1514.2	1516.7
7.5°	1521.1	1519.7	1518.2	1516.7	1515.2	1512.3	1508.0	1503.6	1499.4	1495.0	1496.4
10°	1509.3	1507.3	1505.4	1503.4	1501.5	1498.0	1493.0	1488.0	1483.0	1478.1	1478.4
12.5°	1492.3	1490.2	1488.0	1485.8	1483.7	1479.6	1473.5	1467.4	1461.3	1455.2	1455.0
15°	1464.4	1461.3	1458.3	1455.2	1452.2	1446.8	1439.1	1431.3	1423.6	1415.9	1414.4
17.5°	1429.3	1425.8	1422.2	1418.6	1415.2	1408.4	1398.6	1388.7	1378.9	1369.0	1366.1
20°	1403.4	1399.0	1394.6	1390.1	1385.7	1378.2	1367.7	1357.2	1346.6	1336.2	1332.5
22.5°	1374.5	1369.4	1364.3	1359.2	1354.2	1346.0	1334.8	1323.7	1312.5	1301.2	1296.8
25°	1332.4	1325.5	1318.6	1311.6	1304.7	1294.9	1282.1	1269.5	1256.7	1244.0	1238.2
27.5°	1281.4	1273.7	1266.1	1258.5	1250.8	1239.9	1225.7	1211.6	1197.4	1183.2	1175.1
30°	1246.5	1238.2	1229.9	1221.5	1213.3	1201.3	1185.9	1170.4	1154.9	1139.4	1130.0
32.5°	1211.6	1202.2	1192.8	1183.4	1174.0	1161.1	1144.7	1128.3	1111.9	1095.6	1085.3
35°	1153.1	1143.1	1133.1	1123.2	1113.3	1099.7	1082.5	1065.4	1048.2	1031.0	1019.1
37.5°	1093.8	1082.8	1071.7	1060.6	1049.6	1034.8	1016.5	998.2	979.9	961.6	948.1
40°	1056.0	1043.8	1031.6	1019.5	1007.3	991.3	971.7	952.0	932.4	912.8	898.3
42.5°	1013.1	1000.9	988.8	976.6	964.4	948.2	927.9	907.5	887.2	867.0	851.2
45°	947.6	935.2	922.7	910.3	897.8	880.9	859.6	838.3	817.0	795.7	779.9
47.5°	882.1	868.5	854.8	841.1	827.4	809.9	788.6	767.3	746.0	724.8	707.6
50°	834.3	821.3	808.3	795.3	782.3	764.6	742.2	719.8	697.4	674.9	657.7
52.5°	791.5	777.4	763.3	749.2	735.0	716.8	694.7	672.5	650.3	628.1	610.3
55°	719.8	706.2	692.6	679.1	665.5	647.0	623.4	599.9	576.4	552.9	536.9
57.5°	653.5	638.7	623.9	609.2	594.4	575.2	551.6	527.9	504.3	480.7	465.5
60°	607.7	592.5	577.3	562.1	546.8	527.7	504.7	481.8	458.8	435.9	420.9
62.5°	561.8	546.6	531.4	516.2	501.0	481.9	458.9	435.9	413.0	390.0	376.0
65°	491.9	476.7	461.4	446.2	431.0	412.6	391.0	369.4	347.8	326.2	312.7
67.5°	421.9	406.5	391.1	375.7	360.4	342.3	321.6	300.9	280.2	259.5	249.4
70°	376.0	361.2	346.2	331.2	316.3	299.1	279.8	260.4	241.1	221.7	212.0
72.5°	330.3	315.5	300.8	286.1	271.3	255.2	237.6	220.0	202.4	184.8	176.9
75°	260.2	247.0	233.7	220.4	207.2	192.9	177.7	162.4	147.2	132.0	129.2
77.5°	196.5	184.5	172.5	160.5	148.5	137.5	127.8	118.0	108.1	98.4	96.9
80°	155.7	144.3	132.9	121.6	110.3	101.7	95.9	90.1	84.3	78.4	77.6
82.5°	116.8	107.0	97.2	87.4	77.6	71.4	68.7	65.9	63.2	60.5	59.7
85°	66.0	59.9	53.8	47.8	41.7	38.2	37.4	36.5	35.7	34.9	34.3
87.5°	24.1	22.0	19.9	17.8	15.8	15.0	15.4	15.8	16.3	16.8	16.7
90°	0.8	2.6	4.4	6.2	7.9	10.0	12.3	14.7	17.0	19.3	20.0
92.5°	19.4	20.6	21.9	23.1	24.2	25.5	26.9	28.2	29.5	30.8	31.4
95°	47.4	48.6	49.8	51.1	52.4	53.7	55.1	56.6	58.0	59.4	60.1
97.5°	84.1	85.0	86.0	86.9	87.9	88.8	89.8	90.9	91.9	92.9	93.8
100°	109.2	110.2	111.3	112.3	113.4	114.4	115.3	116.2	117.1	118.0	118.5
102.5°	138.1	138.7	139.3	140.0	140.6	141.5	142.7	143.9	145.0	146.2	146.8
105°	180.6	180.9	181.3	181.6	182.0	183.0	184.6	186.2	187.8	189.4	189.4
107.5°	230.0	230.2	230.4	230.7	230.8	231.3	232.0	232.6	233.2	233.9	234.4
110°	260.9	261.2	261.6	261.9	262.3	262.6	263.0	263.3	263.7	264.0	264.7



TEST NUMBER: P332481-927

CATALOG NUMBER: S123RDIW-S1165D1030U927-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	292.9	293.2	293.3	293.6	293.8	293.9	294.0	294.1	294.1	294.2	295.1
115°	341.1	341.6	342.1	342.7	343.3	343.3	342.9	342.6	342.2	341.9	342.1
117.5°	389.6	389.9	390.3	390.6	391.0	390.9	390.5	390.0	389.5	389.1	389.0
120°	419.8	420.8	421.9	422.9	424.1	424.1	423.2	422.3	421.4	420.6	420.3
122.5°	451.2	452.0	452.8	453.5	454.3	454.5	454.1	453.6	453.1	452.7	452.2
125°	499.2	499.7	500.3	500.8	501.4	501.5	501.1	500.7	500.3	500.0	499.3
127.5°	543.5	544.6	545.8	546.9	548.0	548.4	548.0	547.6	547.2	546.8	545.9
130°	573.1	574.5	575.9	577.3	578.8	579.2	578.7	578.1	577.6	577.0	576.3
132.5°	602.5	604.0	605.4	606.9	608.3	608.8	608.4	608.0	607.6	607.2	606.3
135°	647.7	648.7	649.8	650.9	652.0	652.4	652.2	652.0	651.9	651.6	650.9
137.5°	689.4	690.3	691.2	692.1	693.0	693.6	694.1	694.6	695.1	695.5	694.7
140°	718.3	719.2	720.1	721.0	721.8	722.4	722.5	722.8	722.9	723.1	722.9
142.5°	744.7	745.5	746.4	747.3	748.2	748.8	749.1	749.4	749.8	750.1	749.9
145°	785.7	786.1	786.4	786.8	787.1	787.6	788.1	788.7	789.2	789.7	789.6
147.5°	821.7	822.3	822.9	823.6	824.3	824.8	825.3	825.9	826.3	826.8	826.8
150°	846.7	847.1	847.4	847.8	848.1	848.5	848.8	849.2	849.5	849.9	849.9
152.5°	867.3	867.8	868.2	868.8	869.3	869.6	869.8	870.1	870.3	870.4	870.8
155°	899.7	899.7	899.7	899.7	899.7	899.8	899.9	900.2	900.3	900.5	901.2
157.5°	927.3	927.1	926.9	926.6	926.5	926.4	926.5	926.7	926.9	926.9	927.7
160°	944.6	944.3	943.9	943.6	943.2	943.0	943.0	943.0	943.0	943.0	943.9
162.5°	960.0	959.6	959.0	958.5	958.1	957.8	958.0	958.1	958.3	958.5	959.3
165°	979.9	979.4	978.9	978.3	977.8	977.6	977.6	977.6	977.6	977.6	978.6
167.5°	995.9	995.1	994.4	993.7	993.0	992.7	992.8	993.0	993.2	993.2	994.3
170°	1004.8	1004.1	1003.4	1002.7	1002.0	1001.6	1001.6	1001.6	1001.6	1001.6	1002.8
172.5°	1011.9	1011.1	1010.4	1009.7	1009.0	1008.7	1008.7	1008.7	1008.7	1008.7	1009.8
175°	1019.3	1018.6	1017.9	1017.2	1016.4	1016.1	1016.1	1016.1	1016.1	1016.1	1017.2
177.5°	1022.3	1021.8	1021.2	1020.6	1020.0	1019.8	1019.8	1019.8	1019.8	1019.8	1020.6
180°	1021.7	1021.7	1021.7	1021.7	1021.7	1021.7	1021.7	1021.7	1021.7	1021.7	1021.7



TEST NUMBER: P332481-927

CATALOG NUMBER: S123RDIW-S1165D1030U927-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1535.4	1535.4	1535.4	1535.4	1535.4	1535.4	1535.4	1535.4
2.5°	1529.3	1531.8	1534.1	1535.2	1534.7	1534.3	1533.8	1533.3
5°	1519.2	1521.7	1524.2	1525.1	1524.6	1524.0	1523.4	1522.9
7.5°	1497.8	1499.2	1500.6	1500.8	1499.8	1498.9	1497.9	1497.0
10°	1478.7	1478.9	1479.2	1478.7	1477.3	1475.9	1474.5	1473.1
12.5°	1454.8	1454.7	1454.5	1453.7	1452.1	1450.4	1448.8	1447.2
15°	1413.1	1411.7	1410.3	1408.7	1406.7	1404.8	1402.8	1400.9
17.5°	1363.2	1360.2	1357.2	1354.4	1351.5	1348.6	1345.8	1342.8
20°	1329.0	1325.3	1321.8	1318.3	1314.9	1311.6	1308.4	1305.0
22.5°	1292.3	1287.9	1283.3	1279.5	1276.4	1273.4	1270.3	1267.2
25°	1232.4	1226.5	1220.8	1216.3	1213.3	1210.2	1207.2	1204.1
27.5°	1167.0	1159.0	1150.9	1144.5	1139.9	1135.3	1130.6	1125.9
30°	1120.5	1111.2	1101.8	1094.9	1090.4	1086.0	1081.6	1077.1
32.5°	1075.0	1064.7	1054.4	1046.9	1042.3	1037.6	1033.0	1028.3
35°	1007.3	995.4	983.5	975.0	970.0	965.0	960.0	955.1
37.5°	934.5	921.1	907.5	897.7	891.6	885.4	879.3	873.1
40°	884.0	869.6	855.2	844.9	838.4	832.1	825.8	819.4
42.5°	835.5	819.8	804.1	793.4	787.7	782.0	776.3	770.6
45°	764.1	748.4	732.6	721.4	714.8	708.1	701.5	694.8
47.5°	690.4	673.3	656.1	644.6	638.7	632.7	626.8	620.9
50°	640.6	623.4	606.3	594.5	588.2	581.8	575.4	569.1
52.5°	592.5	574.6	556.8	545.0	539.3	533.7	528.0	522.3
55°	520.8	504.7	488.7	477.9	472.4	466.8	461.3	455.7
57.5°	450.4	435.1	420.0	410.0	405.4	400.7	395.9	391.3
60°	405.9	391.0	376.0	366.2	361.6	356.8	352.1	347.5
62.5°	361.9	347.8	333.7	324.3	319.3	314.4	309.5	304.6
65°	299.1	285.6	272.0	263.7	260.7	257.6	254.6	251.5
67.5°	239.2	229.1	219.0	212.3	209.1	205.7	202.5	199.2
70°	202.2	192.6	182.9	176.6	173.5	170.5	167.4	164.4
72.5°	169.0	161.1	153.1	148.5	147.3	146.0	144.7	143.5
75°	126.4	123.7	120.9	119.3	118.7	118.2	117.6	117.1
77.5°	95.4	93.9	92.4	91.3	90.8	90.2	89.7	89.1
80°	76.8	76.0	75.1	74.5	73.9	73.4	72.8	72.2
82.5°	58.9	58.1	57.2	56.7	56.6	56.5	56.4	56.3
85°	33.7	33.2	32.6	32.4	32.4	32.4	32.4	32.4
87.5°	16.6	16.6	16.5	16.4	16.2	16.1	15.9	15.8
90°	20.7	21.4	22.1	22.7	23.0	23.4	23.7	24.1
92.5°	31.9	32.6	33.1	33.3	33.0	32.9	32.6	32.4
95°	60.8	61.6	62.3	62.6	62.6	62.6	62.6	62.6
97.5°	94.6	95.4	96.3	96.6	96.5	96.5	96.4	96.3
100°	119.1	119.6	120.1	120.6	120.9	121.3	121.6	122.0
102.5°	147.3	147.8	148.4	148.6	148.5	148.5	148.4	148.3
105°	189.4	189.4	189.4	189.6	190.0	190.3	190.7	191.0
107.5°	235.0	235.6	236.1	236.3	236.1	235.9	235.7	235.4
110°	265.5	266.2	266.9	267.0	266.7	266.3	266.0	265.6



TEST NUMBER: P332481-927

CATALOG NUMBER: S123RDIW-S1165D1030U927-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	296.0	296.8	297.6	298.0	297.9	297.9	297.9	297.8
115°	342.2	342.5	342.6	342.6	342.5	342.2	342.1	341.9
117.5°	389.0	389.0	389.0	388.6	388.2	387.7	387.1	386.7
120°	420.2	420.0	419.9	419.5	419.2	418.8	418.5	418.1
122.5°	451.7	451.2	450.8	450.3	449.8	449.3	448.9	448.3
125°	498.6	497.9	497.2	496.5	495.7	495.0	494.3	493.6
127.5°	544.9	543.9	542.9	541.9	541.1	540.3	539.5	538.7
130°	575.6	574.9	574.2	573.2	572.0	570.7	569.5	568.2
132.5°	605.5	604.7	603.8	602.9	601.9	600.9	600.0	599.0
135°	650.2	649.5	648.8	648.3	647.9	647.6	647.2	646.9
137.5°	694.0	693.2	692.5	691.8	691.1	690.5	689.8	689.1
140°	722.8	722.5	722.4	721.7	720.4	719.2	718.0	716.7
142.5°	749.7	749.6	749.4	748.8	747.8	746.9	745.9	745.0
145°	789.4	789.2	789.0	788.5	787.8	787.1	786.4	785.7
147.5°	826.8	826.8	826.8	826.2	825.2	824.1	823.1	822.0
150°	849.9	849.9	849.9	849.4	848.3	847.2	846.2	845.1
152.5°	871.0	871.3	871.6	871.3	870.4	869.4	868.5	867.6
155°	901.9	902.6	903.3	903.1	901.8	900.6	899.4	898.1
157.5°	928.4	929.2	929.9	929.9	928.8	927.9	926.9	925.8
160°	944.8	945.7	946.6	946.7	945.9	945.2	944.5	943.8
162.5°	960.2	961.1	962.0	961.9	960.8	959.6	958.5	957.3
165°	979.7	980.7	981.8	981.8	980.5	979.2	977.9	976.8
167.5°	995.5	996.6	997.7	997.7	996.6	995.5	994.3	993.2
170°	1004.1	1005.4	1006.6	1006.6	1005.4	1004.1	1002.8	1001.6
172.5°	1010.9	1012.0	1013.1	1013.0	1011.8	1010.5	1009.2	1008.1
175°	1018.2	1019.3	1020.3	1020.3	1019.0	1017.7	1016.5	1015.3
177.5°	1021.4	1022.3	1023.2	1023.1	1022.1	1021.1	1020.1	1019.1
180°	1021.7	1021.7	1021.7	1021.7	1021.7	1021.7	1021.7	1021.7

(END OF REPORT)