

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332485-927

Luminaire Tested: **S123RDIW-S1165D1320U927-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332485-927
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-9,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123RDIW-S1165D1320U927-4F0-1E-UDD-F1
Description: DEFINE 3 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 1165 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 1320 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7096.3 lumens
Efficiency: N/A
Efficacy: 93.1 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.06 / 1.22
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 76.2
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332485-927

CATALOG NUMBER: S123RDIW-S1165D1320U927-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P332485-927

CATALOG NUMBER: S123RDIW-S1165D1320U927-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	107	107	107	107	98	98	98	98	83	83	83	68	68	68	55	55	55	49
1	98	94	90	87	90	86	83	80	73	71	69	61	59	58	49	48	47	42
2	89	82	76	71	82	76	71	66	64	61	57	54	51	49	44	42	40	36
3	82	72	65	60	75	67	61	56	57	52	48	48	44	41	39	37	35	30
4	75	64	57	51	69	60	53	48	51	46	42	43	39	36	35	32	30	26
5	69	57	49	44	63	53	46	41	46	40	36	38	34	31	32	29	26	23
6	63	52	44	38	58	48	41	36	41	36	32	35	31	27	29	26	23	20
7	59	47	39	33	54	43	36	32	37	32	28	32	27	24	26	23	21	18
8	55	42	35	30	50	40	33	28	34	29	25	29	25	22	24	21	19	16
9	51	39	31	26	47	36	30	25	31	26	22	27	23	20	22	19	17	15
10	47	36	28	24	44	33	27	23	29	24	20	25	21	18	21	18	15	14

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	16527	16527	16527
5°	16590	16361	16455
10°	16497	16156	16101
15°	16319	15778	15611
20°	16076	15306	14948
25°	15824	14775	14301
30°	15493	14162	13387
35°	15152	13548	12550
40°	14838	12826	11514
45°	14425	12113	10577
50°	13971	11302	9530
55°	13508	10376	8552
60°	13082	9384	7481
65°	12528	8308	6406
70°	11833	6977	5174
75°	10821	5490	4870
80°	9651	4860	4475
85°	8151	4310	4001



TEST NUMBER: P332485-927

CATALOG NUMBER: S123RDIW-S1165D1320U927-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	144.2	2.0
10°-20°	401.2	5.7
20°-30°	577.6	8.1
30°-40°	650.7	9.2
40°-50°	622.5	8.8
50°-60°	509.7	7.2
60°-70°	343.9	4.8
70°-80°	173.0	2.4
80°-90°	49.6	0.7
90°-100°	85.2	1.2
100°-110°	255.0	3.6
110°-120°	433.8	6.1
120°-130°	570.5	8.0
130°-140°	641.3	9.0
140°-150°	630.4	8.9
150°-160°	530.7	7.5
160°-170°	353.3	5.0
170°-180°	123.7	1.7
0°-30°	1123.0	15.8
0°-40°	1773.6	25.0
0°-60°	2905.8	40.9
0°-90°	3472.4	48.9
90°-120°	774.0	10.9
90°-150°	2616.2	36.9
90°-180°	3624.0	51.1
0°-180°	7096.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1535	1535	1535	1535	1535	
5°	1535	1529	1514	1525	1523	146
15°	1464	1450	1416	1410	1401	412
25°	1332	1300	1244	1219	1204	613
35°	1153	1106	1031	979	955	721
45°	948	889	796	727	695	731
55°	720	656	553	483	456	645
65°	492	422	326	268	252	487
75°	260	200	132	120	117	278
85°	66	40	35	32	32	74
90°	1	11	25	29	31	7
95°	61	68	76	80	80	68
105°	231	234	242	243	244	248
115°	437	439	438	439	438	432
125°	639	642	640	636	632	570
135°	829	835	834	830	828	639
145°	1006	1008	1011	1010	1006	628
155°	1152	1152	1153	1156	1150	530
165°	1254	1252	1251	1257	1250	354
175°	1305	1301	1301	1306	1300	124
180°	1308	1308	1308	1308	1308	



TEST NUMBER: P332485-927

CATALOG NUMBER: S123RDIW-S1165D1320U927-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1535.4	1535.4	1535.4	1535.4	1535.4	1535.4	1535.4	1535.4	1535.4	1535.4	1535.4
2.5°	1540.4	1539.4	1538.6	1537.7	1536.8	1535.0	1532.4	1529.7	1527.1	1524.4	1526.9
5°	1535.4	1534.0	1532.6	1531.2	1529.9	1527.5	1524.2	1520.8	1517.5	1514.2	1516.7
7.5°	1521.1	1519.7	1518.2	1516.7	1515.2	1512.3	1508.0	1503.6	1499.4	1495.0	1496.4
10°	1509.3	1507.3	1505.4	1503.4	1501.5	1498.0	1493.0	1488.0	1483.0	1478.1	1478.4
12.5°	1492.3	1490.2	1488.0	1485.8	1483.7	1479.6	1473.5	1467.4	1461.3	1455.2	1455.0
15°	1464.4	1461.3	1458.3	1455.2	1452.2	1446.8	1439.1	1431.3	1423.6	1415.9	1414.4
17.5°	1429.3	1425.8	1422.2	1418.6	1415.2	1408.4	1398.6	1388.7	1378.9	1369.0	1366.1
20°	1403.4	1399.0	1394.6	1390.1	1385.7	1378.2	1367.7	1357.2	1346.6	1336.2	1332.5
22.5°	1374.5	1369.4	1364.3	1359.2	1354.2	1346.0	1334.8	1323.7	1312.5	1301.2	1296.8
25°	1332.4	1325.5	1318.6	1311.6	1304.7	1294.9	1282.1	1269.5	1256.7	1244.0	1238.2
27.5°	1281.4	1273.7	1266.1	1258.5	1250.8	1239.9	1225.7	1211.6	1197.4	1183.2	1175.1
30°	1246.5	1238.2	1229.9	1221.5	1213.3	1201.3	1185.9	1170.4	1154.9	1139.4	1130.0
32.5°	1211.6	1202.2	1192.8	1183.4	1174.0	1161.1	1144.7	1128.3	1111.9	1095.6	1085.3
35°	1153.1	1143.1	1133.1	1123.2	1113.3	1099.7	1082.5	1065.4	1048.2	1031.0	1019.1
37.5°	1093.8	1082.8	1071.7	1060.6	1049.6	1034.8	1016.5	998.2	979.9	961.6	948.1
40°	1056.0	1043.8	1031.6	1019.5	1007.3	991.3	971.7	952.0	932.4	912.8	898.3
42.5°	1013.1	1000.9	988.8	976.6	964.4	948.2	927.9	907.5	887.2	867.0	851.2
45°	947.6	935.2	922.7	910.3	897.8	880.9	859.6	838.3	817.0	795.7	779.9
47.5°	882.1	868.5	854.8	841.1	827.4	809.9	788.6	767.3	746.0	724.8	707.6
50°	834.3	821.3	808.3	795.3	782.3	764.6	742.2	719.8	697.4	674.9	657.7
52.5°	791.5	777.4	763.3	749.2	735.0	716.8	694.7	672.5	650.3	628.1	610.3
55°	719.8	706.2	692.6	679.1	665.5	647.0	623.4	599.9	576.4	552.9	536.9
57.5°	653.5	638.7	623.9	609.2	594.4	575.2	551.6	527.9	504.3	480.7	465.5
60°	607.7	592.5	577.3	562.1	546.8	527.7	504.7	481.8	458.8	435.9	420.9
62.5°	561.8	546.6	531.4	516.2	501.0	481.9	458.9	435.9	413.0	390.0	376.0
65°	491.9	476.7	461.4	446.2	431.0	412.6	391.0	369.4	347.8	326.2	312.7
67.5°	421.9	406.5	391.1	375.7	360.4	342.3	321.6	300.9	280.2	259.5	249.4
70°	376.0	361.2	346.2	331.2	316.3	299.1	279.8	260.4	241.1	221.7	212.0
72.5°	330.3	315.5	300.8	286.1	271.3	255.2	237.6	220.0	202.4	184.8	176.9
75°	260.2	247.0	233.7	220.4	207.2	192.9	177.7	162.4	147.2	132.0	129.2
77.5°	196.5	184.5	172.5	160.5	148.5	137.5	127.8	118.0	108.1	98.4	96.9
80°	155.7	144.3	132.9	121.6	110.3	101.7	95.9	90.1	84.3	78.4	77.6
82.5°	116.8	107.0	97.2	87.4	77.6	71.4	68.7	65.9	63.2	60.5	59.7
85°	66.0	59.9	53.8	47.8	41.7	38.2	37.4	36.5	35.7	34.9	34.3
87.5°	24.1	22.1	20.1	18.1	16.2	15.5	16.1	16.7	17.3	17.9	17.8
90°	1.0	3.3	5.6	7.8	10.1	12.8	15.8	18.7	21.7	24.6	25.6
92.5°	24.9	26.4	28.0	29.5	31.1	32.7	34.4	36.0	37.8	39.5	40.2
95°	60.6	62.2	63.8	65.4	67.0	68.8	70.6	72.4	74.2	76.0	76.9
97.5°	107.7	108.8	110.0	111.2	112.4	113.7	115.0	116.3	117.6	119.0	120.0
100°	139.7	141.1	142.4	143.9	145.2	146.5	147.6	148.8	149.9	151.1	151.7
102.5°	176.7	177.5	178.4	179.2	180.0	181.2	182.7	184.2	185.7	187.2	187.9
105°	231.2	231.6	232.1	232.5	233.0	234.2	236.3	238.4	240.4	242.5	242.5
107.5°	294.5	294.8	295.0	295.3	295.6	296.1	296.9	297.8	298.6	299.4	300.2
110°	333.9	334.4	334.9	335.3	335.7	336.2	336.7	337.2	337.5	338.0	339.0



TEST NUMBER: P332485-927

CATALOG NUMBER: S123RDIW-S1165D1320U927-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	375.0	375.3	375.6	375.8	376.1	376.3	376.4	376.4	376.6	376.7	377.8
115°	436.7	437.4	438.0	438.7	439.4	439.5	439.0	438.6	438.2	437.7	437.9
117.5°	498.8	499.2	499.6	500.1	500.6	500.5	499.9	499.3	498.7	498.1	498.0
120°	537.3	538.7	540.1	541.5	542.8	543.0	541.8	540.7	539.6	538.4	538.1
122.5°	577.7	578.6	579.6	580.7	581.6	581.9	581.2	580.7	580.0	579.5	578.8
125°	639.1	639.8	640.4	641.1	641.8	641.9	641.4	641.0	640.6	640.1	639.2
127.5°	695.8	697.3	698.7	700.1	701.6	702.1	701.6	701.1	700.6	700.1	698.8
130°	733.6	735.4	737.3	739.1	740.9	741.5	740.8	740.1	739.4	738.7	737.8
132.5°	771.4	773.2	775.1	776.9	778.7	779.3	778.9	778.4	777.8	777.4	776.3
135°	829.2	830.5	831.9	833.2	834.6	835.2	835.0	834.7	834.5	834.2	833.4
137.5°	882.6	883.7	884.9	886.0	887.2	888.0	888.6	889.2	889.8	890.4	889.4
140°	919.6	920.7	921.9	923.0	924.2	924.8	925.0	925.3	925.5	925.7	925.5
142.5°	953.2	954.4	955.5	956.7	957.8	958.6	959.0	959.4	959.8	960.3	960.0
145°	1005.8	1006.3	1006.8	1007.3	1007.7	1008.3	1008.9	1009.6	1010.3	1011.0	1010.7
147.5°	1051.9	1052.7	1053.5	1054.4	1055.2	1055.9	1056.5	1057.2	1057.8	1058.4	1058.4
150°	1083.9	1084.4	1084.9	1085.3	1085.8	1086.2	1086.7	1087.1	1087.6	1088.1	1088.1
152.5°	1110.2	1110.9	1111.5	1112.1	1112.8	1113.3	1113.6	1113.8	1114.1	1114.4	1114.8
155°	1151.8	1151.8	1151.8	1151.8	1151.8	1151.9	1152.1	1152.3	1152.5	1152.8	1153.7
157.5°	1187.1	1186.8	1186.5	1186.3	1186.0	1186.0	1186.1	1186.3	1186.5	1186.7	1187.6
160°	1209.3	1208.9	1208.4	1207.9	1207.4	1207.2	1207.2	1207.2	1207.2	1207.2	1208.4
162.5°	1229.0	1228.4	1227.7	1227.1	1226.5	1226.2	1226.5	1226.6	1226.8	1226.9	1228.1
165°	1254.5	1253.8	1253.2	1252.4	1251.8	1251.4	1251.4	1251.4	1251.4	1251.4	1252.8
167.5°	1274.9	1273.9	1273.0	1272.1	1271.2	1270.8	1271.0	1271.2	1271.4	1271.5	1273.0
170°	1286.3	1285.5	1284.5	1283.7	1282.7	1282.2	1282.2	1282.2	1282.2	1282.2	1283.8
172.5°	1295.4	1294.5	1293.6	1292.7	1291.7	1291.3	1291.3	1291.3	1291.3	1291.3	1292.7
175°	1304.9	1303.9	1303.1	1302.1	1301.2	1300.8	1300.8	1300.8	1300.8	1300.8	1302.1
177.5°	1308.8	1308.1	1307.3	1306.5	1305.8	1305.4	1305.4	1305.4	1305.4	1305.4	1306.5
180°	1308.0	1308.0	1308.0	1308.0	1308.0	1308.0	1308.0	1308.0	1308.0	1308.0	1308.0



TEST NUMBER: P332485-927

CATALOG NUMBER: S123RDIW-S1165D1320U927-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1535.4	1535.4	1535.4	1535.4	1535.4	1535.4	1535.4	1535.4
2.5°	1529.3	1531.8	1534.1	1535.2	1534.7	1534.3	1533.8	1533.3
5°	1519.2	1521.7	1524.2	1525.1	1524.6	1524.0	1523.4	1522.9
7.5°	1497.8	1499.2	1500.6	1500.8	1499.8	1498.9	1497.9	1497.0
10°	1478.7	1478.9	1479.2	1478.7	1477.3	1475.9	1474.5	1473.1
12.5°	1454.8	1454.7	1454.5	1453.7	1452.1	1450.4	1448.8	1447.2
15°	1413.1	1411.7	1410.3	1408.7	1406.7	1404.8	1402.8	1400.9
17.5°	1363.2	1360.2	1357.2	1354.4	1351.5	1348.6	1345.8	1342.8
20°	1329.0	1325.3	1321.8	1318.3	1314.9	1311.6	1308.4	1305.0
22.5°	1292.3	1287.9	1283.3	1279.5	1276.4	1273.4	1270.3	1267.2
25°	1232.4	1226.5	1220.8	1216.3	1213.3	1210.2	1207.2	1204.1
27.5°	1167.0	1159.0	1150.9	1144.5	1139.9	1135.3	1130.6	1125.9
30°	1120.5	1111.2	1101.8	1094.9	1090.4	1086.0	1081.6	1077.1
32.5°	1075.0	1064.7	1054.4	1046.9	1042.3	1037.6	1033.0	1028.3
35°	1007.3	995.4	983.5	975.0	970.0	965.0	960.0	955.1
37.5°	934.5	921.1	907.5	897.7	891.6	885.4	879.3	873.1
40°	884.0	869.6	855.2	844.9	838.4	832.1	825.8	819.4
42.5°	835.5	819.8	804.1	793.4	787.7	782.0	776.3	770.6
45°	764.1	748.4	732.6	721.4	714.8	708.1	701.5	694.8
47.5°	690.4	673.3	656.1	644.6	638.7	632.7	626.8	620.9
50°	640.6	623.4	606.3	594.5	588.2	581.8	575.4	569.1
52.5°	592.5	574.6	556.8	545.0	539.3	533.7	528.0	522.3
55°	520.8	504.7	488.7	477.9	472.4	466.8	461.3	455.7
57.5°	450.4	435.1	420.0	410.0	405.4	400.7	395.9	391.3
60°	405.9	391.0	376.0	366.2	361.6	356.8	352.1	347.5
62.5°	361.9	347.8	333.7	324.3	319.3	314.4	309.5	304.6
65°	299.1	285.6	272.0	263.7	260.7	257.6	254.6	251.5
67.5°	239.2	229.1	219.0	212.3	209.1	205.7	202.5	199.2
70°	202.2	192.6	182.9	176.6	173.5	170.5	167.4	164.4
72.5°	169.0	161.1	153.1	148.5	147.3	146.0	144.7	143.5
75°	126.4	123.7	120.9	119.3	118.7	118.2	117.6	117.1
77.5°	95.4	93.9	92.4	91.3	90.8	90.2	89.7	89.1
80°	76.8	76.0	75.1	74.5	73.9	73.4	72.8	72.2
82.5°	58.9	58.1	57.2	56.7	56.6	56.5	56.4	56.3
85°	33.7	33.2	32.6	32.4	32.4	32.4	32.4	32.4
87.5°	17.8	17.7	17.7	17.7	17.5	17.3	17.3	17.1
90°	26.5	27.4	28.3	29.0	29.5	29.9	30.3	30.8
92.5°	40.9	41.7	42.4	42.6	42.3	42.1	41.7	41.5
95°	77.9	78.7	79.7	80.2	80.2	80.2	80.2	80.2
97.5°	121.0	122.2	123.2	123.7	123.6	123.5	123.4	123.3
100°	152.4	153.0	153.8	154.3	154.8	155.3	155.7	156.1
102.5°	188.5	189.3	190.0	190.2	190.1	190.0	190.0	189.9
105°	242.5	242.5	242.5	242.7	243.2	243.6	244.1	244.5
107.5°	300.9	301.6	302.3	302.5	302.3	302.0	301.7	301.4
110°	339.8	340.8	341.7	341.9	341.4	341.0	340.6	340.1



TEST NUMBER: P332485-927

CATALOG NUMBER: S123RDIW-S1165D1320U927-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	378.8	379.9	381.0	381.5	381.4	381.4	381.3	381.2
115°	438.2	438.4	438.6	438.6	438.4	438.2	437.9	437.7
117.5°	498.0	498.0	497.9	497.6	496.9	496.3	495.7	495.0
120°	537.9	537.7	537.5	537.1	536.7	536.2	535.8	535.3
122.5°	578.3	577.7	577.1	576.5	575.8	575.2	574.6	573.9
125°	638.3	637.4	636.4	635.6	634.6	633.7	632.8	631.8
127.5°	697.5	696.2	695.0	693.8	692.8	691.7	690.7	689.6
130°	736.9	736.0	735.1	733.8	732.2	730.6	729.0	727.5
132.5°	775.2	774.0	773.0	771.8	770.6	769.4	768.1	766.9
135°	832.4	831.6	830.6	830.0	829.5	829.0	828.5	828.1
137.5°	888.4	887.5	886.5	885.7	884.8	883.9	883.0	882.2
140°	925.3	925.0	924.8	923.9	922.3	920.7	919.1	917.5
142.5°	959.8	959.6	959.3	958.6	957.4	956.2	954.9	953.7
145°	1010.5	1010.3	1010.1	1009.6	1008.6	1007.7	1006.8	1005.8
147.5°	1058.4	1058.4	1058.4	1057.8	1056.5	1055.0	1053.7	1052.3
150°	1088.1	1088.1	1088.1	1087.3	1086.0	1084.7	1083.2	1081.9
152.5°	1115.1	1115.5	1115.8	1115.4	1114.2	1113.0	1111.8	1110.6
155°	1154.6	1155.6	1156.4	1156.1	1154.5	1152.9	1151.3	1149.7
157.5°	1188.6	1189.5	1190.6	1190.3	1189.1	1187.8	1186.5	1185.3
160°	1209.5	1210.7	1211.8	1212.0	1211.0	1210.1	1209.2	1208.2
162.5°	1229.2	1230.4	1231.5	1231.4	1229.9	1228.4	1227.0	1225.5
165°	1254.2	1255.5	1256.9	1256.8	1255.2	1253.6	1252.0	1250.4
167.5°	1274.4	1275.8	1277.2	1277.2	1275.8	1274.4	1273.0	1271.5
170°	1285.5	1287.1	1288.6	1288.6	1287.1	1285.5	1283.8	1282.2
172.5°	1294.1	1295.5	1297.0	1296.9	1295.3	1293.6	1292.0	1290.5
175°	1303.5	1304.9	1306.2	1306.1	1304.5	1302.9	1301.3	1299.7
177.5°	1307.7	1308.8	1309.9	1309.8	1308.4	1307.2	1305.9	1304.6
180°	1308.0	1308.0	1308.0	1308.0	1308.0	1308.0	1308.0	1308.0

(END OF REPORT)