

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331536-840

Luminaire Tested: **S122DIW-S675D710U840-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331536-840
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-8,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122DIW-S675D710U840-4F0-1E-UDD-F1
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 675 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 710 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5214.3 lumens
Efficiency: N/A
Efficacy: 115.9 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.3
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 45
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331536-840

CATALOG NUMBER: S122DIW-S675D710U840-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P331536-840

CATALOG NUMBER: S122DIW-S675D710U840-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	108	108	108	108	100	100	100	100	85	85	85	71	71	71	58	58	58	52
1	98	94	90	87	91	87	84	81	74	72	70	62	61	59	52	50	49	44
2	90	82	76	71	83	76	71	66	65	61	58	55	52	49	45	43	41	37
3	82	72	65	59	75	67	61	55	57	52	48	48	45	42	40	38	35	31
4	75	64	56	50	69	59	52	47	51	46	41	43	39	36	36	33	30	27
5	69	57	49	43	63	53	46	40	46	40	36	39	34	31	32	29	27	23
6	63	51	43	37	58	48	40	35	41	35	31	35	31	27	29	26	23	20
7	58	46	38	33	54	43	36	31	37	32	27	32	27	24	27	23	21	18
8	54	42	34	29	50	39	32	27	34	28	24	29	25	21	25	21	19	16
9	51	38	31	26	47	36	29	24	31	26	22	27	22	19	23	19	17	15
10	47	35	28	23	44	33	26	22	29	23	20	25	21	17	21	18	15	13

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	17312	17312	17312
5°	17378	17126	17227
10°	17274	16952	17038
15°	17060	16732	16715
20°	16756	16402	16385
25°	16456	15998	15998
30°	16067	15627	15491
35°	15707	15179	14954
40°	15253	14731	14450
45°	14805	14289	13935
50°	14320	13828	13335
55°	13813	13292	12797
60°	13249	12649	12184
65°	12642	12015	11461
70°	11877	11240	10707
75°	10805	10356	10100
80°	9586	9298	8815
85°	7836	7447	6688



TEST NUMBER: P331536-840

CATALOG NUMBER: S122DIW-S675D710U840-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	100.8	1.9
10°-20°	283.7	5.4
20°-30°	417.0	8.0
30°-40°	484.3	9.3
40°-50°	483.8	9.3
50°-60°	421.9	8.1
60°-70°	312.0	6.0
70°-80°	176.7	3.4
80°-90°	51.1	1.0
90°-100°	56.3	1.1
100°-110°	174.8	3.4
110°-120°	298.7	5.7
120°-130°	392.8	7.5
130°-140°	440.9	8.5
140°-150°	432.3	8.3
150°-160°	362.6	7.0
160°-170°	240.5	4.6
170°-180°	84.1	1.6
0°-30°	801.5	15.4
0°-40°	1285.8	24.7
0°-60°	2191.5	42.0
0°-90°	2731.3	52.4
90°-120°	529.8	10.2
90°-150°	1795.8	34.4
90°-180°	2483.0	47.6
0°-180°	5214.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1072	1072	1072	1072	1072	
5°	1072	1068	1057	1064	1063	102
15°	1021	1014	1001	1005	1000	287
25°	924	915	898	900	898	425
35°	797	786	770	764	759	497
45°	648	641	626	615	610	500
55°	491	484	472	460	455	439
65°	331	324	314	305	300	327
75°	173	171	166	160	162	185
85°	42	41	40	37	36	48
90°	1	10	26	25	25	4
95°	39	46	48	48	46	45
105°	161	163	165	166	166	170
115°	300	304	303	302	300	296
125°	436	442	441	438	438	390
135°	564	572	574	573	571	436
145°	685	690	695	695	692	428
155°	783	785	788	791	789	360
165°	852	851	851	856	853	240
175°	886	884	883	888	884	84
180°	888	888	888	888	888	



TEST NUMBER: P331536-840

CATALOG NUMBER: S122DIW-S675D710U840-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1072.2	1072.2	1072.2	1072.2	1072.2	1072.2	1072.2	1072.2	1072.2	1072.2	1072.2
2.5°	1077.1	1076.2	1075.3	1074.4	1073.5	1072.0	1070.0	1067.9	1065.9	1063.9	1065.7
5°	1072.2	1071.3	1070.4	1069.4	1068.5	1066.8	1064.3	1061.8	1059.2	1056.7	1058.5
7.5°	1062.7	1061.3	1059.9	1058.4	1057.0	1055.0	1052.5	1049.9	1047.3	1044.7	1046.5
10°	1053.6	1052.0	1050.4	1048.7	1047.2	1045.0	1042.3	1039.6	1036.7	1034.0	1035.8
12.5°	1041.3	1039.9	1038.3	1036.9	1035.5	1033.5	1030.7	1027.9	1025.2	1022.5	1023.8
15°	1020.6	1019.3	1017.8	1016.5	1015.1	1012.9	1010.0	1006.9	1004.0	1001.0	1002.0
17.5°	994.2	992.8	991.5	990.1	988.8	986.5	983.5	980.5	977.4	974.4	975.5
20°	975.2	973.9	972.5	971.1	969.8	967.5	964.2	961.1	957.9	954.6	955.3
22.5°	956.2	954.3	952.4	950.5	948.6	946.1	943.1	940.1	937.1	934.0	934.1
25°	923.7	921.9	920.1	918.2	916.4	913.5	909.6	905.7	901.8	898.0	898.4
27.5°	886.6	884.9	883.3	881.6	880.0	877.7	874.5	871.5	868.4	865.4	864.6
30°	861.8	860.0	858.2	856.4	854.5	851.9	848.5	845.1	841.6	838.2	837.5
32.5°	835.5	833.9	832.5	831.0	829.6	827.1	823.4	819.8	816.2	812.5	811.3
35°	796.9	794.7	792.3	790.0	787.7	784.8	781.1	777.4	773.8	770.1	768.7
37.5°	753.4	751.3	749.3	747.3	745.4	742.5	738.8	735.2	731.5	727.8	726.1
40°	723.7	721.9	720.0	718.2	716.4	713.7	709.9	706.3	702.7	698.9	696.9
42.5°	694.9	693.0	691.2	689.3	687.5	684.8	681.1	677.4	673.8	670.1	667.8
45°	648.4	646.8	645.2	643.7	642.1	639.5	636.1	632.7	629.2	625.8	623.3
47.5°	602.3	600.8	599.3	597.7	596.2	593.7	590.1	586.5	583.0	579.4	576.7
50°	570.1	569.0	567.8	566.6	565.5	563.3	560.2	556.9	553.7	550.5	547.3
52.5°	538.8	537.2	535.7	534.2	532.7	530.5	527.5	524.4	521.4	518.4	515.7
55°	490.7	489.4	488.0	486.6	485.2	483.1	480.4	477.7	474.9	472.2	469.4
57.5°	442.4	441.4	440.3	439.2	438.1	436.1	433.0	430.0	427.0	423.9	421.2
60°	410.3	409.4	408.5	407.6	406.7	404.6	401.4	398.2	395.0	391.7	389.2
62.5°	379.0	377.5	376.1	374.6	373.1	371.1	368.7	366.2	363.8	361.2	358.9
65°	330.9	329.5	328.2	326.8	325.4	323.6	321.3	319.0	316.7	314.5	312.4
67.5°	282.1	280.9	279.8	278.7	277.6	276.1	274.0	272.0	269.9	267.8	266.2
70°	251.6	250.6	249.7	248.8	247.9	246.4	244.3	242.3	240.2	238.1	236.5
72.5°	220.3	219.2	218.3	217.4	216.5	215.4	214.1	212.8	211.5	210.1	208.5
75°	173.2	172.7	172.3	171.8	171.4	170.6	169.5	168.2	167.1	166.0	164.6
77.5°	131.2	130.4	129.6	128.8	128.1	127.4	126.9	126.4	126.0	125.5	124.9
80°	103.1	102.9	102.6	102.4	102.2	101.8	101.4	100.9	100.5	100.0	99.3
82.5°	76.7	76.6	76.6	76.5	76.5	76.3	76.0	75.8	75.5	75.2	74.4
85°	42.3	42.0	41.8	41.6	41.3	41.1	40.9	40.7	40.4	40.2	39.5
87.5°	14.9	15.0	15.0	15.0	15.1	15.3	15.7	16.1	16.5	16.8	16.2
90°	0.7	2.7	4.7	6.8	8.8	11.6	15.2	18.9	22.5	26.3	25.9
92.5°	13.3	14.8	16.3	17.8	19.2	20.4	21.2	22.1	22.9	23.8	23.9
95°	39.0	40.6	42.3	43.9	45.6	46.7	47.0	47.3	47.7	48.0	48.0
97.5°	71.2	72.6	74.1	75.5	77.1	78.1	78.8	79.4	80.0	80.6	80.6
100°	95.1	96.5	97.9	99.2	100.5	101.4	101.9	102.4	102.9	103.4	103.4
102.5°	120.4	121.4	122.5	123.5	124.6	125.4	126.1	126.7	127.3	127.9	128.2
105°	161.1	161.6	162.1	162.6	163.1	163.5	163.9	164.2	164.5	164.9	165.2
107.5°	202.2	202.9	203.7	204.4	205.1	205.5	205.5	205.5	205.5	205.5	205.6
110°	228.5	229.5	230.6	231.6	232.6	233.1	233.1	233.1	233.1	233.1	233.1



TEST NUMBER: P331536-840

CATALOG NUMBER: S122DIW-S675D710U840-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	257.3	258.3	259.3	260.3	261.4	261.8	261.7	261.5	261.4	261.3	260.8
115°	299.7	300.7	301.7	302.8	303.8	304.1	303.8	303.4	303.1	302.8	302.6
117.5°	342.0	343.4	344.7	346.0	347.3	347.5	346.6	345.7	344.8	343.9	343.5
120°	370.2	371.5	372.8	374.2	375.5	375.5	374.2	372.8	371.5	370.2	370.2
122.5°	396.0	397.6	399.2	400.7	402.3	402.7	401.7	400.8	399.9	399.0	398.6
125°	436.2	437.7	439.1	440.6	442.1	442.6	442.1	441.6	441.1	440.6	440.1
127.5°	475.2	477.2	479.1	480.9	482.8	483.5	482.9	482.3	481.7	481.1	480.5
130°	499.8	502.0	504.1	506.3	508.5	509.4	509.1	508.8	508.4	508.1	507.8
132.5°	527.5	529.2	531.0	532.7	534.4	535.4	535.4	535.5	535.6	535.6	534.9
135°	564.3	566.1	567.9	569.8	571.6	572.7	573.0	573.4	573.7	574.0	573.8
137.5°	603.1	604.6	606.1	607.6	609.0	610.1	610.5	611.0	611.4	611.8	611.7
140°	626.5	627.9	629.4	631.0	632.5	633.6	634.5	635.3	636.1	636.9	636.9
142.5°	650.5	652.0	653.5	655.0	656.4	657.5	658.0	658.6	659.1	659.7	659.8
145°	684.9	686.1	687.2	688.4	689.6	690.6	691.7	692.7	693.7	694.7	694.8
147.5°	715.7	717.0	718.4	719.8	721.2	722.3	723.0	723.6	724.3	725.0	725.3
150°	736.6	737.6	738.6	739.6	740.6	741.4	742.1	742.8	743.5	744.2	744.7
152.5°	755.2	756.2	757.2	758.2	759.2	760.1	760.9	761.7	762.5	763.4	764.0
155°	783.0	783.6	784.1	784.6	785.1	785.6	786.1	786.6	787.1	787.6	788.4
157.5°	806.9	807.3	807.6	807.9	808.3	808.6	808.9	809.2	809.5	809.8	810.9
160°	821.3	821.6	821.9	822.3	822.6	822.9	823.0	823.2	823.3	823.5	824.6
162.5°	834.5	834.6	834.7	834.7	834.8	834.9	835.1	835.3	835.4	835.6	836.7
165°	852.0	851.8	851.7	851.5	851.4	851.3	851.3	851.3	851.3	851.3	852.4
167.5°	866.8	866.3	865.8	865.3	864.7	864.4	864.4	864.3	864.3	864.3	865.5
170°	874.5	874.0	873.5	873.0	872.5	872.2	872.0	871.8	871.7	871.5	872.7
172.5°	879.9	879.4	878.9	878.4	877.9	877.6	877.4	877.3	877.1	876.9	878.1
175°	886.5	886.1	885.6	885.0	884.5	884.1	883.7	883.4	883.1	882.7	883.9
177.5°	889.2	888.8	888.4	888.0	887.6	887.3	887.0	886.8	886.5	886.2	887.0
180°	888.0	888.0	888.0	888.0	888.0	888.0	888.0	888.0	888.0	888.0	888.0



TEST NUMBER: P331536-840

CATALOG NUMBER: S122DIW-S675D710U840-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1072.2	1072.2	1072.2	1072.2	1072.2	1072.2	1072.2	1072.2
2.5°	1067.5	1069.4	1071.3	1072.0	1071.6	1071.3	1070.9	1070.6
5°	1060.4	1062.2	1064.0	1064.7	1064.3	1063.8	1063.4	1062.9
7.5°	1048.4	1050.3	1052.1	1052.7	1052.2	1051.8	1051.3	1050.8
10°	1037.6	1039.6	1041.4	1041.9	1041.3	1040.6	1039.9	1039.2
12.5°	1025.0	1026.3	1027.6	1027.9	1027.4	1027.0	1026.5	1026.0
15°	1002.9	1003.8	1004.7	1004.6	1003.4	1002.3	1001.2	1000.0
17.5°	976.5	977.5	978.7	978.7	977.5	976.4	975.3	974.2
20°	956.0	956.7	957.4	957.3	956.3	955.4	954.5	953.6
22.5°	934.3	934.4	934.5	934.3	933.8	933.2	932.7	932.2
25°	898.9	899.3	899.8	899.8	899.3	898.9	898.4	898.0
27.5°	863.9	863.3	862.6	861.7	860.6	859.5	858.4	857.3
30°	836.8	836.1	835.4	834.6	833.6	832.7	831.8	830.9
32.5°	810.1	808.9	807.6	806.6	805.7	804.8	803.8	802.8
35°	767.4	766.0	764.6	763.4	762.2	761.0	759.9	758.7
37.5°	724.5	722.8	721.0	719.6	718.5	717.4	716.4	715.3
40°	694.9	692.8	690.7	689.2	688.3	687.4	686.5	685.6
42.5°	665.6	663.4	661.2	659.3	658.0	656.8	655.5	654.2
45°	620.8	618.2	615.7	614.0	613.1	612.2	611.3	610.3
47.5°	574.1	571.4	568.8	566.7	565.4	564.1	562.8	561.5
50°	544.1	540.9	537.7	535.5	534.3	533.2	532.1	530.9
52.5°	513.0	510.4	507.8	505.6	504.1	502.6	501.1	499.6
55°	466.7	463.9	461.2	459.2	458.1	457.0	455.8	454.6
57.5°	418.5	415.8	413.1	411.3	410.4	409.6	408.7	407.8
60°	386.7	384.2	381.6	380.1	379.4	378.7	378.0	377.3
62.5°	356.6	354.3	351.9	350.3	349.4	348.5	347.7	346.8
65°	310.3	308.2	306.2	304.6	303.5	302.3	301.1	300.0
67.5°	264.6	263.1	261.5	260.1	259.2	258.3	257.4	256.5
70°	234.9	233.4	231.8	230.5	229.5	228.6	227.7	226.8
72.5°	206.9	205.3	203.7	202.5	201.8	201.1	200.4	199.5
75°	163.2	161.9	160.5	160.1	160.5	161.0	161.4	161.9
77.5°	124.2	123.5	122.8	122.2	121.5	120.9	120.3	119.6
80°	98.7	98.0	97.3	96.6	96.2	95.7	95.3	94.8
82.5°	73.5	72.6	71.8	71.3	71.2	71.1	71.0	70.9
85°	38.9	38.2	37.5	37.0	36.8	36.6	36.4	36.1
87.5°	15.6	14.9	14.3	13.9	13.8	13.6	13.5	13.3
90°	25.5	25.2	24.9	24.8	24.9	25.1	25.3	25.4
92.5°	23.9	24.0	24.1	24.1	24.1	24.2	24.2	24.2
95°	48.0	48.0	48.0	47.8	47.5	47.2	46.8	46.5
97.5°	80.6	80.6	80.6	80.6	80.6	80.6	80.5	80.5
100°	103.4	103.4	103.4	103.3	103.2	103.0	102.8	102.7
102.5°	128.3	128.4	128.6	128.6	128.4	128.2	128.1	127.8
105°	165.5	165.8	166.2	166.3	166.3	166.3	166.3	166.3
107.5°	205.7	205.9	206.0	205.7	204.9	204.2	203.4	202.7
110°	233.1	233.1	233.1	232.8	232.3	231.8	231.3	230.9



TEST NUMBER: P331536-840

CATALOG NUMBER: S122DIW-S675D710U840-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	260.4	260.0	259.6	259.2	258.9	258.5	258.1	257.8
115°	302.5	302.3	302.1	301.7	301.2	300.7	300.2	299.7
117.5°	343.1	342.6	342.2	341.7	341.2	340.7	340.2	339.7
120°	370.2	370.2	370.2	369.9	369.4	368.9	368.4	367.9
122.5°	398.2	397.8	397.4	397.0	396.6	396.3	395.9	395.6
125°	439.6	439.1	438.6	438.3	438.2	438.0	437.8	437.7
127.5°	479.9	479.3	478.7	478.2	477.6	477.1	476.6	476.1
130°	507.5	507.1	506.8	506.2	505.5	504.9	504.2	503.6
132.5°	534.2	533.4	532.7	532.1	531.6	531.0	530.5	530.0
135°	573.7	573.5	573.4	573.0	572.5	572.0	571.5	571.0
137.5°	611.5	611.4	611.3	610.9	610.2	609.6	608.8	608.1
140°	636.9	636.9	636.9	636.6	636.0	635.3	634.6	634.0
142.5°	660.0	660.1	660.2	660.0	659.3	658.6	658.0	657.3
145°	695.0	695.2	695.3	695.1	694.4	693.8	693.1	692.5
147.5°	725.7	726.0	726.4	726.3	725.7	725.0	724.4	723.8
150°	745.1	745.6	746.1	746.1	745.6	745.1	744.7	744.2
152.5°	764.6	765.2	765.9	765.9	765.2	764.6	764.0	763.4
155°	789.2	790.1	790.9	791.1	790.6	790.1	789.6	789.1
157.5°	812.0	813.1	814.3	814.5	813.6	812.8	812.0	811.2
160°	825.6	826.6	827.6	827.7	827.1	826.4	825.8	825.1
162.5°	837.8	839.0	840.1	840.2	839.4	838.7	837.9	837.1
165°	853.6	854.7	856.0	856.2	855.3	854.4	853.6	852.8
167.5°	866.7	867.8	869.0	869.1	868.3	867.4	866.6	865.7
170°	873.8	875.0	876.2	876.3	875.3	874.2	873.2	872.2
172.5°	879.3	880.4	881.6	881.6	880.7	879.7	878.7	877.7
175°	885.0	886.3	887.5	887.5	886.5	885.6	884.5	883.5
177.5°	887.8	888.6	889.4	889.4	888.6	887.8	887.0	886.2
180°	888.0	888.0	888.0	888.0	888.0	888.0	888.0	888.0

(END OF REPORT)