

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331537-840

Luminaire Tested: **S122DIW-S675D970U840-4F0-1E-UDD-A**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P331537-840  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S122DIW-S675D970U840-4F0-1E-UDD-A  
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 675 LUMENS PER FOOT, ASYMMETRIC DIFFUSER  
UPLIGHT 970 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 6870.7 lumens  
Efficiency: N/A  
Efficacy: 130.6 lumens/watt  
Spacing Criteria (0/90/45): 1.08 / 1.16 / 1.23  
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')  
CIE Type: General Diffuse  
  
Input Watts (W): 52.6  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P331537-840

CATALOG NUMBER: S122DIW-S675D970U840-4F0-1E-UDD-A

### Luminous Intensity Polar Plot





TEST NUMBER: P331537-840

CATALOG NUMBER: S122DIW-S675D970U840-4F0-1E-UDD-A

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	106	106	106	106	96	96	96	96	80	80	80	64	64	64	50	50	50	43
1	97	93	89	85	88	85	82	79	70	68	66	57	55	54	45	44	43	37
2	88	81	75	70	81	75	70	65	62	58	55	50	48	46	40	38	37	32
3	81	72	65	59	74	66	60	55	55	51	47	45	42	39	36	34	32	27
4	74	64	56	50	68	59	52	47	49	44	40	40	37	34	32	30	28	24
5	68	57	49	43	62	53	46	41	44	39	35	36	33	30	29	26	24	21
6	63	51	43	38	57	47	40	35	40	35	31	33	29	26	27	24	22	19
7	58	46	39	33	53	43	36	31	36	31	27	30	26	23	24	22	19	17
8	54	42	35	29	49	39	32	28	33	28	24	28	24	21	22	20	18	15
9	50	39	31	26	46	36	29	25	30	25	22	25	22	19	21	18	16	14
10	47	35	28	24	43	33	27	22	28	23	20	24	20	17	19	17	15	13

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	21658	21658	21658	21658
5°	24280	21797	19316	21797
10°	27824	21620	16718	21620
15°	30780	21224	14770	21224
20°	30311	20797	13464	20797
25°	27332	20232	12636	20232
30°	22585	19328	12033	19328
35°	16462	18382	11606	18382
40°	13148	17266	11367	17266
45°	11488	15972	11040	15972
50°	10798	14722	10826	14722
55°	9956	13453	10536	13453
60°	9122	12103	10091	12103
65°	8309	10892	9650	10892
70°	7544	9711	9007	9711
75°	6687	8390	7973	8390
80°	5755	6946	6425	6946
85°	5169	5169	3816	5169



TEST NUMBER: P331537-840

CATALOG NUMBER: S122DIW-S675D970U840-4F0-1E-UDD-A

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	127.7	1.9
10°-20°	371.4	5.4
20°-30°	539.0	7.8
30°-40°	568.8	8.3
40°-50°	503.6	7.3
50°-60°	401.9	5.8
60°-70°	273.2	4.0
70°-80°	140.0	2.0
80°-90°	37.1	0.5
90°-100°	44.5	0.6
100°-110°	163.1	2.4
110°-120°	436.1	6.3
120°-130°	719.8	10.5
130°-140°	765.5	11.1
140°-150°	711.5	10.4
150°-160°	572.1	8.3
160°-170°	368.6	5.4
170°-180°	126.9	1.8
0°-30°	1038.1	15.1
0°-40°	1606.9	23.4
0°-60°	2512.4	36.6
0°-90°	2962.6	43.1
90°-120°	643.7	9.4
90°-150°	2840.5	41.3
90°-180°	3908.0	56.9
0°-180°	6870.7	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	1341	1341	1341	1341	1341	
5°	1498	1345	1192	1345	1498	150
15°	1841	1270	884	1270	1841	508
25°	1534	1136	709	1136	1534	693
35°	835	933	589	933	835	543
45°	503	700	484	700	503	396
55°	354	478	374	478	354	317
65°	218	285	253	285	218	216
75°	107	134	128	134	107	115
85°	28	28	21	28	28	31
90°	26	1	26	1	26	13
95°	42	63	42	63	42	39
105°	73	293	73	293	73	76
115°	79	555	79	555	79	198
125°	825	784	825	784	825	714
135°	1003	971	1003	971	1003	773
145°	1144	1126	1144	1126	1144	715
155°	1241	1240	1241	1240	1241	573
165°	1304	1307	1304	1307	1304	368
175°	1329	1336	1329	1336	1329	127
180°	1334	1334	1334	1334	1334	



TEST NUMBER: P331537-840

CATALOG NUMBER: S122DIW-S675D970U840-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4
2.5°	1403.2	1403.6	1404.5	1397.9	1397.0	1397.0	1391.3	1386.3	1380.6	1372.7	1373.5
5°	1498.1	1503.8	1505.8	1499.6	1490.4	1489.3	1480.6	1466.1	1452.7	1441.9	1434.2
7.5°	1611.3	1613.6	1608.5	1600.3	1593.5	1581.1	1564.8	1548.8	1526.4	1505.9	1490.7
10°	1697.1	1700.2	1691.4	1679.6	1669.8	1655.4	1631.6	1607.4	1578.0	1549.6	1526.9
12.5°	1762.2	1769.9	1758.7	1757.1	1740.3	1720.5	1692.2	1680.0	1638.6	1599.1	1574.8
15°	1841.4	1840.9	1842.0	1832.2	1819.8	1816.6	1786.8	1754.3	1696.1	1672.8	1632.6
17.5°	1818.6	1826.3	1830.0	1829.9	1829.6	1827.7	1818.1	1797.6	1768.4	1730.7	1684.3
20°	1764.1	1774.4	1775.9	1787.9	1794.5	1803.3	1806.9	1801.2	1783.2	1751.7	1711.5
22.5°	1680.0	1682.8	1687.7	1706.2	1720.7	1742.6	1754.1	1773.2	1766.3	1750.9	1717.3
25°	1534.2	1529.0	1547.1	1556.3	1589.8	1624.9	1650.2	1678.0	1702.7	1717.7	1707.9
27.5°	1359.1	1351.4	1378.4	1403.0	1430.3	1468.2	1507.6	1554.1	1592.8	1641.1	1657.7
30°	1211.4	1216.1	1241.9	1268.2	1309.4	1363.0	1407.3	1458.4	1513.6	1567.7	1605.3
32.5°	1052.3	1070.2	1086.4	1126.7	1163.0	1222.8	1287.8	1351.6	1420.4	1481.9	1540.1
35°	835.2	855.8	878.5	907.9	958.9	1018.1	1081.6	1167.6	1261.5	1345.5	1414.6
37.5°	703.0	699.6	712.7	733.9	775.3	823.0	896.1	981.2	1091.6	1190.3	1287.8
40°	623.8	621.7	631.0	650.6	682.1	717.1	781.0	855.8	958.4	1078.9	1195.0
42.5°	569.4	570.6	575.7	589.6	611.1	640.0	687.8	751.4	845.4	959.0	1083.6
45°	503.1	506.8	512.4	519.2	531.5	555.2	582.0	627.4	701.7	796.5	919.2
47.5°	455.6	455.7	461.4	467.3	474.6	488.0	509.9	538.3	590.7	667.9	773.4
50°	429.9	426.4	430.5	435.0	442.8	452.1	466.6	493.3	528.4	590.8	678.9
52.5°	398.6	398.7	402.4	404.1	411.1	420.3	433.5	452.1	483.8	532.6	605.1
55°	353.7	356.2	358.3	361.3	367.6	374.3	384.6	397.0	421.7	458.3	511.9
57.5°	311.3	312.1	314.3	320.1	324.1	330.2	340.0	351.2	367.4	394.5	434.7
60°	282.5	282.5	286.6	289.2	294.4	300.5	308.3	319.1	333.6	355.7	388.2
62.5°	256.1	255.7	257.3	261.6	265.5	271.2	279.0	288.2	301.7	321.4	348.2
65°	217.5	216.5	219.6	220.7	224.8	230.5	236.6	246.4	257.2	271.7	295.4
67.5°	180.5	181.7	183.3	185.3	187.5	193.5	197.6	204.6	213.7	225.7	241.8
70°	159.8	159.8	159.8	161.4	164.4	167.5	171.7	177.3	186.1	196.4	210.9
72.5°	136.7	138.4	140.0	139.1	143.0	144.8	149.8	153.0	161.4	167.9	180.8
75°	107.2	107.2	107.2	109.8	111.4	112.9	116.0	119.1	123.2	131.5	138.1
77.5°	80.0	79.8	80.3	80.9	82.6	84.4	85.3	88.2	92.0	95.7	101.5
80°	61.9	62.9	63.4	64.4	64.4	65.4	65.9	69.6	72.2	74.7	78.4
82.5°	47.9	48.1	48.2	48.4	48.8	49.4	50.7	51.9	52.8	54.9	57.8
85°	27.9	27.4	27.4	28.4	27.9	27.9	28.9	29.9	29.9	30.4	31.9
87.5°	16.0	15.9	16.2	15.7	15.6	15.9	15.7	15.0	15.2	15.5	15.5
90°	26.1	25.7	25.1	24.7	24.3	23.6	22.5	21.4	20.4	19.3	17.6
92.5°	26.1	25.8	25.5	25.2	25.0	24.6	24.0	23.5	22.9	22.4	21.5
95°	41.5	41.7	41.9	42.1	42.3	41.9	40.9	39.8	38.7	37.7	36.2
97.5°	55.3	55.1	54.8	54.6	54.3	53.8	52.9	52.1	51.2	50.4	46.9
100°	64.6	64.2	63.8	63.3	62.9	61.9	60.2	58.5	56.8	55.0	51.4
102.5°	69.3	68.7	68.1	67.5	66.9	65.4	63.2	61.0	58.8	56.6	87.1
105°	73.3	72.5	71.6	70.8	69.9	68.3	65.9	63.6	61.2	58.9	117.4
107.5°	75.4	74.6	73.7	72.9	72.0	72.8	75.2	77.6	80.0	82.4	152.6
110°	76.2	75.3	74.5	73.6	72.8	83.1	104.5	125.9	147.4	168.8	230.9



TEST NUMBER: P331537-840

CATALOG NUMBER: S122DIW-S675D970U840-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	77.1	76.3	75.6	74.9	74.2	113.0	191.3	269.4	347.7	426.0	441.2
115°	79.2	94.5	110.0	125.4	140.9	198.2	297.5	396.8	496.0	595.4	590.1
117.5°	323.1	373.9	424.5	475.2	526.0	563.4	587.4	611.4	635.4	659.4	655.8
120°	588.7	617.5	646.5	675.5	704.4	717.6	715.0	712.5	709.9	707.3	703.5
122.5°	734.6	740.1	745.8	751.3	757.0	759.0	757.5	756.0	754.4	752.9	748.6
125°	825.1	824.4	823.7	823.1	822.4	821.4	819.9	818.4	816.9	815.4	811.3
127.5°	882.1	882.0	881.9	881.8	881.6	880.5	878.3	876.2	873.9	871.7	868.7
130°	917.7	917.9	918.1	918.3	918.6	917.5	915.1	912.7	910.4	908.1	905.6
132.5°	952.4	952.6	952.8	953.0	953.3	952.4	950.4	948.4	946.3	944.3	941.9
135°	1002.6	1003.0	1003.4	1003.9	1004.3	1003.4	1001.3	999.2	997.0	994.9	992.9
137.5°	1048.3	1049.0	1049.8	1050.6	1051.3	1050.6	1048.4	1046.3	1044.3	1042.2	1040.0
140°	1076.9	1077.9	1079.0	1080.2	1081.2	1080.8	1078.8	1076.9	1075.0	1073.1	1070.7
142.5°	1104.7	1105.8	1106.8	1107.9	1108.9	1108.6	1106.9	1105.1	1103.4	1101.6	1098.9
145°	1143.5	1144.6	1145.6	1146.7	1147.8	1147.5	1146.1	1144.6	1143.1	1141.6	1137.9
147.5°	1177.6	1178.5	1179.4	1180.3	1181.2	1181.1	1180.0	1178.9	1177.8	1176.7	1173.1
150°	1198.5	1199.5	1200.6	1201.7	1202.7	1202.6	1201.3	1200.1	1198.8	1197.5	1194.1
152.5°	1216.3	1217.7	1219.1	1220.5	1221.9	1221.9	1220.6	1219.4	1218.1	1216.8	1213.6
155°	1240.9	1242.6	1244.4	1246.1	1247.8	1248.0	1246.7	1245.5	1244.2	1242.8	1240.3
157.5°	1263.5	1265.2	1266.9	1268.5	1270.2	1270.3	1268.9	1267.4	1266.0	1264.5	1262.6
160°	1276.7	1278.2	1279.6	1281.1	1282.6	1282.7	1281.4	1280.2	1278.9	1277.6	1276.4
162.5°	1287.5	1289.3	1291.1	1292.9	1294.8	1295.1	1293.5	1292.1	1290.6	1289.2	1288.1
165°	1303.6	1305.1	1306.7	1308.2	1309.7	1309.7	1308.2	1306.7	1305.1	1303.6	1303.0
167.5°	1313.9	1315.9	1317.8	1319.7	1321.6	1321.8	1320.3	1318.8	1317.3	1315.9	1315.2
170°	1320.1	1322.0	1323.9	1325.9	1327.8	1328.0	1326.5	1325.0	1323.5	1322.0	1321.6
172.5°	1324.7	1326.7	1328.6	1330.5	1332.4	1332.6	1331.1	1329.6	1328.2	1326.7	1326.2
175°	1328.8	1330.9	1333.0	1335.1	1337.4	1337.7	1336.2	1334.6	1333.1	1331.6	1331.2
177.5°	1331.3	1332.8	1334.3	1335.8	1337.5	1337.6	1336.4	1335.2	1334.0	1332.8	1332.6
180°	1333.5	1333.5	1333.5	1333.5	1333.5	1333.5	1333.5	1333.5	1333.5	1333.5	1333.5



TEST NUMBER: P331537-840

CATALOG NUMBER: S122DIW-S675D970U840-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4
2.5°	1376.4	1373.1	1371.1	1363.6	1357.1	1350.5	1348.4	1349.2	1340.2	1331.5	1327.8
5°	1430.1	1419.8	1410.0	1396.0	1379.6	1361.5	1352.2	1344.9	1327.0	1307.4	1296.1
7.5°	1478.1	1463.4	1444.5	1418.3	1394.3	1365.9	1347.9	1331.9	1305.5	1277.9	1260.9
10°	1507.4	1487.2	1463.0	1431.1	1401.7	1367.2	1342.9	1318.7	1287.8	1254.8	1234.2
12.5°	1532.6	1505.4	1481.6	1440.6	1405.8	1362.6	1333.8	1299.7	1267.2	1228.0	1207.8
15°	1592.5	1542.5	1497.0	1450.7	1407.9	1347.6	1315.7	1269.7	1226.9	1178.5	1155.3
17.5°	1638.7	1582.6	1511.1	1452.1	1402.2	1335.4	1288.5	1233.6	1183.0	1127.5	1096.0
20°	1665.2	1600.6	1523.9	1453.8	1393.9	1317.7	1266.7	1210.4	1151.1	1088.7	1054.7
22.5°	1680.8	1613.1	1537.1	1447.5	1377.5	1303.2	1239.0	1177.4	1117.3	1050.1	1014.3
25°	1685.8	1623.9	1543.5	1442.4	1356.9	1272.8	1195.5	1135.7	1063.0	1000.1	948.1
27.5°	1661.2	1616.9	1539.5	1432.7	1333.0	1234.8	1148.6	1080.9	1004.1	935.8	883.5
30°	1631.1	1605.3	1530.0	1422.8	1314.0	1208.4	1113.5	1036.7	960.4	891.3	837.7
32.5°	1584.5	1578.9	1512.8	1408.8	1293.8	1175.0	1076.8	999.2	914.6	846.8	795.7
35°	1493.0	1517.7	1475.9	1377.5	1255.8	1127.4	1021.3	932.6	845.0	780.0	732.1
37.5°	1370.3	1431.7	1420.8	1331.6	1204.5	1075.7	958.5	865.8	782.2	716.7	669.6
40°	1285.7	1364.0	1375.4	1296.6	1168.2	1035.7	911.4	819.2	737.7	677.9	630.5
42.5°	1195.0	1286.6	1317.7	1254.5	1128.5	993.6	869.4	773.8	693.2	635.0	593.0
45°	1042.9	1164.1	1220.2	1184.2	1062.5	924.3	796.5	699.5	626.3	571.7	539.3
47.5°	900.7	1033.1	1108.6	1095.9	989.0	852.1	725.8	632.8	561.5	517.9	488.8
50°	800.1	936.1	1027.4	1031.6	936.1	800.6	673.8	586.1	520.7	480.0	456.3
52.5°	712.7	842.5	942.1	963.9	877.2	747.0	627.2	540.0	482.3	444.8	423.6
55°	598.5	708.3	818.6	858.9	789.2	665.5	554.7	477.9	423.7	398.0	379.4
57.5°	497.6	589.2	691.1	735.5	692.6	586.6	482.7	416.1	372.1	349.5	335.3
60°	444.3	516.5	607.2	660.4	623.3	529.0	438.2	374.8	338.7	318.6	305.2
62.5°	394.9	458.8	535.5	584.1	563.9	474.9	393.6	337.7	306.5	287.6	278.0
65°	325.8	376.4	435.7	480.5	467.1	399.5	333.1	285.1	260.3	245.4	237.6
67.5°	268.3	304.8	345.9	385.2	374.4	326.5	273.2	235.8	217.3	204.5	199.9
70°	232.0	259.8	296.4	327.9	319.1	279.9	237.6	205.7	189.8	178.8	174.2
72.5°	197.3	220.3	248.1	273.9	267.9	235.4	200.2	176.0	163.7	153.7	149.9
75°	149.0	166.5	183.5	200.6	198.9	173.7	153.1	134.5	124.7	117.0	115.4
77.5°	110.0	119.8	131.4	141.5	138.7	124.2	108.1	97.5	90.2	85.0	84.2
80°	84.0	89.7	98.0	105.1	101.6	95.3	82.5	74.7	69.6	64.4	62.4
82.5°	60.9	66.7	71.6	75.4	72.7	67.0	59.0	53.7	50.6	47.2	46.3
85°	31.9	35.0	37.2	38.2	37.2	33.5	29.9	27.9	25.2	23.7	23.2
87.5°	15.6	15.2	14.8	15.2	13.5	13.1	11.0	9.3	9.3	9.4	9.0
90°	15.9	14.1	12.4	10.4	8.1	5.7	3.3	1.0	3.3	5.7	8.1
92.5°	20.7	19.8	19.0	18.7	18.9	19.1	19.3	19.5	19.3	19.1	18.9
95°	34.6	33.1	31.6	34.4	41.5	48.6	55.6	62.7	55.6	48.6	41.5
97.5°	43.4	40.0	36.5	44.7	64.6	84.6	104.5	124.5	104.5	84.6	64.6
100°	47.7	44.0	40.4	53.3	82.7	112.0	141.4	170.8	141.4	112.0	82.7
102.5°	117.5	148.0	178.5	196.8	203.1	209.3	215.5	221.8	215.5	209.3	203.1
105°	175.9	234.5	293.1	319.1	312.7	306.2	299.8	293.4	299.8	306.2	312.7
107.5°	222.8	293.1	363.2	395.8	390.5	385.4	380.2	375.0	380.2	385.4	390.5
110°	292.9	354.8	416.8	445.5	441.0	436.5	432.0	427.5	432.0	436.5	441.0





TEST NUMBER: P331537-840

CATALOG NUMBER: S122DIW-S675D970U840-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	456.6	471.9	487.2	492.8	488.9	484.8	480.9	476.9	480.9	484.8	488.9
115°	584.6	579.3	573.9	569.5	565.8	562.2	558.5	554.8	558.5	562.2	565.8
117.5°	652.1	648.4	644.7	640.9	636.7	632.7	628.6	624.5	628.6	632.7	636.7
120°	699.6	695.7	691.9	688.3	685.1	681.9	678.7	675.5	678.7	681.9	685.1
122.5°	744.5	740.2	736.1	732.3	728.8	725.5	722.1	718.7	722.1	725.5	728.8
125°	807.3	803.1	799.1	795.7	792.8	790.1	787.3	784.5	787.3	790.1	792.8
127.5°	865.7	862.6	859.6	856.5	853.4	850.3	847.3	844.1	847.3	850.3	853.4
130°	903.3	900.9	898.6	895.6	892.2	888.9	885.4	882.0	885.4	888.9	892.2
132.5°	939.6	937.3	934.8	932.2	929.3	926.5	923.5	920.6	923.5	926.5	929.3
135°	991.0	989.1	987.1	984.5	981.1	977.7	974.2	970.8	974.2	977.7	981.1
137.5°	1037.7	1035.6	1033.4	1031.1	1028.7	1026.3	1023.9	1021.5	1023.9	1026.3	1028.7
140°	1068.3	1065.9	1063.6	1061.6	1059.9	1058.1	1056.4	1054.7	1056.4	1058.1	1059.9
142.5°	1096.2	1093.5	1090.8	1088.6	1087.1	1085.6	1084.0	1082.5	1084.0	1085.6	1087.1
145°	1134.3	1130.6	1127.0	1125.3	1125.5	1125.7	1125.9	1126.1	1125.9	1125.7	1125.5
147.5°	1169.4	1165.9	1162.3	1160.8	1161.6	1162.5	1163.3	1164.2	1163.3	1162.5	1161.6
150°	1190.6	1187.2	1183.8	1182.9	1184.4	1185.8	1187.3	1188.8	1187.3	1185.8	1184.4
152.5°	1210.3	1207.0	1203.8	1203.0	1204.7	1206.3	1208.0	1209.7	1208.0	1206.3	1204.7
155°	1237.7	1235.2	1232.5	1232.2	1234.2	1236.1	1238.0	1240.0	1238.0	1236.1	1234.2
157.5°	1260.9	1259.1	1257.3	1257.2	1258.8	1260.4	1262.1	1263.7	1262.1	1260.4	1258.8
160°	1275.1	1273.7	1272.4	1272.4	1273.7	1275.1	1276.4	1277.6	1276.4	1275.1	1273.7
162.5°	1287.0	1285.9	1284.8	1284.9	1286.1	1287.4	1288.7	1290.0	1288.7	1287.4	1286.1
165°	1302.3	1301.7	1301.1	1301.4	1302.7	1303.9	1305.3	1306.6	1305.3	1303.9	1302.7
167.5°	1314.6	1314.0	1313.4	1313.7	1315.0	1316.4	1317.6	1318.9	1317.6	1316.4	1315.0
170°	1321.1	1320.7	1320.3	1320.7	1322.0	1323.3	1324.5	1325.9	1324.5	1323.3	1322.0
172.5°	1325.8	1325.3	1324.9	1325.3	1326.7	1327.9	1329.2	1330.5	1329.2	1327.9	1326.7
175°	1330.8	1330.4	1329.9	1330.5	1332.0	1333.4	1334.9	1336.5	1334.9	1333.4	1332.0
177.5°	1332.4	1332.3	1332.1	1332.6	1333.8	1335.0	1336.3	1337.5	1336.3	1335.0	1333.8
180°	1333.5	1333.5	1333.5	1333.5	1333.5	1333.5	1333.5	1333.5	1333.5	1333.5	1333.5



TEST NUMBER: P331537-840

CATALOG NUMBER: S122DIW-S675D970U840-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4
2.5°	1323.6	1321.2	1312.5	1308.0	1300.5	1293.5	1289.0	1291.1	1292.7	1291.9	1290.6
5°	1285.7	1275.9	1260.9	1248.1	1238.8	1221.7	1214.6	1210.9	1207.9	1204.3	1200.6
7.5°	1240.5	1225.1	1203.7	1185.3	1167.9	1146.8	1134.8	1127.5	1120.1	1112.0	1104.8
10°	1208.4	1186.7	1164.1	1138.2	1117.6	1098.5	1081.6	1070.3	1060.0	1050.2	1042.9
12.5°	1174.6	1149.6	1121.6	1086.3	1063.6	1036.3	1033.7	1013.7	997.6	991.6	983.1
15°	1120.7	1085.7	1050.2	1008.4	990.3	965.5	950.1	934.6	920.7	910.9	908.4
17.5°	1059.6	1014.2	978.9	948.9	919.3	893.9	879.7	867.3	855.9	842.7	841.0
20°	1013.0	973.8	935.1	908.9	878.5	852.6	835.2	822.7	812.9	805.3	798.5
22.5°	968.9	925.9	890.6	861.8	831.8	811.0	797.2	785.3	777.1	768.5	762.2
25°	898.1	864.5	825.9	793.3	768.6	755.3	743.9	733.6	728.4	722.8	715.6
27.5°	836.1	798.8	762.7	737.5	715.8	703.9	695.8	688.8	684.0	680.6	676.6
30°	792.3	754.7	726.4	701.7	683.6	671.8	666.6	662.5	656.8	654.7	652.7
32.5°	750.3	716.4	692.2	670.7	653.5	645.7	641.0	637.3	632.9	630.8	626.6
35°	690.7	662.5	638.7	626.8	613.0	606.2	602.7	597.4	593.4	591.3	590.8
37.5°	634.8	610.2	594.6	579.4	573.5	569.4	564.4	560.9	559.7	559.4	558.9
40°	598.5	578.5	564.5	552.1	549.6	543.3	539.3	536.1	536.1	536.6	536.1
42.5°	565.5	547.4	535.2	524.5	521.5	517.8	513.6	513.4	514.3	516.0	514.3
45°	515.5	502.6	493.8	488.7	483.0	479.4	478.9	480.5	481.0	481.5	483.0
47.5°	469.5	461.0	453.0	447.4	444.8	444.2	443.6	446.4	448.8	449.7	452.1
50°	442.3	432.5	425.9	422.2	420.1	419.1	420.1	423.2	425.3	427.9	429.4
52.5°	411.8	404.9	400.2	397.5	396.7	397.3	397.5	401.0	404.2	405.2	406.0
55°	369.6	364.5	363.5	358.8	360.8	360.3	362.9	365.0	368.1	371.1	371.7
57.5°	327.6	323.5	320.6	321.0	321.6	324.0	326.1	329.7	333.1	336.3	336.6
60°	299.5	297.4	295.9	295.9	296.9	300.0	302.7	306.2	308.3	310.3	311.8
62.5°	274.0	271.9	270.3	271.1	273.9	275.7	278.7	280.6	282.7	284.8	285.5
65°	233.5	232.5	234.1	235.1	235.6	238.1	241.8	243.3	245.4	246.4	250.0
67.5°	196.3	196.5	196.3	197.7	200.8	201.4	204.8	208.3	208.7	210.8	213.1
70°	171.2	172.2	173.2	174.2	176.8	177.8	180.5	182.0	184.0	185.6	187.1
72.5°	148.0	148.2	149.3	149.1	151.3	153.5	155.7	157.2	159.3	161.3	162.8
75°	113.9	113.9	114.9	115.4	118.1	120.7	120.1	121.2	123.2	125.2	126.3
77.5°	83.2	82.1	83.2	83.7	84.5	86.7	87.2	88.6	90.9	90.2	91.4
80°	63.4	61.9	63.4	63.9	63.9	66.6	66.6	67.6	69.1	67.6	69.1
82.5°	45.2	44.5	45.6	45.7	46.6	46.7	47.6	47.8	49.3	48.6	49.3
85°	22.7	22.2	22.7	22.2	22.7	23.2	23.2	22.7	22.7	23.7	22.2
87.5°	9.1	9.1	9.0	9.4	9.3	9.2	9.0	9.2	9.5	8.9	9.0
90°	10.4	12.4	14.1	15.9	17.6	19.3	20.4	21.4	22.5	23.6	24.3
92.5°	18.7	19.0	19.8	20.7	21.5	22.4	22.9	23.5	24.0	24.6	25.0
95°	34.4	31.6	33.1	34.6	36.2	37.7	38.7	39.8	40.9	41.9	42.3
97.5°	44.7	36.5	40.0	43.4	46.9	50.4	51.2	52.1	52.9	53.8	54.3
100°	53.3	40.4	44.0	47.7	51.4	55.0	56.8	58.5	60.2	61.9	62.9
102.5°	196.8	178.5	148.0	117.5	87.1	56.6	58.8	61.0	63.2	65.4	66.9
105°	319.1	293.1	234.5	175.9	117.4	58.9	61.2	63.6	65.9	68.3	69.9
107.5°	395.8	363.2	293.1	222.8	152.6	82.4	80.0	77.6	75.2	72.8	72.0
110°	445.5	416.8	354.8	292.9	230.9	168.8	147.4	125.9	104.5	83.1	72.8



TEST NUMBER: P331537-840

CATALOG NUMBER: S122DIW-S675D970U840-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	492.8	487.2	471.9	456.6	441.2	426.0	347.7	269.4	191.3	113.0	74.2
115°	569.5	573.9	579.3	584.6	590.1	595.4	496.0	396.8	297.5	198.2	140.9
117.5°	640.9	644.7	648.4	652.1	655.8	659.4	635.4	611.4	587.4	563.4	526.0
120°	688.3	691.9	695.7	699.6	703.5	707.3	709.9	712.5	715.0	717.6	704.4
122.5°	732.3	736.1	740.2	744.5	748.6	752.9	754.4	756.0	757.5	759.0	757.0
125°	795.7	799.1	803.1	807.3	811.3	815.4	816.9	818.4	819.9	821.4	822.4
127.5°	856.5	859.6	862.6	865.7	868.7	871.7	873.9	876.2	878.3	880.5	881.6
130°	895.6	898.6	900.9	903.3	905.6	908.1	910.4	912.7	915.1	917.5	918.6
132.5°	932.2	934.8	937.3	939.6	941.9	944.3	946.3	948.4	950.4	952.4	953.3
135°	984.5	987.1	989.1	991.0	992.9	994.9	997.0	999.2	1001.3	1003.4	1004.3
137.5°	1031.1	1033.4	1035.6	1037.7	1040.0	1042.2	1044.3	1046.3	1048.4	1050.6	1051.3
140°	1061.6	1063.6	1065.9	1068.3	1070.7	1073.1	1075.0	1076.9	1078.8	1080.8	1081.2
142.5°	1088.6	1090.8	1093.5	1096.2	1098.9	1101.6	1103.4	1105.1	1106.9	1108.6	1108.9
145°	1125.3	1127.0	1130.6	1134.3	1137.9	1141.6	1143.1	1144.6	1146.1	1147.5	1147.8
147.5°	1160.8	1162.3	1165.9	1169.4	1173.1	1176.7	1177.8	1178.9	1180.0	1181.1	1181.2
150°	1182.9	1183.8	1187.2	1190.6	1194.1	1197.5	1198.8	1200.1	1201.3	1202.6	1202.7
152.5°	1203.0	1203.8	1207.0	1210.3	1213.6	1216.8	1218.1	1219.4	1220.6	1221.9	1221.9
155°	1232.2	1232.5	1235.2	1237.7	1240.3	1242.8	1244.2	1245.5	1246.7	1248.0	1247.8
157.5°	1257.2	1257.3	1259.1	1260.9	1262.6	1264.5	1266.0	1267.4	1268.9	1270.3	1270.2
160°	1272.4	1272.4	1273.7	1275.1	1276.4	1277.6	1278.9	1280.2	1281.4	1282.7	1282.6
162.5°	1284.9	1284.8	1285.9	1287.0	1288.1	1289.2	1290.6	1292.1	1293.5	1295.1	1294.8
165°	1301.4	1301.1	1301.7	1302.3	1303.0	1303.6	1305.1	1306.7	1308.2	1309.7	1309.7
167.5°	1313.7	1313.4	1314.0	1314.6	1315.2	1315.9	1317.3	1318.8	1320.3	1321.8	1321.6
170°	1320.7	1320.3	1320.7	1321.1	1321.6	1322.0	1323.5	1325.0	1326.5	1328.0	1327.8
172.5°	1325.3	1324.9	1325.3	1325.8	1326.2	1326.7	1328.2	1329.6	1331.1	1332.6	1332.4
175°	1330.5	1329.9	1330.4	1330.8	1331.2	1331.6	1333.1	1334.6	1336.2	1337.7	1337.4
177.5°	1332.6	1332.1	1332.3	1332.4	1332.6	1332.8	1334.0	1335.2	1336.4	1337.6	1337.5
180°	1333.5	1333.5	1333.5	1333.5	1333.5	1333.5	1333.5	1333.5	1333.5	1333.5	1333.5



TEST NUMBER: P331537-840

CATALOG NUMBER: S122DIW-S675D970U840-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4
2.5°	1286.6	1285.7	1285.7	1282.0	1285.7	1285.7	1286.6	1290.6	1291.9	1292.7	1291.1
5°	1193.5	1191.8	1189.3	1191.8	1189.3	1191.8	1193.5	1200.6	1204.3	1207.9	1210.9
7.5°	1101.4	1095.2	1094.3	1088.1	1094.3	1095.2	1101.4	1104.8	1112.0	1120.1	1127.5
10°	1034.1	1030.0	1029.5	1019.7	1029.5	1030.0	1034.1	1042.9	1050.2	1060.0	1070.3
12.5°	983.0	973.1	975.0	969.4	975.0	973.1	983.0	983.1	991.6	997.6	1013.7
15°	894.4	894.4	892.3	883.6	892.3	894.4	894.4	908.4	910.9	920.7	934.6
17.5°	830.8	829.8	824.9	827.3	824.9	829.8	830.8	841.0	842.7	855.9	867.3
20°	792.8	789.8	783.6	783.6	783.6	789.8	792.8	798.5	805.3	812.9	822.7
22.5°	757.0	756.8	750.2	752.2	750.2	756.8	757.0	762.2	768.5	777.1	785.3
25°	715.0	710.9	707.8	709.3	707.8	710.9	715.0	715.6	722.8	728.4	733.6
27.5°	675.2	673.0	672.8	668.5	672.8	673.0	675.2	676.6	680.6	684.0	688.8
30°	652.2	647.0	648.0	645.4	648.0	647.0	652.2	652.7	654.7	656.8	662.5
32.5°	625.7	623.9	622.9	620.7	622.9	623.9	625.7	626.6	630.8	632.9	637.3
35°	589.8	590.3	587.7	588.8	587.7	590.3	589.8	590.8	591.3	593.4	597.4
37.5°	558.4	560.0	558.8	559.1	558.8	560.0	558.4	558.9	559.4	559.7	560.9
40°	537.7	537.7	537.7	539.3	537.7	537.7	537.7	536.1	536.6	536.1	536.1
42.5°	517.9	517.1	516.2	516.1	516.2	517.1	517.9	514.3	516.0	514.3	513.4
45°	484.0	485.6	486.1	483.5	486.1	485.6	484.0	483.0	481.5	481.0	480.5
47.5°	453.4	453.6	453.4	455.8	453.4	453.6	453.4	452.1	449.7	448.8	446.4
50°	432.0	431.0	432.0	431.0	432.0	431.0	432.0	429.4	427.9	425.3	423.2
52.5°	409.3	409.5	408.9	408.7	408.9	409.5	409.3	406.0	405.2	404.2	401.0
55°	373.8	374.8	374.3	374.3	374.3	374.8	373.8	371.7	371.1	368.1	365.0
57.5°	337.0	337.9	338.6	336.3	338.6	337.9	337.0	336.6	336.3	333.1	329.7
60°	311.3	314.0	313.5	312.5	313.5	314.0	311.3	311.8	310.3	308.3	306.2
62.5°	287.9	288.8	288.7	288.5	288.7	288.8	287.9	285.5	284.8	282.7	280.6
65°	251.6	252.6	251.1	252.6	251.1	252.6	251.6	250.0	246.4	245.4	243.3
67.5°	212.5	212.8	214.0	214.7	214.0	212.8	212.5	213.1	210.8	208.7	208.3
70°	188.1	187.6	189.1	190.8	189.1	187.6	188.1	187.1	185.6	184.0	182.0
72.5°	162.6	163.7	163.2	164.3	163.2	163.7	162.6	162.8	161.3	159.3	157.2
75°	125.2	126.8	126.3	127.8	126.3	126.8	125.2	126.3	125.2	123.2	121.2
77.5°	90.5	90.7	90.5	91.4	90.5	90.7	90.5	91.4	90.2	90.9	88.6
80°	69.1	68.1	67.1	69.1	67.1	68.1	69.1	69.1	67.6	69.1	67.6
82.5°	48.1	48.7	47.7	47.7	47.7	48.7	48.1	49.3	48.6	49.3	47.8
85°	22.2	21.6	20.6	20.6	20.6	21.6	22.2	22.2	23.7	22.7	22.7
87.5°	9.1	8.8	8.9	8.5	8.9	8.8	9.1	9.0	8.9	9.5	9.2
90°	24.7	25.1	25.7	26.1	25.7	25.1	24.7	24.3	23.6	22.5	21.4
92.5°	25.2	25.5	25.8	26.1	25.8	25.5	25.2	25.0	24.6	24.0	23.5
95°	42.1	41.9	41.7	41.5	41.7	41.9	42.1	42.3	41.9	40.9	39.8
97.5°	54.6	54.8	55.1	55.3	55.1	54.8	54.6	54.3	53.8	52.9	52.1
100°	63.3	63.8	64.2	64.6	64.2	63.8	63.3	62.9	61.9	60.2	58.5
102.5°	67.5	68.1	68.7	69.3	68.7	68.1	67.5	66.9	65.4	63.2	61.0
105°	70.8	71.6	72.5	73.3	72.5	71.6	70.8	69.9	68.3	65.9	63.6
107.5°	72.9	73.7	74.6	75.4	74.6	73.7	72.9	72.0	72.8	75.2	77.6
110°	73.6	74.5	75.3	76.2	75.3	74.5	73.6	72.8	83.1	104.5	125.9



TEST NUMBER: P331537-840

CATALOG NUMBER: S122DIW-S675D970U840-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	74.9	75.6	76.3	77.1	76.3	75.6	74.9	74.2	113.0	191.3	269.4
115°	125.4	110.0	94.5	79.2	94.5	110.0	125.4	140.9	198.2	297.5	396.8
117.5°	475.2	424.5	373.9	323.1	373.9	424.5	475.2	526.0	563.4	587.4	611.4
120°	675.5	646.5	617.5	588.7	617.5	646.5	675.5	704.4	717.6	715.0	712.5
122.5°	751.3	745.8	740.1	734.6	740.1	745.8	751.3	757.0	759.0	757.5	756.0
125°	823.1	823.7	824.4	825.1	824.4	823.7	823.1	822.4	821.4	819.9	818.4
127.5°	881.8	881.9	882.0	882.1	882.0	881.9	881.8	881.6	880.5	878.3	876.2
130°	918.3	918.1	917.9	917.7	917.9	918.1	918.3	918.6	917.5	915.1	912.7
132.5°	953.0	952.8	952.6	952.4	952.6	952.8	953.0	953.3	952.4	950.4	948.4
135°	1003.9	1003.4	1003.0	1002.6	1003.0	1003.4	1003.9	1004.3	1003.4	1001.3	999.2
137.5°	1050.6	1049.8	1049.0	1048.3	1049.0	1049.8	1050.6	1051.3	1050.6	1048.4	1046.3
140°	1080.2	1079.0	1077.9	1076.9	1077.9	1079.0	1080.2	1081.2	1080.8	1078.8	1076.9
142.5°	1107.9	1106.8	1105.8	1104.7	1105.8	1106.8	1107.9	1108.9	1108.6	1106.9	1105.1
145°	1146.7	1145.6	1144.6	1143.5	1144.6	1145.6	1146.7	1147.8	1147.5	1146.1	1144.6
147.5°	1180.3	1179.4	1178.5	1177.6	1178.5	1179.4	1180.3	1181.2	1181.1	1180.0	1178.9
150°	1201.7	1200.6	1199.5	1198.5	1199.5	1200.6	1201.7	1202.7	1202.6	1201.3	1200.1
152.5°	1220.5	1219.1	1217.7	1216.3	1217.7	1219.1	1220.5	1221.9	1221.9	1220.6	1219.4
155°	1246.1	1244.4	1242.6	1240.9	1242.6	1244.4	1246.1	1247.8	1248.0	1246.7	1245.5
157.5°	1268.5	1266.9	1265.2	1263.5	1265.2	1266.9	1268.5	1270.2	1270.3	1268.9	1267.4
160°	1281.1	1279.6	1278.2	1276.7	1278.2	1279.6	1281.1	1282.6	1282.7	1281.4	1280.2
162.5°	1292.9	1291.1	1289.3	1287.5	1289.3	1291.1	1292.9	1294.8	1295.1	1293.5	1292.1
165°	1308.2	1306.7	1305.1	1303.6	1305.1	1306.7	1308.2	1309.7	1309.7	1308.2	1306.7
167.5°	1319.7	1317.8	1315.9	1313.9	1315.9	1317.8	1319.7	1321.6	1321.8	1320.3	1318.8
170°	1325.9	1323.9	1322.0	1320.1	1322.0	1323.9	1325.9	1327.8	1328.0	1326.5	1325.0
172.5°	1330.5	1328.6	1326.7	1324.7	1326.7	1328.6	1330.5	1332.4	1332.6	1331.1	1329.6
175°	1335.1	1333.0	1330.9	1328.8	1330.9	1333.0	1335.1	1337.4	1337.7	1336.2	1334.6
177.5°	1335.8	1334.3	1332.8	1331.3	1332.8	1334.3	1335.8	1337.5	1337.6	1336.4	1335.2
180°	1333.5	1333.5	1333.5	1333.5	1333.5	1333.5	1333.5	1333.5	1333.5	1333.5	1333.5



TEST NUMBER: P331537-840

CATALOG NUMBER: S122DIW-S675D970U840-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4
2.5°	1289.0	1293.5	1300.5	1308.0	1312.5	1321.2	1323.6	1327.8	1331.5	1340.2	1349.2
5°	1214.6	1221.7	1238.8	1248.1	1260.9	1275.9	1285.7	1296.1	1307.4	1327.0	1344.9
7.5°	1134.8	1146.8	1167.9	1185.3	1203.7	1225.1	1240.5	1260.9	1277.9	1305.5	1331.9
10°	1081.6	1098.5	1117.6	1138.2	1164.1	1186.7	1208.4	1234.2	1254.8	1287.8	1318.7
12.5°	1033.7	1036.3	1063.6	1086.3	1121.6	1149.6	1174.6	1207.8	1228.0	1267.2	1299.7
15°	950.1	965.5	990.3	1008.4	1050.2	1085.7	1120.7	1155.3	1178.5	1226.9	1269.7
17.5°	879.7	893.9	919.3	948.9	978.9	1014.2	1059.6	1096.0	1127.5	1183.0	1233.6
20°	835.2	852.6	878.5	908.9	935.1	973.8	1013.0	1054.7	1088.7	1151.1	1210.4
22.5°	797.2	811.0	831.8	861.8	890.6	925.9	968.9	1014.3	1050.1	1117.3	1177.4
25°	743.9	755.3	768.6	793.3	825.9	864.5	898.1	948.1	1000.1	1063.0	1135.7
27.5°	695.8	703.9	715.8	737.5	762.7	798.8	836.1	883.5	935.8	1004.1	1080.9
30°	666.6	671.8	683.6	701.7	726.4	754.7	792.3	837.7	891.3	960.4	1036.7
32.5°	641.0	645.7	653.5	670.7	692.2	716.4	750.3	795.7	846.8	914.6	999.2
35°	602.7	606.2	613.0	626.8	638.7	662.5	690.7	732.1	780.0	845.0	932.6
37.5°	564.4	569.4	573.5	579.4	594.6	610.2	634.8	669.6	716.7	782.2	865.8
40°	539.3	543.3	549.6	552.1	564.5	578.5	598.5	630.5	677.9	737.7	819.2
42.5°	513.6	517.8	521.5	524.5	535.2	547.4	565.5	593.0	635.0	693.2	773.8
45°	478.9	479.4	483.0	488.7	493.8	502.6	515.5	539.3	571.7	626.3	699.5
47.5°	443.6	444.2	444.8	447.4	453.0	461.0	469.5	488.8	517.9	561.5	632.8
50°	420.1	419.1	420.1	422.2	425.9	432.5	442.3	456.3	480.0	520.7	586.1
52.5°	397.5	397.3	396.7	397.5	400.2	404.9	411.8	423.6	444.8	482.3	540.0
55°	362.9	360.3	360.8	358.8	363.5	364.5	369.6	379.4	398.0	423.7	477.9
57.5°	326.1	324.0	321.6	321.0	320.6	323.5	327.6	335.3	349.5	372.1	416.1
60°	302.7	300.0	296.9	295.9	295.9	297.4	299.5	305.2	318.6	338.7	374.8
62.5°	278.7	275.7	273.9	271.1	270.3	271.9	274.0	278.0	287.6	306.5	337.7
65°	241.8	238.1	235.6	235.1	234.1	232.5	233.5	237.6	245.4	260.3	285.1
67.5°	204.8	201.4	200.8	197.7	196.3	196.5	196.3	199.9	204.5	217.3	235.8
70°	180.5	177.8	176.8	174.2	173.2	172.2	171.2	174.2	178.8	189.8	205.7
72.5°	155.7	153.5	151.3	149.1	149.3	148.2	148.0	149.9	153.7	163.7	176.0
75°	120.1	120.7	118.1	115.4	114.9	113.9	113.9	115.4	117.0	124.7	134.5
77.5°	87.2	86.7	84.5	83.7	83.2	82.1	83.2	84.2	85.0	90.2	97.5
80°	66.6	66.6	63.9	63.9	63.4	61.9	63.4	62.4	64.4	69.6	74.7
82.5°	47.6	46.7	46.6	45.7	45.6	44.5	45.2	46.3	47.2	50.6	53.7
85°	23.2	23.2	22.7	22.2	22.7	22.2	22.7	23.2	23.7	25.2	27.9
87.5°	9.0	9.2	9.3	9.4	9.0	9.1	9.1	9.0	9.4	9.3	9.3
90°	20.4	19.3	17.6	15.9	14.1	12.4	10.4	8.1	5.7	3.3	1.0
92.5°	22.9	22.4	21.5	20.7	19.8	19.0	18.7	18.9	19.1	19.3	19.5
95°	38.7	37.7	36.2	34.6	33.1	31.6	34.4	41.5	48.6	55.6	62.7
97.5°	51.2	50.4	46.9	43.4	40.0	36.5	44.7	64.6	84.6	104.5	124.5
100°	56.8	55.0	51.4	47.7	44.0	40.4	53.3	82.7	112.0	141.4	170.8
102.5°	58.8	56.6	87.1	117.5	148.0	178.5	196.8	203.1	209.3	215.5	221.8
105°	61.2	58.9	117.4	175.9	234.5	293.1	319.1	312.7	306.2	299.8	293.4
107.5°	80.0	82.4	152.6	222.8	293.1	363.2	395.8	390.5	385.4	380.2	375.0
110°	147.4	168.8	230.9	292.9	354.8	416.8	445.5	441.0	436.5	432.0	427.5



TEST NUMBER: P331537-840

CATALOG NUMBER: S122DIW-S675D970U840-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	347.7	426.0	441.2	456.6	471.9	487.2	492.8	488.9	484.8	480.9	476.9
115°	496.0	595.4	590.1	584.6	579.3	573.9	569.5	565.8	562.2	558.5	554.8
117.5°	635.4	659.4	655.8	652.1	648.4	644.7	640.9	636.7	632.7	628.6	624.5
120°	709.9	707.3	703.5	699.6	695.7	691.9	688.3	685.1	681.9	678.7	675.5
122.5°	754.4	752.9	748.6	744.5	740.2	736.1	732.3	728.8	725.5	722.1	718.7
125°	816.9	815.4	811.3	807.3	803.1	799.1	795.7	792.8	790.1	787.3	784.5
127.5°	873.9	871.7	868.7	865.7	862.6	859.6	856.5	853.4	850.3	847.3	844.1
130°	910.4	908.1	905.6	903.3	900.9	898.6	895.6	892.2	888.9	885.4	882.0
132.5°	946.3	944.3	941.9	939.6	937.3	934.8	932.2	929.3	926.5	923.5	920.6
135°	997.0	994.9	992.9	991.0	989.1	987.1	984.5	981.1	977.7	974.2	970.8
137.5°	1044.3	1042.2	1040.0	1037.7	1035.6	1033.4	1031.1	1028.7	1026.3	1023.9	1021.5
140°	1075.0	1073.1	1070.7	1068.3	1065.9	1063.6	1061.6	1059.9	1058.1	1056.4	1054.7
142.5°	1103.4	1101.6	1098.9	1096.2	1093.5	1090.8	1088.6	1087.1	1085.6	1084.0	1082.5
145°	1143.1	1141.6	1137.9	1134.3	1130.6	1127.0	1125.3	1125.5	1125.7	1125.9	1126.1
147.5°	1177.8	1176.7	1173.1	1169.4	1165.9	1162.3	1160.8	1161.6	1162.5	1163.3	1164.2
150°	1198.8	1197.5	1194.1	1190.6	1187.2	1183.8	1182.9	1184.4	1185.8	1187.3	1188.8
152.5°	1218.1	1216.8	1213.6	1210.3	1207.0	1203.8	1203.0	1204.7	1206.3	1208.0	1209.7
155°	1244.2	1242.8	1240.3	1237.7	1235.2	1232.5	1232.2	1234.2	1236.1	1238.0	1240.0
157.5°	1266.0	1264.5	1262.6	1260.9	1259.1	1257.3	1257.2	1258.8	1260.4	1262.1	1263.7
160°	1278.9	1277.6	1276.4	1275.1	1273.7	1272.4	1272.4	1273.7	1275.1	1276.4	1277.6
162.5°	1290.6	1289.2	1288.1	1287.0	1285.9	1284.8	1284.9	1286.1	1287.4	1288.7	1290.0
165°	1305.1	1303.6	1303.0	1302.3	1301.7	1301.1	1301.4	1302.7	1303.9	1305.3	1306.6
167.5°	1317.3	1315.9	1315.2	1314.6	1314.0	1313.4	1313.7	1315.0	1316.4	1317.6	1318.9
170°	1323.5	1322.0	1321.6	1321.1	1320.7	1320.3	1320.7	1322.0	1323.3	1324.5	1325.9
172.5°	1328.2	1326.7	1326.2	1325.8	1325.3	1324.9	1325.3	1326.7	1327.9	1329.2	1330.5
175°	1333.1	1331.6	1331.2	1330.8	1330.4	1329.9	1330.5	1332.0	1333.4	1334.9	1336.5
177.5°	1334.0	1332.8	1332.6	1332.4	1332.3	1332.1	1332.6	1333.8	1335.0	1336.3	1337.5
180°	1333.5	1333.5	1333.5	1333.5	1333.5	1333.5	1333.5	1333.5	1333.5	1333.5	1333.5



TEST NUMBER: P331537-840

CATALOG NUMBER: S122DIW-S675D970U840-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4
2.5°	1348.4	1350.5	1357.1	1363.6	1371.1	1373.1	1376.4	1373.5	1372.7	1380.6	1386.3
5°	1352.2	1361.5	1379.6	1396.0	1410.0	1419.8	1430.1	1434.2	1441.9	1452.7	1466.1
7.5°	1347.9	1365.9	1394.3	1418.3	1444.5	1463.4	1478.1	1490.7	1505.9	1526.4	1548.8
10°	1342.9	1367.2	1401.7	1431.1	1463.0	1487.2	1507.4	1526.9	1549.6	1578.0	1607.4
12.5°	1333.8	1362.6	1405.8	1440.6	1481.6	1505.4	1532.6	1574.8	1599.1	1638.6	1680.0
15°	1315.7	1347.6	1407.9	1450.7	1497.0	1542.5	1592.5	1632.6	1672.8	1696.1	1754.3
17.5°	1288.5	1335.4	1402.2	1452.1	1511.1	1582.6	1638.7	1684.3	1730.7	1768.4	1797.6
20°	1266.7	1317.7	1393.9	1453.8	1523.9	1600.6	1665.2	1711.5	1751.7	1783.2	1801.2
22.5°	1239.0	1303.2	1377.5	1447.5	1537.1	1613.1	1680.8	1717.3	1750.9	1766.3	1773.2
25°	1195.5	1272.8	1356.9	1442.4	1543.5	1623.9	1685.8	1707.9	1717.7	1702.7	1678.0
27.5°	1148.6	1234.8	1333.0	1432.7	1539.5	1616.9	1661.2	1657.7	1641.1	1592.8	1554.1
30°	1113.5	1208.4	1314.0	1422.8	1530.0	1605.3	1631.1	1605.3	1567.7	1513.6	1458.4
32.5°	1076.8	1175.0	1293.8	1408.8	1512.8	1578.9	1584.5	1540.1	1481.9	1420.4	1351.6
35°	1021.3	1127.4	1255.8	1377.5	1475.9	1517.7	1493.0	1414.6	1345.5	1261.5	1167.6
37.5°	958.5	1075.7	1204.5	1331.6	1420.8	1431.7	1370.3	1287.8	1190.3	1091.6	981.2
40°	911.4	1035.7	1168.2	1296.6	1375.4	1364.0	1285.7	1195.0	1078.9	958.4	855.8
42.5°	869.4	993.6	1128.5	1254.5	1317.7	1286.6	1195.0	1083.6	959.0	845.4	751.4
45°	796.5	924.3	1062.5	1184.2	1220.2	1164.1	1042.9	919.2	796.5	701.7	627.4
47.5°	725.8	852.1	989.0	1095.9	1108.6	1033.1	900.7	773.4	667.9	590.7	538.3
50°	673.8	800.6	936.1	1031.6	1027.4	936.1	800.1	678.9	590.8	528.4	493.3
52.5°	627.2	747.0	877.2	963.9	942.1	842.5	712.7	605.1	532.6	483.8	452.1
55°	554.7	665.5	789.2	858.9	818.6	708.3	598.5	511.9	458.3	421.7	397.0
57.5°	482.7	586.6	692.6	735.5	691.1	589.2	497.6	434.7	394.5	367.4	351.2
60°	438.2	529.0	623.3	660.4	607.2	516.5	444.3	388.2	355.7	333.6	319.1
62.5°	393.6	474.9	563.9	584.1	535.5	458.8	394.9	348.2	321.4	301.7	288.2
65°	333.1	399.5	467.1	480.5	435.7	376.4	325.8	295.4	271.7	257.2	246.4
67.5°	273.2	326.5	374.4	385.2	345.9	304.8	268.3	241.8	225.7	213.7	204.6
70°	237.6	279.9	319.1	327.9	296.4	259.8	232.0	210.9	196.4	186.1	177.3
72.5°	200.2	235.4	267.9	273.9	248.1	220.3	197.3	180.8	167.9	161.4	153.0
75°	153.1	173.7	198.9	200.6	183.5	166.5	149.0	138.1	131.5	123.2	119.1
77.5°	108.1	124.2	138.7	141.5	131.4	119.8	110.0	101.5	95.7	92.0	88.2
80°	82.5	95.3	101.6	105.1	98.0	89.7	84.0	78.4	74.7	72.2	69.6
82.5°	59.0	67.0	72.7	75.4	71.6	66.7	60.9	57.8	54.9	52.8	51.9
85°	29.9	33.5	37.2	38.2	37.2	35.0	31.9	31.9	30.4	29.9	29.9
87.5°	11.0	13.1	13.5	15.2	14.8	15.2	15.6	15.5	15.5	15.2	15.0
90°	3.3	5.7	8.1	10.4	12.4	14.1	15.9	17.6	19.3	20.4	21.4
92.5°	19.3	19.1	18.9	18.7	19.0	19.8	20.7	21.5	22.4	22.9	23.5
95°	55.6	48.6	41.5	34.4	31.6	33.1	34.6	36.2	37.7	38.7	39.8
97.5°	104.5	84.6	64.6	44.7	36.5	40.0	43.4	46.9	50.4	51.2	52.1
100°	141.4	112.0	82.7	53.3	40.4	44.0	47.7	51.4	55.0	56.8	58.5
102.5°	215.5	209.3	203.1	196.8	178.5	148.0	117.5	87.1	56.6	58.8	61.0
105°	299.8	306.2	312.7	319.1	293.1	234.5	175.9	117.4	58.9	61.2	63.6
107.5°	380.2	385.4	390.5	395.8	363.2	293.1	222.8	152.6	82.4	80.0	77.6
110°	432.0	436.5	441.0	445.5	416.8	354.8	292.9	230.9	168.8	147.4	125.9





TEST NUMBER: P331537-840

CATALOG NUMBER: S122DIW-S675D970U840-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	480.9	484.8	488.9	492.8	487.2	471.9	456.6	441.2	426.0	347.7	269.4
115°	558.5	562.2	565.8	569.5	573.9	579.3	584.6	590.1	595.4	496.0	396.8
117.5°	628.6	632.7	636.7	640.9	644.7	648.4	652.1	655.8	659.4	635.4	611.4
120°	678.7	681.9	685.1	688.3	691.9	695.7	699.6	703.5	707.3	709.9	712.5
122.5°	722.1	725.5	728.8	732.3	736.1	740.2	744.5	748.6	752.9	754.4	756.0
125°	787.3	790.1	792.8	795.7	799.1	803.1	807.3	811.3	815.4	816.9	818.4
127.5°	847.3	850.3	853.4	856.5	859.6	862.6	865.7	868.7	871.7	873.9	876.2
130°	885.4	888.9	892.2	895.6	898.6	900.9	903.3	905.6	908.1	910.4	912.7
132.5°	923.5	926.5	929.3	932.2	934.8	937.3	939.6	941.9	944.3	946.3	948.4
135°	974.2	977.7	981.1	984.5	987.1	989.1	991.0	992.9	994.9	997.0	999.2
137.5°	1023.9	1026.3	1028.7	1031.1	1033.4	1035.6	1037.7	1040.0	1042.2	1044.3	1046.3
140°	1056.4	1058.1	1059.9	1061.6	1063.6	1065.9	1068.3	1070.7	1073.1	1075.0	1076.9
142.5°	1084.0	1085.6	1087.1	1088.6	1090.8	1093.5	1096.2	1098.9	1101.6	1103.4	1105.1
145°	1125.9	1125.7	1125.5	1125.3	1127.0	1130.6	1134.3	1137.9	1141.6	1143.1	1144.6
147.5°	1163.3	1162.5	1161.6	1160.8	1162.3	1165.9	1169.4	1173.1	1176.7	1177.8	1178.9
150°	1187.3	1185.8	1184.4	1182.9	1183.8	1187.2	1190.6	1194.1	1197.5	1198.8	1200.1
152.5°	1208.0	1206.3	1204.7	1203.0	1203.8	1207.0	1210.3	1213.6	1216.8	1218.1	1219.4
155°	1238.0	1236.1	1234.2	1232.2	1232.5	1235.2	1237.7	1240.3	1242.8	1244.2	1245.5
157.5°	1262.1	1260.4	1258.8	1257.2	1257.3	1259.1	1260.9	1262.6	1264.5	1266.0	1267.4
160°	1276.4	1275.1	1273.7	1272.4	1272.4	1273.7	1275.1	1276.4	1277.6	1278.9	1280.2
162.5°	1288.7	1287.4	1286.1	1284.9	1284.8	1285.9	1287.0	1288.1	1289.2	1290.6	1292.1
165°	1305.3	1303.9	1302.7	1301.4	1301.1	1301.7	1302.3	1303.0	1303.6	1305.1	1306.7
167.5°	1317.6	1316.4	1315.0	1313.7	1313.4	1314.0	1314.6	1315.2	1315.9	1317.3	1318.8
170°	1324.5	1323.3	1322.0	1320.7	1320.3	1320.7	1321.1	1321.6	1322.0	1323.5	1325.0
172.5°	1329.2	1327.9	1326.7	1325.3	1324.9	1325.3	1325.8	1326.2	1326.7	1328.2	1329.6
175°	1334.9	1333.4	1332.0	1330.5	1329.9	1330.4	1330.8	1331.2	1331.6	1333.1	1334.6
177.5°	1336.3	1335.0	1333.8	1332.6	1332.1	1332.3	1332.4	1332.6	1332.8	1334.0	1335.2
180°	1333.5	1333.5	1333.5	1333.5	1333.5	1333.5	1333.5	1333.5	1333.5	1333.5	1333.5



TEST NUMBER: P331537-840

CATALOG NUMBER: S122DIW-S675D970U840-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4
2.5°	1391.3	1397.0	1397.0	1397.9	1404.5	1403.6	1403.2
5°	1480.6	1489.3	1490.4	1499.6	1505.8	1503.8	1498.1
7.5°	1564.8	1581.1	1593.5	1600.3	1608.5	1613.6	1611.3
10°	1631.6	1655.4	1669.8	1679.6	1691.4	1700.2	1697.1
12.5°	1692.2	1720.5	1740.3	1757.1	1758.7	1769.9	1762.2
15°	1786.8	1816.6	1819.8	1832.2	1842.0	1840.9	1841.4
17.5°	1818.1	1827.7	1829.6	1829.9	1830.0	1826.3	1818.6
20°	1806.9	1803.3	1794.5	1787.9	1775.9	1774.4	1764.1
22.5°	1754.1	1742.6	1720.7	1706.2	1687.7	1682.8	1680.0
25°	1650.2	1624.9	1589.8	1556.3	1547.1	1529.0	1534.2
27.5°	1507.6	1468.2	1430.3	1403.0	1378.4	1351.4	1359.1
30°	1407.3	1363.0	1309.4	1268.2	1241.9	1216.1	1211.4
32.5°	1287.8	1222.8	1163.0	1126.7	1086.4	1070.2	1052.3
35°	1081.6	1018.1	958.9	907.9	878.5	855.8	835.2
37.5°	896.1	823.0	775.3	733.9	712.7	699.6	703.0
40°	781.0	717.1	682.1	650.6	631.0	621.7	623.8
42.5°	687.8	640.0	611.1	589.6	575.7	570.6	569.4
45°	582.0	555.2	531.5	519.2	512.4	506.8	503.1
47.5°	509.9	488.0	474.6	467.3	461.4	455.7	455.6
50°	466.6	452.1	442.8	435.0	430.5	426.4	429.9
52.5°	433.5	420.3	411.1	404.1	402.4	398.7	398.6
55°	384.6	374.3	367.6	361.3	358.3	356.2	353.7
57.5°	340.0	330.2	324.1	320.1	314.3	312.1	311.3
60°	308.3	300.5	294.4	289.2	286.6	282.5	282.5
62.5°	279.0	271.2	265.5	261.6	257.3	255.7	256.1
65°	236.6	230.5	224.8	220.7	219.6	216.5	217.5
67.5°	197.6	193.5	187.5	185.3	183.3	181.7	180.5
70°	171.7	167.5	164.4	161.4	159.8	159.8	159.8
72.5°	149.8	144.8	143.0	139.1	140.0	138.4	136.7
75°	116.0	112.9	111.4	109.8	107.2	107.2	107.2
77.5°	85.3	84.4	82.6	80.9	80.3	79.8	80.0
80°	65.9	65.4	64.4	64.4	63.4	62.9	61.9
82.5°	50.7	49.4	48.8	48.4	48.2	48.1	47.9
85°	28.9	27.9	27.9	28.4	27.4	27.4	27.9
87.5°	15.7	15.9	15.6	15.7	16.2	15.9	16.0
90°	22.5	23.6	24.3	24.7	25.1	25.7	26.1
92.5°	24.0	24.6	25.0	25.2	25.5	25.8	26.1
95°	40.9	41.9	42.3	42.1	41.9	41.7	41.5
97.5°	52.9	53.8	54.3	54.6	54.8	55.1	55.3
100°	60.2	61.9	62.9	63.3	63.8	64.2	64.6
102.5°	63.2	65.4	66.9	67.5	68.1	68.7	69.3
105°	65.9	68.3	69.9	70.8	71.6	72.5	73.3
107.5°	75.2	72.8	72.0	72.9	73.7	74.6	75.4
110°	104.5	83.1	72.8	73.6	74.5	75.3	76.2



TEST NUMBER: P331537-840

CATALOG NUMBER: S122DIW-S675D970U840-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	191.3	113.0	74.2	74.9	75.6	76.3	77.1
115°	297.5	198.2	140.9	125.4	110.0	94.5	79.2
117.5°	587.4	563.4	526.0	475.2	424.5	373.9	323.1
120°	715.0	717.6	704.4	675.5	646.5	617.5	588.7
122.5°	757.5	759.0	757.0	751.3	745.8	740.1	734.6
125°	819.9	821.4	822.4	823.1	823.7	824.4	825.1
127.5°	878.3	880.5	881.6	881.8	881.9	882.0	882.1
130°	915.1	917.5	918.6	918.3	918.1	917.9	917.7
132.5°	950.4	952.4	953.3	953.0	952.8	952.6	952.4
135°	1001.3	1003.4	1004.3	1003.9	1003.4	1003.0	1002.6
137.5°	1048.4	1050.6	1051.3	1050.6	1049.8	1049.0	1048.3
140°	1078.8	1080.8	1081.2	1080.2	1079.0	1077.9	1076.9
142.5°	1106.9	1108.6	1108.9	1107.9	1106.8	1105.8	1104.7
145°	1146.1	1147.5	1147.8	1146.7	1145.6	1144.6	1143.5
147.5°	1180.0	1181.1	1181.2	1180.3	1179.4	1178.5	1177.6
150°	1201.3	1202.6	1202.7	1201.7	1200.6	1199.5	1198.5
152.5°	1220.6	1221.9	1221.9	1220.5	1219.1	1217.7	1216.3
155°	1246.7	1248.0	1247.8	1246.1	1244.4	1242.6	1240.9
157.5°	1268.9	1270.3	1270.2	1268.5	1266.9	1265.2	1263.5
160°	1281.4	1282.7	1282.6	1281.1	1279.6	1278.2	1276.7
162.5°	1293.5	1295.1	1294.8	1292.9	1291.1	1289.3	1287.5
165°	1308.2	1309.7	1309.7	1308.2	1306.7	1305.1	1303.6
167.5°	1320.3	1321.8	1321.6	1319.7	1317.8	1315.9	1313.9
170°	1326.5	1328.0	1327.8	1325.9	1323.9	1322.0	1320.1
172.5°	1331.1	1332.6	1332.4	1330.5	1328.6	1326.7	1324.7
175°	1336.2	1337.7	1337.4	1335.1	1333.0	1330.9	1328.8
177.5°	1336.4	1337.6	1337.5	1335.8	1334.3	1332.8	1331.3
180°	1333.5	1333.5	1333.5	1333.5	1333.5	1333.5	1333.5

(END OF REPORT)