

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332487-927

Luminaire Tested: **S123RDIW-S1165D1535U927-4F0-1E-UDD-A1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P332487-927  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-9,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S123RDIW-S1165D1535U927-4F0-1E-UDD-A1  
Description: DEFINE 3 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 1165 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING  
UPLIGHT 1535 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 7839.2 lumens  
Efficiency: N/A  
Efficacy: 94.6 lumens/watt  
Spacing Criteria (0/90/45): 1.21 / 1.22 / 1.36  
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')  
CIE Type: General Diffuse  
  
Input Watts (W): 82.9  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332487-927

CATALOG NUMBER: S123RDIW-S1165D1535U927-4F0-1E-UDD-A1

### Luminous Intensity Polar Plot





TEST NUMBER: P332487-927

CATALOG NUMBER: S123RDIW-S1165D1535U927-4F0-1E-UDD-A1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	106	106	106	106	98	98	98	98	81	81	81	66	66	66	53	53	53	46
1	97	93	90	86	89	86	83	80	72	70	68	59	58	56	47	46	46	40
2	89	82	76	71	82	76	71	67	64	60	57	53	50	48	42	41	39	34
3	82	73	66	60	75	67	61	56	57	52	49	47	44	41	38	36	34	30
4	75	65	57	51	69	60	53	48	51	46	42	42	39	36	34	32	30	26
5	69	58	50	44	63	54	47	42	46	40	36	38	34	31	31	28	26	23
6	64	52	44	39	58	48	41	36	41	36	32	35	31	28	28	26	23	20
7	59	47	39	34	54	44	37	32	37	32	28	32	28	25	26	23	21	18
8	55	43	35	30	50	40	33	28	34	29	25	29	25	22	24	21	19	16
9	51	39	32	27	47	37	30	26	31	26	23	27	23	20	22	19	17	15
10	48	36	29	24	44	34	27	23	29	24	20	25	21	18	21	18	16	14

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	15655	15655	15655	15655
5°	18662	15722	13846	15722
10°	23302	15632	12508	15632
15°	27351	15473	11407	15473
20°	30525	15234	10470	15234
25°	30037	14982	9894	14982
30°	21592	14751	9302	14751
35°	14416	14448	8918	14448
40°	10621	14085	8521	14085
45°	8910	13449	8132	13449
50°	7860	12616	7591	12616
55°	6893	11661	6848	11661
60°	6140	10749	6273	10749
65°	5392	9770	5835	9770
70°	4233	8897	5331	8897
75°	3730	7769	4870	7769
80°	3242	6602	4785	6602
85°	2618	5298	5076	5298



TEST NUMBER: P332487-927

CATALOG NUMBER: S123RDIW-S1165D1535U927-4F0-1E-UDD-A1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	143.0	1.8
10°-20°	446.9	5.7
20°-30°	702.0	9.0
30°-40°	732.4	9.3
40°-50°	626.8	8.0
50°-60°	477.7	6.1
60°-70°	306.2	3.9
70°-80°	147.3	1.9
80°-90°	43.5	0.6
90°-100°	99.1	1.3
100°-110°	296.5	3.8
110°-120°	504.3	6.4
120°-130°	663.4	8.5
130°-140°	745.6	9.5
140°-150°	732.9	9.3
150°-160°	617.0	7.9
160°-170°	410.7	5.2
170°-180°	143.8	1.8
0°-30°	1291.9	16.5
0°-40°	2024.3	25.8
0°-60°	3128.9	39.9
0°-90°	3625.9	46.3
90°-120°	899.9	11.5
90°-150°	3041.8	38.8
90°-180°	4213.0	53.7
0°-180°	7839.2	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	1454	1454	1454	1454	1454	
5°	1727	1455	1281	1455	1727	178
15°	2454	1388	1024	1388	2454	696
25°	2529	1262	833	1262	2529	1087
35°	1097	1100	679	1100	1097	719
45°	585	884	534	884	585	460
55°	367	621	365	621	367	332
65°	212	384	229	384	212	208
75°	90	187	117	187	90	96
85°	21	43	41	43	21	25
90°	36	1	36	1	36	18
95°	93	70	93	70	93	96
105°	284	269	284	269	284	302
115°	509	508	509	508	509	504
125°	735	743	735	743	735	657
135°	963	964	963	964	963	740
145°	1170	1170	1170	1170	1170	730
155°	1337	1339	1337	1339	1337	615
165°	1454	1459	1454	1459	1454	410
175°	1511	1517	1511	1517	1511	144
180°	1521	1521	1521	1521	1521	



TEST NUMBER: P332487-927

CATALOG NUMBER: S123RDIW-S1165D1535U927-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1454.4	1454.4	1454.4	1454.4	1454.4	1454.4	1454.4	1454.4	1454.4	1454.4	1454.4
2.5°	1549.1	1551.1	1544.6	1543.6	1536.1	1534.1	1534.1	1523.7	1517.2	1508.8	1503.8
5°	1727.2	1737.2	1732.2	1720.9	1702.2	1697.9	1686.1	1667.4	1646.2	1620.1	1607.7
7.5°	1949.6	1963.2	1958.0	1940.6	1921.0	1905.3	1871.8	1840.9	1797.4	1759.3	1726.6
10°	2131.9	2117.6	2106.3	2089.5	2071.5	2042.2	2007.4	1959.4	1904.0	1860.4	1811.9
12.5°	2268.3	2266.0	2251.8	2234.5	2209.0	2181.2	2138.3	2080.0	2015.5	1952.6	1897.0
15°	2454.4	2458.1	2448.8	2430.7	2394.6	2345.4	2280.7	2256.5	2164.2	2095.8	2027.3
17.5°	2583.1	2582.4	2581.2	2556.1	2519.3	2484.3	2424.2	2360.4	2277.0	2180.5	2088.2
20°	2664.8	2658.6	2659.9	2631.9	2604.5	2564.0	2505.4	2412.7	2344.2	2232.8	2137.5
22.5°	2662.8	2661.7	2666.3	2656.7	2636.9	2605.8	2559.8	2481.4	2394.1	2281.6	2174.4
25°	2529.1	2524.1	2553.4	2561.5	2593.3	2598.8	2585.1	2542.2	2459.4	2343.6	2211.0
27.5°	2116.7	2113.9	2168.3	2236.3	2322.4	2389.4	2454.2	2485.4	2459.4	2376.5	2243.6
30°	1737.2	1795.6	1823.0	1921.4	2031.0	2161.8	2276.3	2385.3	2412.0	2376.0	2267.0
32.5°	1442.2	1493.3	1516.2	1600.7	1702.8	1855.9	2027.7	2182.1	2291.1	2318.6	2253.0
35°	1097.1	1097.7	1150.0	1187.3	1282.0	1439.6	1606.4	1813.1	2018.6	2174.2	2190.4
37.5°	875.4	878.5	910.1	947.4	1018.4	1101.7	1248.6	1420.5	1657.8	1896.8	2036.9
40°	755.9	761.4	785.1	821.9	872.9	935.8	1050.4	1212.3	1410.2	1676.1	1893.4
42.5°	679.1	688.2	700.4	728.7	760.3	819.3	911.9	1037.0	1217.0	1468.4	1719.1
45°	585.3	590.3	599.6	612.7	641.3	682.4	744.7	828.7	978.2	1180.5	1431.4
47.5°	516.3	513.7	523.5	534.1	553.2	581.1	622.9	691.5	798.1	960.4	1173.3
50°	469.4	468.8	475.7	483.8	501.8	522.4	556.7	608.3	693.0	827.5	1022.4
52.5°	425.6	428.0	432.8	442.9	456.0	472.6	503.4	540.6	613.3	729.4	891.8
55°	367.3	369.2	376.0	381.7	391.0	407.8	427.1	458.3	508.1	589.0	722.9
57.5°	318.1	317.2	323.8	325.1	335.7	349.4	364.3	388.5	424.6	484.8	575.0
60°	285.2	283.3	288.9	293.3	298.9	310.1	322.5	346.2	374.9	419.1	496.2
62.5°	255.2	254.4	258.5	262.8	267.5	277.7	288.1	306.3	329.0	366.2	427.5
65°	211.7	213.6	215.4	217.3	219.8	226.0	236.0	248.4	264.0	290.2	334.4
67.5°	166.4	168.3	168.9	172.7	178.1	182.0	188.1	199.2	209.9	232.0	257.1
70°	134.5	133.9	134.5	136.3	143.2	150.0	158.1	166.3	173.1	188.6	209.8
72.5°	115.6	114.5	116.1	116.5	119.8	121.7	126.7	134.4	143.2	153.8	169.0
75°	89.7	89.7	89.7	89.7	92.1	93.4	95.3	97.1	100.2	105.2	116.5
77.5°	66.2	66.4	67.3	67.9	68.4	69.1	70.3	72.1	73.2	75.8	80.7
80°	52.3	52.9	52.3	52.9	52.9	54.2	54.8	56.6	57.3	60.4	62.3
82.5°	39.4	39.0	39.4	40.0	40.0	41.2	41.4	42.7	42.9	44.4	46.3
85°	21.2	20.0	21.2	20.5	21.8	20.5	21.2	22.4	22.4	23.1	25.5
87.5°	12.1	13.1	12.0	12.4	12.2	12.6	12.4	12.1	12.9	12.2	12.0
90°	35.8	35.3	34.8	34.2	33.7	33.0	31.8	30.8	29.7	28.7	25.2
92.5°	48.2	48.6	48.9	49.2	49.5	49.3	48.4	47.5	46.7	45.9	43.9
95°	93.2	93.2	93.2	93.2	93.2	92.6	91.6	90.5	89.4	88.4	86.3
97.5°	143.4	143.5	143.5	143.7	143.8	143.2	142.0	140.8	139.6	138.3	136.8
100°	181.6	181.0	180.5	180.0	179.4	178.8	178.0	177.2	176.4	175.6	174.3
102.5°	220.8	220.9	220.9	221.1	221.2	220.9	220.1	219.3	218.5	217.6	215.9
105°	284.3	283.8	283.3	282.7	282.2	281.9	281.9	281.9	281.9	281.9	279.6
107.5°	350.5	350.8	351.1	351.4	351.7	351.5	350.6	349.8	349.0	348.1	347.1
110°	395.4	395.9	396.5	397.0	397.5	397.3	396.2	395.1	394.1	393.0	392.4



TEST NUMBER: P332487-927

CATALOG NUMBER: S123RDIW-S1165D1535U927-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	443.1	443.3	443.4	443.5	443.6	443.0	441.7	440.5	439.2	437.9	437.8
115°	508.9	509.1	509.5	509.7	509.9	509.9	509.7	509.5	509.1	508.9	509.5
117.5°	575.5	576.3	577.0	577.7	578.5	578.9	579.0	579.0	579.1	579.2	579.8
120°	622.3	622.9	623.4	624.0	624.5	624.9	625.2	625.4	625.7	626.0	627.2
122.5°	667.3	668.0	668.8	669.6	670.3	671.0	671.7	672.3	673.0	673.8	674.5
125°	734.7	735.7	736.8	737.8	738.9	740.0	741.0	742.1	743.1	744.3	744.7
127.5°	801.8	803.0	804.2	805.5	806.7	808.0	809.5	811.0	812.5	814.0	814.6
130°	845.7	847.6	849.5	851.4	853.2	854.7	855.7	856.7	857.9	858.9	859.7
132.5°	891.6	893.0	894.5	896.0	897.4	898.7	900.0	901.3	902.5	903.8	904.4
135°	962.8	963.4	963.8	964.4	965.0	965.7	966.8	967.9	968.9	970.0	970.3
137.5°	1025.6	1026.7	1027.7	1028.6	1029.7	1030.8	1031.9	1033.0	1034.1	1035.2	1034.5
140°	1066.8	1068.6	1070.5	1072.3	1074.2	1075.2	1075.5	1075.8	1076.0	1076.3	1076.0
142.5°	1108.8	1110.2	1111.7	1113.1	1114.5	1115.4	1115.6	1115.9	1116.2	1116.4	1115.9
145°	1169.5	1170.5	1171.6	1172.7	1173.7	1174.4	1174.6	1174.9	1175.2	1175.4	1174.6
147.5°	1223.4	1225.0	1226.7	1228.3	1229.9	1230.7	1230.7	1230.7	1230.7	1230.7	1229.9
150°	1257.9	1259.5	1261.1	1262.7	1264.2	1265.0	1265.0	1265.0	1265.0	1265.0	1264.5
152.5°	1291.3	1292.7	1294.1	1295.5	1296.9	1297.4	1296.9	1296.5	1296.1	1295.6	1295.3
155°	1336.7	1338.6	1340.5	1342.3	1344.2	1344.6	1343.5	1342.4	1341.4	1340.3	1340.1
157.5°	1378.1	1379.5	1381.0	1382.5	1384.0	1384.2	1383.1	1382.0	1380.9	1379.7	1379.5
160°	1404.8	1405.9	1406.9	1408.0	1409.1	1408.9	1407.6	1406.3	1404.9	1403.6	1403.6
162.5°	1424.9	1426.6	1428.3	1430.0	1431.7	1431.9	1430.5	1429.2	1427.9	1426.6	1426.3
165°	1453.8	1455.6	1457.5	1459.4	1461.3	1461.3	1459.8	1458.2	1456.6	1455.0	1455.0
167.5°	1478.4	1480.0	1481.7	1483.4	1484.9	1484.9	1483.4	1481.7	1480.0	1478.4	1478.2
170°	1490.8	1492.7	1494.5	1496.4	1498.3	1498.3	1496.4	1494.5	1492.7	1490.8	1490.8
172.5°	1500.4	1502.2	1504.1	1505.9	1507.8	1507.9	1506.3	1504.6	1503.0	1501.3	1501.3
175°	1511.2	1513.0	1514.8	1516.7	1518.5	1518.7	1517.1	1515.5	1513.9	1512.4	1512.4
177.5°	1516.9	1518.4	1519.8	1521.3	1522.8	1522.9	1521.6	1520.4	1519.1	1517.8	1517.8
180°	1520.7	1520.7	1520.7	1520.7	1520.7	1520.7	1520.7	1520.7	1520.7	1520.7	1520.7



TEST NUMBER: P332487-927

CATALOG NUMBER: S123RDIW-S1165D1535U927-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1454.4	1454.4	1454.4	1454.4	1454.4	1454.4	1454.4	1454.4	1454.4	1454.4	1454.4
2.5°	1501.8	1500.3	1493.3	1485.3	1474.9	1467.9	1462.4	1459.4	1450.5	1439.6	1432.0
5°	1594.6	1575.9	1555.9	1531.7	1509.3	1486.2	1471.9	1455.1	1434.6	1411.5	1395.3
7.5°	1693.9	1657.3	1617.9	1577.2	1536.9	1500.8	1468.9	1441.6	1408.9	1375.9	1352.7
10°	1770.1	1716.6	1661.2	1604.5	1552.8	1504.3	1466.9	1430.2	1391.0	1353.0	1324.4
12.5°	1839.4	1768.9	1705.0	1635.4	1569.3	1511.2	1457.5	1414.2	1367.1	1326.6	1294.0
15°	1927.1	1854.8	1777.6	1671.7	1584.0	1510.5	1445.1	1388.5	1331.2	1281.4	1249.6
17.5°	2009.0	1900.3	1796.5	1708.3	1594.2	1502.4	1422.6	1354.9	1292.0	1239.1	1200.1
20°	2042.9	1937.6	1825.0	1712.2	1600.1	1497.5	1404.6	1329.9	1264.6	1204.8	1168.7
22.5°	2063.2	1944.1	1825.4	1704.3	1585.2	1478.5	1386.7	1304.6	1233.7	1176.9	1132.3
25°	2087.1	1945.1	1814.3	1694.8	1573.4	1457.6	1348.6	1261.5	1184.9	1124.5	1077.1
27.5°	2102.8	1935.8	1781.2	1648.4	1525.2	1409.8	1310.0	1217.6	1140.0	1076.0	1025.2
30°	2105.7	1928.3	1755.8	1612.0	1486.8	1381.0	1275.2	1186.8	1104.5	1036.6	989.4
32.5°	2109.7	1909.9	1721.4	1568.7	1440.5	1335.7	1239.8	1155.3	1071.2	1004.3	956.0
35°	2093.3	1899.7	1669.3	1493.7	1365.4	1263.9	1177.4	1099.5	1016.8	952.0	902.9
37.5°	2022.5	1859.2	1615.3	1409.3	1275.2	1181.1	1110.6	1042.7	966.9	897.0	850.6
40°	1951.3	1819.3	1573.4	1358.0	1217.9	1121.3	1057.9	1002.4	929.0	863.6	813.8
42.5°	1845.2	1765.1	1533.5	1304.2	1153.1	1060.1	1006.5	954.6	890.1	823.7	776.9
45°	1650.6	1661.2	1452.0	1218.5	1063.4	970.0	919.6	883.5	826.2	771.4	723.5
47.5°	1406.5	1505.5	1356.2	1127.2	968.9	881.3	837.2	805.6	767.1	713.3	669.6
50°	1247.1	1388.5	1279.5	1066.0	909.7	822.5	778.9	753.4	719.8	677.4	635.7
52.5°	1100.2	1252.0	1186.8	997.7	845.4	765.7	723.1	702.1	675.4	635.6	597.9
55°	897.2	1051.0	1036.1	894.7	749.0	677.4	645.1	621.4	603.3	573.5	543.6
57.5°	725.7	871.6	879.2	780.1	664.1	593.3	565.5	547.6	535.8	513.3	485.7
60°	617.7	751.5	777.7	703.0	603.3	541.1	513.7	499.3	490.0	472.0	450.8
62.5°	528.0	641.9	671.5	617.7	545.0	486.8	465.3	451.5	445.2	429.6	410.9
65°	404.1	498.8	527.4	497.5	459.5	412.8	395.4	383.6	378.0	369.2	355.5
67.5°	303.9	372.8	404.3	383.2	369.5	339.9	328.8	322.5	317.5	311.6	300.1
70°	244.1	295.1	327.5	321.9	310.7	295.1	287.0	282.7	277.7	272.7	262.8
72.5°	196.2	231.4	261.7	264.6	255.4	252.3	245.2	243.4	240.3	234.3	228.9
75°	130.2	154.4	175.5	183.7	187.4	190.5	187.4	186.8	186.2	181.2	178.1
77.5°	85.3	98.4	111.7	125.6	131.3	135.6	136.6	138.9	137.2	134.6	133.1
80°	65.4	68.5	77.8	89.7	99.0	102.7	105.2	106.5	105.8	105.2	102.7
82.5°	47.5	50.1	54.4	62.7	70.6	76.8	78.3	78.1	79.5	79.9	77.8
85°	25.5	26.1	27.4	28.7	33.0	39.8	41.7	42.9	44.2	44.2	40.5
87.5°	12.4	11.2	11.4	10.9	11.8	11.7	14.2	16.2	17.2	15.8	16.2
90°	21.8	18.3	14.9	11.8	9.2	6.5	3.9	1.2	3.9	6.5	9.2
92.5°	41.9	40.0	38.0	36.1	34.3	32.5	30.7	28.9	30.7	32.5	34.3
95°	84.1	82.0	79.9	78.0	76.0	74.2	72.3	70.5	72.3	74.2	76.0
97.5°	135.2	133.7	132.1	130.7	129.4	127.9	126.6	125.2	126.6	127.9	129.4
100°	172.9	171.6	170.3	168.8	167.2	165.6	164.1	162.5	164.1	165.6	167.2
102.5°	214.1	212.4	210.6	209.3	208.3	207.4	206.4	205.5	206.4	207.4	208.3
105°	277.1	274.7	272.4	270.9	270.4	269.8	269.3	268.8	269.3	269.8	270.4
107.5°	346.2	345.2	344.3	343.6	343.3	343.0	342.7	342.4	342.7	343.0	343.3
110°	392.0	391.4	390.9	390.4	389.8	389.3	388.8	388.2	388.8	389.3	389.8





TEST NUMBER: P332487-927

CATALOG NUMBER: S123RDIW-S1165D1535U927-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	437.7	437.6	437.5	437.3	437.0	436.7	436.3	436.0	436.3	436.7	437.0
115°	509.9	510.5	511.0	510.9	510.1	509.3	508.5	507.7	508.5	509.3	510.1
117.5°	580.5	581.2	581.9	581.9	581.5	580.9	580.4	579.9	580.4	580.9	581.5
120°	628.6	629.9	631.3	631.1	629.5	628.0	626.4	624.8	626.4	628.0	629.5
122.5°	675.1	675.8	676.5	676.3	675.1	673.9	672.7	671.6	672.7	673.9	675.1
125°	745.3	745.8	746.3	746.2	745.4	744.7	743.8	743.0	743.8	744.7	745.4
127.5°	815.2	815.7	816.3	815.8	814.0	812.4	810.6	809.0	810.6	812.4	814.0
130°	860.5	861.3	862.1	861.4	859.3	857.1	855.1	852.9	855.1	857.1	859.3
132.5°	905.0	905.5	906.2	905.4	903.2	901.1	899.0	896.9	899.0	901.1	903.2
135°	970.5	970.8	971.1	970.4	968.8	967.2	965.6	964.0	965.6	967.2	968.8
137.5°	1033.8	1033.2	1032.5	1031.4	1030.2	1028.8	1027.5	1026.1	1027.5	1028.8	1030.2
140°	1075.8	1075.5	1075.2	1074.4	1073.1	1071.8	1070.5	1069.1	1070.5	1071.8	1073.1
142.5°	1115.5	1115.0	1114.5	1113.6	1112.3	1111.0	1109.6	1108.3	1109.6	1111.0	1112.3
145°	1173.9	1173.1	1172.3	1171.6	1171.1	1170.5	1170.1	1169.5	1170.1	1170.5	1171.1
147.5°	1229.2	1228.4	1227.6	1226.9	1225.9	1224.9	1223.9	1223.0	1223.9	1224.9	1225.9
150°	1264.0	1263.5	1262.9	1262.4	1261.9	1261.3	1260.8	1260.3	1260.8	1261.3	1261.9
152.5°	1295.0	1294.7	1294.3	1293.8	1293.1	1292.4	1291.6	1290.9	1291.6	1292.4	1293.1
155°	1339.7	1339.5	1339.3	1339.1	1339.1	1339.1	1339.1	1339.1	1339.1	1339.1	1339.1
157.5°	1379.3	1379.1	1378.9	1379.0	1379.3	1379.6	1379.9	1380.2	1379.9	1379.6	1379.3
160°	1403.6	1403.6	1403.6	1403.9	1404.4	1404.9	1405.5	1406.0	1405.5	1404.9	1404.4
162.5°	1426.2	1425.9	1425.7	1426.0	1426.7	1427.4	1428.2	1428.9	1428.2	1427.4	1426.7
165°	1455.0	1455.0	1455.0	1455.4	1456.2	1457.0	1457.8	1458.6	1457.8	1457.0	1456.2
167.5°	1478.0	1477.7	1477.6	1478.0	1479.0	1480.1	1481.1	1482.3	1481.1	1480.1	1479.0
170°	1490.8	1490.8	1490.8	1491.4	1492.4	1493.5	1494.5	1495.6	1494.5	1493.5	1492.4
172.5°	1501.3	1501.3	1501.3	1501.9	1502.9	1504.0	1505.1	1506.1	1505.1	1504.0	1502.9
175°	1512.4	1512.4	1512.4	1512.8	1513.9	1515.0	1516.1	1517.1	1516.1	1515.0	1513.9
177.5°	1517.8	1517.8	1517.8	1518.2	1519.1	1520.0	1520.8	1521.6	1520.8	1520.0	1519.1
180°	1520.7	1520.7	1520.7	1520.7	1520.7	1520.7	1520.7	1520.7	1520.7	1520.7	1520.7



TEST NUMBER: P332487-927

CATALOG NUMBER: S123RDIW-S1165D1535U927-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1454.4	1454.4	1454.4	1454.4	1454.4	1454.4	1454.4	1454.4	1454.4	1454.4	1454.4
2.5°	1429.6	1423.1	1418.6	1408.7	1402.2	1395.2	1388.2	1392.7	1392.2	1391.7	1391.7
5°	1381.6	1367.3	1354.2	1337.4	1326.8	1313.8	1303.8	1302.5	1305.0	1296.3	1291.3
7.5°	1334.0	1314.5	1295.9	1277.4	1257.7	1242.1	1232.2	1227.6	1221.2	1215.8	1210.3
10°	1300.7	1277.6	1259.6	1236.5	1215.4	1196.7	1184.9	1176.8	1172.4	1168.1	1160.0
12.5°	1266.3	1243.8	1220.8	1194.7	1174.6	1152.9	1144.0	1135.0	1126.6	1121.7	1110.6
15°	1216.0	1186.8	1162.4	1135.0	1112.6	1091.5	1079.0	1061.0	1058.4	1052.3	1041.0
17.5°	1165.5	1133.8	1100.3	1080.0	1054.7	1032.7	1013.8	1007.7	989.8	983.1	973.4
20°	1125.7	1096.5	1071.0	1044.2	1007.4	986.9	971.9	963.8	949.5	940.8	934.5
22.5°	1091.3	1061.6	1032.1	1000.8	970.6	947.5	936.6	924.0	916.2	904.0	897.2
25°	1042.3	1009.9	974.4	940.8	919.0	901.6	884.2	872.9	861.7	856.1	843.7
27.5°	985.2	951.4	918.2	892.7	865.9	848.7	833.0	823.0	809.5	800.1	793.2
30°	953.9	914.0	885.3	862.4	828.1	811.9	800.1	787.7	777.7	767.7	760.9
32.5°	917.5	881.1	854.0	825.5	799.2	781.5	766.2	755.3	746.8	737.3	730.5
35°	860.5	830.0	801.9	773.3	754.0	735.9	717.9	708.5	700.4	691.7	685.6
37.5°	808.9	780.4	753.8	726.6	702.7	688.0	673.4	666.3	655.4	649.5	643.2
40°	777.1	749.0	720.4	694.3	669.3	658.1	645.1	634.5	624.5	620.1	613.3
42.5°	742.2	714.2	690.0	661.9	641.4	626.2	614.2	602.6	595.1	588.7	584.9
45°	690.5	665.6	641.9	613.9	594.6	581.5	567.8	557.2	550.4	546.1	539.2
47.5°	640.3	615.4	591.4	567.0	548.3	533.4	519.7	512.3	503.2	497.9	493.2
50°	604.0	581.5	556.0	533.6	514.9	499.9	488.8	479.4	471.3	464.5	461.4
52.5°	570.6	546.7	524.7	503.7	484.0	467.1	456.9	447.0	440.9	433.1	429.5
55°	515.6	492.5	473.8	453.3	434.0	419.6	407.2	398.5	392.3	383.6	378.6
57.5°	463.8	443.2	420.9	403.1	383.2	371.1	360.8	349.0	341.4	334.5	329.6
60°	429.0	405.4	386.0	369.2	351.8	336.2	326.9	317.5	309.4	302.6	298.3
62.5°	392.6	371.9	353.6	335.3	319.4	305.9	295.0	287.2	280.0	275.7	271.3
65°	336.8	320.7	302.0	287.0	272.1	262.1	253.4	246.5	241.6	238.4	234.7
67.5°	285.5	269.8	253.5	238.8	228.9	221.3	215.6	209.7	207.2	203.2	200.7
70°	252.2	236.0	221.7	210.5	200.5	194.9	191.2	186.8	184.3	179.4	176.8
72.5°	215.8	204.1	193.8	184.6	176.6	171.5	166.8	161.4	157.4	151.9	149.4
75°	170.0	159.4	151.3	145.0	140.1	133.2	126.4	120.8	118.9	117.1	116.5
77.5°	125.9	119.1	113.3	108.1	101.9	96.9	95.4	94.1	93.8	92.8	92.8
80°	99.0	92.8	88.4	82.1	78.4	78.4	78.4	77.2	77.8	77.8	77.8
82.5°	73.6	67.9	65.5	63.3	62.5	63.0	63.0	63.3	62.9	63.8	63.4
85°	37.9	38.6	39.8	39.2	39.8	39.8	41.1	40.5	41.1	39.8	41.1
87.5°	16.3	18.4	19.6	20.8	21.9	22.2	22.9	23.1	23.8	24.0	24.2
90°	11.8	14.9	18.3	21.8	25.2	28.7	29.7	30.8	31.8	33.0	33.7
92.5°	36.1	38.0	40.0	41.9	43.9	45.9	46.7	47.5	48.4	49.3	49.5
95°	78.0	79.9	82.0	84.1	86.3	88.4	89.4	90.5	91.6	92.6	93.2
97.5°	130.7	132.1	133.7	135.2	136.8	138.3	139.6	140.8	142.0	143.2	143.8
100°	168.8	170.3	171.6	172.9	174.3	175.6	176.4	177.2	178.0	178.8	179.4
102.5°	209.3	210.6	212.4	214.1	215.9	217.6	218.5	219.3	220.1	220.9	221.2
105°	270.9	272.4	274.7	277.1	279.6	281.9	281.9	281.9	281.9	281.9	282.2
107.5°	343.6	344.3	345.2	346.2	347.1	348.1	349.0	349.8	350.6	351.5	351.7
110°	390.4	390.9	391.4	392.0	392.4	393.0	394.1	395.1	396.2	397.3	397.5



TEST NUMBER: P332487-927

CATALOG NUMBER: S123RDIW-S1165D1535U927-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	437.3	437.5	437.6	437.7	437.8	437.9	439.2	440.5	441.7	443.0	443.6
115°	510.9	511.0	510.5	509.9	509.5	508.9	509.1	509.5	509.7	509.9	509.9
117.5°	581.9	581.9	581.2	580.5	579.8	579.2	579.1	579.0	579.0	578.9	578.5
120°	631.1	631.3	629.9	628.6	627.2	626.0	625.7	625.4	625.2	624.9	624.5
122.5°	676.3	676.5	675.8	675.1	674.5	673.8	673.0	672.3	671.7	671.0	670.3
125°	746.2	746.3	745.8	745.3	744.7	744.3	743.1	742.1	741.0	740.0	738.9
127.5°	815.8	816.3	815.7	815.2	814.6	814.0	812.5	811.0	809.5	808.0	806.7
130°	861.4	862.1	861.3	860.5	859.7	858.9	857.9	856.7	855.7	854.7	853.2
132.5°	905.4	906.2	905.5	905.0	904.4	903.8	902.5	901.3	900.0	898.7	897.4
135°	970.4	971.1	970.8	970.5	970.3	970.0	968.9	967.9	966.8	965.7	965.0
137.5°	1031.4	1032.5	1033.2	1033.8	1034.5	1035.2	1034.1	1033.0	1031.9	1030.8	1029.7
140°	1074.4	1075.2	1075.5	1075.8	1076.0	1076.3	1076.0	1075.8	1075.5	1075.2	1074.2
142.5°	1113.6	1114.5	1115.0	1115.5	1115.9	1116.4	1116.2	1115.9	1115.6	1115.4	1114.5
145°	1171.6	1172.3	1173.1	1173.9	1174.6	1175.4	1175.2	1174.9	1174.6	1174.4	1173.7
147.5°	1226.9	1227.6	1228.4	1229.2	1229.9	1230.7	1230.7	1230.7	1230.7	1230.7	1229.9
150°	1262.4	1262.9	1263.5	1264.0	1264.5	1265.0	1265.0	1265.0	1265.0	1265.0	1264.2
152.5°	1293.8	1294.3	1294.7	1295.0	1295.3	1295.6	1296.1	1296.5	1296.9	1297.4	1296.9
155°	1339.1	1339.3	1339.5	1339.7	1340.1	1340.3	1341.4	1342.4	1343.5	1344.6	1344.2
157.5°	1379.0	1378.9	1379.1	1379.3	1379.5	1379.7	1380.9	1382.0	1383.1	1384.2	1384.0
160°	1403.9	1403.6	1403.6	1403.6	1403.6	1403.6	1404.9	1406.3	1407.6	1408.9	1409.1
162.5°	1426.0	1425.7	1425.9	1426.2	1426.3	1426.6	1427.9	1429.2	1430.5	1431.9	1431.7
165°	1455.4	1455.0	1455.0	1455.0	1455.0	1455.0	1456.6	1458.2	1459.8	1461.3	1461.3
167.5°	1478.0	1477.6	1477.7	1478.0	1478.2	1478.4	1480.0	1481.7	1483.4	1484.9	1484.9
170°	1491.4	1490.8	1490.8	1490.8	1490.8	1490.8	1492.7	1494.5	1496.4	1498.3	1498.3
172.5°	1501.9	1501.3	1501.3	1501.3	1501.3	1501.3	1503.0	1504.6	1506.3	1507.9	1507.8
175°	1512.8	1512.4	1512.4	1512.4	1512.4	1512.4	1513.9	1515.5	1517.1	1518.7	1518.5
177.5°	1518.2	1517.8	1517.8	1517.8	1517.8	1517.8	1519.1	1520.4	1521.6	1522.9	1522.8
180°	1520.7	1520.7	1520.7	1520.7	1520.7	1520.7	1520.7	1520.7	1520.7	1520.7	1520.7



TEST NUMBER: P332487-927

CATALOG NUMBER: S123RDIW-S1165D1535U927-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1454.4	1454.4	1454.4	1454.4	1454.4	1454.4	1454.4	1454.4	1454.4	1454.4	1454.4
2.5°	1385.8	1385.2	1385.8	1383.7	1385.8	1385.2	1385.8	1391.7	1391.7	1392.2	1392.7
5°	1289.4	1288.9	1287.0	1281.4	1287.0	1288.9	1289.4	1291.3	1296.3	1305.0	1302.5
7.5°	1205.4	1204.5	1199.0	1199.2	1199.0	1204.5	1205.4	1210.3	1215.8	1221.2	1227.6
10°	1155.6	1156.2	1148.7	1144.4	1148.7	1156.2	1155.6	1160.0	1168.1	1172.4	1176.8
12.5°	1107.3	1104.5	1098.4	1093.6	1098.4	1104.5	1107.3	1110.6	1121.7	1126.6	1135.0
15°	1043.5	1037.3	1022.4	1023.6	1022.4	1037.3	1043.5	1041.0	1052.3	1058.4	1061.0
17.5°	968.4	963.8	963.6	954.9	963.6	963.8	968.4	973.4	983.1	989.8	1007.7
20°	924.6	921.5	922.7	914.0	922.7	921.5	924.6	934.5	940.8	949.5	963.8
22.5°	890.3	887.1	881.9	879.2	881.9	887.1	890.3	897.2	904.0	916.2	924.0
25°	840.0	835.0	830.0	833.1	830.0	835.0	840.0	843.7	856.1	861.7	872.9
27.5°	789.6	785.9	780.9	780.3	780.9	785.9	789.6	793.2	800.1	809.5	823.0
30°	757.7	754.0	751.5	748.4	751.5	754.0	757.7	760.9	767.7	777.7	787.7
32.5°	725.4	724.6	720.2	719.5	720.2	724.6	725.4	730.5	737.3	746.8	755.3
35°	683.0	679.3	678.0	678.7	678.0	679.3	683.0	685.6	691.7	700.4	708.5
37.5°	642.8	637.8	635.6	633.3	635.6	637.8	642.8	643.2	649.5	655.4	666.3
40°	613.9	609.0	607.7	606.4	607.7	609.0	613.9	613.3	620.1	624.5	634.5
42.5°	581.5	579.6	578.8	576.6	578.8	579.6	581.5	584.9	588.7	595.1	602.6
45°	537.3	536.7	533.0	534.2	533.0	536.7	537.3	539.2	546.1	550.4	557.2
47.5°	490.8	488.0	485.4	487.1	485.4	488.0	490.8	493.2	497.9	503.2	512.3
50°	458.9	457.6	452.0	453.3	452.0	457.6	458.9	461.4	464.5	471.3	479.4
52.5°	427.0	422.2	420.2	419.4	420.2	422.2	427.0	429.5	433.1	440.9	447.0
55°	374.2	368.6	366.1	364.9	366.1	368.6	374.2	378.6	383.6	392.3	398.5
57.5°	322.4	320.9	318.9	320.3	318.9	320.9	322.4	329.6	334.5	341.4	349.0
60°	292.0	292.0	292.0	291.4	292.0	292.0	292.0	298.3	302.6	309.4	317.5
62.5°	268.6	267.1	266.6	267.5	266.6	267.1	268.6	271.3	275.7	280.0	287.2
65°	232.9	232.3	229.7	229.1	229.7	232.3	232.9	234.7	238.4	241.6	246.5
67.5°	199.2	196.9	196.1	195.3	196.1	196.9	199.2	200.7	203.2	207.2	209.7
70°	173.7	172.5	168.7	169.4	168.7	172.5	173.7	176.8	179.4	184.3	186.8
72.5°	146.3	145.0	144.3	143.5	144.3	145.0	146.3	149.4	151.9	157.4	161.4
75°	115.8	115.2	114.5	117.1	114.5	115.2	115.8	116.5	117.1	118.9	120.8
77.5°	92.8	92.8	93.2	92.1	93.2	92.8	92.8	92.8	92.8	93.8	94.1
80°	77.8	77.8	77.2	77.2	77.2	77.8	77.8	77.8	77.8	77.8	77.2
82.5°	62.4	62.9	63.3	62.3	63.3	62.9	62.4	63.4	63.8	62.9	63.3
85°	41.1	40.5	41.7	41.1	41.7	40.5	41.1	41.1	39.8	41.1	40.5
87.5°	25.3	24.4	24.5	25.1	24.5	24.4	25.3	24.2	24.0	23.8	23.1
90°	34.2	34.8	35.3	35.8	35.3	34.8	34.2	33.7	33.0	31.8	30.8
92.5°	49.2	48.9	48.6	48.2	48.6	48.9	49.2	49.5	49.3	48.4	47.5
95°	93.2	93.2	93.2	93.2	93.2	93.2	93.2	93.2	92.6	91.6	90.5
97.5°	143.7	143.5	143.5	143.4	143.5	143.5	143.7	143.8	143.2	142.0	140.8
100°	180.0	180.5	181.0	181.6	181.0	180.5	180.0	179.4	178.8	178.0	177.2
102.5°	221.1	220.9	220.9	220.8	220.9	220.9	221.1	221.2	220.9	220.1	219.3
105°	282.7	283.3	283.8	284.3	283.8	283.3	282.7	282.2	281.9	281.9	281.9
107.5°	351.4	351.1	350.8	350.5	350.8	351.1	351.4	351.7	351.5	350.6	349.8
110°	397.0	396.5	395.9	395.4	395.9	396.5	397.0	397.5	397.3	396.2	395.1



TEST NUMBER: P332487-927

CATALOG NUMBER: S123RDIW-S1165D1535U927-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	443.5	443.4	443.3	443.1	443.3	443.4	443.5	443.6	443.0	441.7	440.5
115°	509.7	509.5	509.1	508.9	509.1	509.5	509.7	509.9	509.9	509.7	509.5
117.5°	577.7	577.0	576.3	575.5	576.3	577.0	577.7	578.5	578.9	579.0	579.0
120°	624.0	623.4	622.9	622.3	622.9	623.4	624.0	624.5	624.9	625.2	625.4
122.5°	669.6	668.8	668.0	667.3	668.0	668.8	669.6	670.3	671.0	671.7	672.3
125°	737.8	736.8	735.7	734.7	735.7	736.8	737.8	738.9	740.0	741.0	742.1
127.5°	805.5	804.2	803.0	801.8	803.0	804.2	805.5	806.7	808.0	809.5	811.0
130°	851.4	849.5	847.6	845.7	847.6	849.5	851.4	853.2	854.7	855.7	856.7
132.5°	896.0	894.5	893.0	891.6	893.0	894.5	896.0	897.4	898.7	900.0	901.3
135°	964.4	963.8	963.4	962.8	963.4	963.8	964.4	965.0	965.7	966.8	967.9
137.5°	1028.6	1027.7	1026.7	1025.6	1026.7	1027.7	1028.6	1029.7	1030.8	1031.9	1033.0
140°	1072.3	1070.5	1068.6	1066.8	1068.6	1070.5	1072.3	1074.2	1075.2	1075.5	1075.8
142.5°	1113.1	1111.7	1110.2	1108.8	1110.2	1111.7	1113.1	1114.5	1115.4	1115.6	1115.9
145°	1172.7	1171.6	1170.5	1169.5	1170.5	1171.6	1172.7	1173.7	1174.4	1174.6	1174.9
147.5°	1228.3	1226.7	1225.0	1223.4	1225.0	1226.7	1228.3	1229.9	1230.7	1230.7	1230.7
150°	1262.7	1261.1	1259.5	1257.9	1259.5	1261.1	1262.7	1264.2	1265.0	1265.0	1265.0
152.5°	1295.5	1294.1	1292.7	1291.3	1292.7	1294.1	1295.5	1296.9	1297.4	1296.9	1296.5
155°	1342.3	1340.5	1338.6	1336.7	1338.6	1340.5	1342.3	1344.2	1344.6	1343.5	1342.4
157.5°	1382.5	1381.0	1379.5	1378.1	1379.5	1381.0	1382.5	1384.0	1384.2	1383.1	1382.0
160°	1408.0	1406.9	1405.9	1404.8	1405.9	1406.9	1408.0	1409.1	1408.9	1407.6	1406.3
162.5°	1430.0	1428.3	1426.6	1424.9	1426.6	1428.3	1430.0	1431.7	1431.9	1430.5	1429.2
165°	1459.4	1457.5	1455.6	1453.8	1455.6	1457.5	1459.4	1461.3	1461.3	1459.8	1458.2
167.5°	1483.4	1481.7	1480.0	1478.4	1480.0	1481.7	1483.4	1484.9	1484.9	1483.4	1481.7
170°	1496.4	1494.5	1492.7	1490.8	1492.7	1494.5	1496.4	1498.3	1498.3	1496.4	1494.5
172.5°	1505.9	1504.1	1502.2	1500.4	1502.2	1504.1	1505.9	1507.8	1507.9	1506.3	1504.6
175°	1516.7	1514.8	1513.0	1511.2	1513.0	1514.8	1516.7	1518.5	1518.7	1517.1	1515.5
177.5°	1521.3	1519.8	1518.4	1516.9	1518.4	1519.8	1521.3	1522.8	1522.9	1521.6	1520.4
180°	1520.7	1520.7	1520.7	1520.7	1520.7	1520.7	1520.7	1520.7	1520.7	1520.7	1520.7



TEST NUMBER: P332487-927

CATALOG NUMBER: S123RDIW-S1165D1535U927-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1454.4	1454.4	1454.4	1454.4	1454.4	1454.4	1454.4	1454.4	1454.4	1454.4	1454.4
2.5°	1388.2	1395.2	1402.2	1408.7	1418.6	1423.1	1429.6	1432.0	1439.6	1450.5	1459.4
5°	1303.8	1313.8	1326.8	1337.4	1354.2	1367.3	1381.6	1395.3	1411.5	1434.6	1455.1
7.5°	1232.2	1242.1	1257.7	1277.4	1295.9	1314.5	1334.0	1352.7	1375.9	1408.9	1441.6
10°	1184.9	1196.7	1215.4	1236.5	1259.6	1277.6	1300.7	1324.4	1353.0	1391.0	1430.2
12.5°	1144.0	1152.9	1174.6	1194.7	1220.8	1243.8	1266.3	1294.0	1326.6	1367.1	1414.2
15°	1079.0	1091.5	1112.6	1135.0	1162.4	1186.8	1216.0	1249.6	1281.4	1331.2	1388.5
17.5°	1013.8	1032.7	1054.7	1080.0	1100.3	1133.8	1165.5	1200.1	1239.1	1292.0	1354.9
20°	971.9	986.9	1007.4	1044.2	1071.0	1096.5	1125.7	1168.7	1204.8	1264.6	1329.9
22.5°	936.6	947.5	970.6	1000.8	1032.1	1061.6	1091.3	1132.3	1176.9	1233.7	1304.6
25°	884.2	901.6	919.0	940.8	974.4	1009.9	1042.3	1077.1	1124.5	1184.9	1261.5
27.5°	833.0	848.7	865.9	892.7	918.2	951.4	985.2	1025.2	1076.0	1140.0	1217.6
30°	800.1	811.9	828.1	862.4	885.3	914.0	953.9	989.4	1036.6	1104.5	1186.8
32.5°	766.2	781.5	799.2	825.5	854.0	881.1	917.5	956.0	1004.3	1071.2	1155.3
35°	717.9	735.9	754.0	773.3	801.9	830.0	860.5	902.9	952.0	1016.8	1099.5
37.5°	673.4	688.0	702.7	726.6	753.8	780.4	808.9	850.6	897.0	966.9	1042.7
40°	645.1	658.1	669.3	694.3	720.4	749.0	777.1	813.8	863.6	929.0	1002.4
42.5°	614.2	626.2	641.4	661.9	690.0	714.2	742.2	776.9	823.7	890.1	954.6
45°	567.8	581.5	594.6	613.9	641.9	665.6	690.5	723.5	771.4	826.2	883.5
47.5°	519.7	533.4	548.3	567.0	591.4	615.4	640.3	669.6	713.3	767.1	805.6
50°	488.8	499.9	514.9	533.6	556.0	581.5	604.0	635.7	677.4	719.8	753.4
52.5°	456.9	467.1	484.0	503.7	524.7	546.7	570.6	597.9	635.6	675.4	702.1
55°	407.2	419.6	434.0	453.3	473.8	492.5	515.6	543.6	573.5	603.3	621.4
57.5°	360.8	371.1	383.2	403.1	420.9	443.2	463.8	485.7	513.3	535.8	547.6
60°	326.9	336.2	351.8	369.2	386.0	405.4	429.0	450.8	472.0	490.0	499.3
62.5°	295.0	305.9	319.4	335.3	353.6	371.9	392.6	410.9	429.6	445.2	451.5
65°	253.4	262.1	272.1	287.0	302.0	320.7	336.8	355.5	369.2	378.0	383.6
67.5°	215.6	221.3	228.9	238.8	253.5	269.8	285.5	300.1	311.6	317.5	322.5
70°	191.2	194.9	200.5	210.5	221.7	236.0	252.2	262.8	272.7	277.7	282.7
72.5°	166.8	171.5	176.6	184.6	193.8	204.1	215.8	228.9	234.3	240.3	243.4
75°	126.4	133.2	140.1	145.0	151.3	159.4	170.0	178.1	181.2	186.2	186.8
77.5°	95.4	96.9	101.9	108.1	113.3	119.1	125.9	133.1	134.6	137.2	138.9
80°	78.4	78.4	78.4	82.1	88.4	92.8	99.0	102.7	105.2	105.8	106.5
82.5°	63.0	63.0	62.5	63.3	65.5	67.9	73.6	77.8	79.9	79.5	78.1
85°	41.1	39.8	39.8	39.2	39.8	38.6	37.9	40.5	44.2	44.2	42.9
87.5°	22.9	22.2	21.9	20.8	19.6	18.4	16.3	16.2	15.8	17.2	16.2
90°	29.7	28.7	25.2	21.8	18.3	14.9	11.8	9.2	6.5	3.9	1.2
92.5°	46.7	45.9	43.9	41.9	40.0	38.0	36.1	34.3	32.5	30.7	28.9
95°	89.4	88.4	86.3	84.1	82.0	79.9	78.0	76.0	74.2	72.3	70.5
97.5°	139.6	138.3	136.8	135.2	133.7	132.1	130.7	129.4	127.9	126.6	125.2
100°	176.4	175.6	174.3	172.9	171.6	170.3	168.8	167.2	165.6	164.1	162.5
102.5°	218.5	217.6	215.9	214.1	212.4	210.6	209.3	208.3	207.4	206.4	205.5
105°	281.9	281.9	279.6	277.1	274.7	272.4	270.9	270.4	269.8	269.3	268.8
107.5°	349.0	348.1	347.1	346.2	345.2	344.3	343.6	343.3	343.0	342.7	342.4
110°	394.1	393.0	392.4	392.0	391.4	390.9	390.4	389.8	389.3	388.8	388.2



TEST NUMBER: P332487-927

CATALOG NUMBER: S123RDIW-S1165D1535U927-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	439.2	437.9	437.8	437.7	437.6	437.5	437.3	437.0	436.7	436.3	436.0
115°	509.1	508.9	509.5	509.9	510.5	511.0	510.9	510.1	509.3	508.5	507.7
117.5°	579.1	579.2	579.8	580.5	581.2	581.9	581.9	581.5	580.9	580.4	579.9
120°	625.7	626.0	627.2	628.6	629.9	631.3	631.1	629.5	628.0	626.4	624.8
122.5°	673.0	673.8	674.5	675.1	675.8	676.5	676.3	675.1	673.9	672.7	671.6
125°	743.1	744.3	744.7	745.3	745.8	746.3	746.2	745.4	744.7	743.8	743.0
127.5°	812.5	814.0	814.6	815.2	815.7	816.3	815.8	814.0	812.4	810.6	809.0
130°	857.9	858.9	859.7	860.5	861.3	862.1	861.4	859.3	857.1	855.1	852.9
132.5°	902.5	903.8	904.4	905.0	905.5	906.2	905.4	903.2	901.1	899.0	896.9
135°	968.9	970.0	970.3	970.5	970.8	971.1	970.4	968.8	967.2	965.6	964.0
137.5°	1034.1	1035.2	1034.5	1033.8	1033.2	1032.5	1031.4	1030.2	1028.8	1027.5	1026.1
140°	1076.0	1076.3	1076.0	1075.8	1075.5	1075.2	1074.4	1073.1	1071.8	1070.5	1069.1
142.5°	1116.2	1116.4	1115.9	1115.5	1115.0	1114.5	1113.6	1112.3	1111.0	1109.6	1108.3
145°	1175.2	1175.4	1174.6	1173.9	1173.1	1172.3	1171.6	1171.1	1170.5	1170.1	1169.5
147.5°	1230.7	1230.7	1229.9	1229.2	1228.4	1227.6	1226.9	1225.9	1224.9	1223.9	1223.0
150°	1265.0	1265.0	1264.5	1264.0	1263.5	1262.9	1262.4	1261.9	1261.3	1260.8	1260.3
152.5°	1296.1	1295.6	1295.3	1295.0	1294.7	1294.3	1293.8	1293.1	1292.4	1291.6	1290.9
155°	1341.4	1340.3	1340.1	1339.7	1339.5	1339.3	1339.1	1339.1	1339.1	1339.1	1339.1
157.5°	1380.9	1379.7	1379.5	1379.3	1379.1	1378.9	1379.0	1379.3	1379.6	1379.9	1380.2
160°	1404.9	1403.6	1403.6	1403.6	1403.6	1403.6	1403.9	1404.4	1404.9	1405.5	1406.0
162.5°	1427.9	1426.6	1426.3	1426.2	1425.9	1425.7	1426.0	1426.7	1427.4	1428.2	1428.9
165°	1456.6	1455.0	1455.0	1455.0	1455.0	1455.0	1455.4	1456.2	1457.0	1457.8	1458.6
167.5°	1480.0	1478.4	1478.2	1478.0	1477.7	1477.6	1478.0	1479.0	1480.1	1481.1	1482.3
170°	1492.7	1490.8	1490.8	1490.8	1490.8	1490.8	1491.4	1492.4	1493.5	1494.5	1495.6
172.5°	1503.0	1501.3	1501.3	1501.3	1501.3	1501.3	1501.9	1502.9	1504.0	1505.1	1506.1
175°	1513.9	1512.4	1512.4	1512.4	1512.4	1512.4	1512.8	1513.9	1515.0	1516.1	1517.1
177.5°	1519.1	1517.8	1517.8	1517.8	1517.8	1517.8	1518.2	1519.1	1520.0	1520.8	1521.6
180°	1520.7	1520.7	1520.7	1520.7	1520.7	1520.7	1520.7	1520.7	1520.7	1520.7	1520.7



TEST NUMBER: P332487-927

CATALOG NUMBER: S123RDIW-S1165D1535U927-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1454.4	1454.4	1454.4	1454.4	1454.4	1454.4	1454.4	1454.4	1454.4	1454.4	1454.4
2.5°	1462.4	1467.9	1474.9	1485.3	1493.3	1500.3	1501.8	1503.8	1508.8	1517.2	1523.7
5°	1471.9	1486.2	1509.3	1531.7	1555.9	1575.9	1594.6	1607.7	1620.1	1646.2	1667.4
7.5°	1468.9	1500.8	1536.9	1577.2	1617.9	1657.3	1693.9	1726.6	1759.3	1797.4	1840.9
10°	1466.9	1504.3	1552.8	1604.5	1661.2	1716.6	1770.1	1811.9	1860.4	1904.0	1959.4
12.5°	1457.5	1511.2	1569.3	1635.4	1705.0	1768.9	1839.4	1897.0	1952.6	2015.5	2080.0
15°	1445.1	1510.5	1584.0	1671.7	1777.6	1854.8	1927.1	2027.3	2095.8	2164.2	2256.5
17.5°	1422.6	1502.4	1594.2	1708.3	1796.5	1900.3	2009.0	2088.2	2180.5	2277.0	2360.4
20°	1404.6	1497.5	1600.1	1712.2	1825.0	1937.6	2042.9	2137.5	2232.8	2344.2	2412.7
22.5°	1386.7	1478.5	1585.2	1704.3	1825.4	1944.1	2063.2	2174.4	2281.6	2394.1	2481.4
25°	1348.6	1457.6	1573.4	1694.8	1814.3	1945.1	2087.1	2211.0	2343.6	2459.4	2542.2
27.5°	1310.0	1409.8	1525.2	1648.4	1781.2	1935.8	2102.8	2243.6	2376.5	2459.4	2485.4
30°	1275.2	1381.0	1486.8	1612.0	1755.8	1928.3	2105.7	2267.0	2376.0	2412.0	2385.3
32.5°	1239.8	1335.7	1440.5	1568.7	1721.4	1909.9	2109.7	2253.0	2318.6	2291.1	2182.1
35°	1177.4	1263.9	1365.4	1493.7	1669.3	1899.7	2093.3	2190.4	2174.2	2018.6	1813.1
37.5°	1110.6	1181.1	1275.2	1409.3	1615.3	1859.2	2022.5	2036.9	1896.8	1657.8	1420.5
40°	1057.9	1121.3	1217.9	1358.0	1573.4	1819.3	1951.3	1893.4	1676.1	1410.2	1212.3
42.5°	1006.5	1060.1	1153.1	1304.2	1533.5	1765.1	1845.2	1719.1	1468.4	1217.0	1037.0
45°	919.6	970.0	1063.4	1218.5	1452.0	1661.2	1650.6	1431.4	1180.5	978.2	828.7
47.5°	837.2	881.3	968.9	1127.2	1356.2	1505.5	1406.5	1173.3	960.4	798.1	691.5
50°	778.9	822.5	909.7	1066.0	1279.5	1388.5	1247.1	1022.4	827.5	693.0	608.3
52.5°	723.1	765.7	845.4	997.7	1186.8	1252.0	1100.2	891.8	729.4	613.3	540.6
55°	645.1	677.4	749.0	894.7	1036.1	1051.0	897.2	722.9	589.0	508.1	458.3
57.5°	565.5	593.3	664.1	780.1	879.2	871.6	725.7	575.0	484.8	424.6	388.5
60°	513.7	541.1	603.3	703.0	777.7	751.5	617.7	496.2	419.1	374.9	346.2
62.5°	465.3	486.8	545.0	617.7	671.5	641.9	528.0	427.5	366.2	329.0	306.3
65°	395.4	412.8	459.5	497.5	527.4	498.8	404.1	334.4	290.2	264.0	248.4
67.5°	328.8	339.9	369.5	383.2	404.3	372.8	303.9	257.1	232.0	209.9	199.2
70°	287.0	295.1	310.7	321.9	327.5	295.1	244.1	209.8	188.6	173.1	166.3
72.5°	245.2	252.3	255.4	264.6	261.7	231.4	196.2	169.0	153.8	143.2	134.4
75°	187.4	190.5	187.4	183.7	175.5	154.4	130.2	116.5	105.2	100.2	97.1
77.5°	136.6	135.6	131.3	125.6	111.7	98.4	85.3	80.7	75.8	73.2	72.1
80°	105.2	102.7	99.0	89.7	77.8	68.5	65.4	62.3	60.4	57.3	56.6
82.5°	78.3	76.8	70.6	62.7	54.4	50.1	47.5	46.3	44.4	42.9	42.7
85°	41.7	39.8	33.0	28.7	27.4	26.1	25.5	25.5	23.1	22.4	22.4
87.5°	14.2	11.7	11.8	10.9	11.4	11.2	12.4	12.0	12.2	12.9	12.1
90°	3.9	6.5	9.2	11.8	14.9	18.3	21.8	25.2	28.7	29.7	30.8
92.5°	30.7	32.5	34.3	36.1	38.0	40.0	41.9	43.9	45.9	46.7	47.5
95°	72.3	74.2	76.0	78.0	79.9	82.0	84.1	86.3	88.4	89.4	90.5
97.5°	126.6	127.9	129.4	130.7	132.1	133.7	135.2	136.8	138.3	139.6	140.8
100°	164.1	165.6	167.2	168.8	170.3	171.6	172.9	174.3	175.6	176.4	177.2
102.5°	206.4	207.4	208.3	209.3	210.6	212.4	214.1	215.9	217.6	218.5	219.3
105°	269.3	269.8	270.4	270.9	272.4	274.7	277.1	279.6	281.9	281.9	281.9
107.5°	342.7	343.0	343.3	343.6	344.3	345.2	346.2	347.1	348.1	349.0	349.8
110°	388.8	389.3	389.8	390.4	390.9	391.4	392.0	392.4	393.0	394.1	395.1





TEST NUMBER: P332487-927

CATALOG NUMBER: S123RDIW-S1165D1535U927-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	436.3	436.7	437.0	437.3	437.5	437.6	437.7	437.8	437.9	439.2	440.5
115°	508.5	509.3	510.1	510.9	511.0	510.5	509.9	509.5	508.9	509.1	509.5
117.5°	580.4	580.9	581.5	581.9	581.9	581.2	580.5	579.8	579.2	579.1	579.0
120°	626.4	628.0	629.5	631.1	631.3	629.9	628.6	627.2	626.0	625.7	625.4
122.5°	672.7	673.9	675.1	676.3	676.5	675.8	675.1	674.5	673.8	673.0	672.3
125°	743.8	744.7	745.4	746.2	746.3	745.8	745.3	744.7	744.3	743.1	742.1
127.5°	810.6	812.4	814.0	815.8	816.3	815.7	815.2	814.6	814.0	812.5	811.0
130°	855.1	857.1	859.3	861.4	862.1	861.3	860.5	859.7	858.9	857.9	856.7
132.5°	899.0	901.1	903.2	905.4	906.2	905.5	905.0	904.4	903.8	902.5	901.3
135°	965.6	967.2	968.8	970.4	971.1	970.8	970.5	970.3	970.0	968.9	967.9
137.5°	1027.5	1028.8	1030.2	1031.4	1032.5	1033.2	1033.8	1034.5	1035.2	1034.1	1033.0
140°	1070.5	1071.8	1073.1	1074.4	1075.2	1075.5	1075.8	1076.0	1076.3	1076.0	1075.8
142.5°	1109.6	1111.0	1112.3	1113.6	1114.5	1115.0	1115.5	1115.9	1116.4	1116.2	1115.9
145°	1170.1	1170.5	1171.1	1171.6	1172.3	1173.1	1173.9	1174.6	1175.4	1175.2	1174.9
147.5°	1223.9	1224.9	1225.9	1226.9	1227.6	1228.4	1229.2	1229.9	1230.7	1230.7	1230.7
150°	1260.8	1261.3	1261.9	1262.4	1262.9	1263.5	1264.0	1264.5	1265.0	1265.0	1265.0
152.5°	1291.6	1292.4	1293.1	1293.8	1294.3	1294.7	1295.0	1295.3	1295.6	1296.1	1296.5
155°	1339.1	1339.1	1339.1	1339.1	1339.3	1339.5	1339.7	1340.1	1340.3	1341.4	1342.4
157.5°	1379.9	1379.6	1379.3	1379.0	1378.9	1379.1	1379.3	1379.5	1379.7	1380.9	1382.0
160°	1405.5	1404.9	1404.4	1403.9	1403.6	1403.6	1403.6	1403.6	1403.6	1404.9	1406.3
162.5°	1428.2	1427.4	1426.7	1426.0	1425.7	1425.9	1426.2	1426.3	1426.6	1427.9	1429.2
165°	1457.8	1457.0	1456.2	1455.4	1455.0	1455.0	1455.0	1455.0	1455.0	1456.6	1458.2
167.5°	1481.1	1480.1	1479.0	1478.0	1477.6	1477.7	1478.0	1478.2	1478.4	1480.0	1481.7
170°	1494.5	1493.5	1492.4	1491.4	1490.8	1490.8	1490.8	1490.8	1490.8	1492.7	1494.5
172.5°	1505.1	1504.0	1502.9	1501.9	1501.3	1501.3	1501.3	1501.3	1501.3	1503.0	1504.6
175°	1516.1	1515.0	1513.9	1512.8	1512.4	1512.4	1512.4	1512.4	1512.4	1513.9	1515.5
177.5°	1520.8	1520.0	1519.1	1518.2	1517.8	1517.8	1517.8	1517.8	1517.8	1519.1	1520.4
180°	1520.7	1520.7	1520.7	1520.7	1520.7	1520.7	1520.7	1520.7	1520.7	1520.7	1520.7



TEST NUMBER: P332487-927

CATALOG NUMBER: S123RDIW-S1165D1535U927-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	1454.4	1454.4	1454.4	1454.4	1454.4	1454.4	1454.4
2.5°	1534.1	1534.1	1536.1	1543.6	1544.6	1551.1	1549.1
5°	1686.1	1697.9	1702.2	1720.9	1732.2	1737.2	1727.2
7.5°	1871.8	1905.3	1921.0	1940.6	1958.0	1963.2	1949.6
10°	2007.4	2042.2	2071.5	2089.5	2106.3	2117.6	2131.9
12.5°	2138.3	2181.2	2209.0	2234.5	2251.8	2266.0	2268.3
15°	2280.7	2345.4	2394.6	2430.7	2448.8	2458.1	2454.4
17.5°	2424.2	2484.3	2519.3	2556.1	2581.2	2582.4	2583.1
20°	2505.4	2564.0	2604.5	2631.9	2659.9	2658.6	2664.8
22.5°	2559.8	2605.8	2636.9	2656.7	2666.3	2661.7	2662.8
25°	2585.1	2598.8	2593.3	2561.5	2553.4	2524.1	2529.1
27.5°	2454.2	2389.4	2322.4	2236.3	2168.3	2113.9	2116.7
30°	2276.3	2161.8	2031.0	1921.4	1823.0	1795.6	1737.2
32.5°	2027.7	1855.9	1702.8	1600.7	1516.2	1493.3	1442.2
35°	1606.4	1439.6	1282.0	1187.3	1150.0	1097.7	1097.1
37.5°	1248.6	1101.7	1018.4	947.4	910.1	878.5	875.4
40°	1050.4	935.8	872.9	821.9	785.1	761.4	755.9
42.5°	911.9	819.3	760.3	728.7	700.4	688.2	679.1
45°	744.7	682.4	641.3	612.7	599.6	590.3	585.3
47.5°	622.9	581.1	553.2	534.1	523.5	513.7	516.3
50°	556.7	522.4	501.8	483.8	475.7	468.8	469.4
52.5°	503.4	472.6	456.0	442.9	432.8	428.0	425.6
55°	427.1	407.8	391.0	381.7	376.0	369.2	367.3
57.5°	364.3	349.4	335.7	325.1	323.8	317.2	318.1
60°	322.5	310.1	298.9	293.3	288.9	283.3	285.2
62.5°	288.1	277.7	267.5	262.8	258.5	254.4	255.2
65°	236.0	226.0	219.8	217.3	215.4	213.6	211.7
67.5°	188.1	182.0	178.1	172.7	168.9	168.3	166.4
70°	158.1	150.0	143.2	136.3	134.5	133.9	134.5
72.5°	126.7	121.7	119.8	116.5	116.1	114.5	115.6
75°	95.3	93.4	92.1	89.7	89.7	89.7	89.7
77.5°	70.3	69.1	68.4	67.9	67.3	66.4	66.2
80°	54.8	54.2	52.9	52.9	52.3	52.9	52.3
82.5°	41.4	41.2	40.0	40.0	39.4	39.0	39.4
85°	21.2	20.5	21.8	20.5	21.2	20.0	21.2
87.5°	12.4	12.6	12.2	12.4	12.0	13.1	12.1
90°	31.8	33.0	33.7	34.2	34.8	35.3	35.8
92.5°	48.4	49.3	49.5	49.2	48.9	48.6	48.2
95°	91.6	92.6	93.2	93.2	93.2	93.2	93.2
97.5°	142.0	143.2	143.8	143.7	143.5	143.5	143.4
100°	178.0	178.8	179.4	180.0	180.5	181.0	181.6
102.5°	220.1	220.9	221.2	221.1	220.9	220.9	220.8
105°	281.9	281.9	282.2	282.7	283.3	283.8	284.3
107.5°	350.6	351.5	351.7	351.4	351.1	350.8	350.5
110°	396.2	397.3	397.5	397.0	396.5	395.9	395.4



TEST NUMBER: P332487-927

CATALOG NUMBER: S123RDIW-S1165D1535U927-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	441.7	443.0	443.6	443.5	443.4	443.3	443.1
115°	509.7	509.9	509.9	509.7	509.5	509.1	508.9
117.5°	579.0	578.9	578.5	577.7	577.0	576.3	575.5
120°	625.2	624.9	624.5	624.0	623.4	622.9	622.3
122.5°	671.7	671.0	670.3	669.6	668.8	668.0	667.3
125°	741.0	740.0	738.9	737.8	736.8	735.7	734.7
127.5°	809.5	808.0	806.7	805.5	804.2	803.0	801.8
130°	855.7	854.7	853.2	851.4	849.5	847.6	845.7
132.5°	900.0	898.7	897.4	896.0	894.5	893.0	891.6
135°	966.8	965.7	965.0	964.4	963.8	963.4	962.8
137.5°	1031.9	1030.8	1029.7	1028.6	1027.7	1026.7	1025.6
140°	1075.5	1075.2	1074.2	1072.3	1070.5	1068.6	1066.8
142.5°	1115.6	1115.4	1114.5	1113.1	1111.7	1110.2	1108.8
145°	1174.6	1174.4	1173.7	1172.7	1171.6	1170.5	1169.5
147.5°	1230.7	1230.7	1229.9	1228.3	1226.7	1225.0	1223.4
150°	1265.0	1265.0	1264.2	1262.7	1261.1	1259.5	1257.9
152.5°	1296.9	1297.4	1296.9	1295.5	1294.1	1292.7	1291.3
155°	1343.5	1344.6	1344.2	1342.3	1340.5	1338.6	1336.7
157.5°	1383.1	1384.2	1384.0	1382.5	1381.0	1379.5	1378.1
160°	1407.6	1408.9	1409.1	1408.0	1406.9	1405.9	1404.8
162.5°	1430.5	1431.9	1431.7	1430.0	1428.3	1426.6	1424.9
165°	1459.8	1461.3	1461.3	1459.4	1457.5	1455.6	1453.8
167.5°	1483.4	1484.9	1484.9	1483.4	1481.7	1480.0	1478.4
170°	1496.4	1498.3	1498.3	1496.4	1494.5	1492.7	1490.8
172.5°	1506.3	1507.9	1507.8	1505.9	1504.1	1502.2	1500.4
175°	1517.1	1518.7	1518.5	1516.7	1514.8	1513.0	1511.2
177.5°	1521.6	1522.9	1522.8	1521.3	1519.8	1518.4	1516.9
180°	1520.7	1520.7	1520.7	1520.7	1520.7	1520.7	1520.7

(END OF REPORT)