

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331580-840

Luminaire Tested: **S122DIW-S865D1440U840-4F0-1E-UDD-A1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331580-840
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-8,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122DIW-S865D1440U840-4F0-1E-UDD-A1
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 865 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 1440 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 8898.4 lumens
Efficiency: N/A
Efficacy: 116.2 lumens/watt
Spacing Criteria (0/90/45): 1.08 / 1.16 / 1.23
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 76.6
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331580-840

CATALOG NUMBER: S122DIW-S865D1440U840-4F0-1E-UDD-A1

Luminous Intensity Polar Plot





TEST NUMBER: P331580-840

CATALOG NUMBER: S122DIW-S865D1440U840-4F0-1E-UDD-A1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	106	106	106	106	97	97	97	97	80	80	80	64	64	64	50	50	50	43				
1	97	93	89	86	88	85	82	79	70	68	66	57	56	54	45	44	43	37				
2	88	81	75	70	81	75	70	65	62	58	55	51	48	46	40	38	37	32				
3	81	72	65	59	74	66	60	55	55	51	47	45	42	39	36	34	32	27				
4	74	64	56	50	68	59	52	47	49	44	40	40	37	34	32	30	28	24				
5	68	57	49	43	62	53	46	41	44	39	35	36	33	30	29	27	24	21				
6	63	51	43	38	57	47	40	35	40	35	31	33	29	26	27	24	22	19				
7	58	46	39	33	53	43	36	31	36	31	27	30	26	23	24	22	19	17				
8	54	42	35	30	49	39	32	28	33	28	24	28	24	21	23	20	18	15				
9	50	39	31	26	46	36	29	25	31	25	22	26	22	19	21	18	16	14				
10	47	35	28	24	43	33	27	22	28	23	20	24	20	17	19	17	15	13				

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	28150	28150	28150	28150
5°	31561	28336	25109	28336
10°	36166	28103	21730	28103
15°	40010	27587	19198	27587
20°	39400	27034	17500	27034
25°	35527	26298	16425	26298
30°	29358	25124	15642	25124
35°	21396	23893	15084	23893
40°	17089	22443	14773	22443
45°	14933	20763	14351	20763
50°	14039	19138	14071	19138
55°	12940	17486	13695	17486
60°	11858	15733	13114	15733
65°	10804	14155	12542	14155
70°	9805	12623	11703	12623
75°	8696	10911	10368	10911
80°	7476	9028	8350	9028
85°	6706	6706	4965	6706



TEST NUMBER: P331580-840

CATALOG NUMBER: S122DIW-S865D1440U840-4F0-1E-UDD-A1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	166.1	1.9
10°-20°	482.7	5.4
20°-30°	700.6	7.9
30°-40°	739.3	8.3
40°-50°	654.6	7.4
50°-60°	522.4	5.9
60°-70°	355.1	4.0
70°-80°	182.0	2.0
80°-90°	51.1	0.6
90°-100°	114.3	1.3
100°-110°	355.0	4.0
110°-120°	606.9	6.8
120°-130°	798.1	9.0
130°-140°	895.8	10.1
140°-150°	878.3	9.9
150°-160°	736.7	8.3
160°-170°	488.6	5.5
170°-180°	170.8	1.9
0°-30°	1349.4	15.2
0°-40°	2088.7	23.5
0°-60°	3265.7	36.7
0°-90°	3853.9	43.3
90°-120°	1076.2	12.1
90°-150°	3648.4	41.0
90°-180°	5045.0	56.7
0°-180°	8898.4	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1744	1744	1744	1744	1744	
5°	1947	1748	1549	1748	1947	194
15°	2394	1650	1148	1650	2394	660
25°	1994	1476	922	1476	1994	901
35°	1086	1212	765	1212	1086	706
45°	654	909	628	909	654	514
55°	460	621	486	621	460	412
65°	283	370	328	370	283	281
75°	139	175	166	175	139	149
85°	36	36	27	36	36	41
90°	52	2	52	2	52	24
95°	94	79	94	79	94	105
105°	338	327	338	327	338	355
115°	609	609	609	609	609	601
125°	889	886	889	886	889	793
135°	1160	1146	1160	1146	1160	893
145°	1407	1392	1407	1392	1407	878
155°	1603	1591	1603	1591	1603	738
165°	1732	1731	1732	1731	1732	489
175°	1795	1801	1795	1801	1795	171
180°	1804	1804	1804	1804	1804	



TEST NUMBER: P331580-840

CATALOG NUMBER: S122DIW-S865D1440U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1743.5	1743.5	1743.5	1743.5	1743.5	1743.5	1743.5	1743.5	1743.5	1743.5	1743.5
2.5°	1824.0	1824.5	1825.6	1817.1	1815.9	1815.9	1808.5	1802.0	1794.5	1784.3	1785.4
5°	1947.3	1954.7	1957.3	1949.3	1937.2	1935.9	1924.5	1905.7	1888.3	1874.2	1864.2
7.5°	2094.5	2097.4	2090.8	2080.2	2071.2	2055.2	2034.0	2013.3	1984.2	1957.5	1937.6
10°	2205.9	2210.0	2198.6	2183.1	2170.4	2151.6	2120.8	2089.3	2051.1	2014.3	1984.8
12.5°	2290.7	2300.6	2285.9	2283.9	2262.1	2236.3	2199.7	2183.7	2130.0	2078.6	2047.0
15°	2393.6	2392.9	2394.3	2381.5	2365.4	2361.4	2322.6	2280.4	2204.6	2174.4	2122.2
17.5°	2363.8	2374.0	2378.7	2378.5	2378.1	2375.6	2363.2	2336.5	2298.6	2249.7	2189.3
20°	2293.1	2306.4	2308.5	2323.9	2332.6	2344.0	2348.6	2341.3	2317.8	2276.9	2224.7
22.5°	2183.7	2187.5	2193.7	2217.8	2236.6	2265.2	2280.1	2304.8	2295.8	2275.9	2232.2
25°	1994.2	1987.5	2010.9	2023.0	2066.6	2112.1	2145.0	2181.1	2213.3	2232.7	2220.0
27.5°	1766.7	1756.6	1791.7	1823.7	1859.1	1908.4	1959.6	2020.0	2070.3	2133.1	2154.7
30°	1574.7	1580.7	1614.3	1648.4	1702.0	1771.7	1829.4	1895.7	1967.4	2037.7	2086.7
32.5°	1367.8	1391.0	1412.2	1464.5	1511.8	1589.4	1673.9	1756.9	1846.2	1926.2	2002.0
35°	1085.5	1112.4	1141.9	1180.0	1246.4	1323.4	1405.8	1517.7	1639.7	1749.0	1838.8
37.5°	913.7	909.5	926.3	953.9	1007.6	1069.9	1164.8	1275.4	1418.9	1547.2	1673.9
40°	810.8	808.1	820.2	845.7	886.6	932.1	1015.2	1112.4	1245.7	1402.5	1553.3
42.5°	740.0	741.6	748.3	766.3	794.4	831.8	894.0	976.7	1098.8	1246.5	1408.6
45°	654.0	658.7	666.1	674.8	690.8	721.6	756.5	815.5	912.0	1035.3	1194.8
47.5°	592.1	592.2	599.8	607.3	616.9	634.3	662.7	699.7	767.8	868.2	1005.3
50°	558.9	554.2	559.6	565.5	575.6	587.6	606.4	641.3	686.8	767.9	882.5
52.5°	518.2	518.3	523.1	525.3	534.3	546.4	563.5	587.6	628.9	692.4	786.6
55°	459.7	463.0	465.7	469.7	477.8	486.5	499.9	515.9	548.2	595.7	665.4
57.5°	404.8	405.8	408.5	416.2	421.2	429.3	442.0	456.6	477.5	512.7	565.1
60°	367.2	367.2	372.5	375.9	382.6	390.6	400.7	414.8	433.5	462.3	504.6
62.5°	333.0	332.3	334.5	340.0	345.1	352.6	362.6	374.6	392.2	417.9	452.6
65°	282.8	281.4	285.5	286.8	292.2	299.5	307.6	320.3	334.4	353.1	384.0
67.5°	234.5	236.1	238.3	240.9	243.8	251.6	256.9	265.9	277.8	293.4	314.3
70°	207.7	207.7	207.7	209.7	213.8	217.8	223.2	230.6	241.9	255.3	274.1
72.5°	177.7	179.9	182.0	180.8	185.9	188.3	194.7	198.8	209.7	218.3	234.9
75°	139.4	139.4	139.4	142.7	144.7	146.7	150.8	154.8	160.2	170.9	179.6
77.5°	104.0	103.7	104.4	105.2	107.3	109.8	111.0	114.6	119.6	124.5	131.9
80°	80.4	81.8	82.4	83.7	83.7	85.1	85.7	90.5	93.8	97.1	101.9
82.5°	62.2	62.4	62.6	62.8	63.4	64.2	65.9	67.5	68.6	71.4	75.0
85°	36.2	35.5	35.5	36.9	36.2	36.2	37.6	38.9	38.9	39.5	41.5
87.5°	24.3	24.2	24.7	24.1	24.0	24.5	24.7	24.3	25.0	25.7	24.7
90°	51.8	51.4	51.1	50.8	50.4	50.6	51.3	51.9	52.6	53.3	45.8
92.5°	49.3	49.3	49.2	49.1	49.1	49.0	48.8	48.7	48.6	48.4	46.7
95°	94.4	95.0	95.7	96.4	97.0	97.5	97.5	97.5	97.5	97.5	96.7
97.5°	163.5	163.6	163.6	163.7	163.8	163.8	163.8	163.8	163.8	163.8	162.5
100°	208.5	208.9	209.2	209.5	210.0	210.1	210.1	210.1	210.1	210.1	209.0
102.5°	259.7	260.0	260.4	260.7	261.1	261.2	260.8	260.5	260.3	260.0	258.7
105°	338.0	338.0	338.0	338.0	338.0	337.6	337.0	336.3	335.6	335.0	334.3
107.5°	411.6	413.2	414.8	416.4	417.9	418.5	418.3	418.0	417.7	417.5	417.5
110°	468.9	469.9	470.9	471.9	472.9	473.5	473.5	473.5	473.5	473.5	473.5



TEST NUMBER: P331580-840

CATALOG NUMBER: S122DIW-S865D1440U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	523.7	524.4	525.2	525.9	526.6	527.5	528.3	529.1	529.9	530.7	531.0
115°	608.9	610.0	611.0	612.0	613.0	613.7	614.0	614.4	614.7	615.1	615.7
117.5°	690.2	691.3	692.3	693.3	694.3	695.3	696.1	696.9	697.7	698.5	700.3
120°	747.5	748.5	749.5	750.5	751.5	752.0	752.0	752.0	752.0	752.0	754.8
122.5°	803.5	804.3	805.1	805.8	806.5	807.3	808.1	808.9	809.7	810.5	812.4
125°	889.1	889.5	889.8	890.1	890.5	891.1	892.1	893.1	894.1	895.1	896.3
127.5°	967.0	968.2	969.2	970.3	971.4	972.5	973.7	974.9	976.1	977.4	978.7
130°	1023.1	1024.4	1025.8	1027.1	1028.4	1029.5	1030.2	1030.9	1031.6	1032.2	1032.9
132.5°	1076.6	1077.7	1078.8	1079.9	1081.0	1082.3	1083.8	1085.3	1086.7	1088.2	1088.1
135°	1160.1	1161.1	1162.2	1163.2	1164.2	1164.9	1165.2	1165.5	1165.9	1166.2	1165.5
137.5°	1235.6	1237.0	1238.3	1239.7	1241.0	1241.8	1242.1	1242.3	1242.6	1242.9	1242.0
140°	1288.0	1289.3	1290.7	1292.0	1293.4	1294.0	1294.0	1294.0	1294.0	1294.0	1292.4
142.5°	1335.4	1336.9	1338.2	1339.6	1340.9	1341.4	1341.2	1340.9	1340.6	1340.4	1339.2
145°	1406.7	1408.1	1409.5	1410.8	1412.1	1412.6	1412.3	1412.0	1411.6	1411.3	1409.3
147.5°	1470.4	1471.7	1472.9	1474.2	1475.5	1475.8	1475.0	1474.3	1473.6	1472.8	1471.5
150°	1511.8	1512.8	1513.8	1514.8	1515.8	1515.8	1514.8	1513.8	1512.8	1511.8	1510.5
152.5°	1550.7	1552.1	1553.3	1554.6	1555.9	1555.9	1554.6	1553.3	1552.1	1550.7	1549.1
155°	1603.2	1604.2	1605.2	1606.2	1607.2	1606.8	1605.2	1603.5	1601.7	1600.0	1599.0
157.5°	1648.2	1649.8	1651.4	1653.0	1654.7	1654.4	1652.0	1649.7	1647.4	1645.2	1644.6
160°	1676.2	1677.6	1678.9	1680.2	1681.6	1681.2	1679.2	1677.2	1675.2	1673.1	1672.8
162.5°	1700.5	1702.2	1703.8	1705.5	1707.1	1706.7	1704.5	1702.1	1699.8	1697.5	1697.2
165°	1732.5	1734.2	1736.0	1737.6	1739.3	1739.0	1736.6	1734.2	1731.8	1729.5	1729.5
167.5°	1758.7	1760.5	1762.2	1764.0	1765.7	1765.4	1763.1	1760.7	1758.4	1756.0	1756.1
170°	1772.1	1774.1	1776.2	1778.2	1780.2	1780.1	1777.7	1775.3	1772.9	1770.6	1770.9
172.5°	1783.1	1785.1	1787.2	1789.2	1791.2	1791.0	1788.7	1786.2	1783.9	1781.5	1781.9
175°	1794.9	1797.0	1799.0	1801.0	1803.1	1802.9	1800.5	1798.2	1795.8	1793.4	1794.1
177.5°	1800.4	1802.0	1803.7	1805.3	1807.0	1807.0	1805.3	1803.7	1802.0	1800.4	1801.0
180°	1804.1	1804.1	1804.1	1804.1	1804.1	1804.1	1804.1	1804.1	1804.1	1804.1	1804.1



TEST NUMBER: P331580-840

CATALOG NUMBER: S122DIW-S865D1440U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1743.5	1743.5	1743.5	1743.5	1743.5	1743.5	1743.5	1743.5	1743.5	1743.5	1743.5
2.5°	1789.2	1784.8	1782.2	1772.5	1763.9	1755.3	1752.7	1753.7	1742.0	1730.7	1725.9
5°	1858.9	1845.4	1832.7	1814.6	1793.2	1769.7	1757.7	1748.3	1724.8	1699.4	1684.7
7.5°	1921.3	1902.1	1877.6	1843.6	1812.3	1775.4	1752.0	1731.2	1697.0	1661.0	1639.0
10°	1959.3	1933.2	1901.7	1860.2	1822.0	1777.1	1745.6	1714.1	1673.9	1631.0	1604.2
12.5°	1992.1	1956.8	1925.8	1872.5	1827.4	1771.2	1733.8	1689.4	1647.1	1596.2	1569.9
15°	2069.9	2004.9	1945.9	1885.6	1830.0	1751.6	1710.1	1650.4	1594.8	1531.9	1501.7
17.5°	2130.1	2057.1	1964.2	1887.5	1822.6	1735.9	1674.9	1603.4	1537.6	1465.6	1424.6
20°	2164.4	2080.6	1980.7	1889.7	1811.9	1712.7	1646.4	1573.4	1496.3	1415.2	1371.0
22.5°	2184.7	2096.7	1997.9	1881.6	1790.5	1693.9	1610.5	1530.5	1452.4	1364.8	1318.5
25°	2191.2	2110.8	2006.3	1874.9	1763.7	1654.5	1554.0	1476.2	1381.7	1300.0	1232.3
27.5°	2159.3	2101.6	2001.1	1862.3	1732.7	1605.0	1493.0	1404.9	1305.3	1216.5	1148.4
30°	2120.2	2086.7	1988.8	1849.5	1708.1	1570.7	1447.4	1347.6	1248.4	1158.6	1088.9
32.5°	2059.6	2052.3	1966.3	1831.2	1681.8	1527.3	1399.7	1298.8	1188.9	1100.7	1034.2
35°	1940.6	1972.8	1918.4	1790.5	1632.3	1465.5	1327.5	1212.2	1098.3	1013.8	951.5
37.5°	1781.1	1861.0	1846.7	1730.8	1565.6	1398.3	1245.9	1125.4	1016.8	931.6	870.4
40°	1671.2	1773.0	1787.8	1685.3	1518.4	1346.3	1184.8	1064.8	958.9	881.2	819.5
42.5°	1553.3	1672.2	1712.7	1630.6	1466.9	1291.5	1130.0	1005.8	901.0	825.5	770.7
45°	1355.6	1513.1	1586.1	1539.2	1381.1	1201.4	1035.3	909.3	814.2	743.2	700.9
47.5°	1170.7	1342.8	1441.1	1424.5	1285.5	1107.6	943.3	822.4	729.8	673.2	635.4
50°	1040.0	1216.9	1335.4	1340.9	1216.9	1040.7	875.9	761.9	676.8	623.9	593.0
52.5°	926.3	1095.2	1224.6	1252.9	1140.2	971.0	815.3	701.9	626.9	578.2	550.7
55°	778.0	920.7	1064.1	1116.4	1025.9	865.1	721.0	621.2	550.8	517.4	493.2
57.5°	646.8	765.8	898.2	955.9	900.2	762.5	627.4	540.8	483.6	454.3	435.9
60°	577.6	671.5	789.4	858.4	810.1	687.5	569.6	487.2	440.3	414.1	396.7
62.5°	513.3	596.4	696.1	759.2	733.0	617.3	511.7	438.9	398.4	374.0	361.3
65°	423.5	489.2	566.2	624.5	607.1	519.3	432.9	370.5	338.4	318.9	308.9
67.5°	348.7	396.2	449.6	500.7	486.7	424.4	355.0	306.5	282.6	265.8	259.7
70°	301.5	337.7	385.3	426.2	414.8	363.9	308.9	267.4	246.6	232.6	226.5
72.5°	256.5	286.3	322.6	356.0	348.3	306.0	260.1	228.7	212.8	199.9	194.9
75°	193.7	216.4	238.5	260.6	258.6	225.8	199.0	174.9	162.2	152.1	150.1
77.5°	143.0	155.7	170.8	183.9	180.3	161.5	140.5	126.6	117.2	110.6	109.5
80°	109.3	116.6	127.3	136.7	132.0	124.0	107.2	97.1	90.5	83.7	81.1
82.5°	79.2	86.5	93.0	98.1	94.5	86.9	76.6	69.8	65.8	61.2	60.2
85°	41.5	45.5	48.3	49.6	48.3	43.5	38.9	36.2	32.8	30.8	30.2
87.5°	23.7	22.3	20.8	20.7	18.3	17.5	14.5	12.1	12.4	12.6	12.4
90°	38.4	31.0	23.5	17.8	13.7	9.6	5.6	1.5	5.6	9.6	13.7
92.5°	44.9	43.1	41.4	39.0	36.1	33.0	30.1	27.1	30.1	33.0	36.1
95°	96.0	95.4	94.7	92.7	89.3	85.9	82.5	79.2	82.5	85.9	89.3
97.5°	161.3	160.0	158.6	156.5	153.6	150.6	147.6	144.6	147.6	150.6	153.6
100°	208.0	207.0	206.0	204.2	201.5	198.7	196.0	193.4	196.0	198.7	201.5
102.5°	257.4	256.2	254.9	253.2	251.0	248.8	246.7	244.5	246.7	248.8	251.0
105°	333.6	333.0	332.2	331.3	330.3	329.3	328.3	327.3	328.3	329.3	330.3
107.5°	417.5	417.5	417.5	416.7	415.3	413.7	412.2	410.7	412.2	413.7	415.3
110°	473.5	473.5	473.5	472.4	470.4	468.4	466.4	464.3	466.4	468.4	470.4



TEST NUMBER: P331580-840

CATALOG NUMBER: S122DIW-S865D1440U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	531.3	531.5	531.8	530.9	528.9	526.8	524.8	522.8	524.8	526.8	528.9
115°	616.4	617.1	617.7	617.1	615.1	613.0	611.0	608.9	611.0	613.0	615.1
117.5°	702.3	704.2	706.1	705.7	703.0	700.2	697.5	694.9	697.5	700.2	703.0
120°	757.5	760.2	763.0	763.0	760.2	757.5	754.8	752.0	754.8	757.5	760.2
122.5°	814.4	816.3	818.1	817.5	814.2	810.9	807.7	804.5	807.7	810.9	814.2
125°	897.3	898.3	899.3	898.3	895.1	892.1	889.1	886.1	889.1	892.1	895.1
127.5°	979.9	981.1	982.3	981.0	977.1	973.2	969.4	965.5	969.4	973.2	977.1
130°	1033.6	1034.2	1034.9	1033.1	1028.6	1024.3	1019.9	1015.4	1019.9	1024.3	1028.6
132.5°	1087.9	1087.8	1087.7	1085.8	1082.3	1078.6	1075.1	1071.5	1075.1	1078.6	1082.3
135°	1164.9	1164.2	1163.5	1161.2	1157.5	1153.9	1150.1	1146.4	1150.1	1153.9	1157.5
137.5°	1241.1	1240.3	1239.4	1237.4	1234.4	1231.3	1228.3	1225.3	1228.3	1231.3	1234.4
140°	1290.7	1289.0	1287.3	1285.0	1281.9	1278.9	1275.8	1272.7	1275.8	1278.9	1281.9
142.5°	1338.1	1336.9	1335.7	1333.6	1330.6	1327.6	1324.5	1321.5	1324.5	1327.6	1330.6
145°	1407.2	1405.2	1403.2	1401.0	1398.6	1396.2	1393.9	1391.5	1393.9	1396.2	1398.6
147.5°	1470.1	1468.7	1467.4	1465.3	1462.5	1459.6	1456.7	1453.9	1456.7	1459.6	1462.5
150°	1509.0	1507.7	1506.3	1504.7	1502.7	1500.7	1498.5	1496.5	1498.5	1500.7	1502.7
152.5°	1547.5	1545.9	1544.3	1542.5	1540.3	1538.3	1536.3	1534.3	1536.3	1538.3	1540.3
155°	1598.0	1597.0	1596.0	1595.0	1594.0	1593.0	1592.0	1590.9	1592.0	1593.0	1594.0
157.5°	1644.0	1643.4	1642.7	1642.0	1641.4	1640.7	1640.0	1639.3	1640.0	1640.7	1641.4
160°	1672.4	1672.1	1671.8	1671.3	1670.6	1669.9	1669.3	1668.6	1669.3	1669.9	1670.6
162.5°	1696.9	1696.5	1696.2	1696.0	1695.8	1695.7	1695.6	1695.4	1695.6	1695.7	1695.8
165°	1729.5	1729.5	1729.5	1729.7	1730.0	1730.3	1730.7	1731.0	1730.7	1730.3	1730.0
167.5°	1756.2	1756.2	1756.3	1756.8	1757.8	1758.8	1759.8	1760.8	1759.8	1758.8	1757.8
170°	1771.3	1771.6	1771.9	1772.6	1773.6	1774.6	1775.6	1776.7	1775.6	1774.6	1773.6
172.5°	1782.2	1782.6	1782.9	1783.6	1784.6	1785.6	1786.7	1787.7	1786.7	1785.6	1784.6
175°	1794.7	1795.4	1796.1	1797.0	1798.0	1799.0	1800.0	1801.0	1800.0	1799.0	1798.0
177.5°	1801.5	1802.0	1802.6	1803.3	1804.1	1804.9	1805.7	1806.5	1805.7	1804.9	1804.1
180°	1804.1	1804.1	1804.1	1804.1	1804.1	1804.1	1804.1	1804.1	1804.1	1804.1	1804.1



TEST NUMBER: P331580-840

CATALOG NUMBER: S122DIW-S865D1440U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1743.5	1743.5	1743.5	1743.5	1743.5	1743.5	1743.5	1743.5	1743.5	1743.5	1743.5
2.5°	1720.5	1717.3	1706.1	1700.2	1690.5	1681.4	1675.5	1678.2	1680.3	1679.2	1677.7
5°	1671.2	1658.5	1639.0	1622.2	1610.2	1588.1	1578.7	1574.1	1570.0	1565.3	1560.6
7.5°	1612.6	1592.5	1564.5	1540.7	1518.1	1490.7	1475.0	1465.6	1456.0	1445.4	1436.0
10°	1570.7	1542.6	1513.1	1479.6	1452.8	1427.9	1405.8	1391.1	1377.8	1364.9	1355.6
12.5°	1526.7	1494.3	1457.8	1412.0	1382.5	1347.1	1343.6	1317.7	1296.8	1288.9	1277.9
15°	1456.8	1411.2	1364.9	1310.7	1287.3	1255.1	1235.0	1214.9	1196.8	1184.1	1180.7
17.5°	1377.4	1318.4	1272.3	1233.3	1194.9	1162.0	1143.5	1127.4	1112.5	1095.5	1093.2
20°	1316.8	1265.8	1215.6	1181.3	1141.9	1108.3	1085.5	1069.4	1056.7	1046.7	1037.9
22.5°	1259.4	1203.7	1157.6	1120.2	1081.3	1054.2	1036.2	1020.7	1010.1	999.0	990.8
25°	1167.3	1123.8	1073.5	1031.3	999.1	981.7	966.9	953.5	946.8	939.5	930.1
27.5°	1086.7	1038.3	991.4	958.7	930.4	914.9	904.5	895.3	889.1	884.7	879.4
30°	1030.0	981.0	944.1	912.0	888.6	873.1	866.5	861.1	853.7	851.0	848.4
32.5°	975.2	931.2	899.7	871.8	849.4	839.4	833.2	828.4	822.6	819.9	814.6
35°	898.0	861.1	830.2	814.9	796.8	788.0	783.4	776.7	771.2	768.6	767.9
37.5°	825.2	793.1	772.8	753.1	745.4	740.0	733.7	729.0	727.4	727.0	726.4
40°	778.0	751.8	733.8	717.7	714.3	706.3	700.9	696.9	696.9	697.6	696.9
42.5°	735.1	711.7	695.7	681.8	677.8	673.1	667.7	667.4	668.5	670.8	668.5
45°	670.0	653.4	642.0	635.2	627.8	623.2	622.5	624.5	625.2	625.9	627.8
47.5°	610.4	599.2	588.9	581.5	578.2	577.4	576.6	580.2	583.4	584.6	587.6
50°	574.9	562.2	553.5	548.8	546.1	544.8	546.1	550.2	552.8	556.1	558.2
52.5°	535.2	526.2	520.3	516.6	515.5	516.3	516.6	521.2	525.5	526.6	527.7
55°	480.5	473.7	472.4	466.4	469.1	468.4	471.7	474.4	478.5	482.5	483.1
57.5°	425.8	420.4	416.8	417.4	418.2	421.1	423.9	428.6	432.9	437.2	437.6
60°	389.3	386.7	384.7	384.7	386.0	390.0	393.3	398.0	400.7	403.4	405.4
62.5°	356.1	353.5	351.4	352.4	356.0	358.4	362.2	364.8	367.5	370.1	371.1
65°	303.6	302.3	304.3	305.6	306.2	309.6	314.3	316.3	318.9	320.3	325.0
67.5°	255.2	255.4	255.2	257.0	260.9	261.8	266.2	270.8	271.4	274.0	277.0
70°	222.5	223.8	225.2	226.5	229.8	231.2	234.5	236.5	239.2	241.3	243.3
72.5°	192.5	192.7	194.1	193.8	196.6	199.5	202.4	204.4	207.0	209.6	211.6
75°	148.0	148.0	149.5	150.1	153.5	156.8	156.1	157.4	160.2	162.8	164.2
77.5°	108.2	106.6	108.2	108.9	109.9	112.7	113.2	115.1	118.2	117.2	118.8
80°	82.4	80.4	82.4	83.1	83.1	86.4	86.4	87.8	89.8	87.8	89.8
82.5°	58.9	57.9	59.4	59.5	60.6	60.7	61.8	62.0	64.0	63.1	64.0
85°	29.5	28.8	29.5	28.8	29.5	30.2	30.2	29.5	29.5	30.8	28.8
87.5°	12.6	13.3	14.2	15.8	16.7	17.7	17.0	16.9	16.7	15.5	15.5
90°	17.8	23.5	31.0	38.4	45.8	53.3	52.6	51.9	51.3	50.6	50.4
92.5°	39.0	41.4	43.1	44.9	46.7	48.4	48.6	48.7	48.8	49.0	49.1
95°	92.7	94.7	95.4	96.0	96.7	97.5	97.5	97.5	97.5	97.5	97.0
97.5°	156.5	158.6	160.0	161.3	162.5	163.8	163.8	163.8	163.8	163.8	163.8
100°	204.2	206.0	207.0	208.0	209.0	210.1	210.1	210.1	210.1	210.1	210.0
102.5°	253.2	254.9	256.2	257.4	258.7	260.0	260.3	260.5	260.8	261.2	261.1
105°	331.3	332.2	333.0	333.6	334.3	335.0	335.6	336.3	337.0	337.6	338.0
107.5°	416.7	417.5	417.5	417.5	417.5	417.5	417.7	418.0	418.3	418.5	417.9
110°	472.4	473.5	473.5	473.5	473.5	473.5	473.5	473.5	473.5	473.5	472.9



TEST NUMBER: P331580-840

CATALOG NUMBER: S122DIW-S865D1440U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	530.9	531.8	531.5	531.3	531.0	530.7	529.9	529.1	528.3	527.5	526.6
115°	617.1	617.7	617.1	616.4	615.7	615.1	614.7	614.4	614.0	613.7	613.0
117.5°	705.7	706.1	704.2	702.3	700.3	698.5	697.7	696.9	696.1	695.3	694.3
120°	763.0	763.0	760.2	757.5	754.8	752.0	752.0	752.0	752.0	752.0	751.5
122.5°	817.5	818.1	816.3	814.4	812.4	810.5	809.7	808.9	808.1	807.3	806.5
125°	898.3	899.3	898.3	897.3	896.3	895.1	894.1	893.1	892.1	891.1	890.5
127.5°	981.0	982.3	981.1	979.9	978.7	977.4	976.1	974.9	973.7	972.5	971.4
130°	1033.1	1034.9	1034.2	1033.6	1032.9	1032.2	1031.6	1030.9	1030.2	1029.5	1028.4
132.5°	1085.8	1087.7	1087.8	1087.9	1088.1	1088.2	1086.7	1085.3	1083.8	1082.3	1081.0
135°	1161.2	1163.5	1164.2	1164.9	1165.5	1166.2	1165.9	1165.5	1165.2	1164.9	1164.2
137.5°	1237.4	1239.4	1240.3	1241.1	1242.0	1242.9	1242.6	1242.3	1242.1	1241.8	1241.0
140°	1285.0	1287.3	1289.0	1290.7	1292.4	1294.0	1294.0	1294.0	1294.0	1294.0	1293.4
142.5°	1333.6	1335.7	1336.9	1338.1	1339.2	1340.4	1340.6	1340.9	1341.2	1341.4	1340.9
145°	1401.0	1403.2	1405.2	1407.2	1409.3	1411.3	1411.6	1412.0	1412.3	1412.6	1412.1
147.5°	1465.3	1467.4	1468.7	1470.1	1471.5	1472.8	1473.6	1474.3	1475.0	1475.8	1475.5
150°	1504.7	1506.3	1507.7	1509.0	1510.5	1511.8	1512.8	1513.8	1514.8	1515.8	1515.8
152.5°	1542.5	1544.3	1545.9	1547.5	1549.1	1550.7	1552.1	1553.3	1554.6	1555.9	1555.9
155°	1595.0	1596.0	1597.0	1598.0	1599.0	1600.0	1601.7	1603.5	1605.2	1606.8	1607.2
157.5°	1642.0	1642.7	1643.4	1644.0	1644.6	1645.2	1647.4	1649.7	1652.0	1654.4	1654.7
160°	1671.3	1671.8	1672.1	1672.4	1672.8	1673.1	1675.2	1677.2	1679.2	1681.2	1681.6
162.5°	1696.0	1696.2	1696.5	1696.9	1697.2	1697.5	1699.8	1702.1	1704.5	1706.7	1707.1
165°	1729.7	1729.5	1729.5	1729.5	1729.5	1729.5	1731.8	1734.2	1736.6	1739.0	1739.3
167.5°	1756.8	1756.3	1756.2	1756.2	1756.1	1756.0	1758.4	1760.7	1763.1	1765.4	1765.7
170°	1772.6	1771.9	1771.6	1771.3	1770.9	1770.6	1772.9	1775.3	1777.7	1780.1	1780.2
172.5°	1783.6	1782.9	1782.6	1782.2	1781.9	1781.5	1783.9	1786.2	1788.7	1791.0	1791.2
175°	1797.0	1796.1	1795.4	1794.7	1794.1	1793.4	1795.8	1798.2	1800.5	1802.9	1803.1
177.5°	1803.3	1802.6	1802.0	1801.5	1801.0	1800.4	1802.0	1803.7	1805.3	1807.0	1807.0
180°	1804.1	1804.1	1804.1	1804.1	1804.1	1804.1	1804.1	1804.1	1804.1	1804.1	1804.1



TEST NUMBER: P331580-840

CATALOG NUMBER: S122DIW-S865D1440U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1743.5	1743.5	1743.5	1743.5	1743.5	1743.5	1743.5	1743.5	1743.5	1743.5	1743.5
2.5°	1672.2	1671.2	1671.2	1666.4	1671.2	1671.2	1672.2	1677.7	1679.2	1680.3	1678.2
5°	1551.3	1549.2	1545.9	1549.2	1545.9	1549.2	1551.3	1560.6	1565.3	1570.0	1574.1
7.5°	1431.6	1423.5	1422.3	1414.4	1422.3	1423.5	1431.6	1436.0	1445.4	1456.0	1465.6
10°	1344.2	1338.9	1338.2	1325.4	1338.2	1338.9	1344.2	1355.6	1364.9	1377.8	1391.1
12.5°	1277.8	1264.9	1267.4	1260.0	1267.4	1264.9	1277.8	1277.9	1288.9	1296.8	1317.7
15°	1162.7	1162.7	1159.9	1148.5	1159.9	1162.7	1162.7	1180.7	1184.1	1196.8	1214.9
17.5°	1079.9	1078.5	1072.2	1075.4	1072.2	1078.5	1079.9	1093.2	1095.5	1112.5	1127.4
20°	1030.6	1026.6	1018.5	1018.5	1018.5	1026.6	1030.6	1037.9	1046.7	1056.7	1069.4
22.5°	984.0	983.7	975.1	977.8	975.1	983.7	984.0	990.8	999.0	1010.1	1020.7
25°	929.4	924.0	920.1	922.0	920.1	924.0	929.4	930.1	939.5	946.8	953.5
27.5°	877.7	874.7	874.4	869.0	874.4	874.7	877.7	879.4	884.7	889.1	895.3
30°	847.7	841.0	842.3	839.0	842.3	841.0	847.7	848.4	851.0	853.7	861.1
32.5°	813.3	810.9	809.6	806.8	809.6	810.9	813.3	814.6	819.9	822.6	828.4
35°	766.6	767.3	763.9	765.3	763.9	767.3	766.6	767.9	768.6	771.2	776.7
37.5°	725.7	727.8	726.3	726.7	726.3	727.8	725.7	726.4	727.0	727.4	729.0
40°	698.9	698.9	698.9	700.9	698.9	698.9	698.9	696.9	697.6	696.9	696.9
42.5°	673.2	672.1	671.1	670.9	671.1	672.1	673.2	668.5	670.8	668.5	667.4
45°	629.2	631.3	631.9	628.5	631.9	631.3	629.2	627.8	625.9	625.2	624.5
47.5°	589.5	589.7	589.5	592.4	589.5	589.7	589.5	587.6	584.6	583.4	580.2
50°	561.6	560.2	561.6	560.2	561.6	560.2	561.6	558.2	556.1	552.8	550.2
52.5°	532.1	532.3	531.5	531.3	531.5	532.3	532.1	527.7	526.6	525.5	521.2
55°	485.8	487.2	486.5	486.5	486.5	487.2	485.8	483.1	482.5	478.5	474.4
57.5°	438.0	439.2	440.1	437.2	440.1	439.2	438.0	437.6	437.2	432.9	428.6
60°	404.8	408.1	407.4	406.1	407.4	408.1	404.8	405.4	403.4	400.7	398.0
62.5°	374.2	375.4	375.3	375.0	375.3	375.4	374.2	371.1	370.1	367.5	364.8
65°	327.0	328.3	326.3	328.3	326.3	328.3	327.0	325.0	320.3	318.9	316.3
67.5°	276.2	276.6	278.1	279.0	278.1	276.6	276.2	277.0	274.0	271.4	270.8
70°	244.6	243.9	245.9	247.9	245.9	243.9	244.6	243.3	241.3	239.2	236.5
72.5°	211.4	212.8	212.2	213.6	212.2	212.8	211.4	211.6	209.6	207.0	204.4
75°	162.8	164.8	164.2	166.2	164.2	164.8	162.8	164.2	162.8	160.2	157.4
77.5°	117.6	118.0	117.6	118.8	117.6	118.0	117.6	118.8	117.2	118.2	115.1
80°	89.8	88.5	87.2	89.8	87.2	88.5	89.8	89.8	87.8	89.8	87.8
82.5°	62.4	63.2	61.9	61.9	61.9	63.2	62.4	64.0	63.1	64.0	62.0
85°	28.8	28.2	26.8	26.8	26.8	28.2	28.8	28.8	30.8	29.5	29.5
87.5°	15.6	15.0	15.1	14.6	15.1	15.0	15.6	15.5	15.5	16.7	16.9
90°	50.8	51.1	51.4	51.8	51.4	51.1	50.8	50.4	50.6	51.3	51.9
92.5°	49.1	49.2	49.3	49.3	49.3	49.2	49.1	49.1	49.0	48.8	48.7
95°	96.4	95.7	95.0	94.4	95.0	95.7	96.4	97.0	97.5	97.5	97.5
97.5°	163.7	163.6	163.6	163.5	163.6	163.6	163.7	163.8	163.8	163.8	163.8
100°	209.5	209.2	208.9	208.5	208.9	209.2	209.5	210.0	210.1	210.1	210.1
102.5°	260.7	260.4	260.0	259.7	260.0	260.4	260.7	261.1	261.2	260.8	260.5
105°	338.0	338.0	338.0	338.0	338.0	338.0	338.0	338.0	337.6	337.0	336.3
107.5°	416.4	414.8	413.2	411.6	413.2	414.8	416.4	417.9	418.5	418.3	418.0
110°	471.9	470.9	469.9	468.9	469.9	470.9	471.9	472.9	473.5	473.5	473.5



TEST NUMBER: P331580-840

CATALOG NUMBER: S122DIW-S865D1440U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	525.9	525.2	524.4	523.7	524.4	525.2	525.9	526.6	527.5	528.3	529.1
115°	612.0	611.0	610.0	608.9	610.0	611.0	612.0	613.0	613.7	614.0	614.4
117.5°	693.3	692.3	691.3	690.2	691.3	692.3	693.3	694.3	695.3	696.1	696.9
120°	750.5	749.5	748.5	747.5	748.5	749.5	750.5	751.5	752.0	752.0	752.0
122.5°	805.8	805.1	804.3	803.5	804.3	805.1	805.8	806.5	807.3	808.1	808.9
125°	890.1	889.8	889.5	889.1	889.5	889.8	890.1	890.5	891.1	892.1	893.1
127.5°	970.3	969.2	968.2	967.0	968.2	969.2	970.3	971.4	972.5	973.7	974.9
130°	1027.1	1025.8	1024.4	1023.1	1024.4	1025.8	1027.1	1028.4	1029.5	1030.2	1030.9
132.5°	1079.9	1078.8	1077.7	1076.6	1077.7	1078.8	1079.9	1081.0	1082.3	1083.8	1085.3
135°	1163.2	1162.2	1161.1	1160.1	1161.1	1162.2	1163.2	1164.2	1164.9	1165.2	1165.5
137.5°	1239.7	1238.3	1237.0	1235.6	1237.0	1238.3	1239.7	1241.0	1241.8	1242.1	1242.3
140°	1292.0	1290.7	1289.3	1288.0	1289.3	1290.7	1292.0	1293.4	1294.0	1294.0	1294.0
142.5°	1339.6	1338.2	1336.9	1335.4	1336.9	1338.2	1339.6	1340.9	1341.4	1341.2	1340.9
145°	1410.8	1409.5	1408.1	1406.7	1408.1	1409.5	1410.8	1412.1	1412.6	1412.3	1412.0
147.5°	1474.2	1472.9	1471.7	1470.4	1471.7	1472.9	1474.2	1475.5	1475.8	1475.0	1474.3
150°	1514.8	1513.8	1512.8	1511.8	1512.8	1513.8	1514.8	1515.8	1515.8	1514.8	1513.8
152.5°	1554.6	1553.3	1552.1	1550.7	1552.1	1553.3	1554.6	1555.9	1555.9	1554.6	1553.3
155°	1606.2	1605.2	1604.2	1603.2	1604.2	1605.2	1606.2	1607.2	1606.8	1605.2	1603.5
157.5°	1653.0	1651.4	1649.8	1648.2	1649.8	1651.4	1653.0	1654.7	1654.4	1652.0	1649.7
160°	1680.2	1678.9	1677.6	1676.2	1677.6	1678.9	1680.2	1681.6	1681.2	1679.2	1677.2
162.5°	1705.5	1703.8	1702.2	1700.5	1702.2	1703.8	1705.5	1707.1	1706.7	1704.5	1702.1
165°	1737.6	1736.0	1734.2	1732.5	1734.2	1736.0	1737.6	1739.3	1739.0	1736.6	1734.2
167.5°	1764.0	1762.2	1760.5	1758.7	1760.5	1762.2	1764.0	1765.7	1765.4	1763.1	1760.7
170°	1778.2	1776.2	1774.1	1772.1	1774.1	1776.2	1778.2	1780.2	1780.1	1777.7	1775.3
172.5°	1789.2	1787.2	1785.1	1783.1	1785.1	1787.2	1789.2	1791.2	1791.0	1788.7	1786.2
175°	1801.0	1799.0	1797.0	1794.9	1797.0	1799.0	1801.0	1803.1	1802.9	1800.5	1798.2
177.5°	1805.3	1803.7	1802.0	1800.4	1802.0	1803.7	1805.3	1807.0	1807.0	1805.3	1803.7
180°	1804.1	1804.1	1804.1	1804.1	1804.1	1804.1	1804.1	1804.1	1804.1	1804.1	1804.1



TEST NUMBER: P331580-840

CATALOG NUMBER: S122DIW-S865D1440U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1743.5	1743.5	1743.5	1743.5	1743.5	1743.5	1743.5	1743.5	1743.5	1743.5	1743.5
2.5°	1675.5	1681.4	1690.5	1700.2	1706.1	1717.3	1720.5	1725.9	1730.7	1742.0	1753.7
5°	1578.7	1588.1	1610.2	1622.2	1639.0	1658.5	1671.2	1684.7	1699.4	1724.8	1748.3
7.5°	1475.0	1490.7	1518.1	1540.7	1564.5	1592.5	1612.6	1639.0	1661.0	1697.0	1731.2
10°	1405.8	1427.9	1452.8	1479.6	1513.1	1542.6	1570.7	1604.2	1631.0	1673.9	1714.1
12.5°	1343.6	1347.1	1382.5	1412.0	1457.8	1494.3	1526.7	1569.9	1596.2	1647.1	1689.4
15°	1235.0	1255.1	1287.3	1310.7	1364.9	1411.2	1456.8	1501.7	1531.9	1594.8	1650.4
17.5°	1143.5	1162.0	1194.9	1233.3	1272.3	1318.4	1377.4	1424.6	1465.6	1537.6	1603.4
20°	1085.5	1108.3	1141.9	1181.3	1215.6	1265.8	1316.8	1371.0	1415.2	1496.3	1573.4
22.5°	1036.2	1054.2	1081.3	1120.2	1157.6	1203.7	1259.4	1318.5	1364.8	1452.4	1530.5
25°	966.9	981.7	999.1	1031.3	1073.5	1123.8	1167.3	1232.3	1300.0	1381.7	1476.2
27.5°	904.5	914.9	930.4	958.7	991.4	1038.3	1086.7	1148.4	1216.5	1305.3	1404.9
30°	866.5	873.1	888.6	912.0	944.1	981.0	1030.0	1088.9	1158.6	1248.4	1347.6
32.5°	833.2	839.4	849.4	871.8	899.7	931.2	975.2	1034.2	1100.7	1188.9	1298.8
35°	783.4	788.0	796.8	814.9	830.2	861.1	898.0	951.5	1013.8	1098.3	1212.2
37.5°	733.7	740.0	745.4	753.1	772.8	793.1	825.2	870.4	931.6	1016.8	1125.4
40°	700.9	706.3	714.3	717.7	733.8	751.8	778.0	819.5	881.2	958.9	1064.8
42.5°	667.7	673.1	677.8	681.8	695.7	711.7	735.1	770.7	825.5	901.0	1005.8
45°	622.5	623.2	627.8	635.2	642.0	653.4	670.0	700.9	743.2	814.2	909.3
47.5°	576.6	577.4	578.2	581.5	588.9	599.2	610.4	635.4	673.2	729.8	822.4
50°	546.1	544.8	546.1	548.8	553.5	562.2	574.9	593.0	623.9	676.8	761.9
52.5°	516.6	516.3	515.5	516.6	520.3	526.2	535.2	550.7	578.2	626.9	701.9
55°	471.7	468.4	469.1	466.4	472.4	473.7	480.5	493.2	517.4	550.8	621.2
57.5°	423.9	421.1	418.2	417.4	416.8	420.4	425.8	435.9	454.3	483.6	540.8
60°	393.3	390.0	386.0	384.7	384.7	386.7	389.3	396.7	414.1	440.3	487.2
62.5°	362.2	358.4	356.0	352.4	351.4	353.5	356.1	361.3	374.0	398.4	438.9
65°	314.3	309.6	306.2	305.6	304.3	302.3	303.6	308.9	318.9	338.4	370.5
67.5°	266.2	261.8	260.9	257.0	255.2	255.4	255.2	259.7	265.8	282.6	306.5
70°	234.5	231.2	229.8	226.5	225.2	223.8	222.5	226.5	232.6	246.6	267.4
72.5°	202.4	199.5	196.6	193.8	194.1	192.7	192.5	194.9	199.9	212.8	228.7
75°	156.1	156.8	153.5	150.1	149.5	148.0	148.0	150.1	152.1	162.2	174.9
77.5°	113.2	112.7	109.9	108.9	108.2	106.6	108.2	109.5	110.6	117.2	126.6
80°	86.4	86.4	83.1	83.1	82.4	80.4	82.4	81.1	83.7	90.5	97.1
82.5°	61.8	60.7	60.6	59.5	59.4	57.9	58.9	60.2	61.2	65.8	69.8
85°	30.2	30.2	29.5	28.8	29.5	28.8	29.5	30.2	30.8	32.8	36.2
87.5°	17.0	17.7	16.7	15.8	14.2	13.3	12.6	12.4	12.6	12.4	12.1
90°	52.6	53.3	45.8	38.4	31.0	23.5	17.8	13.7	9.6	5.6	1.5
92.5°	48.6	48.4	46.7	44.9	43.1	41.4	39.0	36.1	33.0	30.1	27.1
95°	97.5	97.5	96.7	96.0	95.4	94.7	92.7	89.3	85.9	82.5	79.2
97.5°	163.8	163.8	162.5	161.3	160.0	158.6	156.5	153.6	150.6	147.6	144.6
100°	210.1	210.1	209.0	208.0	207.0	206.0	204.2	201.5	198.7	196.0	193.4
102.5°	260.3	260.0	258.7	257.4	256.2	254.9	253.2	251.0	248.8	246.7	244.5
105°	335.6	335.0	334.3	333.6	333.0	332.2	331.3	330.3	329.3	328.3	327.3
107.5°	417.7	417.5	417.5	417.5	417.5	417.5	416.7	415.3	413.7	412.2	410.7
110°	473.5	473.5	473.5	473.5	473.5	473.5	472.4	470.4	468.4	466.4	464.3



TEST NUMBER: P331580-840

CATALOG NUMBER: S122DIW-S865D1440U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	529.9	530.7	531.0	531.3	531.5	531.8	530.9	528.9	526.8	524.8	522.8
115°	614.7	615.1	615.7	616.4	617.1	617.7	617.1	615.1	613.0	611.0	608.9
117.5°	697.7	698.5	700.3	702.3	704.2	706.1	705.7	703.0	700.2	697.5	694.9
120°	752.0	752.0	754.8	757.5	760.2	763.0	763.0	760.2	757.5	754.8	752.0
122.5°	809.7	810.5	812.4	814.4	816.3	818.1	817.5	814.2	810.9	807.7	804.5
125°	894.1	895.1	896.3	897.3	898.3	899.3	898.3	895.1	892.1	889.1	886.1
127.5°	976.1	977.4	978.7	979.9	981.1	982.3	981.0	977.1	973.2	969.4	965.5
130°	1031.6	1032.2	1032.9	1033.6	1034.2	1034.9	1033.1	1028.6	1024.3	1019.9	1015.4
132.5°	1086.7	1088.2	1088.1	1087.9	1087.8	1087.7	1085.8	1082.3	1078.6	1075.1	1071.5
135°	1165.9	1166.2	1165.5	1164.9	1164.2	1163.5	1161.2	1157.5	1153.9	1150.1	1146.4
137.5°	1242.6	1242.9	1242.0	1241.1	1240.3	1239.4	1237.4	1234.4	1231.3	1228.3	1225.3
140°	1294.0	1294.0	1292.4	1290.7	1289.0	1287.3	1285.0	1281.9	1278.9	1275.8	1272.7
142.5°	1340.6	1340.4	1339.2	1338.1	1336.9	1335.7	1333.6	1330.6	1327.6	1324.5	1321.5
145°	1411.6	1411.3	1409.3	1407.2	1405.2	1403.2	1401.0	1398.6	1396.2	1393.9	1391.5
147.5°	1473.6	1472.8	1471.5	1470.1	1468.7	1467.4	1465.3	1462.5	1459.6	1456.7	1453.9
150°	1512.8	1511.8	1510.5	1509.0	1507.7	1506.3	1504.7	1502.7	1500.7	1498.5	1496.5
152.5°	1552.1	1550.7	1549.1	1547.5	1545.9	1544.3	1542.5	1540.3	1538.3	1536.3	1534.3
155°	1601.7	1600.0	1599.0	1598.0	1597.0	1596.0	1595.0	1594.0	1593.0	1592.0	1590.9
157.5°	1647.4	1645.2	1644.6	1644.0	1643.4	1642.7	1642.0	1641.4	1640.7	1640.0	1639.3
160°	1675.2	1673.1	1672.8	1672.4	1672.1	1671.8	1671.3	1670.6	1669.9	1669.3	1668.6
162.5°	1699.8	1697.5	1697.2	1696.9	1696.5	1696.2	1696.0	1695.8	1695.7	1695.6	1695.4
165°	1731.8	1729.5	1729.5	1729.5	1729.5	1729.5	1729.7	1730.0	1730.3	1730.7	1731.0
167.5°	1758.4	1756.0	1756.1	1756.2	1756.2	1756.3	1756.8	1757.8	1758.8	1759.8	1760.8
170°	1772.9	1770.6	1770.9	1771.3	1771.6	1771.9	1772.6	1773.6	1774.6	1775.6	1776.7
172.5°	1783.9	1781.5	1781.9	1782.2	1782.6	1782.9	1783.6	1784.6	1785.6	1786.7	1787.7
175°	1795.8	1793.4	1794.1	1794.7	1795.4	1796.1	1797.0	1798.0	1799.0	1800.0	1801.0
177.5°	1802.0	1800.4	1801.0	1801.5	1802.0	1802.6	1803.3	1804.1	1804.9	1805.7	1806.5
180°	1804.1	1804.1	1804.1	1804.1	1804.1	1804.1	1804.1	1804.1	1804.1	1804.1	1804.1



TEST NUMBER: P331580-840

CATALOG NUMBER: S122DIW-S865D1440U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1743.5	1743.5	1743.5	1743.5	1743.5	1743.5	1743.5	1743.5	1743.5	1743.5	1743.5
2.5°	1752.7	1755.3	1763.9	1772.5	1782.2	1784.8	1789.2	1785.4	1784.3	1794.5	1802.0
5°	1757.7	1769.7	1793.2	1814.6	1832.7	1845.4	1858.9	1864.2	1874.2	1888.3	1905.7
7.5°	1752.0	1775.4	1812.3	1843.6	1877.6	1902.1	1921.3	1937.6	1957.5	1984.2	2013.3
10°	1745.6	1777.1	1822.0	1860.2	1901.7	1933.2	1959.3	1984.8	2014.3	2051.1	2089.3
12.5°	1733.8	1771.2	1827.4	1872.5	1925.8	1956.8	1992.1	2047.0	2078.6	2130.0	2183.7
15°	1710.1	1751.6	1830.0	1885.6	1945.9	2004.9	2069.9	2122.2	2174.4	2204.6	2280.4
17.5°	1674.9	1735.9	1822.6	1887.5	1964.2	2057.1	2130.1	2189.3	2249.7	2298.6	2336.5
20°	1646.4	1712.7	1811.9	1889.7	1980.7	2080.6	2164.4	2224.7	2276.9	2317.8	2341.3
22.5°	1610.5	1693.9	1790.5	1881.6	1997.9	2096.7	2184.7	2232.2	2275.9	2295.8	2304.8
25°	1554.0	1654.5	1763.7	1874.9	2006.3	2110.8	2191.2	2220.0	2232.7	2213.3	2181.1
27.5°	1493.0	1605.0	1732.7	1862.3	2001.1	2101.6	2159.3	2154.7	2133.1	2070.3	2020.0
30°	1447.4	1570.7	1708.1	1849.5	1988.8	2086.7	2120.2	2086.7	2037.7	1967.4	1895.7
32.5°	1399.7	1527.3	1681.8	1831.2	1966.3	2052.3	2059.6	2002.0	1926.2	1846.2	1756.9
35°	1327.5	1465.5	1632.3	1790.5	1918.4	1972.8	1940.6	1838.8	1749.0	1639.7	1517.7
37.5°	1245.9	1398.3	1565.6	1730.8	1846.7	1861.0	1781.1	1673.9	1547.2	1418.9	1275.4
40°	1184.8	1346.3	1518.4	1685.3	1787.8	1773.0	1671.2	1553.3	1402.5	1245.7	1112.4
42.5°	1130.0	1291.5	1466.9	1630.6	1712.7	1672.2	1553.3	1408.6	1246.5	1098.8	976.7
45°	1035.3	1201.4	1381.1	1539.2	1586.1	1513.1	1355.6	1194.8	1035.3	912.0	815.5
47.5°	943.3	1107.6	1285.5	1424.5	1441.1	1342.8	1170.7	1005.3	868.2	767.8	699.7
50°	875.9	1040.7	1216.9	1340.9	1335.4	1216.9	1040.0	882.5	767.9	686.8	641.3
52.5°	815.3	971.0	1140.2	1252.9	1224.6	1095.2	926.3	786.6	692.4	628.9	587.6
55°	721.0	865.1	1025.9	1116.4	1064.1	920.7	778.0	665.4	595.7	548.2	515.9
57.5°	627.4	762.5	900.2	955.9	898.2	765.8	646.8	565.1	512.7	477.5	456.6
60°	569.6	687.5	810.1	858.4	789.4	671.5	577.6	504.6	462.3	433.5	414.8
62.5°	511.7	617.3	733.0	759.2	696.1	596.4	513.3	452.6	417.9	392.2	374.6
65°	432.9	519.3	607.1	624.5	566.2	489.2	423.5	384.0	353.1	334.4	320.3
67.5°	355.0	424.4	486.7	500.7	449.6	396.2	348.7	314.3	293.4	277.8	265.9
70°	308.9	363.9	414.8	426.2	385.3	337.7	301.5	274.1	255.3	241.9	230.6
72.5°	260.1	306.0	348.3	356.0	322.6	286.3	256.5	234.9	218.3	209.7	198.8
75°	199.0	225.8	258.6	260.6	238.5	216.4	193.7	179.6	170.9	160.2	154.8
77.5°	140.5	161.5	180.3	183.9	170.8	155.7	143.0	131.9	124.5	119.6	114.6
80°	107.2	124.0	132.0	136.7	127.3	116.6	109.3	101.9	97.1	93.8	90.5
82.5°	76.6	86.9	94.5	98.1	93.0	86.5	79.2	75.0	71.4	68.6	67.5
85°	38.9	43.5	48.3	49.6	48.3	45.5	41.5	41.5	39.5	38.9	38.9
87.5°	14.5	17.5	18.3	20.7	20.8	22.3	23.7	24.7	25.7	25.0	24.3
90°	5.6	9.6	13.7	17.8	23.5	31.0	38.4	45.8	53.3	52.6	51.9
92.5°	30.1	33.0	36.1	39.0	41.4	43.1	44.9	46.7	48.4	48.6	48.7
95°	82.5	85.9	89.3	92.7	94.7	95.4	96.0	96.7	97.5	97.5	97.5
97.5°	147.6	150.6	153.6	156.5	158.6	160.0	161.3	162.5	163.8	163.8	163.8
100°	196.0	198.7	201.5	204.2	206.0	207.0	208.0	209.0	210.1	210.1	210.1
102.5°	246.7	248.8	251.0	253.2	254.9	256.2	257.4	258.7	260.0	260.3	260.5
105°	328.3	329.3	330.3	331.3	332.2	333.0	333.6	334.3	335.0	335.6	336.3
107.5°	412.2	413.7	415.3	416.7	417.5	417.5	417.5	417.5	417.5	417.7	418.0
110°	466.4	468.4	470.4	472.4	473.5	473.5	473.5	473.5	473.5	473.5	473.5



TEST NUMBER: P331580-840

CATALOG NUMBER: S122DIW-S865D1440U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	524.8	526.8	528.9	530.9	531.8	531.5	531.3	531.0	530.7	529.9	529.1
115°	611.0	613.0	615.1	617.1	617.7	617.1	616.4	615.7	615.1	614.7	614.4
117.5°	697.5	700.2	703.0	705.7	706.1	704.2	702.3	700.3	698.5	697.7	696.9
120°	754.8	757.5	760.2	763.0	763.0	760.2	757.5	754.8	752.0	752.0	752.0
122.5°	807.7	810.9	814.2	817.5	818.1	816.3	814.4	812.4	810.5	809.7	808.9
125°	889.1	892.1	895.1	898.3	899.3	898.3	897.3	896.3	895.1	894.1	893.1
127.5°	969.4	973.2	977.1	981.0	982.3	981.1	979.9	978.7	977.4	976.1	974.9
130°	1019.9	1024.3	1028.6	1033.1	1034.9	1034.2	1033.6	1032.9	1032.2	1031.6	1030.9
132.5°	1075.1	1078.6	1082.3	1085.8	1087.7	1087.8	1087.9	1088.1	1088.2	1086.7	1085.3
135°	1150.1	1153.9	1157.5	1161.2	1163.5	1164.2	1164.9	1165.5	1166.2	1165.9	1165.5
137.5°	1228.3	1231.3	1234.4	1237.4	1239.4	1240.3	1241.1	1242.0	1242.9	1242.6	1242.3
140°	1275.8	1278.9	1281.9	1285.0	1287.3	1289.0	1290.7	1292.4	1294.0	1294.0	1294.0
142.5°	1324.5	1327.6	1330.6	1333.6	1335.7	1336.9	1338.1	1339.2	1340.4	1340.6	1340.9
145°	1393.9	1396.2	1398.6	1401.0	1403.2	1405.2	1407.2	1409.3	1411.3	1411.6	1412.0
147.5°	1456.7	1459.6	1462.5	1465.3	1467.4	1468.7	1470.1	1471.5	1472.8	1473.6	1474.3
150°	1498.5	1500.7	1502.7	1504.7	1506.3	1507.7	1509.0	1510.5	1511.8	1512.8	1513.8
152.5°	1536.3	1538.3	1540.3	1542.5	1544.3	1545.9	1547.5	1549.1	1550.7	1552.1	1553.3
155°	1592.0	1593.0	1594.0	1595.0	1596.0	1597.0	1598.0	1599.0	1600.0	1601.7	1603.5
157.5°	1640.0	1640.7	1641.4	1642.0	1642.7	1643.4	1644.0	1644.6	1645.2	1647.4	1649.7
160°	1669.3	1669.9	1670.6	1671.3	1671.8	1672.1	1672.4	1672.8	1673.1	1675.2	1677.2
162.5°	1695.6	1695.7	1695.8	1696.0	1696.2	1696.5	1696.9	1697.2	1697.5	1699.8	1702.1
165°	1730.7	1730.3	1730.0	1729.7	1729.5	1729.5	1729.5	1729.5	1729.5	1731.8	1734.2
167.5°	1759.8	1758.8	1757.8	1756.8	1756.3	1756.2	1756.2	1756.1	1756.0	1758.4	1760.7
170°	1775.6	1774.6	1773.6	1772.6	1771.9	1771.6	1771.3	1770.9	1770.6	1772.9	1775.3
172.5°	1786.7	1785.6	1784.6	1783.6	1782.9	1782.6	1782.2	1781.9	1781.5	1783.9	1786.2
175°	1800.0	1799.0	1798.0	1797.0	1796.1	1795.4	1794.7	1794.1	1793.4	1795.8	1798.2
177.5°	1805.7	1804.9	1804.1	1803.3	1802.6	1802.0	1801.5	1801.0	1800.4	1802.0	1803.7
180°	1804.1	1804.1	1804.1	1804.1	1804.1	1804.1	1804.1	1804.1	1804.1	1804.1	1804.1



TEST NUMBER: P331580-840

CATALOG NUMBER: S122DIW-S865D1440U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1743.5	1743.5	1743.5	1743.5	1743.5	1743.5	1743.5
2.5°	1808.5	1815.9	1815.9	1817.1	1825.6	1824.5	1824.0
5°	1924.5	1935.9	1937.2	1949.3	1957.3	1954.7	1947.3
7.5°	2034.0	2055.2	2071.2	2080.2	2090.8	2097.4	2094.5
10°	2120.8	2151.6	2170.4	2183.1	2198.6	2210.0	2205.9
12.5°	2199.7	2236.3	2262.1	2283.9	2285.9	2300.6	2290.7
15°	2322.6	2361.4	2365.4	2381.5	2394.3	2392.9	2393.6
17.5°	2363.2	2375.6	2378.1	2378.5	2378.7	2374.0	2363.8
20°	2348.6	2344.0	2332.6	2323.9	2308.5	2306.4	2293.1
22.5°	2280.1	2265.2	2236.6	2217.8	2193.7	2187.5	2183.7
25°	2145.0	2112.1	2066.6	2023.0	2010.9	1987.5	1994.2
27.5°	1959.6	1908.4	1859.1	1823.7	1791.7	1756.6	1766.7
30°	1829.4	1771.7	1702.0	1648.4	1614.3	1580.7	1574.7
32.5°	1673.9	1589.4	1511.8	1464.5	1412.2	1391.0	1367.8
35°	1405.8	1323.4	1246.4	1180.0	1141.9	1112.4	1085.5
37.5°	1164.8	1069.9	1007.6	953.9	926.3	909.5	913.7
40°	1015.2	932.1	886.6	845.7	820.2	808.1	810.8
42.5°	894.0	831.8	794.4	766.3	748.3	741.6	740.0
45°	756.5	721.6	690.8	674.8	666.1	658.7	654.0
47.5°	662.7	634.3	616.9	607.3	599.8	592.2	592.1
50°	606.4	587.6	575.6	565.5	559.6	554.2	558.9
52.5°	563.5	546.4	534.3	525.3	523.1	518.3	518.2
55°	499.9	486.5	477.8	469.7	465.7	463.0	459.7
57.5°	442.0	429.3	421.2	416.2	408.5	405.8	404.8
60°	400.7	390.6	382.6	375.9	372.5	367.2	367.2
62.5°	362.6	352.6	345.1	340.0	334.5	332.3	333.0
65°	307.6	299.5	292.2	286.8	285.5	281.4	282.8
67.5°	256.9	251.6	243.8	240.9	238.3	236.1	234.5
70°	223.2	217.8	213.8	209.7	207.7	207.7	207.7
72.5°	194.7	188.3	185.9	180.8	182.0	179.9	177.7
75°	150.8	146.7	144.7	142.7	139.4	139.4	139.4
77.5°	111.0	109.8	107.3	105.2	104.4	103.7	104.0
80°	85.7	85.1	83.7	83.7	82.4	81.8	80.4
82.5°	65.9	64.2	63.4	62.8	62.6	62.4	62.2
85°	37.6	36.2	36.2	36.9	35.5	35.5	36.2
87.5°	24.7	24.5	24.0	24.1	24.7	24.2	24.3
90°	51.3	50.6	50.4	50.8	51.1	51.4	51.8
92.5°	48.8	49.0	49.1	49.1	49.2	49.3	49.3
95°	97.5	97.5	97.0	96.4	95.7	95.0	94.4
97.5°	163.8	163.8	163.8	163.7	163.6	163.6	163.5
100°	210.1	210.1	210.0	209.5	209.2	208.9	208.5
102.5°	260.8	261.2	261.1	260.7	260.4	260.0	259.7
105°	337.0	337.6	338.0	338.0	338.0	338.0	338.0
107.5°	418.3	418.5	417.9	416.4	414.8	413.2	411.6
110°	473.5	473.5	472.9	471.9	470.9	469.9	468.9



TEST NUMBER: P331580-840

CATALOG NUMBER: S122DIW-S865D1440U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	528.3	527.5	526.6	525.9	525.2	524.4	523.7
115°	614.0	613.7	613.0	612.0	611.0	610.0	608.9
117.5°	696.1	695.3	694.3	693.3	692.3	691.3	690.2
120°	752.0	752.0	751.5	750.5	749.5	748.5	747.5
122.5°	808.1	807.3	806.5	805.8	805.1	804.3	803.5
125°	892.1	891.1	890.5	890.1	889.8	889.5	889.1
127.5°	973.7	972.5	971.4	970.3	969.2	968.2	967.0
130°	1030.2	1029.5	1028.4	1027.1	1025.8	1024.4	1023.1
132.5°	1083.8	1082.3	1081.0	1079.9	1078.8	1077.7	1076.6
135°	1165.2	1164.9	1164.2	1163.2	1162.2	1161.1	1160.1
137.5°	1242.1	1241.8	1241.0	1239.7	1238.3	1237.0	1235.6
140°	1294.0	1294.0	1293.4	1292.0	1290.7	1289.3	1288.0
142.5°	1341.2	1341.4	1340.9	1339.6	1338.2	1336.9	1335.4
145°	1412.3	1412.6	1412.1	1410.8	1409.5	1408.1	1406.7
147.5°	1475.0	1475.8	1475.5	1474.2	1472.9	1471.7	1470.4
150°	1514.8	1515.8	1515.8	1514.8	1513.8	1512.8	1511.8
152.5°	1554.6	1555.9	1555.9	1554.6	1553.3	1552.1	1550.7
155°	1605.2	1606.8	1607.2	1606.2	1605.2	1604.2	1603.2
157.5°	1652.0	1654.4	1654.7	1653.0	1651.4	1649.8	1648.2
160°	1679.2	1681.2	1681.6	1680.2	1678.9	1677.6	1676.2
162.5°	1704.5	1706.7	1707.1	1705.5	1703.8	1702.2	1700.5
165°	1736.6	1739.0	1739.3	1737.6	1736.0	1734.2	1732.5
167.5°	1763.1	1765.4	1765.7	1764.0	1762.2	1760.5	1758.7
170°	1777.7	1780.1	1780.2	1778.2	1776.2	1774.1	1772.1
172.5°	1788.7	1791.0	1791.2	1789.2	1787.2	1785.1	1783.1
175°	1800.5	1802.9	1803.1	1801.0	1799.0	1797.0	1794.9
177.5°	1805.3	1807.0	1807.0	1805.3	1803.7	1802.0	1800.4
180°	1804.1	1804.1	1804.1	1804.1	1804.1	1804.1	1804.1

(END OF REPORT)