

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332489-927

Luminaire Tested: **S123RDIW-S1165D1535U927-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332489-927
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-9,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123RDIW-S1165D1535U927-4F0-1E-UDD-F1
Description: DEFINE 3 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 1165 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 1535 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7686.4 lumens
Efficiency: N/A
Efficacy: 92.7 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.06 / 1.22
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 82.9
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332489-927

CATALOG NUMBER: S123RDIW-S1165D1535U927-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P332489-927

CATALOG NUMBER: S123RDIW-S1165D1535U927-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	106	106	106	106	97	97	97	97	81	81	81	66	66	66	52	52	52	45
1	97	93	89	86	89	85	82	79	71	69	67	58	57	55	46	45	44	39
2	89	81	75	70	81	75	70	65	63	59	56	51	49	46	41	39	38	33
3	81	72	65	59	74	66	60	55	55	51	47	46	42	40	37	34	32	28
4	74	64	56	50	68	59	52	47	49	44	40	41	37	34	33	30	28	24
5	68	57	49	43	62	52	46	40	44	39	35	37	33	30	30	27	25	21
6	63	51	43	37	57	47	40	35	40	35	31	33	29	26	27	24	22	19
7	58	46	38	33	53	43	36	31	36	31	27	30	26	23	25	22	19	17
8	54	42	34	29	49	39	32	27	33	28	24	28	24	21	23	20	18	15
9	50	38	31	26	46	36	29	24	30	25	22	26	22	19	21	18	16	14
10	47	35	28	23	43	33	26	22	28	23	19	24	20	17	20	17	14	12

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	16527	16527	16527
5°	16590	16361	16455
10°	16497	16156	16101
15°	16319	15778	15611
20°	16076	15306	14948
25°	15824	14775	14301
30°	15493	14162	13387
35°	15152	13548	12550
40°	14838	12826	11514
45°	14425	12113	10577
50°	13971	11302	9530
55°	13508	10376	8552
60°	13082	9384	7481
65°	12528	8308	6406
70°	11833	6977	5174
75°	10821	5490	4870
80°	9651	4860	4475
85°	8151	4310	4001



TEST NUMBER: P332489-927

CATALOG NUMBER: S123RDIW-S1165D1535U927-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	144.2	1.9
10°-20°	401.2	5.2
20°-30°	577.6	7.5
30°-40°	650.7	8.5
40°-50°	622.5	8.1
50°-60°	509.7	6.6
60°-70°	343.9	4.5
70°-80°	173.0	2.3
80°-90°	50.3	0.7
90°-100°	99.1	1.3
100°-110°	296.5	3.9
110°-120°	504.3	6.6
120°-130°	663.4	8.6
130°-140°	745.6	9.7
140°-150°	732.9	9.5
150°-160°	617.0	8.0
160°-170°	410.7	5.3
170°-180°	143.8	1.9
0°-30°	1123.0	14.6
0°-40°	1773.6	23.1
0°-60°	2905.8	37.8
0°-90°	3473.1	45.2
90°-120°	899.9	11.7
90°-150°	3041.8	39.6
90°-180°	4213.0	54.8
0°-180°	7686.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1535	1535	1535	1535	1535	
5°	1535	1529	1514	1525	1523	146
15°	1464	1450	1416	1410	1401	412
25°	1332	1300	1244	1219	1204	613
35°	1153	1106	1031	979	955	721
45°	948	889	796	727	695	731
55°	720	656	553	483	456	645
65°	492	422	326	268	252	487
75°	260	200	132	120	117	278
85°	66	40	35	32	32	74
90°	1	13	29	33	36	8
95°	70	79	88	93	93	79
105°	269	272	282	282	284	288
115°	508	511	509	510	509	502
125°	743	746	744	739	735	662
135°	964	971	970	965	963	743
145°	1170	1172	1175	1174	1170	730
155°	1339	1339	1340	1344	1337	616
165°	1459	1455	1455	1461	1454	411
175°	1517	1513	1512	1519	1511	144
180°	1521	1521	1521	1521	1521	



TEST NUMBER: P332489-927

CATALOG NUMBER: S123RDIW-S1165D1535U927-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1535.4	1535.4	1535.4	1535.4	1535.4	1535.4	1535.4	1535.4	1535.4	1535.4	1535.4
2.5°	1540.4	1539.4	1538.6	1537.7	1536.8	1535.0	1532.4	1529.7	1527.1	1524.4	1526.9
5°	1535.4	1534.0	1532.6	1531.2	1529.9	1527.5	1524.2	1520.8	1517.5	1514.2	1516.7
7.5°	1521.1	1519.7	1518.2	1516.7	1515.2	1512.3	1508.0	1503.6	1499.4	1495.0	1496.4
10°	1509.3	1507.3	1505.4	1503.4	1501.5	1498.0	1493.0	1488.0	1483.0	1478.1	1478.4
12.5°	1492.3	1490.2	1488.0	1485.8	1483.7	1479.6	1473.5	1467.4	1461.3	1455.2	1455.0
15°	1464.4	1461.3	1458.3	1455.2	1452.2	1446.8	1439.1	1431.3	1423.6	1415.9	1414.4
17.5°	1429.3	1425.8	1422.2	1418.6	1415.2	1408.4	1398.6	1388.7	1378.9	1369.0	1366.1
20°	1403.4	1399.0	1394.6	1390.1	1385.7	1378.2	1367.7	1357.2	1346.6	1336.2	1332.5
22.5°	1374.5	1369.4	1364.3	1359.2	1354.2	1346.0	1334.8	1323.7	1312.5	1301.2	1296.8
25°	1332.4	1325.5	1318.6	1311.6	1304.7	1294.9	1282.1	1269.5	1256.7	1244.0	1238.2
27.5°	1281.4	1273.7	1266.1	1258.5	1250.8	1239.9	1225.7	1211.6	1197.4	1183.2	1175.1
30°	1246.5	1238.2	1229.9	1221.5	1213.3	1201.3	1185.9	1170.4	1154.9	1139.4	1130.0
32.5°	1211.6	1202.2	1192.8	1183.4	1174.0	1161.1	1144.7	1128.3	1111.9	1095.6	1085.3
35°	1153.1	1143.1	1133.1	1123.2	1113.3	1099.7	1082.5	1065.4	1048.2	1031.0	1019.1
37.5°	1093.8	1082.8	1071.7	1060.6	1049.6	1034.8	1016.5	998.2	979.9	961.6	948.1
40°	1056.0	1043.8	1031.6	1019.5	1007.3	991.3	971.7	952.0	932.4	912.8	898.3
42.5°	1013.1	1000.9	988.8	976.6	964.4	948.2	927.9	907.5	887.2	867.0	851.2
45°	947.6	935.2	922.7	910.3	897.8	880.9	859.6	838.3	817.0	795.7	779.9
47.5°	882.1	868.5	854.8	841.1	827.4	809.9	788.6	767.3	746.0	724.8	707.6
50°	834.3	821.3	808.3	795.3	782.3	764.6	742.2	719.8	697.4	674.9	657.7
52.5°	791.5	777.4	763.3	749.2	735.0	716.8	694.7	672.5	650.3	628.1	610.3
55°	719.8	706.2	692.6	679.1	665.5	647.0	623.4	599.9	576.4	552.9	536.9
57.5°	653.5	638.7	623.9	609.2	594.4	575.2	551.6	527.9	504.3	480.7	465.5
60°	607.7	592.5	577.3	562.1	546.8	527.7	504.7	481.8	458.8	435.9	420.9
62.5°	561.8	546.6	531.4	516.2	501.0	481.9	458.9	435.9	413.0	390.0	376.0
65°	491.9	476.7	461.4	446.2	431.0	412.6	391.0	369.4	347.8	326.2	312.7
67.5°	421.9	406.5	391.1	375.7	360.4	342.3	321.6	300.9	280.2	259.5	249.4
70°	376.0	361.2	346.2	331.2	316.3	299.1	279.8	260.4	241.1	221.7	212.0
72.5°	330.3	315.5	300.8	286.1	271.3	255.2	237.6	220.0	202.4	184.8	176.9
75°	260.2	247.0	233.7	220.4	207.2	192.9	177.7	162.4	147.2	132.0	129.2
77.5°	196.5	184.5	172.5	160.5	148.5	137.5	127.8	118.0	108.1	98.4	96.9
80°	155.7	144.3	132.9	121.6	110.3	101.7	95.9	90.1	84.3	78.4	77.6
82.5°	116.8	107.0	97.2	87.4	77.6	71.4	68.7	65.9	63.2	60.5	59.7
85°	66.0	59.9	53.8	47.8	41.7	38.2	37.4	36.5	35.7	34.9	34.3
87.5°	24.2	22.3	20.4	18.5	16.6	15.9	16.6	17.3	18.0	18.7	18.7
90°	1.2	3.9	6.5	9.2	11.8	14.9	18.3	21.8	25.2	28.7	29.7
92.5°	28.9	30.7	32.5	34.3	36.1	38.0	40.0	41.9	43.9	45.9	46.7
95°	70.5	72.3	74.2	76.0	78.0	79.9	82.0	84.1	86.3	88.4	89.4
97.5°	125.2	126.6	127.9	129.4	130.7	132.1	133.7	135.2	136.8	138.3	139.6
100°	162.5	164.1	165.6	167.2	168.8	170.3	171.6	172.9	174.3	175.6	176.4
102.5°	205.5	206.4	207.4	208.3	209.3	210.6	212.4	214.1	215.9	217.6	218.5
105°	268.8	269.3	269.8	270.4	270.9	272.4	274.7	277.1	279.6	281.9	281.9
107.5°	342.4	342.7	343.0	343.3	343.6	344.3	345.2	346.2	347.1	348.1	349.0
110°	388.2	388.8	389.3	389.8	390.4	390.9	391.4	392.0	392.4	393.0	394.1



TEST NUMBER: P332489-927

CATALOG NUMBER: S123RDIW-S1165D1535U927-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	436.0	436.3	436.7	437.0	437.3	437.5	437.6	437.7	437.8	437.9	439.2
115°	507.7	508.5	509.3	510.1	510.9	511.0	510.5	509.9	509.5	508.9	509.1
117.5°	579.9	580.4	580.9	581.5	581.9	581.9	581.2	580.5	579.8	579.2	579.1
120°	624.8	626.4	628.0	629.5	631.1	631.3	629.9	628.6	627.2	626.0	625.7
122.5°	671.6	672.7	673.9	675.1	676.3	676.5	675.8	675.1	674.5	673.8	673.0
125°	743.0	743.8	744.7	745.4	746.2	746.3	745.8	745.3	744.7	744.3	743.1
127.5°	809.0	810.6	812.4	814.0	815.8	816.3	815.7	815.2	814.6	814.0	812.5
130°	852.9	855.1	857.1	859.3	861.4	862.1	861.3	860.5	859.7	858.9	857.9
132.5°	896.9	899.0	901.1	903.2	905.4	906.2	905.5	905.0	904.4	903.8	902.5
135°	964.0	965.6	967.2	968.8	970.4	971.1	970.8	970.5	970.3	970.0	968.9
137.5°	1026.1	1027.5	1028.8	1030.2	1031.4	1032.5	1033.2	1033.8	1034.5	1035.2	1034.1
140°	1069.1	1070.5	1071.8	1073.1	1074.4	1075.2	1075.5	1075.8	1076.0	1076.3	1076.0
142.5°	1108.3	1109.6	1111.0	1112.3	1113.6	1114.5	1115.0	1115.5	1115.9	1116.4	1116.2
145°	1169.5	1170.1	1170.5	1171.1	1171.6	1172.3	1173.1	1173.9	1174.6	1175.4	1175.2
147.5°	1223.0	1223.9	1224.9	1225.9	1226.9	1227.6	1228.4	1229.2	1229.9	1230.7	1230.7
150°	1260.3	1260.8	1261.3	1261.9	1262.4	1262.9	1263.5	1264.0	1264.5	1265.0	1265.0
152.5°	1290.9	1291.6	1292.4	1293.1	1293.8	1294.3	1294.7	1295.0	1295.3	1295.6	1296.1
155°	1339.1	1339.1	1339.1	1339.1	1339.1	1339.3	1339.5	1339.7	1340.1	1340.3	1341.4
157.5°	1380.2	1379.9	1379.6	1379.3	1379.0	1378.9	1379.1	1379.3	1379.5	1379.7	1380.9
160°	1406.0	1405.5	1404.9	1404.4	1403.9	1403.6	1403.6	1403.6	1403.6	1403.6	1404.9
162.5°	1428.9	1428.2	1427.4	1426.7	1426.0	1425.7	1425.9	1426.2	1426.3	1426.6	1427.9
165°	1458.6	1457.8	1457.0	1456.2	1455.4	1455.0	1455.0	1455.0	1455.0	1455.0	1456.6
167.5°	1482.3	1481.1	1480.1	1479.0	1478.0	1477.6	1477.7	1478.0	1478.2	1478.4	1480.0
170°	1495.6	1494.5	1493.5	1492.4	1491.4	1490.8	1490.8	1490.8	1490.8	1490.8	1492.7
172.5°	1506.1	1505.1	1504.0	1502.9	1501.9	1501.3	1501.3	1501.3	1501.3	1501.3	1503.0
175°	1517.1	1516.1	1515.0	1513.9	1512.8	1512.4	1512.4	1512.4	1512.4	1512.4	1513.9
177.5°	1521.6	1520.8	1520.0	1519.1	1518.2	1517.8	1517.8	1517.8	1517.8	1517.8	1519.1
180°	1520.7	1520.7	1520.7	1520.7	1520.7	1520.7	1520.7	1520.7	1520.7	1520.7	1520.7



TEST NUMBER: P332489-927

CATALOG NUMBER: S123RDIW-S1165D1535U927-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1535.4	1535.4	1535.4	1535.4	1535.4	1535.4	1535.4	1535.4
2.5°	1529.3	1531.8	1534.1	1535.2	1534.7	1534.3	1533.8	1533.3
5°	1519.2	1521.7	1524.2	1525.1	1524.6	1524.0	1523.4	1522.9
7.5°	1497.8	1499.2	1500.6	1500.8	1499.8	1498.9	1497.9	1497.0
10°	1478.7	1478.9	1479.2	1478.7	1477.3	1475.9	1474.5	1473.1
12.5°	1454.8	1454.7	1454.5	1453.7	1452.1	1450.4	1448.8	1447.2
15°	1413.1	1411.7	1410.3	1408.7	1406.7	1404.8	1402.8	1400.9
17.5°	1363.2	1360.2	1357.2	1354.4	1351.5	1348.6	1345.8	1342.8
20°	1329.0	1325.3	1321.8	1318.3	1314.9	1311.6	1308.4	1305.0
22.5°	1292.3	1287.9	1283.3	1279.5	1276.4	1273.4	1270.3	1267.2
25°	1232.4	1226.5	1220.8	1216.3	1213.3	1210.2	1207.2	1204.1
27.5°	1167.0	1159.0	1150.9	1144.5	1139.9	1135.3	1130.6	1125.9
30°	1120.5	1111.2	1101.8	1094.9	1090.4	1086.0	1081.6	1077.1
32.5°	1075.0	1064.7	1054.4	1046.9	1042.3	1037.6	1033.0	1028.3
35°	1007.3	995.4	983.5	975.0	970.0	965.0	960.0	955.1
37.5°	934.5	921.1	907.5	897.7	891.6	885.4	879.3	873.1
40°	884.0	869.6	855.2	844.9	838.4	832.1	825.8	819.4
42.5°	835.5	819.8	804.1	793.4	787.7	782.0	776.3	770.6
45°	764.1	748.4	732.6	721.4	714.8	708.1	701.5	694.8
47.5°	690.4	673.3	656.1	644.6	638.7	632.7	626.8	620.9
50°	640.6	623.4	606.3	594.5	588.2	581.8	575.4	569.1
52.5°	592.5	574.6	556.8	545.0	539.3	533.7	528.0	522.3
55°	520.8	504.7	488.7	477.9	472.4	466.8	461.3	455.7
57.5°	450.4	435.1	420.0	410.0	405.4	400.7	395.9	391.3
60°	405.9	391.0	376.0	366.2	361.6	356.8	352.1	347.5
62.5°	361.9	347.8	333.7	324.3	319.3	314.4	309.5	304.6
65°	299.1	285.6	272.0	263.7	260.7	257.6	254.6	251.5
67.5°	239.2	229.1	219.0	212.3	209.1	205.7	202.5	199.2
70°	202.2	192.6	182.9	176.6	173.5	170.5	167.4	164.4
72.5°	169.0	161.1	153.1	148.5	147.3	146.0	144.7	143.5
75°	126.4	123.7	120.9	119.3	118.7	118.2	117.6	117.1
77.5°	95.4	93.9	92.4	91.3	90.8	90.2	89.7	89.1
80°	76.8	76.0	75.1	74.5	73.9	73.4	72.8	72.2
82.5°	58.9	58.1	57.2	56.7	56.6	56.5	56.4	56.3
85°	33.7	33.2	32.6	32.4	32.4	32.4	32.4	32.4
87.5°	18.7	18.7	18.6	18.6	18.5	18.4	18.2	18.1
90°	30.8	31.8	33.0	33.7	34.2	34.8	35.3	35.8
92.5°	47.5	48.4	49.3	49.5	49.2	48.9	48.6	48.2
95°	90.5	91.6	92.6	93.2	93.2	93.2	93.2	93.2
97.5°	140.8	142.0	143.2	143.8	143.7	143.5	143.5	143.4
100°	177.2	178.0	178.8	179.4	180.0	180.5	181.0	181.6
102.5°	219.3	220.1	220.9	221.2	221.1	220.9	220.9	220.8
105°	281.9	281.9	281.9	282.2	282.7	283.3	283.8	284.3
107.5°	349.8	350.6	351.5	351.7	351.4	351.1	350.8	350.5
110°	395.1	396.2	397.3	397.5	397.0	396.5	395.9	395.4



TEST NUMBER: P332489-927

CATALOG NUMBER: S123RDIW-S1165D1535U927-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	440.5	441.7	443.0	443.6	443.5	443.4	443.3	443.1
115°	509.5	509.7	509.9	509.9	509.7	509.5	509.1	508.9
117.5°	579.0	579.0	578.9	578.5	577.7	577.0	576.3	575.5
120°	625.4	625.2	624.9	624.5	624.0	623.4	622.9	622.3
122.5°	672.3	671.7	671.0	670.3	669.6	668.8	668.0	667.3
125°	742.1	741.0	740.0	738.9	737.8	736.8	735.7	734.7
127.5°	811.0	809.5	808.0	806.7	805.5	804.2	803.0	801.8
130°	856.7	855.7	854.7	853.2	851.4	849.5	847.6	845.7
132.5°	901.3	900.0	898.7	897.4	896.0	894.5	893.0	891.6
135°	967.9	966.8	965.7	965.0	964.4	963.8	963.4	962.8
137.5°	1033.0	1031.9	1030.8	1029.7	1028.6	1027.7	1026.7	1025.6
140°	1075.8	1075.5	1075.2	1074.2	1072.3	1070.5	1068.6	1066.8
142.5°	1115.9	1115.6	1115.4	1114.5	1113.1	1111.7	1110.2	1108.8
145°	1174.9	1174.6	1174.4	1173.7	1172.7	1171.6	1170.5	1169.5
147.5°	1230.7	1230.7	1230.7	1229.9	1228.3	1226.7	1225.0	1223.4
150°	1265.0	1265.0	1265.0	1264.2	1262.7	1261.1	1259.5	1257.9
152.5°	1296.5	1296.9	1297.4	1296.9	1295.5	1294.1	1292.7	1291.3
155°	1342.4	1343.5	1344.6	1344.2	1342.3	1340.5	1338.6	1336.7
157.5°	1382.0	1383.1	1384.2	1384.0	1382.5	1381.0	1379.5	1378.1
160°	1406.3	1407.6	1408.9	1409.1	1408.0	1406.9	1405.9	1404.8
162.5°	1429.2	1430.5	1431.9	1431.7	1430.0	1428.3	1426.6	1424.9
165°	1458.2	1459.8	1461.3	1461.3	1459.4	1457.5	1455.6	1453.8
167.5°	1481.7	1483.4	1484.9	1484.9	1483.4	1481.7	1480.0	1478.4
170°	1494.5	1496.4	1498.3	1498.3	1496.4	1494.5	1492.7	1490.8
172.5°	1504.6	1506.3	1507.9	1507.8	1505.9	1504.1	1502.2	1500.4
175°	1515.5	1517.1	1518.7	1518.5	1516.7	1514.8	1513.0	1511.2
177.5°	1520.4	1521.6	1522.9	1522.8	1521.3	1519.8	1518.4	1516.9
180°	1520.7	1520.7	1520.7	1520.7	1520.7	1520.7	1520.7	1520.7

(END OF REPORT)