

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332474-927

Luminaire Tested: **S123RDIW-S1165D755U927-4F0-1E-UDD-A**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P332474-927  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-5,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S123RDIW-S1165D755U927-4F0-1E-UDD-A  
Description: DEFINE 3 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 1165 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING  
UPLIGHT 755 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 6016.4 lumens  
Efficiency: N/A  
Efficacy: 100.6 lumens/watt  
Spacing Criteria (0/90/45): 1.21 / 1.22 / 1.36  
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')  
CIE Type: Semi-Direct  
  
Input Watts (W): 59.8  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332474-927

CATALOG NUMBER: S123RDIW-S1165D755U927-4F0-1E-UDD-A

### Luminous Intensity Polar Plot





TEST NUMBER: P332474-927

CATALOG NUMBER: S123RDIW-S1165D755U927-4F0-1E-UDD-A

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	110	110	110	110	102	102	102	102	89	89	89	77	77	77	66	66	66	60
1	101	97	93	90	94	91	87	84	79	77	75	69	67	65	59	58	57	52
2	92	85	79	74	86	80	75	71	70	66	63	61	58	56	53	51	49	45
3	85	76	68	63	79	71	65	60	63	58	54	55	51	48	47	45	42	39
4	78	67	60	54	73	63	57	51	56	51	46	49	45	42	43	40	37	34
5	72	60	52	47	67	57	50	45	51	45	41	45	40	37	39	35	33	30
6	66	55	47	41	62	52	44	39	46	40	36	40	36	32	36	32	29	27
7	62	49	42	36	58	47	40	35	42	36	32	37	32	29	33	29	26	24
8	57	45	37	32	54	43	36	31	38	33	28	34	29	26	30	26	24	21
9	53	41	34	29	50	39	32	28	35	30	26	31	27	24	28	24	21	19
10	50	38	31	26	47	36	30	25	33	27	23	29	25	21	26	22	20	18

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	15655	15655	15655	15655
5°	18662	15722	13846	15722
10°	23302	15632	12508	15632
15°	27351	15473	11407	15473
20°	30525	15234	10470	15234
25°	30037	14982	9894	14982
30°	21592	14751	9302	14751
35°	14416	14448	8918	14448
40°	10621	14085	8521	14085
45°	8910	13449	8132	13449
50°	7860	12616	7591	12616
55°	6893	11661	6848	11661
60°	6140	10749	6273	10749
65°	5392	9770	5835	9770
70°	4233	8897	5331	8897
75°	3730	7769	4870	7769
80°	3242	6602	4785	6602
85°	2618	5298	5076	5298



TEST NUMBER: P332474-927

CATALOG NUMBER: S123RDIW-S1165D755U927-4F0-1E-UDD-A

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	143.0	2.4
10°-20°	446.9	7.4
20°-30°	702.0	11.7
30°-40°	732.4	12.2
40°-50°	626.8	10.4
50°-60°	477.7	7.9
60°-70°	306.2	5.1
70°-80°	147.3	2.4
80°-90°	41.2	0.7
90°-100°	28.5	0.5
100°-110°	136.0	2.3
110°-120°	326.6	5.4
120°-130°	415.9	6.9
130°-140°	444.3	7.4
140°-150°	415.5	6.9
150°-160°	335.2	5.6
160°-170°	216.3	3.6
170°-180°	74.5	1.2
0°-30°	1291.9	21.5
0°-40°	2024.3	33.6
0°-60°	3128.9	52.0
0°-90°	3623.6	60.2
90°-120°	491.1	8.2
90°-150°	1766.8	29.4
90°-180°	2393.0	39.8
0°-180°	6016.4	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	1454	1454	1454	1454	1454	
5°	1727	1455	1281	1455	1727	178
15°	2454	1388	1024	1388	2454	696
25°	2529	1262	833	1262	2529	1087
35°	1097	1100	679	1100	1097	719
45°	585	884	534	884	585	460
55°	367	621	365	621	367	332
65°	212	384	229	384	212	208
75°	90	187	117	187	90	96
85°	21	43	41	43	21	25
90°	18	1	18	1	18	9
95°	22	36	22	36	22	19
105°	26	174	26	174	26	59
115°	343	326	343	326	343	317
125°	469	459	469	459	469	419
135°	578	572	578	572	578	445
145°	666	660	666	660	666	416
155°	726	727	726	727	726	335
165°	765	767	765	767	765	216
175°	782	785	782	785	782	74
180°	785	785	785	785	785	



TEST NUMBER: P332474-927

CATALOG NUMBER: S123RDIW-S1165D755U927-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1454.4	1454.4	1454.4	1454.4	1454.4	1454.4	1454.4	1454.4	1454.4	1454.4	1454.4
2.5°	1549.1	1551.1	1544.6	1543.6	1536.1	1534.1	1534.1	1523.7	1517.2	1508.8	1503.8
5°	1727.2	1737.2	1732.2	1720.9	1702.2	1697.9	1686.1	1667.4	1646.2	1620.1	1607.7
7.5°	1949.6	1963.2	1958.0	1940.6	1921.0	1905.3	1871.8	1840.9	1797.4	1759.3	1726.6
10°	2131.9	2117.6	2106.3	2089.5	2071.5	2042.2	2007.4	1959.4	1904.0	1860.4	1811.9
12.5°	2268.3	2266.0	2251.8	2234.5	2209.0	2181.2	2138.3	2080.0	2015.5	1952.6	1897.0
15°	2454.4	2458.1	2448.8	2430.7	2394.6	2345.4	2280.7	2256.5	2164.2	2095.8	2027.3
17.5°	2583.1	2582.4	2581.2	2556.1	2519.3	2484.3	2424.2	2360.4	2277.0	2180.5	2088.2
20°	2664.8	2658.6	2659.9	2631.9	2604.5	2564.0	2505.4	2412.7	2344.2	2232.8	2137.5
22.5°	2662.8	2661.7	2666.3	2656.7	2636.9	2605.8	2559.8	2481.4	2394.1	2281.6	2174.4
25°	2529.1	2524.1	2553.4	2561.5	2593.3	2598.8	2585.1	2542.2	2459.4	2343.6	2211.0
27.5°	2116.7	2113.9	2168.3	2236.3	2322.4	2389.4	2454.2	2485.4	2459.4	2376.5	2243.6
30°	1737.2	1795.6	1823.0	1921.4	2031.0	2161.8	2276.3	2385.3	2412.0	2376.0	2267.0
32.5°	1442.2	1493.3	1516.2	1600.7	1702.8	1855.9	2027.7	2182.1	2291.1	2318.6	2253.0
35°	1097.1	1097.7	1150.0	1187.3	1282.0	1439.6	1606.4	1813.1	2018.6	2174.2	2190.4
37.5°	875.4	878.5	910.1	947.4	1018.4	1101.7	1248.6	1420.5	1657.8	1896.8	2036.9
40°	755.9	761.4	785.1	821.9	872.9	935.8	1050.4	1212.3	1410.2	1676.1	1893.4
42.5°	679.1	688.2	700.4	728.7	760.3	819.3	911.9	1037.0	1217.0	1468.4	1719.1
45°	585.3	590.3	599.6	612.7	641.3	682.4	744.7	828.7	978.2	1180.5	1431.4
47.5°	516.3	513.7	523.5	534.1	553.2	581.1	622.9	691.5	798.1	960.4	1173.3
50°	469.4	468.8	475.7	483.8	501.8	522.4	556.7	608.3	693.0	827.5	1022.4
52.5°	425.6	428.0	432.8	442.9	456.0	472.6	503.4	540.6	613.3	729.4	891.8
55°	367.3	369.2	376.0	381.7	391.0	407.8	427.1	458.3	508.1	589.0	722.9
57.5°	318.1	317.2	323.8	325.1	335.7	349.4	364.3	388.5	424.6	484.8	575.0
60°	285.2	283.3	288.9	293.3	298.9	310.1	322.5	346.2	374.9	419.1	496.2
62.5°	255.2	254.4	258.5	262.8	267.5	277.7	288.1	306.3	329.0	366.2	427.5
65°	211.7	213.6	215.4	217.3	219.8	226.0	236.0	248.4	264.0	290.2	334.4
67.5°	166.4	168.3	168.9	172.7	178.1	182.0	188.1	199.2	209.9	232.0	257.1
70°	134.5	133.9	134.5	136.3	143.2	150.0	158.1	166.3	173.1	188.6	209.8
72.5°	115.6	114.5	116.1	116.5	119.8	121.7	126.7	134.4	143.2	153.8	169.0
75°	89.7	89.7	89.7	89.7	92.1	93.4	95.3	97.1	100.2	105.2	116.5
77.5°	66.2	66.4	67.3	67.9	68.4	69.1	70.3	72.1	73.2	75.8	80.7
80°	52.3	52.9	52.3	52.9	52.9	54.2	54.8	56.6	57.3	60.4	62.3
82.5°	39.4	39.0	39.4	40.0	40.0	41.2	41.4	42.7	42.9	44.4	46.3
85°	21.2	20.0	21.2	20.5	21.8	20.5	21.2	22.4	22.4	23.1	25.5
87.5°	8.5	9.4	8.4	8.8	8.8	9.2	9.1	9.0	9.9	9.3	9.4
90°	17.5	17.2	17.0	16.7	16.5	16.1	15.5	15.1	14.5	14.0	12.3
92.5°	19.3	19.2	19.0	18.9	18.7	18.2	17.4	16.6	15.8	14.9	13.6
95°	22.2	22.2	22.2	22.2	22.2	21.7	20.8	19.9	19.0	18.1	16.6
97.5°	24.0	23.9	23.8	23.6	23.5	22.9	21.9	20.8	19.8	18.8	28.1
100°	24.5	24.3	24.2	24.1	24.0	23.4	22.3	21.3	20.3	19.3	39.5
102.5°	25.0	24.7	24.5	24.2	24.0	25.5	28.8	31.9	35.2	38.3	60.4
105°	25.7	25.4	25.1	24.9	24.6	36.0	58.9	81.8	104.7	127.7	139.3
107.5°	80.6	97.8	115.1	132.4	149.7	166.8	183.5	200.3	217.1	234.0	232.2
110°	160.3	178.8	197.3	215.9	234.4	245.8	250.1	254.4	258.6	262.9	261.5



TEST NUMBER: P332474-927

CATALOG NUMBER: S123RDIW-S1165D755U927-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	275.0	278.9	282.9	286.8	290.7	292.6	292.6	292.5	292.4	292.3	290.9
115°	342.8	342.2	341.7	341.2	340.7	339.8	338.5	337.2	335.9	334.6	333.4
117.5°	380.8	380.6	380.6	380.5	380.3	379.8	378.7	377.7	376.7	375.7	375.0
120°	406.9	406.9	406.9	406.9	406.9	406.4	405.4	404.3	403.3	402.2	401.9
122.5°	432.5	432.5	432.3	432.2	432.1	431.7	430.9	430.2	429.5	428.8	428.3
125°	468.7	468.4	468.2	467.9	467.6	467.4	467.1	466.8	466.6	466.4	465.8
127.5°	503.4	503.7	503.9	504.2	504.5	504.4	504.0	503.6	503.1	502.7	502.1
130°	525.8	526.1	526.3	526.6	526.9	526.7	526.2	525.7	525.1	524.7	524.1
132.5°	546.3	546.7	547.1	547.4	547.8	547.7	547.2	546.7	546.1	545.7	545.2
135°	577.7	578.1	578.5	578.8	579.2	579.2	578.8	578.5	578.1	577.7	577.2
137.5°	607.2	607.4	607.7	608.0	608.2	608.1	607.4	606.8	606.2	605.5	605.3
140°	624.9	625.2	625.4	625.7	626.0	625.8	625.3	624.8	624.2	623.8	623.4
142.5°	641.2	641.6	642.0	642.3	642.7	642.6	642.2	641.8	641.4	641.0	640.6
145°	666.3	666.3	666.3	666.3	666.3	666.1	665.9	665.7	665.4	665.1	664.9
147.5°	684.9	685.6	686.1	686.7	687.3	687.5	687.2	687.0	686.7	686.4	686.2
150°	698.9	699.3	699.7	700.1	700.5	700.5	700.3	700.1	699.8	699.5	699.3
152.5°	710.1	710.7	711.3	711.9	712.5	712.6	712.1	711.6	711.1	710.7	710.6
155°	725.7	726.5	727.3	728.1	728.9	729.0	728.3	727.6	727.0	726.4	726.2
157.5°	738.9	740.0	740.9	742.0	743.0	743.1	742.3	741.6	740.8	740.0	740.1
160°	747.3	748.2	749.2	750.0	751.0	751.0	750.3	749.5	748.7	747.9	748.1
162.5°	755.3	756.1	756.9	757.6	758.4	758.4	757.6	756.7	755.8	754.9	755.0
165°	764.8	765.7	766.6	767.5	768.4	768.3	767.3	766.3	765.2	764.2	764.4
167.5°	771.7	772.7	773.7	774.8	775.9	775.9	774.8	773.7	772.7	771.7	771.7
170°	775.9	776.9	777.9	779.0	780.1	780.1	779.0	777.9	776.9	775.9	775.9
172.5°	778.2	779.3	780.5	781.6	782.8	782.8	781.8	780.8	779.7	778.7	778.6
175°	781.7	782.8	783.8	784.8	785.8	785.9	785.1	784.1	783.2	782.3	782.2
177.5°	782.8	783.8	784.8	785.8	786.9	787.0	786.2	785.4	784.5	783.7	783.6
180°	784.7	784.7	784.7	784.7	784.7	784.7	784.7	784.7	784.7	784.7	784.7



TEST NUMBER: P332474-927

CATALOG NUMBER: S123RDIW-S1165D755U927-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1454.4	1454.4	1454.4	1454.4	1454.4	1454.4	1454.4	1454.4	1454.4	1454.4	1454.4
2.5°	1501.8	1500.3	1493.3	1485.3	1474.9	1467.9	1462.4	1459.4	1450.5	1439.6	1432.0
5°	1594.6	1575.9	1555.9	1531.7	1509.3	1486.2	1471.9	1455.1	1434.6	1411.5	1395.3
7.5°	1693.9	1657.3	1617.9	1577.2	1536.9	1500.8	1468.9	1441.6	1408.9	1375.9	1352.7
10°	1770.1	1716.6	1661.2	1604.5	1552.8	1504.3	1466.9	1430.2	1391.0	1353.0	1324.4
12.5°	1839.4	1768.9	1705.0	1635.4	1569.3	1511.2	1457.5	1414.2	1367.1	1326.6	1294.0
15°	1927.1	1854.8	1777.6	1671.7	1584.0	1510.5	1445.1	1388.5	1331.2	1281.4	1249.6
17.5°	2009.0	1900.3	1796.5	1708.3	1594.2	1502.4	1422.6	1354.9	1292.0	1239.1	1200.1
20°	2042.9	1937.6	1825.0	1712.2	1600.1	1497.5	1404.6	1329.9	1264.6	1204.8	1168.7
22.5°	2063.2	1944.1	1825.4	1704.3	1585.2	1478.5	1386.7	1304.6	1233.7	1176.9	1132.3
25°	2087.1	1945.1	1814.3	1694.8	1573.4	1457.6	1348.6	1261.5	1184.9	1124.5	1077.1
27.5°	2102.8	1935.8	1781.2	1648.4	1525.2	1409.8	1310.0	1217.6	1140.0	1076.0	1025.2
30°	2105.7	1928.3	1755.8	1612.0	1486.8	1381.0	1275.2	1186.8	1104.5	1036.6	989.4
32.5°	2109.7	1909.9	1721.4	1568.7	1440.5	1335.7	1239.8	1155.3	1071.2	1004.3	956.0
35°	2093.3	1899.7	1669.3	1493.7	1365.4	1263.9	1177.4	1099.5	1016.8	952.0	902.9
37.5°	2022.5	1859.2	1615.3	1409.3	1275.2	1181.1	1110.6	1042.7	966.9	897.0	850.6
40°	1951.3	1819.3	1573.4	1358.0	1217.9	1121.3	1057.9	1002.4	929.0	863.6	813.8
42.5°	1845.2	1765.1	1533.5	1304.2	1153.1	1060.1	1006.5	954.6	890.1	823.7	776.9
45°	1650.6	1661.2	1452.0	1218.5	1063.4	970.0	919.6	883.5	826.2	771.4	723.5
47.5°	1406.5	1505.5	1356.2	1127.2	968.9	881.3	837.2	805.6	767.1	713.3	669.6
50°	1247.1	1388.5	1279.5	1066.0	909.7	822.5	778.9	753.4	719.8	677.4	635.7
52.5°	1100.2	1252.0	1186.8	997.7	845.4	765.7	723.1	702.1	675.4	635.6	597.9
55°	897.2	1051.0	1036.1	894.7	749.0	677.4	645.1	621.4	603.3	573.5	543.6
57.5°	725.7	871.6	879.2	780.1	664.1	593.3	565.5	547.6	535.8	513.3	485.7
60°	617.7	751.5	777.7	703.0	603.3	541.1	513.7	499.3	490.0	472.0	450.8
62.5°	528.0	641.9	671.5	617.7	545.0	486.8	465.3	451.5	445.2	429.6	410.9
65°	404.1	498.8	527.4	497.5	459.5	412.8	395.4	383.6	378.0	369.2	355.5
67.5°	303.9	372.8	404.3	383.2	369.5	339.9	328.8	322.5	317.5	311.6	300.1
70°	244.1	295.1	327.5	321.9	310.7	295.1	287.0	282.7	277.7	272.7	262.8
72.5°	196.2	231.4	261.7	264.6	255.4	252.3	245.2	243.4	240.3	234.3	228.9
75°	130.2	154.4	175.5	183.7	187.4	190.5	187.4	186.8	186.2	181.2	178.1
77.5°	85.3	98.4	111.7	125.6	131.3	135.6	136.6	138.9	137.2	134.6	133.1
80°	65.4	68.5	77.8	89.7	99.0	102.7	105.2	106.5	105.8	105.2	102.7
82.5°	47.5	50.1	54.4	62.7	70.6	76.8	78.3	78.1	79.5	79.9	77.8
85°	25.5	26.1	27.4	28.7	33.0	39.8	41.7	42.9	44.2	44.2	40.5
87.5°	10.1	9.3	9.9	9.6	10.9	11.1	13.9	16.1	16.8	15.1	15.4
90°	10.6	9.0	7.3	5.8	4.4	3.2	1.9	0.6	1.9	3.2	4.4
92.5°	12.4	11.1	9.8	9.4	9.7	10.1	10.5	10.9	10.5	10.1	9.7
95°	15.2	13.8	12.4	14.3	19.6	25.0	30.3	35.6	30.3	25.0	19.6
97.5°	37.4	46.7	56.1	61.9	64.3	66.7	69.1	71.5	69.1	66.7	64.3
100°	59.7	79.9	100.1	108.8	106.3	103.7	101.1	98.5	101.1	103.7	106.3
102.5°	82.5	104.6	126.7	136.7	134.9	133.0	131.2	129.3	131.2	133.0	134.9
105°	151.0	162.6	174.3	179.4	178.0	176.6	175.2	173.7	175.2	176.6	178.0
107.5°	230.3	228.5	226.6	225.1	224.0	222.8	221.7	220.5	221.7	222.8	224.0
110°	260.1	258.6	257.2	256.0	254.9	253.9	252.9	251.8	252.9	253.9	254.9





TEST NUMBER: P332474-927

CATALOG NUMBER: S123RDIW-S1165D755U927-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	289.5	288.0	286.6	285.4	284.5	283.5	282.6	281.7	282.6	283.5	284.5
115°	332.2	331.1	329.9	329.0	328.2	327.4	326.6	325.8	326.6	327.4	328.2
117.5°	374.5	373.8	373.3	372.5	371.5	370.6	369.6	368.7	369.6	370.6	371.5
120°	401.5	401.1	400.7	399.9	398.7	397.6	396.4	395.2	396.4	397.6	398.7
122.5°	427.9	427.3	426.8	426.1	425.2	424.2	423.3	422.3	423.3	424.2	425.2
125°	465.3	464.8	464.3	463.5	462.5	461.4	460.4	459.4	460.4	461.4	462.5
127.5°	501.5	500.9	500.3	499.4	498.4	497.3	496.3	495.3	496.3	497.3	498.4
130°	523.6	523.1	522.6	521.8	520.8	519.8	518.7	517.6	518.7	519.8	520.8
132.5°	544.8	544.4	544.0	543.3	542.2	541.1	540.1	539.1	540.1	541.1	542.2
135°	576.6	576.2	575.6	575.0	574.2	573.4	572.7	571.9	572.7	573.4	574.2
137.5°	605.0	604.7	604.4	603.8	602.8	601.8	600.8	599.8	600.8	601.8	602.8
140°	623.0	622.6	622.2	621.6	620.8	620.0	619.2	618.5	619.2	620.0	620.8
142.5°	640.2	639.8	639.4	638.9	638.1	637.3	636.5	635.7	636.5	637.3	638.1
145°	664.6	664.3	664.1	663.5	662.6	661.7	660.8	659.9	660.8	661.7	662.6
147.5°	686.0	685.7	685.4	685.0	684.4	683.8	683.2	682.6	683.2	683.8	684.4
150°	699.0	698.8	698.5	698.2	697.8	697.4	697.0	696.6	697.0	697.4	697.8
152.5°	710.4	710.3	710.1	710.0	709.7	709.6	709.4	709.2	709.4	709.6	709.7
155°	726.1	726.0	725.8	725.9	726.1	726.4	726.7	726.9	726.7	726.4	726.1
157.5°	740.2	740.4	740.5	740.6	740.6	740.6	740.7	740.7	740.7	740.6	740.6
160°	748.1	748.3	748.5	748.5	748.7	748.8	748.9	749.1	748.9	748.8	748.7
162.5°	755.2	755.3	755.4	755.7	756.0	756.3	756.7	757.0	756.7	756.3	756.0
165°	764.5	764.6	764.8	765.0	765.4	765.8	766.2	766.6	766.2	765.8	765.4
167.5°	771.7	771.7	771.7	772.0	772.5	773.0	773.5	774.0	773.5	773.0	772.5
170°	775.9	775.9	775.9	776.2	776.7	777.2	777.7	778.2	777.7	777.2	776.7
172.5°	778.5	778.4	778.2	778.6	779.2	779.7	780.4	781.0	780.4	779.7	779.2
175°	782.0	781.9	781.8	782.0	782.7	783.3	783.9	784.7	783.9	783.3	782.7
177.5°	783.5	783.4	783.3	783.5	784.0	784.5	785.1	785.5	785.1	784.5	784.0
180°	784.7	784.7	784.7	784.7	784.7	784.7	784.7	784.7	784.7	784.7	784.7



TEST NUMBER: P332474-927

CATALOG NUMBER: S123RDIW-S1165D755U927-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1454.4	1454.4	1454.4	1454.4	1454.4	1454.4	1454.4	1454.4	1454.4	1454.4	1454.4
2.5°	1429.6	1423.1	1418.6	1408.7	1402.2	1395.2	1388.2	1392.7	1392.2	1391.7	1391.7
5°	1381.6	1367.3	1354.2	1337.4	1326.8	1313.8	1303.8	1302.5	1305.0	1296.3	1291.3
7.5°	1334.0	1314.5	1295.9	1277.4	1257.7	1242.1	1232.2	1227.6	1221.2	1215.8	1210.3
10°	1300.7	1277.6	1259.6	1236.5	1215.4	1196.7	1184.9	1176.8	1172.4	1168.1	1160.0
12.5°	1266.3	1243.8	1220.8	1194.7	1174.6	1152.9	1144.0	1135.0	1126.6	1121.7	1110.6
15°	1216.0	1186.8	1162.4	1135.0	1112.6	1091.5	1079.0	1061.0	1058.4	1052.3	1041.0
17.5°	1165.5	1133.8	1100.3	1080.0	1054.7	1032.7	1013.8	1007.7	989.8	983.1	973.4
20°	1125.7	1096.5	1071.0	1044.2	1007.4	986.9	971.9	963.8	949.5	940.8	934.5
22.5°	1091.3	1061.6	1032.1	1000.8	970.6	947.5	936.6	924.0	916.2	904.0	897.2
25°	1042.3	1009.9	974.4	940.8	919.0	901.6	884.2	872.9	861.7	856.1	843.7
27.5°	985.2	951.4	918.2	892.7	865.9	848.7	833.0	823.0	809.5	800.1	793.2
30°	953.9	914.0	885.3	862.4	828.1	811.9	800.1	787.7	777.7	767.7	760.9
32.5°	917.5	881.1	854.0	825.5	799.2	781.5	766.2	755.3	746.8	737.3	730.5
35°	860.5	830.0	801.9	773.3	754.0	735.9	717.9	708.5	700.4	691.7	685.6
37.5°	808.9	780.4	753.8	726.6	702.7	688.0	673.4	666.3	655.4	649.5	643.2
40°	777.1	749.0	720.4	694.3	669.3	658.1	645.1	634.5	624.5	620.1	613.3
42.5°	742.2	714.2	690.0	661.9	641.4	626.2	614.2	602.6	595.1	588.7	584.9
45°	690.5	665.6	641.9	613.9	594.6	581.5	567.8	557.2	550.4	546.1	539.2
47.5°	640.3	615.4	591.4	567.0	548.3	533.4	519.7	512.3	503.2	497.9	493.2
50°	604.0	581.5	556.0	533.6	514.9	499.9	488.8	479.4	471.3	464.5	461.4
52.5°	570.6	546.7	524.7	503.7	484.0	467.1	456.9	447.0	440.9	433.1	429.5
55°	515.6	492.5	473.8	453.3	434.0	419.6	407.2	398.5	392.3	383.6	378.6
57.5°	463.8	443.2	420.9	403.1	383.2	371.1	360.8	349.0	341.4	334.5	329.6
60°	429.0	405.4	386.0	369.2	351.8	336.2	326.9	317.5	309.4	302.6	298.3
62.5°	392.6	371.9	353.6	335.3	319.4	305.9	295.0	287.2	280.0	275.7	271.3
65°	336.8	320.7	302.0	287.0	272.1	262.1	253.4	246.5	241.6	238.4	234.7
67.5°	285.5	269.8	253.5	238.8	228.9	221.3	215.6	209.7	207.2	203.2	200.7
70°	252.2	236.0	221.7	210.5	200.5	194.9	191.2	186.8	184.3	179.4	176.8
72.5°	215.8	204.1	193.8	184.6	176.6	171.5	166.8	161.4	157.4	151.9	149.4
75°	170.0	159.4	151.3	145.0	140.1	133.2	126.4	120.8	118.9	117.1	116.5
77.5°	125.9	119.1	113.3	108.1	101.9	96.9	95.4	94.1	93.8	92.8	92.8
80°	99.0	92.8	88.4	82.1	78.4	78.4	78.4	77.2	77.8	77.8	77.8
82.5°	73.6	67.9	65.5	63.3	62.5	63.0	63.0	63.3	62.9	63.8	63.4
85°	37.9	38.6	39.8	39.2	39.8	39.8	41.1	40.5	41.1	39.8	41.1
87.5°	15.1	16.9	17.7	18.5	19.4	19.3	19.8	20.0	20.5	20.7	20.8
90°	5.8	7.3	9.0	10.6	12.3	14.0	14.5	15.1	15.5	16.1	16.5
92.5°	9.4	9.8	11.1	12.4	13.6	14.9	15.8	16.6	17.4	18.2	18.7
95°	14.3	12.4	13.8	15.2	16.6	18.1	19.0	19.9	20.8	21.7	22.2
97.5°	61.9	56.1	46.7	37.4	28.1	18.8	19.8	20.8	21.9	22.9	23.5
100°	108.8	100.1	79.9	59.7	39.5	19.3	20.3	21.3	22.3	23.4	24.0
102.5°	136.7	126.7	104.6	82.5	60.4	38.3	35.2	31.9	28.8	25.5	24.0
105°	179.4	174.3	162.6	151.0	139.3	127.7	104.7	81.8	58.9	36.0	24.6
107.5°	225.1	226.6	228.5	230.3	232.2	234.0	217.1	200.3	183.5	166.8	149.7
110°	256.0	257.2	258.6	260.1	261.5	262.9	258.6	254.4	250.1	245.8	234.4



TEST NUMBER: P332474-927

CATALOG NUMBER: S123RDIW-S1165D755U927-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	285.4	286.6	288.0	289.5	290.9	292.3	292.4	292.5	292.6	292.6	290.7
115°	329.0	329.9	331.1	332.2	333.4	334.6	335.9	337.2	338.5	339.8	340.7
117.5°	372.5	373.3	373.8	374.5	375.0	375.7	376.7	377.7	378.7	379.8	380.3
120°	399.9	400.7	401.1	401.5	401.9	402.2	403.3	404.3	405.4	406.4	406.9
122.5°	426.1	426.8	427.3	427.9	428.3	428.8	429.5	430.2	430.9	431.7	432.1
125°	463.5	464.3	464.8	465.3	465.8	466.4	466.6	466.8	467.1	467.4	467.6
127.5°	499.4	500.3	500.9	501.5	502.1	502.7	503.1	503.6	504.0	504.4	504.5
130°	521.8	522.6	523.1	523.6	524.1	524.7	525.1	525.7	526.2	526.7	526.9
132.5°	543.3	544.0	544.4	544.8	545.2	545.7	546.1	546.7	547.2	547.7	547.8
135°	575.0	575.6	576.2	576.6	577.2	577.7	578.1	578.5	578.8	579.2	579.2
137.5°	603.8	604.4	604.7	605.0	605.3	605.5	606.2	606.8	607.4	608.1	608.2
140°	621.6	622.2	622.6	623.0	623.4	623.8	624.2	624.8	625.3	625.8	626.0
142.5°	638.9	639.4	639.8	640.2	640.6	641.0	641.4	641.8	642.2	642.6	642.7
145°	663.5	664.1	664.3	664.6	664.9	665.1	665.4	665.7	665.9	666.1	666.3
147.5°	685.0	685.4	685.7	686.0	686.2	686.4	686.7	687.0	687.2	687.5	687.3
150°	698.2	698.5	698.8	699.0	699.3	699.5	699.8	700.1	700.3	700.5	700.5
152.5°	710.0	710.1	710.3	710.4	710.6	710.7	711.1	711.6	712.1	712.6	712.5
155°	725.9	725.8	726.0	726.1	726.2	726.4	727.0	727.6	728.3	729.0	728.9
157.5°	740.6	740.5	740.4	740.2	740.1	740.0	740.8	741.6	742.3	743.1	743.0
160°	748.5	748.5	748.3	748.1	748.1	747.9	748.7	749.5	750.3	751.0	751.0
162.5°	755.7	755.4	755.3	755.2	755.0	754.9	755.8	756.7	757.6	758.4	758.4
165°	765.0	764.8	764.6	764.5	764.4	764.2	765.2	766.3	767.3	768.3	768.4
167.5°	772.0	771.7	771.7	771.7	771.7	771.7	772.7	773.7	774.8	775.9	775.9
170°	776.2	775.9	775.9	775.9	775.9	775.9	776.9	777.9	779.0	780.1	780.1
172.5°	778.6	778.2	778.4	778.5	778.6	778.7	779.7	780.8	781.8	782.8	782.8
175°	782.0	781.8	781.9	782.0	782.2	782.3	783.2	784.1	785.1	785.9	785.8
177.5°	783.5	783.3	783.4	783.5	783.6	783.7	784.5	785.4	786.2	787.0	786.9
180°	784.7	784.7	784.7	784.7	784.7	784.7	784.7	784.7	784.7	784.7	784.7



TEST NUMBER: P332474-927

CATALOG NUMBER: S123RDIW-S1165D755U927-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1454.4	1454.4	1454.4	1454.4	1454.4	1454.4	1454.4	1454.4	1454.4	1454.4	1454.4
2.5°	1385.8	1385.2	1385.8	1383.7	1385.8	1385.2	1385.8	1391.7	1391.7	1392.2	1392.7
5°	1289.4	1288.9	1287.0	1281.4	1287.0	1288.9	1289.4	1291.3	1296.3	1305.0	1302.5
7.5°	1205.4	1204.5	1199.0	1199.2	1199.0	1204.5	1205.4	1210.3	1215.8	1221.2	1227.6
10°	1155.6	1156.2	1148.7	1144.4	1148.7	1156.2	1155.6	1160.0	1168.1	1172.4	1176.8
12.5°	1107.3	1104.5	1098.4	1093.6	1098.4	1104.5	1107.3	1110.6	1121.7	1126.6	1135.0
15°	1043.5	1037.3	1022.4	1023.6	1022.4	1037.3	1043.5	1041.0	1052.3	1058.4	1061.0
17.5°	968.4	963.8	963.6	954.9	963.6	963.8	968.4	973.4	983.1	989.8	1007.7
20°	924.6	921.5	922.7	914.0	922.7	921.5	924.6	934.5	940.8	949.5	963.8
22.5°	890.3	887.1	881.9	879.2	881.9	887.1	890.3	897.2	904.0	916.2	924.0
25°	840.0	835.0	830.0	833.1	830.0	835.0	840.0	843.7	856.1	861.7	872.9
27.5°	789.6	785.9	780.9	780.3	780.9	785.9	789.6	793.2	800.1	809.5	823.0
30°	757.7	754.0	751.5	748.4	751.5	754.0	757.7	760.9	767.7	777.7	787.7
32.5°	725.4	724.6	720.2	719.5	720.2	724.6	725.4	730.5	737.3	746.8	755.3
35°	683.0	679.3	678.0	678.7	678.0	679.3	683.0	685.6	691.7	700.4	708.5
37.5°	642.8	637.8	635.6	633.3	635.6	637.8	642.8	643.2	649.5	655.4	666.3
40°	613.9	609.0	607.7	606.4	607.7	609.0	613.9	613.3	620.1	624.5	634.5
42.5°	581.5	579.6	578.8	576.6	578.8	579.6	581.5	584.9	588.7	595.1	602.6
45°	537.3	536.7	533.0	534.2	533.0	536.7	537.3	539.2	546.1	550.4	557.2
47.5°	490.8	488.0	485.4	487.1	485.4	488.0	490.8	493.2	497.9	503.2	512.3
50°	458.9	457.6	452.0	453.3	452.0	457.6	458.9	461.4	464.5	471.3	479.4
52.5°	427.0	422.2	420.2	419.4	420.2	422.2	427.0	429.5	433.1	440.9	447.0
55°	374.2	368.6	366.1	364.9	366.1	368.6	374.2	378.6	383.6	392.3	398.5
57.5°	322.4	320.9	318.9	320.3	318.9	320.9	322.4	329.6	334.5	341.4	349.0
60°	292.0	292.0	292.0	291.4	292.0	292.0	292.0	298.3	302.6	309.4	317.5
62.5°	268.6	267.1	266.6	267.5	266.6	267.1	268.6	271.3	275.7	280.0	287.2
65°	232.9	232.3	229.7	229.1	229.7	232.3	232.9	234.7	238.4	241.6	246.5
67.5°	199.2	196.9	196.1	195.3	196.1	196.9	199.2	200.7	203.2	207.2	209.7
70°	173.7	172.5	168.7	169.4	168.7	172.5	173.7	176.8	179.4	184.3	186.8
72.5°	146.3	145.0	144.3	143.5	144.3	145.0	146.3	149.4	151.9	157.4	161.4
75°	115.8	115.2	114.5	117.1	114.5	115.2	115.8	116.5	117.1	118.9	120.8
77.5°	92.8	92.8	93.2	92.1	93.2	92.8	92.8	92.8	92.8	93.8	94.1
80°	77.8	77.8	77.2	77.2	77.2	77.8	77.8	77.8	77.8	77.8	77.2
82.5°	62.4	62.9	63.3	62.3	63.3	62.9	62.4	63.4	63.8	62.9	63.3
85°	41.1	40.5	41.7	41.1	41.7	40.5	41.1	41.1	39.8	41.1	40.5
87.5°	21.8	20.8	20.9	21.5	20.9	20.8	21.8	20.8	20.7	20.5	20.0
90°	16.7	17.0	17.2	17.5	17.2	17.0	16.7	16.5	16.1	15.5	15.1
92.5°	18.9	19.0	19.2	19.3	19.2	19.0	18.9	18.7	18.2	17.4	16.6
95°	22.2	22.2	22.2	22.2	22.2	22.2	22.2	22.2	21.7	20.8	19.9
97.5°	23.6	23.8	23.9	24.0	23.9	23.8	23.6	23.5	22.9	21.9	20.8
100°	24.1	24.2	24.3	24.5	24.3	24.2	24.1	24.0	23.4	22.3	21.3
102.5°	24.2	24.5	24.7	25.0	24.7	24.5	24.2	24.0	25.5	28.8	31.9
105°	24.9	25.1	25.4	25.7	25.4	25.1	24.9	24.6	36.0	58.9	81.8
107.5°	132.4	115.1	97.8	80.6	97.8	115.1	132.4	149.7	166.8	183.5	200.3
110°	215.9	197.3	178.8	160.3	178.8	197.3	215.9	234.4	245.8	250.1	254.4



TEST NUMBER: P332474-927

CATALOG NUMBER: S123RDIW-S1165D755U927-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	286.8	282.9	278.9	275.0	278.9	282.9	286.8	290.7	292.6	292.6	292.5
115°	341.2	341.7	342.2	342.8	342.2	341.7	341.2	340.7	339.8	338.5	337.2
117.5°	380.5	380.6	380.6	380.8	380.6	380.6	380.5	380.3	379.8	378.7	377.7
120°	406.9	406.9	406.9	406.9	406.9	406.9	406.9	406.9	406.4	405.4	404.3
122.5°	432.2	432.3	432.5	432.5	432.5	432.3	432.2	432.1	431.7	430.9	430.2
125°	467.9	468.2	468.4	468.7	468.4	468.2	467.9	467.6	467.4	467.1	466.8
127.5°	504.2	503.9	503.7	503.4	503.7	503.9	504.2	504.5	504.4	504.0	503.6
130°	526.6	526.3	526.1	525.8	526.1	526.3	526.6	526.9	526.7	526.2	525.7
132.5°	547.4	547.1	546.7	546.3	546.7	547.1	547.4	547.8	547.7	547.2	546.7
135°	578.8	578.5	578.1	577.7	578.1	578.5	578.8	579.2	579.2	578.8	578.5
137.5°	608.0	607.7	607.4	607.2	607.4	607.7	608.0	608.2	608.1	607.4	606.8
140°	625.7	625.4	625.2	624.9	625.2	625.4	625.7	626.0	625.8	625.3	624.8
142.5°	642.3	642.0	641.6	641.2	641.6	642.0	642.3	642.7	642.6	642.2	641.8
145°	666.3	666.3	666.3	666.3	666.3	666.3	666.3	666.3	666.1	665.9	665.7
147.5°	686.7	686.1	685.6	684.9	685.6	686.1	686.7	687.3	687.5	687.2	687.0
150°	700.1	699.7	699.3	698.9	699.3	699.7	700.1	700.5	700.5	700.3	700.1
152.5°	711.9	711.3	710.7	710.1	710.7	711.3	711.9	712.5	712.6	712.1	711.6
155°	728.1	727.3	726.5	725.7	726.5	727.3	728.1	728.9	729.0	728.3	727.6
157.5°	742.0	740.9	740.0	738.9	740.0	740.9	742.0	743.0	743.1	742.3	741.6
160°	750.0	749.2	748.2	747.3	748.2	749.2	750.0	751.0	751.0	750.3	749.5
162.5°	757.6	756.9	756.1	755.3	756.1	756.9	757.6	758.4	758.4	757.6	756.7
165°	767.5	766.6	765.7	764.8	765.7	766.6	767.5	768.4	768.3	767.3	766.3
167.5°	774.8	773.7	772.7	771.7	772.7	773.7	774.8	775.9	775.9	774.8	773.7
170°	779.0	777.9	776.9	775.9	776.9	777.9	779.0	780.1	780.1	779.0	777.9
172.5°	781.6	780.5	779.3	778.2	779.3	780.5	781.6	782.8	782.8	781.8	780.8
175°	784.8	783.8	782.8	781.7	782.8	783.8	784.8	785.8	785.9	785.1	784.1
177.5°	785.8	784.8	783.8	782.8	783.8	784.8	785.8	786.9	787.0	786.2	785.4
180°	784.7	784.7	784.7	784.7	784.7	784.7	784.7	784.7	784.7	784.7	784.7



TEST NUMBER: P332474-927

CATALOG NUMBER: S123RDIW-S1165D755U927-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1454.4	1454.4	1454.4	1454.4	1454.4	1454.4	1454.4	1454.4	1454.4	1454.4	1454.4
2.5°	1388.2	1395.2	1402.2	1408.7	1418.6	1423.1	1429.6	1432.0	1439.6	1450.5	1459.4
5°	1303.8	1313.8	1326.8	1337.4	1354.2	1367.3	1381.6	1395.3	1411.5	1434.6	1455.1
7.5°	1232.2	1242.1	1257.7	1277.4	1295.9	1314.5	1334.0	1352.7	1375.9	1408.9	1441.6
10°	1184.9	1196.7	1215.4	1236.5	1259.6	1277.6	1300.7	1324.4	1353.0	1391.0	1430.2
12.5°	1144.0	1152.9	1174.6	1194.7	1220.8	1243.8	1266.3	1294.0	1326.6	1367.1	1414.2
15°	1079.0	1091.5	1112.6	1135.0	1162.4	1186.8	1216.0	1249.6	1281.4	1331.2	1388.5
17.5°	1013.8	1032.7	1054.7	1080.0	1100.3	1133.8	1165.5	1200.1	1239.1	1292.0	1354.9
20°	971.9	986.9	1007.4	1044.2	1071.0	1096.5	1125.7	1168.7	1204.8	1264.6	1329.9
22.5°	936.6	947.5	970.6	1000.8	1032.1	1061.6	1091.3	1132.3	1176.9	1233.7	1304.6
25°	884.2	901.6	919.0	940.8	974.4	1009.9	1042.3	1077.1	1124.5	1184.9	1261.5
27.5°	833.0	848.7	865.9	892.7	918.2	951.4	985.2	1025.2	1076.0	1140.0	1217.6
30°	800.1	811.9	828.1	862.4	885.3	914.0	953.9	989.4	1036.6	1104.5	1186.8
32.5°	766.2	781.5	799.2	825.5	854.0	881.1	917.5	956.0	1004.3	1071.2	1155.3
35°	717.9	735.9	754.0	773.3	801.9	830.0	860.5	902.9	952.0	1016.8	1099.5
37.5°	673.4	688.0	702.7	726.6	753.8	780.4	808.9	850.6	897.0	966.9	1042.7
40°	645.1	658.1	669.3	694.3	720.4	749.0	777.1	813.8	863.6	929.0	1002.4
42.5°	614.2	626.2	641.4	661.9	690.0	714.2	742.2	776.9	823.7	890.1	954.6
45°	567.8	581.5	594.6	613.9	641.9	665.6	690.5	723.5	771.4	826.2	883.5
47.5°	519.7	533.4	548.3	567.0	591.4	615.4	640.3	669.6	713.3	767.1	805.6
50°	488.8	499.9	514.9	533.6	556.0	581.5	604.0	635.7	677.4	719.8	753.4
52.5°	456.9	467.1	484.0	503.7	524.7	546.7	570.6	597.9	635.6	675.4	702.1
55°	407.2	419.6	434.0	453.3	473.8	492.5	515.6	543.6	573.5	603.3	621.4
57.5°	360.8	371.1	383.2	403.1	420.9	443.2	463.8	485.7	513.3	535.8	547.6
60°	326.9	336.2	351.8	369.2	386.0	405.4	429.0	450.8	472.0	490.0	499.3
62.5°	295.0	305.9	319.4	335.3	353.6	371.9	392.6	410.9	429.6	445.2	451.5
65°	253.4	262.1	272.1	287.0	302.0	320.7	336.8	355.5	369.2	378.0	383.6
67.5°	215.6	221.3	228.9	238.8	253.5	269.8	285.5	300.1	311.6	317.5	322.5
70°	191.2	194.9	200.5	210.5	221.7	236.0	252.2	262.8	272.7	277.7	282.7
72.5°	166.8	171.5	176.6	184.6	193.8	204.1	215.8	228.9	234.3	240.3	243.4
75°	126.4	133.2	140.1	145.0	151.3	159.4	170.0	178.1	181.2	186.2	186.8
77.5°	95.4	96.9	101.9	108.1	113.3	119.1	125.9	133.1	134.6	137.2	138.9
80°	78.4	78.4	78.4	82.1	88.4	92.8	99.0	102.7	105.2	105.8	106.5
82.5°	63.0	63.0	62.5	63.3	65.5	67.9	73.6	77.8	79.9	79.5	78.1
85°	41.1	39.8	39.8	39.2	39.8	38.6	37.9	40.5	44.2	44.2	42.9
87.5°	19.8	19.3	19.4	18.5	17.7	16.9	15.1	15.4	15.1	16.8	16.1
90°	14.5	14.0	12.3	10.6	9.0	7.3	5.8	4.4	3.2	1.9	0.6
92.5°	15.8	14.9	13.6	12.4	11.1	9.8	9.4	9.7	10.1	10.5	10.9
95°	19.0	18.1	16.6	15.2	13.8	12.4	14.3	19.6	25.0	30.3	35.6
97.5°	19.8	18.8	28.1	37.4	46.7	56.1	61.9	64.3	66.7	69.1	71.5
100°	20.3	19.3	39.5	59.7	79.9	100.1	108.8	106.3	103.7	101.1	98.5
102.5°	35.2	38.3	60.4	82.5	104.6	126.7	136.7	134.9	133.0	131.2	129.3
105°	104.7	127.7	139.3	151.0	162.6	174.3	179.4	178.0	176.6	175.2	173.7
107.5°	217.1	234.0	232.2	230.3	228.5	226.6	225.1	224.0	222.8	221.7	220.5
110°	258.6	262.9	261.5	260.1	258.6	257.2	256.0	254.9	253.9	252.9	251.8



TEST NUMBER: P332474-927

CATALOG NUMBER: S123RDIW-S1165D755U927-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	292.4	292.3	290.9	289.5	288.0	286.6	285.4	284.5	283.5	282.6	281.7
115°	335.9	334.6	333.4	332.2	331.1	329.9	329.0	328.2	327.4	326.6	325.8
117.5°	376.7	375.7	375.0	374.5	373.8	373.3	372.5	371.5	370.6	369.6	368.7
120°	403.3	402.2	401.9	401.5	401.1	400.7	399.9	398.7	397.6	396.4	395.2
122.5°	429.5	428.8	428.3	427.9	427.3	426.8	426.1	425.2	424.2	423.3	422.3
125°	466.6	466.4	465.8	465.3	464.8	464.3	463.5	462.5	461.4	460.4	459.4
127.5°	503.1	502.7	502.1	501.5	500.9	500.3	499.4	498.4	497.3	496.3	495.3
130°	525.1	524.7	524.1	523.6	523.1	522.6	521.8	520.8	519.8	518.7	517.6
132.5°	546.1	545.7	545.2	544.8	544.4	544.0	543.3	542.2	541.1	540.1	539.1
135°	578.1	577.7	577.2	576.6	576.2	575.6	575.0	574.2	573.4	572.7	571.9
137.5°	606.2	605.5	605.3	605.0	604.7	604.4	603.8	602.8	601.8	600.8	599.8
140°	624.2	623.8	623.4	623.0	622.6	622.2	621.6	620.8	620.0	619.2	618.5
142.5°	641.4	641.0	640.6	640.2	639.8	639.4	638.9	638.1	637.3	636.5	635.7
145°	665.4	665.1	664.9	664.6	664.3	664.1	663.5	662.6	661.7	660.8	659.9
147.5°	686.7	686.4	686.2	686.0	685.7	685.4	685.0	684.4	683.8	683.2	682.6
150°	699.8	699.5	699.3	699.0	698.8	698.5	698.2	697.8	697.4	697.0	696.6
152.5°	711.1	710.7	710.6	710.4	710.3	710.1	710.0	709.7	709.6	709.4	709.2
155°	727.0	726.4	726.2	726.1	726.0	725.8	725.9	726.1	726.4	726.7	726.9
157.5°	740.8	740.0	740.1	740.2	740.4	740.5	740.6	740.6	740.6	740.7	740.7
160°	748.7	747.9	748.1	748.1	748.3	748.5	748.5	748.7	748.8	748.9	749.1
162.5°	755.8	754.9	755.0	755.2	755.3	755.4	755.7	756.0	756.3	756.7	757.0
165°	765.2	764.2	764.4	764.5	764.6	764.8	765.0	765.4	765.8	766.2	766.6
167.5°	772.7	771.7	771.7	771.7	771.7	771.7	772.0	772.5	773.0	773.5	774.0
170°	776.9	775.9	775.9	775.9	775.9	775.9	776.2	776.7	777.2	777.7	778.2
172.5°	779.7	778.7	778.6	778.5	778.4	778.2	778.6	779.2	779.7	780.4	781.0
175°	783.2	782.3	782.2	782.0	781.9	781.8	782.0	782.7	783.3	783.9	784.7
177.5°	784.5	783.7	783.6	783.5	783.4	783.3	783.5	784.0	784.5	785.1	785.5
180°	784.7	784.7	784.7	784.7	784.7	784.7	784.7	784.7	784.7	784.7	784.7



TEST NUMBER: P332474-927

CATALOG NUMBER: S123RDIW-S1165D755U927-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1454.4	1454.4	1454.4	1454.4	1454.4	1454.4	1454.4	1454.4	1454.4	1454.4	1454.4
2.5°	1462.4	1467.9	1474.9	1485.3	1493.3	1500.3	1501.8	1503.8	1508.8	1517.2	1523.7
5°	1471.9	1486.2	1509.3	1531.7	1555.9	1575.9	1594.6	1607.7	1620.1	1646.2	1667.4
7.5°	1468.9	1500.8	1536.9	1577.2	1617.9	1657.3	1693.9	1726.6	1759.3	1797.4	1840.9
10°	1466.9	1504.3	1552.8	1604.5	1661.2	1716.6	1770.1	1811.9	1860.4	1904.0	1959.4
12.5°	1457.5	1511.2	1569.3	1635.4	1705.0	1768.9	1839.4	1897.0	1952.6	2015.5	2080.0
15°	1445.1	1510.5	1584.0	1671.7	1777.6	1854.8	1927.1	2027.3	2095.8	2164.2	2256.5
17.5°	1422.6	1502.4	1594.2	1708.3	1796.5	1900.3	2009.0	2088.2	2180.5	2277.0	2360.4
20°	1404.6	1497.5	1600.1	1712.2	1825.0	1937.6	2042.9	2137.5	2232.8	2344.2	2412.7
22.5°	1386.7	1478.5	1585.2	1704.3	1825.4	1944.1	2063.2	2174.4	2281.6	2394.1	2481.4
25°	1348.6	1457.6	1573.4	1694.8	1814.3	1945.1	2087.1	2211.0	2343.6	2459.4	2542.2
27.5°	1310.0	1409.8	1525.2	1648.4	1781.2	1935.8	2102.8	2243.6	2376.5	2459.4	2485.4
30°	1275.2	1381.0	1486.8	1612.0	1755.8	1928.3	2105.7	2267.0	2376.0	2412.0	2385.3
32.5°	1239.8	1335.7	1440.5	1568.7	1721.4	1909.9	2109.7	2253.0	2318.6	2291.1	2182.1
35°	1177.4	1263.9	1365.4	1493.7	1669.3	1899.7	2093.3	2190.4	2174.2	2018.6	1813.1
37.5°	1110.6	1181.1	1275.2	1409.3	1615.3	1859.2	2022.5	2036.9	1896.8	1657.8	1420.5
40°	1057.9	1121.3	1217.9	1358.0	1573.4	1819.3	1951.3	1893.4	1676.1	1410.2	1212.3
42.5°	1006.5	1060.1	1153.1	1304.2	1533.5	1765.1	1845.2	1719.1	1468.4	1217.0	1037.0
45°	919.6	970.0	1063.4	1218.5	1452.0	1661.2	1650.6	1431.4	1180.5	978.2	828.7
47.5°	837.2	881.3	968.9	1127.2	1356.2	1505.5	1406.5	1173.3	960.4	798.1	691.5
50°	778.9	822.5	909.7	1066.0	1279.5	1388.5	1247.1	1022.4	827.5	693.0	608.3
52.5°	723.1	765.7	845.4	997.7	1186.8	1252.0	1100.2	891.8	729.4	613.3	540.6
55°	645.1	677.4	749.0	894.7	1036.1	1051.0	897.2	722.9	589.0	508.1	458.3
57.5°	565.5	593.3	664.1	780.1	879.2	871.6	725.7	575.0	484.8	424.6	388.5
60°	513.7	541.1	603.3	703.0	777.7	751.5	617.7	496.2	419.1	374.9	346.2
62.5°	465.3	486.8	545.0	617.7	671.5	641.9	528.0	427.5	366.2	329.0	306.3
65°	395.4	412.8	459.5	497.5	527.4	498.8	404.1	334.4	290.2	264.0	248.4
67.5°	328.8	339.9	369.5	383.2	404.3	372.8	303.9	257.1	232.0	209.9	199.2
70°	287.0	295.1	310.7	321.9	327.5	295.1	244.1	209.8	188.6	173.1	166.3
72.5°	245.2	252.3	255.4	264.6	261.7	231.4	196.2	169.0	153.8	143.2	134.4
75°	187.4	190.5	187.4	183.7	175.5	154.4	130.2	116.5	105.2	100.2	97.1
77.5°	136.6	135.6	131.3	125.6	111.7	98.4	85.3	80.7	75.8	73.2	72.1
80°	105.2	102.7	99.0	89.7	77.8	68.5	65.4	62.3	60.4	57.3	56.6
82.5°	78.3	76.8	70.6	62.7	54.4	50.1	47.5	46.3	44.4	42.9	42.7
85°	41.7	39.8	33.0	28.7	27.4	26.1	25.5	25.5	23.1	22.4	22.4
87.5°	13.9	11.1	10.9	9.6	9.9	9.3	10.1	9.4	9.3	9.9	9.0
90°	1.9	3.2	4.4	5.8	7.3	9.0	10.6	12.3	14.0	14.5	15.1
92.5°	10.5	10.1	9.7	9.4	9.8	11.1	12.4	13.6	14.9	15.8	16.6
95°	30.3	25.0	19.6	14.3	12.4	13.8	15.2	16.6	18.1	19.0	19.9
97.5°	69.1	66.7	64.3	61.9	56.1	46.7	37.4	28.1	18.8	19.8	20.8
100°	101.1	103.7	106.3	108.8	100.1	79.9	59.7	39.5	19.3	20.3	21.3
102.5°	131.2	133.0	134.9	136.7	126.7	104.6	82.5	60.4	38.3	35.2	31.9
105°	175.2	176.6	178.0	179.4	174.3	162.6	151.0	139.3	127.7	104.7	81.8
107.5°	221.7	222.8	224.0	225.1	226.6	228.5	230.3	232.2	234.0	217.1	200.3
110°	252.9	253.9	254.9	256.0	257.2	258.6	260.1	261.5	262.9	258.6	254.4





TEST NUMBER: P332474-927

CATALOG NUMBER: S123RDIW-S1165D755U927-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	282.6	283.5	284.5	285.4	286.6	288.0	289.5	290.9	292.3	292.4	292.5
115°	326.6	327.4	328.2	329.0	329.9	331.1	332.2	333.4	334.6	335.9	337.2
117.5°	369.6	370.6	371.5	372.5	373.3	373.8	374.5	375.0	375.7	376.7	377.7
120°	396.4	397.6	398.7	399.9	400.7	401.1	401.5	401.9	402.2	403.3	404.3
122.5°	423.3	424.2	425.2	426.1	426.8	427.3	427.9	428.3	428.8	429.5	430.2
125°	460.4	461.4	462.5	463.5	464.3	464.8	465.3	465.8	466.4	466.6	466.8
127.5°	496.3	497.3	498.4	499.4	500.3	500.9	501.5	502.1	502.7	503.1	503.6
130°	518.7	519.8	520.8	521.8	522.6	523.1	523.6	524.1	524.7	525.1	525.7
132.5°	540.1	541.1	542.2	543.3	544.0	544.4	544.8	545.2	545.7	546.1	546.7
135°	572.7	573.4	574.2	575.0	575.6	576.2	576.6	577.2	577.7	578.1	578.5
137.5°	600.8	601.8	602.8	603.8	604.4	604.7	605.0	605.3	605.5	606.2	606.8
140°	619.2	620.0	620.8	621.6	622.2	622.6	623.0	623.4	623.8	624.2	624.8
142.5°	636.5	637.3	638.1	638.9	639.4	639.8	640.2	640.6	641.0	641.4	641.8
145°	660.8	661.7	662.6	663.5	664.1	664.3	664.6	664.9	665.1	665.4	665.7
147.5°	683.2	683.8	684.4	685.0	685.4	685.7	686.0	686.2	686.4	686.7	687.0
150°	697.0	697.4	697.8	698.2	698.5	698.8	699.0	699.3	699.5	699.8	700.1
152.5°	709.4	709.6	709.7	710.0	710.1	710.3	710.4	710.6	710.7	711.1	711.6
155°	726.7	726.4	726.1	725.9	725.8	726.0	726.1	726.2	726.4	727.0	727.6
157.5°	740.7	740.6	740.6	740.6	740.5	740.4	740.2	740.1	740.0	740.8	741.6
160°	748.9	748.8	748.7	748.5	748.5	748.3	748.1	748.1	747.9	748.7	749.5
162.5°	756.7	756.3	756.0	755.7	755.4	755.3	755.2	755.0	754.9	755.8	756.7
165°	766.2	765.8	765.4	765.0	764.8	764.6	764.5	764.4	764.2	765.2	766.3
167.5°	773.5	773.0	772.5	772.0	771.7	771.7	771.7	771.7	771.7	772.7	773.7
170°	777.7	777.2	776.7	776.2	775.9	775.9	775.9	775.9	775.9	776.9	777.9
172.5°	780.4	779.7	779.2	778.6	778.2	778.4	778.5	778.6	778.7	779.7	780.8
175°	783.9	783.3	782.7	782.0	781.8	781.9	782.0	782.2	782.3	783.2	784.1
177.5°	785.1	784.5	784.0	783.5	783.3	783.4	783.5	783.6	783.7	784.5	785.4
180°	784.7	784.7	784.7	784.7	784.7	784.7	784.7	784.7	784.7	784.7	784.7



TEST NUMBER: P332474-927

CATALOG NUMBER: S123RDIW-S1165D755U927-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	1454.4	1454.4	1454.4	1454.4	1454.4	1454.4	1454.4
2.5°	1534.1	1534.1	1536.1	1543.6	1544.6	1551.1	1549.1
5°	1686.1	1697.9	1702.2	1720.9	1732.2	1737.2	1727.2
7.5°	1871.8	1905.3	1921.0	1940.6	1958.0	1963.2	1949.6
10°	2007.4	2042.2	2071.5	2089.5	2106.3	2117.6	2131.9
12.5°	2138.3	2181.2	2209.0	2234.5	2251.8	2266.0	2268.3
15°	2280.7	2345.4	2394.6	2430.7	2448.8	2458.1	2454.4
17.5°	2424.2	2484.3	2519.3	2556.1	2581.2	2582.4	2583.1
20°	2505.4	2564.0	2604.5	2631.9	2659.9	2658.6	2664.8
22.5°	2559.8	2605.8	2636.9	2656.7	2666.3	2661.7	2662.8
25°	2585.1	2598.8	2593.3	2561.5	2553.4	2524.1	2529.1
27.5°	2454.2	2389.4	2322.4	2236.3	2168.3	2113.9	2116.7
30°	2276.3	2161.8	2031.0	1921.4	1823.0	1795.6	1737.2
32.5°	2027.7	1855.9	1702.8	1600.7	1516.2	1493.3	1442.2
35°	1606.4	1439.6	1282.0	1187.3	1150.0	1097.7	1097.1
37.5°	1248.6	1101.7	1018.4	947.4	910.1	878.5	875.4
40°	1050.4	935.8	872.9	821.9	785.1	761.4	755.9
42.5°	911.9	819.3	760.3	728.7	700.4	688.2	679.1
45°	744.7	682.4	641.3	612.7	599.6	590.3	585.3
47.5°	622.9	581.1	553.2	534.1	523.5	513.7	516.3
50°	556.7	522.4	501.8	483.8	475.7	468.8	469.4
52.5°	503.4	472.6	456.0	442.9	432.8	428.0	425.6
55°	427.1	407.8	391.0	381.7	376.0	369.2	367.3
57.5°	364.3	349.4	335.7	325.1	323.8	317.2	318.1
60°	322.5	310.1	298.9	293.3	288.9	283.3	285.2
62.5°	288.1	277.7	267.5	262.8	258.5	254.4	255.2
65°	236.0	226.0	219.8	217.3	215.4	213.6	211.7
67.5°	188.1	182.0	178.1	172.7	168.9	168.3	166.4
70°	158.1	150.0	143.2	136.3	134.5	133.9	134.5
72.5°	126.7	121.7	119.8	116.5	116.1	114.5	115.6
75°	95.3	93.4	92.1	89.7	89.7	89.7	89.7
77.5°	70.3	69.1	68.4	67.9	67.3	66.4	66.2
80°	54.8	54.2	52.9	52.9	52.3	52.9	52.3
82.5°	41.4	41.2	40.0	40.0	39.4	39.0	39.4
85°	21.2	20.5	21.8	20.5	21.2	20.0	21.2
87.5°	9.1	9.2	8.8	8.8	8.4	9.4	8.5
90°	15.5	16.1	16.5	16.7	17.0	17.2	17.5
92.5°	17.4	18.2	18.7	18.9	19.0	19.2	19.3
95°	20.8	21.7	22.2	22.2	22.2	22.2	22.2
97.5°	21.9	22.9	23.5	23.6	23.8	23.9	24.0
100°	22.3	23.4	24.0	24.1	24.2	24.3	24.5
102.5°	28.8	25.5	24.0	24.2	24.5	24.7	25.0
105°	58.9	36.0	24.6	24.9	25.1	25.4	25.7
107.5°	183.5	166.8	149.7	132.4	115.1	97.8	80.6
110°	250.1	245.8	234.4	215.9	197.3	178.8	160.3



TEST NUMBER: P332474-927

CATALOG NUMBER: S123RDIW-S1165D755U927-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	292.6	292.6	290.7	286.8	282.9	278.9	275.0
115°	338.5	339.8	340.7	341.2	341.7	342.2	342.8
117.5°	378.7	379.8	380.3	380.5	380.6	380.6	380.8
120°	405.4	406.4	406.9	406.9	406.9	406.9	406.9
122.5°	430.9	431.7	432.1	432.2	432.3	432.5	432.5
125°	467.1	467.4	467.6	467.9	468.2	468.4	468.7
127.5°	504.0	504.4	504.5	504.2	503.9	503.7	503.4
130°	526.2	526.7	526.9	526.6	526.3	526.1	525.8
132.5°	547.2	547.7	547.8	547.4	547.1	546.7	546.3
135°	578.8	579.2	579.2	578.8	578.5	578.1	577.7
137.5°	607.4	608.1	608.2	608.0	607.7	607.4	607.2
140°	625.3	625.8	626.0	625.7	625.4	625.2	624.9
142.5°	642.2	642.6	642.7	642.3	642.0	641.6	641.2
145°	665.9	666.1	666.3	666.3	666.3	666.3	666.3
147.5°	687.2	687.5	687.3	686.7	686.1	685.6	684.9
150°	700.3	700.5	700.5	700.1	699.7	699.3	698.9
152.5°	712.1	712.6	712.5	711.9	711.3	710.7	710.1
155°	728.3	729.0	728.9	728.1	727.3	726.5	725.7
157.5°	742.3	743.1	743.0	742.0	740.9	740.0	738.9
160°	750.3	751.0	751.0	750.0	749.2	748.2	747.3
162.5°	757.6	758.4	758.4	757.6	756.9	756.1	755.3
165°	767.3	768.3	768.4	767.5	766.6	765.7	764.8
167.5°	774.8	775.9	775.9	774.8	773.7	772.7	771.7
170°	779.0	780.1	780.1	779.0	777.9	776.9	775.9
172.5°	781.8	782.8	782.8	781.6	780.5	779.3	778.2
175°	785.1	785.9	785.8	784.8	783.8	782.8	781.7
177.5°	786.2	787.0	786.9	785.8	784.8	783.8	782.8
180°	784.7	784.7	784.7	784.7	784.7	784.7	784.7

(END OF REPORT)