

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331857-840

Luminaire Tested: **S122RDIW-S1005D1240U840-4F0-1E-UDD-A**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P331857-840  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S122RDIW-S1005D1240U840-4F0-1E-UDD-A  
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 1005 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING  
UPLIGHT 1240 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 8856.4 lumens  
Efficiency: N/A  
Efficacy: 116.2 lumens/watt  
Spacing Criteria (0/90/45): 0.86 / 1.16 / 1.02  
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')  
CIE Type: General Diffuse  
  
Input Watts (W): 76.2  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P331857-840

CATALOG NUMBER: S122RDIW-S1005D1240U840-4F0-1E-UDD-A

### Luminous Intensity Polar Plot





TEST NUMBER: P331857-840

CATALOG NUMBER: S122RDIW-S1005D1240U840-4F0-1E-UDD-A

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	106	106	106	106	97	97	97	97	80	80	80	64	64	64	50	50	50	44
1	97	93	89	86	89	85	82	79	71	69	67	58	56	55	45	44	44	38
2	89	82	76	71	81	75	70	66	63	59	56	51	49	47	41	39	38	33
3	82	73	66	60	74	67	61	56	56	52	48	46	43	41	37	35	33	29
4	75	65	57	52	68	60	53	48	50	46	42	42	38	35	33	31	29	25
5	69	58	51	45	63	54	47	42	45	40	37	38	34	31	30	28	26	23
6	64	52	45	39	58	49	42	37	41	36	32	34	31	28	28	25	23	20
7	59	48	40	35	54	44	38	33	38	33	29	32	28	25	26	23	21	18
8	55	43	36	31	51	40	34	29	35	29	26	29	25	22	24	21	19	17
9	51	40	33	28	47	37	31	26	32	27	23	27	23	20	22	19	17	15
10	48	37	30	25	44	34	28	24	29	25	21	25	21	19	21	18	16	14

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	35960	35960	35960	35960
5°	40161	36185	32083	36185
10°	44558	35931	27811	35931
15°	46748	35405	21912	35405
20°	40527	34625	18962	34625
25°	26580	33556	16930	33556
30°	17890	32261	15321	32261
35°	14491	30628	13819	30628
40°	12886	28854	12787	28854
45°	11663	26772	11415	26772
50°	10613	24707	10575	24707
55°	9979	22415	9847	22415
60°	8344	20315	8247	20315
65°	7037	18449	7981	18449
70°	6500	16475	7530	16475
75°	6089	14336	6949	14336
80°	5616	11799	6192	11799
85°	5169	9318	5446	9318



TEST NUMBER: P331857-840

CATALOG NUMBER: S122RDIW-S1005D1240U840-4F0-1E-UDD-A

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	211.1	2.4
10°-20°	588.3	6.6
20°-30°	758.1	8.6
30°-40°	720.4	8.1
40°-50°	617.1	7.0
50°-60°	470.0	5.3
60°-70°	297.1	3.4
70°-80°	148.4	1.7
80°-90°	42.8	0.5
90°-100°	56.9	0.6
100°-110°	208.8	2.4
110°-120°	558.2	6.3
120°-130°	921.5	10.4
130°-140°	980.0	11.1
140°-150°	910.9	10.3
150°-160°	732.3	8.3
160°-170°	471.9	5.3
170°-180°	162.4	1.8
0°-30°	1557.5	17.6
0°-40°	2277.9	25.7
0°-60°	3365.0	38.0
0°-90°	3853.3	43.5
90°-120°	824.0	9.3
90°-150°	3636.4	41.1
90°-180°	5003.0	56.5
0°-180°	8856.4	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	2227	2227	2227	2227	2227	
5°	2478	2233	1980	2233	2478	245
15°	2797	2118	1311	2118	2797	754
25°	1492	1884	950	1884	1492	708
35°	735	1554	701	1554	735	470
45°	511	1172	500	1172	511	395
55°	354	796	350	796	354	311
65°	184	483	209	483	184	187
75°	98	230	111	230	98	103
85°	28	50	29	50	28	31
90°	33	1	33	1	33	16
95°	53	80	53	80	53	50
105°	94	376	94	376	94	98
115°	101	710	101	710	101	254
125°	1056	1004	1056	1004	1056	914
135°	1284	1243	1284	1243	1284	989
145°	1464	1442	1464	1442	1464	915
155°	1589	1587	1589	1587	1589	733
165°	1669	1673	1669	1673	1669	471
175°	1701	1711	1701	1711	1701	162
180°	1707	1707	1707	1707	1707	



TEST NUMBER: P331857-840

CATALOG NUMBER: S122RDIW-S1005D1240U840-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	2227.2	2227.2	2227.2	2227.2	2227.2	2227.2	2227.2	2227.2	2227.2	2227.2	2227.2
2.5°	2317.5	2319.5	2321.3	2316.9	2316.9	2313.2	2305.2	2299.0	2281.7	2279.2	2279.2
5°	2477.9	2476.4	2479.4	2469.4	2455.5	2452.4	2437.7	2418.3	2398.2	2375.8	2371.2
7.5°	2637.4	2635.0	2628.8	2627.2	2616.5	2593.0	2569.4	2544.2	2510.7	2478.1	2461.6
10°	2717.8	2743.4	2727.8	2700.8	2706.2	2669.9	2650.5	2617.3	2589.4	2540.6	2529.8
12.5°	2797.0	2807.1	2802.2	2786.8	2779.9	2754.6	2728.5	2699.6	2648.2	2604.3	2566.3
15°	2796.7	2811.5	2815.3	2810.7	2814.6	2813.0	2799.0	2775.1	2730.2	2682.2	2640.4
17.5°	2590.3	2600.5	2625.9	2643.0	2664.7	2710.6	2733.1	2742.0	2735.3	2708.0	2678.5
20°	2358.7	2341.7	2412.9	2449.3	2480.2	2557.6	2624.1	2649.7	2690.7	2690.0	2682.2
22.5°	2030.6	2034.7	2102.1	2145.4	2235.7	2313.1	2388.9	2485.1	2564.5	2616.9	2647.6
25°	1492.0	1521.5	1588.7	1647.6	1748.2	1892.1	2022.9	2174.5	2317.7	2430.7	2538.3
27.5°	1120.5	1122.8	1176.1	1230.4	1290.2	1408.2	1572.8	1753.9	1958.0	2126.5	2320.2
30°	959.6	954.9	977.3	1010.7	1061.8	1153.1	1276.9	1454.9	1658.4	1912.2	2138.2
32.5°	845.7	846.0	862.8	887.5	929.9	991.5	1076.3	1220.8	1413.2	1662.7	1927.7
35°	735.2	734.4	746.8	764.6	782.3	821.8	879.9	955.7	1088.0	1321.0	1591.9
37.5°	655.9	659.3	665.4	676.5	696.2	718.1	753.0	803.9	898.2	1035.9	1263.5
40°	611.4	612.9	621.4	630.7	642.3	659.3	687.9	729.0	797.9	907.8	1074.1
42.5°	570.5	572.1	578.0	586.7	595.9	612.9	636.6	672.1	727.9	813.6	950.9
45°	510.8	510.8	516.1	520.1	530.1	545.5	564.9	594.3	633.0	696.5	787.8
47.5°	454.7	454.8	458.5	465.1	471.4	483.5	502.5	526.5	554.7	603.8	681.8
50°	422.5	423.3	425.7	431.0	434.9	445.8	460.5	481.3	510.8	548.7	613.7
52.5°	396.6	396.1	399.0	401.3	403.9	411.7	422.7	441.1	467.4	500.4	554.2
55°	354.5	351.3	356.0	359.8	362.1	365.3	371.4	383.0	405.5	433.3	473.6
57.5°	301.8	300.5	303.9	307.4	314.7	323.1	328.3	335.7	347.3	367.3	407.2
60°	258.4	258.4	265.4	267.7	276.3	287.1	297.9	304.2	315.8	328.9	358.3
62.5°	220.0	220.8	224.0	226.3	231.1	244.4	259.5	273.2	284.2	296.7	316.2
65°	184.2	185.7	185.7	187.2	190.4	193.5	199.7	210.5	229.8	247.6	262.4
67.5°	156.3	156.8	157.2	158.8	159.6	163.0	165.4	170.3	174.7	191.6	209.8
70°	137.7	140.1	139.3	140.9	141.6	143.2	146.2	148.6	155.5	159.5	170.3
72.5°	120.4	122.1	122.0	122.9	124.9	125.2	127.6	130.0	134.5	137.7	143.6
75°	97.6	96.7	97.6	99.1	99.9	100.6	100.6	103.7	106.0	109.1	113.0
77.5°	75.2	76.0	75.8	76.0	76.1	77.6	77.4	78.8	81.1	82.6	84.5
80°	60.4	61.1	60.4	61.1	61.9	62.7	61.9	62.7	65.0	66.6	66.6
82.5°	46.8	46.9	47.4	47.6	47.7	47.9	48.9	49.1	50.8	50.5	51.1
85°	27.9	27.1	27.1	27.1	27.9	28.7	27.9	27.9	28.7	28.7	28.7
87.5°	16.6	17.1	17.0	16.9	16.8	16.6	16.3	16.7	15.8	16.1	15.0
90°	33.3	32.8	32.2	31.7	31.2	30.2	28.8	27.5	26.1	24.7	22.5
92.5°	33.3	33.0	32.7	32.3	32.0	31.5	30.8	30.1	29.4	28.7	27.6
95°	53.1	53.4	53.6	53.9	54.2	53.6	52.3	50.9	49.6	48.2	46.3
97.5°	70.9	70.6	70.3	69.9	69.6	68.9	67.8	66.7	65.5	64.5	60.1
100°	82.8	82.2	81.7	81.1	80.6	79.2	77.0	74.8	72.6	70.4	65.7
102.5°	88.7	88.0	87.2	86.3	85.6	83.8	81.0	78.1	75.2	72.4	111.4
105°	93.9	92.8	91.7	90.6	89.5	87.5	84.4	81.4	78.4	75.3	150.3
107.5°	96.6	95.5	94.4	93.3	92.2	93.2	96.2	99.4	102.4	105.5	195.4
110°	97.6	96.5	95.4	94.3	93.2	106.3	133.8	161.3	188.7	216.2	295.5



TEST NUMBER: P331857-840

CATALOG NUMBER: S122RDIW-S1005D1240U840-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	98.6	97.7	96.8	95.9	95.0	144.7	244.9	345.0	445.1	545.2	564.9
115°	101.3	121.1	140.9	160.6	180.4	253.8	380.9	508.0	635.1	762.2	755.4
117.5°	413.5	478.6	543.5	608.4	673.4	721.2	751.9	782.7	813.4	844.2	839.5
120°	753.6	790.6	827.7	864.7	901.8	918.7	915.3	912.1	908.8	905.4	900.6
122.5°	940.3	947.6	954.7	961.9	969.1	971.7	969.8	967.8	965.7	963.8	958.5
125°	1056.2	1055.4	1054.6	1053.7	1052.9	1051.6	1049.7	1047.7	1045.8	1043.9	1038.6
127.5°	1129.3	1129.1	1129.0	1128.8	1128.7	1127.2	1124.4	1121.6	1118.8	1116.0	1112.1
130°	1174.8	1175.1	1175.4	1175.6	1175.9	1174.5	1171.5	1168.5	1165.5	1162.5	1159.4
132.5°	1219.3	1219.5	1219.8	1220.1	1220.3	1219.2	1216.6	1214.1	1211.4	1208.9	1205.9
135°	1283.5	1284.0	1284.6	1285.2	1285.7	1284.6	1281.8	1279.1	1276.4	1273.6	1271.1
137.5°	1342.0	1343.0	1343.9	1344.8	1345.7	1344.9	1342.2	1339.5	1336.9	1334.1	1331.3
140°	1378.7	1380.0	1381.4	1382.7	1384.1	1383.6	1381.1	1378.7	1376.1	1373.7	1370.7
142.5°	1414.2	1415.5	1416.9	1418.4	1419.7	1419.3	1417.0	1414.7	1412.5	1410.3	1406.7
145°	1463.9	1465.2	1466.6	1467.9	1469.4	1469.1	1467.1	1465.2	1463.3	1461.4	1456.7
147.5°	1507.6	1508.7	1509.8	1511.1	1512.2	1512.1	1510.7	1509.2	1507.8	1506.3	1501.8
150°	1534.3	1535.6	1537.0	1538.4	1539.7	1539.6	1538.0	1536.3	1534.7	1533.1	1528.6
152.5°	1557.0	1558.8	1560.6	1562.5	1564.3	1564.4	1562.7	1561.0	1559.4	1557.7	1553.6
155°	1588.6	1590.8	1593.1	1595.2	1597.4	1597.7	1596.1	1594.4	1592.8	1591.1	1587.8
157.5°	1617.5	1619.7	1621.8	1624.0	1626.1	1626.3	1624.4	1622.6	1620.6	1618.8	1616.5
160°	1634.4	1636.3	1638.2	1640.1	1642.0	1642.1	1640.5	1638.9	1637.2	1635.6	1634.0
162.5°	1648.2	1650.5	1652.8	1655.3	1657.6	1657.9	1656.0	1654.2	1652.2	1650.4	1649.0
165°	1668.9	1670.8	1672.7	1674.7	1676.6	1676.6	1674.7	1672.7	1670.8	1668.9	1668.1
167.5°	1682.0	1684.5	1687.0	1689.4	1691.9	1692.1	1690.2	1688.3	1686.4	1684.5	1683.7
170°	1689.9	1692.4	1694.9	1697.4	1699.8	1700.1	1698.2	1696.3	1694.4	1692.4	1691.8
172.5°	1695.9	1698.3	1700.8	1703.2	1705.8	1706.0	1704.0	1702.1	1700.2	1698.3	1697.8
175°	1701.0	1703.7	1706.6	1709.3	1712.0	1712.4	1710.5	1708.6	1706.7	1704.8	1704.2
177.5°	1704.2	1706.3	1708.2	1710.2	1712.1	1712.4	1710.8	1709.3	1707.8	1706.3	1706.0
180°	1707.2	1707.2	1707.2	1707.2	1707.2	1707.2	1707.2	1707.2	1707.2	1707.2	1707.2



TEST NUMBER: P331857-840

CATALOG NUMBER: S122RDIW-S1005D1240U840-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	2227.2	2227.2	2227.2	2227.2	2227.2	2227.2	2227.2	2227.2	2227.2	2227.2	2227.2
2.5°	2280.5	2275.4	2271.2	2260.0	2254.4	2242.0	2240.2	2239.6	2223.5	2208.0	2203.6
5°	2358.7	2346.3	2327.8	2306.1	2283.7	2260.5	2245.0	2232.6	2201.6	2172.2	2155.3
7.5°	2437.7	2411.1	2379.0	2338.0	2303.8	2265.4	2237.0	2211.4	2167.5	2125.4	2097.0
10°	2496.5	2453.2	2410.5	2354.1	2310.0	2266.6	2226.4	2191.6	2142.0	2086.4	2046.9
12.5°	2533.0	2485.4	2426.7	2371.5	2314.3	2259.3	2205.3	2160.6	2102.4	2044.9	1998.0
15°	2582.4	2531.3	2460.1	2381.2	2307.6	2235.7	2173.8	2118.1	2042.3	1973.4	1916.1
17.5°	2622.8	2552.5	2476.1	2384.8	2299.7	2208.2	2128.5	2057.3	1972.9	1889.8	1822.3
20°	2635.7	2566.2	2477.9	2386.6	2286.0	2178.5	2092.5	2015.2	1924.6	1834.0	1756.7
22.5°	2627.8	2573.5	2475.5	2366.2	2263.1	2150.6	2053.6	1963.8	1863.3	1770.9	1681.1
25°	2573.1	2554.6	2461.6	2342.5	2224.8	2094.1	1981.9	1883.6	1769.1	1670.0	1572.5
27.5°	2445.7	2485.8	2428.2	2301.3	2170.5	2030.3	1904.2	1792.3	1673.4	1562.0	1464.8
30°	2323.2	2415.2	2390.5	2272.8	2126.6	1988.8	1847.2	1730.4	1603.5	1488.9	1393.0
32.5°	2155.4	2307.5	2331.7	2233.2	2082.0	1930.7	1782.2	1666.0	1533.5	1412.8	1319.3
35°	1888.2	2115.8	2220.2	2157.6	2005.9	1842.6	1689.3	1553.9	1420.8	1301.6	1208.8
37.5°	1569.5	1879.5	2053.6	2058.0	1918.7	1749.0	1582.1	1447.6	1311.4	1194.4	1094.0
40°	1362.8	1698.6	1925.4	1975.7	1858.1	1674.7	1505.9	1369.0	1235.9	1121.4	1006.0
42.5°	1177.1	1511.7	1790.4	1877.8	1784.4	1602.3	1432.9	1289.7	1160.3	1052.0	934.2
45°	951.9	1244.4	1551.6	1707.9	1656.1	1487.3	1308.6	1172.5	1050.9	957.3	844.2
47.5°	802.9	1009.2	1306.5	1517.8	1516.9	1362.9	1187.1	1056.6	943.9	856.2	764.8
50°	718.1	897.7	1149.2	1389.1	1409.2	1280.0	1112.8	983.6	878.4	786.3	712.8
52.5°	642.0	789.9	1016.1	1246.1	1303.3	1191.4	1029.3	909.9	807.8	723.1	660.1
55°	542.5	657.0	828.8	1043.9	1130.6	1051.7	907.8	796.3	713.5	642.3	588.1
57.5°	458.9	544.8	682.7	855.9	956.8	907.2	788.4	697.9	627.0	562.6	519.9
60°	406.3	476.7	593.6	738.3	849.7	814.9	713.5	629.1	568.8	513.1	472.8
62.5°	356.8	417.3	517.5	634.9	737.0	722.7	639.9	569.1	516.1	465.4	431.3
65°	287.1	331.2	409.4	501.5	583.5	590.5	530.9	482.9	435.7	395.5	365.3
67.5°	228.6	257.4	312.5	390.0	451.5	473.4	437.1	400.4	362.9	331.8	305.7
70°	192.7	215.9	256.1	318.8	375.4	398.5	377.7	349.0	316.5	290.9	268.5
72.5°	156.1	178.7	208.4	254.5	302.9	328.0	320.7	300.1	273.8	252.6	231.4
75°	117.6	124.6	144.7	175.7	213.6	235.3	240.7	229.8	208.9	192.7	180.3
77.5°	86.9	91.2	100.8	117.0	141.8	161.1	169.1	167.7	153.4	143.9	132.3
80°	69.7	72.0	76.6	83.6	102.2	121.5	126.9	126.9	116.8	113.0	101.4
82.5°	52.9	54.6	57.5	61.3	70.0	86.8	92.9	94.1	87.8	82.6	73.5
85°	30.2	29.4	31.0	33.3	34.8	39.5	48.8	50.3	48.8	42.5	40.2
87.5°	14.5	14.7	14.3	13.2	13.2	13.2	15.8	18.2	16.4	15.0	14.4
90°	20.3	18.1	16.0	13.3	10.3	7.3	4.2	1.2	4.2	7.3	10.3
92.5°	26.5	25.3	24.2	23.8	24.1	24.4	24.6	24.9	24.6	24.4	24.1
95°	44.3	42.4	40.5	44.0	53.1	62.2	71.2	80.3	71.2	62.2	53.1
97.5°	55.5	51.1	46.7	57.3	82.8	108.3	133.8	159.4	133.8	108.3	82.8
100°	61.1	56.5	51.7	68.3	105.8	143.4	181.1	218.6	181.1	143.4	105.8
102.5°	150.5	189.5	228.5	252.1	260.0	267.9	275.9	283.9	275.9	267.9	260.0
105°	225.2	300.2	375.2	408.5	400.2	392.0	383.7	375.6	383.7	392.0	400.2
107.5°	285.3	375.2	465.0	506.6	500.0	493.3	486.7	480.1	486.7	493.3	500.0
110°	374.9	454.2	533.5	570.3	564.5	558.8	553.0	547.2	553.0	558.8	564.5





TEST NUMBER: P331857-840

CATALOG NUMBER: S122RDIW-S1005D1240U840-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	584.5	604.1	623.7	631.0	625.8	620.7	615.6	610.5	615.6	620.7	625.8
115°	748.5	741.6	734.8	729.0	724.3	719.6	715.0	710.3	715.0	719.6	724.3
117.5°	834.8	830.0	825.4	820.4	815.2	809.9	804.8	799.5	804.8	809.9	815.2
120°	895.6	890.7	885.8	881.2	877.1	872.9	868.9	864.7	868.9	872.9	877.1
122.5°	953.0	947.7	942.3	937.5	933.1	928.8	924.4	920.1	924.4	928.8	933.1
125°	1033.4	1028.2	1023.0	1018.5	1015.0	1011.5	1007.8	1004.3	1007.8	1011.5	1015.0
127.5°	1108.2	1104.3	1100.4	1096.5	1092.6	1088.5	1084.6	1080.7	1084.6	1088.5	1092.6
130°	1156.4	1153.4	1150.3	1146.7	1142.3	1137.9	1133.5	1129.1	1133.5	1137.9	1142.3
132.5°	1202.9	1199.8	1196.8	1193.5	1189.7	1186.0	1182.2	1178.5	1182.2	1186.0	1189.7
135°	1268.7	1266.2	1263.7	1260.3	1255.9	1251.5	1247.1	1242.7	1247.1	1251.5	1255.9
137.5°	1328.6	1325.8	1322.9	1320.0	1317.0	1313.8	1310.8	1307.7	1310.8	1313.8	1317.0
140°	1367.7	1364.6	1361.6	1359.0	1356.8	1354.6	1352.4	1350.2	1352.4	1354.6	1356.8
142.5°	1403.3	1399.9	1396.4	1393.7	1391.7	1389.8	1387.8	1385.8	1387.8	1389.8	1391.7
145°	1452.1	1447.4	1442.7	1440.6	1440.8	1441.1	1441.4	1441.6	1441.4	1441.1	1440.8
147.5°	1497.1	1492.5	1487.9	1486.1	1487.1	1488.2	1489.2	1490.3	1489.2	1488.2	1487.1
150°	1524.3	1519.8	1515.5	1514.2	1516.1	1518.1	1520.0	1522.0	1520.0	1518.1	1516.1
152.5°	1549.4	1545.2	1541.1	1540.0	1542.2	1544.3	1546.5	1548.6	1546.5	1544.3	1542.2
155°	1584.5	1581.2	1577.9	1577.5	1579.9	1582.5	1584.9	1587.4	1584.9	1582.5	1579.9
157.5°	1614.2	1611.8	1609.5	1609.4	1611.5	1613.6	1615.7	1617.8	1615.7	1613.6	1611.5
160°	1632.2	1630.6	1629.0	1629.0	1630.6	1632.2	1634.0	1635.6	1634.0	1632.2	1630.6
162.5°	1647.5	1646.1	1644.7	1644.8	1646.5	1648.1	1649.7	1651.4	1649.7	1648.1	1646.5
165°	1667.3	1666.5	1665.7	1666.1	1667.7	1669.3	1671.0	1672.6	1671.0	1669.3	1667.7
167.5°	1682.9	1682.2	1681.4	1681.8	1683.5	1685.2	1686.8	1688.5	1686.8	1685.2	1683.5
170°	1691.3	1690.7	1690.2	1690.7	1692.4	1694.0	1695.7	1697.4	1695.7	1694.0	1692.4
172.5°	1697.2	1696.7	1696.2	1696.7	1698.3	1700.0	1701.6	1703.2	1701.6	1700.0	1698.3
175°	1703.6	1703.1	1702.5	1703.2	1705.2	1707.1	1709.0	1710.9	1709.0	1707.1	1705.2
177.5°	1705.8	1705.6	1705.4	1706.0	1707.6	1709.1	1710.6	1712.1	1710.6	1709.1	1707.6
180°	1707.2	1707.2	1707.2	1707.2	1707.2	1707.2	1707.2	1707.2	1707.2	1707.2	1707.2



TEST NUMBER: P331857-840

CATALOG NUMBER: S122RDIW-S1005D1240U840-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	2227.2	2227.2	2227.2	2227.2	2227.2	2227.2	2227.2	2227.2	2227.2	2227.2	2227.2
2.5°	2195.6	2191.3	2183.2	2170.8	2163.4	2150.4	2141.7	2146.7	2148.0	2146.7	2145.5
5°	2136.7	2120.4	2098.0	2076.3	2056.2	2034.5	2022.2	2016.7	2005.9	1999.6	1996.6
7.5°	2065.3	2037.3	2005.6	1967.8	1935.7	1902.2	1885.0	1876.4	1854.3	1842.3	1831.7
10°	2012.1	1967.9	1936.2	1886.7	1856.5	1812.4	1782.2	1783.0	1752.8	1735.8	1723.4
12.5°	1953.3	1904.8	1852.0	1807.5	1765.5	1730.1	1693.6	1679.0	1647.0	1630.5	1597.1
15°	1855.7	1799.3	1743.5	1683.1	1640.6	1585.7	1533.1	1468.8	1416.9	1372.1	1359.7
17.5°	1749.3	1679.3	1623.5	1552.6	1479.7	1387.3	1326.3	1289.0	1257.7	1234.1	1216.4
20°	1676.2	1605.0	1545.4	1438.7	1340.3	1277.7	1232.7	1204.2	1171.6	1146.1	1132.2
22.5°	1599.4	1525.1	1443.9	1324.7	1248.1	1197.8	1157.8	1124.9	1102.9	1083.0	1070.3
25°	1490.5	1409.2	1275.4	1193.3	1131.4	1078.7	1050.9	1030.8	1007.5	980.5	968.2
27.5°	1375.3	1246.1	1149.9	1088.9	1029.9	995.6	970.6	940.6	919.8	907.6	894.7
30°	1289.3	1160.0	1085.0	1018.4	976.6	938.7	909.3	892.3	872.1	851.2	842.7
32.5°	1193.3	1090.0	1018.1	962.7	920.3	888.0	864.7	837.2	822.6	809.8	791.9
35°	1074.1	995.9	930.2	885.3	845.1	818.8	791.6	775.4	749.1	738.3	731.3
37.5°	973.2	905.4	856.4	809.0	777.1	748.0	731.4	705.6	694.2	679.1	664.5
40°	916.3	849.7	802.5	763.8	728.2	706.5	685.6	664.8	647.7	640.8	623.0
42.5°	858.1	803.9	756.7	714.3	690.4	667.5	641.1	625.7	608.1	596.8	585.8
45°	777.7	729.7	689.5	654.7	628.3	604.4	587.3	561.8	551.8	529.4	520.1
47.5°	707.2	662.6	624.2	591.1	565.4	549.8	524.8	504.8	488.8	475.0	463.1
50°	657.0	619.9	582.7	553.3	530.1	507.7	482.1	472.0	447.3	440.3	433.3
52.5°	611.2	575.9	541.9	513.1	489.9	468.1	445.6	432.4	415.8	408.8	403.6
55°	547.1	513.1	480.6	455.0	431.8	409.4	395.5	379.2	371.4	366.1	359.8
57.5°	482.7	452.1	427.2	401.3	378.0	360.1	344.1	334.3	326.3	319.1	311.7
60°	441.9	412.4	390.0	366.1	342.0	327.3	315.0	303.4	294.1	283.3	280.1
62.5°	398.5	372.8	352.2	328.9	308.0	294.6	282.8	271.8	260.6	244.9	240.5
65°	338.9	318.8	297.2	277.8	259.2	246.1	229.0	216.7	212.1	210.5	209.7
67.5°	285.1	266.1	247.5	227.6	210.8	198.5	190.0	188.0	184.8	183.9	181.7
70°	249.2	231.4	212.8	194.2	178.0	175.7	172.6	169.5	165.6	164.1	162.5
72.5°	217.0	198.5	180.0	165.1	158.1	155.2	152.2	149.1	146.4	144.9	143.9
75°	166.4	149.4	136.9	131.6	127.6	125.3	120.7	118.4	116.8	114.5	113.7
77.5°	119.8	110.2	104.5	101.1	97.0	94.5	91.9	89.6	88.0	87.5	86.2
80°	91.3	86.6	82.8	78.2	76.6	73.5	72.7	70.4	71.2	68.9	68.9
82.5°	70.9	65.0	61.8	59.6	58.1	55.5	54.8	53.7	53.8	52.1	52.1
85°	36.4	34.8	33.3	31.7	31.7	29.4	30.2	29.4	29.4	27.9	27.1
87.5°	14.4	14.3	13.5	13.9	14.4	14.2	14.5	14.1	14.4	14.7	14.2
90°	13.3	16.0	18.1	20.3	22.5	24.7	26.1	27.5	28.8	30.2	31.2
92.5°	23.8	24.2	25.3	26.5	27.6	28.7	29.4	30.1	30.8	31.5	32.0
95°	44.0	40.5	42.4	44.3	46.3	48.2	49.6	50.9	52.3	53.6	54.2
97.5°	57.3	46.7	51.1	55.5	60.1	64.5	65.5	66.7	67.8	68.9	69.6
100°	68.3	51.7	56.5	61.1	65.7	70.4	72.6	74.8	77.0	79.2	80.6
102.5°	252.1	228.5	189.5	150.5	111.4	72.4	75.2	78.1	81.0	83.8	85.6
105°	408.5	375.2	300.2	225.2	150.3	75.3	78.4	81.4	84.4	87.5	89.5
107.5°	506.6	465.0	375.2	285.3	195.4	105.5	102.4	99.4	96.2	93.2	92.2
110°	570.3	533.5	454.2	374.9	295.5	216.2	188.7	161.3	133.8	106.3	93.2



TEST NUMBER: P331857-840

CATALOG NUMBER: S122RDIW-S1005D1240U840-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	631.0	623.7	604.1	584.5	564.9	545.2	445.1	345.0	244.9	144.7	95.0
115°	729.0	734.8	741.6	748.5	755.4	762.2	635.1	508.0	380.9	253.8	180.4
117.5°	820.4	825.4	830.0	834.8	839.5	844.2	813.4	782.7	751.9	721.2	673.4
120°	881.2	885.8	890.7	895.6	900.6	905.4	908.8	912.1	915.3	918.7	901.8
122.5°	937.5	942.3	947.7	953.0	958.5	963.8	965.7	967.8	969.8	971.7	969.1
125°	1018.5	1023.0	1028.2	1033.4	1038.6	1043.9	1045.8	1047.7	1049.7	1051.6	1052.9
127.5°	1096.5	1100.4	1104.3	1108.2	1112.1	1116.0	1118.8	1121.6	1124.4	1127.2	1128.7
130°	1146.7	1150.3	1153.4	1156.4	1159.4	1162.5	1165.5	1168.5	1171.5	1174.5	1175.9
132.5°	1193.5	1196.8	1199.8	1202.9	1205.9	1208.9	1211.4	1214.1	1216.6	1219.2	1220.3
135°	1260.3	1263.7	1266.2	1268.7	1271.1	1273.6	1276.4	1279.1	1281.8	1284.6	1285.7
137.5°	1320.0	1322.9	1325.8	1328.6	1331.3	1334.1	1336.9	1339.5	1342.2	1344.9	1345.7
140°	1359.0	1361.6	1364.6	1367.7	1370.7	1373.7	1376.1	1378.7	1381.1	1383.6	1384.1
142.5°	1393.7	1396.4	1399.9	1403.3	1406.7	1410.3	1412.5	1414.7	1417.0	1419.3	1419.7
145°	1440.6	1442.7	1447.4	1452.1	1456.7	1461.4	1463.3	1465.2	1467.1	1469.1	1469.4
147.5°	1486.1	1487.9	1492.5	1497.1	1501.8	1506.3	1507.8	1509.2	1510.7	1512.1	1512.2
150°	1514.2	1515.5	1519.8	1524.3	1528.6	1533.1	1534.7	1536.3	1538.0	1539.6	1539.7
152.5°	1540.0	1541.1	1545.2	1549.4	1553.6	1557.7	1559.4	1561.0	1562.7	1564.4	1564.3
155°	1577.5	1577.9	1581.2	1584.5	1587.8	1591.1	1592.8	1594.4	1596.1	1597.7	1597.4
157.5°	1609.4	1609.5	1611.8	1614.2	1616.5	1618.8	1620.6	1622.6	1624.4	1626.3	1626.1
160°	1629.0	1629.0	1630.6	1632.2	1634.0	1635.6	1637.2	1638.9	1640.5	1642.1	1642.0
162.5°	1644.8	1644.7	1646.1	1647.5	1649.0	1650.4	1652.2	1654.2	1656.0	1657.9	1657.6
165°	1666.1	1665.7	1666.5	1667.3	1668.1	1668.9	1670.8	1672.7	1674.7	1676.6	1676.6
167.5°	1681.8	1681.4	1682.2	1682.9	1683.7	1684.5	1686.4	1688.3	1690.2	1692.1	1691.9
170°	1690.7	1690.2	1690.7	1691.3	1691.8	1692.4	1694.4	1696.3	1698.2	1700.1	1699.8
172.5°	1696.7	1696.2	1696.7	1697.2	1697.8	1698.3	1700.2	1702.1	1704.0	1706.0	1705.8
175°	1703.2	1702.5	1703.1	1703.6	1704.2	1704.8	1706.7	1708.6	1710.5	1712.4	1712.0
177.5°	1706.0	1705.4	1705.6	1705.8	1706.0	1706.3	1707.8	1709.3	1710.8	1712.4	1712.1
180°	1707.2	1707.2	1707.2	1707.2	1707.2	1707.2	1707.2	1707.2	1707.2	1707.2	1707.2



TEST NUMBER: P331857-840

CATALOG NUMBER: S122RDIW-S1005D1240U840-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	2227.2	2227.2	2227.2	2227.2	2227.2	2227.2	2227.2	2227.2	2227.2	2227.2	2227.2
2.5°	2138.7	2139.9	2138.1	2139.3	2138.1	2139.9	2138.7	2145.5	2146.7	2148.0	2146.7
5°	1992.7	1983.4	1981.9	1979.5	1981.9	1983.4	1992.7	1996.6	1999.6	2005.9	2016.7
7.5°	1818.5	1817.1	1813.2	1807.8	1813.2	1817.1	1818.5	1831.7	1842.3	1854.3	1876.4
10°	1706.4	1702.5	1701.7	1696.3	1701.7	1702.5	1706.4	1723.4	1735.8	1752.8	1783.0
12.5°	1575.1	1550.2	1547.6	1534.1	1547.6	1550.2	1575.1	1597.1	1630.5	1647.0	1679.0
15°	1341.1	1336.5	1321.0	1310.9	1321.0	1336.5	1341.1	1359.7	1372.1	1416.9	1468.8
17.5°	1207.4	1192.2	1187.4	1185.3	1187.4	1192.2	1207.4	1216.4	1234.1	1257.7	1289.0
20°	1121.4	1107.4	1105.1	1103.6	1105.1	1107.4	1121.4	1132.2	1146.1	1171.6	1204.2
22.5°	1061.9	1047.3	1041.3	1036.6	1041.3	1047.3	1061.9	1070.3	1083.0	1102.9	1124.9
25°	960.4	954.9	951.9	950.3	951.9	954.9	960.4	968.2	980.5	1007.5	1030.8
27.5°	881.0	869.1	866.8	862.7	866.8	869.1	881.0	894.7	907.6	919.8	940.6
30°	835.8	831.9	826.5	821.8	826.5	831.9	835.8	842.7	851.2	872.1	892.3
32.5°	782.5	779.3	774.5	772.3	774.5	779.3	782.5	791.9	809.8	822.6	837.2
35°	723.6	712.8	708.1	701.1	708.1	712.8	723.6	731.3	738.3	749.1	775.4
37.5°	661.2	655.5	648.9	651.3	648.9	655.5	661.2	664.5	679.1	694.2	705.6
40°	612.9	609.0	607.5	606.7	607.5	609.0	612.9	623.0	640.8	647.7	664.8
42.5°	574.5	563.8	559.8	559.7	559.8	563.8	574.5	585.8	596.8	608.1	625.7
45°	516.1	506.1	499.2	499.9	499.2	506.1	516.1	520.1	529.4	551.8	561.8
47.5°	456.5	456.2	451.8	453.1	451.8	456.2	456.5	463.1	475.0	488.8	504.8
50°	428.0	423.3	420.2	421.0	420.2	423.3	428.0	433.3	440.3	447.3	472.0
52.5°	400.7	396.7	394.3	397.5	394.3	396.7	400.7	403.6	408.8	415.8	432.4
55°	356.0	351.3	350.5	349.8	350.5	351.3	356.0	359.8	366.1	371.4	379.2
57.5°	306.0	302.9	298.2	296.2	298.2	302.9	306.0	311.7	319.1	326.3	334.3
60°	270.0	263.9	256.1	255.4	256.1	263.9	270.0	280.1	283.3	294.1	303.4
62.5°	237.2	236.0	234.5	234.3	234.5	236.0	237.2	240.5	244.9	260.6	271.8
65°	208.1	207.4	208.1	208.9	208.1	207.4	208.1	209.7	210.5	212.1	216.7
67.5°	181.4	180.0	178.6	179.3	178.6	180.0	181.4	181.7	183.9	184.8	188.0
70°	161.0	160.2	159.5	159.5	159.5	160.2	161.0	162.5	164.1	165.6	169.5
72.5°	141.2	141.0	140.3	139.6	140.3	141.0	141.2	143.9	144.9	146.4	149.1
75°	113.0	111.4	111.4	111.4	111.4	111.4	113.0	113.7	114.5	116.8	118.4
77.5°	86.0	85.2	84.5	83.9	84.5	85.2	86.0	86.2	87.5	88.0	89.6
80°	68.1	67.4	66.6	66.6	66.6	67.4	68.1	68.9	68.9	71.2	70.4
82.5°	52.0	51.2	51.1	50.5	51.1	51.2	52.0	52.1	52.1	53.8	53.7
85°	27.9	28.7	27.9	29.4	27.9	28.7	27.9	27.1	27.9	29.4	29.4
87.5°	14.3	13.8	14.6	14.1	14.6	13.8	14.3	14.2	14.7	14.4	14.1
90°	31.7	32.2	32.8	33.3	32.8	32.2	31.7	31.2	30.2	28.8	27.5
92.5°	32.3	32.7	33.0	33.3	33.0	32.7	32.3	32.0	31.5	30.8	30.1
95°	53.9	53.6	53.4	53.1	53.4	53.6	53.9	54.2	53.6	52.3	50.9
97.5°	69.9	70.3	70.6	70.9	70.6	70.3	69.9	69.6	68.9	67.8	66.7
100°	81.1	81.7	82.2	82.8	82.2	81.7	81.1	80.6	79.2	77.0	74.8
102.5°	86.3	87.2	88.0	88.7	88.0	87.2	86.3	85.6	83.8	81.0	78.1
105°	90.6	91.7	92.8	93.9	92.8	91.7	90.6	89.5	87.5	84.4	81.4
107.5°	93.3	94.4	95.5	96.6	95.5	94.4	93.3	92.2	93.2	96.2	99.4
110°	94.3	95.4	96.5	97.6	96.5	95.4	94.3	93.2	106.3	133.8	161.3



TEST NUMBER: P331857-840

CATALOG NUMBER: S122RDIW-S1005D1240U840-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	95.9	96.8	97.7	98.6	97.7	96.8	95.9	95.0	144.7	244.9	345.0
115°	160.6	140.9	121.1	101.3	121.1	140.9	160.6	180.4	253.8	380.9	508.0
117.5°	608.4	543.5	478.6	413.5	478.6	543.5	608.4	673.4	721.2	751.9	782.7
120°	864.7	827.7	790.6	753.6	790.6	827.7	864.7	901.8	918.7	915.3	912.1
122.5°	961.9	954.7	947.6	940.3	947.6	954.7	961.9	969.1	971.7	969.8	967.8
125°	1053.7	1054.6	1055.4	1056.2	1055.4	1054.6	1053.7	1052.9	1051.6	1049.7	1047.7
127.5°	1128.8	1129.0	1129.1	1129.3	1129.1	1129.0	1128.8	1128.7	1127.2	1124.4	1121.6
130°	1175.6	1175.4	1175.1	1174.8	1175.1	1175.4	1175.6	1175.9	1174.5	1171.5	1168.5
132.5°	1220.1	1219.8	1219.5	1219.3	1219.5	1219.8	1220.1	1220.3	1219.2	1216.6	1214.1
135°	1285.2	1284.6	1284.0	1283.5	1284.0	1284.6	1285.2	1285.7	1284.6	1281.8	1279.1
137.5°	1344.8	1343.9	1343.0	1342.0	1343.0	1343.9	1344.8	1345.7	1344.9	1342.2	1339.5
140°	1382.7	1381.4	1380.0	1378.7	1380.0	1381.4	1382.7	1384.1	1383.6	1381.1	1378.7
142.5°	1418.4	1416.9	1415.5	1414.2	1415.5	1416.9	1418.4	1419.7	1419.3	1417.0	1414.7
145°	1467.9	1466.6	1465.2	1463.9	1465.2	1466.6	1467.9	1469.4	1469.1	1467.1	1465.2
147.5°	1511.1	1509.8	1508.7	1507.6	1508.7	1509.8	1511.1	1512.2	1512.1	1510.7	1509.2
150°	1538.4	1537.0	1535.6	1534.3	1535.6	1537.0	1538.4	1539.7	1539.6	1538.0	1536.3
152.5°	1562.5	1560.6	1558.8	1557.0	1558.8	1560.6	1562.5	1564.3	1564.4	1562.7	1561.0
155°	1595.2	1593.1	1590.8	1588.6	1590.8	1593.1	1595.2	1597.4	1597.7	1596.1	1594.4
157.5°	1624.0	1621.8	1619.7	1617.5	1619.7	1621.8	1624.0	1626.1	1626.3	1624.4	1622.6
160°	1640.1	1638.2	1636.3	1634.4	1636.3	1638.2	1640.1	1642.0	1642.1	1640.5	1638.9
162.5°	1655.3	1652.8	1650.5	1648.2	1650.5	1652.8	1655.3	1657.6	1657.9	1656.0	1654.2
165°	1674.7	1672.7	1670.8	1668.9	1670.8	1672.7	1674.7	1676.6	1676.6	1674.7	1672.7
167.5°	1689.4	1687.0	1684.5	1682.0	1684.5	1687.0	1689.4	1691.9	1692.1	1690.2	1688.3
170°	1697.4	1694.9	1692.4	1689.9	1692.4	1694.9	1697.4	1699.8	1700.1	1698.2	1696.3
172.5°	1703.2	1700.8	1698.3	1695.9	1698.3	1700.8	1703.2	1705.8	1706.0	1704.0	1702.1
175°	1709.3	1706.6	1703.7	1701.0	1703.7	1706.6	1709.3	1712.0	1712.4	1710.5	1708.6
177.5°	1710.2	1708.2	1706.3	1704.2	1706.3	1708.2	1710.2	1712.1	1712.4	1710.8	1709.3
180°	1707.2	1707.2	1707.2	1707.2	1707.2	1707.2	1707.2	1707.2	1707.2	1707.2	1707.2



TEST NUMBER: P331857-840

CATALOG NUMBER: S122RDIW-S1005D1240U840-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	2227.2	2227.2	2227.2	2227.2	2227.2	2227.2	2227.2	2227.2	2227.2	2227.2	2227.2
2.5°	2141.7	2150.4	2163.4	2170.8	2183.2	2191.3	2195.6	2203.6	2208.0	2223.5	2239.6
5°	2022.2	2034.5	2056.2	2076.3	2098.0	2120.4	2136.7	2155.3	2172.2	2201.6	2232.6
7.5°	1885.0	1902.2	1935.7	1967.8	2005.6	2037.3	2065.3	2097.0	2125.4	2167.5	2211.4
10°	1782.2	1812.4	1856.5	1886.7	1936.2	1967.9	2012.1	2046.9	2086.4	2142.0	2191.6
12.5°	1693.6	1730.1	1765.5	1807.5	1852.0	1904.8	1953.3	1998.0	2044.9	2102.4	2160.6
15°	1533.1	1585.7	1640.6	1683.1	1743.5	1799.3	1855.7	1916.1	1973.4	2042.3	2118.1
17.5°	1326.3	1387.3	1479.7	1552.6	1623.5	1679.3	1749.3	1822.3	1889.8	1972.9	2057.3
20°	1232.7	1277.7	1340.3	1438.7	1545.4	1605.0	1676.2	1756.7	1834.0	1924.6	2015.2
22.5°	1157.8	1197.8	1248.1	1324.7	1443.9	1525.1	1599.4	1681.1	1770.9	1863.3	1963.8
25°	1050.9	1078.7	1131.4	1193.3	1275.4	1409.2	1490.5	1572.5	1670.0	1769.1	1883.6
27.5°	970.6	995.6	1029.9	1088.9	1149.9	1246.1	1375.3	1464.8	1562.0	1673.4	1792.3
30°	909.3	938.7	976.6	1018.4	1085.0	1160.0	1289.3	1393.0	1488.9	1603.5	1730.4
32.5°	864.7	888.0	920.3	962.7	1018.1	1090.0	1193.3	1319.3	1412.8	1533.5	1666.0
35°	791.6	818.8	845.1	885.3	930.2	995.9	1074.1	1208.8	1301.6	1420.8	1553.9
37.5°	731.4	748.0	777.1	809.0	856.4	905.4	973.2	1094.0	1194.4	1311.4	1447.6
40°	685.6	706.5	728.2	763.8	802.5	849.7	916.3	1006.0	1121.4	1235.9	1369.0
42.5°	641.1	667.5	690.4	714.3	756.7	803.9	858.1	934.2	1052.0	1160.3	1289.7
45°	587.3	604.4	628.3	654.7	689.5	729.7	777.7	844.2	957.3	1050.9	1172.5
47.5°	524.8	549.8	565.4	591.1	624.2	662.6	707.2	764.8	856.2	943.9	1056.6
50°	482.1	507.7	530.1	553.3	582.7	619.9	657.0	712.8	786.3	878.4	983.6
52.5°	445.6	468.1	489.9	513.1	541.9	575.9	611.2	660.1	723.1	807.8	909.9
55°	395.5	409.4	431.8	455.0	480.6	513.1	547.1	588.1	642.3	713.5	796.3
57.5°	344.1	360.1	378.0	401.3	427.2	452.1	482.7	519.9	562.6	627.0	697.9
60°	315.0	327.3	342.0	366.1	390.0	412.4	441.9	472.8	513.1	568.8	629.1
62.5°	282.8	294.6	308.0	328.9	352.2	372.8	398.5	431.3	465.4	516.1	569.1
65°	229.0	246.1	259.2	277.8	297.2	318.8	338.9	365.3	395.5	435.7	482.9
67.5°	190.0	198.5	210.8	227.6	247.5	266.1	285.1	305.7	331.8	362.9	400.4
70°	172.6	175.7	178.0	194.2	212.8	231.4	249.2	268.5	290.9	316.5	349.0
72.5°	152.2	155.2	158.1	165.1	180.0	198.5	217.0	231.4	252.6	273.8	300.1
75°	120.7	125.3	127.6	131.6	136.9	149.4	166.4	180.3	192.7	208.9	229.8
77.5°	91.9	94.5	97.0	101.1	104.5	110.2	119.8	132.3	143.9	153.4	167.7
80°	72.7	73.5	76.6	78.2	82.8	86.6	91.3	101.4	113.0	116.8	126.9
82.5°	54.8	55.5	58.1	59.6	61.8	65.0	70.9	73.5	82.6	87.8	94.1
85°	30.2	29.4	31.7	31.7	33.3	34.8	36.4	40.2	42.5	48.8	50.3
87.5°	14.5	14.2	14.4	13.9	13.5	14.3	14.4	14.4	15.0	16.4	18.2
90°	26.1	24.7	22.5	20.3	18.1	16.0	13.3	10.3	7.3	4.2	1.2
92.5°	29.4	28.7	27.6	26.5	25.3	24.2	23.8	24.1	24.4	24.6	24.9
95°	49.6	48.2	46.3	44.3	42.4	40.5	44.0	53.1	62.2	71.2	80.3
97.5°	65.5	64.5	60.1	55.5	51.1	46.7	57.3	82.8	108.3	133.8	159.4
100°	72.6	70.4	65.7	61.1	56.5	51.7	68.3	105.8	143.4	181.1	218.6
102.5°	75.2	72.4	111.4	150.5	189.5	228.5	252.1	260.0	267.9	275.9	283.9
105°	78.4	75.3	150.3	225.2	300.2	375.2	408.5	400.2	392.0	383.7	375.6
107.5°	102.4	105.5	195.4	285.3	375.2	465.0	506.6	500.0	493.3	486.7	480.1
110°	188.7	216.2	295.5	374.9	454.2	533.5	570.3	564.5	558.8	553.0	547.2



TEST NUMBER: P331857-840

CATALOG NUMBER: S122RDIW-S1005D1240U840-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	445.1	545.2	564.9	584.5	604.1	623.7	631.0	625.8	620.7	615.6	610.5
115°	635.1	762.2	755.4	748.5	741.6	734.8	729.0	724.3	719.6	715.0	710.3
117.5°	813.4	844.2	839.5	834.8	830.0	825.4	820.4	815.2	809.9	804.8	799.5
120°	908.8	905.4	900.6	895.6	890.7	885.8	881.2	877.1	872.9	868.9	864.7
122.5°	965.7	963.8	958.5	953.0	947.7	942.3	937.5	933.1	928.8	924.4	920.1
125°	1045.8	1043.9	1038.6	1033.4	1028.2	1023.0	1018.5	1015.0	1011.5	1007.8	1004.3
127.5°	1118.8	1116.0	1112.1	1108.2	1104.3	1100.4	1096.5	1092.6	1088.5	1084.6	1080.7
130°	1165.5	1162.5	1159.4	1156.4	1153.4	1150.3	1146.7	1142.3	1137.9	1133.5	1129.1
132.5°	1211.4	1208.9	1205.9	1202.9	1199.8	1196.8	1193.5	1189.7	1186.0	1182.2	1178.5
135°	1276.4	1273.6	1271.1	1268.7	1266.2	1263.7	1260.3	1255.9	1251.5	1247.1	1242.7
137.5°	1336.9	1334.1	1331.3	1328.6	1325.8	1322.9	1320.0	1317.0	1313.8	1310.8	1307.7
140°	1376.1	1373.7	1370.7	1367.7	1364.6	1361.6	1359.0	1356.8	1354.6	1352.4	1350.2
142.5°	1412.5	1410.3	1406.7	1403.3	1399.9	1396.4	1393.7	1391.7	1389.8	1387.8	1385.8
145°	1463.3	1461.4	1456.7	1452.1	1447.4	1442.7	1440.6	1440.8	1441.1	1441.4	1441.6
147.5°	1507.8	1506.3	1501.8	1497.1	1492.5	1487.9	1486.1	1487.1	1488.2	1489.2	1490.3
150°	1534.7	1533.1	1528.6	1524.3	1519.8	1515.5	1514.2	1516.1	1518.1	1520.0	1522.0
152.5°	1559.4	1557.7	1553.6	1549.4	1545.2	1541.1	1540.0	1542.2	1544.3	1546.5	1548.6
155°	1592.8	1591.1	1587.8	1584.5	1581.2	1577.9	1577.5	1579.9	1582.5	1584.9	1587.4
157.5°	1620.6	1618.8	1616.5	1614.2	1611.8	1609.5	1609.4	1611.5	1613.6	1615.7	1617.8
160°	1637.2	1635.6	1634.0	1632.2	1630.6	1629.0	1629.0	1630.6	1632.2	1634.0	1635.6
162.5°	1652.2	1650.4	1649.0	1647.5	1646.1	1644.7	1644.8	1646.5	1648.1	1649.7	1651.4
165°	1670.8	1668.9	1668.1	1667.3	1666.5	1665.7	1666.1	1667.7	1669.3	1671.0	1672.6
167.5°	1686.4	1684.5	1683.7	1682.9	1682.2	1681.4	1681.8	1683.5	1685.2	1686.8	1688.5
170°	1694.4	1692.4	1691.8	1691.3	1690.7	1690.2	1690.7	1692.4	1694.0	1695.7	1697.4
172.5°	1700.2	1698.3	1697.8	1697.2	1696.7	1696.2	1696.7	1698.3	1700.0	1701.6	1703.2
175°	1706.7	1704.8	1704.2	1703.6	1703.1	1702.5	1703.2	1705.2	1707.1	1709.0	1710.9
177.5°	1707.8	1706.3	1706.0	1705.8	1705.6	1705.4	1706.0	1707.6	1709.1	1710.6	1712.1
180°	1707.2	1707.2	1707.2	1707.2	1707.2	1707.2	1707.2	1707.2	1707.2	1707.2	1707.2



TEST NUMBER: P331857-840

CATALOG NUMBER: S122RDIW-S1005D1240U840-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	2227.2	2227.2	2227.2	2227.2	2227.2	2227.2	2227.2	2227.2	2227.2	2227.2	2227.2
2.5°	2240.2	2242.0	2254.4	2260.0	2271.2	2275.4	2280.5	2279.2	2279.2	2281.7	2299.0
5°	2245.0	2260.5	2283.7	2306.1	2327.8	2346.3	2358.7	2371.2	2375.8	2398.2	2418.3
7.5°	2237.0	2265.4	2303.8	2338.0	2379.0	2411.1	2437.7	2461.6	2478.1	2510.7	2544.2
10°	2226.4	2266.6	2310.0	2354.1	2410.5	2453.2	2496.5	2529.8	2540.6	2589.4	2617.3
12.5°	2205.3	2259.3	2314.3	2371.5	2426.7	2485.4	2533.0	2566.3	2604.3	2648.2	2699.6
15°	2173.8	2235.7	2307.6	2381.2	2460.1	2531.3	2582.4	2640.4	2682.2	2730.2	2775.1
17.5°	2128.5	2208.2	2299.7	2384.8	2476.1	2552.5	2622.8	2678.5	2708.0	2735.3	2742.0
20°	2092.5	2178.5	2286.0	2386.6	2477.9	2566.2	2635.7	2682.2	2690.0	2690.7	2649.7
22.5°	2053.6	2150.6	2263.1	2366.2	2475.5	2573.5	2627.8	2647.6	2616.9	2564.5	2485.1
25°	1981.9	2094.1	2224.8	2342.5	2461.6	2554.6	2573.1	2538.3	2430.7	2317.7	2174.5
27.5°	1904.2	2030.3	2170.5	2301.3	2428.2	2485.8	2445.7	2320.2	2126.5	1958.0	1753.9
30°	1847.2	1988.8	2126.6	2272.8	2390.5	2415.2	2323.2	2138.2	1912.2	1658.4	1454.9
32.5°	1782.2	1930.7	2082.0	2233.2	2331.7	2307.5	2155.4	1927.7	1662.7	1413.2	1220.8
35°	1689.3	1842.6	2005.9	2157.6	2220.2	2115.8	1888.2	1591.9	1321.0	1088.0	955.7
37.5°	1582.1	1749.0	1918.7	2058.0	2053.6	1879.5	1569.5	1263.5	1035.9	898.2	803.9
40°	1505.9	1674.7	1858.1	1975.7	1925.4	1698.6	1362.8	1074.1	907.8	797.9	729.0
42.5°	1432.9	1602.3	1784.4	1877.8	1790.4	1511.7	1177.1	950.9	813.6	727.9	672.1
45°	1308.6	1487.3	1656.1	1707.9	1551.6	1244.4	951.9	787.8	696.5	633.0	594.3
47.5°	1187.1	1362.9	1516.9	1517.8	1306.5	1009.2	802.9	681.8	603.8	554.7	526.5
50°	1112.8	1280.0	1409.2	1389.1	1149.2	897.7	718.1	613.7	548.7	510.8	481.3
52.5°	1029.3	1191.4	1303.3	1246.1	1016.1	789.9	642.0	554.2	500.4	467.4	441.1
55°	907.8	1051.7	1130.6	1043.9	828.8	657.0	542.5	473.6	433.3	405.5	383.0
57.5°	788.4	907.2	956.8	855.9	682.7	544.8	458.9	407.2	367.3	347.3	335.7
60°	713.5	814.9	849.7	738.3	593.6	476.7	406.3	358.3	328.9	315.8	304.2
62.5°	639.9	722.7	737.0	634.9	517.5	417.3	356.8	316.2	296.7	284.2	273.2
65°	530.9	590.5	583.5	501.5	409.4	331.2	287.1	262.4	247.6	229.8	210.5
67.5°	437.1	473.4	451.5	390.0	312.5	257.4	228.6	209.8	191.6	174.7	170.3
70°	377.7	398.5	375.4	318.8	256.1	215.9	192.7	170.3	159.5	155.5	148.6
72.5°	320.7	328.0	302.9	254.5	208.4	178.7	156.1	143.6	137.7	134.5	130.0
75°	240.7	235.3	213.6	175.7	144.7	124.6	117.6	113.0	109.1	106.0	103.7
77.5°	169.1	161.1	141.8	117.0	100.8	91.2	86.9	84.5	82.6	81.1	78.8
80°	126.9	121.5	102.2	83.6	76.6	72.0	69.7	66.6	66.6	65.0	62.7
82.5°	92.9	86.8	70.0	61.3	57.5	54.6	52.9	51.1	50.5	50.8	49.1
85°	48.8	39.5	34.8	33.3	31.0	29.4	30.2	28.7	28.7	28.7	27.9
87.5°	15.8	13.2	13.2	13.2	14.3	14.7	14.5	15.0	16.1	15.8	16.7
90°	4.2	7.3	10.3	13.3	16.0	18.1	20.3	22.5	24.7	26.1	27.5
92.5°	24.6	24.4	24.1	23.8	24.2	25.3	26.5	27.6	28.7	29.4	30.1
95°	71.2	62.2	53.1	44.0	40.5	42.4	44.3	46.3	48.2	49.6	50.9
97.5°	133.8	108.3	82.8	57.3	46.7	51.1	55.5	60.1	64.5	65.5	66.7
100°	181.1	143.4	105.8	68.3	51.7	56.5	61.1	65.7	70.4	72.6	74.8
102.5°	275.9	267.9	260.0	252.1	228.5	189.5	150.5	111.4	72.4	75.2	78.1
105°	383.7	392.0	400.2	408.5	375.2	300.2	225.2	150.3	75.3	78.4	81.4
107.5°	486.7	493.3	500.0	506.6	465.0	375.2	285.3	195.4	105.5	102.4	99.4
110°	553.0	558.8	564.5	570.3	533.5	454.2	374.9	295.5	216.2	188.7	161.3





TEST NUMBER: P331857-840

CATALOG NUMBER: S122RDIW-S1005D1240U840-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	615.6	620.7	625.8	631.0	623.7	604.1	584.5	564.9	545.2	445.1	345.0
115°	715.0	719.6	724.3	729.0	734.8	741.6	748.5	755.4	762.2	635.1	508.0
117.5°	804.8	809.9	815.2	820.4	825.4	830.0	834.8	839.5	844.2	813.4	782.7
120°	868.9	872.9	877.1	881.2	885.8	890.7	895.6	900.6	905.4	908.8	912.1
122.5°	924.4	928.8	933.1	937.5	942.3	947.7	953.0	958.5	963.8	965.7	967.8
125°	1007.8	1011.5	1015.0	1018.5	1023.0	1028.2	1033.4	1038.6	1043.9	1045.8	1047.7
127.5°	1084.6	1088.5	1092.6	1096.5	1100.4	1104.3	1108.2	1112.1	1116.0	1118.8	1121.6
130°	1133.5	1137.9	1142.3	1146.7	1150.3	1153.4	1156.4	1159.4	1162.5	1165.5	1168.5
132.5°	1182.2	1186.0	1189.7	1193.5	1196.8	1199.8	1202.9	1205.9	1208.9	1211.4	1214.1
135°	1247.1	1251.5	1255.9	1260.3	1263.7	1266.2	1268.7	1271.1	1273.6	1276.4	1279.1
137.5°	1310.8	1313.8	1317.0	1320.0	1322.9	1325.8	1328.6	1331.3	1334.1	1336.9	1339.5
140°	1352.4	1354.6	1356.8	1359.0	1361.6	1364.6	1367.7	1370.7	1373.7	1376.1	1378.7
142.5°	1387.8	1389.8	1391.7	1393.7	1396.4	1399.9	1403.3	1406.7	1410.3	1412.5	1414.7
145°	1441.4	1441.1	1440.8	1440.6	1442.7	1447.4	1452.1	1456.7	1461.4	1463.3	1465.2
147.5°	1489.2	1488.2	1487.1	1486.1	1487.9	1492.5	1497.1	1501.8	1506.3	1507.8	1509.2
150°	1520.0	1518.1	1516.1	1514.2	1515.5	1519.8	1524.3	1528.6	1533.1	1534.7	1536.3
152.5°	1546.5	1544.3	1542.2	1540.0	1541.1	1545.2	1549.4	1553.6	1557.7	1559.4	1561.0
155°	1584.9	1582.5	1579.9	1577.5	1577.9	1581.2	1584.5	1587.8	1591.1	1592.8	1594.4
157.5°	1615.7	1613.6	1611.5	1609.4	1609.5	1611.8	1614.2	1616.5	1618.8	1620.6	1622.6
160°	1634.0	1632.2	1630.6	1629.0	1629.0	1630.6	1632.2	1634.0	1635.6	1637.2	1638.9
162.5°	1649.7	1648.1	1646.5	1644.8	1644.7	1646.1	1647.5	1649.0	1650.4	1652.2	1654.2
165°	1671.0	1669.3	1667.7	1666.1	1665.7	1666.5	1667.3	1668.1	1668.9	1670.8	1672.7
167.5°	1686.8	1685.2	1683.5	1681.8	1681.4	1682.2	1682.9	1683.7	1684.5	1686.4	1688.3
170°	1695.7	1694.0	1692.4	1690.7	1690.2	1690.7	1691.3	1691.8	1692.4	1694.4	1696.3
172.5°	1701.6	1700.0	1698.3	1696.7	1696.2	1696.7	1697.2	1697.8	1698.3	1700.2	1702.1
175°	1709.0	1707.1	1705.2	1703.2	1702.5	1703.1	1703.6	1704.2	1704.8	1706.7	1708.6
177.5°	1710.6	1709.1	1707.6	1706.0	1705.4	1705.6	1705.8	1706.0	1706.3	1707.8	1709.3
180°	1707.2	1707.2	1707.2	1707.2	1707.2	1707.2	1707.2	1707.2	1707.2	1707.2	1707.2



TEST NUMBER: P331857-840

CATALOG NUMBER: S122RDIW-S1005D1240U840-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	2227.2	2227.2	2227.2	2227.2	2227.2	2227.2	2227.2
2.5°	2305.2	2313.2	2316.9	2316.9	2321.3	2319.5	2317.5
5°	2437.7	2452.4	2455.5	2469.4	2479.4	2476.4	2477.9
7.5°	2569.4	2593.0	2616.5	2627.2	2628.8	2635.0	2637.4
10°	2650.5	2669.9	2706.2	2700.8	2727.8	2743.4	2717.8
12.5°	2728.5	2754.6	2779.9	2786.8	2802.2	2807.1	2797.0
15°	2799.0	2813.0	2814.6	2810.7	2815.3	2811.5	2796.7
17.5°	2733.1	2710.6	2664.7	2643.0	2625.9	2600.5	2590.3
20°	2624.1	2557.6	2480.2	2449.3	2412.9	2341.7	2358.7
22.5°	2388.9	2313.1	2235.7	2145.4	2102.1	2034.7	2030.6
25°	2022.9	1892.1	1748.2	1647.6	1588.7	1521.5	1492.0
27.5°	1572.8	1408.2	1290.2	1230.4	1176.1	1122.8	1120.5
30°	1276.9	1153.1	1061.8	1010.7	977.3	954.9	959.6
32.5°	1076.3	991.5	929.9	887.5	862.8	846.0	845.7
35°	879.9	821.8	782.3	764.6	746.8	734.4	735.2
37.5°	753.0	718.1	696.2	676.5	665.4	659.3	655.9
40°	687.9	659.3	642.3	630.7	621.4	612.9	611.4
42.5°	636.6	612.9	595.9	586.7	578.0	572.1	570.5
45°	564.9	545.5	530.1	520.1	516.1	510.8	510.8
47.5°	502.5	483.5	471.4	465.1	458.5	454.8	454.7
50°	460.5	445.8	434.9	431.0	425.7	423.3	422.5
52.5°	422.7	411.7	403.9	401.3	399.0	396.1	396.6
55°	371.4	365.3	362.1	359.8	356.0	351.3	354.5
57.5°	328.3	323.1	314.7	307.4	303.9	300.5	301.8
60°	297.9	287.1	276.3	267.7	265.4	258.4	258.4
62.5°	259.5	244.4	231.1	226.3	224.0	220.8	220.0
65°	199.7	193.5	190.4	187.2	185.7	185.7	184.2
67.5°	165.4	163.0	159.6	158.8	157.2	156.8	156.3
70°	146.2	143.2	141.6	140.9	139.3	140.1	137.7
72.5°	127.6	125.2	124.9	122.9	122.0	122.1	120.4
75°	100.6	100.6	99.9	99.1	97.6	96.7	97.6
77.5°	77.4	77.6	76.1	76.0	75.8	76.0	75.2
80°	61.9	62.7	61.9	61.1	60.4	61.1	60.4
82.5°	48.9	47.9	47.7	47.6	47.4	46.9	46.8
85°	27.9	28.7	27.9	27.1	27.1	27.1	27.9
87.5°	16.3	16.6	16.8	16.9	17.0	17.1	16.6
90°	28.8	30.2	31.2	31.7	32.2	32.8	33.3
92.5°	30.8	31.5	32.0	32.3	32.7	33.0	33.3
95°	52.3	53.6	54.2	53.9	53.6	53.4	53.1
97.5°	67.8	68.9	69.6	69.9	70.3	70.6	70.9
100°	77.0	79.2	80.6	81.1	81.7	82.2	82.8
102.5°	81.0	83.8	85.6	86.3	87.2	88.0	88.7
105°	84.4	87.5	89.5	90.6	91.7	92.8	93.9
107.5°	96.2	93.2	92.2	93.3	94.4	95.5	96.6
110°	133.8	106.3	93.2	94.3	95.4	96.5	97.6



TEST NUMBER: P331857-840

CATALOG NUMBER: S122RDIW-S1005D1240U840-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	244.9	144.7	95.0	95.9	96.8	97.7	98.6
115°	380.9	253.8	180.4	160.6	140.9	121.1	101.3
117.5°	751.9	721.2	673.4	608.4	543.5	478.6	413.5
120°	915.3	918.7	901.8	864.7	827.7	790.6	753.6
122.5°	969.8	971.7	969.1	961.9	954.7	947.6	940.3
125°	1049.7	1051.6	1052.9	1053.7	1054.6	1055.4	1056.2
127.5°	1124.4	1127.2	1128.7	1128.8	1129.0	1129.1	1129.3
130°	1171.5	1174.5	1175.9	1175.6	1175.4	1175.1	1174.8
132.5°	1216.6	1219.2	1220.3	1220.1	1219.8	1219.5	1219.3
135°	1281.8	1284.6	1285.7	1285.2	1284.6	1284.0	1283.5
137.5°	1342.2	1344.9	1345.7	1344.8	1343.9	1343.0	1342.0
140°	1381.1	1383.6	1384.1	1382.7	1381.4	1380.0	1378.7
142.5°	1417.0	1419.3	1419.7	1418.4	1416.9	1415.5	1414.2
145°	1467.1	1469.1	1469.4	1467.9	1466.6	1465.2	1463.9
147.5°	1510.7	1512.1	1512.2	1511.1	1509.8	1508.7	1507.6
150°	1538.0	1539.6	1539.7	1538.4	1537.0	1535.6	1534.3
152.5°	1562.7	1564.4	1564.3	1562.5	1560.6	1558.8	1557.0
155°	1596.1	1597.7	1597.4	1595.2	1593.1	1590.8	1588.6
157.5°	1624.4	1626.3	1626.1	1624.0	1621.8	1619.7	1617.5
160°	1640.5	1642.1	1642.0	1640.1	1638.2	1636.3	1634.4
162.5°	1656.0	1657.9	1657.6	1655.3	1652.8	1650.5	1648.2
165°	1674.7	1676.6	1676.6	1674.7	1672.7	1670.8	1668.9
167.5°	1690.2	1692.1	1691.9	1689.4	1687.0	1684.5	1682.0
170°	1698.2	1700.1	1699.8	1697.4	1694.9	1692.4	1689.9
172.5°	1704.0	1706.0	1705.8	1703.2	1700.8	1698.3	1695.9
175°	1710.5	1712.4	1712.0	1709.3	1706.6	1703.7	1701.0
177.5°	1710.8	1712.4	1712.1	1710.2	1708.2	1706.3	1704.2
180°	1707.2	1707.2	1707.2	1707.2	1707.2	1707.2	1707.2

(END OF REPORT)