

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332477-927

Luminaire Tested: **S123RDIW-S1165D755U927-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332477-927
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-9,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123RDIW-S1165D755U927-4F0-1E-UDD-F1
Description: DEFINE 3 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 1165 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 755 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5544.6 lumens
Efficiency: N/A
Efficacy: 92.7 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.06 / 1.22
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 59.8
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332477-927

CATALOG NUMBER: S123RDIW-S1165D755U927-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P332477-927

CATALOG NUMBER: S123RDIW-S1165D755U927-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	110	110	110	110	103	103	103	103	90	90	90	79	79	79	68	68	68	63
1	101	97	93	90	95	91	88	85	80	77	75	70	68	66	60	59	58	54
2	92	85	79	74	86	80	75	70	71	66	63	62	59	56	54	51	49	45
3	84	75	68	62	79	71	64	59	63	58	53	55	51	48	48	45	43	39
4	78	67	59	53	72	63	56	50	56	50	46	49	45	41	43	40	37	34
5	71	60	52	46	67	56	49	44	50	44	40	44	40	36	39	35	32	30
6	66	54	46	40	62	51	44	38	45	39	35	40	36	32	36	32	29	26
7	61	49	41	35	57	46	39	34	41	35	31	37	32	28	33	29	26	23
8	57	44	37	31	53	42	35	30	38	32	28	34	29	25	30	26	23	21
9	53	41	33	28	50	39	32	27	35	29	25	31	26	23	28	24	21	19
10	50	37	30	25	47	36	29	24	32	27	23	29	24	21	26	22	19	17

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	16527	16527	16527
5°	16590	16361	16455
10°	16497	16156	16101
15°	16319	15778	15611
20°	16076	15306	14948
25°	15824	14775	14301
30°	15493	14162	13387
35°	15152	13548	12550
40°	14838	12826	11514
45°	14425	12113	10577
50°	13971	11302	9530
55°	13508	10376	8552
60°	13082	9384	7481
65°	12528	8308	6406
70°	11833	6977	5174
75°	10821	5490	4870
80°	9651	4860	4475
85°	8151	4310	4001



TEST NUMBER: P332477-927

CATALOG NUMBER: S123RDIW-S1165D755U927-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	144.2	2.6
10°-20°	401.2	7.2
20°-30°	577.6	10.4
30°-40°	650.7	11.7
40°-50°	622.5	11.2
50°-60°	509.7	9.2
60°-70°	343.9	6.2
70°-80°	173.0	3.1
80°-90°	48.0	0.9
90°-100°	48.8	0.9
100°-110°	145.9	2.6
110°-120°	248.2	4.5
120°-130°	326.5	5.9
130°-140°	367.0	6.6
140°-150°	360.7	6.5
150°-160°	303.7	5.5
160°-170°	202.2	3.6
170°-180°	70.8	1.3
0°-30°	1123.0	20.3
0°-40°	1773.6	32.0
0°-60°	2905.8	52.4
0°-90°	3470.8	62.6
90°-120°	442.9	8.0
90°-150°	1497.2	27.0
90°-180°	2074.0	37.4
0°-180°	5544.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1535	1535	1535	1535	1535	
5°	1535	1529	1514	1525	1523	146
15°	1464	1450	1416	1410	1401	412
25°	1332	1300	1244	1219	1204	613
35°	1153	1106	1031	979	955	721
45°	948	889	796	727	695	731
55°	720	656	553	483	456	645
65°	492	422	326	268	252	487
75°	260	200	132	120	117	278
85°	66	40	35	32	32	74
90°	1	7	14	16	18	5
95°	35	39	44	46	46	39
105°	132	134	139	139	140	142
115°	250	251	250	251	250	247
125°	366	367	366	364	362	326
135°	474	478	477	475	474	366
145°	576	577	579	578	576	359
155°	659	659	660	662	658	303
165°	718	716	716	719	716	202
175°	747	745	744	748	744	71
180°	748	748	748	748	748	



TEST NUMBER: P332477-927

CATALOG NUMBER: S123RDIW-S1165D755U927-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1535.4	1535.4	1535.4	1535.4	1535.4	1535.4	1535.4	1535.4	1535.4	1535.4	1535.4
2.5°	1540.4	1539.4	1538.6	1537.7	1536.8	1535.0	1532.4	1529.7	1527.1	1524.4	1526.9
5°	1535.4	1534.0	1532.6	1531.2	1529.9	1527.5	1524.2	1520.8	1517.5	1514.2	1516.7
7.5°	1521.1	1519.7	1518.2	1516.7	1515.2	1512.3	1508.0	1503.6	1499.4	1495.0	1496.4
10°	1509.3	1507.3	1505.4	1503.4	1501.5	1498.0	1493.0	1488.0	1483.0	1478.1	1478.4
12.5°	1492.3	1490.2	1488.0	1485.8	1483.7	1479.6	1473.5	1467.4	1461.3	1455.2	1455.0
15°	1464.4	1461.3	1458.3	1455.2	1452.2	1446.8	1439.1	1431.3	1423.6	1415.9	1414.4
17.5°	1429.3	1425.8	1422.2	1418.6	1415.2	1408.4	1398.6	1388.7	1378.9	1369.0	1366.1
20°	1403.4	1399.0	1394.6	1390.1	1385.7	1378.2	1367.7	1357.2	1346.6	1336.2	1332.5
22.5°	1374.5	1369.4	1364.3	1359.2	1354.2	1346.0	1334.8	1323.7	1312.5	1301.2	1296.8
25°	1332.4	1325.5	1318.6	1311.6	1304.7	1294.9	1282.1	1269.5	1256.7	1244.0	1238.2
27.5°	1281.4	1273.7	1266.1	1258.5	1250.8	1239.9	1225.7	1211.6	1197.4	1183.2	1175.1
30°	1246.5	1238.2	1229.9	1221.5	1213.3	1201.3	1185.9	1170.4	1154.9	1139.4	1130.0
32.5°	1211.6	1202.2	1192.8	1183.4	1174.0	1161.1	1144.7	1128.3	1111.9	1095.6	1085.3
35°	1153.1	1143.1	1133.1	1123.2	1113.3	1099.7	1082.5	1065.4	1048.2	1031.0	1019.1
37.5°	1093.8	1082.8	1071.7	1060.6	1049.6	1034.8	1016.5	998.2	979.9	961.6	948.1
40°	1056.0	1043.8	1031.6	1019.5	1007.3	991.3	971.7	952.0	932.4	912.8	898.3
42.5°	1013.1	1000.9	988.8	976.6	964.4	948.2	927.9	907.5	887.2	867.0	851.2
45°	947.6	935.2	922.7	910.3	897.8	880.9	859.6	838.3	817.0	795.7	779.9
47.5°	882.1	868.5	854.8	841.1	827.4	809.9	788.6	767.3	746.0	724.8	707.6
50°	834.3	821.3	808.3	795.3	782.3	764.6	742.2	719.8	697.4	674.9	657.7
52.5°	791.5	777.4	763.3	749.2	735.0	716.8	694.7	672.5	650.3	628.1	610.3
55°	719.8	706.2	692.6	679.1	665.5	647.0	623.4	599.9	576.4	552.9	536.9
57.5°	653.5	638.7	623.9	609.2	594.4	575.2	551.6	527.9	504.3	480.7	465.5
60°	607.7	592.5	577.3	562.1	546.8	527.7	504.7	481.8	458.8	435.9	420.9
62.5°	561.8	546.6	531.4	516.2	501.0	481.9	458.9	435.9	413.0	390.0	376.0
65°	491.9	476.7	461.4	446.2	431.0	412.6	391.0	369.4	347.8	326.2	312.7
67.5°	421.9	406.5	391.1	375.7	360.4	342.3	321.6	300.9	280.2	259.5	249.4
70°	376.0	361.2	346.2	331.2	316.3	299.1	279.8	260.4	241.1	221.7	212.0
72.5°	330.3	315.5	300.8	286.1	271.3	255.2	237.6	220.0	202.4	184.8	176.9
75°	260.2	247.0	233.7	220.4	207.2	192.9	177.7	162.4	147.2	132.0	129.2
77.5°	196.5	184.5	172.5	160.5	148.5	137.5	127.8	118.0	108.1	98.4	96.9
80°	155.7	144.3	132.9	121.6	110.3	101.7	95.9	90.1	84.3	78.4	77.6
82.5°	116.8	107.0	97.2	87.4	77.6	71.4	68.7	65.9	63.2	60.5	59.7
85°	66.0	59.9	53.8	47.8	41.7	38.2	37.4	36.5	35.7	34.9	34.3
87.5°	24.0	21.9	19.6	17.5	15.4	14.4	14.7	15.1	15.4	15.8	15.7
90°	0.6	1.9	3.2	4.5	5.8	7.3	9.0	10.7	12.4	14.1	14.7
92.5°	14.3	15.1	16.0	16.9	17.7	18.7	19.6	20.7	21.6	22.6	23.0
95°	34.7	35.6	36.5	37.5	38.3	39.3	40.4	41.4	42.5	43.5	44.0
97.5°	61.6	62.3	63.0	63.7	64.3	65.0	65.8	66.5	67.3	68.1	68.7
100°	79.9	80.7	81.5	82.3	83.1	83.8	84.4	85.2	85.8	86.4	86.8
102.5°	101.2	101.6	102.1	102.5	103.0	103.7	104.6	105.4	106.2	107.1	107.5
105°	132.3	132.5	132.8	133.1	133.3	134.0	135.2	136.4	137.6	138.8	138.8
107.5°	168.5	168.7	168.8	169.0	169.1	169.4	169.9	170.4	170.9	171.3	171.7
110°	191.1	191.4	191.6	191.9	192.1	192.4	192.7	192.9	193.2	193.5	194.0



TEST NUMBER: P332477-927

CATALOG NUMBER: S123RDIW-S1165D755U927-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	214.6	214.8	214.9	215.1	215.2	215.3	215.4	215.5	215.5	215.6	216.2
115°	249.9	250.3	250.6	251.0	251.4	251.5	251.3	251.0	250.7	250.5	250.6
117.5°	285.4	285.7	285.9	286.2	286.5	286.5	286.1	285.7	285.4	285.0	285.0
120°	307.5	308.3	309.1	309.9	310.7	310.7	310.1	309.4	308.8	308.1	308.0
122.5°	330.6	331.1	331.7	332.3	332.9	333.0	332.6	332.3	332.0	331.6	331.3
125°	365.8	366.1	366.5	366.9	367.3	367.3	367.1	366.9	366.5	366.3	365.8
127.5°	398.2	399.0	399.9	400.7	401.6	401.8	401.6	401.2	400.9	400.7	399.9
130°	419.9	420.9	421.9	422.9	424.0	424.4	424.0	423.6	423.2	422.8	422.2
132.5°	441.5	442.5	443.5	444.6	445.7	446.0	445.8	445.4	445.1	444.9	444.3
135°	474.5	475.3	476.1	476.9	477.6	478.0	477.8	477.7	477.6	477.4	476.9
137.5°	505.1	505.7	506.4	507.1	507.7	508.2	508.5	508.9	509.2	509.5	509.0
140°	526.2	526.9	527.6	528.2	528.9	529.3	529.4	529.5	529.7	529.8	529.7
142.5°	545.6	546.2	546.8	547.5	548.1	548.6	548.8	549.1	549.3	549.5	549.4
145°	575.7	575.9	576.2	576.4	576.7	577.0	577.4	577.8	578.2	578.6	578.5
147.5°	602.0	602.5	602.9	603.4	603.9	604.3	604.7	605.0	605.4	605.8	605.8
150°	620.4	620.6	620.8	621.2	621.4	621.6	621.9	622.2	622.4	622.7	622.7
152.5°	635.4	635.7	636.1	636.5	636.8	637.1	637.2	637.4	637.5	637.7	637.9
155°	659.2	659.2	659.2	659.2	659.2	659.2	659.3	659.5	659.6	659.7	660.3
157.5°	679.4	679.2	679.1	678.9	678.7	678.7	678.8	678.9	679.1	679.1	679.7
160°	692.1	691.8	691.6	691.3	691.0	690.9	690.9	690.9	690.9	690.9	691.6
162.5°	703.4	703.0	702.6	702.3	701.9	701.8	701.9	702.0	702.1	702.2	702.8
165°	718.0	717.6	717.2	716.8	716.4	716.1	716.1	716.1	716.1	716.1	716.9
167.5°	729.6	729.0	728.6	728.0	727.5	727.3	727.4	727.5	727.6	727.7	728.5
170°	736.2	735.6	735.1	734.6	734.0	733.8	733.8	733.8	733.8	733.8	734.7
172.5°	741.3	740.8	740.3	739.7	739.3	738.9	738.9	738.9	738.9	738.9	739.8
175°	746.7	746.2	745.7	745.2	744.7	744.4	744.4	744.4	744.4	744.4	745.2
177.5°	749.0	748.5	748.1	747.7	747.3	747.1	747.1	747.1	747.1	747.1	747.7
180°	748.5	748.5	748.5	748.5	748.5	748.5	748.5	748.5	748.5	748.5	748.5



TEST NUMBER: P332477-927

CATALOG NUMBER: S123RDIW-S1165D755U927-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1535.4	1535.4	1535.4	1535.4	1535.4	1535.4	1535.4	1535.4
2.5°	1529.3	1531.8	1534.1	1535.2	1534.7	1534.3	1533.8	1533.3
5°	1519.2	1521.7	1524.2	1525.1	1524.6	1524.0	1523.4	1522.9
7.5°	1497.8	1499.2	1500.6	1500.8	1499.8	1498.9	1497.9	1497.0
10°	1478.7	1478.9	1479.2	1478.7	1477.3	1475.9	1474.5	1473.1
12.5°	1454.8	1454.7	1454.5	1453.7	1452.1	1450.4	1448.8	1447.2
15°	1413.1	1411.7	1410.3	1408.7	1406.7	1404.8	1402.8	1400.9
17.5°	1363.2	1360.2	1357.2	1354.4	1351.5	1348.6	1345.8	1342.8
20°	1329.0	1325.3	1321.8	1318.3	1314.9	1311.6	1308.4	1305.0
22.5°	1292.3	1287.9	1283.3	1279.5	1276.4	1273.4	1270.3	1267.2
25°	1232.4	1226.5	1220.8	1216.3	1213.3	1210.2	1207.2	1204.1
27.5°	1167.0	1159.0	1150.9	1144.5	1139.9	1135.3	1130.6	1125.9
30°	1120.5	1111.2	1101.8	1094.9	1090.4	1086.0	1081.6	1077.1
32.5°	1075.0	1064.7	1054.4	1046.9	1042.3	1037.6	1033.0	1028.3
35°	1007.3	995.4	983.5	975.0	970.0	965.0	960.0	955.1
37.5°	934.5	921.1	907.5	897.7	891.6	885.4	879.3	873.1
40°	884.0	869.6	855.2	844.9	838.4	832.1	825.8	819.4
42.5°	835.5	819.8	804.1	793.4	787.7	782.0	776.3	770.6
45°	764.1	748.4	732.6	721.4	714.8	708.1	701.5	694.8
47.5°	690.4	673.3	656.1	644.6	638.7	632.7	626.8	620.9
50°	640.6	623.4	606.3	594.5	588.2	581.8	575.4	569.1
52.5°	592.5	574.6	556.8	545.0	539.3	533.7	528.0	522.3
55°	520.8	504.7	488.7	477.9	472.4	466.8	461.3	455.7
57.5°	450.4	435.1	420.0	410.0	405.4	400.7	395.9	391.3
60°	405.9	391.0	376.0	366.2	361.6	356.8	352.1	347.5
62.5°	361.9	347.8	333.7	324.3	319.3	314.4	309.5	304.6
65°	299.1	285.6	272.0	263.7	260.7	257.6	254.6	251.5
67.5°	239.2	229.1	219.0	212.3	209.1	205.7	202.5	199.2
70°	202.2	192.6	182.9	176.6	173.5	170.5	167.4	164.4
72.5°	169.0	161.1	153.1	148.5	147.3	146.0	144.7	143.5
75°	126.4	123.7	120.9	119.3	118.7	118.2	117.6	117.1
77.5°	95.4	93.9	92.4	91.3	90.8	90.2	89.7	89.1
80°	76.8	76.0	75.1	74.5	73.9	73.4	72.8	72.2
82.5°	58.9	58.1	57.2	56.7	56.6	56.5	56.4	56.3
85°	33.7	33.2	32.6	32.4	32.4	32.4	32.4	32.4
87.5°	15.5	15.4	15.3	15.1	15.0	14.8	14.7	14.5
90°	15.1	15.7	16.2	16.6	16.9	17.1	17.3	17.7
92.5°	23.4	23.8	24.2	24.4	24.2	24.1	23.9	23.8
95°	44.5	45.1	45.6	45.9	45.9	45.9	45.9	45.9
97.5°	69.3	69.9	70.5	70.7	70.7	70.7	70.6	70.6
100°	87.2	87.6	88.0	88.3	88.6	88.9	89.1	89.4
102.5°	107.9	108.3	108.7	108.8	108.8	108.8	108.7	108.7
105°	138.8	138.8	138.8	138.9	139.2	139.4	139.7	140.0
107.5°	172.1	172.6	173.0	173.2	173.0	172.9	172.7	172.5
110°	194.5	195.0	195.5	195.7	195.4	195.1	194.9	194.6



TEST NUMBER: P332477-927

CATALOG NUMBER: S123RDIW-S1165D755U927-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	216.8	217.5	218.1	218.3	218.3	218.2	218.2	218.2
115°	250.7	250.9	251.0	251.0	250.9	250.7	250.6	250.5
117.5°	285.0	284.9	284.9	284.8	284.4	284.0	283.7	283.3
120°	307.8	307.7	307.6	307.4	307.1	306.9	306.6	306.3
122.5°	331.0	330.6	330.3	329.9	329.5	329.2	328.8	328.4
125°	365.3	364.7	364.2	363.7	363.2	362.7	362.1	361.6
127.5°	399.2	398.5	397.8	397.0	396.5	395.9	395.3	394.7
130°	421.8	421.2	420.6	419.9	419.1	418.1	417.2	416.3
132.5°	443.6	443.0	442.4	441.7	441.0	440.3	439.6	438.9
135°	476.4	475.9	475.4	475.0	474.7	474.4	474.2	473.9
137.5°	508.4	507.9	507.4	506.8	506.4	505.8	505.3	504.9
140°	529.5	529.4	529.3	528.7	527.8	526.9	526.0	525.1
142.5°	549.3	549.1	549.0	548.6	547.9	547.2	546.4	545.7
145°	578.3	578.2	578.1	577.7	577.2	576.7	576.2	575.7
147.5°	605.8	605.8	605.8	605.4	604.6	603.8	603.0	602.2
150°	622.7	622.7	622.7	622.3	621.5	620.8	620.0	619.2
152.5°	638.2	638.3	638.6	638.3	637.6	637.0	636.3	635.6
155°	660.8	661.3	661.8	661.6	660.7	659.8	658.9	658.0
157.5°	680.2	680.8	681.4	681.2	680.5	679.8	679.1	678.3
160°	692.2	692.8	693.5	693.6	693.1	692.5	692.0	691.5
162.5°	703.5	704.2	704.8	704.7	703.9	703.1	702.2	701.3
165°	717.7	718.5	719.3	719.2	718.4	717.4	716.5	715.6
167.5°	729.3	730.2	730.9	730.9	730.2	729.3	728.5	727.7
170°	735.6	736.6	737.4	737.4	736.6	735.6	734.7	733.8
172.5°	740.6	741.4	742.2	742.2	741.2	740.4	739.4	738.6
175°	746.0	746.7	747.5	747.5	746.6	745.6	744.7	743.8
177.5°	748.4	749.0	749.6	749.6	748.8	748.1	747.3	746.6
180°	748.5	748.5	748.5	748.5	748.5	748.5	748.5	748.5

(END OF REPORT)