

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332401-927

Luminaire Tested: **S123RDIW-S340D1030U927-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P332401-927  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-9,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S123RDIW-S340D1030U927-4F0-1E-UDD-F1  
Description: DEFINE 3 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 340 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED  
HOUSING  
UPLIGHT 1030 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 3861.9 lumens  
Efficiency: N/A  
Efficacy: 101.6 lumens/watt  
Spacing Criteria (0/90/45): 1.21 / 1.06 / 1.22  
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')  
CIE Type: Semi-Indirect


Input Watts (W): 38  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332401-927

CATALOG NUMBER: S123RDIW-S340D1030U927-4F0-1E-UDD-F1

### Luminous Intensity Polar Plot





TEST NUMBER: P332401-927

CATALOG NUMBER: S123RDIW-S340D1030U927-4F0-1E-UDD-F1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	102	102	102	102	91	91	91	91	70	70	70	52	52	52	35	35	35	27
1	93	89	85	82	83	79	76	73	62	60	58	46	44	43	31	30	30	23
2	85	78	72	67	75	69	65	60	54	51	48	40	38	36	27	26	25	19
3	77	68	61	56	69	61	55	51	48	44	41	36	33	31	24	23	22	17
4	71	60	53	47	63	54	48	43	43	38	35	32	29	27	22	20	19	14
5	65	54	46	40	58	48	42	37	38	33	30	29	25	23	20	18	16	13
6	60	48	40	35	53	43	37	32	34	29	26	26	23	20	18	16	14	11
7	55	43	36	30	49	39	32	28	31	26	23	23	20	18	16	14	13	10
8	51	39	32	27	45	35	29	24	28	23	20	21	18	16	15	13	11	9
9	47	36	28	24	42	32	26	22	26	21	18	20	16	14	14	12	10	8
10	44	33	26	21	39	30	23	19	24	19	16	18	15	13	13	11	9	7

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	4899	4899	4899
5°	4917	4850	4878
10°	4889	4790	4773
15°	4837	4677	4628
20°	4765	4537	4431
25°	4691	4380	4240
30°	4593	4197	3967
35°	4491	4016	3720
40°	4398	3801	3413
45°	4276	3589	3136
50°	4141	3349	2825
55°	4003	3076	2535
60°	3877	2781	2217
65°	3713	2463	1897
70°	3509	2068	1533
75°	3211	1626	1443
80°	2858	1444	1327
85°	2421	1272	1186



TEST NUMBER: P332401-927

CATALOG NUMBER: S123RDIW-S340D1030U927-4F0-1E-UDD-F1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	42.7	1.1
10°-20°	118.9	3.1
20°-30°	171.2	4.4
30°-40°	192.9	5.0
40°-50°	184.5	4.8
50°-60°	151.1	3.9
60°-70°	101.9	2.6
70°-80°	51.3	1.3
80°-90°	16.6	0.4
90°-100°	66.6	1.7
100°-110°	199.2	5.2
110°-120°	338.8	8.8
120°-130°	445.7	11.5
130°-140°	500.9	13.0
140°-150°	492.4	12.8
150°-160°	414.5	10.7
160°-170°	275.9	7.1
170°-180°	96.6	2.5
0°-30°	332.9	8.6
0°-40°	525.7	13.6
0°-60°	861.4	22.3
0°-90°	1031.2	26.7
90°-120°	604.6	15.7
90°-150°	2043.6	52.9
90°-180°	2831.0	73.3
0°-180°	3861.9	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	455	455	455	455	455	
5°	455	453	449	452	452	43
15°	434	430	420	418	415	122
25°	395	385	369	361	357	182
35°	342	328	306	290	283	214
45°	281	264	236	215	206	217
55°	213	195	164	143	135	191
65°	146	125	97	79	74	144
75°	77	59	39	36	35	82
85°	20	12	10	10	10	22
90°	1	9	19	22	24	4
95°	47	53	59	62	63	53
105°	181	182	189	190	191	193
115°	341	343	342	343	342	337
125°	499	501	500	497	494	445
135°	648	652	652	649	647	499
145°	786	787	790	789	786	491
155°	900	900	900	903	898	414
165°	980	978	978	982	977	276
175°	1019	1016	1016	1020	1015	97
180°	1022	1022	1022	1022	1022	



TEST NUMBER: P332401-927

CATALOG NUMBER: S123RDIW-S340D1030U927-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	455.1	455.1	455.1	455.1	455.1	455.1	455.1	455.1	455.1	455.1	455.1
2.5°	456.6	456.3	456.1	455.8	455.6	455.0	454.2	453.4	452.7	451.9	452.6
5°	455.1	454.7	454.3	453.9	453.4	452.8	451.8	450.8	449.8	448.9	449.6
7.5°	450.9	450.4	450.0	449.6	449.2	448.3	447.0	445.8	444.4	443.1	443.5
10°	447.3	446.8	446.2	445.7	445.0	444.0	442.6	441.1	439.6	438.2	438.2
12.5°	442.4	441.7	441.1	440.5	439.8	438.6	436.7	435.0	433.2	431.3	431.3
15°	434.1	433.2	432.3	431.3	430.5	428.9	426.6	424.3	422.0	419.7	419.3
17.5°	423.7	422.6	421.6	420.5	419.5	417.5	414.5	411.6	408.8	405.8	405.0
20°	416.0	414.7	413.4	412.1	410.7	408.5	405.4	402.3	399.2	396.1	395.0
22.5°	407.4	405.9	404.4	402.9	401.4	399.0	395.7	392.4	389.0	385.7	384.4
25°	395.0	392.9	390.9	388.8	386.7	383.8	380.1	376.3	372.5	368.8	367.0
27.5°	379.9	377.6	375.3	373.0	370.7	367.6	363.4	359.1	354.9	350.7	348.3
30°	369.5	367.0	364.6	362.1	359.7	356.1	351.5	346.9	342.3	337.7	334.9
32.5°	359.2	356.3	353.6	350.8	348.0	344.2	339.3	334.5	329.6	324.7	321.7
35°	341.8	338.8	335.9	333.0	330.0	326.0	320.9	315.8	310.7	305.6	302.1
37.5°	324.2	320.9	317.7	314.4	311.1	306.7	301.3	295.9	290.5	285.0	281.1
40°	313.0	309.4	305.8	302.2	298.6	293.8	288.0	282.2	276.4	270.5	266.3
42.5°	300.3	296.7	293.1	289.5	285.9	281.1	275.0	269.0	263.0	257.0	252.3
45°	280.9	277.2	273.5	269.8	266.1	261.1	254.8	248.5	242.2	235.8	231.2
47.5°	261.5	257.5	253.3	249.3	245.3	240.1	233.8	227.4	221.2	214.8	209.8
50°	247.3	243.4	239.6	235.8	231.9	226.6	220.0	213.3	206.7	200.0	195.0
52.5°	234.6	230.4	226.2	222.0	217.9	212.5	205.9	199.3	192.7	186.2	180.9
55°	213.3	209.3	205.3	201.3	197.3	191.8	184.8	177.8	170.9	163.9	159.1
57.5°	193.7	189.3	185.0	180.5	176.2	170.5	163.5	156.5	149.5	142.5	138.0
60°	180.1	175.6	171.1	166.6	162.1	156.5	149.6	142.8	136.0	129.2	124.8
62.5°	166.5	162.0	157.5	153.0	148.5	142.8	136.0	129.2	122.4	115.6	111.5
65°	145.8	141.3	136.8	132.3	127.8	122.3	115.9	109.5	103.1	96.7	92.7
67.5°	125.1	120.5	115.9	111.4	106.8	101.5	95.3	89.2	83.0	76.9	73.9
70°	111.5	107.0	102.6	98.2	93.8	88.6	82.9	77.2	71.5	65.7	62.8
72.5°	97.9	93.6	89.2	84.8	80.4	75.7	70.4	65.2	60.0	54.7	52.4
75°	77.2	73.2	69.2	65.4	61.4	57.2	52.7	48.2	43.6	39.1	38.3
77.5°	58.2	54.7	51.1	47.5	44.0	40.8	37.9	34.9	32.1	29.2	28.8
80°	46.1	42.8	39.5	36.0	32.7	30.2	28.4	26.7	25.0	23.3	23.0
82.5°	34.6	31.7	28.8	25.9	23.0	21.2	20.4	19.6	18.8	17.9	17.7
85°	19.6	17.7	15.9	14.2	12.4	11.3	11.1	10.9	10.6	10.3	10.1
87.5°	7.2	6.9	6.5	6.2	5.8	5.9	6.3	6.7	7.2	7.7	7.8
90°	0.8	2.6	4.4	6.2	7.9	10.0	12.3	14.7	17.0	19.3	20.0
92.5°	19.4	20.6	21.9	23.1	24.2	25.5	26.9	28.2	29.5	30.8	31.4
95°	47.4	48.6	49.8	51.1	52.4	53.7	55.1	56.6	58.0	59.4	60.1
97.5°	84.1	85.0	86.0	86.9	87.9	88.8	89.8	90.9	91.9	92.9	93.8
100°	109.2	110.2	111.3	112.3	113.4	114.4	115.3	116.2	117.1	118.0	118.5
102.5°	138.1	138.7	139.3	140.0	140.6	141.5	142.7	143.9	145.0	146.2	146.8
105°	180.6	180.9	181.3	181.6	182.0	183.0	184.6	186.2	187.8	189.4	189.4
107.5°	230.0	230.2	230.4	230.7	230.8	231.3	232.0	232.6	233.2	233.9	234.4
110°	260.9	261.2	261.6	261.9	262.3	262.6	263.0	263.3	263.7	264.0	264.7



TEST NUMBER: P332401-927

CATALOG NUMBER: S123RDIW-S340D1030U927-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	292.9	293.2	293.3	293.6	293.8	293.9	294.0	294.1	294.1	294.2	295.1
115°	341.1	341.6	342.1	342.7	343.3	343.3	342.9	342.6	342.2	341.9	342.1
117.5°	389.6	389.9	390.3	390.6	391.0	390.9	390.5	390.0	389.5	389.1	389.0
120°	419.8	420.8	421.9	422.9	424.1	424.1	423.2	422.3	421.4	420.6	420.3
122.5°	451.2	452.0	452.8	453.5	454.3	454.5	454.1	453.6	453.1	452.7	452.2
125°	499.2	499.7	500.3	500.8	501.4	501.5	501.1	500.7	500.3	500.0	499.3
127.5°	543.5	544.6	545.8	546.9	548.0	548.4	548.0	547.6	547.2	546.8	545.9
130°	573.1	574.5	575.9	577.3	578.8	579.2	578.7	578.1	577.6	577.0	576.3
132.5°	602.5	604.0	605.4	606.9	608.3	608.8	608.4	608.0	607.6	607.2	606.3
135°	647.7	648.7	649.8	650.9	652.0	652.4	652.2	652.0	651.9	651.6	650.9
137.5°	689.4	690.3	691.2	692.1	693.0	693.6	694.1	694.6	695.1	695.5	694.7
140°	718.3	719.2	720.1	721.0	721.8	722.4	722.5	722.8	722.9	723.1	722.9
142.5°	744.7	745.5	746.4	747.3	748.2	748.8	749.1	749.4	749.8	750.1	749.9
145°	785.7	786.1	786.4	786.8	787.1	787.6	788.1	788.7	789.2	789.7	789.6
147.5°	821.7	822.3	822.9	823.6	824.3	824.8	825.3	825.9	826.3	826.8	826.8
150°	846.7	847.1	847.4	847.8	848.1	848.5	848.8	849.2	849.5	849.9	849.9
152.5°	867.3	867.8	868.2	868.8	869.3	869.6	869.8	870.1	870.3	870.4	870.8
155°	899.7	899.7	899.7	899.7	899.7	899.8	899.9	900.2	900.3	900.5	901.2
157.5°	927.3	927.1	926.9	926.6	926.5	926.4	926.5	926.7	926.9	926.9	927.7
160°	944.6	944.3	943.9	943.6	943.2	943.0	943.0	943.0	943.0	943.0	943.9
162.5°	960.0	959.6	959.0	958.5	958.1	957.8	958.0	958.1	958.3	958.5	959.3
165°	979.9	979.4	978.9	978.3	977.8	977.6	977.6	977.6	977.6	977.6	978.6
167.5°	995.9	995.1	994.4	993.7	993.0	992.7	992.8	993.0	993.2	993.2	994.3
170°	1004.8	1004.1	1003.4	1002.7	1002.0	1001.6	1001.6	1001.6	1001.6	1001.6	1002.8
172.5°	1011.9	1011.1	1010.4	1009.7	1009.0	1008.7	1008.7	1008.7	1008.7	1008.7	1009.8
175°	1019.3	1018.6	1017.9	1017.2	1016.4	1016.1	1016.1	1016.1	1016.1	1016.1	1017.2
177.5°	1022.3	1021.8	1021.2	1020.6	1020.0	1019.8	1019.8	1019.8	1019.8	1019.8	1020.6
180°	1021.7	1021.7	1021.7	1021.7	1021.7	1021.7	1021.7	1021.7	1021.7	1021.7	1021.7



TEST NUMBER: P332401-927

CATALOG NUMBER: S123RDIW-S340D1030U927-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	455.1	455.1	455.1	455.1	455.1	455.1	455.1	455.1
2.5°	453.3	454.0	454.8	455.0	455.0	454.8	454.6	454.6
5°	450.4	451.1	451.8	452.1	451.9	451.8	451.6	451.5
7.5°	444.0	444.4	444.8	444.9	444.6	444.3	444.0	443.8
10°	438.3	438.4	438.5	438.3	437.9	437.5	437.0	436.7
12.5°	431.3	431.2	431.2	430.9	430.4	429.9	429.4	429.0
15°	418.8	418.4	418.0	417.6	417.0	416.4	415.8	415.3
17.5°	404.1	403.2	402.3	401.5	400.6	399.7	398.9	398.1
20°	394.0	392.8	391.8	390.8	389.8	388.8	387.9	386.8
22.5°	383.1	381.8	380.4	379.3	378.3	377.5	376.5	375.7
25°	365.3	363.6	361.9	360.5	359.7	358.8	357.8	357.0
27.5°	345.9	343.6	341.2	339.3	337.9	336.5	335.2	333.7
30°	332.2	329.4	326.6	324.6	323.2	321.9	320.6	319.2
32.5°	318.6	315.6	312.5	310.3	309.0	307.6	306.2	304.8
35°	298.6	295.0	291.5	289.0	287.6	286.1	284.6	283.1
37.5°	277.0	273.0	269.0	266.1	264.3	262.4	260.6	258.8
40°	262.1	257.8	253.5	250.4	248.5	246.7	244.8	242.9
42.5°	247.6	243.0	238.4	235.2	233.5	231.8	230.1	228.4
45°	226.5	221.8	217.1	213.8	211.9	209.9	207.9	206.0
47.5°	204.6	199.6	194.5	191.1	189.3	187.6	185.8	184.0
50°	189.9	184.8	179.7	176.3	174.4	172.5	170.6	168.7
52.5°	175.6	170.3	165.1	161.6	159.9	158.2	156.5	154.8
55°	154.4	149.6	144.9	141.6	140.1	138.4	136.7	135.1
57.5°	133.5	129.0	124.5	121.5	120.2	118.7	117.4	116.0
60°	120.3	115.9	111.5	108.5	107.2	105.8	104.4	103.0
62.5°	107.3	103.1	98.9	96.1	94.7	93.2	91.7	90.3
65°	88.6	84.7	80.6	78.2	77.2	76.4	75.5	74.5
67.5°	70.9	67.9	64.9	62.9	61.9	61.0	60.0	59.1
70°	60.0	57.1	54.2	52.4	51.4	50.5	49.6	48.7
72.5°	50.1	47.8	45.4	44.0	43.6	43.3	42.9	42.5
75°	37.5	36.7	35.8	35.3	35.2	35.0	34.9	34.7
77.5°	28.3	27.8	27.4	27.1	26.9	26.8	26.6	26.5
80°	22.7	22.5	22.3	22.1	21.9	21.7	21.5	21.4
82.5°	17.4	17.2	17.0	16.8	16.8	16.7	16.7	16.7
85°	10.0	9.8	9.7	9.6	9.6	9.6	9.6	9.6
87.5°	7.8	7.9	8.0	8.1	8.1	8.1	8.1	8.1
90°	20.7	21.4	22.1	22.7	23.0	23.4	23.7	24.1
92.5°	31.9	32.6	33.1	33.3	33.0	32.9	32.6	32.4
95°	60.8	61.6	62.3	62.6	62.6	62.6	62.6	62.6
97.5°	94.6	95.4	96.3	96.6	96.5	96.5	96.4	96.3
100°	119.1	119.6	120.1	120.6	120.9	121.3	121.6	122.0
102.5°	147.3	147.8	148.4	148.6	148.5	148.5	148.4	148.3
105°	189.4	189.4	189.4	189.6	190.0	190.3	190.7	191.0
107.5°	235.0	235.6	236.1	236.3	236.1	235.9	235.7	235.4
110°	265.5	266.2	266.9	267.0	266.7	266.3	266.0	265.6





TEST NUMBER: P332401-927

CATALOG NUMBER: S123RDIW-S340D1030U927-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	296.0	296.8	297.6	298.0	297.9	297.9	297.9	297.8
115°	342.2	342.5	342.6	342.6	342.5	342.2	342.1	341.9
117.5°	389.0	389.0	389.0	388.6	388.2	387.7	387.1	386.7
120°	420.2	420.0	419.9	419.5	419.2	418.8	418.5	418.1
122.5°	451.7	451.2	450.8	450.3	449.8	449.3	448.9	448.3
125°	498.6	497.9	497.2	496.5	495.7	495.0	494.3	493.6
127.5°	544.9	543.9	542.9	541.9	541.1	540.3	539.5	538.7
130°	575.6	574.9	574.2	573.2	572.0	570.7	569.5	568.2
132.5°	605.5	604.7	603.8	602.9	601.9	600.9	600.0	599.0
135°	650.2	649.5	648.8	648.3	647.9	647.6	647.2	646.9
137.5°	694.0	693.2	692.5	691.8	691.1	690.5	689.8	689.1
140°	722.8	722.5	722.4	721.7	720.4	719.2	718.0	716.7
142.5°	749.7	749.6	749.4	748.8	747.8	746.9	745.9	745.0
145°	789.4	789.2	789.0	788.5	787.8	787.1	786.4	785.7
147.5°	826.8	826.8	826.8	826.2	825.2	824.1	823.1	822.0
150°	849.9	849.9	849.9	849.4	848.3	847.2	846.2	845.1
152.5°	871.0	871.3	871.6	871.3	870.4	869.4	868.5	867.6
155°	901.9	902.6	903.3	903.1	901.8	900.6	899.4	898.1
157.5°	928.4	929.2	929.9	929.9	928.8	927.9	926.9	925.8
160°	944.8	945.7	946.6	946.7	945.9	945.2	944.5	943.8
162.5°	960.2	961.1	962.0	961.9	960.8	959.6	958.5	957.3
165°	979.7	980.7	981.8	981.8	980.5	979.2	977.9	976.8
167.5°	995.5	996.6	997.7	997.7	996.6	995.5	994.3	993.2
170°	1004.1	1005.4	1006.6	1006.6	1005.4	1004.1	1002.8	1001.6
172.5°	1010.9	1012.0	1013.1	1013.0	1011.8	1010.5	1009.2	1008.1
175°	1018.2	1019.3	1020.3	1020.3	1019.0	1017.7	1016.5	1015.3
177.5°	1021.4	1022.3	1023.2	1023.1	1022.1	1021.1	1020.1	1019.1
180°	1021.7	1021.7	1021.7	1021.7	1021.7	1021.7	1021.7	1021.7

(END OF REPORT)