

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332405-927

Luminaire Tested: **S123RDIW-S340D1320U927-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332405-927
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-9,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123RDIW-S340D1320U927-4F0-1E-UDD-F1
Description: DEFINE 3 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 340 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 1320 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4655.9 lumens
Efficiency: N/A
Efficacy: 99.9 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.06 / 1.22
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 46.6
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332405-927

CATALOG NUMBER: S123RDIW-S340D1320U927-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P332405-927

CATALOG NUMBER: S123RDIW-S340D1320U927-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	101	101	101	101	89	89	89	89	68	68	68	48	48	48	31	31	31	22
1	92	88	84	81	81	78	75	72	59	58	56	43	41	40	27	27	26	19
2	84	77	71	66	74	68	63	59	52	49	46	38	36	34	24	23	22	16
3	76	67	60	55	67	60	54	50	46	42	39	33	31	29	21	20	19	14
4	70	60	52	46	62	53	47	42	41	37	33	30	27	25	19	18	16	12
5	64	53	45	40	56	47	41	36	37	32	29	27	24	21	17	16	14	10
6	59	47	40	34	52	42	36	31	33	28	25	24	21	19	16	14	13	9
7	54	43	35	30	48	38	32	27	30	25	22	22	19	16	14	13	11	8
8	50	38	31	26	44	35	28	24	27	22	19	20	17	15	13	11	10	7
9	47	35	28	23	41	31	25	21	25	20	17	18	15	13	12	10	9	7
10	43	32	25	21	38	29	23	19	23	18	15	17	14	12	11	9	8	6

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	4899	4899	4899
5°	4917	4850	4878
10°	4889	4790	4773
15°	4837	4677	4628
20°	4765	4537	4431
25°	4691	4380	4240
30°	4593	4197	3967
35°	4491	4016	3720
40°	4398	3801	3413
45°	4276	3589	3136
50°	4141	3349	2825
55°	4003	3076	2535
60°	3877	2781	2217
65°	3713	2463	1897
70°	3509	2068	1533
75°	3211	1626	1443
80°	2858	1444	1327
85°	2421	1272	1186



TEST NUMBER: P332405-927

CATALOG NUMBER: S123RDIW-S340D1320U927-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	42.7	0.9
10°-20°	118.9	2.6
20°-30°	171.2	3.7
30°-40°	192.9	4.1
40°-50°	184.5	4.0
50°-60°	151.1	3.2
60°-70°	101.9	2.2
70°-80°	51.3	1.1
80°-90°	17.4	0.4
90°-100°	85.2	1.8
100°-110°	255.0	5.5
110°-120°	433.8	9.3
120°-130°	570.5	12.3
130°-140°	641.3	13.8
140°-150°	630.4	13.5
150°-160°	530.7	11.4
160°-170°	353.3	7.6
170°-180°	123.7	2.7
0°-30°	332.9	7.1
0°-40°	525.7	11.3
0°-60°	861.4	18.5
0°-90°	1032.0	22.2
90°-120°	774.0	16.6
90°-150°	2616.2	56.2
90°-180°	3624.0	77.8
0°-180°	4655.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	455	455	455	455	455	
5°	455	453	449	452	452	43
15°	434	430	420	418	415	122
25°	395	385	369	361	357	182
35°	342	328	306	290	283	214
45°	281	264	236	215	206	217
55°	213	195	164	143	135	191
65°	146	125	97	79	74	144
75°	77	59	39	36	35	82
85°	20	12	10	10	10	22
90°	1	11	25	29	31	5
95°	61	68	76	80	80	68
105°	231	234	242	243	244	248
115°	437	439	438	439	438	432
125°	639	642	640	636	632	570
135°	829	835	834	830	828	639
145°	1006	1008	1011	1010	1006	628
155°	1152	1152	1153	1156	1150	530
165°	1254	1252	1251	1257	1250	354
175°	1305	1301	1301	1306	1300	124
180°	1308	1308	1308	1308	1308	



TEST NUMBER: P332405-927

CATALOG NUMBER: S123RDIW-S340D1320U927-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	455.1	455.1	455.1	455.1	455.1	455.1	455.1	455.1	455.1	455.1	455.1
2.5°	456.6	456.3	456.1	455.8	455.6	455.0	454.2	453.4	452.7	451.9	452.6
5°	455.1	454.7	454.3	453.9	453.4	452.8	451.8	450.8	449.8	448.9	449.6
7.5°	450.9	450.4	450.0	449.6	449.2	448.3	447.0	445.8	444.4	443.1	443.5
10°	447.3	446.8	446.2	445.7	445.0	444.0	442.6	441.1	439.6	438.2	438.2
12.5°	442.4	441.7	441.1	440.5	439.8	438.6	436.7	435.0	433.2	431.3	431.3
15°	434.1	433.2	432.3	431.3	430.5	428.9	426.6	424.3	422.0	419.7	419.3
17.5°	423.7	422.6	421.6	420.5	419.5	417.5	414.5	411.6	408.8	405.8	405.0
20°	416.0	414.7	413.4	412.1	410.7	408.5	405.4	402.3	399.2	396.1	395.0
22.5°	407.4	405.9	404.4	402.9	401.4	399.0	395.7	392.4	389.0	385.7	384.4
25°	395.0	392.9	390.9	388.8	386.7	383.8	380.1	376.3	372.5	368.8	367.0
27.5°	379.9	377.6	375.3	373.0	370.7	367.6	363.4	359.1	354.9	350.7	348.3
30°	369.5	367.0	364.6	362.1	359.7	356.1	351.5	346.9	342.3	337.7	334.9
32.5°	359.2	356.3	353.6	350.8	348.0	344.2	339.3	334.5	329.6	324.7	321.7
35°	341.8	338.8	335.9	333.0	330.0	326.0	320.9	315.8	310.7	305.6	302.1
37.5°	324.2	320.9	317.7	314.4	311.1	306.7	301.3	295.9	290.5	285.0	281.1
40°	313.0	309.4	305.8	302.2	298.6	293.8	288.0	282.2	276.4	270.5	266.3
42.5°	300.3	296.7	293.1	289.5	285.9	281.1	275.0	269.0	263.0	257.0	252.3
45°	280.9	277.2	273.5	269.8	266.1	261.1	254.8	248.5	242.2	235.8	231.2
47.5°	261.5	257.5	253.3	249.3	245.3	240.1	233.8	227.4	221.2	214.8	209.8
50°	247.3	243.4	239.6	235.8	231.9	226.6	220.0	213.3	206.7	200.0	195.0
52.5°	234.6	230.4	226.2	222.0	217.9	212.5	205.9	199.3	192.7	186.2	180.9
55°	213.3	209.3	205.3	201.3	197.3	191.8	184.8	177.8	170.9	163.9	159.1
57.5°	193.7	189.3	185.0	180.5	176.2	170.5	163.5	156.5	149.5	142.5	138.0
60°	180.1	175.6	171.1	166.6	162.1	156.5	149.6	142.8	136.0	129.2	124.8
62.5°	166.5	162.0	157.5	153.0	148.5	142.8	136.0	129.2	122.4	115.6	111.5
65°	145.8	141.3	136.8	132.3	127.8	122.3	115.9	109.5	103.1	96.7	92.7
67.5°	125.1	120.5	115.9	111.4	106.8	101.5	95.3	89.2	83.0	76.9	73.9
70°	111.5	107.0	102.6	98.2	93.8	88.6	82.9	77.2	71.5	65.7	62.8
72.5°	97.9	93.6	89.2	84.8	80.4	75.7	70.4	65.2	60.0	54.7	52.4
75°	77.2	73.2	69.2	65.4	61.4	57.2	52.7	48.2	43.6	39.1	38.3
77.5°	58.2	54.7	51.1	47.5	44.0	40.8	37.9	34.9	32.1	29.2	28.8
80°	46.1	42.8	39.5	36.0	32.7	30.2	28.4	26.7	25.0	23.3	23.0
82.5°	34.6	31.7	28.8	25.9	23.0	21.2	20.4	19.6	18.8	17.9	17.7
85°	19.6	17.7	15.9	14.2	12.4	11.3	11.1	10.9	10.6	10.3	10.1
87.5°	7.3	7.1	6.7	6.5	6.3	6.4	7.0	7.6	8.2	8.8	8.9
90°	1.0	3.3	5.6	7.8	10.1	12.8	15.8	18.7	21.7	24.6	25.6
92.5°	24.9	26.4	28.0	29.5	31.1	32.7	34.4	36.0	37.8	39.5	40.2
95°	60.6	62.2	63.8	65.4	67.0	68.8	70.6	72.4	74.2	76.0	76.9
97.5°	107.7	108.8	110.0	111.2	112.4	113.7	115.0	116.3	117.6	119.0	120.0
100°	139.7	141.1	142.4	143.9	145.2	146.5	147.6	148.8	149.9	151.1	151.7
102.5°	176.7	177.5	178.4	179.2	180.0	181.2	182.7	184.2	185.7	187.2	187.9
105°	231.2	231.6	232.1	232.5	233.0	234.2	236.3	238.4	240.4	242.5	242.5
107.5°	294.5	294.8	295.0	295.3	295.6	296.1	296.9	297.8	298.6	299.4	300.2
110°	333.9	334.4	334.9	335.3	335.7	336.2	336.7	337.2	337.5	338.0	339.0



TEST NUMBER: P332405-927

CATALOG NUMBER: S123RDIW-S340D1320U927-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	375.0	375.3	375.6	375.8	376.1	376.3	376.4	376.4	376.6	376.7	377.8
115°	436.7	437.4	438.0	438.7	439.4	439.5	439.0	438.6	438.2	437.7	437.9
117.5°	498.8	499.2	499.6	500.1	500.6	500.5	499.9	499.3	498.7	498.1	498.0
120°	537.3	538.7	540.1	541.5	542.8	543.0	541.8	540.7	539.6	538.4	538.1
122.5°	577.7	578.6	579.6	580.7	581.6	581.9	581.2	580.7	580.0	579.5	578.8
125°	639.1	639.8	640.4	641.1	641.8	641.9	641.4	641.0	640.6	640.1	639.2
127.5°	695.8	697.3	698.7	700.1	701.6	702.1	701.6	701.1	700.6	700.1	698.8
130°	733.6	735.4	737.3	739.1	740.9	741.5	740.8	740.1	739.4	738.7	737.8
132.5°	771.4	773.2	775.1	776.9	778.7	779.3	778.9	778.4	777.8	777.4	776.3
135°	829.2	830.5	831.9	833.2	834.6	835.2	835.0	834.7	834.5	834.2	833.4
137.5°	882.6	883.7	884.9	886.0	887.2	888.0	888.6	889.2	889.8	890.4	889.4
140°	919.6	920.7	921.9	923.0	924.2	924.8	925.0	925.3	925.5	925.7	925.5
142.5°	953.2	954.4	955.5	956.7	957.8	958.6	959.0	959.4	959.8	960.3	960.0
145°	1005.8	1006.3	1006.8	1007.3	1007.7	1008.3	1008.9	1009.6	1010.3	1011.0	1010.7
147.5°	1051.9	1052.7	1053.5	1054.4	1055.2	1055.9	1056.5	1057.2	1057.8	1058.4	1058.4
150°	1083.9	1084.4	1084.9	1085.3	1085.8	1086.2	1086.7	1087.1	1087.6	1088.1	1088.1
152.5°	1110.2	1110.9	1111.5	1112.1	1112.8	1113.3	1113.6	1113.8	1114.1	1114.4	1114.8
155°	1151.8	1151.8	1151.8	1151.8	1151.8	1151.9	1152.1	1152.3	1152.5	1152.8	1153.7
157.5°	1187.1	1186.8	1186.5	1186.3	1186.0	1186.0	1186.1	1186.3	1186.5	1186.7	1187.6
160°	1209.3	1208.9	1208.4	1207.9	1207.4	1207.2	1207.2	1207.2	1207.2	1207.2	1208.4
162.5°	1229.0	1228.4	1227.7	1227.1	1226.5	1226.2	1226.5	1226.6	1226.8	1226.9	1228.1
165°	1254.5	1253.8	1253.2	1252.4	1251.8	1251.4	1251.4	1251.4	1251.4	1251.4	1252.8
167.5°	1274.9	1273.9	1273.0	1272.1	1271.2	1270.8	1271.0	1271.2	1271.4	1271.5	1273.0
170°	1286.3	1285.5	1284.5	1283.7	1282.7	1282.2	1282.2	1282.2	1282.2	1282.2	1283.8
172.5°	1295.4	1294.5	1293.6	1292.7	1291.7	1291.3	1291.3	1291.3	1291.3	1291.3	1292.7
175°	1304.9	1303.9	1303.1	1302.1	1301.2	1300.8	1300.8	1300.8	1300.8	1300.8	1302.1
177.5°	1308.8	1308.1	1307.3	1306.5	1305.8	1305.4	1305.4	1305.4	1305.4	1305.4	1306.5
180°	1308.0	1308.0	1308.0	1308.0	1308.0	1308.0	1308.0	1308.0	1308.0	1308.0	1308.0



TEST NUMBER: P332405-927

CATALOG NUMBER: S123RDIW-S340D1320U927-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	455.1	455.1	455.1	455.1	455.1	455.1	455.1	455.1
2.5°	453.3	454.0	454.8	455.0	455.0	454.8	454.6	454.6
5°	450.4	451.1	451.8	452.1	451.9	451.8	451.6	451.5
7.5°	444.0	444.4	444.8	444.9	444.6	444.3	444.0	443.8
10°	438.3	438.4	438.5	438.3	437.9	437.5	437.0	436.7
12.5°	431.3	431.2	431.2	430.9	430.4	429.9	429.4	429.0
15°	418.8	418.4	418.0	417.6	417.0	416.4	415.8	415.3
17.5°	404.1	403.2	402.3	401.5	400.6	399.7	398.9	398.1
20°	394.0	392.8	391.8	390.8	389.8	388.8	387.9	386.8
22.5°	383.1	381.8	380.4	379.3	378.3	377.5	376.5	375.7
25°	365.3	363.6	361.9	360.5	359.7	358.8	357.8	357.0
27.5°	345.9	343.6	341.2	339.3	337.9	336.5	335.2	333.7
30°	332.2	329.4	326.6	324.6	323.2	321.9	320.6	319.2
32.5°	318.6	315.6	312.5	310.3	309.0	307.6	306.2	304.8
35°	298.6	295.0	291.5	289.0	287.6	286.1	284.6	283.1
37.5°	277.0	273.0	269.0	266.1	264.3	262.4	260.6	258.8
40°	262.1	257.8	253.5	250.4	248.5	246.7	244.8	242.9
42.5°	247.6	243.0	238.4	235.2	233.5	231.8	230.1	228.4
45°	226.5	221.8	217.1	213.8	211.9	209.9	207.9	206.0
47.5°	204.6	199.6	194.5	191.1	189.3	187.6	185.8	184.0
50°	189.9	184.8	179.7	176.3	174.4	172.5	170.6	168.7
52.5°	175.6	170.3	165.1	161.6	159.9	158.2	156.5	154.8
55°	154.4	149.6	144.9	141.6	140.1	138.4	136.7	135.1
57.5°	133.5	129.0	124.5	121.5	120.2	118.7	117.4	116.0
60°	120.3	115.9	111.5	108.5	107.2	105.8	104.4	103.0
62.5°	107.3	103.1	98.9	96.1	94.7	93.2	91.7	90.3
65°	88.6	84.7	80.6	78.2	77.2	76.4	75.5	74.5
67.5°	70.9	67.9	64.9	62.9	61.9	61.0	60.0	59.1
70°	60.0	57.1	54.2	52.4	51.4	50.5	49.6	48.7
72.5°	50.1	47.8	45.4	44.0	43.6	43.3	42.9	42.5
75°	37.5	36.7	35.8	35.3	35.2	35.0	34.9	34.7
77.5°	28.3	27.8	27.4	27.1	26.9	26.8	26.6	26.5
80°	22.7	22.5	22.3	22.1	21.9	21.7	21.5	21.4
82.5°	17.4	17.2	17.0	16.8	16.8	16.7	16.7	16.7
85°	10.0	9.8	9.7	9.6	9.6	9.6	9.6	9.6
87.5°	9.0	9.1	9.3	9.3	9.3	9.3	9.3	9.4
90°	26.5	27.4	28.3	29.0	29.5	29.9	30.3	30.8
92.5°	40.9	41.7	42.4	42.6	42.3	42.1	41.7	41.5
95°	77.9	78.7	79.7	80.2	80.2	80.2	80.2	80.2
97.5°	121.0	122.2	123.2	123.7	123.6	123.5	123.4	123.3
100°	152.4	153.0	153.8	154.3	154.8	155.3	155.7	156.1
102.5°	188.5	189.3	190.0	190.2	190.1	190.0	190.0	189.9
105°	242.5	242.5	242.5	242.7	243.2	243.6	244.1	244.5
107.5°	300.9	301.6	302.3	302.5	302.3	302.0	301.7	301.4
110°	339.8	340.8	341.7	341.9	341.4	341.0	340.6	340.1



TEST NUMBER: P332405-927

CATALOG NUMBER: S123RDIW-S340D1320U927-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	378.8	379.9	381.0	381.5	381.4	381.4	381.3	381.2
115°	438.2	438.4	438.6	438.6	438.4	438.2	437.9	437.7
117.5°	498.0	498.0	497.9	497.6	496.9	496.3	495.7	495.0
120°	537.9	537.7	537.5	537.1	536.7	536.2	535.8	535.3
122.5°	578.3	577.7	577.1	576.5	575.8	575.2	574.6	573.9
125°	638.3	637.4	636.4	635.6	634.6	633.7	632.8	631.8
127.5°	697.5	696.2	695.0	693.8	692.8	691.7	690.7	689.6
130°	736.9	736.0	735.1	733.8	732.2	730.6	729.0	727.5
132.5°	775.2	774.0	773.0	771.8	770.6	769.4	768.1	766.9
135°	832.4	831.6	830.6	830.0	829.5	829.0	828.5	828.1
137.5°	888.4	887.5	886.5	885.7	884.8	883.9	883.0	882.2
140°	925.3	925.0	924.8	923.9	922.3	920.7	919.1	917.5
142.5°	959.8	959.6	959.3	958.6	957.4	956.2	954.9	953.7
145°	1010.5	1010.3	1010.1	1009.6	1008.6	1007.7	1006.8	1005.8
147.5°	1058.4	1058.4	1058.4	1057.8	1056.5	1055.0	1053.7	1052.3
150°	1088.1	1088.1	1088.1	1087.3	1086.0	1084.7	1083.2	1081.9
152.5°	1115.1	1115.5	1115.8	1115.4	1114.2	1113.0	1111.8	1110.6
155°	1154.6	1155.6	1156.4	1156.1	1154.5	1152.9	1151.3	1149.7
157.5°	1188.6	1189.5	1190.6	1190.3	1189.1	1187.8	1186.5	1185.3
160°	1209.5	1210.7	1211.8	1212.0	1211.0	1210.1	1209.2	1208.2
162.5°	1229.2	1230.4	1231.5	1231.4	1229.9	1228.4	1227.0	1225.5
165°	1254.2	1255.5	1256.9	1256.8	1255.2	1253.6	1252.0	1250.4
167.5°	1274.4	1275.8	1277.2	1277.2	1275.8	1274.4	1273.0	1271.5
170°	1285.5	1287.1	1288.6	1288.6	1287.1	1285.5	1283.8	1282.2
172.5°	1294.1	1295.5	1297.0	1296.9	1295.3	1293.6	1292.0	1290.5
175°	1303.5	1304.9	1306.2	1306.1	1304.5	1302.9	1301.3	1299.7
177.5°	1307.7	1308.8	1309.9	1309.8	1308.4	1307.2	1305.9	1304.6
180°	1308.0	1308.0	1308.0	1308.0	1308.0	1308.0	1308.0	1308.0

(END OF REPORT)