

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331847-840

Luminaire Tested: **S122RDIW-S1005D435U840-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331847-840
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122RDIW-S1005D435U840-4F0-1E-UDD-F
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 1005 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 435 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5266.9 lumens
Efficiency: N/A
Efficacy: 100.5 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 52.4
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331847-840

CATALOG NUMBER: S122RDIW-S1005D435U840-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P331847-840

CATALOG NUMBER: S122RDIW-S1005D435U840-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	111	111	111	111	105	105	105	105	93	93	93	82	82	82	72	72	72	67
1	102	98	94	91	96	93	89	86	82	80	78	73	71	69	64	63	62	58
2	94	86	80	75	88	82	76	72	73	69	65	65	62	59	57	55	53	49
3	86	77	69	64	81	72	66	61	65	60	56	58	54	51	51	48	46	42
4	79	68	60	54	74	65	58	52	58	53	48	52	48	44	46	43	40	37
5	73	61	53	47	68	58	51	45	52	47	42	47	42	39	42	38	35	33
6	67	55	47	41	63	53	45	40	48	42	37	43	38	34	38	35	31	29
7	62	50	42	37	59	48	41	36	43	37	33	39	34	31	35	31	28	26
8	58	46	38	33	55	44	37	32	40	34	30	36	31	28	33	29	26	23
9	54	42	35	30	51	40	33	29	37	31	27	33	29	25	30	26	23	21
10	51	39	32	27	48	37	31	26	34	28	24	31	26	23	28	24	21	19

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	27611	27611	27611
5°	27716	27266	27417
10°	27506	26820	26591
15°	27189	26024	25275
20°	26751	24890	23639
25°	26302	23599	22057
30°	25682	22275	20025
35°	25074	20834	18242
40°	24464	19344	16179
45°	23749	17671	14312
50°	23016	15978	12479
55°	22261	14159	10716
60°	21390	12245	8896
65°	20397	10288	8103
70°	19218	8478	7449
75°	17767	7723	6949
80°	15676	6908	6332
85°	12338	5446	5446



TEST NUMBER: P331847-840

CATALOG NUMBER: S122RDIW-S1005D435U840-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	160.1	3.0
10°-20°	439.5	8.3
20°-30°	617.2	11.7
30°-40°	673.0	12.8
40°-50°	618.8	11.7
50°-60°	486.0	9.2
60°-70°	316.9	6.0
70°-80°	163.4	3.1
80°-90°	43.9	0.8
90°-100°	19.9	0.4
100°-110°	73.0	1.4
110°-120°	195.0	3.7
120°-130°	322.0	6.1
130°-140°	342.4	6.5
140°-150°	318.3	6.0
150°-160°	255.9	4.9
160°-170°	164.9	3.1
170°-180°	56.8	1.1
0°-30°	1216.8	23.1
0°-40°	1889.8	35.9
0°-60°	2994.7	56.9
0°-90°	3518.8	66.8
90°-120°	287.9	5.5
90°-150°	1270.6	24.1
90°-180°	1748.0	33.2
0°-180°	5266.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1710	1710	1710	1710	1710	
5°	1710	1702	1682	1695	1692	162
15°	1627	1608	1557	1528	1512	458
25°	1476	1424	1325	1264	1238	679
35°	1272	1190	1057	963	926	796
45°	1040	933	774	668	627	803
55°	791	668	503	414	381	706
65°	534	408	269	219	212	529
75°	285	180	124	114	111	301
85°	67	36	29	29	29	78
90°	0	5	9	11	12	4
95°	28	15	17	19	19	34
105°	131	137	26	31	33	140
115°	248	256	266	76	35	244
125°	351	357	365	368	369	313
135°	434	441	445	449	448	335
145°	504	504	511	513	512	315
155°	555	551	556	558	555	255
165°	584	582	583	586	583	165
175°	598	595	596	598	594	57
180°	596	596	596	596	596	



TEST NUMBER: P331847-840

CATALOG NUMBER: S122RDIW-S1005D435U840-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1710.1	1710.1	1710.1	1710.1	1710.1	1710.1	1710.1	1710.1	1710.1	1710.1	1710.1
2.5°	1716.4	1715.0	1713.5	1712.2	1710.8	1708.6	1705.6	1702.6	1699.6	1696.6	1699.3
5°	1710.1	1708.4	1706.7	1705.0	1703.2	1700.2	1695.7	1691.2	1686.8	1682.3	1685.4
7.5°	1692.5	1690.4	1688.3	1686.1	1683.9	1680.3	1675.1	1669.8	1664.7	1659.4	1660.3
10°	1677.7	1675.3	1672.8	1670.4	1668.0	1663.3	1656.5	1649.6	1642.7	1635.9	1634.9
12.5°	1659.1	1656.1	1653.1	1650.2	1647.3	1641.3	1632.5	1623.8	1615.0	1606.2	1604.3
15°	1626.6	1622.8	1619.0	1615.2	1611.4	1603.7	1592.1	1580.3	1568.6	1556.9	1550.4
17.5°	1586.6	1580.8	1575.1	1569.3	1563.6	1553.2	1538.1	1523.2	1508.1	1493.2	1485.4
20°	1556.9	1550.0	1543.2	1536.3	1529.4	1517.4	1500.2	1483.0	1465.8	1448.6	1440.0
22.5°	1524.7	1517.0	1509.3	1501.7	1493.9	1480.4	1461.0	1441.6	1422.2	1402.8	1391.7
25°	1476.4	1465.4	1454.4	1443.4	1432.4	1415.6	1392.9	1370.2	1347.5	1324.7	1310.7
27.5°	1418.3	1406.3	1394.3	1382.4	1370.4	1351.6	1326.1	1300.4	1274.9	1249.3	1232.8
30°	1377.5	1364.3	1351.3	1338.2	1325.1	1304.8	1277.3	1249.8	1222.3	1194.8	1177.2
32.5°	1337.8	1322.5	1307.3	1292.0	1276.7	1255.1	1227.0	1198.9	1170.8	1142.8	1122.8
35°	1272.1	1254.7	1237.1	1219.5	1202.0	1178.1	1147.8	1117.6	1087.3	1057.0	1035.4
37.5°	1206.6	1187.3	1168.0	1148.7	1129.5	1103.8	1071.5	1039.3	1006.9	974.7	950.9
40°	1160.7	1140.1	1119.4	1098.8	1078.2	1051.2	1017.8	984.5	951.1	917.8	893.3
42.5°	1113.7	1092.0	1070.3	1048.4	1026.7	998.7	964.2	929.7	895.2	860.8	835.6
45°	1040.1	1016.9	993.9	970.9	947.9	918.3	882.1	846.1	809.9	773.9	749.4
47.5°	968.2	943.8	919.4	894.9	870.5	839.7	802.4	765.1	727.8	690.5	666.3
50°	916.3	891.8	867.4	842.9	818.5	787.4	749.6	711.8	673.9	636.1	612.4
52.5°	865.5	839.9	814.5	788.9	763.4	732.2	695.1	658.1	621.1	584.1	561.2
55°	790.8	764.1	737.2	710.3	683.6	651.6	614.4	577.2	540.2	503.0	482.3
57.5°	714.4	686.9	659.3	631.9	604.3	572.7	537.0	501.3	465.6	429.9	411.0
60°	662.4	634.9	607.3	579.9	552.3	520.9	485.4	450.0	414.5	379.2	361.6
62.5°	611.7	584.1	556.6	529.1	501.6	470.9	437.2	403.3	369.6	335.9	319.1
65°	533.9	506.0	478.3	450.4	422.5	393.1	362.1	331.2	300.2	269.3	257.6
67.5°	459.0	431.4	403.7	376.1	348.4	320.6	292.9	265.0	237.1	209.2	203.9
70°	407.1	380.2	353.4	326.6	299.7	274.5	250.7	227.0	203.3	179.6	176.1
72.5°	357.5	331.7	306.1	280.3	254.6	232.2	213.2	194.1	175.0	156.0	153.1
75°	284.8	260.6	236.6	212.6	188.4	170.6	158.9	147.2	135.5	123.8	121.4
77.5°	213.3	192.2	171.1	150.0	128.8	115.4	109.8	104.1	98.5	92.9	91.5
80°	168.6	151.2	133.6	116.0	98.6	88.1	84.6	81.2	77.8	74.3	72.9
82.5°	127.8	114.1	100.5	86.7	73.1	65.0	62.7	60.4	58.1	55.7	54.9
85°	66.6	59.3	52.1	44.8	37.7	33.5	32.5	31.5	30.4	29.4	29.4
87.5°	19.9	17.9	16.0	13.9	11.9	11.0	11.2	11.3	11.5	11.6	11.4
90°	0.4	1.5	2.5	3.6	4.6	5.6	6.4	7.1	7.9	8.6	9.1
92.5°	8.7	8.6	8.5	8.4	8.4	8.5	8.9	9.3	9.6	10.0	10.3
95°	28.1	24.8	21.7	18.6	15.3	14.1	14.8	15.5	16.2	16.9	17.3
97.5°	55.6	46.8	37.9	28.9	20.0	16.4	17.9	19.4	21.0	22.5	22.9
100°	76.4	63.2	50.1	37.0	23.8	18.1	19.7	21.3	22.9	24.6	25.3
102.5°	99.2	96.4	93.6	90.9	88.1	79.9	66.2	52.6	39.0	25.2	26.3
105°	131.2	134.1	136.9	139.9	142.7	131.1	104.9	78.7	52.5	26.4	27.4
107.5°	167.7	170.1	172.4	174.7	177.0	162.5	131.1	99.7	68.3	36.9	35.7
110°	191.2	193.2	195.2	197.2	199.2	186.4	158.6	131.0	103.2	75.5	65.9



TEST NUMBER: P331847-840

CATALOG NUMBER: S122RDIW-S1005D435U840-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	213.3	215.1	216.9	218.6	220.5	217.9	211.1	204.2	197.3	190.6	155.5
115°	248.2	249.8	251.5	253.1	254.7	256.7	259.1	261.6	263.9	266.3	221.9
117.5°	279.3	281.1	283.0	284.8	286.6	288.4	290.0	291.6	293.4	295.0	284.3
120°	302.2	303.6	305.0	306.5	307.9	309.5	311.2	313.0	314.7	316.4	317.5
122.5°	321.4	323.0	324.5	326.0	327.5	329.2	331.1	333.0	334.9	336.8	337.5
125°	350.9	352.1	353.5	354.7	355.9	357.4	359.3	361.1	362.9	364.8	365.4
127.5°	377.6	379.0	380.3	381.7	383.1	384.5	385.9	387.2	388.6	389.9	390.9
130°	394.6	396.1	397.6	399.1	400.6	401.9	403.0	404.0	405.2	406.2	407.2
132.5°	411.8	413.0	414.3	415.7	417.0	418.2	419.2	420.3	421.3	422.4	423.3
135°	434.2	435.8	437.3	438.8	440.4	441.5	442.4	443.3	444.1	445.0	446.0
137.5°	457.0	458.0	459.1	460.2	461.2	462.2	463.2	464.2	465.1	466.2	467.1
140°	471.8	472.5	473.3	474.0	474.8	475.7	476.9	477.9	478.9	480.0	480.8
142.5°	484.2	484.9	485.5	486.3	487.0	488.0	489.1	490.3	491.5	492.7	493.5
145°	503.7	503.6	503.5	503.4	503.3	504.1	505.7	507.4	509.0	510.6	511.3
147.5°	520.7	520.4	520.0	519.7	519.3	519.9	521.5	523.1	524.7	526.3	526.8
150°	531.8	531.1	530.4	529.8	529.1	529.5	531.1	532.6	534.1	535.6	536.2
152.5°	541.1	540.4	539.6	538.9	538.1	538.5	539.9	541.4	542.8	544.3	544.8
155°	554.6	553.8	552.9	552.1	551.2	551.4	552.5	553.6	554.8	555.9	556.5
157.5°	565.2	564.5	563.8	563.1	562.4	562.4	563.2	564.0	564.8	565.6	566.2
160°	571.5	570.9	570.4	569.8	569.2	569.2	569.8	570.4	570.9	571.5	572.1
162.5°	577.0	576.4	575.8	575.3	574.7	574.7	575.1	575.6	576.1	576.6	577.3
165°	584.4	583.9	583.3	582.7	582.1	582.0	582.3	582.6	582.9	583.1	583.8
167.5°	590.0	589.4	588.9	588.2	587.6	587.5	587.7	588.0	588.3	588.5	589.3
170°	593.1	592.5	591.9	591.4	590.8	590.6	590.8	591.0	591.2	591.4	592.0
172.5°	595.1	594.6	594.0	593.4	592.8	592.7	592.8	593.0	593.2	593.4	594.1
175°	597.8	597.1	596.4	595.8	595.1	594.9	595.1	595.3	595.4	595.6	596.3
177.5°	598.2	597.7	597.1	596.6	596.1	595.8	595.9	596.0	596.1	596.1	596.7
180°	596.5	596.5	596.5	596.5	596.5	596.5	596.5	596.5	596.5	596.5	596.5



TEST NUMBER: P331847-840

CATALOG NUMBER: S122RDIW-S1005D435U840-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1710.1	1710.1	1710.1	1710.1	1710.1	1710.1	1710.1	1710.1
2.5°	1702.0	1704.8	1707.6	1708.6	1708.1	1707.6	1707.0	1706.5
5°	1688.5	1691.6	1694.7	1695.7	1694.7	1693.6	1692.6	1691.6
7.5°	1661.1	1662.0	1662.9	1662.5	1660.7	1658.9	1657.2	1655.4
10°	1633.8	1632.7	1631.7	1630.2	1628.1	1626.1	1624.0	1621.9
12.5°	1602.5	1600.5	1598.7	1596.1	1592.7	1589.2	1585.8	1582.4
15°	1543.9	1537.3	1530.8	1525.8	1522.4	1518.9	1515.5	1512.1
17.5°	1477.6	1469.9	1462.1	1455.2	1449.4	1443.4	1437.4	1431.6
20°	1431.4	1422.8	1414.2	1406.1	1398.6	1391.0	1383.4	1375.8
22.5°	1380.7	1369.6	1358.5	1350.1	1344.5	1338.9	1333.2	1327.6
25°	1296.6	1282.5	1268.4	1258.8	1253.5	1248.4	1243.2	1238.1
27.5°	1216.4	1199.9	1183.5	1171.1	1163.0	1154.8	1146.6	1138.4
30°	1159.7	1142.2	1124.6	1111.3	1102.0	1092.7	1083.4	1074.1
32.5°	1102.8	1082.8	1062.7	1048.3	1039.7	1030.9	1022.1	1013.4
35°	1013.7	992.1	970.4	955.7	948.2	940.6	933.0	925.5
37.5°	927.0	903.1	879.2	862.9	854.3	845.7	837.0	828.3
40°	868.9	844.4	820.1	803.4	794.5	785.5	776.6	767.6
42.5°	810.3	785.1	759.8	742.9	734.2	725.5	716.9	708.2
45°	725.0	700.5	676.1	659.8	651.6	643.3	635.0	626.8
47.5°	642.0	617.7	593.4	577.5	570.1	562.6	555.0	547.5
50°	588.7	564.9	541.2	525.6	518.5	511.2	504.0	496.8
52.5°	538.3	515.3	492.5	477.7	471.0	464.3	457.7	451.0
55°	461.7	441.1	420.4	406.9	400.3	393.7	387.3	380.7
57.5°	392.1	373.1	354.3	342.0	336.6	331.0	325.6	320.0
60°	344.1	326.6	309.0	297.5	292.0	286.5	280.9	275.5
62.5°	302.5	285.7	269.0	258.9	255.7	252.4	249.0	245.8
65°	245.9	234.2	222.5	216.1	215.1	214.1	213.1	212.1
67.5°	198.5	193.2	187.7	184.5	183.5	182.4	181.3	180.2
70°	172.7	169.3	165.8	163.4	162.0	160.6	159.3	157.8
72.5°	150.3	147.3	144.4	142.6	141.8	141.0	140.1	139.3
75°	119.0	116.6	114.2	112.8	112.5	112.1	111.8	111.4
77.5°	90.1	88.8	87.4	86.3	85.8	85.3	84.7	84.2
80°	71.5	70.2	68.8	68.1	68.1	68.1	68.1	68.1
82.5°	54.0	53.2	52.4	52.0	52.0	52.0	52.0	52.0
85°	29.4	29.4	29.4	29.4	29.4	29.4	29.4	29.4
87.5°	11.3	11.1	10.9	10.8	10.9	10.9	11.0	11.0
90°	9.6	10.1	10.5	10.9	11.1	11.3	11.5	11.6
92.5°	10.5	10.8	11.0	11.2	11.3	11.4	11.5	11.6
95°	17.8	18.3	18.8	19.0	18.9	18.8	18.7	18.6
97.5°	23.3	23.7	24.0	24.3	24.4	24.5	24.6	24.7
100°	26.2	26.9	27.7	28.2	28.4	28.6	28.7	28.9
102.5°	27.3	28.3	29.3	29.9	30.2	30.5	30.7	31.0
105°	28.5	29.5	30.6	31.3	31.6	32.0	32.4	32.8
107.5°	34.7	33.6	32.5	32.2	32.6	33.0	33.3	33.7
110°	56.4	46.8	37.2	32.5	32.9	33.3	33.7	34.1



TEST NUMBER: P331847-840

CATALOG NUMBER: S122RDIW-S1005D435U840-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	120.6	85.5	50.6	33.2	33.5	33.8	34.1	34.4
115°	177.5	133.1	88.7	63.0	56.1	49.2	42.3	35.3
117.5°	273.5	262.8	252.0	235.3	212.6	189.9	167.2	144.5
120°	318.7	319.8	321.0	315.1	302.2	289.2	276.2	263.3
122.5°	338.1	338.8	339.5	338.6	336.1	333.6	331.0	328.5
125°	366.1	366.8	367.4	367.9	368.2	368.5	368.8	369.0
127.5°	391.9	392.8	393.8	394.4	394.5	394.5	394.6	394.6
130°	408.3	409.3	410.4	410.9	410.8	410.7	410.6	410.5
132.5°	424.2	425.1	426.0	426.4	426.3	426.2	426.2	426.1
135°	447.0	447.9	448.9	449.2	449.1	448.9	448.7	448.5
137.5°	468.1	469.0	469.9	470.2	469.9	469.6	469.3	468.9
140°	481.7	482.6	483.4	483.6	483.1	482.6	482.2	481.7
142.5°	494.3	495.1	495.9	496.0	495.5	495.1	494.6	494.1
145°	512.0	512.6	513.3	513.4	512.9	512.4	512.0	511.5
147.5°	527.4	527.9	528.4	528.4	528.0	527.6	527.1	526.7
150°	536.8	537.3	538.0	538.1	537.6	537.0	536.5	536.1
152.5°	545.4	546.0	546.6	546.5	545.9	545.3	544.6	544.0
155°	557.1	557.6	558.3	558.2	557.3	556.6	555.8	555.1
157.5°	566.9	567.5	568.3	568.2	567.4	566.6	565.9	565.2
160°	572.6	573.2	573.8	573.7	573.1	572.4	571.7	571.1
162.5°	577.9	578.7	579.3	579.2	578.3	577.5	576.7	575.9
165°	584.5	585.1	585.8	585.8	585.1	584.5	583.8	583.1
167.5°	590.0	590.6	591.3	591.2	590.3	589.5	588.5	587.7
170°	592.7	593.4	594.0	593.9	593.1	592.2	591.4	590.5
172.5°	594.7	595.4	596.1	596.0	595.1	594.3	593.4	592.6
175°	597.0	597.6	598.3	598.2	597.2	596.3	595.3	594.4
177.5°	597.2	597.7	598.3	598.2	597.5	596.8	596.1	595.5
180°	596.5	596.5	596.5	596.5	596.5	596.5	596.5	596.5

(END OF REPORT)