

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331856-840

Luminaire Tested: **S122RDIW-S1005D970U840-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P331856-840  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-8,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S122RDIW-S1005D970U840-4F0-1E-UDD-F1  
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 1005 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED  
HOUSING  
UPLIGHT 970 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 6911.3 lumens  
Efficiency: N/A  
Efficacy: 102.5 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16  
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')  
CIE Type: General Diffuse


Input Watts (W): 67.4  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P331856-840

CATALOG NUMBER: S122RDIW-S1005D970U840-4F0-1E-UDD-F1

### Luminous Intensity Polar Plot





TEST NUMBER: P331856-840

CATALOG NUMBER: S122RDIW-S1005D970U840-4F0-1E-UDD-F1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	107	107	107	107	99	99	99	99	84	84	84	70	70	70	57	57	57	51
1	98	94	91	87	91	87	84	81	74	72	70	62	61	59	51	50	49	44
2	90	83	77	72	83	77	72	67	66	62	59	55	53	50	46	44	42	38
3	82	73	66	61	76	68	62	57	58	54	50	49	46	43	41	38	36	32
4	76	65	58	52	70	61	54	49	52	47	43	44	40	37	37	34	32	28
5	70	58	50	45	64	54	47	42	47	41	37	40	36	33	33	30	28	25
6	64	53	45	39	59	49	42	37	42	37	33	36	32	29	30	27	25	22
7	60	48	40	34	55	45	38	33	39	33	29	33	29	26	28	25	22	20
8	55	43	36	31	51	41	34	29	35	30	26	30	26	23	26	23	20	18
9	52	40	32	27	48	37	31	26	33	27	23	28	24	21	24	21	18	16
10	48	36	29	25	45	34	28	24	30	25	21	26	22	19	22	19	17	15

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	27611	27611	27611
5°	27716	27266	27417
10°	27506	26820	26591
15°	27189	26024	25275
20°	26751	24890	23639
25°	26302	23599	22057
30°	25682	22275	20025
35°	25074	20834	18242
40°	24464	19344	16179
45°	23749	17671	14312
50°	23016	15978	12479
55°	22261	14159	10716
60°	21390	12245	8896
65°	20397	10288	8103
70°	19218	8478	7449
75°	17767	7723	6949
80°	15676	6908	6332
85°	12338	5446	5446



TEST NUMBER: P331856-840

CATALOG NUMBER: S122RDIW-S1005D970U840-4F0-1E-UDD-F1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	160.1	2.3
10°-20°	439.5	6.4
20°-30°	617.2	8.9
30°-40°	673.0	9.7
40°-50°	618.8	9.0
50°-60°	486.0	7.0
60°-70°	316.9	4.6
70°-80°	163.4	2.4
80°-90°	47.2	0.7
90°-100°	76.8	1.1
100°-110°	238.5	3.5
110°-120°	407.7	5.9
120°-130°	536.2	7.8
130°-140°	601.8	8.7
140°-150°	590.1	8.5
150°-160°	494.9	7.2
160°-170°	328.3	4.7
170°-180°	114.7	1.7
0°-30°	1216.8	17.6
0°-40°	1889.8	27.3
0°-60°	2994.7	43.3
0°-90°	3522.2	51.0
90°-120°	723.1	10.5
90°-150°	2451.2	35.5
90°-180°	3389.0	49.0
0°-180°	6911.3	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1710	1710	1710	1710	1710	
5°	1710	1702	1682	1695	1692	162
15°	1627	1608	1557	1528	1512	458
25°	1476	1424	1325	1264	1238	679
35°	1272	1190	1057	963	926	796
45°	1040	933	774	668	627	803
55°	791	668	503	414	381	706
65°	534	408	269	219	212	529
75°	285	180	124	114	111	301
85°	67	36	29	29	29	78
90°	1	14	36	34	35	6
95°	53	63	65	65	63	61
105°	220	223	225	227	227	232
115°	409	415	413	412	409	405
125°	595	604	602	598	597	532
135°	770	781	784	782	779	595
145°	935	942	948	949	945	584
155°	1069	1072	1075	1080	1077	492
165°	1163	1162	1162	1168	1164	328
175°	1210	1207	1205	1211	1206	115
180°	1212	1212	1212	1212	1212	



TEST NUMBER: P331856-840

CATALOG NUMBER: S122RDIW-S1005D970U840-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1710.1	1710.1	1710.1	1710.1	1710.1	1710.1	1710.1	1710.1	1710.1	1710.1	1710.1
2.5°	1716.4	1715.0	1713.5	1712.2	1710.8	1708.6	1705.6	1702.6	1699.6	1696.6	1699.3
5°	1710.1	1708.4	1706.7	1705.0	1703.2	1700.2	1695.7	1691.2	1686.8	1682.3	1685.4
7.5°	1692.5	1690.4	1688.3	1686.1	1683.9	1680.3	1675.1	1669.8	1664.7	1659.4	1660.3
10°	1677.7	1675.3	1672.8	1670.4	1668.0	1663.3	1656.5	1649.6	1642.7	1635.9	1634.9
12.5°	1659.1	1656.1	1653.1	1650.2	1647.3	1641.3	1632.5	1623.8	1615.0	1606.2	1604.3
15°	1626.6	1622.8	1619.0	1615.2	1611.4	1603.7	1592.1	1580.3	1568.6	1556.9	1550.4
17.5°	1586.6	1580.8	1575.1	1569.3	1563.6	1553.2	1538.1	1523.2	1508.1	1493.2	1485.4
20°	1556.9	1550.0	1543.2	1536.3	1529.4	1517.4	1500.2	1483.0	1465.8	1448.6	1440.0
22.5°	1524.7	1517.0	1509.3	1501.7	1493.9	1480.4	1461.0	1441.6	1422.2	1402.8	1391.7
25°	1476.4	1465.4	1454.4	1443.4	1432.4	1415.6	1392.9	1370.2	1347.5	1324.7	1310.7
27.5°	1418.3	1406.3	1394.3	1382.4	1370.4	1351.6	1326.1	1300.4	1274.9	1249.3	1232.8
30°	1377.5	1364.3	1351.3	1338.2	1325.1	1304.8	1277.3	1249.8	1222.3	1194.8	1177.2
32.5°	1337.8	1322.5	1307.3	1292.0	1276.7	1255.1	1227.0	1198.9	1170.8	1142.8	1122.8
35°	1272.1	1254.7	1237.1	1219.5	1202.0	1178.1	1147.8	1117.6	1087.3	1057.0	1035.4
37.5°	1206.6	1187.3	1168.0	1148.7	1129.5	1103.8	1071.5	1039.3	1006.9	974.7	950.9
40°	1160.7	1140.1	1119.4	1098.8	1078.2	1051.2	1017.8	984.5	951.1	917.8	893.3
42.5°	1113.7	1092.0	1070.3	1048.4	1026.7	998.7	964.2	929.7	895.2	860.8	835.6
45°	1040.1	1016.9	993.9	970.9	947.9	918.3	882.1	846.1	809.9	773.9	749.4
47.5°	968.2	943.8	919.4	894.9	870.5	839.7	802.4	765.1	727.8	690.5	666.3
50°	916.3	891.8	867.4	842.9	818.5	787.4	749.6	711.8	673.9	636.1	612.4
52.5°	865.5	839.9	814.5	788.9	763.4	732.2	695.1	658.1	621.1	584.1	561.2
55°	790.8	764.1	737.2	710.3	683.6	651.6	614.4	577.2	540.2	503.0	482.3
57.5°	714.4	686.9	659.3	631.9	604.3	572.7	537.0	501.3	465.6	429.9	411.0
60°	662.4	634.9	607.3	579.9	552.3	520.9	485.4	450.0	414.5	379.2	361.6
62.5°	611.7	584.1	556.6	529.1	501.6	470.9	437.2	403.3	369.6	335.9	319.1
65°	533.9	506.0	478.3	450.4	422.5	393.1	362.1	331.2	300.2	269.3	257.6
67.5°	459.0	431.4	403.7	376.1	348.4	320.6	292.9	265.0	237.1	209.2	203.9
70°	407.1	380.2	353.4	326.6	299.7	274.5	250.7	227.0	203.3	179.6	176.1
72.5°	357.5	331.7	306.1	280.3	254.6	232.2	213.2	194.1	175.0	156.0	153.1
75°	284.8	260.6	236.6	212.6	188.4	170.6	158.9	147.2	135.5	123.8	121.4
77.5°	213.3	192.2	171.1	150.0	128.8	115.4	109.8	104.1	98.5	92.9	91.5
80°	168.6	151.2	133.6	116.0	98.6	88.1	84.6	81.2	77.8	74.3	72.9
82.5°	127.8	114.1	100.5	86.7	73.1	65.0	62.7	60.4	58.1	55.7	54.9
85°	66.6	59.3	52.1	44.8	37.7	33.5	32.5	31.5	30.4	29.4	29.4
87.5°	20.0	18.4	16.7	15.0	13.4	13.0	14.0	15.0	16.1	17.1	16.7
90°	1.0	3.7	6.5	9.2	11.9	15.8	20.8	25.8	30.8	35.7	35.3
92.5°	18.2	20.2	22.2	24.2	26.3	27.8	29.0	30.2	31.3	32.5	32.6
95°	53.2	55.4	57.8	60.0	62.3	63.6	64.1	64.5	65.0	65.4	65.4
97.5°	97.1	99.2	101.2	103.2	105.1	106.6	107.4	108.4	109.2	110.1	110.1
100°	129.9	131.7	133.5	135.3	137.1	138.5	139.1	139.8	140.5	141.2	141.2
102.5°	164.3	165.7	167.1	168.6	170.1	171.3	172.1	173.0	173.8	174.7	174.9
105°	219.9	220.6	221.3	222.0	222.7	223.2	223.7	224.1	224.6	225.0	225.5
107.5°	276.0	277.0	277.9	278.9	279.9	280.4	280.4	280.4	280.4	280.4	280.6
110°	311.9	313.4	314.7	316.1	317.4	318.1	318.1	318.1	318.1	318.1	318.1



TEST NUMBER: P331856-840

CATALOG NUMBER: S122RDIW-S1005D970U840-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	351.2	352.6	354.0	355.4	356.7	357.3	357.1	356.9	356.8	356.6	356.0
115°	409.1	410.5	411.8	413.2	414.5	415.1	414.5	414.1	413.6	413.2	413.0
117.5°	466.9	468.7	470.5	472.3	474.1	474.3	473.1	471.8	470.6	469.3	468.8
120°	505.3	507.2	509.0	510.8	512.6	512.6	510.8	509.0	507.2	505.3	505.3
122.5°	540.5	542.7	544.8	547.0	549.2	549.7	548.4	547.1	545.8	544.5	544.0
125°	595.3	597.3	599.4	601.5	603.5	604.2	603.5	602.8	602.1	601.5	600.8
127.5°	648.7	651.3	653.9	656.5	659.0	659.9	659.1	658.3	657.5	656.7	655.8
130°	682.3	685.2	688.1	691.2	694.1	695.3	694.9	694.4	694.0	693.5	693.1
132.5°	719.8	722.3	724.7	727.1	729.5	730.7	730.8	730.9	731.0	731.1	730.1
135°	770.2	772.7	775.2	777.7	780.2	781.6	782.1	782.5	783.0	783.5	783.3
137.5°	823.1	825.3	827.3	829.3	831.3	832.7	833.2	833.8	834.5	835.1	834.9
140°	855.1	857.2	859.2	861.2	863.2	864.8	866.1	867.2	868.3	869.4	869.4
142.5°	887.9	889.9	891.9	893.9	896.1	897.5	898.2	899.0	899.8	900.5	900.7
145°	934.8	936.4	938.1	939.7	941.3	942.7	944.1	945.4	946.8	948.2	948.4
147.5°	976.8	978.8	980.7	982.5	984.4	985.8	986.7	987.6	988.6	989.5	990.0
150°	1005.4	1006.8	1008.1	1009.6	1010.9	1012.1	1013.0	1013.9	1014.8	1015.7	1016.3
152.5°	1030.9	1032.2	1033.6	1034.9	1036.3	1037.5	1038.6	1039.7	1040.8	1041.9	1042.7
155°	1068.8	1069.5	1070.3	1071.0	1071.6	1072.3	1073.0	1073.7	1074.3	1075.0	1076.1
157.5°	1101.4	1101.9	1102.3	1102.8	1103.2	1103.7	1104.1	1104.5	1104.9	1105.3	1106.8
160°	1121.1	1121.5	1122.0	1122.4	1122.9	1123.2	1123.5	1123.7	1123.9	1124.1	1125.5
162.5°	1139.0	1139.1	1139.2	1139.3	1139.4	1139.5	1139.8	1140.0	1140.2	1140.4	1142.1
165°	1163.0	1162.8	1162.6	1162.3	1162.1	1162.0	1162.0	1162.0	1162.0	1162.0	1163.6
167.5°	1183.1	1182.3	1181.6	1180.9	1180.3	1179.9	1179.9	1179.8	1179.8	1179.7	1181.3
170°	1193.7	1193.0	1192.3	1191.6	1190.9	1190.5	1190.2	1190.0	1189.8	1189.6	1191.1
172.5°	1201.0	1200.3	1199.6	1199.0	1198.3	1197.8	1197.6	1197.4	1197.2	1196.9	1198.5
175°	1210.0	1209.3	1208.7	1208.0	1207.3	1206.7	1206.3	1205.8	1205.4	1204.9	1206.5
177.5°	1213.8	1213.2	1212.6	1212.0	1211.5	1211.0	1210.7	1210.3	1210.0	1209.6	1210.7
180°	1212.0	1212.0	1212.0	1212.0	1212.0	1212.0	1212.0	1212.0	1212.0	1212.0	1212.0



TEST NUMBER: P331856-840

CATALOG NUMBER: S122RDIW-S1005D970U840-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1710.1	1710.1	1710.1	1710.1	1710.1	1710.1	1710.1	1710.1
2.5°	1702.0	1704.8	1707.6	1708.6	1708.1	1707.6	1707.0	1706.5
5°	1688.5	1691.6	1694.7	1695.7	1694.7	1693.6	1692.6	1691.6
7.5°	1661.1	1662.0	1662.9	1662.5	1660.7	1658.9	1657.2	1655.4
10°	1633.8	1632.7	1631.7	1630.2	1628.1	1626.1	1624.0	1621.9
12.5°	1602.5	1600.5	1598.7	1596.1	1592.7	1589.2	1585.8	1582.4
15°	1543.9	1537.3	1530.8	1525.8	1522.4	1518.9	1515.5	1512.1
17.5°	1477.6	1469.9	1462.1	1455.2	1449.4	1443.4	1437.4	1431.6
20°	1431.4	1422.8	1414.2	1406.1	1398.6	1391.0	1383.4	1375.8
22.5°	1380.7	1369.6	1358.5	1350.1	1344.5	1338.9	1333.2	1327.6
25°	1296.6	1282.5	1268.4	1258.8	1253.5	1248.4	1243.2	1238.1
27.5°	1216.4	1199.9	1183.5	1171.1	1163.0	1154.8	1146.6	1138.4
30°	1159.7	1142.2	1124.6	1111.3	1102.0	1092.7	1083.4	1074.1
32.5°	1102.8	1082.8	1062.7	1048.3	1039.7	1030.9	1022.1	1013.4
35°	1013.7	992.1	970.4	955.7	948.2	940.6	933.0	925.5
37.5°	927.0	903.1	879.2	862.9	854.3	845.7	837.0	828.3
40°	868.9	844.4	820.1	803.4	794.5	785.5	776.6	767.6
42.5°	810.3	785.1	759.8	742.9	734.2	725.5	716.9	708.2
45°	725.0	700.5	676.1	659.8	651.6	643.3	635.0	626.8
47.5°	642.0	617.7	593.4	577.5	570.1	562.6	555.0	547.5
50°	588.7	564.9	541.2	525.6	518.5	511.2	504.0	496.8
52.5°	538.3	515.3	492.5	477.7	471.0	464.3	457.7	451.0
55°	461.7	441.1	420.4	406.9	400.3	393.7	387.3	380.7
57.5°	392.1	373.1	354.3	342.0	336.6	331.0	325.6	320.0
60°	344.1	326.6	309.0	297.5	292.0	286.5	280.9	275.5
62.5°	302.5	285.7	269.0	258.9	255.7	252.4	249.0	245.8
65°	245.9	234.2	222.5	216.1	215.1	214.1	213.1	212.1
67.5°	198.5	193.2	187.7	184.5	183.5	182.4	181.3	180.2
70°	172.7	169.3	165.8	163.4	162.0	160.6	159.3	157.8
72.5°	150.3	147.3	144.4	142.6	141.8	141.0	140.1	139.3
75°	119.0	116.6	114.2	112.8	112.5	112.1	111.8	111.4
77.5°	90.1	88.8	87.4	86.3	85.8	85.3	84.7	84.2
80°	71.5	70.2	68.8	68.1	68.1	68.1	68.1	68.1
82.5°	54.0	53.2	52.4	52.0	52.0	52.0	52.0	52.0
85°	29.4	29.4	29.4	29.4	29.4	29.4	29.4	29.4
87.5°	16.4	16.0	15.6	15.5	15.5	15.6	15.6	15.7
90°	34.8	34.4	33.9	33.8	34.1	34.3	34.5	34.7
92.5°	32.7	32.8	32.9	32.9	33.0	33.0	33.1	33.1
95°	65.4	65.4	65.4	65.2	64.7	64.3	63.8	63.4
97.5°	110.1	110.1	110.1	110.1	110.0	110.0	109.9	109.9
100°	141.2	141.2	141.2	141.1	140.8	140.6	140.4	140.2
102.5°	175.1	175.2	175.4	175.4	175.2	174.9	174.7	174.5
105°	225.9	226.4	226.8	227.1	227.1	227.1	227.1	227.1
107.5°	280.8	281.0	281.1	280.7	279.7	278.6	277.6	276.6
110°	318.1	318.1	318.1	317.8	317.1	316.4	315.7	315.1





TEST NUMBER: P331856-840

CATALOG NUMBER: S122RDIW-S1005D970U840-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	355.5	355.0	354.4	353.9	353.4	352.8	352.3	351.8
115°	412.7	412.5	412.3	411.8	411.2	410.5	409.8	409.1
117.5°	468.2	467.7	467.1	466.5	465.9	465.1	464.4	463.7
120°	505.3	505.3	505.3	504.9	504.2	503.6	502.9	502.2
122.5°	543.5	542.9	542.4	541.9	541.4	540.9	540.4	539.9
125°	600.1	599.4	598.7	598.2	598.0	597.8	597.5	597.3
127.5°	655.0	654.2	653.4	652.6	651.9	651.2	650.5	649.7
130°	692.6	692.2	691.7	690.9	690.0	689.1	688.2	687.3
132.5°	729.1	728.1	727.1	726.3	725.6	724.8	724.1	723.4
135°	783.0	782.8	782.5	782.1	781.4	780.7	780.1	779.4
137.5°	834.7	834.6	834.4	833.7	832.8	831.9	831.0	830.1
140°	869.4	869.4	869.4	869.0	868.1	867.2	866.3	865.4
142.5°	900.9	901.1	901.2	900.9	900.0	899.1	898.2	897.3
145°	948.7	948.9	949.1	948.8	947.9	947.0	946.0	945.1
147.5°	990.5	991.0	991.5	991.3	990.5	989.6	988.8	987.8
150°	1017.0	1017.7	1018.4	1018.4	1017.7	1017.0	1016.3	1015.7
152.5°	1043.6	1044.5	1045.3	1045.3	1044.5	1043.6	1042.7	1041.9
155°	1077.3	1078.4	1079.5	1079.7	1079.1	1078.4	1077.7	1077.0
157.5°	1108.4	1109.9	1111.5	1111.7	1110.6	1109.5	1108.4	1107.3
160°	1126.8	1128.2	1129.5	1129.8	1128.9	1128.0	1127.1	1126.2
162.5°	1143.6	1145.1	1146.7	1146.9	1145.8	1144.7	1143.6	1142.6
165°	1165.2	1166.7	1168.3	1168.5	1167.4	1166.3	1165.2	1164.0
167.5°	1183.0	1184.6	1186.1	1186.3	1185.2	1184.0	1182.8	1181.6
170°	1192.8	1194.4	1196.0	1196.1	1194.7	1193.4	1191.9	1190.6
172.5°	1200.1	1201.7	1203.3	1203.5	1202.0	1200.7	1199.3	1198.0
175°	1208.1	1209.7	1211.2	1211.4	1210.0	1208.7	1207.3	1206.0
177.5°	1211.8	1212.8	1214.0	1214.0	1212.8	1211.8	1210.7	1209.6
180°	1212.0	1212.0	1212.0	1212.0	1212.0	1212.0	1212.0	1212.0

(END OF REPORT)