

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332421-927

Luminaire Tested: **S123RDIW-S560D1030U927-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332421-927
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-9,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123RDIW-S560D1030U927-4F0-1E-UDD-F1
Description: DEFINE 3 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 560 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 1030 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4524.0 lumens
Efficiency: N/A
Efficacy: 100.1 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.06 / 1.22
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 45.2
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332421-927

CATALOG NUMBER: S123RDIW-S560D1030U927-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P332421-927

CATALOG NUMBER: S123RDIW-S560D1030U927-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	104	104	104	104	94	94	94	94	76	76	76	60	60	60	45	45	45	37
1	95	91	87	84	86	83	80	77	67	65	63	53	51	50	40	39	38	32
2	87	80	74	69	79	73	68	63	59	56	53	47	44	42	35	34	32	27
3	79	70	63	58	72	64	58	53	52	48	44	41	38	36	31	29	28	23
4	73	62	55	49	66	57	50	45	47	42	38	37	34	31	28	26	24	20
5	67	55	48	42	60	51	44	39	42	37	33	33	30	27	25	23	21	18
6	61	50	42	36	56	46	39	34	38	32	29	30	26	24	23	21	19	16
7	57	45	37	32	51	41	34	30	34	29	25	27	24	21	21	19	17	14
8	53	41	33	28	48	37	31	26	31	26	22	25	21	19	20	17	15	13
9	49	37	30	25	44	34	28	23	28	24	20	23	19	17	18	15	14	11
10	46	34	27	22	42	31	25	21	26	21	18	21	18	15	17	14	12	10

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	8054	8054	8054
5°	8084	7973	8018
10°	8039	7873	7847
15°	7952	7689	7608
20°	7834	7458	7285
25°	7712	7201	6969
30°	7549	6901	6524
35°	7384	6603	6116
40°	7231	6250	5611
45°	7030	5903	5154
50°	6807	5508	4644
55°	6583	5056	4168
60°	6374	4573	3645
65°	6105	4050	3123
70°	5766	3402	2521
75°	5273	2674	2371
80°	4705	2374	2182
85°	3977	2100	1951



TEST NUMBER: P332421-927

CATALOG NUMBER: S123RDIW-S560D1030U927-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	70.3	1.6
10°-20°	195.5	4.3
20°-30°	281.5	6.2
30°-40°	317.1	7.0
40°-50°	303.3	6.7
50°-60°	248.4	5.5
60°-70°	167.6	3.7
70°-80°	84.3	1.9
80°-90°	25.3	0.6
90°-100°	66.6	1.5
100°-110°	199.2	4.4
110°-120°	338.8	7.5
120°-130°	445.7	9.9
130°-140°	500.9	11.1
140°-150°	492.4	10.9
150°-160°	414.5	9.2
160°-170°	275.9	6.1
170°-180°	96.6	2.1
0°-30°	547.2	12.1
0°-40°	864.3	19.1
0°-60°	1416.1	31.3
0°-90°	1693.3	37.4
90°-120°	604.6	13.4
90°-150°	2043.6	45.2
90°-180°	2831.0	62.6
0°-180°	4524.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	748	748	748	748	748	
5°	748	745	738	743	742	71
15°	714	706	690	687	683	201
25°	649	633	606	594	587	298
35°	562	539	502	477	465	352
45°	462	433	388	354	339	356
55°	351	320	269	236	222	314
65°	240	206	159	130	123	237
75°	127	97	64	58	57	135
85°	32	19	17	16	16	36
90°	1	9	19	22	24	4
95°	47	53	59	62	63	53
105°	181	182	189	190	191	193
115°	341	343	342	343	342	337
125°	499	501	500	497	494	445
135°	648	652	652	649	647	499
145°	786	787	790	789	786	491
155°	900	900	900	903	898	414
165°	980	978	978	982	977	276
175°	1019	1016	1016	1020	1015	97
180°	1022	1022	1022	1022	1022	



TEST NUMBER: P332421-927

CATALOG NUMBER: S123RDIW-S560D1030U927-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	748.2	748.2	748.2	748.2	748.2	748.2	748.2	748.2	748.2	748.2	748.2
2.5°	750.7	750.2	749.8	749.3	748.9	748.1	746.8	745.4	744.2	742.9	744.1
5°	748.2	747.6	746.9	746.2	745.5	744.4	742.8	741.2	739.5	737.9	739.1
7.5°	741.3	740.6	739.8	739.1	738.4	737.0	734.9	732.8	730.6	728.6	729.2
10°	735.5	734.5	733.6	732.6	731.7	730.0	727.6	725.2	722.7	720.3	720.4
12.5°	727.2	726.2	725.1	724.1	723.0	721.0	718.0	715.1	712.1	709.2	709.1
15°	713.6	712.2	710.7	709.2	707.7	705.0	701.3	697.5	693.7	690.0	689.3
17.5°	696.5	694.8	693.1	691.3	689.6	686.3	681.5	676.8	671.9	667.2	665.7
20°	683.9	681.8	679.6	677.4	675.3	671.6	666.5	661.4	656.2	651.1	649.4
22.5°	669.8	667.3	664.9	662.3	659.9	655.9	650.5	645.0	639.6	634.1	631.9
25°	649.3	645.9	642.5	639.2	635.8	631.1	624.8	618.6	612.4	606.3	603.4
27.5°	624.4	620.7	617.0	613.2	609.5	604.2	597.3	590.4	583.5	576.6	572.7
30°	607.4	603.4	599.4	595.3	591.3	585.4	577.9	570.4	562.8	555.2	550.6
32.5°	590.4	585.9	581.3	576.7	572.1	565.9	557.9	549.9	541.9	533.9	528.9
35°	561.9	557.1	552.2	547.4	542.5	535.9	527.5	519.2	510.8	502.5	496.6
37.5°	533.1	527.7	522.3	516.8	511.4	504.3	495.4	486.5	477.5	468.6	462.0
40°	514.6	508.7	502.7	496.8	490.8	483.1	473.6	464.0	454.4	444.8	437.8
42.5°	493.7	487.7	481.9	475.9	470.0	462.1	452.2	442.3	432.4	422.5	414.8
45°	461.8	455.7	449.6	443.6	437.5	429.3	418.9	408.5	398.2	387.8	380.1
47.5°	429.8	423.2	416.5	409.9	403.2	394.7	384.3	373.9	363.5	353.2	344.8
50°	406.5	400.2	393.9	387.5	381.2	372.6	361.6	350.8	339.8	328.9	320.5
52.5°	385.7	378.8	371.9	365.0	358.2	349.4	338.5	327.7	316.9	306.1	297.4
55°	350.8	344.1	337.5	330.9	324.3	315.3	303.8	292.4	280.9	269.4	261.6
57.5°	318.5	311.2	304.0	296.8	289.6	280.3	268.8	257.3	245.7	234.2	226.9
60°	296.1	288.8	281.3	273.9	266.5	257.1	246.0	234.8	223.6	212.4	205.1
62.5°	273.8	266.4	259.0	251.5	244.2	234.8	223.6	212.5	201.2	190.0	183.2
65°	239.7	232.3	224.9	217.5	210.0	201.1	190.5	180.1	169.5	159.0	152.4
67.5°	205.6	198.1	190.6	183.1	175.6	166.8	156.7	146.6	136.6	126.4	121.5
70°	183.2	175.9	168.7	161.4	154.2	145.8	136.3	126.9	117.5	108.1	103.3
72.5°	160.9	153.8	146.6	139.4	132.2	124.4	115.8	107.2	98.6	90.1	86.2
75°	126.8	120.3	113.9	107.4	100.9	94.0	86.6	79.1	71.8	64.3	63.0
77.5°	95.8	89.9	84.1	78.2	72.3	67.0	62.3	57.5	52.7	47.9	47.2
80°	75.9	70.3	64.8	59.3	53.7	49.6	46.7	43.9	41.0	38.3	37.8
82.5°	57.0	52.1	47.4	42.6	37.8	34.8	33.4	32.2	30.8	29.5	29.1
85°	32.2	29.2	26.2	23.3	20.3	18.6	18.2	17.8	17.4	17.0	16.7
87.5°	11.8	11.0	10.1	9.3	8.5	8.3	8.8	9.3	9.7	10.1	10.2
90°	0.8	2.6	4.4	6.2	7.9	10.0	12.3	14.7	17.0	19.3	20.0
92.5°	19.4	20.6	21.9	23.1	24.2	25.5	26.9	28.2	29.5	30.8	31.4
95°	47.4	48.6	49.8	51.1	52.4	53.7	55.1	56.6	58.0	59.4	60.1
97.5°	84.1	85.0	86.0	86.9	87.9	88.8	89.8	90.9	91.9	92.9	93.8
100°	109.2	110.2	111.3	112.3	113.4	114.4	115.3	116.2	117.1	118.0	118.5
102.5°	138.1	138.7	139.3	140.0	140.6	141.5	142.7	143.9	145.0	146.2	146.8
105°	180.6	180.9	181.3	181.6	182.0	183.0	184.6	186.2	187.8	189.4	189.4
107.5°	230.0	230.2	230.4	230.7	230.8	231.3	232.0	232.6	233.2	233.9	234.4
110°	260.9	261.2	261.6	261.9	262.3	262.6	263.0	263.3	263.7	264.0	264.7



TEST NUMBER: P332421-927

CATALOG NUMBER: S123RDIW-S560D1030U927-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	292.9	293.2	293.3	293.6	293.8	293.9	294.0	294.1	294.1	294.2	295.1
115°	341.1	341.6	342.1	342.7	343.3	343.3	342.9	342.6	342.2	341.9	342.1
117.5°	389.6	389.9	390.3	390.6	391.0	390.9	390.5	390.0	389.5	389.1	389.0
120°	419.8	420.8	421.9	422.9	424.1	424.1	423.2	422.3	421.4	420.6	420.3
122.5°	451.2	452.0	452.8	453.5	454.3	454.5	454.1	453.6	453.1	452.7	452.2
125°	499.2	499.7	500.3	500.8	501.4	501.5	501.1	500.7	500.3	500.0	499.3
127.5°	543.5	544.6	545.8	546.9	548.0	548.4	548.0	547.6	547.2	546.8	545.9
130°	573.1	574.5	575.9	577.3	578.8	579.2	578.7	578.1	577.6	577.0	576.3
132.5°	602.5	604.0	605.4	606.9	608.3	608.8	608.4	608.0	607.6	607.2	606.3
135°	647.7	648.7	649.8	650.9	652.0	652.4	652.2	652.0	651.9	651.6	650.9
137.5°	689.4	690.3	691.2	692.1	693.0	693.6	694.1	694.6	695.1	695.5	694.7
140°	718.3	719.2	720.1	721.0	721.8	722.4	722.5	722.8	722.9	723.1	722.9
142.5°	744.7	745.5	746.4	747.3	748.2	748.8	749.1	749.4	749.8	750.1	749.9
145°	785.7	786.1	786.4	786.8	787.1	787.6	788.1	788.7	789.2	789.7	789.6
147.5°	821.7	822.3	822.9	823.6	824.3	824.8	825.3	825.9	826.3	826.8	826.8
150°	846.7	847.1	847.4	847.8	848.1	848.5	848.8	849.2	849.5	849.9	849.9
152.5°	867.3	867.8	868.2	868.8	869.3	869.6	869.8	870.1	870.3	870.4	870.8
155°	899.7	899.7	899.7	899.7	899.7	899.8	899.9	900.2	900.3	900.5	901.2
157.5°	927.3	927.1	926.9	926.6	926.5	926.4	926.5	926.7	926.9	926.9	927.7
160°	944.6	944.3	943.9	943.6	943.2	943.0	943.0	943.0	943.0	943.0	943.9
162.5°	960.0	959.6	959.0	958.5	958.1	957.8	958.0	958.1	958.3	958.5	959.3
165°	979.9	979.4	978.9	978.3	977.8	977.6	977.6	977.6	977.6	977.6	978.6
167.5°	995.9	995.1	994.4	993.7	993.0	992.7	992.8	993.0	993.2	993.2	994.3
170°	1004.8	1004.1	1003.4	1002.7	1002.0	1001.6	1001.6	1001.6	1001.6	1001.6	1002.8
172.5°	1011.9	1011.1	1010.4	1009.7	1009.0	1008.7	1008.7	1008.7	1008.7	1008.7	1009.8
175°	1019.3	1018.6	1017.9	1017.2	1016.4	1016.1	1016.1	1016.1	1016.1	1016.1	1017.2
177.5°	1022.3	1021.8	1021.2	1020.6	1020.0	1019.8	1019.8	1019.8	1019.8	1019.8	1020.6
180°	1021.7	1021.7	1021.7	1021.7	1021.7	1021.7	1021.7	1021.7	1021.7	1021.7	1021.7



TEST NUMBER: P332421-927

CATALOG NUMBER: S123RDIW-S560D1030U927-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	748.2	748.2	748.2	748.2	748.2	748.2	748.2	748.2
2.5°	745.3	746.5	747.7	748.1	747.9	747.7	747.5	747.3
5°	740.3	741.6	742.8	743.2	743.0	742.7	742.4	742.1
7.5°	729.9	730.6	731.3	731.3	730.9	730.5	730.0	729.5
10°	720.6	720.7	720.8	720.6	719.9	719.2	718.6	717.9
12.5°	709.0	708.9	708.8	708.4	707.6	706.8	706.1	705.3
15°	688.6	687.9	687.3	686.4	685.5	684.6	683.7	682.7
17.5°	664.3	662.9	661.4	660.0	658.6	657.2	655.8	654.4
20°	647.6	645.9	644.1	642.5	640.8	639.2	637.5	636.0
22.5°	629.8	627.6	625.4	623.5	622.0	620.5	619.0	617.5
25°	600.6	597.7	594.9	592.7	591.3	589.8	588.3	586.8
27.5°	568.7	564.8	560.9	557.8	555.5	553.3	551.0	548.7
30°	546.1	541.5	536.9	533.5	531.4	529.3	527.0	524.9
32.5°	523.9	518.8	513.8	510.2	507.9	505.6	503.4	501.1
35°	490.8	485.1	479.3	475.2	472.7	470.3	467.9	465.4
37.5°	455.4	448.9	442.3	437.5	434.5	431.5	428.5	425.5
40°	430.8	423.7	416.8	411.7	408.6	405.5	402.4	399.3
42.5°	407.2	399.5	391.8	386.6	383.8	381.0	378.3	375.5
45°	372.4	364.7	357.0	351.6	348.3	345.1	341.8	338.6
47.5°	336.4	328.1	319.7	314.1	311.2	308.3	305.5	302.5
50°	312.2	303.8	295.5	289.7	286.6	283.5	280.4	277.3
52.5°	288.8	280.0	271.3	265.6	262.8	260.1	257.3	254.5
55°	253.8	246.0	238.1	232.9	230.2	227.5	224.8	222.1
57.5°	219.4	212.1	204.7	199.9	197.6	195.3	193.0	190.7
60°	197.8	190.5	183.2	178.5	176.2	173.9	171.6	169.3
62.5°	176.3	169.5	162.6	158.0	155.7	153.2	150.8	148.5
65°	145.8	139.2	132.5	128.5	127.1	125.6	124.1	122.6
67.5°	116.6	111.6	106.7	103.5	101.9	100.3	98.7	97.1
70°	98.5	93.9	89.1	86.0	84.5	83.1	81.6	80.1
72.5°	82.3	78.5	74.6	72.4	71.8	71.1	70.5	69.9
75°	61.6	60.3	58.9	58.1	57.8	57.6	57.3	57.0
77.5°	46.5	45.8	45.0	44.5	44.3	44.0	43.7	43.4
80°	37.4	37.0	36.6	36.3	36.0	35.7	35.5	35.2
82.5°	28.7	28.3	27.9	27.6	27.6	27.6	27.5	27.4
85°	16.5	16.2	15.9	15.8	15.8	15.8	15.8	15.8
87.5°	10.2	10.3	10.3	10.3	10.3	10.2	10.2	10.1
90°	20.7	21.4	22.1	22.7	23.0	23.4	23.7	24.1
92.5°	31.9	32.6	33.1	33.3	33.0	32.9	32.6	32.4
95°	60.8	61.6	62.3	62.6	62.6	62.6	62.6	62.6
97.5°	94.6	95.4	96.3	96.6	96.5	96.5	96.4	96.3
100°	119.1	119.6	120.1	120.6	120.9	121.3	121.6	122.0
102.5°	147.3	147.8	148.4	148.6	148.5	148.5	148.4	148.3
105°	189.4	189.4	189.4	189.6	190.0	190.3	190.7	191.0
107.5°	235.0	235.6	236.1	236.3	236.1	235.9	235.7	235.4
110°	265.5	266.2	266.9	267.0	266.7	266.3	266.0	265.6



TEST NUMBER: P332421-927

CATALOG NUMBER: S123RDIW-S560D1030U927-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	296.0	296.8	297.6	298.0	297.9	297.9	297.9	297.8
115°	342.2	342.5	342.6	342.6	342.5	342.2	342.1	341.9
117.5°	389.0	389.0	389.0	388.6	388.2	387.7	387.1	386.7
120°	420.2	420.0	419.9	419.5	419.2	418.8	418.5	418.1
122.5°	451.7	451.2	450.8	450.3	449.8	449.3	448.9	448.3
125°	498.6	497.9	497.2	496.5	495.7	495.0	494.3	493.6
127.5°	544.9	543.9	542.9	541.9	541.1	540.3	539.5	538.7
130°	575.6	574.9	574.2	573.2	572.0	570.7	569.5	568.2
132.5°	605.5	604.7	603.8	602.9	601.9	600.9	600.0	599.0
135°	650.2	649.5	648.8	648.3	647.9	647.6	647.2	646.9
137.5°	694.0	693.2	692.5	691.8	691.1	690.5	689.8	689.1
140°	722.8	722.5	722.4	721.7	720.4	719.2	718.0	716.7
142.5°	749.7	749.6	749.4	748.8	747.8	746.9	745.9	745.0
145°	789.4	789.2	789.0	788.5	787.8	787.1	786.4	785.7
147.5°	826.8	826.8	826.8	826.2	825.2	824.1	823.1	822.0
150°	849.9	849.9	849.9	849.4	848.3	847.2	846.2	845.1
152.5°	871.0	871.3	871.6	871.3	870.4	869.4	868.5	867.6
155°	901.9	902.6	903.3	903.1	901.8	900.6	899.4	898.1
157.5°	928.4	929.2	929.9	929.9	928.8	927.9	926.9	925.8
160°	944.8	945.7	946.6	946.7	945.9	945.2	944.5	943.8
162.5°	960.2	961.1	962.0	961.9	960.8	959.6	958.5	957.3
165°	979.7	980.7	981.8	981.8	980.5	979.2	977.9	976.8
167.5°	995.5	996.6	997.7	997.7	996.6	995.5	994.3	993.2
170°	1004.1	1005.4	1006.6	1006.6	1005.4	1004.1	1002.8	1001.6
172.5°	1010.9	1012.0	1013.1	1013.0	1011.8	1010.5	1009.2	1008.1
175°	1018.2	1019.3	1020.3	1020.3	1019.0	1017.7	1016.5	1015.3
177.5°	1021.4	1022.3	1023.2	1023.1	1022.1	1021.1	1020.1	1019.1
180°	1021.7	1021.7	1021.7	1021.7	1021.7	1021.7	1021.7	1021.7

(END OF REPORT)