

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331779-840

Luminaire Tested: **S122RDIW-S290D1240U840-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331779-840
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122RDIW-S290D1240U840-4F0-1E-UDD-F
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 290 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 1240 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6049.9 lumens
Efficiency: N/A
Efficacy: 129.8 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 46.6
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331779-840

CATALOG NUMBER: S122RDIW-S290D1240U840-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P331779-840

CATALOG NUMBER: S122RDIW-S290D1240U840-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	99	99	99	99	87	87	87	87	65	65	65	45	45	45	26	26	26	17
1	91	87	83	80	80	76	73	71	57	55	53	39	38	37	23	23	22	15
2	83	76	70	65	72	67	62	58	50	47	44	35	33	31	21	20	19	13
3	75	67	60	54	66	59	53	49	44	41	37	31	29	27	18	17	16	11
4	69	59	52	46	60	52	46	41	39	35	32	28	25	23	17	15	14	10
5	63	52	45	39	55	46	40	35	35	31	27	25	22	20	15	13	12	8
6	58	47	39	34	51	42	35	30	32	27	24	22	19	17	14	12	11	7
7	54	42	35	29	47	37	31	27	29	24	21	20	17	15	12	11	10	7
8	50	38	31	26	44	34	28	23	26	21	18	18	16	13	11	10	9	6
9	46	35	28	23	40	31	25	21	24	19	16	17	14	12	10	9	8	5
10	43	32	25	20	38	28	22	18	22	17	15	15	13	11	10	8	7	5

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	8186	8186	8186
5°	8217	8083	8126
10°	8153	7950	7883
15°	8058	7714	7492
20°	7930	7378	7009
25°	7798	6996	6538
30°	7612	6604	5936
35°	7433	6177	5409
40°	7253	5735	4795
45°	7040	5236	4242
50°	6822	4735	3697
55°	6598	4197	3178
60°	6339	3630	2638
65°	6044	3049	2399
70°	5698	2511	2209
75°	5265	2289	2059
80°	4649	2046	1878
85°	3649	1612	1612



TEST NUMBER: P331779-840

CATALOG NUMBER: S122RDIW-S290D1240U840-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	47.4	0.8
10°-20°	130.3	2.2
20°-30°	183.0	3.0
30°-40°	199.5	3.3
40°-50°	183.4	3.0
50°-60°	144.1	2.4
60°-70°	93.9	1.6
70°-80°	48.4	0.8
80°-90°	16.8	0.3
90°-100°	56.9	0.9
100°-110°	208.8	3.5
110°-120°	558.2	9.2
120°-130°	921.5	15.2
130°-140°	980.0	16.2
140°-150°	910.9	15.1
150°-160°	732.3	12.1
160°-170°	471.9	7.8
170°-180°	162.4	2.7
0°-30°	360.7	6.0
0°-40°	560.2	9.3
0°-60°	887.7	14.7
0°-90°	1046.8	17.3
90°-120°	824.0	13.6
90°-150°	3636.4	60.1
90°-180°	5003.0	82.7
0°-180°	6049.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	507	507	507	507	507	
5°	507	504	499	502	501	48
15°	482	476	462	453	448	136
25°	438	422	393	375	367	201
35°	377	353	313	285	274	236
45°	308	277	229	198	186	238
55°	234	198	149	123	113	209
65°	158	121	80	65	63	157
75°	84	53	37	34	33	89
85°	20	11	9	9	9	23
90°	1	15	25	31	33	5
95°	80	42	48	54	53	98
105°	376	392	75	88	94	401
115°	710	732	762	217	101	699
125°	1004	1021	1044	1052	1056	895
135°	1243	1262	1274	1285	1284	959
145°	1442	1442	1461	1469	1464	901
155°	1587	1578	1591	1598	1589	731
165°	1673	1666	1669	1677	1669	472
175°	1711	1703	1705	1712	1701	163
180°	1707	1707	1707	1707	1707	



TEST NUMBER: P331779-840

CATALOG NUMBER: S122RDIW-S290D1240U840-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	507.0	507.0	507.0	507.0	507.0	507.0	507.0	507.0	507.0	507.0	507.0
2.5°	508.8	508.4	508.0	507.6	507.2	506.4	505.5	504.7	503.8	502.9	503.7
5°	507.0	506.4	505.9	505.4	504.9	503.9	502.6	501.3	500.0	498.7	499.6
7.5°	501.7	501.1	500.4	499.8	499.2	498.1	496.6	494.9	493.4	491.9	492.1
10°	497.3	496.6	495.8	495.1	494.4	493.0	491.0	489.0	487.0	484.9	484.6
12.5°	491.8	490.9	490.0	489.2	488.3	486.6	483.9	481.3	478.7	476.1	475.5
15°	482.1	481.0	479.9	478.8	477.7	475.3	471.9	468.5	464.9	461.5	459.6
17.5°	470.3	468.6	466.9	465.1	463.4	460.4	456.0	451.5	447.1	442.6	440.3
20°	461.5	459.5	457.5	455.3	453.3	449.8	444.6	439.6	434.5	429.4	426.9
22.5°	452.0	449.7	447.4	445.1	442.8	438.8	433.0	427.3	421.6	415.9	412.5
25°	437.7	434.3	431.1	427.9	424.6	419.6	412.8	406.2	399.4	392.7	388.5
27.5°	420.4	416.9	413.3	409.8	406.2	400.6	393.0	385.5	377.9	370.3	365.5
30°	408.3	404.5	400.5	396.7	392.8	386.8	378.6	370.5	362.3	354.2	349.0
32.5°	396.6	392.0	387.5	382.9	378.4	372.0	363.8	355.4	347.1	338.7	332.9
35°	377.1	371.9	366.7	361.5	356.3	349.2	340.2	331.2	322.3	313.4	306.9
37.5°	357.7	351.9	346.2	340.5	334.8	327.2	317.6	308.0	298.5	288.9	281.9
40°	344.1	338.0	331.8	325.7	319.6	311.6	301.7	291.9	282.0	272.1	264.8
42.5°	330.1	323.7	317.2	310.8	304.4	296.0	285.8	275.6	265.4	255.2	247.7
45°	308.3	301.4	294.6	287.8	280.9	272.2	261.5	250.7	240.0	229.3	222.2
47.5°	287.0	279.7	272.6	265.3	258.0	248.9	237.8	226.8	215.7	204.7	197.5
50°	271.6	264.4	257.1	249.8	242.7	233.4	222.2	211.0	199.8	188.5	181.5
52.5°	256.5	248.9	241.5	233.9	226.3	217.0	206.0	195.1	184.1	173.1	166.3
55°	234.4	226.5	218.5	210.6	202.6	193.2	182.1	171.1	160.1	149.1	143.0
57.5°	211.8	203.6	195.4	187.3	179.2	169.8	159.2	148.7	138.0	127.4	121.8
60°	196.3	188.2	180.1	171.9	163.7	154.4	143.9	133.4	122.9	112.4	107.1
62.5°	181.3	173.2	165.0	156.8	148.7	139.6	129.6	119.6	109.6	99.6	94.6
65°	158.2	150.0	141.8	133.5	125.2	116.5	107.3	98.2	89.0	79.8	76.3
67.5°	136.0	127.8	119.7	111.5	103.3	95.0	86.7	78.6	70.3	62.0	60.4
70°	120.7	112.7	104.7	96.8	88.9	81.4	74.3	67.3	60.3	53.2	52.2
72.5°	105.9	98.4	90.7	83.1	75.4	68.9	63.2	57.6	51.9	46.3	45.3
75°	84.4	77.3	70.2	63.0	55.8	50.6	47.1	43.6	40.2	36.7	36.0
77.5°	63.2	57.0	50.7	44.4	38.2	34.2	32.5	30.9	29.2	27.6	27.2
80°	50.0	44.8	39.6	34.4	29.2	26.1	25.0	24.0	23.0	22.0	21.6
82.5°	37.9	33.8	29.8	25.8	21.7	19.3	18.6	17.9	17.2	16.6	16.3
85°	19.7	17.6	15.5	13.3	11.2	9.9	9.6	9.3	9.0	8.7	8.7
87.5°	6.2	6.1	6.1	6.0	6.0	6.2	6.6	7.0	7.5	7.9	8.1
90°	1.2	4.2	7.3	10.3	13.3	16.0	18.1	20.3	22.5	24.7	26.1
92.5°	24.9	24.6	24.4	24.1	23.8	24.2	25.3	26.5	27.6	28.7	29.4
95°	80.3	71.2	62.2	53.1	44.0	40.5	42.4	44.3	46.3	48.2	49.6
97.5°	159.4	133.8	108.3	82.8	57.3	46.7	51.1	55.5	60.1	64.5	65.5
100°	218.6	181.1	143.4	105.8	68.3	51.7	56.5	61.1	65.7	70.4	72.6
102.5°	283.9	275.9	267.9	260.0	252.1	228.5	189.5	150.5	111.4	72.4	75.2
105°	375.6	383.7	392.0	400.2	408.5	375.2	300.2	225.2	150.3	75.3	78.4
107.5°	480.1	486.7	493.3	500.0	506.6	465.0	375.2	285.3	195.4	105.5	102.4
110°	547.2	553.0	558.8	564.5	570.3	533.5	454.2	374.9	295.5	216.2	188.7



TEST NUMBER: P331779-840

CATALOG NUMBER: S122RDIW-S290D1240U840-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	610.5	615.6	620.7	625.8	631.0	623.7	604.1	584.5	564.9	545.2	445.1
115°	710.3	715.0	719.6	724.3	729.0	734.8	741.6	748.5	755.4	762.2	635.1
117.5°	799.5	804.8	809.9	815.2	820.4	825.4	830.0	834.8	839.5	844.2	813.4
120°	864.7	868.9	872.9	877.1	881.2	885.8	890.7	895.6	900.6	905.4	908.8
122.5°	920.1	924.4	928.8	933.1	937.5	942.3	947.7	953.0	958.5	963.8	965.7
125°	1004.3	1007.8	1011.5	1015.0	1018.5	1023.0	1028.2	1033.4	1038.6	1043.9	1045.8
127.5°	1080.7	1084.6	1088.5	1092.6	1096.5	1100.4	1104.3	1108.2	1112.1	1116.0	1118.8
130°	1129.1	1133.5	1137.9	1142.3	1146.7	1150.3	1153.4	1156.4	1159.4	1162.5	1165.5
132.5°	1178.5	1182.2	1186.0	1189.7	1193.5	1196.8	1199.8	1202.9	1205.9	1208.9	1211.4
135°	1242.7	1247.1	1251.5	1255.9	1260.3	1263.7	1266.2	1268.7	1271.1	1273.6	1276.4
137.5°	1307.7	1310.8	1313.8	1317.0	1320.0	1322.9	1325.8	1328.6	1331.3	1334.1	1336.9
140°	1350.2	1352.4	1354.6	1356.8	1359.0	1361.6	1364.6	1367.7	1370.7	1373.7	1376.1
142.5°	1385.8	1387.8	1389.8	1391.7	1393.7	1396.4	1399.9	1403.3	1406.7	1410.3	1412.5
145°	1441.6	1441.4	1441.1	1440.8	1440.6	1442.7	1447.4	1452.1	1456.7	1461.4	1463.3
147.5°	1490.3	1489.2	1488.2	1487.1	1486.1	1487.9	1492.5	1497.1	1501.8	1506.3	1507.8
150°	1522.0	1520.0	1518.1	1516.1	1514.2	1515.5	1519.8	1524.3	1528.6	1533.1	1534.7
152.5°	1548.6	1546.5	1544.3	1542.2	1540.0	1541.1	1545.2	1549.4	1553.6	1557.7	1559.4
155°	1587.4	1584.9	1582.5	1579.9	1577.5	1577.9	1581.2	1584.5	1587.8	1591.1	1592.8
157.5°	1617.8	1615.7	1613.6	1611.5	1609.4	1609.5	1611.8	1614.2	1616.5	1618.8	1620.6
160°	1635.6	1634.0	1632.2	1630.6	1629.0	1629.0	1630.6	1632.2	1634.0	1635.6	1637.2
162.5°	1651.4	1649.7	1648.1	1646.5	1644.8	1644.7	1646.1	1647.5	1649.0	1650.4	1652.2
165°	1672.6	1671.0	1669.3	1667.7	1666.1	1665.7	1666.5	1667.3	1668.1	1668.9	1670.8
167.5°	1688.5	1686.8	1685.2	1683.5	1681.8	1681.4	1682.2	1682.9	1683.7	1684.5	1686.4
170°	1697.4	1695.7	1694.0	1692.4	1690.7	1690.2	1690.7	1691.3	1691.8	1692.4	1694.4
172.5°	1703.2	1701.6	1700.0	1698.3	1696.7	1696.2	1696.7	1697.2	1697.8	1698.3	1700.2
175°	1710.9	1709.0	1707.1	1705.2	1703.2	1702.5	1703.1	1703.6	1704.2	1704.8	1706.7
177.5°	1712.1	1710.6	1709.1	1707.6	1706.0	1705.4	1705.6	1705.8	1706.0	1706.3	1707.8
180°	1707.2	1707.2	1707.2	1707.2	1707.2	1707.2	1707.2	1707.2	1707.2	1707.2	1707.2



TEST NUMBER: P331779-840

CATALOG NUMBER: S122RDIW-S290D1240U840-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	507.0	507.0	507.0	507.0	507.0	507.0	507.0	507.0
2.5°	504.5	505.3	506.1	506.4	506.3	506.1	505.9	505.8
5°	500.5	501.4	502.3	502.6	502.3	502.0	501.7	501.4
7.5°	492.4	492.7	492.9	492.8	492.3	491.7	491.2	490.7
10°	484.3	484.0	483.7	483.2	482.6	482.0	481.4	480.8
12.5°	475.0	474.4	473.9	473.1	472.1	471.1	470.1	469.1
15°	457.7	455.7	453.7	452.3	451.3	450.2	449.2	448.2
17.5°	438.0	435.7	433.4	431.4	429.6	427.9	426.1	424.3
20°	424.3	421.7	419.2	416.8	414.5	412.3	410.1	407.9
22.5°	409.3	406.0	402.7	400.2	398.5	396.9	395.2	393.5
25°	384.4	380.1	376.0	373.1	371.6	370.0	368.5	367.0
27.5°	360.5	355.7	350.8	347.2	344.8	342.3	339.9	337.5
30°	343.8	338.6	333.4	329.4	326.6	323.9	321.1	318.4
32.5°	326.9	320.9	315.0	310.7	308.2	305.6	303.0	300.4
35°	300.5	294.1	287.6	283.3	281.0	278.8	276.6	274.4
37.5°	274.8	267.7	260.6	255.8	253.3	250.6	248.1	245.5
40°	257.6	250.3	243.1	238.1	235.5	232.9	230.1	227.5
42.5°	240.1	232.7	225.2	220.3	217.6	215.1	212.5	210.0
45°	214.9	207.6	200.5	195.6	193.2	190.7	188.2	185.8
47.5°	190.3	183.1	175.9	171.2	169.0	166.7	164.5	162.3
50°	174.5	167.4	160.4	155.8	153.7	151.6	149.4	147.2
52.5°	159.6	152.8	146.0	141.6	139.7	137.6	135.6	133.7
55°	136.8	130.8	124.6	120.6	118.7	116.7	114.8	112.9
57.5°	116.2	110.6	105.0	101.4	99.8	98.2	96.5	94.8
60°	102.0	96.8	91.6	88.2	86.5	84.9	83.3	81.7
62.5°	89.7	84.7	79.8	76.7	75.7	74.8	73.8	72.8
65°	72.9	69.4	65.9	64.0	63.7	63.4	63.1	62.8
67.5°	58.9	57.3	55.6	54.7	54.3	54.0	53.7	53.4
70°	51.2	50.2	49.2	48.5	48.0	47.6	47.2	46.8
72.5°	44.5	43.6	42.8	42.3	42.0	41.8	41.5	41.3
75°	35.2	34.5	33.8	33.4	33.3	33.2	33.1	33.0
77.5°	26.7	26.3	25.9	25.7	25.4	25.2	25.1	24.9
80°	21.2	20.8	20.4	20.2	20.2	20.2	20.2	20.2
82.5°	16.1	15.8	15.6	15.5	15.5	15.5	15.5	15.5
85°	8.7	8.7	8.7	8.7	8.7	8.7	8.7	8.7
87.5°	8.3	8.5	8.7	8.8	8.9	9.0	9.1	9.2
90°	27.5	28.8	30.2	31.2	31.7	32.2	32.8	33.3
92.5°	30.1	30.8	31.5	32.0	32.3	32.7	33.0	33.3
95°	50.9	52.3	53.6	54.2	53.9	53.6	53.4	53.1
97.5°	66.7	67.8	68.9	69.6	69.9	70.3	70.6	70.9
100°	74.8	77.0	79.2	80.6	81.1	81.7	82.2	82.8
102.5°	78.1	81.0	83.8	85.6	86.3	87.2	88.0	88.7
105°	81.4	84.4	87.5	89.5	90.6	91.7	92.8	93.9
107.5°	99.4	96.2	93.2	92.2	93.3	94.4	95.5	96.6
110°	161.3	133.8	106.3	93.2	94.3	95.4	96.5	97.6



TEST NUMBER: P331779-840

CATALOG NUMBER: S122RDIW-S290D1240U840-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	345.0	244.9	144.7	95.0	95.9	96.8	97.7	98.6
115°	508.0	380.9	253.8	180.4	160.6	140.9	121.1	101.3
117.5°	782.7	751.9	721.2	673.4	608.4	543.5	478.6	413.5
120°	912.1	915.3	918.7	901.8	864.7	827.7	790.6	753.6
122.5°	967.8	969.8	971.7	969.1	961.9	954.7	947.6	940.3
125°	1047.7	1049.7	1051.6	1052.9	1053.7	1054.6	1055.4	1056.2
127.5°	1121.6	1124.4	1127.2	1128.7	1128.8	1129.0	1129.1	1129.3
130°	1168.5	1171.5	1174.5	1175.9	1175.6	1175.4	1175.1	1174.8
132.5°	1214.1	1216.6	1219.2	1220.3	1220.1	1219.8	1219.5	1219.3
135°	1279.1	1281.8	1284.6	1285.7	1285.2	1284.6	1284.0	1283.5
137.5°	1339.5	1342.2	1344.9	1345.7	1344.8	1343.9	1343.0	1342.0
140°	1378.7	1381.1	1383.6	1384.1	1382.7	1381.4	1380.0	1378.7
142.5°	1414.7	1417.0	1419.3	1419.7	1418.4	1416.9	1415.5	1414.2
145°	1465.2	1467.1	1469.1	1469.4	1467.9	1466.6	1465.2	1463.9
147.5°	1509.2	1510.7	1512.1	1512.2	1511.1	1509.8	1508.7	1507.6
150°	1536.3	1538.0	1539.6	1539.7	1538.4	1537.0	1535.6	1534.3
152.5°	1561.0	1562.7	1564.4	1564.3	1562.5	1560.6	1558.8	1557.0
155°	1594.4	1596.1	1597.7	1597.4	1595.2	1593.1	1590.8	1588.6
157.5°	1622.6	1624.4	1626.3	1626.1	1624.0	1621.8	1619.7	1617.5
160°	1638.9	1640.5	1642.1	1642.0	1640.1	1638.2	1636.3	1634.4
162.5°	1654.2	1656.0	1657.9	1657.6	1655.3	1652.8	1650.5	1648.2
165°	1672.7	1674.7	1676.6	1676.6	1674.7	1672.7	1670.8	1668.9
167.5°	1688.3	1690.2	1692.1	1691.9	1689.4	1687.0	1684.5	1682.0
170°	1696.3	1698.2	1700.1	1699.8	1697.4	1694.9	1692.4	1689.9
172.5°	1702.1	1704.0	1706.0	1705.8	1703.2	1700.8	1698.3	1695.9
175°	1708.6	1710.5	1712.4	1712.0	1709.3	1706.6	1703.7	1701.0
177.5°	1709.3	1710.8	1712.4	1712.1	1710.2	1708.2	1706.3	1704.2
180°	1707.2	1707.2	1707.2	1707.2	1707.2	1707.2	1707.2	1707.2

(END OF REPORT)