

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332426-927

Luminaire Tested: **S123RDIW-S560D1535U927-4F0-1E-UDD-A**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P332426-927  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-5,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S123RDIW-S560D1535U927-4F0-1E-UDD-A  
Description: DEFINE 3 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 560 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING  
UPLIGHT 1535 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 6630.4 lumens  
Efficiency: N/A  
Efficacy: 109.4 lumens/watt  
Spacing Criteria (0/90/45): 1.21 / 1.22 / 1.36  
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')  
CIE Type: Semi-Indirect


Input Watts (W): 60.6  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332426-927

CATALOG NUMBER: S123RDIW-S560D1535U927-4F0-1E-UDD-A

### Luminous Intensity Polar Plot



— 0°-180°    - - 45°-225°    - - - 90°-270°    - . - . 135°-315°



TEST NUMBER: P332426-927

CATALOG NUMBER: S123RDIW-S560D1535U927-4F0-1E-UDD-A

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	102	102	102	102	91	91	91	91	70	70	70	52	52	52	35	35	35	27
1	93	89	85	82	83	79	76	74	62	60	58	46	45	44	31	30	30	23
2	85	78	72	67	76	70	65	61	55	51	49	41	39	37	28	27	26	20
3	77	69	62	56	69	62	56	51	48	44	41	36	34	31	25	23	22	17
4	71	61	53	48	63	55	48	44	43	39	35	32	29	27	22	21	19	15
5	65	54	47	41	58	49	42	37	39	34	30	29	26	24	20	18	17	13
6	60	49	41	35	53	44	37	32	35	30	26	26	23	21	18	17	15	12
7	55	44	36	31	49	40	33	28	31	27	23	24	21	18	17	15	13	10
8	51	40	32	27	46	36	29	25	29	24	21	22	19	16	16	14	12	9
9	48	36	29	24	43	33	26	22	26	22	18	20	17	15	14	12	11	9
10	44	33	26	22	40	30	24	20	24	20	17	19	15	13	13	11	10	8

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	7629	7629	7629	7629
5°	9095	7662	6748	7662
10°	11355	7618	6096	7618
15°	13329	7540	5558	7540
20°	14875	7424	5102	7424
25°	14638	7301	4822	7301
30°	10521	7188	4533	7188
35°	7025	7041	4346	7041
40°	5176	6864	4154	6864
45°	4341	6555	3962	6555
50°	3831	6149	3699	6149
55°	3359	5684	3337	5684
60°	2990	5240	3057	5240
65°	2626	4760	2845	4760
70°	2061	4337	2596	4337
75°	1817	3785	2371	3785
80°	1581	3217	2331	3217
85°	1272	2581	2470	2581



TEST NUMBER: P332426-927

CATALOG NUMBER: S123RDIW-S560D1535U927-4F0-1E-UDD-A

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	69.7	1.1
10°-20°	217.8	3.3
20°-30°	342.1	5.2
30°-40°	356.9	5.4
40°-50°	305.5	4.6
50°-60°	232.8	3.5
60°-70°	149.2	2.3
70°-80°	71.8	1.1
80°-90°	23.5	0.4
90°-100°	58.0	0.9
100°-110°	276.2	4.2
110°-120°	663.5	10.0
120°-130°	844.9	12.7
130°-140°	902.7	13.6
140°-150°	844.1	12.7
150°-160°	680.9	10.3
160°-170°	439.5	6.6
170°-180°	151.5	2.3
0°-30°	629.6	9.5
0°-40°	986.5	14.9
0°-60°	1524.8	23.0
0°-90°	1769.2	26.7
90°-120°	997.6	15.0
90°-150°	3589.3	54.1
90°-180°	4861.0	73.3
0°-180°	6630.4	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	709	709	709	709	709	
5°	842	709	624	709	842	87
15°	1196	677	499	677	1196	339
25°	1232	615	406	615	1232	530
35°	535	536	331	536	535	351
45°	285	431	260	431	285	224
55°	179	303	178	303	179	162
65°	103	187	112	187	103	101
75°	44	91	57	91	44	47
85°	10	21	20	21	10	13
90°	36	1	36	1	36	16
95°	45	72	45	72	45	38
105°	52	353	52	353	52	119
115°	696	662	696	662	696	643
125°	952	933	952	933	952	850
135°	1174	1162	1174	1162	1174	905
145°	1354	1341	1354	1341	1354	845
155°	1474	1477	1474	1477	1474	680
165°	1554	1557	1554	1557	1554	439
175°	1588	1594	1588	1594	1588	151
180°	1594	1594	1594	1594	1594	



TEST NUMBER: P332426-927

CATALOG NUMBER: S123RDIW-S560D1535U927-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	708.8	708.8	708.8	708.8	708.8	708.8	708.8	708.8	708.8	708.8	708.8
2.5°	754.9	755.9	752.7	752.3	748.6	747.7	747.7	742.5	739.3	735.2	732.8
5°	841.7	846.5	844.1	838.7	829.6	827.4	821.7	812.5	802.2	789.5	783.5
7.5°	950.1	956.7	954.1	945.7	936.2	928.4	912.2	897.1	875.9	857.4	841.5
10°	1038.9	1031.9	1026.5	1018.3	1009.5	995.2	978.3	954.9	927.9	906.7	883.0
12.5°	1105.4	1104.3	1097.3	1088.9	1076.5	1063.0	1042.0	1013.6	982.2	951.5	924.5
15°	1196.1	1197.9	1193.3	1184.6	1167.0	1143.0	1111.4	1099.6	1054.7	1021.3	987.9
17.5°	1258.9	1258.5	1257.8	1245.6	1227.7	1210.6	1181.4	1150.2	1109.6	1062.6	1017.6
20°	1298.6	1295.6	1296.2	1282.5	1269.2	1249.5	1221.0	1175.8	1142.4	1088.1	1041.6
22.5°	1297.7	1297.0	1299.3	1294.7	1285.0	1269.9	1247.4	1209.3	1166.6	1111.8	1059.6
25°	1232.5	1230.1	1244.4	1248.2	1263.8	1266.5	1259.8	1238.9	1198.5	1142.1	1077.4
27.5°	1031.5	1030.2	1056.6	1089.7	1131.8	1164.4	1196.0	1211.2	1198.5	1158.1	1093.4
30°	846.5	875.0	888.4	936.4	989.8	1053.4	1109.3	1162.4	1175.4	1157.9	1104.8
32.5°	702.8	727.7	738.9	780.1	829.8	904.4	988.2	1063.3	1116.5	1130.0	1098.0
35°	534.6	535.0	560.4	578.6	624.7	701.5	782.8	883.5	983.7	1059.5	1067.5
37.5°	426.6	428.1	443.5	461.7	496.3	536.9	608.5	692.2	807.9	924.3	992.6
40°	368.4	371.1	382.6	400.5	425.4	456.1	511.9	590.7	687.2	816.8	922.7
42.5°	331.0	335.4	341.4	355.1	370.5	399.3	444.4	505.3	593.0	715.6	837.7
45°	285.2	287.6	292.2	298.6	312.5	332.6	362.9	403.9	476.7	575.3	697.6
47.5°	251.6	250.3	255.1	260.3	269.6	283.2	303.6	337.0	389.0	468.0	571.8
50°	228.8	228.5	231.8	235.8	244.5	254.6	271.2	296.4	337.7	403.2	498.2
52.5°	207.4	208.6	211.0	215.9	222.2	230.3	245.3	263.4	298.9	355.5	434.6
55°	179.0	179.9	183.2	186.0	190.5	198.8	208.2	223.3	247.6	287.0	352.3
57.5°	155.0	154.6	157.8	158.4	163.6	170.2	177.5	189.3	206.9	236.2	280.2
60°	138.9	138.1	140.8	142.9	145.6	151.1	157.2	168.7	182.7	204.2	241.9
62.5°	124.4	124.0	126.0	128.1	130.3	135.3	140.5	149.2	160.3	178.5	208.3
65°	103.1	104.1	105.0	105.9	107.1	110.1	115.0	121.0	128.7	141.4	163.0
67.5°	81.0	82.0	82.3	84.1	86.7	88.6	91.7	97.0	102.3	113.0	125.3
70°	65.5	65.2	65.5	66.5	69.8	73.1	77.1	81.0	84.4	92.0	102.3
72.5°	56.3	55.8	56.6	56.7	58.4	59.3	61.8	65.5	69.8	74.9	82.4
75°	43.7	43.7	43.7	43.7	44.9	45.6	46.4	47.4	48.9	51.3	56.7
77.5°	32.3	32.3	32.8	33.0	33.4	33.7	34.2	35.2	35.6	37.0	39.3
80°	25.5	25.8	25.5	25.8	25.8	26.4	26.7	27.6	27.9	29.5	30.3
82.5°	19.2	19.0	19.2	19.5	19.5	20.1	20.1	20.8	20.9	21.6	22.6
85°	10.3	9.7	10.3	10.0	10.6	10.0	10.3	10.9	10.9	11.2	12.4
87.5°	9.5	9.9	9.3	9.4	9.3	9.4	9.3	9.0	9.3	8.9	8.4
90°	35.5	35.0	34.5	34.0	33.4	32.6	31.6	30.5	29.5	28.4	25.0
92.5°	39.3	39.0	38.7	38.3	38.0	37.1	35.4	33.7	32.0	30.3	27.7
95°	45.0	45.0	45.0	45.0	45.0	44.0	42.2	40.4	38.6	36.7	33.8
97.5°	48.8	48.6	48.2	48.0	47.8	46.6	44.4	42.4	40.2	38.1	35.1
100°	49.7	49.5	49.2	49.0	48.7	47.5	45.4	43.3	41.2	39.1	36.2
102.5°	50.7	50.2	49.7	49.3	48.8	51.8	58.4	64.9	71.4	78.0	122.8
105°	52.1	51.6	51.1	50.5	50.0	73.0	119.6	166.2	212.8	259.4	283.0
107.5°	163.7	198.8	233.9	269.0	304.1	338.7	372.9	407.0	441.2	475.4	471.7
110°	325.7	363.3	400.9	438.6	476.2	499.4	508.0	516.7	525.5	534.1	531.2



TEST NUMBER: P332426-927

CATALOG NUMBER: S123RDIW-S560D1535U927-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	558.7	566.7	574.6	582.6	590.6	594.5	594.3	594.1	594.0	593.8	590.9
115°	696.4	695.3	694.3	693.2	692.1	690.3	687.7	685.1	682.4	679.8	677.4
117.5°	773.6	773.4	773.2	772.9	772.8	771.6	769.4	767.4	765.2	763.2	761.9
120°	826.6	826.6	826.6	826.6	826.6	825.6	823.5	821.4	819.3	817.1	816.3
122.5°	878.8	878.5	878.3	878.1	877.9	877.1	875.6	874.1	872.7	871.2	870.1
125°	952.2	951.6	951.1	950.6	950.1	949.5	949.0	948.5	948.0	947.5	946.4
127.5°	1022.8	1023.3	1023.8	1024.4	1024.8	1024.7	1023.9	1023.0	1022.2	1021.4	1020.1
130°	1068.3	1068.7	1069.3	1069.8	1070.3	1070.1	1069.1	1067.9	1066.9	1065.9	1064.9
132.5°	1109.9	1110.6	1111.4	1112.1	1112.9	1112.7	1111.7	1110.6	1109.5	1108.5	1107.6
135°	1173.6	1174.4	1175.2	1176.0	1176.8	1176.8	1176.0	1175.2	1174.4	1173.6	1172.6
137.5°	1233.6	1234.1	1234.6	1235.2	1235.6	1235.3	1234.1	1232.8	1231.5	1230.3	1229.7
140°	1269.6	1270.1	1270.7	1271.1	1271.7	1271.4	1270.3	1269.3	1268.3	1267.2	1266.4
142.5°	1302.7	1303.5	1304.2	1305.0	1305.7	1305.6	1304.8	1303.9	1303.1	1302.3	1301.5
145°	1353.7	1353.7	1353.7	1353.7	1353.7	1353.4	1352.9	1352.3	1351.8	1351.3	1350.8
147.5°	1391.5	1392.7	1394.0	1395.2	1396.4	1396.8	1396.2	1395.7	1395.2	1394.6	1394.1
150°	1420.0	1420.8	1421.6	1422.4	1423.2	1423.2	1422.8	1422.2	1421.7	1421.2	1420.6
152.5°	1442.7	1443.9	1445.1	1446.4	1447.6	1447.7	1446.8	1445.8	1444.9	1443.9	1443.6
155°	1474.5	1476.0	1477.6	1479.2	1480.7	1480.9	1479.6	1478.3	1476.9	1475.6	1475.4
157.5°	1501.2	1503.2	1505.3	1507.4	1509.4	1509.7	1508.1	1506.5	1504.9	1503.3	1503.6
160°	1518.3	1520.1	1521.9	1523.8	1525.7	1525.7	1524.2	1522.7	1521.1	1519.5	1519.7
162.5°	1534.4	1536.0	1537.6	1539.3	1540.9	1540.8	1539.1	1537.2	1535.5	1533.7	1533.9
165°	1553.8	1555.6	1557.5	1559.3	1561.2	1561.1	1558.9	1556.8	1554.7	1552.6	1552.9
167.5°	1567.8	1569.9	1572.0	1574.1	1576.2	1576.2	1574.1	1572.0	1569.9	1567.8	1567.8
170°	1576.3	1578.4	1580.5	1582.6	1584.8	1584.8	1582.6	1580.5	1578.4	1576.3	1576.3
172.5°	1581.0	1583.3	1585.7	1588.0	1590.3	1590.4	1588.3	1586.2	1584.1	1582.0	1581.8
175°	1588.2	1590.2	1592.4	1594.4	1596.6	1596.7	1594.8	1593.0	1591.2	1589.4	1589.0
177.5°	1590.3	1592.4	1594.5	1596.6	1598.7	1598.9	1597.2	1595.5	1593.9	1592.2	1592.0
180°	1594.0	1594.0	1594.0	1594.0	1594.0	1594.0	1594.0	1594.0	1594.0	1594.0	1594.0



TEST NUMBER: P332426-927

CATALOG NUMBER: S123RDIW-S560D1535U927-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	708.8	708.8	708.8	708.8	708.8	708.8	708.8	708.8	708.8	708.8	708.8
2.5°	731.8	731.1	727.7	723.8	718.7	715.3	712.6	711.2	706.9	701.5	697.8
5°	777.1	767.9	758.3	746.4	735.5	724.3	717.3	709.1	699.1	687.9	679.9
7.5°	825.5	807.6	788.4	768.6	748.9	731.3	715.8	702.5	686.6	670.5	659.2
10°	862.6	836.5	809.5	781.9	756.7	733.1	714.9	697.0	677.9	659.3	645.4
12.5°	896.4	862.1	830.9	796.9	764.8	736.5	710.3	689.2	666.2	646.5	630.6
15°	939.1	903.9	866.3	814.7	771.9	736.1	704.3	676.6	648.7	624.5	609.0
17.5°	979.0	926.1	875.5	832.4	776.9	732.1	693.2	660.2	629.6	603.9	584.8
20°	995.5	944.3	889.3	834.4	779.8	729.8	684.5	648.1	616.2	587.1	569.5
22.5°	1005.4	947.4	889.5	830.5	772.5	720.5	675.8	635.7	601.2	573.5	551.8
25°	1017.1	947.8	884.2	825.9	766.8	710.3	657.2	614.7	577.4	548.0	524.9
27.5°	1024.7	943.3	868.0	803.3	743.2	687.1	638.4	593.3	555.5	524.3	499.6
30°	1026.2	939.7	855.6	785.5	724.5	673.0	621.4	578.3	538.3	505.2	482.1
32.5°	1028.1	930.7	838.9	764.5	702.0	650.9	604.2	563.0	522.0	489.4	465.9
35°	1020.1	925.7	813.5	727.9	665.4	615.9	573.8	535.8	495.5	463.9	440.0
37.5°	985.6	906.0	787.1	686.7	621.4	575.6	541.2	508.2	471.2	437.1	414.5
40°	950.9	886.6	766.8	661.8	593.5	546.4	515.5	488.5	452.7	420.8	396.6
42.5°	899.2	860.2	747.3	635.6	561.9	516.6	490.5	465.2	433.8	401.4	378.6
45°	804.4	809.5	707.6	593.8	518.2	472.7	448.1	430.6	402.7	376.0	352.6
47.5°	685.4	733.6	660.9	549.3	472.2	429.4	408.0	392.6	373.8	347.6	326.3
50°	607.8	676.6	623.5	519.4	443.3	400.8	379.6	367.2	350.8	330.1	309.8
52.5°	536.1	610.1	578.4	486.2	412.0	373.1	352.4	342.1	329.2	309.7	291.4
55°	437.2	512.1	504.9	436.0	365.0	330.1	314.3	302.9	294.0	279.5	264.9
57.5°	353.6	424.7	428.5	380.2	323.6	289.1	275.6	266.9	261.1	250.2	236.7
60°	301.0	366.2	379.0	342.5	294.0	263.6	250.3	243.4	238.8	230.0	219.7
62.5°	257.3	312.8	327.3	301.0	265.6	237.2	226.8	220.1	217.0	209.4	200.3
65°	196.9	243.0	257.0	242.4	223.9	201.1	192.7	186.9	184.2	179.9	173.3
67.5°	148.1	181.7	197.0	186.7	180.1	165.6	160.3	157.2	154.7	151.9	146.2
70°	118.9	143.9	159.6	156.9	151.4	143.9	139.9	137.8	135.3	132.9	128.0
72.5°	95.6	112.7	127.5	129.0	124.5	122.9	119.5	118.6	117.1	114.2	111.5
75°	63.5	75.3	85.6	89.5	91.3	92.8	91.3	91.0	90.7	88.3	86.7
77.5°	41.6	47.9	54.4	61.2	64.0	66.1	66.5	67.7	66.9	65.6	64.9
80°	31.8	33.4	37.9	43.7	48.2	50.1	51.3	51.9	51.6	51.3	50.1
82.5°	23.1	24.4	26.5	30.6	34.4	37.5	38.2	38.0	38.7	38.9	37.9
85°	12.4	12.8	13.4	13.9	16.1	19.4	20.4	20.9	21.5	21.5	19.7
87.5°	8.2	7.3	7.1	6.5	6.7	6.4	7.3	8.0	8.8	8.3	8.9
90°	21.5	18.1	14.7	11.7	9.1	6.4	3.8	1.2	3.8	6.4	9.1
92.5°	25.2	22.6	20.0	19.1	19.8	20.5	21.3	22.0	21.3	20.5	19.8
95°	30.9	28.0	25.1	29.1	39.8	50.7	61.5	72.2	61.5	50.7	39.8
97.5°	76.0	95.0	113.9	125.8	130.6	135.5	140.4	145.2	140.4	135.5	130.6
100°	121.2	162.2	203.3	221.2	215.9	210.6	205.4	200.2	205.4	210.6	215.9
102.5°	167.6	212.5	257.3	277.8	274.0	270.3	266.5	262.7	266.5	270.3	274.0
105°	306.7	330.4	354.1	364.5	361.6	358.7	355.8	352.9	355.8	358.7	361.6
107.5°	467.9	464.1	460.4	457.4	455.1	452.7	450.4	448.1	450.4	452.7	455.1
110°	528.3	525.5	522.5	520.1	517.9	515.8	513.7	511.6	513.7	515.8	517.9





TEST NUMBER: P332426-927

CATALOG NUMBER: S123RDIW-S560D1535U927-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	588.0	585.1	582.3	579.8	578.0	576.1	574.2	572.3	574.2	576.1	578.0
115°	675.0	672.7	670.3	668.4	666.8	665.2	663.6	662.0	663.6	665.2	666.8
117.5°	760.7	759.5	758.4	756.8	754.8	752.8	750.9	748.9	750.9	752.8	754.8
120°	815.6	814.8	814.0	812.5	810.1	807.7	805.3	803.0	805.3	807.7	810.1
122.5°	869.2	868.2	867.2	865.7	863.7	861.8	859.8	857.9	859.8	861.8	863.7
125°	945.3	944.3	943.3	941.7	939.5	937.5	935.3	933.2	935.3	937.5	939.5
127.5°	1018.8	1017.6	1016.3	1014.6	1012.5	1010.4	1008.3	1006.2	1008.3	1010.4	1012.5
130°	1063.7	1062.7	1061.7	1060.1	1058.0	1055.9	1053.8	1051.6	1053.8	1055.9	1058.0
132.5°	1106.8	1106.0	1105.2	1103.7	1101.5	1099.5	1097.3	1095.3	1097.3	1099.5	1101.5
135°	1171.6	1170.4	1169.4	1168.2	1166.6	1165.0	1163.4	1161.8	1163.4	1165.0	1166.6
137.5°	1229.1	1228.5	1228.0	1226.6	1224.6	1222.7	1220.7	1218.6	1220.7	1222.7	1224.6
140°	1265.6	1264.8	1264.0	1262.9	1261.3	1259.7	1258.1	1256.6	1258.1	1259.7	1261.3
142.5°	1300.7	1299.9	1299.1	1297.9	1296.3	1294.7	1293.2	1291.6	1293.2	1294.7	1296.3
145°	1350.2	1349.7	1349.2	1348.0	1346.2	1344.3	1342.4	1340.6	1342.4	1344.3	1346.2
147.5°	1393.6	1393.1	1392.5	1391.6	1390.4	1389.3	1388.1	1386.8	1388.1	1389.3	1390.4
150°	1420.1	1419.6	1419.0	1418.4	1417.6	1416.8	1416.0	1415.2	1416.0	1416.8	1417.6
152.5°	1443.3	1443.0	1442.6	1442.3	1441.9	1441.5	1441.2	1440.8	1441.2	1441.5	1441.9
155°	1475.1	1474.9	1474.6	1474.7	1475.3	1475.8	1476.3	1476.8	1476.3	1475.8	1475.3
157.5°	1503.9	1504.1	1504.4	1504.6	1504.6	1504.7	1504.8	1504.8	1504.8	1504.7	1504.6
160°	1520.0	1520.3	1520.5	1520.8	1521.1	1521.3	1521.5	1521.9	1521.5	1521.3	1521.1
162.5°	1534.2	1534.5	1534.7	1535.2	1535.9	1536.6	1537.2	1537.9	1537.2	1536.6	1535.9
165°	1553.2	1553.4	1553.7	1554.2	1555.0	1555.8	1556.6	1557.4	1556.6	1555.8	1555.0
167.5°	1567.8	1567.8	1567.8	1568.3	1569.4	1570.4	1571.5	1572.5	1571.5	1570.4	1569.4
170°	1576.3	1576.3	1576.3	1576.8	1577.9	1578.9	1580.0	1581.0	1580.0	1578.9	1577.9
172.5°	1581.6	1581.4	1581.1	1581.7	1582.9	1584.2	1585.5	1586.7	1585.5	1584.2	1582.9
175°	1588.8	1588.6	1588.2	1588.8	1590.1	1591.4	1592.8	1594.0	1592.8	1591.4	1590.1
177.5°	1591.7	1591.6	1591.3	1591.7	1592.8	1593.9	1594.9	1595.9	1594.9	1593.9	1592.8
180°	1594.0	1594.0	1594.0	1594.0	1594.0	1594.0	1594.0	1594.0	1594.0	1594.0	1594.0



TEST NUMBER: P332426-927

CATALOG NUMBER: S123RDIW-S560D1535U927-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	708.8	708.8	708.8	708.8	708.8	708.8	708.8	708.8	708.8	708.8	708.8
2.5°	696.6	693.5	691.3	686.4	683.3	679.9	676.5	678.7	678.4	678.2	678.2
5°	673.3	666.3	660.0	651.7	646.6	640.2	635.3	634.8	636.0	631.7	629.3
7.5°	650.1	640.6	631.5	622.5	612.9	605.2	600.5	598.3	595.2	592.6	589.8
10°	633.8	622.7	613.8	602.6	592.3	583.2	577.4	573.5	571.3	569.2	565.3
12.5°	617.1	606.1	594.8	582.2	572.4	561.8	557.5	553.1	549.0	546.6	541.2
15°	592.6	578.3	566.5	553.1	542.2	531.9	525.9	517.1	515.8	512.8	507.3
17.5°	568.0	552.5	536.2	526.3	514.0	503.3	494.0	491.1	482.4	479.1	474.4
20°	548.6	534.3	521.9	508.8	490.9	480.9	473.6	469.7	462.7	458.4	455.4
22.5°	531.9	517.3	503.0	487.7	472.9	461.8	456.4	450.3	446.5	440.5	437.2
25°	507.9	492.2	474.8	458.4	447.8	439.3	430.9	425.4	419.9	417.2	411.1
27.5°	480.1	463.7	447.5	435.1	422.0	413.6	405.9	401.1	394.5	389.9	386.6
30°	464.9	445.4	431.5	420.3	403.5	395.7	389.9	383.8	379.0	374.1	370.7
32.5°	447.1	429.4	416.1	402.3	389.4	380.9	373.4	368.0	363.9	359.3	356.0
35°	419.3	404.5	390.8	376.8	367.4	358.6	349.8	345.3	341.4	337.1	334.1
37.5°	394.2	380.3	367.3	354.1	342.5	335.3	328.2	324.7	319.4	316.6	313.5
40°	378.7	365.0	351.1	338.3	326.1	320.8	314.3	309.2	304.4	302.2	298.9
42.5°	361.7	348.0	336.3	322.5	312.6	305.1	299.3	293.7	290.0	286.9	285.0
45°	336.5	324.3	312.8	299.2	289.8	283.4	276.7	271.6	268.2	266.1	262.8
47.5°	312.0	299.9	288.2	276.3	267.2	259.9	253.3	249.6	245.3	242.6	240.3
50°	294.3	283.4	270.9	260.0	251.0	243.7	238.2	233.6	229.7	226.3	224.8
52.5°	278.1	266.4	255.6	245.5	235.9	227.6	222.7	217.9	214.9	211.0	209.3
55°	251.2	240.0	230.9	220.9	211.5	204.5	198.4	194.2	191.2	186.9	184.5
57.5°	226.0	215.9	205.1	196.5	186.7	180.9	175.8	170.0	166.4	163.0	160.7
60°	209.1	197.5	188.1	179.9	171.4	163.8	159.3	154.7	150.8	147.4	145.4
62.5°	191.3	181.3	172.4	163.4	155.7	149.0	143.8	139.9	136.5	134.4	132.2
65°	164.1	156.3	147.2	139.9	132.6	127.8	123.5	120.2	117.7	116.2	114.4
67.5°	139.2	131.5	123.6	116.4	111.5	107.8	105.0	102.2	101.0	99.0	97.8
70°	122.9	115.0	108.1	102.6	97.7	95.0	93.2	91.0	89.8	87.4	86.2
72.5°	105.2	99.5	94.4	89.9	86.0	83.6	81.3	78.7	76.7	74.1	72.8
75°	82.9	77.7	73.8	70.7	68.3	65.0	61.6	58.9	58.0	57.0	56.7
77.5°	61.3	58.1	55.2	52.7	49.7	47.2	46.5	45.9	45.7	45.2	45.2
80°	48.2	45.2	43.1	40.1	38.3	38.3	38.3	37.6	37.9	37.9	37.9
82.5°	35.9	33.0	31.9	30.8	30.5	30.7	30.7	30.8	30.7	31.1	30.9
85°	18.5	18.8	19.4	19.1	19.4	19.4	20.0	19.7	20.0	19.4	20.0
87.5°	9.1	10.5	11.4	12.4	13.2	13.7	14.2	14.3	14.8	15.1	15.2
90°	11.7	14.7	18.1	21.5	25.0	28.4	29.5	30.5	31.6	32.6	33.4
92.5°	19.1	20.0	22.6	25.2	27.7	30.3	32.0	33.7	35.4	37.1	38.0
95°	29.1	25.1	28.0	30.9	33.8	36.7	38.6	40.4	42.2	44.0	45.0
97.5°	125.8	113.9	95.0	76.0	57.1	38.1	40.2	42.4	44.4	46.6	47.8
100°	221.2	203.3	162.2	121.2	80.2	39.1	41.2	43.3	45.4	47.5	48.7
102.5°	277.8	257.3	212.5	167.6	122.8	78.0	71.4	64.9	58.4	51.8	48.8
105°	364.5	354.1	330.4	306.7	283.0	259.4	212.8	166.2	119.6	73.0	50.0
107.5°	457.4	460.4	464.1	467.9	471.7	475.4	441.2	407.0	372.9	338.7	304.1
110°	520.1	522.5	525.5	528.3	531.2	534.1	525.5	516.7	508.0	499.4	476.2



TEST NUMBER: P332426-927

CATALOG NUMBER: S123RDIW-S560D1535U927-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	579.8	582.3	585.1	588.0	590.9	593.8	594.0	594.1	594.3	594.5	590.6
115°	668.4	670.3	672.7	675.0	677.4	679.8	682.4	685.1	687.7	690.3	692.1
117.5°	756.8	758.4	759.5	760.7	761.9	763.2	765.2	767.4	769.4	771.6	772.8
120°	812.5	814.0	814.8	815.6	816.3	817.1	819.3	821.4	823.5	825.6	826.6
122.5°	865.7	867.2	868.2	869.2	870.1	871.2	872.7	874.1	875.6	877.1	877.9
125°	941.7	943.3	944.3	945.3	946.4	947.5	948.0	948.5	949.0	949.5	950.1
127.5°	1014.6	1016.3	1017.6	1018.8	1020.1	1021.4	1022.2	1023.0	1023.9	1024.7	1024.8
130°	1060.1	1061.7	1062.7	1063.7	1064.9	1065.9	1066.9	1067.9	1069.1	1070.1	1070.3
132.5°	1103.7	1105.2	1106.0	1106.8	1107.6	1108.5	1109.5	1110.6	1111.7	1112.7	1112.9
135°	1168.2	1169.4	1170.4	1171.6	1172.6	1173.6	1174.4	1175.2	1176.0	1176.8	1176.8
137.5°	1226.6	1228.0	1228.5	1229.1	1229.7	1230.3	1231.5	1232.8	1234.1	1235.3	1235.6
140°	1262.9	1264.0	1264.8	1265.6	1266.4	1267.2	1268.3	1269.3	1270.3	1271.4	1271.7
142.5°	1297.9	1299.1	1299.9	1300.7	1301.5	1302.3	1303.1	1303.9	1304.8	1305.6	1305.7
145°	1348.0	1349.2	1349.7	1350.2	1350.8	1351.3	1351.8	1352.3	1352.9	1353.4	1353.7
147.5°	1391.6	1392.5	1393.1	1393.6	1394.1	1394.6	1395.2	1395.7	1396.2	1396.8	1396.4
150°	1418.4	1419.0	1419.6	1420.1	1420.6	1421.2	1421.7	1422.2	1422.8	1423.2	1423.2
152.5°	1442.3	1442.6	1443.0	1443.3	1443.6	1443.9	1444.9	1445.8	1446.8	1447.7	1447.6
155°	1474.7	1474.6	1474.9	1475.1	1475.4	1475.6	1476.9	1478.3	1479.6	1480.9	1480.7
157.5°	1504.6	1504.4	1504.1	1503.9	1503.6	1503.3	1504.9	1506.5	1508.1	1509.7	1509.4
160°	1520.8	1520.5	1520.3	1520.0	1519.7	1519.5	1521.1	1522.7	1524.2	1525.7	1525.7
162.5°	1535.2	1534.7	1534.5	1534.2	1533.9	1533.7	1535.5	1537.2	1539.1	1540.8	1540.9
165°	1554.2	1553.7	1553.4	1553.2	1552.9	1552.6	1554.7	1556.8	1558.9	1561.1	1561.2
167.5°	1568.3	1567.8	1567.8	1567.8	1567.8	1567.8	1569.9	1572.0	1574.1	1576.2	1576.2
170°	1576.8	1576.3	1576.3	1576.3	1576.3	1576.3	1578.4	1580.5	1582.6	1584.8	1584.8
172.5°	1581.7	1581.1	1581.4	1581.6	1581.8	1582.0	1584.1	1586.2	1588.3	1590.4	1590.3
175°	1588.8	1588.2	1588.6	1588.8	1589.0	1589.4	1591.2	1593.0	1594.8	1596.7	1596.6
177.5°	1591.7	1591.3	1591.6	1591.7	1592.0	1592.2	1593.9	1595.5	1597.2	1598.9	1598.7
180°	1594.0	1594.0	1594.0	1594.0	1594.0	1594.0	1594.0	1594.0	1594.0	1594.0	1594.0

TEST NUMBER: P332426-927

CATALOG NUMBER: S123RDIW-S560D1535U927-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	708.8	708.8	708.8	708.8	708.8	708.8	708.8	708.8	708.8	708.8	708.8
2.5°	675.3	675.0	675.3	674.3	675.3	675.0	675.3	678.2	678.2	678.4	678.7
5°	628.4	628.0	627.2	624.5	627.2	628.0	628.4	629.3	631.7	636.0	634.8
7.5°	587.4	587.0	584.3	584.4	584.3	587.0	587.4	589.8	592.6	595.2	598.3
10°	563.2	563.5	559.8	557.7	559.8	563.5	563.2	565.3	569.2	571.3	573.5
12.5°	539.6	538.2	535.3	532.9	535.3	538.2	539.6	541.2	546.6	549.0	553.1
15°	508.5	505.5	498.2	498.8	498.2	505.5	508.5	507.3	512.8	515.8	517.1
17.5°	471.9	469.7	469.6	465.3	469.6	469.7	471.9	474.4	479.1	482.4	491.1
20°	450.6	449.1	449.6	445.4	449.6	449.1	450.6	455.4	458.4	462.7	469.7
22.5°	433.8	432.3	429.8	428.4	429.8	432.3	433.8	437.2	440.5	446.5	450.3
25°	409.3	406.9	404.5	406.0	404.5	406.9	409.3	411.1	417.2	419.9	425.4
27.5°	384.8	382.9	380.6	380.2	380.6	382.9	384.8	386.6	389.9	394.5	401.1
30°	369.2	367.4	366.2	364.7	366.2	367.4	369.2	370.7	374.1	379.0	383.8
32.5°	353.5	353.2	350.9	350.6	350.9	353.2	353.5	356.0	359.3	363.9	368.0
35°	332.9	331.1	330.4	330.7	330.4	331.1	332.9	334.1	337.1	341.4	345.3
37.5°	313.2	310.9	309.7	308.6	309.7	310.9	313.2	313.5	316.6	319.4	324.7
40°	299.2	296.8	296.1	295.6	296.1	296.8	299.2	298.9	302.2	304.4	309.2
42.5°	283.4	282.4	282.1	281.0	282.1	282.4	283.4	285.0	286.9	290.0	293.7
45°	261.8	261.6	259.8	260.3	259.8	261.6	261.8	262.8	266.1	268.2	271.6
47.5°	239.2	237.8	236.5	237.4	236.5	237.8	239.2	240.3	242.6	245.3	249.6
50°	223.6	223.0	220.3	220.9	220.3	223.0	223.6	224.8	226.3	229.7	233.6
52.5°	208.1	205.8	204.8	204.4	204.8	205.8	208.1	209.3	211.0	214.9	217.9
55°	182.4	179.6	178.4	177.8	178.4	179.6	182.4	184.5	186.9	191.2	194.2
57.5°	157.1	156.4	155.4	156.1	155.4	156.4	157.1	160.7	163.0	166.4	170.0
60°	142.3	142.3	142.3	142.0	142.3	142.3	142.3	145.4	147.4	150.8	154.7
62.5°	130.9	130.2	129.9	130.3	129.9	130.2	130.9	132.2	134.4	136.5	139.9
65°	113.4	113.2	111.9	111.7	111.9	113.2	113.4	114.4	116.2	117.7	120.2
67.5°	97.0	95.9	95.6	95.1	95.6	95.9	97.0	97.8	99.0	101.0	102.2
70°	84.7	84.1	82.2	82.5	82.2	84.1	84.7	86.2	87.4	89.8	91.0
72.5°	71.3	70.7	70.3	69.9	70.3	70.7	71.3	72.8	74.1	76.7	78.7
75°	56.4	56.2	55.8	57.0	55.8	56.2	56.4	56.7	57.0	58.0	58.9
77.5°	45.2	45.2	45.4	44.9	45.4	45.2	45.2	45.2	45.2	45.7	45.9
80°	37.9	37.9	37.6	37.6	37.6	37.9	37.9	37.9	37.9	37.9	37.6
82.5°	30.4	30.7	30.8	30.3	30.8	30.7	30.4	30.9	31.1	30.7	30.8
85°	20.0	19.7	20.4	20.0	20.4	19.7	20.0	20.0	19.4	20.0	19.7
87.5°	15.8	15.4	15.5	15.8	15.5	15.4	15.8	15.2	15.1	14.8	14.3
90°	34.0	34.5	35.0	35.5	35.0	34.5	34.0	33.4	32.6	31.6	30.5
92.5°	38.3	38.7	39.0	39.3	39.0	38.7	38.3	38.0	37.1	35.4	33.7
95°	45.0	45.0	45.0	45.0	45.0	45.0	45.0	45.0	44.0	42.2	40.4
97.5°	48.0	48.2	48.6	48.8	48.6	48.2	48.0	47.8	46.6	44.4	42.4
100°	49.0	49.2	49.5	49.7	49.5	49.2	49.0	48.7	47.5	45.4	43.3
102.5°	49.3	49.7	50.2	50.7	50.2	49.7	49.3	48.8	51.8	58.4	64.9
105°	50.5	51.1	51.6	52.1	51.6	51.1	50.5	50.0	73.0	119.6	166.2
107.5°	269.0	233.9	198.8	163.7	198.8	233.9	269.0	304.1	338.7	372.9	407.0
110°	438.6	400.9	363.3	325.7	363.3	400.9	438.6	476.2	499.4	508.0	516.7



TEST NUMBER: P332426-927

CATALOG NUMBER: S123RDIW-S560D1535U927-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	582.6	574.6	566.7	558.7	566.7	574.6	582.6	590.6	594.5	594.3	594.1
115°	693.2	694.3	695.3	696.4	695.3	694.3	693.2	692.1	690.3	687.7	685.1
117.5°	772.9	773.2	773.4	773.6	773.4	773.2	772.9	772.8	771.6	769.4	767.4
120°	826.6	826.6	826.6	826.6	826.6	826.6	826.6	826.6	825.6	823.5	821.4
122.5°	878.1	878.3	878.5	878.8	878.5	878.3	878.1	877.9	877.1	875.6	874.1
125°	950.6	951.1	951.6	952.2	951.6	951.1	950.6	950.1	949.5	949.0	948.5
127.5°	1024.4	1023.8	1023.3	1022.8	1023.3	1023.8	1024.4	1024.8	1024.7	1023.9	1023.0
130°	1069.8	1069.3	1068.7	1068.3	1068.7	1069.3	1069.8	1070.3	1070.1	1069.1	1067.9
132.5°	1112.1	1111.4	1110.6	1109.9	1110.6	1111.4	1112.1	1112.9	1112.7	1111.7	1110.6
135°	1176.0	1175.2	1174.4	1173.6	1174.4	1175.2	1176.0	1176.8	1176.8	1176.0	1175.2
137.5°	1235.2	1234.6	1234.1	1233.6	1234.1	1234.6	1235.2	1235.6	1235.3	1234.1	1232.8
140°	1271.1	1270.7	1270.1	1269.6	1270.1	1270.7	1271.1	1271.7	1271.4	1270.3	1269.3
142.5°	1305.0	1304.2	1303.5	1302.7	1303.5	1304.2	1305.0	1305.7	1305.6	1304.8	1303.9
145°	1353.7	1353.7	1353.7	1353.7	1353.7	1353.7	1353.7	1353.7	1353.4	1352.9	1352.3
147.5°	1395.2	1394.0	1392.7	1391.5	1392.7	1394.0	1395.2	1396.4	1396.8	1396.2	1395.7
150°	1422.4	1421.6	1420.8	1420.0	1420.8	1421.6	1422.4	1423.2	1423.2	1422.8	1422.2
152.5°	1446.4	1445.1	1443.9	1442.7	1443.9	1445.1	1446.4	1447.6	1447.7	1446.8	1445.8
155°	1479.2	1477.6	1476.0	1474.5	1476.0	1477.6	1479.2	1480.7	1480.9	1479.6	1478.3
157.5°	1507.4	1505.3	1503.2	1501.2	1503.2	1505.3	1507.4	1509.4	1509.7	1508.1	1506.5
160°	1523.8	1521.9	1520.1	1518.3	1520.1	1521.9	1523.8	1525.7	1525.7	1524.2	1522.7
162.5°	1539.3	1537.6	1536.0	1534.4	1536.0	1537.6	1539.3	1540.9	1540.8	1539.1	1537.2
165°	1559.3	1557.5	1555.6	1553.8	1555.6	1557.5	1559.3	1561.2	1561.1	1558.9	1556.8
167.5°	1574.1	1572.0	1569.9	1567.8	1569.9	1572.0	1574.1	1576.2	1576.2	1574.1	1572.0
170°	1582.6	1580.5	1578.4	1576.3	1578.4	1580.5	1582.6	1584.8	1584.8	1582.6	1580.5
172.5°	1588.0	1585.7	1583.3	1581.0	1583.3	1585.7	1588.0	1590.3	1590.4	1588.3	1586.2
175°	1594.4	1592.4	1590.2	1588.2	1590.2	1592.4	1594.4	1596.6	1596.7	1594.8	1593.0
177.5°	1596.6	1594.5	1592.4	1590.3	1592.4	1594.5	1596.6	1598.7	1598.9	1597.2	1595.5
180°	1594.0	1594.0	1594.0	1594.0	1594.0	1594.0	1594.0	1594.0	1594.0	1594.0	1594.0



TEST NUMBER: P332426-927

CATALOG NUMBER: S123RDIW-S560D1535U927-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	708.8	708.8	708.8	708.8	708.8	708.8	708.8	708.8	708.8	708.8	708.8
2.5°	676.5	679.9	683.3	686.4	691.3	693.5	696.6	697.8	701.5	706.9	711.2
5°	635.3	640.2	646.6	651.7	660.0	666.3	673.3	679.9	687.9	699.1	709.1
7.5°	600.5	605.2	612.9	622.5	631.5	640.6	650.1	659.2	670.5	686.6	702.5
10°	577.4	583.2	592.3	602.6	613.8	622.7	633.8	645.4	659.3	677.9	697.0
12.5°	557.5	561.8	572.4	582.2	594.8	606.1	617.1	630.6	646.5	666.2	689.2
15°	525.9	531.9	542.2	553.1	566.5	578.3	592.6	609.0	624.5	648.7	676.6
17.5°	494.0	503.3	514.0	526.3	536.2	552.5	568.0	584.8	603.9	629.6	660.2
20°	473.6	480.9	490.9	508.8	521.9	534.3	548.6	569.5	587.1	616.2	648.1
22.5°	456.4	461.8	472.9	487.7	503.0	517.3	531.9	551.8	573.5	601.2	635.7
25°	430.9	439.3	447.8	458.4	474.8	492.2	507.9	524.9	548.0	577.4	614.7
27.5°	405.9	413.6	422.0	435.1	447.5	463.7	480.1	499.6	524.3	555.5	593.3
30°	389.9	395.7	403.5	420.3	431.5	445.4	464.9	482.1	505.2	538.3	578.3
32.5°	373.4	380.9	389.4	402.3	416.1	429.4	447.1	465.9	489.4	522.0	563.0
35°	349.8	358.6	367.4	376.8	390.8	404.5	419.3	440.0	463.9	495.5	535.8
37.5°	328.2	335.3	342.5	354.1	367.3	380.3	394.2	414.5	437.1	471.2	508.2
40°	314.3	320.8	326.1	338.3	351.1	365.0	378.7	396.6	420.8	452.7	488.5
42.5°	299.3	305.1	312.6	322.5	336.3	348.0	361.7	378.6	401.4	433.8	465.2
45°	276.7	283.4	289.8	299.2	312.8	324.3	336.5	352.6	376.0	402.7	430.6
47.5°	253.3	259.9	267.2	276.3	288.2	299.9	312.0	326.3	347.6	373.8	392.6
50°	238.2	243.7	251.0	260.0	270.9	283.4	294.3	309.8	330.1	350.8	367.2
52.5°	222.7	227.6	235.9	245.5	255.6	266.4	278.1	291.4	309.7	329.2	342.1
55°	198.4	204.5	211.5	220.9	230.9	240.0	251.2	264.9	279.5	294.0	302.9
57.5°	175.8	180.9	186.7	196.5	205.1	215.9	226.0	236.7	250.2	261.1	266.9
60°	159.3	163.8	171.4	179.9	188.1	197.5	209.1	219.7	230.0	238.8	243.4
62.5°	143.8	149.0	155.7	163.4	172.4	181.3	191.3	200.3	209.4	217.0	220.1
65°	123.5	127.8	132.6	139.9	147.2	156.3	164.1	173.3	179.9	184.2	186.9
67.5°	105.0	107.8	111.5	116.4	123.6	131.5	139.2	146.2	151.9	154.7	157.2
70°	93.2	95.0	97.7	102.6	108.1	115.0	122.9	128.0	132.9	135.3	137.8
72.5°	81.3	83.6	86.0	89.9	94.4	99.5	105.2	111.5	114.2	117.1	118.6
75°	61.6	65.0	68.3	70.7	73.8	77.7	82.9	86.7	88.3	90.7	91.0
77.5°	46.5	47.2	49.7	52.7	55.2	58.1	61.3	64.9	65.6	66.9	67.7
80°	38.3	38.3	38.3	40.1	43.1	45.2	48.2	50.1	51.3	51.6	51.9
82.5°	30.7	30.7	30.5	30.8	31.9	33.0	35.9	37.9	38.9	38.7	38.0
85°	20.0	19.4	19.4	19.1	19.4	18.8	18.5	19.7	21.5	21.5	20.9
87.5°	14.2	13.7	13.2	12.4	11.4	10.5	9.1	8.9	8.3	8.8	8.0
90°	29.5	28.4	25.0	21.5	18.1	14.7	11.7	9.1	6.4	3.8	1.2
92.5°	32.0	30.3	27.7	25.2	22.6	20.0	19.1	19.8	20.5	21.3	22.0
95°	38.6	36.7	33.8	30.9	28.0	25.1	29.1	39.8	50.7	61.5	72.2
97.5°	40.2	38.1	57.1	76.0	95.0	113.9	125.8	130.6	135.5	140.4	145.2
100°	41.2	39.1	80.2	121.2	162.2	203.3	221.2	215.9	210.6	205.4	200.2
102.5°	71.4	78.0	122.8	167.6	212.5	257.3	277.8	274.0	270.3	266.5	262.7
105°	212.8	259.4	283.0	306.7	330.4	354.1	364.5	361.6	358.7	355.8	352.9
107.5°	441.2	475.4	471.7	467.9	464.1	460.4	457.4	455.1	452.7	450.4	448.1
110°	525.5	534.1	531.2	528.3	525.5	522.5	520.1	517.9	515.8	513.7	511.6



TEST NUMBER: P332426-927

CATALOG NUMBER: S123RDIW-S560D1535U927-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	594.0	593.8	590.9	588.0	585.1	582.3	579.8	578.0	576.1	574.2	572.3
115°	682.4	679.8	677.4	675.0	672.7	670.3	668.4	666.8	665.2	663.6	662.0
117.5°	765.2	763.2	761.9	760.7	759.5	758.4	756.8	754.8	752.8	750.9	748.9
120°	819.3	817.1	816.3	815.6	814.8	814.0	812.5	810.1	807.7	805.3	803.0
122.5°	872.7	871.2	870.1	869.2	868.2	867.2	865.7	863.7	861.8	859.8	857.9
125°	948.0	947.5	946.4	945.3	944.3	943.3	941.7	939.5	937.5	935.3	933.2
127.5°	1022.2	1021.4	1020.1	1018.8	1017.6	1016.3	1014.6	1012.5	1010.4	1008.3	1006.2
130°	1066.9	1065.9	1064.9	1063.7	1062.7	1061.7	1060.1	1058.0	1055.9	1053.8	1051.6
132.5°	1109.5	1108.5	1107.6	1106.8	1106.0	1105.2	1103.7	1101.5	1099.5	1097.3	1095.3
135°	1174.4	1173.6	1172.6	1171.6	1170.4	1169.4	1168.2	1166.6	1165.0	1163.4	1161.8
137.5°	1231.5	1230.3	1229.7	1229.1	1228.5	1228.0	1226.6	1224.6	1222.7	1220.7	1218.6
140°	1268.3	1267.2	1266.4	1265.6	1264.8	1264.0	1262.9	1261.3	1259.7	1258.1	1256.6
142.5°	1303.1	1302.3	1301.5	1300.7	1299.9	1299.1	1297.9	1296.3	1294.7	1293.2	1291.6
145°	1351.8	1351.3	1350.8	1350.2	1349.7	1349.2	1348.0	1346.2	1344.3	1342.4	1340.6
147.5°	1395.2	1394.6	1394.1	1393.6	1393.1	1392.5	1391.6	1390.4	1389.3	1388.1	1386.8
150°	1421.7	1421.2	1420.6	1420.1	1419.6	1419.0	1418.4	1417.6	1416.8	1416.0	1415.2
152.5°	1444.9	1443.9	1443.6	1443.3	1443.0	1442.6	1442.3	1441.9	1441.5	1441.2	1440.8
155°	1476.9	1475.6	1475.4	1475.1	1474.9	1474.6	1474.7	1475.3	1475.8	1476.3	1476.8
157.5°	1504.9	1503.3	1503.6	1503.9	1504.1	1504.4	1504.6	1504.6	1504.7	1504.8	1504.8
160°	1521.1	1519.5	1519.7	1520.0	1520.3	1520.5	1520.8	1521.1	1521.3	1521.5	1521.9
162.5°	1535.5	1533.7	1533.9	1534.2	1534.5	1534.7	1535.2	1535.9	1536.6	1537.2	1537.9
165°	1554.7	1552.6	1552.9	1553.2	1553.4	1553.7	1554.2	1555.0	1555.8	1556.6	1557.4
167.5°	1569.9	1567.8	1567.8	1567.8	1567.8	1567.8	1568.3	1569.4	1570.4	1571.5	1572.5
170°	1578.4	1576.3	1576.3	1576.3	1576.3	1576.3	1576.8	1577.9	1578.9	1580.0	1581.0
172.5°	1584.1	1582.0	1581.8	1581.6	1581.4	1581.1	1581.7	1582.9	1584.2	1585.5	1586.7
175°	1591.2	1589.4	1589.0	1588.8	1588.6	1588.2	1588.8	1590.1	1591.4	1592.8	1594.0
177.5°	1593.9	1592.2	1592.0	1591.7	1591.6	1591.3	1591.7	1592.8	1593.9	1594.9	1595.9
180°	1594.0	1594.0	1594.0	1594.0	1594.0	1594.0	1594.0	1594.0	1594.0	1594.0	1594.0



TEST NUMBER: P332426-927

CATALOG NUMBER: S123RDIW-S560D1535U927-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	708.8	708.8	708.8	708.8	708.8	708.8	708.8	708.8	708.8	708.8	708.8
2.5°	712.6	715.3	718.7	723.8	727.7	731.1	731.8	732.8	735.2	739.3	742.5
5°	717.3	724.3	735.5	746.4	758.3	767.9	777.1	783.5	789.5	802.2	812.5
7.5°	715.8	731.3	748.9	768.6	788.4	807.6	825.5	841.5	857.4	875.9	897.1
10°	714.9	733.1	756.7	781.9	809.5	836.5	862.6	883.0	906.7	927.9	954.9
12.5°	710.3	736.5	764.8	796.9	830.9	862.1	896.4	924.5	951.5	982.2	1013.6
15°	704.3	736.1	771.9	814.7	866.3	903.9	939.1	987.9	1021.3	1054.7	1099.6
17.5°	693.2	732.1	776.9	832.4	875.5	926.1	979.0	1017.6	1062.6	1109.6	1150.2
20°	684.5	729.8	779.8	834.4	889.3	944.3	995.5	1041.6	1088.1	1142.4	1175.8
22.5°	675.8	720.5	772.5	830.5	889.5	947.4	1005.4	1059.6	1111.8	1166.6	1209.3
25°	657.2	710.3	766.8	825.9	884.2	947.8	1017.1	1077.4	1142.1	1198.5	1238.9
27.5°	638.4	687.1	743.2	803.3	868.0	943.3	1024.7	1093.4	1158.1	1198.5	1211.2
30°	621.4	673.0	724.5	785.5	855.6	939.7	1026.2	1104.8	1157.9	1175.4	1162.4
32.5°	604.2	650.9	702.0	764.5	838.9	930.7	1028.1	1098.0	1130.0	1116.5	1063.3
35°	573.8	615.9	665.4	727.9	813.5	925.7	1020.1	1067.5	1059.5	983.7	883.5
37.5°	541.2	575.6	621.4	686.7	787.1	906.0	985.6	992.6	924.3	807.9	692.2
40°	515.5	546.4	593.5	661.8	766.8	886.6	950.9	922.7	816.8	687.2	590.7
42.5°	490.5	516.6	561.9	635.6	747.3	860.2	899.2	837.7	715.6	593.0	505.3
45°	448.1	472.7	518.2	593.8	707.6	809.5	804.4	697.6	575.3	476.7	403.9
47.5°	408.0	429.4	472.2	549.3	660.9	733.6	685.4	571.8	468.0	389.0	337.0
50°	379.6	400.8	443.3	519.4	623.5	676.6	607.8	498.2	403.2	337.7	296.4
52.5°	352.4	373.1	412.0	486.2	578.4	610.1	536.1	434.6	355.5	298.9	263.4
55°	314.3	330.1	365.0	436.0	504.9	512.1	437.2	352.3	287.0	247.6	223.3
57.5°	275.6	289.1	323.6	380.2	428.5	424.7	353.6	280.2	236.2	206.9	189.3
60°	250.3	263.6	294.0	342.5	379.0	366.2	301.0	241.9	204.2	182.7	168.7
62.5°	226.8	237.2	265.6	301.0	327.3	312.8	257.3	208.3	178.5	160.3	149.2
65°	192.7	201.1	223.9	242.4	257.0	243.0	196.9	163.0	141.4	128.7	121.0
67.5°	160.3	165.6	180.1	186.7	197.0	181.7	148.1	125.3	113.0	102.3	97.0
70°	139.9	143.9	151.4	156.9	159.6	143.9	118.9	102.3	92.0	84.4	81.0
72.5°	119.5	122.9	124.5	129.0	127.5	112.7	95.6	82.4	74.9	69.8	65.5
75°	91.3	92.8	91.3	89.5	85.6	75.3	63.5	56.7	51.3	48.9	47.4
77.5°	66.5	66.1	64.0	61.2	54.4	47.9	41.6	39.3	37.0	35.6	35.2
80°	51.3	50.1	48.2	43.7	37.9	33.4	31.8	30.3	29.5	27.9	27.6
82.5°	38.2	37.5	34.4	30.6	26.5	24.4	23.1	22.6	21.6	20.9	20.8
85°	20.4	19.4	16.1	13.9	13.4	12.8	12.4	12.4	11.2	10.9	10.9
87.5°	7.3	6.4	6.7	6.5	7.1	7.3	8.2	8.4	8.9	9.3	9.0
90°	3.8	6.4	9.1	11.7	14.7	18.1	21.5	25.0	28.4	29.5	30.5
92.5°	21.3	20.5	19.8	19.1	20.0	22.6	25.2	27.7	30.3	32.0	33.7
95°	61.5	50.7	39.8	29.1	25.1	28.0	30.9	33.8	36.7	38.6	40.4
97.5°	140.4	135.5	130.6	125.8	113.9	95.0	76.0	57.1	38.1	40.2	42.4
100°	205.4	210.6	215.9	221.2	203.3	162.2	121.2	80.2	39.1	41.2	43.3
102.5°	266.5	270.3	274.0	277.8	257.3	212.5	167.6	122.8	78.0	71.4	64.9
105°	355.8	358.7	361.6	364.5	354.1	330.4	306.7	283.0	259.4	212.8	166.2
107.5°	450.4	452.7	455.1	457.4	460.4	464.1	467.9	471.7	475.4	441.2	407.0
110°	513.7	515.8	517.9	520.1	522.5	525.5	528.3	531.2	534.1	525.5	516.7





TEST NUMBER: P332426-927

CATALOG NUMBER: S123RDIW-S560D1535U927-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	574.2	576.1	578.0	579.8	582.3	585.1	588.0	590.9	593.8	594.0	594.1
115°	663.6	665.2	666.8	668.4	670.3	672.7	675.0	677.4	679.8	682.4	685.1
117.5°	750.9	752.8	754.8	756.8	758.4	759.5	760.7	761.9	763.2	765.2	767.4
120°	805.3	807.7	810.1	812.5	814.0	814.8	815.6	816.3	817.1	819.3	821.4
122.5°	859.8	861.8	863.7	865.7	867.2	868.2	869.2	870.1	871.2	872.7	874.1
125°	935.3	937.5	939.5	941.7	943.3	944.3	945.3	946.4	947.5	948.0	948.5
127.5°	1008.3	1010.4	1012.5	1014.6	1016.3	1017.6	1018.8	1020.1	1021.4	1022.2	1023.0
130°	1053.8	1055.9	1058.0	1060.1	1061.7	1062.7	1063.7	1064.9	1065.9	1066.9	1067.9
132.5°	1097.3	1099.5	1101.5	1103.7	1105.2	1106.0	1106.8	1107.6	1108.5	1109.5	1110.6
135°	1163.4	1165.0	1166.6	1168.2	1169.4	1170.4	1171.6	1172.6	1173.6	1174.4	1175.2
137.5°	1220.7	1222.7	1224.6	1226.6	1228.0	1228.5	1229.1	1229.7	1230.3	1231.5	1232.8
140°	1258.1	1259.7	1261.3	1262.9	1264.0	1264.8	1265.6	1266.4	1267.2	1268.3	1269.3
142.5°	1293.2	1294.7	1296.3	1297.9	1299.1	1299.9	1300.7	1301.5	1302.3	1303.1	1303.9
145°	1342.4	1344.3	1346.2	1348.0	1349.2	1349.7	1350.2	1350.8	1351.3	1351.8	1352.3
147.5°	1388.1	1389.3	1390.4	1391.6	1392.5	1393.1	1393.6	1394.1	1394.6	1395.2	1395.7
150°	1416.0	1416.8	1417.6	1418.4	1419.0	1419.6	1420.1	1420.6	1421.2	1421.7	1422.2
152.5°	1441.2	1441.5	1441.9	1442.3	1442.6	1443.0	1443.3	1443.6	1443.9	1444.9	1445.8
155°	1476.3	1475.8	1475.3	1474.7	1474.6	1474.9	1475.1	1475.4	1475.6	1476.9	1478.3
157.5°	1504.8	1504.7	1504.6	1504.6	1504.4	1504.1	1503.9	1503.6	1503.3	1504.9	1506.5
160°	1521.5	1521.3	1521.1	1520.8	1520.5	1520.3	1520.0	1519.7	1519.5	1521.1	1522.7
162.5°	1537.2	1536.6	1535.9	1535.2	1534.7	1534.5	1534.2	1533.9	1533.7	1535.5	1537.2
165°	1556.6	1555.8	1555.0	1554.2	1553.7	1553.4	1553.2	1552.9	1552.6	1554.7	1556.8
167.5°	1571.5	1570.4	1569.4	1568.3	1567.8	1567.8	1567.8	1567.8	1567.8	1569.9	1572.0
170°	1580.0	1578.9	1577.9	1576.8	1576.3	1576.3	1576.3	1576.3	1576.3	1578.4	1580.5
172.5°	1585.5	1584.2	1582.9	1581.7	1581.1	1581.4	1581.6	1581.8	1582.0	1584.1	1586.2
175°	1592.8	1591.4	1590.1	1588.8	1588.2	1588.6	1588.8	1589.0	1589.4	1591.2	1593.0
177.5°	1594.9	1593.9	1592.8	1591.7	1591.3	1591.6	1591.7	1592.0	1592.2	1593.9	1595.5
180°	1594.0	1594.0	1594.0	1594.0	1594.0	1594.0	1594.0	1594.0	1594.0	1594.0	1594.0



TEST NUMBER: P332426-927

CATALOG NUMBER: S123RDIW-S560D1535U927-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	708.8	708.8	708.8	708.8	708.8	708.8	708.8
2.5°	747.7	747.7	748.6	752.3	752.7	755.9	754.9
5°	821.7	827.4	829.6	838.7	844.1	846.5	841.7
7.5°	912.2	928.4	936.2	945.7	954.1	956.7	950.1
10°	978.3	995.2	1009.5	1018.3	1026.5	1031.9	1038.9
12.5°	1042.0	1063.0	1076.5	1088.9	1097.3	1104.3	1105.4
15°	1111.4	1143.0	1167.0	1184.6	1193.3	1197.9	1196.1
17.5°	1181.4	1210.6	1227.7	1245.6	1257.8	1258.5	1258.9
20°	1221.0	1249.5	1269.2	1282.5	1296.2	1295.6	1298.6
22.5°	1247.4	1269.9	1285.0	1294.7	1299.3	1297.0	1297.7
25°	1259.8	1266.5	1263.8	1248.2	1244.4	1230.1	1232.5
27.5°	1196.0	1164.4	1131.8	1089.7	1056.6	1030.2	1031.5
30°	1109.3	1053.4	989.8	936.4	888.4	875.0	846.5
32.5°	988.2	904.4	829.8	780.1	738.9	727.7	702.8
35°	782.8	701.5	624.7	578.6	560.4	535.0	534.6
37.5°	608.5	536.9	496.3	461.7	443.5	428.1	426.6
40°	511.9	456.1	425.4	400.5	382.6	371.1	368.4
42.5°	444.4	399.3	370.5	355.1	341.4	335.4	331.0
45°	362.9	332.6	312.5	298.6	292.2	287.6	285.2
47.5°	303.6	283.2	269.6	260.3	255.1	250.3	251.6
50°	271.2	254.6	244.5	235.8	231.8	228.5	228.8
52.5°	245.3	230.3	222.2	215.9	211.0	208.6	207.4
55°	208.2	198.8	190.5	186.0	183.2	179.9	179.0
57.5°	177.5	170.2	163.6	158.4	157.8	154.6	155.0
60°	157.2	151.1	145.6	142.9	140.8	138.1	138.9
62.5°	140.5	135.3	130.3	128.1	126.0	124.0	124.4
65°	115.0	110.1	107.1	105.9	105.0	104.1	103.1
67.5°	91.7	88.6	86.7	84.1	82.3	82.0	81.0
70°	77.1	73.1	69.8	66.5	65.5	65.2	65.5
72.5°	61.8	59.3	58.4	56.7	56.6	55.8	56.3
75°	46.4	45.6	44.9	43.7	43.7	43.7	43.7
77.5°	34.2	33.7	33.4	33.0	32.8	32.3	32.3
80°	26.7	26.4	25.8	25.8	25.5	25.8	25.5
82.5°	20.1	20.1	19.5	19.5	19.2	19.0	19.2
85°	10.3	10.0	10.6	10.0	10.3	9.7	10.3
87.5°	9.3	9.4	9.3	9.4	9.3	9.9	9.5
90°	31.6	32.6	33.4	34.0	34.5	35.0	35.5
92.5°	35.4	37.1	38.0	38.3	38.7	39.0	39.3
95°	42.2	44.0	45.0	45.0	45.0	45.0	45.0
97.5°	44.4	46.6	47.8	48.0	48.2	48.6	48.8
100°	45.4	47.5	48.7	49.0	49.2	49.5	49.7
102.5°	58.4	51.8	48.8	49.3	49.7	50.2	50.7
105°	119.6	73.0	50.0	50.5	51.1	51.6	52.1
107.5°	372.9	338.7	304.1	269.0	233.9	198.8	163.7
110°	508.0	499.4	476.2	438.6	400.9	363.3	325.7



TEST NUMBER: P332426-927

CATALOG NUMBER: S123RDIW-S560D1535U927-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	594.3	594.5	590.6	582.6	574.6	566.7	558.7
115°	687.7	690.3	692.1	693.2	694.3	695.3	696.4
117.5°	769.4	771.6	772.8	772.9	773.2	773.4	773.6
120°	823.5	825.6	826.6	826.6	826.6	826.6	826.6
122.5°	875.6	877.1	877.9	878.1	878.3	878.5	878.8
125°	949.0	949.5	950.1	950.6	951.1	951.6	952.2
127.5°	1023.9	1024.7	1024.8	1024.4	1023.8	1023.3	1022.8
130°	1069.1	1070.1	1070.3	1069.8	1069.3	1068.7	1068.3
132.5°	1111.7	1112.7	1112.9	1112.1	1111.4	1110.6	1109.9
135°	1176.0	1176.8	1176.8	1176.0	1175.2	1174.4	1173.6
137.5°	1234.1	1235.3	1235.6	1235.2	1234.6	1234.1	1233.6
140°	1270.3	1271.4	1271.7	1271.1	1270.7	1270.1	1269.6
142.5°	1304.8	1305.6	1305.7	1305.0	1304.2	1303.5	1302.7
145°	1352.9	1353.4	1353.7	1353.7	1353.7	1353.7	1353.7
147.5°	1396.2	1396.8	1396.4	1395.2	1394.0	1392.7	1391.5
150°	1422.8	1423.2	1423.2	1422.4	1421.6	1420.8	1420.0
152.5°	1446.8	1447.7	1447.6	1446.4	1445.1	1443.9	1442.7
155°	1479.6	1480.9	1480.7	1479.2	1477.6	1476.0	1474.5
157.5°	1508.1	1509.7	1509.4	1507.4	1505.3	1503.2	1501.2
160°	1524.2	1525.7	1525.7	1523.8	1521.9	1520.1	1518.3
162.5°	1539.1	1540.8	1540.9	1539.3	1537.6	1536.0	1534.4
165°	1558.9	1561.1	1561.2	1559.3	1557.5	1555.6	1553.8
167.5°	1574.1	1576.2	1576.2	1574.1	1572.0	1569.9	1567.8
170°	1582.6	1584.8	1584.8	1582.6	1580.5	1578.4	1576.3
172.5°	1588.3	1590.4	1590.3	1588.0	1585.7	1583.3	1581.0
175°	1594.8	1596.7	1596.6	1594.4	1592.4	1590.2	1588.2
177.5°	1597.2	1598.9	1598.7	1596.6	1594.5	1592.4	1590.3
180°	1594.0	1594.0	1594.0	1594.0	1594.0	1594.0	1594.0

(END OF REPORT)