

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331784-840

Luminaire Tested: **S122RDIW-S290D1440U840-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P331784-840  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-8,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S122RDIW-S290D1440U840-4F0-1E-UDD-F1  
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 290 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED  
HOUSING  
UPLIGHT 1440 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 6094.3 lumens  
Efficiency: N/A  
Efficacy: 114.1 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16  
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')  
CIE Type: Semi-Indirect


Input Watts (W): 53.4  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P331784-840

CATALOG NUMBER: S122RDIW-S290D1440U840-4F0-1E-UDD-F1

### Luminous Intensity Polar Plot





TEST NUMBER: P331784-840

CATALOG NUMBER: S122RDIW-S290D1440U840-4F0-1E-UDD-F1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	99	99	99	99	87	87	87	87	65	65	65	45	45	45	26	26	26	17
1	91	87	83	80	80	76	73	71	57	55	53	39	38	37	23	23	22	15
2	83	76	70	65	72	67	62	58	50	47	44	35	33	31	21	20	19	13
3	75	67	60	54	66	59	53	49	44	41	37	31	29	27	18	17	16	11
4	69	59	51	46	60	52	46	41	39	35	32	27	25	23	16	15	14	9
5	63	52	45	39	55	46	40	35	35	31	27	25	22	20	15	13	12	8
6	58	47	39	34	51	41	35	30	32	27	24	22	19	17	13	12	11	7
7	54	42	35	29	47	37	31	26	28	24	21	20	17	15	12	11	10	7
8	50	38	31	26	43	34	28	23	26	21	18	18	16	13	11	10	9	6
9	46	35	27	23	40	31	25	21	24	19	16	17	14	12	10	9	8	5
10	43	31	25	20	38	28	22	18	22	17	15	15	13	11	10	8	7	5

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	8186	8186	8186
5°	8217	8083	8126
10°	8153	7950	7883
15°	8058	7714	7492
20°	7930	7378	7009
25°	7798	6996	6538
30°	7612	6604	5936
35°	7433	6177	5409
40°	7253	5735	4795
45°	7040	5236	4242
50°	6822	4735	3697
55°	6598	4197	3178
60°	6339	3630	2638
65°	6044	3049	2399
70°	5698	2511	2209
75°	5265	2289	2059
80°	4649	2046	1878
85°	3649	1612	1612



TEST NUMBER: P331784-840

CATALOG NUMBER: S122RDIW-S290D1440U840-4F0-1E-UDD-F1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	47.4	0.8
10°-20°	130.3	2.1
20°-30°	183.0	3.0
30°-40°	199.5	3.3
40°-50°	183.4	3.0
50°-60°	144.1	2.4
60°-70°	93.9	1.5
70°-80°	48.4	0.8
80°-90°	19.8	0.3
90°-100°	114.3	1.9
100°-110°	355.0	5.8
110°-120°	606.9	10.0
120°-130°	798.1	13.1
130°-140°	895.8	14.7
140°-150°	878.3	14.4
150°-160°	736.7	12.1
160°-170°	488.6	8.0
170°-180°	170.8	2.8
0°-30°	360.7	5.9
0°-40°	560.2	9.2
0°-60°	887.7	14.6
0°-90°	1049.8	17.2
90°-120°	1076.2	17.7
90°-150°	3648.4	59.9
90°-180°	5045.0	82.8
0°-180°	6094.3	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	507	507	507	507	507	
5°	507	504	499	502	501	48
15°	482	476	462	453	448	136
25°	438	422	393	375	367	201
35°	377	353	313	285	274	236
45°	308	277	229	198	186	238
55°	234	198	149	123	113	209
65°	158	121	80	65	63	157
75°	84	53	37	34	33	89
85°	20	11	9	9	9	23
90°	2	21	53	50	52	5
95°	79	94	98	97	94	91
105°	327	332	335	338	338	346
115°	609	617	615	613	609	602
125°	886	899	895	891	889	791
135°	1146	1162	1166	1165	1160	885
145°	1392	1402	1411	1412	1407	869
155°	1591	1596	1600	1607	1603	732
165°	1731	1730	1730	1739	1732	488
175°	1801	1797	1793	1803	1795	171
180°	1804	1804	1804	1804	1804	



TEST NUMBER: P331784-840

CATALOG NUMBER: S122RDIW-S290D1440U840-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	507.0	507.0	507.0	507.0	507.0	507.0	507.0	507.0	507.0	507.0	507.0
2.5°	508.8	508.4	508.0	507.6	507.2	506.4	505.5	504.7	503.8	502.9	503.7
5°	507.0	506.4	505.9	505.4	504.9	503.9	502.6	501.3	500.0	498.7	499.6
7.5°	501.7	501.1	500.4	499.8	499.2	498.1	496.6	494.9	493.4	491.9	492.1
10°	497.3	496.6	495.8	495.1	494.4	493.0	491.0	489.0	487.0	484.9	484.6
12.5°	491.8	490.9	490.0	489.2	488.3	486.6	483.9	481.3	478.7	476.1	475.5
15°	482.1	481.0	479.9	478.8	477.7	475.3	471.9	468.5	464.9	461.5	459.6
17.5°	470.3	468.6	466.9	465.1	463.4	460.4	456.0	451.5	447.1	442.6	440.3
20°	461.5	459.5	457.5	455.3	453.3	449.8	444.6	439.6	434.5	429.4	426.9
22.5°	452.0	449.7	447.4	445.1	442.8	438.8	433.0	427.3	421.6	415.9	412.5
25°	437.7	434.3	431.1	427.9	424.6	419.6	412.8	406.2	399.4	392.7	388.5
27.5°	420.4	416.9	413.3	409.8	406.2	400.6	393.0	385.5	377.9	370.3	365.5
30°	408.3	404.5	400.5	396.7	392.8	386.8	378.6	370.5	362.3	354.2	349.0
32.5°	396.6	392.0	387.5	382.9	378.4	372.0	363.8	355.4	347.1	338.7	332.9
35°	377.1	371.9	366.7	361.5	356.3	349.2	340.2	331.2	322.3	313.4	306.9
37.5°	357.7	351.9	346.2	340.5	334.8	327.2	317.6	308.0	298.5	288.9	281.9
40°	344.1	338.0	331.8	325.7	319.6	311.6	301.7	291.9	282.0	272.1	264.8
42.5°	330.1	323.7	317.2	310.8	304.4	296.0	285.8	275.6	265.4	255.2	247.7
45°	308.3	301.4	294.6	287.8	280.9	272.2	261.5	250.7	240.0	229.3	222.2
47.5°	287.0	279.7	272.6	265.3	258.0	248.9	237.8	226.8	215.7	204.7	197.5
50°	271.6	264.4	257.1	249.8	242.7	233.4	222.2	211.0	199.8	188.5	181.5
52.5°	256.5	248.9	241.5	233.9	226.3	217.0	206.0	195.1	184.1	173.1	166.3
55°	234.4	226.5	218.5	210.6	202.6	193.2	182.1	171.1	160.1	149.1	143.0
57.5°	211.8	203.6	195.4	187.3	179.2	169.8	159.2	148.7	138.0	127.4	121.8
60°	196.3	188.2	180.1	171.9	163.7	154.4	143.9	133.4	122.9	112.4	107.1
62.5°	181.3	173.2	165.0	156.8	148.7	139.6	129.6	119.6	109.6	99.6	94.6
65°	158.2	150.0	141.8	133.5	125.2	116.5	107.3	98.2	89.0	79.8	76.3
67.5°	136.0	127.8	119.7	111.5	103.3	95.0	86.7	78.6	70.3	62.0	60.4
70°	120.7	112.7	104.7	96.8	88.9	81.4	74.3	67.3	60.3	53.2	52.2
72.5°	105.9	98.4	90.7	83.1	75.4	68.9	63.2	57.6	51.9	46.3	45.3
75°	84.4	77.3	70.2	63.0	55.8	50.6	47.1	43.6	40.2	36.7	36.0
77.5°	63.2	57.0	50.7	44.4	38.2	34.2	32.5	30.9	29.2	27.6	27.2
80°	50.0	44.8	39.6	34.4	29.2	26.1	25.0	24.0	23.0	22.0	21.6
82.5°	37.9	33.8	29.8	25.8	21.7	19.3	18.6	17.9	17.2	16.6	16.3
85°	19.7	17.6	15.5	13.3	11.2	9.9	9.6	9.3	9.0	8.7	8.7
87.5°	6.2	6.4	6.5	6.7	6.8	7.7	9.1	10.6	12.1	13.6	13.3
90°	1.5	5.6	9.6	13.7	17.8	23.5	31.0	38.4	45.8	53.3	52.6
92.5°	27.1	30.1	33.0	36.1	39.0	41.4	43.1	44.9	46.7	48.4	48.6
95°	79.2	82.5	85.9	89.3	92.7	94.7	95.4	96.0	96.7	97.5	97.5
97.5°	144.6	147.6	150.6	153.6	156.5	158.6	160.0	161.3	162.5	163.8	163.8
100°	193.4	196.0	198.7	201.5	204.2	206.0	207.0	208.0	209.0	210.1	210.1
102.5°	244.5	246.7	248.8	251.0	253.2	254.9	256.2	257.4	258.7	260.0	260.3
105°	327.3	328.3	329.3	330.3	331.3	332.2	333.0	333.6	334.3	335.0	335.6
107.5°	410.7	412.2	413.7	415.3	416.7	417.5	417.5	417.5	417.5	417.5	417.7
110°	464.3	466.4	468.4	470.4	472.4	473.5	473.5	473.5	473.5	473.5	473.5



TEST NUMBER: P331784-840

CATALOG NUMBER: S122RDIW-S290D1440U840-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	522.8	524.8	526.8	528.9	530.9	531.8	531.5	531.3	531.0	530.7	529.9
115°	608.9	611.0	613.0	615.1	617.1	617.7	617.1	616.4	615.7	615.1	614.7
117.5°	694.9	697.5	700.2	703.0	705.7	706.1	704.2	702.3	700.3	698.5	697.7
120°	752.0	754.8	757.5	760.2	763.0	763.0	760.2	757.5	754.8	752.0	752.0
122.5°	804.5	807.7	810.9	814.2	817.5	818.1	816.3	814.4	812.4	810.5	809.7
125°	886.1	889.1	892.1	895.1	898.3	899.3	898.3	897.3	896.3	895.1	894.1
127.5°	965.5	969.4	973.2	977.1	981.0	982.3	981.1	979.9	978.7	977.4	976.1
130°	1015.4	1019.9	1024.3	1028.6	1033.1	1034.9	1034.2	1033.6	1032.9	1032.2	1031.6
132.5°	1071.5	1075.1	1078.6	1082.3	1085.8	1087.7	1087.8	1087.9	1088.1	1088.2	1086.7
135°	1146.4	1150.1	1153.9	1157.5	1161.2	1163.5	1164.2	1164.9	1165.5	1166.2	1165.9
137.5°	1225.3	1228.3	1231.3	1234.4	1237.4	1239.4	1240.3	1241.1	1242.0	1242.9	1242.6
140°	1272.7	1275.8	1278.9	1281.9	1285.0	1287.3	1289.0	1290.7	1292.4	1294.0	1294.0
142.5°	1321.5	1324.5	1327.6	1330.6	1333.6	1335.7	1336.9	1338.1	1339.2	1340.4	1340.6
145°	1391.5	1393.9	1396.2	1398.6	1401.0	1403.2	1405.2	1407.2	1409.3	1411.3	1411.6
147.5°	1453.9	1456.7	1459.6	1462.5	1465.3	1467.4	1468.7	1470.1	1471.5	1472.8	1473.6
150°	1496.5	1498.5	1500.7	1502.7	1504.7	1506.3	1507.7	1509.0	1510.5	1511.8	1512.8
152.5°	1534.3	1536.3	1538.3	1540.3	1542.5	1544.3	1545.9	1547.5	1549.1	1550.7	1552.1
155°	1590.9	1592.0	1593.0	1594.0	1595.0	1596.0	1597.0	1598.0	1599.0	1600.0	1601.7
157.5°	1639.3	1640.0	1640.7	1641.4	1642.0	1642.7	1643.4	1644.0	1644.6	1645.2	1647.4
160°	1668.6	1669.3	1669.9	1670.6	1671.3	1671.8	1672.1	1672.4	1672.8	1673.1	1675.2
162.5°	1695.4	1695.6	1695.7	1695.8	1696.0	1696.2	1696.5	1696.9	1697.2	1697.5	1699.8
165°	1731.0	1730.7	1730.3	1730.0	1729.7	1729.5	1729.5	1729.5	1729.5	1729.5	1731.8
167.5°	1760.8	1759.8	1758.8	1757.8	1756.8	1756.3	1756.2	1756.2	1756.1	1756.0	1758.4
170°	1776.7	1775.6	1774.6	1773.6	1772.6	1771.9	1771.6	1771.3	1770.9	1770.6	1772.9
172.5°	1787.7	1786.7	1785.6	1784.6	1783.6	1782.9	1782.6	1782.2	1781.9	1781.5	1783.9
175°	1801.0	1800.0	1799.0	1798.0	1797.0	1796.1	1795.4	1794.7	1794.1	1793.4	1795.8
177.5°	1806.5	1805.7	1804.9	1804.1	1803.3	1802.6	1802.0	1801.5	1801.0	1800.4	1802.0
180°	1804.1	1804.1	1804.1	1804.1	1804.1	1804.1	1804.1	1804.1	1804.1	1804.1	1804.1



TEST NUMBER: P331784-840

CATALOG NUMBER: S122RDIW-S290D1440U840-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	507.0	507.0	507.0	507.0	507.0	507.0	507.0	507.0
2.5°	504.5	505.3	506.1	506.4	506.3	506.1	505.9	505.8
5°	500.5	501.4	502.3	502.6	502.3	502.0	501.7	501.4
7.5°	492.4	492.7	492.9	492.8	492.3	491.7	491.2	490.7
10°	484.3	484.0	483.7	483.2	482.6	482.0	481.4	480.8
12.5°	475.0	474.4	473.9	473.1	472.1	471.1	470.1	469.1
15°	457.7	455.7	453.7	452.3	451.3	450.2	449.2	448.2
17.5°	438.0	435.7	433.4	431.4	429.6	427.9	426.1	424.3
20°	424.3	421.7	419.2	416.8	414.5	412.3	410.1	407.9
22.5°	409.3	406.0	402.7	400.2	398.5	396.9	395.2	393.5
25°	384.4	380.1	376.0	373.1	371.6	370.0	368.5	367.0
27.5°	360.5	355.7	350.8	347.2	344.8	342.3	339.9	337.5
30°	343.8	338.6	333.4	329.4	326.6	323.9	321.1	318.4
32.5°	326.9	320.9	315.0	310.7	308.2	305.6	303.0	300.4
35°	300.5	294.1	287.6	283.3	281.0	278.8	276.6	274.4
37.5°	274.8	267.7	260.6	255.8	253.3	250.6	248.1	245.5
40°	257.6	250.3	243.1	238.1	235.5	232.9	230.1	227.5
42.5°	240.1	232.7	225.2	220.3	217.6	215.1	212.5	210.0
45°	214.9	207.6	200.5	195.6	193.2	190.7	188.2	185.8
47.5°	190.3	183.1	175.9	171.2	169.0	166.7	164.5	162.3
50°	174.5	167.4	160.4	155.8	153.7	151.6	149.4	147.2
52.5°	159.6	152.8	146.0	141.6	139.7	137.6	135.6	133.7
55°	136.8	130.8	124.6	120.6	118.7	116.7	114.8	112.9
57.5°	116.2	110.6	105.0	101.4	99.8	98.2	96.5	94.8
60°	102.0	96.8	91.6	88.2	86.5	84.9	83.3	81.7
62.5°	89.7	84.7	79.8	76.7	75.7	74.8	73.8	72.8
65°	72.9	69.4	65.9	64.0	63.7	63.4	63.1	62.8
67.5°	58.9	57.3	55.6	54.7	54.3	54.0	53.7	53.4
70°	51.2	50.2	49.2	48.5	48.0	47.6	47.2	46.8
72.5°	44.5	43.6	42.8	42.3	42.0	41.8	41.5	41.3
75°	35.2	34.5	33.8	33.4	33.3	33.2	33.1	33.0
77.5°	26.7	26.3	25.9	25.7	25.4	25.2	25.1	24.9
80°	21.2	20.8	20.4	20.2	20.2	20.2	20.2	20.2
82.5°	16.1	15.8	15.6	15.5	15.5	15.5	15.5	15.5
85°	8.7	8.7	8.7	8.7	8.7	8.7	8.7	8.7
87.5°	13.1	12.9	12.7	12.6	12.7	12.8	12.8	12.9
90°	51.9	51.3	50.6	50.4	50.8	51.1	51.4	51.8
92.5°	48.7	48.8	49.0	49.1	49.1	49.2	49.3	49.3
95°	97.5	97.5	97.5	97.0	96.4	95.7	95.0	94.4
97.5°	163.8	163.8	163.8	163.8	163.7	163.6	163.6	163.5
100°	210.1	210.1	210.1	210.0	209.5	209.2	208.9	208.5
102.5°	260.5	260.8	261.2	261.1	260.7	260.4	260.0	259.7
105°	336.3	337.0	337.6	338.0	338.0	338.0	338.0	338.0
107.5°	418.0	418.3	418.5	417.9	416.4	414.8	413.2	411.6
110°	473.5	473.5	473.5	472.9	471.9	470.9	469.9	468.9





TEST NUMBER: P331784-840

CATALOG NUMBER: S122RDIW-S290D1440U840-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	529.1	528.3	527.5	526.6	525.9	525.2	524.4	523.7
115°	614.4	614.0	613.7	613.0	612.0	611.0	610.0	608.9
117.5°	696.9	696.1	695.3	694.3	693.3	692.3	691.3	690.2
120°	752.0	752.0	752.0	751.5	750.5	749.5	748.5	747.5
122.5°	808.9	808.1	807.3	806.5	805.8	805.1	804.3	803.5
125°	893.1	892.1	891.1	890.5	890.1	889.8	889.5	889.1
127.5°	974.9	973.7	972.5	971.4	970.3	969.2	968.2	967.0
130°	1030.9	1030.2	1029.5	1028.4	1027.1	1025.8	1024.4	1023.1
132.5°	1085.3	1083.8	1082.3	1081.0	1079.9	1078.8	1077.7	1076.6
135°	1165.5	1165.2	1164.9	1164.2	1163.2	1162.2	1161.1	1160.1
137.5°	1242.3	1242.1	1241.8	1241.0	1239.7	1238.3	1237.0	1235.6
140°	1294.0	1294.0	1294.0	1293.4	1292.0	1290.7	1289.3	1288.0
142.5°	1340.9	1341.2	1341.4	1340.9	1339.6	1338.2	1336.9	1335.4
145°	1412.0	1412.3	1412.6	1412.1	1410.8	1409.5	1408.1	1406.7
147.5°	1474.3	1475.0	1475.8	1475.5	1474.2	1472.9	1471.7	1470.4
150°	1513.8	1514.8	1515.8	1515.8	1514.8	1513.8	1512.8	1511.8
152.5°	1553.3	1554.6	1555.9	1555.9	1554.6	1553.3	1552.1	1550.7
155°	1603.5	1605.2	1606.8	1607.2	1606.2	1605.2	1604.2	1603.2
157.5°	1649.7	1652.0	1654.4	1654.7	1653.0	1651.4	1649.8	1648.2
160°	1677.2	1679.2	1681.2	1681.6	1680.2	1678.9	1677.6	1676.2
162.5°	1702.1	1704.5	1706.7	1707.1	1705.5	1703.8	1702.2	1700.5
165°	1734.2	1736.6	1739.0	1739.3	1737.6	1736.0	1734.2	1732.5
167.5°	1760.7	1763.1	1765.4	1765.7	1764.0	1762.2	1760.5	1758.7
170°	1775.3	1777.7	1780.1	1780.2	1778.2	1776.2	1774.1	1772.1
172.5°	1786.2	1788.7	1791.0	1791.2	1789.2	1787.2	1785.1	1783.1
175°	1798.2	1800.5	1802.9	1803.1	1801.0	1799.0	1797.0	1794.9
177.5°	1803.7	1805.3	1807.0	1807.0	1805.3	1803.7	1802.0	1800.4
180°	1804.1	1804.1	1804.1	1804.1	1804.1	1804.1	1804.1	1804.1

(END OF REPORT)