

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332416-927

Luminaire Tested: **S123RDIW-S560D755U927-4F0-1E-UDD-F**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P332416-927  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-5,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S123RDIW-S560D755U927-4F0-1E-UDD-F  
Description: DEFINE 3 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 560 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED  
HOUSING  
UPLIGHT 755 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 4085.3 lumens  
Efficiency: N/A  
Efficacy: 108.7 lumens/watt  
Spacing Criteria (0/90/45): 1.21 / 1.06 / 1.22  
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')  
CIE Type: General Diffuse


Input Watts (W): 37.6  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332416-927

CATALOG NUMBER: S123RDIW-S560D755U927-4F0-1E-UDD-F

### Luminous Intensity Polar Plot





TEST NUMBER: P332416-927

CATALOG NUMBER: S123RDIW-S560D755U927-4F0-1E-UDD-F

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	105	105	105	105	96	96	96	96	79	79	79	63	63	63	48	48	48	41
1	96	92	88	85	88	84	81	78	69	67	65	56	54	53	43	42	41	35
2	88	81	75	70	80	74	69	64	61	57	54	49	47	44	38	37	35	30
3	80	71	64	58	73	65	59	54	54	49	46	44	40	38	34	32	30	26
4	73	63	55	49	67	58	51	46	48	43	39	39	35	33	31	28	26	22
5	67	56	48	42	61	52	45	40	43	38	34	35	31	28	28	25	23	20
6	62	50	43	37	57	46	39	34	39	34	30	32	28	25	25	22	20	17
7	57	46	38	32	52	42	35	30	35	30	26	29	25	22	23	20	18	15
8	53	41	34	29	49	38	31	27	32	27	23	26	23	20	21	18	16	14
9	50	38	30	25	45	35	28	24	29	24	21	24	21	18	20	17	15	13
10	46	35	28	23	42	32	26	21	27	22	19	23	19	16	18	15	13	11

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	8054	8054	8054
5°	8084	7973	8018
10°	8039	7873	7847
15°	7952	7689	7608
20°	7834	7458	7285
25°	7712	7201	6969
30°	7549	6901	6524
35°	7384	6603	6116
40°	7231	6250	5611
45°	7030	5903	5154
50°	6807	5508	4644
55°	6583	5056	4168
60°	6374	4573	3645
65°	6105	4050	3123
70°	5766	3402	2521
75°	5273	2674	2371
80°	4705	2374	2182
85°	3977	2100	1951



TEST NUMBER: P332416-927

CATALOG NUMBER: S123RDIW-S560D755U927-4F0-1E-UDD-F

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	70.3	1.7
10°-20°	195.5	4.8
20°-30°	281.5	6.9
30°-40°	317.1	7.8
40°-50°	303.3	7.4
50°-60°	248.4	6.1
60°-70°	167.6	4.1
70°-80°	84.3	2.1
80°-90°	24.5	0.6
90°-100°	28.5	0.7
100°-110°	136.0	3.3
110°-120°	326.6	8.0
120°-130°	415.9	10.2
130°-140°	444.3	10.9
140°-150°	415.5	10.2
150°-160°	335.2	8.2
160°-170°	216.3	5.3
170°-180°	74.5	1.8
0°-30°	547.2	13.4
0°-40°	864.3	21.2
0°-60°	1416.1	34.7
0°-90°	1692.5	41.4
90°-120°	491.1	12.0
90°-150°	1766.8	43.2
90°-180°	2393.0	58.6
0°-180°	4085.3	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	748	748	748	748	748	
5°	748	745	738	743	742	71
15°	714	706	690	687	683	201
25°	649	633	606	594	587	298
35°	562	539	502	477	465	352
45°	462	433	388	354	339	356
55°	351	320	269	236	222	314
65°	240	206	159	130	123	237
75°	127	97	64	58	57	135
85°	32	19	17	16	16	36
90°	1	7	14	16	18	3
95°	36	13	18	22	22	44
105°	174	177	128	30	26	184
115°	326	329	335	340	343	322
125°	459	464	466	468	469	410
135°	572	575	578	579	578	440
145°	660	664	665	666	666	413
155°	727	726	726	729	726	335
165°	767	765	764	768	765	216
175°	785	782	782	786	782	75
180°	785	785	785	785	785	



TEST NUMBER: P332416-927

CATALOG NUMBER: S123RDIW-S560D755U927-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	748.2	748.2	748.2	748.2	748.2	748.2	748.2	748.2	748.2	748.2	748.2
2.5°	750.7	750.2	749.8	749.3	748.9	748.1	746.8	745.4	744.2	742.9	744.1
5°	748.2	747.6	746.9	746.2	745.5	744.4	742.8	741.2	739.5	737.9	739.1
7.5°	741.3	740.6	739.8	739.1	738.4	737.0	734.9	732.8	730.6	728.6	729.2
10°	735.5	734.5	733.6	732.6	731.7	730.0	727.6	725.2	722.7	720.3	720.4
12.5°	727.2	726.2	725.1	724.1	723.0	721.0	718.0	715.1	712.1	709.2	709.1
15°	713.6	712.2	710.7	709.2	707.7	705.0	701.3	697.5	693.7	690.0	689.3
17.5°	696.5	694.8	693.1	691.3	689.6	686.3	681.5	676.8	671.9	667.2	665.7
20°	683.9	681.8	679.6	677.4	675.3	671.6	666.5	661.4	656.2	651.1	649.4
22.5°	669.8	667.3	664.9	662.3	659.9	655.9	650.5	645.0	639.6	634.1	631.9
25°	649.3	645.9	642.5	639.2	635.8	631.1	624.8	618.6	612.4	606.3	603.4
27.5°	624.4	620.7	617.0	613.2	609.5	604.2	597.3	590.4	583.5	576.6	572.7
30°	607.4	603.4	599.4	595.3	591.3	585.4	577.9	570.4	562.8	555.2	550.6
32.5°	590.4	585.9	581.3	576.7	572.1	565.9	557.9	549.9	541.9	533.9	528.9
35°	561.9	557.1	552.2	547.4	542.5	535.9	527.5	519.2	510.8	502.5	496.6
37.5°	533.1	527.7	522.3	516.8	511.4	504.3	495.4	486.5	477.5	468.6	462.0
40°	514.6	508.7	502.7	496.8	490.8	483.1	473.6	464.0	454.4	444.8	437.8
42.5°	493.7	487.7	481.9	475.9	470.0	462.1	452.2	442.3	432.4	422.5	414.8
45°	461.8	455.7	449.6	443.6	437.5	429.3	418.9	408.5	398.2	387.8	380.1
47.5°	429.8	423.2	416.5	409.9	403.2	394.7	384.3	373.9	363.5	353.2	344.8
50°	406.5	400.2	393.9	387.5	381.2	372.6	361.6	350.8	339.8	328.9	320.5
52.5°	385.7	378.8	371.9	365.0	358.2	349.4	338.5	327.7	316.9	306.1	297.4
55°	350.8	344.1	337.5	330.9	324.3	315.3	303.8	292.4	280.9	269.4	261.6
57.5°	318.5	311.2	304.0	296.8	289.6	280.3	268.8	257.3	245.7	234.2	226.9
60°	296.1	288.8	281.3	273.9	266.5	257.1	246.0	234.8	223.6	212.4	205.1
62.5°	273.8	266.4	259.0	251.5	244.2	234.8	223.6	212.5	201.2	190.0	183.2
65°	239.7	232.3	224.9	217.5	210.0	201.1	190.5	180.1	169.5	159.0	152.4
67.5°	205.6	198.1	190.6	183.1	175.6	166.8	156.7	146.6	136.6	126.4	121.5
70°	183.2	175.9	168.7	161.4	154.2	145.8	136.3	126.9	117.5	108.1	103.3
72.5°	160.9	153.8	146.6	139.4	132.2	124.4	115.8	107.2	98.6	90.1	86.2
75°	126.8	120.3	113.9	107.4	100.9	94.0	86.6	79.1	71.8	64.3	63.0
77.5°	95.8	89.9	84.1	78.2	72.3	67.0	62.3	57.5	52.7	47.9	47.2
80°	75.9	70.3	64.8	59.3	53.7	49.6	46.7	43.9	41.0	38.3	37.8
82.5°	57.0	52.1	47.4	42.6	37.8	34.8	33.4	32.2	30.8	29.5	29.1
85°	32.2	29.2	26.2	23.3	20.3	18.6	18.2	17.8	17.4	17.0	16.7
87.5°	11.8	10.9	9.9	9.0	8.1	7.8	8.1	8.4	8.8	9.1	9.1
90°	0.6	1.9	3.2	4.4	5.8	7.3	9.0	10.6	12.3	14.0	14.5
92.5°	10.9	10.5	10.1	9.7	9.4	9.8	11.1	12.4	13.6	14.9	15.8
95°	35.6	30.3	25.0	19.6	14.3	12.4	13.8	15.2	16.6	18.1	19.0
97.5°	71.5	69.1	66.7	64.3	61.9	56.1	46.7	37.4	28.1	18.8	19.8
100°	98.5	101.1	103.7	106.3	108.8	100.1	79.9	59.7	39.5	19.3	20.3
102.5°	129.3	131.2	133.0	134.9	136.7	126.7	104.6	82.5	60.4	38.3	35.2
105°	173.7	175.2	176.6	178.0	179.4	174.3	162.6	151.0	139.3	127.7	104.7
107.5°	220.5	221.7	222.8	224.0	225.1	226.6	228.5	230.3	232.2	234.0	217.1
110°	251.8	252.9	253.9	254.9	256.0	257.2	258.6	260.1	261.5	262.9	258.6



TEST NUMBER: P332416-927

CATALOG NUMBER: S123RDIW-S560D755U927-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	281.7	282.6	283.5	284.5	285.4	286.6	288.0	289.5	290.9	292.3	292.4
115°	325.8	326.6	327.4	328.2	329.0	329.9	331.1	332.2	333.4	334.6	335.9
117.5°	368.7	369.6	370.6	371.5	372.5	373.3	373.8	374.5	375.0	375.7	376.7
120°	395.2	396.4	397.6	398.7	399.9	400.7	401.1	401.5	401.9	402.2	403.3
122.5°	422.3	423.3	424.2	425.2	426.1	426.8	427.3	427.9	428.3	428.8	429.5
125°	459.4	460.4	461.4	462.5	463.5	464.3	464.8	465.3	465.8	466.4	466.6
127.5°	495.3	496.3	497.3	498.4	499.4	500.3	500.9	501.5	502.1	502.7	503.1
130°	517.6	518.7	519.8	520.8	521.8	522.6	523.1	523.6	524.1	524.7	525.1
132.5°	539.1	540.1	541.1	542.2	543.3	544.0	544.4	544.8	545.2	545.7	546.1
135°	571.9	572.7	573.4	574.2	575.0	575.6	576.2	576.6	577.2	577.7	578.1
137.5°	599.8	600.8	601.8	602.8	603.8	604.4	604.7	605.0	605.3	605.5	606.2
140°	618.5	619.2	620.0	620.8	621.6	622.2	622.6	623.0	623.4	623.8	624.2
142.5°	635.7	636.5	637.3	638.1	638.9	639.4	639.8	640.2	640.6	641.0	641.4
145°	659.9	660.8	661.7	662.6	663.5	664.1	664.3	664.6	664.9	665.1	665.4
147.5°	682.6	683.2	683.8	684.4	685.0	685.4	685.7	686.0	686.2	686.4	686.7
150°	696.6	697.0	697.4	697.8	698.2	698.5	698.8	699.0	699.3	699.5	699.8
152.5°	709.2	709.4	709.6	709.7	710.0	710.1	710.3	710.4	710.6	710.7	711.1
155°	726.9	726.7	726.4	726.1	725.9	725.8	726.0	726.1	726.2	726.4	727.0
157.5°	740.7	740.7	740.6	740.6	740.6	740.5	740.4	740.2	740.1	740.0	740.8
160°	749.1	748.9	748.8	748.7	748.5	748.5	748.3	748.1	748.1	747.9	748.7
162.5°	757.0	756.7	756.3	756.0	755.7	755.4	755.3	755.2	755.0	754.9	755.8
165°	766.6	766.2	765.8	765.4	765.0	764.8	764.6	764.5	764.4	764.2	765.2
167.5°	774.0	773.5	773.0	772.5	772.0	771.7	771.7	771.7	771.7	771.7	772.7
170°	778.2	777.7	777.2	776.7	776.2	775.9	775.9	775.9	775.9	775.9	776.9
172.5°	781.0	780.4	779.7	779.2	778.6	778.2	778.4	778.5	778.6	778.7	779.7
175°	784.7	783.9	783.3	782.7	782.0	781.8	781.9	782.0	782.2	782.3	783.2
177.5°	785.5	785.1	784.5	784.0	783.5	783.3	783.4	783.5	783.6	783.7	784.5
180°	784.7	784.7	784.7	784.7	784.7	784.7	784.7	784.7	784.7	784.7	784.7



TEST NUMBER: P332416-927

CATALOG NUMBER: S123RDIW-S560D755U927-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	748.2	748.2	748.2	748.2	748.2	748.2	748.2	748.2
2.5°	745.3	746.5	747.7	748.1	747.9	747.7	747.5	747.3
5°	740.3	741.6	742.8	743.2	743.0	742.7	742.4	742.1
7.5°	729.9	730.6	731.3	731.3	730.9	730.5	730.0	729.5
10°	720.6	720.7	720.8	720.6	719.9	719.2	718.6	717.9
12.5°	709.0	708.9	708.8	708.4	707.6	706.8	706.1	705.3
15°	688.6	687.9	687.3	686.4	685.5	684.6	683.7	682.7
17.5°	664.3	662.9	661.4	660.0	658.6	657.2	655.8	654.4
20°	647.6	645.9	644.1	642.5	640.8	639.2	637.5	636.0
22.5°	629.8	627.6	625.4	623.5	622.0	620.5	619.0	617.5
25°	600.6	597.7	594.9	592.7	591.3	589.8	588.3	586.8
27.5°	568.7	564.8	560.9	557.8	555.5	553.3	551.0	548.7
30°	546.1	541.5	536.9	533.5	531.4	529.3	527.0	524.9
32.5°	523.9	518.8	513.8	510.2	507.9	505.6	503.4	501.1
35°	490.8	485.1	479.3	475.2	472.7	470.3	467.9	465.4
37.5°	455.4	448.9	442.3	437.5	434.5	431.5	428.5	425.5
40°	430.8	423.7	416.8	411.7	408.6	405.5	402.4	399.3
42.5°	407.2	399.5	391.8	386.6	383.8	381.0	378.3	375.5
45°	372.4	364.7	357.0	351.6	348.3	345.1	341.8	338.6
47.5°	336.4	328.1	319.7	314.1	311.2	308.3	305.5	302.5
50°	312.2	303.8	295.5	289.7	286.6	283.5	280.4	277.3
52.5°	288.8	280.0	271.3	265.6	262.8	260.1	257.3	254.5
55°	253.8	246.0	238.1	232.9	230.2	227.5	224.8	222.1
57.5°	219.4	212.1	204.7	199.9	197.6	195.3	193.0	190.7
60°	197.8	190.5	183.2	178.5	176.2	173.9	171.6	169.3
62.5°	176.3	169.5	162.6	158.0	155.7	153.2	150.8	148.5
65°	145.8	139.2	132.5	128.5	127.1	125.6	124.1	122.6
67.5°	116.6	111.6	106.7	103.5	101.9	100.3	98.7	97.1
70°	98.5	93.9	89.1	86.0	84.5	83.1	81.6	80.1
72.5°	82.3	78.5	74.6	72.4	71.8	71.1	70.5	69.9
75°	61.6	60.3	58.9	58.1	57.8	57.6	57.3	57.0
77.5°	46.5	45.8	45.0	44.5	44.3	44.0	43.7	43.4
80°	37.4	37.0	36.6	36.3	36.0	35.7	35.5	35.2
82.5°	28.7	28.3	27.9	27.6	27.6	27.6	27.5	27.4
85°	16.5	16.2	15.9	15.8	15.8	15.8	15.8	15.8
87.5°	9.1	9.1	9.1	9.0	9.0	9.0	8.9	8.9
90°	15.1	15.5	16.1	16.5	16.7	17.0	17.2	17.5
92.5°	16.6	17.4	18.2	18.7	18.9	19.0	19.2	19.3
95°	19.9	20.8	21.7	22.2	22.2	22.2	22.2	22.2
97.5°	20.8	21.9	22.9	23.5	23.6	23.8	23.9	24.0
100°	21.3	22.3	23.4	24.0	24.1	24.2	24.3	24.5
102.5°	31.9	28.8	25.5	24.0	24.2	24.5	24.7	25.0
105°	81.8	58.9	36.0	24.6	24.9	25.1	25.4	25.7
107.5°	200.3	183.5	166.8	149.7	132.4	115.1	97.8	80.6
110°	254.4	250.1	245.8	234.4	215.9	197.3	178.8	160.3





TEST NUMBER: P332416-927

CATALOG NUMBER: S123RDIW-S560D755U927-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	292.5	292.6	292.6	290.7	286.8	282.9	278.9	275.0
115°	337.2	338.5	339.8	340.7	341.2	341.7	342.2	342.8
117.5°	377.7	378.7	379.8	380.3	380.5	380.6	380.6	380.8
120°	404.3	405.4	406.4	406.9	406.9	406.9	406.9	406.9
122.5°	430.2	430.9	431.7	432.1	432.2	432.3	432.5	432.5
125°	466.8	467.1	467.4	467.6	467.9	468.2	468.4	468.7
127.5°	503.6	504.0	504.4	504.5	504.2	503.9	503.7	503.4
130°	525.7	526.2	526.7	526.9	526.6	526.3	526.1	525.8
132.5°	546.7	547.2	547.7	547.8	547.4	547.1	546.7	546.3
135°	578.5	578.8	579.2	579.2	578.8	578.5	578.1	577.7
137.5°	606.8	607.4	608.1	608.2	608.0	607.7	607.4	607.2
140°	624.8	625.3	625.8	626.0	625.7	625.4	625.2	624.9
142.5°	641.8	642.2	642.6	642.7	642.3	642.0	641.6	641.2
145°	665.7	665.9	666.1	666.3	666.3	666.3	666.3	666.3
147.5°	687.0	687.2	687.5	687.3	686.7	686.1	685.6	684.9
150°	700.1	700.3	700.5	700.5	700.1	699.7	699.3	698.9
152.5°	711.6	712.1	712.6	712.5	711.9	711.3	710.7	710.1
155°	727.6	728.3	729.0	728.9	728.1	727.3	726.5	725.7
157.5°	741.6	742.3	743.1	743.0	742.0	740.9	740.0	738.9
160°	749.5	750.3	751.0	751.0	750.0	749.2	748.2	747.3
162.5°	756.7	757.6	758.4	758.4	757.6	756.9	756.1	755.3
165°	766.3	767.3	768.3	768.4	767.5	766.6	765.7	764.8
167.5°	773.7	774.8	775.9	775.9	774.8	773.7	772.7	771.7
170°	777.9	779.0	780.1	780.1	779.0	777.9	776.9	775.9
172.5°	780.8	781.8	782.8	782.8	781.6	780.5	779.3	778.2
175°	784.1	785.1	785.9	785.8	784.8	783.8	782.8	781.7
177.5°	785.4	786.2	787.0	786.9	785.8	784.8	783.8	782.8
180°	784.7	784.7	784.7	784.7	784.7	784.7	784.7	784.7

(END OF REPORT)