

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331765-840

Luminaire Tested: **S122RDIW-S290D435U840-4F0-1E-UDD-A**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331765-840
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122RDIW-S290D435U840-4F0-1E-UDD-A
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 290 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 435 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2890.5 lumens
Efficiency: N/A
Efficacy: 125.7 lumens/watt
Spacing Criteria (0/90/45): 0.86 / 1.16 / 1.02
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 23
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331765-840

CATALOG NUMBER: S122RDIW-S290D435U840-4F0-1E-UDD-A

Luminous Intensity Polar Plot





TEST NUMBER: P331765-840

CATALOG NUMBER: S122RDIW-S290D435U840-4F0-1E-UDD-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	105	105	105	105	95	95	95	95	78	78	78	61	61	61	47	47	47	40
1	96	92	88	85	87	84	81	78	69	67	65	55	53	52	42	41	40	34
2	88	81	75	71	80	74	69	65	61	58	55	49	47	45	38	36	35	30
3	81	72	65	60	73	66	60	55	54	50	47	44	41	38	34	32	31	26
4	74	64	57	51	67	59	52	47	49	44	40	40	36	34	31	29	27	23
5	68	57	50	44	62	53	46	41	44	39	35	36	32	30	28	26	24	21
6	63	52	44	39	57	48	41	36	40	35	31	33	29	26	26	23	21	18
7	58	47	39	34	53	43	37	32	36	31	28	30	26	23	24	21	19	17
8	54	43	35	30	50	39	33	28	33	28	25	28	24	21	22	20	18	15
9	51	39	32	27	46	36	30	26	31	26	22	25	22	19	21	18	16	14
10	47	36	29	25	43	33	27	23	28	24	20	24	20	18	19	17	15	13

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	10658	10658	10658	10658
5°	11904	10726	9511	10726
10°	13209	10650	8243	10650
15°	13857	10494	6496	10494
20°	12014	10263	5620	10263
25°	7878	9948	5018	9948
30°	5304	9562	4542	9562
35°	4295	9079	4096	9079
40°	3819	8553	3792	8553
45°	3457	7935	3382	7935
50°	3145	7322	3135	7322
55°	2956	6643	2919	6643
60°	2474	6022	2444	6022
65°	2086	5467	2365	5467
70°	1926	4881	2233	4881
75°	1803	4255	2059	4255
80°	1664	3505	1832	3505
85°	1538	2760	1612	2760



TEST NUMBER: P331765-840

CATALOG NUMBER: S122RDIW-S290D435U840-4F0-1E-UDD-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	62.6	2.2
10°-20°	174.4	6.0
20°-30°	224.7	7.8
30°-40°	213.5	7.4
40°-50°	182.9	6.3
50°-60°	139.3	4.8
60°-70°	88.1	3.0
70°-80°	44.0	1.5
80°-90°	12.9	0.4
90°-100°	19.9	0.7
100°-110°	73.0	2.5
110°-120°	195.0	6.7
120°-130°	322.0	11.1
130°-140°	342.4	11.8
140°-150°	318.3	11.0
150°-160°	255.9	8.9
160°-170°	164.9	5.7
170°-180°	56.8	2.0
0°-30°	461.7	16.0
0°-40°	675.2	23.4
0°-60°	997.5	34.5
0°-90°	1142.4	39.5
90°-120°	287.9	10.0
90°-150°	1270.6	44.0
90°-180°	1748.0	60.5
0°-180°	2890.5	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	660	660	660	660	660	
5°	734	662	587	662	734	72
15°	829	628	389	628	829	224
25°	442	558	282	558	442	210
35°	218	461	208	461	218	139
45°	151	348	148	348	151	117
55°	105	236	104	236	105	92
65°	55	143	62	143	55	56
75°	29	68	33	68	29	31
85°	8	15	9	15	8	9
90°	12	0	12	0	12	5
95°	19	28	19	28	19	17
105°	33	131	33	131	33	34
115°	35	248	35	248	35	89
125°	369	351	369	351	369	319
135°	448	434	448	434	448	346
145°	512	504	512	504	512	320
155°	555	555	555	555	555	256
165°	583	584	583	584	583	165
175°	594	598	594	598	594	57
180°	596	596	596	596	596	



TEST NUMBER: P331765-840

CATALOG NUMBER: S122RDIW-S290D435U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	660.1	660.1	660.1	660.1	660.1	660.1	660.1	660.1	660.1	660.1	660.1
2.5°	687.0	687.5	688.1	686.8	686.8	685.7	683.3	681.5	676.3	675.6	675.6
5°	734.5	734.1	735.0	732.0	727.9	726.9	722.6	716.8	710.8	704.3	702.9
7.5°	781.7	781.0	779.2	778.7	775.6	768.6	761.6	754.2	744.3	734.6	729.7
10°	805.7	813.2	808.6	800.6	802.1	791.4	785.7	775.8	767.5	753.1	749.9
12.5°	829.1	832.1	830.6	826.1	824.0	816.6	808.8	800.2	785.0	772.0	760.7
15°	829.0	833.3	834.6	833.1	834.2	833.8	829.7	822.6	809.3	795.1	782.6
17.5°	767.8	770.8	778.4	783.5	789.9	803.4	810.2	812.7	810.8	802.6	794.0
20°	699.2	694.2	715.3	726.0	735.2	758.1	777.9	785.5	797.6	797.4	795.1
22.5°	601.9	603.1	623.1	635.9	662.7	685.7	708.1	736.6	760.1	775.7	784.8
25°	442.2	451.0	470.9	488.4	518.2	560.9	599.7	644.6	687.0	720.5	752.5
27.5°	332.1	332.9	348.6	364.8	382.4	417.4	466.3	519.9	580.4	630.4	687.7
30°	284.5	283.1	289.7	299.6	314.8	341.8	378.5	431.2	491.6	566.8	633.8
32.5°	250.6	250.7	255.8	263.1	275.6	293.9	319.0	361.9	418.9	492.9	571.4
35°	217.9	217.7	221.4	226.6	231.9	243.6	260.8	283.3	322.6	391.5	471.8
37.5°	194.4	195.4	197.2	200.6	206.3	212.9	223.2	238.3	266.2	307.1	374.6
40°	181.2	181.7	184.2	186.9	190.4	195.4	203.9	216.1	236.5	269.0	318.4
42.5°	169.2	169.6	171.4	173.9	176.6	181.7	188.7	199.2	215.8	241.2	281.9
45°	151.4	151.4	153.0	154.1	157.1	161.7	167.4	176.2	187.6	206.4	233.5
47.5°	134.8	134.8	135.9	137.8	139.8	143.3	149.0	156.1	164.4	178.9	202.1
50°	125.2	125.5	126.1	127.7	129.0	132.1	136.5	142.7	151.4	162.7	181.9
52.5°	117.5	117.4	118.3	119.0	119.8	122.0	125.3	130.8	138.6	148.3	164.3
55°	105.0	104.1	105.5	106.6	107.3	108.3	110.1	113.5	120.2	128.5	140.4
57.5°	89.5	89.1	90.1	91.1	93.3	95.7	97.4	99.5	102.9	108.9	120.7
60°	76.6	76.6	78.7	79.4	81.9	85.1	88.4	90.2	93.6	97.5	106.2
62.5°	65.2	65.4	66.3	67.1	68.5	72.4	77.0	81.0	84.2	88.0	93.7
65°	54.6	55.0	55.0	55.5	56.5	57.4	59.2	62.4	68.2	73.4	77.8
67.5°	46.4	46.5	46.7	47.1	47.3	48.3	49.1	50.5	51.8	56.8	62.2
70°	40.8	41.5	41.3	41.7	42.0	42.4	43.3	44.0	46.2	47.3	50.5
72.5°	35.6	36.2	36.2	36.5	37.1	37.2	37.9	38.6	39.9	40.8	42.6
75°	28.9	28.7	28.9	29.4	29.6	29.8	29.8	30.7	31.4	32.3	33.5
77.5°	22.3	22.5	22.5	22.5	22.6	23.0	22.9	23.3	24.0	24.5	25.0
80°	17.9	18.1	17.9	18.1	18.4	18.6	18.4	18.6	19.3	19.7	19.7
82.5°	13.8	13.9	14.0	14.0	14.1	14.1	14.5	14.5	15.0	14.9	15.1
85°	8.3	8.1	8.1	8.1	8.3	8.5	8.3	8.3	8.5	8.5	8.5
87.5°	5.3	5.5	5.4	5.4	5.3	5.3	5.2	5.3	4.9	5.0	4.6
90°	11.6	11.5	11.3	11.1	10.9	10.5	10.1	9.6	9.1	8.6	7.9
92.5°	11.6	11.5	11.4	11.3	11.2	11.0	10.8	10.5	10.3	10.0	9.6
95°	18.6	18.7	18.8	18.9	19.0	18.8	18.3	17.8	17.3	16.9	16.2
97.5°	24.7	24.6	24.5	24.4	24.3	24.0	23.7	23.3	22.9	22.5	21.0
100°	28.9	28.7	28.6	28.4	28.2	27.7	26.9	26.2	25.3	24.6	22.9
102.5°	31.0	30.7	30.5	30.2	29.9	29.3	28.3	27.3	26.3	25.2	39.0
105°	32.8	32.4	32.0	31.6	31.3	30.6	29.5	28.5	27.4	26.4	52.5
107.5°	33.7	33.3	33.0	32.6	32.2	32.5	33.6	34.7	35.7	36.9	68.3
110°	34.1	33.7	33.3	32.9	32.5	37.2	46.8	56.4	65.9	75.5	103.2



TEST NUMBER: P331765-840

CATALOG NUMBER: S122RDIW-S290D435U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	34.4	34.1	33.8	33.5	33.2	50.6	85.5	120.6	155.5	190.6	197.3
115°	35.3	42.3	49.2	56.1	63.0	88.7	133.1	177.5	221.9	266.3	263.9
117.5°	144.5	167.2	189.9	212.6	235.3	252.0	262.8	273.5	284.3	295.0	293.4
120°	263.3	276.2	289.2	302.2	315.1	321.0	319.8	318.7	317.5	316.4	314.7
122.5°	328.5	331.0	333.6	336.1	338.6	339.5	338.8	338.1	337.5	336.8	334.9
125°	369.0	368.8	368.5	368.2	367.9	367.4	366.8	366.1	365.4	364.8	362.9
127.5°	394.6	394.6	394.5	394.5	394.4	393.8	392.8	391.9	390.9	389.9	388.6
130°	410.5	410.6	410.7	410.8	410.9	410.4	409.3	408.3	407.2	406.2	405.2
132.5°	426.1	426.2	426.2	426.3	426.4	426.0	425.1	424.2	423.3	422.4	421.3
135°	448.5	448.7	448.9	449.1	449.2	448.9	447.9	447.0	446.0	445.0	444.1
137.5°	468.9	469.3	469.6	469.9	470.2	469.9	469.0	468.1	467.1	466.2	465.1
140°	481.7	482.2	482.6	483.1	483.6	483.4	482.6	481.7	480.8	480.0	478.9
142.5°	494.1	494.6	495.1	495.5	496.0	495.9	495.1	494.3	493.5	492.7	491.5
145°	511.5	512.0	512.4	512.9	513.4	513.3	512.6	512.0	511.3	510.6	509.0
147.5°	526.7	527.1	527.6	528.0	528.4	528.4	527.9	527.4	526.8	526.3	524.7
150°	536.1	536.5	537.0	537.6	538.1	538.0	537.3	536.8	536.2	535.6	534.1
152.5°	544.0	544.6	545.3	545.9	546.5	546.6	546.0	545.4	544.8	544.3	542.8
155°	555.1	555.8	556.6	557.3	558.2	558.3	557.6	557.1	556.5	555.9	554.8
157.5°	565.2	565.9	566.6	567.4	568.2	568.3	567.5	566.9	566.2	565.6	564.8
160°	571.1	571.7	572.4	573.1	573.7	573.8	573.2	572.6	572.1	571.5	570.9
162.5°	575.9	576.7	577.5	578.3	579.2	579.3	578.7	577.9	577.3	576.6	576.1
165°	583.1	583.8	584.5	585.1	585.8	585.8	585.1	584.5	583.8	583.1	582.9
167.5°	587.7	588.5	589.5	590.3	591.2	591.3	590.6	590.0	589.3	588.5	588.3
170°	590.5	591.4	592.2	593.1	593.9	594.0	593.4	592.7	592.0	591.4	591.2
172.5°	592.6	593.4	594.3	595.1	596.0	596.1	595.4	594.7	594.1	593.4	593.2
175°	594.4	595.3	596.3	597.2	598.2	598.3	597.6	597.0	596.3	595.6	595.4
177.5°	595.5	596.1	596.8	597.5	598.2	598.3	597.7	597.2	596.7	596.1	596.1
180°	596.5	596.5	596.5	596.5	596.5	596.5	596.5	596.5	596.5	596.5	596.5



TEST NUMBER: P331765-840

CATALOG NUMBER: S122RDIW-S290D435U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	660.1	660.1	660.1	660.1	660.1	660.1	660.1	660.1	660.1	660.1	660.1
2.5°	676.0	674.5	673.2	669.9	668.2	664.6	664.1	663.9	659.1	654.5	653.2
5°	699.2	695.5	690.0	683.6	676.9	670.0	665.5	661.8	652.6	643.9	638.8
7.5°	722.6	714.7	705.2	693.1	682.9	671.6	663.1	655.5	642.5	630.0	621.6
10°	740.0	727.2	714.6	697.8	684.7	671.9	659.9	649.6	635.0	618.4	606.7
12.5°	750.8	736.7	719.3	703.0	686.0	669.6	653.7	640.5	623.2	606.1	592.3
15°	765.5	750.3	729.2	705.8	684.1	662.7	644.4	627.8	605.4	584.9	567.9
17.5°	777.5	756.6	734.0	706.9	681.7	654.6	631.0	609.9	584.8	560.2	540.2
20°	781.3	760.6	734.5	707.4	677.6	645.7	620.3	597.3	570.5	543.6	520.7
22.5°	778.9	762.9	733.8	701.4	670.9	637.5	608.7	582.1	552.3	524.9	498.4
25°	762.8	757.2	729.7	694.4	659.5	620.8	587.4	558.4	524.4	495.0	466.2
27.5°	725.0	736.9	719.8	682.2	643.4	601.9	564.4	531.3	496.0	463.0	434.2
30°	688.6	715.9	708.6	673.7	630.4	589.6	547.5	512.9	475.3	441.3	412.9
32.5°	638.9	684.0	691.2	662.0	617.1	572.3	528.3	493.8	454.5	418.8	391.0
35°	559.7	627.1	658.1	639.5	594.6	546.1	500.8	460.6	421.1	385.9	358.3
37.5°	465.2	557.1	608.7	610.1	568.8	518.5	469.0	429.1	388.7	354.1	324.3
40°	403.9	503.5	570.8	585.6	550.8	496.4	446.4	405.8	366.4	332.3	298.2
42.5°	348.9	448.1	530.7	556.6	529.0	474.9	424.7	382.3	344.0	311.8	276.9
45°	282.2	368.9	459.9	506.2	490.9	440.9	387.9	347.5	311.5	283.8	250.2
47.5°	238.0	299.1	387.3	449.9	449.7	404.0	351.8	313.3	279.8	253.8	226.7
50°	212.9	266.1	340.6	411.7	417.7	379.4	329.8	291.5	260.3	233.1	211.3
52.5°	190.3	234.2	301.1	369.4	386.4	353.1	305.1	269.7	239.4	214.3	195.7
55°	160.8	194.8	245.7	309.4	335.2	311.7	269.0	236.0	211.5	190.4	174.3
57.5°	136.0	161.5	202.4	253.7	283.6	268.9	233.7	206.8	185.8	166.7	154.1
60°	120.5	141.3	175.9	218.8	251.9	241.6	211.5	186.5	168.6	152.1	140.2
62.5°	105.7	123.7	153.4	188.2	218.4	214.2	189.7	168.6	153.0	137.9	127.8
65°	85.1	98.2	121.4	148.7	173.0	175.0	157.3	143.1	129.2	117.2	108.3
67.5°	67.8	76.3	92.6	115.6	133.8	140.4	129.6	118.7	107.6	98.4	90.6
70°	57.2	64.0	75.9	94.5	111.3	118.2	111.9	103.4	93.8	86.2	79.6
72.5°	46.3	53.0	61.8	75.4	89.8	97.3	95.0	89.0	81.2	74.8	68.6
75°	34.8	37.0	42.9	52.1	63.3	69.8	71.3	68.2	61.9	57.2	53.4
77.5°	25.8	27.1	29.9	34.6	42.0	47.8	50.1	49.7	45.4	42.7	39.2
80°	20.6	21.3	22.7	24.7	30.3	36.1	37.7	37.7	34.6	33.5	30.1
82.5°	15.7	16.2	17.1	18.2	20.7	25.8	27.6	27.9	26.1	24.5	21.8
85°	9.0	8.7	9.2	9.9	10.3	11.7	14.4	14.9	14.4	12.6	11.9
87.5°	4.5	4.5	4.4	4.0	4.0	4.0	4.7	5.5	4.8	4.5	4.3
90°	7.1	6.4	5.6	4.6	3.6	2.5	1.5	0.4	1.5	2.5	3.6
92.5°	9.3	8.9	8.5	8.4	8.4	8.5	8.6	8.7	8.6	8.5	8.4
95°	15.5	14.8	14.1	15.3	18.6	21.7	24.8	28.1	24.8	21.7	18.6
97.5°	19.4	17.9	16.4	20.0	28.9	37.9	46.8	55.6	46.8	37.9	28.9
100°	21.3	19.7	18.1	23.8	37.0	50.1	63.2	76.4	63.2	50.1	37.0
102.5°	52.6	66.2	79.9	88.1	90.9	93.6	96.4	99.2	96.4	93.6	90.9
105°	78.7	104.9	131.1	142.7	139.9	136.9	134.1	131.2	134.1	136.9	139.9
107.5°	99.7	131.1	162.5	177.0	174.7	172.4	170.1	167.7	170.1	172.4	174.7
110°	131.0	158.6	186.4	199.2	197.2	195.2	193.2	191.2	193.2	195.2	197.2



TEST NUMBER: P331765-840

CATALOG NUMBER: S122RDIW-S290D435U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	204.2	211.1	217.9	220.5	218.6	216.9	215.1	213.3	215.1	216.9	218.6
115°	261.6	259.1	256.7	254.7	253.1	251.5	249.8	248.2	249.8	251.5	253.1
117.5°	291.6	290.0	288.4	286.6	284.8	283.0	281.1	279.3	281.1	283.0	284.8
120°	313.0	311.2	309.5	307.9	306.5	305.0	303.6	302.2	303.6	305.0	306.5
122.5°	333.0	331.1	329.2	327.5	326.0	324.5	323.0	321.4	323.0	324.5	326.0
125°	361.1	359.3	357.4	355.9	354.7	353.5	352.1	350.9	352.1	353.5	354.7
127.5°	387.2	385.9	384.5	383.1	381.7	380.3	379.0	377.6	379.0	380.3	381.7
130°	404.0	403.0	401.9	400.6	399.1	397.6	396.1	394.6	396.1	397.6	399.1
132.5°	420.3	419.2	418.2	417.0	415.7	414.3	413.0	411.8	413.0	414.3	415.7
135°	443.3	442.4	441.5	440.4	438.8	437.3	435.8	434.2	435.8	437.3	438.8
137.5°	464.2	463.2	462.2	461.2	460.2	459.1	458.0	457.0	458.0	459.1	460.2
140°	477.9	476.9	475.7	474.8	474.0	473.3	472.5	471.8	472.5	473.3	474.0
142.5°	490.3	489.1	488.0	487.0	486.3	485.5	484.9	484.2	484.9	485.5	486.3
145°	507.4	505.7	504.1	503.3	503.4	503.5	503.6	503.7	503.6	503.5	503.4
147.5°	523.1	521.5	519.9	519.3	519.7	520.0	520.4	520.7	520.4	520.0	519.7
150°	532.6	531.1	529.5	529.1	529.8	530.4	531.1	531.8	531.1	530.4	529.8
152.5°	541.4	539.9	538.5	538.1	538.9	539.6	540.4	541.1	540.4	539.6	538.9
155°	553.6	552.5	551.4	551.2	552.1	552.9	553.8	554.6	553.8	552.9	552.1
157.5°	564.0	563.2	562.4	562.4	563.1	563.8	564.5	565.2	564.5	563.8	563.1
160°	570.4	569.8	569.2	569.2	569.8	570.4	570.9	571.5	570.9	570.4	569.8
162.5°	575.6	575.1	574.7	574.7	575.3	575.8	576.4	577.0	576.4	575.8	575.3
165°	582.6	582.3	582.0	582.1	582.7	583.3	583.9	584.4	583.9	583.3	582.7
167.5°	588.0	587.7	587.5	587.6	588.2	588.9	589.4	590.0	589.4	588.9	588.2
170°	591.0	590.8	590.6	590.8	591.4	591.9	592.5	593.1	592.5	591.9	591.4
172.5°	593.0	592.8	592.7	592.8	593.4	594.0	594.6	595.1	594.6	594.0	593.4
175°	595.3	595.1	594.9	595.1	595.8	596.4	597.1	597.8	597.1	596.4	595.8
177.5°	596.0	595.9	595.8	596.1	596.6	597.1	597.7	598.2	597.7	597.1	596.6
180°	596.5	596.5	596.5	596.5	596.5	596.5	596.5	596.5	596.5	596.5	596.5



TEST NUMBER: P331765-840

CATALOG NUMBER: S122RDIW-S290D435U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	660.1	660.1	660.1	660.1	660.1	660.1	660.1	660.1	660.1	660.1	660.1
2.5°	650.9	649.5	647.1	643.5	641.3	637.4	634.9	636.3	636.7	636.3	636.0
5°	633.4	628.5	621.9	615.4	609.5	603.1	599.4	597.8	594.6	592.8	591.8
7.5°	612.2	603.9	594.5	583.3	573.8	563.8	558.8	556.2	549.7	546.1	543.0
10°	596.4	583.3	573.9	559.3	550.3	537.2	528.3	528.6	519.6	514.5	510.9
12.5°	579.0	564.6	549.0	535.7	523.3	512.8	502.0	497.7	488.2	483.3	473.4
15°	550.1	533.3	516.8	499.0	486.4	470.0	454.4	435.4	420.0	406.7	403.0
17.5°	518.6	497.8	481.2	460.2	438.6	411.2	393.1	382.0	372.8	365.8	360.5
20°	496.9	475.7	458.1	426.5	397.3	378.7	365.5	356.9	347.3	339.7	335.6
22.5°	474.1	452.1	428.0	392.6	369.9	355.1	343.3	333.5	326.9	321.0	317.2
25°	441.8	417.7	378.0	353.8	335.4	319.7	311.5	305.6	298.7	290.6	287.0
27.5°	407.7	369.4	340.8	322.8	305.3	295.2	287.7	278.8	272.7	269.0	265.2
30°	382.1	343.9	321.6	301.8	289.5	278.2	269.5	264.5	258.5	252.4	249.8
32.5°	353.8	323.2	301.7	285.4	272.8	263.2	256.3	248.1	243.9	240.0	234.8
35°	318.4	295.2	275.7	262.5	250.4	242.7	234.7	229.8	222.1	218.8	216.8
37.5°	288.5	268.4	253.9	239.8	230.4	221.8	216.8	209.1	205.8	201.3	196.9
40°	271.6	251.9	237.9	226.4	215.8	209.4	203.3	197.0	192.0	190.0	184.7
42.5°	254.4	238.3	224.3	211.8	204.7	197.8	190.1	185.5	180.3	176.9	173.7
45°	230.6	216.3	204.4	194.1	186.2	179.2	174.1	166.5	163.6	156.9	154.1
47.5°	209.6	196.4	185.0	175.2	167.6	163.0	155.6	149.7	144.9	140.8	137.2
50°	194.8	183.7	172.7	164.0	157.1	150.5	142.9	140.0	132.6	130.5	128.5
52.5°	181.2	170.7	160.7	152.1	145.2	138.8	132.1	128.2	123.2	121.2	119.7
55°	162.2	152.1	142.5	134.9	128.1	121.4	117.2	112.4	110.1	108.5	106.6
57.5°	143.1	134.0	126.6	119.0	112.0	106.7	102.0	99.1	96.7	94.6	92.4
60°	131.0	122.3	115.6	108.5	101.4	97.0	93.4	89.9	87.2	83.9	83.0
62.5°	118.2	110.5	104.4	97.5	91.3	87.4	83.8	80.6	77.3	72.6	71.3
65°	100.5	94.5	88.1	82.3	76.9	72.9	67.9	64.2	62.8	62.4	62.2
67.5°	84.5	78.9	73.3	67.5	62.5	58.9	56.2	55.7	54.7	54.5	53.8
70°	73.8	68.6	63.1	57.6	52.7	52.1	51.2	50.2	49.1	48.7	48.2
72.5°	64.3	58.9	53.3	49.0	46.9	46.0	45.1	44.1	43.4	42.9	42.7
75°	49.3	44.2	40.6	39.0	37.9	37.2	35.7	35.1	34.6	33.9	33.7
77.5°	35.5	32.6	31.0	30.0	28.8	28.1	27.3	26.6	26.1	26.0	25.5
80°	27.1	25.7	24.5	23.1	22.7	21.8	21.6	20.9	21.1	20.4	20.4
82.5°	21.0	19.3	18.3	17.7	17.2	16.5	16.3	16.0	16.0	15.5	15.5
85°	10.8	10.3	9.9	9.4	9.4	8.7	9.0	8.7	8.7	8.3	8.1
87.5°	4.4	4.4	4.2	4.3	4.5	4.4	4.5	4.4	4.5	4.6	4.5
90°	4.6	5.6	6.4	7.1	7.9	8.6	9.1	9.6	10.1	10.5	10.9
92.5°	8.4	8.5	8.9	9.3	9.6	10.0	10.3	10.5	10.8	11.0	11.2
95°	15.3	14.1	14.8	15.5	16.2	16.9	17.3	17.8	18.3	18.8	19.0
97.5°	20.0	16.4	17.9	19.4	21.0	22.5	22.9	23.3	23.7	24.0	24.3
100°	23.8	18.1	19.7	21.3	22.9	24.6	25.3	26.2	26.9	27.7	28.2
102.5°	88.1	79.9	66.2	52.6	39.0	25.2	26.3	27.3	28.3	29.3	29.9
105°	142.7	131.1	104.9	78.7	52.5	26.4	27.4	28.5	29.5	30.6	31.3
107.5°	177.0	162.5	131.1	99.7	68.3	36.9	35.7	34.7	33.6	32.5	32.2
110°	199.2	186.4	158.6	131.0	103.2	75.5	65.9	56.4	46.8	37.2	32.5



TEST NUMBER: P331765-840

CATALOG NUMBER: S122RDIW-S290D435U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	220.5	217.9	211.1	204.2	197.3	190.6	155.5	120.6	85.5	50.6	33.2
115°	254.7	256.7	259.1	261.6	263.9	266.3	221.9	177.5	133.1	88.7	63.0
117.5°	286.6	288.4	290.0	291.6	293.4	295.0	284.3	273.5	262.8	252.0	235.3
120°	307.9	309.5	311.2	313.0	314.7	316.4	317.5	318.7	319.8	321.0	315.1
122.5°	327.5	329.2	331.1	333.0	334.9	336.8	337.5	338.1	338.8	339.5	338.6
125°	355.9	357.4	359.3	361.1	362.9	364.8	365.4	366.1	366.8	367.4	367.9
127.5°	383.1	384.5	385.9	387.2	388.6	389.9	390.9	391.9	392.8	393.8	394.4
130°	400.6	401.9	403.0	404.0	405.2	406.2	407.2	408.3	409.3	410.4	410.9
132.5°	417.0	418.2	419.2	420.3	421.3	422.4	423.3	424.2	425.1	426.0	426.4
135°	440.4	441.5	442.4	443.3	444.1	445.0	446.0	447.0	447.9	448.9	449.2
137.5°	461.2	462.2	463.2	464.2	465.1	466.2	467.1	468.1	469.0	469.9	470.2
140°	474.8	475.7	476.9	477.9	478.9	480.0	480.8	481.7	482.6	483.4	483.6
142.5°	487.0	488.0	489.1	490.3	491.5	492.7	493.5	494.3	495.1	495.9	496.0
145°	503.3	504.1	505.7	507.4	509.0	510.6	511.3	512.0	512.6	513.3	513.4
147.5°	519.3	519.9	521.5	523.1	524.7	526.3	526.8	527.4	527.9	528.4	528.4
150°	529.1	529.5	531.1	532.6	534.1	535.6	536.2	536.8	537.3	538.0	538.1
152.5°	538.1	538.5	539.9	541.4	542.8	544.3	544.8	545.4	546.0	546.6	546.5
155°	551.2	551.4	552.5	553.6	554.8	555.9	556.5	557.1	557.6	558.3	558.2
157.5°	562.4	562.4	563.2	564.0	564.8	565.6	566.2	566.9	567.5	568.3	568.2
160°	569.2	569.2	569.8	570.4	570.9	571.5	572.1	572.6	573.2	573.8	573.7
162.5°	574.7	574.7	575.1	575.6	576.1	576.6	577.3	577.9	578.7	579.3	579.2
165°	582.1	582.0	582.3	582.6	582.9	583.1	583.8	584.5	585.1	585.8	585.8
167.5°	587.6	587.5	587.7	588.0	588.3	588.5	589.3	590.0	590.6	591.3	591.2
170°	590.8	590.6	590.8	591.0	591.2	591.4	592.0	592.7	593.4	594.0	593.9
172.5°	592.8	592.7	592.8	593.0	593.2	593.4	594.1	594.7	595.4	596.1	596.0
175°	595.1	594.9	595.1	595.3	595.4	595.6	596.3	597.0	597.6	598.3	598.2
177.5°	596.1	595.8	595.9	596.0	596.1	596.1	596.7	597.2	597.7	598.3	598.2
180°	596.5	596.5	596.5	596.5	596.5	596.5	596.5	596.5	596.5	596.5	596.5



TEST NUMBER: P331765-840

CATALOG NUMBER: S122RDIW-S290D435U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	660.1	660.1	660.1	660.1	660.1	660.1	660.1	660.1	660.1	660.1	660.1
2.5°	634.0	634.3	633.8	634.1	633.8	634.3	634.0	636.0	636.3	636.7	636.3
5°	590.7	587.9	587.4	586.8	587.4	587.9	590.7	591.8	592.8	594.6	597.8
7.5°	539.1	538.7	537.5	535.8	537.5	538.7	539.1	543.0	546.1	549.7	556.2
10°	505.8	504.6	504.4	502.8	504.4	504.6	505.8	510.9	514.5	519.6	528.6
12.5°	466.9	459.5	458.8	454.7	458.8	459.5	466.9	473.4	483.3	488.2	497.7
15°	397.6	396.2	391.5	388.6	391.5	396.2	397.6	403.0	406.7	420.0	435.4
17.5°	357.9	353.4	351.9	351.3	351.9	353.4	357.9	360.5	365.8	372.8	382.0
20°	332.3	328.3	327.6	327.1	327.6	328.3	332.3	335.6	339.7	347.3	356.9
22.5°	314.8	310.4	308.7	307.3	308.7	310.4	314.8	317.2	321.0	326.9	333.5
25°	284.7	283.1	282.2	281.7	282.2	283.1	284.7	287.0	290.6	298.7	305.6
27.5°	261.2	257.6	256.9	255.7	256.9	257.6	261.2	265.2	269.0	272.7	278.8
30°	247.7	246.6	245.0	243.6	245.0	246.6	247.7	249.8	252.4	258.5	264.5
32.5°	232.0	231.0	229.5	228.9	229.5	231.0	232.0	234.8	240.0	243.9	248.1
35°	214.5	211.3	209.8	207.8	209.8	211.3	214.5	216.8	218.8	222.1	229.8
37.5°	196.0	194.3	192.4	193.1	192.4	194.3	196.0	196.9	201.3	205.8	209.1
40°	181.7	180.6	180.1	179.9	180.1	180.6	181.7	184.7	190.0	192.0	197.0
42.5°	170.3	167.1	165.9	165.9	165.9	167.1	170.3	173.7	176.9	180.3	185.5
45°	153.0	150.1	147.9	148.1	147.9	150.1	153.0	154.1	156.9	163.6	166.5
47.5°	135.3	135.2	133.9	134.3	133.9	135.2	135.3	137.2	140.8	144.9	149.7
50°	126.8	125.5	124.5	124.8	124.5	125.5	126.8	128.5	130.5	132.6	140.0
52.5°	118.8	117.5	116.8	117.9	116.8	117.5	118.8	119.7	121.2	123.2	128.2
55°	105.5	104.1	103.9	103.7	103.9	104.1	105.5	106.6	108.5	110.1	112.4
57.5°	90.7	89.8	88.4	87.9	88.4	89.8	90.7	92.4	94.6	96.7	99.1
60°	80.1	78.3	75.9	75.7	75.9	78.3	80.1	83.0	83.9	87.2	89.9
62.5°	70.3	70.0	69.5	69.5	69.5	70.0	70.3	71.3	72.6	77.3	80.6
65°	61.7	61.5	61.7	61.9	61.7	61.5	61.7	62.2	62.4	62.8	64.2
67.5°	53.7	53.3	52.9	53.1	52.9	53.3	53.7	53.8	54.5	54.7	55.7
70°	47.7	47.5	47.3	47.3	47.3	47.5	47.7	48.2	48.7	49.1	50.2
72.5°	41.8	41.8	41.6	41.4	41.6	41.8	41.8	42.7	42.9	43.4	44.1
75°	33.5	33.0	33.0	33.0	33.0	33.0	33.5	33.7	33.9	34.6	35.1
77.5°	25.5	25.2	25.0	24.8	25.0	25.2	25.5	25.5	26.0	26.1	26.6
80°	20.2	20.0	19.7	19.7	19.7	20.0	20.2	20.4	20.4	21.1	20.9
82.5°	15.5	15.1	15.1	14.9	15.1	15.1	15.5	15.5	15.5	16.0	16.0
85°	8.3	8.5	8.3	8.7	8.3	8.5	8.3	8.1	8.3	8.7	8.7
87.5°	4.6	4.4	4.6	4.5	4.6	4.4	4.6	4.5	4.6	4.5	4.4
90°	11.1	11.3	11.5	11.6	11.5	11.3	11.1	10.9	10.5	10.1	9.6
92.5°	11.3	11.4	11.5	11.6	11.5	11.4	11.3	11.2	11.0	10.8	10.5
95°	18.9	18.8	18.7	18.6	18.7	18.8	18.9	19.0	18.8	18.3	17.8
97.5°	24.4	24.5	24.6	24.7	24.6	24.5	24.4	24.3	24.0	23.7	23.3
100°	28.4	28.6	28.7	28.9	28.7	28.6	28.4	28.2	27.7	26.9	26.2
102.5°	30.2	30.5	30.7	31.0	30.7	30.5	30.2	29.9	29.3	28.3	27.3
105°	31.6	32.0	32.4	32.8	32.4	32.0	31.6	31.3	30.6	29.5	28.5
107.5°	32.6	33.0	33.3	33.7	33.3	33.0	32.6	32.2	32.5	33.6	34.7
110°	32.9	33.3	33.7	34.1	33.7	33.3	32.9	32.5	37.2	46.8	56.4



TEST NUMBER: P331765-840

CATALOG NUMBER: S122RDIW-S290D435U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	33.5	33.8	34.1	34.4	34.1	33.8	33.5	33.2	50.6	85.5	120.6
115°	56.1	49.2	42.3	35.3	42.3	49.2	56.1	63.0	88.7	133.1	177.5
117.5°	212.6	189.9	167.2	144.5	167.2	189.9	212.6	235.3	252.0	262.8	273.5
120°	302.2	289.2	276.2	263.3	276.2	289.2	302.2	315.1	321.0	319.8	318.7
122.5°	336.1	333.6	331.0	328.5	331.0	333.6	336.1	338.6	339.5	338.8	338.1
125°	368.2	368.5	368.8	369.0	368.8	368.5	368.2	367.9	367.4	366.8	366.1
127.5°	394.5	394.5	394.6	394.6	394.6	394.5	394.5	394.4	393.8	392.8	391.9
130°	410.8	410.7	410.6	410.5	410.6	410.7	410.8	410.9	410.4	409.3	408.3
132.5°	426.3	426.2	426.2	426.1	426.2	426.2	426.3	426.4	426.0	425.1	424.2
135°	449.1	448.9	448.7	448.5	448.7	448.9	449.1	449.2	448.9	447.9	447.0
137.5°	469.9	469.6	469.3	468.9	469.3	469.6	469.9	470.2	469.9	469.0	468.1
140°	483.1	482.6	482.2	481.7	482.2	482.6	483.1	483.6	483.4	482.6	481.7
142.5°	495.5	495.1	494.6	494.1	494.6	495.1	495.5	496.0	495.9	495.1	494.3
145°	512.9	512.4	512.0	511.5	512.0	512.4	512.9	513.4	513.3	512.6	512.0
147.5°	528.0	527.6	527.1	526.7	527.1	527.6	528.0	528.4	528.4	527.9	527.4
150°	537.6	537.0	536.5	536.1	536.5	537.0	537.6	538.1	538.0	537.3	536.8
152.5°	545.9	545.3	544.6	544.0	544.6	545.3	545.9	546.5	546.6	546.0	545.4
155°	557.3	556.6	555.8	555.1	555.8	556.6	557.3	558.2	558.3	557.6	557.1
157.5°	567.4	566.6	565.9	565.2	565.9	566.6	567.4	568.2	568.3	567.5	566.9
160°	573.1	572.4	571.7	571.1	571.7	572.4	573.1	573.7	573.8	573.2	572.6
162.5°	578.3	577.5	576.7	575.9	576.7	577.5	578.3	579.2	579.3	578.7	577.9
165°	585.1	584.5	583.8	583.1	583.8	584.5	585.1	585.8	585.8	585.1	584.5
167.5°	590.3	589.5	588.5	587.7	588.5	589.5	590.3	591.2	591.3	590.6	590.0
170°	593.1	592.2	591.4	590.5	591.4	592.2	593.1	593.9	594.0	593.4	592.7
172.5°	595.1	594.3	593.4	592.6	593.4	594.3	595.1	596.0	596.1	595.4	594.7
175°	597.2	596.3	595.3	594.4	595.3	596.3	597.2	598.2	598.3	597.6	597.0
177.5°	597.5	596.8	596.1	595.5	596.1	596.8	597.5	598.2	598.3	597.7	597.2
180°	596.5	596.5	596.5	596.5	596.5	596.5	596.5	596.5	596.5	596.5	596.5



TEST NUMBER: P331765-840

CATALOG NUMBER: S122RDIW-S290D435U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	660.1	660.1	660.1	660.1	660.1	660.1	660.1	660.1	660.1	660.1	660.1
2.5°	634.9	637.4	641.3	643.5	647.1	649.5	650.9	653.2	654.5	659.1	663.9
5°	599.4	603.1	609.5	615.4	621.9	628.5	633.4	638.8	643.9	652.6	661.8
7.5°	558.8	563.8	573.8	583.3	594.5	603.9	612.2	621.6	630.0	642.5	655.5
10°	528.3	537.2	550.3	559.3	573.9	583.3	596.4	606.7	618.4	635.0	649.6
12.5°	502.0	512.8	523.3	535.7	549.0	564.6	579.0	592.3	606.1	623.2	640.5
15°	454.4	470.0	486.4	499.0	516.8	533.3	550.1	567.9	584.9	605.4	627.8
17.5°	393.1	411.2	438.6	460.2	481.2	497.8	518.6	540.2	560.2	584.8	609.9
20°	365.5	378.7	397.3	426.5	458.1	475.7	496.9	520.7	543.6	570.5	597.3
22.5°	343.3	355.1	369.9	392.6	428.0	452.1	474.1	498.4	524.9	552.3	582.1
25°	311.5	319.7	335.4	353.8	378.0	417.7	441.8	466.2	495.0	524.4	558.4
27.5°	287.7	295.2	305.3	322.8	340.8	369.4	407.7	434.2	463.0	496.0	531.3
30°	269.5	278.2	289.5	301.8	321.6	343.9	382.1	412.9	441.3	475.3	512.9
32.5°	256.3	263.2	272.8	285.4	301.7	323.2	353.8	391.0	418.8	454.5	493.8
35°	234.7	242.7	250.4	262.5	275.7	295.2	318.4	358.3	385.9	421.1	460.6
37.5°	216.8	221.8	230.4	239.8	253.9	268.4	288.5	324.3	354.1	388.7	429.1
40°	203.3	209.4	215.8	226.4	237.9	251.9	271.6	298.2	332.3	366.4	405.8
42.5°	190.1	197.8	204.7	211.8	224.3	238.3	254.4	276.9	311.8	344.0	382.3
45°	174.1	179.2	186.2	194.1	204.4	216.3	230.6	250.2	283.8	311.5	347.5
47.5°	155.6	163.0	167.6	175.2	185.0	196.4	209.6	226.7	253.8	279.8	313.3
50°	142.9	150.5	157.1	164.0	172.7	183.7	194.8	211.3	233.1	260.3	291.5
52.5°	132.1	138.8	145.2	152.1	160.7	170.7	181.2	195.7	214.3	239.4	269.7
55°	117.2	121.4	128.1	134.9	142.5	152.1	162.2	174.3	190.4	211.5	236.0
57.5°	102.0	106.7	112.0	119.0	126.6	134.0	143.1	154.1	166.7	185.8	206.8
60°	93.4	97.0	101.4	108.5	115.6	122.3	131.0	140.2	152.1	168.6	186.5
62.5°	83.8	87.4	91.3	97.5	104.4	110.5	118.2	127.8	137.9	153.0	168.6
65°	67.9	72.9	76.9	82.3	88.1	94.5	100.5	108.3	117.2	129.2	143.1
67.5°	56.2	58.9	62.5	67.5	73.3	78.9	84.5	90.6	98.4	107.6	118.7
70°	51.2	52.1	52.7	57.6	63.1	68.6	73.8	79.6	86.2	93.8	103.4
72.5°	45.1	46.0	46.9	49.0	53.3	58.9	64.3	68.6	74.8	81.2	89.0
75°	35.7	37.2	37.9	39.0	40.6	44.2	49.3	53.4	57.2	61.9	68.2
77.5°	27.3	28.1	28.8	30.0	31.0	32.6	35.5	39.2	42.7	45.4	49.7
80°	21.6	21.8	22.7	23.1	24.5	25.7	27.1	30.1	33.5	34.6	37.7
82.5°	16.3	16.5	17.2	17.7	18.3	19.3	21.0	21.8	24.5	26.1	27.9
85°	9.0	8.7	9.4	9.4	9.9	10.3	10.8	11.9	12.6	14.4	14.9
87.5°	4.5	4.4	4.5	4.3	4.2	4.4	4.4	4.3	4.5	4.8	5.5
90°	9.1	8.6	7.9	7.1	6.4	5.6	4.6	3.6	2.5	1.5	0.4
92.5°	10.3	10.0	9.6	9.3	8.9	8.5	8.4	8.4	8.5	8.6	8.7
95°	17.3	16.9	16.2	15.5	14.8	14.1	15.3	18.6	21.7	24.8	28.1
97.5°	22.9	22.5	21.0	19.4	17.9	16.4	20.0	28.9	37.9	46.8	55.6
100°	25.3	24.6	22.9	21.3	19.7	18.1	23.8	37.0	50.1	63.2	76.4
102.5°	26.3	25.2	39.0	52.6	66.2	79.9	88.1	90.9	93.6	96.4	99.2
105°	27.4	26.4	52.5	78.7	104.9	131.1	142.7	139.9	136.9	134.1	131.2
107.5°	35.7	36.9	68.3	99.7	131.1	162.5	177.0	174.7	172.4	170.1	167.7
110°	65.9	75.5	103.2	131.0	158.6	186.4	199.2	197.2	195.2	193.2	191.2



TEST NUMBER: P331765-840

CATALOG NUMBER: S122RDIW-S290D435U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	155.5	190.6	197.3	204.2	211.1	217.9	220.5	218.6	216.9	215.1	213.3
115°	221.9	266.3	263.9	261.6	259.1	256.7	254.7	253.1	251.5	249.8	248.2
117.5°	284.3	295.0	293.4	291.6	290.0	288.4	286.6	284.8	283.0	281.1	279.3
120°	317.5	316.4	314.7	313.0	311.2	309.5	307.9	306.5	305.0	303.6	302.2
122.5°	337.5	336.8	334.9	333.0	331.1	329.2	327.5	326.0	324.5	323.0	321.4
125°	365.4	364.8	362.9	361.1	359.3	357.4	355.9	354.7	353.5	352.1	350.9
127.5°	390.9	389.9	388.6	387.2	385.9	384.5	383.1	381.7	380.3	379.0	377.6
130°	407.2	406.2	405.2	404.0	403.0	401.9	400.6	399.1	397.6	396.1	394.6
132.5°	423.3	422.4	421.3	420.3	419.2	418.2	417.0	415.7	414.3	413.0	411.8
135°	446.0	445.0	444.1	443.3	442.4	441.5	440.4	438.8	437.3	435.8	434.2
137.5°	467.1	466.2	465.1	464.2	463.2	462.2	461.2	460.2	459.1	458.0	457.0
140°	480.8	480.0	478.9	477.9	476.9	475.7	474.8	474.0	473.3	472.5	471.8
142.5°	493.5	492.7	491.5	490.3	489.1	488.0	487.0	486.3	485.5	484.9	484.2
145°	511.3	510.6	509.0	507.4	505.7	504.1	503.3	503.4	503.5	503.6	503.7
147.5°	526.8	526.3	524.7	523.1	521.5	519.9	519.3	519.7	520.0	520.4	520.7
150°	536.2	535.6	534.1	532.6	531.1	529.5	529.1	529.8	530.4	531.1	531.8
152.5°	544.8	544.3	542.8	541.4	539.9	538.5	538.1	538.9	539.6	540.4	541.1
155°	556.5	555.9	554.8	553.6	552.5	551.4	551.2	552.1	552.9	553.8	554.6
157.5°	566.2	565.6	564.8	564.0	563.2	562.4	562.4	563.1	563.8	564.5	565.2
160°	572.1	571.5	570.9	570.4	569.8	569.2	569.2	569.8	570.4	570.9	571.5
162.5°	577.3	576.6	576.1	575.6	575.1	574.7	574.7	575.3	575.8	576.4	577.0
165°	583.8	583.1	582.9	582.6	582.3	582.0	582.1	582.7	583.3	583.9	584.4
167.5°	589.3	588.5	588.3	588.0	587.7	587.5	587.6	588.2	588.9	589.4	590.0
170°	592.0	591.4	591.2	591.0	590.8	590.6	590.8	591.4	591.9	592.5	593.1
172.5°	594.1	593.4	593.2	593.0	592.8	592.7	592.8	593.4	594.0	594.6	595.1
175°	596.3	595.6	595.4	595.3	595.1	594.9	595.1	595.8	596.4	597.1	597.8
177.5°	596.7	596.1	596.1	596.0	595.9	595.8	596.1	596.6	597.1	597.7	598.2
180°	596.5	596.5	596.5	596.5	596.5	596.5	596.5	596.5	596.5	596.5	596.5



TEST NUMBER: P331765-840

CATALOG NUMBER: S122RDIW-S290D435U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	660.1	660.1	660.1	660.1	660.1	660.1	660.1	660.1	660.1	660.1	660.1
2.5°	664.1	664.6	668.2	669.9	673.2	674.5	676.0	675.6	675.6	676.3	681.5
5°	665.5	670.0	676.9	683.6	690.0	695.5	699.2	702.9	704.3	710.8	716.8
7.5°	663.1	671.6	682.9	693.1	705.2	714.7	722.6	729.7	734.6	744.3	754.2
10°	659.9	671.9	684.7	697.8	714.6	727.2	740.0	749.9	753.1	767.5	775.8
12.5°	653.7	669.6	686.0	703.0	719.3	736.7	750.8	760.7	772.0	785.0	800.2
15°	644.4	662.7	684.1	705.8	729.2	750.3	765.5	782.6	795.1	809.3	822.6
17.5°	631.0	654.6	681.7	706.9	734.0	756.6	777.5	794.0	802.6	810.8	812.7
20°	620.3	645.7	677.6	707.4	734.5	760.6	781.3	795.1	797.4	797.6	785.5
22.5°	608.7	637.5	670.9	701.4	733.8	762.9	778.9	784.8	775.7	760.1	736.6
25°	587.4	620.8	659.5	694.4	729.7	757.2	762.8	752.5	720.5	687.0	644.6
27.5°	564.4	601.9	643.4	682.2	719.8	736.9	725.0	687.7	630.4	580.4	519.9
30°	547.5	589.6	630.4	673.7	708.6	715.9	688.6	633.8	566.8	491.6	431.2
32.5°	528.3	572.3	617.1	662.0	691.2	684.0	638.9	571.4	492.9	418.9	361.9
35°	500.8	546.1	594.6	639.5	658.1	627.1	559.7	471.8	391.5	322.6	283.3
37.5°	469.0	518.5	568.8	610.1	608.7	557.1	465.2	374.6	307.1	266.2	238.3
40°	446.4	496.4	550.8	585.6	570.8	503.5	403.9	318.4	269.0	236.5	216.1
42.5°	424.7	474.9	529.0	556.6	530.7	448.1	348.9	281.9	241.2	215.8	199.2
45°	387.9	440.9	490.9	506.2	459.9	368.9	282.2	233.5	206.4	187.6	176.2
47.5°	351.8	404.0	449.7	449.9	387.3	299.1	238.0	202.1	178.9	164.4	156.1
50°	329.8	379.4	417.7	411.7	340.6	266.1	212.9	181.9	162.7	151.4	142.7
52.5°	305.1	353.1	386.4	369.4	301.1	234.2	190.3	164.3	148.3	138.6	130.8
55°	269.0	311.7	335.2	309.4	245.7	194.8	160.8	140.4	128.5	120.2	113.5
57.5°	233.7	268.9	283.6	253.7	202.4	161.5	136.0	120.7	108.9	102.9	99.5
60°	211.5	241.6	251.9	218.8	175.9	141.3	120.5	106.2	97.5	93.6	90.2
62.5°	189.7	214.2	218.4	188.2	153.4	123.7	105.7	93.7	88.0	84.2	81.0
65°	157.3	175.0	173.0	148.7	121.4	98.2	85.1	77.8	73.4	68.2	62.4
67.5°	129.6	140.4	133.8	115.6	92.6	76.3	67.8	62.2	56.8	51.8	50.5
70°	111.9	118.2	111.3	94.5	75.9	64.0	57.2	50.5	47.3	46.2	44.0
72.5°	95.0	97.3	89.8	75.4	61.8	53.0	46.3	42.6	40.8	39.9	38.6
75°	71.3	69.8	63.3	52.1	42.9	37.0	34.8	33.5	32.3	31.4	30.7
77.5°	50.1	47.8	42.0	34.6	29.9	27.1	25.8	25.0	24.5	24.0	23.3
80°	37.7	36.1	30.3	24.7	22.7	21.3	20.6	19.7	19.7	19.3	18.6
82.5°	27.6	25.8	20.7	18.2	17.1	16.2	15.7	15.1	14.9	15.0	14.5
85°	14.4	11.7	10.3	9.9	9.2	8.7	9.0	8.5	8.5	8.5	8.3
87.5°	4.7	4.0	4.0	4.0	4.4	4.5	4.5	4.6	5.0	4.9	5.3
90°	1.5	2.5	3.6	4.6	5.6	6.4	7.1	7.9	8.6	9.1	9.6
92.5°	8.6	8.5	8.4	8.4	8.5	8.9	9.3	9.6	10.0	10.3	10.5
95°	24.8	21.7	18.6	15.3	14.1	14.8	15.5	16.2	16.9	17.3	17.8
97.5°	46.8	37.9	28.9	20.0	16.4	17.9	19.4	21.0	22.5	22.9	23.3
100°	63.2	50.1	37.0	23.8	18.1	19.7	21.3	22.9	24.6	25.3	26.2
102.5°	96.4	93.6	90.9	88.1	79.9	66.2	52.6	39.0	25.2	26.3	27.3
105°	134.1	136.9	139.9	142.7	131.1	104.9	78.7	52.5	26.4	27.4	28.5
107.5°	170.1	172.4	174.7	177.0	162.5	131.1	99.7	68.3	36.9	35.7	34.7
110°	193.2	195.2	197.2	199.2	186.4	158.6	131.0	103.2	75.5	65.9	56.4



TEST NUMBER: P331765-840

CATALOG NUMBER: S122RDIW-S290D435U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	215.1	216.9	218.6	220.5	217.9	211.1	204.2	197.3	190.6	155.5	120.6
115°	249.8	251.5	253.1	254.7	256.7	259.1	261.6	263.9	266.3	221.9	177.5
117.5°	281.1	283.0	284.8	286.6	288.4	290.0	291.6	293.4	295.0	284.3	273.5
120°	303.6	305.0	306.5	307.9	309.5	311.2	313.0	314.7	316.4	317.5	318.7
122.5°	323.0	324.5	326.0	327.5	329.2	331.1	333.0	334.9	336.8	337.5	338.1
125°	352.1	353.5	354.7	355.9	357.4	359.3	361.1	362.9	364.8	365.4	366.1
127.5°	379.0	380.3	381.7	383.1	384.5	385.9	387.2	388.6	389.9	390.9	391.9
130°	396.1	397.6	399.1	400.6	401.9	403.0	404.0	405.2	406.2	407.2	408.3
132.5°	413.0	414.3	415.7	417.0	418.2	419.2	420.3	421.3	422.4	423.3	424.2
135°	435.8	437.3	438.8	440.4	441.5	442.4	443.3	444.1	445.0	446.0	447.0
137.5°	458.0	459.1	460.2	461.2	462.2	463.2	464.2	465.1	466.2	467.1	468.1
140°	472.5	473.3	474.0	474.8	475.7	476.9	477.9	478.9	480.0	480.8	481.7
142.5°	484.9	485.5	486.3	487.0	488.0	489.1	490.3	491.5	492.7	493.5	494.3
145°	503.6	503.5	503.4	503.3	504.1	505.7	507.4	509.0	510.6	511.3	512.0
147.5°	520.4	520.0	519.7	519.3	519.9	521.5	523.1	524.7	526.3	526.8	527.4
150°	531.1	530.4	529.8	529.1	529.5	531.1	532.6	534.1	535.6	536.2	536.8
152.5°	540.4	539.6	538.9	538.1	538.5	539.9	541.4	542.8	544.3	544.8	545.4
155°	553.8	552.9	552.1	551.2	551.4	552.5	553.6	554.8	555.9	556.5	557.1
157.5°	564.5	563.8	563.1	562.4	562.4	563.2	564.0	564.8	565.6	566.2	566.9
160°	570.9	570.4	569.8	569.2	569.2	569.8	570.4	570.9	571.5	572.1	572.6
162.5°	576.4	575.8	575.3	574.7	574.7	575.1	575.6	576.1	576.6	577.3	577.9
165°	583.9	583.3	582.7	582.1	582.0	582.3	582.6	582.9	583.1	583.8	584.5
167.5°	589.4	588.9	588.2	587.6	587.5	587.7	588.0	588.3	588.5	589.3	590.0
170°	592.5	591.9	591.4	590.8	590.6	590.8	591.0	591.2	591.4	592.0	592.7
172.5°	594.6	594.0	593.4	592.8	592.7	592.8	593.0	593.2	593.4	594.1	594.7
175°	597.1	596.4	595.8	595.1	594.9	595.1	595.3	595.4	595.6	596.3	597.0
177.5°	597.7	597.1	596.6	596.1	595.8	595.9	596.0	596.1	596.1	596.7	597.2
180°	596.5	596.5	596.5	596.5	596.5	596.5	596.5	596.5	596.5	596.5	596.5



TEST NUMBER: P331765-840

CATALOG NUMBER: S122RDIW-S290D435U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	660.1	660.1	660.1	660.1	660.1	660.1	660.1
2.5°	683.3	685.7	686.8	686.8	688.1	687.5	687.0
5°	722.6	726.9	727.9	732.0	735.0	734.1	734.5
7.5°	761.6	768.6	775.6	778.7	779.2	781.0	781.7
10°	785.7	791.4	802.1	800.6	808.6	813.2	805.7
12.5°	808.8	816.6	824.0	826.1	830.6	832.1	829.1
15°	829.7	833.8	834.2	833.1	834.6	833.3	829.0
17.5°	810.2	803.4	789.9	783.5	778.4	770.8	767.8
20°	777.9	758.1	735.2	726.0	715.3	694.2	699.2
22.5°	708.1	685.7	662.7	635.9	623.1	603.1	601.9
25°	599.7	560.9	518.2	488.4	470.9	451.0	442.2
27.5°	466.3	417.4	382.4	364.8	348.6	332.9	332.1
30°	378.5	341.8	314.8	299.6	289.7	283.1	284.5
32.5°	319.0	293.9	275.6	263.1	255.8	250.7	250.6
35°	260.8	243.6	231.9	226.6	221.4	217.7	217.9
37.5°	223.2	212.9	206.3	200.6	197.2	195.4	194.4
40°	203.9	195.4	190.4	186.9	184.2	181.7	181.2
42.5°	188.7	181.7	176.6	173.9	171.4	169.6	169.2
45°	167.4	161.7	157.1	154.1	153.0	151.4	151.4
47.5°	149.0	143.3	139.8	137.8	135.9	134.8	134.8
50°	136.5	132.1	129.0	127.7	126.1	125.5	125.2
52.5°	125.3	122.0	119.8	119.0	118.3	117.4	117.5
55°	110.1	108.3	107.3	106.6	105.5	104.1	105.0
57.5°	97.4	95.7	93.3	91.1	90.1	89.1	89.5
60°	88.4	85.1	81.9	79.4	78.7	76.6	76.6
62.5°	77.0	72.4	68.5	67.1	66.3	65.4	65.2
65°	59.2	57.4	56.5	55.5	55.0	55.0	54.6
67.5°	49.1	48.3	47.3	47.1	46.7	46.5	46.4
70°	43.3	42.4	42.0	41.7	41.3	41.5	40.8
72.5°	37.9	37.2	37.1	36.5	36.2	36.2	35.6
75°	29.8	29.8	29.6	29.4	28.9	28.7	28.9
77.5°	22.9	23.0	22.6	22.5	22.5	22.5	22.3
80°	18.4	18.6	18.4	18.1	17.9	18.1	17.9
82.5°	14.5	14.1	14.1	14.0	14.0	13.9	13.8
85°	8.3	8.5	8.3	8.1	8.1	8.1	8.3
87.5°	5.2	5.3	5.3	5.4	5.4	5.5	5.3
90°	10.1	10.5	10.9	11.1	11.3	11.5	11.6
92.5°	10.8	11.0	11.2	11.3	11.4	11.5	11.6
95°	18.3	18.8	19.0	18.9	18.8	18.7	18.6
97.5°	23.7	24.0	24.3	24.4	24.5	24.6	24.7
100°	26.9	27.7	28.2	28.4	28.6	28.7	28.9
102.5°	28.3	29.3	29.9	30.2	30.5	30.7	31.0
105°	29.5	30.6	31.3	31.6	32.0	32.4	32.8
107.5°	33.6	32.5	32.2	32.6	33.0	33.3	33.7
110°	46.8	37.2	32.5	32.9	33.3	33.7	34.1



TEST NUMBER: P331765-840

CATALOG NUMBER: S122RDIW-S290D435U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	85.5	50.6	33.2	33.5	33.8	34.1	34.4
115°	133.1	88.7	63.0	56.1	49.2	42.3	35.3
117.5°	262.8	252.0	235.3	212.6	189.9	167.2	144.5
120°	319.8	321.0	315.1	302.2	289.2	276.2	263.3
122.5°	338.8	339.5	338.6	336.1	333.6	331.0	328.5
125°	366.8	367.4	367.9	368.2	368.5	368.8	369.0
127.5°	392.8	393.8	394.4	394.5	394.5	394.6	394.6
130°	409.3	410.4	410.9	410.8	410.7	410.6	410.5
132.5°	425.1	426.0	426.4	426.3	426.2	426.2	426.1
135°	447.9	448.9	449.2	449.1	448.9	448.7	448.5
137.5°	469.0	469.9	470.2	469.9	469.6	469.3	468.9
140°	482.6	483.4	483.6	483.1	482.6	482.2	481.7
142.5°	495.1	495.9	496.0	495.5	495.1	494.6	494.1
145°	512.6	513.3	513.4	512.9	512.4	512.0	511.5
147.5°	527.9	528.4	528.4	528.0	527.6	527.1	526.7
150°	537.3	538.0	538.1	537.6	537.0	536.5	536.1
152.5°	546.0	546.6	546.5	545.9	545.3	544.6	544.0
155°	557.6	558.3	558.2	557.3	556.6	555.8	555.1
157.5°	567.5	568.3	568.2	567.4	566.6	565.9	565.2
160°	573.2	573.8	573.7	573.1	572.4	571.7	571.1
162.5°	578.7	579.3	579.2	578.3	577.5	576.7	575.9
165°	585.1	585.8	585.8	585.1	584.5	583.8	583.1
167.5°	590.6	591.3	591.2	590.3	589.5	588.5	587.7
170°	593.4	594.0	593.9	593.1	592.2	591.4	590.5
172.5°	595.4	596.1	596.0	595.1	594.3	593.4	592.6
175°	597.6	598.3	598.2	597.2	596.3	595.3	594.4
177.5°	597.7	598.3	598.2	597.5	596.8	596.1	595.5
180°	596.5	596.5	596.5	596.5	596.5	596.5	596.5

(END OF REPORT)