

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332449-927

Luminaire Tested: **S123RDIW-S775D1535U927-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P332449-927  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-9,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S123RDIW-S775D1535U927-4F0-1E-UDD-F1  
Description: DEFINE 3 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 775 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED  
HOUSING  
UPLIGHT 1535 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 6528.3 lumens  
Efficiency: N/A  
Efficacy: 95.9 lumens/watt  
Spacing Criteria (0/90/45): 1.21 / 1.06 / 1.22  
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')  
CIE Type: Semi-Indirect


Input Watts (W): 68.1  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332449-927

CATALOG NUMBER: S123RDIW-S775D1535U927-4F0-1E-UDD-F1

### Luminous Intensity Polar Plot





TEST NUMBER: P332449-927

CATALOG NUMBER: S123RDIW-S775D1535U927-4F0-1E-UDD-F1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	104	104	104	104	94	94	94	94	75	75	75	58	58	58	43	43	43
1	95	91	87	84	86	82	79	76	66	64	62	52	50	49	38	37	37
2	86	79	73	69	78	72	67	63	58	55	52	46	43	41	34	32	31
3	79	70	63	57	71	64	58	53	52	47	44	40	37	35	30	28	27
4	72	62	54	49	65	56	50	45	46	41	37	36	33	30	27	25	23
5	66	55	47	42	60	50	43	38	41	36	32	32	29	26	24	22	20
6	61	49	42	36	55	45	38	33	37	32	28	29	26	23	22	20	18
7	56	45	37	32	51	41	34	29	34	28	25	27	23	20	20	18	16
8	52	40	33	28	47	37	30	26	31	26	22	24	21	18	19	16	14
9	49	37	30	25	44	34	27	23	28	23	20	22	19	16	17	15	13
10	45	34	27	22	41	31	25	21	26	21	18	21	17	15	16	14	12

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	11009	11009	11009
5°	11051	10899	10962
10°	10989	10762	10726
15°	10871	10510	10399
20°	10709	10195	9958
25°	10542	9841	9526
30°	10320	9434	8918
35°	10093	9025	8360
40°	9884	8543	7669
45°	9608	8068	7046
50°	9306	7529	6348
55°	8997	6912	5697
60°	8714	6250	4982
65°	8344	5535	4266
70°	7884	4648	3446
75°	7207	3656	3244
80°	6428	3242	2982
85°	5434	2865	2655



TEST NUMBER: P332449-927

CATALOG NUMBER: S123RDIW-S775D1535U927-4F0-1E-UDD-F1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	96.0	1.5
10°-20°	267.2	4.1
20°-30°	384.8	5.9
30°-40°	433.4	6.6
40°-50°	414.6	6.4
50°-60°	339.6	5.2
60°-70°	229.1	3.5
70°-80°	115.3	1.8
80°-90°	35.0	0.5
90°-100°	99.1	1.5
100°-110°	296.5	4.5
110°-120°	504.3	7.7
120°-130°	663.4	10.2
130°-140°	745.6	11.4
140°-150°	732.9	11.2
150°-160°	617.0	9.5
160°-170°	410.7	6.3
170°-180°	143.8	2.2
0°-30°	748.0	11.5
0°-40°	1181.5	18.1
0°-60°	1935.6	29.7
0°-90°	2315.0	35.5
90°-120°	899.9	13.8
90°-150°	3041.8	46.6
90°-180°	4213.0	64.5
0°-180°	6528.3	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1023	1023	1023	1023	1023	
5°	1023	1018	1009	1016	1014	97
15°	976	966	943	939	933	275
25°	888	866	829	812	802	408
35°	768	737	687	652	636	481
45°	631	592	530	484	463	487
55°	479	437	368	322	304	430
65°	328	281	217	178	168	324
75°	173	133	88	80	78	185
85°	44	27	23	22	22	49
90°	1	13	29	33	36	7
95°	70	79	88	93	93	79
105°	269	272	282	282	284	288
115°	508	511	509	510	509	502
125°	743	746	744	739	735	662
135°	964	971	970	965	963	743
145°	1170	1172	1175	1174	1170	730
155°	1339	1339	1340	1344	1337	616
165°	1459	1455	1455	1461	1454	411
175°	1517	1513	1512	1519	1511	144
180°	1521	1521	1521	1521	1521	



TEST NUMBER: P332449-927

CATALOG NUMBER: S123RDIW-S775D1535U927-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1022.8	1022.8	1022.8	1022.8	1022.8	1022.8	1022.8	1022.8	1022.8	1022.8	1022.8
2.5°	1026.0	1025.5	1024.8	1024.3	1023.7	1022.5	1020.7	1019.0	1017.2	1015.4	1017.1
5°	1022.8	1021.8	1020.9	1020.0	1019.1	1017.5	1015.3	1013.0	1010.8	1008.7	1010.3
7.5°	1013.3	1012.3	1011.3	1010.3	1009.3	1007.3	1004.5	1001.6	998.8	995.9	996.8
10°	1005.4	1004.0	1002.7	1001.5	1000.1	997.8	994.5	991.3	987.9	984.6	984.8
12.5°	994.0	992.6	991.2	989.8	988.3	985.6	981.5	977.5	973.4	969.3	969.2
15°	975.5	973.4	971.4	969.4	967.3	963.8	958.6	953.5	948.2	943.1	942.2
17.5°	952.0	949.7	947.4	945.0	942.6	938.2	931.6	925.0	918.5	912.0	910.0
20°	934.9	931.8	928.9	926.0	923.1	918.1	911.0	904.0	897.1	890.0	887.6
22.5°	915.6	912.2	908.8	905.4	902.0	896.6	889.1	881.7	874.3	866.8	863.8
25°	887.6	883.0	878.3	873.7	869.1	862.5	854.1	845.6	837.1	828.6	824.7
27.5°	853.5	848.4	843.4	838.3	833.2	825.9	816.5	807.1	797.6	788.1	782.8
30°	830.3	824.7	819.3	813.7	808.2	800.3	790.0	779.6	769.3	759.0	752.7
32.5°	807.1	800.8	794.6	788.3	782.0	773.4	762.5	751.6	740.7	729.8	722.9
35°	768.1	761.4	754.8	748.2	741.6	732.5	721.1	709.6	698.2	686.8	678.9
37.5°	728.6	721.2	713.8	706.5	699.1	689.4	677.2	665.0	652.8	640.6	631.5
40°	703.4	695.3	687.1	679.1	671.0	660.4	647.3	634.2	621.1	608.0	598.4
42.5°	674.9	666.8	658.6	650.5	642.5	631.6	618.1	604.5	591.0	577.5	567.0
45°	631.2	623.0	614.7	606.3	598.0	586.8	572.6	558.4	544.2	530.0	519.5
47.5°	587.6	578.5	569.4	560.3	551.2	539.6	525.4	511.1	496.9	482.8	471.3
50°	555.7	547.1	538.4	529.7	521.1	509.3	494.4	479.4	464.5	449.6	438.2
52.5°	527.2	517.8	508.4	499.0	489.6	477.5	462.7	448.0	433.2	418.4	406.5
55°	479.4	470.4	461.4	452.3	443.3	430.9	415.3	399.7	384.0	368.3	357.6
57.5°	435.3	425.5	415.7	405.8	395.9	383.2	367.4	351.6	335.9	320.2	310.1
60°	404.8	394.7	384.5	374.4	364.2	351.5	336.2	320.9	305.6	290.3	280.4
62.5°	374.2	364.1	353.9	343.8	333.7	321.0	305.7	290.4	275.1	259.8	250.4
65°	327.6	317.5	307.4	297.2	287.1	274.8	260.5	246.1	231.7	217.3	208.3
67.5°	281.1	270.8	260.5	250.3	240.0	228.0	214.2	200.4	186.6	172.9	166.1
70°	250.5	240.6	230.6	220.6	210.7	199.2	186.3	173.5	160.6	147.7	141.2
72.5°	220.0	210.2	200.3	190.5	180.8	170.0	158.3	146.6	134.8	123.1	117.8
75°	173.3	164.5	155.7	146.8	138.0	128.5	118.4	108.2	98.1	87.9	86.1
77.5°	130.9	122.9	114.9	106.9	98.9	91.7	85.1	78.6	72.1	65.5	64.6
80°	103.7	96.1	88.6	81.0	73.4	67.7	63.8	60.0	56.2	52.3	51.7
82.5°	77.8	71.3	64.7	58.2	51.7	47.5	45.7	43.9	42.1	40.3	39.8
85°	44.0	39.9	35.9	31.8	27.7	25.4	24.9	24.3	23.8	23.2	22.9
87.5°	16.2	15.1	14.0	12.9	11.8	11.6	12.3	13.0	13.7	14.3	14.4
90°	1.2	3.9	6.5	9.2	11.8	14.9	18.3	21.8	25.2	28.7	29.7
92.5°	28.9	30.7	32.5	34.3	36.1	38.0	40.0	41.9	43.9	45.9	46.7
95°	70.5	72.3	74.2	76.0	78.0	79.9	82.0	84.1	86.3	88.4	89.4
97.5°	125.2	126.6	127.9	129.4	130.7	132.1	133.7	135.2	136.8	138.3	139.6
100°	162.5	164.1	165.6	167.2	168.8	170.3	171.6	172.9	174.3	175.6	176.4
102.5°	205.5	206.4	207.4	208.3	209.3	210.6	212.4	214.1	215.9	217.6	218.5
105°	268.8	269.3	269.8	270.4	270.9	272.4	274.7	277.1	279.6	281.9	281.9
107.5°	342.4	342.7	343.0	343.3	343.6	344.3	345.2	346.2	347.1	348.1	349.0
110°	388.2	388.8	389.3	389.8	390.4	390.9	391.4	392.0	392.4	393.0	394.1



TEST NUMBER: P332449-927

CATALOG NUMBER: S123RDIW-S775D1535U927-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	436.0	436.3	436.7	437.0	437.3	437.5	437.6	437.7	437.8	437.9	439.2
115°	507.7	508.5	509.3	510.1	510.9	511.0	510.5	509.9	509.5	508.9	509.1
117.5°	579.9	580.4	580.9	581.5	581.9	581.9	581.2	580.5	579.8	579.2	579.1
120°	624.8	626.4	628.0	629.5	631.1	631.3	629.9	628.6	627.2	626.0	625.7
122.5°	671.6	672.7	673.9	675.1	676.3	676.5	675.8	675.1	674.5	673.8	673.0
125°	743.0	743.8	744.7	745.4	746.2	746.3	745.8	745.3	744.7	744.3	743.1
127.5°	809.0	810.6	812.4	814.0	815.8	816.3	815.7	815.2	814.6	814.0	812.5
130°	852.9	855.1	857.1	859.3	861.4	862.1	861.3	860.5	859.7	858.9	857.9
132.5°	896.9	899.0	901.1	903.2	905.4	906.2	905.5	905.0	904.4	903.8	902.5
135°	964.0	965.6	967.2	968.8	970.4	971.1	970.8	970.5	970.3	970.0	968.9
137.5°	1026.1	1027.5	1028.8	1030.2	1031.4	1032.5	1033.2	1033.8	1034.5	1035.2	1034.1
140°	1069.1	1070.5	1071.8	1073.1	1074.4	1075.2	1075.5	1075.8	1076.0	1076.3	1076.0
142.5°	1108.3	1109.6	1111.0	1112.3	1113.6	1114.5	1115.0	1115.5	1115.9	1116.4	1116.2
145°	1169.5	1170.1	1170.5	1171.1	1171.6	1172.3	1173.1	1173.9	1174.6	1175.4	1175.2
147.5°	1223.0	1223.9	1224.9	1225.9	1226.9	1227.6	1228.4	1229.2	1229.9	1230.7	1230.7
150°	1260.3	1260.8	1261.3	1261.9	1262.4	1262.9	1263.5	1264.0	1264.5	1265.0	1265.0
152.5°	1290.9	1291.6	1292.4	1293.1	1293.8	1294.3	1294.7	1295.0	1295.3	1295.6	1296.1
155°	1339.1	1339.1	1339.1	1339.1	1339.1	1339.3	1339.5	1339.7	1340.1	1340.3	1341.4
157.5°	1380.2	1379.9	1379.6	1379.3	1379.0	1378.9	1379.1	1379.3	1379.5	1379.7	1380.9
160°	1406.0	1405.5	1404.9	1404.4	1403.9	1403.6	1403.6	1403.6	1403.6	1403.6	1404.9
162.5°	1428.9	1428.2	1427.4	1426.7	1426.0	1425.7	1425.9	1426.2	1426.3	1426.6	1427.9
165°	1458.6	1457.8	1457.0	1456.2	1455.4	1455.0	1455.0	1455.0	1455.0	1455.0	1456.6
167.5°	1482.3	1481.1	1480.1	1479.0	1478.0	1477.6	1477.7	1478.0	1478.2	1478.4	1480.0
170°	1495.6	1494.5	1493.5	1492.4	1491.4	1490.8	1490.8	1490.8	1490.8	1490.8	1492.7
172.5°	1506.1	1505.1	1504.0	1502.9	1501.9	1501.3	1501.3	1501.3	1501.3	1501.3	1503.0
175°	1517.1	1516.1	1515.0	1513.9	1512.8	1512.4	1512.4	1512.4	1512.4	1512.4	1513.9
177.5°	1521.6	1520.8	1520.0	1519.1	1518.2	1517.8	1517.8	1517.8	1517.8	1517.8	1519.1
180°	1520.7	1520.7	1520.7	1520.7	1520.7	1520.7	1520.7	1520.7	1520.7	1520.7	1520.7



TEST NUMBER: P332449-927

CATALOG NUMBER: S123RDIW-S775D1535U927-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1022.8	1022.8	1022.8	1022.8	1022.8	1022.8	1022.8	1022.8
2.5°	1018.7	1020.3	1021.9	1022.6	1022.3	1022.0	1021.7	1021.4
5°	1011.9	1013.6	1015.3	1015.9	1015.6	1015.2	1014.8	1014.5
7.5°	997.8	998.6	999.6	999.7	999.1	998.5	997.8	997.2
10°	985.0	985.2	985.3	985.0	984.0	983.1	982.2	981.3
12.5°	969.1	969.0	968.9	968.3	967.3	966.1	965.1	964.0
15°	941.3	940.3	939.4	938.3	937.1	935.7	934.5	933.2
17.5°	908.0	906.1	904.1	902.2	900.2	898.3	896.4	894.5
20°	885.3	882.8	880.4	878.1	875.9	873.7	871.5	869.3
22.5°	860.9	857.9	854.8	852.3	850.2	848.2	846.1	844.1
25°	820.9	817.1	813.2	810.2	808.2	806.1	804.1	802.1
27.5°	777.4	772.1	766.7	762.4	759.3	756.2	753.1	750.0
30°	746.5	740.1	733.9	729.3	726.4	723.4	720.4	717.5
32.5°	716.1	709.2	702.3	697.4	694.3	691.2	688.1	685.0
35°	671.0	663.1	655.1	649.5	646.2	642.9	639.5	636.2
37.5°	622.5	613.5	604.5	598.0	593.9	589.8	585.7	581.6
40°	588.8	579.2	569.7	562.8	558.5	554.3	550.0	545.8
42.5°	556.5	546.1	535.6	528.5	524.7	520.9	517.1	513.3
45°	509.1	498.5	488.0	480.5	476.1	471.7	467.3	462.9
47.5°	459.9	448.5	437.0	429.4	425.4	421.4	417.6	413.6
50°	426.7	415.3	403.9	396.0	391.8	387.5	383.3	379.1
52.5°	394.7	382.8	370.9	363.1	359.3	355.5	351.6	347.8
55°	346.9	336.2	325.5	318.3	314.7	310.9	307.3	303.6
57.5°	300.0	289.9	279.8	273.1	270.1	266.9	263.7	260.6
60°	270.4	260.5	250.5	244.0	240.8	237.7	234.6	231.4
62.5°	241.1	231.7	222.4	216.0	212.7	209.5	206.2	202.9
65°	199.2	190.2	181.2	175.6	173.6	171.6	169.6	167.5
67.5°	159.4	152.7	145.8	141.4	139.3	137.0	134.9	132.7
70°	134.8	128.3	121.8	117.6	115.6	113.5	111.5	109.5
72.5°	112.6	107.3	102.0	98.9	98.1	97.3	96.4	95.5
75°	84.2	82.4	80.6	79.5	79.1	78.7	78.3	78.0
77.5°	63.5	62.5	61.6	60.8	60.5	60.1	59.7	59.4
80°	51.2	50.6	50.1	49.6	49.2	48.9	48.5	48.1
82.5°	39.2	38.7	38.1	37.8	37.7	37.6	37.5	37.5
85°	22.5	22.1	21.8	21.5	21.5	21.5	21.5	21.5
87.5°	14.5	14.6	14.7	14.7	14.6	14.6	14.5	14.5
90°	30.8	31.8	33.0	33.7	34.2	34.8	35.3	35.8
92.5°	47.5	48.4	49.3	49.5	49.2	48.9	48.6	48.2
95°	90.5	91.6	92.6	93.2	93.2	93.2	93.2	93.2
97.5°	140.8	142.0	143.2	143.8	143.7	143.5	143.5	143.4
100°	177.2	178.0	178.8	179.4	180.0	180.5	181.0	181.6
102.5°	219.3	220.1	220.9	221.2	221.1	220.9	220.9	220.8
105°	281.9	281.9	281.9	282.2	282.7	283.3	283.8	284.3
107.5°	349.8	350.6	351.5	351.7	351.4	351.1	350.8	350.5
110°	395.1	396.2	397.3	397.5	397.0	396.5	395.9	395.4





TEST NUMBER: P332449-927

CATALOG NUMBER: S123RDIW-S775D1535U927-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	440.5	441.7	443.0	443.6	443.5	443.4	443.3	443.1
115°	509.5	509.7	509.9	509.9	509.7	509.5	509.1	508.9
117.5°	579.0	579.0	578.9	578.5	577.7	577.0	576.3	575.5
120°	625.4	625.2	624.9	624.5	624.0	623.4	622.9	622.3
122.5°	672.3	671.7	671.0	670.3	669.6	668.8	668.0	667.3
125°	742.1	741.0	740.0	738.9	737.8	736.8	735.7	734.7
127.5°	811.0	809.5	808.0	806.7	805.5	804.2	803.0	801.8
130°	856.7	855.7	854.7	853.2	851.4	849.5	847.6	845.7
132.5°	901.3	900.0	898.7	897.4	896.0	894.5	893.0	891.6
135°	967.9	966.8	965.7	965.0	964.4	963.8	963.4	962.8
137.5°	1033.0	1031.9	1030.8	1029.7	1028.6	1027.7	1026.7	1025.6
140°	1075.8	1075.5	1075.2	1074.2	1072.3	1070.5	1068.6	1066.8
142.5°	1115.9	1115.6	1115.4	1114.5	1113.1	1111.7	1110.2	1108.8
145°	1174.9	1174.6	1174.4	1173.7	1172.7	1171.6	1170.5	1169.5
147.5°	1230.7	1230.7	1230.7	1229.9	1228.3	1226.7	1225.0	1223.4
150°	1265.0	1265.0	1265.0	1264.2	1262.7	1261.1	1259.5	1257.9
152.5°	1296.5	1296.9	1297.4	1296.9	1295.5	1294.1	1292.7	1291.3
155°	1342.4	1343.5	1344.6	1344.2	1342.3	1340.5	1338.6	1336.7
157.5°	1382.0	1383.1	1384.2	1384.0	1382.5	1381.0	1379.5	1378.1
160°	1406.3	1407.6	1408.9	1409.1	1408.0	1406.9	1405.9	1404.8
162.5°	1429.2	1430.5	1431.9	1431.7	1430.0	1428.3	1426.6	1424.9
165°	1458.2	1459.8	1461.3	1461.3	1459.4	1457.5	1455.6	1453.8
167.5°	1481.7	1483.4	1484.9	1484.9	1483.4	1481.7	1480.0	1478.4
170°	1494.5	1496.4	1498.3	1498.3	1496.4	1494.5	1492.7	1490.8
172.5°	1504.6	1506.3	1507.9	1507.8	1505.9	1504.1	1502.2	1500.4
175°	1515.5	1517.1	1518.7	1518.5	1516.7	1514.8	1513.0	1511.2
177.5°	1520.4	1521.6	1522.9	1522.8	1521.3	1519.8	1518.4	1516.9
180°	1520.7	1520.7	1520.7	1520.7	1520.7	1520.7	1520.7	1520.7

(END OF REPORT)