

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331798-840

Luminaire Tested: **S122RDIW-S485D1240U840-4F0-1E-UDD-A1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331798-840
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-8,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122RDIW-S485D1240U840-4F0-1E-UDD-A1
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 485 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 1240 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6220.7 lumens
Efficiency: N/A
Efficacy: 115.6 lumens/watt
Spacing Criteria (0/90/45): 0.86 / 1.16 / 1.02
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 53.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331798-840

CATALOG NUMBER: S122RDIW-S485D1240U840-4F0-1E-UDD-A1

Luminous Intensity Polar Plot





TEST NUMBER: P331798-840

CATALOG NUMBER: S122RDIW-S485D1240U840-4F0-1E-UDD-A1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	102	102	102	102	92	92	92	92	72	72	72	54	54	54	38	38	38	30
1	94	90	86	83	84	81	78	75	64	62	60	48	47	46	34	34	33	26
2	86	79	73	68	77	71	66	62	57	53	50	43	41	39	31	29	28	23
3	79	70	63	58	70	63	57	53	50	46	43	39	36	34	28	26	25	20
4	72	62	55	49	65	56	50	45	45	41	37	35	32	29	25	23	22	18
5	66	55	48	42	59	50	44	39	40	36	32	31	28	26	23	21	19	16
6	61	50	42	37	55	45	39	34	37	32	28	28	25	23	21	19	17	14
7	57	45	38	32	51	41	34	30	33	29	25	26	23	20	19	17	16	13
8	53	41	34	29	47	37	31	27	30	26	22	24	21	18	18	16	14	12
9	49	37	30	26	44	34	28	24	28	23	20	22	19	16	17	14	13	11
10	46	34	27	23	41	31	25	21	26	21	18	20	17	15	15	13	12	10

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	17525	17525	17525	17525
5°	19571	17634	15635	17634
10°	21713	17510	13554	17510
15°	22781	17254	10678	17254
20°	19749	16873	9241	16873
25°	12953	16352	8250	16352
30°	8720	15720	7467	15720
35°	7062	14927	6733	14927
40°	6279	14060	6232	14060
45°	5683	13047	5562	13047
50°	5172	12039	5152	12039
55°	4861	10925	4799	10925
60°	4066	9901	4017	9901
65°	3431	8989	3889	8989
70°	3172	8030	3668	8030
75°	2969	6987	3387	6987
80°	2734	5746	3013	5746
85°	2501	4539	2649	4539



TEST NUMBER: P331798-840

CATALOG NUMBER: S122RDIW-S485D1240U840-4F0-1E-UDD-A1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	102.9	1.7
10°-20°	286.7	4.6
20°-30°	369.4	5.9
30°-40°	351.1	5.6
40°-50°	300.7	4.8
50°-60°	229.0	3.7
60°-70°	144.8	2.3
70°-80°	72.3	1.2
80°-90°	25.0	0.4
90°-100°	98.3	1.6
100°-110°	305.4	4.9
110°-120°	522.0	8.4
120°-130°	686.4	11.0
130°-140°	770.4	12.4
140°-150°	755.4	12.1
150°-160°	633.6	10.2
160°-170°	420.3	6.8
170°-180°	146.9	2.4
0°-30°	759.0	12.2
0°-40°	1110.1	17.8
0°-60°	1639.8	26.4
0°-90°	1881.9	30.3
90°-120°	925.7	14.9
90°-150°	3138.0	50.4
90°-180°	4339.0	69.8
0°-180°	6220.7	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1085	1085	1085	1085	1085	
5°	1208	1088	965	1088	1208	119
15°	1363	1032	639	1032	1363	368
25°	727	918	463	918	727	345
35°	358	757	342	757	358	229
45°	249	571	244	571	249	193
55°	173	388	170	388	173	152
65°	90	235	102	235	90	91
75°	48	112	54	112	48	50
85°	14	24	14	24	14	16
90°	44	1	44	1	44	20
95°	81	68	81	68	81	91
105°	291	282	291	282	291	306
115°	524	524	524	524	524	517
125°	765	762	765	762	765	682
135°	998	986	998	986	998	768
145°	1210	1197	1210	1197	1210	756
155°	1379	1368	1379	1368	1379	635
165°	1490	1489	1490	1489	1490	420
175°	1544	1549	1544	1549	1544	147
180°	1552	1552	1552	1552	1552	



TEST NUMBER: P331798-840

CATALOG NUMBER: S122RDIW-S485D1240U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1085.4	1085.4	1085.4	1085.4	1085.4	1085.4	1085.4	1085.4	1085.4	1085.4	1085.4
2.5°	1129.4	1130.3	1131.3	1129.1	1129.1	1127.3	1123.4	1120.3	1111.9	1110.6	1110.6
5°	1207.5	1206.8	1208.3	1203.4	1196.6	1195.1	1187.9	1178.5	1168.7	1157.7	1155.5
7.5°	1285.3	1284.1	1281.1	1280.2	1275.1	1263.6	1252.1	1239.8	1223.6	1207.6	1199.6
10°	1324.4	1336.9	1329.4	1316.2	1318.8	1301.1	1291.6	1275.5	1261.8	1238.1	1232.8
12.5°	1363.0	1368.0	1365.5	1358.1	1354.7	1342.4	1329.7	1315.6	1290.5	1269.2	1250.6
15°	1362.9	1370.1	1372.0	1369.7	1371.6	1370.8	1364.0	1352.3	1330.5	1307.1	1286.8
17.5°	1262.3	1267.3	1279.6	1288.0	1298.6	1320.9	1331.9	1336.3	1332.9	1319.6	1305.3
20°	1149.4	1141.1	1175.9	1193.6	1208.7	1246.4	1278.8	1291.2	1311.2	1310.9	1307.1
22.5°	989.6	991.5	1024.4	1045.4	1089.5	1127.2	1164.2	1211.0	1249.7	1275.3	1290.2
25°	727.1	741.4	774.3	802.8	851.9	922.1	985.8	1059.8	1129.4	1184.6	1237.0
27.5°	546.0	547.1	573.1	599.7	628.7	686.2	766.5	854.7	954.2	1036.2	1130.6
30°	467.7	465.3	476.4	492.5	517.5	561.9	622.3	709.0	808.2	931.9	1042.0
32.5°	412.1	412.2	420.5	432.5	453.1	483.1	524.5	594.9	688.7	810.3	939.4
35°	358.3	357.9	364.0	372.6	381.2	400.5	428.8	465.7	530.3	643.8	775.8
37.5°	319.6	321.3	324.3	329.7	339.2	349.9	367.0	391.7	437.7	504.8	615.7
40°	297.9	298.7	302.9	307.4	313.1	321.3	335.3	355.3	388.8	442.3	523.4
42.5°	278.0	278.7	281.8	285.9	290.3	298.7	310.2	327.5	354.8	396.5	463.4
45°	248.9	248.9	251.6	253.4	258.3	265.9	275.3	289.6	308.5	339.4	384.0
47.5°	221.6	221.7	223.4	226.6	229.7	235.6	244.9	256.6	270.3	294.3	332.2
50°	205.9	206.3	207.4	210.1	212.0	217.2	224.4	234.6	248.9	267.4	299.0
52.5°	193.2	193.0	194.4	195.6	196.8	200.7	206.0	215.0	227.8	243.9	270.1
55°	172.7	171.2	173.5	175.3	176.5	178.0	181.0	186.7	197.6	211.2	230.8
57.5°	147.0	146.4	148.0	149.8	153.3	157.4	160.0	163.6	169.3	178.9	198.4
60°	125.9	125.9	129.4	130.5	134.6	139.9	145.2	148.2	153.9	160.3	174.6
62.5°	107.2	107.6	109.2	110.3	112.6	119.1	126.5	133.1	138.5	144.6	154.1
65°	89.8	90.5	90.5	91.3	92.8	94.3	97.3	102.6	112.0	120.7	127.8
67.5°	76.1	76.4	76.6	77.4	77.8	79.4	80.6	83.0	85.1	93.4	102.3
70°	67.2	68.3	67.9	68.7	69.0	69.8	71.3	72.4	75.8	77.7	83.0
72.5°	58.7	59.5	59.5	59.9	60.9	61.0	62.2	63.3	65.5	67.2	70.0
75°	47.6	47.2	47.6	48.3	48.7	49.0	49.0	50.5	51.7	53.2	55.0
77.5°	36.7	37.1	37.0	37.1	37.1	37.8	37.7	38.4	39.5	40.3	41.2
80°	29.4	29.8	29.4	29.8	30.2	30.5	30.2	30.5	31.7	32.4	32.4
82.5°	22.8	22.8	23.1	23.1	23.2	23.3	23.8	23.9	24.7	24.5	24.8
85°	13.5	13.2	13.2	13.2	13.5	13.9	13.5	13.5	13.9	13.9	13.9
87.5°	13.7	13.9	13.9	13.8	13.8	13.8	13.9	14.3	14.1	14.6	13.0
90°	44.5	44.2	43.9	43.6	43.3	43.5	44.1	44.6	45.2	45.8	39.4
92.5°	42.4	42.4	42.3	42.2	42.2	42.1	42.0	41.9	41.7	41.6	40.1
95°	81.2	81.8	82.3	82.9	83.5	83.8	83.8	83.8	83.8	83.8	83.2
97.5°	140.7	140.7	140.8	140.8	140.9	140.9	140.9	140.9	140.9	140.9	139.8
100°	179.4	179.7	180.0	180.3	180.6	180.7	180.7	180.7	180.7	180.7	179.9
102.5°	223.4	223.7	224.0	224.3	224.6	224.6	224.4	224.1	223.9	223.7	222.6
105°	290.7	290.7	290.7	290.7	290.7	290.4	289.8	289.2	288.6	288.1	287.5
107.5°	354.1	355.4	356.8	358.1	359.4	360.0	359.7	359.5	359.3	359.0	359.0
110°	403.3	404.1	405.1	406.0	406.8	407.3	407.3	407.3	407.3	407.3	407.3



TEST NUMBER: P331798-840

CATALOG NUMBER: S122RDIW-S485D1240U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	450.4	451.1	451.7	452.3	453.0	453.6	454.3	455.0	455.8	456.5	456.7
115°	523.8	524.6	525.5	526.4	527.3	527.9	528.2	528.5	528.8	529.0	529.6
117.5°	593.7	594.6	595.4	596.3	597.2	597.9	598.6	599.4	600.1	600.8	602.4
120°	643.0	643.8	644.7	645.5	646.4	646.8	646.8	646.8	646.8	646.8	649.1
122.5°	691.2	691.8	692.4	693.1	693.7	694.4	695.1	695.8	696.4	697.1	698.7
125°	764.7	765.0	765.3	765.6	765.9	766.5	767.3	768.2	769.1	769.9	770.8
127.5°	831.7	832.7	833.6	834.6	835.5	836.5	837.5	838.6	839.6	840.6	841.7
130°	879.9	881.1	882.3	883.4	884.6	885.4	886.1	886.7	887.2	887.8	888.4
132.5°	926.0	927.0	927.9	928.9	929.8	930.9	932.1	933.4	934.7	935.9	935.8
135°	997.7	998.7	999.6	1000.4	1001.3	1001.9	1002.2	1002.5	1002.7	1003.0	1002.5
137.5°	1062.8	1063.9	1065.1	1066.2	1067.4	1068.1	1068.3	1068.5	1068.8	1069.0	1068.2
140°	1107.8	1108.9	1110.1	1111.3	1112.5	1113.0	1113.0	1113.0	1113.0	1113.0	1111.6
142.5°	1148.6	1149.8	1150.9	1152.2	1153.3	1153.8	1153.6	1153.3	1153.1	1152.9	1151.9
145°	1209.9	1211.1	1212.2	1213.5	1214.6	1215.0	1214.8	1214.5	1214.2	1213.9	1212.1
147.5°	1264.7	1265.8	1266.9	1268.0	1269.1	1269.3	1268.7	1268.0	1267.4	1266.8	1265.6
150°	1300.3	1301.1	1302.0	1302.9	1303.7	1303.7	1302.9	1302.0	1301.1	1300.3	1299.1
152.5°	1333.8	1334.9	1336.1	1337.1	1338.2	1338.2	1337.1	1336.1	1334.9	1333.8	1332.4
155°	1378.9	1379.7	1380.6	1381.5	1382.3	1382.0	1380.6	1379.2	1377.7	1376.2	1375.3
157.5°	1417.5	1419.0	1420.4	1421.8	1423.2	1422.9	1420.9	1419.0	1416.9	1415.0	1414.4
160°	1441.7	1442.9	1444.0	1445.2	1446.3	1446.0	1444.3	1442.6	1440.8	1439.1	1438.8
162.5°	1462.7	1464.0	1465.4	1466.8	1468.2	1467.9	1465.9	1464.0	1462.0	1460.1	1459.8
165°	1490.2	1491.6	1493.1	1494.5	1495.9	1495.7	1493.6	1491.6	1489.6	1487.5	1487.5
167.5°	1512.7	1514.2	1515.7	1517.2	1518.7	1518.4	1516.4	1514.4	1512.4	1510.3	1510.4
170°	1524.2	1525.9	1527.7	1529.4	1531.2	1531.1	1528.9	1526.9	1524.9	1522.9	1523.2
172.5°	1533.6	1535.4	1537.1	1538.8	1540.5	1540.4	1538.4	1536.4	1534.4	1532.3	1532.6
175°	1543.8	1545.6	1547.3	1549.0	1550.8	1550.6	1548.6	1546.6	1544.6	1542.5	1543.1
177.5°	1548.5	1549.9	1551.4	1552.8	1554.1	1554.1	1552.8	1551.4	1549.9	1548.5	1549.0
180°	1551.7	1551.7	1551.7	1551.7	1551.7	1551.7	1551.7	1551.7	1551.7	1551.7	1551.7



TEST NUMBER: P331798-840

CATALOG NUMBER: S122RDIW-S485D1240U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1085.4	1085.4	1085.4	1085.4	1085.4	1085.4	1085.4	1085.4	1085.4	1085.4	1085.4
2.5°	1111.3	1108.9	1106.8	1101.4	1098.6	1092.6	1091.7	1091.4	1083.6	1076.0	1073.9
5°	1149.4	1143.5	1134.4	1123.8	1112.9	1101.6	1094.0	1088.0	1072.9	1058.5	1050.3
7.5°	1187.9	1175.0	1159.3	1139.3	1122.7	1104.0	1090.1	1077.6	1056.2	1035.7	1021.9
10°	1216.6	1195.5	1174.8	1147.2	1125.7	1104.6	1085.0	1068.0	1043.9	1016.7	997.4
12.5°	1234.4	1211.1	1182.6	1155.7	1127.8	1101.0	1074.7	1052.9	1024.6	996.5	973.6
15°	1258.5	1233.6	1198.9	1160.4	1124.6	1089.5	1059.3	1032.2	995.2	961.7	933.7
17.5°	1278.2	1243.9	1206.6	1162.2	1120.6	1076.1	1037.2	1002.5	961.4	920.9	888.1
20°	1284.4	1250.5	1207.5	1163.1	1114.0	1061.6	1019.8	982.0	937.9	893.7	856.1
22.5°	1280.5	1254.2	1206.3	1153.1	1102.9	1048.0	1000.8	956.9	908.1	863.0	819.3
25°	1253.9	1244.9	1199.6	1141.6	1084.2	1020.5	965.8	917.9	862.1	813.9	766.3
27.5°	1191.8	1211.4	1183.4	1121.5	1057.7	989.4	928.0	873.4	815.5	761.1	713.8
30°	1132.2	1177.0	1164.9	1107.6	1036.3	969.2	900.2	843.2	781.4	725.6	678.8
32.5°	1050.4	1124.5	1136.3	1088.3	1014.6	940.8	868.5	811.8	747.3	688.4	642.9
35°	920.2	1031.1	1082.0	1051.4	977.4	898.0	823.2	757.3	692.4	634.3	589.1
37.5°	764.9	915.8	1000.8	1002.9	935.0	852.3	771.0	705.5	639.0	582.1	533.1
40°	664.1	827.8	938.3	962.8	905.4	816.1	733.9	667.1	602.3	546.4	490.3
42.5°	573.6	736.7	872.5	915.1	869.6	780.8	698.3	628.5	565.4	512.6	455.2
45°	463.8	606.4	756.1	832.3	807.1	724.8	637.7	571.4	512.1	466.5	411.4
47.5°	391.3	491.8	636.6	739.7	739.2	664.2	578.6	514.9	460.0	417.3	372.6
50°	349.9	437.5	560.1	676.9	686.7	623.8	542.3	479.3	428.1	383.1	347.3
52.5°	312.9	385.0	495.1	607.2	635.1	580.6	501.6	443.4	393.6	352.3	321.6
55°	264.4	320.1	403.9	508.8	551.0	512.5	442.3	388.1	347.7	313.1	286.6
57.5°	223.6	265.5	332.6	417.1	466.3	442.0	384.3	340.1	305.6	274.2	253.4
60°	198.0	232.3	289.2	359.8	414.0	397.1	347.7	306.6	277.2	250.0	230.5
62.5°	173.9	203.4	252.2	309.4	359.2	352.1	311.8	277.3	251.6	226.8	210.3
65°	139.9	161.4	199.4	244.4	284.4	287.7	258.7	235.3	212.3	192.7	178.0
67.5°	111.4	125.4	152.3	190.1	220.0	230.8	213.0	195.1	176.8	161.7	149.0
70°	93.9	105.2	124.8	155.4	182.9	194.2	184.0	170.1	154.2	141.8	130.9
72.5°	76.1	87.2	101.6	124.0	147.6	159.9	156.3	146.2	133.4	123.1	112.8
75°	57.4	60.7	70.5	85.6	104.1	114.6	117.2	112.0	101.8	93.9	87.9
77.5°	42.4	44.4	49.1	57.1	69.1	78.5	82.4	81.8	74.7	70.2	64.5
80°	33.9	35.0	37.4	40.7	49.8	59.2	61.8	61.8	57.0	55.0	49.4
82.5°	25.8	26.7	28.0	29.9	34.1	42.3	45.2	45.8	42.7	40.3	35.9
85°	14.7	14.3	15.0	16.3	17.0	19.2	23.7	24.5	23.7	20.7	19.6
87.5°	11.7	10.8	9.5	8.2	7.8	7.4	8.2	9.0	8.5	8.3	8.4
90°	33.0	26.7	20.2	15.2	11.8	8.3	4.8	1.3	4.8	8.3	11.8
92.5°	38.6	37.1	35.5	33.5	31.0	28.5	25.9	23.3	25.9	28.5	31.0
95°	82.6	82.1	81.5	79.8	76.9	73.9	71.0	68.1	71.0	73.9	76.9
97.5°	138.7	137.5	136.4	134.6	132.1	129.6	126.9	124.4	126.9	129.6	132.1
100°	178.9	178.0	177.2	175.6	173.3	171.0	168.6	166.3	168.6	171.0	173.3
102.5°	221.5	220.4	219.2	217.7	215.9	214.0	212.2	210.3	212.2	214.0	215.9
105°	286.9	286.3	285.8	285.0	284.2	283.3	282.4	281.6	282.4	283.3	284.2
107.5°	359.0	359.0	359.0	358.4	357.1	355.9	354.6	353.3	354.6	355.9	357.1
110°	407.3	407.3	407.3	406.4	404.7	402.8	401.1	399.4	401.1	402.8	404.7



TEST NUMBER: P331798-840

CATALOG NUMBER: S122RDIW-S485D1240U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	457.0	457.2	457.4	456.7	454.9	453.1	451.4	449.7	451.4	453.1	454.9
115°	530.2	530.8	531.3	530.8	529.0	527.3	525.5	523.8	525.5	527.3	529.0
117.5°	604.0	605.6	607.3	606.9	604.6	602.3	600.0	597.6	600.0	602.3	604.6
120°	651.6	653.9	656.2	656.2	653.9	651.6	649.1	646.8	649.1	651.6	653.9
122.5°	700.4	702.1	703.7	703.1	700.2	697.5	694.7	691.9	694.7	697.5	700.2
125°	771.7	772.5	773.5	772.5	769.9	767.3	764.7	762.0	764.7	767.3	769.9
127.5°	842.7	843.8	844.9	843.7	840.4	837.1	833.7	830.4	833.7	837.1	840.4
130°	889.0	889.6	890.1	888.5	884.7	881.0	877.2	873.4	877.2	881.0	884.7
132.5°	935.7	935.6	935.5	933.9	930.8	927.8	924.6	921.6	924.6	927.8	930.8
135°	1001.9	1001.3	1000.7	998.9	995.6	992.4	989.2	986.0	989.2	992.4	995.6
137.5°	1067.5	1066.7	1066.0	1064.3	1061.7	1059.0	1056.4	1053.8	1056.4	1059.0	1061.7
140°	1110.1	1108.6	1107.2	1105.2	1102.6	1099.9	1097.3	1094.7	1097.3	1099.9	1102.6
142.5°	1150.8	1149.8	1148.8	1147.1	1144.5	1141.9	1139.2	1136.6	1139.2	1141.9	1144.5
145°	1210.3	1208.6	1206.9	1205.0	1203.0	1200.9	1198.9	1196.8	1198.9	1200.9	1203.0
147.5°	1264.5	1263.2	1262.1	1260.3	1257.9	1255.4	1252.9	1250.5	1252.9	1255.4	1257.9
150°	1298.0	1296.8	1295.7	1294.1	1292.4	1290.7	1288.9	1287.2	1288.9	1290.7	1292.4
152.5°	1331.0	1329.6	1328.2	1326.7	1324.8	1323.1	1321.4	1319.7	1321.4	1323.1	1324.8
155°	1374.4	1373.6	1372.7	1371.9	1371.0	1370.1	1369.3	1368.4	1369.3	1370.1	1371.0
157.5°	1413.9	1413.4	1412.9	1412.3	1411.8	1411.2	1410.6	1410.0	1410.6	1411.2	1411.8
160°	1438.5	1438.1	1437.9	1437.4	1436.9	1436.3	1435.7	1435.1	1435.7	1436.3	1436.9
162.5°	1459.5	1459.2	1458.9	1458.6	1458.5	1458.4	1458.3	1458.1	1458.3	1458.4	1458.5
165°	1487.5	1487.5	1487.5	1487.6	1487.9	1488.2	1488.5	1488.8	1488.5	1488.2	1487.9
167.5°	1510.5	1510.5	1510.6	1511.0	1511.9	1512.8	1513.6	1514.5	1513.6	1512.8	1511.9
170°	1523.5	1523.8	1524.1	1524.6	1525.5	1526.4	1527.2	1528.1	1527.2	1526.4	1525.5
172.5°	1532.9	1533.2	1533.5	1534.1	1534.9	1535.8	1536.7	1537.5	1536.7	1535.8	1534.9
175°	1543.7	1544.3	1544.9	1545.6	1546.4	1547.3	1548.2	1549.0	1548.2	1547.3	1546.4
177.5°	1549.4	1549.9	1550.4	1551.0	1551.7	1552.4	1553.1	1553.8	1553.1	1552.4	1551.7
180°	1551.7	1551.7	1551.7	1551.7	1551.7	1551.7	1551.7	1551.7	1551.7	1551.7	1551.7



TEST NUMBER: P331798-840

CATALOG NUMBER: S122RDIW-S485D1240U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1085.4	1085.4	1085.4	1085.4	1085.4	1085.4	1085.4	1085.4	1085.4	1085.4	1085.4
2.5°	1070.0	1067.8	1063.9	1057.9	1054.3	1047.9	1043.7	1046.1	1046.7	1046.1	1045.5
5°	1041.3	1033.3	1022.4	1011.8	1002.0	991.5	985.4	982.8	977.4	974.5	973.0
7.5°	1006.4	992.8	977.3	959.0	943.3	927.0	918.6	914.4	903.6	897.8	892.6
10°	980.5	959.0	943.5	919.4	904.7	883.2	868.5	868.9	854.1	845.9	839.8
12.5°	951.9	928.3	902.5	880.8	860.4	843.1	825.4	818.2	802.5	794.6	778.3
15°	904.3	876.8	849.7	820.2	799.5	772.7	747.1	715.8	690.5	668.6	662.6
17.5°	852.4	818.4	791.1	756.6	721.0	676.0	646.3	628.1	612.9	601.4	592.8
20°	816.9	782.1	753.2	701.0	653.2	622.6	600.8	586.8	571.0	558.6	551.7
22.5°	779.4	743.3	703.7	645.5	608.2	583.7	564.2	548.2	537.5	527.8	521.6
25°	726.3	686.7	621.5	581.5	551.4	525.7	512.1	502.3	491.0	477.8	471.8
27.5°	670.2	607.2	560.4	530.7	501.9	485.2	473.0	458.4	448.3	442.3	436.1
30°	628.2	565.3	528.8	496.2	475.9	457.5	443.1	434.8	425.1	414.9	410.7
32.5°	581.5	531.2	496.1	469.2	448.5	432.7	421.4	408.0	400.9	394.7	386.0
35°	523.4	485.3	453.3	431.4	411.8	399.0	385.8	377.9	365.1	359.8	356.4
37.5°	474.2	441.2	417.3	394.3	378.7	364.6	356.5	343.9	338.3	330.9	323.8
40°	446.5	414.0	391.1	372.2	354.9	344.3	334.2	324.0	315.7	312.3	303.6
42.5°	418.2	391.7	368.7	348.1	336.5	325.3	312.5	305.0	296.3	290.8	285.5
45°	379.0	355.7	336.0	319.0	306.2	294.6	286.2	273.8	268.9	257.9	253.4
47.5°	344.6	322.9	304.2	288.0	275.5	267.9	255.8	246.0	238.2	231.5	225.7
50°	320.1	302.1	284.0	269.6	258.3	247.4	235.0	230.0	217.9	214.6	211.2
52.5°	297.8	280.6	264.1	250.0	238.7	228.1	217.1	210.8	202.6	199.1	196.7
55°	266.6	250.0	234.2	221.8	210.5	199.4	192.7	184.8	181.0	178.3	175.3
57.5°	235.2	220.4	208.1	195.6	184.2	175.5	167.6	162.9	159.0	155.5	151.9
60°	215.3	201.0	190.1	178.3	166.7	159.6	153.5	147.8	143.3	138.0	136.5
62.5°	194.2	181.7	171.7	160.3	150.1	143.5	137.8	132.5	127.0	119.4	117.2
65°	165.2	155.4	144.8	135.4	126.3	120.0	111.6	105.6	103.3	102.6	102.2
67.5°	139.0	129.7	120.6	111.0	102.7	96.7	92.5	91.6	90.1	89.6	88.6
70°	121.4	112.8	103.7	94.6	86.7	85.6	84.1	82.6	80.7	80.0	79.2
72.5°	105.7	96.7	87.8	80.5	77.1	75.6	74.1	72.6	71.4	70.6	70.2
75°	81.1	72.8	66.8	64.1	62.2	61.1	58.9	57.7	57.0	55.8	55.4
77.5°	58.4	53.7	50.9	49.3	47.3	46.0	44.8	43.6	42.8	42.6	42.0
80°	44.5	42.2	40.4	38.1	37.4	35.9	35.4	34.3	34.7	33.5	33.5
82.5°	34.5	31.7	30.1	29.1	28.3	27.1	26.7	26.2	26.3	25.4	25.4
85°	17.8	17.0	16.3	15.5	15.5	14.3	14.7	14.3	14.3	13.5	13.2
87.5°	8.8	9.5	10.2	11.4	12.7	13.7	13.5	13.1	13.0	12.9	12.6
90°	15.2	20.2	26.7	33.0	39.4	45.8	45.2	44.6	44.1	43.5	43.3
92.5°	33.5	35.5	37.1	38.6	40.1	41.6	41.7	41.9	42.0	42.1	42.2
95°	79.8	81.5	82.1	82.6	83.2	83.8	83.8	83.8	83.8	83.8	83.5
97.5°	134.6	136.4	137.5	138.7	139.8	140.9	140.9	140.9	140.9	140.9	140.9
100°	175.6	177.2	178.0	178.9	179.9	180.7	180.7	180.7	180.7	180.7	180.6
102.5°	217.7	219.2	220.4	221.5	222.6	223.7	223.9	224.1	224.4	224.6	224.6
105°	285.0	285.8	286.3	286.9	287.5	288.1	288.6	289.2	289.8	290.4	290.7
107.5°	358.4	359.0	359.0	359.0	359.0	359.0	359.3	359.5	359.7	360.0	359.4
110°	406.4	407.3	407.3	407.3	407.3	407.3	407.3	407.3	407.3	407.3	406.8



TEST NUMBER: P331798-840

CATALOG NUMBER: S122RDIW-S485D1240U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	456.7	457.4	457.2	457.0	456.7	456.5	455.8	455.0	454.3	453.6	453.0
115°	530.8	531.3	530.8	530.2	529.6	529.0	528.8	528.5	528.2	527.9	527.3
117.5°	606.9	607.3	605.6	604.0	602.4	600.8	600.1	599.4	598.6	597.9	597.2
120°	656.2	656.2	653.9	651.6	649.1	646.8	646.8	646.8	646.8	646.8	646.4
122.5°	703.1	703.7	702.1	700.4	698.7	697.1	696.4	695.8	695.1	694.4	693.7
125°	772.5	773.5	772.5	771.7	770.8	769.9	769.1	768.2	767.3	766.5	765.9
127.5°	843.7	844.9	843.8	842.7	841.7	840.6	839.6	838.6	837.5	836.5	835.5
130°	888.5	890.1	889.6	889.0	888.4	887.8	887.2	886.7	886.1	885.4	884.6
132.5°	933.9	935.5	935.6	935.7	935.8	935.9	934.7	933.4	932.1	930.9	929.8
135°	998.9	1000.7	1001.3	1001.9	1002.5	1003.0	1002.7	1002.5	1002.2	1001.9	1001.3
137.5°	1064.3	1066.0	1066.7	1067.5	1068.2	1069.0	1068.8	1068.5	1068.3	1068.1	1067.4
140°	1105.2	1107.2	1108.6	1110.1	1111.6	1113.0	1113.0	1113.0	1113.0	1113.0	1112.5
142.5°	1147.1	1148.8	1149.8	1150.8	1151.9	1152.9	1153.1	1153.3	1153.6	1153.8	1153.3
145°	1205.0	1206.9	1208.6	1210.3	1212.1	1213.9	1214.2	1214.5	1214.8	1215.0	1214.6
147.5°	1260.3	1262.1	1263.2	1264.5	1265.6	1266.8	1267.4	1268.0	1268.7	1269.3	1269.1
150°	1294.1	1295.7	1296.8	1298.0	1299.1	1300.3	1301.1	1302.0	1302.9	1303.7	1303.7
152.5°	1326.7	1328.2	1329.6	1331.0	1332.4	1333.8	1334.9	1336.1	1337.1	1338.2	1338.2
155°	1371.9	1372.7	1373.6	1374.4	1375.3	1376.2	1377.7	1379.2	1380.6	1382.0	1382.3
157.5°	1412.3	1412.9	1413.4	1413.9	1414.4	1415.0	1416.9	1419.0	1420.9	1422.9	1423.2
160°	1437.4	1437.9	1438.1	1438.5	1438.8	1439.1	1440.8	1442.6	1444.3	1446.0	1446.3
162.5°	1458.6	1458.9	1459.2	1459.5	1459.8	1460.1	1462.0	1464.0	1465.9	1467.9	1468.2
165°	1487.6	1487.5	1487.5	1487.5	1487.5	1487.5	1489.6	1491.6	1493.6	1495.7	1495.9
167.5°	1511.0	1510.6	1510.5	1510.5	1510.4	1510.3	1512.4	1514.4	1516.4	1518.4	1518.7
170°	1524.6	1524.1	1523.8	1523.5	1523.2	1522.9	1524.9	1526.9	1528.9	1531.1	1531.2
172.5°	1534.1	1533.5	1533.2	1532.9	1532.6	1532.3	1534.4	1536.4	1538.4	1540.4	1540.5
175°	1545.6	1544.9	1544.3	1543.7	1543.1	1542.5	1544.6	1546.6	1548.6	1550.6	1550.8
177.5°	1551.0	1550.4	1549.9	1549.4	1549.0	1548.5	1549.9	1551.4	1552.8	1554.1	1554.1
180°	1551.7	1551.7	1551.7	1551.7	1551.7	1551.7	1551.7	1551.7	1551.7	1551.7	1551.7



TEST NUMBER: P331798-840

CATALOG NUMBER: S122RDIW-S485D1240U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1085.4	1085.4	1085.4	1085.4	1085.4	1085.4	1085.4	1085.4	1085.4	1085.4	1085.4
2.5°	1042.2	1042.8	1041.9	1042.5	1041.9	1042.8	1042.2	1045.5	1046.1	1046.7	1046.1
5°	971.1	966.5	965.8	964.7	965.8	966.5	971.1	973.0	974.5	977.4	982.8
7.5°	886.2	885.4	883.6	880.9	883.6	885.4	886.2	892.6	897.8	903.6	914.4
10°	831.5	829.7	829.3	826.7	829.3	829.7	831.5	839.8	845.9	854.1	868.9
12.5°	767.6	755.5	754.2	747.6	754.2	755.5	767.6	778.3	794.6	802.5	818.2
15°	653.6	651.3	643.8	638.8	643.8	651.3	653.6	662.6	668.6	690.5	715.8
17.5°	588.3	581.0	578.7	577.6	578.7	581.0	588.3	592.8	601.4	612.9	628.1
20°	546.4	539.7	538.6	537.8	538.6	539.7	546.4	551.7	558.6	571.0	586.8
22.5°	517.5	510.4	507.5	505.2	507.5	510.4	517.5	521.6	527.8	537.5	548.2
25°	468.0	465.3	463.8	463.1	463.8	465.3	468.0	471.8	477.8	491.0	502.3
27.5°	429.3	423.5	422.3	420.4	422.3	423.5	429.3	436.1	442.3	448.3	458.4
30°	407.3	405.4	402.7	400.5	402.7	405.4	407.3	410.7	414.9	425.1	434.8
32.5°	381.3	379.8	377.4	376.4	377.4	379.8	381.3	386.0	394.7	400.9	408.0
35°	352.6	347.3	345.1	341.6	345.1	347.3	352.6	356.4	359.8	365.1	377.9
37.5°	322.2	319.4	316.3	317.4	316.3	319.4	322.2	323.8	330.9	338.3	343.9
40°	298.7	296.8	296.0	295.7	296.0	296.8	298.7	303.6	312.3	315.7	324.0
42.5°	279.9	274.8	272.8	272.8	272.8	274.8	279.9	285.5	290.8	296.3	305.0
45°	251.6	246.6	243.3	243.6	243.3	246.6	251.6	253.4	257.9	268.9	273.8
47.5°	222.5	222.3	220.2	220.9	220.2	222.3	222.5	225.7	231.5	238.2	246.0
50°	208.5	206.3	204.8	205.1	204.8	206.3	208.5	211.2	214.6	217.9	230.0
52.5°	195.3	193.3	192.1	193.7	192.1	193.3	195.3	196.7	199.1	202.6	210.8
55°	173.5	171.2	170.9	170.5	170.9	171.2	173.5	175.3	178.3	181.0	184.8
57.5°	149.2	147.6	145.3	144.4	145.3	147.6	149.2	151.9	155.5	159.0	162.9
60°	131.6	128.6	124.8	124.4	124.8	128.6	131.6	136.5	138.0	143.3	147.8
62.5°	115.6	115.0	114.3	114.2	114.3	115.0	115.6	117.2	119.4	127.0	132.5
65°	101.5	101.1	101.5	101.8	101.5	101.1	101.5	102.2	102.6	103.3	105.6
67.5°	88.4	87.8	87.1	87.4	87.1	87.8	88.4	88.6	89.6	90.1	91.6
70°	78.5	78.1	77.7	77.7	77.7	78.1	78.5	79.2	80.0	80.7	82.6
72.5°	68.8	68.7	68.4	68.1	68.4	68.7	68.8	70.2	70.6	71.4	72.6
75°	55.0	54.3	54.3	54.3	54.3	54.3	55.0	55.4	55.8	57.0	57.7
77.5°	41.9	41.6	41.2	40.9	41.2	41.6	41.9	42.0	42.6	42.8	43.6
80°	33.2	32.8	32.4	32.4	32.4	32.8	33.2	33.5	33.5	34.7	34.3
82.5°	25.3	24.9	24.8	24.5	24.8	24.9	25.3	25.4	25.4	26.3	26.2
85°	13.5	13.9	13.5	14.3	13.5	13.9	13.5	13.2	13.5	14.3	14.3
87.5°	12.6	12.4	12.7	12.5	12.7	12.4	12.6	12.6	12.9	13.0	13.1
90°	43.6	43.9	44.2	44.5	44.2	43.9	43.6	43.3	43.5	44.1	44.6
92.5°	42.2	42.3	42.4	42.4	42.4	42.3	42.2	42.2	42.1	42.0	41.9
95°	82.9	82.3	81.8	81.2	81.8	82.3	82.9	83.5	83.8	83.8	83.8
97.5°	140.8	140.8	140.7	140.7	140.7	140.8	140.8	140.9	140.9	140.9	140.9
100°	180.3	180.0	179.7	179.4	179.7	180.0	180.3	180.6	180.7	180.7	180.7
102.5°	224.3	224.0	223.7	223.4	223.7	224.0	224.3	224.6	224.6	224.4	224.1
105°	290.7	290.7	290.7	290.7	290.7	290.7	290.7	290.7	290.4	289.8	289.2
107.5°	358.1	356.8	355.4	354.1	355.4	356.8	358.1	359.4	360.0	359.7	359.5
110°	406.0	405.1	404.1	403.3	404.1	405.1	406.0	406.8	407.3	407.3	407.3



TEST NUMBER: P331798-840

CATALOG NUMBER: S122RDIW-S485D1240U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	452.3	451.7	451.1	450.4	451.1	451.7	452.3	453.0	453.6	454.3	455.0
115°	526.4	525.5	524.6	523.8	524.6	525.5	526.4	527.3	527.9	528.2	528.5
117.5°	596.3	595.4	594.6	593.7	594.6	595.4	596.3	597.2	597.9	598.6	599.4
120°	645.5	644.7	643.8	643.0	643.8	644.7	645.5	646.4	646.8	646.8	646.8
122.5°	693.1	692.4	691.8	691.2	691.8	692.4	693.1	693.7	694.4	695.1	695.8
125°	765.6	765.3	765.0	764.7	765.0	765.3	765.6	765.9	766.5	767.3	768.2
127.5°	834.6	833.6	832.7	831.7	832.7	833.6	834.6	835.5	836.5	837.5	838.6
130°	883.4	882.3	881.1	879.9	881.1	882.3	883.4	884.6	885.4	886.1	886.7
132.5°	928.9	927.9	927.0	926.0	927.0	927.9	928.9	929.8	930.9	932.1	933.4
135°	1000.4	999.6	998.7	997.7	998.7	999.6	1000.4	1001.3	1001.9	1002.2	1002.5
137.5°	1066.2	1065.1	1063.9	1062.8	1063.9	1065.1	1066.2	1067.4	1068.1	1068.3	1068.5
140°	1111.3	1110.1	1108.9	1107.8	1108.9	1110.1	1111.3	1112.5	1113.0	1113.0	1113.0
142.5°	1152.2	1150.9	1149.8	1148.6	1149.8	1150.9	1152.2	1153.3	1153.8	1153.6	1153.3
145°	1213.5	1212.2	1211.1	1209.9	1211.1	1212.2	1213.5	1214.6	1215.0	1214.8	1214.5
147.5°	1268.0	1266.9	1265.8	1264.7	1265.8	1266.9	1268.0	1269.1	1269.3	1268.7	1268.0
150°	1302.9	1302.0	1301.1	1300.3	1301.1	1302.0	1302.9	1303.7	1303.7	1302.9	1302.0
152.5°	1337.1	1336.1	1334.9	1333.8	1334.9	1336.1	1337.1	1338.2	1338.2	1337.1	1336.1
155°	1381.5	1380.6	1379.7	1378.9	1379.7	1380.6	1381.5	1382.3	1382.0	1380.6	1379.2
157.5°	1421.8	1420.4	1419.0	1417.5	1419.0	1420.4	1421.8	1423.2	1422.9	1420.9	1419.0
160°	1445.2	1444.0	1442.9	1441.7	1442.9	1444.0	1445.2	1446.3	1446.0	1444.3	1442.6
162.5°	1466.8	1465.4	1464.0	1462.7	1464.0	1465.4	1466.8	1468.2	1467.9	1465.9	1464.0
165°	1494.5	1493.1	1491.6	1490.2	1491.6	1493.1	1494.5	1495.9	1495.7	1493.6	1491.6
167.5°	1517.2	1515.7	1514.2	1512.7	1514.2	1515.7	1517.2	1518.7	1518.4	1516.4	1514.4
170°	1529.4	1527.7	1525.9	1524.2	1525.9	1527.7	1529.4	1531.2	1531.1	1528.9	1526.9
172.5°	1538.8	1537.1	1535.4	1533.6	1535.4	1537.1	1538.8	1540.5	1540.4	1538.4	1536.4
175°	1549.0	1547.3	1545.6	1543.8	1545.6	1547.3	1549.0	1550.8	1550.6	1548.6	1546.6
177.5°	1552.8	1551.4	1549.9	1548.5	1549.9	1551.4	1552.8	1554.1	1554.1	1552.8	1551.4
180°	1551.7	1551.7	1551.7	1551.7	1551.7	1551.7	1551.7	1551.7	1551.7	1551.7	1551.7



TEST NUMBER: P331798-840

CATALOG NUMBER: S122RDIW-S485D1240U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1085.4	1085.4	1085.4	1085.4	1085.4	1085.4	1085.4	1085.4	1085.4	1085.4	1085.4
2.5°	1043.7	1047.9	1054.3	1057.9	1063.9	1067.8	1070.0	1073.9	1076.0	1083.6	1091.4
5°	985.4	991.5	1002.0	1011.8	1022.4	1033.3	1041.3	1050.3	1058.5	1072.9	1088.0
7.5°	918.6	927.0	943.3	959.0	977.3	992.8	1006.4	1021.9	1035.7	1056.2	1077.6
10°	868.5	883.2	904.7	919.4	943.5	959.0	980.5	997.4	1016.7	1043.9	1068.0
12.5°	825.4	843.1	860.4	880.8	902.5	928.3	951.9	973.6	996.5	1024.6	1052.9
15°	747.1	772.7	799.5	820.2	849.7	876.8	904.3	933.7	961.7	995.2	1032.2
17.5°	646.3	676.0	721.0	756.6	791.1	818.4	852.4	888.1	920.9	961.4	1002.5
20°	600.8	622.6	653.2	701.0	753.2	782.1	816.9	856.1	893.7	937.9	982.0
22.5°	564.2	583.7	608.2	645.5	703.7	743.3	779.4	819.3	863.0	908.1	956.9
25°	512.1	525.7	551.4	581.5	621.5	686.7	726.3	766.3	813.9	862.1	917.9
27.5°	473.0	485.2	501.9	530.7	560.4	607.2	670.2	713.8	761.1	815.5	873.4
30°	443.1	457.5	475.9	496.2	528.8	565.3	628.2	678.8	725.6	781.4	843.2
32.5°	421.4	432.7	448.5	469.2	496.1	531.2	581.5	642.9	688.4	747.3	811.8
35°	385.8	399.0	411.8	431.4	453.3	485.3	523.4	589.1	634.3	692.4	757.3
37.5°	356.5	364.6	378.7	394.3	417.3	441.2	474.2	533.1	582.1	639.0	705.5
40°	334.2	344.3	354.9	372.2	391.1	414.0	446.5	490.3	546.4	602.3	667.1
42.5°	312.5	325.3	336.5	348.1	368.7	391.7	418.2	455.2	512.6	565.4	628.5
45°	286.2	294.6	306.2	319.0	336.0	355.7	379.0	411.4	466.5	512.1	571.4
47.5°	255.8	267.9	275.5	288.0	304.2	322.9	344.6	372.6	417.3	460.0	514.9
50°	235.0	247.4	258.3	269.6	284.0	302.1	320.1	347.3	383.1	428.1	479.3
52.5°	217.1	228.1	238.7	250.0	264.1	280.6	297.8	321.6	352.3	393.6	443.4
55°	192.7	199.4	210.5	221.8	234.2	250.0	266.6	286.6	313.1	347.7	388.1
57.5°	167.6	175.5	184.2	195.6	208.1	220.4	235.2	253.4	274.2	305.6	340.1
60°	153.5	159.6	166.7	178.3	190.1	201.0	215.3	230.5	250.0	277.2	306.6
62.5°	137.8	143.5	150.1	160.3	171.7	181.7	194.2	210.3	226.8	251.6	277.3
65°	111.6	120.0	126.3	135.4	144.8	155.4	165.2	178.0	192.7	212.3	235.3
67.5°	92.5	96.7	102.7	111.0	120.6	129.7	139.0	149.0	161.7	176.8	195.1
70°	84.1	85.6	86.7	94.6	103.7	112.8	121.4	130.9	141.8	154.2	170.1
72.5°	74.1	75.6	77.1	80.5	87.8	96.7	105.7	112.8	123.1	133.4	146.2
75°	58.9	61.1	62.2	64.1	66.8	72.8	81.1	87.9	93.9	101.8	112.0
77.5°	44.8	46.0	47.3	49.3	50.9	53.7	58.4	64.5	70.2	74.7	81.8
80°	35.4	35.9	37.4	38.1	40.4	42.2	44.5	49.4	55.0	57.0	61.8
82.5°	26.7	27.1	28.3	29.1	30.1	31.7	34.5	35.9	40.3	42.7	45.8
85°	14.7	14.3	15.5	15.5	16.3	17.0	17.8	19.6	20.7	23.7	24.5
87.5°	13.5	13.7	12.7	11.4	10.2	9.5	8.8	8.4	8.3	8.5	9.0
90°	45.2	45.8	39.4	33.0	26.7	20.2	15.2	11.8	8.3	4.8	1.3
92.5°	41.7	41.6	40.1	38.6	37.1	35.5	33.5	31.0	28.5	25.9	23.3
95°	83.8	83.8	83.2	82.6	82.1	81.5	79.8	76.9	73.9	71.0	68.1
97.5°	140.9	140.9	139.8	138.7	137.5	136.4	134.6	132.1	129.6	126.9	124.4
100°	180.7	180.7	179.9	178.9	178.0	177.2	175.6	173.3	171.0	168.6	166.3
102.5°	223.9	223.7	222.6	221.5	220.4	219.2	217.7	215.9	214.0	212.2	210.3
105°	288.6	288.1	287.5	286.9	286.3	285.8	285.0	284.2	283.3	282.4	281.6
107.5°	359.3	359.0	359.0	359.0	359.0	359.0	358.4	357.1	355.9	354.6	353.3
110°	407.3	407.3	407.3	407.3	407.3	407.3	406.4	404.7	402.8	401.1	399.4



TEST NUMBER: P331798-840

CATALOG NUMBER: S122RDIW-S485D1240U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	455.8	456.5	456.7	457.0	457.2	457.4	456.7	454.9	453.1	451.4	449.7
115°	528.8	529.0	529.6	530.2	530.8	531.3	530.8	529.0	527.3	525.5	523.8
117.5°	600.1	600.8	602.4	604.0	605.6	607.3	606.9	604.6	602.3	600.0	597.6
120°	646.8	646.8	649.1	651.6	653.9	656.2	656.2	653.9	651.6	649.1	646.8
122.5°	696.4	697.1	698.7	700.4	702.1	703.7	703.1	700.2	697.5	694.7	691.9
125°	769.1	769.9	770.8	771.7	772.5	773.5	772.5	769.9	767.3	764.7	762.0
127.5°	839.6	840.6	841.7	842.7	843.8	844.9	843.7	840.4	837.1	833.7	830.4
130°	887.2	887.8	888.4	889.0	889.6	890.1	888.5	884.7	881.0	877.2	873.4
132.5°	934.7	935.9	935.8	935.7	935.6	935.5	933.9	930.8	927.8	924.6	921.6
135°	1002.7	1003.0	1002.5	1001.9	1001.3	1000.7	998.9	995.6	992.4	989.2	986.0
137.5°	1068.8	1069.0	1068.2	1067.5	1066.7	1066.0	1064.3	1061.7	1059.0	1056.4	1053.8
140°	1113.0	1113.0	1111.6	1110.1	1108.6	1107.2	1105.2	1102.6	1099.9	1097.3	1094.7
142.5°	1153.1	1152.9	1151.9	1150.8	1149.8	1148.8	1147.1	1144.5	1141.9	1139.2	1136.6
145°	1214.2	1213.9	1212.1	1210.3	1208.6	1206.9	1205.0	1203.0	1200.9	1198.9	1196.8
147.5°	1267.4	1266.8	1265.6	1264.5	1263.2	1262.1	1260.3	1257.9	1255.4	1252.9	1250.5
150°	1301.1	1300.3	1299.1	1298.0	1296.8	1295.7	1294.1	1292.4	1290.7	1288.9	1287.2
152.5°	1334.9	1333.8	1332.4	1331.0	1329.6	1328.2	1326.7	1324.8	1323.1	1321.4	1319.7
155°	1377.7	1376.2	1375.3	1374.4	1373.6	1372.7	1371.9	1371.0	1370.1	1369.3	1368.4
157.5°	1416.9	1415.0	1414.4	1413.9	1413.4	1412.9	1412.3	1411.8	1411.2	1410.6	1410.0
160°	1440.8	1439.1	1438.8	1438.5	1438.1	1437.9	1437.4	1436.9	1436.3	1435.7	1435.1
162.5°	1462.0	1460.1	1459.8	1459.5	1459.2	1458.9	1458.6	1458.5	1458.4	1458.3	1458.1
165°	1489.6	1487.5	1487.5	1487.5	1487.5	1487.5	1487.6	1487.9	1488.2	1488.5	1488.8
167.5°	1512.4	1510.3	1510.4	1510.5	1510.5	1510.6	1511.0	1511.9	1512.8	1513.6	1514.5
170°	1524.9	1522.9	1523.2	1523.5	1523.8	1524.1	1524.6	1525.5	1526.4	1527.2	1528.1
172.5°	1534.4	1532.3	1532.6	1532.9	1533.2	1533.5	1534.1	1534.9	1535.8	1536.7	1537.5
175°	1544.6	1542.5	1543.1	1543.7	1544.3	1544.9	1545.6	1546.4	1547.3	1548.2	1549.0
177.5°	1549.9	1548.5	1549.0	1549.4	1549.9	1550.4	1551.0	1551.7	1552.4	1553.1	1553.8
180°	1551.7	1551.7	1551.7	1551.7	1551.7	1551.7	1551.7	1551.7	1551.7	1551.7	1551.7



TEST NUMBER: P331798-840

CATALOG NUMBER: S122RDIW-S485D1240U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1085.4	1085.4	1085.4	1085.4	1085.4	1085.4	1085.4	1085.4	1085.4	1085.4	1085.4
2.5°	1091.7	1092.6	1098.6	1101.4	1106.8	1108.9	1111.3	1110.6	1110.6	1111.9	1120.3
5°	1094.0	1101.6	1112.9	1123.8	1134.4	1143.5	1149.4	1155.5	1157.7	1168.7	1178.5
7.5°	1090.1	1104.0	1122.7	1139.3	1159.3	1175.0	1187.9	1199.6	1207.6	1223.6	1239.8
10°	1085.0	1104.6	1125.7	1147.2	1174.8	1195.5	1216.6	1232.8	1238.1	1261.8	1275.5
12.5°	1074.7	1101.0	1127.8	1155.7	1182.6	1211.1	1234.4	1250.6	1269.2	1290.5	1315.6
15°	1059.3	1089.5	1124.6	1160.4	1198.9	1233.6	1258.5	1286.8	1307.1	1330.5	1352.3
17.5°	1037.2	1076.1	1120.6	1162.2	1206.6	1243.9	1278.2	1305.3	1319.6	1332.9	1336.3
20°	1019.8	1061.6	1114.0	1163.1	1207.5	1250.5	1284.4	1307.1	1310.9	1311.2	1291.2
22.5°	1000.8	1048.0	1102.9	1153.1	1206.3	1254.2	1280.5	1290.2	1275.3	1249.7	1211.0
25°	965.8	1020.5	1084.2	1141.6	1199.6	1244.9	1253.9	1237.0	1184.6	1129.4	1059.8
27.5°	928.0	989.4	1057.7	1121.5	1183.4	1211.4	1191.8	1130.6	1036.2	954.2	854.7
30°	900.2	969.2	1036.3	1107.6	1164.9	1177.0	1132.2	1042.0	931.9	808.2	709.0
32.5°	868.5	940.8	1014.6	1088.3	1136.3	1124.5	1050.4	939.4	810.3	688.7	594.9
35°	823.2	898.0	977.4	1051.4	1082.0	1031.1	920.2	775.8	643.8	530.3	465.7
37.5°	771.0	852.3	935.0	1002.9	1000.8	915.8	764.9	615.7	504.8	437.7	391.7
40°	733.9	816.1	905.4	962.8	938.3	827.8	664.1	523.4	442.3	388.8	355.3
42.5°	698.3	780.8	869.6	915.1	872.5	736.7	573.6	463.4	396.5	354.8	327.5
45°	637.7	724.8	807.1	832.3	756.1	606.4	463.8	384.0	339.4	308.5	289.6
47.5°	578.6	664.2	739.2	739.7	636.6	491.8	391.3	332.2	294.3	270.3	256.6
50°	542.3	623.8	686.7	676.9	560.1	437.5	349.9	299.0	267.4	248.9	234.6
52.5°	501.6	580.6	635.1	607.2	495.1	385.0	312.9	270.1	243.9	227.8	215.0
55°	442.3	512.5	551.0	508.8	403.9	320.1	264.4	230.8	211.2	197.6	186.7
57.5°	384.3	442.0	466.3	417.1	332.6	265.5	223.6	198.4	178.9	169.3	163.6
60°	347.7	397.1	414.0	359.8	289.2	232.3	198.0	174.6	160.3	153.9	148.2
62.5°	311.8	352.1	359.2	309.4	252.2	203.4	173.9	154.1	144.6	138.5	133.1
65°	258.7	287.7	284.4	244.4	199.4	161.4	139.9	127.8	120.7	112.0	102.6
67.5°	213.0	230.8	220.0	190.1	152.3	125.4	111.4	102.3	93.4	85.1	83.0
70°	184.0	194.2	182.9	155.4	124.8	105.2	93.9	83.0	77.7	75.8	72.4
72.5°	156.3	159.9	147.6	124.0	101.6	87.2	76.1	70.0	67.2	65.5	63.3
75°	117.2	114.6	104.1	85.6	70.5	60.7	57.4	55.0	53.2	51.7	50.5
77.5°	82.4	78.5	69.1	57.1	49.1	44.4	42.4	41.2	40.3	39.5	38.4
80°	61.8	59.2	49.8	40.7	37.4	35.0	33.9	32.4	32.4	31.7	30.5
82.5°	45.2	42.3	34.1	29.9	28.0	26.7	25.8	24.8	24.5	24.7	23.9
85°	23.7	19.2	17.0	16.3	15.0	14.3	14.7	13.9	13.9	13.9	13.5
87.5°	8.2	7.4	7.8	8.2	9.5	10.8	11.7	13.0	14.6	14.1	14.3
90°	4.8	8.3	11.8	15.2	20.2	26.7	33.0	39.4	45.8	45.2	44.6
92.5°	25.9	28.5	31.0	33.5	35.5	37.1	38.6	40.1	41.6	41.7	41.9
95°	71.0	73.9	76.9	79.8	81.5	82.1	82.6	83.2	83.8	83.8	83.8
97.5°	126.9	129.6	132.1	134.6	136.4	137.5	138.7	139.8	140.9	140.9	140.9
100°	168.6	171.0	173.3	175.6	177.2	178.0	178.9	179.9	180.7	180.7	180.7
102.5°	212.2	214.0	215.9	217.7	219.2	220.4	221.5	222.6	223.7	223.9	224.1
105°	282.4	283.3	284.2	285.0	285.8	286.3	286.9	287.5	288.1	288.6	289.2
107.5°	354.6	355.9	357.1	358.4	359.0	359.0	359.0	359.0	359.0	359.3	359.5
110°	401.1	402.8	404.7	406.4	407.3	407.3	407.3	407.3	407.3	407.3	407.3



TEST NUMBER: P331798-840

CATALOG NUMBER: S122RDIW-S485D1240U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	451.4	453.1	454.9	456.7	457.4	457.2	457.0	456.7	456.5	455.8	455.0
115°	525.5	527.3	529.0	530.8	531.3	530.8	530.2	529.6	529.0	528.8	528.5
117.5°	600.0	602.3	604.6	606.9	607.3	605.6	604.0	602.4	600.8	600.1	599.4
120°	649.1	651.6	653.9	656.2	656.2	653.9	651.6	649.1	646.8	646.8	646.8
122.5°	694.7	697.5	700.2	703.1	703.7	702.1	700.4	698.7	697.1	696.4	695.8
125°	764.7	767.3	769.9	772.5	773.5	772.5	771.7	770.8	769.9	769.1	768.2
127.5°	833.7	837.1	840.4	843.7	844.9	843.8	842.7	841.7	840.6	839.6	838.6
130°	877.2	881.0	884.7	888.5	890.1	889.6	889.0	888.4	887.8	887.2	886.7
132.5°	924.6	927.8	930.8	933.9	935.5	935.6	935.7	935.8	935.9	934.7	933.4
135°	989.2	992.4	995.6	998.9	1000.7	1001.3	1001.9	1002.5	1003.0	1002.7	1002.5
137.5°	1056.4	1059.0	1061.7	1064.3	1066.0	1066.7	1067.5	1068.2	1069.0	1068.8	1068.5
140°	1097.3	1099.9	1102.6	1105.2	1107.2	1108.6	1110.1	1111.6	1113.0	1113.0	1113.0
142.5°	1139.2	1141.9	1144.5	1147.1	1148.8	1149.8	1150.8	1151.9	1152.9	1153.1	1153.3
145°	1198.9	1200.9	1203.0	1205.0	1206.9	1208.6	1210.3	1212.1	1213.9	1214.2	1214.5
147.5°	1252.9	1255.4	1257.9	1260.3	1262.1	1263.2	1264.5	1265.6	1266.8	1267.4	1268.0
150°	1288.9	1290.7	1292.4	1294.1	1295.7	1296.8	1298.0	1299.1	1300.3	1301.1	1302.0
152.5°	1321.4	1323.1	1324.8	1326.7	1328.2	1329.6	1331.0	1332.4	1333.8	1334.9	1336.1
155°	1369.3	1370.1	1371.0	1371.9	1372.7	1373.6	1374.4	1375.3	1376.2	1377.7	1379.2
157.5°	1410.6	1411.2	1411.8	1412.3	1412.9	1413.4	1413.9	1414.4	1415.0	1416.9	1419.0
160°	1435.7	1436.3	1436.9	1437.4	1437.9	1438.1	1438.5	1438.8	1439.1	1440.8	1442.6
162.5°	1458.3	1458.4	1458.5	1458.6	1458.9	1459.2	1459.5	1459.8	1460.1	1462.0	1464.0
165°	1488.5	1488.2	1487.9	1487.6	1487.5	1487.5	1487.5	1487.5	1487.5	1489.6	1491.6
167.5°	1513.6	1512.8	1511.9	1511.0	1510.6	1510.5	1510.5	1510.4	1510.3	1512.4	1514.4
170°	1527.2	1526.4	1525.5	1524.6	1524.1	1523.8	1523.5	1523.2	1522.9	1524.9	1526.9
172.5°	1536.7	1535.8	1534.9	1534.1	1533.5	1533.2	1532.9	1532.6	1532.3	1534.4	1536.4
175°	1548.2	1547.3	1546.4	1545.6	1544.9	1544.3	1543.7	1543.1	1542.5	1544.6	1546.6
177.5°	1553.1	1552.4	1551.7	1551.0	1550.4	1549.9	1549.4	1549.0	1548.5	1549.9	1551.4
180°	1551.7	1551.7	1551.7	1551.7	1551.7	1551.7	1551.7	1551.7	1551.7	1551.7	1551.7



TEST NUMBER: P331798-840

CATALOG NUMBER: S122RDIW-S485D1240U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1085.4	1085.4	1085.4	1085.4	1085.4	1085.4	1085.4
2.5°	1123.4	1127.3	1129.1	1129.1	1131.3	1130.3	1129.4
5°	1187.9	1195.1	1196.6	1203.4	1208.3	1206.8	1207.5
7.5°	1252.1	1263.6	1275.1	1280.2	1281.1	1284.1	1285.3
10°	1291.6	1301.1	1318.8	1316.2	1329.4	1336.9	1324.4
12.5°	1329.7	1342.4	1354.7	1358.1	1365.5	1368.0	1363.0
15°	1364.0	1370.8	1371.6	1369.7	1372.0	1370.1	1362.9
17.5°	1331.9	1320.9	1298.6	1288.0	1279.6	1267.3	1262.3
20°	1278.8	1246.4	1208.7	1193.6	1175.9	1141.1	1149.4
22.5°	1164.2	1127.2	1089.5	1045.4	1024.4	991.5	989.6
25°	985.8	922.1	851.9	802.8	774.3	741.4	727.1
27.5°	766.5	686.2	628.7	599.7	573.1	547.1	546.0
30°	622.3	561.9	517.5	492.5	476.4	465.3	467.7
32.5°	524.5	483.1	453.1	432.5	420.5	412.2	412.1
35°	428.8	400.5	381.2	372.6	364.0	357.9	358.3
37.5°	367.0	349.9	339.2	329.7	324.3	321.3	319.6
40°	335.3	321.3	313.1	307.4	302.9	298.7	297.9
42.5°	310.2	298.7	290.3	285.9	281.8	278.7	278.0
45°	275.3	265.9	258.3	253.4	251.6	248.9	248.9
47.5°	244.9	235.6	229.7	226.6	223.4	221.7	221.6
50°	224.4	217.2	212.0	210.1	207.4	206.3	205.9
52.5°	206.0	200.7	196.8	195.6	194.4	193.0	193.2
55°	181.0	178.0	176.5	175.3	173.5	171.2	172.7
57.5°	160.0	157.4	153.3	149.8	148.0	146.4	147.0
60°	145.2	139.9	134.6	130.5	129.4	125.9	125.9
62.5°	126.5	119.1	112.6	110.3	109.2	107.6	107.2
65°	97.3	94.3	92.8	91.3	90.5	90.5	89.8
67.5°	80.6	79.4	77.8	77.4	76.6	76.4	76.1
70°	71.3	69.8	69.0	68.7	67.9	68.3	67.2
72.5°	62.2	61.0	60.9	59.9	59.5	59.5	58.7
75°	49.0	49.0	48.7	48.3	47.6	47.2	47.6
77.5°	37.7	37.8	37.1	37.1	37.0	37.1	36.7
80°	30.2	30.5	30.2	29.8	29.4	29.8	29.4
82.5°	23.8	23.3	23.2	23.1	23.1	22.8	22.8
85°	13.5	13.9	13.5	13.2	13.2	13.2	13.5
87.5°	13.9	13.8	13.8	13.8	13.9	13.9	13.7
90°	44.1	43.5	43.3	43.6	43.9	44.2	44.5
92.5°	42.0	42.1	42.2	42.2	42.3	42.4	42.4
95°	83.8	83.8	83.5	82.9	82.3	81.8	81.2
97.5°	140.9	140.9	140.9	140.8	140.8	140.7	140.7
100°	180.7	180.7	180.6	180.3	180.0	179.7	179.4
102.5°	224.4	224.6	224.6	224.3	224.0	223.7	223.4
105°	289.8	290.4	290.7	290.7	290.7	290.7	290.7
107.5°	359.7	360.0	359.4	358.1	356.8	355.4	354.1
110°	407.3	407.3	406.8	406.0	405.1	404.1	403.3



TEST NUMBER: P331798-840

CATALOG NUMBER: S122RDIW-S485D1240U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	454.3	453.6	453.0	452.3	451.7	451.1	450.4
115°	528.2	527.9	527.3	526.4	525.5	524.6	523.8
117.5°	598.6	597.9	597.2	596.3	595.4	594.6	593.7
120°	646.8	646.8	646.4	645.5	644.7	643.8	643.0
122.5°	695.1	694.4	693.7	693.1	692.4	691.8	691.2
125°	767.3	766.5	765.9	765.6	765.3	765.0	764.7
127.5°	837.5	836.5	835.5	834.6	833.6	832.7	831.7
130°	886.1	885.4	884.6	883.4	882.3	881.1	879.9
132.5°	932.1	930.9	929.8	928.9	927.9	927.0	926.0
135°	1002.2	1001.9	1001.3	1000.4	999.6	998.7	997.7
137.5°	1068.3	1068.1	1067.4	1066.2	1065.1	1063.9	1062.8
140°	1113.0	1113.0	1112.5	1111.3	1110.1	1108.9	1107.8
142.5°	1153.6	1153.8	1153.3	1152.2	1150.9	1149.8	1148.6
145°	1214.8	1215.0	1214.6	1213.5	1212.2	1211.1	1209.9
147.5°	1268.7	1269.3	1269.1	1268.0	1266.9	1265.8	1264.7
150°	1302.9	1303.7	1303.7	1302.9	1302.0	1301.1	1300.3
152.5°	1337.1	1338.2	1338.2	1337.1	1336.1	1334.9	1333.8
155°	1380.6	1382.0	1382.3	1381.5	1380.6	1379.7	1378.9
157.5°	1420.9	1422.9	1423.2	1421.8	1420.4	1419.0	1417.5
160°	1444.3	1446.0	1446.3	1445.2	1444.0	1442.9	1441.7
162.5°	1465.9	1467.9	1468.2	1466.8	1465.4	1464.0	1462.7
165°	1493.6	1495.7	1495.9	1494.5	1493.1	1491.6	1490.2
167.5°	1516.4	1518.4	1518.7	1517.2	1515.7	1514.2	1512.7
170°	1528.9	1531.1	1531.2	1529.4	1527.7	1525.9	1524.2
172.5°	1538.4	1540.4	1540.5	1538.8	1537.1	1535.4	1533.6
175°	1548.6	1550.6	1550.8	1549.0	1547.3	1545.6	1543.8
177.5°	1552.8	1554.1	1554.1	1552.8	1551.4	1549.9	1548.5
180°	1551.7	1551.7	1551.7	1551.7	1551.7	1551.7	1551.7

(END OF REPORT)