

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331799-840

Luminaire Tested: **S122RDIW-S485D1240U840-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331799-840
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122RDIW-S485D1240U840-4F0-1E-UDD-F
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 485 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 1240 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6721.3 lumens
Efficiency: N/A
Efficacy: 124.9 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 53.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331799-840

CATALOG NUMBER: S122RDIW-S485D1240U840-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P331799-840

CATALOG NUMBER: S122RDIW-S485D1240U840-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	101	101	101	101	90	90	90	90	70	70	70	51	51	51	34	34	34
1	93	88	85	82	82	79	76	73	61	59	57	45	44	43	30	29	29
2	84	77	72	67	75	69	64	60	54	51	48	40	38	36	27	26	25
3	77	68	61	56	69	61	55	51	48	44	41	35	33	31	24	22	21
4	71	60	53	47	63	54	48	43	42	38	35	32	29	26	21	20	18
5	65	54	46	41	58	48	42	37	38	33	30	28	25	23	19	18	16
6	60	48	41	35	53	43	37	32	34	30	26	26	23	20	18	16	14
7	55	43	36	31	49	39	33	28	31	26	23	23	20	18	16	14	13
8	51	39	32	27	45	35	29	25	28	24	20	21	18	16	15	13	12
9	47	36	29	24	42	32	26	22	26	21	18	20	16	14	14	12	10
10	44	33	26	21	39	30	24	20	24	19	16	18	15	13	13	11	9

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	13454	13454	13454
5°	13506	13287	13361
10°	13404	13070	12959
15°	13249	12682	12318
20°	13036	12129	11519
25°	12818	11501	10750
30°	12515	10856	9758
35°	12220	10153	8889
40°	11921	9428	7885
45°	11574	8611	6976
50°	11215	7784	6081
55°	10849	6899	5222
60°	10424	5968	4334
65°	9941	5012	3947
70°	9361	4131	3635
75°	8659	3762	3387
80°	7643	3366	3087
85°	6002	2649	2649



TEST NUMBER: P331799-840

CATALOG NUMBER: S122RDIW-S485D1240U840-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	78.0	1.2
10°-20°	214.2	3.2
20°-30°	300.8	4.5
30°-40°	328.0	4.9
40°-50°	301.6	4.5
50°-60°	236.8	3.5
60°-70°	154.4	2.3
70°-80°	79.6	1.2
80°-90°	24.9	0.4
90°-100°	56.9	0.8
100°-110°	208.8	3.1
110°-120°	558.2	8.3
120°-130°	921.5	13.7
130°-140°	980.0	14.6
140°-150°	910.9	13.6
150°-160°	732.3	10.9
160°-170°	471.9	7.0
170°-180°	162.4	2.4
0°-30°	593.0	8.8
0°-40°	921.0	13.7
0°-60°	1459.4	21.7
0°-90°	1718.3	25.6
90°-120°	824.0	12.3
90°-150°	3636.4	54.1
90°-180°	5003.0	74.4
0°-180°	6721.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	833	833	833	833	833	
5°	833	829	820	826	824	79
15°	793	783	759	745	737	223
25°	720	694	646	616	603	331
35°	620	580	515	469	451	388
45°	507	455	377	326	306	391
55°	385	325	245	202	186	344
65°	260	199	131	107	103	258
75°	139	87	60	55	54	147
85°	32	17	14	14	14	38
90°	1	15	25	31	33	5
95°	80	42	48	54	53	98
105°	376	392	75	88	94	401
115°	710	732	762	217	101	699
125°	1004	1021	1044	1052	1056	895
135°	1243	1262	1274	1285	1284	959
145°	1442	1442	1461	1469	1464	901
155°	1587	1578	1591	1598	1589	731
165°	1673	1666	1669	1677	1669	472
175°	1711	1703	1705	1712	1701	163
180°	1707	1707	1707	1707	1707	



TEST NUMBER: P331799-840

CATALOG NUMBER: S122RDIW-S485D1240U840-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	833.3	833.3	833.3	833.3	833.3	833.3	833.3	833.3	833.3	833.3	833.3
2.5°	836.4	835.8	835.1	834.4	833.7	832.6	831.2	829.7	828.2	826.8	828.1
5°	833.3	832.5	831.7	830.9	830.0	828.5	826.4	824.2	822.0	819.8	821.3
7.5°	824.8	823.7	822.7	821.6	820.6	818.8	816.3	813.7	811.2	808.7	809.1
10°	817.6	816.4	815.2	814.1	812.8	810.6	807.3	803.9	800.5	797.2	796.7
12.5°	808.5	807.1	805.6	804.2	802.7	799.9	795.6	791.3	787.0	782.7	781.8
15°	792.6	790.8	789.0	787.1	785.3	781.5	775.8	770.1	764.5	758.7	755.6
17.5°	773.3	770.4	767.6	764.8	761.9	756.9	749.6	742.3	735.0	727.6	723.9
20°	758.7	755.4	752.0	748.7	745.3	739.4	731.0	722.7	714.3	705.9	701.8
22.5°	743.1	739.3	735.5	731.7	728.0	721.4	712.0	702.5	693.1	683.6	678.2
25°	719.5	714.2	708.8	703.4	698.0	689.8	678.7	667.7	656.6	645.6	638.7
27.5°	691.2	685.3	679.4	673.7	667.8	658.6	646.2	633.7	621.3	608.7	600.8
30°	671.3	664.9	658.5	652.2	645.8	635.9	622.5	609.0	595.6	582.3	573.7
32.5°	652.0	644.5	637.0	629.7	622.2	611.6	597.9	584.2	570.6	556.9	547.1
35°	620.0	611.4	602.9	594.3	585.7	574.1	559.4	544.6	529.9	515.1	504.5
37.5°	587.9	578.6	569.2	559.8	550.5	537.9	522.2	506.4	490.7	475.0	463.3
40°	565.6	555.6	545.5	535.5	525.4	512.3	496.0	479.8	463.5	447.3	435.4
42.5°	542.7	532.1	521.5	511.0	500.4	486.7	469.9	453.0	436.3	419.5	407.2
45°	506.9	495.6	484.3	473.1	461.9	447.5	429.9	412.3	394.7	377.1	365.2
47.5°	471.8	459.9	448.1	436.2	424.2	409.2	391.0	372.8	354.7	336.5	324.7
50°	446.5	434.5	422.7	410.8	398.9	383.7	365.3	346.9	328.4	309.9	298.4
52.5°	421.7	409.3	396.9	384.5	372.0	356.8	338.7	320.7	302.7	284.7	273.5
55°	385.4	372.3	359.2	346.2	333.2	317.5	299.4	281.3	263.2	245.1	235.1
57.5°	348.1	334.8	321.3	307.9	294.5	279.1	261.8	244.3	226.9	209.5	200.3
60°	322.8	309.4	296.0	282.6	269.1	253.9	236.6	219.3	202.1	184.8	176.2
62.5°	298.0	284.7	271.2	257.8	244.4	229.5	213.1	196.6	180.2	163.7	155.5
65°	260.2	246.6	233.1	219.4	205.9	191.6	176.5	161.4	146.3	131.2	125.5
67.5°	223.7	210.3	196.7	183.3	169.8	156.2	142.7	129.2	115.5	102.0	99.4
70°	198.3	185.3	172.2	159.2	146.0	133.7	122.2	110.6	99.1	87.5	85.8
72.5°	174.2	161.7	149.2	136.6	124.1	113.2	103.9	94.6	85.3	76.0	74.6
75°	138.8	127.0	115.3	103.6	91.8	83.1	77.5	71.7	66.0	60.3	59.2
77.5°	103.9	93.6	83.3	73.0	62.8	56.2	53.5	50.8	48.0	45.2	44.5
80°	82.2	73.6	65.1	56.6	48.0	42.9	41.2	39.6	37.9	36.2	35.5
82.5°	62.3	55.6	49.0	42.3	35.6	31.7	30.6	29.4	28.3	27.2	26.8
85°	32.4	28.9	25.3	21.9	18.4	16.4	15.9	15.3	14.8	14.3	14.3
87.5°	9.9	9.4	9.0	8.5	8.0	8.0	8.5	8.9	9.3	9.8	9.9
90°	1.2	4.2	7.3	10.3	13.3	16.0	18.1	20.3	22.5	24.7	26.1
92.5°	24.9	24.6	24.4	24.1	23.8	24.2	25.3	26.5	27.6	28.7	29.4
95°	80.3	71.2	62.2	53.1	44.0	40.5	42.4	44.3	46.3	48.2	49.6
97.5°	159.4	133.8	108.3	82.8	57.3	46.7	51.1	55.5	60.1	64.5	65.5
100°	218.6	181.1	143.4	105.8	68.3	51.7	56.5	61.1	65.7	70.4	72.6
102.5°	283.9	275.9	267.9	260.0	252.1	228.5	189.5	150.5	111.4	72.4	75.2
105°	375.6	383.7	392.0	400.2	408.5	375.2	300.2	225.2	150.3	75.3	78.4
107.5°	480.1	486.7	493.3	500.0	506.6	465.0	375.2	285.3	195.4	105.5	102.4
110°	547.2	553.0	558.8	564.5	570.3	533.5	454.2	374.9	295.5	216.2	188.7



TEST NUMBER: P331799-840

CATALOG NUMBER: S122RDIW-S485D1240U840-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	610.5	615.6	620.7	625.8	631.0	623.7	604.1	584.5	564.9	545.2	445.1
115°	710.3	715.0	719.6	724.3	729.0	734.8	741.6	748.5	755.4	762.2	635.1
117.5°	799.5	804.8	809.9	815.2	820.4	825.4	830.0	834.8	839.5	844.2	813.4
120°	864.7	868.9	872.9	877.1	881.2	885.8	890.7	895.6	900.6	905.4	908.8
122.5°	920.1	924.4	928.8	933.1	937.5	942.3	947.7	953.0	958.5	963.8	965.7
125°	1004.3	1007.8	1011.5	1015.0	1018.5	1023.0	1028.2	1033.4	1038.6	1043.9	1045.8
127.5°	1080.7	1084.6	1088.5	1092.6	1096.5	1100.4	1104.3	1108.2	1112.1	1116.0	1118.8
130°	1129.1	1133.5	1137.9	1142.3	1146.7	1150.3	1153.4	1156.4	1159.4	1162.5	1165.5
132.5°	1178.5	1182.2	1186.0	1189.7	1193.5	1196.8	1199.8	1202.9	1205.9	1208.9	1211.4
135°	1242.7	1247.1	1251.5	1255.9	1260.3	1263.7	1266.2	1268.7	1271.1	1273.6	1276.4
137.5°	1307.7	1310.8	1313.8	1317.0	1320.0	1322.9	1325.8	1328.6	1331.3	1334.1	1336.9
140°	1350.2	1352.4	1354.6	1356.8	1359.0	1361.6	1364.6	1367.7	1370.7	1373.7	1376.1
142.5°	1385.8	1387.8	1389.8	1391.7	1393.7	1396.4	1399.9	1403.3	1406.7	1410.3	1412.5
145°	1441.6	1441.4	1441.1	1440.8	1440.6	1442.7	1447.4	1452.1	1456.7	1461.4	1463.3
147.5°	1490.3	1489.2	1488.2	1487.1	1486.1	1487.9	1492.5	1497.1	1501.8	1506.3	1507.8
150°	1522.0	1520.0	1518.1	1516.1	1514.2	1515.5	1519.8	1524.3	1528.6	1533.1	1534.7
152.5°	1548.6	1546.5	1544.3	1542.2	1540.0	1541.1	1545.2	1549.4	1553.6	1557.7	1559.4
155°	1587.4	1584.9	1582.5	1579.9	1577.5	1577.9	1581.2	1584.5	1587.8	1591.1	1592.8
157.5°	1617.8	1615.7	1613.6	1611.5	1609.4	1609.5	1611.8	1614.2	1616.5	1618.8	1620.6
160°	1635.6	1634.0	1632.2	1630.6	1629.0	1629.0	1630.6	1632.2	1634.0	1635.6	1637.2
162.5°	1651.4	1649.7	1648.1	1646.5	1644.8	1644.7	1646.1	1647.5	1649.0	1650.4	1652.2
165°	1672.6	1671.0	1669.3	1667.7	1666.1	1665.7	1666.5	1667.3	1668.1	1668.9	1670.8
167.5°	1688.5	1686.8	1685.2	1683.5	1681.8	1681.4	1682.2	1682.9	1683.7	1684.5	1686.4
170°	1697.4	1695.7	1694.0	1692.4	1690.7	1690.2	1690.7	1691.3	1691.8	1692.4	1694.4
172.5°	1703.2	1701.6	1700.0	1698.3	1696.7	1696.2	1696.7	1697.2	1697.8	1698.3	1700.2
175°	1710.9	1709.0	1707.1	1705.2	1703.2	1702.5	1703.1	1703.6	1704.2	1704.8	1706.7
177.5°	1712.1	1710.6	1709.1	1707.6	1706.0	1705.4	1705.6	1705.8	1706.0	1706.3	1707.8
180°	1707.2	1707.2	1707.2	1707.2	1707.2	1707.2	1707.2	1707.2	1707.2	1707.2	1707.2



TEST NUMBER: P331799-840

CATALOG NUMBER: S122RDIW-S485D1240U840-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	833.3	833.3	833.3	833.3	833.3	833.3	833.3	833.3
2.5°	829.4	830.8	832.1	832.6	832.4	832.1	831.8	831.6
5°	822.8	824.4	825.9	826.4	825.9	825.4	824.9	824.4
7.5°	809.5	809.9	810.4	810.2	809.3	808.4	807.6	806.7
10°	796.2	795.7	795.2	794.5	793.5	792.4	791.4	790.4
12.5°	780.9	780.0	779.1	777.8	776.1	774.5	772.7	771.1
15°	752.3	749.2	746.0	743.6	741.8	740.2	738.5	736.9
17.5°	720.0	716.3	712.5	709.1	706.3	703.4	700.5	697.6
20°	697.5	693.4	689.1	685.2	681.6	677.8	674.2	670.4
22.5°	672.8	667.4	662.1	657.9	655.2	652.5	649.7	646.9
25°	631.9	625.0	618.1	613.4	610.9	608.3	605.9	603.4
27.5°	592.8	584.7	576.7	570.8	566.7	562.8	558.8	554.8
30°	565.1	556.6	548.1	541.5	536.9	532.5	528.0	523.4
32.5°	537.3	527.7	517.9	510.9	506.6	502.4	498.1	493.8
35°	494.0	483.4	472.9	465.7	462.1	458.4	454.7	451.0
37.5°	451.7	440.1	428.5	420.5	416.4	412.1	407.9	403.6
40°	423.4	411.5	399.6	391.5	387.2	382.8	378.4	374.1
42.5°	394.9	382.5	370.3	362.0	357.8	353.6	349.3	345.1
45°	353.3	341.4	329.5	321.5	317.5	313.5	309.4	305.5
47.5°	312.9	301.0	289.2	281.4	277.8	274.2	270.4	266.8
50°	286.8	275.3	263.7	256.2	252.7	249.1	245.6	242.1
52.5°	262.3	251.2	239.9	232.8	229.5	226.3	223.0	219.7
55°	225.0	214.9	204.9	198.2	195.1	191.9	188.7	185.5
57.5°	191.1	181.9	172.7	166.7	164.0	161.4	158.6	155.9
60°	167.6	159.2	150.6	145.0	142.3	139.6	136.9	134.2
62.5°	147.3	139.3	131.1	126.2	124.6	123.0	121.4	119.8
65°	119.9	114.1	108.5	105.3	104.8	104.3	103.8	103.3
67.5°	96.7	94.1	91.5	90.0	89.4	88.9	88.4	87.8
70°	84.1	82.5	80.8	79.6	79.0	78.3	77.6	77.0
72.5°	73.2	71.8	70.4	69.5	69.1	68.7	68.3	67.9
75°	58.0	56.9	55.6	54.9	54.8	54.6	54.4	54.3
77.5°	43.9	43.2	42.6	42.1	41.8	41.6	41.3	41.0
80°	34.8	34.2	33.5	33.2	33.2	33.2	33.2	33.2
82.5°	26.4	26.0	25.5	25.3	25.3	25.3	25.3	25.3
85°	14.3	14.3	14.3	14.3	14.3	14.3	14.3	14.3
87.5°	10.1	10.2	10.3	10.5	10.6	10.7	10.8	10.9
90°	27.5	28.8	30.2	31.2	31.7	32.2	32.8	33.3
92.5°	30.1	30.8	31.5	32.0	32.3	32.7	33.0	33.3
95°	50.9	52.3	53.6	54.2	53.9	53.6	53.4	53.1
97.5°	66.7	67.8	68.9	69.6	69.9	70.3	70.6	70.9
100°	74.8	77.0	79.2	80.6	81.1	81.7	82.2	82.8
102.5°	78.1	81.0	83.8	85.6	86.3	87.2	88.0	88.7
105°	81.4	84.4	87.5	89.5	90.6	91.7	92.8	93.9
107.5°	99.4	96.2	93.2	92.2	93.3	94.4	95.5	96.6
110°	161.3	133.8	106.3	93.2	94.3	95.4	96.5	97.6



TEST NUMBER: P331799-840

CATALOG NUMBER: S122RDIW-S485D1240U840-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	345.0	244.9	144.7	95.0	95.9	96.8	97.7	98.6
115°	508.0	380.9	253.8	180.4	160.6	140.9	121.1	101.3
117.5°	782.7	751.9	721.2	673.4	608.4	543.5	478.6	413.5
120°	912.1	915.3	918.7	901.8	864.7	827.7	790.6	753.6
122.5°	967.8	969.8	971.7	969.1	961.9	954.7	947.6	940.3
125°	1047.7	1049.7	1051.6	1052.9	1053.7	1054.6	1055.4	1056.2
127.5°	1121.6	1124.4	1127.2	1128.7	1128.8	1129.0	1129.1	1129.3
130°	1168.5	1171.5	1174.5	1175.9	1175.6	1175.4	1175.1	1174.8
132.5°	1214.1	1216.6	1219.2	1220.3	1220.1	1219.8	1219.5	1219.3
135°	1279.1	1281.8	1284.6	1285.7	1285.2	1284.6	1284.0	1283.5
137.5°	1339.5	1342.2	1344.9	1345.7	1344.8	1343.9	1343.0	1342.0
140°	1378.7	1381.1	1383.6	1384.1	1382.7	1381.4	1380.0	1378.7
142.5°	1414.7	1417.0	1419.3	1419.7	1418.4	1416.9	1415.5	1414.2
145°	1465.2	1467.1	1469.1	1469.4	1467.9	1466.6	1465.2	1463.9
147.5°	1509.2	1510.7	1512.1	1512.2	1511.1	1509.8	1508.7	1507.6
150°	1536.3	1538.0	1539.6	1539.7	1538.4	1537.0	1535.6	1534.3
152.5°	1561.0	1562.7	1564.4	1564.3	1562.5	1560.6	1558.8	1557.0
155°	1594.4	1596.1	1597.7	1597.4	1595.2	1593.1	1590.8	1588.6
157.5°	1622.6	1624.4	1626.3	1626.1	1624.0	1621.8	1619.7	1617.5
160°	1638.9	1640.5	1642.1	1642.0	1640.1	1638.2	1636.3	1634.4
162.5°	1654.2	1656.0	1657.9	1657.6	1655.3	1652.8	1650.5	1648.2
165°	1672.7	1674.7	1676.6	1676.6	1674.7	1672.7	1670.8	1668.9
167.5°	1688.3	1690.2	1692.1	1691.9	1689.4	1687.0	1684.5	1682.0
170°	1696.3	1698.2	1700.1	1699.8	1697.4	1694.9	1692.4	1689.9
172.5°	1702.1	1704.0	1706.0	1705.8	1703.2	1700.8	1698.3	1695.9
175°	1708.6	1710.5	1712.4	1712.0	1709.3	1706.6	1703.7	1701.0
177.5°	1709.3	1710.8	1712.4	1712.1	1710.2	1708.2	1706.3	1704.2
180°	1707.2	1707.2	1707.2	1707.2	1707.2	1707.2	1707.2	1707.2

(END OF REPORT)