

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331802-840

Luminaire Tested: **S122RDIW-S485D1440U840-4F0-1E-UDD-A1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331802-840
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-8,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122RDIW-S485D1440U840-4F0-1E-UDD-A1
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 485 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 1440 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6927.4 lumens
Efficiency: N/A
Efficacy: 114.3 lumens/watt
Spacing Criteria (0/90/45): 0.86 / 1.16 / 1.02
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 60.6
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331802-840

CATALOG NUMBER: S122RDIW-S485D1440U840-4F0-1E-UDD-A1

Luminous Intensity Polar Plot



73% Up

27% Dn



TEST NUMBER: P331802-840

CATALOG NUMBER: S122RDIW-S485D1440U840-4F0-1E-UDD-A1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	102	102	102	102	91	91	91	91	71	71	71	52	52	52	35	35	35	27
1	93	89	85	82	83	80	77	74	62	60	59	46	45	44	32	31	30	24
2	85	78	73	68	76	70	65	61	55	52	49	41	39	37	28	27	26	21
3	78	69	62	57	69	62	56	52	49	45	42	37	34	32	26	24	23	18
4	71	61	54	48	64	55	49	44	44	39	36	33	30	28	23	21	20	16
5	66	55	47	42	59	49	43	38	39	35	31	30	27	24	21	19	18	14
6	60	49	42	36	54	44	38	33	35	31	27	27	24	22	19	17	16	13
7	56	44	37	32	50	40	34	29	32	28	24	25	22	19	18	16	14	11
8	52	40	33	28	46	37	30	26	29	25	22	23	20	17	16	14	13	10
9	48	37	30	25	43	33	27	23	27	22	19	21	18	16	15	13	12	10
10	45	34	27	22	40	31	25	21	25	20	17	19	16	14	14	12	11	9

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	17525	17525	17525	17525
5°	19571	17634	15635	17634
10°	21713	17510	13554	17510
15°	22781	17254	10678	17254
20°	19749	16873	9241	16873
25°	12953	16352	8250	16352
30°	8720	15720	7467	15720
35°	7062	14927	6733	14927
40°	6279	14060	6232	14060
45°	5683	13047	5562	13047
50°	5172	12039	5152	12039
55°	4861	10925	4799	10925
60°	4066	9901	4017	9901
65°	3431	8989	3889	8989
70°	3172	8030	3668	8030
75°	2969	6987	3387	6987
80°	2734	5746	3013	5746
85°	2501	4539	2649	4539



TEST NUMBER: P331802-840

CATALOG NUMBER: S122RDIW-S485D1440U840-4F0-1E-UDD-A1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	102.9	1.5
10°-20°	286.7	4.1
20°-30°	369.4	5.3
30°-40°	351.1	5.1
40°-50°	300.7	4.3
50°-60°	229.0	3.3
60°-70°	144.8	2.1
70°-80°	72.3	1.0
80°-90°	26.0	0.4
90°-100°	114.3	1.7
100°-110°	355.0	5.1
110°-120°	606.9	8.8
120°-130°	798.1	11.5
130°-140°	895.8	12.9
140°-150°	878.3	12.7
150°-160°	736.7	10.6
160°-170°	488.6	7.1
170°-180°	170.8	2.5
0°-30°	759.0	11.0
0°-40°	1110.1	16.0
0°-60°	1639.8	23.7
0°-90°	1882.9	27.2
90°-120°	1076.2	15.5
90°-150°	3648.4	52.7
90°-180°	5045.0	72.8
0°-180°	6927.4	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1085	1085	1085	1085	1085	
5°	1208	1088	965	1088	1208	119
15°	1363	1032	639	1032	1363	368
25°	727	918	463	918	727	345
35°	358	757	342	757	358	229
45°	249	571	244	571	249	193
55°	173	388	170	388	173	152
65°	90	235	102	235	90	91
75°	48	112	54	112	48	50
85°	14	24	14	24	14	16
90°	52	2	52	2	52	23
95°	94	79	94	79	94	105
105°	338	327	338	327	338	355
115°	609	609	609	609	609	601
125°	889	886	889	886	889	793
135°	1160	1146	1160	1146	1160	893
145°	1407	1392	1407	1392	1407	878
155°	1603	1591	1603	1591	1603	738
165°	1732	1731	1732	1731	1732	489
175°	1795	1801	1795	1801	1795	171
180°	1804	1804	1804	1804	1804	



TEST NUMBER: P331802-840

CATALOG NUMBER: S122RDIW-S485D1440U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1085.4	1085.4	1085.4	1085.4	1085.4	1085.4	1085.4	1085.4	1085.4	1085.4	1085.4
2.5°	1129.4	1130.3	1131.3	1129.1	1129.1	1127.3	1123.4	1120.3	1111.9	1110.6	1110.6
5°	1207.5	1206.8	1208.3	1203.4	1196.6	1195.1	1187.9	1178.5	1168.7	1157.7	1155.5
7.5°	1285.3	1284.1	1281.1	1280.2	1275.1	1263.6	1252.1	1239.8	1223.6	1207.6	1199.6
10°	1324.4	1336.9	1329.4	1316.2	1318.8	1301.1	1291.6	1275.5	1261.8	1238.1	1232.8
12.5°	1363.0	1368.0	1365.5	1358.1	1354.7	1342.4	1329.7	1315.6	1290.5	1269.2	1250.6
15°	1362.9	1370.1	1372.0	1369.7	1371.6	1370.8	1364.0	1352.3	1330.5	1307.1	1286.8
17.5°	1262.3	1267.3	1279.6	1288.0	1298.6	1320.9	1331.9	1336.3	1332.9	1319.6	1305.3
20°	1149.4	1141.1	1175.9	1193.6	1208.7	1246.4	1278.8	1291.2	1311.2	1310.9	1307.1
22.5°	989.6	991.5	1024.4	1045.4	1089.5	1127.2	1164.2	1211.0	1249.7	1275.3	1290.2
25°	727.1	741.4	774.3	802.8	851.9	922.1	985.8	1059.8	1129.4	1184.6	1237.0
27.5°	546.0	547.1	573.1	599.7	628.7	686.2	766.5	854.7	954.2	1036.2	1130.6
30°	467.7	465.3	476.4	492.5	517.5	561.9	622.3	709.0	808.2	931.9	1042.0
32.5°	412.1	412.2	420.5	432.5	453.1	483.1	524.5	594.9	688.7	810.3	939.4
35°	358.3	357.9	364.0	372.6	381.2	400.5	428.8	465.7	530.3	643.8	775.8
37.5°	319.6	321.3	324.3	329.7	339.2	349.9	367.0	391.7	437.7	504.8	615.7
40°	297.9	298.7	302.9	307.4	313.1	321.3	335.3	355.3	388.8	442.3	523.4
42.5°	278.0	278.7	281.8	285.9	290.3	298.7	310.2	327.5	354.8	396.5	463.4
45°	248.9	248.9	251.6	253.4	258.3	265.9	275.3	289.6	308.5	339.4	384.0
47.5°	221.6	221.7	223.4	226.6	229.7	235.6	244.9	256.6	270.3	294.3	332.2
50°	205.9	206.3	207.4	210.1	212.0	217.2	224.4	234.6	248.9	267.4	299.0
52.5°	193.2	193.0	194.4	195.6	196.8	200.7	206.0	215.0	227.8	243.9	270.1
55°	172.7	171.2	173.5	175.3	176.5	178.0	181.0	186.7	197.6	211.2	230.8
57.5°	147.0	146.4	148.0	149.8	153.3	157.4	160.0	163.6	169.3	178.9	198.4
60°	125.9	125.9	129.4	130.5	134.6	139.9	145.2	148.2	153.9	160.3	174.6
62.5°	107.2	107.6	109.2	110.3	112.6	119.1	126.5	133.1	138.5	144.6	154.1
65°	89.8	90.5	90.5	91.3	92.8	94.3	97.3	102.6	112.0	120.7	127.8
67.5°	76.1	76.4	76.6	77.4	77.8	79.4	80.6	83.0	85.1	93.4	102.3
70°	67.2	68.3	67.9	68.7	69.0	69.8	71.3	72.4	75.8	77.7	83.0
72.5°	58.7	59.5	59.5	59.9	60.9	61.0	62.2	63.3	65.5	67.2	70.0
75°	47.6	47.2	47.6	48.3	48.7	49.0	49.0	50.5	51.7	53.2	55.0
77.5°	36.7	37.1	37.0	37.1	37.1	37.8	37.7	38.4	39.5	40.3	41.2
80°	29.4	29.8	29.4	29.8	30.2	30.5	30.2	30.5	31.7	32.4	32.4
82.5°	22.8	22.8	23.1	23.1	23.2	23.3	23.8	23.9	24.7	24.5	24.8
85°	13.5	13.2	13.2	13.2	13.5	13.9	13.5	13.5	13.9	13.9	13.9
87.5°	15.1	15.5	15.3	15.2	15.2	15.2	15.3	15.9	15.7	16.1	14.3
90°	51.8	51.4	51.1	50.8	50.4	50.6	51.3	51.9	52.6	53.3	45.8
92.5°	49.3	49.3	49.2	49.1	49.1	49.0	48.8	48.7	48.6	48.4	46.7
95°	94.4	95.0	95.7	96.4	97.0	97.5	97.5	97.5	97.5	97.5	96.7
97.5°	163.5	163.6	163.6	163.7	163.8	163.8	163.8	163.8	163.8	163.8	162.5
100°	208.5	208.9	209.2	209.5	210.0	210.1	210.1	210.1	210.1	210.1	209.0
102.5°	259.7	260.0	260.4	260.7	261.1	261.2	260.8	260.5	260.3	260.0	258.7
105°	338.0	338.0	338.0	338.0	338.0	337.6	337.0	336.3	335.6	335.0	334.3
107.5°	411.6	413.2	414.8	416.4	417.9	418.5	418.3	418.0	417.7	417.5	417.5
110°	468.9	469.9	470.9	471.9	472.9	473.5	473.5	473.5	473.5	473.5	473.5



TEST NUMBER: P331802-840

CATALOG NUMBER: S122RDIW-S485D1440U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	523.7	524.4	525.2	525.9	526.6	527.5	528.3	529.1	529.9	530.7	531.0
115°	608.9	610.0	611.0	612.0	613.0	613.7	614.0	614.4	614.7	615.1	615.7
117.5°	690.2	691.3	692.3	693.3	694.3	695.3	696.1	696.9	697.7	698.5	700.3
120°	747.5	748.5	749.5	750.5	751.5	752.0	752.0	752.0	752.0	752.0	754.8
122.5°	803.5	804.3	805.1	805.8	806.5	807.3	808.1	808.9	809.7	810.5	812.4
125°	889.1	889.5	889.8	890.1	890.5	891.1	892.1	893.1	894.1	895.1	896.3
127.5°	967.0	968.2	969.2	970.3	971.4	972.5	973.7	974.9	976.1	977.4	978.7
130°	1023.1	1024.4	1025.8	1027.1	1028.4	1029.5	1030.2	1030.9	1031.6	1032.2	1032.9
132.5°	1076.6	1077.7	1078.8	1079.9	1081.0	1082.3	1083.8	1085.3	1086.7	1088.2	1088.1
135°	1160.1	1161.1	1162.2	1163.2	1164.2	1164.9	1165.2	1165.5	1165.9	1166.2	1165.5
137.5°	1235.6	1237.0	1238.3	1239.7	1241.0	1241.8	1242.1	1242.3	1242.6	1242.9	1242.0
140°	1288.0	1289.3	1290.7	1292.0	1293.4	1294.0	1294.0	1294.0	1294.0	1294.0	1292.4
142.5°	1335.4	1336.9	1338.2	1339.6	1340.9	1341.4	1341.2	1340.9	1340.6	1340.4	1339.2
145°	1406.7	1408.1	1409.5	1410.8	1412.1	1412.6	1412.3	1412.0	1411.6	1411.3	1409.3
147.5°	1470.4	1471.7	1472.9	1474.2	1475.5	1475.8	1475.0	1474.3	1473.6	1472.8	1471.5
150°	1511.8	1512.8	1513.8	1514.8	1515.8	1515.8	1514.8	1513.8	1512.8	1511.8	1510.5
152.5°	1550.7	1552.1	1553.3	1554.6	1555.9	1555.9	1554.6	1553.3	1552.1	1550.7	1549.1
155°	1603.2	1604.2	1605.2	1606.2	1607.2	1606.8	1605.2	1603.5	1601.7	1600.0	1599.0
157.5°	1648.2	1649.8	1651.4	1653.0	1654.7	1654.4	1652.0	1649.7	1647.4	1645.2	1644.6
160°	1676.2	1677.6	1678.9	1680.2	1681.6	1681.2	1679.2	1677.2	1675.2	1673.1	1672.8
162.5°	1700.5	1702.2	1703.8	1705.5	1707.1	1706.7	1704.5	1702.1	1699.8	1697.5	1697.2
165°	1732.5	1734.2	1736.0	1737.6	1739.3	1739.0	1736.6	1734.2	1731.8	1729.5	1729.5
167.5°	1758.7	1760.5	1762.2	1764.0	1765.7	1765.4	1763.1	1760.7	1758.4	1756.0	1756.1
170°	1772.1	1774.1	1776.2	1778.2	1780.2	1780.1	1777.7	1775.3	1772.9	1770.6	1770.9
172.5°	1783.1	1785.1	1787.2	1789.2	1791.2	1791.0	1788.7	1786.2	1783.9	1781.5	1781.9
175°	1794.9	1797.0	1799.0	1801.0	1803.1	1802.9	1800.5	1798.2	1795.8	1793.4	1794.1
177.5°	1800.4	1802.0	1803.7	1805.3	1807.0	1807.0	1805.3	1803.7	1802.0	1800.4	1801.0
180°	1804.1	1804.1	1804.1	1804.1	1804.1	1804.1	1804.1	1804.1	1804.1	1804.1	1804.1



TEST NUMBER: P331802-840

CATALOG NUMBER: S122RDIW-S485D1440U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1085.4	1085.4	1085.4	1085.4	1085.4	1085.4	1085.4	1085.4	1085.4	1085.4	1085.4
2.5°	1111.3	1108.9	1106.8	1101.4	1098.6	1092.6	1091.7	1091.4	1083.6	1076.0	1073.9
5°	1149.4	1143.5	1134.4	1123.8	1112.9	1101.6	1094.0	1088.0	1072.9	1058.5	1050.3
7.5°	1187.9	1175.0	1159.3	1139.3	1122.7	1104.0	1090.1	1077.6	1056.2	1035.7	1021.9
10°	1216.6	1195.5	1174.8	1147.2	1125.7	1104.6	1085.0	1068.0	1043.9	1016.7	997.4
12.5°	1234.4	1211.1	1182.6	1155.7	1127.8	1101.0	1074.7	1052.9	1024.6	996.5	973.6
15°	1258.5	1233.6	1198.9	1160.4	1124.6	1089.5	1059.3	1032.2	995.2	961.7	933.7
17.5°	1278.2	1243.9	1206.6	1162.2	1120.6	1076.1	1037.2	1002.5	961.4	920.9	888.1
20°	1284.4	1250.5	1207.5	1163.1	1114.0	1061.6	1019.8	982.0	937.9	893.7	856.1
22.5°	1280.5	1254.2	1206.3	1153.1	1102.9	1048.0	1000.8	956.9	908.1	863.0	819.3
25°	1253.9	1244.9	1199.6	1141.6	1084.2	1020.5	965.8	917.9	862.1	813.9	766.3
27.5°	1191.8	1211.4	1183.4	1121.5	1057.7	989.4	928.0	873.4	815.5	761.1	713.8
30°	1132.2	1177.0	1164.9	1107.6	1036.3	969.2	900.2	843.2	781.4	725.6	678.8
32.5°	1050.4	1124.5	1136.3	1088.3	1014.6	940.8	868.5	811.8	747.3	688.4	642.9
35°	920.2	1031.1	1082.0	1051.4	977.4	898.0	823.2	757.3	692.4	634.3	589.1
37.5°	764.9	915.8	1000.8	1002.9	935.0	852.3	771.0	705.5	639.0	582.1	533.1
40°	664.1	827.8	938.3	962.8	905.4	816.1	733.9	667.1	602.3	546.4	490.3
42.5°	573.6	736.7	872.5	915.1	869.6	780.8	698.3	628.5	565.4	512.6	455.2
45°	463.8	606.4	756.1	832.3	807.1	724.8	637.7	571.4	512.1	466.5	411.4
47.5°	391.3	491.8	636.6	739.7	739.2	664.2	578.6	514.9	460.0	417.3	372.6
50°	349.9	437.5	560.1	676.9	686.7	623.8	542.3	479.3	428.1	383.1	347.3
52.5°	312.9	385.0	495.1	607.2	635.1	580.6	501.6	443.4	393.6	352.3	321.6
55°	264.4	320.1	403.9	508.8	551.0	512.5	442.3	388.1	347.7	313.1	286.6
57.5°	223.6	265.5	332.6	417.1	466.3	442.0	384.3	340.1	305.6	274.2	253.4
60°	198.0	232.3	289.2	359.8	414.0	397.1	347.7	306.6	277.2	250.0	230.5
62.5°	173.9	203.4	252.2	309.4	359.2	352.1	311.8	277.3	251.6	226.8	210.3
65°	139.9	161.4	199.4	244.4	284.4	287.7	258.7	235.3	212.3	192.7	178.0
67.5°	111.4	125.4	152.3	190.1	220.0	230.8	213.0	195.1	176.8	161.7	149.0
70°	93.9	105.2	124.8	155.4	182.9	194.2	184.0	170.1	154.2	141.8	130.9
72.5°	76.1	87.2	101.6	124.0	147.6	159.9	156.3	146.2	133.4	123.1	112.8
75°	57.4	60.7	70.5	85.6	104.1	114.6	117.2	112.0	101.8	93.9	87.9
77.5°	42.4	44.4	49.1	57.1	69.1	78.5	82.4	81.8	74.7	70.2	64.5
80°	33.9	35.0	37.4	40.7	49.8	59.2	61.8	61.8	57.0	55.0	49.4
82.5°	25.8	26.7	28.0	29.9	34.1	42.3	45.2	45.8	42.7	40.3	35.9
85°	14.7	14.3	15.0	16.3	17.0	19.2	23.7	24.5	23.7	20.7	19.6
87.5°	12.8	11.6	10.1	8.7	8.2	7.7	8.4	9.1	8.7	8.6	8.8
90°	38.4	31.0	23.5	17.8	13.7	9.6	5.6	1.5	5.6	9.6	13.7
92.5°	44.9	43.1	41.4	39.0	36.1	33.0	30.1	27.1	30.1	33.0	36.1
95°	96.0	95.4	94.7	92.7	89.3	85.9	82.5	79.2	82.5	85.9	89.3
97.5°	161.3	160.0	158.6	156.5	153.6	150.6	147.6	144.6	147.6	150.6	153.6
100°	208.0	207.0	206.0	204.2	201.5	198.7	196.0	193.4	196.0	198.7	201.5
102.5°	257.4	256.2	254.9	253.2	251.0	248.8	246.7	244.5	246.7	248.8	251.0
105°	333.6	333.0	332.2	331.3	330.3	329.3	328.3	327.3	328.3	329.3	330.3
107.5°	417.5	417.5	417.5	416.7	415.3	413.7	412.2	410.7	412.2	413.7	415.3
110°	473.5	473.5	473.5	472.4	470.4	468.4	466.4	464.3	466.4	468.4	470.4



TEST NUMBER: P331802-840

CATALOG NUMBER: S122RDIW-S485D1440U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	531.3	531.5	531.8	530.9	528.9	526.8	524.8	522.8	524.8	526.8	528.9
115°	616.4	617.1	617.7	617.1	615.1	613.0	611.0	608.9	611.0	613.0	615.1
117.5°	702.3	704.2	706.1	705.7	703.0	700.2	697.5	694.9	697.5	700.2	703.0
120°	757.5	760.2	763.0	763.0	760.2	757.5	754.8	752.0	754.8	757.5	760.2
122.5°	814.4	816.3	818.1	817.5	814.2	810.9	807.7	804.5	807.7	810.9	814.2
125°	897.3	898.3	899.3	898.3	895.1	892.1	889.1	886.1	889.1	892.1	895.1
127.5°	979.9	981.1	982.3	981.0	977.1	973.2	969.4	965.5	969.4	973.2	977.1
130°	1033.6	1034.2	1034.9	1033.1	1028.6	1024.3	1019.9	1015.4	1019.9	1024.3	1028.6
132.5°	1087.9	1087.8	1087.7	1085.8	1082.3	1078.6	1075.1	1071.5	1075.1	1078.6	1082.3
135°	1164.9	1164.2	1163.5	1161.2	1157.5	1153.9	1150.1	1146.4	1150.1	1153.9	1157.5
137.5°	1241.1	1240.3	1239.4	1237.4	1234.4	1231.3	1228.3	1225.3	1228.3	1231.3	1234.4
140°	1290.7	1289.0	1287.3	1285.0	1281.9	1278.9	1275.8	1272.7	1275.8	1278.9	1281.9
142.5°	1338.1	1336.9	1335.7	1333.6	1330.6	1327.6	1324.5	1321.5	1324.5	1327.6	1330.6
145°	1407.2	1405.2	1403.2	1401.0	1398.6	1396.2	1393.9	1391.5	1393.9	1396.2	1398.6
147.5°	1470.1	1468.7	1467.4	1465.3	1462.5	1459.6	1456.7	1453.9	1456.7	1459.6	1462.5
150°	1509.0	1507.7	1506.3	1504.7	1502.7	1500.7	1498.5	1496.5	1498.5	1500.7	1502.7
152.5°	1547.5	1545.9	1544.3	1542.5	1540.3	1538.3	1536.3	1534.3	1536.3	1538.3	1540.3
155°	1598.0	1597.0	1596.0	1595.0	1594.0	1593.0	1592.0	1590.9	1592.0	1593.0	1594.0
157.5°	1644.0	1643.4	1642.7	1642.0	1641.4	1640.7	1640.0	1639.3	1640.0	1640.7	1641.4
160°	1672.4	1672.1	1671.8	1671.3	1670.6	1669.9	1669.3	1668.6	1669.3	1669.9	1670.6
162.5°	1696.9	1696.5	1696.2	1696.0	1695.8	1695.7	1695.6	1695.4	1695.6	1695.7	1695.8
165°	1729.5	1729.5	1729.5	1729.7	1730.0	1730.3	1730.7	1731.0	1730.7	1730.3	1730.0
167.5°	1756.2	1756.2	1756.3	1756.8	1757.8	1758.8	1759.8	1760.8	1759.8	1758.8	1757.8
170°	1771.3	1771.6	1771.9	1772.6	1773.6	1774.6	1775.6	1776.7	1775.6	1774.6	1773.6
172.5°	1782.2	1782.6	1782.9	1783.6	1784.6	1785.6	1786.7	1787.7	1786.7	1785.6	1784.6
175°	1794.7	1795.4	1796.1	1797.0	1798.0	1799.0	1800.0	1801.0	1800.0	1799.0	1798.0
177.5°	1801.5	1802.0	1802.6	1803.3	1804.1	1804.9	1805.7	1806.5	1805.7	1804.9	1804.1
180°	1804.1	1804.1	1804.1	1804.1	1804.1	1804.1	1804.1	1804.1	1804.1	1804.1	1804.1



TEST NUMBER: P331802-840

CATALOG NUMBER: S122RDIW-S485D1440U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1085.4	1085.4	1085.4	1085.4	1085.4	1085.4	1085.4	1085.4	1085.4	1085.4	1085.4
2.5°	1070.0	1067.8	1063.9	1057.9	1054.3	1047.9	1043.7	1046.1	1046.7	1046.1	1045.5
5°	1041.3	1033.3	1022.4	1011.8	1002.0	991.5	985.4	982.8	977.4	974.5	973.0
7.5°	1006.4	992.8	977.3	959.0	943.3	927.0	918.6	914.4	903.6	897.8	892.6
10°	980.5	959.0	943.5	919.4	904.7	883.2	868.5	868.9	854.1	845.9	839.8
12.5°	951.9	928.3	902.5	880.8	860.4	843.1	825.4	818.2	802.5	794.6	778.3
15°	904.3	876.8	849.7	820.2	799.5	772.7	747.1	715.8	690.5	668.6	662.6
17.5°	852.4	818.4	791.1	756.6	721.0	676.0	646.3	628.1	612.9	601.4	592.8
20°	816.9	782.1	753.2	701.0	653.2	622.6	600.8	586.8	571.0	558.6	551.7
22.5°	779.4	743.3	703.7	645.5	608.2	583.7	564.2	548.2	537.5	527.8	521.6
25°	726.3	686.7	621.5	581.5	551.4	525.7	512.1	502.3	491.0	477.8	471.8
27.5°	670.2	607.2	560.4	530.7	501.9	485.2	473.0	458.4	448.3	442.3	436.1
30°	628.2	565.3	528.8	496.2	475.9	457.5	443.1	434.8	425.1	414.9	410.7
32.5°	581.5	531.2	496.1	469.2	448.5	432.7	421.4	408.0	400.9	394.7	386.0
35°	523.4	485.3	453.3	431.4	411.8	399.0	385.8	377.9	365.1	359.8	356.4
37.5°	474.2	441.2	417.3	394.3	378.7	364.6	356.5	343.9	338.3	330.9	323.8
40°	446.5	414.0	391.1	372.2	354.9	344.3	334.2	324.0	315.7	312.3	303.6
42.5°	418.2	391.7	368.7	348.1	336.5	325.3	312.5	305.0	296.3	290.8	285.5
45°	379.0	355.7	336.0	319.0	306.2	294.6	286.2	273.8	268.9	257.9	253.4
47.5°	344.6	322.9	304.2	288.0	275.5	267.9	255.8	246.0	238.2	231.5	225.7
50°	320.1	302.1	284.0	269.6	258.3	247.4	235.0	230.0	217.9	214.6	211.2
52.5°	297.8	280.6	264.1	250.0	238.7	228.1	217.1	210.8	202.6	199.1	196.7
55°	266.6	250.0	234.2	221.8	210.5	199.4	192.7	184.8	181.0	178.3	175.3
57.5°	235.2	220.4	208.1	195.6	184.2	175.5	167.6	162.9	159.0	155.5	151.9
60°	215.3	201.0	190.1	178.3	166.7	159.6	153.5	147.8	143.3	138.0	136.5
62.5°	194.2	181.7	171.7	160.3	150.1	143.5	137.8	132.5	127.0	119.4	117.2
65°	165.2	155.4	144.8	135.4	126.3	120.0	111.6	105.6	103.3	102.6	102.2
67.5°	139.0	129.7	120.6	111.0	102.7	96.7	92.5	91.6	90.1	89.6	88.6
70°	121.4	112.8	103.7	94.6	86.7	85.6	84.1	82.6	80.7	80.0	79.2
72.5°	105.7	96.7	87.8	80.5	77.1	75.6	74.1	72.6	71.4	70.6	70.2
75°	81.1	72.8	66.8	64.1	62.2	61.1	58.9	57.7	57.0	55.8	55.4
77.5°	58.4	53.7	50.9	49.3	47.3	46.0	44.8	43.6	42.8	42.6	42.0
80°	44.5	42.2	40.4	38.1	37.4	35.9	35.4	34.3	34.7	33.5	33.5
82.5°	34.5	31.7	30.1	29.1	28.3	27.1	26.7	26.2	26.3	25.4	25.4
85°	17.8	17.0	16.3	15.5	15.5	14.3	14.7	14.3	14.3	13.5	13.2
87.5°	9.3	10.1	11.0	12.5	14.0	15.1	15.0	14.6	14.4	14.3	14.0
90°	17.8	23.5	31.0	38.4	45.8	53.3	52.6	51.9	51.3	50.6	50.4
92.5°	39.0	41.4	43.1	44.9	46.7	48.4	48.6	48.7	48.8	49.0	49.1
95°	92.7	94.7	95.4	96.0	96.7	97.5	97.5	97.5	97.5	97.5	97.0
97.5°	156.5	158.6	160.0	161.3	162.5	163.8	163.8	163.8	163.8	163.8	163.8
100°	204.2	206.0	207.0	208.0	209.0	210.1	210.1	210.1	210.1	210.1	210.0
102.5°	253.2	254.9	256.2	257.4	258.7	260.0	260.3	260.5	260.8	261.2	261.1
105°	331.3	332.2	333.0	333.6	334.3	335.0	335.6	336.3	337.0	337.6	338.0
107.5°	416.7	417.5	417.5	417.5	417.5	417.5	417.7	418.0	418.3	418.5	417.9
110°	472.4	473.5	473.5	473.5	473.5	473.5	473.5	473.5	473.5	473.5	472.9



TEST NUMBER: P331802-840

CATALOG NUMBER: S122RDIW-S485D1440U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	530.9	531.8	531.5	531.3	531.0	530.7	529.9	529.1	528.3	527.5	526.6
115°	617.1	617.7	617.1	616.4	615.7	615.1	614.7	614.4	614.0	613.7	613.0
117.5°	705.7	706.1	704.2	702.3	700.3	698.5	697.7	696.9	696.1	695.3	694.3
120°	763.0	763.0	760.2	757.5	754.8	752.0	752.0	752.0	752.0	752.0	751.5
122.5°	817.5	818.1	816.3	814.4	812.4	810.5	809.7	808.9	808.1	807.3	806.5
125°	898.3	899.3	898.3	897.3	896.3	895.1	894.1	893.1	892.1	891.1	890.5
127.5°	981.0	982.3	981.1	979.9	978.7	977.4	976.1	974.9	973.7	972.5	971.4
130°	1033.1	1034.9	1034.2	1033.6	1032.9	1032.2	1031.6	1030.9	1030.2	1029.5	1028.4
132.5°	1085.8	1087.7	1087.8	1087.9	1088.1	1088.2	1086.7	1085.3	1083.8	1082.3	1081.0
135°	1161.2	1163.5	1164.2	1164.9	1165.5	1166.2	1165.9	1165.5	1165.2	1164.9	1164.2
137.5°	1237.4	1239.4	1240.3	1241.1	1242.0	1242.9	1242.6	1242.3	1242.1	1241.8	1241.0
140°	1285.0	1287.3	1289.0	1290.7	1292.4	1294.0	1294.0	1294.0	1294.0	1294.0	1293.4
142.5°	1333.6	1335.7	1336.9	1338.1	1339.2	1340.4	1340.6	1340.9	1341.2	1341.4	1340.9
145°	1401.0	1403.2	1405.2	1407.2	1409.3	1411.3	1411.6	1412.0	1412.3	1412.6	1412.1
147.5°	1465.3	1467.4	1468.7	1470.1	1471.5	1472.8	1473.6	1474.3	1475.0	1475.8	1475.5
150°	1504.7	1506.3	1507.7	1509.0	1510.5	1511.8	1512.8	1513.8	1514.8	1515.8	1515.8
152.5°	1542.5	1544.3	1545.9	1547.5	1549.1	1550.7	1552.1	1553.3	1554.6	1555.9	1555.9
155°	1595.0	1596.0	1597.0	1598.0	1599.0	1600.0	1601.7	1603.5	1605.2	1606.8	1607.2
157.5°	1642.0	1642.7	1643.4	1644.0	1644.6	1645.2	1647.4	1649.7	1652.0	1654.4	1654.7
160°	1671.3	1671.8	1672.1	1672.4	1672.8	1673.1	1675.2	1677.2	1679.2	1681.2	1681.6
162.5°	1696.0	1696.2	1696.5	1696.9	1697.2	1697.5	1699.8	1702.1	1704.5	1706.7	1707.1
165°	1729.7	1729.5	1729.5	1729.5	1729.5	1729.5	1731.8	1734.2	1736.6	1739.0	1739.3
167.5°	1756.8	1756.3	1756.2	1756.2	1756.1	1756.0	1758.4	1760.7	1763.1	1765.4	1765.7
170°	1772.6	1771.9	1771.6	1771.3	1770.9	1770.6	1772.9	1775.3	1777.7	1780.1	1780.2
172.5°	1783.6	1782.9	1782.6	1782.2	1781.9	1781.5	1783.9	1786.2	1788.7	1791.0	1791.2
175°	1797.0	1796.1	1795.4	1794.7	1794.1	1793.4	1795.8	1798.2	1800.5	1802.9	1803.1
177.5°	1803.3	1802.6	1802.0	1801.5	1801.0	1800.4	1802.0	1803.7	1805.3	1807.0	1807.0
180°	1804.1	1804.1	1804.1	1804.1	1804.1	1804.1	1804.1	1804.1	1804.1	1804.1	1804.1



TEST NUMBER: P331802-840

CATALOG NUMBER: S122RDIW-S485D1440U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1085.4	1085.4	1085.4	1085.4	1085.4	1085.4	1085.4	1085.4	1085.4	1085.4	1085.4
2.5°	1042.2	1042.8	1041.9	1042.5	1041.9	1042.8	1042.2	1045.5	1046.1	1046.7	1046.1
5°	971.1	966.5	965.8	964.7	965.8	966.5	971.1	973.0	974.5	977.4	982.8
7.5°	886.2	885.4	883.6	880.9	883.6	885.4	886.2	892.6	897.8	903.6	914.4
10°	831.5	829.7	829.3	826.7	829.3	829.7	831.5	839.8	845.9	854.1	868.9
12.5°	767.6	755.5	754.2	747.6	754.2	755.5	767.6	778.3	794.6	802.5	818.2
15°	653.6	651.3	643.8	638.8	643.8	651.3	653.6	662.6	668.6	690.5	715.8
17.5°	588.3	581.0	578.7	577.6	578.7	581.0	588.3	592.8	601.4	612.9	628.1
20°	546.4	539.7	538.6	537.8	538.6	539.7	546.4	551.7	558.6	571.0	586.8
22.5°	517.5	510.4	507.5	505.2	507.5	510.4	517.5	521.6	527.8	537.5	548.2
25°	468.0	465.3	463.8	463.1	463.8	465.3	468.0	471.8	477.8	491.0	502.3
27.5°	429.3	423.5	422.3	420.4	422.3	423.5	429.3	436.1	442.3	448.3	458.4
30°	407.3	405.4	402.7	400.5	402.7	405.4	407.3	410.7	414.9	425.1	434.8
32.5°	381.3	379.8	377.4	376.4	377.4	379.8	381.3	386.0	394.7	400.9	408.0
35°	352.6	347.3	345.1	341.6	345.1	347.3	352.6	356.4	359.8	365.1	377.9
37.5°	322.2	319.4	316.3	317.4	316.3	319.4	322.2	323.8	330.9	338.3	343.9
40°	298.7	296.8	296.0	295.7	296.0	296.8	298.7	303.6	312.3	315.7	324.0
42.5°	279.9	274.8	272.8	272.8	272.8	274.8	279.9	285.5	290.8	296.3	305.0
45°	251.6	246.6	243.3	243.6	243.3	246.6	251.6	253.4	257.9	268.9	273.8
47.5°	222.5	222.3	220.2	220.9	220.2	222.3	222.5	225.7	231.5	238.2	246.0
50°	208.5	206.3	204.8	205.1	204.8	206.3	208.5	211.2	214.6	217.9	230.0
52.5°	195.3	193.3	192.1	193.7	192.1	193.3	195.3	196.7	199.1	202.6	210.8
55°	173.5	171.2	170.9	170.5	170.9	171.2	173.5	175.3	178.3	181.0	184.8
57.5°	149.2	147.6	145.3	144.4	145.3	147.6	149.2	151.9	155.5	159.0	162.9
60°	131.6	128.6	124.8	124.4	124.8	128.6	131.6	136.5	138.0	143.3	147.8
62.5°	115.6	115.0	114.3	114.2	114.3	115.0	115.6	117.2	119.4	127.0	132.5
65°	101.5	101.1	101.5	101.8	101.5	101.1	101.5	102.2	102.6	103.3	105.6
67.5°	88.4	87.8	87.1	87.4	87.1	87.8	88.4	88.6	89.6	90.1	91.6
70°	78.5	78.1	77.7	77.7	77.7	78.1	78.5	79.2	80.0	80.7	82.6
72.5°	68.8	68.7	68.4	68.1	68.4	68.7	68.8	70.2	70.6	71.4	72.6
75°	55.0	54.3	54.3	54.3	54.3	54.3	55.0	55.4	55.8	57.0	57.7
77.5°	41.9	41.6	41.2	40.9	41.2	41.6	41.9	42.0	42.6	42.8	43.6
80°	33.2	32.8	32.4	32.4	32.4	32.8	33.2	33.5	33.5	34.7	34.3
82.5°	25.3	24.9	24.8	24.5	24.8	24.9	25.3	25.4	25.4	26.3	26.2
85°	13.5	13.9	13.5	14.3	13.5	13.9	13.5	13.2	13.5	14.3	14.3
87.5°	14.0	13.8	14.2	13.9	14.2	13.8	14.0	14.0	14.3	14.4	14.6
90°	50.8	51.1	51.4	51.8	51.4	51.1	50.8	50.4	50.6	51.3	51.9
92.5°	49.1	49.2	49.3	49.3	49.3	49.2	49.1	49.1	49.0	48.8	48.7
95°	96.4	95.7	95.0	94.4	95.0	95.7	96.4	97.0	97.5	97.5	97.5
97.5°	163.7	163.6	163.6	163.5	163.6	163.6	163.7	163.8	163.8	163.8	163.8
100°	209.5	209.2	208.9	208.5	208.9	209.2	209.5	210.0	210.1	210.1	210.1
102.5°	260.7	260.4	260.0	259.7	260.0	260.4	260.7	261.1	261.2	260.8	260.5
105°	338.0	338.0	338.0	338.0	338.0	338.0	338.0	338.0	337.6	337.0	336.3
107.5°	416.4	414.8	413.2	411.6	413.2	414.8	416.4	417.9	418.5	418.3	418.0
110°	471.9	470.9	469.9	468.9	469.9	470.9	471.9	472.9	473.5	473.5	473.5



TEST NUMBER: P331802-840

CATALOG NUMBER: S122RDIW-S485D1440U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	525.9	525.2	524.4	523.7	524.4	525.2	525.9	526.6	527.5	528.3	529.1
115°	612.0	611.0	610.0	608.9	610.0	611.0	612.0	613.0	613.7	614.0	614.4
117.5°	693.3	692.3	691.3	690.2	691.3	692.3	693.3	694.3	695.3	696.1	696.9
120°	750.5	749.5	748.5	747.5	748.5	749.5	750.5	751.5	752.0	752.0	752.0
122.5°	805.8	805.1	804.3	803.5	804.3	805.1	805.8	806.5	807.3	808.1	808.9
125°	890.1	889.8	889.5	889.1	889.5	889.8	890.1	890.5	891.1	892.1	893.1
127.5°	970.3	969.2	968.2	967.0	968.2	969.2	970.3	971.4	972.5	973.7	974.9
130°	1027.1	1025.8	1024.4	1023.1	1024.4	1025.8	1027.1	1028.4	1029.5	1030.2	1030.9
132.5°	1079.9	1078.8	1077.7	1076.6	1077.7	1078.8	1079.9	1081.0	1082.3	1083.8	1085.3
135°	1163.2	1162.2	1161.1	1160.1	1161.1	1162.2	1163.2	1164.2	1164.9	1165.2	1165.5
137.5°	1239.7	1238.3	1237.0	1235.6	1237.0	1238.3	1239.7	1241.0	1241.8	1242.1	1242.3
140°	1292.0	1290.7	1289.3	1288.0	1289.3	1290.7	1292.0	1293.4	1294.0	1294.0	1294.0
142.5°	1339.6	1338.2	1336.9	1335.4	1336.9	1338.2	1339.6	1340.9	1341.4	1341.2	1340.9
145°	1410.8	1409.5	1408.1	1406.7	1408.1	1409.5	1410.8	1412.1	1412.6	1412.3	1412.0
147.5°	1474.2	1472.9	1471.7	1470.4	1471.7	1472.9	1474.2	1475.5	1475.8	1475.0	1474.3
150°	1514.8	1513.8	1512.8	1511.8	1512.8	1513.8	1514.8	1515.8	1515.8	1514.8	1513.8
152.5°	1554.6	1553.3	1552.1	1550.7	1552.1	1553.3	1554.6	1555.9	1555.9	1554.6	1553.3
155°	1606.2	1605.2	1604.2	1603.2	1604.2	1605.2	1606.2	1607.2	1606.8	1605.2	1603.5
157.5°	1653.0	1651.4	1649.8	1648.2	1649.8	1651.4	1653.0	1654.7	1654.4	1652.0	1649.7
160°	1680.2	1678.9	1677.6	1676.2	1677.6	1678.9	1680.2	1681.6	1681.2	1679.2	1677.2
162.5°	1705.5	1703.8	1702.2	1700.5	1702.2	1703.8	1705.5	1707.1	1706.7	1704.5	1702.1
165°	1737.6	1736.0	1734.2	1732.5	1734.2	1736.0	1737.6	1739.3	1739.0	1736.6	1734.2
167.5°	1764.0	1762.2	1760.5	1758.7	1760.5	1762.2	1764.0	1765.7	1765.4	1763.1	1760.7
170°	1778.2	1776.2	1774.1	1772.1	1774.1	1776.2	1778.2	1780.2	1780.1	1777.7	1775.3
172.5°	1789.2	1787.2	1785.1	1783.1	1785.1	1787.2	1789.2	1791.2	1791.0	1788.7	1786.2
175°	1801.0	1799.0	1797.0	1794.9	1797.0	1799.0	1801.0	1803.1	1802.9	1800.5	1798.2
177.5°	1805.3	1803.7	1802.0	1800.4	1802.0	1803.7	1805.3	1807.0	1807.0	1805.3	1803.7
180°	1804.1	1804.1	1804.1	1804.1	1804.1	1804.1	1804.1	1804.1	1804.1	1804.1	1804.1



TEST NUMBER: P331802-840

CATALOG NUMBER: S122RDIW-S485D1440U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1085.4	1085.4	1085.4	1085.4	1085.4	1085.4	1085.4	1085.4	1085.4	1085.4	1085.4
2.5°	1043.7	1047.9	1054.3	1057.9	1063.9	1067.8	1070.0	1073.9	1076.0	1083.6	1091.4
5°	985.4	991.5	1002.0	1011.8	1022.4	1033.3	1041.3	1050.3	1058.5	1072.9	1088.0
7.5°	918.6	927.0	943.3	959.0	977.3	992.8	1006.4	1021.9	1035.7	1056.2	1077.6
10°	868.5	883.2	904.7	919.4	943.5	959.0	980.5	997.4	1016.7	1043.9	1068.0
12.5°	825.4	843.1	860.4	880.8	902.5	928.3	951.9	973.6	996.5	1024.6	1052.9
15°	747.1	772.7	799.5	820.2	849.7	876.8	904.3	933.7	961.7	995.2	1032.2
17.5°	646.3	676.0	721.0	756.6	791.1	818.4	852.4	888.1	920.9	961.4	1002.5
20°	600.8	622.6	653.2	701.0	753.2	782.1	816.9	856.1	893.7	937.9	982.0
22.5°	564.2	583.7	608.2	645.5	703.7	743.3	779.4	819.3	863.0	908.1	956.9
25°	512.1	525.7	551.4	581.5	621.5	686.7	726.3	766.3	813.9	862.1	917.9
27.5°	473.0	485.2	501.9	530.7	560.4	607.2	670.2	713.8	761.1	815.5	873.4
30°	443.1	457.5	475.9	496.2	528.8	565.3	628.2	678.8	725.6	781.4	843.2
32.5°	421.4	432.7	448.5	469.2	496.1	531.2	581.5	642.9	688.4	747.3	811.8
35°	385.8	399.0	411.8	431.4	453.3	485.3	523.4	589.1	634.3	692.4	757.3
37.5°	356.5	364.6	378.7	394.3	417.3	441.2	474.2	533.1	582.1	639.0	705.5
40°	334.2	344.3	354.9	372.2	391.1	414.0	446.5	490.3	546.4	602.3	667.1
42.5°	312.5	325.3	336.5	348.1	368.7	391.7	418.2	455.2	512.6	565.4	628.5
45°	286.2	294.6	306.2	319.0	336.0	355.7	379.0	411.4	466.5	512.1	571.4
47.5°	255.8	267.9	275.5	288.0	304.2	322.9	344.6	372.6	417.3	460.0	514.9
50°	235.0	247.4	258.3	269.6	284.0	302.1	320.1	347.3	383.1	428.1	479.3
52.5°	217.1	228.1	238.7	250.0	264.1	280.6	297.8	321.6	352.3	393.6	443.4
55°	192.7	199.4	210.5	221.8	234.2	250.0	266.6	286.6	313.1	347.7	388.1
57.5°	167.6	175.5	184.2	195.6	208.1	220.4	235.2	253.4	274.2	305.6	340.1
60°	153.5	159.6	166.7	178.3	190.1	201.0	215.3	230.5	250.0	277.2	306.6
62.5°	137.8	143.5	150.1	160.3	171.7	181.7	194.2	210.3	226.8	251.6	277.3
65°	111.6	120.0	126.3	135.4	144.8	155.4	165.2	178.0	192.7	212.3	235.3
67.5°	92.5	96.7	102.7	111.0	120.6	129.7	139.0	149.0	161.7	176.8	195.1
70°	84.1	85.6	86.7	94.6	103.7	112.8	121.4	130.9	141.8	154.2	170.1
72.5°	74.1	75.6	77.1	80.5	87.8	96.7	105.7	112.8	123.1	133.4	146.2
75°	58.9	61.1	62.2	64.1	66.8	72.8	81.1	87.9	93.9	101.8	112.0
77.5°	44.8	46.0	47.3	49.3	50.9	53.7	58.4	64.5	70.2	74.7	81.8
80°	35.4	35.9	37.4	38.1	40.4	42.2	44.5	49.4	55.0	57.0	61.8
82.5°	26.7	27.1	28.3	29.1	30.1	31.7	34.5	35.9	40.3	42.7	45.8
85°	14.7	14.3	15.5	15.5	16.3	17.0	17.8	19.6	20.7	23.7	24.5
87.5°	15.0	15.1	14.0	12.5	11.0	10.1	9.3	8.8	8.6	8.7	9.1
90°	52.6	53.3	45.8	38.4	31.0	23.5	17.8	13.7	9.6	5.6	1.5
92.5°	48.6	48.4	46.7	44.9	43.1	41.4	39.0	36.1	33.0	30.1	27.1
95°	97.5	97.5	96.7	96.0	95.4	94.7	92.7	89.3	85.9	82.5	79.2
97.5°	163.8	163.8	162.5	161.3	160.0	158.6	156.5	153.6	150.6	147.6	144.6
100°	210.1	210.1	209.0	208.0	207.0	206.0	204.2	201.5	198.7	196.0	193.4
102.5°	260.3	260.0	258.7	257.4	256.2	254.9	253.2	251.0	248.8	246.7	244.5
105°	335.6	335.0	334.3	333.6	333.0	332.2	331.3	330.3	329.3	328.3	327.3
107.5°	417.7	417.5	417.5	417.5	417.5	417.5	416.7	415.3	413.7	412.2	410.7
110°	473.5	473.5	473.5	473.5	473.5	473.5	472.4	470.4	468.4	466.4	464.3



TEST NUMBER: P331802-840

CATALOG NUMBER: S122RDIW-S485D1440U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	529.9	530.7	531.0	531.3	531.5	531.8	530.9	528.9	526.8	524.8	522.8
115°	614.7	615.1	615.7	616.4	617.1	617.7	617.1	615.1	613.0	611.0	608.9
117.5°	697.7	698.5	700.3	702.3	704.2	706.1	705.7	703.0	700.2	697.5	694.9
120°	752.0	752.0	754.8	757.5	760.2	763.0	763.0	760.2	757.5	754.8	752.0
122.5°	809.7	810.5	812.4	814.4	816.3	818.1	817.5	814.2	810.9	807.7	804.5
125°	894.1	895.1	896.3	897.3	898.3	899.3	898.3	895.1	892.1	889.1	886.1
127.5°	976.1	977.4	978.7	979.9	981.1	982.3	981.0	977.1	973.2	969.4	965.5
130°	1031.6	1032.2	1032.9	1033.6	1034.2	1034.9	1033.1	1028.6	1024.3	1019.9	1015.4
132.5°	1086.7	1088.2	1088.1	1087.9	1087.8	1087.7	1085.8	1082.3	1078.6	1075.1	1071.5
135°	1165.9	1166.2	1165.5	1164.9	1164.2	1163.5	1161.2	1157.5	1153.9	1150.1	1146.4
137.5°	1242.6	1242.9	1242.0	1241.1	1240.3	1239.4	1237.4	1234.4	1231.3	1228.3	1225.3
140°	1294.0	1294.0	1292.4	1290.7	1289.0	1287.3	1285.0	1281.9	1278.9	1275.8	1272.7
142.5°	1340.6	1340.4	1339.2	1338.1	1336.9	1335.7	1333.6	1330.6	1327.6	1324.5	1321.5
145°	1411.6	1411.3	1409.3	1407.2	1405.2	1403.2	1401.0	1398.6	1396.2	1393.9	1391.5
147.5°	1473.6	1472.8	1471.5	1470.1	1468.7	1467.4	1465.3	1462.5	1459.6	1456.7	1453.9
150°	1512.8	1511.8	1510.5	1509.0	1507.7	1506.3	1504.7	1502.7	1500.7	1498.5	1496.5
152.5°	1552.1	1550.7	1549.1	1547.5	1545.9	1544.3	1542.5	1540.3	1538.3	1536.3	1534.3
155°	1601.7	1600.0	1599.0	1598.0	1597.0	1596.0	1595.0	1594.0	1593.0	1592.0	1590.9
157.5°	1647.4	1645.2	1644.6	1644.0	1643.4	1642.7	1642.0	1641.4	1640.7	1640.0	1639.3
160°	1675.2	1673.1	1672.8	1672.4	1672.1	1671.8	1671.3	1670.6	1669.9	1669.3	1668.6
162.5°	1699.8	1697.5	1697.2	1696.9	1696.5	1696.2	1696.0	1695.8	1695.7	1695.6	1695.4
165°	1731.8	1729.5	1729.5	1729.5	1729.5	1729.5	1729.7	1730.0	1730.3	1730.7	1731.0
167.5°	1758.4	1756.0	1756.1	1756.2	1756.2	1756.3	1756.8	1757.8	1758.8	1759.8	1760.8
170°	1772.9	1770.6	1770.9	1771.3	1771.6	1771.9	1772.6	1773.6	1774.6	1775.6	1776.7
172.5°	1783.9	1781.5	1781.9	1782.2	1782.6	1782.9	1783.6	1784.6	1785.6	1786.7	1787.7
175°	1795.8	1793.4	1794.1	1794.7	1795.4	1796.1	1797.0	1798.0	1799.0	1800.0	1801.0
177.5°	1802.0	1800.4	1801.0	1801.5	1802.0	1802.6	1803.3	1804.1	1804.9	1805.7	1806.5
180°	1804.1	1804.1	1804.1	1804.1	1804.1	1804.1	1804.1	1804.1	1804.1	1804.1	1804.1



TEST NUMBER: P331802-840

CATALOG NUMBER: S122RDIW-S485D1440U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1085.4	1085.4	1085.4	1085.4	1085.4	1085.4	1085.4	1085.4	1085.4	1085.4	1085.4
2.5°	1091.7	1092.6	1098.6	1101.4	1106.8	1108.9	1111.3	1110.6	1110.6	1111.9	1120.3
5°	1094.0	1101.6	1112.9	1123.8	1134.4	1143.5	1149.4	1155.5	1157.7	1168.7	1178.5
7.5°	1090.1	1104.0	1122.7	1139.3	1159.3	1175.0	1187.9	1199.6	1207.6	1223.6	1239.8
10°	1085.0	1104.6	1125.7	1147.2	1174.8	1195.5	1216.6	1232.8	1238.1	1261.8	1275.5
12.5°	1074.7	1101.0	1127.8	1155.7	1182.6	1211.1	1234.4	1250.6	1269.2	1290.5	1315.6
15°	1059.3	1089.5	1124.6	1160.4	1198.9	1233.6	1258.5	1286.8	1307.1	1330.5	1352.3
17.5°	1037.2	1076.1	1120.6	1162.2	1206.6	1243.9	1278.2	1305.3	1319.6	1332.9	1336.3
20°	1019.8	1061.6	1114.0	1163.1	1207.5	1250.5	1284.4	1307.1	1310.9	1311.2	1291.2
22.5°	1000.8	1048.0	1102.9	1153.1	1206.3	1254.2	1280.5	1290.2	1275.3	1249.7	1211.0
25°	965.8	1020.5	1084.2	1141.6	1199.6	1244.9	1253.9	1237.0	1184.6	1129.4	1059.8
27.5°	928.0	989.4	1057.7	1121.5	1183.4	1211.4	1191.8	1130.6	1036.2	954.2	854.7
30°	900.2	969.2	1036.3	1107.6	1164.9	1177.0	1132.2	1042.0	931.9	808.2	709.0
32.5°	868.5	940.8	1014.6	1088.3	1136.3	1124.5	1050.4	939.4	810.3	688.7	594.9
35°	823.2	898.0	977.4	1051.4	1082.0	1031.1	920.2	775.8	643.8	530.3	465.7
37.5°	771.0	852.3	935.0	1002.9	1000.8	915.8	764.9	615.7	504.8	437.7	391.7
40°	733.9	816.1	905.4	962.8	938.3	827.8	664.1	523.4	442.3	388.8	355.3
42.5°	698.3	780.8	869.6	915.1	872.5	736.7	573.6	463.4	396.5	354.8	327.5
45°	637.7	724.8	807.1	832.3	756.1	606.4	463.8	384.0	339.4	308.5	289.6
47.5°	578.6	664.2	739.2	739.7	636.6	491.8	391.3	332.2	294.3	270.3	256.6
50°	542.3	623.8	686.7	676.9	560.1	437.5	349.9	299.0	267.4	248.9	234.6
52.5°	501.6	580.6	635.1	607.2	495.1	385.0	312.9	270.1	243.9	227.8	215.0
55°	442.3	512.5	551.0	508.8	403.9	320.1	264.4	230.8	211.2	197.6	186.7
57.5°	384.3	442.0	466.3	417.1	332.6	265.5	223.6	198.4	178.9	169.3	163.6
60°	347.7	397.1	414.0	359.8	289.2	232.3	198.0	174.6	160.3	153.9	148.2
62.5°	311.8	352.1	359.2	309.4	252.2	203.4	173.9	154.1	144.6	138.5	133.1
65°	258.7	287.7	284.4	244.4	199.4	161.4	139.9	127.8	120.7	112.0	102.6
67.5°	213.0	230.8	220.0	190.1	152.3	125.4	111.4	102.3	93.4	85.1	83.0
70°	184.0	194.2	182.9	155.4	124.8	105.2	93.9	83.0	77.7	75.8	72.4
72.5°	156.3	159.9	147.6	124.0	101.6	87.2	76.1	70.0	67.2	65.5	63.3
75°	117.2	114.6	104.1	85.6	70.5	60.7	57.4	55.0	53.2	51.7	50.5
77.5°	82.4	78.5	69.1	57.1	49.1	44.4	42.4	41.2	40.3	39.5	38.4
80°	61.8	59.2	49.8	40.7	37.4	35.0	33.9	32.4	32.4	31.7	30.5
82.5°	45.2	42.3	34.1	29.9	28.0	26.7	25.8	24.8	24.5	24.7	23.9
85°	23.7	19.2	17.0	16.3	15.0	14.3	14.7	13.9	13.9	13.9	13.5
87.5°	8.4	7.7	8.2	8.7	10.1	11.6	12.8	14.3	16.1	15.7	15.9
90°	5.6	9.6	13.7	17.8	23.5	31.0	38.4	45.8	53.3	52.6	51.9
92.5°	30.1	33.0	36.1	39.0	41.4	43.1	44.9	46.7	48.4	48.6	48.7
95°	82.5	85.9	89.3	92.7	94.7	95.4	96.0	96.7	97.5	97.5	97.5
97.5°	147.6	150.6	153.6	156.5	158.6	160.0	161.3	162.5	163.8	163.8	163.8
100°	196.0	198.7	201.5	204.2	206.0	207.0	208.0	209.0	210.1	210.1	210.1
102.5°	246.7	248.8	251.0	253.2	254.9	256.2	257.4	258.7	260.0	260.3	260.5
105°	328.3	329.3	330.3	331.3	332.2	333.0	333.6	334.3	335.0	335.6	336.3
107.5°	412.2	413.7	415.3	416.7	417.5	417.5	417.5	417.5	417.5	417.7	418.0
110°	466.4	468.4	470.4	472.4	473.5	473.5	473.5	473.5	473.5	473.5	473.5



TEST NUMBER: P331802-840

CATALOG NUMBER: S122RDIW-S485D1440U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	524.8	526.8	528.9	530.9	531.8	531.5	531.3	531.0	530.7	529.9	529.1
115°	611.0	613.0	615.1	617.1	617.7	617.1	616.4	615.7	615.1	614.7	614.4
117.5°	697.5	700.2	703.0	705.7	706.1	704.2	702.3	700.3	698.5	697.7	696.9
120°	754.8	757.5	760.2	763.0	763.0	760.2	757.5	754.8	752.0	752.0	752.0
122.5°	807.7	810.9	814.2	817.5	818.1	816.3	814.4	812.4	810.5	809.7	808.9
125°	889.1	892.1	895.1	898.3	899.3	898.3	897.3	896.3	895.1	894.1	893.1
127.5°	969.4	973.2	977.1	981.0	982.3	981.1	979.9	978.7	977.4	976.1	974.9
130°	1019.9	1024.3	1028.6	1033.1	1034.9	1034.2	1033.6	1032.9	1032.2	1031.6	1030.9
132.5°	1075.1	1078.6	1082.3	1085.8	1087.7	1087.8	1087.9	1088.1	1088.2	1086.7	1085.3
135°	1150.1	1153.9	1157.5	1161.2	1163.5	1164.2	1164.9	1165.5	1166.2	1165.9	1165.5
137.5°	1228.3	1231.3	1234.4	1237.4	1239.4	1240.3	1241.1	1242.0	1242.9	1242.6	1242.3
140°	1275.8	1278.9	1281.9	1285.0	1287.3	1289.0	1290.7	1292.4	1294.0	1294.0	1294.0
142.5°	1324.5	1327.6	1330.6	1333.6	1335.7	1336.9	1338.1	1339.2	1340.4	1340.6	1340.9
145°	1393.9	1396.2	1398.6	1401.0	1403.2	1405.2	1407.2	1409.3	1411.3	1411.6	1412.0
147.5°	1456.7	1459.6	1462.5	1465.3	1467.4	1468.7	1470.1	1471.5	1472.8	1473.6	1474.3
150°	1498.5	1500.7	1502.7	1504.7	1506.3	1507.7	1509.0	1510.5	1511.8	1512.8	1513.8
152.5°	1536.3	1538.3	1540.3	1542.5	1544.3	1545.9	1547.5	1549.1	1550.7	1552.1	1553.3
155°	1592.0	1593.0	1594.0	1595.0	1596.0	1597.0	1598.0	1599.0	1600.0	1601.7	1603.5
157.5°	1640.0	1640.7	1641.4	1642.0	1642.7	1643.4	1644.0	1644.6	1645.2	1647.4	1649.7
160°	1669.3	1669.9	1670.6	1671.3	1671.8	1672.1	1672.4	1672.8	1673.1	1675.2	1677.2
162.5°	1695.6	1695.7	1695.8	1696.0	1696.2	1696.5	1696.9	1697.2	1697.5	1699.8	1702.1
165°	1730.7	1730.3	1730.0	1729.7	1729.5	1729.5	1729.5	1729.5	1729.5	1731.8	1734.2
167.5°	1759.8	1758.8	1757.8	1756.8	1756.3	1756.2	1756.2	1756.1	1756.0	1758.4	1760.7
170°	1775.6	1774.6	1773.6	1772.6	1771.9	1771.6	1771.3	1770.9	1770.6	1772.9	1775.3
172.5°	1786.7	1785.6	1784.6	1783.6	1782.9	1782.6	1782.2	1781.9	1781.5	1783.9	1786.2
175°	1800.0	1799.0	1798.0	1797.0	1796.1	1795.4	1794.7	1794.1	1793.4	1795.8	1798.2
177.5°	1805.7	1804.9	1804.1	1803.3	1802.6	1802.0	1801.5	1801.0	1800.4	1802.0	1803.7
180°	1804.1	1804.1	1804.1	1804.1	1804.1	1804.1	1804.1	1804.1	1804.1	1804.1	1804.1



TEST NUMBER: P331802-840

CATALOG NUMBER: S122RDIW-S485D1440U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1085.4	1085.4	1085.4	1085.4	1085.4	1085.4	1085.4
2.5°	1123.4	1127.3	1129.1	1129.1	1131.3	1130.3	1129.4
5°	1187.9	1195.1	1196.6	1203.4	1208.3	1206.8	1207.5
7.5°	1252.1	1263.6	1275.1	1280.2	1281.1	1284.1	1285.3
10°	1291.6	1301.1	1318.8	1316.2	1329.4	1336.9	1324.4
12.5°	1329.7	1342.4	1354.7	1358.1	1365.5	1368.0	1363.0
15°	1364.0	1370.8	1371.6	1369.7	1372.0	1370.1	1362.9
17.5°	1331.9	1320.9	1298.6	1288.0	1279.6	1267.3	1262.3
20°	1278.8	1246.4	1208.7	1193.6	1175.9	1141.1	1149.4
22.5°	1164.2	1127.2	1089.5	1045.4	1024.4	991.5	989.6
25°	985.8	922.1	851.9	802.8	774.3	741.4	727.1
27.5°	766.5	686.2	628.7	599.7	573.1	547.1	546.0
30°	622.3	561.9	517.5	492.5	476.4	465.3	467.7
32.5°	524.5	483.1	453.1	432.5	420.5	412.2	412.1
35°	428.8	400.5	381.2	372.6	364.0	357.9	358.3
37.5°	367.0	349.9	339.2	329.7	324.3	321.3	319.6
40°	335.3	321.3	313.1	307.4	302.9	298.7	297.9
42.5°	310.2	298.7	290.3	285.9	281.8	278.7	278.0
45°	275.3	265.9	258.3	253.4	251.6	248.9	248.9
47.5°	244.9	235.6	229.7	226.6	223.4	221.7	221.6
50°	224.4	217.2	212.0	210.1	207.4	206.3	205.9
52.5°	206.0	200.7	196.8	195.6	194.4	193.0	193.2
55°	181.0	178.0	176.5	175.3	173.5	171.2	172.7
57.5°	160.0	157.4	153.3	149.8	148.0	146.4	147.0
60°	145.2	139.9	134.6	130.5	129.4	125.9	125.9
62.5°	126.5	119.1	112.6	110.3	109.2	107.6	107.2
65°	97.3	94.3	92.8	91.3	90.5	90.5	89.8
67.5°	80.6	79.4	77.8	77.4	76.6	76.4	76.1
70°	71.3	69.8	69.0	68.7	67.9	68.3	67.2
72.5°	62.2	61.0	60.9	59.9	59.5	59.5	58.7
75°	49.0	49.0	48.7	48.3	47.6	47.2	47.6
77.5°	37.7	37.8	37.1	37.1	37.0	37.1	36.7
80°	30.2	30.5	30.2	29.8	29.4	29.8	29.4
82.5°	23.8	23.3	23.2	23.1	23.1	22.8	22.8
85°	13.5	13.9	13.5	13.2	13.2	13.2	13.5
87.5°	15.3	15.2	15.2	15.2	15.3	15.5	15.1
90°	51.3	50.6	50.4	50.8	51.1	51.4	51.8
92.5°	48.8	49.0	49.1	49.1	49.2	49.3	49.3
95°	97.5	97.5	97.0	96.4	95.7	95.0	94.4
97.5°	163.8	163.8	163.8	163.7	163.6	163.6	163.5
100°	210.1	210.1	210.0	209.5	209.2	208.9	208.5
102.5°	260.8	261.2	261.1	260.7	260.4	260.0	259.7
105°	337.0	337.6	338.0	338.0	338.0	338.0	338.0
107.5°	418.3	418.5	417.9	416.4	414.8	413.2	411.6
110°	473.5	473.5	472.9	471.9	470.9	469.9	468.9



TEST NUMBER: P331802-840

CATALOG NUMBER: S122RDIW-S485D1440U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	528.3	527.5	526.6	525.9	525.2	524.4	523.7
115°	614.0	613.7	613.0	612.0	611.0	610.0	608.9
117.5°	696.1	695.3	694.3	693.3	692.3	691.3	690.2
120°	752.0	752.0	751.5	750.5	749.5	748.5	747.5
122.5°	808.1	807.3	806.5	805.8	805.1	804.3	803.5
125°	892.1	891.1	890.5	890.1	889.8	889.5	889.1
127.5°	973.7	972.5	971.4	970.3	969.2	968.2	967.0
130°	1030.2	1029.5	1028.4	1027.1	1025.8	1024.4	1023.1
132.5°	1083.8	1082.3	1081.0	1079.9	1078.8	1077.7	1076.6
135°	1165.2	1164.9	1164.2	1163.2	1162.2	1161.1	1160.1
137.5°	1242.1	1241.8	1241.0	1239.7	1238.3	1237.0	1235.6
140°	1294.0	1294.0	1293.4	1292.0	1290.7	1289.3	1288.0
142.5°	1341.2	1341.4	1340.9	1339.6	1338.2	1336.9	1335.4
145°	1412.3	1412.6	1412.1	1410.8	1409.5	1408.1	1406.7
147.5°	1475.0	1475.8	1475.5	1474.2	1472.9	1471.7	1470.4
150°	1514.8	1515.8	1515.8	1514.8	1513.8	1512.8	1511.8
152.5°	1554.6	1555.9	1555.9	1554.6	1553.3	1552.1	1550.7
155°	1605.2	1606.8	1607.2	1606.2	1605.2	1604.2	1603.2
157.5°	1652.0	1654.4	1654.7	1653.0	1651.4	1649.8	1648.2
160°	1679.2	1681.2	1681.6	1680.2	1678.9	1677.6	1676.2
162.5°	1704.5	1706.7	1707.1	1705.5	1703.8	1702.2	1700.5
165°	1736.6	1739.0	1739.3	1737.6	1736.0	1734.2	1732.5
167.5°	1763.1	1765.4	1765.7	1764.0	1762.2	1760.5	1758.7
170°	1777.7	1780.1	1780.2	1778.2	1776.2	1774.1	1772.1
172.5°	1788.7	1791.0	1791.2	1789.2	1787.2	1785.1	1783.1
175°	1800.5	1802.9	1803.1	1801.0	1799.0	1797.0	1794.9
177.5°	1805.3	1807.0	1807.0	1805.3	1803.7	1802.0	1800.4
180°	1804.1	1804.1	1804.1	1804.1	1804.1	1804.1	1804.1

(END OF REPORT)