

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332185-830

Luminaire Tested: **S123DIW-S1000D460U830-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332185-830
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-9,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123DIW-S1000D460U830-4F0-1E-UDD-F1
Description: DEFINE 3 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 1000 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 460 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5390.3 lumens
Efficiency: N/A
Efficacy: 116.7 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 46.2
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332185-830

CATALOG NUMBER: S123DIW-S1000D460U830-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P332185-830

CATALOG NUMBER: S123DIW-S1000D460U830-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	112	112	112	112	107	107	107	107	96	96	96	86	86	86	76	76	76	72
1	103	98	94	90	97	93	90	86	84	81	79	75	73	71	67	66	64	61
2	93	86	79	74	88	81	76	71	73	69	65	66	63	59	59	57	54	51
3	85	75	68	62	80	72	65	59	65	59	55	58	54	50	53	49	46	43
4	78	67	58	52	74	64	56	50	58	52	47	52	47	43	47	43	40	37
5	72	60	51	45	68	57	49	43	52	45	40	47	42	37	42	38	35	32
6	66	54	45	39	63	51	43	38	47	40	35	42	37	33	38	34	30	28
7	61	49	40	34	58	46	39	33	42	36	31	39	33	29	35	31	27	25
8	57	44	36	31	54	42	35	30	39	32	28	35	30	26	32	28	24	22
9	53	40	33	27	50	39	32	27	36	29	25	33	27	24	30	25	22	20
10	50	37	30	25	47	36	29	24	33	27	23	30	25	21	28	23	20	18

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	16060	16060	16060
5°	16134	15913	16024
10°	16027	15774	15872
15°	15840	15597	15624
20°	15621	15341	15356
25°	15327	15037	15007
30°	15003	14701	14588
35°	14666	14345	14160
40°	14313	13952	13735
45°	13922	13592	13259
50°	13534	13147	12782
55°	13024	12688	12301
60°	12510	12152	11765
65°	12055	11566	11207
70°	11383	10902	10414
75°	10405	10031	9603
80°	9385	8988	8901
85°	8238	7929	7595



TEST NUMBER: P332185-830

CATALOG NUMBER: S123DIW-S1000D460U830-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	140.5	2.6
10°-20°	396.8	7.4
20°-30°	586.2	10.9
30°-40°	684.7	12.7
40°-50°	688.4	12.8
50°-60°	604.7	11.2
60°-70°	450.5	8.4
70°-80°	256.7	4.8
80°-90°	75.3	1.4
90°-100°	35.4	0.7
100°-110°	106.0	2.0
110°-120°	180.3	3.3
120°-130°	237.2	4.4
130°-140°	266.6	4.9
140°-150°	262.1	4.9
150°-160°	220.6	4.1
160°-170°	146.9	2.7
170°-180°	51.4	1.0
0°-30°	1123.5	20.8
0°-40°	1808.2	33.5
0°-60°	3101.3	57.5
0°-90°	3883.8	72.1
90°-120°	321.8	6.0
90°-150°	1087.6	20.2
90°-180°	1507.0	28.0
0°-180°	5390.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1492	1492	1492	1492	1492	
5°	1493	1486	1473	1485	1483	141
15°	1421	1416	1400	1409	1402	401
25°	1290	1282	1266	1267	1264	594
35°	1116	1108	1092	1084	1078	698
45°	915	909	893	878	871	706
55°	694	692	676	662	656	621
65°	473	467	454	444	440	467
75°	250	245	241	235	231	267
85°	67	64	64	62	62	73
90°	0	5	10	12	13	5
95°	25	28	32	33	33	28
105°	96	97	101	101	102	103
115°	182	183	182	182	182	180
125°	266	267	266	264	263	237
135°	345	347	347	345	344	266
145°	418	419	420	420	418	261
155°	479	479	479	481	478	220
165°	522	520	520	522	520	147
175°	542	541	541	543	540	52
180°	544	544	544	544	544	



TEST NUMBER: P332185-830

CATALOG NUMBER: S123DIW-S1000D460U830-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1492.0	1492.0	1492.0	1492.0	1492.0	1492.0	1492.0	1492.0	1492.0	1492.0	1492.0
2.5°	1497.0	1496.2	1495.2	1494.3	1493.5	1491.7	1489.2	1486.7	1484.2	1481.7	1483.9
5°	1493.2	1491.8	1490.3	1488.9	1487.5	1485.3	1482.1	1478.9	1475.8	1472.7	1475.6
7.5°	1478.6	1477.2	1475.7	1474.3	1472.9	1470.6	1467.4	1464.1	1460.8	1457.5	1460.1
10°	1466.3	1464.9	1463.4	1462.0	1460.6	1458.0	1454.3	1450.6	1446.9	1443.2	1445.8
12.5°	1449.8	1448.7	1447.5	1446.2	1445.1	1442.7	1439.3	1435.8	1432.3	1428.8	1430.7
15°	1421.4	1420.2	1419.1	1418.0	1416.8	1414.4	1410.7	1407.0	1403.3	1399.6	1401.8
17.5°	1388.3	1386.8	1385.3	1383.8	1382.3	1379.8	1376.0	1372.3	1368.7	1364.9	1366.5
20°	1363.7	1362.0	1360.3	1358.5	1356.8	1354.1	1350.4	1346.7	1343.0	1339.3	1340.4
22.5°	1336.0	1334.3	1332.6	1330.8	1329.1	1326.4	1322.7	1319.0	1315.3	1311.5	1312.5
25°	1290.5	1288.8	1287.1	1285.4	1283.6	1281.0	1277.2	1273.6	1269.9	1266.1	1266.4
27.5°	1242.1	1240.4	1238.7	1237.1	1235.4	1232.6	1228.6	1224.6	1220.6	1216.6	1216.8
30°	1207.1	1205.7	1204.3	1202.9	1201.5	1198.7	1194.8	1190.7	1186.8	1182.8	1182.8
32.5°	1172.2	1170.4	1168.5	1166.6	1164.7	1162.2	1159.1	1156.1	1153.0	1149.9	1148.3
35°	1116.1	1114.4	1112.7	1111.0	1109.2	1106.5	1102.8	1099.1	1095.4	1091.7	1090.0
37.5°	1058.6	1056.4	1054.2	1052.1	1049.9	1047.0	1043.2	1039.4	1035.7	1031.9	1029.8
40°	1018.6	1016.8	1015.1	1013.4	1011.7	1008.9	1004.8	1000.9	996.9	992.9	990.6
42.5°	978.5	976.6	974.7	972.7	970.8	967.8	963.8	959.9	955.8	951.9	949.6
45°	914.6	913.5	912.4	911.3	910.1	907.7	904.0	900.2	896.5	892.9	889.5
47.5°	851.3	849.6	848.0	846.3	844.7	842.1	838.7	835.2	831.7	828.2	824.8
50°	808.2	806.7	805.3	803.9	802.5	799.9	796.2	792.5	788.8	785.1	781.9
52.5°	763.0	762.0	761.1	760.2	759.1	756.7	752.8	748.9	744.9	740.9	738.3
55°	694.0	693.7	693.4	693.1	692.9	690.9	687.2	683.4	679.8	676.1	672.9
57.5°	628.3	627.4	626.4	625.5	624.4	622.5	619.5	616.5	613.6	610.7	607.8
60°	581.1	580.8	580.5	580.2	579.9	578.2	574.7	571.3	567.9	564.5	561.8
62.5°	539.0	538.3	537.5	536.8	536.1	534.0	530.6	527.2	523.8	520.3	517.7
65°	473.3	471.9	470.5	469.1	467.7	465.5	462.7	459.9	456.9	454.1	451.9
67.5°	403.9	402.6	401.3	400.1	398.8	397.1	394.9	392.8	390.6	388.4	386.4
70°	361.7	360.1	358.4	356.7	355.0	353.2	351.5	349.8	348.1	346.4	344.4
72.5°	317.6	316.4	315.1	313.9	312.6	311.0	309.1	307.2	305.2	303.2	301.5
75°	250.2	249.0	247.9	246.8	245.6	244.6	243.7	242.9	242.0	241.2	239.8
77.5°	190.4	189.7	189.1	188.5	187.8	187.0	186.1	185.0	184.0	182.9	182.0
80°	151.4	150.5	149.7	148.8	148.0	147.2	146.7	146.1	145.5	145.0	144.7
82.5°	113.4	113.2	113.1	112.9	112.7	112.5	112.4	112.4	112.3	112.2	111.6
85°	66.7	66.2	65.6	65.0	64.5	64.2	64.2	64.2	64.2	64.2	63.5
87.5°	26.8	26.3	25.8	25.3	24.8	24.5	24.6	24.6	24.6	24.6	24.5
90°	0.5	1.4	2.4	3.3	4.2	5.3	6.5	7.8	9.0	10.3	10.7
92.5°	10.4	11.0	11.6	12.3	12.9	13.6	14.3	15.0	15.7	16.4	16.7
95°	25.2	25.8	26.5	27.2	27.9	28.6	29.3	30.1	30.8	31.6	32.0
97.5°	44.8	45.2	45.7	46.3	46.8	47.2	47.8	48.4	48.9	49.5	49.9
100°	58.1	58.6	59.2	59.8	60.3	60.9	61.4	61.8	62.3	62.8	63.1
102.5°	73.4	73.8	74.2	74.5	74.8	75.3	76.0	76.5	77.2	77.9	78.1
105°	96.1	96.3	96.5	96.7	96.9	97.4	98.2	99.1	99.9	100.8	100.8
107.5°	122.4	122.5	122.6	122.7	122.9	123.1	123.5	123.8	124.1	124.5	124.8
110°	138.8	139.0	139.2	139.4	139.6	139.8	140.0	140.2	140.3	140.5	140.9



TEST NUMBER: P332185-830

CATALOG NUMBER: S123DIW-S1000D460U830-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	155.9	156.0	156.2	156.3	156.4	156.5	156.5	156.6	156.6	156.6	157.0
115°	181.5	181.8	182.1	182.4	182.7	182.8	182.6	182.4	182.2	182.0	182.1
117.5°	207.4	207.5	207.7	207.9	208.1	208.0	207.8	207.5	207.4	207.1	207.1
120°	223.4	223.9	224.5	225.1	225.6	225.7	225.3	224.8	224.3	223.9	223.8
122.5°	240.2	240.5	241.0	241.4	241.8	241.9	241.7	241.4	241.2	240.9	240.6
125°	265.7	266.0	266.3	266.6	266.8	266.8	266.6	266.5	266.3	266.1	265.7
127.5°	289.3	289.8	290.5	291.1	291.7	291.9	291.7	291.4	291.2	291.1	290.5
130°	305.0	305.8	306.5	307.3	308.0	308.2	307.9	307.6	307.4	307.1	306.7
132.5°	320.7	321.4	322.3	323.0	323.8	324.0	323.8	323.6	323.4	323.2	322.7
135°	344.7	345.3	345.8	346.4	346.9	347.2	347.1	347.0	346.9	346.9	346.5
137.5°	366.9	367.4	367.9	368.3	368.8	369.2	369.4	369.7	369.9	370.1	369.8
140°	382.3	382.8	383.2	383.7	384.2	384.5	384.6	384.7	384.7	384.8	384.7
142.5°	396.3	396.8	397.3	397.8	398.2	398.5	398.7	398.9	399.1	399.2	399.1
145°	418.2	418.4	418.6	418.8	419.0	419.1	419.4	419.7	420.0	420.3	420.2
147.5°	437.3	437.6	438.0	438.3	438.7	438.9	439.2	439.5	439.8	440.1	440.1
150°	450.6	450.8	451.0	451.2	451.4	451.6	451.8	451.9	452.1	452.3	452.3
152.5°	461.6	461.8	462.1	462.3	462.6	462.8	462.9	463.1	463.2	463.3	463.4
155°	478.8	478.8	478.8	478.8	478.8	478.9	479.0	479.1	479.2	479.3	479.7
157.5°	493.5	493.4	493.3	493.1	493.0	493.0	493.1	493.2	493.2	493.3	493.7
160°	502.8	502.6	502.4	502.2	502.0	501.9	501.9	501.9	501.9	501.9	502.4
162.5°	511.0	510.7	510.4	510.1	509.9	509.8	509.8	509.9	510.0	510.1	510.6
165°	521.5	521.2	520.9	520.7	520.4	520.3	520.3	520.3	520.3	520.3	520.8
167.5°	530.0	529.6	529.2	528.9	528.5	528.3	528.4	528.5	528.6	528.6	529.2
170°	534.8	534.4	534.0	533.7	533.3	533.1	533.1	533.1	533.1	533.1	533.8
172.5°	538.6	538.2	537.8	537.4	537.0	536.8	536.8	536.8	536.8	536.8	537.4
175°	542.4	542.1	541.7	541.3	540.9	540.7	540.7	540.7	540.7	540.7	541.3
177.5°	544.1	543.8	543.5	543.2	542.9	542.7	542.7	542.7	542.7	542.7	543.2
180°	543.8	543.8	543.8	543.8	543.8	543.8	543.8	543.8	543.8	543.8	543.8



TEST NUMBER: P332185-830

CATALOG NUMBER: S123DIW-S1000D460U830-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1492.0	1492.0	1492.0	1492.0	1492.0	1492.0	1492.0	1492.0
2.5°	1486.2	1488.6	1490.8	1491.9	1491.6	1491.4	1491.1	1490.9
5°	1478.4	1481.2	1484.1	1485.3	1484.7	1484.1	1483.6	1483.0
7.5°	1462.7	1465.3	1467.8	1469.0	1468.6	1468.3	1467.9	1467.5
10°	1448.3	1450.9	1453.5	1454.4	1453.9	1453.3	1452.7	1452.2
12.5°	1432.6	1434.5	1436.3	1437.1	1436.8	1436.4	1436.1	1435.8
15°	1404.1	1406.4	1408.7	1409.0	1407.3	1405.5	1403.8	1402.1
17.5°	1368.1	1369.7	1371.3	1371.8	1371.2	1370.6	1369.9	1369.3
20°	1341.5	1342.7	1343.9	1344.0	1343.1	1342.3	1341.4	1340.6
22.5°	1313.4	1314.3	1315.2	1315.1	1314.1	1313.0	1311.9	1310.8
25°	1266.7	1267.1	1267.3	1267.1	1266.1	1265.3	1264.4	1263.6
27.5°	1217.1	1217.3	1217.6	1217.1	1216.1	1214.9	1213.9	1212.8
30°	1182.8	1182.8	1182.8	1181.8	1179.8	1177.8	1175.8	1173.7
32.5°	1146.7	1145.2	1143.6	1142.2	1141.1	1140.0	1139.0	1137.8
35°	1088.3	1086.6	1084.9	1083.3	1081.9	1080.4	1079.0	1077.6
37.5°	1027.8	1025.8	1023.7	1022.2	1021.3	1020.4	1019.5	1018.6
40°	988.4	986.1	983.8	982.0	980.9	979.8	978.6	977.5
42.5°	947.3	945.0	942.7	941.0	939.9	938.8	937.6	936.5
45°	886.0	882.6	879.2	876.8	875.3	873.9	872.5	871.0
47.5°	821.4	818.1	814.7	812.5	811.2	809.9	808.7	807.4
50°	778.8	775.7	772.5	770.2	768.5	766.7	765.0	763.3
52.5°	735.6	732.9	730.3	728.0	726.3	724.6	722.9	721.2
55°	669.8	666.7	663.5	661.2	659.8	658.4	657.0	655.5
57.5°	605.0	602.3	599.5	597.2	595.6	593.9	592.3	590.6
60°	559.3	556.8	554.2	552.2	550.7	549.3	547.9	546.5
62.5°	515.2	512.6	510.0	508.3	507.3	506.3	505.4	504.4
65°	449.6	447.2	445.0	443.5	442.6	441.8	440.8	440.0
67.5°	384.5	382.5	380.5	378.9	377.7	376.5	375.2	374.1
70°	342.3	340.4	338.4	336.7	335.3	333.8	332.4	330.9
72.5°	299.7	297.9	296.1	294.9	294.2	293.4	292.8	292.0
75°	238.4	236.9	235.4	234.3	233.5	232.6	231.8	230.9
77.5°	181.0	180.0	179.1	178.6	178.6	178.6	178.6	178.6
80°	144.4	144.1	143.8	143.6	143.6	143.6	143.6	143.6
82.5°	111.1	110.6	110.1	109.7	109.4	109.2	109.1	108.8
85°	63.0	62.4	61.8	61.5	61.5	61.5	61.5	61.5
87.5°	24.3	24.1	24.0	23.9	24.0	24.0	24.0	24.1
90°	11.0	11.4	11.8	12.1	12.3	12.4	12.6	12.8
92.5°	17.0	17.3	17.6	17.7	17.6	17.4	17.3	17.2
95°	32.3	32.7	33.1	33.3	33.3	33.3	33.3	33.3
97.5°	50.3	50.8	51.2	51.4	51.4	51.4	51.3	51.3
100°	63.3	63.6	63.9	64.2	64.4	64.6	64.8	64.9
102.5°	78.4	78.7	79.0	79.1	79.1	79.0	79.0	78.9
105°	100.8	100.8	100.8	100.9	101.1	101.3	101.5	101.7
107.5°	125.1	125.4	125.6	125.7	125.6	125.5	125.5	125.4
110°	141.3	141.7	142.0	142.1	141.9	141.8	141.6	141.4



TEST NUMBER: P332185-830

CATALOG NUMBER: S123DIW-S1000D460U830-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	157.5	158.0	158.4	158.6	158.5	158.5	158.5	158.4
115°	182.2	182.3	182.4	182.4	182.3	182.2	182.1	182.0
117.5°	207.1	207.0	207.0	206.9	206.6	206.3	206.0	205.8
120°	223.7	223.6	223.5	223.3	223.1	222.9	222.7	222.5
122.5°	240.4	240.2	239.9	239.7	239.4	239.1	238.8	238.6
125°	265.3	264.9	264.6	264.2	263.8	263.4	263.1	262.7
127.5°	290.0	289.5	288.9	288.4	288.0	287.6	287.1	286.7
130°	306.3	305.9	305.6	305.1	304.4	303.8	303.1	302.4
132.5°	322.3	321.8	321.3	320.8	320.4	319.8	319.3	318.8
135°	346.1	345.7	345.3	345.1	344.9	344.7	344.5	344.3
137.5°	369.4	369.0	368.5	368.2	367.8	367.5	367.1	366.7
140°	384.7	384.6	384.5	384.1	383.4	382.8	382.1	381.4
142.5°	399.0	398.9	398.8	398.5	398.0	397.5	397.0	396.4
145°	420.1	420.0	419.9	419.7	419.3	419.0	418.6	418.2
147.5°	440.1	440.1	440.1	439.8	439.2	438.6	438.0	437.4
150°	452.3	452.3	452.3	452.0	451.5	450.9	450.3	449.8
152.5°	463.5	463.7	463.9	463.7	463.3	462.7	462.2	461.8
155°	480.0	480.4	480.8	480.6	479.9	479.3	478.6	478.0
157.5°	494.2	494.6	494.9	494.8	494.4	493.8	493.2	492.8
160°	502.8	503.3	503.8	503.8	503.4	503.0	502.7	502.3
162.5°	511.0	511.5	512.0	511.9	511.3	510.7	510.1	509.4
165°	521.4	522.0	522.5	522.5	521.8	521.1	520.5	519.8
167.5°	529.8	530.4	530.9	530.9	530.4	529.8	529.2	528.6
170°	534.4	535.1	535.7	535.7	535.1	534.4	533.8	533.1
172.5°	538.0	538.6	539.1	539.1	538.5	537.8	537.2	536.5
175°	541.9	542.4	543.0	543.0	542.3	541.7	541.0	540.4
177.5°	543.7	544.1	544.5	544.5	543.9	543.5	542.9	542.3
180°	543.8	543.8	543.8	543.8	543.8	543.8	543.8	543.8

(END OF REPORT)