

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332233-830

Luminaire Tested: **S123DIW-S1165D1320U830-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332233-830
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-9,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123DIW-S1165D1320U830-4F0-1E-UDD-F1
Description: DEFINE 3 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 1165 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 1320 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 8799.9 lumens
Efficiency: N/A
Efficacy: 115.5 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 76.2
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332233-830

CATALOG NUMBER: S123DIW-S1165D1320U830-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P332233-830

CATALOG NUMBER: S123DIW-S1165D1320U830-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	107	107	107	107	99	99	99	99	84	84	84		70	70	70		57	57	57	51
1	98	94	90	86	90	87	83	80	73	71	69		61	60	58		50	49	48	43
2	89	82	75	70	82	76	70	66	64	60	57		54	51	48		44	42	40	36
3	81	72	64	59	75	67	60	55	57	52	48		48	44	41		39	37	34	30
4	74	63	56	49	68	59	52	46	50	45	41		42	38	35		35	32	30	26
5	68	57	48	42	63	53	45	40	45	39	35		38	34	30		32	28	26	23
6	63	51	43	37	58	47	40	35	41	35	31		34	30	27		29	25	23	20
7	58	46	38	32	54	43	36	30	37	31	27		31	27	24		26	23	20	18
8	54	42	34	28	50	39	32	27	34	28	24		29	24	21		24	21	18	16
9	50	38	30	25	46	35	29	24	31	25	21		26	22	19		22	19	16	14
10	47	35	28	23	43	33	26	22	28	23	19		24	20	17		21	17	15	13

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	18547	18547	18547
5°	18634	18377	18506
10°	18510	18218	18332
15°	18293	18013	18046
20°	18040	17718	17734
25°	17701	17368	17332
30°	17329	16978	16850
35°	16938	16567	16353
40°	16530	16114	15864
45°	16081	15696	15314
50°	15630	15183	14763
55°	15041	14653	14208
60°	14449	14034	13586
65°	13924	13359	12944
70°	13149	12589	12032
75°	12015	11582	11088
80°	10835	10377	10290
85°	9510	9152	8793



TEST NUMBER: P332233-830

CATALOG NUMBER: S123DIW-S1165D1320U830-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	162.3	1.8
10°-20°	458.3	5.2
20°-30°	677.0	7.7
30°-40°	790.8	9.0
40°-50°	795.1	9.0
50°-60°	698.4	7.9
60°-70°	520.3	5.9
70°-80°	296.4	3.4
80°-90°	89.7	1.0
90°-100°	101.4	1.2
100°-110°	303.4	3.4
110°-120°	516.1	5.9
120°-130°	678.8	7.7
130°-140°	763.0	8.7
140°-150°	750.0	8.5
150°-160°	631.4	7.2
160°-170°	420.3	4.8
170°-180°	147.2	1.7
0°-30°	1297.6	14.7
0°-40°	2088.4	23.7
0°-60°	3581.8	40.7
0°-90°	4488.2	51.0
90°-120°	920.9	10.5
90°-150°	3112.8	35.4
90°-180°	4312.0	49.0
0°-180°	8799.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1723	1723	1723	1723	1723	
5°	1725	1717	1701	1715	1713	163
15°	1642	1635	1616	1627	1619	463
25°	1490	1481	1462	1464	1459	686
35°	1289	1280	1261	1252	1244	806
45°	1056	1050	1031	1014	1006	815
55°	802	799	781	765	757	718
65°	547	539	524	513	508	539
75°	289	283	278	271	267	309
85°	77	74	74	71	71	85
90°	1	14	29	34	37	9
95°	72	81	90	95	95	81
105°	275	278	288	289	291	295
115°	520	523	521	522	521	514
125°	760	764	762	757	752	678
135°	987	993	993	988	985	760
145°	1197	1199	1203	1202	1197	747
155°	1370	1370	1372	1376	1368	631
165°	1493	1489	1489	1495	1488	421
175°	1553	1548	1548	1554	1546	147
180°	1556	1556	1556	1556	1556	



TEST NUMBER: P332233-830

CATALOG NUMBER: S123DIW-S1165D1320U830-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1723.1	1723.1	1723.1	1723.1	1723.1	1723.1	1723.1	1723.1	1723.1	1723.1	1723.1
2.5°	1729.0	1728.0	1726.9	1725.9	1724.8	1722.8	1720.0	1717.0	1714.1	1711.2	1713.8
5°	1724.6	1723.0	1721.3	1719.7	1718.0	1715.3	1711.8	1708.1	1704.5	1700.8	1704.1
7.5°	1707.7	1706.0	1704.4	1702.7	1701.1	1698.4	1694.6	1690.9	1687.2	1683.4	1686.3
10°	1693.5	1691.8	1690.2	1688.5	1686.9	1683.9	1679.6	1675.4	1671.0	1666.8	1669.7
12.5°	1674.5	1673.1	1671.7	1670.4	1669.0	1666.2	1662.3	1658.2	1654.2	1650.2	1652.4
15°	1641.6	1640.3	1639.0	1637.7	1636.3	1633.5	1629.3	1624.9	1620.7	1616.4	1619.0
17.5°	1603.4	1601.7	1600.0	1598.3	1596.5	1593.6	1589.2	1585.0	1580.6	1576.4	1578.3
20°	1574.9	1572.9	1570.9	1569.0	1567.1	1563.9	1559.6	1555.4	1551.0	1546.8	1548.1
22.5°	1542.9	1541.0	1539.0	1537.0	1535.0	1531.9	1527.6	1523.3	1519.1	1514.8	1515.8
25°	1490.4	1488.5	1486.5	1484.5	1482.6	1479.4	1475.2	1470.9	1466.6	1462.4	1462.6
27.5°	1434.5	1432.6	1430.7	1428.7	1426.8	1423.6	1419.0	1414.4	1409.8	1405.1	1405.4
30°	1394.2	1392.5	1390.9	1389.2	1387.6	1384.5	1379.9	1375.3	1370.6	1366.0	1366.0
32.5°	1353.9	1351.7	1349.5	1347.4	1345.2	1342.3	1338.8	1335.2	1331.6	1328.1	1326.3
35°	1289.0	1287.0	1285.1	1283.1	1281.1	1278.0	1273.7	1269.4	1265.1	1260.8	1258.9
37.5°	1222.6	1220.1	1217.6	1215.1	1212.6	1209.2	1204.9	1200.5	1196.2	1191.8	1189.4
40°	1176.4	1174.4	1172.4	1170.4	1168.5	1165.2	1160.6	1155.9	1151.3	1146.8	1144.2
42.5°	1130.1	1127.9	1125.7	1123.4	1121.2	1117.8	1113.1	1108.5	1103.9	1099.4	1096.7
45°	1056.4	1055.1	1053.8	1052.4	1051.1	1048.3	1044.1	1039.7	1035.5	1031.1	1027.3
47.5°	983.2	981.3	979.4	977.4	975.5	972.6	968.6	964.5	960.5	956.5	952.6
50°	933.4	931.8	930.1	928.5	926.8	923.9	919.5	915.3	911.0	906.7	903.1
52.5°	881.3	880.1	879.0	877.9	876.8	873.9	869.4	864.9	860.4	855.7	852.6
55°	801.5	801.3	800.9	800.6	800.2	798.0	793.6	789.4	785.0	780.8	777.2
57.5°	725.7	724.5	723.4	722.4	721.2	719.0	715.5	712.1	708.7	705.2	702.0
60°	671.2	670.8	670.5	670.1	669.9	667.7	663.7	659.8	655.8	651.9	648.9
62.5°	622.5	621.7	620.9	620.0	619.2	616.7	612.7	608.8	604.9	601.0	597.9
65°	546.7	545.1	543.4	541.8	540.1	537.6	534.3	531.0	527.7	524.5	521.9
67.5°	466.4	465.0	463.5	462.0	460.6	458.6	456.1	453.6	451.1	448.7	446.3
70°	417.8	415.8	413.9	411.9	409.9	407.9	406.0	404.0	402.0	400.0	397.8
72.5°	366.8	365.4	363.9	362.5	361.1	359.2	356.9	354.7	352.5	350.2	348.2
75°	288.9	287.6	286.3	284.9	283.6	282.5	281.5	280.5	279.6	278.5	276.9
77.5°	219.9	219.1	218.4	217.7	217.0	216.0	214.8	213.7	212.4	211.3	210.2
80°	174.8	173.8	172.9	171.8	170.9	170.0	169.4	168.7	168.1	167.4	167.1
82.5°	131.0	130.7	130.5	130.4	130.2	130.0	129.9	129.8	129.6	129.5	128.9
85°	77.0	76.3	75.7	75.0	74.4	74.1	74.1	74.1	74.1	74.1	73.4
87.5°	31.1	30.8	30.5	30.3	30.1	30.2	30.6	31.1	31.5	32.0	31.9
90°	1.2	4.0	6.7	9.3	12.1	15.2	18.8	22.2	25.8	29.3	30.4
92.5°	29.6	31.4	33.3	35.2	36.9	38.9	40.9	42.9	45.0	46.9	47.8
95°	72.1	74.0	76.0	77.9	79.7	81.8	84.0	86.1	88.3	90.5	91.5
97.5°	128.1	129.5	130.9	132.3	133.7	135.3	136.9	138.4	140.0	141.6	142.8
100°	166.3	167.9	169.5	171.2	172.8	174.3	175.6	177.0	178.3	179.7	180.5
102.5°	210.3	211.2	212.3	213.2	214.1	215.6	217.4	219.1	220.9	222.7	223.6
105°	275.0	275.6	276.2	276.6	277.2	278.7	281.2	283.6	286.1	288.5	288.5
107.5°	350.3	350.7	351.0	351.4	351.7	352.3	353.3	354.3	355.2	356.2	357.1
110°	397.3	397.8	398.4	398.9	399.4	400.0	400.6	401.1	401.6	402.2	403.3



TEST NUMBER: P332233-830

CATALOG NUMBER: S123DIW-S1165D1320U830-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	446.2	446.5	446.9	447.1	447.5	447.7	447.8	447.9	448.1	448.2	449.5
115°	519.5	520.4	521.1	522.0	522.8	522.9	522.4	521.9	521.3	520.8	521.0
117.5°	593.4	593.9	594.5	595.0	595.6	595.5	594.7	594.1	593.3	592.7	592.6
120°	639.3	640.9	642.6	644.2	645.8	646.0	644.6	643.3	642.0	640.6	640.3
122.5°	687.3	688.4	689.7	690.9	692.0	692.3	691.5	690.9	690.1	689.5	688.7
125°	760.3	761.2	762.0	762.8	763.6	763.7	763.2	762.7	762.1	761.6	760.5
127.5°	827.8	829.6	831.3	833.0	834.8	835.4	834.8	834.2	833.6	833.0	831.4
130°	872.8	875.0	877.2	879.4	881.6	882.2	881.4	880.6	879.8	878.9	877.9
132.5°	917.8	920.0	922.2	924.4	926.5	927.3	926.7	926.1	925.5	924.9	923.6
135°	986.6	988.2	989.8	991.4	993.1	993.7	993.4	993.2	992.9	992.6	991.6
137.5°	1050.1	1051.4	1052.8	1054.1	1055.6	1056.6	1057.2	1058.0	1058.7	1059.4	1058.2
140°	1094.1	1095.4	1096.8	1098.2	1099.6	1100.3	1100.6	1100.9	1101.2	1101.5	1101.2
142.5°	1134.2	1135.6	1136.9	1138.3	1139.6	1140.6	1141.0	1141.5	1142.0	1142.6	1142.3
145°	1196.7	1197.3	1197.9	1198.4	1198.9	1199.7	1200.4	1201.3	1202.1	1202.9	1202.6
147.5°	1251.5	1252.5	1253.5	1254.5	1255.5	1256.3	1257.1	1257.8	1258.6	1259.3	1259.3
150°	1289.7	1290.2	1290.8	1291.3	1291.8	1292.4	1293.0	1293.5	1294.0	1294.6	1294.6
152.5°	1321.0	1321.7	1322.5	1323.2	1324.0	1324.6	1324.9	1325.2	1325.6	1325.9	1326.3
155°	1370.4	1370.4	1370.4	1370.4	1370.4	1370.6	1370.7	1371.0	1371.3	1371.6	1372.7
157.5°	1412.4	1412.1	1411.7	1411.5	1411.1	1411.1	1411.3	1411.5	1411.7	1411.9	1413.1
160°	1438.8	1438.3	1437.8	1437.2	1436.6	1436.3	1436.3	1436.3	1436.3	1436.3	1437.8
162.5°	1462.3	1461.5	1460.8	1460.0	1459.2	1459.0	1459.2	1459.4	1459.6	1459.8	1461.2
165°	1492.6	1491.8	1491.0	1490.2	1489.4	1488.9	1488.9	1488.9	1488.9	1488.9	1490.5
167.5°	1516.8	1515.7	1514.7	1513.5	1512.5	1512.0	1512.2	1512.5	1512.7	1512.9	1514.6
170°	1530.5	1529.5	1528.3	1527.3	1526.2	1525.6	1525.6	1525.6	1525.6	1525.6	1527.5
172.5°	1541.2	1540.2	1539.1	1538.0	1536.9	1536.3	1536.3	1536.3	1536.3	1536.3	1538.0
175°	1552.6	1551.4	1550.4	1549.3	1548.1	1547.7	1547.7	1547.7	1547.7	1547.7	1549.3
177.5°	1557.2	1556.3	1555.4	1554.5	1553.7	1553.2	1553.2	1553.2	1553.2	1553.2	1554.5
180°	1556.2	1556.2	1556.2	1556.2	1556.2	1556.2	1556.2	1556.2	1556.2	1556.2	1556.2



TEST NUMBER: P332233-830

CATALOG NUMBER: S123DIW-S1165D1320U830-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1723.1	1723.1	1723.1	1723.1	1723.1	1723.1	1723.1	1723.1
2.5°	1716.5	1719.1	1721.7	1723.0	1722.7	1722.4	1722.1	1721.9
5°	1707.4	1710.7	1714.0	1715.3	1714.7	1714.0	1713.4	1712.7
7.5°	1689.3	1692.2	1695.3	1696.5	1696.1	1695.7	1695.4	1695.0
10°	1672.7	1675.7	1678.7	1679.8	1679.1	1678.5	1677.8	1677.2
12.5°	1654.5	1656.7	1658.9	1659.8	1659.3	1659.0	1658.6	1658.2
15°	1621.6	1624.3	1626.9	1627.3	1625.3	1623.3	1621.4	1619.4
17.5°	1580.1	1582.0	1583.8	1584.3	1583.7	1582.9	1582.2	1581.5
20°	1549.4	1550.8	1552.1	1552.2	1551.2	1550.2	1549.3	1548.2
22.5°	1516.9	1518.0	1519.0	1518.9	1517.7	1516.4	1515.1	1513.9
25°	1463.0	1463.3	1463.7	1463.3	1462.4	1461.3	1460.4	1459.3
27.5°	1405.7	1405.9	1406.2	1405.7	1404.5	1403.2	1401.9	1400.7
30°	1366.0	1366.0	1366.0	1364.9	1362.5	1360.3	1357.9	1355.7
32.5°	1324.4	1322.6	1320.7	1319.2	1318.0	1316.6	1315.4	1314.2
35°	1256.9	1254.9	1252.9	1251.1	1249.4	1247.8	1246.1	1244.5
37.5°	1187.0	1184.7	1182.3	1180.6	1179.5	1178.5	1177.4	1176.4
40°	1141.5	1138.9	1136.2	1134.3	1132.9	1131.6	1130.3	1129.0
42.5°	1094.1	1091.5	1088.8	1086.8	1085.5	1084.2	1082.9	1081.6
45°	1023.3	1019.4	1015.4	1012.6	1011.0	1009.3	1007.7	1006.0
47.5°	948.8	944.9	940.9	938.3	936.9	935.4	934.0	932.6
50°	899.5	895.9	892.2	889.5	887.5	885.5	883.5	881.6
52.5°	849.6	846.5	843.4	840.8	838.9	836.9	834.9	832.9
55°	773.5	770.0	766.3	763.6	762.0	760.3	758.7	757.1
57.5°	698.8	695.6	692.3	689.8	687.9	686.0	684.0	682.1
60°	646.0	643.0	640.1	637.7	636.1	634.4	632.8	631.1
62.5°	595.0	592.0	589.1	587.0	585.9	584.8	583.7	582.6
65°	519.2	516.6	514.0	512.2	511.1	510.2	509.2	508.2
67.5°	444.0	441.7	439.4	437.5	436.2	434.8	433.4	432.1
70°	395.4	393.1	390.8	388.8	387.2	385.5	383.9	382.3
72.5°	346.2	344.1	342.0	340.6	339.8	338.9	338.1	337.2
75°	275.2	273.6	271.9	270.6	269.7	268.6	267.7	266.6
77.5°	209.1	207.9	206.8	206.2	206.2	206.2	206.2	206.2
80°	166.7	166.5	166.1	166.0	166.0	166.0	166.0	166.0
82.5°	128.3	127.7	127.1	126.7	126.4	126.2	125.9	125.6
85°	72.8	72.1	71.4	71.2	71.2	71.2	71.2	71.2
87.5°	31.9	31.8	31.8	31.8	31.9	32.0	32.1	32.2
90°	31.5	32.6	33.6	34.5	35.1	35.6	36.1	36.7
92.5°	48.6	49.6	50.4	50.7	50.3	50.0	49.7	49.4
95°	92.7	93.7	94.8	95.4	95.4	95.4	95.4	95.4
97.5°	144.0	145.3	146.6	147.1	147.0	146.9	146.8	146.7
100°	181.3	182.1	182.9	183.6	184.2	184.7	185.3	185.8
102.5°	224.3	225.2	226.0	226.3	226.2	226.1	226.0	225.9
105°	288.5	288.5	288.5	288.8	289.4	289.8	290.4	291.0
107.5°	358.0	358.8	359.7	360.0	359.7	359.3	359.0	358.6
110°	404.4	405.5	406.5	406.8	406.2	405.8	405.2	404.6



TEST NUMBER: P332233-830

CATALOG NUMBER: S123DIW-S1165D1320U830-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	450.7	452.0	453.4	453.9	453.8	453.7	453.6	453.6
115°	521.3	521.6	521.9	521.9	521.6	521.3	521.0	520.8
117.5°	592.6	592.5	592.4	592.0	591.3	590.5	589.7	589.0
120°	640.0	639.8	639.5	639.0	638.6	638.0	637.4	636.9
122.5°	688.1	687.3	686.6	685.9	685.1	684.4	683.6	682.9
125°	759.4	758.4	757.2	756.2	755.1	753.9	752.9	751.8
127.5°	829.9	828.4	826.9	825.5	824.3	823.0	821.8	820.5
130°	876.8	875.7	874.6	873.1	871.2	869.3	867.4	865.5
132.5°	922.3	921.0	919.7	918.3	916.8	915.4	913.9	912.5
135°	990.4	989.4	988.3	987.5	986.9	986.4	985.8	985.3
137.5°	1057.1	1055.9	1054.8	1053.8	1052.7	1051.7	1050.7	1049.6
140°	1100.9	1100.6	1100.3	1099.3	1097.4	1095.4	1093.5	1091.7
142.5°	1142.0	1141.7	1141.4	1140.6	1139.1	1137.6	1136.1	1134.7
145°	1202.3	1202.1	1201.8	1201.2	1200.0	1198.9	1197.9	1196.7
147.5°	1259.3	1259.3	1259.3	1258.6	1257.0	1255.3	1253.7	1252.1
150°	1294.6	1294.6	1294.6	1293.7	1292.1	1290.5	1288.8	1287.2
152.5°	1326.7	1327.2	1327.6	1327.1	1325.7	1324.3	1322.9	1321.4
155°	1373.8	1374.9	1375.9	1375.5	1373.7	1371.8	1369.8	1367.9
157.5°	1414.2	1415.3	1416.5	1416.3	1414.8	1413.2	1411.7	1410.2
160°	1439.1	1440.5	1441.8	1442.0	1440.9	1439.8	1438.7	1437.6
162.5°	1462.5	1464.0	1465.3	1465.1	1463.4	1461.6	1459.9	1458.1
165°	1492.2	1493.8	1495.4	1495.3	1493.5	1491.6	1489.6	1487.7
167.5°	1516.3	1518.0	1519.7	1519.7	1518.0	1516.3	1514.6	1512.9
170°	1529.5	1531.3	1533.2	1533.2	1531.3	1529.5	1527.5	1525.6
172.5°	1539.7	1541.4	1543.1	1543.0	1541.2	1539.2	1537.3	1535.4
175°	1550.9	1552.6	1554.2	1554.0	1552.1	1550.2	1548.3	1546.4
177.5°	1555.9	1557.2	1558.5	1558.4	1556.8	1555.3	1553.8	1552.3
180°	1556.2	1556.2	1556.2	1556.2	1556.2	1556.2	1556.2	1556.2

(END OF REPORT)