

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331788-840

Luminaire Tested: **S122RDIW-S485D435U840-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331788-840
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-8,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122RDIW-S485D435U840-4F0-1E-UDD-F1
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 485 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 435 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3232.2 lumens
Efficiency: N/A
Efficacy: 107.0 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 30.2
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331788-840

CATALOG NUMBER: S122RDIW-S485D435U840-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P331788-840

CATALOG NUMBER: S122RDIW-S485D435U840-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	108	108	108	108	100	100	100	100	85	85	85	71	71	71	59	59	59	53
1	99	95	91	88	92	88	85	82	75	73	71	64	62	61	53	52	51	46
2	91	83	77	72	84	78	72	68	67	63	59	56	54	51	47	45	44	39
3	83	74	67	61	77	69	62	57	59	55	51	50	47	44	42	40	38	34
4	76	66	58	52	70	61	54	49	53	48	44	45	41	38	38	35	33	29
5	70	59	51	45	65	55	48	43	48	42	38	41	37	33	35	31	29	26
6	65	53	45	39	60	50	42	37	43	38	33	37	33	30	32	28	26	23
7	60	48	40	35	56	45	38	33	39	34	30	34	30	26	29	26	23	21
8	56	44	36	31	52	41	34	29	36	30	27	31	27	24	27	23	21	19
9	52	40	33	28	48	38	31	26	33	28	24	29	25	21	25	21	19	17
10	49	37	30	25	45	35	28	24	31	25	22	27	22	19	23	20	17	15

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	13454	13454	13454
5°	13506	13287	13361
10°	13404	13070	12959
15°	13249	12682	12318
20°	13036	12129	11519
25°	12818	11501	10750
30°	12515	10856	9758
35°	12220	10153	8889
40°	11921	9428	7885
45°	11574	8611	6976
50°	11215	7784	6081
55°	10849	6899	5222
60°	10424	5968	4334
65°	9941	5012	3947
70°	9361	4131	3635
75°	8659	3762	3387
80°	7643	3366	3087
85°	6002	2649	2649



TEST NUMBER: P331788-840

CATALOG NUMBER: S122RDIW-S485D435U840-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	78.0	2.4
10°-20°	214.2	6.6
20°-30°	300.8	9.3
30°-40°	328.0	10.1
40°-50°	301.6	9.3
50°-60°	236.8	7.3
60°-70°	154.4	4.8
70°-80°	79.6	2.5
80°-90°	22.8	0.7
90°-100°	34.4	1.1
100°-110°	106.7	3.3
110°-120°	182.4	5.6
120°-130°	239.9	7.4
130°-140°	269.2	8.3
140°-150°	263.9	8.2
150°-160°	221.4	6.8
160°-170°	146.8	4.5
170°-180°	51.3	1.6
0°-30°	593.0	18.3
0°-40°	921.0	28.5
0°-60°	1459.4	45.2
0°-90°	1716.2	53.1
90°-120°	323.4	10.0
90°-150°	1096.4	33.9
90°-180°	1516.0	46.9
0°-180°	3232.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	833	833	833	833	833	
5°	833	829	820	826	824	79
15°	793	783	759	745	737	223
25°	720	694	646	616	603	331
35°	620	580	515	469	451	388
45°	507	455	377	326	306	391
55°	385	325	245	202	186	344
65°	260	199	131	107	103	258
75°	139	87	60	55	54	147
85°	32	17	14	14	14	38
90°	0	6	16	15	16	3
95°	24	28	29	29	28	27
105°	98	100	101	102	102	104
115°	183	186	185	184	183	181
125°	266	270	269	268	267	238
135°	345	349	350	350	349	266
145°	418	421	424	424	423	261
155°	478	480	481	483	482	220
165°	520	520	520	523	521	147
175°	541	540	539	542	540	51
180°	542	542	542	542	542	



TEST NUMBER: P331788-840

CATALOG NUMBER: S122RDIW-S485D435U840-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	833.3	833.3	833.3	833.3	833.3	833.3	833.3	833.3	833.3	833.3	833.3
2.5°	836.4	835.8	835.1	834.4	833.7	832.6	831.2	829.7	828.2	826.8	828.1
5°	833.3	832.5	831.7	830.9	830.0	828.5	826.4	824.2	822.0	819.8	821.3
7.5°	824.8	823.7	822.7	821.6	820.6	818.8	816.3	813.7	811.2	808.7	809.1
10°	817.6	816.4	815.2	814.1	812.8	810.6	807.3	803.9	800.5	797.2	796.7
12.5°	808.5	807.1	805.6	804.2	802.7	799.9	795.6	791.3	787.0	782.7	781.8
15°	792.6	790.8	789.0	787.1	785.3	781.5	775.8	770.1	764.5	758.7	755.6
17.5°	773.3	770.4	767.6	764.8	761.9	756.9	749.6	742.3	735.0	727.6	723.9
20°	758.7	755.4	752.0	748.7	745.3	739.4	731.0	722.7	714.3	705.9	701.8
22.5°	743.1	739.3	735.5	731.7	728.0	721.4	712.0	702.5	693.1	683.6	678.2
25°	719.5	714.2	708.8	703.4	698.0	689.8	678.7	667.7	656.6	645.6	638.7
27.5°	691.2	685.3	679.4	673.7	667.8	658.6	646.2	633.7	621.3	608.7	600.8
30°	671.3	664.9	658.5	652.2	645.8	635.9	622.5	609.0	595.6	582.3	573.7
32.5°	652.0	644.5	637.0	629.7	622.2	611.6	597.9	584.2	570.6	556.9	547.1
35°	620.0	611.4	602.9	594.3	585.7	574.1	559.4	544.6	529.9	515.1	504.5
37.5°	587.9	578.6	569.2	559.8	550.5	537.9	522.2	506.4	490.7	475.0	463.3
40°	565.6	555.6	545.5	535.5	525.4	512.3	496.0	479.8	463.5	447.3	435.4
42.5°	542.7	532.1	521.5	511.0	500.4	486.7	469.9	453.0	436.3	419.5	407.2
45°	506.9	495.6	484.3	473.1	461.9	447.5	429.9	412.3	394.7	377.1	365.2
47.5°	471.8	459.9	448.1	436.2	424.2	409.2	391.0	372.8	354.7	336.5	324.7
50°	446.5	434.5	422.7	410.8	398.9	383.7	365.3	346.9	328.4	309.9	298.4
52.5°	421.7	409.3	396.9	384.5	372.0	356.8	338.7	320.7	302.7	284.7	273.5
55°	385.4	372.3	359.2	346.2	333.2	317.5	299.4	281.3	263.2	245.1	235.1
57.5°	348.1	334.8	321.3	307.9	294.5	279.1	261.8	244.3	226.9	209.5	200.3
60°	322.8	309.4	296.0	282.6	269.1	253.9	236.6	219.3	202.1	184.8	176.2
62.5°	298.0	284.7	271.2	257.8	244.4	229.5	213.1	196.6	180.2	163.7	155.5
65°	260.2	246.6	233.1	219.4	205.9	191.6	176.5	161.4	146.3	131.2	125.5
67.5°	223.7	210.3	196.7	183.3	169.8	156.2	142.7	129.2	115.5	102.0	99.4
70°	198.3	185.3	172.2	159.2	146.0	133.7	122.2	110.6	99.1	87.5	85.8
72.5°	174.2	161.7	149.2	136.6	124.1	113.2	103.9	94.6	85.3	76.0	74.6
75°	138.8	127.0	115.3	103.6	91.8	83.1	77.5	71.7	66.0	60.3	59.2
77.5°	103.9	93.6	83.3	73.0	62.8	56.2	53.5	50.8	48.0	45.2	44.5
80°	82.2	73.6	65.1	56.6	48.0	42.9	41.2	39.6	37.9	36.2	35.5
82.5°	62.3	55.6	49.0	42.3	35.6	31.7	30.6	29.4	28.3	27.2	26.8
85°	32.4	28.9	25.3	21.9	18.4	16.4	15.9	15.3	14.8	14.3	14.3
87.5°	9.8	8.9	8.1	7.3	6.5	6.3	6.7	7.2	7.6	8.1	7.9
90°	0.5	1.7	2.9	4.1	5.4	7.1	9.3	11.5	13.7	16.1	15.9
92.5°	8.2	9.1	9.9	10.8	11.7	12.4	12.9	13.5	14.0	14.5	14.5
95°	23.8	24.8	25.9	26.9	27.9	28.5	28.7	28.9	29.1	29.3	29.3
97.5°	43.4	44.3	45.2	46.2	47.1	47.7	48.1	48.5	48.9	49.2	49.2
100°	58.1	58.9	59.7	60.6	61.4	61.9	62.2	62.5	62.8	63.1	63.1
102.5°	73.5	74.1	74.7	75.4	76.0	76.6	77.0	77.4	77.8	78.2	78.3
105°	98.4	98.7	99.0	99.3	99.6	99.9	100.1	100.3	100.5	100.7	100.9
107.5°	123.4	123.9	124.3	124.8	125.2	125.4	125.4	125.4	125.4	125.4	125.5
110°	139.6	140.2	140.8	141.4	142.0	142.3	142.3	142.3	142.3	142.3	142.3



TEST NUMBER: P331788-840

CATALOG NUMBER: S122RDIW-S485D435U840-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	157.1	157.7	158.3	159.0	159.6	159.9	159.8	159.7	159.6	159.5	159.3
115°	183.0	183.6	184.2	184.8	185.4	185.6	185.4	185.2	185.0	184.8	184.7
117.5°	208.8	209.6	210.5	211.3	212.1	212.2	211.7	211.1	210.5	210.0	209.6
120°	226.0	226.8	227.6	228.4	229.2	229.2	228.4	227.6	226.8	226.0	226.0
122.5°	241.8	242.8	243.7	244.7	245.7	245.9	245.3	244.7	244.2	243.6	243.4
125°	266.3	267.2	268.1	269.0	269.9	270.2	269.9	269.6	269.3	269.0	268.7
127.5°	290.1	291.3	292.5	293.7	294.8	295.2	294.9	294.5	294.1	293.8	293.4
130°	305.2	306.5	307.8	309.1	310.4	311.0	310.8	310.6	310.4	310.2	310.0
132.5°	322.0	323.1	324.2	325.3	326.3	326.9	326.9	327.0	327.0	327.0	326.6
135°	344.6	345.7	346.8	347.9	349.0	349.6	349.8	350.0	350.2	350.4	350.3
137.5°	368.2	369.1	370.0	370.9	371.8	372.4	372.7	373.0	373.2	373.5	373.4
140°	382.5	383.4	384.4	385.3	386.2	386.9	387.4	387.9	388.4	388.9	388.9
142.5°	397.2	398.1	399.0	399.9	400.8	401.4	401.7	402.1	402.4	402.8	402.9
145°	418.2	418.9	419.6	420.3	421.0	421.7	422.3	422.9	423.5	424.1	424.2
147.5°	437.0	437.8	438.7	439.5	440.4	441.0	441.4	441.8	442.2	442.6	442.8
150°	449.8	450.4	451.0	451.6	452.2	452.7	453.1	453.5	453.9	454.3	454.6
152.5°	461.1	461.7	462.3	462.9	463.5	464.1	464.5	465.0	465.5	466.1	466.5
155°	478.1	478.4	478.7	479.1	479.4	479.7	480.0	480.3	480.6	480.9	481.4
157.5°	492.7	492.9	493.1	493.3	493.5	493.6	493.8	494.0	494.2	494.4	495.1
160°	501.5	501.7	501.9	502.1	502.3	502.4	502.5	502.6	502.7	502.8	503.4
162.5°	509.5	509.6	509.6	509.6	509.7	509.8	509.9	510.0	510.1	510.2	510.8
165°	520.2	520.1	520.0	519.9	519.8	519.8	519.8	519.8	519.8	519.8	520.5
167.5°	529.2	528.9	528.6	528.3	528.0	527.8	527.8	527.8	527.8	527.8	528.5
170°	533.9	533.6	533.3	533.0	532.7	532.5	532.4	532.3	532.2	532.1	532.8
172.5°	537.2	536.9	536.6	536.3	536.0	535.8	535.7	535.6	535.5	535.4	536.1
175°	541.3	541.0	540.7	540.4	540.1	539.8	539.6	539.4	539.2	539.0	539.7
177.5°	542.9	542.7	542.4	542.2	541.9	541.7	541.6	541.4	541.2	541.1	541.6
180°	542.2	542.2	542.2	542.2	542.2	542.2	542.2	542.2	542.2	542.2	542.2



TEST NUMBER: P331788-840

CATALOG NUMBER: S122RDIW-S485D435U840-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	833.3	833.3	833.3	833.3	833.3	833.3	833.3	833.3
2.5°	829.4	830.8	832.1	832.6	832.4	832.1	831.8	831.6
5°	822.8	824.4	825.9	826.4	825.9	825.4	824.9	824.4
7.5°	809.5	809.9	810.4	810.2	809.3	808.4	807.6	806.7
10°	796.2	795.7	795.2	794.5	793.5	792.4	791.4	790.4
12.5°	780.9	780.0	779.1	777.8	776.1	774.5	772.7	771.1
15°	752.3	749.2	746.0	743.6	741.8	740.2	738.5	736.9
17.5°	720.0	716.3	712.5	709.1	706.3	703.4	700.5	697.6
20°	697.5	693.4	689.1	685.2	681.6	677.8	674.2	670.4
22.5°	672.8	667.4	662.1	657.9	655.2	652.5	649.7	646.9
25°	631.9	625.0	618.1	613.4	610.9	608.3	605.9	603.4
27.5°	592.8	584.7	576.7	570.8	566.7	562.8	558.8	554.8
30°	565.1	556.6	548.1	541.5	536.9	532.5	528.0	523.4
32.5°	537.3	527.7	517.9	510.9	506.6	502.4	498.1	493.8
35°	494.0	483.4	472.9	465.7	462.1	458.4	454.7	451.0
37.5°	451.7	440.1	428.5	420.5	416.4	412.1	407.9	403.6
40°	423.4	411.5	399.6	391.5	387.2	382.8	378.4	374.1
42.5°	394.9	382.5	370.3	362.0	357.8	353.6	349.3	345.1
45°	353.3	341.4	329.5	321.5	317.5	313.5	309.4	305.5
47.5°	312.9	301.0	289.2	281.4	277.8	274.2	270.4	266.8
50°	286.8	275.3	263.7	256.2	252.7	249.1	245.6	242.1
52.5°	262.3	251.2	239.9	232.8	229.5	226.3	223.0	219.7
55°	225.0	214.9	204.9	198.2	195.1	191.9	188.7	185.5
57.5°	191.1	181.9	172.7	166.7	164.0	161.4	158.6	155.9
60°	167.6	159.2	150.6	145.0	142.3	139.6	136.9	134.2
62.5°	147.3	139.3	131.1	126.2	124.6	123.0	121.4	119.8
65°	119.9	114.1	108.5	105.3	104.8	104.3	103.8	103.3
67.5°	96.7	94.1	91.5	90.0	89.4	88.9	88.4	87.8
70°	84.1	82.5	80.8	79.6	79.0	78.3	77.6	77.0
72.5°	73.2	71.8	70.4	69.5	69.1	68.7	68.3	67.9
75°	58.0	56.9	55.6	54.9	54.8	54.6	54.4	54.3
77.5°	43.9	43.2	42.6	42.1	41.8	41.6	41.3	41.0
80°	34.8	34.2	33.5	33.2	33.2	33.2	33.2	33.2
82.5°	26.4	26.0	25.5	25.3	25.3	25.3	25.3	25.3
85°	14.3	14.3	14.3	14.3	14.3	14.3	14.3	14.3
87.5°	7.7	7.5	7.4	7.3	7.3	7.3	7.3	7.4
90°	15.7	15.5	15.2	15.1	15.2	15.3	15.5	15.6
92.5°	14.6	14.6	14.7	14.7	14.7	14.7	14.8	14.8
95°	29.3	29.3	29.3	29.2	29.0	28.8	28.6	28.4
97.5°	49.2	49.2	49.2	49.2	49.2	49.2	49.2	49.2
100°	63.1	63.1	63.1	63.1	63.0	62.9	62.8	62.7
102.5°	78.3	78.4	78.5	78.5	78.4	78.3	78.2	78.1
105°	101.1	101.3	101.5	101.6	101.6	101.6	101.6	101.6
107.5°	125.6	125.7	125.8	125.6	125.1	124.6	124.2	123.7
110°	142.3	142.3	142.3	142.1	141.8	141.5	141.2	140.9



TEST NUMBER: P331788-840

CATALOG NUMBER: S122RDIW-S485D435U840-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	159.1	158.8	158.5	158.2	158.0	157.8	157.6	157.4
115°	184.6	184.5	184.4	184.2	183.9	183.6	183.3	183.0
117.5°	209.4	209.1	208.9	208.6	208.3	208.0	207.7	207.4
120°	226.0	226.0	226.0	225.9	225.6	225.3	225.0	224.7
122.5°	243.1	242.9	242.6	242.4	242.2	242.0	241.7	241.5
125°	268.4	268.1	267.8	267.6	267.5	267.4	267.3	267.2
127.5°	293.0	292.7	292.3	292.0	291.5	291.2	290.9	290.6
130°	309.8	309.6	309.4	309.1	308.7	308.3	307.9	307.5
132.5°	326.2	325.7	325.3	324.9	324.6	324.2	323.9	323.6
135°	350.2	350.1	350.0	349.8	349.5	349.2	348.9	348.6
137.5°	373.3	373.2	373.2	372.9	372.5	372.1	371.7	371.3
140°	388.9	388.9	388.9	388.7	388.3	387.9	387.5	387.1
142.5°	402.9	403.0	403.1	402.9	402.5	402.1	401.7	401.3
145°	424.3	424.4	424.5	424.3	423.9	423.5	423.1	422.7
147.5°	443.0	443.3	443.5	443.4	443.0	442.6	442.2	441.9
150°	454.9	455.2	455.6	455.6	455.2	454.9	454.6	454.3
152.5°	466.8	467.2	467.6	467.6	467.2	466.8	466.5	466.1
155°	481.9	482.4	482.9	483.0	482.7	482.4	482.1	481.8
157.5°	495.7	496.4	497.2	497.3	496.8	496.2	495.8	495.3
160°	504.0	504.6	505.2	505.3	504.9	504.5	504.1	503.7
162.5°	511.5	512.2	512.9	513.0	512.5	512.0	511.5	511.1
165°	521.2	521.9	522.6	522.7	522.2	521.7	521.2	520.7
167.5°	529.2	529.9	530.6	530.7	530.1	529.6	529.1	528.6
170°	533.5	534.2	534.9	535.0	534.4	533.8	533.2	532.6
172.5°	536.8	537.6	538.3	538.3	537.7	537.0	536.4	535.8
175°	540.4	541.1	541.8	541.9	541.3	540.7	540.1	539.5
177.5°	542.1	542.5	543.0	543.0	542.5	542.1	541.6	541.1
180°	542.2	542.2	542.2	542.2	542.2	542.2	542.2	542.2

(END OF REPORT)