

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332238-830

Luminaire Tested: **S123DIW-S1165D1535U830-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332238-830
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-5,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123DIW-S1165D1535U830-4F0-1E-UDD-F
Description: DEFINE 3 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 1165 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 1535 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 10272.8 lumens
Efficiency: N/A
Efficacy: 123.9 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 82.9
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332238-830

CATALOG NUMBER: S123DIW-S1165D1535U830-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P332238-830

CATALOG NUMBER: S123DIW-S1165D1535U830-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	106	106	106	106	97	97	97	97	80	80	80	64	64	64	50	50	50	44
1	96	92	88	85	88	84	81	78	70	68	65	57	55	54	44	43	42	37
2	88	80	74	69	80	74	68	64	61	57	54	50	47	45	39	37	36	31
3	80	71	63	57	73	65	58	53	54	49	45	44	41	38	35	32	30	26
4	73	62	55	49	67	57	50	45	48	43	39	39	35	32	31	28	26	22
5	67	56	47	41	61	51	44	39	43	37	33	35	31	28	28	25	23	19
6	62	50	42	36	56	46	39	34	38	33	29	32	28	24	25	22	20	17
7	57	45	37	31	52	41	34	29	35	29	25	29	25	22	23	20	18	15
8	53	41	33	28	48	38	31	26	32	26	23	26	22	19	21	18	16	13
9	49	37	30	25	45	34	28	23	29	24	20	24	20	17	19	16	14	12
10	46	34	27	22	42	31	25	21	27	22	18	22	18	16	18	15	13	11

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	18547	18547	18547
5°	18634	18377	18506
10°	18510	18218	18332
15°	18293	18013	18046
20°	18040	17718	17734
25°	17701	17368	17332
30°	17329	16978	16850
35°	16938	16567	16353
40°	16530	16114	15864
45°	16081	15696	15314
50°	15630	15183	14763
55°	15041	14653	14208
60°	14449	14034	13586
65°	13924	13359	12944
70°	13149	12589	12032
75°	12015	11582	11088
80°	10835	10377	10290
85°	9510	9152	8793



TEST NUMBER: P332238-830

CATALOG NUMBER: S123DIW-S1165D1535U830-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	162.3	1.6
10°-20°	458.3	4.5
20°-30°	677.0	6.6
30°-40°	790.8	7.7
40°-50°	795.1	7.7
50°-60°	698.4	6.8
60°-70°	520.3	5.1
70°-80°	296.4	2.9
80°-90°	90.4	0.9
90°-100°	69.0	0.7
100°-110°	328.6	3.2
110°-120°	789.4	7.7
120°-130°	1005.2	9.8
130°-140°	1074.1	10.5
140°-150°	1004.4	9.8
150°-160°	810.1	7.9
160°-170°	522.9	5.1
170°-180°	180.2	1.8
0°-30°	1297.6	12.6
0°-40°	2088.4	20.3
0°-60°	3581.8	34.9
0°-90°	4488.9	43.7
90°-120°	1187.0	11.6
90°-150°	4270.6	41.6
90°-180°	5784.0	56.3
0°-180°	10272.8	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1723	1723	1723	1723	1723	
5°	1725	1717	1701	1715	1713	163
15°	1642	1635	1616	1627	1619	463
25°	1490	1481	1462	1464	1459	686
35°	1289	1280	1261	1252	1244	806
45°	1056	1050	1031	1014	1006	815
55°	802	799	781	765	757	718
65°	547	539	524	513	508	539
75°	289	283	278	271	267	309
85°	77	74	74	71	71	85
90°	1	16	34	39	42	8
95°	86	32	44	53	54	106
105°	420	428	309	73	62	445
115°	788	796	809	822	829	777
125°	1110	1121	1127	1130	1133	991
135°	1382	1391	1396	1400	1396	1064
145°	1595	1604	1608	1610	1611	998
155°	1757	1754	1756	1762	1754	809
165°	1853	1849	1847	1857	1849	523
175°	1897	1890	1891	1900	1890	180
180°	1897	1897	1897	1897	1897	



TEST NUMBER: P332238-830

CATALOG NUMBER: S123DIW-S1165D1535U830-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1723.1	1723.1	1723.1	1723.1	1723.1	1723.1	1723.1	1723.1	1723.1	1723.1	1723.1
2.5°	1729.0	1728.0	1726.9	1725.9	1724.8	1722.8	1720.0	1717.0	1714.1	1711.2	1713.8
5°	1724.6	1723.0	1721.3	1719.7	1718.0	1715.3	1711.8	1708.1	1704.5	1700.8	1704.1
7.5°	1707.7	1706.0	1704.4	1702.7	1701.1	1698.4	1694.6	1690.9	1687.2	1683.4	1686.3
10°	1693.5	1691.8	1690.2	1688.5	1686.9	1683.9	1679.6	1675.4	1671.0	1666.8	1669.7
12.5°	1674.5	1673.1	1671.7	1670.4	1669.0	1666.2	1662.3	1658.2	1654.2	1650.2	1652.4
15°	1641.6	1640.3	1639.0	1637.7	1636.3	1633.5	1629.3	1624.9	1620.7	1616.4	1619.0
17.5°	1603.4	1601.7	1600.0	1598.3	1596.5	1593.6	1589.2	1585.0	1580.6	1576.4	1578.3
20°	1574.9	1572.9	1570.9	1569.0	1567.1	1563.9	1559.6	1555.4	1551.0	1546.8	1548.1
22.5°	1542.9	1541.0	1539.0	1537.0	1535.0	1531.9	1527.6	1523.3	1519.1	1514.8	1515.8
25°	1490.4	1488.5	1486.5	1484.5	1482.6	1479.4	1475.2	1470.9	1466.6	1462.4	1462.6
27.5°	1434.5	1432.6	1430.7	1428.7	1426.8	1423.6	1419.0	1414.4	1409.8	1405.1	1405.4
30°	1394.2	1392.5	1390.9	1389.2	1387.6	1384.5	1379.9	1375.3	1370.6	1366.0	1366.0
32.5°	1353.9	1351.7	1349.5	1347.4	1345.2	1342.3	1338.8	1335.2	1331.6	1328.1	1326.3
35°	1289.0	1287.0	1285.1	1283.1	1281.1	1278.0	1273.7	1269.4	1265.1	1260.8	1258.9
37.5°	1222.6	1220.1	1217.6	1215.1	1212.6	1209.2	1204.9	1200.5	1196.2	1191.8	1189.4
40°	1176.4	1174.4	1172.4	1170.4	1168.5	1165.2	1160.6	1155.9	1151.3	1146.8	1144.2
42.5°	1130.1	1127.9	1125.7	1123.4	1121.2	1117.8	1113.1	1108.5	1103.9	1099.4	1096.7
45°	1056.4	1055.1	1053.8	1052.4	1051.1	1048.3	1044.1	1039.7	1035.5	1031.1	1027.3
47.5°	983.2	981.3	979.4	977.4	975.5	972.6	968.6	964.5	960.5	956.5	952.6
50°	933.4	931.8	930.1	928.5	926.8	923.9	919.5	915.3	911.0	906.7	903.1
52.5°	881.3	880.1	879.0	877.9	876.8	873.9	869.4	864.9	860.4	855.7	852.6
55°	801.5	801.3	800.9	800.6	800.2	798.0	793.6	789.4	785.0	780.8	777.2
57.5°	725.7	724.5	723.4	722.4	721.2	719.0	715.5	712.1	708.7	705.2	702.0
60°	671.2	670.8	670.5	670.1	669.9	667.7	663.7	659.8	655.8	651.9	648.9
62.5°	622.5	621.7	620.9	620.0	619.2	616.7	612.7	608.8	604.9	601.0	597.9
65°	546.7	545.1	543.4	541.8	540.1	537.6	534.3	531.0	527.7	524.5	521.9
67.5°	466.4	465.0	463.5	462.0	460.6	458.6	456.1	453.6	451.1	448.7	446.3
70°	417.8	415.8	413.9	411.9	409.9	407.9	406.0	404.0	402.0	400.0	397.8
72.5°	366.8	365.4	363.9	362.5	361.1	359.2	356.9	354.7	352.5	350.2	348.2
75°	288.9	287.6	286.3	284.9	283.6	282.5	281.5	280.5	279.6	278.5	276.9
77.5°	219.9	219.1	218.4	217.7	217.0	216.0	214.8	213.7	212.4	211.3	210.2
80°	174.8	173.8	172.9	171.8	170.9	170.0	169.4	168.7	168.1	167.4	167.1
82.5°	131.0	130.7	130.5	130.4	130.2	130.0	129.9	129.8	129.6	129.5	128.9
85°	77.0	76.3	75.7	75.0	74.4	74.1	74.1	74.1	74.1	74.1	73.4
87.5°	31.1	30.9	30.7	30.6	30.4	30.6	31.2	31.8	32.3	32.8	32.8
90°	1.4	4.5	7.6	10.8	13.9	17.5	21.6	25.6	29.8	33.8	35.1
92.5°	26.2	25.4	24.4	23.6	22.7	23.8	26.9	30.0	33.0	36.1	38.1
95°	86.0	73.1	60.3	47.4	34.6	29.9	33.4	36.8	40.2	43.6	45.9
97.5°	172.8	167.0	161.3	155.4	149.7	135.5	113.0	90.5	68.0	45.3	47.9
100°	238.2	244.4	250.6	256.9	263.2	241.9	193.0	144.2	95.4	46.5	49.0
102.5°	312.5	317.1	321.6	326.0	330.5	306.1	252.8	199.4	146.1	92.7	84.9
105°	419.9	423.4	426.8	430.3	433.7	421.3	393.1	365.0	336.8	308.6	253.2
107.5°	533.2	535.9	538.7	541.5	544.2	547.8	552.2	556.8	561.2	565.6	525.0
110°	608.7	611.2	613.7	616.2	618.8	621.7	625.2	628.6	632.1	635.5	625.2



TEST NUMBER: P332238-830

CATALOG NUMBER: S123DIW-S1165D1535U830-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	680.9	683.2	685.4	687.7	689.8	692.8	696.2	699.6	703.0	706.5	706.7
115°	787.7	789.6	791.5	793.3	795.2	797.6	800.4	803.1	806.0	808.8	811.9
117.5°	891.1	893.4	895.7	898.1	900.4	902.3	903.7	905.1	906.5	908.0	910.5
120°	955.4	958.2	961.0	963.8	966.7	968.6	969.4	970.3	971.3	972.2	974.8
122.5°	1020.8	1023.0	1025.4	1027.7	1030.0	1031.8	1032.9	1034.2	1035.3	1036.5	1038.3
125°	1110.3	1112.9	1115.4	1117.9	1120.4	1122.3	1123.5	1124.7	1126.1	1127.3	1127.9
127.5°	1197.1	1199.7	1202.2	1204.7	1207.2	1209.2	1210.7	1212.2	1213.7	1215.2	1216.2
130°	1251.2	1253.8	1256.3	1258.8	1261.3	1263.2	1264.4	1265.6	1267.0	1268.2	1269.4
132.5°	1303.2	1305.6	1308.2	1310.6	1313.2	1314.9	1315.9	1316.9	1317.9	1318.9	1320.1
135°	1382.3	1384.2	1386.1	1388.0	1389.9	1391.4	1392.6	1393.9	1395.2	1396.4	1397.3
137.5°	1449.9	1452.4	1454.7	1457.1	1459.4	1461.0	1461.7	1462.4	1463.1	1463.8	1465.3
140°	1495.1	1496.9	1498.8	1500.7	1502.6	1503.9	1504.9	1505.8	1506.7	1507.7	1509.0
142.5°	1536.7	1538.6	1540.5	1542.4	1544.3	1545.7	1546.6	1547.6	1548.5	1549.4	1550.4
145°	1595.1	1597.2	1599.5	1601.7	1603.8	1605.2	1605.9	1606.5	1607.1	1607.8	1608.4
147.5°	1650.0	1651.5	1652.9	1654.4	1655.8	1656.8	1657.5	1658.1	1658.7	1659.3	1660.0
150°	1683.9	1684.8	1685.7	1686.7	1687.6	1688.4	1689.0	1689.7	1690.3	1690.9	1691.5
152.5°	1714.3	1714.8	1715.1	1715.6	1716.1	1716.5	1716.8	1717.2	1717.6	1718.0	1719.1
155°	1757.1	1756.5	1755.9	1755.3	1754.6	1754.4	1754.8	1755.1	1755.4	1755.7	1757.3
157.5°	1790.4	1790.4	1790.3	1790.2	1790.2	1790.0	1789.6	1789.3	1789.0	1788.7	1790.5
160°	1810.7	1810.3	1810.1	1809.8	1809.4	1809.1	1808.8	1808.5	1808.2	1807.9	1809.8
162.5°	1829.9	1829.0	1828.2	1827.4	1826.6	1826.0	1825.7	1825.4	1825.0	1824.8	1826.9
165°	1852.9	1852.0	1851.1	1850.1	1849.2	1848.6	1848.2	1847.9	1847.7	1847.3	1849.8
167.5°	1870.9	1869.7	1868.5	1867.3	1866.0	1865.4	1865.4	1865.4	1865.4	1865.4	1867.8
170°	1881.1	1879.9	1878.6	1877.4	1876.1	1875.5	1875.5	1875.5	1875.5	1875.5	1878.0
172.5°	1887.9	1886.4	1884.9	1883.4	1881.9	1881.2	1881.5	1881.8	1882.0	1882.3	1884.8
175°	1896.6	1895.1	1893.5	1892.0	1890.4	1889.7	1890.1	1890.4	1890.6	1891.0	1893.2
177.5°	1898.8	1897.6	1896.4	1895.2	1893.9	1893.4	1893.7	1893.9	1894.1	1894.4	1896.4
180°	1896.6	1896.6	1896.6	1896.6	1896.6	1896.6	1896.6	1896.6	1896.6	1896.6	1896.6



TEST NUMBER: P332238-830

CATALOG NUMBER: S123DIW-S1165D1535U830-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1723.1	1723.1	1723.1	1723.1	1723.1	1723.1	1723.1	1723.1
2.5°	1716.5	1719.1	1721.7	1723.0	1722.7	1722.4	1722.1	1721.9
5°	1707.4	1710.7	1714.0	1715.3	1714.7	1714.0	1713.4	1712.7
7.5°	1689.3	1692.2	1695.3	1696.5	1696.1	1695.7	1695.4	1695.0
10°	1672.7	1675.7	1678.7	1679.8	1679.1	1678.5	1677.8	1677.2
12.5°	1654.5	1656.7	1658.9	1659.8	1659.3	1659.0	1658.6	1658.2
15°	1621.6	1624.3	1626.9	1627.3	1625.3	1623.3	1621.4	1619.4
17.5°	1580.1	1582.0	1583.8	1584.3	1583.7	1582.9	1582.2	1581.5
20°	1549.4	1550.8	1552.1	1552.2	1551.2	1550.2	1549.3	1548.2
22.5°	1516.9	1518.0	1519.0	1518.9	1517.7	1516.4	1515.1	1513.9
25°	1463.0	1463.3	1463.7	1463.3	1462.4	1461.3	1460.4	1459.3
27.5°	1405.7	1405.9	1406.2	1405.7	1404.5	1403.2	1401.9	1400.7
30°	1366.0	1366.0	1366.0	1364.9	1362.5	1360.3	1357.9	1355.7
32.5°	1324.4	1322.6	1320.7	1319.2	1318.0	1316.6	1315.4	1314.2
35°	1256.9	1254.9	1252.9	1251.1	1249.4	1247.8	1246.1	1244.5
37.5°	1187.0	1184.7	1182.3	1180.6	1179.5	1178.5	1177.4	1176.4
40°	1141.5	1138.9	1136.2	1134.3	1132.9	1131.6	1130.3	1129.0
42.5°	1094.1	1091.5	1088.8	1086.8	1085.5	1084.2	1082.9	1081.6
45°	1023.3	1019.4	1015.4	1012.6	1011.0	1009.3	1007.7	1006.0
47.5°	948.8	944.9	940.9	938.3	936.9	935.4	934.0	932.6
50°	899.5	895.9	892.2	889.5	887.5	885.5	883.5	881.6
52.5°	849.6	846.5	843.4	840.8	838.9	836.9	834.9	832.9
55°	773.5	770.0	766.3	763.6	762.0	760.3	758.7	757.1
57.5°	698.8	695.6	692.3	689.8	687.9	686.0	684.0	682.1
60°	646.0	643.0	640.1	637.7	636.1	634.4	632.8	631.1
62.5°	595.0	592.0	589.1	587.0	585.9	584.8	583.7	582.6
65°	519.2	516.6	514.0	512.2	511.1	510.2	509.2	508.2
67.5°	444.0	441.7	439.4	437.5	436.2	434.8	433.4	432.1
70°	395.4	393.1	390.8	388.8	387.2	385.5	383.9	382.3
72.5°	346.2	344.1	342.0	340.6	339.8	338.9	338.1	337.2
75°	275.2	273.6	271.9	270.6	269.7	268.6	267.7	266.6
77.5°	209.1	207.9	206.8	206.2	206.2	206.2	206.2	206.2
80°	166.7	166.5	166.1	166.0	166.0	166.0	166.0	166.0
82.5°	128.3	127.7	127.1	126.7	126.4	126.2	125.9	125.6
85°	72.8	72.1	71.4	71.2	71.2	71.2	71.2	71.2
87.5°	32.8	32.8	32.8	32.8	33.0	33.1	33.2	33.4
90°	36.3	37.6	38.8	39.8	40.4	41.0	41.7	42.2
92.5°	40.1	42.1	44.1	45.2	45.6	46.0	46.4	46.8
95°	48.1	50.2	52.4	53.5	53.5	53.5	53.5	53.5
97.5°	50.4	52.9	55.4	56.8	57.1	57.4	57.8	58.1
100°	51.5	54.0	56.6	58.0	58.2	58.5	58.9	59.2
102.5°	77.2	69.5	61.6	58.1	58.6	59.2	59.8	60.3
105°	197.7	142.3	86.9	59.5	60.1	60.8	61.4	62.0
107.5°	484.3	443.7	403.0	361.8	320.1	278.2	236.5	194.7
110°	614.8	604.5	594.2	566.6	521.8	477.0	432.3	387.5



TEST NUMBER: P332238-830

CATALOG NUMBER: S123DIW-S1165D1535U830-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	706.9	707.1	707.3	702.7	693.1	683.7	674.3	664.8
115°	815.1	818.2	821.3	823.5	824.8	826.0	827.3	828.6
117.5°	913.0	915.5	918.0	919.5	919.6	919.9	920.2	920.4
120°	977.3	979.8	982.3	983.5	983.5	983.5	983.5	983.5
122.5°	1040.0	1041.8	1043.6	1044.5	1044.8	1045.0	1045.3	1045.6
125°	1128.5	1129.2	1129.7	1130.4	1131.1	1131.6	1132.3	1132.9
127.5°	1217.2	1218.2	1219.2	1219.4	1218.8	1218.1	1217.5	1216.9
130°	1270.6	1272.0	1273.2	1273.5	1272.9	1272.2	1271.6	1271.0
132.5°	1321.4	1322.7	1323.9	1324.1	1323.2	1322.4	1321.4	1320.6
135°	1398.3	1399.2	1400.1	1400.1	1399.2	1398.3	1397.3	1396.4
137.5°	1466.8	1468.3	1469.8	1470.2	1469.6	1469.0	1468.3	1467.7
140°	1510.2	1511.5	1512.7	1513.1	1512.4	1511.8	1511.2	1510.5
142.5°	1551.4	1552.5	1553.4	1553.5	1552.7	1551.7	1550.9	1550.0
145°	1609.0	1609.7	1610.2	1610.6	1610.6	1610.6	1610.6	1610.6
147.5°	1660.6	1661.2	1661.9	1661.4	1660.0	1658.6	1657.1	1655.7
150°	1692.1	1692.8	1693.4	1693.3	1692.3	1691.4	1690.5	1689.5
152.5°	1720.2	1721.4	1722.5	1722.3	1720.9	1719.4	1718.0	1716.6
155°	1758.9	1760.4	1762.0	1761.8	1759.9	1758.0	1756.1	1754.4
157.5°	1792.4	1794.3	1796.2	1795.9	1793.5	1791.0	1788.6	1786.1
160°	1811.7	1813.5	1815.3	1815.2	1813.0	1810.8	1808.6	1806.5
162.5°	1829.0	1831.2	1833.2	1833.3	1831.5	1829.5	1827.6	1825.6
165°	1852.3	1854.8	1857.4	1857.5	1855.3	1853.1	1850.9	1848.7
167.5°	1870.4	1872.8	1875.4	1875.4	1872.8	1870.4	1867.8	1865.4
170°	1880.5	1883.0	1885.6	1885.6	1883.0	1880.5	1878.0	1875.5
172.5°	1887.3	1889.8	1892.2	1892.2	1889.4	1886.7	1883.9	1881.1
175°	1895.4	1897.5	1899.8	1899.6	1897.1	1894.6	1892.1	1889.6
177.5°	1898.4	1900.4	1902.4	1902.1	1899.6	1897.1	1894.6	1892.2
180°	1896.6	1896.6	1896.6	1896.6	1896.6	1896.6	1896.6	1896.6

(END OF REPORT)