

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332107-830

Luminaire Tested: **S123DIW-S340D1030U830-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P332107-830  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-9,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S123DIW-S340D1030U830-4F0-1E-UDD-F1  
Description: DEFINE 3 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 340 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
UPLIGHT 1030 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 4700.6 lumens  
Efficiency: N/A  
Efficacy: 123.7 lumens/watt  
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31  
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')  
CIE Type: Semi-Indirect


Input Watts (W): 38  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332107-830

CATALOG NUMBER: S123DIW-S340D1030U830-4F0-1E-UDD-F1

### Luminous Intensity Polar Plot





TEST NUMBER: P332107-830

CATALOG NUMBER: S123DIW-S340D1030U830-4F0-1E-UDD-F1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	102	102	102	102	91	91	91	91	71	71	71	53	53	53	36	36	36	28
1	93	89	85	81	83	79	76	73	62	60	58	46	45	44	32	31	30	24
2	85	77	71	66	75	69	64	60	55	51	48	41	39	37	28	27	26	20
3	77	68	61	55	69	61	55	50	48	44	40	36	33	31	25	23	22	17
4	70	60	52	47	63	54	47	42	43	38	34	32	29	26	22	20	19	14
5	64	53	45	40	57	48	41	36	38	33	29	29	25	23	20	18	16	13
6	59	48	40	34	53	43	36	31	34	29	25	26	22	20	18	16	14	11
7	55	43	35	30	49	39	32	27	31	26	22	23	20	17	16	14	13	10
8	51	39	31	26	45	35	29	24	28	23	20	21	18	15	15	13	11	9
9	47	35	28	23	42	32	26	21	26	21	18	20	16	14	14	12	10	8
10	44	32	25	21	39	29	23	19	23	19	16	18	15	12	13	11	9	7

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	5498	5498	5498
5°	5524	5448	5486
10°	5487	5400	5434
15°	5422	5340	5349
20°	5347	5252	5257
25°	5247	5149	5138
30°	5137	5033	4994
35°	5021	4911	4847
40°	4900	4776	4703
45°	4766	4654	4539
50°	4632	4501	4376
55°	4459	4344	4211
60°	4284	4159	4028
65°	4126	3958	3836
70°	3899	3733	3566
75°	3564	3435	3290
80°	3211	3081	3050
85°	2816	2717	2606



TEST NUMBER: P332107-830

CATALOG NUMBER: S123DIW-S340D1030U830-4F0-1E-UDD-F1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	48.1	1.0
10°-20°	135.9	2.9
20°-30°	200.7	4.3
30°-40°	234.4	5.0
40°-50°	235.7	5.0
50°-60°	207.0	4.4
60°-70°	154.2	3.3
70°-80°	87.9	1.9
80°-90°	28.8	0.6
90°-100°	79.2	1.7
100°-110°	237.0	5.0
110°-120°	403.1	8.6
120°-130°	530.3	11.3
130°-140°	596.0	12.7
140°-150°	585.8	12.5
150°-160°	493.2	10.5
160°-170°	328.3	7.0
170°-180°	115.0	2.4
0°-30°	384.6	8.2
0°-40°	619.1	13.2
0°-60°	1061.7	22.6
0°-90°	1332.7	28.4
90°-120°	719.4	15.3
90°-150°	2431.5	51.7
90°-180°	3368.0	71.6
0°-180°	4700.6	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	511	511	511	511	511	
5°	511	509	504	508	508	48
15°	487	485	479	482	480	137
25°	442	439	434	434	433	203
35°	382	379	374	371	369	239
45°	313	311	306	301	298	242
55°	238	237	232	227	224	213
65°	162	160	155	152	151	160
75°	86	84	83	80	79	92
85°	23	22	22	21	21	25
90°	1	11	23	27	29	5
95°	56	63	71	74	74	63
105°	215	217	225	226	227	230
115°	406	408	407	408	407	401
125°	594	597	595	591	587	529
135°	771	776	775	772	770	594
145°	935	937	940	938	935	584
155°	1070	1070	1071	1075	1069	493
165°	1166	1163	1163	1168	1162	329
175°	1213	1209	1209	1214	1208	115
180°	1216	1216	1216	1216	1216	



TEST NUMBER: P332107-830

CATALOG NUMBER: S123DIW-S340D1030U830-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	510.8	510.8	510.8	510.8	510.8	510.8	510.8	510.8	510.8	510.8	510.8
2.5°	512.6	512.2	511.9	511.6	511.2	510.7	509.8	509.0	508.1	507.3	508.0
5°	511.2	510.7	510.2	509.7	509.3	508.5	507.4	506.3	505.2	504.2	505.1
7.5°	506.2	505.7	505.2	504.7	504.3	503.4	502.4	501.2	500.1	499.0	499.8
10°	502.0	501.5	501.0	500.5	500.0	499.2	497.9	496.6	495.3	494.1	494.9
12.5°	496.3	496.0	495.5	495.1	494.7	493.9	492.8	491.5	490.3	489.2	489.8
15°	486.6	486.3	485.8	485.4	485.0	484.2	483.0	481.6	480.4	479.2	479.9
17.5°	475.2	474.8	474.3	473.7	473.3	472.4	471.1	469.9	468.5	467.3	467.8
20°	466.8	466.3	465.7	465.1	464.5	463.5	462.3	461.0	459.8	458.5	458.9
22.5°	457.3	456.8	456.2	455.6	455.1	454.1	452.8	451.6	450.3	449.0	449.3
25°	441.8	441.2	440.6	440.1	439.5	438.6	437.2	436.0	434.7	433.5	433.6
27.5°	425.2	424.6	424.0	423.5	422.9	422.0	420.7	419.2	417.9	416.5	416.6
30°	413.3	412.7	412.3	411.8	411.3	410.4	409.1	407.6	406.3	404.9	404.9
32.5°	401.3	400.7	400.0	399.4	398.8	397.8	396.8	395.8	394.7	393.7	393.1
35°	382.1	381.5	380.9	380.3	379.8	378.8	377.6	376.3	375.0	373.7	373.2
37.5°	362.4	361.7	360.9	360.1	359.5	358.4	357.1	355.8	354.6	353.3	352.6
40°	348.7	348.1	347.5	346.9	346.4	345.3	344.0	342.6	341.3	339.9	339.1
42.5°	335.0	334.3	333.7	333.0	332.3	331.3	330.0	328.6	327.3	325.8	325.1
45°	313.1	312.7	312.4	312.0	311.6	310.8	309.4	308.2	306.9	305.7	304.5
47.5°	291.4	290.9	290.3	289.7	289.2	288.3	287.1	285.9	284.7	283.5	282.4
50°	276.6	276.2	275.7	275.2	274.8	273.8	272.6	271.4	270.0	268.8	267.7
52.5°	261.2	260.9	260.5	260.2	259.9	259.0	257.7	256.4	255.1	253.6	252.8
55°	237.6	237.5	237.4	237.3	237.2	236.5	235.3	233.9	232.7	231.5	230.4
57.5°	215.1	214.8	214.4	214.1	213.8	213.1	212.1	211.0	210.1	209.1	208.1
60°	199.0	198.9	198.8	198.7	198.6	197.9	196.7	195.6	194.4	193.2	192.4
62.5°	184.5	184.3	184.1	183.8	183.5	182.9	181.6	180.5	179.3	178.1	177.3
65°	162.0	161.6	161.1	160.6	160.1	159.4	158.4	157.4	156.5	155.4	154.7
67.5°	138.3	137.8	137.4	137.0	136.6	135.9	135.3	134.5	133.7	133.0	132.3
70°	123.9	123.3	122.7	122.1	121.5	120.9	120.4	119.7	119.1	118.6	117.9
72.5°	108.8	108.3	107.9	107.4	107.0	106.5	105.8	105.2	104.5	103.9	103.2
75°	85.7	85.2	84.8	84.5	84.1	83.7	83.4	83.1	82.8	82.6	82.1
77.5°	65.1	64.9	64.8	64.6	64.3	64.0	63.7	63.3	63.0	62.6	62.3
80°	51.8	51.6	51.3	51.0	50.6	50.4	50.2	50.0	49.9	49.7	49.5
82.5°	38.8	38.7	38.7	38.6	38.5	38.5	38.5	38.5	38.5	38.4	38.2
85°	22.8	22.6	22.4	22.2	22.1	22.0	22.0	22.0	22.0	22.0	21.8
87.5°	9.3	9.5	9.7	9.9	10.1	10.5	10.9	11.4	11.9	12.3	12.4
90°	0.9	3.1	5.2	7.4	9.4	11.9	14.6	17.4	20.2	22.9	23.8
92.5°	23.1	24.5	26.0	27.4	28.8	30.3	32.0	33.6	35.1	36.7	37.3
95°	56.4	57.8	59.3	60.8	62.3	63.9	65.6	67.3	69.0	70.7	71.5
97.5°	100.1	101.1	102.3	103.4	104.5	105.7	106.9	108.1	109.3	110.6	111.6
100°	129.9	131.1	132.4	133.7	135.0	136.1	137.2	138.3	139.3	140.3	141.0
102.5°	164.3	165.0	165.8	166.5	167.3	168.3	169.8	171.2	172.6	174.0	174.7
105°	214.9	215.3	215.7	216.1	216.6	217.7	219.6	221.5	223.5	225.4	225.4
107.5°	273.7	273.9	274.2	274.5	274.7	275.2	276.0	276.7	277.5	278.2	278.9
110°	310.4	310.8	311.2	311.6	312.1	312.5	312.9	313.3	313.8	314.1	315.0



TEST NUMBER: P332107-830

CATALOG NUMBER: S123DIW-S340D1030U830-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	348.6	348.8	349.0	349.3	349.6	349.7	349.8	349.9	350.0	350.1	351.1
115°	405.9	406.4	407.1	407.7	408.4	408.5	408.0	407.6	407.2	406.8	407.0
117.5°	463.5	463.9	464.4	464.8	465.2	465.1	464.6	464.0	463.4	463.0	462.9
120°	499.5	500.7	502.0	503.2	504.5	504.6	503.5	502.5	501.4	500.4	500.1
122.5°	536.9	537.8	538.8	539.6	540.5	540.7	540.3	539.7	539.1	538.6	538.0
125°	594.0	594.6	595.2	595.9	596.5	596.6	596.2	595.8	595.3	594.9	594.1
127.5°	646.7	648.0	649.4	650.7	652.1	652.5	652.1	651.6	651.1	650.6	649.5
130°	681.8	683.5	685.2	686.9	688.6	689.1	688.5	687.9	687.2	686.5	685.7
132.5°	716.9	718.6	720.3	722.1	723.8	724.3	723.9	723.4	722.9	722.5	721.4
135°	770.6	771.8	773.2	774.4	775.7	776.2	776.0	775.8	775.6	775.3	774.5
137.5°	820.3	821.3	822.4	823.4	824.5	825.3	825.9	826.4	827.0	827.6	826.6
140°	854.6	855.7	856.8	857.8	858.8	859.5	859.7	860.0	860.2	860.4	860.2
142.5°	886.0	887.0	888.1	889.1	890.2	890.9	891.3	891.6	892.1	892.5	892.2
145°	934.8	935.3	935.7	936.1	936.5	937.1	937.7	938.4	939.0	939.6	939.4
147.5°	977.6	978.4	979.1	980.0	980.7	981.4	981.9	982.6	983.2	983.7	983.7
150°	1007.4	1007.9	1008.2	1008.7	1009.1	1009.6	1009.9	1010.4	1010.8	1011.3	1011.3
152.5°	1031.9	1032.5	1033.0	1033.7	1034.3	1034.6	1034.9	1035.2	1035.5	1035.7	1036.0
155°	1070.4	1070.4	1070.4	1070.4	1070.4	1070.5	1070.7	1071.0	1071.2	1071.4	1072.2
157.5°	1103.3	1103.1	1102.8	1102.5	1102.3	1102.2	1102.4	1102.6	1102.8	1102.9	1103.8
160°	1123.9	1123.5	1123.0	1122.7	1122.2	1122.0	1122.0	1122.0	1122.0	1122.0	1123.0
162.5°	1142.3	1141.7	1141.0	1140.5	1139.9	1139.6	1139.8	1140.0	1140.2	1140.4	1141.4
165°	1165.9	1165.3	1164.7	1164.0	1163.4	1163.1	1163.1	1163.1	1163.1	1163.1	1164.3
167.5°	1184.9	1184.0	1183.2	1182.3	1181.5	1181.1	1181.3	1181.5	1181.7	1181.8	1183.1
170°	1195.5	1194.7	1193.8	1193.0	1192.1	1191.8	1191.8	1191.8	1191.8	1191.8	1193.2
172.5°	1203.9	1203.1	1202.2	1201.4	1200.5	1200.1	1200.1	1200.1	1200.1	1200.1	1201.5
175°	1212.8	1211.9	1211.1	1210.2	1209.4	1208.9	1208.9	1208.9	1208.9	1208.9	1210.2
177.5°	1216.4	1215.7	1215.0	1214.3	1213.6	1213.3	1213.3	1213.3	1213.3	1213.3	1214.3
180°	1215.6	1215.6	1215.6	1215.6	1215.6	1215.6	1215.6	1215.6	1215.6	1215.6	1215.6



TEST NUMBER: P332107-830

CATALOG NUMBER: S123DIW-S340D1030U830-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	510.8	510.8	510.8	510.8	510.8	510.8	510.8	510.8
2.5°	508.8	509.6	510.4	510.8	510.7	510.6	510.5	510.4
5°	506.1	507.1	508.1	508.5	508.3	508.1	507.8	507.7
7.5°	500.8	501.6	502.5	502.8	502.8	502.7	502.6	502.4
10°	495.9	496.7	497.6	497.9	497.8	497.6	497.4	497.2
12.5°	490.4	491.1	491.7	492.0	491.9	491.7	491.6	491.5
15°	480.7	481.5	482.3	482.4	481.7	481.2	480.6	480.0
17.5°	468.3	468.9	469.5	469.7	469.4	469.2	469.0	468.8
20°	459.3	459.7	460.1	460.1	459.8	459.5	459.2	458.9
22.5°	449.6	450.0	450.3	450.3	449.9	449.5	449.1	448.7
25°	433.7	433.8	433.9	433.8	433.5	433.2	432.9	432.6
27.5°	416.7	416.8	416.8	416.7	416.3	415.9	415.6	415.2
30°	404.9	404.9	404.9	404.5	403.9	403.2	402.6	401.8
32.5°	392.6	392.0	391.5	391.1	390.7	390.3	389.9	389.6
35°	372.6	372.0	371.4	370.9	370.4	369.9	369.4	368.9
37.5°	351.9	351.2	350.4	350.0	349.7	349.3	349.0	348.7
40°	338.4	337.6	336.8	336.2	335.8	335.5	335.1	334.7
42.5°	324.3	323.5	322.7	322.2	321.8	321.4	321.0	320.6
45°	303.3	302.2	301.0	300.2	299.6	299.2	298.7	298.2
47.5°	281.3	280.1	278.9	278.1	277.7	277.3	276.8	276.4
50°	266.6	265.5	264.5	263.6	263.1	262.5	261.9	261.3
52.5°	251.8	250.9	250.0	249.2	248.6	248.1	247.5	246.9
55°	229.3	228.2	227.2	226.4	225.9	225.4	224.9	224.4
57.5°	207.2	206.1	205.2	204.4	203.9	203.3	202.7	202.2
60°	191.5	190.6	189.7	189.1	188.5	188.0	187.6	187.1
62.5°	176.3	175.5	174.7	174.0	173.7	173.3	173.1	172.7
65°	153.9	153.2	152.3	151.8	151.6	151.2	150.9	150.6
67.5°	131.6	130.9	130.3	129.7	129.3	128.8	128.5	128.1
70°	117.3	116.5	115.8	115.3	114.8	114.3	113.8	113.3
72.5°	102.6	102.0	101.4	100.9	100.8	100.5	100.2	99.9
75°	81.6	81.1	80.6	80.2	79.9	79.6	79.4	79.1
77.5°	61.9	61.6	61.3	61.2	61.2	61.2	61.2	61.2
80°	49.4	49.3	49.2	49.2	49.2	49.2	49.2	49.2
82.5°	38.1	37.9	37.7	37.5	37.5	37.4	37.3	37.2
85°	21.6	21.4	21.2	21.1	21.1	21.1	21.1	21.1
87.5°	12.5	12.6	12.7	12.7	12.8	12.9	13.0	13.1
90°	24.6	25.4	26.3	27.0	27.3	27.8	28.2	28.7
92.5°	38.0	38.7	39.4	39.6	39.3	39.1	38.8	38.5
95°	72.4	73.2	74.1	74.5	74.5	74.5	74.5	74.5
97.5°	112.5	113.5	114.5	114.9	114.8	114.8	114.7	114.6
100°	141.7	142.3	142.9	143.5	143.8	144.3	144.7	145.2
102.5°	175.2	175.9	176.5	176.8	176.7	176.6	176.5	176.4
105°	225.4	225.4	225.4	225.6	226.0	226.4	226.9	227.2
107.5°	279.7	280.3	281.0	281.2	281.0	280.7	280.4	280.1
110°	315.8	316.7	317.5	317.7	317.4	316.9	316.5	316.0





TEST NUMBER: P332107-830

CATALOG NUMBER: S123DIW-S340D1030U830-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	352.1	353.1	354.1	354.6	354.5	354.4	354.4	354.3
115°	407.2	407.5	407.6	407.6	407.5	407.2	407.0	406.8
117.5°	462.9	462.8	462.8	462.4	461.8	461.3	460.6	460.1
120°	499.9	499.7	499.5	499.2	498.8	498.3	497.9	497.5
122.5°	537.4	536.9	536.4	535.7	535.2	534.6	534.0	533.4
125°	593.2	592.4	591.5	590.7	589.8	589.0	588.1	587.3
127.5°	648.3	647.1	645.9	644.8	643.9	642.9	641.9	640.9
130°	684.9	684.0	683.2	682.0	680.5	679.0	677.6	676.1
132.5°	720.5	719.4	718.4	717.4	716.1	715.0	713.9	712.8
135°	773.6	772.8	771.9	771.4	770.9	770.5	770.1	769.7
137.5°	825.8	824.8	824.0	823.1	822.3	821.5	820.7	819.9
140°	860.0	859.7	859.5	858.7	857.1	855.7	854.2	852.7
142.5°	892.0	891.8	891.6	890.9	889.8	888.6	887.5	886.4
145°	939.2	939.0	938.8	938.2	937.4	936.5	935.7	934.8
147.5°	983.7	983.7	983.7	983.1	981.8	980.5	979.3	978.0
150°	1011.3	1011.3	1011.3	1010.6	1009.4	1008.0	1006.8	1005.5
152.5°	1036.3	1036.7	1037.1	1036.7	1035.6	1034.4	1033.3	1032.3
155°	1073.1	1073.9	1074.8	1074.5	1073.0	1071.5	1070.1	1068.6
157.5°	1104.7	1105.6	1106.5	1106.4	1105.1	1104.0	1102.8	1101.5
160°	1124.2	1125.2	1126.2	1126.3	1125.5	1124.6	1123.8	1122.9
162.5°	1142.5	1143.5	1144.6	1144.4	1143.1	1141.7	1140.4	1139.0
165°	1165.6	1166.9	1168.2	1168.1	1166.6	1165.1	1163.6	1162.2
167.5°	1184.4	1185.7	1187.0	1187.0	1185.7	1184.4	1183.1	1181.8
170°	1194.7	1196.2	1197.7	1197.7	1196.2	1194.7	1193.2	1191.8
172.5°	1202.8	1204.1	1205.4	1205.3	1203.8	1202.3	1200.8	1199.4
175°	1211.4	1212.8	1214.0	1213.9	1212.4	1210.9	1209.5	1208.0
177.5°	1215.3	1216.4	1217.4	1217.3	1216.1	1214.9	1213.7	1212.6
180°	1215.6	1215.6	1215.6	1215.6	1215.6	1215.6	1215.6	1215.6

(END OF REPORT)