

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331795-840

Luminaire Tested: **S122RDIW-S485D970U840-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331795-840
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122RDIW-S485D970U840-4F0-1E-UDD-F
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 485 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 970 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5625.4 lumens
Efficiency: N/A
Efficacy: 124.5 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 45.2
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331795-840

CATALOG NUMBER: S122RDIW-S485D970U840-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P331795-840

CATALOG NUMBER: S122RDIW-S485D970U840-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	103	103	103	103	92	92	92	92	73	73	73	55	55	55	38	38	38	38	38	38	31
1	94	90	86	83	84	81	78	75	64	62	60	48	47	46	34	33	33	33	33	33	26
2	86	79	73	68	77	71	66	62	56	53	50	43	41	39	30	29	28	28	28	28	22
3	78	69	62	57	70	63	57	52	50	46	42	38	35	33	27	26	24	24	24	24	19
4	72	61	54	48	64	55	49	44	44	40	36	34	31	29	24	23	21	21	21	21	17
5	66	55	47	41	59	50	43	38	40	35	31	31	27	25	22	20	19	19	19	19	15
6	61	49	41	36	54	44	38	33	36	31	27	28	24	22	20	18	16	16	16	16	13
7	56	44	37	31	50	40	34	29	32	28	24	25	22	19	19	16	15	15	15	15	12
8	52	40	33	28	47	36	30	26	30	25	21	23	20	17	17	15	13	13	13	13	11
9	48	37	29	25	43	33	27	23	27	22	19	21	18	16	16	14	12	12	12	12	10
10	45	33	27	22	40	31	24	20	25	20	17	20	16	14	15	12	11	11	11	11	9

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	13454	13454	13454
5°	13506	13287	13361
10°	13404	13070	12959
15°	13249	12682	12318
20°	13036	12129	11519
25°	12818	11501	10750
30°	12515	10856	9758
35°	12220	10153	8889
40°	11921	9428	7885
45°	11574	8611	6976
50°	11215	7784	6081
55°	10849	6899	5222
60°	10424	5968	4334
65°	9941	5012	3947
70°	9361	4131	3635
75°	8659	3762	3387
80°	7643	3366	3087
85°	6002	2649	2649



TEST NUMBER: P331795-840

CATALOG NUMBER: S122RDIW-S485D970U840-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	78.0	1.4
10°-20°	214.2	3.8
20°-30°	300.8	5.3
30°-40°	328.0	5.8
40°-50°	301.6	5.4
50°-60°	236.8	4.2
60°-70°	154.4	2.7
70°-80°	79.6	1.4
80°-90°	23.9	0.4
90°-100°	44.5	0.8
100°-110°	163.1	2.9
110°-120°	436.1	7.8
120°-130°	719.8	12.8
130°-140°	765.5	13.6
140°-150°	711.5	12.6
150°-160°	572.1	10.2
160°-170°	368.6	6.6
170°-180°	126.9	2.3
0°-30°	593.0	10.5
0°-40°	921.0	16.4
0°-60°	1459.4	25.9
0°-90°	1717.4	30.5
90°-120°	643.7	11.4
90°-150°	2840.5	50.5
90°-180°	3908.0	69.5
0°-180°	5625.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	833	833	833	833	833	
5°	833	829	820	826	824	79
15°	793	783	759	745	737	223
25°	720	694	646	616	603	331
35°	620	580	515	469	451	388
45°	507	455	377	326	306	391
55°	385	325	245	202	186	344
65°	260	199	131	107	103	258
75°	139	87	60	55	54	147
85°	32	17	14	14	14	38
90°	1	11	19	24	26	4
95°	63	33	38	42	42	77
105°	293	306	59	69	73	313
115°	555	572	595	170	79	546
125°	784	797	815	822	825	699
135°	971	986	995	1004	1003	750
145°	1126	1126	1142	1148	1144	704
155°	1240	1232	1243	1248	1241	571
165°	1307	1301	1304	1310	1304	369
175°	1336	1330	1332	1338	1329	127
180°	1334	1334	1334	1334	1334	



TEST NUMBER: P331795-840

CATALOG NUMBER: S122RDIW-S485D970U840-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	833.3	833.3	833.3	833.3	833.3	833.3	833.3	833.3	833.3	833.3	833.3
2.5°	836.4	835.8	835.1	834.4	833.7	832.6	831.2	829.7	828.2	826.8	828.1
5°	833.3	832.5	831.7	830.9	830.0	828.5	826.4	824.2	822.0	819.8	821.3
7.5°	824.8	823.7	822.7	821.6	820.6	818.8	816.3	813.7	811.2	808.7	809.1
10°	817.6	816.4	815.2	814.1	812.8	810.6	807.3	803.9	800.5	797.2	796.7
12.5°	808.5	807.1	805.6	804.2	802.7	799.9	795.6	791.3	787.0	782.7	781.8
15°	792.6	790.8	789.0	787.1	785.3	781.5	775.8	770.1	764.5	758.7	755.6
17.5°	773.3	770.4	767.6	764.8	761.9	756.9	749.6	742.3	735.0	727.6	723.9
20°	758.7	755.4	752.0	748.7	745.3	739.4	731.0	722.7	714.3	705.9	701.8
22.5°	743.1	739.3	735.5	731.7	728.0	721.4	712.0	702.5	693.1	683.6	678.2
25°	719.5	714.2	708.8	703.4	698.0	689.8	678.7	667.7	656.6	645.6	638.7
27.5°	691.2	685.3	679.4	673.7	667.8	658.6	646.2	633.7	621.3	608.7	600.8
30°	671.3	664.9	658.5	652.2	645.8	635.9	622.5	609.0	595.6	582.3	573.7
32.5°	652.0	644.5	637.0	629.7	622.2	611.6	597.9	584.2	570.6	556.9	547.1
35°	620.0	611.4	602.9	594.3	585.7	574.1	559.4	544.6	529.9	515.1	504.5
37.5°	587.9	578.6	569.2	559.8	550.5	537.9	522.2	506.4	490.7	475.0	463.3
40°	565.6	555.6	545.5	535.5	525.4	512.3	496.0	479.8	463.5	447.3	435.4
42.5°	542.7	532.1	521.5	511.0	500.4	486.7	469.9	453.0	436.3	419.5	407.2
45°	506.9	495.6	484.3	473.1	461.9	447.5	429.9	412.3	394.7	377.1	365.2
47.5°	471.8	459.9	448.1	436.2	424.2	409.2	391.0	372.8	354.7	336.5	324.7
50°	446.5	434.5	422.7	410.8	398.9	383.7	365.3	346.9	328.4	309.9	298.4
52.5°	421.7	409.3	396.9	384.5	372.0	356.8	338.7	320.7	302.7	284.7	273.5
55°	385.4	372.3	359.2	346.2	333.2	317.5	299.4	281.3	263.2	245.1	235.1
57.5°	348.1	334.8	321.3	307.9	294.5	279.1	261.8	244.3	226.9	209.5	200.3
60°	322.8	309.4	296.0	282.6	269.1	253.9	236.6	219.3	202.1	184.8	176.2
62.5°	298.0	284.7	271.2	257.8	244.4	229.5	213.1	196.6	180.2	163.7	155.5
65°	260.2	246.6	233.1	219.4	205.9	191.6	176.5	161.4	146.3	131.2	125.5
67.5°	223.7	210.3	196.7	183.3	169.8	156.2	142.7	129.2	115.5	102.0	99.4
70°	198.3	185.3	172.2	159.2	146.0	133.7	122.2	110.6	99.1	87.5	85.8
72.5°	174.2	161.7	149.2	136.6	124.1	113.2	103.9	94.6	85.3	76.0	74.6
75°	138.8	127.0	115.3	103.6	91.8	83.1	77.5	71.7	66.0	60.3	59.2
77.5°	103.9	93.6	83.3	73.0	62.8	56.2	53.5	50.8	48.0	45.2	44.5
80°	82.2	73.6	65.1	56.6	48.0	42.9	41.2	39.6	37.9	36.2	35.5
82.5°	62.3	55.6	49.0	42.3	35.6	31.7	30.6	29.4	28.3	27.2	26.8
85°	32.4	28.9	25.3	21.9	18.4	16.4	15.9	15.3	14.8	14.3	14.3
87.5°	9.9	9.3	8.7	8.1	7.5	7.3	7.7	8.0	8.4	8.7	8.8
90°	1.0	3.3	5.7	8.1	10.4	12.4	14.1	15.9	17.6	19.3	20.4
92.5°	19.5	19.3	19.1	18.9	18.7	19.0	19.8	20.7	21.5	22.4	22.9
95°	62.7	55.6	48.6	41.5	34.4	31.6	33.1	34.6	36.2	37.7	38.7
97.5°	124.5	104.5	84.6	64.6	44.7	36.5	40.0	43.4	46.9	50.4	51.2
100°	170.8	141.4	112.0	82.7	53.3	40.4	44.0	47.7	51.4	55.0	56.8
102.5°	221.8	215.5	209.3	203.1	196.8	178.5	148.0	117.5	87.1	56.6	58.8
105°	293.4	299.8	306.2	312.7	319.1	293.1	234.5	175.9	117.4	58.9	61.2
107.5°	375.0	380.2	385.4	390.5	395.8	363.2	293.1	222.8	152.6	82.4	80.0
110°	427.5	432.0	436.5	441.0	445.5	416.8	354.8	292.9	230.9	168.8	147.4



TEST NUMBER: P331795-840

CATALOG NUMBER: S122RDIW-S485D970U840-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	476.9	480.9	484.8	488.9	492.8	487.2	471.9	456.6	441.2	426.0	347.7
115°	554.8	558.5	562.2	565.8	569.5	573.9	579.3	584.6	590.1	595.4	496.0
117.5°	624.5	628.6	632.7	636.7	640.9	644.7	648.4	652.1	655.8	659.4	635.4
120°	675.5	678.7	681.9	685.1	688.3	691.9	695.7	699.6	703.5	707.3	709.9
122.5°	718.7	722.1	725.5	728.8	732.3	736.1	740.2	744.5	748.6	752.9	754.4
125°	784.5	787.3	790.1	792.8	795.7	799.1	803.1	807.3	811.3	815.4	816.9
127.5°	844.1	847.3	850.3	853.4	856.5	859.6	862.6	865.7	868.7	871.7	873.9
130°	882.0	885.4	888.9	892.2	895.6	898.6	900.9	903.3	905.6	908.1	910.4
132.5°	920.6	923.5	926.5	929.3	932.2	934.8	937.3	939.6	941.9	944.3	946.3
135°	970.8	974.2	977.7	981.1	984.5	987.1	989.1	991.0	992.9	994.9	997.0
137.5°	1021.5	1023.9	1026.3	1028.7	1031.1	1033.4	1035.6	1037.7	1040.0	1042.2	1044.3
140°	1054.7	1056.4	1058.1	1059.9	1061.6	1063.6	1065.9	1068.3	1070.7	1073.1	1075.0
142.5°	1082.5	1084.0	1085.6	1087.1	1088.6	1090.8	1093.5	1096.2	1098.9	1101.6	1103.4
145°	1126.1	1125.9	1125.7	1125.5	1125.3	1127.0	1130.6	1134.3	1137.9	1141.6	1143.1
147.5°	1164.2	1163.3	1162.5	1161.6	1160.8	1162.3	1165.9	1169.4	1173.1	1176.7	1177.8
150°	1188.8	1187.3	1185.8	1184.4	1182.9	1183.8	1187.2	1190.6	1194.1	1197.5	1198.8
152.5°	1209.7	1208.0	1206.3	1204.7	1203.0	1203.8	1207.0	1210.3	1213.6	1216.8	1218.1
155°	1240.0	1238.0	1236.1	1234.2	1232.2	1232.5	1235.2	1237.7	1240.3	1242.8	1244.2
157.5°	1263.7	1262.1	1260.4	1258.8	1257.2	1257.3	1259.1	1260.9	1262.6	1264.5	1266.0
160°	1277.6	1276.4	1275.1	1273.7	1272.4	1272.4	1273.7	1275.1	1276.4	1277.6	1278.9
162.5°	1290.0	1288.7	1287.4	1286.1	1284.9	1284.8	1285.9	1287.0	1288.1	1289.2	1290.6
165°	1306.6	1305.3	1303.9	1302.7	1301.4	1301.1	1301.7	1302.3	1303.0	1303.6	1305.1
167.5°	1318.9	1317.6	1316.4	1315.0	1313.7	1313.4	1314.0	1314.6	1315.2	1315.9	1317.3
170°	1325.9	1324.5	1323.3	1322.0	1320.7	1320.3	1320.7	1321.1	1321.6	1322.0	1323.5
172.5°	1330.5	1329.2	1327.9	1326.7	1325.3	1324.9	1325.3	1325.8	1326.2	1326.7	1328.2
175°	1336.5	1334.9	1333.4	1332.0	1330.5	1329.9	1330.4	1330.8	1331.2	1331.6	1333.1
177.5°	1337.5	1336.3	1335.0	1333.8	1332.6	1332.1	1332.3	1332.4	1332.6	1332.8	1334.0
180°	1333.5	1333.5	1333.5	1333.5	1333.5	1333.5	1333.5	1333.5	1333.5	1333.5	1333.5



TEST NUMBER: P331795-840

CATALOG NUMBER: S122RDIW-S485D970U840-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	833.3	833.3	833.3	833.3	833.3	833.3	833.3	833.3
2.5°	829.4	830.8	832.1	832.6	832.4	832.1	831.8	831.6
5°	822.8	824.4	825.9	826.4	825.9	825.4	824.9	824.4
7.5°	809.5	809.9	810.4	810.2	809.3	808.4	807.6	806.7
10°	796.2	795.7	795.2	794.5	793.5	792.4	791.4	790.4
12.5°	780.9	780.0	779.1	777.8	776.1	774.5	772.7	771.1
15°	752.3	749.2	746.0	743.6	741.8	740.2	738.5	736.9
17.5°	720.0	716.3	712.5	709.1	706.3	703.4	700.5	697.6
20°	697.5	693.4	689.1	685.2	681.6	677.8	674.2	670.4
22.5°	672.8	667.4	662.1	657.9	655.2	652.5	649.7	646.9
25°	631.9	625.0	618.1	613.4	610.9	608.3	605.9	603.4
27.5°	592.8	584.7	576.7	570.8	566.7	562.8	558.8	554.8
30°	565.1	556.6	548.1	541.5	536.9	532.5	528.0	523.4
32.5°	537.3	527.7	517.9	510.9	506.6	502.4	498.1	493.8
35°	494.0	483.4	472.9	465.7	462.1	458.4	454.7	451.0
37.5°	451.7	440.1	428.5	420.5	416.4	412.1	407.9	403.6
40°	423.4	411.5	399.6	391.5	387.2	382.8	378.4	374.1
42.5°	394.9	382.5	370.3	362.0	357.8	353.6	349.3	345.1
45°	353.3	341.4	329.5	321.5	317.5	313.5	309.4	305.5
47.5°	312.9	301.0	289.2	281.4	277.8	274.2	270.4	266.8
50°	286.8	275.3	263.7	256.2	252.7	249.1	245.6	242.1
52.5°	262.3	251.2	239.9	232.8	229.5	226.3	223.0	219.7
55°	225.0	214.9	204.9	198.2	195.1	191.9	188.7	185.5
57.5°	191.1	181.9	172.7	166.7	164.0	161.4	158.6	155.9
60°	167.6	159.2	150.6	145.0	142.3	139.6	136.9	134.2
62.5°	147.3	139.3	131.1	126.2	124.6	123.0	121.4	119.8
65°	119.9	114.1	108.5	105.3	104.8	104.3	103.8	103.3
67.5°	96.7	94.1	91.5	90.0	89.4	88.9	88.4	87.8
70°	84.1	82.5	80.8	79.6	79.0	78.3	77.6	77.0
72.5°	73.2	71.8	70.4	69.5	69.1	68.7	68.3	67.9
75°	58.0	56.9	55.6	54.9	54.8	54.6	54.4	54.3
77.5°	43.9	43.2	42.6	42.1	41.8	41.6	41.3	41.0
80°	34.8	34.2	33.5	33.2	33.2	33.2	33.2	33.2
82.5°	26.4	26.0	25.5	25.3	25.3	25.3	25.3	25.3
85°	14.3	14.3	14.3	14.3	14.3	14.3	14.3	14.3
87.5°	8.9	8.9	9.0	9.1	9.2	9.3	9.4	9.4
90°	21.4	22.5	23.6	24.3	24.7	25.1	25.7	26.1
92.5°	23.5	24.0	24.6	25.0	25.2	25.5	25.8	26.1
95°	39.8	40.9	41.9	42.3	42.1	41.9	41.7	41.5
97.5°	52.1	52.9	53.8	54.3	54.6	54.8	55.1	55.3
100°	58.5	60.2	61.9	62.9	63.3	63.8	64.2	64.6
102.5°	61.0	63.2	65.4	66.9	67.5	68.1	68.7	69.3
105°	63.6	65.9	68.3	69.9	70.8	71.6	72.5	73.3
107.5°	77.6	75.2	72.8	72.0	72.9	73.7	74.6	75.4
110°	125.9	104.5	83.1	72.8	73.6	74.5	75.3	76.2



TEST NUMBER: P331795-840

CATALOG NUMBER: S122RDIW-S485D970U840-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	269.4	191.3	113.0	74.2	74.9	75.6	76.3	77.1
115°	396.8	297.5	198.2	140.9	125.4	110.0	94.5	79.2
117.5°	611.4	587.4	563.4	526.0	475.2	424.5	373.9	323.1
120°	712.5	715.0	717.6	704.4	675.5	646.5	617.5	588.7
122.5°	756.0	757.5	759.0	757.0	751.3	745.8	740.1	734.6
125°	818.4	819.9	821.4	822.4	823.1	823.7	824.4	825.1
127.5°	876.2	878.3	880.5	881.6	881.8	881.9	882.0	882.1
130°	912.7	915.1	917.5	918.6	918.3	918.1	917.9	917.7
132.5°	948.4	950.4	952.4	953.3	953.0	952.8	952.6	952.4
135°	999.2	1001.3	1003.4	1004.3	1003.9	1003.4	1003.0	1002.6
137.5°	1046.3	1048.4	1050.6	1051.3	1050.6	1049.8	1049.0	1048.3
140°	1076.9	1078.8	1080.8	1081.2	1080.2	1079.0	1077.9	1076.9
142.5°	1105.1	1106.9	1108.6	1108.9	1107.9	1106.8	1105.8	1104.7
145°	1144.6	1146.1	1147.5	1147.8	1146.7	1145.6	1144.6	1143.5
147.5°	1178.9	1180.0	1181.1	1181.2	1180.3	1179.4	1178.5	1177.6
150°	1200.1	1201.3	1202.6	1202.7	1201.7	1200.6	1199.5	1198.5
152.5°	1219.4	1220.6	1221.9	1221.9	1220.5	1219.1	1217.7	1216.3
155°	1245.5	1246.7	1248.0	1247.8	1246.1	1244.4	1242.6	1240.9
157.5°	1267.4	1268.9	1270.3	1270.2	1268.5	1266.9	1265.2	1263.5
160°	1280.2	1281.4	1282.7	1282.6	1281.1	1279.6	1278.2	1276.7
162.5°	1292.1	1293.5	1295.1	1294.8	1292.9	1291.1	1289.3	1287.5
165°	1306.7	1308.2	1309.7	1309.7	1308.2	1306.7	1305.1	1303.6
167.5°	1318.8	1320.3	1321.8	1321.6	1319.7	1317.8	1315.9	1313.9
170°	1325.0	1326.5	1328.0	1327.8	1325.9	1323.9	1322.0	1320.1
172.5°	1329.6	1331.1	1332.6	1332.4	1330.5	1328.6	1326.7	1324.7
175°	1334.6	1336.2	1337.7	1337.4	1335.1	1333.0	1330.9	1328.8
177.5°	1335.2	1336.4	1337.6	1337.5	1335.8	1334.3	1332.8	1331.3
180°	1333.5	1333.5	1333.5	1333.5	1333.5	1333.5	1333.5	1333.5

(END OF REPORT)