

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332112-830

Luminaire Tested: **S123DIW-S340D1320U830-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332112-830
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-5,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123DIW-S340D1320U830-4F0-1E-UDD-F
Description: DEFINE 3 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 340 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 1320 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6308.3 lumens
Efficiency: N/A
Efficacy: 135.4 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 46.6
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332112-830

CATALOG NUMBER: S123DIW-S340D1320U830-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P332112-830

CATALOG NUMBER: S123DIW-S340D1320U830-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	100	100	100	100	89	89	89	89	67	67	67	48	48	48	30	30	30	21
1	91	87	83	80	81	77	74	71	59	57	55	42	41	39	26	25	25	18
2	83	76	70	65	73	67	63	58	51	48	45	37	35	33	23	22	21	15
3	76	67	60	54	67	59	53	49	45	41	38	32	30	28	20	19	18	13
4	69	59	51	46	61	52	46	41	40	36	32	29	26	24	18	17	15	11
5	63	52	45	39	56	47	40	35	36	31	28	26	23	20	16	15	13	9
6	58	47	39	33	51	42	35	30	32	27	24	23	20	18	15	13	12	8
7	54	42	34	29	47	37	31	26	29	24	21	21	18	16	13	12	10	7
8	50	38	31	25	44	34	27	23	26	22	18	19	16	14	12	10	9	6
9	46	34	27	22	41	31	25	20	24	19	16	17	14	12	11	9	8	6
10	43	31	25	20	38	28	22	18	22	18	15	16	13	11	10	9	7	5

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	5498	5498	5498
5°	5524	5448	5486
10°	5487	5400	5434
15°	5422	5340	5349
20°	5347	5252	5257
25°	5247	5149	5138
30°	5137	5033	4994
35°	5021	4911	4847
40°	4900	4776	4703
45°	4766	4654	4539
50°	4632	4501	4376
55°	4459	4344	4211
60°	4284	4159	4028
65°	4126	3958	3836
70°	3899	3733	3566
75°	3564	3435	3290
80°	3211	3081	3050
85°	2816	2717	2606



TEST NUMBER: P332112-830

CATALOG NUMBER: S123DIW-S340D1320U830-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	48.1	0.8
10°-20°	135.9	2.2
20°-30°	200.7	3.2
30°-40°	234.4	3.7
40°-50°	235.7	3.7
50°-60°	207.0	3.3
60°-70°	154.2	2.4
70°-80°	87.9	1.4
80°-90°	29.8	0.5
90°-100°	59.3	0.9
100°-110°	282.7	4.5
110°-120°	679.0	10.8
120°-130°	864.6	13.7
130°-140°	923.8	14.6
140°-150°	863.8	13.7
150°-160°	696.8	11.0
160°-170°	449.7	7.1
170°-180°	155.0	2.5
0°-30°	384.6	6.1
0°-40°	619.1	9.8
0°-60°	1061.7	16.8
0°-90°	1333.6	21.1
90°-120°	1020.9	16.2
90°-150°	3673.1	58.2
90°-180°	4975.0	78.9
0°-180°	6308.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	511	511	511	511	511	
5°	511	509	504	508	508	48
15°	487	485	479	482	480	137
25°	442	439	434	434	433	203
35°	382	379	374	371	369	239
45°	313	311	306	301	298	242
55°	238	237	232	227	224	213
65°	162	160	155	152	151	160
75°	86	84	83	80	79	92
85°	23	22	22	21	21	25
90°	1	14	29	34	36	5
95°	74	28	38	46	46	91
105°	361	368	265	63	53	383
115°	678	685	696	707	713	669
125°	955	964	970	972	974	853
135°	1189	1196	1201	1204	1201	915
145°	1372	1380	1383	1385	1385	858
155°	1511	1509	1510	1515	1509	696
165°	1594	1590	1589	1598	1590	450
175°	1631	1626	1626	1634	1625	155
180°	1631	1631	1631	1631	1631	



TEST NUMBER: P332112-830

CATALOG NUMBER: S123DIW-S340D1320U830-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	510.8	510.8	510.8	510.8	510.8	510.8	510.8	510.8	510.8	510.8	510.8
2.5°	512.6	512.2	511.9	511.6	511.2	510.7	509.8	509.0	508.1	507.3	508.0
5°	511.2	510.7	510.2	509.7	509.3	508.5	507.4	506.3	505.2	504.2	505.1
7.5°	506.2	505.7	505.2	504.7	504.3	503.4	502.4	501.2	500.1	499.0	499.8
10°	502.0	501.5	501.0	500.5	500.0	499.2	497.9	496.6	495.3	494.1	494.9
12.5°	496.3	496.0	495.5	495.1	494.7	493.9	492.8	491.5	490.3	489.2	489.8
15°	486.6	486.3	485.8	485.4	485.0	484.2	483.0	481.6	480.4	479.2	479.9
17.5°	475.2	474.8	474.3	473.7	473.3	472.4	471.1	469.9	468.5	467.3	467.8
20°	466.8	466.3	465.7	465.1	464.5	463.5	462.3	461.0	459.8	458.5	458.9
22.5°	457.3	456.8	456.2	455.6	455.1	454.1	452.8	451.6	450.3	449.0	449.3
25°	441.8	441.2	440.6	440.1	439.5	438.6	437.2	436.0	434.7	433.5	433.6
27.5°	425.2	424.6	424.0	423.5	422.9	422.0	420.7	419.2	417.9	416.5	416.6
30°	413.3	412.7	412.3	411.8	411.3	410.4	409.1	407.6	406.3	404.9	404.9
32.5°	401.3	400.7	400.0	399.4	398.8	397.8	396.8	395.8	394.7	393.7	393.1
35°	382.1	381.5	380.9	380.3	379.8	378.8	377.6	376.3	375.0	373.7	373.2
37.5°	362.4	361.7	360.9	360.1	359.5	358.4	357.1	355.8	354.6	353.3	352.6
40°	348.7	348.1	347.5	346.9	346.4	345.3	344.0	342.6	341.3	339.9	339.1
42.5°	335.0	334.3	333.7	333.0	332.3	331.3	330.0	328.6	327.3	325.8	325.1
45°	313.1	312.7	312.4	312.0	311.6	310.8	309.4	308.2	306.9	305.7	304.5
47.5°	291.4	290.9	290.3	289.7	289.2	288.3	287.1	285.9	284.7	283.5	282.4
50°	276.6	276.2	275.7	275.2	274.8	273.8	272.6	271.4	270.0	268.8	267.7
52.5°	261.2	260.9	260.5	260.2	259.9	259.0	257.7	256.4	255.1	253.6	252.8
55°	237.6	237.5	237.4	237.3	237.2	236.5	235.3	233.9	232.7	231.5	230.4
57.5°	215.1	214.8	214.4	214.1	213.8	213.1	212.1	211.0	210.1	209.1	208.1
60°	199.0	198.9	198.8	198.7	198.6	197.9	196.7	195.6	194.4	193.2	192.4
62.5°	184.5	184.3	184.1	183.8	183.5	182.9	181.6	180.5	179.3	178.1	177.3
65°	162.0	161.6	161.1	160.6	160.1	159.4	158.4	157.4	156.5	155.4	154.7
67.5°	138.3	137.8	137.4	137.0	136.6	135.9	135.3	134.5	133.7	133.0	132.3
70°	123.9	123.3	122.7	122.1	121.5	120.9	120.4	119.7	119.1	118.6	117.9
72.5°	108.8	108.3	107.9	107.4	107.0	106.5	105.8	105.2	104.5	103.9	103.2
75°	85.7	85.2	84.8	84.5	84.1	83.7	83.4	83.1	82.8	82.6	82.1
77.5°	65.1	64.9	64.8	64.6	64.3	64.0	63.7	63.3	63.0	62.6	62.3
80°	51.8	51.6	51.3	51.0	50.6	50.4	50.2	50.0	49.9	49.7	49.5
82.5°	38.8	38.7	38.7	38.6	38.5	38.5	38.5	38.5	38.5	38.4	38.2
85°	22.8	22.6	22.4	22.2	22.1	22.0	22.0	22.0	22.0	22.0	21.8
87.5°	9.3	9.7	10.0	10.3	10.6	11.0	11.7	12.3	12.9	13.6	13.7
90°	1.2	3.9	6.6	9.3	12.0	15.1	18.6	22.1	25.5	29.1	30.2
92.5°	22.5	21.8	21.0	20.3	19.5	20.5	23.1	25.7	28.4	31.0	32.7
95°	73.9	62.9	51.8	40.8	29.8	25.7	28.7	31.7	34.6	37.6	39.5
97.5°	148.5	143.6	138.6	133.7	128.8	116.6	97.2	77.9	58.4	39.0	41.2
100°	204.8	210.2	215.6	220.9	226.4	208.0	166.1	124.0	82.0	40.0	42.1
102.5°	268.8	272.7	276.5	280.4	284.4	263.3	217.4	171.5	125.6	79.7	73.0
105°	361.2	364.1	367.1	370.0	373.0	362.4	338.1	313.9	289.6	265.4	217.7
107.5°	458.6	461.0	463.4	465.7	468.1	471.2	475.0	478.8	482.7	486.4	451.5
110°	523.6	525.8	527.8	530.0	532.2	534.7	537.7	540.6	543.7	546.6	537.7



TEST NUMBER: P332112-830

CATALOG NUMBER: S123DIW-S340D1320U830-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	585.6	587.6	589.5	591.4	593.3	595.8	598.8	601.7	604.7	607.7	607.8
115°	677.5	679.1	680.7	682.3	683.9	686.0	688.3	690.8	693.2	695.7	698.3
117.5°	766.5	768.5	770.4	772.4	774.4	776.0	777.2	778.5	779.8	781.0	783.2
120°	821.7	824.2	826.5	829.0	831.4	833.0	833.8	834.6	835.5	836.2	838.4
122.5°	878.0	880.0	881.9	883.9	885.9	887.4	888.4	889.5	890.5	891.6	893.1
125°	955.0	957.2	959.3	961.5	963.7	965.3	966.3	967.4	968.5	969.6	970.1
127.5°	1029.6	1031.8	1034.0	1036.1	1038.3	1040.0	1041.3	1042.6	1043.9	1045.2	1046.0
130°	1076.2	1078.4	1080.5	1082.7	1084.9	1086.5	1087.5	1088.6	1089.7	1090.7	1091.8
132.5°	1120.8	1122.9	1125.1	1127.3	1129.4	1131.0	1131.8	1132.7	1133.5	1134.3	1135.5
135°	1188.9	1190.5	1192.1	1193.7	1195.4	1196.7	1197.8	1198.9	1200.0	1201.1	1201.8
137.5°	1247.1	1249.2	1251.2	1253.2	1255.3	1256.6	1257.2	1257.8	1258.4	1259.0	1260.3
140°	1285.9	1287.5	1289.1	1290.7	1292.3	1293.5	1294.4	1295.1	1296.0	1296.8	1297.9
142.5°	1321.7	1323.3	1325.0	1326.6	1328.2	1329.5	1330.2	1331.1	1331.8	1332.7	1333.5
145°	1372.0	1373.9	1375.7	1377.6	1379.5	1380.6	1381.2	1381.8	1382.3	1382.8	1383.4
147.5°	1419.2	1420.4	1421.6	1422.9	1424.2	1425.0	1425.6	1426.1	1426.6	1427.2	1427.8
150°	1448.3	1449.1	1449.9	1450.7	1451.5	1452.2	1452.7	1453.2	1453.8	1454.3	1454.9
152.5°	1474.4	1474.8	1475.2	1475.6	1475.9	1476.3	1476.7	1477.0	1477.2	1477.6	1478.6
155°	1511.3	1510.8	1510.2	1509.7	1509.1	1509.0	1509.3	1509.6	1509.9	1510.0	1511.5
157.5°	1539.9	1539.8	1539.8	1539.7	1539.6	1539.5	1539.3	1539.0	1538.7	1538.4	1540.0
160°	1557.4	1557.1	1556.8	1556.5	1556.2	1556.0	1555.8	1555.5	1555.2	1554.9	1556.5
162.5°	1573.9	1573.1	1572.4	1571.7	1571.0	1570.6	1570.3	1570.0	1569.7	1569.4	1571.3
165°	1593.7	1592.9	1592.0	1591.3	1590.4	1590.0	1589.7	1589.4	1589.1	1588.8	1591.0
167.5°	1609.2	1608.2	1607.0	1606.0	1604.9	1604.4	1604.4	1604.4	1604.4	1604.4	1606.6
170°	1618.0	1616.8	1615.8	1614.8	1613.6	1613.1	1613.1	1613.1	1613.1	1613.1	1615.2
172.5°	1623.8	1622.5	1621.2	1619.9	1618.6	1618.1	1618.3	1618.5	1618.7	1618.9	1621.1
175°	1631.3	1629.9	1628.6	1627.2	1625.9	1625.3	1625.6	1625.9	1626.2	1626.5	1628.3
177.5°	1633.2	1632.1	1631.1	1630.0	1628.9	1628.5	1628.7	1628.9	1629.1	1629.4	1631.1
180°	1631.3	1631.3	1631.3	1631.3	1631.3	1631.3	1631.3	1631.3	1631.3	1631.3	1631.3



TEST NUMBER: P332112-830

CATALOG NUMBER: S123DIW-S340D1320U830-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	510.8	510.8	510.8	510.8	510.8	510.8	510.8	510.8
2.5°	508.8	509.6	510.4	510.8	510.7	510.6	510.5	510.4
5°	506.1	507.1	508.1	508.5	508.3	508.1	507.8	507.7
7.5°	500.8	501.6	502.5	502.8	502.8	502.7	502.6	502.4
10°	495.9	496.7	497.6	497.9	497.8	497.6	497.4	497.2
12.5°	490.4	491.1	491.7	492.0	491.9	491.7	491.6	491.5
15°	480.7	481.5	482.3	482.4	481.7	481.2	480.6	480.0
17.5°	468.3	468.9	469.5	469.7	469.4	469.2	469.0	468.8
20°	459.3	459.7	460.1	460.1	459.8	459.5	459.2	458.9
22.5°	449.6	450.0	450.3	450.3	449.9	449.5	449.1	448.7
25°	433.7	433.8	433.9	433.8	433.5	433.2	432.9	432.6
27.5°	416.7	416.8	416.8	416.7	416.3	415.9	415.6	415.2
30°	404.9	404.9	404.9	404.5	403.9	403.2	402.6	401.8
32.5°	392.6	392.0	391.5	391.1	390.7	390.3	389.9	389.6
35°	372.6	372.0	371.4	370.9	370.4	369.9	369.4	368.9
37.5°	351.9	351.2	350.4	350.0	349.7	349.3	349.0	348.7
40°	338.4	337.6	336.8	336.2	335.8	335.5	335.1	334.7
42.5°	324.3	323.5	322.7	322.2	321.8	321.4	321.0	320.6
45°	303.3	302.2	301.0	300.2	299.6	299.2	298.7	298.2
47.5°	281.3	280.1	278.9	278.1	277.7	277.3	276.8	276.4
50°	266.6	265.5	264.5	263.6	263.1	262.5	261.9	261.3
52.5°	251.8	250.9	250.0	249.2	248.6	248.1	247.5	246.9
55°	229.3	228.2	227.2	226.4	225.9	225.4	224.9	224.4
57.5°	207.2	206.1	205.2	204.4	203.9	203.3	202.7	202.2
60°	191.5	190.6	189.7	189.1	188.5	188.0	187.6	187.1
62.5°	176.3	175.5	174.7	174.0	173.7	173.3	173.1	172.7
65°	153.9	153.2	152.3	151.8	151.6	151.2	150.9	150.6
67.5°	131.6	130.9	130.3	129.7	129.3	128.8	128.5	128.1
70°	117.3	116.5	115.8	115.3	114.8	114.3	113.8	113.3
72.5°	102.6	102.0	101.4	100.9	100.8	100.5	100.2	99.9
75°	81.6	81.1	80.6	80.2	79.9	79.6	79.4	79.1
77.5°	61.9	61.6	61.3	61.2	61.2	61.2	61.2	61.2
80°	49.4	49.3	49.2	49.2	49.2	49.2	49.2	49.2
82.5°	38.1	37.9	37.7	37.5	37.5	37.4	37.3	37.2
85°	21.6	21.4	21.2	21.1	21.1	21.1	21.1	21.1
87.5°	13.9	13.9	14.1	14.2	14.3	14.4	14.5	14.6
90°	31.2	32.3	33.4	34.2	34.8	35.3	35.8	36.4
92.5°	34.5	36.2	37.9	38.9	39.3	39.6	39.9	40.2
95°	41.4	43.3	45.1	46.1	46.1	46.1	46.1	46.1
97.5°	43.4	45.5	47.6	48.8	49.1	49.4	49.7	50.0
100°	44.3	46.5	48.6	49.9	50.0	50.3	50.6	50.9
102.5°	66.4	59.7	53.1	50.0	50.4	50.9	51.4	51.8
105°	170.0	122.4	74.7	51.2	51.7	52.2	52.8	53.3
107.5°	416.6	381.6	346.7	311.2	275.3	239.3	203.4	167.5
110°	528.8	519.9	511.0	487.3	448.8	410.3	371.8	333.3



TEST NUMBER: P332112-830

CATALOG NUMBER: S123DIW-S340D1320U830-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	608.0	608.1	608.3	604.4	596.2	588.1	579.9	571.8
115°	701.1	703.7	706.4	708.3	709.4	710.5	711.5	712.7
117.5°	785.3	787.4	789.6	790.8	791.0	791.2	791.5	791.6
120°	840.6	842.7	844.9	845.9	845.9	845.9	845.9	845.9
122.5°	894.6	896.1	897.6	898.4	898.6	898.8	899.1	899.3
125°	970.6	971.2	971.7	972.2	972.8	973.4	973.8	974.4
127.5°	1046.9	1047.7	1048.7	1048.8	1048.3	1047.7	1047.2	1046.6
130°	1092.9	1094.0	1095.0	1095.3	1094.8	1094.3	1093.7	1093.2
132.5°	1136.5	1137.6	1138.7	1138.9	1138.1	1137.4	1136.6	1135.9
135°	1202.7	1203.4	1204.3	1204.3	1203.4	1202.7	1201.8	1201.1
137.5°	1261.6	1262.8	1264.1	1264.5	1263.9	1263.5	1262.9	1262.3
140°	1298.9	1300.0	1301.1	1301.4	1300.8	1300.2	1299.8	1299.2
142.5°	1334.4	1335.2	1336.1	1336.1	1335.4	1334.6	1333.9	1333.1
145°	1383.9	1384.4	1385.0	1385.3	1385.3	1385.3	1385.3	1385.3
147.5°	1428.2	1428.8	1429.4	1429.0	1427.8	1426.5	1425.3	1424.0
150°	1455.4	1455.9	1456.5	1456.3	1455.6	1454.7	1454.0	1453.1
152.5°	1479.5	1480.5	1481.5	1481.4	1480.1	1478.8	1477.6	1476.4
155°	1512.8	1514.1	1515.5	1515.3	1513.7	1512.1	1510.5	1508.9
157.5°	1541.7	1543.3	1544.9	1544.6	1542.6	1540.5	1538.3	1536.3
160°	1558.1	1559.8	1561.4	1561.2	1559.3	1557.5	1555.6	1553.7
162.5°	1573.1	1575.0	1576.8	1576.9	1575.2	1573.6	1571.9	1570.2
165°	1593.2	1595.3	1597.5	1597.6	1595.7	1593.8	1592.0	1590.1
167.5°	1608.7	1610.8	1613.0	1613.0	1610.8	1608.7	1606.6	1604.4
170°	1617.4	1619.6	1621.7	1621.7	1619.6	1617.4	1615.2	1613.1
172.5°	1623.2	1625.4	1627.6	1627.4	1625.0	1622.7	1620.3	1618.0
175°	1630.2	1632.1	1634.0	1633.8	1631.7	1629.6	1627.4	1625.2
177.5°	1632.8	1634.6	1636.3	1636.1	1633.9	1631.7	1629.6	1627.4
180°	1631.3	1631.3	1631.3	1631.3	1631.3	1631.3	1631.3	1631.3

(END OF REPORT)