

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331796-840

Luminaire Tested: **S122RDIW-S485D970U840-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331796-840
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-8,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122RDIW-S485D970U840-4F0-1E-UDD-F1
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 485 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 970 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5108.1 lumens
Efficiency: N/A
Efficacy: 113.0 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 45.2
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331796-840

CATALOG NUMBER: S122RDIW-S485D970U840-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P331796-840

CATALOG NUMBER: S122RDIW-S485D970U840-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	103	103	103	103	93	93	93	93	74	74	74	57	57	57	41	41	41
1	94	90	87	83	85	82	79	76	65	63	61	50	49	48	37	36	35
2	86	79	73	69	78	72	67	63	58	54	51	45	42	40	33	31	30
3	79	70	63	57	71	63	57	53	51	47	43	40	37	35	29	28	26
4	72	62	54	49	65	56	50	45	46	41	37	36	32	30	26	24	23
5	66	55	48	42	60	50	44	39	41	36	32	32	29	26	24	22	20
6	61	50	42	36	55	45	38	34	37	32	28	29	26	23	22	19	18
7	56	45	37	32	51	41	34	29	33	28	25	26	23	20	20	18	16
8	52	41	33	28	47	37	31	26	30	26	22	24	21	18	18	16	14
9	49	37	30	25	44	34	28	23	28	23	20	22	19	16	17	15	13
10	45	34	27	22	41	31	25	21	26	21	18	21	17	15	16	13	12

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	13454	13454	13454
5°	13506	13287	13361
10°	13404	13070	12959
15°	13249	12682	12318
20°	13036	12129	11519
25°	12818	11501	10750
30°	12515	10856	9758
35°	12220	10153	8889
40°	11921	9428	7885
45°	11574	8611	6976
50°	11215	7784	6081
55°	10849	6899	5222
60°	10424	5968	4334
65°	9941	5012	3947
70°	9361	4131	3635
75°	8659	3762	3387
80°	7643	3366	3087
85°	6002	2649	2649



TEST NUMBER: P331796-840

CATALOG NUMBER: S122RDIW-S485D970U840-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	78.0	1.5
10°-20°	214.2	4.2
20°-30°	300.8	5.9
30°-40°	328.0	6.4
40°-50°	301.6	5.9
50°-60°	236.8	4.6
60°-70°	154.4	3.0
70°-80°	79.6	1.6
80°-90°	25.5	0.5
90°-100°	76.8	1.5
100°-110°	238.5	4.7
110°-120°	407.7	8.0
120°-130°	536.2	10.5
130°-140°	601.8	11.8
140°-150°	590.1	11.6
150°-160°	494.9	9.7
160°-170°	328.3	6.4
170°-180°	114.7	2.2
0°-30°	593.0	11.6
0°-40°	921.0	18.0
0°-60°	1459.4	28.6
0°-90°	1718.9	33.7
90°-120°	723.1	14.2
90°-150°	2451.2	48.0
90°-180°	3389.0	66.3
0°-180°	5108.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	833	833	833	833	833	
5°	833	829	820	826	824	79
15°	793	783	759	745	737	223
25°	720	694	646	616	603	331
35°	620	580	515	469	451	388
45°	507	455	377	326	306	391
55°	385	325	245	202	186	344
65°	260	199	131	107	103	258
75°	139	87	60	55	54	147
85°	32	17	14	14	14	38
90°	1	14	36	34	35	4
95°	53	63	65	65	63	61
105°	220	223	225	227	227	232
115°	409	415	413	412	409	405
125°	595	604	602	598	597	532
135°	770	781	784	782	779	595
145°	935	942	948	949	945	584
155°	1069	1072	1075	1080	1077	492
165°	1163	1162	1162	1168	1164	328
175°	1210	1207	1205	1211	1206	115
180°	1212	1212	1212	1212	1212	



TEST NUMBER: P331796-840

CATALOG NUMBER: S122RDIW-S485D970U840-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	833.3	833.3	833.3	833.3	833.3	833.3	833.3	833.3	833.3	833.3	833.3
2.5°	836.4	835.8	835.1	834.4	833.7	832.6	831.2	829.7	828.2	826.8	828.1
5°	833.3	832.5	831.7	830.9	830.0	828.5	826.4	824.2	822.0	819.8	821.3
7.5°	824.8	823.7	822.7	821.6	820.6	818.8	816.3	813.7	811.2	808.7	809.1
10°	817.6	816.4	815.2	814.1	812.8	810.6	807.3	803.9	800.5	797.2	796.7
12.5°	808.5	807.1	805.6	804.2	802.7	799.9	795.6	791.3	787.0	782.7	781.8
15°	792.6	790.8	789.0	787.1	785.3	781.5	775.8	770.1	764.5	758.7	755.6
17.5°	773.3	770.4	767.6	764.8	761.9	756.9	749.6	742.3	735.0	727.6	723.9
20°	758.7	755.4	752.0	748.7	745.3	739.4	731.0	722.7	714.3	705.9	701.8
22.5°	743.1	739.3	735.5	731.7	728.0	721.4	712.0	702.5	693.1	683.6	678.2
25°	719.5	714.2	708.8	703.4	698.0	689.8	678.7	667.7	656.6	645.6	638.7
27.5°	691.2	685.3	679.4	673.7	667.8	658.6	646.2	633.7	621.3	608.7	600.8
30°	671.3	664.9	658.5	652.2	645.8	635.9	622.5	609.0	595.6	582.3	573.7
32.5°	652.0	644.5	637.0	629.7	622.2	611.6	597.9	584.2	570.6	556.9	547.1
35°	620.0	611.4	602.9	594.3	585.7	574.1	559.4	544.6	529.9	515.1	504.5
37.5°	587.9	578.6	569.2	559.8	550.5	537.9	522.2	506.4	490.7	475.0	463.3
40°	565.6	555.6	545.5	535.5	525.4	512.3	496.0	479.8	463.5	447.3	435.4
42.5°	542.7	532.1	521.5	511.0	500.4	486.7	469.9	453.0	436.3	419.5	407.2
45°	506.9	495.6	484.3	473.1	461.9	447.5	429.9	412.3	394.7	377.1	365.2
47.5°	471.8	459.9	448.1	436.2	424.2	409.2	391.0	372.8	354.7	336.5	324.7
50°	446.5	434.5	422.7	410.8	398.9	383.7	365.3	346.9	328.4	309.9	298.4
52.5°	421.7	409.3	396.9	384.5	372.0	356.8	338.7	320.7	302.7	284.7	273.5
55°	385.4	372.3	359.2	346.2	333.2	317.5	299.4	281.3	263.2	245.1	235.1
57.5°	348.1	334.8	321.3	307.9	294.5	279.1	261.8	244.3	226.9	209.5	200.3
60°	322.8	309.4	296.0	282.6	269.1	253.9	236.6	219.3	202.1	184.8	176.2
62.5°	298.0	284.7	271.2	257.8	244.4	229.5	213.1	196.6	180.2	163.7	155.5
65°	260.2	246.6	233.1	219.4	205.9	191.6	176.5	161.4	146.3	131.2	125.5
67.5°	223.7	210.3	196.7	183.3	169.8	156.2	142.7	129.2	115.5	102.0	99.4
70°	198.3	185.3	172.2	159.2	146.0	133.7	122.2	110.6	99.1	87.5	85.8
72.5°	174.2	161.7	149.2	136.6	124.1	113.2	103.9	94.6	85.3	76.0	74.6
75°	138.8	127.0	115.3	103.6	91.8	83.1	77.5	71.7	66.0	60.3	59.2
77.5°	103.9	93.6	83.3	73.0	62.8	56.2	53.5	50.8	48.0	45.2	44.5
80°	82.2	73.6	65.1	56.6	48.0	42.9	41.2	39.6	37.9	36.2	35.5
82.5°	62.3	55.6	49.0	42.3	35.6	31.7	30.6	29.4	28.3	27.2	26.8
85°	32.4	28.9	25.3	21.9	18.4	16.4	15.9	15.3	14.8	14.3	14.3
87.5°	9.9	9.3	8.8	8.3	7.8	8.0	9.0	10.0	11.0	12.0	11.7
90°	1.0	3.7	6.5	9.2	11.9	15.8	20.8	25.8	30.8	35.7	35.3
92.5°	18.2	20.2	22.2	24.2	26.3	27.8	29.0	30.2	31.3	32.5	32.6
95°	53.2	55.4	57.8	60.0	62.3	63.6	64.1	64.5	65.0	65.4	65.4
97.5°	97.1	99.2	101.2	103.2	105.1	106.6	107.4	108.4	109.2	110.1	110.1
100°	129.9	131.7	133.5	135.3	137.1	138.5	139.1	139.8	140.5	141.2	141.2
102.5°	164.3	165.7	167.1	168.6	170.1	171.3	172.1	173.0	173.8	174.7	174.9
105°	219.9	220.6	221.3	222.0	222.7	223.2	223.7	224.1	224.6	225.0	225.5
107.5°	276.0	277.0	277.9	278.9	279.9	280.4	280.4	280.4	280.4	280.4	280.6
110°	311.9	313.4	314.7	316.1	317.4	318.1	318.1	318.1	318.1	318.1	318.1



TEST NUMBER: P331796-840

CATALOG NUMBER: S122RDIW-S485D970U840-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	351.2	352.6	354.0	355.4	356.7	357.3	357.1	356.9	356.8	356.6	356.0
115°	409.1	410.5	411.8	413.2	414.5	415.1	414.5	414.1	413.6	413.2	413.0
117.5°	466.9	468.7	470.5	472.3	474.1	474.3	473.1	471.8	470.6	469.3	468.8
120°	505.3	507.2	509.0	510.8	512.6	512.6	510.8	509.0	507.2	505.3	505.3
122.5°	540.5	542.7	544.8	547.0	549.2	549.7	548.4	547.1	545.8	544.5	544.0
125°	595.3	597.3	599.4	601.5	603.5	604.2	603.5	602.8	602.1	601.5	600.8
127.5°	648.7	651.3	653.9	656.5	659.0	659.9	659.1	658.3	657.5	656.7	655.8
130°	682.3	685.2	688.1	691.2	694.1	695.3	694.9	694.4	694.0	693.5	693.1
132.5°	719.8	722.3	724.7	727.1	729.5	730.7	730.8	730.9	731.0	731.1	730.1
135°	770.2	772.7	775.2	777.7	780.2	781.6	782.1	782.5	783.0	783.5	783.3
137.5°	823.1	825.3	827.3	829.3	831.3	832.7	833.2	833.8	834.5	835.1	834.9
140°	855.1	857.2	859.2	861.2	863.2	864.8	866.1	867.2	868.3	869.4	869.4
142.5°	887.9	889.9	891.9	893.9	896.1	897.5	898.2	899.0	899.8	900.5	900.7
145°	934.8	936.4	938.1	939.7	941.3	942.7	944.1	945.4	946.8	948.2	948.4
147.5°	976.8	978.8	980.7	982.5	984.4	985.8	986.7	987.6	988.6	989.5	990.0
150°	1005.4	1006.8	1008.1	1009.6	1010.9	1012.1	1013.0	1013.9	1014.8	1015.7	1016.3
152.5°	1030.9	1032.2	1033.6	1034.9	1036.3	1037.5	1038.6	1039.7	1040.8	1041.9	1042.7
155°	1068.8	1069.5	1070.3	1071.0	1071.6	1072.3	1073.0	1073.7	1074.3	1075.0	1076.1
157.5°	1101.4	1101.9	1102.3	1102.8	1103.2	1103.7	1104.1	1104.5	1104.9	1105.3	1106.8
160°	1121.1	1121.5	1122.0	1122.4	1122.9	1123.2	1123.5	1123.7	1123.9	1124.1	1125.5
162.5°	1139.0	1139.1	1139.2	1139.3	1139.4	1139.5	1139.8	1140.0	1140.2	1140.4	1142.1
165°	1163.0	1162.8	1162.6	1162.3	1162.1	1162.0	1162.0	1162.0	1162.0	1162.0	1163.6
167.5°	1183.1	1182.3	1181.6	1180.9	1180.3	1179.9	1179.9	1179.8	1179.8	1179.7	1181.3
170°	1193.7	1193.0	1192.3	1191.6	1190.9	1190.5	1190.2	1190.0	1189.8	1189.6	1191.1
172.5°	1201.0	1200.3	1199.6	1199.0	1198.3	1197.8	1197.6	1197.4	1197.2	1196.9	1198.5
175°	1210.0	1209.3	1208.7	1208.0	1207.3	1206.7	1206.3	1205.8	1205.4	1204.9	1206.5
177.5°	1213.8	1213.2	1212.6	1212.0	1211.5	1211.0	1210.7	1210.3	1210.0	1209.6	1210.7
180°	1212.0	1212.0	1212.0	1212.0	1212.0	1212.0	1212.0	1212.0	1212.0	1212.0	1212.0



TEST NUMBER: P331796-840

CATALOG NUMBER: S122RDIW-S485D970U840-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	833.3	833.3	833.3	833.3	833.3	833.3	833.3	833.3
2.5°	829.4	830.8	832.1	832.6	832.4	832.1	831.8	831.6
5°	822.8	824.4	825.9	826.4	825.9	825.4	824.9	824.4
7.5°	809.5	809.9	810.4	810.2	809.3	808.4	807.6	806.7
10°	796.2	795.7	795.2	794.5	793.5	792.4	791.4	790.4
12.5°	780.9	780.0	779.1	777.8	776.1	774.5	772.7	771.1
15°	752.3	749.2	746.0	743.6	741.8	740.2	738.5	736.9
17.5°	720.0	716.3	712.5	709.1	706.3	703.4	700.5	697.6
20°	697.5	693.4	689.1	685.2	681.6	677.8	674.2	670.4
22.5°	672.8	667.4	662.1	657.9	655.2	652.5	649.7	646.9
25°	631.9	625.0	618.1	613.4	610.9	608.3	605.9	603.4
27.5°	592.8	584.7	576.7	570.8	566.7	562.8	558.8	554.8
30°	565.1	556.6	548.1	541.5	536.9	532.5	528.0	523.4
32.5°	537.3	527.7	517.9	510.9	506.6	502.4	498.1	493.8
35°	494.0	483.4	472.9	465.7	462.1	458.4	454.7	451.0
37.5°	451.7	440.1	428.5	420.5	416.4	412.1	407.9	403.6
40°	423.4	411.5	399.6	391.5	387.2	382.8	378.4	374.1
42.5°	394.9	382.5	370.3	362.0	357.8	353.6	349.3	345.1
45°	353.3	341.4	329.5	321.5	317.5	313.5	309.4	305.5
47.5°	312.9	301.0	289.2	281.4	277.8	274.2	270.4	266.8
50°	286.8	275.3	263.7	256.2	252.7	249.1	245.6	242.1
52.5°	262.3	251.2	239.9	232.8	229.5	226.3	223.0	219.7
55°	225.0	214.9	204.9	198.2	195.1	191.9	188.7	185.5
57.5°	191.1	181.9	172.7	166.7	164.0	161.4	158.6	155.9
60°	167.6	159.2	150.6	145.0	142.3	139.6	136.9	134.2
62.5°	147.3	139.3	131.1	126.2	124.6	123.0	121.4	119.8
65°	119.9	114.1	108.5	105.3	104.8	104.3	103.8	103.3
67.5°	96.7	94.1	91.5	90.0	89.4	88.9	88.4	87.8
70°	84.1	82.5	80.8	79.6	79.0	78.3	77.6	77.0
72.5°	73.2	71.8	70.4	69.5	69.1	68.7	68.3	67.9
75°	58.0	56.9	55.6	54.9	54.8	54.6	54.4	54.3
77.5°	43.9	43.2	42.6	42.1	41.8	41.6	41.3	41.0
80°	34.8	34.2	33.5	33.2	33.2	33.2	33.2	33.2
82.5°	26.4	26.0	25.5	25.3	25.3	25.3	25.3	25.3
85°	14.3	14.3	14.3	14.3	14.3	14.3	14.3	14.3
87.5°	11.5	11.3	11.1	11.0	11.0	11.1	11.1	11.2
90°	34.8	34.4	33.9	33.8	34.1	34.3	34.5	34.7
92.5°	32.7	32.8	32.9	32.9	33.0	33.0	33.1	33.1
95°	65.4	65.4	65.4	65.2	64.7	64.3	63.8	63.4
97.5°	110.1	110.1	110.1	110.1	110.0	110.0	109.9	109.9
100°	141.2	141.2	141.2	141.1	140.8	140.6	140.4	140.2
102.5°	175.1	175.2	175.4	175.4	175.2	174.9	174.7	174.5
105°	225.9	226.4	226.8	227.1	227.1	227.1	227.1	227.1
107.5°	280.8	281.0	281.1	280.7	279.7	278.6	277.6	276.6
110°	318.1	318.1	318.1	317.8	317.1	316.4	315.7	315.1



TEST NUMBER: P331796-840

CATALOG NUMBER: S122RDIW-S485D970U840-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	355.5	355.0	354.4	353.9	353.4	352.8	352.3	351.8
115°	412.7	412.5	412.3	411.8	411.2	410.5	409.8	409.1
117.5°	468.2	467.7	467.1	466.5	465.9	465.1	464.4	463.7
120°	505.3	505.3	505.3	504.9	504.2	503.6	502.9	502.2
122.5°	543.5	542.9	542.4	541.9	541.4	540.9	540.4	539.9
125°	600.1	599.4	598.7	598.2	598.0	597.8	597.5	597.3
127.5°	655.0	654.2	653.4	652.6	651.9	651.2	650.5	649.7
130°	692.6	692.2	691.7	690.9	690.0	689.1	688.2	687.3
132.5°	729.1	728.1	727.1	726.3	725.6	724.8	724.1	723.4
135°	783.0	782.8	782.5	782.1	781.4	780.7	780.1	779.4
137.5°	834.7	834.6	834.4	833.7	832.8	831.9	831.0	830.1
140°	869.4	869.4	869.4	869.0	868.1	867.2	866.3	865.4
142.5°	900.9	901.1	901.2	900.9	900.0	899.1	898.2	897.3
145°	948.7	948.9	949.1	948.8	947.9	947.0	946.0	945.1
147.5°	990.5	991.0	991.5	991.3	990.5	989.6	988.8	987.8
150°	1017.0	1017.7	1018.4	1018.4	1017.7	1017.0	1016.3	1015.7
152.5°	1043.6	1044.5	1045.3	1045.3	1044.5	1043.6	1042.7	1041.9
155°	1077.3	1078.4	1079.5	1079.7	1079.1	1078.4	1077.7	1077.0
157.5°	1108.4	1109.9	1111.5	1111.7	1110.6	1109.5	1108.4	1107.3
160°	1126.8	1128.2	1129.5	1129.8	1128.9	1128.0	1127.1	1126.2
162.5°	1143.6	1145.1	1146.7	1146.9	1145.8	1144.7	1143.6	1142.6
165°	1165.2	1166.7	1168.3	1168.5	1167.4	1166.3	1165.2	1164.0
167.5°	1183.0	1184.6	1186.1	1186.3	1185.2	1184.0	1182.8	1181.6
170°	1192.8	1194.4	1196.0	1196.1	1194.7	1193.4	1191.9	1190.6
172.5°	1200.1	1201.7	1203.3	1203.5	1202.0	1200.7	1199.3	1198.0
175°	1208.1	1209.7	1211.2	1211.4	1210.0	1208.7	1207.3	1206.0
177.5°	1211.8	1212.8	1214.0	1214.0	1212.8	1211.8	1210.7	1209.6
180°	1212.0	1212.0	1212.0	1212.0	1212.0	1212.0	1212.0	1212.0

(END OF REPORT)