

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332118-830

Luminaire Tested: **S123DIW-S340D1535U830-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332118-830
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-5,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123DIW-S340D1535U830-4F0-1E-UDD-F
Description: DEFINE 3 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 340 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 1535 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7118.2 lumens
Efficiency: N/A
Efficacy: 133.3 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 53.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332118-830

CATALOG NUMBER: S123DIW-S340D1535U830-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P332118-830

CATALOG NUMBER: S123DIW-S340D1535U830-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	100	100	100	100	88	88	88	88	66	66	66	46	46	46	27	27	27	19
1	91	87	83	80	80	76	73	71	58	56	54	40	39	38	24	24	23	16
2	83	76	70	65	73	67	62	58	50	47	44	35	33	32	21	20	19	13
3	75	66	59	54	66	59	53	48	44	40	37	31	29	27	19	17	16	11
4	69	58	51	45	60	52	46	41	39	35	32	28	25	23	17	15	14	10
5	63	52	44	39	55	46	40	35	35	30	27	25	22	20	15	13	12	8
6	58	46	39	33	51	41	35	30	31	27	23	22	19	17	14	12	11	7
7	53	42	34	29	47	37	31	26	28	24	20	20	17	15	12	11	9	6
8	49	38	30	25	43	33	27	23	26	21	18	18	15	13	11	10	8	6
9	46	34	27	22	40	30	24	20	23	19	16	17	14	12	10	9	8	5
10	43	31	24	20	37	28	22	18	21	17	14	15	12	10	10	8	7	5

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	5498	5498	5498
5°	5524	5448	5486
10°	5487	5400	5434
15°	5422	5340	5349
20°	5347	5252	5257
25°	5247	5149	5138
30°	5137	5033	4994
35°	5021	4911	4847
40°	4900	4776	4703
45°	4766	4654	4539
50°	4632	4501	4376
55°	4459	4344	4211
60°	4284	4159	4028
65°	4126	3958	3836
70°	3899	3733	3566
75°	3564	3435	3290
80°	3211	3081	3050
85°	2816	2717	2606



TEST NUMBER: P332118-830

CATALOG NUMBER: S123DIW-S340D1535U830-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	48.1	0.7
10°-20°	135.9	1.9
20°-30°	200.7	2.8
30°-40°	234.4	3.3
40°-50°	235.7	3.3
50°-60°	207.0	2.9
60°-70°	154.2	2.2
70°-80°	87.9	1.2
80°-90°	30.5	0.4
90°-100°	69.0	1.0
100°-110°	328.6	4.6
110°-120°	789.4	11.1
120°-130°	1005.2	14.1
130°-140°	1074.1	15.1
140°-150°	1004.4	14.1
150°-160°	810.1	11.4
160°-170°	522.9	7.3
170°-180°	180.2	2.5
0°-30°	384.6	5.4
0°-40°	619.1	8.7
0°-60°	1061.7	14.9
0°-90°	1334.4	18.7
90°-120°	1187.0	16.7
90°-150°	4270.6	60.0
90°-180°	5784.0	81.3
0°-180°	7118.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	511	511	511	511	511	
5°	511	509	504	508	508	48
15°	487	485	479	482	480	137
25°	442	439	434	434	433	203
35°	382	379	374	371	369	239
45°	313	311	306	301	298	242
55°	238	237	232	227	224	213
65°	162	160	155	152	151	160
75°	86	84	83	80	79	92
85°	23	22	22	21	21	25
90°	1	16	34	39	42	5
95°	86	32	44	53	54	106
105°	420	428	309	73	62	445
115°	788	796	809	822	829	777
125°	1110	1121	1127	1130	1133	991
135°	1382	1391	1396	1400	1396	1064
145°	1595	1604	1608	1610	1611	998
155°	1757	1754	1756	1762	1754	809
165°	1853	1849	1847	1857	1849	523
175°	1897	1890	1891	1900	1890	180
180°	1897	1897	1897	1897	1897	



TEST NUMBER: P332118-830

CATALOG NUMBER: S123DIW-S340D1535U830-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	510.8	510.8	510.8	510.8	510.8	510.8	510.8	510.8	510.8	510.8	510.8
2.5°	512.6	512.2	511.9	511.6	511.2	510.7	509.8	509.0	508.1	507.3	508.0
5°	511.2	510.7	510.2	509.7	509.3	508.5	507.4	506.3	505.2	504.2	505.1
7.5°	506.2	505.7	505.2	504.7	504.3	503.4	502.4	501.2	500.1	499.0	499.8
10°	502.0	501.5	501.0	500.5	500.0	499.2	497.9	496.6	495.3	494.1	494.9
12.5°	496.3	496.0	495.5	495.1	494.7	493.9	492.8	491.5	490.3	489.2	489.8
15°	486.6	486.3	485.8	485.4	485.0	484.2	483.0	481.6	480.4	479.2	479.9
17.5°	475.2	474.8	474.3	473.7	473.3	472.4	471.1	469.9	468.5	467.3	467.8
20°	466.8	466.3	465.7	465.1	464.5	463.5	462.3	461.0	459.8	458.5	458.9
22.5°	457.3	456.8	456.2	455.6	455.1	454.1	452.8	451.6	450.3	449.0	449.3
25°	441.8	441.2	440.6	440.1	439.5	438.6	437.2	436.0	434.7	433.5	433.6
27.5°	425.2	424.6	424.0	423.5	422.9	422.0	420.7	419.2	417.9	416.5	416.6
30°	413.3	412.7	412.3	411.8	411.3	410.4	409.1	407.6	406.3	404.9	404.9
32.5°	401.3	400.7	400.0	399.4	398.8	397.8	396.8	395.8	394.7	393.7	393.1
35°	382.1	381.5	380.9	380.3	379.8	378.8	377.6	376.3	375.0	373.7	373.2
37.5°	362.4	361.7	360.9	360.1	359.5	358.4	357.1	355.8	354.6	353.3	352.6
40°	348.7	348.1	347.5	346.9	346.4	345.3	344.0	342.6	341.3	339.9	339.1
42.5°	335.0	334.3	333.7	333.0	332.3	331.3	330.0	328.6	327.3	325.8	325.1
45°	313.1	312.7	312.4	312.0	311.6	310.8	309.4	308.2	306.9	305.7	304.5
47.5°	291.4	290.9	290.3	289.7	289.2	288.3	287.1	285.9	284.7	283.5	282.4
50°	276.6	276.2	275.7	275.2	274.8	273.8	272.6	271.4	270.0	268.8	267.7
52.5°	261.2	260.9	260.5	260.2	259.9	259.0	257.7	256.4	255.1	253.6	252.8
55°	237.6	237.5	237.4	237.3	237.2	236.5	235.3	233.9	232.7	231.5	230.4
57.5°	215.1	214.8	214.4	214.1	213.8	213.1	212.1	211.0	210.1	209.1	208.1
60°	199.0	198.9	198.8	198.7	198.6	197.9	196.7	195.6	194.4	193.2	192.4
62.5°	184.5	184.3	184.1	183.8	183.5	182.9	181.6	180.5	179.3	178.1	177.3
65°	162.0	161.6	161.1	160.6	160.1	159.4	158.4	157.4	156.5	155.4	154.7
67.5°	138.3	137.8	137.4	137.0	136.6	135.9	135.3	134.5	133.7	133.0	132.3
70°	123.9	123.3	122.7	122.1	121.5	120.9	120.4	119.7	119.1	118.6	117.9
72.5°	108.8	108.3	107.9	107.4	107.0	106.5	105.8	105.2	104.5	103.9	103.2
75°	85.7	85.2	84.8	84.5	84.1	83.7	83.4	83.1	82.8	82.6	82.1
77.5°	65.1	64.9	64.8	64.6	64.3	64.0	63.7	63.3	63.0	62.6	62.3
80°	51.8	51.6	51.3	51.0	50.6	50.4	50.2	50.0	49.9	49.7	49.5
82.5°	38.8	38.7	38.7	38.6	38.5	38.5	38.5	38.5	38.5	38.4	38.2
85°	22.8	22.6	22.4	22.2	22.1	22.0	22.0	22.0	22.0	22.0	21.8
87.5°	9.4	9.8	10.2	10.6	11.0	11.6	12.3	13.0	13.8	14.5	14.7
90°	1.4	4.5	7.6	10.8	13.9	17.5	21.6	25.6	29.8	33.8	35.1
92.5°	26.2	25.4	24.4	23.6	22.7	23.8	26.9	30.0	33.0	36.1	38.1
95°	86.0	73.1	60.3	47.4	34.6	29.9	33.4	36.8	40.2	43.6	45.9
97.5°	172.8	167.0	161.3	155.4	149.7	135.5	113.0	90.5	68.0	45.3	47.9
100°	238.2	244.4	250.6	256.9	263.2	241.9	193.0	144.2	95.4	46.5	49.0
102.5°	312.5	317.1	321.6	326.0	330.5	306.1	252.8	199.4	146.1	92.7	84.9
105°	419.9	423.4	426.8	430.3	433.7	421.3	393.1	365.0	336.8	308.6	253.2
107.5°	533.2	535.9	538.7	541.5	544.2	547.8	552.2	556.8	561.2	565.6	525.0
110°	608.7	611.2	613.7	616.2	618.8	621.7	625.2	628.6	632.1	635.5	625.2



TEST NUMBER: P332118-830

CATALOG NUMBER: S123DIW-S340D1535U830-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	680.9	683.2	685.4	687.7	689.8	692.8	696.2	699.6	703.0	706.5	706.7
115°	787.7	789.6	791.5	793.3	795.2	797.6	800.4	803.1	806.0	808.8	811.9
117.5°	891.1	893.4	895.7	898.1	900.4	902.3	903.7	905.1	906.5	908.0	910.5
120°	955.4	958.2	961.0	963.8	966.7	968.6	969.4	970.3	971.3	972.2	974.8
122.5°	1020.8	1023.0	1025.4	1027.7	1030.0	1031.8	1032.9	1034.2	1035.3	1036.5	1038.3
125°	1110.3	1112.9	1115.4	1117.9	1120.4	1122.3	1123.5	1124.7	1126.1	1127.3	1127.9
127.5°	1197.1	1199.7	1202.2	1204.7	1207.2	1209.2	1210.7	1212.2	1213.7	1215.2	1216.2
130°	1251.2	1253.8	1256.3	1258.8	1261.3	1263.2	1264.4	1265.6	1267.0	1268.2	1269.4
132.5°	1303.2	1305.6	1308.2	1310.6	1313.2	1314.9	1315.9	1316.9	1317.9	1318.9	1320.1
135°	1382.3	1384.2	1386.1	1388.0	1389.9	1391.4	1392.6	1393.9	1395.2	1396.4	1397.3
137.5°	1449.9	1452.4	1454.7	1457.1	1459.4	1461.0	1461.7	1462.4	1463.1	1463.8	1465.3
140°	1495.1	1496.9	1498.8	1500.7	1502.6	1503.9	1504.9	1505.8	1506.7	1507.7	1509.0
142.5°	1536.7	1538.6	1540.5	1542.4	1544.3	1545.7	1546.6	1547.6	1548.5	1549.4	1550.4
145°	1595.1	1597.2	1599.5	1601.7	1603.8	1605.2	1605.9	1606.5	1607.1	1607.8	1608.4
147.5°	1650.0	1651.5	1652.9	1654.4	1655.8	1656.8	1657.5	1658.1	1658.7	1659.3	1660.0
150°	1683.9	1684.8	1685.7	1686.7	1687.6	1688.4	1689.0	1689.7	1690.3	1690.9	1691.5
152.5°	1714.3	1714.8	1715.1	1715.6	1716.1	1716.5	1716.8	1717.2	1717.6	1718.0	1719.1
155°	1757.1	1756.5	1755.9	1755.3	1754.6	1754.4	1754.8	1755.1	1755.4	1755.7	1757.3
157.5°	1790.4	1790.4	1790.3	1790.2	1790.2	1790.0	1789.6	1789.3	1789.0	1788.7	1790.5
160°	1810.7	1810.3	1810.1	1809.8	1809.4	1809.1	1808.8	1808.5	1808.2	1807.9	1809.8
162.5°	1829.9	1829.0	1828.2	1827.4	1826.6	1826.0	1825.7	1825.4	1825.0	1824.8	1826.9
165°	1852.9	1852.0	1851.1	1850.1	1849.2	1848.6	1848.2	1847.9	1847.7	1847.3	1849.8
167.5°	1870.9	1869.7	1868.5	1867.3	1866.0	1865.4	1865.4	1865.4	1865.4	1865.4	1867.8
170°	1881.1	1879.9	1878.6	1877.4	1876.1	1875.5	1875.5	1875.5	1875.5	1875.5	1878.0
172.5°	1887.9	1886.4	1884.9	1883.4	1881.9	1881.2	1881.5	1881.8	1882.0	1882.3	1884.8
175°	1896.6	1895.1	1893.5	1892.0	1890.4	1889.7	1890.1	1890.4	1890.6	1891.0	1893.2
177.5°	1898.8	1897.6	1896.4	1895.2	1893.9	1893.4	1893.7	1893.9	1894.1	1894.4	1896.4
180°	1896.6	1896.6	1896.6	1896.6	1896.6	1896.6	1896.6	1896.6	1896.6	1896.6	1896.6



TEST NUMBER: P332118-830

CATALOG NUMBER: S123DIW-S340D1535U830-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	510.8	510.8	510.8	510.8	510.8	510.8	510.8	510.8
2.5°	508.8	509.6	510.4	510.8	510.7	510.6	510.5	510.4
5°	506.1	507.1	508.1	508.5	508.3	508.1	507.8	507.7
7.5°	500.8	501.6	502.5	502.8	502.8	502.7	502.6	502.4
10°	495.9	496.7	497.6	497.9	497.8	497.6	497.4	497.2
12.5°	490.4	491.1	491.7	492.0	491.9	491.7	491.6	491.5
15°	480.7	481.5	482.3	482.4	481.7	481.2	480.6	480.0
17.5°	468.3	468.9	469.5	469.7	469.4	469.2	469.0	468.8
20°	459.3	459.7	460.1	460.1	459.8	459.5	459.2	458.9
22.5°	449.6	450.0	450.3	450.3	449.9	449.5	449.1	448.7
25°	433.7	433.8	433.9	433.8	433.5	433.2	432.9	432.6
27.5°	416.7	416.8	416.8	416.7	416.3	415.9	415.6	415.2
30°	404.9	404.9	404.9	404.5	403.9	403.2	402.6	401.8
32.5°	392.6	392.0	391.5	391.1	390.7	390.3	389.9	389.6
35°	372.6	372.0	371.4	370.9	370.4	369.9	369.4	368.9
37.5°	351.9	351.2	350.4	350.0	349.7	349.3	349.0	348.7
40°	338.4	337.6	336.8	336.2	335.8	335.5	335.1	334.7
42.5°	324.3	323.5	322.7	322.2	321.8	321.4	321.0	320.6
45°	303.3	302.2	301.0	300.2	299.6	299.2	298.7	298.2
47.5°	281.3	280.1	278.9	278.1	277.7	277.3	276.8	276.4
50°	266.6	265.5	264.5	263.6	263.1	262.5	261.9	261.3
52.5°	251.8	250.9	250.0	249.2	248.6	248.1	247.5	246.9
55°	229.3	228.2	227.2	226.4	225.9	225.4	224.9	224.4
57.5°	207.2	206.1	205.2	204.4	203.9	203.3	202.7	202.2
60°	191.5	190.6	189.7	189.1	188.5	188.0	187.6	187.1
62.5°	176.3	175.5	174.7	174.0	173.7	173.3	173.1	172.7
65°	153.9	153.2	152.3	151.8	151.6	151.2	150.9	150.6
67.5°	131.6	130.9	130.3	129.7	129.3	128.8	128.5	128.1
70°	117.3	116.5	115.8	115.3	114.8	114.3	113.8	113.3
72.5°	102.6	102.0	101.4	100.9	100.8	100.5	100.2	99.9
75°	81.6	81.1	80.6	80.2	79.9	79.6	79.4	79.1
77.5°	61.9	61.6	61.3	61.2	61.2	61.2	61.2	61.2
80°	49.4	49.3	49.2	49.2	49.2	49.2	49.2	49.2
82.5°	38.1	37.9	37.7	37.5	37.5	37.4	37.3	37.2
85°	21.6	21.4	21.2	21.1	21.1	21.1	21.1	21.1
87.5°	14.8	15.0	15.2	15.4	15.5	15.6	15.7	15.8
90°	36.3	37.6	38.8	39.8	40.4	41.0	41.7	42.2
92.5°	40.1	42.1	44.1	45.2	45.6	46.0	46.4	46.8
95°	48.1	50.2	52.4	53.5	53.5	53.5	53.5	53.5
97.5°	50.4	52.9	55.4	56.8	57.1	57.4	57.8	58.1
100°	51.5	54.0	56.6	58.0	58.2	58.5	58.9	59.2
102.5°	77.2	69.5	61.6	58.1	58.6	59.2	59.8	60.3
105°	197.7	142.3	86.9	59.5	60.1	60.8	61.4	62.0
107.5°	484.3	443.7	403.0	361.8	320.1	278.2	236.5	194.7
110°	614.8	604.5	594.2	566.6	521.8	477.0	432.3	387.5



TEST NUMBER: P332118-830

CATALOG NUMBER: S123DIW-S340D1535U830-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	706.9	707.1	707.3	702.7	693.1	683.7	674.3	664.8
115°	815.1	818.2	821.3	823.5	824.8	826.0	827.3	828.6
117.5°	913.0	915.5	918.0	919.5	919.6	919.9	920.2	920.4
120°	977.3	979.8	982.3	983.5	983.5	983.5	983.5	983.5
122.5°	1040.0	1041.8	1043.6	1044.5	1044.8	1045.0	1045.3	1045.6
125°	1128.5	1129.2	1129.7	1130.4	1131.1	1131.6	1132.3	1132.9
127.5°	1217.2	1218.2	1219.2	1219.4	1218.8	1218.1	1217.5	1216.9
130°	1270.6	1272.0	1273.2	1273.5	1272.9	1272.2	1271.6	1271.0
132.5°	1321.4	1322.7	1323.9	1324.1	1323.2	1322.4	1321.4	1320.6
135°	1398.3	1399.2	1400.1	1400.1	1399.2	1398.3	1397.3	1396.4
137.5°	1466.8	1468.3	1469.8	1470.2	1469.6	1469.0	1468.3	1467.7
140°	1510.2	1511.5	1512.7	1513.1	1512.4	1511.8	1511.2	1510.5
142.5°	1551.4	1552.5	1553.4	1553.5	1552.7	1551.7	1550.9	1550.0
145°	1609.0	1609.7	1610.2	1610.6	1610.6	1610.6	1610.6	1610.6
147.5°	1660.6	1661.2	1661.9	1661.4	1660.0	1658.6	1657.1	1655.7
150°	1692.1	1692.8	1693.4	1693.3	1692.3	1691.4	1690.5	1689.5
152.5°	1720.2	1721.4	1722.5	1722.3	1720.9	1719.4	1718.0	1716.6
155°	1758.9	1760.4	1762.0	1761.8	1759.9	1758.0	1756.1	1754.4
157.5°	1792.4	1794.3	1796.2	1795.9	1793.5	1791.0	1788.6	1786.1
160°	1811.7	1813.5	1815.3	1815.2	1813.0	1810.8	1808.6	1806.5
162.5°	1829.0	1831.2	1833.2	1833.3	1831.5	1829.5	1827.6	1825.6
165°	1852.3	1854.8	1857.4	1857.5	1855.3	1853.1	1850.9	1848.7
167.5°	1870.4	1872.8	1875.4	1875.4	1872.8	1870.4	1867.8	1865.4
170°	1880.5	1883.0	1885.6	1885.6	1883.0	1880.5	1878.0	1875.5
172.5°	1887.3	1889.8	1892.2	1892.2	1889.4	1886.7	1883.9	1881.1
175°	1895.4	1897.5	1899.8	1899.6	1897.1	1894.6	1892.1	1889.6
177.5°	1898.4	1900.4	1902.4	1902.1	1899.6	1897.1	1894.6	1892.2
180°	1896.6	1896.6	1896.6	1896.6	1896.6	1896.6	1896.6	1896.6

(END OF REPORT)